

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331789-840

Luminaire Tested: **S122RDIW-S485D710U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331789-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D710U840-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4741.3 lumens
Efficiency: N/A
Efficacy: 126.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331789-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331789-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	40	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	36	35	30
3	81	72	65	60	73	66	60	55	54	50	47	44	41	39	34	32	31	26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	23	22	18
7	58	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19	17
8	54	43	35	30	50	39	33	28	33	28	25	28	24	21	22	20	18	15
9	51	39	32	27	46	36	30	26	31	26	22	25	22	19	21	18	16	14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17525	17525	17525	17525
5°	19571	17634	15635	17634
10°	21713	17510	13554	17510
15°	22781	17254	10678	17254
20°	19749	16873	9241	16873
25°	12953	16352	8250	16352
30°	8720	15720	7467	15720
35°	7062	14927	6733	14927
40°	6279	14060	6232	14060
45°	5683	13047	5562	13047
50°	5172	12039	5152	12039
55°	4861	10925	4799	10925
60°	4066	9901	4017	9901
65°	3431	8989	3889	8989
70°	3172	8030	3668	8030
75°	2969	6987	3387	6987
80°	2734	5746	3013	5746
85°	2501	4539	2649	4539



TEST NUMBER: P331789-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.9	2.2
10°-20°	286.7	6.0
20°-30°	369.4	7.8
30°-40°	351.1	7.4
40°-50°	300.7	6.3
50°-60°	229.0	4.8
60°-70°	144.8	3.1
70°-80°	72.3	1.5
80°-90°	21.2	0.4
90°-100°	32.6	0.7
100°-110°	119.5	2.5
110°-120°	319.5	6.7
120°-130°	527.3	11.1
130°-140°	560.8	11.8
140°-150°	521.3	11.0
150°-160°	419.1	8.8
160°-170°	270.1	5.7
170°-180°	93.0	2.0
0°-30°	759.0	16.0
0°-40°	1110.1	23.4
0°-60°	1639.8	34.6
0°-90°	1878.1	39.6
90°-120°	471.6	9.9
90°-150°	2081.0	43.9
90°-180°	2863.0	60.4
0°-180°	4741.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1085	1085	1085	1085	1085	
5°	1208	1088	965	1088	1208	119
15°	1363	1032	639	1032	1363	368
25°	727	918	463	918	727	345
35°	358	757	342	757	358	229
45°	249	571	244	571	249	193
55°	173	388	170	388	173	152
65°	90	235	102	235	90	91
75°	48	112	54	112	48	50
85°	14	24	14	24	14	15
90°	19	1	19	1	19	9
95°	30	46	30	46	30	28
105°	54	215	54	215	54	56
115°	58	406	58	406	58	145
125°	604	575	604	575	604	523
135°	735	711	735	711	735	566
145°	838	825	838	825	838	524
155°	909	908	909	908	909	419
165°	955	957	955	957	955	270
175°	974	979	974	979	974	93
180°	977	977	977	977	977	



TEST NUMBER: P331789-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1129.4	1130.3	1131.3	1129.1	1129.1	1127.3	1123.4	1120.3	1111.9	1110.6	1110.6
5°	1207.5	1206.8	1208.3	1203.4	1196.6	1195.1	1187.9	1178.5	1168.7	1157.7	1155.5
7.5°	1285.3	1284.1	1281.1	1280.2	1275.1	1263.6	1252.1	1239.8	1223.6	1207.6	1199.6
10°	1324.4	1336.9	1329.4	1316.2	1318.8	1301.1	1291.6	1275.5	1261.8	1238.1	1232.8
12.5°	1363.0	1368.0	1365.5	1358.1	1354.7	1342.4	1329.7	1315.6	1290.5	1269.2	1250.6
15°	1362.9	1370.1	1372.0	1369.7	1371.6	1370.8	1364.0	1352.3	1330.5	1307.1	1286.8
17.5°	1262.3	1267.3	1279.6	1288.0	1298.6	1320.9	1331.9	1336.3	1332.9	1319.6	1305.3
20°	1149.4	1141.1	1175.9	1193.6	1208.7	1246.4	1278.8	1291.2	1311.2	1310.9	1307.1
22.5°	989.6	991.5	1024.4	1045.4	1089.5	1127.2	1164.2	1211.0	1249.7	1275.3	1290.2
25°	727.1	741.4	774.3	802.8	851.9	922.1	985.8	1059.8	1129.4	1184.6	1237.0
27.5°	546.0	547.1	573.1	599.7	628.7	686.2	766.5	854.7	954.2	1036.2	1130.6
30°	467.7	465.3	476.4	492.5	517.5	561.9	622.3	709.0	808.2	931.9	1042.0
32.5°	412.1	412.2	420.5	432.5	453.1	483.1	524.5	594.9	688.7	810.3	939.4
35°	358.3	357.9	364.0	372.6	381.2	400.5	428.8	465.7	530.3	643.8	775.8
37.5°	319.6	321.3	324.3	329.7	339.2	349.9	367.0	391.7	437.7	504.8	615.7
40°	297.9	298.7	302.9	307.4	313.1	321.3	335.3	355.3	388.8	442.3	523.4
42.5°	278.0	278.7	281.8	285.9	290.3	298.7	310.2	327.5	354.8	396.5	463.4
45°	248.9	248.9	251.6	253.4	258.3	265.9	275.3	289.6	308.5	339.4	384.0
47.5°	221.6	221.7	223.4	226.6	229.7	235.6	244.9	256.6	270.3	294.3	332.2
50°	205.9	206.3	207.4	210.1	212.0	217.2	224.4	234.6	248.9	267.4	299.0
52.5°	193.2	193.0	194.4	195.6	196.8	200.7	206.0	215.0	227.8	243.9	270.1
55°	172.7	171.2	173.5	175.3	176.5	178.0	181.0	186.7	197.6	211.2	230.8
57.5°	147.0	146.4	148.0	149.8	153.3	157.4	160.0	163.6	169.3	178.9	198.4
60°	125.9	125.9	129.4	130.5	134.6	139.9	145.2	148.2	153.9	160.3	174.6
62.5°	107.2	107.6	109.2	110.3	112.6	119.1	126.5	133.1	138.5	144.6	154.1
65°	89.8	90.5	90.5	91.3	92.8	94.3	97.3	102.6	112.0	120.7	127.8
67.5°	76.1	76.4	76.6	77.4	77.8	79.4	80.6	83.0	85.1	93.4	102.3
70°	67.2	68.3	67.9	68.7	69.0	69.8	71.3	72.4	75.8	77.7	83.0
72.5°	58.7	59.5	59.5	59.9	60.9	61.0	62.2	63.3	65.5	67.2	70.0
75°	47.6	47.2	47.6	48.3	48.7	49.0	49.0	50.5	51.7	53.2	55.0
77.5°	36.7	37.1	37.0	37.1	37.1	37.8	37.7	38.4	39.5	40.3	41.2
80°	29.4	29.8	29.4	29.8	30.2	30.5	30.2	30.5	31.7	32.4	32.4
82.5°	22.8	22.8	23.1	23.1	23.2	23.3	23.8	23.9	24.7	24.5	24.8
85°	13.5	13.2	13.2	13.2	13.5	13.9	13.5	13.5	13.9	13.9	13.9
87.5°	8.7	8.9	8.8	8.8	8.7	8.6	8.4	8.6	8.1	8.3	7.7
90°	19.1	18.8	18.5	18.2	17.9	17.3	16.5	15.8	14.9	14.1	12.9
92.5°	19.1	18.9	18.7	18.5	18.4	18.1	17.7	17.3	16.8	16.4	15.8
95°	30.4	30.6	30.7	30.9	31.0	30.7	29.9	29.2	28.4	27.6	26.5
97.5°	40.6	40.4	40.2	40.0	39.8	39.4	38.8	38.2	37.6	36.9	34.3
100°	47.4	47.1	46.8	46.5	46.2	45.3	44.0	42.8	41.5	40.3	37.7
102.5°	50.8	50.3	49.9	49.5	49.0	48.0	46.4	44.7	43.0	41.4	63.7
105°	53.7	53.1	52.5	51.8	51.2	50.0	48.3	46.6	44.8	43.1	86.0
107.5°	55.2	54.6	54.0	53.4	52.8	53.3	55.1	56.9	58.6	60.4	111.8
110°	55.8	55.2	54.6	53.9	53.3	60.9	76.5	92.3	108.1	123.7	169.2



TEST NUMBER: P331789-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	56.5	55.9	55.4	54.9	54.4	82.8	140.2	197.4	254.8	312.0	323.3
115°	58.0	69.3	80.6	91.9	103.2	145.2	217.9	290.7	363.5	436.2	432.2
117.5°	236.7	273.9	311.0	348.2	385.4	412.7	430.3	448.0	465.5	483.1	480.4
120°	431.2	452.4	473.6	494.8	516.0	525.7	523.8	522.0	520.1	518.2	515.3
122.5°	538.2	542.3	546.3	550.5	554.6	556.1	554.9	553.8	552.7	551.6	548.5
125°	604.4	604.0	603.5	603.0	602.6	601.8	600.7	599.6	598.4	597.3	594.4
127.5°	646.3	646.2	646.1	646.0	645.9	645.1	643.5	641.9	640.3	638.6	636.4
130°	672.4	672.5	672.7	672.8	673.0	672.2	670.4	668.7	667.0	665.3	663.5
132.5°	697.8	697.9	698.1	698.2	698.4	697.7	696.3	694.8	693.3	691.9	690.1
135°	734.6	734.9	735.2	735.5	735.8	735.2	733.6	732.1	730.4	728.9	727.5
137.5°	768.0	768.6	769.1	769.6	770.2	769.7	768.1	766.6	765.1	763.6	761.9
140°	789.0	789.7	790.5	791.3	792.1	791.8	790.4	789.0	787.6	786.2	784.4
142.5°	809.3	810.1	810.9	811.7	812.4	812.2	810.9	809.6	808.4	807.1	805.1
145°	837.8	838.5	839.3	840.1	840.9	840.7	839.6	838.5	837.5	836.4	833.6
147.5°	862.7	863.4	864.1	864.7	865.5	865.4	864.5	863.7	862.9	862.0	859.4
150°	878.1	878.8	879.6	880.4	881.2	881.1	880.2	879.2	878.3	877.4	874.8
152.5°	891.0	892.1	893.1	894.1	895.2	895.2	894.3	893.3	892.4	891.5	889.1
155°	909.2	910.4	911.7	912.9	914.1	914.3	913.4	912.4	911.5	910.6	908.7
157.5°	925.6	927.0	928.2	929.4	930.6	930.7	929.6	928.6	927.5	926.3	925.0
160°	935.3	936.4	937.5	938.6	939.7	939.8	938.9	937.9	937.0	936.0	935.0
162.5°	943.2	944.5	945.9	947.3	948.7	948.8	947.7	946.6	945.5	944.5	943.7
165°	955.1	956.2	957.4	958.4	959.5	959.5	958.4	957.4	956.2	955.1	954.6
167.5°	962.6	964.0	965.4	966.8	968.3	968.4	967.3	966.2	965.1	964.0	963.6
170°	967.1	968.6	970.0	971.4	972.8	972.9	971.8	970.8	969.7	968.6	968.3
172.5°	970.5	971.9	973.3	974.7	976.1	976.3	975.2	974.1	973.0	971.9	971.6
175°	973.5	975.0	976.6	978.2	979.8	980.0	978.9	977.9	976.7	975.6	975.3
177.5°	975.3	976.4	977.5	978.8	979.9	980.0	979.1	978.3	977.3	976.4	976.3
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331789-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1111.3	1108.9	1106.8	1101.4	1098.6	1092.6	1091.7	1091.4	1083.6	1076.0	1073.9
5°	1149.4	1143.5	1134.4	1123.8	1112.9	1101.6	1094.0	1088.0	1072.9	1058.5	1050.3
7.5°	1187.9	1175.0	1159.3	1139.3	1122.7	1104.0	1090.1	1077.6	1056.2	1035.7	1021.9
10°	1216.6	1195.5	1174.8	1147.2	1125.7	1104.6	1085.0	1068.0	1043.9	1016.7	997.4
12.5°	1234.4	1211.1	1182.6	1155.7	1127.8	1101.0	1074.7	1052.9	1024.6	996.5	973.6
15°	1258.5	1233.6	1198.9	1160.4	1124.6	1089.5	1059.3	1032.2	995.2	961.7	933.7
17.5°	1278.2	1243.9	1206.6	1162.2	1120.6	1076.1	1037.2	1002.5	961.4	920.9	888.1
20°	1284.4	1250.5	1207.5	1163.1	1114.0	1061.6	1019.8	982.0	937.9	893.7	856.1
22.5°	1280.5	1254.2	1206.3	1153.1	1102.9	1048.0	1000.8	956.9	908.1	863.0	819.3
25°	1253.9	1244.9	1199.6	1141.6	1084.2	1020.5	965.8	917.9	862.1	813.9	766.3
27.5°	1191.8	1211.4	1183.4	1121.5	1057.7	989.4	928.0	873.4	815.5	761.1	713.8
30°	1132.2	1177.0	1164.9	1107.6	1036.3	969.2	900.2	843.2	781.4	725.6	678.8
32.5°	1050.4	1124.5	1136.3	1088.3	1014.6	940.8	868.5	811.8	747.3	688.4	642.9
35°	920.2	1031.1	1082.0	1051.4	977.4	898.0	823.2	757.3	692.4	634.3	589.1
37.5°	764.9	915.8	1000.8	1002.9	935.0	852.3	771.0	705.5	639.0	582.1	533.1
40°	664.1	827.8	938.3	962.8	905.4	816.1	733.9	667.1	602.3	546.4	490.3
42.5°	573.6	736.7	872.5	915.1	869.6	780.8	698.3	628.5	565.4	512.6	455.2
45°	463.8	606.4	756.1	832.3	807.1	724.8	637.7	571.4	512.1	466.5	411.4
47.5°	391.3	491.8	636.6	739.7	739.2	664.2	578.6	514.9	460.0	417.3	372.6
50°	349.9	437.5	560.1	676.9	686.7	623.8	542.3	479.3	428.1	383.1	347.3
52.5°	312.9	385.0	495.1	607.2	635.1	580.6	501.6	443.4	393.6	352.3	321.6
55°	264.4	320.1	403.9	508.8	551.0	512.5	442.3	388.1	347.7	313.1	286.6
57.5°	223.6	265.5	332.6	417.1	466.3	442.0	384.3	340.1	305.6	274.2	253.4
60°	198.0	232.3	289.2	359.8	414.0	397.1	347.7	306.6	277.2	250.0	230.5
62.5°	173.9	203.4	252.2	309.4	359.2	352.1	311.8	277.3	251.6	226.8	210.3
65°	139.9	161.4	199.4	244.4	284.4	287.7	258.7	235.3	212.3	192.7	178.0
67.5°	111.4	125.4	152.3	190.1	220.0	230.8	213.0	195.1	176.8	161.7	149.0
70°	93.9	105.2	124.8	155.4	182.9	194.2	184.0	170.1	154.2	141.8	130.9
72.5°	76.1	87.2	101.6	124.0	147.6	159.9	156.3	146.2	133.4	123.1	112.8
75°	57.4	60.7	70.5	85.6	104.1	114.6	117.2	112.0	101.8	93.9	87.9
77.5°	42.4	44.4	49.1	57.1	69.1	78.5	82.4	81.8	74.7	70.2	64.5
80°	33.9	35.0	37.4	40.7	49.8	59.2	61.8	61.8	57.0	55.0	49.4
82.5°	25.8	26.7	28.0	29.9	34.1	42.3	45.2	45.8	42.7	40.3	35.9
85°	14.7	14.3	15.0	16.3	17.0	19.2	23.7	24.5	23.7	20.7	19.6
87.5°	7.5	7.5	7.3	6.7	6.6	6.6	7.8	8.9	8.1	7.5	7.2
90°	11.6	10.4	9.1	7.6	5.9	4.1	2.4	0.7	2.4	4.1	5.9
92.5°	15.1	14.5	13.9	13.6	13.8	13.9	14.1	14.2	14.1	13.9	13.8
95°	25.3	24.2	23.1	25.2	30.4	35.5	40.8	45.9	40.8	35.5	30.4
97.5°	31.8	29.3	26.8	32.7	47.4	62.0	76.5	91.2	76.5	62.0	47.4
100°	34.9	32.3	29.6	39.1	60.6	82.1	103.6	125.1	103.6	82.1	60.6
102.5°	86.1	108.5	130.8	144.2	148.8	153.3	157.9	162.5	157.9	153.3	148.8
105°	128.9	171.8	214.7	233.8	229.0	224.4	219.6	214.9	219.6	224.4	229.0
107.5°	163.3	214.7	266.1	289.9	286.1	282.4	278.5	274.7	278.5	282.4	286.1
110°	214.5	259.9	305.3	326.4	323.1	319.8	316.5	313.2	316.5	319.8	323.1



TEST NUMBER: P331789-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	334.5	345.7	356.9	361.0	358.1	355.3	352.3	349.4	352.3	355.3	358.1
115°	428.4	424.4	420.5	417.2	414.5	411.8	409.2	406.5	409.2	411.8	414.5
117.5°	477.8	475.0	472.3	469.5	466.5	463.5	460.5	457.6	460.5	463.5	466.5
120°	512.5	509.7	506.9	504.3	501.9	499.6	497.3	494.8	497.3	499.6	501.9
122.5°	545.4	542.3	539.3	536.4	534.0	531.5	529.1	526.5	529.1	531.5	534.0
125°	591.4	588.4	585.4	582.9	580.9	578.9	576.8	574.7	576.8	578.9	580.9
127.5°	634.2	632.0	629.8	627.5	625.2	623.0	620.7	618.4	620.7	623.0	625.2
130°	661.8	660.0	658.3	656.2	653.7	651.2	648.6	646.1	648.6	651.2	653.7
132.5°	688.3	686.6	684.9	683.0	680.9	678.7	676.6	674.5	676.6	678.7	680.9
135°	726.1	724.7	723.3	721.2	718.7	716.2	713.7	711.2	713.7	716.2	718.7
137.5°	760.3	758.7	757.1	755.4	753.7	751.9	750.1	748.4	750.1	751.9	753.7
140°	782.6	780.9	779.2	777.7	776.5	775.2	774.0	772.7	774.0	775.2	776.5
142.5°	803.1	801.1	799.1	797.6	796.5	795.4	794.2	793.0	794.2	795.4	796.5
145°	831.0	828.3	825.7	824.4	824.6	824.8	824.9	825.1	824.9	824.8	824.6
147.5°	856.8	854.1	851.5	850.5	851.1	851.7	852.3	852.8	852.3	851.7	851.1
150°	872.3	869.8	867.3	866.6	867.7	868.8	869.9	871.0	869.9	868.8	867.7
152.5°	886.7	884.3	881.9	881.3	882.5	883.8	885.0	886.3	885.0	883.8	882.5
155°	906.8	904.9	903.0	902.8	904.2	905.6	907.1	908.5	907.1	905.6	904.2
157.5°	923.7	922.4	921.1	921.1	922.2	923.4	924.6	925.8	924.6	923.4	922.2
160°	934.1	933.2	932.2	932.2	933.2	934.1	935.0	936.0	935.0	934.1	933.2
162.5°	942.9	942.0	941.2	941.3	942.2	943.2	944.1	945.0	944.1	943.2	942.2
165°	954.1	953.7	953.2	953.4	954.4	955.3	956.2	957.3	956.2	955.3	954.4
167.5°	963.1	962.7	962.3	962.5	963.4	964.4	965.3	966.2	965.3	964.4	963.4
170°	968.0	967.6	967.2	967.6	968.6	969.5	970.4	971.4	970.4	969.5	968.6
172.5°	971.3	971.0	970.7	971.0	971.9	972.9	973.8	974.7	973.8	972.9	971.9
175°	975.0	974.6	974.3	974.7	975.8	976.9	978.1	979.2	978.1	976.9	975.8
177.5°	976.2	976.0	975.9	976.3	977.2	978.1	979.0	979.9	979.0	978.1	977.2
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331789-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1070.0	1067.8	1063.9	1057.9	1054.3	1047.9	1043.7	1046.1	1046.7	1046.1	1045.5
5°	1041.3	1033.3	1022.4	1011.8	1002.0	991.5	985.4	982.8	977.4	974.5	973.0
7.5°	1006.4	992.8	977.3	959.0	943.3	927.0	918.6	914.4	903.6	897.8	892.6
10°	980.5	959.0	943.5	919.4	904.7	883.2	868.5	868.9	854.1	845.9	839.8
12.5°	951.9	928.3	902.5	880.8	860.4	843.1	825.4	818.2	802.5	794.6	778.3
15°	904.3	876.8	849.7	820.2	799.5	772.7	747.1	715.8	690.5	668.6	662.6
17.5°	852.4	818.4	791.1	756.6	721.0	676.0	646.3	628.1	612.9	601.4	592.8
20°	816.9	782.1	753.2	701.0	653.2	622.6	600.8	586.8	571.0	558.6	551.7
22.5°	779.4	743.3	703.7	645.5	608.2	583.7	564.2	548.2	537.5	527.8	521.6
25°	726.3	686.7	621.5	581.5	551.4	525.7	512.1	502.3	491.0	477.8	471.8
27.5°	670.2	607.2	560.4	530.7	501.9	485.2	473.0	458.4	448.3	442.3	436.1
30°	628.2	565.3	528.8	496.2	475.9	457.5	443.1	434.8	425.1	414.9	410.7
32.5°	581.5	531.2	496.1	469.2	448.5	432.7	421.4	408.0	400.9	394.7	386.0
35°	523.4	485.3	453.3	431.4	411.8	399.0	385.8	377.9	365.1	359.8	356.4
37.5°	474.2	441.2	417.3	394.3	378.7	364.6	356.5	343.9	338.3	330.9	323.8
40°	446.5	414.0	391.1	372.2	354.9	344.3	334.2	324.0	315.7	312.3	303.6
42.5°	418.2	391.7	368.7	348.1	336.5	325.3	312.5	305.0	296.3	290.8	285.5
45°	379.0	355.7	336.0	319.0	306.2	294.6	286.2	273.8	268.9	257.9	253.4
47.5°	344.6	322.9	304.2	288.0	275.5	267.9	255.8	246.0	238.2	231.5	225.7
50°	320.1	302.1	284.0	269.6	258.3	247.4	235.0	230.0	217.9	214.6	211.2
52.5°	297.8	280.6	264.1	250.0	238.7	228.1	217.1	210.8	202.6	199.1	196.7
55°	266.6	250.0	234.2	221.8	210.5	199.4	192.7	184.8	181.0	178.3	175.3
57.5°	235.2	220.4	208.1	195.6	184.2	175.5	167.6	162.9	159.0	155.5	151.9
60°	215.3	201.0	190.1	178.3	166.7	159.6	153.5	147.8	143.3	138.0	136.5
62.5°	194.2	181.7	171.7	160.3	150.1	143.5	137.8	132.5	127.0	119.4	117.2
65°	165.2	155.4	144.8	135.4	126.3	120.0	111.6	105.6	103.3	102.6	102.2
67.5°	139.0	129.7	120.6	111.0	102.7	96.7	92.5	91.6	90.1	89.6	88.6
70°	121.4	112.8	103.7	94.6	86.7	85.6	84.1	82.6	80.7	80.0	79.2
72.5°	105.7	96.7	87.8	80.5	77.1	75.6	74.1	72.6	71.4	70.6	70.2
75°	81.1	72.8	66.8	64.1	62.2	61.1	58.9	57.7	57.0	55.8	55.4
77.5°	58.4	53.7	50.9	49.3	47.3	46.0	44.8	43.6	42.8	42.6	42.0
80°	44.5	42.2	40.4	38.1	37.4	35.9	35.4	34.3	34.7	33.5	33.5
82.5°	34.5	31.7	30.1	29.1	28.3	27.1	26.7	26.2	26.3	25.4	25.4
85°	17.8	17.0	16.3	15.5	15.5	14.3	14.7	14.3	14.3	13.5	13.2
87.5°	7.3	7.3	6.9	7.2	7.4	7.4	7.5	7.4	7.5	7.7	7.5
90°	7.6	9.1	10.4	11.6	12.9	14.1	14.9	15.8	16.5	17.3	17.9
92.5°	13.6	13.9	14.5	15.1	15.8	16.4	16.8	17.3	17.7	18.1	18.4
95°	25.2	23.1	24.2	25.3	26.5	27.6	28.4	29.2	29.9	30.7	31.0
97.5°	32.7	26.8	29.3	31.8	34.3	36.9	37.6	38.2	38.8	39.4	39.8
100°	39.1	29.6	32.3	34.9	37.7	40.3	41.5	42.8	44.0	45.3	46.2
102.5°	144.2	130.8	108.5	86.1	63.7	41.4	43.0	44.7	46.4	48.0	49.0
105°	233.8	214.7	171.8	128.9	86.0	43.1	44.8	46.6	48.3	50.0	51.2
107.5°	289.9	266.1	214.7	163.3	111.8	60.4	58.6	56.9	55.1	53.3	52.8
110°	326.4	305.3	259.9	214.5	169.2	123.7	108.1	92.3	76.5	60.9	53.3



TEST NUMBER: P331789-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	361.0	356.9	345.7	334.5	323.3	312.0	254.8	197.4	140.2	82.8	54.4
115°	417.2	420.5	424.4	428.4	432.2	436.2	363.5	290.7	217.9	145.2	103.2
117.5°	469.5	472.3	475.0	477.8	480.4	483.1	465.5	448.0	430.3	412.7	385.4
120°	504.3	506.9	509.7	512.5	515.3	518.2	520.1	522.0	523.8	525.7	516.0
122.5°	536.4	539.3	542.3	545.4	548.5	551.6	552.7	553.8	554.9	556.1	554.6
125°	582.9	585.4	588.4	591.4	594.4	597.3	598.4	599.6	600.7	601.8	602.6
127.5°	627.5	629.8	632.0	634.2	636.4	638.6	640.3	641.9	643.5	645.1	645.9
130°	656.2	658.3	660.0	661.8	663.5	665.3	667.0	668.7	670.4	672.2	673.0
132.5°	683.0	684.9	686.6	688.3	690.1	691.9	693.3	694.8	696.3	697.7	698.4
135°	721.2	723.3	724.7	726.1	727.5	728.9	730.4	732.1	733.6	735.2	735.8
137.5°	755.4	757.1	758.7	760.3	761.9	763.6	765.1	766.6	768.1	769.7	770.2
140°	777.7	779.2	780.9	782.6	784.4	786.2	787.6	789.0	790.4	791.8	792.1
142.5°	797.6	799.1	801.1	803.1	805.1	807.1	808.4	809.6	810.9	812.2	812.4
145°	824.4	825.7	828.3	831.0	833.6	836.4	837.5	838.5	839.6	840.7	840.9
147.5°	850.5	851.5	854.1	856.8	859.4	862.0	862.9	863.7	864.5	865.4	865.5
150°	866.6	867.3	869.8	872.3	874.8	877.4	878.3	879.2	880.2	881.1	881.2
152.5°	881.3	881.9	884.3	886.7	889.1	891.5	892.4	893.3	894.3	895.2	895.2
155°	902.8	903.0	904.9	906.8	908.7	910.6	911.5	912.4	913.4	914.3	914.1
157.5°	921.1	921.1	922.4	923.7	925.0	926.3	927.5	928.6	929.6	930.7	930.6
160°	932.2	932.2	933.2	934.1	935.0	936.0	937.0	937.9	938.9	939.8	939.7
162.5°	941.3	941.2	942.0	942.9	943.7	944.5	945.5	946.6	947.7	948.8	948.7
165°	953.4	953.2	953.7	954.1	954.6	955.1	956.2	957.4	958.4	959.5	959.5
167.5°	962.5	962.3	962.7	963.1	963.6	964.0	965.1	966.2	967.3	968.4	968.3
170°	967.6	967.2	967.6	968.0	968.3	968.6	969.7	970.8	971.8	972.9	972.8
172.5°	971.0	970.7	971.0	971.3	971.6	971.9	973.0	974.1	975.2	976.3	976.1
175°	974.7	974.3	974.6	975.0	975.3	975.6	976.7	977.9	978.9	980.0	979.8
177.5°	976.3	975.9	976.0	976.2	976.3	976.4	977.3	978.3	979.1	980.0	979.9
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331789-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1042.2	1042.8	1041.9	1042.5	1041.9	1042.8	1042.2	1045.5	1046.1	1046.7	1046.1
5°	971.1	966.5	965.8	964.7	965.8	966.5	971.1	973.0	974.5	977.4	982.8
7.5°	886.2	885.4	883.6	880.9	883.6	885.4	886.2	892.6	897.8	903.6	914.4
10°	831.5	829.7	829.3	826.7	829.3	829.7	831.5	839.8	845.9	854.1	868.9
12.5°	767.6	755.5	754.2	747.6	754.2	755.5	767.6	778.3	794.6	802.5	818.2
15°	653.6	651.3	643.8	638.8	643.8	651.3	653.6	662.6	668.6	690.5	715.8
17.5°	588.3	581.0	578.7	577.6	578.7	581.0	588.3	592.8	601.4	612.9	628.1
20°	546.4	539.7	538.6	537.8	538.6	539.7	546.4	551.7	558.6	571.0	586.8
22.5°	517.5	510.4	507.5	505.2	507.5	510.4	517.5	521.6	527.8	537.5	548.2
25°	468.0	465.3	463.8	463.1	463.8	465.3	468.0	471.8	477.8	491.0	502.3
27.5°	429.3	423.5	422.3	420.4	422.3	423.5	429.3	436.1	442.3	448.3	458.4
30°	407.3	405.4	402.7	400.5	402.7	405.4	407.3	410.7	414.9	425.1	434.8
32.5°	381.3	379.8	377.4	376.4	377.4	379.8	381.3	386.0	394.7	400.9	408.0
35°	352.6	347.3	345.1	341.6	345.1	347.3	352.6	356.4	359.8	365.1	377.9
37.5°	322.2	319.4	316.3	317.4	316.3	319.4	322.2	323.8	330.9	338.3	343.9
40°	298.7	296.8	296.0	295.7	296.0	296.8	298.7	303.6	312.3	315.7	324.0
42.5°	279.9	274.8	272.8	272.8	272.8	274.8	279.9	285.5	290.8	296.3	305.0
45°	251.6	246.6	243.3	243.6	243.3	246.6	251.6	253.4	257.9	268.9	273.8
47.5°	222.5	222.3	220.2	220.9	220.2	222.3	222.5	225.7	231.5	238.2	246.0
50°	208.5	206.3	204.8	205.1	204.8	206.3	208.5	211.2	214.6	217.9	230.0
52.5°	195.3	193.3	192.1	193.7	192.1	193.3	195.3	196.7	199.1	202.6	210.8
55°	173.5	171.2	170.9	170.5	170.9	171.2	173.5	175.3	178.3	181.0	184.8
57.5°	149.2	147.6	145.3	144.4	145.3	147.6	149.2	151.9	155.5	159.0	162.9
60°	131.6	128.6	124.8	124.4	124.8	128.6	131.6	136.5	138.0	143.3	147.8
62.5°	115.6	115.0	114.3	114.2	114.3	115.0	115.6	117.2	119.4	127.0	132.5
65°	101.5	101.1	101.5	101.8	101.5	101.1	101.5	102.2	102.6	103.3	105.6
67.5°	88.4	87.8	87.1	87.4	87.1	87.8	88.4	88.6	89.6	90.1	91.6
70°	78.5	78.1	77.7	77.7	77.7	78.1	78.5	79.2	80.0	80.7	82.6
72.5°	68.8	68.7	68.4	68.1	68.4	68.7	68.8	70.2	70.6	71.4	72.6
75°	55.0	54.3	54.3	54.3	54.3	54.3	55.0	55.4	55.8	57.0	57.7
77.5°	41.9	41.6	41.2	40.9	41.2	41.6	41.9	42.0	42.6	42.8	43.6
80°	33.2	32.8	32.4	32.4	32.4	32.8	33.2	33.5	33.5	34.7	34.3
82.5°	25.3	24.9	24.8	24.5	24.8	24.9	25.3	25.4	25.4	26.3	26.2
85°	13.5	13.9	13.5	14.3	13.5	13.9	13.5	13.2	13.5	14.3	14.3
87.5°	7.6	7.3	7.7	7.5	7.7	7.3	7.6	7.5	7.7	7.5	7.4
90°	18.2	18.5	18.8	19.1	18.8	18.5	18.2	17.9	17.3	16.5	15.8
92.5°	18.5	18.7	18.9	19.1	18.9	18.7	18.5	18.4	18.1	17.7	17.3
95°	30.9	30.7	30.6	30.4	30.6	30.7	30.9	31.0	30.7	29.9	29.2
97.5°	40.0	40.2	40.4	40.6	40.4	40.2	40.0	39.8	39.4	38.8	38.2
100°	46.5	46.8	47.1	47.4	47.1	46.8	46.5	46.2	45.3	44.0	42.8
102.5°	49.5	49.9	50.3	50.8	50.3	49.9	49.5	49.0	48.0	46.4	44.7
105°	51.8	52.5	53.1	53.7	53.1	52.5	51.8	51.2	50.0	48.3	46.6
107.5°	53.4	54.0	54.6	55.2	54.6	54.0	53.4	52.8	53.3	55.1	56.9
110°	53.9	54.6	55.2	55.8	55.2	54.6	53.9	53.3	60.9	76.5	92.3



TEST NUMBER: P331789-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	54.9	55.4	55.9	56.5	55.9	55.4	54.9	54.4	82.8	140.2	197.4
115°	91.9	80.6	69.3	58.0	69.3	80.6	91.9	103.2	145.2	217.9	290.7
117.5°	348.2	311.0	273.9	236.7	273.9	311.0	348.2	385.4	412.7	430.3	448.0
120°	494.8	473.6	452.4	431.2	452.4	473.6	494.8	516.0	525.7	523.8	522.0
122.5°	550.5	546.3	542.3	538.2	542.3	546.3	550.5	554.6	556.1	554.9	553.8
125°	603.0	603.5	604.0	604.4	604.0	603.5	603.0	602.6	601.8	600.7	599.6
127.5°	646.0	646.1	646.2	646.3	646.2	646.1	646.0	645.9	645.1	643.5	641.9
130°	672.8	672.7	672.5	672.4	672.5	672.7	672.8	673.0	672.2	670.4	668.7
132.5°	698.2	698.1	697.9	697.8	697.9	698.1	698.2	698.4	697.7	696.3	694.8
135°	735.5	735.2	734.9	734.6	734.9	735.2	735.5	735.8	735.2	733.6	732.1
137.5°	769.6	769.1	768.6	768.0	768.6	769.1	769.6	770.2	769.7	768.1	766.6
140°	791.3	790.5	789.7	789.0	789.7	790.5	791.3	792.1	791.8	790.4	789.0
142.5°	811.7	810.9	810.1	809.3	810.1	810.9	811.7	812.4	812.2	810.9	809.6
145°	840.1	839.3	838.5	837.8	838.5	839.3	840.1	840.9	840.7	839.6	838.5
147.5°	864.7	864.1	863.4	862.7	863.4	864.1	864.7	865.5	865.4	864.5	863.7
150°	880.4	879.6	878.8	878.1	878.8	879.6	880.4	881.2	881.1	880.2	879.2
152.5°	894.1	893.1	892.1	891.0	892.1	893.1	894.1	895.2	895.2	894.3	893.3
155°	912.9	911.7	910.4	909.2	910.4	911.7	912.9	914.1	914.3	913.4	912.4
157.5°	929.4	928.2	927.0	925.6	927.0	928.2	929.4	930.6	930.7	929.6	928.6
160°	938.6	937.5	936.4	935.3	936.4	937.5	938.6	939.7	939.8	938.9	937.9
162.5°	947.3	945.9	944.5	943.2	944.5	945.9	947.3	948.7	948.8	947.7	946.6
165°	958.4	957.4	956.2	955.1	956.2	957.4	958.4	959.5	959.5	958.4	957.4
167.5°	966.8	965.4	964.0	962.6	964.0	965.4	966.8	968.3	968.4	967.3	966.2
170°	971.4	970.0	968.6	967.1	968.6	970.0	971.4	972.8	972.9	971.8	970.8
172.5°	974.7	973.3	971.9	970.5	971.9	973.3	974.7	976.1	976.3	975.2	974.1
175°	978.2	976.6	975.0	973.5	975.0	976.6	978.2	979.8	980.0	978.9	977.9
177.5°	978.8	977.5	976.4	975.3	976.4	977.5	978.8	979.9	980.0	979.1	978.3
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331789-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1043.7	1047.9	1054.3	1057.9	1063.9	1067.8	1070.0	1073.9	1076.0	1083.6	1091.4
5°	985.4	991.5	1002.0	1011.8	1022.4	1033.3	1041.3	1050.3	1058.5	1072.9	1088.0
7.5°	918.6	927.0	943.3	959.0	977.3	992.8	1006.4	1021.9	1035.7	1056.2	1077.6
10°	868.5	883.2	904.7	919.4	943.5	959.0	980.5	997.4	1016.7	1043.9	1068.0
12.5°	825.4	843.1	860.4	880.8	902.5	928.3	951.9	973.6	996.5	1024.6	1052.9
15°	747.1	772.7	799.5	820.2	849.7	876.8	904.3	933.7	961.7	995.2	1032.2
17.5°	646.3	676.0	721.0	756.6	791.1	818.4	852.4	888.1	920.9	961.4	1002.5
20°	600.8	622.6	653.2	701.0	753.2	782.1	816.9	856.1	893.7	937.9	982.0
22.5°	564.2	583.7	608.2	645.5	703.7	743.3	779.4	819.3	863.0	908.1	956.9
25°	512.1	525.7	551.4	581.5	621.5	686.7	726.3	766.3	813.9	862.1	917.9
27.5°	473.0	485.2	501.9	530.7	560.4	607.2	670.2	713.8	761.1	815.5	873.4
30°	443.1	457.5	475.9	496.2	528.8	565.3	628.2	678.8	725.6	781.4	843.2
32.5°	421.4	432.7	448.5	469.2	496.1	531.2	581.5	642.9	688.4	747.3	811.8
35°	385.8	399.0	411.8	431.4	453.3	485.3	523.4	589.1	634.3	692.4	757.3
37.5°	356.5	364.6	378.7	394.3	417.3	441.2	474.2	533.1	582.1	639.0	705.5
40°	334.2	344.3	354.9	372.2	391.1	414.0	446.5	490.3	546.4	602.3	667.1
42.5°	312.5	325.3	336.5	348.1	368.7	391.7	418.2	455.2	512.6	565.4	628.5
45°	286.2	294.6	306.2	319.0	336.0	355.7	379.0	411.4	466.5	512.1	571.4
47.5°	255.8	267.9	275.5	288.0	304.2	322.9	344.6	372.6	417.3	460.0	514.9
50°	235.0	247.4	258.3	269.6	284.0	302.1	320.1	347.3	383.1	428.1	479.3
52.5°	217.1	228.1	238.7	250.0	264.1	280.6	297.8	321.6	352.3	393.6	443.4
55°	192.7	199.4	210.5	221.8	234.2	250.0	266.6	286.6	313.1	347.7	388.1
57.5°	167.6	175.5	184.2	195.6	208.1	220.4	235.2	253.4	274.2	305.6	340.1
60°	153.5	159.6	166.7	178.3	190.1	201.0	215.3	230.5	250.0	277.2	306.6
62.5°	137.8	143.5	150.1	160.3	171.7	181.7	194.2	210.3	226.8	251.6	277.3
65°	111.6	120.0	126.3	135.4	144.8	155.4	165.2	178.0	192.7	212.3	235.3
67.5°	92.5	96.7	102.7	111.0	120.6	129.7	139.0	149.0	161.7	176.8	195.1
70°	84.1	85.6	86.7	94.6	103.7	112.8	121.4	130.9	141.8	154.2	170.1
72.5°	74.1	75.6	77.1	80.5	87.8	96.7	105.7	112.8	123.1	133.4	146.2
75°	58.9	61.1	62.2	64.1	66.8	72.8	81.1	87.9	93.9	101.8	112.0
77.5°	44.8	46.0	47.3	49.3	50.9	53.7	58.4	64.5	70.2	74.7	81.8
80°	35.4	35.9	37.4	38.1	40.4	42.2	44.5	49.4	55.0	57.0	61.8
82.5°	26.7	27.1	28.3	29.1	30.1	31.7	34.5	35.9	40.3	42.7	45.8
85°	14.7	14.3	15.5	15.5	16.3	17.0	17.8	19.6	20.7	23.7	24.5
87.5°	7.5	7.4	7.4	7.2	6.9	7.3	7.3	7.2	7.5	8.1	8.9
90°	14.9	14.1	12.9	11.6	10.4	9.1	7.6	5.9	4.1	2.4	0.7
92.5°	16.8	16.4	15.8	15.1	14.5	13.9	13.6	13.8	13.9	14.1	14.2
95°	28.4	27.6	26.5	25.3	24.2	23.1	25.2	30.4	35.5	40.8	45.9
97.5°	37.6	36.9	34.3	31.8	29.3	26.8	32.7	47.4	62.0	76.5	91.2
100°	41.5	40.3	37.7	34.9	32.3	29.6	39.1	60.6	82.1	103.6	125.1
102.5°	43.0	41.4	63.7	86.1	108.5	130.8	144.2	148.8	153.3	157.9	162.5
105°	44.8	43.1	86.0	128.9	171.8	214.7	233.8	229.0	224.4	219.6	214.9
107.5°	58.6	60.4	111.8	163.3	214.7	266.1	289.9	286.1	282.4	278.5	274.7
110°	108.1	123.7	169.2	214.5	259.9	305.3	326.4	323.1	319.8	316.5	313.2



TEST NUMBER: P331789-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	254.8	312.0	323.3	334.5	345.7	356.9	361.0	358.1	355.3	352.3	349.4
115°	363.5	436.2	432.2	428.4	424.4	420.5	417.2	414.5	411.8	409.2	406.5
117.5°	465.5	483.1	480.4	477.8	475.0	472.3	469.5	466.5	463.5	460.5	457.6
120°	520.1	518.2	515.3	512.5	509.7	506.9	504.3	501.9	499.6	497.3	494.8
122.5°	552.7	551.6	548.5	545.4	542.3	539.3	536.4	534.0	531.5	529.1	526.5
125°	598.4	597.3	594.4	591.4	588.4	585.4	582.9	580.9	578.9	576.8	574.7
127.5°	640.3	638.6	636.4	634.2	632.0	629.8	627.5	625.2	623.0	620.7	618.4
130°	667.0	665.3	663.5	661.8	660.0	658.3	656.2	653.7	651.2	648.6	646.1
132.5°	693.3	691.9	690.1	688.3	686.6	684.9	683.0	680.9	678.7	676.6	674.5
135°	730.4	728.9	727.5	726.1	724.7	723.3	721.2	718.7	716.2	713.7	711.2
137.5°	765.1	763.6	761.9	760.3	758.7	757.1	755.4	753.7	751.9	750.1	748.4
140°	787.6	786.2	784.4	782.6	780.9	779.2	777.7	776.5	775.2	774.0	772.7
142.5°	808.4	807.1	805.1	803.1	801.1	799.1	797.6	796.5	795.4	794.2	793.0
145°	837.5	836.4	833.6	831.0	828.3	825.7	824.4	824.6	824.8	824.9	825.1
147.5°	862.9	862.0	859.4	856.8	854.1	851.5	850.5	851.1	851.7	852.3	852.8
150°	878.3	877.4	874.8	872.3	869.8	867.3	866.6	867.7	868.8	869.9	871.0
152.5°	892.4	891.5	889.1	886.7	884.3	881.9	881.3	882.5	883.8	885.0	886.3
155°	911.5	910.6	908.7	906.8	904.9	903.0	902.8	904.2	905.6	907.1	908.5
157.5°	927.5	926.3	925.0	923.7	922.4	921.1	921.1	922.2	923.4	924.6	925.8
160°	937.0	936.0	935.0	934.1	933.2	932.2	932.2	933.2	934.1	935.0	936.0
162.5°	945.5	944.5	943.7	942.9	942.0	941.2	941.3	942.2	943.2	944.1	945.0
165°	956.2	955.1	954.6	954.1	953.7	953.2	953.4	954.4	955.3	956.2	957.3
167.5°	965.1	964.0	963.6	963.1	962.7	962.3	962.5	963.4	964.4	965.3	966.2
170°	969.7	968.6	968.3	968.0	967.6	967.2	967.6	968.6	969.5	970.4	971.4
172.5°	973.0	971.9	971.6	971.3	971.0	970.7	971.0	971.9	972.9	973.8	974.7
175°	976.7	975.6	975.3	975.0	974.6	974.3	974.7	975.8	976.9	978.1	979.2
177.5°	977.3	976.4	976.3	976.2	976.0	975.9	976.3	977.2	978.1	979.0	979.9
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331789-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1091.7	1092.6	1098.6	1101.4	1106.8	1108.9	1111.3	1110.6	1110.6	1111.9	1120.3
5°	1094.0	1101.6	1112.9	1123.8	1134.4	1143.5	1149.4	1155.5	1157.7	1168.7	1178.5
7.5°	1090.1	1104.0	1122.7	1139.3	1159.3	1175.0	1187.9	1199.6	1207.6	1223.6	1239.8
10°	1085.0	1104.6	1125.7	1147.2	1174.8	1195.5	1216.6	1232.8	1238.1	1261.8	1275.5
12.5°	1074.7	1101.0	1127.8	1155.7	1182.6	1211.1	1234.4	1250.6	1269.2	1290.5	1315.6
15°	1059.3	1089.5	1124.6	1160.4	1198.9	1233.6	1258.5	1286.8	1307.1	1330.5	1352.3
17.5°	1037.2	1076.1	1120.6	1162.2	1206.6	1243.9	1278.2	1305.3	1319.6	1332.9	1336.3
20°	1019.8	1061.6	1114.0	1163.1	1207.5	1250.5	1284.4	1307.1	1310.9	1311.2	1291.2
22.5°	1000.8	1048.0	1102.9	1153.1	1206.3	1254.2	1280.5	1290.2	1275.3	1249.7	1211.0
25°	965.8	1020.5	1084.2	1141.6	1199.6	1244.9	1253.9	1237.0	1184.6	1129.4	1059.8
27.5°	928.0	989.4	1057.7	1121.5	1183.4	1211.4	1191.8	1130.6	1036.2	954.2	854.7
30°	900.2	969.2	1036.3	1107.6	1164.9	1177.0	1132.2	1042.0	931.9	808.2	709.0
32.5°	868.5	940.8	1014.6	1088.3	1136.3	1124.5	1050.4	939.4	810.3	688.7	594.9
35°	823.2	898.0	977.4	1051.4	1082.0	1031.1	920.2	775.8	643.8	530.3	465.7
37.5°	771.0	852.3	935.0	1002.9	1000.8	915.8	764.9	615.7	504.8	437.7	391.7
40°	733.9	816.1	905.4	962.8	938.3	827.8	664.1	523.4	442.3	388.8	355.3
42.5°	698.3	780.8	869.6	915.1	872.5	736.7	573.6	463.4	396.5	354.8	327.5
45°	637.7	724.8	807.1	832.3	756.1	606.4	463.8	384.0	339.4	308.5	289.6
47.5°	578.6	664.2	739.2	739.7	636.6	491.8	391.3	332.2	294.3	270.3	256.6
50°	542.3	623.8	686.7	676.9	560.1	437.5	349.9	299.0	267.4	248.9	234.6
52.5°	501.6	580.6	635.1	607.2	495.1	385.0	312.9	270.1	243.9	227.8	215.0
55°	442.3	512.5	551.0	508.8	403.9	320.1	264.4	230.8	211.2	197.6	186.7
57.5°	384.3	442.0	466.3	417.1	332.6	265.5	223.6	198.4	178.9	169.3	163.6
60°	347.7	397.1	414.0	359.8	289.2	232.3	198.0	174.6	160.3	153.9	148.2
62.5°	311.8	352.1	359.2	309.4	252.2	203.4	173.9	154.1	144.6	138.5	133.1
65°	258.7	287.7	284.4	244.4	199.4	161.4	139.9	127.8	120.7	112.0	102.6
67.5°	213.0	230.8	220.0	190.1	152.3	125.4	111.4	102.3	93.4	85.1	83.0
70°	184.0	194.2	182.9	155.4	124.8	105.2	93.9	83.0	77.7	75.8	72.4
72.5°	156.3	159.9	147.6	124.0	101.6	87.2	76.1	70.0	67.2	65.5	63.3
75°	117.2	114.6	104.1	85.6	70.5	60.7	57.4	55.0	53.2	51.7	50.5
77.5°	82.4	78.5	69.1	57.1	49.1	44.4	42.4	41.2	40.3	39.5	38.4
80°	61.8	59.2	49.8	40.7	37.4	35.0	33.9	32.4	32.4	31.7	30.5
82.5°	45.2	42.3	34.1	29.9	28.0	26.7	25.8	24.8	24.5	24.7	23.9
85°	23.7	19.2	17.0	16.3	15.0	14.3	14.7	13.9	13.9	13.9	13.5
87.5°	7.8	6.6	6.6	6.7	7.3	7.5	7.5	7.7	8.3	8.1	8.6
90°	2.4	4.1	5.9	7.6	9.1	10.4	11.6	12.9	14.1	14.9	15.8
92.5°	14.1	13.9	13.8	13.6	13.9	14.5	15.1	15.8	16.4	16.8	17.3
95°	40.8	35.5	30.4	25.2	23.1	24.2	25.3	26.5	27.6	28.4	29.2
97.5°	76.5	62.0	47.4	32.7	26.8	29.3	31.8	34.3	36.9	37.6	38.2
100°	103.6	82.1	60.6	39.1	29.6	32.3	34.9	37.7	40.3	41.5	42.8
102.5°	157.9	153.3	148.8	144.2	130.8	108.5	86.1	63.7	41.4	43.0	44.7
105°	219.6	224.4	229.0	233.8	214.7	171.8	128.9	86.0	43.1	44.8	46.6
107.5°	278.5	282.4	286.1	289.9	266.1	214.7	163.3	111.8	60.4	58.6	56.9
110°	316.5	319.8	323.1	326.4	305.3	259.9	214.5	169.2	123.7	108.1	92.3



TEST NUMBER: P331789-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	352.3	355.3	358.1	361.0	356.9	345.7	334.5	323.3	312.0	254.8	197.4
115°	409.2	411.8	414.5	417.2	420.5	424.4	428.4	432.2	436.2	363.5	290.7
117.5°	460.5	463.5	466.5	469.5	472.3	475.0	477.8	480.4	483.1	465.5	448.0
120°	497.3	499.6	501.9	504.3	506.9	509.7	512.5	515.3	518.2	520.1	522.0
122.5°	529.1	531.5	534.0	536.4	539.3	542.3	545.4	548.5	551.6	552.7	553.8
125°	576.8	578.9	580.9	582.9	585.4	588.4	591.4	594.4	597.3	598.4	599.6
127.5°	620.7	623.0	625.2	627.5	629.8	632.0	634.2	636.4	638.6	640.3	641.9
130°	648.6	651.2	653.7	656.2	658.3	660.0	661.8	663.5	665.3	667.0	668.7
132.5°	676.6	678.7	680.9	683.0	684.9	686.6	688.3	690.1	691.9	693.3	694.8
135°	713.7	716.2	718.7	721.2	723.3	724.7	726.1	727.5	728.9	730.4	732.1
137.5°	750.1	751.9	753.7	755.4	757.1	758.7	760.3	761.9	763.6	765.1	766.6
140°	774.0	775.2	776.5	777.7	779.2	780.9	782.6	784.4	786.2	787.6	789.0
142.5°	794.2	795.4	796.5	797.6	799.1	801.1	803.1	805.1	807.1	808.4	809.6
145°	824.9	824.8	824.6	824.4	825.7	828.3	831.0	833.6	836.4	837.5	838.5
147.5°	852.3	851.7	851.1	850.5	851.5	854.1	856.8	859.4	862.0	862.9	863.7
150°	869.9	868.8	867.7	866.6	867.3	869.8	872.3	874.8	877.4	878.3	879.2
152.5°	885.0	883.8	882.5	881.3	881.9	884.3	886.7	889.1	891.5	892.4	893.3
155°	907.1	905.6	904.2	902.8	903.0	904.9	906.8	908.7	910.6	911.5	912.4
157.5°	924.6	923.4	922.2	921.1	921.1	922.4	923.7	925.0	926.3	927.5	928.6
160°	935.0	934.1	933.2	932.2	932.2	933.2	934.1	935.0	936.0	937.0	937.9
162.5°	944.1	943.2	942.2	941.3	941.2	942.0	942.9	943.7	944.5	945.5	946.6
165°	956.2	955.3	954.4	953.4	953.2	953.7	954.1	954.6	955.1	956.2	957.4
167.5°	965.3	964.4	963.4	962.5	962.3	962.7	963.1	963.6	964.0	965.1	966.2
170°	970.4	969.5	968.6	967.6	967.2	967.6	968.0	968.3	968.6	969.7	970.8
172.5°	973.8	972.9	971.9	971.0	970.7	971.0	971.3	971.6	971.9	973.0	974.1
175°	978.1	976.9	975.8	974.7	974.3	974.6	975.0	975.3	975.6	976.7	977.9
177.5°	979.0	978.1	977.2	976.3	975.9	976.0	976.2	976.3	976.4	977.3	978.3
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331789-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1123.4	1127.3	1129.1	1129.1	1131.3	1130.3	1129.4
5°	1187.9	1195.1	1196.6	1203.4	1208.3	1206.8	1207.5
7.5°	1252.1	1263.6	1275.1	1280.2	1281.1	1284.1	1285.3
10°	1291.6	1301.1	1318.8	1316.2	1329.4	1336.9	1324.4
12.5°	1329.7	1342.4	1354.7	1358.1	1365.5	1368.0	1363.0
15°	1364.0	1370.8	1371.6	1369.7	1372.0	1370.1	1362.9
17.5°	1331.9	1320.9	1298.6	1288.0	1279.6	1267.3	1262.3
20°	1278.8	1246.4	1208.7	1193.6	1175.9	1141.1	1149.4
22.5°	1164.2	1127.2	1089.5	1045.4	1024.4	991.5	989.6
25°	985.8	922.1	851.9	802.8	774.3	741.4	727.1
27.5°	766.5	686.2	628.7	599.7	573.1	547.1	546.0
30°	622.3	561.9	517.5	492.5	476.4	465.3	467.7
32.5°	524.5	483.1	453.1	432.5	420.5	412.2	412.1
35°	428.8	400.5	381.2	372.6	364.0	357.9	358.3
37.5°	367.0	349.9	339.2	329.7	324.3	321.3	319.6
40°	335.3	321.3	313.1	307.4	302.9	298.7	297.9
42.5°	310.2	298.7	290.3	285.9	281.8	278.7	278.0
45°	275.3	265.9	258.3	253.4	251.6	248.9	248.9
47.5°	244.9	235.6	229.7	226.6	223.4	221.7	221.6
50°	224.4	217.2	212.0	210.1	207.4	206.3	205.9
52.5°	206.0	200.7	196.8	195.6	194.4	193.0	193.2
55°	181.0	178.0	176.5	175.3	173.5	171.2	172.7
57.5°	160.0	157.4	153.3	149.8	148.0	146.4	147.0
60°	145.2	139.9	134.6	130.5	129.4	125.9	125.9
62.5°	126.5	119.1	112.6	110.3	109.2	107.6	107.2
65°	97.3	94.3	92.8	91.3	90.5	90.5	89.8
67.5°	80.6	79.4	77.8	77.4	76.6	76.4	76.1
70°	71.3	69.8	69.0	68.7	67.9	68.3	67.2
72.5°	62.2	61.0	60.9	59.9	59.5	59.5	58.7
75°	49.0	49.0	48.7	48.3	47.6	47.2	47.6
77.5°	37.7	37.8	37.1	37.1	37.0	37.1	36.7
80°	30.2	30.5	30.2	29.8	29.4	29.8	29.4
82.5°	23.8	23.3	23.2	23.1	23.1	22.8	22.8
85°	13.5	13.9	13.5	13.2	13.2	13.2	13.5
87.5°	8.4	8.6	8.7	8.8	8.8	8.9	8.7
90°	16.5	17.3	17.9	18.2	18.5	18.8	19.1
92.5°	17.7	18.1	18.4	18.5	18.7	18.9	19.1
95°	29.9	30.7	31.0	30.9	30.7	30.6	30.4
97.5°	38.8	39.4	39.8	40.0	40.2	40.4	40.6
100°	44.0	45.3	46.2	46.5	46.8	47.1	47.4
102.5°	46.4	48.0	49.0	49.5	49.9	50.3	50.8
105°	48.3	50.0	51.2	51.8	52.5	53.1	53.7
107.5°	55.1	53.3	52.8	53.4	54.0	54.6	55.2
110°	76.5	60.9	53.3	53.9	54.6	55.2	55.8



TEST NUMBER: P331789-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	140.2	82.8	54.4	54.9	55.4	55.9	56.5
115°	217.9	145.2	103.2	91.9	80.6	69.3	58.0
117.5°	430.3	412.7	385.4	348.2	311.0	273.9	236.7
120°	523.8	525.7	516.0	494.8	473.6	452.4	431.2
122.5°	554.9	556.1	554.6	550.5	546.3	542.3	538.2
125°	600.7	601.8	602.6	603.0	603.5	604.0	604.4
127.5°	643.5	645.1	645.9	646.0	646.1	646.2	646.3
130°	670.4	672.2	673.0	672.8	672.7	672.5	672.4
132.5°	696.3	697.7	698.4	698.2	698.1	697.9	697.8
135°	733.6	735.2	735.8	735.5	735.2	734.9	734.6
137.5°	768.1	769.7	770.2	769.6	769.1	768.6	768.0
140°	790.4	791.8	792.1	791.3	790.5	789.7	789.0
142.5°	810.9	812.2	812.4	811.7	810.9	810.1	809.3
145°	839.6	840.7	840.9	840.1	839.3	838.5	837.8
147.5°	864.5	865.4	865.5	864.7	864.1	863.4	862.7
150°	880.2	881.1	881.2	880.4	879.6	878.8	878.1
152.5°	894.3	895.2	895.2	894.1	893.1	892.1	891.0
155°	913.4	914.3	914.1	912.9	911.7	910.4	909.2
157.5°	929.6	930.7	930.6	929.4	928.2	927.0	925.6
160°	938.9	939.8	939.7	938.6	937.5	936.4	935.3
162.5°	947.7	948.8	948.7	947.3	945.9	944.5	943.2
165°	958.4	959.5	959.5	958.4	957.4	956.2	955.1
167.5°	967.3	968.4	968.3	966.8	965.4	964.0	962.6
170°	971.8	972.9	972.8	971.4	970.0	968.6	967.1
172.5°	975.2	976.3	976.1	974.7	973.3	971.9	970.5
175°	978.9	980.0	979.8	978.2	976.6	975.0	973.5
177.5°	979.1	980.0	979.9	978.8	977.5	976.4	975.3
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0

(END OF REPORT)