

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331791-840

Luminaire Tested: **S122RDIW-S485D710U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331791-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D710U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4579.7 lumens
Efficiency: N/A
Efficacy: 121.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331791-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331791-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33	28
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	24
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	16	13
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14	12
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13454	13454	13454
5°	13506	13287	13361
10°	13404	13070	12959
15°	13249	12682	12318
20°	13036	12129	11519
25°	12818	11501	10750
30°	12515	10856	9758
35°	12220	10153	8889
40°	11921	9428	7885
45°	11574	8611	6976
50°	11215	7784	6081
55°	10849	6899	5222
60°	10424	5968	4334
65°	9941	5012	3947
70°	9361	4131	3635
75°	8659	3762	3387
80°	7643	3366	3087
85°	6002	2649	2649



TEST NUMBER: P331791-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	1.7
10°-20°	214.2	4.7
20°-30°	300.8	6.6
30°-40°	328.0	7.2
40°-50°	301.6	6.6
50°-60°	236.8	5.2
60°-70°	154.4	3.4
70°-80°	79.6	1.7
80°-90°	23.1	0.5
90°-100°	32.6	0.7
100°-110°	119.5	2.6
110°-120°	319.5	7.0
120°-130°	527.3	11.5
130°-140°	560.8	12.2
140°-150°	521.3	11.4
150°-160°	419.1	9.2
160°-170°	270.1	5.9
170°-180°	93.0	2.0
0°-30°	593.0	12.9
0°-40°	921.0	20.1
0°-60°	1459.4	31.9
0°-90°	1716.5	37.5
90°-120°	471.6	10.3
90°-150°	2081.0	45.4
90°-180°	2863.0	62.5
0°-180°	4579.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	833	833	833	833	833	
5°	833	829	820	826	824	79
15°	793	783	759	745	737	223
25°	720	694	646	616	603	331
35°	620	580	515	469	451	388
45°	507	455	377	326	306	391
55°	385	325	245	202	186	344
65°	260	199	131	107	103	258
75°	139	87	60	55	54	147
85°	32	17	14	14	14	38
90°	1	8	14	18	19	3
95°	46	24	28	31	30	56
105°	215	224	43	51	54	230
115°	406	419	436	124	58	400
125°	575	584	597	602	604	512
135°	711	722	729	736	735	549
145°	825	825	836	841	838	516
155°	908	903	911	914	909	418
165°	957	953	955	960	955	270
175°	979	974	976	980	974	93
180°	977	977	977	977	977	



TEST NUMBER: P331791-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	836.4	835.8	835.1	834.4	833.7	832.6	831.2	829.7	828.2	826.8	828.1
5°	833.3	832.5	831.7	830.9	830.0	828.5	826.4	824.2	822.0	819.8	821.3
7.5°	824.8	823.7	822.7	821.6	820.6	818.8	816.3	813.7	811.2	808.7	809.1
10°	817.6	816.4	815.2	814.1	812.8	810.6	807.3	803.9	800.5	797.2	796.7
12.5°	808.5	807.1	805.6	804.2	802.7	799.9	795.6	791.3	787.0	782.7	781.8
15°	792.6	790.8	789.0	787.1	785.3	781.5	775.8	770.1	764.5	758.7	755.6
17.5°	773.3	770.4	767.6	764.8	761.9	756.9	749.6	742.3	735.0	727.6	723.9
20°	758.7	755.4	752.0	748.7	745.3	739.4	731.0	722.7	714.3	705.9	701.8
22.5°	743.1	739.3	735.5	731.7	728.0	721.4	712.0	702.5	693.1	683.6	678.2
25°	719.5	714.2	708.8	703.4	698.0	689.8	678.7	667.7	656.6	645.6	638.7
27.5°	691.2	685.3	679.4	673.7	667.8	658.6	646.2	633.7	621.3	608.7	600.8
30°	671.3	664.9	658.5	652.2	645.8	635.9	622.5	609.0	595.6	582.3	573.7
32.5°	652.0	644.5	637.0	629.7	622.2	611.6	597.9	584.2	570.6	556.9	547.1
35°	620.0	611.4	602.9	594.3	585.7	574.1	559.4	544.6	529.9	515.1	504.5
37.5°	587.9	578.6	569.2	559.8	550.5	537.9	522.2	506.4	490.7	475.0	463.3
40°	565.6	555.6	545.5	535.5	525.4	512.3	496.0	479.8	463.5	447.3	435.4
42.5°	542.7	532.1	521.5	511.0	500.4	486.7	469.9	453.0	436.3	419.5	407.2
45°	506.9	495.6	484.3	473.1	461.9	447.5	429.9	412.3	394.7	377.1	365.2
47.5°	471.8	459.9	448.1	436.2	424.2	409.2	391.0	372.8	354.7	336.5	324.7
50°	446.5	434.5	422.7	410.8	398.9	383.7	365.3	346.9	328.4	309.9	298.4
52.5°	421.7	409.3	396.9	384.5	372.0	356.8	338.7	320.7	302.7	284.7	273.5
55°	385.4	372.3	359.2	346.2	333.2	317.5	299.4	281.3	263.2	245.1	235.1
57.5°	348.1	334.8	321.3	307.9	294.5	279.1	261.8	244.3	226.9	209.5	200.3
60°	322.8	309.4	296.0	282.6	269.1	253.9	236.6	219.3	202.1	184.8	176.2
62.5°	298.0	284.7	271.2	257.8	244.4	229.5	213.1	196.6	180.2	163.7	155.5
65°	260.2	246.6	233.1	219.4	205.9	191.6	176.5	161.4	146.3	131.2	125.5
67.5°	223.7	210.3	196.7	183.3	169.8	156.2	142.7	129.2	115.5	102.0	99.4
70°	198.3	185.3	172.2	159.2	146.0	133.7	122.2	110.6	99.1	87.5	85.8
72.5°	174.2	161.7	149.2	136.6	124.1	113.2	103.9	94.6	85.3	76.0	74.6
75°	138.8	127.0	115.3	103.6	91.8	83.1	77.5	71.7	66.0	60.3	59.2
77.5°	103.9	93.6	83.3	73.0	62.8	56.2	53.5	50.8	48.0	45.2	44.5
80°	82.2	73.6	65.1	56.6	48.0	42.9	41.2	39.6	37.9	36.2	35.5
82.5°	62.3	55.6	49.0	42.3	35.6	31.7	30.6	29.4	28.3	27.2	26.8
85°	32.4	28.9	25.3	21.9	18.4	16.4	15.9	15.3	14.8	14.3	14.3
87.5°	9.8	9.1	8.4	7.6	6.9	6.7	6.9	7.2	7.4	7.7	7.7
90°	0.7	2.4	4.1	5.9	7.6	9.1	10.4	11.6	12.9	14.1	14.9
92.5°	14.2	14.1	13.9	13.8	13.6	13.9	14.5	15.1	15.8	16.4	16.8
95°	45.9	40.8	35.5	30.4	25.2	23.1	24.2	25.3	26.5	27.6	28.4
97.5°	91.2	76.5	62.0	47.4	32.7	26.8	29.3	31.8	34.3	36.9	37.6
100°	125.1	103.6	82.1	60.6	39.1	29.6	32.3	34.9	37.7	40.3	41.5
102.5°	162.5	157.9	153.3	148.8	144.2	130.8	108.5	86.1	63.7	41.4	43.0
105°	214.9	219.6	224.4	229.0	233.8	214.7	171.8	128.9	86.0	43.1	44.8
107.5°	274.7	278.5	282.4	286.1	289.9	266.1	214.7	163.3	111.8	60.4	58.6
110°	313.2	316.5	319.8	323.1	326.4	305.3	259.9	214.5	169.2	123.7	108.1



TEST NUMBER: P331791-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	349.4	352.3	355.3	358.1	361.0	356.9	345.7	334.5	323.3	312.0	254.8
115°	406.5	409.2	411.8	414.5	417.2	420.5	424.4	428.4	432.2	436.2	363.5
117.5°	457.6	460.5	463.5	466.5	469.5	472.3	475.0	477.8	480.4	483.1	465.5
120°	494.8	497.3	499.6	501.9	504.3	506.9	509.7	512.5	515.3	518.2	520.1
122.5°	526.5	529.1	531.5	534.0	536.4	539.3	542.3	545.4	548.5	551.6	552.7
125°	574.7	576.8	578.9	580.9	582.9	585.4	588.4	591.4	594.4	597.3	598.4
127.5°	618.4	620.7	623.0	625.2	627.5	629.8	632.0	634.2	636.4	638.6	640.3
130°	646.1	648.6	651.2	653.7	656.2	658.3	660.0	661.8	663.5	665.3	667.0
132.5°	674.5	676.6	678.7	680.9	683.0	684.9	686.6	688.3	690.1	691.9	693.3
135°	711.2	713.7	716.2	718.7	721.2	723.3	724.7	726.1	727.5	728.9	730.4
137.5°	748.4	750.1	751.9	753.7	755.4	757.1	758.7	760.3	761.9	763.6	765.1
140°	772.7	774.0	775.2	776.5	777.7	779.2	780.9	782.6	784.4	786.2	787.6
142.5°	793.0	794.2	795.4	796.5	797.6	799.1	801.1	803.1	805.1	807.1	808.4
145°	825.1	824.9	824.8	824.6	824.4	825.7	828.3	831.0	833.6	836.4	837.5
147.5°	852.8	852.3	851.7	851.1	850.5	851.5	854.1	856.8	859.4	862.0	862.9
150°	871.0	869.9	868.8	867.7	866.6	867.3	869.8	872.3	874.8	877.4	878.3
152.5°	886.3	885.0	883.8	882.5	881.3	881.9	884.3	886.7	889.1	891.5	892.4
155°	908.5	907.1	905.6	904.2	902.8	903.0	904.9	906.8	908.7	910.6	911.5
157.5°	925.8	924.6	923.4	922.2	921.1	921.1	922.4	923.7	925.0	926.3	927.5
160°	936.0	935.0	934.1	933.2	932.2	932.2	933.2	934.1	935.0	936.0	937.0
162.5°	945.0	944.1	943.2	942.2	941.3	941.2	942.0	942.9	943.7	944.5	945.5
165°	957.3	956.2	955.3	954.4	953.4	953.2	953.7	954.1	954.6	955.1	956.2
167.5°	966.2	965.3	964.4	963.4	962.5	962.3	962.7	963.1	963.6	964.0	965.1
170°	971.4	970.4	969.5	968.6	967.6	967.2	967.6	968.0	968.3	968.6	969.7
172.5°	974.7	973.8	972.9	971.9	971.0	970.7	971.0	971.3	971.6	971.9	973.0
175°	979.2	978.1	976.9	975.8	974.7	974.3	974.6	975.0	975.3	975.6	976.7
177.5°	979.9	979.0	978.1	977.2	976.3	975.9	976.0	976.2	976.3	976.4	977.3
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331791-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	829.4	830.8	832.1	832.6	832.4	832.1	831.8	831.6
5°	822.8	824.4	825.9	826.4	825.9	825.4	824.9	824.4
7.5°	809.5	809.9	810.4	810.2	809.3	808.4	807.6	806.7
10°	796.2	795.7	795.2	794.5	793.5	792.4	791.4	790.4
12.5°	780.9	780.0	779.1	777.8	776.1	774.5	772.7	771.1
15°	752.3	749.2	746.0	743.6	741.8	740.2	738.5	736.9
17.5°	720.0	716.3	712.5	709.1	706.3	703.4	700.5	697.6
20°	697.5	693.4	689.1	685.2	681.6	677.8	674.2	670.4
22.5°	672.8	667.4	662.1	657.9	655.2	652.5	649.7	646.9
25°	631.9	625.0	618.1	613.4	610.9	608.3	605.9	603.4
27.5°	592.8	584.7	576.7	570.8	566.7	562.8	558.8	554.8
30°	565.1	556.6	548.1	541.5	536.9	532.5	528.0	523.4
32.5°	537.3	527.7	517.9	510.9	506.6	502.4	498.1	493.8
35°	494.0	483.4	472.9	465.7	462.1	458.4	454.7	451.0
37.5°	451.7	440.1	428.5	420.5	416.4	412.1	407.9	403.6
40°	423.4	411.5	399.6	391.5	387.2	382.8	378.4	374.1
42.5°	394.9	382.5	370.3	362.0	357.8	353.6	349.3	345.1
45°	353.3	341.4	329.5	321.5	317.5	313.5	309.4	305.5
47.5°	312.9	301.0	289.2	281.4	277.8	274.2	270.4	266.8
50°	286.8	275.3	263.7	256.2	252.7	249.1	245.6	242.1
52.5°	262.3	251.2	239.9	232.8	229.5	226.3	223.0	219.7
55°	225.0	214.9	204.9	198.2	195.1	191.9	188.7	185.5
57.5°	191.1	181.9	172.7	166.7	164.0	161.4	158.6	155.9
60°	167.6	159.2	150.6	145.0	142.3	139.6	136.9	134.2
62.5°	147.3	139.3	131.1	126.2	124.6	123.0	121.4	119.8
65°	119.9	114.1	108.5	105.3	104.8	104.3	103.8	103.3
67.5°	96.7	94.1	91.5	90.0	89.4	88.9	88.4	87.8
70°	84.1	82.5	80.8	79.6	79.0	78.3	77.6	77.0
72.5°	73.2	71.8	70.4	69.5	69.1	68.7	68.3	67.9
75°	58.0	56.9	55.6	54.9	54.8	54.6	54.4	54.3
77.5°	43.9	43.2	42.6	42.1	41.8	41.6	41.3	41.0
80°	34.8	34.2	33.5	33.2	33.2	33.2	33.2	33.2
82.5°	26.4	26.0	25.5	25.3	25.3	25.3	25.3	25.3
85°	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.3
87.5°	7.7	7.7	7.8	7.8	7.9	7.9	8.0	8.1
90°	15.8	16.5	17.3	17.9	18.2	18.5	18.8	19.1
92.5°	17.3	17.7	18.1	18.4	18.5	18.7	18.9	19.1
95°	29.2	29.9	30.7	31.0	30.9	30.7	30.6	30.4
97.5°	38.2	38.8	39.4	39.8	40.0	40.2	40.4	40.6
100°	42.8	44.0	45.3	46.2	46.5	46.8	47.1	47.4
102.5°	44.7	46.4	48.0	49.0	49.5	49.9	50.3	50.8
105°	46.6	48.3	50.0	51.2	51.8	52.5	53.1	53.7
107.5°	56.9	55.1	53.3	52.8	53.4	54.0	54.6	55.2
110°	92.3	76.5	60.9	53.3	53.9	54.6	55.2	55.8



TEST NUMBER: P331791-840

CATALOG NUMBER: S122RDIW-S485D710U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	197.4	140.2	82.8	54.4	54.9	55.4	55.9	56.5
115°	290.7	217.9	145.2	103.2	91.9	80.6	69.3	58.0
117.5°	448.0	430.3	412.7	385.4	348.2	311.0	273.9	236.7
120°	522.0	523.8	525.7	516.0	494.8	473.6	452.4	431.2
122.5°	553.8	554.9	556.1	554.6	550.5	546.3	542.3	538.2
125°	599.6	600.7	601.8	602.6	603.0	603.5	604.0	604.4
127.5°	641.9	643.5	645.1	645.9	646.0	646.1	646.2	646.3
130°	668.7	670.4	672.2	673.0	672.8	672.7	672.5	672.4
132.5°	694.8	696.3	697.7	698.4	698.2	698.1	697.9	697.8
135°	732.1	733.6	735.2	735.8	735.5	735.2	734.9	734.6
137.5°	766.6	768.1	769.7	770.2	769.6	769.1	768.6	768.0
140°	789.0	790.4	791.8	792.1	791.3	790.5	789.7	789.0
142.5°	809.6	810.9	812.2	812.4	811.7	810.9	810.1	809.3
145°	838.5	839.6	840.7	840.9	840.1	839.3	838.5	837.8
147.5°	863.7	864.5	865.4	865.5	864.7	864.1	863.4	862.7
150°	879.2	880.2	881.1	881.2	880.4	879.6	878.8	878.1
152.5°	893.3	894.3	895.2	895.2	894.1	893.1	892.1	891.0
155°	912.4	913.4	914.3	914.1	912.9	911.7	910.4	909.2
157.5°	928.6	929.6	930.7	930.6	929.4	928.2	927.0	925.6
160°	937.9	938.9	939.8	939.7	938.6	937.5	936.4	935.3
162.5°	946.6	947.7	948.8	948.7	947.3	945.9	944.5	943.2
165°	957.4	958.4	959.5	959.5	958.4	957.4	956.2	955.1
167.5°	966.2	967.3	968.4	968.3	966.8	965.4	964.0	962.6
170°	970.8	971.8	972.9	972.8	971.4	970.0	968.6	967.1
172.5°	974.1	975.2	976.3	976.1	974.7	973.3	971.9	970.5
175°	977.9	978.9	980.0	979.8	978.2	976.6	975.0	973.5
177.5°	978.3	979.1	980.0	979.9	978.8	977.5	976.4	975.3
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0

(END OF REPORT)