

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331818-840

Luminaire Tested: **S122RDIW-S675D1240U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331818-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S675D1240U840-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6908.9 lumens  
Efficiency: N/A  
Efficacy: 112.5 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 61.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331818-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331818-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	37																				
1	95	91	88	85	86	83	80	77	68	65	64	53	52	51	40	39	38	32																				
2	87	81	75	70	79	73	69	64	60	56	54	47	45	43	36	35	33	28																				
3	80	71	64	59	73	65	59	55	53	49	46	43	40	37	32	31	29	25																				
4	74	63	56	50	67	58	52	47	48	43	40	38	35	32	29	27	26	22																				
5	68	57	49	44	61	52	45	41	43	38	34	35	31	29	27	25	23	19																				
6	63	51	44	38	57	47	40	36	39	34	30	32	28	25	25	22	20	17																				
7	58	46	39	34	53	43	36	31	36	31	27	29	25	23	23	20	18	16																				
8	54	42	35	30	49	39	32	28	33	28	24	27	23	20	21	19	17	14																				
9	50	39	32	27	46	36	29	25	30	25	22	25	21	19	20	17	15	13																				
10	47	36	29	24	43	33	27	23	28	23	20	23	19	17	18	16	14	12																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	23954	23954	23954	23954
5°	26752	24104	21371	24104
10°	29681	23935	18525	23935
15°	31141	23584	14596	23584
20°	26996	23063	12631	23063
25°	17706	22352	11277	22352
30°	11917	21490	10206	21490
35°	9652	20402	9207	20402
40°	8585	19220	8517	19220
45°	7768	17831	7606	17831
50°	7068	16458	7043	16458
55°	6646	14933	6559	14933
60°	5561	13533	5493	13533
65°	4688	12287	5318	12287
70°	4334	10976	5013	10976
75°	4049	9551	4629	9551
80°	3738	7857	4119	7857
85°	3446	6206	3631	6206



TEST NUMBER: P331818-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.6	2.0
10°-20°	391.9	5.7
20°-30°	505.0	7.3
30°-40°	479.9	6.9
40°-50°	411.1	6.0
50°-60°	313.0	4.5
60°-70°	197.9	2.9
70°-80°	98.8	1.4
80°-90°	31.9	0.5
90°-100°	98.3	1.4
100°-110°	305.4	4.4
110°-120°	522.0	7.6
120°-130°	686.4	9.9
130°-140°	770.4	11.2
140°-150°	755.4	10.9
150°-160°	633.6	9.2
160°-170°	420.3	6.1
170°-180°	146.9	2.1
0°-30°	1037.5	15.0
0°-40°	1517.4	22.0
0°-60°	2241.5	32.4
0°-90°	2570.1	37.2
90°-120°	925.7	13.4
90°-150°	3138.0	45.4
90°-180°	4339.0	62.8
0°-180°	6908.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1484	1484	1484	1484	1484	
5°	1651	1487	1319	1487	1651	163
15°	1863	1411	873	1411	1863	503
25°	994	1255	633	1255	994	472
35°	490	1035	467	1035	490	313
45°	340	781	333	781	340	263
55°	236	530	233	530	236	207
65°	123	322	139	322	123	125
75°	65	153	74	153	65	69
85°	19	34	20	34	19	21
90°	44	1	44	1	44	20
95°	81	68	81	68	81	91
105°	291	282	291	282	291	306
115°	524	524	524	524	524	517
125°	765	762	765	762	765	682
135°	998	986	998	986	998	768
145°	1210	1197	1210	1197	1210	756
155°	1379	1368	1379	1368	1379	635
165°	1490	1489	1490	1489	1490	420
175°	1544	1549	1544	1549	1544	147
180°	1552	1552	1552	1552	1552	



TEST NUMBER: P331818-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1543.8	1545.0	1546.3	1543.4	1543.4	1540.9	1535.5	1531.5	1519.8	1518.2	1518.2
5°	1650.6	1649.5	1651.6	1645.0	1635.7	1633.6	1623.8	1610.9	1597.5	1582.6	1579.4
7.5°	1756.8	1755.2	1751.1	1750.0	1742.8	1727.3	1711.5	1694.8	1672.4	1650.7	1639.8
10°	1810.4	1827.5	1817.1	1799.1	1802.7	1778.5	1765.5	1743.4	1724.8	1692.3	1685.2
12.5°	1863.2	1869.9	1866.6	1856.3	1851.7	1834.9	1817.6	1798.3	1764.0	1734.8	1709.5
15°	1863.0	1872.8	1875.3	1872.3	1874.8	1873.8	1864.5	1848.6	1818.7	1786.7	1758.9
17.5°	1725.5	1732.2	1749.2	1760.6	1775.0	1805.5	1820.6	1826.4	1822.0	1803.8	1784.2
20°	1571.2	1559.8	1607.3	1631.5	1652.1	1703.6	1748.0	1765.0	1792.3	1791.8	1786.7
22.5°	1352.6	1355.3	1400.3	1429.1	1489.2	1540.8	1591.3	1655.4	1708.2	1743.1	1763.6
25°	993.9	1013.5	1058.3	1097.5	1164.5	1260.4	1347.5	1448.6	1543.9	1619.1	1690.8
27.5°	746.4	747.9	783.5	819.6	859.4	938.0	1047.6	1168.3	1304.2	1416.4	1545.5
30°	639.2	636.1	651.1	673.3	707.2	768.1	850.5	969.2	1104.7	1273.7	1424.3
32.5°	563.3	563.5	574.8	591.2	619.5	660.5	716.9	813.2	941.4	1107.6	1284.0
35°	489.7	489.2	497.5	509.3	521.2	547.4	586.1	636.6	724.8	879.9	1060.4
37.5°	437.0	439.2	443.2	450.6	463.7	478.4	501.6	535.5	598.2	690.0	841.7
40°	407.3	408.3	413.9	420.1	427.9	439.2	458.3	485.5	531.5	604.7	715.5
42.5°	380.0	381.0	385.1	390.8	396.9	408.3	424.0	447.7	484.8	542.0	633.4
45°	340.2	340.2	343.9	346.4	353.1	363.5	376.3	395.9	421.7	463.9	524.7
47.5°	302.9	303.0	305.4	309.8	314.1	322.0	334.8	350.7	369.5	402.2	454.1
50°	281.4	282.0	283.5	287.1	289.7	296.9	306.7	320.6	340.2	365.5	408.8
52.5°	264.2	263.8	265.8	267.3	269.1	274.3	281.6	293.9	311.3	333.4	369.2
55°	236.1	234.0	237.1	239.7	241.3	243.3	247.4	255.2	270.1	288.7	315.5
57.5°	201.1	200.3	202.4	204.8	209.6	215.2	218.6	223.6	231.4	244.7	271.2
60°	172.2	172.2	176.8	178.3	184.0	191.3	198.4	202.6	210.4	219.0	238.6
62.5°	146.6	147.0	149.2	150.8	153.9	162.8	172.9	182.0	189.2	197.6	210.7
65°	122.7	123.7	123.7	124.7	126.8	128.9	133.0	140.2	153.1	164.9	174.7
67.5°	104.1	104.4	104.7	105.7	106.3	108.6	110.2	113.4	116.4	127.6	139.8
70°	91.8	93.3	92.8	93.8	94.3	95.3	97.5	99.0	103.6	106.2	113.4
72.5°	80.2	81.3	81.2	81.9	83.2	83.4	85.0	86.6	89.6	91.8	95.6
75°	64.9	64.4	64.9	65.9	66.4	67.1	67.1	69.1	70.6	72.7	75.2
77.5°	50.1	50.6	50.5	50.6	50.7	51.6	51.5	52.5	54.0	55.0	56.2
80°	40.2	40.7	40.2	40.7	41.2	41.7	41.2	41.7	43.3	44.3	44.3
82.5°	31.1	31.2	31.5	31.6	31.7	31.8	32.6	32.7	33.8	33.6	34.0
85°	18.6	18.1	18.1	18.1	18.6	19.1	18.6	18.6	19.1	19.1	19.1
87.5°	15.6	15.9	15.8	15.8	15.7	15.8	15.9	16.4	16.1	16.6	14.9
90°	44.5	44.2	43.9	43.6	43.3	43.5	44.1	44.6	45.2	45.8	39.4
92.5°	42.4	42.4	42.3	42.2	42.2	42.1	42.0	41.9	41.7	41.6	40.1
95°	81.2	81.8	82.3	82.9	83.5	83.8	83.8	83.8	83.8	83.8	83.2
97.5°	140.7	140.7	140.8	140.8	140.9	140.9	140.9	140.9	140.9	140.9	139.8
100°	179.4	179.7	180.0	180.3	180.6	180.7	180.7	180.7	180.7	180.7	179.9
102.5°	223.4	223.7	224.0	224.3	224.6	224.6	224.4	224.1	223.9	223.7	222.6
105°	290.7	290.7	290.7	290.7	290.7	290.4	289.8	289.2	288.6	288.1	287.5
107.5°	354.1	355.4	356.8	358.1	359.4	360.0	359.7	359.5	359.3	359.0	359.0
110°	403.3	404.1	405.1	406.0	406.8	407.3	407.3	407.3	407.3	407.3	407.3



TEST NUMBER: P331818-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	450.4	451.1	451.7	452.3	453.0	453.6	454.3	455.0	455.8	456.5	456.7
115°	523.8	524.6	525.5	526.4	527.3	527.9	528.2	528.5	528.8	529.0	529.6
117.5°	593.7	594.6	595.4	596.3	597.2	597.9	598.6	599.4	600.1	600.8	602.4
120°	643.0	643.8	644.7	645.5	646.4	646.8	646.8	646.8	646.8	646.8	649.1
122.5°	691.2	691.8	692.4	693.1	693.7	694.4	695.1	695.8	696.4	697.1	698.7
125°	764.7	765.0	765.3	765.6	765.9	766.5	767.3	768.2	769.1	769.9	770.8
127.5°	831.7	832.7	833.6	834.6	835.5	836.5	837.5	838.6	839.6	840.6	841.7
130°	879.9	881.1	882.3	883.4	884.6	885.4	886.1	886.7	887.2	887.8	888.4
132.5°	926.0	927.0	927.9	928.9	929.8	930.9	932.1	933.4	934.7	935.9	935.8
135°	997.7	998.7	999.6	1000.4	1001.3	1001.9	1002.2	1002.5	1002.7	1003.0	1002.5
137.5°	1062.8	1063.9	1065.1	1066.2	1067.4	1068.1	1068.3	1068.5	1068.8	1069.0	1068.2
140°	1107.8	1108.9	1110.1	1111.3	1112.5	1113.0	1113.0	1113.0	1113.0	1113.0	1111.6
142.5°	1148.6	1149.8	1150.9	1152.2	1153.3	1153.8	1153.6	1153.3	1153.1	1152.9	1151.9
145°	1209.9	1211.1	1212.2	1213.5	1214.6	1215.0	1214.8	1214.5	1214.2	1213.9	1212.1
147.5°	1264.7	1265.8	1266.9	1268.0	1269.1	1269.3	1268.7	1268.0	1267.4	1266.8	1265.6
150°	1300.3	1301.1	1302.0	1302.9	1303.7	1303.7	1302.9	1302.0	1301.1	1300.3	1299.1
152.5°	1333.8	1334.9	1336.1	1337.1	1338.2	1338.2	1337.1	1336.1	1334.9	1333.8	1332.4
155°	1378.9	1379.7	1380.6	1381.5	1382.3	1382.0	1380.6	1379.2	1377.7	1376.2	1375.3
157.5°	1417.5	1419.0	1420.4	1421.8	1423.2	1422.9	1420.9	1419.0	1416.9	1415.0	1414.4
160°	1441.7	1442.9	1444.0	1445.2	1446.3	1446.0	1444.3	1442.6	1440.8	1439.1	1438.8
162.5°	1462.7	1464.0	1465.4	1466.8	1468.2	1467.9	1465.9	1464.0	1462.0	1460.1	1459.8
165°	1490.2	1491.6	1493.1	1494.5	1495.9	1495.7	1493.6	1491.6	1489.6	1487.5	1487.5
167.5°	1512.7	1514.2	1515.7	1517.2	1518.7	1518.4	1516.4	1514.4	1512.4	1510.3	1510.4
170°	1524.2	1525.9	1527.7	1529.4	1531.2	1531.1	1528.9	1526.9	1524.9	1522.9	1523.2
172.5°	1533.6	1535.4	1537.1	1538.8	1540.5	1540.4	1538.4	1536.4	1534.4	1532.3	1532.6
175°	1543.8	1545.6	1547.3	1549.0	1550.8	1550.6	1548.6	1546.6	1544.6	1542.5	1543.1
177.5°	1548.5	1549.9	1551.4	1552.8	1554.1	1554.1	1552.8	1551.4	1549.9	1548.5	1549.0
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331818-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1519.0	1515.7	1512.9	1505.4	1501.8	1493.5	1492.3	1491.9	1481.1	1470.8	1467.9
5°	1571.2	1563.0	1550.5	1536.1	1521.2	1505.7	1495.4	1487.2	1466.5	1446.9	1435.6
7.5°	1623.8	1606.1	1584.7	1557.4	1534.6	1509.0	1490.1	1473.1	1443.8	1415.7	1396.8
10°	1662.9	1634.1	1605.8	1568.1	1538.7	1509.8	1483.1	1459.9	1426.8	1389.8	1363.4
12.5°	1687.3	1655.6	1616.5	1579.6	1541.7	1504.9	1469.1	1439.3	1400.5	1362.1	1330.9
15°	1720.2	1686.2	1638.7	1586.2	1537.2	1489.2	1448.0	1410.9	1360.4	1314.5	1276.4
17.5°	1747.1	1700.3	1649.3	1588.5	1531.9	1470.9	1417.7	1370.4	1314.1	1258.8	1213.9
20°	1755.8	1709.4	1650.6	1589.7	1522.8	1451.1	1393.9	1342.3	1282.0	1221.7	1170.1
22.5°	1750.4	1714.3	1648.9	1576.2	1507.5	1432.5	1367.9	1308.1	1241.2	1179.6	1119.8
25°	1714.0	1701.6	1639.8	1560.3	1482.1	1394.9	1320.2	1254.7	1178.4	1112.5	1047.4
27.5°	1629.1	1655.9	1617.5	1533.0	1445.8	1352.4	1268.4	1193.9	1114.7	1040.5	975.7
30°	1547.5	1608.8	1592.4	1514.0	1416.5	1324.8	1230.5	1152.7	1068.1	991.8	927.9
32.5°	1435.7	1537.1	1553.2	1487.6	1386.8	1286.1	1187.2	1109.7	1021.5	941.1	878.8
35°	1257.8	1409.4	1478.9	1437.1	1336.2	1227.4	1125.3	1035.1	946.4	867.1	805.2
37.5°	1045.5	1251.9	1367.9	1370.9	1278.1	1165.0	1053.9	964.3	873.5	795.6	728.7
40°	907.8	1131.5	1282.5	1316.1	1237.7	1115.5	1003.1	911.9	823.2	746.9	670.1
42.5°	784.1	1006.9	1192.7	1250.9	1188.6	1067.2	954.5	859.1	773.0	700.7	622.3
45°	634.1	828.9	1033.6	1137.7	1103.2	990.8	871.7	780.9	700.0	637.6	562.4
47.5°	534.8	672.2	870.2	1011.1	1010.5	907.9	790.7	703.9	628.8	570.4	509.4
50°	478.4	597.9	765.5	925.3	938.7	852.6	741.2	655.2	585.1	523.7	474.7
52.5°	427.7	526.2	676.8	830.0	868.2	793.7	685.6	606.1	538.1	481.7	439.7
55°	361.3	437.7	552.1	695.4	753.2	700.5	604.7	530.5	475.2	427.9	391.7
57.5°	305.7	362.9	454.7	570.2	637.3	604.3	525.1	464.8	417.7	374.8	346.3
60°	270.6	317.5	395.4	491.8	566.0	542.8	475.2	419.1	378.9	341.7	315.0
62.5°	237.6	277.9	344.7	422.9	491.0	481.4	426.2	379.1	343.9	310.0	287.3
65°	191.3	220.7	272.7	334.1	388.7	393.3	353.7	321.6	290.2	263.4	243.3
67.5°	152.3	171.5	208.1	259.8	300.7	315.4	291.1	266.7	241.8	221.1	203.6
70°	128.4	143.8	170.7	212.4	250.0	265.5	251.6	232.5	210.9	193.8	178.8
72.5°	104.0	119.1	138.9	169.5	201.8	218.4	213.6	200.0	182.4	168.2	154.1
75°	78.4	83.0	96.4	117.0	142.3	156.7	160.4	153.1	139.2	128.4	120.1
77.5°	58.0	60.7	67.2	78.0	94.4	107.3	112.6	111.8	102.2	95.8	88.2
80°	46.4	48.0	51.0	55.6	68.1	80.9	84.5	84.5	77.9	75.2	67.6
82.5°	35.2	36.4	38.3	40.8	46.6	57.9	61.9	62.7	58.5	55.0	49.0
85°	20.1	19.6	20.6	22.1	23.2	26.3	32.5	33.5	32.5	28.4	26.8
87.5°	13.6	12.7	11.5	10.1	9.8	9.5	10.9	12.2	11.3	10.7	10.6
90°	33.0	26.7	20.2	15.2	11.8	8.3	4.8	1.3	4.8	8.3	11.8
92.5°	38.6	37.1	35.5	33.5	31.0	28.5	25.9	23.3	25.9	28.5	31.0
95°	82.6	82.1	81.5	79.8	76.9	73.9	71.0	68.1	71.0	73.9	76.9
97.5°	138.7	137.5	136.4	134.6	132.1	129.6	126.9	124.4	126.9	129.6	132.1
100°	178.9	178.0	177.2	175.6	173.3	171.0	168.6	166.3	168.6	171.0	173.3
102.5°	221.5	220.4	219.2	217.7	215.9	214.0	212.2	210.3	212.2	214.0	215.9
105°	286.9	286.3	285.8	285.0	284.2	283.3	282.4	281.6	282.4	283.3	284.2
107.5°	359.0	359.0	359.0	358.4	357.1	355.9	354.6	353.3	354.6	355.9	357.1
110°	407.3	407.3	407.3	406.4	404.7	402.8	401.1	399.4	401.1	402.8	404.7





TEST NUMBER: P331818-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	457.0	457.2	457.4	456.7	454.9	453.1	451.4	449.7	451.4	453.1	454.9
115°	530.2	530.8	531.3	530.8	529.0	527.3	525.5	523.8	525.5	527.3	529.0
117.5°	604.0	605.6	607.3	606.9	604.6	602.3	600.0	597.6	600.0	602.3	604.6
120°	651.6	653.9	656.2	656.2	653.9	651.6	649.1	646.8	649.1	651.6	653.9
122.5°	700.4	702.1	703.7	703.1	700.2	697.5	694.7	691.9	694.7	697.5	700.2
125°	771.7	772.5	773.5	772.5	769.9	767.3	764.7	762.0	764.7	767.3	769.9
127.5°	842.7	843.8	844.9	843.7	840.4	837.1	833.7	830.4	833.7	837.1	840.4
130°	889.0	889.6	890.1	888.5	884.7	881.0	877.2	873.4	877.2	881.0	884.7
132.5°	935.7	935.6	935.5	933.9	930.8	927.8	924.6	921.6	924.6	927.8	930.8
135°	1001.9	1001.3	1000.7	998.9	995.6	992.4	989.2	986.0	989.2	992.4	995.6
137.5°	1067.5	1066.7	1066.0	1064.3	1061.7	1059.0	1056.4	1053.8	1056.4	1059.0	1061.7
140°	1110.1	1108.6	1107.2	1105.2	1102.6	1099.9	1097.3	1094.7	1097.3	1099.9	1102.6
142.5°	1150.8	1149.8	1148.8	1147.1	1144.5	1141.9	1139.2	1136.6	1139.2	1141.9	1144.5
145°	1210.3	1208.6	1206.9	1205.0	1203.0	1200.9	1198.9	1196.8	1198.9	1200.9	1203.0
147.5°	1264.5	1263.2	1262.1	1260.3	1257.9	1255.4	1252.9	1250.5	1252.9	1255.4	1257.9
150°	1298.0	1296.8	1295.7	1294.1	1292.4	1290.7	1288.9	1287.2	1288.9	1290.7	1292.4
152.5°	1331.0	1329.6	1328.2	1326.7	1324.8	1323.1	1321.4	1319.7	1321.4	1323.1	1324.8
155°	1374.4	1373.6	1372.7	1371.9	1371.0	1370.1	1369.3	1368.4	1369.3	1370.1	1371.0
157.5°	1413.9	1413.4	1412.9	1412.3	1411.8	1411.2	1410.6	1410.0	1410.6	1411.2	1411.8
160°	1438.5	1438.1	1437.9	1437.4	1436.9	1436.3	1435.7	1435.1	1435.7	1436.3	1436.9
162.5°	1459.5	1459.2	1458.9	1458.6	1458.5	1458.4	1458.3	1458.1	1458.3	1458.4	1458.5
165°	1487.5	1487.5	1487.5	1487.6	1487.9	1488.2	1488.5	1488.8	1488.5	1488.2	1487.9
167.5°	1510.5	1510.5	1510.6	1511.0	1511.9	1512.8	1513.6	1514.5	1513.6	1512.8	1511.9
170°	1523.5	1523.8	1524.1	1524.6	1525.5	1526.4	1527.2	1528.1	1527.2	1526.4	1525.5
172.5°	1532.9	1533.2	1533.5	1534.1	1534.9	1535.8	1536.7	1537.5	1536.7	1535.8	1534.9
175°	1543.7	1544.3	1544.9	1545.6	1546.4	1547.3	1548.2	1549.0	1548.2	1547.3	1546.4
177.5°	1549.4	1549.9	1550.4	1551.0	1551.7	1552.4	1553.1	1553.8	1553.1	1552.4	1551.7
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331818-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1462.6	1459.7	1454.3	1446.0	1441.1	1432.4	1426.6	1430.0	1430.8	1430.0	1429.2
5°	1423.3	1412.4	1397.5	1383.0	1369.7	1355.2	1347.0	1343.3	1336.2	1332.0	1330.0
7.5°	1375.7	1357.1	1336.0	1310.8	1289.4	1267.1	1255.7	1249.9	1235.2	1227.2	1220.1
10°	1340.3	1310.9	1289.8	1256.8	1236.7	1207.3	1187.2	1187.7	1167.6	1156.2	1148.0
12.5°	1301.1	1268.8	1233.7	1204.0	1176.0	1152.5	1128.2	1118.4	1097.0	1086.1	1063.9
15°	1236.2	1198.5	1161.4	1121.2	1092.9	1056.2	1021.2	978.4	943.8	913.9	905.7
17.5°	1165.2	1118.6	1081.4	1034.2	985.6	924.0	883.4	858.6	837.8	822.0	810.2
20°	1116.5	1069.1	1029.5	958.3	892.8	851.1	821.2	802.1	780.4	763.5	754.2
22.5°	1065.4	1015.9	961.8	882.4	831.4	797.9	771.2	749.3	734.7	721.3	713.0
25°	992.8	938.7	849.5	794.9	753.7	718.6	700.0	686.6	671.2	653.1	644.9
27.5°	916.1	830.0	766.0	725.4	686.0	663.2	646.5	626.5	612.7	604.6	596.0
30°	858.8	772.7	722.8	678.4	650.6	625.3	605.7	594.4	581.0	567.0	561.4
32.5°	794.9	726.1	678.2	641.3	613.0	591.5	576.0	557.6	548.0	539.4	527.6
35°	715.5	663.5	619.7	589.8	562.9	545.4	527.4	516.5	499.0	491.8	487.2
37.5°	648.2	603.1	570.5	538.9	517.7	498.3	487.3	470.0	462.4	452.4	442.6
40°	610.4	566.0	534.5	508.8	485.0	470.6	456.8	442.8	431.4	426.9	415.0
42.5°	571.6	535.5	504.0	475.7	459.9	444.6	427.1	416.9	405.1	397.6	390.2
45°	518.1	486.1	459.3	436.1	418.6	402.6	391.2	374.3	367.6	352.5	346.4
47.5°	471.1	441.3	415.8	393.7	376.6	366.2	349.6	336.3	325.6	316.4	308.5
50°	437.7	412.9	388.2	368.6	353.1	338.2	321.1	314.5	297.9	293.3	288.7
52.5°	407.2	383.6	360.9	341.7	326.3	311.7	296.8	288.0	276.9	272.3	268.9
55°	364.5	341.7	320.1	303.1	287.6	272.7	263.4	252.6	247.4	243.8	239.7
57.5°	321.5	301.1	284.6	267.3	251.8	239.9	229.1	222.7	217.3	212.6	207.6
60°	294.4	274.8	259.8	243.8	227.8	218.0	209.8	202.1	195.9	188.6	186.6
62.5°	265.5	248.3	234.7	219.0	205.2	196.2	188.3	181.1	173.6	163.1	160.2
65°	225.8	212.4	197.9	185.1	172.7	163.9	152.6	144.3	141.3	140.2	139.7
67.5°	190.0	177.2	164.8	151.7	140.4	132.3	126.5	125.2	123.1	122.5	121.1
70°	166.0	154.1	141.8	129.4	118.6	117.0	114.9	112.9	110.3	109.3	108.3
72.5°	144.5	132.3	119.9	110.0	105.3	103.4	101.4	99.3	97.6	96.5	95.8
75°	110.8	99.5	91.3	87.7	85.0	83.5	80.4	78.9	77.9	76.2	75.7
77.5°	79.8	73.4	69.6	67.4	64.6	63.0	61.2	59.7	58.6	58.3	57.5
80°	60.8	57.8	55.1	52.1	51.0	49.0	48.5	47.0	47.5	45.8	45.8
82.5°	47.3	43.3	41.1	39.7	38.7	37.1	36.5	35.7	35.9	34.7	34.7
85°	24.2	23.2	22.1	21.1	21.1	19.6	20.1	19.6	19.6	18.6	18.1
87.5°	10.9	11.5	11.9	13.2	14.4	15.3	15.2	14.7	14.5	14.4	14.0
90°	15.2	20.2	26.7	33.0	39.4	45.8	45.2	44.6	44.1	43.5	43.3
92.5°	33.5	35.5	37.1	38.6	40.1	41.6	41.7	41.9	42.0	42.1	42.2
95°	79.8	81.5	82.1	82.6	83.2	83.8	83.8	83.8	83.8	83.8	83.5
97.5°	134.6	136.4	137.5	138.7	139.8	140.9	140.9	140.9	140.9	140.9	140.9
100°	175.6	177.2	178.0	178.9	179.9	180.7	180.7	180.7	180.7	180.7	180.6
102.5°	217.7	219.2	220.4	221.5	222.6	223.7	223.9	224.1	224.4	224.6	224.6
105°	285.0	285.8	286.3	286.9	287.5	288.1	288.6	289.2	289.8	290.4	290.7
107.5°	358.4	359.0	359.0	359.0	359.0	359.0	359.3	359.5	359.7	360.0	359.4
110°	406.4	407.3	407.3	407.3	407.3	407.3	407.3	407.3	407.3	407.3	406.8



TEST NUMBER: P331818-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	456.7	457.4	457.2	457.0	456.7	456.5	455.8	455.0	454.3	453.6	453.0
115°	530.8	531.3	530.8	530.2	529.6	529.0	528.8	528.5	528.2	527.9	527.3
117.5°	606.9	607.3	605.6	604.0	602.4	600.8	600.1	599.4	598.6	597.9	597.2
120°	656.2	656.2	653.9	651.6	649.1	646.8	646.8	646.8	646.8	646.8	646.4
122.5°	703.1	703.7	702.1	700.4	698.7	697.1	696.4	695.8	695.1	694.4	693.7
125°	772.5	773.5	772.5	771.7	770.8	769.9	769.1	768.2	767.3	766.5	765.9
127.5°	843.7	844.9	843.8	842.7	841.7	840.6	839.6	838.6	837.5	836.5	835.5
130°	888.5	890.1	889.6	889.0	888.4	887.8	887.2	886.7	886.1	885.4	884.6
132.5°	933.9	935.5	935.6	935.7	935.8	935.9	934.7	933.4	932.1	930.9	929.8
135°	998.9	1000.7	1001.3	1001.9	1002.5	1003.0	1002.7	1002.5	1002.2	1001.9	1001.3
137.5°	1064.3	1066.0	1066.7	1067.5	1068.2	1069.0	1068.8	1068.5	1068.3	1068.1	1067.4
140°	1105.2	1107.2	1108.6	1110.1	1111.6	1113.0	1113.0	1113.0	1113.0	1113.0	1112.5
142.5°	1147.1	1148.8	1149.8	1150.8	1151.9	1152.9	1153.1	1153.3	1153.6	1153.8	1153.3
145°	1205.0	1206.9	1208.6	1210.3	1212.1	1213.9	1214.2	1214.5	1214.8	1215.0	1214.6
147.5°	1260.3	1262.1	1263.2	1264.5	1265.6	1266.8	1267.4	1268.0	1268.7	1269.3	1269.1
150°	1294.1	1295.7	1296.8	1298.0	1299.1	1300.3	1301.1	1302.0	1302.9	1303.7	1303.7
152.5°	1326.7	1328.2	1329.6	1331.0	1332.4	1333.8	1334.9	1336.1	1337.1	1338.2	1338.2
155°	1371.9	1372.7	1373.6	1374.4	1375.3	1376.2	1377.7	1379.2	1380.6	1382.0	1382.3
157.5°	1412.3	1412.9	1413.4	1413.9	1414.4	1415.0	1416.9	1419.0	1420.9	1422.9	1423.2
160°	1437.4	1437.9	1438.1	1438.5	1438.8	1439.1	1440.8	1442.6	1444.3	1446.0	1446.3
162.5°	1458.6	1458.9	1459.2	1459.5	1459.8	1460.1	1462.0	1464.0	1465.9	1467.9	1468.2
165°	1487.6	1487.5	1487.5	1487.5	1487.5	1487.5	1489.6	1491.6	1493.6	1495.7	1495.9
167.5°	1511.0	1510.6	1510.5	1510.5	1510.4	1510.3	1512.4	1514.4	1516.4	1518.4	1518.7
170°	1524.6	1524.1	1523.8	1523.5	1523.2	1522.9	1524.9	1526.9	1528.9	1531.1	1531.2
172.5°	1534.1	1533.5	1533.2	1532.9	1532.6	1532.3	1534.4	1536.4	1538.4	1540.4	1540.5
175°	1545.6	1544.9	1544.3	1543.7	1543.1	1542.5	1544.6	1546.6	1548.6	1550.6	1550.8
177.5°	1551.0	1550.4	1549.9	1549.4	1549.0	1548.5	1549.9	1551.4	1552.8	1554.1	1554.1
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331818-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1424.6	1425.4	1424.2	1425.0	1424.2	1425.4	1424.6	1429.2	1430.0	1430.8	1430.0
5°	1327.4	1321.2	1320.2	1318.6	1320.2	1321.2	1327.4	1330.0	1332.0	1336.2	1343.3
7.5°	1211.3	1210.3	1207.8	1204.2	1207.8	1210.3	1211.3	1220.1	1227.2	1235.2	1249.9
10°	1136.6	1134.1	1133.6	1129.9	1133.6	1134.1	1136.6	1148.0	1156.2	1167.6	1187.7
12.5°	1049.2	1032.6	1030.9	1021.9	1030.9	1032.6	1049.2	1063.9	1086.1	1097.0	1118.4
15°	893.3	890.3	879.9	873.2	879.9	890.3	893.3	905.7	913.9	943.8	978.4
17.5°	804.3	794.2	790.9	789.5	790.9	794.2	804.3	810.2	822.0	837.8	858.6
20°	746.9	737.7	736.1	735.1	736.1	737.7	746.9	754.2	763.5	780.4	802.1
22.5°	707.3	697.6	693.7	690.5	693.7	697.6	707.3	713.0	721.3	734.7	749.3
25°	639.7	636.1	634.1	633.0	634.1	636.1	639.7	644.9	653.1	671.2	686.6
27.5°	586.8	578.9	577.3	574.7	577.3	578.9	586.8	596.0	604.6	612.7	626.5
30°	556.7	554.1	550.6	547.4	550.6	554.1	556.7	561.4	567.0	581.0	594.4
32.5°	521.3	519.1	515.9	514.4	515.9	519.1	521.3	527.6	539.4	548.0	557.6
35°	482.0	474.7	471.7	467.1	471.7	474.7	482.0	487.2	491.8	499.0	516.5
37.5°	440.4	436.7	432.3	433.8	432.3	436.7	440.4	442.6	452.4	462.4	470.0
40°	408.3	405.7	404.7	404.1	404.7	405.7	408.3	415.0	426.9	431.4	442.8
42.5°	382.7	375.6	372.9	372.8	372.9	375.6	382.7	390.2	397.6	405.1	416.9
45°	343.9	337.1	332.4	333.1	332.4	337.1	343.9	346.4	352.5	367.6	374.3
47.5°	304.1	303.9	300.9	301.8	300.9	303.9	304.1	308.5	316.4	325.6	336.3
50°	285.1	282.0	279.9	280.4	279.9	282.0	285.1	288.7	293.3	297.9	314.5
52.5°	266.9	264.3	262.6	264.8	262.6	264.3	266.9	268.9	272.3	276.9	288.0
55°	237.1	234.0	233.5	233.0	233.5	234.0	237.1	239.7	243.8	247.4	252.6
57.5°	203.8	201.8	198.6	197.3	198.6	201.8	203.8	207.6	212.6	217.3	222.7
60°	179.9	175.8	170.7	170.1	170.7	175.8	179.9	186.6	188.6	195.9	202.1
62.5°	158.0	157.2	156.2	156.1	156.2	157.2	158.0	160.2	163.1	173.6	181.1
65°	138.7	138.1	138.7	139.2	138.7	138.1	138.7	139.7	140.2	141.3	144.3
67.5°	120.9	119.9	119.0	119.4	119.0	119.9	120.9	121.1	122.5	123.1	125.2
70°	107.2	106.7	106.2	106.2	106.2	106.7	107.2	108.3	109.3	110.3	112.9
72.5°	94.0	93.9	93.4	93.0	93.4	93.9	94.0	95.8	96.5	97.6	99.3
75°	75.2	74.2	74.2	74.2	74.2	74.2	75.2	75.7	76.2	77.9	78.9
77.5°	57.4	56.9	56.2	55.8	56.2	56.9	57.4	57.5	58.3	58.6	59.7
80°	45.3	44.8	44.3	44.3	44.3	44.8	45.3	45.8	45.8	47.5	47.0
82.5°	34.6	34.1	34.0	33.6	34.0	34.1	34.6	34.7	34.7	35.9	35.7
85°	18.6	19.1	18.6	19.6	18.6	19.1	18.6	18.1	18.6	19.6	19.6
87.5°	14.1	13.7	14.2	13.8	14.2	13.7	14.1	14.0	14.4	14.5	14.7
90°	43.6	43.9	44.2	44.5	44.2	43.9	43.6	43.3	43.5	44.1	44.6
92.5°	42.2	42.3	42.4	42.4	42.4	42.3	42.2	42.2	42.1	42.0	41.9
95°	82.9	82.3	81.8	81.2	81.8	82.3	82.9	83.5	83.8	83.8	83.8
97.5°	140.8	140.8	140.7	140.7	140.7	140.8	140.8	140.9	140.9	140.9	140.9
100°	180.3	180.0	179.7	179.4	179.7	180.0	180.3	180.6	180.7	180.7	180.7
102.5°	224.3	224.0	223.7	223.4	223.7	224.0	224.3	224.6	224.6	224.4	224.1
105°	290.7	290.7	290.7	290.7	290.7	290.7	290.7	290.7	290.4	289.8	289.2
107.5°	358.1	356.8	355.4	354.1	355.4	356.8	358.1	359.4	360.0	359.7	359.5
110°	406.0	405.1	404.1	403.3	404.1	405.1	406.0	406.8	407.3	407.3	407.3



TEST NUMBER: P331818-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	452.3	451.7	451.1	450.4	451.1	451.7	452.3	453.0	453.6	454.3	455.0
115°	526.4	525.5	524.6	523.8	524.6	525.5	526.4	527.3	527.9	528.2	528.5
117.5°	596.3	595.4	594.6	593.7	594.6	595.4	596.3	597.2	597.9	598.6	599.4
120°	645.5	644.7	643.8	643.0	643.8	644.7	645.5	646.4	646.8	646.8	646.8
122.5°	693.1	692.4	691.8	691.2	691.8	692.4	693.1	693.7	694.4	695.1	695.8
125°	765.6	765.3	765.0	764.7	765.0	765.3	765.6	765.9	766.5	767.3	768.2
127.5°	834.6	833.6	832.7	831.7	832.7	833.6	834.6	835.5	836.5	837.5	838.6
130°	883.4	882.3	881.1	879.9	881.1	882.3	883.4	884.6	885.4	886.1	886.7
132.5°	928.9	927.9	927.0	926.0	927.0	927.9	928.9	929.8	930.9	932.1	933.4
135°	1000.4	999.6	998.7	997.7	998.7	999.6	1000.4	1001.3	1001.9	1002.2	1002.5
137.5°	1066.2	1065.1	1063.9	1062.8	1063.9	1065.1	1066.2	1067.4	1068.1	1068.3	1068.5
140°	1111.3	1110.1	1108.9	1107.8	1108.9	1110.1	1111.3	1112.5	1113.0	1113.0	1113.0
142.5°	1152.2	1150.9	1149.8	1148.6	1149.8	1150.9	1152.2	1153.3	1153.8	1153.6	1153.3
145°	1213.5	1212.2	1211.1	1209.9	1211.1	1212.2	1213.5	1214.6	1215.0	1214.8	1214.5
147.5°	1268.0	1266.9	1265.8	1264.7	1265.8	1266.9	1268.0	1269.1	1269.3	1268.7	1268.0
150°	1302.9	1302.0	1301.1	1300.3	1301.1	1302.0	1302.9	1303.7	1303.7	1302.9	1302.0
152.5°	1337.1	1336.1	1334.9	1333.8	1334.9	1336.1	1337.1	1338.2	1338.2	1337.1	1336.1
155°	1381.5	1380.6	1379.7	1378.9	1379.7	1380.6	1381.5	1382.3	1382.0	1380.6	1379.2
157.5°	1421.8	1420.4	1419.0	1417.5	1419.0	1420.4	1421.8	1423.2	1422.9	1420.9	1419.0
160°	1445.2	1444.0	1442.9	1441.7	1442.9	1444.0	1445.2	1446.3	1446.0	1444.3	1442.6
162.5°	1466.8	1465.4	1464.0	1462.7	1464.0	1465.4	1466.8	1468.2	1467.9	1465.9	1464.0
165°	1494.5	1493.1	1491.6	1490.2	1491.6	1493.1	1494.5	1495.9	1495.7	1493.6	1491.6
167.5°	1517.2	1515.7	1514.2	1512.7	1514.2	1515.7	1517.2	1518.7	1518.4	1516.4	1514.4
170°	1529.4	1527.7	1525.9	1524.2	1525.9	1527.7	1529.4	1531.2	1531.1	1528.9	1526.9
172.5°	1538.8	1537.1	1535.4	1533.6	1535.4	1537.1	1538.8	1540.5	1540.4	1538.4	1536.4
175°	1549.0	1547.3	1545.6	1543.8	1545.6	1547.3	1549.0	1550.8	1550.6	1548.6	1546.6
177.5°	1552.8	1551.4	1549.9	1548.5	1549.9	1551.4	1552.8	1554.1	1554.1	1552.8	1551.4
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331818-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1426.6	1432.4	1441.1	1446.0	1454.3	1459.7	1462.6	1467.9	1470.8	1481.1	1491.9
5°	1347.0	1355.2	1369.7	1383.0	1397.5	1412.4	1423.3	1435.6	1446.9	1466.5	1487.2
7.5°	1255.7	1267.1	1289.4	1310.8	1336.0	1357.1	1375.7	1396.8	1415.7	1443.8	1473.1
10°	1187.2	1207.3	1236.7	1256.8	1289.8	1310.9	1340.3	1363.4	1389.8	1426.8	1459.9
12.5°	1128.2	1152.5	1176.0	1204.0	1233.7	1268.8	1301.1	1330.9	1362.1	1400.5	1439.3
15°	1021.2	1056.2	1092.9	1121.2	1161.4	1198.5	1236.2	1276.4	1314.5	1360.4	1410.9
17.5°	883.4	924.0	985.6	1034.2	1081.4	1118.6	1165.2	1213.9	1258.8	1314.1	1370.4
20°	821.2	851.1	892.8	958.3	1029.5	1069.1	1116.5	1170.1	1221.7	1282.0	1342.3
22.5°	771.2	797.9	831.4	882.4	961.8	1015.9	1065.4	1119.8	1179.6	1241.2	1308.1
25°	700.0	718.6	753.7	794.9	849.5	938.7	992.8	1047.4	1112.5	1178.4	1254.7
27.5°	646.5	663.2	686.0	725.4	766.0	830.0	916.1	975.7	1040.5	1114.7	1193.9
30°	605.7	625.3	650.6	678.4	722.8	772.7	858.8	927.9	991.8	1068.1	1152.7
32.5°	576.0	591.5	613.0	641.3	678.2	726.1	794.9	878.8	941.1	1021.5	1109.7
35°	527.4	545.4	562.9	589.8	619.7	663.5	715.5	805.2	867.1	946.4	1035.1
37.5°	487.3	498.3	517.7	538.9	570.5	603.1	648.2	728.7	795.6	873.5	964.3
40°	456.8	470.6	485.0	508.8	534.5	566.0	610.4	670.1	746.9	823.2	911.9
42.5°	427.1	444.6	459.9	475.7	504.0	535.5	571.6	622.3	700.7	773.0	859.1
45°	391.2	402.6	418.6	436.1	459.3	486.1	518.1	562.4	637.6	700.0	780.9
47.5°	349.6	366.2	376.6	393.7	415.8	441.3	471.1	509.4	570.4	628.8	703.9
50°	321.1	338.2	353.1	368.6	388.2	412.9	437.7	474.7	523.7	585.1	655.2
52.5°	296.8	311.7	326.3	341.7	360.9	383.6	407.2	439.7	481.7	538.1	606.1
55°	263.4	272.7	287.6	303.1	320.1	341.7	364.5	391.7	427.9	475.2	530.5
57.5°	229.1	239.9	251.8	267.3	284.6	301.1	321.5	346.3	374.8	417.7	464.8
60°	209.8	218.0	227.8	243.8	259.8	274.8	294.4	315.0	341.7	378.9	419.1
62.5°	188.3	196.2	205.2	219.0	234.7	248.3	265.5	287.3	310.0	343.9	379.1
65°	152.6	163.9	172.7	185.1	197.9	212.4	225.8	243.3	263.4	290.2	321.6
67.5°	126.5	132.3	140.4	151.7	164.8	177.2	190.0	203.6	221.1	241.8	266.7
70°	114.9	117.0	118.6	129.4	141.8	154.1	166.0	178.8	193.8	210.9	232.5
72.5°	101.4	103.4	105.3	110.0	119.9	132.3	144.5	154.1	168.2	182.4	200.0
75°	80.4	83.5	85.0	87.7	91.3	99.5	110.8	120.1	128.4	139.2	153.1
77.5°	61.2	63.0	64.6	67.4	69.6	73.4	79.8	88.2	95.8	102.2	111.8
80°	48.5	49.0	51.0	52.1	55.1	57.8	60.8	67.6	75.2	77.9	84.5
82.5°	36.5	37.1	38.7	39.7	41.1	43.3	47.3	49.0	55.0	58.5	62.7
85°	20.1	19.6	21.1	21.1	22.1	23.2	24.2	26.8	28.4	32.5	33.5
87.5°	15.2	15.3	14.4	13.2	11.9	11.5	10.9	10.6	10.7	11.3	12.2
90°	45.2	45.8	39.4	33.0	26.7	20.2	15.2	11.8	8.3	4.8	1.3
92.5°	41.7	41.6	40.1	38.6	37.1	35.5	33.5	31.0	28.5	25.9	23.3
95°	83.8	83.8	83.2	82.6	82.1	81.5	79.8	76.9	73.9	71.0	68.1
97.5°	140.9	140.9	139.8	138.7	137.5	136.4	134.6	132.1	129.6	126.9	124.4
100°	180.7	180.7	179.9	178.9	178.0	177.2	175.6	173.3	171.0	168.6	166.3
102.5°	223.9	223.7	222.6	221.5	220.4	219.2	217.7	215.9	214.0	212.2	210.3
105°	288.6	288.1	287.5	286.9	286.3	285.8	285.0	284.2	283.3	282.4	281.6
107.5°	359.3	359.0	359.0	359.0	359.0	359.0	358.4	357.1	355.9	354.6	353.3
110°	407.3	407.3	407.3	407.3	407.3	407.3	406.4	404.7	402.8	401.1	399.4



TEST NUMBER: P331818-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	455.8	456.5	456.7	457.0	457.2	457.4	456.7	454.9	453.1	451.4	449.7
115°	528.8	529.0	529.6	530.2	530.8	531.3	530.8	529.0	527.3	525.5	523.8
117.5°	600.1	600.8	602.4	604.0	605.6	607.3	606.9	604.6	602.3	600.0	597.6
120°	646.8	646.8	649.1	651.6	653.9	656.2	656.2	653.9	651.6	649.1	646.8
122.5°	696.4	697.1	698.7	700.4	702.1	703.7	703.1	700.2	697.5	694.7	691.9
125°	769.1	769.9	770.8	771.7	772.5	773.5	772.5	769.9	767.3	764.7	762.0
127.5°	839.6	840.6	841.7	842.7	843.8	844.9	843.7	840.4	837.1	833.7	830.4
130°	887.2	887.8	888.4	889.0	889.6	890.1	888.5	884.7	881.0	877.2	873.4
132.5°	934.7	935.9	935.8	935.7	935.6	935.5	933.9	930.8	927.8	924.6	921.6
135°	1002.7	1003.0	1002.5	1001.9	1001.3	1000.7	998.9	995.6	992.4	989.2	986.0
137.5°	1068.8	1069.0	1068.2	1067.5	1066.7	1066.0	1064.3	1061.7	1059.0	1056.4	1053.8
140°	1113.0	1113.0	1111.6	1110.1	1108.6	1107.2	1105.2	1102.6	1099.9	1097.3	1094.7
142.5°	1153.1	1152.9	1151.9	1150.8	1149.8	1148.8	1147.1	1144.5	1141.9	1139.2	1136.6
145°	1214.2	1213.9	1212.1	1210.3	1208.6	1206.9	1205.0	1203.0	1200.9	1198.9	1196.8
147.5°	1267.4	1266.8	1265.6	1264.5	1263.2	1262.1	1260.3	1257.9	1255.4	1252.9	1250.5
150°	1301.1	1300.3	1299.1	1298.0	1296.8	1295.7	1294.1	1292.4	1290.7	1288.9	1287.2
152.5°	1334.9	1333.8	1332.4	1331.0	1329.6	1328.2	1326.7	1324.8	1323.1	1321.4	1319.7
155°	1377.7	1376.2	1375.3	1374.4	1373.6	1372.7	1371.9	1371.0	1370.1	1369.3	1368.4
157.5°	1416.9	1415.0	1414.4	1413.9	1413.4	1412.9	1412.3	1411.8	1411.2	1410.6	1410.0
160°	1440.8	1439.1	1438.8	1438.5	1438.1	1437.9	1437.4	1436.9	1436.3	1435.7	1435.1
162.5°	1462.0	1460.1	1459.8	1459.5	1459.2	1458.9	1458.6	1458.5	1458.4	1458.3	1458.1
165°	1489.6	1487.5	1487.5	1487.5	1487.5	1487.5	1487.6	1487.9	1488.2	1488.5	1488.8
167.5°	1512.4	1510.3	1510.4	1510.5	1510.5	1510.6	1511.0	1511.9	1512.8	1513.6	1514.5
170°	1524.9	1522.9	1523.2	1523.5	1523.8	1524.1	1524.6	1525.5	1526.4	1527.2	1528.1
172.5°	1534.4	1532.3	1532.6	1532.9	1533.2	1533.5	1534.1	1534.9	1535.8	1536.7	1537.5
175°	1544.6	1542.5	1543.1	1543.7	1544.3	1544.9	1545.6	1546.4	1547.3	1548.2	1549.0
177.5°	1549.9	1548.5	1549.0	1549.4	1549.9	1550.4	1551.0	1551.7	1552.4	1553.1	1553.8
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331818-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1492.3	1493.5	1501.8	1505.4	1512.9	1515.7	1519.0	1518.2	1518.2	1519.8	1531.5
5°	1495.4	1505.7	1521.2	1536.1	1550.5	1563.0	1571.2	1579.4	1582.6	1597.5	1610.9
7.5°	1490.1	1509.0	1534.6	1557.4	1584.7	1606.1	1623.8	1639.8	1650.7	1672.4	1694.8
10°	1483.1	1509.8	1538.7	1568.1	1605.8	1634.1	1662.9	1685.2	1692.3	1724.8	1743.4
12.5°	1469.1	1504.9	1541.7	1579.6	1616.5	1655.6	1687.3	1709.5	1734.8	1764.0	1798.3
15°	1448.0	1489.2	1537.2	1586.2	1638.7	1686.2	1720.2	1758.9	1786.7	1818.7	1848.6
17.5°	1417.7	1470.9	1531.9	1588.5	1649.3	1700.3	1747.1	1784.2	1803.8	1822.0	1826.4
20°	1393.9	1451.1	1522.8	1589.7	1650.6	1709.4	1755.8	1786.7	1791.8	1792.3	1765.0
22.5°	1367.9	1432.5	1507.5	1576.2	1648.9	1714.3	1750.4	1763.6	1743.1	1708.2	1655.4
25°	1320.2	1394.9	1482.1	1560.3	1639.8	1701.6	1714.0	1690.8	1619.1	1543.9	1448.6
27.5°	1268.4	1352.4	1445.8	1533.0	1617.5	1655.9	1629.1	1545.5	1416.4	1304.2	1168.3
30°	1230.5	1324.8	1416.5	1514.0	1592.4	1608.8	1547.5	1424.3	1273.7	1104.7	969.2
32.5°	1187.2	1286.1	1386.8	1487.6	1553.2	1537.1	1435.7	1284.0	1107.6	941.4	813.2
35°	1125.3	1227.4	1336.2	1437.1	1478.9	1409.4	1257.8	1060.4	879.9	724.8	636.6
37.5°	1053.9	1165.0	1278.1	1370.9	1367.9	1251.9	1045.5	841.7	690.0	598.2	535.5
40°	1003.1	1115.5	1237.7	1316.1	1282.5	1131.5	907.8	715.5	604.7	531.5	485.5
42.5°	954.5	1067.2	1188.6	1250.9	1192.7	1006.9	784.1	633.4	542.0	484.8	447.7
45°	871.7	990.8	1103.2	1137.7	1033.6	828.9	634.1	524.7	463.9	421.7	395.9
47.5°	790.7	907.9	1010.5	1011.1	870.2	672.2	534.8	454.1	402.2	369.5	350.7
50°	741.2	852.6	938.7	925.3	765.5	597.9	478.4	408.8	365.5	340.2	320.6
52.5°	685.6	793.7	868.2	830.0	676.8	526.2	427.7	369.2	333.4	311.3	293.9
55°	604.7	700.5	753.2	695.4	552.1	437.7	361.3	315.5	288.7	270.1	255.2
57.5°	525.1	604.3	637.3	570.2	454.7	362.9	305.7	271.2	244.7	231.4	223.6
60°	475.2	542.8	566.0	491.8	395.4	317.5	270.6	238.6	219.0	210.4	202.6
62.5°	426.2	481.4	491.0	422.9	344.7	277.9	237.6	210.7	197.6	189.2	182.0
65°	353.7	393.3	388.7	334.1	272.7	220.7	191.3	174.7	164.9	153.1	140.2
67.5°	291.1	315.4	300.7	259.8	208.1	171.5	152.3	139.8	127.6	116.4	113.4
70°	251.6	265.5	250.0	212.4	170.7	143.8	128.4	113.4	106.2	103.6	99.0
72.5°	213.6	218.4	201.8	169.5	138.9	119.1	104.0	95.6	91.8	89.6	86.6
75°	160.4	156.7	142.3	117.0	96.4	83.0	78.4	75.2	72.7	70.6	69.1
77.5°	112.6	107.3	94.4	78.0	67.2	60.7	58.0	56.2	55.0	54.0	52.5
80°	84.5	80.9	68.1	55.6	51.0	48.0	46.4	44.3	44.3	43.3	41.7
82.5°	61.9	57.9	46.6	40.8	38.3	36.4	35.2	34.0	33.6	33.8	32.7
85°	32.5	26.3	23.2	22.1	20.6	19.6	20.1	19.1	19.1	19.1	18.6
87.5°	10.9	9.5	9.8	10.1	11.5	12.7	13.6	14.9	16.6	16.1	16.4
90°	4.8	8.3	11.8	15.2	20.2	26.7	33.0	39.4	45.8	45.2	44.6
92.5°	25.9	28.5	31.0	33.5	35.5	37.1	38.6	40.1	41.6	41.7	41.9
95°	71.0	73.9	76.9	79.8	81.5	82.1	82.6	83.2	83.8	83.8	83.8
97.5°	126.9	129.6	132.1	134.6	136.4	137.5	138.7	139.8	140.9	140.9	140.9
100°	168.6	171.0	173.3	175.6	177.2	178.0	178.9	179.9	180.7	180.7	180.7
102.5°	212.2	214.0	215.9	217.7	219.2	220.4	221.5	222.6	223.7	223.9	224.1
105°	282.4	283.3	284.2	285.0	285.8	286.3	286.9	287.5	288.1	288.6	289.2
107.5°	354.6	355.9	357.1	358.4	359.0	359.0	359.0	359.0	359.0	359.3	359.5
110°	401.1	402.8	404.7	406.4	407.3	407.3	407.3	407.3	407.3	407.3	407.3





TEST NUMBER: P331818-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	451.4	453.1	454.9	456.7	457.4	457.2	457.0	456.7	456.5	455.8	455.0
115°	525.5	527.3	529.0	530.8	531.3	530.8	530.2	529.6	529.0	528.8	528.5
117.5°	600.0	602.3	604.6	606.9	607.3	605.6	604.0	602.4	600.8	600.1	599.4
120°	649.1	651.6	653.9	656.2	656.2	653.9	651.6	649.1	646.8	646.8	646.8
122.5°	694.7	697.5	700.2	703.1	703.7	702.1	700.4	698.7	697.1	696.4	695.8
125°	764.7	767.3	769.9	772.5	773.5	772.5	771.7	770.8	769.9	769.1	768.2
127.5°	833.7	837.1	840.4	843.7	844.9	843.8	842.7	841.7	840.6	839.6	838.6
130°	877.2	881.0	884.7	888.5	890.1	889.6	889.0	888.4	887.8	887.2	886.7
132.5°	924.6	927.8	930.8	933.9	935.5	935.6	935.7	935.8	935.9	934.7	933.4
135°	989.2	992.4	995.6	998.9	1000.7	1001.3	1001.9	1002.5	1003.0	1002.7	1002.5
137.5°	1056.4	1059.0	1061.7	1064.3	1066.0	1066.7	1067.5	1068.2	1069.0	1068.8	1068.5
140°	1097.3	1099.9	1102.6	1105.2	1107.2	1108.6	1110.1	1111.6	1113.0	1113.0	1113.0
142.5°	1139.2	1141.9	1144.5	1147.1	1148.8	1149.8	1150.8	1151.9	1152.9	1153.1	1153.3
145°	1198.9	1200.9	1203.0	1205.0	1206.9	1208.6	1210.3	1212.1	1213.9	1214.2	1214.5
147.5°	1252.9	1255.4	1257.9	1260.3	1262.1	1263.2	1264.5	1265.6	1266.8	1267.4	1268.0
150°	1288.9	1290.7	1292.4	1294.1	1295.7	1296.8	1298.0	1299.1	1300.3	1301.1	1302.0
152.5°	1321.4	1323.1	1324.8	1326.7	1328.2	1329.6	1331.0	1332.4	1333.8	1334.9	1336.1
155°	1369.3	1370.1	1371.0	1371.9	1372.7	1373.6	1374.4	1375.3	1376.2	1377.7	1379.2
157.5°	1410.6	1411.2	1411.8	1412.3	1412.9	1413.4	1413.9	1414.4	1415.0	1416.9	1419.0
160°	1435.7	1436.3	1436.9	1437.4	1437.9	1438.1	1438.5	1438.8	1439.1	1440.8	1442.6
162.5°	1458.3	1458.4	1458.5	1458.6	1458.9	1459.2	1459.5	1459.8	1460.1	1462.0	1464.0
165°	1488.5	1488.2	1487.9	1487.6	1487.5	1487.5	1487.5	1487.5	1487.5	1489.6	1491.6
167.5°	1513.6	1512.8	1511.9	1511.0	1510.6	1510.5	1510.5	1510.4	1510.3	1512.4	1514.4
170°	1527.2	1526.4	1525.5	1524.6	1524.1	1523.8	1523.5	1523.2	1522.9	1524.9	1526.9
172.5°	1536.7	1535.8	1534.9	1534.1	1533.5	1533.2	1532.9	1532.6	1532.3	1534.4	1536.4
175°	1548.2	1547.3	1546.4	1545.6	1544.9	1544.3	1543.7	1543.1	1542.5	1544.6	1546.6
177.5°	1553.1	1552.4	1551.7	1551.0	1550.4	1549.9	1549.4	1549.0	1548.5	1549.9	1551.4
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331818-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1535.5	1540.9	1543.4	1543.4	1546.3	1545.0	1543.8
5°	1623.8	1633.6	1635.7	1645.0	1651.6	1649.5	1650.6
7.5°	1711.5	1727.3	1742.8	1750.0	1751.1	1755.2	1756.8
10°	1765.5	1778.5	1802.7	1799.1	1817.1	1827.5	1810.4
12.5°	1817.6	1834.9	1851.7	1856.3	1866.6	1869.9	1863.2
15°	1864.5	1873.8	1874.8	1872.3	1875.3	1872.8	1863.0
17.5°	1820.6	1805.5	1775.0	1760.6	1749.2	1732.2	1725.5
20°	1748.0	1703.6	1652.1	1631.5	1607.3	1559.8	1571.2
22.5°	1591.3	1540.8	1489.2	1429.1	1400.3	1355.3	1352.6
25°	1347.5	1260.4	1164.5	1097.5	1058.3	1013.5	993.9
27.5°	1047.6	938.0	859.4	819.6	783.5	747.9	746.4
30°	850.5	768.1	707.2	673.3	651.1	636.1	639.2
32.5°	716.9	660.5	619.5	591.2	574.8	563.5	563.3
35°	586.1	547.4	521.2	509.3	497.5	489.2	489.7
37.5°	501.6	478.4	463.7	450.6	443.2	439.2	437.0
40°	458.3	439.2	427.9	420.1	413.9	408.3	407.3
42.5°	424.0	408.3	396.9	390.8	385.1	381.0	380.0
45°	376.3	363.5	353.1	346.4	343.9	340.2	340.2
47.5°	334.8	322.0	314.1	309.8	305.4	303.0	302.9
50°	306.7	296.9	289.7	287.1	283.5	282.0	281.4
52.5°	281.6	274.3	269.1	267.3	265.8	263.8	264.2
55°	247.4	243.3	241.3	239.7	237.1	234.0	236.1
57.5°	218.6	215.2	209.6	204.8	202.4	200.3	201.1
60°	198.4	191.3	184.0	178.3	176.8	172.2	172.2
62.5°	172.9	162.8	153.9	150.8	149.2	147.0	146.6
65°	133.0	128.9	126.8	124.7	123.7	123.7	122.7
67.5°	110.2	108.6	106.3	105.7	104.7	104.4	104.1
70°	97.5	95.3	94.3	93.8	92.8	93.3	91.8
72.5°	85.0	83.4	83.2	81.9	81.2	81.3	80.2
75°	67.1	67.1	66.4	65.9	64.9	64.4	64.9
77.5°	51.5	51.6	50.7	50.6	50.5	50.6	50.1
80°	41.2	41.7	41.2	40.7	40.2	40.7	40.2
82.5°	32.6	31.8	31.7	31.6	31.5	31.2	31.1
85°	18.6	19.1	18.6	18.1	18.1	18.1	18.6
87.5°	15.9	15.8	15.7	15.8	15.8	15.9	15.6
90°	44.1	43.5	43.3	43.6	43.9	44.2	44.5
92.5°	42.0	42.1	42.2	42.2	42.3	42.4	42.4
95°	83.8	83.8	83.5	82.9	82.3	81.8	81.2
97.5°	140.9	140.9	140.9	140.8	140.8	140.7	140.7
100°	180.7	180.7	180.6	180.3	180.0	179.7	179.4
102.5°	224.4	224.6	224.6	224.3	224.0	223.7	223.4
105°	289.8	290.4	290.7	290.7	290.7	290.7	290.7
107.5°	359.7	360.0	359.4	358.1	356.8	355.4	354.1
110°	407.3	407.3	406.8	406.0	405.1	404.1	403.3



TEST NUMBER: P331818-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	454.3	453.6	453.0	452.3	451.7	451.1	450.4
115°	528.2	527.9	527.3	526.4	525.5	524.6	523.8
117.5°	598.6	597.9	597.2	596.3	595.4	594.6	593.7
120°	646.8	646.8	646.4	645.5	644.7	643.8	643.0
122.5°	695.1	694.4	693.7	693.1	692.4	691.8	691.2
125°	767.3	766.5	765.9	765.6	765.3	765.0	764.7
127.5°	837.5	836.5	835.5	834.6	833.6	832.7	831.7
130°	886.1	885.4	884.6	883.4	882.3	881.1	879.9
132.5°	932.1	930.9	929.8	928.9	927.9	927.0	926.0
135°	1002.2	1001.9	1001.3	1000.4	999.6	998.7	997.7
137.5°	1068.3	1068.1	1067.4	1066.2	1065.1	1063.9	1062.8
140°	1113.0	1113.0	1112.5	1111.3	1110.1	1108.9	1107.8
142.5°	1153.6	1153.8	1153.3	1152.2	1150.9	1149.8	1148.6
145°	1214.8	1215.0	1214.6	1213.5	1212.2	1211.1	1209.9
147.5°	1268.7	1269.3	1269.1	1268.0	1266.9	1265.8	1264.7
150°	1302.9	1303.7	1303.7	1302.9	1302.0	1301.1	1300.3
152.5°	1337.1	1338.2	1338.2	1337.1	1336.1	1334.9	1333.8
155°	1380.6	1382.0	1382.3	1381.5	1380.6	1379.7	1378.9
157.5°	1420.9	1422.9	1423.2	1421.8	1420.4	1419.0	1417.5
160°	1444.3	1446.0	1446.3	1445.2	1444.0	1442.9	1441.7
162.5°	1465.9	1467.9	1468.2	1466.8	1465.4	1464.0	1462.7
165°	1493.6	1495.7	1495.9	1494.5	1493.1	1491.6	1490.2
167.5°	1516.4	1518.4	1518.7	1517.2	1515.7	1514.2	1512.7
170°	1528.9	1531.1	1531.2	1529.4	1527.7	1525.9	1524.2
172.5°	1538.4	1540.4	1540.5	1538.8	1537.1	1535.4	1533.6
175°	1548.6	1550.6	1550.8	1549.0	1547.3	1545.6	1543.8
177.5°	1552.8	1554.1	1554.1	1552.8	1551.4	1549.9	1548.5
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7

(END OF REPORT)