

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331787

Luminaire Tested: **S122RDIW-S485D435U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331787
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D435U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3429.8 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331787

CATALOG NUMBER: S122RDIW-S485D435U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331787

CATALOG NUMBER: S122RDIW-S485D435U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43
2	90	83	77	72	83	76	71	67	65	61	58	54	52	49	45	43	41	36
3	82	73	66	60	76	68	62	57	58	53	49	48	45	42	40	38	36	31
4	75	65	57	51	69	60	54	48	52	47	42	44	40	37	36	33	31	27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	24
6	64	52	44	39	59	49	42	37	42	37	32	36	32	28	30	27	24	21
7	59	47	40	34	55	44	37	32	38	33	29	33	28	25	27	24	22	19
8	55	43	36	30	51	40	34	29	35	30	26	30	26	23	25	22	20	17
9	51	39	32	27	48	37	30	26	32	27	23	28	23	20	23	20	18	16
10	48	36	29	25	44	34	28	23	30	25	21	26	22	19	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13324	13324	13324
5°	13374	13157	13230
10°	13273	12942	12832
15°	13120	12558	12197
20°	12909	12010	11407
25°	12693	11389	10644
30°	12392	10750	9663
35°	12100	10054	8803
40°	11805	9335	7807
45°	11460	8526	6907
50°	11105	7709	6021
55°	10742	6832	5171
60°	10320	5909	4292
65°	9845	4963	3908
70°	9272	4088	3597
75°	8571	3724	3356
80°	7569	3329	3059
85°	5947	2631	2631



TEST NUMBER: P331787

CATALOG NUMBER: S122RDIW-S485D435U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.2	2.3
10°-20°	212.1	6.2
20°-30°	297.8	8.7
30°-40°	324.8	9.5
40°-50°	298.6	8.7
50°-60°	234.5	6.8
60°-70°	152.9	4.5
70°-80°	78.8	2.3
80°-90°	21.9	0.6
90°-100°	19.7	0.6
100°-110°	72.3	2.1
110°-120°	193.1	5.6
120°-130°	318.8	9.3
130°-140°	339.1	9.9
140°-150°	315.2	9.2
150°-160°	253.4	7.4
160°-170°	163.3	4.8
170°-180°	56.2	1.6
0°-30°	587.2	17.1
0°-40°	912.0	26.6
0°-60°	1445.1	42.1
0°-90°	1698.8	49.5
90°-120°	285.1	8.3
90°-150°	1258.2	36.7
90°-180°	1731.0	50.5
0°-180°	3429.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	825	825	825	825	825	
5°	825	821	812	818	816	78
15°	785	776	751	738	730	221
25°	712	687	639	610	598	327
35°	614	574	510	465	447	384
45°	502	450	373	322	302	387
55°	382	322	243	200	184	341
65°	258	197	130	106	102	255
75°	137	87	60	55	54	145
85°	32	17	14	14	14	38
90°	0	5	8	11	12	3
95°	28	15	17	19	18	34
105°	130	136	26	31	32	139
115°	246	253	264	75	35	242
125°	348	353	361	364	365	310
135°	430	437	441	445	444	332
145°	499	499	506	508	506	312
155°	549	546	550	553	550	253
165°	579	576	577	580	577	163
175°	592	589	590	592	589	56
180°	591	591	591	591	591	



TEST NUMBER: P331787

CATALOG NUMBER: S122RDIW-S485D435U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	828.2	827.6	826.9	826.2	825.6	824.5	823.1	821.6	820.1	818.7	820.0
5°	825.2	824.4	823.6	822.8	821.9	820.4	818.3	816.1	814.0	811.8	813.3
7.5°	816.7	815.7	814.7	813.6	812.6	810.8	808.3	805.8	803.3	800.8	801.2
10°	809.6	808.4	807.2	806.1	804.9	802.7	799.4	796.0	792.7	789.4	788.9
12.5°	800.6	799.2	797.7	796.3	794.9	792.1	787.8	783.6	779.3	775.1	774.2
15°	784.9	783.1	781.3	779.4	777.6	773.9	768.2	762.6	757.0	751.3	748.2
17.5°	765.7	762.9	760.1	757.3	754.5	749.5	742.3	735.0	727.8	720.5	716.8
20°	751.3	748.0	744.7	741.4	738.0	732.2	723.9	715.6	707.3	699.0	694.9
22.5°	735.8	732.1	728.3	724.6	720.9	714.4	705.0	695.6	686.3	676.9	671.6
25°	712.5	707.2	701.9	696.5	691.2	683.1	672.1	661.2	650.2	639.3	632.5
27.5°	684.4	678.6	672.8	667.1	661.3	652.2	639.9	627.5	615.2	602.8	594.9
30°	664.7	658.4	652.1	645.8	639.5	629.7	616.4	603.1	589.8	576.6	568.1
32.5°	645.6	638.2	630.8	623.5	616.1	605.6	592.1	578.5	565.0	551.5	541.8
35°	613.9	605.4	597.0	588.5	580.0	568.5	553.9	539.3	524.7	510.1	499.6
37.5°	582.2	572.9	563.6	554.3	545.1	532.6	517.1	501.5	485.9	470.4	458.8
40°	560.1	550.2	540.2	530.3	520.3	507.3	491.2	475.1	459.0	442.9	431.1
42.5°	537.4	526.9	516.4	506.0	495.5	481.9	465.3	448.6	432.0	415.4	403.2
45°	501.9	490.8	479.6	468.5	457.4	443.1	425.7	408.3	390.8	373.4	361.6
47.5°	467.2	455.4	443.7	431.9	420.1	405.2	387.2	369.2	351.2	333.2	321.5
50°	442.1	430.3	418.6	406.8	395.0	380.0	361.7	343.5	325.2	306.9	295.5
52.5°	417.6	405.3	393.0	380.7	368.4	353.3	335.4	317.6	299.7	281.9	270.8
55°	381.6	368.7	355.7	342.8	329.9	314.4	296.5	278.6	260.6	242.7	232.8
57.5°	344.7	331.5	318.2	304.9	291.6	276.4	259.2	241.9	224.7	207.5	198.3
60°	319.6	306.4	293.1	279.8	266.5	251.4	234.3	217.2	200.1	183.0	174.5
62.5°	295.1	281.9	268.6	255.3	242.0	227.3	211.0	194.7	178.4	162.1	154.0
65°	257.7	244.2	230.8	217.3	203.9	189.7	174.8	159.8	144.9	129.9	124.3
67.5°	221.5	208.2	194.8	181.5	168.1	154.7	141.3	127.9	114.4	101.0	98.4
70°	196.4	183.5	170.5	157.6	144.6	132.4	121.0	109.5	98.1	86.6	85.0
72.5°	172.5	160.1	147.7	135.3	122.9	112.1	102.9	93.7	84.5	75.3	73.9
75°	137.4	125.8	114.2	102.6	90.9	82.3	76.7	71.0	65.4	59.7	58.6
77.5°	102.9	92.7	82.5	72.3	62.2	55.7	53.0	50.3	47.5	44.8	44.1
80°	81.4	72.9	64.5	56.0	47.5	42.5	40.8	39.2	37.5	35.8	35.2
82.5°	61.7	55.1	48.5	41.9	35.3	31.4	30.3	29.1	28.0	26.9	26.5
85°	32.1	28.6	25.1	21.7	18.2	16.2	15.7	15.2	14.7	14.2	14.2
87.5°	9.6	8.8	7.9	7.1	6.2	5.9	6.0	6.2	6.3	6.5	6.5
90°	0.4	1.5	2.5	3.6	4.6	5.5	6.3	7.0	7.8	8.5	9.0
92.5°	8.6	8.5	8.4	8.3	8.3	8.4	8.8	9.2	9.5	9.9	10.2
95°	27.8	24.6	21.5	18.4	15.2	14.0	14.7	15.3	16.0	16.7	17.1
97.5°	55.1	46.3	37.5	28.6	19.8	16.2	17.7	19.2	20.8	22.3	22.7
100°	75.7	62.6	49.6	36.6	23.6	17.9	19.5	21.1	22.7	24.4	25.1
102.5°	98.2	95.5	92.7	90.0	87.2	79.1	65.6	52.1	38.6	25.0	26.0
105°	129.9	132.8	135.6	138.5	141.3	129.8	103.9	77.9	52.0	26.1	27.1
107.5°	166.1	168.4	170.7	173.0	175.3	160.9	129.8	98.7	67.6	36.5	35.4
110°	189.3	191.3	193.3	195.3	197.3	184.6	157.1	129.7	102.2	74.8	65.3



TEST NUMBER: P331787

CATALOG NUMBER: S122RDIW-S485D435U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	211.2	213.0	214.8	216.5	218.3	215.8	209.0	202.2	195.4	188.7	154.0
115°	245.8	247.4	249.0	250.6	252.2	254.2	256.6	259.0	261.3	263.7	219.7
117.5°	276.6	278.4	280.2	282.0	283.8	285.6	287.2	288.8	290.5	292.1	281.5
120°	299.2	300.6	302.0	303.5	304.9	306.5	308.2	309.9	311.6	313.3	314.4
122.5°	318.3	319.8	321.3	322.8	324.3	326.0	327.9	329.7	331.6	333.5	334.2
125°	347.5	348.7	350.0	351.2	352.4	353.9	355.8	357.6	359.4	361.2	361.8
127.5°	373.9	375.3	376.6	378.0	379.4	380.7	382.1	383.4	384.8	386.1	387.1
130°	390.7	392.2	393.7	395.2	396.7	398.0	399.1	400.1	401.2	402.2	403.2
132.5°	407.8	409.0	410.3	411.6	412.9	414.1	415.1	416.2	417.2	418.3	419.2
135°	430.0	431.5	433.0	434.5	436.1	437.2	438.1	439.0	439.8	440.7	441.6
137.5°	452.5	453.5	454.6	455.7	456.7	457.7	458.7	459.7	460.6	461.6	462.5
140°	467.2	467.9	468.7	469.4	470.2	471.1	472.2	473.2	474.2	475.3	476.1
142.5°	479.5	480.2	480.8	481.5	482.2	483.2	484.3	485.5	486.7	487.9	488.7
145°	498.8	498.7	498.6	498.5	498.4	499.2	500.8	502.4	504.0	505.6	506.3
147.5°	515.6	515.3	514.9	514.6	514.2	514.8	516.4	518.0	519.6	521.2	521.7
150°	526.6	525.9	525.2	524.6	523.9	524.3	525.9	527.4	528.9	530.4	531.0
152.5°	535.8	535.1	534.3	533.6	532.8	533.2	534.6	536.1	537.5	539.0	539.5
155°	549.2	548.4	547.5	546.7	545.8	546.0	547.1	548.2	549.4	550.5	551.1
157.5°	559.7	559.0	558.3	557.6	556.9	556.9	557.7	558.5	559.3	560.1	560.7
160°	565.9	565.3	564.8	564.2	563.6	563.6	564.2	564.8	565.3	565.9	566.5
162.5°	571.4	570.8	570.2	569.7	569.1	569.1	569.5	570.0	570.5	571.0	571.7
165°	578.7	578.2	577.6	577.0	576.4	576.3	576.6	576.9	577.2	577.4	578.1
167.5°	584.2	583.6	583.1	582.5	581.9	581.8	582.0	582.3	582.6	582.8	583.5
170°	587.3	586.7	586.1	585.6	585.0	584.8	585.0	585.2	585.4	585.6	586.2
172.5°	589.3	588.8	588.2	587.6	587.0	586.9	587.0	587.2	587.4	587.6	588.3
175°	592.0	591.3	590.6	590.0	589.3	589.1	589.3	589.5	589.6	589.8	590.5
177.5°	592.4	591.9	591.3	590.8	590.3	590.0	590.1	590.2	590.3	590.3	590.9
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331787

CATALOG NUMBER: S122RDIW-S485D435U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	821.3	822.7	824.0	824.5	824.3	824.0	823.7	823.5
5°	814.8	816.3	817.8	818.3	817.8	817.3	816.8	816.3
7.5°	801.6	802.0	802.5	802.3	801.4	800.5	799.7	798.8
10°	788.4	787.9	787.4	786.7	785.7	784.7	783.7	782.7
12.5°	773.3	772.4	771.5	770.2	768.5	766.9	765.2	763.6
15°	745.0	741.9	738.7	736.3	734.6	733.0	731.3	729.7
17.5°	713.0	709.3	705.5	702.2	699.4	696.5	693.7	690.8
20°	690.7	686.6	682.4	678.5	674.9	671.2	667.6	663.9
22.5°	666.2	660.9	655.6	651.5	648.8	646.1	643.4	640.6
25°	625.7	618.9	612.1	607.4	604.9	602.4	600.0	597.5
27.5°	587.0	579.0	571.1	565.2	561.2	557.3	553.3	549.4
30°	559.6	551.2	542.7	536.2	531.7	527.3	522.8	518.3
32.5°	532.1	522.5	512.8	505.9	501.7	497.5	493.2	489.0
35°	489.2	478.7	468.3	461.2	457.6	453.9	450.3	446.6
37.5°	447.3	435.8	424.3	416.4	412.3	408.1	403.9	399.7
40°	419.3	407.5	395.7	387.7	383.4	379.1	374.7	370.4
42.5°	391.0	378.8	366.7	358.5	354.3	350.1	345.9	341.7
45°	349.8	338.1	326.3	318.4	314.4	310.4	306.4	302.5
47.5°	309.8	298.1	286.4	278.7	275.1	271.5	267.8	264.2
50°	284.0	272.6	261.1	253.7	250.2	246.7	243.2	239.7
52.5°	259.7	248.7	237.6	230.5	227.3	224.1	220.8	217.6
55°	222.8	212.8	202.9	196.3	193.2	190.0	186.9	183.7
57.5°	189.2	180.1	171.0	165.1	162.4	159.8	157.1	154.4
60°	166.0	157.6	149.1	143.6	140.9	138.2	135.6	132.9
62.5°	145.9	137.9	129.8	125.0	123.4	121.8	120.2	118.6
65°	118.7	113.0	107.4	104.3	103.8	103.3	102.8	102.3
67.5°	95.8	93.2	90.6	89.1	88.5	88.0	87.5	86.9
70°	83.3	81.7	80.0	78.8	78.2	77.5	76.8	76.2
72.5°	72.5	71.1	69.7	68.8	68.4	68.0	67.6	67.2
75°	57.4	56.3	55.1	54.4	54.3	54.1	53.9	53.8
77.5°	43.5	42.8	42.2	41.7	41.4	41.2	40.9	40.6
80°	34.5	33.9	33.2	32.9	32.9	32.9	32.9	32.9
82.5°	26.1	25.7	25.3	25.1	25.1	25.1	25.1	25.1
85°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2
87.5°	6.4	6.4	6.3	6.3	6.4	6.4	6.5	6.5
90°	9.5	10.0	10.4	10.8	11.0	11.2	11.4	11.5
92.5°	10.4	10.7	10.9	11.1	11.2	11.3	11.4	11.5
95°	17.6	18.1	18.6	18.8	18.7	18.6	18.5	18.4
97.5°	23.1	23.5	23.8	24.1	24.2	24.3	24.4	24.5
100°	25.9	26.6	27.4	27.9	28.1	28.3	28.4	28.6
102.5°	27.0	28.0	29.0	29.6	29.9	30.2	30.4	30.7
105°	28.2	29.2	30.3	31.0	31.3	31.7	32.1	32.5
107.5°	34.4	33.3	32.2	31.9	32.3	32.7	33.0	33.4
110°	55.8	46.3	36.8	32.2	32.6	33.0	33.4	33.8



TEST NUMBER: P331787

CATALOG NUMBER: S122RDIW-S485D435U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	119.4	84.7	50.1	32.9	33.2	33.5	33.8	34.1
115°	175.8	131.8	87.8	62.4	55.6	48.7	41.9	35.0
117.5°	270.8	260.2	249.5	233.0	210.5	188.0	165.6	143.1
120°	315.6	316.7	317.9	312.0	299.2	286.4	273.5	260.7
122.5°	334.8	335.5	336.2	335.3	332.8	330.3	327.8	325.3
125°	362.5	363.2	363.8	364.3	364.6	364.9	365.2	365.4
127.5°	388.1	389.0	390.0	390.5	390.6	390.6	390.7	390.7
130°	404.3	405.3	406.4	406.9	406.8	406.7	406.6	406.5
132.5°	420.1	420.9	421.8	422.2	422.1	422.0	422.0	421.9
135°	442.6	443.5	444.5	444.8	444.7	444.5	444.3	444.1
137.5°	463.5	464.4	465.3	465.6	465.3	465.0	464.7	464.3
140°	477.0	477.9	478.7	478.9	478.4	477.9	477.5	477.0
142.5°	489.5	490.3	491.1	491.2	490.7	490.3	489.8	489.3
145°	507.0	507.6	508.3	508.4	507.9	507.4	507.0	506.5
147.5°	522.2	522.7	523.2	523.2	522.8	522.4	522.0	521.6
150°	531.6	532.1	532.7	532.8	532.3	531.8	531.3	530.9
152.5°	540.1	540.7	541.3	541.2	540.6	540.0	539.3	538.7
155°	551.7	552.2	552.8	552.7	551.9	551.2	550.4	549.7
157.5°	561.4	562.0	562.7	562.6	561.9	561.1	560.4	559.7
160°	567.0	567.6	568.2	568.1	567.5	566.8	566.1	565.5
162.5°	572.3	573.0	573.6	573.5	572.7	571.9	571.1	570.3
165°	578.8	579.4	580.1	580.1	579.4	578.8	578.1	577.4
167.5°	584.2	584.8	585.5	585.4	584.5	583.7	582.8	582.0
170°	586.9	587.6	588.2	588.1	587.3	586.4	585.6	584.7
172.5°	588.9	589.6	590.3	590.2	589.3	588.5	587.6	586.8
175°	591.2	591.8	592.5	592.4	591.4	590.5	589.5	588.6
177.5°	591.4	591.9	592.5	592.4	591.7	591.0	590.3	589.7
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7

(END OF REPORT)