

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331820-840

Luminaire Tested: **S122RDIW-S675D1240U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331820-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D1240U840-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6687.9 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331820-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331820-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	95	91	87	84	86	82	79	76	66	64	62	51	50	49	38	37	36	30
2	87	80	74	69	78	72	67	63	58	55	52	46	43	41	34	32	31	26
3	79	70	63	58	71	64	58	53	52	47	44	41	38	35	30	28	27	22
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23	19
5	67	56	48	42	60	51	44	39	41	36	33	33	29	27	25	22	21	17
6	61	50	42	37	55	46	39	34	37	32	29	30	26	23	23	20	18	15
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	21	18	16	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15	12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	23	41	31	25	21	26	21	18	21	18	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18392	18392	18392
5°	18462	18162	18263
10°	18321	17864	17713
15°	18111	17336	16836
20°	17819	16579	15747
25°	17521	15720	14694
30°	17107	14838	13340
35°	16703	13878	12151
40°	16297	12886	10777
45°	15819	11768	9533
50°	15330	10643	8312
55°	14829	9433	7139
60°	14247	8157	5926
65°	13589	6854	5398
70°	12798	5646	4961
75°	11834	5147	4629
80°	10451	4603	4212
85°	8207	3631	3631



TEST NUMBER: P331820-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.6	1.6
10°-20°	292.8	4.4
20°-30°	411.1	6.1
30°-40°	448.3	6.7
40°-50°	412.2	6.2
50°-60°	323.8	4.8
60°-70°	211.1	3.2
70°-80°	108.8	1.6
80°-90°	34.4	0.5
90°-100°	98.3	1.5
100°-110°	305.4	4.6
110°-120°	522.0	7.8
120°-130°	686.4	10.3
130°-140°	770.4	11.5
140°-150°	755.4	11.3
150°-160°	633.6	9.5
160°-170°	420.3	6.3
170°-180°	146.9	2.2
0°-30°	810.5	12.1
0°-40°	1258.9	18.8
0°-60°	1994.8	29.8
0°-90°	2349.2	35.1
90°-120°	925.7	13.8
90°-150°	3138.0	46.9
90°-180°	4339.0	64.9
0°-180°	6687.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1139	1139	1139	1139	1139	
5°	1139	1134	1121	1129	1127	108
15°	1084	1071	1037	1018	1007	305
25°	984	949	882	842	825	452
35°	847	793	704	642	616	530
45°	693	622	515	445	418	535
55°	527	445	335	276	254	471
65°	356	272	179	146	141	352
75°	190	120	82	76	74	201
85°	44	24	20	20	20	52
90°	1	18	46	43	44	5
95°	68	81	84	84	81	78
105°	282	285	288	291	291	297
115°	524	531	529	528	524	518
125°	762	773	770	766	765	681
135°	986	1000	1003	1002	998	761
145°	1197	1206	1214	1215	1210	747
155°	1368	1372	1376	1382	1379	630
165°	1489	1488	1488	1496	1490	420
175°	1549	1545	1542	1551	1544	147
180°	1552	1552	1552	1552	1552	



TEST NUMBER: P331820-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1
2.5°	1143.3	1142.4	1141.5	1140.5	1139.6	1138.1	1136.1	1134.1	1132.2	1130.1	1132.0
5°	1139.1	1138.0	1136.9	1135.7	1134.6	1132.6	1129.5	1126.6	1123.6	1120.6	1122.7
7.5°	1127.4	1126.0	1124.6	1123.2	1121.8	1119.2	1115.8	1112.4	1108.8	1105.4	1105.9
10°	1117.5	1115.9	1114.3	1112.7	1111.1	1108.0	1103.4	1098.8	1094.3	1089.6	1089.0
12.5°	1105.1	1103.2	1101.2	1099.2	1097.2	1093.4	1087.5	1081.7	1075.7	1069.9	1068.6
15°	1083.5	1081.0	1078.4	1075.9	1073.4	1068.2	1060.5	1052.7	1044.9	1037.1	1032.8
17.5°	1056.9	1053.1	1049.2	1045.3	1041.5	1034.6	1024.6	1014.6	1004.6	994.6	989.5
20°	1037.1	1032.5	1027.9	1023.4	1018.8	1010.8	999.3	987.8	976.4	964.9	959.2
22.5°	1015.6	1010.6	1005.4	1000.3	995.1	986.1	973.2	960.3	947.4	934.4	927.1
25°	983.5	976.1	968.9	961.5	954.2	942.9	927.9	912.7	897.6	882.4	873.0
27.5°	944.7	936.8	928.8	920.8	912.8	900.3	883.3	866.3	849.2	832.1	821.2
30°	917.6	908.8	900.1	891.4	882.7	869.2	850.8	832.5	814.2	795.9	784.2
32.5°	891.1	880.9	870.8	860.6	850.4	836.0	817.3	798.6	779.9	761.2	747.9
35°	847.4	835.8	824.0	812.3	800.7	784.8	764.6	744.5	724.3	704.1	689.6
37.5°	803.8	790.8	778.0	765.2	752.3	735.2	713.8	692.3	670.8	649.2	633.4
40°	773.2	759.4	745.7	732.0	718.2	700.2	678.0	655.8	633.6	611.4	595.1
42.5°	741.8	727.4	712.9	698.4	684.0	665.2	642.3	619.4	596.3	573.4	556.5
45°	692.8	677.4	662.1	646.7	631.4	611.7	587.6	563.6	539.5	515.4	499.2
47.5°	644.9	628.6	612.4	596.1	579.9	559.4	534.5	509.7	484.8	460.0	443.8
50°	610.3	594.0	577.7	561.5	545.2	524.5	499.3	474.1	448.9	423.7	407.9
52.5°	576.5	559.5	542.5	525.5	508.5	487.7	463.0	438.4	413.7	389.1	373.9
55°	526.8	509.0	491.1	473.2	455.3	434.0	409.3	384.6	359.8	335.1	321.3
57.5°	475.8	457.6	439.2	420.9	402.5	381.5	357.7	334.0	310.1	286.4	273.8
60°	441.2	422.9	404.6	386.3	367.9	347.0	323.4	299.7	276.2	252.6	240.9
62.5°	407.4	389.1	370.7	352.4	334.1	313.7	291.2	268.7	246.2	223.7	212.6
65°	355.7	337.1	318.5	300.0	281.4	261.9	241.3	220.7	200.0	179.4	171.6
67.5°	305.8	287.3	268.9	250.5	232.1	213.6	195.0	176.5	157.9	139.4	135.8
70°	271.1	253.3	235.4	217.5	199.7	182.8	167.0	151.2	135.4	119.6	117.2
72.5°	238.1	221.0	203.9	186.7	169.6	154.7	142.0	129.3	116.6	103.9	102.0
75°	189.7	173.7	157.6	141.6	125.5	113.6	105.8	98.1	90.3	82.5	80.9
77.5°	142.1	127.9	113.9	99.9	85.8	76.9	73.1	69.4	65.6	61.9	60.9
80°	112.4	100.7	89.0	77.4	65.6	58.7	56.4	54.0	51.8	49.5	48.6
82.5°	85.1	76.0	67.0	57.8	48.7	43.3	41.8	40.2	38.7	37.2	36.6
85°	44.3	39.5	34.7	29.9	25.0	22.3	21.6	21.0	20.3	19.6	19.6
87.5°	13.4	12.7	11.9	11.1	10.4	10.6	11.9	13.2	14.4	15.8	15.5
90°	1.3	4.8	8.3	11.8	15.2	20.2	26.7	33.0	39.4	45.8	45.2
92.5°	23.3	25.9	28.5	31.0	33.5	35.5	37.1	38.6	40.1	41.6	41.7
95°	68.1	71.0	73.9	76.9	79.8	81.5	82.1	82.6	83.2	83.8	83.8
97.5°	124.4	126.9	129.6	132.1	134.6	136.4	137.5	138.7	139.8	140.9	140.9
100°	166.3	168.6	171.0	173.3	175.6	177.2	178.0	178.9	179.9	180.7	180.7
102.5°	210.3	212.2	214.0	215.9	217.7	219.2	220.4	221.5	222.6	223.7	223.9
105°	281.6	282.4	283.3	284.2	285.0	285.8	286.3	286.9	287.5	288.1	288.6
107.5°	353.3	354.6	355.9	357.1	358.4	359.0	359.0	359.0	359.0	359.0	359.3
110°	399.4	401.1	402.8	404.7	406.4	407.3	407.3	407.3	407.3	407.3	407.3



TEST NUMBER: P331820-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	449.7	451.4	453.1	454.9	456.7	457.4	457.2	457.0	456.7	456.5	455.8
115°	523.8	525.5	527.3	529.0	530.8	531.3	530.8	530.2	529.6	529.0	528.8
117.5°	597.6	600.0	602.3	604.6	606.9	607.3	605.6	604.0	602.4	600.8	600.1
120°	646.8	649.1	651.6	653.9	656.2	656.2	653.9	651.6	649.1	646.8	646.8
122.5°	691.9	694.7	697.5	700.2	703.1	703.7	702.1	700.4	698.7	697.1	696.4
125°	762.0	764.7	767.3	769.9	772.5	773.5	772.5	771.7	770.8	769.9	769.1
127.5°	830.4	833.7	837.1	840.4	843.7	844.9	843.8	842.7	841.7	840.6	839.6
130°	873.4	877.2	881.0	884.7	888.5	890.1	889.6	889.0	888.4	887.8	887.2
132.5°	921.6	924.6	927.8	930.8	933.9	935.5	935.6	935.7	935.8	935.9	934.7
135°	986.0	989.2	992.4	995.6	998.9	1000.7	1001.3	1001.9	1002.5	1003.0	1002.7
137.5°	1053.8	1056.4	1059.0	1061.7	1064.3	1066.0	1066.7	1067.5	1068.2	1069.0	1068.8
140°	1094.7	1097.3	1099.9	1102.6	1105.2	1107.2	1108.6	1110.1	1111.6	1113.0	1113.0
142.5°	1136.6	1139.2	1141.9	1144.5	1147.1	1148.8	1149.8	1150.8	1151.9	1152.9	1153.1
145°	1196.8	1198.9	1200.9	1203.0	1205.0	1206.9	1208.6	1210.3	1212.1	1213.9	1214.2
147.5°	1250.5	1252.9	1255.4	1257.9	1260.3	1262.1	1263.2	1264.5	1265.6	1266.8	1267.4
150°	1287.2	1288.9	1290.7	1292.4	1294.1	1295.7	1296.8	1298.0	1299.1	1300.3	1301.1
152.5°	1319.7	1321.4	1323.1	1324.8	1326.7	1328.2	1329.6	1331.0	1332.4	1333.8	1334.9
155°	1368.4	1369.3	1370.1	1371.0	1371.9	1372.7	1373.6	1374.4	1375.3	1376.2	1377.7
157.5°	1410.0	1410.6	1411.2	1411.8	1412.3	1412.9	1413.4	1413.9	1414.4	1415.0	1416.9
160°	1435.1	1435.7	1436.3	1436.9	1437.4	1437.9	1438.1	1438.5	1438.8	1439.1	1440.8
162.5°	1458.1	1458.3	1458.4	1458.5	1458.6	1458.9	1459.2	1459.5	1459.8	1460.1	1462.0
165°	1488.8	1488.5	1488.2	1487.9	1487.6	1487.5	1487.5	1487.5	1487.5	1487.5	1489.6
167.5°	1514.5	1513.6	1512.8	1511.9	1511.0	1510.6	1510.5	1510.5	1510.4	1510.3	1512.4
170°	1528.1	1527.2	1526.4	1525.5	1524.6	1524.1	1523.8	1523.5	1523.2	1522.9	1524.9
172.5°	1537.5	1536.7	1535.8	1534.9	1534.1	1533.5	1533.2	1532.9	1532.6	1532.3	1534.4
175°	1549.0	1548.2	1547.3	1546.4	1545.6	1544.9	1544.3	1543.7	1543.1	1542.5	1544.6
177.5°	1553.8	1553.1	1552.4	1551.7	1551.0	1550.4	1549.9	1549.4	1549.0	1548.5	1549.9
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331820-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1
2.5°	1133.8	1135.6	1137.4	1138.1	1137.8	1137.4	1137.1	1136.7
5°	1124.7	1126.8	1128.8	1129.5	1128.8	1128.1	1127.5	1126.8
7.5°	1106.5	1107.1	1107.7	1107.4	1106.2	1105.1	1103.9	1102.7
10°	1088.3	1087.6	1086.9	1085.9	1084.5	1083.2	1081.8	1080.4
12.5°	1067.4	1066.2	1064.9	1063.2	1060.9	1058.6	1056.3	1054.0
15°	1028.4	1024.0	1019.7	1016.3	1014.1	1011.8	1009.5	1007.2
17.5°	984.3	979.1	973.9	969.4	965.4	961.5	957.6	953.6
20°	953.5	947.8	942.0	936.6	931.6	926.6	921.5	916.5
22.5°	919.7	912.3	904.9	899.4	895.5	891.8	888.1	884.3
25°	863.6	854.2	844.9	838.5	835.1	831.6	828.2	824.8
27.5°	810.2	799.3	788.4	780.1	774.7	769.2	763.8	758.3
30°	772.5	760.8	749.1	740.2	734.0	727.8	721.6	715.5
32.5°	734.6	721.2	707.9	698.3	692.5	686.7	680.9	675.1
35°	675.3	660.9	646.4	636.6	631.6	626.5	621.6	616.5
37.5°	617.4	601.6	585.7	574.8	569.1	563.3	557.5	551.8
40°	578.8	562.5	546.2	535.1	529.2	523.2	517.3	511.3
42.5°	539.8	522.9	506.1	494.8	489.1	483.3	477.6	471.7
45°	482.9	466.7	450.4	439.5	434.0	428.5	423.0	417.5
47.5°	427.7	411.5	395.3	384.8	379.7	374.8	369.7	364.8
50°	392.1	376.3	360.5	350.1	345.4	340.5	335.8	330.9
52.5°	358.6	343.3	328.0	318.2	313.8	309.3	304.9	300.4
55°	307.6	293.8	280.0	271.0	266.7	262.3	257.9	253.6
57.5°	261.2	248.6	236.0	227.8	224.2	220.6	216.8	213.2
60°	229.2	217.5	205.8	198.1	194.5	190.9	187.1	183.5
62.5°	201.5	190.3	179.2	172.5	170.3	168.1	165.9	163.7
65°	163.8	156.0	148.2	144.0	143.3	142.6	141.9	141.3
67.5°	132.2	128.7	125.1	122.9	122.2	121.5	120.8	120.0
70°	115.0	112.7	110.4	108.9	107.9	106.9	106.0	105.1
72.5°	100.1	98.2	96.2	95.0	94.4	93.9	93.3	92.8
75°	79.3	77.7	76.0	75.1	74.9	74.7	74.4	74.2
77.5°	60.0	59.1	58.2	57.6	57.2	56.9	56.5	56.0
80°	47.7	46.8	45.8	45.3	45.3	45.3	45.3	45.3
82.5°	36.1	35.4	34.9	34.6	34.6	34.6	34.6	34.6
85°	19.6	19.6	19.6	19.6	19.6	19.6	19.6	19.6
87.5°	15.1	14.8	14.5	14.4	14.5	14.5	14.6	14.6
90°	44.6	44.1	43.5	43.3	43.6	43.9	44.2	44.5
92.5°	41.9	42.0	42.1	42.2	42.2	42.3	42.4	42.4
95°	83.8	83.8	83.8	83.5	82.9	82.3	81.8	81.2
97.5°	140.9	140.9	140.9	140.9	140.8	140.8	140.7	140.7
100°	180.7	180.7	180.7	180.6	180.3	180.0	179.7	179.4
102.5°	224.1	224.4	224.6	224.6	224.3	224.0	223.7	223.4
105°	289.2	289.8	290.4	290.7	290.7	290.7	290.7	290.7
107.5°	359.5	359.7	360.0	359.4	358.1	356.8	355.4	354.1
110°	407.3	407.3	407.3	406.8	406.0	405.1	404.1	403.3



TEST NUMBER: P331820-840

CATALOG NUMBER: S122RDIW-S675D1240U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	455.0	454.3	453.6	453.0	452.3	451.7	451.1	450.4
115°	528.5	528.2	527.9	527.3	526.4	525.5	524.6	523.8
117.5°	599.4	598.6	597.9	597.2	596.3	595.4	594.6	593.7
120°	646.8	646.8	646.8	646.4	645.5	644.7	643.8	643.0
122.5°	695.8	695.1	694.4	693.7	693.1	692.4	691.8	691.2
125°	768.2	767.3	766.5	765.9	765.6	765.3	765.0	764.7
127.5°	838.6	837.5	836.5	835.5	834.6	833.6	832.7	831.7
130°	886.7	886.1	885.4	884.6	883.4	882.3	881.1	879.9
132.5°	933.4	932.1	930.9	929.8	928.9	927.9	927.0	926.0
135°	1002.5	1002.2	1001.9	1001.3	1000.4	999.6	998.7	997.7
137.5°	1068.5	1068.3	1068.1	1067.4	1066.2	1065.1	1063.9	1062.8
140°	1113.0	1113.0	1113.0	1112.5	1111.3	1110.1	1108.9	1107.8
142.5°	1153.3	1153.6	1153.8	1153.3	1152.2	1150.9	1149.8	1148.6
145°	1214.5	1214.8	1215.0	1214.6	1213.5	1212.2	1211.1	1209.9
147.5°	1268.0	1268.7	1269.3	1269.1	1268.0	1266.9	1265.8	1264.7
150°	1302.0	1302.9	1303.7	1303.7	1302.9	1302.0	1301.1	1300.3
152.5°	1336.1	1337.1	1338.2	1338.2	1337.1	1336.1	1334.9	1333.8
155°	1379.2	1380.6	1382.0	1382.3	1381.5	1380.6	1379.7	1378.9
157.5°	1419.0	1420.9	1422.9	1423.2	1421.8	1420.4	1419.0	1417.5
160°	1442.6	1444.3	1446.0	1446.3	1445.2	1444.0	1442.9	1441.7
162.5°	1464.0	1465.9	1467.9	1468.2	1466.8	1465.4	1464.0	1462.7
165°	1491.6	1493.6	1495.7	1495.9	1494.5	1493.1	1491.6	1490.2
167.5°	1514.4	1516.4	1518.4	1518.7	1517.2	1515.7	1514.2	1512.7
170°	1526.9	1528.9	1531.1	1531.2	1529.4	1527.7	1525.9	1524.2
172.5°	1536.4	1538.4	1540.4	1540.5	1538.8	1537.1	1535.4	1533.6
175°	1546.6	1548.6	1550.6	1550.8	1549.0	1547.3	1545.6	1543.8
177.5°	1551.4	1552.8	1554.1	1554.1	1552.8	1551.4	1549.9	1548.5
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7

(END OF REPORT)