

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331791

Luminaire Tested: **S122RDIW-S485D710U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331791
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D710U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4534.9 lumens
Efficiency: N/A
Efficacy: 120.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331791

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331791

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37								
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32								
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33	28								
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	24								
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21								
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18								
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16								
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15								
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	16	13								
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14	12								
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13324	13324	13324
5°	13374	13157	13230
10°	13273	12942	12832
15°	13120	12558	12197
20°	12909	12010	11407
25°	12693	11389	10644
30°	12392	10750	9663
35°	12100	10054	8803
40°	11805	9335	7807
45°	11460	8526	6907
50°	11105	7709	6021
55°	10742	6832	5171
60°	10320	5909	4292
65°	9845	4963	3908
70°	9272	4088	3597
75°	8571	3724	3356
80°	7569	3329	3059
85°	5947	2631	2631



TEST NUMBER: P331791

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.2	1.7
10°-20°	212.1	4.7
20°-30°	297.8	6.6
30°-40°	324.8	7.2
40°-50°	298.6	6.6
50°-60°	234.5	5.2
60°-70°	152.9	3.4
70°-80°	78.8	1.7
80°-90°	22.8	0.5
90°-100°	32.3	0.7
100°-110°	118.3	2.6
110°-120°	316.3	7.0
120°-130°	522.2	11.5
130°-140°	555.4	12.2
140°-150°	516.2	11.4
150°-160°	415.0	9.2
160°-170°	267.4	5.9
170°-180°	92.1	2.0
0°-30°	587.2	12.9
0°-40°	912.0	20.1
0°-60°	1445.1	31.9
0°-90°	1699.7	37.5
90°-120°	467.0	10.3
90°-150°	2060.7	45.4
90°-180°	2835.0	62.5
0°-180°	4534.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	825	825	825	825	825	
5°	825	821	812	818	816	78
15°	785	776	751	738	730	221
25°	712	687	639	610	598	327
35°	614	574	510	465	447	384
45°	502	450	373	322	302	387
55°	382	322	243	200	184	341
65°	258	197	130	106	102	255
75°	137	87	60	55	54	145
85°	32	17	14	14	14	38
90°	1	8	14	17	19	3
95°	46	24	27	31	30	56
105°	213	222	43	50	53	227
115°	402	415	432	123	57	396
125°	569	578	592	596	598	507
135°	704	715	722	728	727	544
145°	817	817	828	833	830	511
155°	900	894	902	905	900	414
165°	948	944	946	950	946	268
175°	970	965	966	970	964	92
180°	968	968	968	968	968	



TEST NUMBER: P331791

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	828.2	827.6	826.9	826.2	825.6	824.5	823.1	821.6	820.1	818.7	820.0
5°	825.2	824.4	823.6	822.8	821.9	820.4	818.3	816.1	814.0	811.8	813.3
7.5°	816.7	815.7	814.7	813.6	812.6	810.8	808.3	805.8	803.3	800.8	801.2
10°	809.6	808.4	807.2	806.1	804.9	802.7	799.4	796.0	792.7	789.4	788.9
12.5°	800.6	799.2	797.7	796.3	794.9	792.1	787.8	783.6	779.3	775.1	774.2
15°	784.9	783.1	781.3	779.4	777.6	773.9	768.2	762.6	757.0	751.3	748.2
17.5°	765.7	762.9	760.1	757.3	754.5	749.5	742.3	735.0	727.8	720.5	716.8
20°	751.3	748.0	744.7	741.4	738.0	732.2	723.9	715.6	707.3	699.0	694.9
22.5°	735.8	732.1	728.3	724.6	720.9	714.4	705.0	695.6	686.3	676.9	671.6
25°	712.5	707.2	701.9	696.5	691.2	683.1	672.1	661.2	650.2	639.3	632.5
27.5°	684.4	678.6	672.8	667.1	661.3	652.2	639.9	627.5	615.2	602.8	594.9
30°	664.7	658.4	652.1	645.8	639.5	629.7	616.4	603.1	589.8	576.6	568.1
32.5°	645.6	638.2	630.8	623.5	616.1	605.6	592.1	578.5	565.0	551.5	541.8
35°	613.9	605.4	597.0	588.5	580.0	568.5	553.9	539.3	524.7	510.1	499.6
37.5°	582.2	572.9	563.6	554.3	545.1	532.6	517.1	501.5	485.9	470.4	458.8
40°	560.1	550.2	540.2	530.3	520.3	507.3	491.2	475.1	459.0	442.9	431.1
42.5°	537.4	526.9	516.4	506.0	495.5	481.9	465.3	448.6	432.0	415.4	403.2
45°	501.9	490.8	479.6	468.5	457.4	443.1	425.7	408.3	390.8	373.4	361.6
47.5°	467.2	455.4	443.7	431.9	420.1	405.2	387.2	369.2	351.2	333.2	321.5
50°	442.1	430.3	418.6	406.8	395.0	380.0	361.7	343.5	325.2	306.9	295.5
52.5°	417.6	405.3	393.0	380.7	368.4	353.3	335.4	317.6	299.7	281.9	270.8
55°	381.6	368.7	355.7	342.8	329.9	314.4	296.5	278.6	260.6	242.7	232.8
57.5°	344.7	331.5	318.2	304.9	291.6	276.4	259.2	241.9	224.7	207.5	198.3
60°	319.6	306.4	293.1	279.8	266.5	251.4	234.3	217.2	200.1	183.0	174.5
62.5°	295.1	281.9	268.6	255.3	242.0	227.3	211.0	194.7	178.4	162.1	154.0
65°	257.7	244.2	230.8	217.3	203.9	189.7	174.8	159.8	144.9	129.9	124.3
67.5°	221.5	208.2	194.8	181.5	168.1	154.7	141.3	127.9	114.4	101.0	98.4
70°	196.4	183.5	170.5	157.6	144.6	132.4	121.0	109.5	98.1	86.6	85.0
72.5°	172.5	160.1	147.7	135.3	122.9	112.1	102.9	93.7	84.5	75.3	73.9
75°	137.4	125.8	114.2	102.6	90.9	82.3	76.7	71.0	65.4	59.7	58.6
77.5°	102.9	92.7	82.5	72.3	62.2	55.7	53.0	50.3	47.5	44.8	44.1
80°	81.4	72.9	64.5	56.0	47.5	42.5	40.8	39.2	37.5	35.8	35.2
82.5°	61.7	55.1	48.5	41.9	35.3	31.4	30.3	29.1	28.0	26.9	26.5
85°	32.1	28.6	25.1	21.7	18.2	16.2	15.7	15.2	14.7	14.2	14.2
87.5°	9.7	9.0	8.3	7.5	6.8	6.6	6.8	7.1	7.3	7.6	7.6
90°	0.7	2.4	4.1	5.8	7.5	9.0	10.3	11.5	12.8	14.0	14.8
92.5°	14.1	14.0	13.8	13.7	13.5	13.8	14.4	15.0	15.6	16.2	16.6
95°	45.5	40.4	35.2	30.1	25.0	22.9	24.0	25.1	26.2	27.3	28.1
97.5°	90.3	75.8	61.4	46.9	32.4	26.5	29.0	31.5	34.0	36.5	37.2
100°	123.9	102.6	81.3	60.0	38.7	29.3	32.0	34.6	37.3	39.9	41.1
102.5°	160.9	156.4	151.8	147.3	142.8	129.5	107.4	85.3	63.1	41.0	42.6
105°	212.8	217.5	222.2	226.8	231.5	212.6	170.1	127.6	85.2	42.7	44.4
107.5°	272.0	275.8	279.6	283.3	287.1	263.5	212.6	161.7	110.7	59.8	58.0
110°	310.1	313.4	316.7	319.9	323.2	302.3	257.4	212.4	167.5	122.5	107.0



TEST NUMBER: P331791

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	346.0	348.9	351.8	354.6	357.5	353.4	342.3	331.2	320.1	309.0	252.3
115°	402.5	405.2	407.8	410.5	413.1	416.4	420.3	424.2	428.0	431.9	359.9
117.5°	453.1	456.0	459.0	461.9	464.9	467.7	470.4	473.1	475.7	478.4	461.0
120°	490.0	492.4	494.7	497.0	499.4	501.9	504.7	507.5	510.3	513.1	515.0
122.5°	521.4	523.9	526.3	528.8	531.2	534.0	537.0	540.1	543.1	546.2	547.3
125°	569.1	571.2	573.2	575.2	577.2	579.7	582.7	585.6	588.6	591.5	592.6
127.5°	612.4	614.6	616.9	619.1	621.4	623.6	625.8	628.0	630.2	632.4	634.0
130°	639.8	642.3	644.8	647.3	649.8	651.9	653.6	655.3	657.0	658.8	660.5
132.5°	667.9	670.0	672.1	674.2	676.3	678.2	679.9	681.6	683.4	685.1	686.5
135°	704.3	706.7	709.2	711.7	714.2	716.2	717.6	719.0	720.4	721.8	723.3
137.5°	741.1	742.8	744.6	746.3	748.0	749.7	751.3	752.9	754.5	756.1	757.6
140°	765.2	766.4	767.6	768.9	770.1	771.6	773.3	775.0	776.7	778.5	779.9
142.5°	785.3	786.4	787.6	788.7	789.8	791.3	793.3	795.3	797.2	799.2	800.5
145°	817.0	816.8	816.7	816.5	816.3	817.6	820.2	822.9	825.5	828.2	829.3
147.5°	844.5	844.0	843.4	842.8	842.2	843.2	845.8	848.4	851.0	853.6	854.5
150°	862.5	861.4	860.3	859.2	858.1	858.8	861.3	863.8	866.3	868.8	869.7
152.5°	877.6	876.4	875.2	873.9	872.7	873.3	875.7	878.0	880.4	882.8	883.7
155°	899.6	898.2	896.8	895.4	894.0	894.2	896.1	897.9	899.8	901.7	902.6
157.5°	916.8	915.6	914.4	913.2	912.1	912.1	913.4	914.7	916.0	917.3	918.4
160°	926.9	925.9	925.0	924.1	923.1	923.1	924.1	925.0	925.9	926.9	927.8
162.5°	935.8	934.9	934.0	933.0	932.1	932.0	932.8	933.7	934.5	935.3	936.3
165°	947.9	946.9	946.0	945.1	944.1	943.9	944.4	944.8	945.3	945.8	946.9
167.5°	956.8	955.9	955.0	954.0	953.1	952.9	953.3	953.7	954.2	954.6	955.7
170°	961.9	960.9	960.0	959.1	958.1	957.8	958.1	958.5	958.8	959.1	960.2
172.5°	965.2	964.3	963.4	962.4	961.5	961.2	961.5	961.8	962.1	962.4	963.5
175°	969.6	968.5	967.4	966.3	965.2	964.8	965.1	965.5	965.8	966.1	967.2
177.5°	970.3	969.4	968.5	967.7	966.8	966.4	966.5	966.7	966.8	966.9	967.8
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331791

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	821.3	822.7	824.0	824.5	824.3	824.0	823.7	823.5
5°	814.8	816.3	817.8	818.3	817.8	817.3	816.8	816.3
7.5°	801.6	802.0	802.5	802.3	801.4	800.5	799.7	798.8
10°	788.4	787.9	787.4	786.7	785.7	784.7	783.7	782.7
12.5°	773.3	772.4	771.5	770.2	768.5	766.9	765.2	763.6
15°	745.0	741.9	738.7	736.3	734.6	733.0	731.3	729.7
17.5°	713.0	709.3	705.5	702.2	699.4	696.5	693.7	690.8
20°	690.7	686.6	682.4	678.5	674.9	671.2	667.6	663.9
22.5°	666.2	660.9	655.6	651.5	648.8	646.1	643.4	640.6
25°	625.7	618.9	612.1	607.4	604.9	602.4	600.0	597.5
27.5°	587.0	579.0	571.1	565.2	561.2	557.3	553.3	549.4
30°	559.6	551.2	542.7	536.2	531.7	527.3	522.8	518.3
32.5°	532.1	522.5	512.8	505.9	501.7	497.5	493.2	489.0
35°	489.2	478.7	468.3	461.2	457.6	453.9	450.3	446.6
37.5°	447.3	435.8	424.3	416.4	412.3	408.1	403.9	399.7
40°	419.3	407.5	395.7	387.7	383.4	379.1	374.7	370.4
42.5°	391.0	378.8	366.7	358.5	354.3	350.1	345.9	341.7
45°	349.8	338.1	326.3	318.4	314.4	310.4	306.4	302.5
47.5°	309.8	298.1	286.4	278.7	275.1	271.5	267.8	264.2
50°	284.0	272.6	261.1	253.7	250.2	246.7	243.2	239.7
52.5°	259.7	248.7	237.6	230.5	227.3	224.1	220.8	217.6
55°	222.8	212.8	202.9	196.3	193.2	190.0	186.9	183.7
57.5°	189.2	180.1	171.0	165.1	162.4	159.8	157.1	154.4
60°	166.0	157.6	149.1	143.6	140.9	138.2	135.6	132.9
62.5°	145.9	137.9	129.8	125.0	123.4	121.8	120.2	118.6
65°	118.7	113.0	107.4	104.3	103.8	103.3	102.8	102.3
67.5°	95.8	93.2	90.6	89.1	88.5	88.0	87.5	86.9
70°	83.3	81.7	80.0	78.8	78.2	77.5	76.8	76.2
72.5°	72.5	71.1	69.7	68.8	68.4	68.0	67.6	67.2
75°	57.4	56.3	55.1	54.4	54.3	54.1	53.9	53.8
77.5°	43.5	42.8	42.2	41.7	41.4	41.2	40.9	40.6
80°	34.5	33.9	33.2	32.9	32.9	32.9	32.9	32.9
82.5°	26.1	25.7	25.3	25.1	25.1	25.1	25.1	25.1
85°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2
87.5°	7.6	7.6	7.7	7.7	7.8	7.8	7.9	8.0
90°	15.6	16.3	17.1	17.7	18.0	18.3	18.6	18.9
92.5°	17.1	17.5	17.9	18.2	18.3	18.5	18.7	18.9
95°	28.9	29.6	30.4	30.7	30.6	30.4	30.3	30.1
97.5°	37.8	38.4	39.0	39.4	39.6	39.8	40.0	40.2
100°	42.4	43.6	44.9	45.7	46.0	46.3	46.6	46.9
102.5°	44.3	45.9	47.5	48.5	49.0	49.4	49.8	50.3
105°	46.1	47.8	49.5	50.7	51.3	52.0	52.6	53.2
107.5°	56.3	54.6	52.8	52.3	52.9	53.5	54.1	54.7
110°	91.4	75.8	60.3	52.8	53.4	54.1	54.7	55.3



TEST NUMBER: P331791

CATALOG NUMBER: S122RDIW-S485D710U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	195.5	138.8	82.0	53.9	54.4	54.9	55.4	55.9
115°	287.9	215.8	143.8	102.2	91.0	79.8	68.6	57.4
117.5°	443.6	426.1	408.7	381.6	344.8	308.0	271.2	234.4
120°	516.9	518.7	520.6	511.0	490.0	469.0	448.0	427.0
122.5°	548.4	549.5	550.7	549.2	545.1	541.0	537.0	532.9
125°	593.7	594.8	595.9	596.7	597.1	597.6	598.1	598.5
127.5°	635.6	637.2	638.8	639.6	639.7	639.8	639.9	640.0
130°	662.2	663.9	665.6	666.4	666.2	666.1	665.9	665.8
132.5°	688.0	689.5	690.9	691.6	691.4	691.3	691.1	691.0
135°	724.9	726.4	728.0	728.6	728.3	728.0	727.7	727.4
137.5°	759.1	760.6	762.2	762.7	762.1	761.6	761.1	760.5
140°	781.3	782.7	784.1	784.4	783.6	782.8	782.0	781.3
142.5°	801.7	803.0	804.3	804.5	803.8	803.0	802.2	801.4
145°	830.3	831.4	832.5	832.7	831.9	831.1	830.3	829.6
147.5°	855.3	856.1	856.9	857.0	856.3	855.7	855.0	854.3
150°	870.6	871.6	872.5	872.6	871.8	871.0	870.2	869.5
152.5°	884.6	885.6	886.5	886.5	885.4	884.4	883.4	882.3
155°	903.5	904.5	905.4	905.2	904.0	902.8	901.5	900.3
157.5°	919.5	920.5	921.6	921.5	920.3	919.1	917.9	916.6
160°	928.7	929.7	930.6	930.5	929.4	928.3	927.3	926.2
162.5°	937.4	938.4	939.5	939.4	938.0	936.7	935.3	934.0
165°	948.0	949.0	950.1	950.1	949.0	948.0	946.9	945.8
167.5°	956.8	957.9	958.9	958.8	957.4	956.0	954.6	953.2
170°	961.3	962.3	963.4	963.3	961.9	960.5	959.1	957.7
172.5°	964.6	965.7	966.8	966.6	965.2	963.8	962.4	961.0
175°	968.3	969.3	970.4	970.2	968.6	967.1	965.5	964.0
177.5°	968.7	969.5	970.4	970.3	969.2	968.0	966.9	965.8
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5

(END OF REPORT)