

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331823-840

Luminaire Tested: **S122RDIW-S675D1440U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331823-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D1440U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8164.7 lumens
Efficiency: N/A
Efficacy: 119.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331823-840

CATALOG NUMBER: S122RDIW-S675D1440U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331823-840

CATALOG NUMBER: S122RDIW-S675D1440U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37	29
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25
2	85	78	72	68	76	70	65	61	55	52	49	42	40	38	29	28	27	21
3	78	69	62	57	69	62	56	51	49	45	42	37	34	32	26	24	23	18
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	23	22	20	16
5	65	54	47	41	58	49	43	38	39	34	31	30	27	24	21	19	18	14
6	60	49	41	36	54	44	37	33	35	30	27	27	24	21	19	17	16	12
7	56	44	36	31	50	40	33	29	32	27	24	25	21	19	18	16	14	11
8	52	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	22	40	30	24	20	24	20	17	19	16	14	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18392	18392	18392
5°	18462	18162	18263
10°	18321	17864	17713
15°	18111	17336	16836
20°	17819	16579	15747
25°	17521	15720	14694
30°	17107	14838	13340
35°	16703	13878	12151
40°	16297	12886	10777
45°	15819	11768	9533
50°	15330	10643	8312
55°	14829	9433	7139
60°	14247	8157	5926
65°	13589	6854	5398
70°	12798	5646	4961
75°	11834	5147	4629
80°	10451	4603	4212
85°	8207	3631	3631



TEST NUMBER: P331823-840

CATALOG NUMBER: S122RDIW-S675D1440U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.6	1.3
10°-20°	292.8	3.6
20°-30°	411.1	5.0
30°-40°	448.3	5.5
40°-50°	412.2	5.0
50°-60°	323.8	4.0
60°-70°	211.1	2.6
70°-80°	108.8	1.3
80°-90°	33.1	0.4
90°-100°	66.2	0.8
100°-110°	242.8	3.0
110°-120°	649.0	7.9
120°-130°	1071.4	13.1
130°-140°	1139.4	14.0
140°-150°	1059.0	13.0
150°-160°	851.5	10.4
160°-170°	548.7	6.7
170°-180°	188.9	2.3
0°-30°	810.5	9.9
0°-40°	1258.9	15.4
0°-60°	1994.8	24.4
0°-90°	2347.9	28.8
90°-120°	958.1	11.7
90°-150°	4227.9	51.8
90°-180°	5817.0	71.2
0°-180°	8164.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1139	1139	1139	1139	1139	
5°	1139	1134	1121	1129	1127	108
15°	1084	1071	1037	1018	1007	305
25°	984	949	882	842	825	452
35°	847	793	704	642	616	530
45°	693	622	515	445	418	535
55°	527	445	335	276	254	471
65°	356	272	179	146	141	352
75°	190	120	82	76	74	201
85°	44	24	20	20	20	52
90°	1	17	29	36	39	6
95°	93	49	56	63	62	114
105°	437	456	88	103	109	467
115°	826	851	886	252	118	813
125°	1168	1187	1214	1223	1228	1041
135°	1445	1467	1481	1494	1492	1116
145°	1676	1676	1699	1708	1702	1048
155°	1846	1834	1850	1857	1847	850
165°	1945	1937	1940	1949	1940	549
175°	1989	1980	1982	1991	1978	189
180°	1985	1985	1985	1985	1985	



TEST NUMBER: P331823-840

CATALOG NUMBER: S122RDIW-S675D1440U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1
2.5°	1143.3	1142.4	1141.5	1140.5	1139.6	1138.1	1136.1	1134.1	1132.2	1130.1	1132.0
5°	1139.1	1138.0	1136.9	1135.7	1134.6	1132.6	1129.5	1126.6	1123.6	1120.6	1122.7
7.5°	1127.4	1126.0	1124.6	1123.2	1121.8	1119.2	1115.8	1112.4	1108.8	1105.4	1105.9
10°	1117.5	1115.9	1114.3	1112.7	1111.1	1108.0	1103.4	1098.8	1094.3	1089.6	1089.0
12.5°	1105.1	1103.2	1101.2	1099.2	1097.2	1093.4	1087.5	1081.7	1075.7	1069.9	1068.6
15°	1083.5	1081.0	1078.4	1075.9	1073.4	1068.2	1060.5	1052.7	1044.9	1037.1	1032.8
17.5°	1056.9	1053.1	1049.2	1045.3	1041.5	1034.6	1024.6	1014.6	1004.6	994.6	989.5
20°	1037.1	1032.5	1027.9	1023.4	1018.8	1010.8	999.3	987.8	976.4	964.9	959.2
22.5°	1015.6	1010.6	1005.4	1000.3	995.1	986.1	973.2	960.3	947.4	934.4	927.1
25°	983.5	976.1	968.9	961.5	954.2	942.9	927.9	912.7	897.6	882.4	873.0
27.5°	944.7	936.8	928.8	920.8	912.8	900.3	883.3	866.3	849.2	832.1	821.2
30°	917.6	908.8	900.1	891.4	882.7	869.2	850.8	832.5	814.2	795.9	784.2
32.5°	891.1	880.9	870.8	860.6	850.4	836.0	817.3	798.6	779.9	761.2	747.9
35°	847.4	835.8	824.0	812.3	800.7	784.8	764.6	744.5	724.3	704.1	689.6
37.5°	803.8	790.8	778.0	765.2	752.3	735.2	713.8	692.3	670.8	649.2	633.4
40°	773.2	759.4	745.7	732.0	718.2	700.2	678.0	655.8	633.6	611.4	595.1
42.5°	741.8	727.4	712.9	698.4	684.0	665.2	642.3	619.4	596.3	573.4	556.5
45°	692.8	677.4	662.1	646.7	631.4	611.7	587.6	563.6	539.5	515.4	499.2
47.5°	644.9	628.6	612.4	596.1	579.9	559.4	534.5	509.7	484.8	460.0	443.8
50°	610.3	594.0	577.7	561.5	545.2	524.5	499.3	474.1	448.9	423.7	407.9
52.5°	576.5	559.5	542.5	525.5	508.5	487.7	463.0	438.4	413.7	389.1	373.9
55°	526.8	509.0	491.1	473.2	455.3	434.0	409.3	384.6	359.8	335.1	321.3
57.5°	475.8	457.6	439.2	420.9	402.5	381.5	357.7	334.0	310.1	286.4	273.8
60°	441.2	422.9	404.6	386.3	367.9	347.0	323.4	299.7	276.2	252.6	240.9
62.5°	407.4	389.1	370.7	352.4	334.1	313.7	291.2	268.7	246.2	223.7	212.6
65°	355.7	337.1	318.5	300.0	281.4	261.9	241.3	220.7	200.0	179.4	171.6
67.5°	305.8	287.3	268.9	250.5	232.1	213.6	195.0	176.5	157.9	139.4	135.8
70°	271.1	253.3	235.4	217.5	199.7	182.8	167.0	151.2	135.4	119.6	117.2
72.5°	238.1	221.0	203.9	186.7	169.6	154.7	142.0	129.3	116.6	103.9	102.0
75°	189.7	173.7	157.6	141.6	125.5	113.6	105.8	98.1	90.3	82.5	80.9
77.5°	142.1	127.9	113.9	99.9	85.8	76.9	73.1	69.4	65.6	61.9	60.9
80°	112.4	100.7	89.0	77.4	65.6	58.7	56.4	54.0	51.8	49.5	48.6
82.5°	85.1	76.0	67.0	57.8	48.7	43.3	41.8	40.2	38.7	37.2	36.6
85°	44.3	39.5	34.7	29.9	25.0	22.3	21.6	21.0	20.3	19.6	19.6
87.5°	13.5	12.7	11.9	11.2	10.4	10.3	10.8	11.3	11.8	12.3	12.5
90°	1.4	4.9	8.5	12.0	15.5	18.5	21.1	23.6	26.2	28.7	30.3
92.5°	29.0	28.7	28.4	28.1	27.8	28.2	29.5	30.8	32.0	33.3	34.1
95°	93.3	82.8	72.3	61.8	51.2	47.1	49.3	51.5	53.8	56.0	57.6
97.5°	185.3	155.6	125.9	96.2	66.6	54.3	59.5	64.6	69.8	74.9	76.2
100°	254.2	210.5	166.7	123.0	79.3	60.2	65.5	71.0	76.4	81.9	84.4
102.5°	330.0	320.8	311.5	302.3	293.1	265.7	220.4	174.9	129.6	84.1	87.5
105°	436.7	446.2	455.8	465.3	474.9	436.2	349.0	261.9	174.7	87.7	91.1
107.5°	558.2	565.8	573.6	581.3	589.1	540.7	436.2	331.6	227.1	122.7	119.1
110°	636.3	643.0	649.6	656.4	663.1	620.3	528.1	435.9	343.6	251.4	219.4



TEST NUMBER: P331823-840

CATALOG NUMBER: S122RDIW-S675D1440U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	709.8	715.7	721.6	727.6	733.6	725.1	702.4	679.5	656.7	634.0	517.6
115°	825.9	831.3	836.7	842.1	847.6	854.2	862.2	870.2	878.2	886.2	738.4
117.5°	929.6	935.6	941.7	947.8	953.8	959.6	965.0	970.6	976.0	981.6	945.8
120°	1005.4	1010.2	1014.9	1019.8	1024.5	1029.8	1035.5	1041.3	1047.0	1052.8	1056.6
122.5°	1069.8	1074.8	1079.8	1084.9	1089.9	1095.6	1101.8	1108.0	1114.3	1120.5	1122.9
125°	1167.7	1171.8	1176.0	1180.1	1184.3	1189.4	1195.5	1201.5	1207.6	1213.7	1215.9
127.5°	1256.5	1261.0	1265.7	1270.2	1274.9	1279.4	1283.9	1288.5	1293.0	1297.6	1300.8
130°	1312.7	1317.9	1322.9	1328.1	1333.2	1337.5	1341.0	1344.5	1348.0	1351.5	1355.0
132.5°	1370.2	1374.5	1378.9	1383.2	1387.6	1391.5	1395.0	1398.5	1402.0	1405.5	1408.6
135°	1444.9	1450.0	1455.1	1460.2	1465.3	1469.3	1472.2	1475.0	1477.9	1480.8	1484.0
137.5°	1520.5	1524.0	1527.6	1531.2	1534.7	1538.1	1541.4	1544.7	1547.9	1551.2	1554.3
140°	1569.8	1572.4	1575.0	1577.5	1580.0	1583.1	1586.6	1590.1	1593.7	1597.1	1600.0
142.5°	1611.2	1613.5	1615.8	1618.1	1620.4	1623.6	1627.6	1631.6	1635.6	1639.6	1642.2
145°	1676.2	1675.8	1675.5	1675.2	1674.9	1677.4	1682.8	1688.3	1693.6	1699.1	1701.3
147.5°	1732.7	1731.5	1730.3	1729.1	1727.9	1729.9	1735.3	1740.7	1746.1	1751.4	1753.0
150°	1769.5	1767.3	1765.0	1762.8	1760.5	1762.0	1767.1	1772.2	1777.3	1782.4	1784.3
152.5°	1800.5	1798.1	1795.5	1793.0	1790.6	1791.7	1796.5	1801.4	1806.2	1811.1	1813.0
155°	1845.6	1842.7	1839.9	1836.9	1834.1	1834.6	1838.5	1842.3	1846.1	1849.9	1851.8
157.5°	1881.0	1878.6	1876.1	1873.7	1871.3	1871.4	1874.0	1876.7	1879.4	1882.1	1884.3
160°	1901.6	1899.7	1897.8	1895.9	1894.0	1894.0	1895.9	1897.8	1899.7	1901.6	1903.5
162.5°	1920.0	1918.1	1916.2	1914.3	1912.4	1912.2	1913.9	1915.5	1917.2	1918.8	1921.1
165°	1944.7	1942.8	1940.9	1938.9	1937.0	1936.6	1937.5	1938.4	1939.4	1940.4	1942.7
167.5°	1963.1	1961.2	1959.2	1957.3	1955.4	1954.9	1955.8	1956.7	1957.6	1958.5	1960.8
170°	1973.5	1971.6	1969.6	1967.7	1965.8	1965.1	1965.8	1966.4	1967.0	1967.7	1969.9
172.5°	1980.3	1978.4	1976.5	1974.6	1972.7	1972.1	1972.7	1973.3	1974.0	1974.6	1976.8
175°	1989.2	1987.0	1984.8	1982.6	1980.3	1979.5	1980.1	1980.7	1981.5	1982.1	1984.3
177.5°	1990.6	1988.9	1987.1	1985.3	1983.5	1982.8	1983.0	1983.3	1983.5	1983.8	1985.6
180°	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9



TEST NUMBER: P331823-840

CATALOG NUMBER: S122RDIW-S675D1440U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1
2.5°	1133.8	1135.6	1137.4	1138.1	1137.8	1137.4	1137.1	1136.7
5°	1124.7	1126.8	1128.8	1129.5	1128.8	1128.1	1127.5	1126.8
7.5°	1106.5	1107.1	1107.7	1107.4	1106.2	1105.1	1103.9	1102.7
10°	1088.3	1087.6	1086.9	1085.9	1084.5	1083.2	1081.8	1080.4
12.5°	1067.4	1066.2	1064.9	1063.2	1060.9	1058.6	1056.3	1054.0
15°	1028.4	1024.0	1019.7	1016.3	1014.1	1011.8	1009.5	1007.2
17.5°	984.3	979.1	973.9	969.4	965.4	961.5	957.6	953.6
20°	953.5	947.8	942.0	936.6	931.6	926.6	921.5	916.5
22.5°	919.7	912.3	904.9	899.4	895.5	891.8	888.1	884.3
25°	863.6	854.2	844.9	838.5	835.1	831.6	828.2	824.8
27.5°	810.2	799.3	788.4	780.1	774.7	769.2	763.8	758.3
30°	772.5	760.8	749.1	740.2	734.0	727.8	721.6	715.5
32.5°	734.6	721.2	707.9	698.3	692.5	686.7	680.9	675.1
35°	675.3	660.9	646.4	636.6	631.6	626.5	621.6	616.5
37.5°	617.4	601.6	585.7	574.8	569.1	563.3	557.5	551.8
40°	578.8	562.5	546.2	535.1	529.2	523.2	517.3	511.3
42.5°	539.8	522.9	506.1	494.8	489.1	483.3	477.6	471.7
45°	482.9	466.7	450.4	439.5	434.0	428.5	423.0	417.5
47.5°	427.7	411.5	395.3	384.8	379.7	374.8	369.7	364.8
50°	392.1	376.3	360.5	350.1	345.4	340.5	335.8	330.9
52.5°	358.6	343.3	328.0	318.2	313.8	309.3	304.9	300.4
55°	307.6	293.8	280.0	271.0	266.7	262.3	257.9	253.6
57.5°	261.2	248.6	236.0	227.8	224.2	220.6	216.8	213.2
60°	229.2	217.5	205.8	198.1	194.5	190.9	187.1	183.5
62.5°	201.5	190.3	179.2	172.5	170.3	168.1	165.9	163.7
65°	163.8	156.0	148.2	144.0	143.3	142.6	141.9	141.3
67.5°	132.2	128.7	125.1	122.9	122.2	121.5	120.8	120.0
70°	115.0	112.7	110.4	108.9	107.9	106.9	106.0	105.1
72.5°	100.1	98.2	96.2	95.0	94.4	93.9	93.3	92.8
75°	79.3	77.7	76.0	75.1	74.9	74.7	74.4	74.2
77.5°	60.0	59.1	58.2	57.6	57.2	56.9	56.5	56.0
80°	47.7	46.8	45.8	45.3	45.3	45.3	45.3	45.3
82.5°	36.1	35.4	34.9	34.6	34.6	34.6	34.6	34.6
85°	19.6	19.6	19.6	19.6	19.6	19.6	19.6	19.6
87.5°	12.6	12.7	12.9	13.0	13.1	13.2	13.4	13.5
90°	31.9	33.5	35.1	36.3	36.9	37.5	38.2	38.8
92.5°	34.9	35.9	36.7	37.3	37.7	38.0	38.4	38.8
95°	59.2	60.8	62.4	63.0	62.7	62.4	62.1	61.8
97.5°	77.6	78.8	80.1	80.9	81.3	81.7	82.1	82.4
100°	86.9	89.6	92.1	93.7	94.3	94.9	95.6	96.2
102.5°	90.8	94.1	97.5	99.6	100.5	101.3	102.2	103.1
105°	94.6	98.2	101.7	104.0	105.3	106.6	107.9	109.2
107.5°	115.5	111.9	108.4	107.2	108.5	109.8	111.1	112.3
110°	187.5	155.6	123.7	108.4	109.7	110.9	112.2	113.5



TEST NUMBER: P331823-840

CATALOG NUMBER: S122RDIW-S675D1440U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	401.1	284.7	168.2	110.5	111.6	112.6	113.6	114.6
115°	590.7	442.8	295.1	209.6	186.7	163.7	140.8	117.8
117.5°	910.1	874.3	838.6	782.9	707.4	631.9	556.3	480.9
120°	1060.5	1064.3	1068.1	1048.4	1005.4	962.3	919.2	876.2
122.5°	1125.2	1127.5	1129.7	1126.7	1118.3	1110.0	1101.7	1093.3
125°	1218.1	1220.3	1222.5	1224.2	1225.2	1226.1	1227.1	1228.0
127.5°	1304.0	1307.3	1310.5	1312.3	1312.4	1312.6	1312.8	1313.0
130°	1358.6	1362.1	1365.5	1367.2	1366.9	1366.5	1366.2	1365.8
132.5°	1411.5	1414.5	1417.5	1418.9	1418.6	1418.3	1418.0	1417.5
135°	1487.1	1490.4	1493.6	1494.8	1494.2	1493.6	1492.9	1492.3
137.5°	1557.4	1560.5	1563.7	1564.7	1563.6	1562.6	1561.5	1560.3
140°	1602.9	1605.8	1608.6	1609.2	1607.7	1606.1	1604.5	1602.9
142.5°	1644.9	1647.5	1650.1	1650.6	1649.0	1647.4	1645.9	1644.3
145°	1703.5	1705.8	1708.1	1708.4	1706.8	1705.2	1703.5	1702.0
147.5°	1754.7	1756.4	1758.1	1758.2	1756.9	1755.5	1754.1	1752.8
150°	1786.2	1788.2	1790.1	1790.2	1788.7	1787.1	1785.4	1783.8
152.5°	1814.9	1816.8	1818.8	1818.7	1816.5	1814.5	1812.4	1810.3
155°	1853.7	1855.6	1857.5	1857.2	1854.7	1852.2	1849.6	1847.0
157.5°	1886.4	1888.5	1890.8	1890.6	1888.1	1885.6	1883.1	1880.7
160°	1905.4	1907.3	1909.3	1909.1	1906.9	1904.6	1902.4	1900.2
162.5°	1923.2	1925.4	1927.5	1927.2	1924.5	1921.8	1919.0	1916.3
165°	1944.9	1947.1	1949.3	1949.3	1947.1	1944.9	1942.7	1940.4
167.5°	1963.0	1965.2	1967.4	1967.1	1964.3	1961.4	1958.5	1955.6
170°	1972.2	1974.4	1976.6	1976.3	1973.5	1970.5	1967.7	1964.8
172.5°	1979.0	1981.3	1983.5	1983.2	1980.3	1977.4	1974.6	1971.7
175°	1986.5	1988.7	1990.9	1990.5	1987.3	1984.1	1981.0	1977.7
177.5°	1987.3	1989.1	1990.9	1990.6	1988.3	1986.1	1983.8	1981.5
180°	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9	1984.9

(END OF REPORT)