

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331807-840

Luminaire Tested: **S122RDIW-S675D435U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331807-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S675D435U840-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 435 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4092.6 lumens  
Efficiency: N/A  
Efficacy: 108.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331807-840

CATALOG NUMBER: S122RDIW-S675D435U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331807-840

CATALOG NUMBER: S122RDIW-S675D435U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	91	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	46	42
3	84	75	67	62	78	70	64	59	61	56	52	53	49	46	45	42	40	36
4	77	66	59	53	72	62	55	50	55	49	45	47	43	40	41	38	35	32
5	71	60	52	46	66	56	49	44	49	44	39	43	38	35	37	34	31	28
6	66	54	46	40	61	50	43	38	45	39	35	39	34	31	34	30	28	25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	27	25	22
8	57	44	37	31	53	42	35	30	37	32	27	33	28	25	29	25	22	20
9	53	41	33	28	49	38	32	27	34	29	25	30	26	23	26	23	20	18
10	49	37	30	26	46	35	29	25	32	26	23	28	24	21	25	21	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18392	18392	18392
5°	18462	18162	18263
10°	18321	17864	17713
15°	18111	17336	16836
20°	17819	16579	15747
25°	17521	15720	14694
30°	17107	14838	13340
35°	16703	13878	12151
40°	16297	12886	10777
45°	15819	11768	9533
50°	15330	10643	8312
55°	14829	9433	7139
60°	14247	8157	5926
65°	13589	6854	5398
70°	12798	5646	4961
75°	11834	5147	4629
80°	10451	4603	4212
85°	8207	3631	3631



TEST NUMBER: P331807-840

CATALOG NUMBER: S122RDIW-S675D435U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.6	2.6
10°-20°	292.8	7.2
20°-30°	411.1	10.0
30°-40°	448.3	11.0
40°-50°	412.2	10.1
50°-60°	323.8	7.9
60°-70°	211.1	5.2
70°-80°	108.8	2.7
80°-90°	29.7	0.7
90°-100°	19.9	0.5
100°-110°	73.0	1.8
110°-120°	195.0	4.8
120°-130°	322.0	7.9
130°-140°	342.4	8.4
140°-150°	318.3	7.8
150°-160°	255.9	6.3
160°-170°	164.9	4.0
170°-180°	56.8	1.4
0°-30°	810.5	19.8
0°-40°	1258.9	30.8
0°-60°	1994.8	48.7
0°-90°	2344.4	57.3
90°-120°	287.9	7.0
90°-150°	1270.6	31.0
90°-180°	1748.0	42.7
0°-180°	4092.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1139	1139	1139	1139	1139	
5°	1139	1134	1121	1129	1127	108
15°	1084	1071	1037	1018	1007	305
25°	984	949	882	842	825	452
35°	847	793	704	642	616	530
45°	693	622	515	445	418	535
55°	527	445	335	276	254	471
65°	356	272	179	146	141	352
75°	190	120	82	76	74	201
85°	44	24	20	20	20	52
90°	0	5	9	11	12	3
95°	28	15	17	19	19	34
105°	131	137	26	31	33	140
115°	248	256	266	76	35	244
125°	351	357	365	368	369	313
135°	434	441	445	449	448	335
145°	504	504	511	513	512	315
155°	555	551	556	558	555	255
165°	584	582	583	586	583	165
175°	598	595	596	598	594	57
180°	596	596	596	596	596	



TEST NUMBER: P331807-840

CATALOG NUMBER: S122RDIW-S675D435U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1
2.5°	1143.3	1142.4	1141.5	1140.5	1139.6	1138.1	1136.1	1134.1	1132.2	1130.1	1132.0
5°	1139.1	1138.0	1136.9	1135.7	1134.6	1132.6	1129.5	1126.6	1123.6	1120.6	1122.7
7.5°	1127.4	1126.0	1124.6	1123.2	1121.8	1119.2	1115.8	1112.4	1108.8	1105.4	1105.9
10°	1117.5	1115.9	1114.3	1112.7	1111.1	1108.0	1103.4	1098.8	1094.3	1089.6	1089.0
12.5°	1105.1	1103.2	1101.2	1099.2	1097.2	1093.4	1087.5	1081.7	1075.7	1069.9	1068.6
15°	1083.5	1081.0	1078.4	1075.9	1073.4	1068.2	1060.5	1052.7	1044.9	1037.1	1032.8
17.5°	1056.9	1053.1	1049.2	1045.3	1041.5	1034.6	1024.6	1014.6	1004.6	994.6	989.5
20°	1037.1	1032.5	1027.9	1023.4	1018.8	1010.8	999.3	987.8	976.4	964.9	959.2
22.5°	1015.6	1010.6	1005.4	1000.3	995.1	986.1	973.2	960.3	947.4	934.4	927.1
25°	983.5	976.1	968.9	961.5	954.2	942.9	927.9	912.7	897.6	882.4	873.0
27.5°	944.7	936.8	928.8	920.8	912.8	900.3	883.3	866.3	849.2	832.1	821.2
30°	917.6	908.8	900.1	891.4	882.7	869.2	850.8	832.5	814.2	795.9	784.2
32.5°	891.1	880.9	870.8	860.6	850.4	836.0	817.3	798.6	779.9	761.2	747.9
35°	847.4	835.8	824.0	812.3	800.7	784.8	764.6	744.5	724.3	704.1	689.6
37.5°	803.8	790.8	778.0	765.2	752.3	735.2	713.8	692.3	670.8	649.2	633.4
40°	773.2	759.4	745.7	732.0	718.2	700.2	678.0	655.8	633.6	611.4	595.1
42.5°	741.8	727.4	712.9	698.4	684.0	665.2	642.3	619.4	596.3	573.4	556.5
45°	692.8	677.4	662.1	646.7	631.4	611.7	587.6	563.6	539.5	515.4	499.2
47.5°	644.9	628.6	612.4	596.1	579.9	559.4	534.5	509.7	484.8	460.0	443.8
50°	610.3	594.0	577.7	561.5	545.2	524.5	499.3	474.1	448.9	423.7	407.9
52.5°	576.5	559.5	542.5	525.5	508.5	487.7	463.0	438.4	413.7	389.1	373.9
55°	526.8	509.0	491.1	473.2	455.3	434.0	409.3	384.6	359.8	335.1	321.3
57.5°	475.8	457.6	439.2	420.9	402.5	381.5	357.7	334.0	310.1	286.4	273.8
60°	441.2	422.9	404.6	386.3	367.9	347.0	323.4	299.7	276.2	252.6	240.9
62.5°	407.4	389.1	370.7	352.4	334.1	313.7	291.2	268.7	246.2	223.7	212.6
65°	355.7	337.1	318.5	300.0	281.4	261.9	241.3	220.7	200.0	179.4	171.6
67.5°	305.8	287.3	268.9	250.5	232.1	213.6	195.0	176.5	157.9	139.4	135.8
70°	271.1	253.3	235.4	217.5	199.7	182.8	167.0	151.2	135.4	119.6	117.2
72.5°	238.1	221.0	203.9	186.7	169.6	154.7	142.0	129.3	116.6	103.9	102.0
75°	189.7	173.7	157.6	141.6	125.5	113.6	105.8	98.1	90.3	82.5	80.9
77.5°	142.1	127.9	113.9	99.9	85.8	76.9	73.1	69.4	65.6	61.9	60.9
80°	112.4	100.7	89.0	77.4	65.6	58.7	56.4	54.0	51.8	49.5	48.6
82.5°	85.1	76.0	67.0	57.8	48.7	43.3	41.8	40.2	38.7	37.2	36.6
85°	44.3	39.5	34.7	29.9	25.0	22.3	21.6	21.0	20.3	19.6	19.6
87.5°	13.3	12.0	10.8	9.5	8.3	7.7	7.9	8.0	8.2	8.3	8.3
90°	0.4	1.5	2.5	3.6	4.6	5.6	6.4	7.1	7.9	8.6	9.1
92.5°	8.7	8.6	8.5	8.4	8.4	8.5	8.9	9.3	9.6	10.0	10.3
95°	28.1	24.8	21.7	18.6	15.3	14.1	14.8	15.5	16.2	16.9	17.3
97.5°	55.6	46.8	37.9	28.9	20.0	16.4	17.9	19.4	21.0	22.5	22.9
100°	76.4	63.2	50.1	37.0	23.8	18.1	19.7	21.3	22.9	24.6	25.3
102.5°	99.2	96.4	93.6	90.9	88.1	79.9	66.2	52.6	39.0	25.2	26.3
105°	131.2	134.1	136.9	139.9	142.7	131.1	104.9	78.7	52.5	26.4	27.4
107.5°	167.7	170.1	172.4	174.7	177.0	162.5	131.1	99.7	68.3	36.9	35.7
110°	191.2	193.2	195.2	197.2	199.2	186.4	158.6	131.0	103.2	75.5	65.9



TEST NUMBER: P331807-840

CATALOG NUMBER: S122RDIW-S675D435U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	213.3	215.1	216.9	218.6	220.5	217.9	211.1	204.2	197.3	190.6	155.5
115°	248.2	249.8	251.5	253.1	254.7	256.7	259.1	261.6	263.9	266.3	221.9
117.5°	279.3	281.1	283.0	284.8	286.6	288.4	290.0	291.6	293.4	295.0	284.3
120°	302.2	303.6	305.0	306.5	307.9	309.5	311.2	313.0	314.7	316.4	317.5
122.5°	321.4	323.0	324.5	326.0	327.5	329.2	331.1	333.0	334.9	336.8	337.5
125°	350.9	352.1	353.5	354.7	355.9	357.4	359.3	361.1	362.9	364.8	365.4
127.5°	377.6	379.0	380.3	381.7	383.1	384.5	385.9	387.2	388.6	389.9	390.9
130°	394.6	396.1	397.6	399.1	400.6	401.9	403.0	404.0	405.2	406.2	407.2
132.5°	411.8	413.0	414.3	415.7	417.0	418.2	419.2	420.3	421.3	422.4	423.3
135°	434.2	435.8	437.3	438.8	440.4	441.5	442.4	443.3	444.1	445.0	446.0
137.5°	457.0	458.0	459.1	460.2	461.2	462.2	463.2	464.2	465.1	466.2	467.1
140°	471.8	472.5	473.3	474.0	474.8	475.7	476.9	477.9	478.9	480.0	480.8
142.5°	484.2	484.9	485.5	486.3	487.0	488.0	489.1	490.3	491.5	492.7	493.5
145°	503.7	503.6	503.5	503.4	503.3	504.1	505.7	507.4	509.0	510.6	511.3
147.5°	520.7	520.4	520.0	519.7	519.3	519.9	521.5	523.1	524.7	526.3	526.8
150°	531.8	531.1	530.4	529.8	529.1	529.5	531.1	532.6	534.1	535.6	536.2
152.5°	541.1	540.4	539.6	538.9	538.1	538.5	539.9	541.4	542.8	544.3	544.8
155°	554.6	553.8	552.9	552.1	551.2	551.4	552.5	553.6	554.8	555.9	556.5
157.5°	565.2	564.5	563.8	563.1	562.4	562.4	563.2	564.0	564.8	565.6	566.2
160°	571.5	570.9	570.4	569.8	569.2	569.2	569.8	570.4	570.9	571.5	572.1
162.5°	577.0	576.4	575.8	575.3	574.7	574.7	575.1	575.6	576.1	576.6	577.3
165°	584.4	583.9	583.3	582.7	582.1	582.0	582.3	582.6	582.9	583.1	583.8
167.5°	590.0	589.4	588.9	588.2	587.6	587.5	587.7	588.0	588.3	588.5	589.3
170°	593.1	592.5	591.9	591.4	590.8	590.6	590.8	591.0	591.2	591.4	592.0
172.5°	595.1	594.6	594.0	593.4	592.8	592.7	592.8	593.0	593.2	593.4	594.1
175°	597.8	597.1	596.4	595.8	595.1	594.9	595.1	595.3	595.4	595.6	596.3
177.5°	598.2	597.7	597.1	596.6	596.1	595.8	595.9	596.0	596.1	596.1	596.7
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5



TEST NUMBER: P331807-840

CATALOG NUMBER: S122RDIW-S675D435U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1
2.5°	1133.8	1135.6	1137.4	1138.1	1137.8	1137.4	1137.1	1136.7
5°	1124.7	1126.8	1128.8	1129.5	1128.8	1128.1	1127.5	1126.8
7.5°	1106.5	1107.1	1107.7	1107.4	1106.2	1105.1	1103.9	1102.7
10°	1088.3	1087.6	1086.9	1085.9	1084.5	1083.2	1081.8	1080.4
12.5°	1067.4	1066.2	1064.9	1063.2	1060.9	1058.6	1056.3	1054.0
15°	1028.4	1024.0	1019.7	1016.3	1014.1	1011.8	1009.5	1007.2
17.5°	984.3	979.1	973.9	969.4	965.4	961.5	957.6	953.6
20°	953.5	947.8	942.0	936.6	931.6	926.6	921.5	916.5
22.5°	919.7	912.3	904.9	899.4	895.5	891.8	888.1	884.3
25°	863.6	854.2	844.9	838.5	835.1	831.6	828.2	824.8
27.5°	810.2	799.3	788.4	780.1	774.7	769.2	763.8	758.3
30°	772.5	760.8	749.1	740.2	734.0	727.8	721.6	715.5
32.5°	734.6	721.2	707.9	698.3	692.5	686.7	680.9	675.1
35°	675.3	660.9	646.4	636.6	631.6	626.5	621.6	616.5
37.5°	617.4	601.6	585.7	574.8	569.1	563.3	557.5	551.8
40°	578.8	562.5	546.2	535.1	529.2	523.2	517.3	511.3
42.5°	539.8	522.9	506.1	494.8	489.1	483.3	477.6	471.7
45°	482.9	466.7	450.4	439.5	434.0	428.5	423.0	417.5
47.5°	427.7	411.5	395.3	384.8	379.7	374.8	369.7	364.8
50°	392.1	376.3	360.5	350.1	345.4	340.5	335.8	330.9
52.5°	358.6	343.3	328.0	318.2	313.8	309.3	304.9	300.4
55°	307.6	293.8	280.0	271.0	266.7	262.3	257.9	253.6
57.5°	261.2	248.6	236.0	227.8	224.2	220.6	216.8	213.2
60°	229.2	217.5	205.8	198.1	194.5	190.9	187.1	183.5
62.5°	201.5	190.3	179.2	172.5	170.3	168.1	165.9	163.7
65°	163.8	156.0	148.2	144.0	143.3	142.6	141.9	141.3
67.5°	132.2	128.7	125.1	122.9	122.2	121.5	120.8	120.0
70°	115.0	112.7	110.4	108.9	107.9	106.9	106.0	105.1
72.5°	100.1	98.2	96.2	95.0	94.4	93.9	93.3	92.8
75°	79.3	77.7	76.0	75.1	74.9	74.7	74.4	74.2
77.5°	60.0	59.1	58.2	57.6	57.2	56.9	56.5	56.0
80°	47.7	46.8	45.8	45.3	45.3	45.3	45.3	45.3
82.5°	36.1	35.4	34.9	34.6	34.6	34.6	34.6	34.6
85°	19.6	19.6	19.6	19.6	19.6	19.6	19.6	19.6
87.5°	8.2	8.1	8.0	8.0	8.0	8.0	8.1	8.1
90°	9.6	10.1	10.5	10.9	11.1	11.3	11.5	11.6
92.5°	10.5	10.8	11.0	11.2	11.3	11.4	11.5	11.6
95°	17.8	18.3	18.8	19.0	18.9	18.8	18.7	18.6
97.5°	23.3	23.7	24.0	24.3	24.4	24.5	24.6	24.7
100°	26.2	26.9	27.7	28.2	28.4	28.6	28.7	28.9
102.5°	27.3	28.3	29.3	29.9	30.2	30.5	30.7	31.0
105°	28.5	29.5	30.6	31.3	31.6	32.0	32.4	32.8
107.5°	34.7	33.6	32.5	32.2	32.6	33.0	33.3	33.7
110°	56.4	46.8	37.2	32.5	32.9	33.3	33.7	34.1





TEST NUMBER: P331807-840

CATALOG NUMBER: S122RDIW-S675D435U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	120.6	85.5	50.6	33.2	33.5	33.8	34.1	34.4
115°	177.5	133.1	88.7	63.0	56.1	49.2	42.3	35.3
117.5°	273.5	262.8	252.0	235.3	212.6	189.9	167.2	144.5
120°	318.7	319.8	321.0	315.1	302.2	289.2	276.2	263.3
122.5°	338.1	338.8	339.5	338.6	336.1	333.6	331.0	328.5
125°	366.1	366.8	367.4	367.9	368.2	368.5	368.8	369.0
127.5°	391.9	392.8	393.8	394.4	394.5	394.5	394.6	394.6
130°	408.3	409.3	410.4	410.9	410.8	410.7	410.6	410.5
132.5°	424.2	425.1	426.0	426.4	426.3	426.2	426.2	426.1
135°	447.0	447.9	448.9	449.2	449.1	448.9	448.7	448.5
137.5°	468.1	469.0	469.9	470.2	469.9	469.6	469.3	468.9
140°	481.7	482.6	483.4	483.6	483.1	482.6	482.2	481.7
142.5°	494.3	495.1	495.9	496.0	495.5	495.1	494.6	494.1
145°	512.0	512.6	513.3	513.4	512.9	512.4	512.0	511.5
147.5°	527.4	527.9	528.4	528.4	528.0	527.6	527.1	526.7
150°	536.8	537.3	538.0	538.1	537.6	537.0	536.5	536.1
152.5°	545.4	546.0	546.6	546.5	545.9	545.3	544.6	544.0
155°	557.1	557.6	558.3	558.2	557.3	556.6	555.8	555.1
157.5°	566.9	567.5	568.3	568.2	567.4	566.6	565.9	565.2
160°	572.6	573.2	573.8	573.7	573.1	572.4	571.7	571.1
162.5°	577.9	578.7	579.3	579.2	578.3	577.5	576.7	575.9
165°	584.5	585.1	585.8	585.8	585.1	584.5	583.8	583.1
167.5°	590.0	590.6	591.3	591.2	590.3	589.5	588.5	587.7
170°	592.7	593.4	594.0	593.9	593.1	592.2	591.4	590.5
172.5°	594.7	595.4	596.1	596.0	595.1	594.3	593.4	592.6
175°	597.0	597.6	598.3	598.2	597.2	596.3	595.3	594.4
177.5°	597.2	597.7	598.3	598.2	597.5	596.8	596.1	595.5
180°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5

(END OF REPORT)