

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331794

Luminaire Tested: **S122RDIW-S485D970U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331794
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D970U835-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5218.3 lumens
Efficiency: N/A
Efficacy: 115.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331794

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331794

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36																				
1	95	91	87	84	86	83	80	77	67	65	63	52	51	50	39	38	37	31																				
2	87	80	74	70	79	73	68	64	59	56	53	47	44	42	35	33	32	27																				
3	80	71	64	59	72	65	59	54	53	49	45	42	39	37	31	30	28	24																				
4	73	63	56	50	66	58	51	46	47	43	39	37	34	32	28	26	25	21																				
5	67	57	49	43	61	52	45	40	42	38	34	34	31	28	26	24	22	19																				
6	62	51	43	38	56	47	40	35	38	34	30	31	27	25	24	22	20	17																				
7	58	46	39	33	52	42	36	31	35	30	27	28	25	22	22	20	18	15																				
8	54	42	35	30	49	39	32	28	32	27	24	26	23	20	20	18	16	14																				
9	50	38	31	27	45	35	29	25	30	25	21	24	21	18	19	17	15	13																				
10	47	35	28	24	42	33	26	22	27	23	19	22	19	16	18	15	14	12																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17354	17354	17354	17354
5°	19379	17462	15483	17462
10°	21502	17339	13421	17339
15°	22559	17085	10574	17085
20°	19557	16708	9149	16708
25°	12827	16192	8170	16192
30°	8634	15567	7394	15567
35°	6993	14781	6668	14781
40°	6218	13923	6171	13923
45°	5628	12919	5507	12919
50°	5122	11921	5102	11921
55°	4814	10818	4752	10818
60°	4027	9804	3978	9804
65°	3396	8902	3851	8902
70°	3139	7950	3630	7950
75°	2938	6918	3356	6918
80°	2706	5690	2985	5690
85°	2482	4502	2631	4502



TEST NUMBER: P331794

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.9	2.0
10°-20°	283.9	5.4
20°-30°	365.8	7.0
30°-40°	347.6	6.7
40°-50°	297.8	5.7
50°-60°	226.8	4.3
60°-70°	143.4	2.7
70°-80°	71.6	1.4
80°-90°	23.4	0.4
90°-100°	76.0	1.5
100°-110°	236.2	4.5
110°-120°	403.8	7.7
120°-130°	531.0	10.2
130°-140°	595.9	11.4
140°-150°	584.3	11.2
150°-160°	490.1	9.4
160°-170°	325.1	6.2
170°-180°	113.6	2.2
0°-30°	751.6	14.4
0°-40°	1099.2	21.1
0°-60°	1623.8	31.1
0°-90°	1862.2	35.7
90°-120°	716.0	13.7
90°-150°	2427.3	46.5
90°-180°	3356.0	64.3
0°-180°	5218.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1075	1075	1075	1075	1075	
5°	1196	1077	955	1077	1196	118
15°	1350	1022	633	1022	1350	364
25°	720	909	459	909	720	342
35°	355	750	338	750	355	227
45°	246	566	241	566	246	191
55°	171	384	169	384	171	150
65°	89	233	101	233	89	90
75°	47	111	54	111	47	50
85°	13	24	14	24	13	15
90°	34	1	34	1	34	16
95°	63	53	63	53	63	70
105°	225	218	225	218	225	237
115°	405	405	405	405	405	400
125°	592	590	592	590	592	527
135°	772	763	772	763	772	594
145°	936	926	936	926	936	584
155°	1066	1058	1066	1058	1066	491
165°	1153	1152	1153	1152	1153	325
175°	1194	1198	1194	1198	1194	113
180°	1200	1200	1200	1200	1200	



TEST NUMBER: P331794

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1118.4	1119.3	1120.2	1118.1	1118.1	1116.3	1112.4	1109.4	1101.0	1099.8	1099.8
5°	1195.7	1195.0	1196.5	1191.6	1184.9	1183.4	1176.3	1167.0	1157.3	1146.4	1144.2
7.5°	1272.7	1271.6	1268.6	1267.7	1262.6	1251.3	1239.9	1227.7	1211.6	1195.8	1187.9
10°	1311.5	1323.8	1316.4	1303.3	1305.9	1288.4	1279.0	1263.0	1249.5	1226.0	1220.8
12.5°	1349.7	1354.6	1352.2	1344.8	1341.5	1329.3	1316.7	1302.7	1277.9	1256.8	1238.4
15°	1349.6	1356.7	1358.6	1356.3	1358.2	1357.4	1350.7	1339.1	1317.5	1294.3	1274.2
17.5°	1250.0	1254.9	1267.1	1275.4	1285.9	1308.0	1318.9	1323.2	1319.9	1306.7	1292.5
20°	1138.2	1130.0	1164.4	1181.9	1196.9	1234.2	1266.3	1278.6	1298.4	1298.1	1294.3
22.5°	979.9	981.8	1014.4	1035.2	1078.9	1116.2	1152.8	1199.2	1237.5	1262.8	1277.6
25°	720.0	734.2	766.7	795.0	843.6	913.1	976.2	1049.4	1118.4	1173.0	1224.9
27.5°	540.7	541.8	567.5	593.8	622.6	679.5	759.0	846.4	944.9	1026.1	1119.6
30°	463.1	460.8	471.7	487.7	512.4	556.4	616.2	702.1	800.3	922.8	1031.8
32.5°	408.1	408.2	416.4	428.3	448.7	478.4	519.4	589.1	682.0	802.4	930.2
35°	354.8	354.4	360.4	369.0	377.5	396.6	424.6	461.2	525.1	637.5	768.2
37.5°	316.5	318.2	321.1	326.5	335.9	346.5	363.4	387.9	433.4	499.9	609.7
40°	295.0	295.8	299.9	304.4	310.0	318.2	332.0	351.8	385.0	438.0	518.3
42.5°	275.3	276.0	279.0	283.1	287.5	295.8	307.2	324.3	351.3	392.6	458.9
45°	246.5	246.5	249.1	250.9	255.8	263.3	272.6	286.8	305.5	336.1	380.2
47.5°	219.4	219.5	221.2	224.4	227.5	233.3	242.5	254.1	267.7	291.4	329.0
50°	203.9	204.3	205.4	208.0	209.9	215.1	222.2	232.3	246.5	264.8	296.1
52.5°	191.3	191.1	192.5	193.7	194.9	198.7	204.0	212.9	225.6	241.5	267.5
55°	171.0	169.5	171.8	173.6	174.8	176.3	179.2	184.9	195.7	209.1	228.5
57.5°	145.6	145.0	146.6	148.3	151.8	155.9	158.4	162.0	167.6	177.2	196.5
60°	124.7	124.7	128.1	129.2	133.3	138.5	143.8	146.8	152.4	158.7	172.9
62.5°	106.2	106.5	108.1	109.2	111.5	117.9	125.3	131.8	137.1	143.2	152.6
65°	88.9	89.6	89.6	90.4	91.9	93.4	96.3	101.6	110.9	119.5	126.6
67.5°	75.4	75.7	75.9	76.6	77.0	78.6	79.8	82.2	84.3	92.5	101.3
70°	66.5	67.6	67.2	68.0	68.3	69.1	70.6	71.7	75.1	76.9	82.2
72.5°	58.1	58.9	58.9	59.3	60.3	60.4	61.6	62.7	64.9	66.5	69.3
75°	47.1	46.7	47.1	47.8	48.2	48.5	48.5	50.0	51.2	52.7	54.5
77.5°	36.3	36.7	36.6	36.7	36.7	37.4	37.3	38.0	39.1	39.9	40.8
80°	29.1	29.5	29.1	29.5	29.9	30.2	29.9	30.2	31.4	32.1	32.1
82.5°	22.6	22.6	22.9	22.9	23.0	23.1	23.6	23.7	24.5	24.3	24.6
85°	13.4	13.1	13.1	13.1	13.4	13.8	13.4	13.4	13.8	13.8	13.8
87.5°	11.7	11.9	11.9	11.8	11.8	11.8	11.9	12.3	12.1	12.5	11.2
90°	34.4	34.2	34.0	33.8	33.5	33.6	34.1	34.5	35.0	35.4	30.5
92.5°	32.8	32.8	32.7	32.7	32.6	32.6	32.5	32.4	32.3	32.2	31.0
95°	62.8	63.2	63.7	64.1	64.6	64.8	64.8	64.8	64.8	64.8	64.4
97.5°	108.8	108.8	108.9	108.9	109.0	109.0	109.0	109.0	109.0	109.0	108.1
100°	138.8	139.0	139.2	139.4	139.7	139.8	139.8	139.8	139.8	139.8	139.1
102.5°	172.8	173.0	173.2	173.5	173.7	173.7	173.5	173.4	173.2	173.0	172.1
105°	224.9	224.9	224.9	224.9	224.9	224.6	224.2	223.7	223.3	222.8	222.4
107.5°	273.9	274.9	275.9	277.0	278.0	278.4	278.3	278.1	277.9	277.7	277.7
110°	312.0	312.6	313.3	314.0	314.7	315.0	315.0	315.0	315.0	315.0	315.0



TEST NUMBER: P331794

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	348.4	348.9	349.4	349.9	350.4	350.9	351.5	352.0	352.5	353.1	353.3
115°	405.1	405.8	406.5	407.2	407.8	408.3	408.5	408.7	409.0	409.2	409.6
117.5°	459.2	459.9	460.6	461.3	461.9	462.5	463.1	463.6	464.2	464.7	466.0
120°	497.3	498.0	498.7	499.3	500.0	500.4	500.4	500.4	500.4	500.4	502.2
122.5°	534.6	535.1	535.6	536.1	536.6	537.1	537.6	538.2	538.7	539.2	540.5
125°	591.5	591.7	592.0	592.2	592.4	592.9	593.5	594.2	594.9	595.6	596.2
127.5°	643.4	644.1	644.8	645.5	646.2	647.0	647.8	648.6	649.4	650.3	651.1
130°	680.6	681.5	682.4	683.3	684.2	684.9	685.4	685.8	686.3	686.7	687.2
132.5°	716.3	717.0	717.7	718.5	719.2	720.0	721.0	722.0	723.0	724.0	723.9
135°	771.8	772.5	773.1	773.8	774.5	774.9	775.2	775.4	775.6	775.8	775.4
137.5°	822.0	822.9	823.8	824.7	825.6	826.2	826.4	826.5	826.7	826.9	826.3
140°	856.9	857.8	858.7	859.6	860.5	860.9	860.9	860.9	860.9	860.9	859.8
142.5°	888.5	889.4	890.3	891.2	892.1	892.4	892.3	892.1	891.9	891.7	891.0
145°	935.9	936.8	937.7	938.6	939.5	939.8	939.6	939.4	939.1	938.9	937.6
147.5°	978.2	979.1	979.9	980.8	981.6	981.8	981.3	980.8	980.3	979.8	978.9
150°	1005.8	1006.4	1007.1	1007.8	1008.5	1008.5	1007.8	1007.1	1006.4	1005.8	1004.9
152.5°	1031.7	1032.5	1033.4	1034.3	1035.1	1035.1	1034.3	1033.4	1032.5	1031.7	1030.6
155°	1066.5	1067.2	1067.9	1068.6	1069.2	1069.0	1067.9	1066.8	1065.6	1064.5	1063.8
157.5°	1096.5	1097.6	1098.7	1099.8	1100.8	1100.6	1099.1	1097.6	1096.0	1094.5	1094.1
160°	1115.2	1116.1	1117.0	1117.9	1118.8	1118.5	1117.2	1115.8	1114.5	1113.1	1112.9
162.5°	1131.4	1132.4	1133.5	1134.6	1135.7	1135.5	1133.9	1132.4	1130.9	1129.3	1129.1
165°	1152.6	1153.8	1154.9	1156.0	1157.1	1156.9	1155.3	1153.8	1152.2	1150.6	1150.6
167.5°	1170.1	1171.2	1172.4	1173.6	1174.7	1174.5	1173.0	1171.4	1169.8	1168.2	1168.3
170°	1179.0	1180.3	1181.7	1183.0	1184.4	1184.3	1182.7	1181.1	1179.5	1178.0	1178.2
172.5°	1186.3	1187.6	1189.0	1190.3	1191.7	1191.5	1190.0	1188.4	1186.8	1185.2	1185.5
175°	1194.2	1195.5	1196.9	1198.2	1199.6	1199.4	1197.9	1196.3	1194.7	1193.1	1193.6
177.5°	1197.8	1198.9	1200.0	1201.0	1202.1	1202.1	1201.0	1200.0	1198.9	1197.8	1198.2
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331794

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1100.4	1098.1	1096.0	1090.6	1087.9	1081.9	1081.0	1080.7	1073.0	1065.5	1063.4
5°	1138.2	1132.3	1123.3	1112.8	1102.0	1090.8	1083.3	1077.4	1062.4	1048.2	1040.0
7.5°	1176.3	1163.5	1148.0	1128.2	1111.7	1093.2	1079.5	1067.1	1045.9	1025.6	1011.9
10°	1204.7	1183.8	1163.3	1136.0	1114.7	1093.8	1074.4	1057.6	1033.7	1006.8	987.7
12.5°	1222.3	1199.3	1171.0	1144.4	1116.8	1090.2	1064.2	1042.6	1014.6	986.8	964.1
15°	1246.2	1221.5	1187.2	1149.1	1113.6	1078.9	1049.0	1022.1	985.5	952.3	924.6
17.5°	1265.7	1231.7	1194.8	1150.8	1109.7	1065.6	1027.1	992.7	952.0	911.9	879.4
20°	1271.9	1238.3	1195.7	1151.7	1103.1	1051.2	1009.8	972.4	928.7	885.0	847.7
22.5°	1268.0	1241.9	1194.5	1141.8	1092.1	1037.8	991.0	947.6	899.2	854.6	811.3
25°	1241.7	1232.7	1187.9	1130.4	1073.6	1010.5	956.4	908.9	853.7	805.9	758.8
27.5°	1180.2	1199.6	1171.8	1110.5	1047.4	979.7	918.9	864.9	807.5	753.7	706.8
30°	1121.1	1165.5	1153.5	1096.8	1026.2	959.7	891.4	835.0	773.8	718.5	672.2
32.5°	1040.1	1113.5	1125.2	1077.7	1004.7	931.6	860.0	803.9	740.0	681.7	636.6
35°	911.2	1021.0	1071.4	1041.1	967.9	889.2	815.2	749.9	685.6	628.1	583.3
37.5°	757.4	906.9	991.0	993.1	925.9	844.0	763.5	698.6	632.8	576.4	527.9
40°	657.6	819.7	929.1	953.4	896.6	808.1	726.7	660.6	596.4	541.1	485.5
42.5°	568.0	729.5	864.0	906.2	861.1	773.2	691.5	622.4	559.9	507.6	450.8
45°	459.3	600.5	748.7	824.2	799.2	717.7	631.5	565.8	507.1	461.9	407.4
47.5°	387.5	487.0	630.4	732.5	732.0	657.7	572.9	509.9	455.5	413.2	369.0
50°	346.5	433.2	554.6	670.3	680.0	617.7	537.0	474.6	423.9	379.4	343.9
52.5°	309.8	381.2	490.3	601.3	628.9	574.9	496.7	439.1	389.8	348.9	318.5
55°	261.8	317.0	400.0	503.8	545.6	507.5	438.0	384.3	344.3	310.0	283.8
57.5°	221.4	262.9	329.4	413.0	461.7	437.7	380.5	336.8	302.6	271.5	250.9
60°	196.1	230.0	286.4	356.3	410.0	393.2	344.3	303.6	274.5	247.6	228.2
62.5°	172.2	201.4	249.7	306.4	355.7	348.7	308.8	274.6	249.1	224.6	208.2
65°	138.5	159.8	197.5	242.0	281.6	284.9	256.2	233.0	210.2	190.8	176.3
67.5°	110.3	124.2	150.8	188.2	217.9	228.5	210.9	193.2	175.1	160.1	147.5
70°	93.0	104.2	123.6	153.9	181.1	192.3	182.2	168.4	152.7	140.4	129.6
72.5°	75.4	86.3	100.6	122.8	146.2	158.3	154.8	144.8	132.1	121.9	111.7
75°	56.8	60.1	69.8	84.8	103.1	113.5	116.1	110.9	100.8	93.0	87.0
77.5°	42.0	44.0	48.6	56.5	68.4	77.7	81.6	81.0	74.0	69.5	63.9
80°	33.6	34.7	37.0	40.3	49.3	58.6	61.2	61.2	56.4	54.5	48.9
82.5°	25.5	26.4	27.7	29.6	33.8	41.9	44.8	45.4	42.3	39.9	35.5
85°	14.6	14.2	14.9	16.1	16.8	19.0	23.5	24.3	23.5	20.5	19.4
87.5°	10.2	9.5	8.5	7.4	7.2	7.0	7.9	8.9	8.2	7.9	7.8
90°	25.5	20.6	15.6	11.8	9.1	6.4	3.7	1.0	3.7	6.4	9.1
92.5°	29.9	28.7	27.5	26.0	24.0	22.0	20.0	18.0	20.0	22.0	24.0
95°	63.9	63.5	63.0	61.7	59.4	57.2	54.9	52.7	54.9	57.2	59.4
97.5°	107.3	106.4	105.6	104.1	102.2	100.2	98.2	96.2	98.2	100.2	102.2
100°	138.4	137.7	137.1	135.8	134.0	132.2	130.4	128.6	130.4	132.2	134.0
102.5°	171.3	170.4	169.6	168.4	167.0	165.5	164.1	162.7	164.1	165.5	167.0
105°	221.9	221.5	221.0	220.5	219.8	219.1	218.4	217.8	218.4	219.1	219.8
107.5°	277.7	277.7	277.7	277.2	276.2	275.2	274.3	273.3	274.3	275.2	276.2
110°	315.0	315.0	315.0	314.3	313.0	311.6	310.3	308.9	310.3	311.6	313.0



TEST NUMBER: P331794

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	353.4	353.6	353.8	353.2	351.9	350.5	349.2	347.8	349.2	350.5	351.9
115°	410.1	410.5	411.0	410.5	409.2	407.8	406.5	405.1	406.5	407.8	409.2
117.5°	467.2	468.5	469.7	469.5	467.7	465.9	464.1	462.3	464.1	465.9	467.7
120°	504.0	505.8	507.6	507.6	505.8	504.0	502.2	500.4	502.2	504.0	505.8
122.5°	541.8	543.0	544.3	543.8	541.7	539.5	537.4	535.2	537.4	539.5	541.7
125°	596.9	597.6	598.3	597.6	595.6	593.5	591.5	589.5	591.5	593.5	595.6
127.5°	651.9	652.7	653.5	652.6	650.1	647.5	644.9	642.4	644.9	647.5	650.1
130°	687.6	688.1	688.5	687.3	684.4	681.4	678.5	675.6	678.5	681.4	684.4
132.5°	723.8	723.7	723.6	722.4	720.0	717.6	715.2	712.8	715.2	717.6	720.0
135°	774.9	774.5	774.0	772.6	770.1	767.6	765.2	762.7	765.2	767.6	770.1
137.5°	825.7	825.1	824.6	823.2	821.2	819.2	817.2	815.1	817.2	819.2	821.2
140°	858.7	857.6	856.4	854.8	852.8	850.8	848.8	846.7	848.8	850.8	852.8
142.5°	890.2	889.4	888.7	887.3	885.2	883.2	881.2	879.2	881.2	883.2	885.2
145°	936.2	934.9	933.5	932.1	930.5	928.9	927.3	925.7	927.3	928.9	930.5
147.5°	978.0	977.1	976.2	974.8	972.9	971.1	969.2	967.3	969.2	971.1	972.9
150°	1004.0	1003.1	1002.2	1001.0	999.7	998.3	997.0	995.6	997.0	998.3	999.7
152.5°	1029.5	1028.5	1027.4	1026.2	1024.8	1023.5	1022.1	1020.8	1022.1	1023.5	1024.8
155°	1063.2	1062.5	1061.8	1061.1	1060.5	1059.8	1059.1	1058.4	1059.1	1059.8	1060.5
157.5°	1093.7	1093.3	1092.9	1092.4	1092.0	1091.5	1091.1	1090.6	1091.1	1091.5	1092.0
160°	1112.7	1112.5	1112.2	1111.9	1111.4	1111.0	1110.5	1110.1	1110.5	1111.0	1111.4
162.5°	1128.9	1128.7	1128.4	1128.3	1128.2	1128.1	1128.0	1127.9	1128.0	1128.1	1128.2
165°	1150.6	1150.6	1150.6	1150.7	1150.9	1151.2	1151.4	1151.6	1151.4	1151.2	1150.9
167.5°	1168.3	1168.4	1168.4	1168.8	1169.4	1170.1	1170.8	1171.5	1170.8	1170.1	1169.4
170°	1178.4	1178.6	1178.9	1179.3	1180.0	1180.7	1181.3	1182.0	1181.3	1180.7	1180.0
172.5°	1185.7	1185.9	1186.1	1186.6	1187.3	1187.9	1188.6	1189.3	1188.6	1187.9	1187.3
175°	1194.0	1194.5	1194.9	1195.5	1196.2	1196.9	1197.5	1198.2	1197.5	1196.9	1196.2
177.5°	1198.5	1198.9	1199.2	1199.7	1200.2	1200.8	1201.3	1201.9	1201.3	1200.8	1200.2
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331794

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1059.5	1057.4	1053.5	1047.6	1044.0	1037.7	1033.5	1035.9	1036.5	1035.9	1035.3
5°	1031.1	1023.2	1012.4	1001.9	992.2	981.8	975.8	973.2	967.9	965.0	963.5
7.5°	996.6	983.1	967.8	949.6	934.1	917.9	909.6	905.5	894.8	889.0	883.9
10°	970.9	949.6	934.3	910.4	895.9	874.6	860.0	860.4	845.8	837.6	831.6
12.5°	942.6	919.2	893.7	872.2	852.0	834.9	817.3	810.2	794.7	786.8	770.7
15°	895.5	868.2	841.4	812.2	791.7	765.2	739.8	708.8	683.8	662.1	656.1
17.5°	844.1	810.4	783.4	749.2	714.0	669.4	640.0	622.0	606.9	595.5	587.0
20°	808.9	774.5	745.8	694.2	646.8	616.5	594.9	581.1	565.4	553.1	546.3
22.5°	771.8	736.0	696.8	639.2	602.3	578.0	558.7	542.8	532.2	522.6	516.5
25°	719.2	680.0	615.4	575.8	546.0	520.6	507.1	497.4	486.2	473.1	467.2
27.5°	663.7	601.3	554.9	525.5	497.0	480.5	468.4	453.9	443.9	438.0	431.8
30°	622.1	559.8	523.6	491.4	471.3	453.0	438.8	430.6	420.9	410.8	406.7
32.5°	575.8	526.0	491.3	464.6	444.1	428.5	417.3	404.0	397.0	390.8	382.2
35°	518.3	480.6	448.9	427.2	407.8	395.1	382.0	374.2	361.5	356.3	352.9
37.5°	469.6	436.9	413.2	390.4	375.0	361.0	353.0	340.5	335.0	327.7	320.6
40°	442.1	410.0	387.3	368.6	351.4	340.9	330.9	320.8	312.6	309.2	300.6
42.5°	414.1	387.9	365.1	344.7	333.2	322.1	309.4	302.0	293.4	288.0	282.7
45°	375.3	352.2	332.7	315.9	303.2	291.7	283.4	271.1	266.3	255.4	250.9
47.5°	341.2	319.7	301.2	285.2	272.8	265.3	253.3	243.6	235.9	229.2	223.5
50°	317.0	299.1	281.2	267.0	255.8	245.0	232.7	227.8	215.8	212.5	209.1
52.5°	294.9	277.9	261.5	247.6	236.4	225.9	215.0	208.7	200.6	197.2	194.8
55°	264.0	247.6	231.9	219.6	208.4	197.5	190.8	183.0	179.2	176.6	173.6
57.5°	232.9	218.2	206.1	193.7	182.4	173.8	166.0	161.3	157.4	154.0	150.4
60°	213.2	199.0	188.2	176.6	165.1	158.0	152.0	146.4	141.9	136.7	135.2
62.5°	192.3	179.9	170.0	158.7	148.6	142.1	136.5	131.2	125.8	118.2	116.1
65°	163.6	153.9	143.4	134.1	125.1	118.8	110.5	104.6	102.3	101.6	101.2
67.5°	137.6	128.4	119.4	109.9	101.7	95.8	91.6	90.7	89.2	88.7	87.7
70°	120.2	111.7	102.7	93.7	85.9	84.8	83.3	81.8	79.9	79.2	78.4
72.5°	104.7	95.8	86.9	79.7	76.3	74.9	73.4	71.9	70.7	69.9	69.5
75°	80.3	72.1	66.1	63.5	61.6	60.5	58.3	57.1	56.4	55.3	54.9
77.5°	57.8	53.2	50.4	48.8	46.8	45.6	44.4	43.2	42.4	42.2	41.6
80°	44.1	41.8	40.0	37.7	37.0	35.5	35.1	34.0	34.4	33.2	33.2
82.5°	34.2	31.4	29.8	28.8	28.0	26.8	26.4	25.9	26.0	25.2	25.2
85°	17.6	16.8	16.1	15.3	15.3	14.2	14.6	14.2	14.2	13.4	13.1
87.5°	8.0	8.5	8.9	9.9	10.9	11.6	11.5	11.1	11.0	10.9	10.6
90°	11.8	15.6	20.6	25.5	30.5	35.4	35.0	34.5	34.1	33.6	33.5
92.5°	26.0	27.5	28.7	29.9	31.0	32.2	32.3	32.4	32.5	32.6	32.6
95°	61.7	63.0	63.5	63.9	64.4	64.8	64.8	64.8	64.8	64.8	64.6
97.5°	104.1	105.6	106.4	107.3	108.1	109.0	109.0	109.0	109.0	109.0	109.0
100°	135.8	137.1	137.7	138.4	139.1	139.8	139.8	139.8	139.8	139.8	139.7
102.5°	168.4	169.6	170.4	171.3	172.1	173.0	173.2	173.4	173.5	173.7	173.7
105°	220.5	221.0	221.5	221.9	222.4	222.8	223.3	223.7	224.2	224.6	224.9
107.5°	277.2	277.7	277.7	277.7	277.7	277.7	277.9	278.1	278.3	278.4	278.0
110°	314.3	315.0	315.0	315.0	315.0	315.0	315.0	315.0	315.0	315.0	314.7



TEST NUMBER: P331794

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	353.2	353.8	353.6	353.4	353.3	353.1	352.5	352.0	351.5	350.9	350.4
115°	410.5	411.0	410.5	410.1	409.6	409.2	409.0	408.7	408.5	408.3	407.8
117.5°	469.5	469.7	468.5	467.2	466.0	464.7	464.2	463.6	463.1	462.5	461.9
120°	507.6	507.6	505.8	504.0	502.2	500.4	500.4	500.4	500.4	500.4	500.0
122.5°	543.8	544.3	543.0	541.8	540.5	539.2	538.7	538.2	537.6	537.1	536.6
125°	597.6	598.3	597.6	596.9	596.2	595.6	594.9	594.2	593.5	592.9	592.4
127.5°	652.6	653.5	652.7	651.9	651.1	650.3	649.4	648.6	647.8	647.0	646.2
130°	687.3	688.5	688.1	687.6	687.2	686.7	686.3	685.8	685.4	684.9	684.2
132.5°	722.4	723.6	723.7	723.8	723.9	724.0	723.0	722.0	721.0	720.0	719.2
135°	772.6	774.0	774.5	774.9	775.4	775.8	775.6	775.4	775.2	774.9	774.5
137.5°	823.2	824.6	825.1	825.7	826.3	826.9	826.7	826.5	826.4	826.2	825.6
140°	854.8	856.4	857.6	858.7	859.8	860.9	860.9	860.9	860.9	860.9	860.5
142.5°	887.3	888.7	889.4	890.2	891.0	891.7	891.9	892.1	892.3	892.4	892.1
145°	932.1	933.5	934.9	936.2	937.6	938.9	939.1	939.4	939.6	939.8	939.5
147.5°	974.8	976.2	977.1	978.0	978.9	979.8	980.3	980.8	981.3	981.8	981.6
150°	1001.0	1002.2	1003.1	1004.0	1004.9	1005.8	1006.4	1007.1	1007.8	1008.5	1008.5
152.5°	1026.2	1027.4	1028.5	1029.5	1030.6	1031.7	1032.5	1033.4	1034.3	1035.1	1035.1
155°	1061.1	1061.8	1062.5	1063.2	1063.8	1064.5	1065.6	1066.8	1067.9	1069.0	1069.2
157.5°	1092.4	1092.9	1093.3	1093.7	1094.1	1094.5	1096.0	1097.6	1099.1	1100.6	1100.8
160°	1111.9	1112.2	1112.5	1112.7	1112.9	1113.1	1114.5	1115.8	1117.2	1118.5	1118.8
162.5°	1128.3	1128.4	1128.7	1128.9	1129.1	1129.3	1130.9	1132.4	1133.9	1135.5	1135.7
165°	1150.7	1150.6	1150.6	1150.6	1150.6	1150.6	1152.2	1153.8	1155.3	1156.9	1157.1
167.5°	1168.8	1168.4	1168.4	1168.3	1168.3	1168.2	1169.8	1171.4	1173.0	1174.5	1174.7
170°	1179.3	1178.9	1178.6	1178.4	1178.2	1178.0	1179.5	1181.1	1182.7	1184.3	1184.4
172.5°	1186.6	1186.1	1185.9	1185.7	1185.5	1185.2	1186.8	1188.4	1190.0	1191.5	1191.7
175°	1195.5	1194.9	1194.5	1194.0	1193.6	1193.1	1194.7	1196.3	1197.9	1199.4	1199.6
177.5°	1199.7	1199.2	1198.9	1198.5	1198.2	1197.8	1198.9	1200.0	1201.0	1202.1	1202.1
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331794

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1032.0	1032.6	1031.7	1032.3	1031.7	1032.6	1032.0	1035.3	1035.9	1036.5	1035.9
5°	961.6	957.1	956.4	955.3	956.4	957.1	961.6	963.5	965.0	967.9	973.2
7.5°	877.5	876.8	875.0	872.3	875.0	876.8	877.5	883.9	889.0	894.8	905.5
10°	823.4	821.6	821.2	818.6	821.2	821.6	823.4	831.6	837.6	845.8	860.4
12.5°	760.1	748.1	746.8	740.3	746.8	748.1	760.1	770.7	786.8	794.7	810.2
15°	647.2	644.9	637.5	632.6	637.5	644.9	647.2	656.1	662.1	683.8	708.8
17.5°	582.6	575.3	573.0	572.0	573.0	575.3	582.6	587.0	595.5	606.9	622.0
20°	541.1	534.4	533.3	532.5	533.3	534.4	541.1	546.3	553.1	565.4	581.1
22.5°	512.4	505.4	502.5	500.3	502.5	505.4	512.4	516.5	522.6	532.2	542.8
25°	463.4	460.8	459.3	458.6	459.3	460.8	463.4	467.2	473.1	486.2	497.4
27.5°	425.1	419.4	418.2	416.3	418.2	419.4	425.1	431.8	438.0	443.9	453.9
30°	403.3	401.4	398.8	396.6	398.8	401.4	403.3	406.7	410.8	420.9	430.6
32.5°	377.6	376.1	373.7	372.7	373.7	376.1	377.6	382.2	390.8	397.0	404.0
35°	349.2	343.9	341.7	338.3	341.7	343.9	349.2	352.9	356.3	361.5	374.2
37.5°	319.1	316.3	313.2	314.3	313.2	316.3	319.1	320.6	327.7	335.0	340.5
40°	295.8	293.9	293.1	292.8	293.1	293.9	295.8	300.6	309.2	312.6	320.8
42.5°	277.2	272.1	270.1	270.1	270.1	272.1	277.2	282.7	288.0	293.4	302.0
45°	249.1	244.2	240.9	241.2	240.9	244.2	249.1	250.9	255.4	266.3	271.1
47.5°	220.3	220.1	218.0	218.7	218.0	220.1	220.3	223.5	229.2	235.9	243.6
50°	206.5	204.3	202.8	203.1	202.8	204.3	206.5	209.1	212.5	215.8	227.8
52.5°	193.4	191.4	190.2	191.8	190.2	191.4	193.4	194.8	197.2	200.6	208.7
55°	171.8	169.5	169.2	168.8	169.2	169.5	171.8	173.6	176.6	179.2	183.0
57.5°	147.7	146.2	143.9	143.0	143.9	146.2	147.7	150.4	154.0	157.4	161.3
60°	130.3	127.3	123.6	123.2	123.6	127.3	130.3	135.2	136.7	141.9	146.4
62.5°	114.5	113.9	113.2	113.1	113.2	113.9	114.5	116.1	118.2	125.8	131.2
65°	100.5	100.1	100.5	100.8	100.5	100.1	100.5	101.2	101.6	102.3	104.6
67.5°	87.5	86.9	86.2	86.5	86.2	86.9	87.5	87.7	88.7	89.2	90.7
70°	77.7	77.3	76.9	76.9	76.9	77.3	77.7	78.4	79.2	79.9	81.8
72.5°	68.1	68.0	67.7	67.4	67.7	68.0	68.1	69.5	69.9	70.7	71.9
75°	54.5	53.8	53.8	53.8	53.8	53.8	54.5	54.9	55.3	56.4	57.1
77.5°	41.5	41.2	40.8	40.5	40.8	41.2	41.5	41.6	42.2	42.4	43.2
80°	32.9	32.5	32.1	32.1	32.1	32.5	32.9	33.2	33.2	34.4	34.0
82.5°	25.1	24.7	24.6	24.3	24.6	24.7	25.1	25.2	25.2	26.0	25.9
85°	13.4	13.8	13.4	14.2	13.4	13.8	13.4	13.1	13.4	14.2	14.2
87.5°	10.6	10.4	10.7	10.5	10.7	10.4	10.6	10.6	10.9	11.0	11.1
90°	33.8	34.0	34.2	34.4	34.2	34.0	33.8	33.5	33.6	34.1	34.5
92.5°	32.7	32.7	32.8	32.8	32.8	32.7	32.7	32.6	32.6	32.5	32.4
95°	64.1	63.7	63.2	62.8	63.2	63.7	64.1	64.6	64.8	64.8	64.8
97.5°	108.9	108.9	108.8	108.8	108.8	108.9	108.9	109.0	109.0	109.0	109.0
100°	139.4	139.2	139.0	138.8	139.0	139.2	139.4	139.7	139.8	139.8	139.8
102.5°	173.5	173.2	173.0	172.8	173.0	173.2	173.5	173.7	173.7	173.5	173.4
105°	224.9	224.9	224.9	224.9	224.9	224.9	224.9	224.9	224.6	224.2	223.7
107.5°	277.0	275.9	274.9	273.9	274.9	275.9	277.0	278.0	278.4	278.3	278.1
110°	314.0	313.3	312.6	312.0	312.6	313.3	314.0	314.7	315.0	315.0	315.0



TEST NUMBER: P331794

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	349.9	349.4	348.9	348.4	348.9	349.4	349.9	350.4	350.9	351.5	352.0
115°	407.2	406.5	405.8	405.1	405.8	406.5	407.2	407.8	408.3	408.5	408.7
117.5°	461.3	460.6	459.9	459.2	459.9	460.6	461.3	461.9	462.5	463.1	463.6
120°	499.3	498.7	498.0	497.3	498.0	498.7	499.3	500.0	500.4	500.4	500.4
122.5°	536.1	535.6	535.1	534.6	535.1	535.6	536.1	536.6	537.1	537.6	538.2
125°	592.2	592.0	591.7	591.5	591.7	592.0	592.2	592.4	592.9	593.5	594.2
127.5°	645.5	644.8	644.1	643.4	644.1	644.8	645.5	646.2	647.0	647.8	648.6
130°	683.3	682.4	681.5	680.6	681.5	682.4	683.3	684.2	684.9	685.4	685.8
132.5°	718.5	717.7	717.0	716.3	717.0	717.7	718.5	719.2	720.0	721.0	722.0
135°	773.8	773.1	772.5	771.8	772.5	773.1	773.8	774.5	774.9	775.2	775.4
137.5°	824.7	823.8	822.9	822.0	822.9	823.8	824.7	825.6	826.2	826.4	826.5
140°	859.6	858.7	857.8	856.9	857.8	858.7	859.6	860.5	860.9	860.9	860.9
142.5°	891.2	890.3	889.4	888.5	889.4	890.3	891.2	892.1	892.4	892.3	892.1
145°	938.6	937.7	936.8	935.9	936.8	937.7	938.6	939.5	939.8	939.6	939.4
147.5°	980.8	979.9	979.1	978.2	979.1	979.9	980.8	981.6	981.8	981.3	980.8
150°	1007.8	1007.1	1006.4	1005.8	1006.4	1007.1	1007.8	1008.5	1008.5	1007.8	1007.1
152.5°	1034.3	1033.4	1032.5	1031.7	1032.5	1033.4	1034.3	1035.1	1035.1	1034.3	1033.4
155°	1068.6	1067.9	1067.2	1066.5	1067.2	1067.9	1068.6	1069.2	1069.0	1067.9	1066.8
157.5°	1099.8	1098.7	1097.6	1096.5	1097.6	1098.7	1099.8	1100.8	1100.6	1099.1	1097.6
160°	1117.9	1117.0	1116.1	1115.2	1116.1	1117.0	1117.9	1118.8	1118.5	1117.2	1115.8
162.5°	1134.6	1133.5	1132.4	1131.4	1132.4	1133.5	1134.6	1135.7	1135.5	1133.9	1132.4
165°	1156.0	1154.9	1153.8	1152.6	1153.8	1154.9	1156.0	1157.1	1156.9	1155.3	1153.8
167.5°	1173.6	1172.4	1171.2	1170.1	1171.2	1172.4	1173.6	1174.7	1174.5	1173.0	1171.4
170°	1183.0	1181.7	1180.3	1179.0	1180.3	1181.7	1183.0	1184.4	1184.3	1182.7	1181.1
172.5°	1190.3	1189.0	1187.6	1186.3	1187.6	1189.0	1190.3	1191.7	1191.5	1190.0	1188.4
175°	1198.2	1196.9	1195.5	1194.2	1195.5	1196.9	1198.2	1199.6	1199.4	1197.9	1196.3
177.5°	1201.0	1200.0	1198.9	1197.8	1198.9	1200.0	1201.0	1202.1	1202.1	1201.0	1200.0
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331794

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1033.5	1037.7	1044.0	1047.6	1053.5	1057.4	1059.5	1063.4	1065.5	1073.0	1080.7
5°	975.8	981.8	992.2	1001.9	1012.4	1023.2	1031.1	1040.0	1048.2	1062.4	1077.4
7.5°	909.6	917.9	934.1	949.6	967.8	983.1	996.6	1011.9	1025.6	1045.9	1067.1
10°	860.0	874.6	895.9	910.4	934.3	949.6	970.9	987.7	1006.8	1033.7	1057.6
12.5°	817.3	834.9	852.0	872.2	893.7	919.2	942.6	964.1	986.8	1014.6	1042.6
15°	739.8	765.2	791.7	812.2	841.4	868.2	895.5	924.6	952.3	985.5	1022.1
17.5°	640.0	669.4	714.0	749.2	783.4	810.4	844.1	879.4	911.9	952.0	992.7
20°	594.9	616.5	646.8	694.2	745.8	774.5	808.9	847.7	885.0	928.7	972.4
22.5°	558.7	578.0	602.3	639.2	696.8	736.0	771.8	811.3	854.6	899.2	947.6
25°	507.1	520.6	546.0	575.8	615.4	680.0	719.2	758.8	805.9	853.7	908.9
27.5°	468.4	480.5	497.0	525.5	554.9	601.3	663.7	706.8	753.7	807.5	864.9
30°	438.8	453.0	471.3	491.4	523.6	559.8	622.1	672.2	718.5	773.8	835.0
32.5°	417.3	428.5	444.1	464.6	491.3	526.0	575.8	636.6	681.7	740.0	803.9
35°	382.0	395.1	407.8	427.2	448.9	480.6	518.3	583.3	628.1	685.6	749.9
37.5°	353.0	361.0	375.0	390.4	413.2	436.9	469.6	527.9	576.4	632.8	698.6
40°	330.9	340.9	351.4	368.6	387.3	410.0	442.1	485.5	541.1	596.4	660.6
42.5°	309.4	322.1	333.2	344.7	365.1	387.9	414.1	450.8	507.6	559.9	622.4
45°	283.4	291.7	303.2	315.9	332.7	352.2	375.3	407.4	461.9	507.1	565.8
47.5°	253.3	265.3	272.8	285.2	301.2	319.7	341.2	369.0	413.2	455.5	509.9
50°	232.7	245.0	255.8	267.0	281.2	299.1	317.0	343.9	379.4	423.9	474.6
52.5°	215.0	225.9	236.4	247.6	261.5	277.9	294.9	318.5	348.9	389.8	439.1
55°	190.8	197.5	208.4	219.6	231.9	247.6	264.0	283.8	310.0	344.3	384.3
57.5°	166.0	173.8	182.4	193.7	206.1	218.2	232.9	250.9	271.5	302.6	336.8
60°	152.0	158.0	165.1	176.6	188.2	199.0	213.2	228.2	247.6	274.5	303.6
62.5°	136.5	142.1	148.6	158.7	170.0	179.9	192.3	208.2	224.6	249.1	274.6
65°	110.5	118.8	125.1	134.1	143.4	153.9	163.6	176.3	190.8	210.2	233.0
67.5°	91.6	95.8	101.7	109.9	119.4	128.4	137.6	147.5	160.1	175.1	193.2
70°	83.3	84.8	85.9	93.7	102.7	111.7	120.2	129.6	140.4	152.7	168.4
72.5°	73.4	74.9	76.3	79.7	86.9	95.8	104.7	111.7	121.9	132.1	144.8
75°	58.3	60.5	61.6	63.5	66.1	72.1	80.3	87.0	93.0	100.8	110.9
77.5°	44.4	45.6	46.8	48.8	50.4	53.2	57.8	63.9	69.5	74.0	81.0
80°	35.1	35.5	37.0	37.7	40.0	41.8	44.1	48.9	54.5	56.4	61.2
82.5°	26.4	26.8	28.0	28.8	29.8	31.4	34.2	35.5	39.9	42.3	45.4
85°	14.6	14.2	15.3	15.3	16.1	16.8	17.6	19.4	20.5	23.5	24.3
87.5°	11.5	11.6	10.9	9.9	8.9	8.5	8.0	7.8	7.9	8.2	8.9
90°	35.0	35.4	30.5	25.5	20.6	15.6	11.8	9.1	6.4	3.7	1.0
92.5°	32.3	32.2	31.0	29.9	28.7	27.5	26.0	24.0	22.0	20.0	18.0
95°	64.8	64.8	64.4	63.9	63.5	63.0	61.7	59.4	57.2	54.9	52.7
97.5°	109.0	109.0	108.1	107.3	106.4	105.6	104.1	102.2	100.2	98.2	96.2
100°	139.8	139.8	139.1	138.4	137.7	137.1	135.8	134.0	132.2	130.4	128.6
102.5°	173.2	173.0	172.1	171.3	170.4	169.6	168.4	167.0	165.5	164.1	162.7
105°	223.3	222.8	222.4	221.9	221.5	221.0	220.5	219.8	219.1	218.4	217.8
107.5°	277.9	277.7	277.7	277.7	277.7	277.7	277.2	276.2	275.2	274.3	273.3
110°	315.0	315.0	315.0	315.0	315.0	315.0	314.3	313.0	311.6	310.3	308.9



TEST NUMBER: P331794

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	352.5	353.1	353.3	353.4	353.6	353.8	353.2	351.9	350.5	349.2	347.8
115°	409.0	409.2	409.6	410.1	410.5	411.0	410.5	409.2	407.8	406.5	405.1
117.5°	464.2	464.7	466.0	467.2	468.5	469.7	469.5	467.7	465.9	464.1	462.3
120°	500.4	500.4	502.2	504.0	505.8	507.6	507.6	505.8	504.0	502.2	500.4
122.5°	538.7	539.2	540.5	541.8	543.0	544.3	543.8	541.7	539.5	537.4	535.2
125°	594.9	595.6	596.2	596.9	597.6	598.3	597.6	595.6	593.5	591.5	589.5
127.5°	649.4	650.3	651.1	651.9	652.7	653.5	652.6	650.1	647.5	644.9	642.4
130°	686.3	686.7	687.2	687.6	688.1	688.5	687.3	684.4	681.4	678.5	675.6
132.5°	723.0	724.0	723.9	723.8	723.7	723.6	722.4	720.0	717.6	715.2	712.8
135°	775.6	775.8	775.4	774.9	774.5	774.0	772.6	770.1	767.6	765.2	762.7
137.5°	826.7	826.9	826.3	825.7	825.1	824.6	823.2	821.2	819.2	817.2	815.1
140°	860.9	860.9	859.8	858.7	857.6	856.4	854.8	852.8	850.8	848.8	846.7
142.5°	891.9	891.7	891.0	890.2	889.4	888.7	887.3	885.2	883.2	881.2	879.2
145°	939.1	938.9	937.6	936.2	934.9	933.5	932.1	930.5	928.9	927.3	925.7
147.5°	980.3	979.8	978.9	978.0	977.1	976.2	974.8	972.9	971.1	969.2	967.3
150°	1006.4	1005.8	1004.9	1004.0	1003.1	1002.2	1001.0	999.7	998.3	997.0	995.6
152.5°	1032.5	1031.7	1030.6	1029.5	1028.5	1027.4	1026.2	1024.8	1023.5	1022.1	1020.8
155°	1065.6	1064.5	1063.8	1063.2	1062.5	1061.8	1061.1	1060.5	1059.8	1059.1	1058.4
157.5°	1096.0	1094.5	1094.1	1093.7	1093.3	1092.9	1092.4	1092.0	1091.5	1091.1	1090.6
160°	1114.5	1113.1	1112.9	1112.7	1112.5	1112.2	1111.9	1111.4	1111.0	1110.5	1110.1
162.5°	1130.9	1129.3	1129.1	1128.9	1128.7	1128.4	1128.3	1128.2	1128.1	1128.0	1127.9
165°	1152.2	1150.6	1150.6	1150.6	1150.6	1150.6	1150.7	1150.9	1151.2	1151.4	1151.6
167.5°	1169.8	1168.2	1168.3	1168.3	1168.4	1168.4	1168.8	1169.4	1170.1	1170.8	1171.5
170°	1179.5	1178.0	1178.2	1178.4	1178.6	1178.9	1179.3	1180.0	1180.7	1181.3	1182.0
172.5°	1186.8	1185.2	1185.5	1185.7	1185.9	1186.1	1186.6	1187.3	1187.9	1188.6	1189.3
175°	1194.7	1193.1	1193.6	1194.0	1194.5	1194.9	1195.5	1196.2	1196.9	1197.5	1198.2
177.5°	1198.9	1197.8	1198.2	1198.5	1198.9	1199.2	1199.7	1200.2	1200.8	1201.3	1201.9
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331794

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1081.0	1081.9	1087.9	1090.6	1096.0	1098.1	1100.4	1099.8	1099.8	1101.0	1109.4
5°	1083.3	1090.8	1102.0	1112.8	1123.3	1132.3	1138.2	1144.2	1146.4	1157.3	1167.0
7.5°	1079.5	1093.2	1111.7	1128.2	1148.0	1163.5	1176.3	1187.9	1195.8	1211.6	1227.7
10°	1074.4	1093.8	1114.7	1136.0	1163.3	1183.8	1204.7	1220.8	1226.0	1249.5	1263.0
12.5°	1064.2	1090.2	1116.8	1144.4	1171.0	1199.3	1222.3	1238.4	1256.8	1277.9	1302.7
15°	1049.0	1078.9	1113.6	1149.1	1187.2	1221.5	1246.2	1274.2	1294.3	1317.5	1339.1
17.5°	1027.1	1065.6	1109.7	1150.8	1194.8	1231.7	1265.7	1292.5	1306.7	1319.9	1323.2
20°	1009.8	1051.2	1103.1	1151.7	1195.7	1238.3	1271.9	1294.3	1298.1	1298.4	1278.6
22.5°	991.0	1037.8	1092.1	1141.8	1194.5	1241.9	1268.0	1277.6	1262.8	1237.5	1199.2
25°	956.4	1010.5	1073.6	1130.4	1187.9	1232.7	1241.7	1224.9	1173.0	1118.4	1049.4
27.5°	918.9	979.7	1047.4	1110.5	1171.8	1199.6	1180.2	1119.6	1026.1	944.9	846.4
30°	891.4	959.7	1026.2	1096.8	1153.5	1165.5	1121.1	1031.8	922.8	800.3	702.1
32.5°	860.0	931.6	1004.7	1077.7	1125.2	1113.5	1040.1	930.2	802.4	682.0	589.1
35°	815.2	889.2	967.9	1041.1	1071.4	1021.0	911.2	768.2	637.5	525.1	461.2
37.5°	763.5	844.0	925.9	993.1	991.0	906.9	757.4	609.7	499.9	433.4	387.9
40°	726.7	808.1	896.6	953.4	929.1	819.7	657.6	518.3	438.0	385.0	351.8
42.5°	691.5	773.2	861.1	906.2	864.0	729.5	568.0	458.9	392.6	351.3	324.3
45°	631.5	717.7	799.2	824.2	748.7	600.5	459.3	380.2	336.1	305.5	286.8
47.5°	572.9	657.7	732.0	732.5	630.4	487.0	387.5	329.0	291.4	267.7	254.1
50°	537.0	617.7	680.0	670.3	554.6	433.2	346.5	296.1	264.8	246.5	232.3
52.5°	496.7	574.9	628.9	601.3	490.3	381.2	309.8	267.5	241.5	225.6	212.9
55°	438.0	507.5	545.6	503.8	400.0	317.0	261.8	228.5	209.1	195.7	184.9
57.5°	380.5	437.7	461.7	413.0	329.4	262.9	221.4	196.5	177.2	167.6	162.0
60°	344.3	393.2	410.0	356.3	286.4	230.0	196.1	172.9	158.7	152.4	146.8
62.5°	308.8	348.7	355.7	306.4	249.7	201.4	172.2	152.6	143.2	137.1	131.8
65°	256.2	284.9	281.6	242.0	197.5	159.8	138.5	126.6	119.5	110.9	101.6
67.5°	210.9	228.5	217.9	188.2	150.8	124.2	110.3	101.3	92.5	84.3	82.2
70°	182.2	192.3	181.1	153.9	123.6	104.2	93.0	82.2	76.9	75.1	71.7
72.5°	154.8	158.3	146.2	122.8	100.6	86.3	75.4	69.3	66.5	64.9	62.7
75°	116.1	113.5	103.1	84.8	69.8	60.1	56.8	54.5	52.7	51.2	50.0
77.5°	81.6	77.7	68.4	56.5	48.6	44.0	42.0	40.8	39.9	39.1	38.0
80°	61.2	58.6	49.3	40.3	37.0	34.7	33.6	32.1	32.1	31.4	30.2
82.5°	44.8	41.9	33.8	29.6	27.7	26.4	25.5	24.6	24.3	24.5	23.7
85°	23.5	19.0	16.8	16.1	14.9	14.2	14.6	13.8	13.8	13.8	13.4
87.5°	7.9	7.0	7.2	7.4	8.5	9.5	10.2	11.2	12.5	12.1	12.3
90°	3.7	6.4	9.1	11.8	15.6	20.6	25.5	30.5	35.4	35.0	34.5
92.5°	20.0	22.0	24.0	26.0	27.5	28.7	29.9	31.0	32.2	32.3	32.4
95°	54.9	57.2	59.4	61.7	63.0	63.5	63.9	64.4	64.8	64.8	64.8
97.5°	98.2	100.2	102.2	104.1	105.6	106.4	107.3	108.1	109.0	109.0	109.0
100°	130.4	132.2	134.0	135.8	137.1	137.7	138.4	139.1	139.8	139.8	139.8
102.5°	164.1	165.5	167.0	168.4	169.6	170.4	171.3	172.1	173.0	173.2	173.4
105°	218.4	219.1	219.8	220.5	221.0	221.5	221.9	222.4	222.8	223.3	223.7
107.5°	274.3	275.2	276.2	277.2	277.7	277.7	277.7	277.7	277.7	277.9	278.1
110°	310.3	311.6	313.0	314.3	315.0	315.0	315.0	315.0	315.0	315.0	315.0



TEST NUMBER: P331794

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	349.2	350.5	351.9	353.2	353.8	353.6	353.4	353.3	353.1	352.5	352.0
115°	406.5	407.8	409.2	410.5	411.0	410.5	410.1	409.6	409.2	409.0	408.7
117.5°	464.1	465.9	467.7	469.5	469.7	468.5	467.2	466.0	464.7	464.2	463.6
120°	502.2	504.0	505.8	507.6	507.6	505.8	504.0	502.2	500.4	500.4	500.4
122.5°	537.4	539.5	541.7	543.8	544.3	543.0	541.8	540.5	539.2	538.7	538.2
125°	591.5	593.5	595.6	597.6	598.3	597.6	596.9	596.2	595.6	594.9	594.2
127.5°	644.9	647.5	650.1	652.6	653.5	652.7	651.9	651.1	650.3	649.4	648.6
130°	678.5	681.4	684.4	687.3	688.5	688.1	687.6	687.2	686.7	686.3	685.8
132.5°	715.2	717.6	720.0	722.4	723.6	723.7	723.8	723.9	724.0	723.0	722.0
135°	765.2	767.6	770.1	772.6	774.0	774.5	774.9	775.4	775.8	775.6	775.4
137.5°	817.2	819.2	821.2	823.2	824.6	825.1	825.7	826.3	826.9	826.7	826.5
140°	848.8	850.8	852.8	854.8	856.4	857.6	858.7	859.8	860.9	860.9	860.9
142.5°	881.2	883.2	885.2	887.3	888.7	889.4	890.2	891.0	891.7	891.9	892.1
145°	927.3	928.9	930.5	932.1	933.5	934.9	936.2	937.6	938.9	939.1	939.4
147.5°	969.2	971.1	972.9	974.8	976.2	977.1	978.0	978.9	979.8	980.3	980.8
150°	997.0	998.3	999.7	1001.0	1002.2	1003.1	1004.0	1004.9	1005.8	1006.4	1007.1
152.5°	1022.1	1023.5	1024.8	1026.2	1027.4	1028.5	1029.5	1030.6	1031.7	1032.5	1033.4
155°	1059.1	1059.8	1060.5	1061.1	1061.8	1062.5	1063.2	1063.8	1064.5	1065.6	1066.8
157.5°	1091.1	1091.5	1092.0	1092.4	1092.9	1093.3	1093.7	1094.1	1094.5	1096.0	1097.6
160°	1110.5	1111.0	1111.4	1111.9	1112.2	1112.5	1112.7	1112.9	1113.1	1114.5	1115.8
162.5°	1128.0	1128.1	1128.2	1128.3	1128.4	1128.7	1128.9	1129.1	1129.3	1130.9	1132.4
165°	1151.4	1151.2	1150.9	1150.7	1150.6	1150.6	1150.6	1150.6	1150.6	1152.2	1153.8
167.5°	1170.8	1170.1	1169.4	1168.8	1168.4	1168.4	1168.3	1168.3	1168.2	1169.8	1171.4
170°	1181.3	1180.7	1180.0	1179.3	1178.9	1178.6	1178.4	1178.2	1178.0	1179.5	1181.1
172.5°	1188.6	1187.9	1187.3	1186.6	1186.1	1185.9	1185.7	1185.5	1185.2	1186.8	1188.4
175°	1197.5	1196.9	1196.2	1195.5	1194.9	1194.5	1194.0	1193.6	1193.1	1194.7	1196.3
177.5°	1201.3	1200.8	1200.2	1199.7	1199.2	1198.9	1198.5	1198.2	1197.8	1198.9	1200.0
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331794

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1112.4	1116.3	1118.1	1118.1	1120.2	1119.3	1118.4
5°	1176.3	1183.4	1184.9	1191.6	1196.5	1195.0	1195.7
7.5°	1239.9	1251.3	1262.6	1267.7	1268.6	1271.6	1272.7
10°	1279.0	1288.4	1305.9	1303.3	1316.4	1323.8	1311.5
12.5°	1316.7	1329.3	1341.5	1344.8	1352.2	1354.6	1349.7
15°	1350.7	1357.4	1358.2	1356.3	1358.6	1356.7	1349.6
17.5°	1318.9	1308.0	1285.9	1275.4	1267.1	1254.9	1250.0
20°	1266.3	1234.2	1196.9	1181.9	1164.4	1130.0	1138.2
22.5°	1152.8	1116.2	1078.9	1035.2	1014.4	981.8	979.9
25°	976.2	913.1	843.6	795.0	766.7	734.2	720.0
27.5°	759.0	679.5	622.6	593.8	567.5	541.8	540.7
30°	616.2	556.4	512.4	487.7	471.7	460.8	463.1
32.5°	519.4	478.4	448.7	428.3	416.4	408.2	408.1
35°	424.6	396.6	377.5	369.0	360.4	354.4	354.8
37.5°	363.4	346.5	335.9	326.5	321.1	318.2	316.5
40°	332.0	318.2	310.0	304.4	299.9	295.8	295.0
42.5°	307.2	295.8	287.5	283.1	279.0	276.0	275.3
45°	272.6	263.3	255.8	250.9	249.1	246.5	246.5
47.5°	242.5	233.3	227.5	224.4	221.2	219.5	219.4
50°	222.2	215.1	209.9	208.0	205.4	204.3	203.9
52.5°	204.0	198.7	194.9	193.7	192.5	191.1	191.3
55°	179.2	176.3	174.8	173.6	171.8	169.5	171.0
57.5°	158.4	155.9	151.8	148.3	146.6	145.0	145.6
60°	143.8	138.5	133.3	129.2	128.1	124.7	124.7
62.5°	125.3	117.9	111.5	109.2	108.1	106.5	106.2
65°	96.3	93.4	91.9	90.4	89.6	89.6	88.9
67.5°	79.8	78.6	77.0	76.6	75.9	75.7	75.4
70°	70.6	69.1	68.3	68.0	67.2	67.6	66.5
72.5°	61.6	60.4	60.3	59.3	58.9	58.9	58.1
75°	48.5	48.5	48.2	47.8	47.1	46.7	47.1
77.5°	37.3	37.4	36.7	36.7	36.6	36.7	36.3
80°	29.9	30.2	29.9	29.5	29.1	29.5	29.1
82.5°	23.6	23.1	23.0	22.9	22.9	22.6	22.6
85°	13.4	13.8	13.4	13.1	13.1	13.1	13.4
87.5°	11.9	11.8	11.8	11.8	11.9	11.9	11.7
90°	34.1	33.6	33.5	33.8	34.0	34.2	34.4
92.5°	32.5	32.6	32.6	32.7	32.7	32.8	32.8
95°	64.8	64.8	64.6	64.1	63.7	63.2	62.8
97.5°	109.0	109.0	109.0	108.9	108.9	108.8	108.8
100°	139.8	139.8	139.7	139.4	139.2	139.0	138.8
102.5°	173.5	173.7	173.7	173.5	173.2	173.0	172.8
105°	224.2	224.6	224.9	224.9	224.9	224.9	224.9
107.5°	278.3	278.4	278.0	277.0	275.9	274.9	273.9
110°	315.0	315.0	314.7	314.0	313.3	312.6	312.0



TEST NUMBER: P331794

CATALOG NUMBER: S122RDIW-S485D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	351.5	350.9	350.4	349.9	349.4	348.9	348.4
115°	408.5	408.3	407.8	407.2	406.5	405.8	405.1
117.5°	463.1	462.5	461.9	461.3	460.6	459.9	459.2
120°	500.4	500.4	500.0	499.3	498.7	498.0	497.3
122.5°	537.6	537.1	536.6	536.1	535.6	535.1	534.6
125°	593.5	592.9	592.4	592.2	592.0	591.7	591.5
127.5°	647.8	647.0	646.2	645.5	644.8	644.1	643.4
130°	685.4	684.9	684.2	683.3	682.4	681.5	680.6
132.5°	721.0	720.0	719.2	718.5	717.7	717.0	716.3
135°	775.2	774.9	774.5	773.8	773.1	772.5	771.8
137.5°	826.4	826.2	825.6	824.7	823.8	822.9	822.0
140°	860.9	860.9	860.5	859.6	858.7	857.8	856.9
142.5°	892.3	892.4	892.1	891.2	890.3	889.4	888.5
145°	939.6	939.8	939.5	938.6	937.7	936.8	935.9
147.5°	981.3	981.8	981.6	980.8	979.9	979.1	978.2
150°	1007.8	1008.5	1008.5	1007.8	1007.1	1006.4	1005.8
152.5°	1034.3	1035.1	1035.1	1034.3	1033.4	1032.5	1031.7
155°	1067.9	1069.0	1069.2	1068.6	1067.9	1067.2	1066.5
157.5°	1099.1	1100.6	1100.8	1099.8	1098.7	1097.6	1096.5
160°	1117.2	1118.5	1118.8	1117.9	1117.0	1116.1	1115.2
162.5°	1133.9	1135.5	1135.7	1134.6	1133.5	1132.4	1131.4
165°	1155.3	1156.9	1157.1	1156.0	1154.9	1153.8	1152.6
167.5°	1173.0	1174.5	1174.7	1173.6	1172.4	1171.2	1170.1
170°	1182.7	1184.3	1184.4	1183.0	1181.7	1180.3	1179.0
172.5°	1190.0	1191.5	1191.7	1190.3	1189.0	1187.6	1186.3
175°	1197.9	1199.4	1199.6	1198.2	1196.9	1195.5	1194.2
177.5°	1201.0	1202.1	1202.1	1201.0	1200.0	1198.9	1197.8
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2

(END OF REPORT)