

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331812-840

Luminaire Tested: **S122RDIW-S675D710U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331812-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D710U840-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4829.5 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331812-840

CATALOG NUMBER: S122RDIW-S675D710U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331812-840

CATALOG NUMBER: S122RDIW-S675D710U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	87	90	87	83	80	73	71	69	61	59	58	49	48	47	42
2	90	82	77	72	82	76	71	67	65	61	58	54	51	49	44	42	40	36
3	82	73	66	60	75	67	61	56	57	53	49	48	45	42	39	37	35	31
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	33	31	27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24
6	64	52	44	39	59	49	42	36	42	36	32	35	31	28	29	26	24	21
7	59	47	39	34	54	44	37	32	38	32	29	32	28	25	27	24	21	19
8	55	43	35	30	51	40	33	29	35	29	25	30	25	22	25	22	19	17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18392	18392	18392
5°	18462	18162	18263
10°	18321	17864	17713
15°	18111	17336	16836
20°	17819	16579	15747
25°	17521	15720	14694
30°	17107	14838	13340
35°	16703	13878	12151
40°	16297	12886	10777
45°	15819	11768	9533
50°	15330	10643	8312
55°	14829	9433	7139
60°	14247	8157	5926
65°	13589	6854	5398
70°	12798	5646	4961
75°	11834	5147	4629
80°	10451	4603	4212
85°	8207	3631	3631



TEST NUMBER: P331812-840

CATALOG NUMBER: S122RDIW-S675D710U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.6	2.2
10°-20°	292.8	6.1
20°-30°	411.1	8.5
30°-40°	448.3	9.3
40°-50°	412.2	8.5
50°-60°	323.8	6.7
60°-70°	211.1	4.4
70°-80°	108.8	2.3
80°-90°	31.8	0.7
90°-100°	56.3	1.2
100°-110°	174.8	3.6
110°-120°	298.7	6.2
120°-130°	392.8	8.1
130°-140°	440.9	9.1
140°-150°	432.3	9.0
150°-160°	362.6	7.5
160°-170°	240.5	5.0
170°-180°	84.1	1.7
0°-30°	810.5	16.8
0°-40°	1258.9	26.1
0°-60°	1994.8	41.3
0°-90°	2346.5	48.6
90°-120°	529.8	11.0
90°-150°	1795.8	37.2
90°-180°	2483.0	51.4
0°-180°	4829.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1139	1139	1139	1139	1139	
5°	1139	1134	1121	1129	1127	108
15°	1084	1071	1037	1018	1007	305
25°	984	949	882	842	825	452
35°	847	793	704	642	616	530
45°	693	622	515	445	418	535
55°	527	445	335	276	254	471
65°	356	272	179	146	141	352
75°	190	120	82	76	74	201
85°	44	24	20	20	20	52
90°	1	10	26	25	25	4
95°	39	46	48	48	46	45
105°	161	163	165	166	166	170
115°	300	304	303	302	300	296
125°	436	442	441	438	438	390
135°	564	572	574	573	571	436
145°	685	690	695	695	692	428
155°	783	785	788	791	789	360
165°	852	851	851	856	853	240
175°	886	884	883	888	884	84
180°	888	888	888	888	888	



TEST NUMBER: P331812-840

CATALOG NUMBER: S122RDIW-S675D710U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1
2.5°	1143.3	1142.4	1141.5	1140.5	1139.6	1138.1	1136.1	1134.1	1132.2	1130.1	1132.0
5°	1139.1	1138.0	1136.9	1135.7	1134.6	1132.6	1129.5	1126.6	1123.6	1120.6	1122.7
7.5°	1127.4	1126.0	1124.6	1123.2	1121.8	1119.2	1115.8	1112.4	1108.8	1105.4	1105.9
10°	1117.5	1115.9	1114.3	1112.7	1111.1	1108.0	1103.4	1098.8	1094.3	1089.6	1089.0
12.5°	1105.1	1103.2	1101.2	1099.2	1097.2	1093.4	1087.5	1081.7	1075.7	1069.9	1068.6
15°	1083.5	1081.0	1078.4	1075.9	1073.4	1068.2	1060.5	1052.7	1044.9	1037.1	1032.8
17.5°	1056.9	1053.1	1049.2	1045.3	1041.5	1034.6	1024.6	1014.6	1004.6	994.6	989.5
20°	1037.1	1032.5	1027.9	1023.4	1018.8	1010.8	999.3	987.8	976.4	964.9	959.2
22.5°	1015.6	1010.6	1005.4	1000.3	995.1	986.1	973.2	960.3	947.4	934.4	927.1
25°	983.5	976.1	968.9	961.5	954.2	942.9	927.9	912.7	897.6	882.4	873.0
27.5°	944.7	936.8	928.8	920.8	912.8	900.3	883.3	866.3	849.2	832.1	821.2
30°	917.6	908.8	900.1	891.4	882.7	869.2	850.8	832.5	814.2	795.9	784.2
32.5°	891.1	880.9	870.8	860.6	850.4	836.0	817.3	798.6	779.9	761.2	747.9
35°	847.4	835.8	824.0	812.3	800.7	784.8	764.6	744.5	724.3	704.1	689.6
37.5°	803.8	790.8	778.0	765.2	752.3	735.2	713.8	692.3	670.8	649.2	633.4
40°	773.2	759.4	745.7	732.0	718.2	700.2	678.0	655.8	633.6	611.4	595.1
42.5°	741.8	727.4	712.9	698.4	684.0	665.2	642.3	619.4	596.3	573.4	556.5
45°	692.8	677.4	662.1	646.7	631.4	611.7	587.6	563.6	539.5	515.4	499.2
47.5°	644.9	628.6	612.4	596.1	579.9	559.4	534.5	509.7	484.8	460.0	443.8
50°	610.3	594.0	577.7	561.5	545.2	524.5	499.3	474.1	448.9	423.7	407.9
52.5°	576.5	559.5	542.5	525.5	508.5	487.7	463.0	438.4	413.7	389.1	373.9
55°	526.8	509.0	491.1	473.2	455.3	434.0	409.3	384.6	359.8	335.1	321.3
57.5°	475.8	457.6	439.2	420.9	402.5	381.5	357.7	334.0	310.1	286.4	273.8
60°	441.2	422.9	404.6	386.3	367.9	347.0	323.4	299.7	276.2	252.6	240.9
62.5°	407.4	389.1	370.7	352.4	334.1	313.7	291.2	268.7	246.2	223.7	212.6
65°	355.7	337.1	318.5	300.0	281.4	261.9	241.3	220.7	200.0	179.4	171.6
67.5°	305.8	287.3	268.9	250.5	232.1	213.6	195.0	176.5	157.9	139.4	135.8
70°	271.1	253.3	235.4	217.5	199.7	182.8	167.0	151.2	135.4	119.6	117.2
72.5°	238.1	221.0	203.9	186.7	169.6	154.7	142.0	129.3	116.6	103.9	102.0
75°	189.7	173.7	157.6	141.6	125.5	113.6	105.8	98.1	90.3	82.5	80.9
77.5°	142.1	127.9	113.9	99.9	85.8	76.9	73.1	69.4	65.6	61.9	60.9
80°	112.4	100.7	89.0	77.4	65.6	58.7	56.4	54.0	51.8	49.5	48.6
82.5°	85.1	76.0	67.0	57.8	48.7	43.3	41.8	40.2	38.7	37.2	36.6
85°	44.3	39.5	34.7	29.9	25.0	22.3	21.6	21.0	20.3	19.6	19.6
87.5°	13.3	12.3	11.2	10.1	9.1	8.9	9.7	10.4	11.1	11.8	11.6
90°	0.7	2.7	4.7	6.8	8.8	11.6	15.2	18.9	22.5	26.3	25.9
92.5°	13.3	14.8	16.3	17.8	19.2	20.4	21.2	22.1	22.9	23.8	23.9
95°	39.0	40.6	42.3	43.9	45.6	46.7	47.0	47.3	47.7	48.0	48.0
97.5°	71.2	72.6	74.1	75.5	77.1	78.1	78.8	79.4	80.0	80.6	80.6
100°	95.1	96.5	97.9	99.2	100.5	101.4	101.9	102.4	102.9	103.4	103.4
102.5°	120.4	121.4	122.5	123.5	124.6	125.4	126.1	126.7	127.3	127.9	128.2
105°	161.1	161.6	162.1	162.6	163.1	163.5	163.9	164.2	164.5	164.9	165.2
107.5°	202.2	202.9	203.7	204.4	205.1	205.5	205.5	205.5	205.5	205.5	205.6
110°	228.5	229.5	230.6	231.6	232.6	233.1	233.1	233.1	233.1	233.1	233.1



TEST NUMBER: P331812-840

CATALOG NUMBER: S122RDIW-S675D710U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	257.3	258.3	259.3	260.3	261.4	261.8	261.7	261.5	261.4	261.3	260.8
115°	299.7	300.7	301.7	302.8	303.8	304.1	303.8	303.4	303.1	302.8	302.6
117.5°	342.0	343.4	344.7	346.0	347.3	347.5	346.6	345.7	344.8	343.9	343.5
120°	370.2	371.5	372.8	374.2	375.5	375.5	374.2	372.8	371.5	370.2	370.2
122.5°	396.0	397.6	399.2	400.7	402.3	402.7	401.7	400.8	399.9	399.0	398.6
125°	436.2	437.7	439.1	440.6	442.1	442.6	442.1	441.6	441.1	440.6	440.1
127.5°	475.2	477.2	479.1	480.9	482.8	483.5	482.9	482.3	481.7	481.1	480.5
130°	499.8	502.0	504.1	506.3	508.5	509.4	509.1	508.8	508.4	508.1	507.8
132.5°	527.5	529.2	531.0	532.7	534.4	535.4	535.4	535.5	535.6	535.6	534.9
135°	564.3	566.1	567.9	569.8	571.6	572.7	573.0	573.4	573.7	574.0	573.8
137.5°	603.1	604.6	606.1	607.6	609.0	610.1	610.5	611.0	611.4	611.8	611.7
140°	626.5	627.9	629.4	631.0	632.5	633.6	634.5	635.3	636.1	636.9	636.9
142.5°	650.5	652.0	653.5	655.0	656.4	657.5	658.0	658.6	659.1	659.7	659.8
145°	684.9	686.1	687.2	688.4	689.6	690.6	691.7	692.7	693.7	694.7	694.8
147.5°	715.7	717.0	718.4	719.8	721.2	722.3	723.0	723.6	724.3	725.0	725.3
150°	736.6	737.6	738.6	739.6	740.6	741.4	742.1	742.8	743.5	744.2	744.7
152.5°	755.2	756.2	757.2	758.2	759.2	760.1	760.9	761.7	762.5	763.4	764.0
155°	783.0	783.6	784.1	784.6	785.1	785.6	786.1	786.6	787.1	787.6	788.4
157.5°	806.9	807.3	807.6	807.9	808.3	808.6	808.9	809.2	809.5	809.8	810.9
160°	821.3	821.6	821.9	822.3	822.6	822.9	823.0	823.2	823.3	823.5	824.6
162.5°	834.5	834.6	834.7	834.7	834.8	834.9	835.1	835.3	835.4	835.6	836.7
165°	852.0	851.8	851.7	851.5	851.4	851.3	851.3	851.3	851.3	851.3	852.4
167.5°	866.8	866.3	865.8	865.3	864.7	864.4	864.4	864.3	864.3	864.3	865.5
170°	874.5	874.0	873.5	873.0	872.5	872.2	872.0	871.8	871.7	871.5	872.7
172.5°	879.9	879.4	878.9	878.4	877.9	877.6	877.4	877.3	877.1	876.9	878.1
175°	886.5	886.1	885.6	885.0	884.5	884.1	883.7	883.4	883.1	882.7	883.9
177.5°	889.2	888.8	888.4	888.0	887.6	887.3	887.0	886.8	886.5	886.2	887.0
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331812-840

CATALOG NUMBER: S122RDIW-S675D710U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1
2.5°	1133.8	1135.6	1137.4	1138.1	1137.8	1137.4	1137.1	1136.7
5°	1124.7	1126.8	1128.8	1129.5	1128.8	1128.1	1127.5	1126.8
7.5°	1106.5	1107.1	1107.7	1107.4	1106.2	1105.1	1103.9	1102.7
10°	1088.3	1087.6	1086.9	1085.9	1084.5	1083.2	1081.8	1080.4
12.5°	1067.4	1066.2	1064.9	1063.2	1060.9	1058.6	1056.3	1054.0
15°	1028.4	1024.0	1019.7	1016.3	1014.1	1011.8	1009.5	1007.2
17.5°	984.3	979.1	973.9	969.4	965.4	961.5	957.6	953.6
20°	953.5	947.8	942.0	936.6	931.6	926.6	921.5	916.5
22.5°	919.7	912.3	904.9	899.4	895.5	891.8	888.1	884.3
25°	863.6	854.2	844.9	838.5	835.1	831.6	828.2	824.8
27.5°	810.2	799.3	788.4	780.1	774.7	769.2	763.8	758.3
30°	772.5	760.8	749.1	740.2	734.0	727.8	721.6	715.5
32.5°	734.6	721.2	707.9	698.3	692.5	686.7	680.9	675.1
35°	675.3	660.9	646.4	636.6	631.6	626.5	621.6	616.5
37.5°	617.4	601.6	585.7	574.8	569.1	563.3	557.5	551.8
40°	578.8	562.5	546.2	535.1	529.2	523.2	517.3	511.3
42.5°	539.8	522.9	506.1	494.8	489.1	483.3	477.6	471.7
45°	482.9	466.7	450.4	439.5	434.0	428.5	423.0	417.5
47.5°	427.7	411.5	395.3	384.8	379.7	374.8	369.7	364.8
50°	392.1	376.3	360.5	350.1	345.4	340.5	335.8	330.9
52.5°	358.6	343.3	328.0	318.2	313.8	309.3	304.9	300.4
55°	307.6	293.8	280.0	271.0	266.7	262.3	257.9	253.6
57.5°	261.2	248.6	236.0	227.8	224.2	220.6	216.8	213.2
60°	229.2	217.5	205.8	198.1	194.5	190.9	187.1	183.5
62.5°	201.5	190.3	179.2	172.5	170.3	168.1	165.9	163.7
65°	163.8	156.0	148.2	144.0	143.3	142.6	141.9	141.3
67.5°	132.2	128.7	125.1	122.9	122.2	121.5	120.8	120.0
70°	115.0	112.7	110.4	108.9	107.9	106.9	106.0	105.1
72.5°	100.1	98.2	96.2	95.0	94.4	93.9	93.3	92.8
75°	79.3	77.7	76.0	75.1	74.9	74.7	74.4	74.2
77.5°	60.0	59.1	58.2	57.6	57.2	56.9	56.5	56.0
80°	47.7	46.8	45.8	45.3	45.3	45.3	45.3	45.3
82.5°	36.1	35.4	34.9	34.6	34.6	34.6	34.6	34.6
85°	19.6	19.6	19.6	19.6	19.6	19.6	19.6	19.6
87.5°	11.3	11.1	10.8	10.7	10.8	10.8	10.8	10.9
90°	25.5	25.2	24.9	24.8	24.9	25.1	25.3	25.4
92.5°	23.9	24.0	24.1	24.1	24.1	24.2	24.2	24.2
95°	48.0	48.0	48.0	47.8	47.5	47.2	46.8	46.5
97.5°	80.6	80.6	80.6	80.6	80.6	80.6	80.5	80.5
100°	103.4	103.4	103.4	103.3	103.2	103.0	102.8	102.7
102.5°	128.3	128.4	128.6	128.6	128.4	128.2	128.1	127.8
105°	165.5	165.8	166.2	166.3	166.3	166.3	166.3	166.3
107.5°	205.7	205.9	206.0	205.7	204.9	204.2	203.4	202.7
110°	233.1	233.1	233.1	232.8	232.3	231.8	231.3	230.9



TEST NUMBER: P331812-840

CATALOG NUMBER: S122RDIW-S675D710U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	260.4	260.0	259.6	259.2	258.9	258.5	258.1	257.8
115°	302.5	302.3	302.1	301.7	301.2	300.7	300.2	299.7
117.5°	343.1	342.6	342.2	341.7	341.2	340.7	340.2	339.7
120°	370.2	370.2	370.2	369.9	369.4	368.9	368.4	367.9
122.5°	398.2	397.8	397.4	397.0	396.6	396.3	395.9	395.6
125°	439.6	439.1	438.6	438.3	438.2	438.0	437.8	437.7
127.5°	479.9	479.3	478.7	478.2	477.6	477.1	476.6	476.1
130°	507.5	507.1	506.8	506.2	505.5	504.9	504.2	503.6
132.5°	534.2	533.4	532.7	532.1	531.6	531.0	530.5	530.0
135°	573.7	573.5	573.4	573.0	572.5	572.0	571.5	571.0
137.5°	611.5	611.4	611.3	610.9	610.2	609.6	608.8	608.1
140°	636.9	636.9	636.9	636.6	636.0	635.3	634.6	634.0
142.5°	660.0	660.1	660.2	660.0	659.3	658.6	658.0	657.3
145°	695.0	695.2	695.3	695.1	694.4	693.8	693.1	692.5
147.5°	725.7	726.0	726.4	726.3	725.7	725.0	724.4	723.8
150°	745.1	745.6	746.1	746.1	745.6	745.1	744.7	744.2
152.5°	764.6	765.2	765.9	765.9	765.2	764.6	764.0	763.4
155°	789.2	790.1	790.9	791.1	790.6	790.1	789.6	789.1
157.5°	812.0	813.1	814.3	814.5	813.6	812.8	812.0	811.2
160°	825.6	826.6	827.6	827.7	827.1	826.4	825.8	825.1
162.5°	837.8	839.0	840.1	840.2	839.4	838.7	837.9	837.1
165°	853.6	854.7	856.0	856.2	855.3	854.4	853.6	852.8
167.5°	866.7	867.8	869.0	869.1	868.3	867.4	866.6	865.7
170°	873.8	875.0	876.2	876.3	875.3	874.2	873.2	872.2
172.5°	879.3	880.4	881.6	881.6	880.7	879.7	878.7	877.7
175°	885.0	886.3	887.5	887.5	886.5	885.6	884.5	883.5
177.5°	887.8	888.6	889.4	889.4	888.6	887.8	887.0	886.2
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0

(END OF REPORT)