

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331844-840

Luminaire Tested: **S122RDIW-S865D1440U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331844-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S865D1440U840-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8097.2 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331844-840

CATALOG NUMBER: S122RDIW-S865D1440U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331844-840

CATALOG NUMBER: S122RDIW-S865D1440U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	88	84	86	83	80	77	67	65	63	53	52	51	40	39	38	32
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33	28
3	80	71	64	58	72	64	58	54	53	48	45	42	39	37	32	30	28	24
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	18
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14	12
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23909	23909	23909
5°	24000	23608	23738
10°	23815	23222	23023
15°	23542	22534	21884
20°	23163	21551	20469
25°	22775	20436	19099
30°	22236	19287	17339
35°	21711	18039	15794
40°	21182	16750	14010
45°	20562	15299	12392
50°	19926	13835	10803
55°	19277	12262	9278
60°	18519	10601	7702
65°	17662	8909	7014
70°	16636	7336	6449
75°	15384	6687	6014
80°	13575	5979	5486
85°	10689	4705	4705



TEST NUMBER: P331844-840

CATALOG NUMBER: S122RDIW-S865D1440U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.6	1.7
10°-20°	380.6	4.7
20°-30°	534.4	6.6
30°-40°	582.7	7.2
40°-50°	535.8	6.6
50°-60°	420.8	5.2
60°-70°	274.4	3.4
70°-80°	141.5	1.7
80°-90°	43.9	0.5
90°-100°	114.3	1.4
100°-110°	355.0	4.4
110°-120°	606.9	7.5
120°-130°	798.1	9.9
130°-140°	895.8	11.1
140°-150°	878.3	10.8
150°-160°	736.7	9.1
160°-170°	488.6	6.0
170°-180°	170.8	2.1
0°-30°	1053.6	13.0
0°-40°	1636.3	20.2
0°-60°	2593.0	32.0
0°-90°	3052.7	37.7
90°-120°	1076.2	13.3
90°-150°	3648.4	45.1
90°-180°	5045.0	62.3
0°-180°	8097.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1481	1481	1481	1481	1481	
5°	1481	1473	1457	1468	1465	140
15°	1408	1392	1348	1323	1309	397
25°	1278	1233	1147	1094	1072	588
35°	1102	1030	915	834	801	689
45°	900	808	670	578	543	695
55°	685	578	436	358	330	612
65°	462	353	233	190	184	458
75°	247	155	107	98	96	261
85°	58	31	25	25	25	68
90°	2	21	53	50	52	7
95°	79	94	98	97	94	91
105°	327	332	335	338	338	346
115°	609	617	615	613	609	602
125°	886	899	895	891	889	791
135°	1146	1162	1166	1165	1160	885
145°	1392	1402	1411	1412	1407	869
155°	1591	1596	1600	1607	1603	732
165°	1731	1730	1730	1739	1732	488
175°	1801	1797	1793	1803	1795	171
180°	1804	1804	1804	1804	1804	



TEST NUMBER: P331844-840

CATALOG NUMBER: S122RDIW-S865D1440U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8
2.5°	1486.1	1484.9	1483.7	1482.5	1481.4	1479.5	1476.8	1474.2	1471.6	1468.9	1471.4
5°	1480.8	1479.3	1477.7	1476.2	1474.8	1472.1	1468.2	1464.4	1460.5	1456.6	1459.3
7.5°	1465.4	1463.6	1461.8	1460.0	1458.0	1454.9	1450.4	1445.8	1441.3	1436.7	1437.5
10°	1452.6	1450.5	1448.4	1446.3	1444.2	1440.3	1434.3	1428.4	1422.4	1416.4	1415.5
12.5°	1436.5	1433.9	1431.4	1428.9	1426.2	1421.2	1413.5	1405.9	1398.3	1390.7	1389.1
15°	1408.4	1405.1	1401.8	1398.6	1395.2	1388.6	1378.5	1368.4	1358.2	1348.1	1342.4
17.5°	1373.8	1368.8	1363.8	1358.8	1353.8	1344.8	1331.8	1318.8	1305.9	1292.8	1286.2
20°	1348.1	1342.1	1336.2	1330.2	1324.2	1313.8	1298.9	1284.0	1269.2	1254.3	1246.8
22.5°	1320.2	1313.5	1306.9	1300.2	1293.5	1281.8	1265.0	1248.2	1231.4	1214.6	1205.0
25°	1278.4	1268.9	1259.3	1249.8	1240.3	1225.7	1206.0	1186.4	1166.7	1147.1	1134.9
27.5°	1228.0	1217.6	1207.3	1196.9	1186.6	1170.3	1148.1	1126.0	1103.8	1081.7	1067.4
30°	1192.7	1181.3	1170.0	1158.7	1147.4	1129.8	1106.0	1082.2	1058.3	1034.5	1019.4
32.5°	1158.3	1145.1	1131.9	1118.6	1105.4	1086.7	1062.4	1038.0	1013.8	989.5	972.2
35°	1101.5	1086.3	1071.2	1055.9	1040.8	1020.1	993.8	967.7	941.5	915.2	896.5
37.5°	1044.7	1028.0	1011.4	994.6	978.0	955.6	927.8	899.8	871.9	843.9	823.2
40°	1005.0	987.1	969.3	951.4	933.5	910.2	881.3	852.4	823.5	794.7	773.5
42.5°	964.3	945.4	926.7	907.9	889.0	864.6	834.9	805.0	775.2	745.3	723.5
45°	900.5	880.5	860.6	840.6	820.7	795.1	763.9	732.6	701.3	670.0	648.8
47.5°	838.3	817.2	796.1	774.9	753.8	727.0	694.8	662.5	630.2	597.9	576.9
50°	793.3	772.1	751.0	729.8	708.7	681.8	649.0	616.2	583.5	550.8	530.2
52.5°	749.3	727.2	705.2	683.1	661.0	633.9	601.9	569.8	537.8	505.7	485.8
55°	684.8	661.6	638.3	615.1	591.9	564.1	532.0	499.8	467.7	435.6	417.7
57.5°	618.5	594.7	570.9	547.0	523.3	495.9	464.9	434.0	403.1	372.2	355.9
60°	573.5	549.7	525.9	502.1	478.3	451.0	420.3	389.6	359.0	328.3	313.2
62.5°	529.6	505.7	481.9	458.1	434.2	407.8	378.5	349.3	320.0	290.7	276.3
65°	462.3	438.2	414.0	389.9	365.9	340.3	313.6	286.8	259.9	233.2	223.1
67.5°	397.5	373.5	349.6	325.6	301.6	277.6	253.6	229.4	205.3	181.2	176.5
70°	352.4	329.2	306.0	282.8	259.5	237.6	217.1	196.5	176.0	155.4	152.5
72.5°	309.5	287.3	265.0	242.8	220.5	201.1	184.6	168.0	151.6	135.1	132.6
75°	246.6	225.7	204.9	184.0	163.2	147.7	137.5	127.4	117.3	107.2	105.1
77.5°	184.7	166.3	148.0	129.8	111.5	100.0	95.0	90.2	85.3	80.4	79.2
80°	146.0	130.9	115.7	100.5	85.3	76.2	73.2	70.3	67.3	64.3	63.1
82.5°	110.7	98.9	86.9	75.1	63.3	56.4	54.3	52.3	50.3	48.3	47.6
85°	57.7	51.4	45.1	38.9	32.6	29.1	28.2	27.3	26.4	25.4	25.4
87.5°	17.5	16.4	15.2	14.1	13.1	13.2	14.7	16.3	17.8	19.2	18.9
90°	1.5	5.6	9.6	13.7	17.8	23.5	31.0	38.4	45.8	53.3	52.6
92.5°	27.1	30.1	33.0	36.1	39.0	41.4	43.1	44.9	46.7	48.4	48.6
95°	79.2	82.5	85.9	89.3	92.7	94.7	95.4	96.0	96.7	97.5	97.5
97.5°	144.6	147.6	150.6	153.6	156.5	158.6	160.0	161.3	162.5	163.8	163.8
100°	193.4	196.0	198.7	201.5	204.2	206.0	207.0	208.0	209.0	210.1	210.1
102.5°	244.5	246.7	248.8	251.0	253.2	254.9	256.2	257.4	258.7	260.0	260.3
105°	327.3	328.3	329.3	330.3	331.3	332.2	333.0	333.6	334.3	335.0	335.6
107.5°	410.7	412.2	413.7	415.3	416.7	417.5	417.5	417.5	417.5	417.5	417.7
110°	464.3	466.4	468.4	470.4	472.4	473.5	473.5	473.5	473.5	473.5	473.5



TEST NUMBER: P331844-840

CATALOG NUMBER: S122RDIW-S865D1440U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	522.8	524.8	526.8	528.9	530.9	531.8	531.5	531.3	531.0	530.7	529.9
115°	608.9	611.0	613.0	615.1	617.1	617.7	617.1	616.4	615.7	615.1	614.7
117.5°	694.9	697.5	700.2	703.0	705.7	706.1	704.2	702.3	700.3	698.5	697.7
120°	752.0	754.8	757.5	760.2	763.0	763.0	760.2	757.5	754.8	752.0	752.0
122.5°	804.5	807.7	810.9	814.2	817.5	818.1	816.3	814.4	812.4	810.5	809.7
125°	886.1	889.1	892.1	895.1	898.3	899.3	898.3	897.3	896.3	895.1	894.1
127.5°	965.5	969.4	973.2	977.1	981.0	982.3	981.1	979.9	978.7	977.4	976.1
130°	1015.4	1019.9	1024.3	1028.6	1033.1	1034.9	1034.2	1033.6	1032.9	1032.2	1031.6
132.5°	1071.5	1075.1	1078.6	1082.3	1085.8	1087.7	1087.8	1087.9	1088.1	1088.2	1086.7
135°	1146.4	1150.1	1153.9	1157.5	1161.2	1163.5	1164.2	1164.9	1165.5	1166.2	1165.9
137.5°	1225.3	1228.3	1231.3	1234.4	1237.4	1239.4	1240.3	1241.1	1242.0	1242.9	1242.6
140°	1272.7	1275.8	1278.9	1281.9	1285.0	1287.3	1289.0	1290.7	1292.4	1294.0	1294.0
142.5°	1321.5	1324.5	1327.6	1330.6	1333.6	1335.7	1336.9	1338.1	1339.2	1340.4	1340.6
145°	1391.5	1393.9	1396.2	1398.6	1401.0	1403.2	1405.2	1407.2	1409.3	1411.3	1411.6
147.5°	1453.9	1456.7	1459.6	1462.5	1465.3	1467.4	1468.7	1470.1	1471.5	1472.8	1473.6
150°	1496.5	1498.5	1500.7	1502.7	1504.7	1506.3	1507.7	1509.0	1510.5	1511.8	1512.8
152.5°	1534.3	1536.3	1538.3	1540.3	1542.5	1544.3	1545.9	1547.5	1549.1	1550.7	1552.1
155°	1590.9	1592.0	1593.0	1594.0	1595.0	1596.0	1597.0	1598.0	1599.0	1600.0	1601.7
157.5°	1639.3	1640.0	1640.7	1641.4	1642.0	1642.7	1643.4	1644.0	1644.6	1645.2	1647.4
160°	1668.6	1669.3	1669.9	1670.6	1671.3	1671.8	1672.1	1672.4	1672.8	1673.1	1675.2
162.5°	1695.4	1695.6	1695.7	1695.8	1696.0	1696.2	1696.5	1696.9	1697.2	1697.5	1699.8
165°	1731.0	1730.7	1730.3	1730.0	1729.7	1729.5	1729.5	1729.5	1729.5	1729.5	1731.8
167.5°	1760.8	1759.8	1758.8	1757.8	1756.8	1756.3	1756.2	1756.2	1756.1	1756.0	1758.4
170°	1776.7	1775.6	1774.6	1773.6	1772.6	1771.9	1771.6	1771.3	1770.9	1770.6	1772.9
172.5°	1787.7	1786.7	1785.6	1784.6	1783.6	1782.9	1782.6	1782.2	1781.9	1781.5	1783.9
175°	1801.0	1800.0	1799.0	1798.0	1797.0	1796.1	1795.4	1794.7	1794.1	1793.4	1795.8
177.5°	1806.5	1805.7	1804.9	1804.1	1803.3	1802.6	1802.0	1801.5	1801.0	1800.4	1802.0
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331844-840

CATALOG NUMBER: S122RDIW-S865D1440U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8
2.5°	1473.7	1476.1	1478.4	1479.5	1478.9	1478.4	1478.0	1477.5
5°	1462.0	1464.6	1467.3	1468.2	1467.3	1466.4	1465.5	1464.6
7.5°	1438.4	1439.1	1439.9	1439.5	1437.9	1436.4	1434.8	1433.3
10°	1414.6	1413.7	1412.8	1411.5	1409.7	1408.0	1406.1	1404.3
12.5°	1387.5	1385.8	1384.2	1382.0	1379.0	1376.0	1373.0	1370.1
15°	1336.8	1331.1	1325.4	1321.1	1318.2	1315.1	1312.2	1309.2
17.5°	1279.4	1272.6	1266.0	1260.0	1254.9	1249.8	1244.7	1239.5
20°	1239.4	1231.9	1224.5	1217.5	1210.9	1204.4	1197.8	1191.3
22.5°	1195.5	1185.9	1176.3	1169.0	1164.2	1159.2	1154.4	1149.5
25°	1122.7	1110.4	1098.2	1089.8	1085.4	1081.0	1076.5	1072.1
27.5°	1053.2	1038.9	1024.7	1014.1	1007.0	999.9	992.8	985.7
30°	1004.1	989.0	973.7	962.1	954.1	946.0	938.1	930.0
32.5°	954.8	937.5	920.2	907.7	900.2	892.6	885.0	877.5
35°	877.7	859.0	840.2	827.6	821.0	814.5	807.9	801.3
37.5°	802.6	781.9	761.3	747.2	739.7	732.2	724.7	717.2
40°	752.3	731.2	710.0	695.6	687.9	680.1	672.4	664.7
42.5°	701.7	679.7	657.9	643.2	635.7	628.2	620.7	613.2
45°	627.7	606.6	585.4	571.3	564.1	557.0	549.9	542.7
47.5°	555.8	534.8	513.8	500.1	493.6	487.1	480.6	474.1
50°	509.7	489.1	468.6	455.1	448.9	442.6	436.4	430.1
52.5°	466.1	446.3	426.4	413.6	407.8	402.0	396.3	390.5
55°	399.8	381.9	364.1	352.2	346.6	340.9	335.3	329.6
57.5°	339.5	323.2	306.8	296.2	291.4	286.6	281.9	277.1
60°	297.9	282.8	267.5	257.6	252.8	248.0	243.3	238.5
62.5°	261.9	247.4	232.9	224.2	221.4	218.5	215.6	212.8
65°	212.9	202.8	192.7	187.1	186.2	185.4	184.5	183.6
67.5°	171.9	167.2	162.6	159.8	158.9	157.8	156.9	156.0
70°	149.5	146.5	143.5	141.5	140.3	139.1	137.8	136.6
72.5°	130.1	127.5	125.0	123.5	122.7	122.0	121.3	120.6
75°	103.0	101.0	98.9	97.7	97.4	97.0	96.7	96.4
77.5°	78.1	76.9	75.6	74.8	74.3	73.8	73.4	72.9
80°	61.9	60.8	59.6	59.0	59.0	59.0	59.0	59.0
82.5°	46.9	46.0	45.3	45.0	45.0	45.0	45.0	45.0
85°	25.4	25.4	25.4	25.4	25.4	25.4	25.4	25.4
87.5°	18.5	18.1	17.8	17.6	17.7	17.7	17.8	17.9
90°	51.9	51.3	50.6	50.4	50.8	51.1	51.4	51.8
92.5°	48.7	48.8	49.0	49.1	49.1	49.2	49.3	49.3
95°	97.5	97.5	97.5	97.0	96.4	95.7	95.0	94.4
97.5°	163.8	163.8	163.8	163.8	163.7	163.6	163.6	163.5
100°	210.1	210.1	210.1	210.0	209.5	209.2	208.9	208.5
102.5°	260.5	260.8	261.2	261.1	260.7	260.4	260.0	259.7
105°	336.3	337.0	337.6	338.0	338.0	338.0	338.0	338.0
107.5°	418.0	418.3	418.5	417.9	416.4	414.8	413.2	411.6
110°	473.5	473.5	473.5	472.9	471.9	470.9	469.9	468.9



TEST NUMBER: P331844-840

CATALOG NUMBER: S122RDIW-S865D1440U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	529.1	528.3	527.5	526.6	525.9	525.2	524.4	523.7
115°	614.4	614.0	613.7	613.0	612.0	611.0	610.0	608.9
117.5°	696.9	696.1	695.3	694.3	693.3	692.3	691.3	690.2
120°	752.0	752.0	752.0	751.5	750.5	749.5	748.5	747.5
122.5°	808.9	808.1	807.3	806.5	805.8	805.1	804.3	803.5
125°	893.1	892.1	891.1	890.5	890.1	889.8	889.5	889.1
127.5°	974.9	973.7	972.5	971.4	970.3	969.2	968.2	967.0
130°	1030.9	1030.2	1029.5	1028.4	1027.1	1025.8	1024.4	1023.1
132.5°	1085.3	1083.8	1082.3	1081.0	1079.9	1078.8	1077.7	1076.6
135°	1165.5	1165.2	1164.9	1164.2	1163.2	1162.2	1161.1	1160.1
137.5°	1242.3	1242.1	1241.8	1241.0	1239.7	1238.3	1237.0	1235.6
140°	1294.0	1294.0	1294.0	1293.4	1292.0	1290.7	1289.3	1288.0
142.5°	1340.9	1341.2	1341.4	1340.9	1339.6	1338.2	1336.9	1335.4
145°	1412.0	1412.3	1412.6	1412.1	1410.8	1409.5	1408.1	1406.7
147.5°	1474.3	1475.0	1475.8	1475.5	1474.2	1472.9	1471.7	1470.4
150°	1513.8	1514.8	1515.8	1515.8	1514.8	1513.8	1512.8	1511.8
152.5°	1553.3	1554.6	1555.9	1555.9	1554.6	1553.3	1552.1	1550.7
155°	1603.5	1605.2	1606.8	1607.2	1606.2	1605.2	1604.2	1603.2
157.5°	1649.7	1652.0	1654.4	1654.7	1653.0	1651.4	1649.8	1648.2
160°	1677.2	1679.2	1681.2	1681.6	1680.2	1678.9	1677.6	1676.2
162.5°	1702.1	1704.5	1706.7	1707.1	1705.5	1703.8	1702.2	1700.5
165°	1734.2	1736.6	1739.0	1739.3	1737.6	1736.0	1734.2	1732.5
167.5°	1760.7	1763.1	1765.4	1765.7	1764.0	1762.2	1760.5	1758.7
170°	1775.3	1777.7	1780.1	1780.2	1778.2	1776.2	1774.1	1772.1
172.5°	1786.2	1788.7	1791.0	1791.2	1789.2	1787.2	1785.1	1783.1
175°	1798.2	1800.5	1802.9	1803.1	1801.0	1799.0	1797.0	1794.9
177.5°	1803.7	1805.3	1807.0	1807.0	1805.3	1803.7	1802.0	1800.4
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1

(END OF REPORT)