

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331822

Luminaire Tested: **S122RDIW-S675D1440U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331822  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S675D1440U835-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7541.3 lumens  
Efficiency: N/A  
Efficacy: 110.7 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331822

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331822

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34								
1	95	91	87	84	85	82	79	76	66	64	62	51	50	48	37	36	36	29								
2	87	80	74	69	78	72	67	63	58	55	52	45	43	41	33	32	31	26								
3	79	71	64	58	71	64	58	54	52	48	44	41	38	36	30	28	27	22								
4	73	63	55	50	66	57	51	46	46	42	38	36	33	31	27	25	24	20								
5	67	56	49	43	60	51	45	40	42	37	33	33	30	27	25	23	21	18								
6	62	51	43	37	56	46	40	35	38	33	29	30	27	24	23	21	19	16								
7	57	46	38	33	52	42	35	31	34	30	26	27	24	21	21	19	17	14								
8	53	42	34	29	48	38	32	27	31	27	23	25	22	19	19	17	15	13								
9	50	38	31	26	45	35	29	24	29	24	21	23	20	17	18	16	14	12								
10	46	35	28	24	42	32	26	22	27	22	19	22	18	16	17	15	13	11								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	23720	23720	23720	23720
5°	26491	23869	21162	23869
10°	29391	23700	18344	23700
15°	30837	23353	14454	23353
20°	26734	22838	12507	22838
25°	17533	22133	11166	22133
30°	11801	21280	10107	21280
35°	9558	20203	9116	20203
40°	8500	19032	8435	19032
45°	7693	17657	7531	17657
50°	7001	16297	6975	16297
55°	6581	14787	6494	14787
60°	5506	13401	5438	13401
65°	4642	12168	5265	12168
70°	4291	10867	4966	10867
75°	4011	9457	4585	9457
80°	3701	7782	4082	7782
85°	3409	6150	3594	6150



TEST NUMBER: P331822

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.3	1.8
10°-20°	388.0	5.1
20°-30°	500.0	6.6
30°-40°	475.2	6.3
40°-50°	407.1	5.4
50°-60°	310.0	4.1
60°-70°	196.0	2.6
70°-80°	97.9	1.3
80°-90°	32.6	0.4
90°-100°	113.2	1.5
100°-110°	351.6	4.7
110°-120°	601.0	8.0
120°-130°	790.3	10.5
130°-140°	887.0	11.8
140°-150°	869.7	11.5
150°-160°	729.5	9.7
160°-170°	483.8	6.4
170°-180°	169.1	2.2
0°-30°	1027.3	13.6
0°-40°	1502.5	19.9
0°-60°	2219.6	29.4
0°-90°	2546.0	33.8
90°-120°	1065.7	14.1
90°-150°	3612.8	47.9
90°-180°	4995.0	66.2
0°-180°	7541.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1469	1469	1469	1469	1469	
5°	1634	1473	1306	1473	1634	161
15°	1845	1397	865	1397	1845	498
25°	984	1242	627	1242	984	467
35°	485	1025	462	1025	485	310
45°	337	773	330	773	337	261
55°	234	525	231	525	234	205
65°	122	318	138	318	122	124
75°	64	152	74	152	64	68
85°	18	33	19	33	18	21
90°	51	2	51	2	51	23
95°	94	78	94	78	94	104
105°	335	324	335	324	335	352
115°	603	603	603	603	603	596
125°	880	877	880	877	880	785
135°	1149	1135	1149	1135	1149	884
145°	1393	1378	1393	1378	1393	870
155°	1588	1575	1588	1575	1588	731
165°	1716	1714	1716	1714	1716	484
175°	1777	1783	1777	1783	1777	169
180°	1786	1786	1786	1786	1786	



TEST NUMBER: P331822

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1528.7	1529.9	1531.2	1528.3	1528.3	1525.8	1520.5	1516.5	1505.0	1503.4	1503.4
5°	1634.5	1633.4	1635.5	1628.9	1619.7	1617.6	1607.9	1595.2	1581.9	1567.1	1564.0
7.5°	1739.6	1738.1	1734.0	1732.9	1725.8	1710.4	1694.8	1678.2	1656.1	1634.6	1623.8
10°	1792.7	1809.6	1799.3	1781.5	1785.1	1761.1	1748.3	1726.4	1708.0	1675.8	1668.7
12.5°	1845.0	1851.6	1848.4	1838.2	1833.6	1817.0	1799.8	1780.7	1746.8	1717.9	1692.8
15°	1844.8	1854.5	1857.0	1854.0	1856.5	1855.5	1846.3	1830.5	1800.9	1769.2	1741.7
17.5°	1708.6	1715.3	1732.1	1743.4	1757.7	1787.9	1802.8	1808.6	1804.2	1786.2	1766.8
20°	1555.9	1544.6	1591.6	1615.6	1636.0	1687.0	1730.9	1747.8	1774.8	1774.3	1769.2
22.5°	1339.4	1342.1	1386.6	1415.1	1474.7	1525.7	1575.8	1639.2	1691.5	1726.1	1746.4
25°	984.2	1003.6	1048.0	1086.8	1153.1	1248.1	1334.3	1434.4	1528.8	1603.3	1674.3
27.5°	739.1	740.6	775.8	811.6	851.0	928.8	1037.4	1156.9	1291.5	1402.6	1530.4
30°	633.0	629.9	644.7	666.7	700.3	760.6	842.2	959.7	1093.9	1261.3	1410.4
32.5°	557.8	558.0	569.2	585.4	613.4	654.0	709.9	805.3	932.2	1096.8	1271.5
35°	484.9	484.4	492.6	504.3	516.1	542.1	580.4	630.4	717.7	871.3	1050.0
37.5°	432.7	434.9	438.9	446.2	459.2	473.7	496.7	530.3	592.4	683.3	833.5
40°	403.3	404.3	409.9	416.0	423.7	434.9	453.8	480.8	526.3	598.8	708.5
42.5°	376.3	377.3	381.3	387.0	393.0	404.3	419.9	443.3	480.1	536.7	627.2
45°	336.9	336.9	340.5	343.0	349.7	359.9	372.6	392.0	417.6	459.4	519.6
47.5°	299.9	300.0	302.4	306.8	311.0	318.9	331.5	347.3	365.9	398.3	449.7
50°	278.7	279.2	280.7	284.3	286.9	294.0	303.7	317.5	336.9	361.9	404.8
52.5°	261.6	261.2	263.2	264.7	266.5	271.6	278.8	291.0	308.3	330.1	365.6
55°	233.8	231.7	234.8	237.4	238.9	240.9	245.0	252.7	267.5	285.9	312.4
57.5°	199.1	198.3	200.4	202.8	207.6	213.1	216.5	221.4	229.1	242.3	268.6
60°	170.5	170.5	175.1	176.6	182.2	189.4	196.5	200.6	208.3	216.9	236.3
62.5°	145.2	145.6	147.7	149.3	152.4	161.2	171.2	180.2	187.4	195.7	208.6
65°	121.5	122.5	122.5	123.5	125.6	127.6	131.7	138.8	151.6	163.3	173.0
67.5°	103.1	103.4	103.7	104.7	105.3	107.5	109.1	112.3	115.3	126.4	138.4
70°	90.9	92.4	91.9	92.9	93.4	94.4	96.5	98.0	102.6	105.2	112.3
72.5°	79.4	80.5	80.4	81.1	82.4	82.6	84.2	85.8	88.7	90.9	94.7
75°	64.3	63.8	64.3	65.3	65.8	66.4	66.4	68.4	69.9	72.0	74.5
77.5°	49.6	50.1	50.0	50.1	50.2	51.1	51.0	52.0	53.5	54.5	55.7
80°	39.8	40.3	39.8	40.3	40.8	41.3	40.8	41.3	42.9	43.9	43.9
82.5°	30.8	30.9	31.2	31.3	31.4	31.5	32.3	32.4	33.5	33.3	33.7
85°	18.4	17.9	17.9	17.9	18.4	18.9	18.4	18.4	18.9	18.9	18.9
87.5°	16.8	17.1	17.1	17.0	16.9	17.0	17.1	17.6	17.4	17.9	16.0
90°	51.3	50.9	50.6	50.3	49.9	50.1	50.8	51.4	52.1	52.8	45.4
92.5°	48.8	48.8	48.7	48.6	48.6	48.5	48.3	48.2	48.1	47.9	46.2
95°	93.5	94.1	94.8	95.5	96.1	96.5	96.5	96.5	96.5	96.5	95.8
97.5°	161.9	162.0	162.0	162.1	162.2	162.2	162.2	162.2	162.2	162.2	160.9
100°	206.5	206.9	207.2	207.5	207.9	208.0	208.0	208.0	208.0	208.0	207.0
102.5°	257.2	257.5	257.9	258.2	258.5	258.6	258.3	258.0	257.8	257.5	256.2
105°	334.7	334.7	334.7	334.7	334.7	334.3	333.7	333.0	332.3	331.7	331.0
107.5°	407.6	409.2	410.7	412.3	413.8	414.4	414.2	413.9	413.6	413.4	413.4
110°	464.3	465.3	466.3	467.3	468.3	468.9	468.9	468.9	468.9	468.9	468.9



TEST NUMBER: P331822

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	518.6	519.3	520.1	520.8	521.5	522.3	523.1	523.9	524.7	525.5	525.8
115°	603.0	604.0	605.0	606.0	607.0	607.7	608.0	608.4	608.7	609.1	609.7
117.5°	683.5	684.5	685.5	686.5	687.5	688.5	689.3	690.1	690.9	691.7	693.5
120°	740.2	741.2	742.2	743.2	744.2	744.7	744.7	744.7	744.7	744.7	747.4
122.5°	795.7	796.4	797.2	797.9	798.6	799.4	800.2	801.0	801.8	802.6	804.5
125°	880.4	880.8	881.1	881.4	881.8	882.4	883.4	884.4	885.4	886.4	887.5
127.5°	957.6	958.7	959.7	960.8	961.9	963.0	964.2	965.4	966.6	967.9	969.1
130°	1013.1	1014.4	1015.8	1017.1	1018.4	1019.4	1020.1	1020.8	1021.5	1022.1	1022.8
132.5°	1066.1	1067.2	1068.3	1069.4	1070.4	1071.7	1073.2	1074.7	1076.1	1077.6	1077.5
135°	1148.8	1149.8	1150.8	1151.8	1152.8	1153.5	1153.8	1154.1	1154.5	1154.8	1154.1
137.5°	1223.5	1224.9	1226.2	1227.6	1228.9	1229.7	1230.0	1230.2	1230.5	1230.8	1229.9
140°	1275.4	1276.7	1278.1	1279.4	1280.8	1281.4	1281.4	1281.4	1281.4	1281.4	1279.8
142.5°	1322.4	1323.8	1325.1	1326.5	1327.8	1328.3	1328.1	1327.8	1327.5	1327.3	1326.1
145°	1393.0	1394.3	1395.7	1397.0	1398.3	1398.8	1398.5	1398.2	1397.8	1397.5	1395.5
147.5°	1456.0	1457.3	1458.5	1459.8	1461.1	1461.4	1460.6	1459.9	1459.2	1458.4	1457.1
150°	1497.0	1498.0	1499.0	1500.0	1501.0	1501.0	1500.0	1499.0	1498.0	1497.0	1495.7
152.5°	1535.6	1536.9	1538.1	1539.4	1540.7	1540.7	1539.4	1538.1	1536.9	1535.6	1534.0
155°	1587.5	1588.5	1589.5	1590.5	1591.5	1591.1	1589.5	1587.8	1586.1	1584.4	1583.4
157.5°	1632.1	1633.7	1635.3	1636.9	1638.5	1638.2	1635.9	1633.6	1631.3	1629.1	1628.5
160°	1659.8	1661.2	1662.5	1663.8	1665.2	1664.8	1662.8	1660.8	1658.8	1656.8	1656.5
162.5°	1683.9	1685.6	1687.2	1688.8	1690.4	1690.0	1687.8	1685.5	1683.2	1680.9	1680.6
165°	1715.6	1717.3	1719.0	1720.6	1722.3	1722.0	1719.6	1717.3	1714.9	1712.6	1712.6
167.5°	1741.5	1743.3	1745.0	1746.8	1748.5	1748.2	1745.9	1743.5	1741.2	1738.8	1738.9
170°	1754.8	1756.8	1758.8	1760.8	1762.8	1762.7	1760.3	1758.0	1755.6	1753.3	1753.6
172.5°	1765.7	1767.7	1769.7	1771.7	1773.7	1773.5	1771.2	1768.8	1766.5	1764.1	1764.5
175°	1777.4	1779.4	1781.4	1783.4	1785.5	1785.3	1782.9	1780.6	1778.3	1775.9	1776.6
177.5°	1782.8	1784.4	1786.1	1787.7	1789.3	1789.3	1787.7	1786.1	1784.4	1782.8	1783.4
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331822

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1504.2	1500.9	1498.1	1490.7	1487.1	1478.9	1477.7	1477.3	1466.6	1456.4	1453.6
5°	1555.9	1547.7	1535.4	1521.1	1506.3	1491.0	1480.8	1472.7	1452.2	1432.8	1421.6
7.5°	1607.9	1590.4	1569.2	1542.2	1519.6	1494.3	1475.5	1458.7	1429.7	1401.9	1383.2
10°	1646.7	1618.1	1590.1	1552.8	1523.7	1495.1	1468.6	1445.6	1412.9	1376.2	1350.1
12.5°	1670.8	1639.4	1600.7	1564.2	1526.6	1490.2	1454.7	1425.2	1386.8	1348.8	1317.9
15°	1703.4	1669.7	1622.7	1570.7	1522.2	1474.7	1433.9	1397.1	1347.1	1301.7	1263.9
17.5°	1730.0	1683.7	1633.2	1573.0	1516.9	1456.5	1403.9	1357.0	1301.3	1246.5	1202.0
20°	1738.6	1692.7	1634.5	1574.2	1507.9	1436.9	1380.3	1329.2	1269.5	1209.8	1158.7
22.5°	1733.3	1697.6	1632.8	1560.8	1492.8	1418.5	1354.5	1295.3	1229.1	1168.1	1108.9
25°	1697.3	1685.0	1623.8	1545.1	1467.6	1381.3	1307.3	1242.4	1166.9	1101.6	1037.2
27.5°	1613.2	1639.7	1601.7	1518.0	1431.7	1339.2	1256.0	1182.2	1103.8	1030.3	966.2
30°	1532.4	1593.1	1576.8	1499.2	1402.7	1311.9	1218.5	1141.4	1057.7	982.1	918.8
32.5°	1421.7	1522.1	1538.0	1473.1	1373.3	1273.5	1175.6	1098.9	1011.5	931.9	870.2
35°	1245.5	1395.6	1464.5	1423.1	1323.1	1215.4	1114.3	1025.0	937.2	858.6	797.3
37.5°	1035.3	1239.7	1354.5	1357.5	1265.6	1153.6	1043.6	954.9	865.0	787.8	721.6
40°	898.9	1120.4	1270.0	1303.2	1225.6	1104.6	993.3	903.0	815.2	739.6	663.6
42.5°	776.4	997.1	1181.0	1238.7	1177.0	1056.8	945.2	850.7	765.4	693.9	616.2
45°	627.9	820.8	1023.5	1126.6	1092.4	981.1	863.2	773.3	693.2	631.4	556.9
47.5°	529.6	665.6	861.7	1001.2	1000.6	899.0	783.0	697.0	622.7	564.8	504.4
50°	473.7	592.1	758.0	916.3	929.5	844.3	734.0	648.8	579.4	518.6	470.1
52.5°	423.5	521.1	670.2	821.9	859.7	785.9	678.9	600.2	532.8	477.0	435.4
55°	357.8	433.4	546.7	688.6	745.8	693.7	598.8	525.3	470.6	423.7	387.9
57.5°	302.7	359.4	450.3	564.6	631.1	598.4	520.0	460.3	413.6	371.1	342.9
60°	268.0	314.4	391.5	487.0	560.5	537.5	470.6	415.0	375.2	338.4	311.9
62.5°	235.3	275.2	341.3	418.8	486.2	476.7	422.0	375.4	340.5	307.0	284.5
65°	189.4	218.5	270.0	330.8	384.9	389.5	350.2	318.5	287.4	260.8	240.9
67.5°	150.8	169.8	206.1	257.3	297.8	312.3	288.3	264.1	239.4	218.9	201.6
70°	127.1	142.4	169.0	210.3	247.6	262.9	249.1	230.2	208.8	191.9	177.1
72.5°	103.0	117.9	137.5	167.8	199.8	216.3	211.5	198.0	180.6	166.6	152.6
75°	77.6	82.2	95.5	115.9	140.9	155.2	158.8	151.6	137.8	127.1	118.9
77.5°	57.4	60.1	66.5	77.2	93.5	106.3	111.5	110.7	101.2	94.9	87.3
80°	45.9	47.5	50.5	55.1	67.4	80.1	83.7	83.7	77.1	74.5	66.9
82.5°	34.9	36.0	37.9	40.4	46.1	57.3	61.3	62.1	57.9	54.5	48.5
85°	19.9	19.4	20.4	21.9	23.0	26.0	32.2	33.2	32.2	28.1	26.5
87.5°	14.5	13.5	12.0	10.5	10.1	9.7	10.9	12.1	11.3	10.9	10.9
90°	38.0	30.7	23.3	17.6	13.6	9.5	5.5	1.5	5.5	9.5	13.6
92.5°	44.5	42.7	41.0	38.6	35.7	32.7	29.8	26.8	29.8	32.7	35.7
95°	95.1	94.5	93.8	91.8	88.4	85.1	81.7	78.4	81.7	85.1	88.4
97.5°	159.7	158.4	157.1	155.0	152.1	149.1	146.2	143.2	146.2	149.1	152.1
100°	206.0	205.0	204.0	202.2	199.5	196.8	194.1	191.5	194.1	196.8	199.5
102.5°	254.9	253.7	252.4	250.7	248.5	246.4	244.3	242.1	244.3	246.4	248.5
105°	330.3	329.7	329.0	328.1	327.1	326.1	325.1	324.1	325.1	326.1	327.1
107.5°	413.4	413.4	413.4	412.6	411.2	409.7	408.2	406.7	408.2	409.7	411.2
110°	468.9	468.9	468.9	467.8	465.8	463.8	461.8	459.8	461.8	463.8	465.8





TEST NUMBER: P331822

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	526.1	526.3	526.6	525.7	523.7	521.7	519.7	517.7	519.7	521.7	523.7
115°	610.4	611.1	611.7	611.1	609.1	607.0	605.0	603.0	605.0	607.0	609.1
117.5°	695.4	697.3	699.2	698.8	696.1	693.4	690.7	688.1	690.7	693.4	696.1
120°	750.1	752.8	755.5	755.5	752.8	750.1	747.4	744.7	747.4	750.1	752.8
122.5°	806.4	808.3	810.1	809.5	806.2	803.0	799.8	796.6	799.8	803.0	806.2
125°	888.5	889.5	890.5	889.5	886.4	883.4	880.4	877.4	880.4	883.4	886.4
127.5°	970.3	971.5	972.7	971.4	967.6	963.7	959.9	956.1	959.9	963.7	967.6
130°	1023.5	1024.1	1024.8	1023.0	1018.6	1014.3	1009.9	1005.5	1009.9	1014.3	1018.6
132.5°	1077.3	1077.2	1077.1	1075.2	1071.7	1068.1	1064.6	1061.0	1064.6	1068.1	1071.7
135°	1153.5	1152.8	1152.1	1149.9	1146.2	1142.6	1138.9	1135.2	1138.9	1142.6	1146.2
137.5°	1229.0	1228.2	1227.3	1225.3	1222.3	1219.3	1216.3	1213.3	1216.3	1219.3	1222.3
140°	1278.1	1276.4	1274.7	1272.4	1269.4	1266.4	1263.3	1260.3	1263.3	1266.4	1269.4
142.5°	1325.0	1323.8	1322.7	1320.6	1317.6	1314.6	1311.6	1308.6	1311.6	1314.6	1317.6
145°	1393.5	1391.5	1389.5	1387.3	1384.9	1382.6	1380.3	1377.9	1380.3	1382.6	1384.9
147.5°	1455.7	1454.4	1453.1	1451.0	1448.2	1445.3	1442.5	1439.7	1442.5	1445.3	1448.2
150°	1494.3	1493.0	1491.6	1490.0	1488.0	1486.0	1483.9	1481.9	1483.9	1486.0	1488.0
152.5°	1532.4	1530.8	1529.2	1527.4	1525.3	1523.3	1521.3	1519.3	1521.3	1523.3	1525.3
155°	1582.4	1581.4	1580.4	1579.4	1578.4	1577.4	1576.4	1575.4	1576.4	1577.4	1578.4
157.5°	1627.9	1627.3	1626.7	1626.0	1625.4	1624.7	1624.0	1623.3	1624.0	1624.7	1625.4
160°	1656.1	1655.8	1655.5	1655.0	1654.3	1653.6	1653.0	1652.3	1653.0	1653.6	1654.3
162.5°	1680.3	1679.9	1679.6	1679.4	1679.2	1679.1	1679.0	1678.8	1679.0	1679.1	1679.2
165°	1712.6	1712.6	1712.6	1712.8	1713.1	1713.4	1713.8	1714.1	1713.8	1713.4	1713.1
167.5°	1739.0	1739.0	1739.1	1739.6	1740.6	1741.6	1742.6	1743.6	1742.6	1741.6	1740.6
170°	1754.0	1754.3	1754.6	1755.3	1756.3	1757.3	1758.3	1759.3	1758.3	1757.3	1756.3
172.5°	1764.8	1765.2	1765.5	1766.2	1767.2	1768.2	1769.2	1770.2	1769.2	1768.2	1767.2
175°	1777.2	1777.9	1778.6	1779.4	1780.4	1781.4	1782.4	1783.4	1782.4	1781.4	1780.4
177.5°	1783.9	1784.4	1785.0	1785.7	1786.5	1787.3	1788.1	1788.9	1788.1	1787.3	1786.5
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331822

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1448.3	1445.4	1440.1	1431.9	1427.0	1418.4	1412.7	1416.0	1416.8	1416.0	1415.2
5°	1409.4	1398.6	1383.8	1369.5	1356.3	1342.0	1333.8	1330.2	1323.1	1319.0	1317.0
7.5°	1362.3	1343.8	1322.9	1298.0	1276.8	1254.7	1243.4	1237.7	1223.1	1215.2	1208.2
10°	1327.2	1298.1	1277.2	1244.5	1224.6	1195.5	1175.6	1176.1	1156.2	1144.9	1136.8
12.5°	1288.4	1256.4	1221.6	1192.2	1164.5	1141.2	1117.2	1107.5	1086.3	1075.5	1053.5
15°	1224.1	1186.8	1150.1	1110.2	1082.2	1045.9	1011.2	968.8	934.6	905.0	896.9
17.5°	1153.8	1107.7	1070.8	1024.1	976.0	915.0	874.8	850.2	829.6	814.0	802.3
20°	1105.6	1058.7	1019.4	948.9	884.1	842.8	813.2	794.3	772.8	756.0	746.8
22.5°	1055.0	1006.0	952.4	873.8	823.3	790.1	763.7	742.0	727.5	714.3	706.0
25°	983.1	929.5	841.2	787.1	746.3	711.6	693.2	679.9	664.6	646.7	638.6
27.5°	907.2	821.9	758.5	718.3	679.3	656.7	640.2	620.4	606.7	598.7	590.2
30°	850.4	765.2	715.7	671.8	644.2	619.2	599.8	588.6	575.3	561.5	555.9
32.5°	787.1	719.0	671.6	635.0	607.0	585.7	570.4	552.2	542.6	534.1	522.4
35°	708.5	657.0	613.6	584.0	557.4	540.1	522.2	511.5	494.1	487.0	482.4
37.5°	641.9	597.2	564.9	533.6	512.6	493.4	482.5	465.4	457.9	448.0	438.3
40°	604.4	560.5	529.3	503.8	480.3	466.0	452.3	438.5	427.2	422.7	410.9
42.5°	566.0	530.3	499.1	471.1	455.4	440.3	422.9	412.8	401.1	393.7	386.4
45°	513.0	481.4	454.8	431.8	414.5	398.7	387.4	370.6	364.0	349.1	343.0
47.5°	466.5	437.0	411.7	389.9	372.9	362.6	346.2	333.0	322.4	313.3	305.5
50°	433.4	408.9	384.4	365.0	349.7	334.9	318.0	311.4	295.0	290.4	285.9
52.5°	403.2	379.9	357.4	338.4	323.1	308.7	293.9	285.2	274.2	269.6	266.3
55°	360.9	338.4	317.0	300.1	284.8	270.0	260.8	250.1	245.0	241.4	237.4
57.5°	318.4	298.2	281.8	264.7	249.3	237.6	226.9	220.5	215.2	210.5	205.6
60°	291.5	272.1	257.3	241.4	225.6	215.9	207.8	200.1	194.0	186.8	184.8
62.5°	262.9	245.9	232.4	216.9	203.2	194.3	186.5	179.3	171.9	161.5	158.6
65°	223.6	210.3	196.0	183.3	171.0	162.3	151.1	142.9	139.9	138.8	138.3
67.5°	188.1	175.5	163.2	150.2	139.0	131.0	125.3	124.0	121.9	121.3	119.9
70°	164.4	152.6	140.4	128.1	117.4	115.9	113.8	111.8	109.2	108.2	107.2
72.5°	143.1	131.0	118.7	108.9	104.3	102.4	100.4	98.3	96.6	95.6	94.9
75°	109.7	98.5	90.4	86.8	84.2	82.7	79.6	78.1	77.1	75.5	75.0
77.5°	79.0	72.7	68.9	66.7	64.0	62.4	60.6	59.1	58.0	57.7	56.9
80°	60.2	57.2	54.6	51.6	50.5	48.5	48.0	46.5	47.0	45.4	45.4
82.5°	46.8	42.9	40.7	39.3	38.3	36.7	36.1	35.4	35.5	34.4	34.4
85°	24.0	23.0	21.9	20.9	20.9	19.4	19.9	19.4	19.4	18.4	17.9
87.5°	11.3	12.0	12.7	14.1	15.6	16.7	16.5	16.0	15.9	15.7	15.3
90°	17.6	23.3	30.7	38.0	45.4	52.8	52.1	51.4	50.8	50.1	49.9
92.5°	38.6	41.0	42.7	44.5	46.2	47.9	48.1	48.2	48.3	48.5	48.6
95°	91.8	93.8	94.5	95.1	95.8	96.5	96.5	96.5	96.5	96.5	96.1
97.5°	155.0	157.1	158.4	159.7	160.9	162.2	162.2	162.2	162.2	162.2	162.2
100°	202.2	204.0	205.0	206.0	207.0	208.0	208.0	208.0	208.0	208.0	207.9
102.5°	250.7	252.4	253.7	254.9	256.2	257.5	257.8	258.0	258.3	258.6	258.5
105°	328.1	329.0	329.7	330.3	331.0	331.7	332.3	333.0	333.7	334.3	334.7
107.5°	412.6	413.4	413.4	413.4	413.4	413.4	413.6	413.9	414.2	414.4	413.8
110°	467.8	468.9	468.9	468.9	468.9	468.9	468.9	468.9	468.9	468.9	468.3



TEST NUMBER: P331822

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	525.7	526.6	526.3	526.1	525.8	525.5	524.7	523.9	523.1	522.3	521.5
115°	611.1	611.7	611.1	610.4	609.7	609.1	608.7	608.4	608.0	607.7	607.0
117.5°	698.8	699.2	697.3	695.4	693.5	691.7	690.9	690.1	689.3	688.5	687.5
120°	755.5	755.5	752.8	750.1	747.4	744.7	744.7	744.7	744.7	744.7	744.2
122.5°	809.5	810.1	808.3	806.4	804.5	802.6	801.8	801.0	800.2	799.4	798.6
125°	889.5	890.5	889.5	888.5	887.5	886.4	885.4	884.4	883.4	882.4	881.8
127.5°	971.4	972.7	971.5	970.3	969.1	967.9	966.6	965.4	964.2	963.0	961.9
130°	1023.0	1024.8	1024.1	1023.5	1022.8	1022.1	1021.5	1020.8	1020.1	1019.4	1018.4
132.5°	1075.2	1077.1	1077.2	1077.3	1077.5	1077.6	1076.1	1074.7	1073.2	1071.7	1070.4
135°	1149.9	1152.1	1152.8	1153.5	1154.1	1154.8	1154.5	1154.1	1153.8	1153.5	1152.8
137.5°	1225.3	1227.3	1228.2	1229.0	1229.9	1230.8	1230.5	1230.2	1230.0	1229.7	1228.9
140°	1272.4	1274.7	1276.4	1278.1	1279.8	1281.4	1281.4	1281.4	1281.4	1281.4	1280.8
142.5°	1320.6	1322.7	1323.8	1325.0	1326.1	1327.3	1327.5	1327.8	1328.1	1328.3	1327.8
145°	1387.3	1389.5	1391.5	1393.5	1395.5	1397.5	1397.8	1398.2	1398.5	1398.8	1398.3
147.5°	1451.0	1453.1	1454.4	1455.7	1457.1	1458.4	1459.2	1459.9	1460.6	1461.4	1461.1
150°	1490.0	1491.6	1493.0	1494.3	1495.7	1497.0	1498.0	1499.0	1500.0	1501.0	1501.0
152.5°	1527.4	1529.2	1530.8	1532.4	1534.0	1535.6	1536.9	1538.1	1539.4	1540.7	1540.7
155°	1579.4	1580.4	1581.4	1582.4	1583.4	1584.4	1586.1	1587.8	1589.5	1591.1	1591.5
157.5°	1626.0	1626.7	1627.3	1627.9	1628.5	1629.1	1631.3	1633.6	1635.9	1638.2	1638.5
160°	1655.0	1655.5	1655.8	1656.1	1656.5	1656.8	1658.8	1660.8	1662.8	1664.8	1665.2
162.5°	1679.4	1679.6	1679.9	1680.3	1680.6	1680.9	1683.2	1685.5	1687.8	1690.0	1690.4
165°	1712.8	1712.6	1712.6	1712.6	1712.6	1712.6	1714.9	1717.3	1719.6	1722.0	1722.3
167.5°	1739.6	1739.1	1739.0	1739.0	1738.9	1738.8	1741.2	1743.5	1745.9	1748.2	1748.5
170°	1755.3	1754.6	1754.3	1754.0	1753.6	1753.3	1755.6	1758.0	1760.3	1762.7	1762.8
172.5°	1766.2	1765.5	1765.2	1764.8	1764.5	1764.1	1766.5	1768.8	1771.2	1773.5	1773.7
175°	1779.4	1778.6	1777.9	1777.2	1776.6	1775.9	1778.3	1780.6	1782.9	1785.3	1785.5
177.5°	1785.7	1785.0	1784.4	1783.9	1783.4	1782.8	1784.4	1786.1	1787.7	1789.3	1789.3
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331822

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1410.7	1411.5	1410.3	1411.1	1410.3	1411.5	1410.7	1415.2	1416.0	1416.8	1416.0
5°	1314.4	1308.3	1307.3	1305.7	1307.3	1308.3	1314.4	1317.0	1319.0	1323.1	1330.2
7.5°	1199.5	1198.5	1196.0	1192.4	1196.0	1198.5	1199.5	1208.2	1215.2	1223.1	1237.7
10°	1125.5	1123.0	1122.5	1118.9	1122.5	1123.0	1125.5	1136.8	1144.9	1156.2	1176.1
12.5°	1039.0	1022.5	1020.8	1011.9	1020.8	1022.5	1039.0	1053.5	1075.5	1086.3	1107.5
15°	884.6	881.6	871.3	864.7	871.3	881.6	884.6	896.9	905.0	934.6	968.8
17.5°	796.4	786.4	783.2	781.8	783.2	786.4	796.4	802.3	814.0	829.6	850.2
20°	739.6	730.5	728.9	727.9	728.9	730.5	739.6	746.8	756.0	772.8	794.3
22.5°	700.4	690.8	686.9	683.8	686.9	690.8	700.4	706.0	714.3	727.5	742.0
25°	633.5	629.9	627.9	626.8	627.9	629.9	633.5	638.6	646.7	664.6	679.9
27.5°	581.1	573.2	571.7	569.1	571.7	573.2	581.1	590.2	598.7	606.7	620.4
30°	551.3	548.7	545.2	542.1	545.2	548.7	551.3	555.9	561.5	575.3	588.6
32.5°	516.2	514.0	510.9	509.4	510.9	514.0	516.2	522.4	534.1	542.6	552.2
35°	477.3	470.1	467.1	462.5	467.1	470.1	477.3	482.4	487.0	494.1	511.5
37.5°	436.1	432.4	428.1	429.6	428.1	432.4	436.1	438.3	448.0	457.9	465.4
40°	404.3	401.7	400.7	400.2	400.7	401.7	404.3	410.9	422.7	427.2	438.5
42.5°	379.0	371.9	369.3	369.2	369.3	371.9	379.0	386.4	393.7	401.1	412.8
45°	340.5	333.8	329.2	329.8	329.2	333.8	340.5	343.0	349.1	364.0	370.6
47.5°	301.1	300.9	298.0	298.9	298.0	300.9	301.1	305.5	313.3	322.4	333.0
50°	282.3	279.2	277.2	277.7	277.2	279.2	282.3	285.9	290.4	295.0	311.4
52.5°	264.3	261.7	260.0	262.2	260.0	261.7	264.3	266.3	269.6	274.2	285.2
55°	234.8	231.7	231.2	230.7	231.2	231.7	234.8	237.4	241.4	245.0	250.1
57.5°	201.8	199.8	196.7	195.4	196.7	199.8	201.8	205.6	210.5	215.2	220.5
60°	178.1	174.1	169.0	168.4	169.0	174.1	178.1	184.8	186.8	194.0	200.1
62.5°	156.5	155.7	154.7	154.6	154.7	155.7	156.5	158.6	161.5	171.9	179.3
65°	137.3	136.8	137.3	137.8	137.3	136.8	137.3	138.3	138.8	139.9	142.9
67.5°	119.7	118.7	117.8	118.2	117.8	118.7	119.7	119.9	121.3	121.9	124.0
70°	106.2	105.7	105.2	105.2	105.2	105.7	106.2	107.2	108.2	109.2	111.8
72.5°	93.1	93.0	92.5	92.1	92.5	93.0	93.1	94.9	95.6	96.6	98.3
75°	74.5	73.5	73.5	73.5	73.5	73.5	74.5	75.0	75.5	77.1	78.1
77.5°	56.8	56.3	55.7	55.3	55.7	56.3	56.8	56.9	57.7	58.0	59.1
80°	44.9	44.4	43.9	43.9	43.9	44.4	44.9	45.4	45.4	47.0	46.5
82.5°	34.3	33.8	33.7	33.3	33.7	33.8	34.3	34.4	34.4	35.5	35.4
85°	18.4	18.9	18.4	19.4	18.4	18.9	18.4	17.9	18.4	19.4	19.4
87.5°	15.4	15.0	15.5	15.2	15.5	15.0	15.4	15.3	15.7	15.9	16.0
90°	50.3	50.6	50.9	51.3	50.9	50.6	50.3	49.9	50.1	50.8	51.4
92.5°	48.6	48.7	48.8	48.8	48.8	48.7	48.6	48.6	48.5	48.3	48.2
95°	95.5	94.8	94.1	93.5	94.1	94.8	95.5	96.1	96.5	96.5	96.5
97.5°	162.1	162.0	162.0	161.9	162.0	162.0	162.1	162.2	162.2	162.2	162.2
100°	207.5	207.2	206.9	206.5	206.9	207.2	207.5	207.9	208.0	208.0	208.0
102.5°	258.2	257.9	257.5	257.2	257.5	257.9	258.2	258.5	258.6	258.3	258.0
105°	334.7	334.7	334.7	334.7	334.7	334.7	334.7	334.7	334.3	333.7	333.0
107.5°	412.3	410.7	409.2	407.6	409.2	410.7	412.3	413.8	414.4	414.2	413.9
110°	467.3	466.3	465.3	464.3	465.3	466.3	467.3	468.3	468.9	468.9	468.9



TEST NUMBER: P331822

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	520.8	520.1	519.3	518.6	519.3	520.1	520.8	521.5	522.3	523.1	523.9
115°	606.0	605.0	604.0	603.0	604.0	605.0	606.0	607.0	607.7	608.0	608.4
117.5°	686.5	685.5	684.5	683.5	684.5	685.5	686.5	687.5	688.5	689.3	690.1
120°	743.2	742.2	741.2	740.2	741.2	742.2	743.2	744.2	744.7	744.7	744.7
122.5°	797.9	797.2	796.4	795.7	796.4	797.2	797.9	798.6	799.4	800.2	801.0
125°	881.4	881.1	880.8	880.4	880.8	881.1	881.4	881.8	882.4	883.4	884.4
127.5°	960.8	959.7	958.7	957.6	958.7	959.7	960.8	961.9	963.0	964.2	965.4
130°	1017.1	1015.8	1014.4	1013.1	1014.4	1015.8	1017.1	1018.4	1019.4	1020.1	1020.8
132.5°	1069.4	1068.3	1067.2	1066.1	1067.2	1068.3	1069.4	1070.4	1071.7	1073.2	1074.7
135°	1151.8	1150.8	1149.8	1148.8	1149.8	1150.8	1151.8	1152.8	1153.5	1153.8	1154.1
137.5°	1227.6	1226.2	1224.9	1223.5	1224.9	1226.2	1227.6	1228.9	1229.7	1230.0	1230.2
140°	1279.4	1278.1	1276.7	1275.4	1276.7	1278.1	1279.4	1280.8	1281.4	1281.4	1281.4
142.5°	1326.5	1325.1	1323.8	1322.4	1323.8	1325.1	1326.5	1327.8	1328.3	1328.1	1327.8
145°	1397.0	1395.7	1394.3	1393.0	1394.3	1395.7	1397.0	1398.3	1398.8	1398.5	1398.2
147.5°	1459.8	1458.5	1457.3	1456.0	1457.3	1458.5	1459.8	1461.1	1461.4	1460.6	1459.9
150°	1500.0	1499.0	1498.0	1497.0	1498.0	1499.0	1500.0	1501.0	1501.0	1500.0	1499.0
152.5°	1539.4	1538.1	1536.9	1535.6	1536.9	1538.1	1539.4	1540.7	1540.7	1539.4	1538.1
155°	1590.5	1589.5	1588.5	1587.5	1588.5	1589.5	1590.5	1591.5	1591.1	1589.5	1587.8
157.5°	1636.9	1635.3	1633.7	1632.1	1633.7	1635.3	1636.9	1638.5	1638.2	1635.9	1633.6
160°	1663.8	1662.5	1661.2	1659.8	1661.2	1662.5	1663.8	1665.2	1664.8	1662.8	1660.8
162.5°	1688.8	1687.2	1685.6	1683.9	1685.6	1687.2	1688.8	1690.4	1690.0	1687.8	1685.5
165°	1720.6	1719.0	1717.3	1715.6	1717.3	1719.0	1720.6	1722.3	1722.0	1719.6	1717.3
167.5°	1746.8	1745.0	1743.3	1741.5	1743.3	1745.0	1746.8	1748.5	1748.2	1745.9	1743.5
170°	1760.8	1758.8	1756.8	1754.8	1756.8	1758.8	1760.8	1762.8	1762.7	1760.3	1758.0
172.5°	1771.7	1769.7	1767.7	1765.7	1767.7	1769.7	1771.7	1773.7	1773.5	1771.2	1768.8
175°	1783.4	1781.4	1779.4	1777.4	1779.4	1781.4	1783.4	1785.5	1785.3	1782.9	1780.6
177.5°	1787.7	1786.1	1784.4	1782.8	1784.4	1786.1	1787.7	1789.3	1789.3	1787.7	1786.1
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331822

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1412.7	1418.4	1427.0	1431.9	1440.1	1445.4	1448.3	1453.6	1456.4	1466.6	1477.3
5°	1333.8	1342.0	1356.3	1369.5	1383.8	1398.6	1409.4	1421.6	1432.8	1452.2	1472.7
7.5°	1243.4	1254.7	1276.8	1298.0	1322.9	1343.8	1362.3	1383.2	1401.9	1429.7	1458.7
10°	1175.6	1195.5	1224.6	1244.5	1277.2	1298.1	1327.2	1350.1	1376.2	1412.9	1445.6
12.5°	1117.2	1141.2	1164.5	1192.2	1221.6	1256.4	1288.4	1317.9	1348.8	1386.8	1425.2
15°	1011.2	1045.9	1082.2	1110.2	1150.1	1186.8	1224.1	1263.9	1301.7	1347.1	1397.1
17.5°	874.8	915.0	976.0	1024.1	1070.8	1107.7	1153.8	1202.0	1246.5	1301.3	1357.0
20°	813.2	842.8	884.1	948.9	1019.4	1058.7	1105.6	1158.7	1209.8	1269.5	1329.2
22.5°	763.7	790.1	823.3	873.8	952.4	1006.0	1055.0	1108.9	1168.1	1229.1	1295.3
25°	693.2	711.6	746.3	787.1	841.2	929.5	983.1	1037.2	1101.6	1166.9	1242.4
27.5°	640.2	656.7	679.3	718.3	758.5	821.9	907.2	966.2	1030.3	1103.8	1182.2
30°	599.8	619.2	644.2	671.8	715.7	765.2	850.4	918.8	982.1	1057.7	1141.4
32.5°	570.4	585.7	607.0	635.0	671.6	719.0	787.1	870.2	931.9	1011.5	1098.9
35°	522.2	540.1	557.4	584.0	613.6	657.0	708.5	797.3	858.6	937.2	1025.0
37.5°	482.5	493.4	512.6	533.6	564.9	597.2	641.9	721.6	787.8	865.0	954.9
40°	452.3	466.0	480.3	503.8	529.3	560.5	604.4	663.6	739.6	815.2	903.0
42.5°	422.9	440.3	455.4	471.1	499.1	530.3	566.0	616.2	693.9	765.4	850.7
45°	387.4	398.7	414.5	431.8	454.8	481.4	513.0	556.9	631.4	693.2	773.3
47.5°	346.2	362.6	372.9	389.9	411.7	437.0	466.5	504.4	564.8	622.7	697.0
50°	318.0	334.9	349.7	365.0	384.4	408.9	433.4	470.1	518.6	579.4	648.8
52.5°	293.9	308.7	323.1	338.4	357.4	379.9	403.2	435.4	477.0	532.8	600.2
55°	260.8	270.0	284.8	300.1	317.0	338.4	360.9	387.9	423.7	470.6	525.3
57.5°	226.9	237.6	249.3	264.7	281.8	298.2	318.4	342.9	371.1	413.6	460.3
60°	207.8	215.9	225.6	241.4	257.3	272.1	291.5	311.9	338.4	375.2	415.0
62.5°	186.5	194.3	203.2	216.9	232.4	245.9	262.9	284.5	307.0	340.5	375.4
65°	151.1	162.3	171.0	183.3	196.0	210.3	223.6	240.9	260.8	287.4	318.5
67.5°	125.3	131.0	139.0	150.2	163.2	175.5	188.1	201.6	218.9	239.4	264.1
70°	113.8	115.9	117.4	128.1	140.4	152.6	164.4	177.1	191.9	208.8	230.2
72.5°	100.4	102.4	104.3	108.9	118.7	131.0	143.1	152.6	166.6	180.6	198.0
75°	79.6	82.7	84.2	86.8	90.4	98.5	109.7	118.9	127.1	137.8	151.6
77.5°	60.6	62.4	64.0	66.7	68.9	72.7	79.0	87.3	94.9	101.2	110.7
80°	48.0	48.5	50.5	51.6	54.6	57.2	60.2	66.9	74.5	77.1	83.7
82.5°	36.1	36.7	38.3	39.3	40.7	42.9	46.8	48.5	54.5	57.9	62.1
85°	19.9	19.4	20.9	20.9	21.9	23.0	24.0	26.5	28.1	32.2	33.2
87.5°	16.5	16.7	15.6	14.1	12.7	12.0	11.3	10.9	10.9	11.3	12.1
90°	52.1	52.8	45.4	38.0	30.7	23.3	17.6	13.6	9.5	5.5	1.5
92.5°	48.1	47.9	46.2	44.5	42.7	41.0	38.6	35.7	32.7	29.8	26.8
95°	96.5	96.5	95.8	95.1	94.5	93.8	91.8	88.4	85.1	81.7	78.4
97.5°	162.2	162.2	160.9	159.7	158.4	157.1	155.0	152.1	149.1	146.2	143.2
100°	208.0	208.0	207.0	206.0	205.0	204.0	202.2	199.5	196.8	194.1	191.5
102.5°	257.8	257.5	256.2	254.9	253.7	252.4	250.7	248.5	246.4	244.3	242.1
105°	332.3	331.7	331.0	330.3	329.7	329.0	328.1	327.1	326.1	325.1	324.1
107.5°	413.6	413.4	413.4	413.4	413.4	413.4	412.6	411.2	409.7	408.2	406.7
110°	468.9	468.9	468.9	468.9	468.9	468.9	467.8	465.8	463.8	461.8	459.8



TEST NUMBER: P331822

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	524.7	525.5	525.8	526.1	526.3	526.6	525.7	523.7	521.7	519.7	517.7
115°	608.7	609.1	609.7	610.4	611.1	611.7	611.1	609.1	607.0	605.0	603.0
117.5°	690.9	691.7	693.5	695.4	697.3	699.2	698.8	696.1	693.4	690.7	688.1
120°	744.7	744.7	747.4	750.1	752.8	755.5	755.5	752.8	750.1	747.4	744.7
122.5°	801.8	802.6	804.5	806.4	808.3	810.1	809.5	806.2	803.0	799.8	796.6
125°	885.4	886.4	887.5	888.5	889.5	890.5	889.5	886.4	883.4	880.4	877.4
127.5°	966.6	967.9	969.1	970.3	971.5	972.7	971.4	967.6	963.7	959.9	956.1
130°	1021.5	1022.1	1022.8	1023.5	1024.1	1024.8	1023.0	1018.6	1014.3	1009.9	1005.5
132.5°	1076.1	1077.6	1077.5	1077.3	1077.2	1077.1	1075.2	1071.7	1068.1	1064.6	1061.0
135°	1154.5	1154.8	1154.1	1153.5	1152.8	1152.1	1149.9	1146.2	1142.6	1138.9	1135.2
137.5°	1230.5	1230.8	1229.9	1229.0	1228.2	1227.3	1225.3	1222.3	1219.3	1216.3	1213.3
140°	1281.4	1281.4	1279.8	1278.1	1276.4	1274.7	1272.4	1269.4	1266.4	1263.3	1260.3
142.5°	1327.5	1327.3	1326.1	1325.0	1323.8	1322.7	1320.6	1317.6	1314.6	1311.6	1308.6
145°	1397.8	1397.5	1395.5	1393.5	1391.5	1389.5	1387.3	1384.9	1382.6	1380.3	1377.9
147.5°	1459.2	1458.4	1457.1	1455.7	1454.4	1453.1	1451.0	1448.2	1445.3	1442.5	1439.7
150°	1498.0	1497.0	1495.7	1494.3	1493.0	1491.6	1490.0	1488.0	1486.0	1483.9	1481.9
152.5°	1536.9	1535.6	1534.0	1532.4	1530.8	1529.2	1527.4	1525.3	1523.3	1521.3	1519.3
155°	1586.1	1584.4	1583.4	1582.4	1581.4	1580.4	1579.4	1578.4	1577.4	1576.4	1575.4
157.5°	1631.3	1629.1	1628.5	1627.9	1627.3	1626.7	1626.0	1625.4	1624.7	1624.0	1623.3
160°	1658.8	1656.8	1656.5	1656.1	1655.8	1655.5	1655.0	1654.3	1653.6	1653.0	1652.3
162.5°	1683.2	1680.9	1680.6	1680.3	1679.9	1679.6	1679.4	1679.2	1679.1	1679.0	1678.8
165°	1714.9	1712.6	1712.6	1712.6	1712.6	1712.6	1712.8	1713.1	1713.4	1713.8	1714.1
167.5°	1741.2	1738.8	1738.9	1739.0	1739.0	1739.1	1739.6	1740.6	1741.6	1742.6	1743.6
170°	1755.6	1753.3	1753.6	1754.0	1754.3	1754.6	1755.3	1756.3	1757.3	1758.3	1759.3
172.5°	1766.5	1764.1	1764.5	1764.8	1765.2	1765.5	1766.2	1767.2	1768.2	1769.2	1770.2
175°	1778.3	1775.9	1776.6	1777.2	1777.9	1778.6	1779.4	1780.4	1781.4	1782.4	1783.4
177.5°	1784.4	1782.8	1783.4	1783.9	1784.4	1785.0	1785.7	1786.5	1787.3	1788.1	1788.9
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331822

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1477.7	1478.9	1487.1	1490.7	1498.1	1500.9	1504.2	1503.4	1503.4	1505.0	1516.5
5°	1480.8	1491.0	1506.3	1521.1	1535.4	1547.7	1555.9	1564.0	1567.1	1581.9	1595.2
7.5°	1475.5	1494.3	1519.6	1542.2	1569.2	1590.4	1607.9	1623.8	1634.6	1656.1	1678.2
10°	1468.6	1495.1	1523.7	1552.8	1590.1	1618.1	1646.7	1668.7	1675.8	1708.0	1726.4
12.5°	1454.7	1490.2	1526.6	1564.2	1600.7	1639.4	1670.8	1692.8	1717.9	1746.8	1780.7
15°	1433.9	1474.7	1522.2	1570.7	1622.7	1669.7	1703.4	1741.7	1769.2	1800.9	1830.5
17.5°	1403.9	1456.5	1516.9	1573.0	1633.2	1683.7	1730.0	1766.8	1786.2	1804.2	1808.6
20°	1380.3	1436.9	1507.9	1574.2	1634.5	1692.7	1738.6	1769.2	1774.3	1774.8	1747.8
22.5°	1354.5	1418.5	1492.8	1560.8	1632.8	1697.6	1733.3	1746.4	1726.1	1691.5	1639.2
25°	1307.3	1381.3	1467.6	1545.1	1623.8	1685.0	1697.3	1674.3	1603.3	1528.8	1434.4
27.5°	1256.0	1339.2	1431.7	1518.0	1601.7	1639.7	1613.2	1530.4	1402.6	1291.5	1156.9
30°	1218.5	1311.9	1402.7	1499.2	1576.8	1593.1	1532.4	1410.4	1261.3	1093.9	959.7
32.5°	1175.6	1273.5	1373.3	1473.1	1538.0	1522.1	1421.7	1271.5	1096.8	932.2	805.3
35°	1114.3	1215.4	1323.1	1423.1	1464.5	1395.6	1245.5	1050.0	871.3	717.7	630.4
37.5°	1043.6	1153.6	1265.6	1357.5	1354.5	1239.7	1035.3	833.5	683.3	592.4	530.3
40°	993.3	1104.6	1225.6	1303.2	1270.0	1120.4	898.9	708.5	598.8	526.3	480.8
42.5°	945.2	1056.8	1177.0	1238.7	1181.0	997.1	776.4	627.2	536.7	480.1	443.3
45°	863.2	981.1	1092.4	1126.6	1023.5	820.8	627.9	519.6	459.4	417.6	392.0
47.5°	783.0	899.0	1000.6	1001.2	861.7	665.6	529.6	449.7	398.3	365.9	347.3
50°	734.0	844.3	929.5	916.3	758.0	592.1	473.7	404.8	361.9	336.9	317.5
52.5°	678.9	785.9	859.7	821.9	670.2	521.1	423.5	365.6	330.1	308.3	291.0
55°	598.8	693.7	745.8	688.6	546.7	433.4	357.8	312.4	285.9	267.5	252.7
57.5°	520.0	598.4	631.1	564.6	450.3	359.4	302.7	268.6	242.3	229.1	221.4
60°	470.6	537.5	560.5	487.0	391.5	314.4	268.0	236.3	216.9	208.3	200.6
62.5°	422.0	476.7	486.2	418.8	341.3	275.2	235.3	208.6	195.7	187.4	180.2
65°	350.2	389.5	384.9	330.8	270.0	218.5	189.4	173.0	163.3	151.6	138.8
67.5°	288.3	312.3	297.8	257.3	206.1	169.8	150.8	138.4	126.4	115.3	112.3
70°	249.1	262.9	247.6	210.3	169.0	142.4	127.1	112.3	105.2	102.6	98.0
72.5°	211.5	216.3	199.8	167.8	137.5	117.9	103.0	94.7	90.9	88.7	85.8
75°	158.8	155.2	140.9	115.9	95.5	82.2	77.6	74.5	72.0	69.9	68.4
77.5°	111.5	106.3	93.5	77.2	66.5	60.1	57.4	55.7	54.5	53.5	52.0
80°	83.7	80.1	67.4	55.1	50.5	47.5	45.9	43.9	43.9	42.9	41.3
82.5°	61.3	57.3	46.1	40.4	37.9	36.0	34.9	33.7	33.3	33.5	32.4
85°	32.2	26.0	23.0	21.9	20.4	19.4	19.9	18.9	18.9	18.9	18.4
87.5°	10.9	9.7	10.1	10.5	12.0	13.5	14.5	16.0	17.9	17.4	17.6
90°	5.5	9.5	13.6	17.6	23.3	30.7	38.0	45.4	52.8	52.1	51.4
92.5°	29.8	32.7	35.7	38.6	41.0	42.7	44.5	46.2	47.9	48.1	48.2
95°	81.7	85.1	88.4	91.8	93.8	94.5	95.1	95.8	96.5	96.5	96.5
97.5°	146.2	149.1	152.1	155.0	157.1	158.4	159.7	160.9	162.2	162.2	162.2
100°	194.1	196.8	199.5	202.2	204.0	205.0	206.0	207.0	208.0	208.0	208.0
102.5°	244.3	246.4	248.5	250.7	252.4	253.7	254.9	256.2	257.5	257.8	258.0
105°	325.1	326.1	327.1	328.1	329.0	329.7	330.3	331.0	331.7	332.3	333.0
107.5°	408.2	409.7	411.2	412.6	413.4	413.4	413.4	413.4	413.4	413.6	413.9
110°	461.8	463.8	465.8	467.8	468.9	468.9	468.9	468.9	468.9	468.9	468.9





TEST NUMBER: P331822

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	519.7	521.7	523.7	525.7	526.6	526.3	526.1	525.8	525.5	524.7	523.9
115°	605.0	607.0	609.1	611.1	611.7	611.1	610.4	609.7	609.1	608.7	608.4
117.5°	690.7	693.4	696.1	698.8	699.2	697.3	695.4	693.5	691.7	690.9	690.1
120°	747.4	750.1	752.8	755.5	755.5	752.8	750.1	747.4	744.7	744.7	744.7
122.5°	799.8	803.0	806.2	809.5	810.1	808.3	806.4	804.5	802.6	801.8	801.0
125°	880.4	883.4	886.4	889.5	890.5	889.5	888.5	887.5	886.4	885.4	884.4
127.5°	959.9	963.7	967.6	971.4	972.7	971.5	970.3	969.1	967.9	966.6	965.4
130°	1009.9	1014.3	1018.6	1023.0	1024.8	1024.1	1023.5	1022.8	1022.1	1021.5	1020.8
132.5°	1064.6	1068.1	1071.7	1075.2	1077.1	1077.2	1077.3	1077.5	1077.6	1076.1	1074.7
135°	1138.9	1142.6	1146.2	1149.9	1152.1	1152.8	1153.5	1154.1	1154.8	1154.5	1154.1
137.5°	1216.3	1219.3	1222.3	1225.3	1227.3	1228.2	1229.0	1229.9	1230.8	1230.5	1230.2
140°	1263.3	1266.4	1269.4	1272.4	1274.7	1276.4	1278.1	1279.8	1281.4	1281.4	1281.4
142.5°	1311.6	1314.6	1317.6	1320.6	1322.7	1323.8	1325.0	1326.1	1327.3	1327.5	1327.8
145°	1380.3	1382.6	1384.9	1387.3	1389.5	1391.5	1393.5	1395.5	1397.5	1397.8	1398.2
147.5°	1442.5	1445.3	1448.2	1451.0	1453.1	1454.4	1455.7	1457.1	1458.4	1459.2	1459.9
150°	1483.9	1486.0	1488.0	1490.0	1491.6	1493.0	1494.3	1495.7	1497.0	1498.0	1499.0
152.5°	1521.3	1523.3	1525.3	1527.4	1529.2	1530.8	1532.4	1534.0	1535.6	1536.9	1538.1
155°	1576.4	1577.4	1578.4	1579.4	1580.4	1581.4	1582.4	1583.4	1584.4	1586.1	1587.8
157.5°	1624.0	1624.7	1625.4	1626.0	1626.7	1627.3	1627.9	1628.5	1629.1	1631.3	1633.6
160°	1653.0	1653.6	1654.3	1655.0	1655.5	1655.8	1656.1	1656.5	1656.8	1658.8	1660.8
162.5°	1679.0	1679.1	1679.2	1679.4	1679.6	1679.9	1680.3	1680.6	1680.9	1683.2	1685.5
165°	1713.8	1713.4	1713.1	1712.8	1712.6	1712.6	1712.6	1712.6	1712.6	1714.9	1717.3
167.5°	1742.6	1741.6	1740.6	1739.6	1739.1	1739.0	1739.0	1738.9	1738.8	1741.2	1743.5
170°	1758.3	1757.3	1756.3	1755.3	1754.6	1754.3	1754.0	1753.6	1753.3	1755.6	1758.0
172.5°	1769.2	1768.2	1767.2	1766.2	1765.5	1765.2	1764.8	1764.5	1764.1	1766.5	1768.8
175°	1782.4	1781.4	1780.4	1779.4	1778.6	1777.9	1777.2	1776.6	1775.9	1778.3	1780.6
177.5°	1788.1	1787.3	1786.5	1785.7	1785.0	1784.4	1783.9	1783.4	1782.8	1784.4	1786.1
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331822

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1520.5	1525.8	1528.3	1528.3	1531.2	1529.9	1528.7
5°	1607.9	1617.6	1619.7	1628.9	1635.5	1633.4	1634.5
7.5°	1694.8	1710.4	1725.8	1732.9	1734.0	1738.1	1739.6
10°	1748.3	1761.1	1785.1	1781.5	1799.3	1809.6	1792.7
12.5°	1799.8	1817.0	1833.6	1838.2	1848.4	1851.6	1845.0
15°	1846.3	1855.5	1856.5	1854.0	1857.0	1854.5	1844.8
17.5°	1802.8	1787.9	1757.7	1743.4	1732.1	1715.3	1708.6
20°	1730.9	1687.0	1636.0	1615.6	1591.6	1544.6	1555.9
22.5°	1575.8	1525.7	1474.7	1415.1	1386.6	1342.1	1339.4
25°	1334.3	1248.1	1153.1	1086.8	1048.0	1003.6	984.2
27.5°	1037.4	928.8	851.0	811.6	775.8	740.6	739.1
30°	842.2	760.6	700.3	666.7	644.7	629.9	633.0
32.5°	709.9	654.0	613.4	585.4	569.2	558.0	557.8
35°	580.4	542.1	516.1	504.3	492.6	484.4	484.9
37.5°	496.7	473.7	459.2	446.2	438.9	434.9	432.7
40°	453.8	434.9	423.7	416.0	409.9	404.3	403.3
42.5°	419.9	404.3	393.0	387.0	381.3	377.3	376.3
45°	372.6	359.9	349.7	343.0	340.5	336.9	336.9
47.5°	331.5	318.9	311.0	306.8	302.4	300.0	299.9
50°	303.7	294.0	286.9	284.3	280.7	279.2	278.7
52.5°	278.8	271.6	266.5	264.7	263.2	261.2	261.6
55°	245.0	240.9	238.9	237.4	234.8	231.7	233.8
57.5°	216.5	213.1	207.6	202.8	200.4	198.3	199.1
60°	196.5	189.4	182.2	176.6	175.1	170.5	170.5
62.5°	171.2	161.2	152.4	149.3	147.7	145.6	145.2
65°	131.7	127.6	125.6	123.5	122.5	122.5	121.5
67.5°	109.1	107.5	105.3	104.7	103.7	103.4	103.1
70°	96.5	94.4	93.4	92.9	91.9	92.4	90.9
72.5°	84.2	82.6	82.4	81.1	80.4	80.5	79.4
75°	66.4	66.4	65.8	65.3	64.3	63.8	64.3
77.5°	51.0	51.1	50.2	50.1	50.0	50.1	49.6
80°	40.8	41.3	40.8	40.3	39.8	40.3	39.8
82.5°	32.3	31.5	31.4	31.3	31.2	30.9	30.8
85°	18.4	18.9	18.4	17.9	17.9	17.9	18.4
87.5°	17.1	17.0	16.9	17.0	17.1	17.1	16.8
90°	50.8	50.1	49.9	50.3	50.6	50.9	51.3
92.5°	48.3	48.5	48.6	48.6	48.7	48.8	48.8
95°	96.5	96.5	96.1	95.5	94.8	94.1	93.5
97.5°	162.2	162.2	162.2	162.1	162.0	162.0	161.9
100°	208.0	208.0	207.9	207.5	207.2	206.9	206.5
102.5°	258.3	258.6	258.5	258.2	257.9	257.5	257.2
105°	333.7	334.3	334.7	334.7	334.7	334.7	334.7
107.5°	414.2	414.4	413.8	412.3	410.7	409.2	407.6
110°	468.9	468.9	468.3	467.3	466.3	465.3	464.3



TEST NUMBER: P331822

CATALOG NUMBER: S122RDIW-S675D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	523.1	522.3	521.5	520.8	520.1	519.3	518.6
115°	608.0	607.7	607.0	606.0	605.0	604.0	603.0
117.5°	689.3	688.5	687.5	686.5	685.5	684.5	683.5
120°	744.7	744.7	744.2	743.2	742.2	741.2	740.2
122.5°	800.2	799.4	798.6	797.9	797.2	796.4	795.7
125°	883.4	882.4	881.8	881.4	881.1	880.8	880.4
127.5°	964.2	963.0	961.9	960.8	959.7	958.7	957.6
130°	1020.1	1019.4	1018.4	1017.1	1015.8	1014.4	1013.1
132.5°	1073.2	1071.7	1070.4	1069.4	1068.3	1067.2	1066.1
135°	1153.8	1153.5	1152.8	1151.8	1150.8	1149.8	1148.8
137.5°	1230.0	1229.7	1228.9	1227.6	1226.2	1224.9	1223.5
140°	1281.4	1281.4	1280.8	1279.4	1278.1	1276.7	1275.4
142.5°	1328.1	1328.3	1327.8	1326.5	1325.1	1323.8	1322.4
145°	1398.5	1398.8	1398.3	1397.0	1395.7	1394.3	1393.0
147.5°	1460.6	1461.4	1461.1	1459.8	1458.5	1457.3	1456.0
150°	1500.0	1501.0	1501.0	1500.0	1499.0	1498.0	1497.0
152.5°	1539.4	1540.7	1540.7	1539.4	1538.1	1536.9	1535.6
155°	1589.5	1591.1	1591.5	1590.5	1589.5	1588.5	1587.5
157.5°	1635.9	1638.2	1638.5	1636.9	1635.3	1633.7	1632.1
160°	1662.8	1664.8	1665.2	1663.8	1662.5	1661.2	1659.8
162.5°	1687.8	1690.0	1690.4	1688.8	1687.2	1685.6	1683.9
165°	1719.6	1722.0	1722.3	1720.6	1719.0	1717.3	1715.6
167.5°	1745.9	1748.2	1748.5	1746.8	1745.0	1743.3	1741.5
170°	1760.3	1762.7	1762.8	1760.8	1758.8	1756.8	1754.8
172.5°	1771.2	1773.5	1773.7	1771.7	1769.7	1767.7	1765.7
175°	1782.9	1785.3	1785.5	1783.4	1781.4	1779.4	1777.4
177.5°	1787.7	1789.3	1789.3	1787.7	1786.1	1784.4	1782.8
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5

(END OF REPORT)