

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331608-940

Luminaire Tested: **S122DIW-S1005D1240U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331608-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D1240U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7452.4 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331608-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331608-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34
3	81	71	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33	29
4	74	63	55	49	68	59	52	46	50	44	40	41	37	34	34	31	29	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22946	22946	22946
5°	23034	22702	22835
10°	22897	22471	22584
15°	22614	22181	22158
20°	22213	21742	21720
25°	21814	21205	21205
30°	21300	20713	20534
35°	20820	20120	19825
40°	20219	19530	19153
45°	19628	18941	18472
50°	18982	18331	17678
55°	18311	17619	16963
60°	17563	16769	16152
65°	16756	15924	15194
70°	15739	14903	14195
75°	14323	13724	13381
80°	12710	12329	11688
85°	10374	9874	8855



TEST NUMBER: P331608-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.6	1.8
10°-20°	376.0	5.0
20°-30°	552.7	7.4
30°-40°	642.0	8.6
40°-50°	641.3	8.6
50°-60°	559.3	7.5
60°-70°	413.6	5.5
70°-80°	234.2	3.1
80°-90°	68.5	0.9
90°-100°	86.8	1.2
100°-110°	269.6	3.6
110°-120°	460.9	6.2
120°-130°	606.1	8.1
130°-140°	680.3	9.1
140°-150°	667.1	9.0
150°-160°	559.5	7.5
160°-170°	371.1	5.0
170°-180°	129.7	1.7
0°-30°	1062.4	14.3
0°-40°	1704.4	22.9
0°-60°	2905.1	39.0
0°-90°	3621.3	48.6
90°-120°	817.4	11.0
90°-150°	2770.9	37.2
90°-180°	3831.0	51.4
0°-180°	7452.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1421	1421	1421	1421	1421	
5°	1421	1415	1401	1411	1409	135
15°	1353	1344	1327	1332	1326	381
25°	1224	1213	1190	1193	1190	563
35°	1056	1042	1021	1013	1006	659
45°	860	849	830	815	809	663
55°	650	642	626	610	603	581
65°	439	430	417	405	398	434
75°	230	227	220	212	214	245
85°	56	55	53	49	48	64
90°	1	16	40	38	39	6
95°	60	71	74	74	72	69
105°	249	252	254	257	257	263
115°	462	469	467	466	462	457
125°	673	683	680	677	675	601
135°	871	883	886	884	881	672
145°	1057	1065	1072	1073	1068	660
155°	1208	1212	1215	1220	1218	556
165°	1315	1314	1314	1321	1316	371
175°	1368	1364	1362	1369	1363	130
180°	1370	1370	1370	1370	1370	



TEST NUMBER: P331608-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2
2.5°	1427.8	1426.6	1425.4	1424.2	1422.9	1421.0	1418.4	1415.7	1413.0	1410.3	1412.7
5°	1421.2	1420.0	1418.8	1417.6	1416.4	1414.1	1410.8	1407.4	1404.1	1400.7	1403.2
7.5°	1408.6	1406.8	1404.9	1403.0	1401.1	1398.5	1395.1	1391.7	1388.3	1384.9	1387.3
10°	1396.6	1394.5	1392.4	1390.3	1388.1	1385.3	1381.6	1378.0	1374.3	1370.6	1373.1
12.5°	1380.3	1378.3	1376.4	1374.6	1372.7	1369.9	1366.3	1362.6	1359.1	1355.4	1357.1
15°	1352.9	1351.1	1349.2	1347.5	1345.6	1342.7	1338.8	1334.8	1330.9	1327.0	1328.2
17.5°	1317.9	1316.1	1314.3	1312.4	1310.6	1307.7	1303.7	1299.7	1295.7	1291.7	1293.1
20°	1292.8	1290.9	1289.1	1287.3	1285.5	1282.5	1278.2	1274.0	1269.7	1265.4	1266.3
22.5°	1267.7	1265.1	1262.6	1260.0	1257.4	1254.2	1250.2	1246.2	1242.2	1238.1	1238.3
25°	1224.5	1222.0	1219.6	1217.2	1214.8	1210.9	1205.8	1200.6	1195.4	1190.3	1190.9
27.5°	1175.3	1173.0	1170.9	1168.7	1166.5	1163.4	1159.3	1155.2	1151.2	1147.1	1146.2
30°	1142.5	1140.1	1137.6	1135.1	1132.7	1129.3	1124.7	1120.2	1115.6	1111.0	1110.1
32.5°	1107.5	1105.5	1103.6	1101.6	1099.7	1096.4	1091.5	1086.7	1081.9	1077.1	1075.5
35°	1056.3	1053.3	1050.3	1047.2	1044.2	1040.3	1035.4	1030.6	1025.7	1020.8	1019.0
37.5°	998.7	996.0	993.4	990.7	988.0	984.3	979.4	974.6	969.6	964.8	962.5
40°	959.3	956.9	954.5	952.1	949.6	946.0	941.1	936.3	931.4	926.6	923.8
42.5°	921.0	918.6	916.2	913.8	911.3	907.7	902.9	898.0	893.1	888.2	885.3
45°	859.6	857.5	855.3	853.2	851.0	847.7	843.2	838.7	834.1	829.5	826.2
47.5°	798.3	796.4	794.3	792.4	790.3	786.9	782.2	777.5	772.8	768.0	764.5
50°	755.7	754.2	752.7	751.2	749.7	746.7	742.5	738.2	734.0	729.8	725.5
52.5°	714.2	712.2	710.2	708.2	706.1	703.1	699.1	695.1	691.2	687.2	683.6
55°	650.5	648.6	646.8	645.1	643.2	640.4	636.9	633.2	629.5	625.9	622.2
57.5°	586.6	585.1	583.6	582.2	580.7	578.0	574.0	570.0	566.0	562.0	558.4
60°	543.9	542.7	541.4	540.3	539.0	536.3	532.1	527.8	523.5	519.3	515.9
62.5°	502.4	500.4	498.5	496.5	494.5	492.0	488.7	485.4	482.1	478.8	475.7
65°	438.6	436.8	435.1	433.2	431.4	428.9	425.9	422.8	419.8	416.8	414.1
67.5°	373.9	372.5	371.0	369.5	368.1	366.0	363.2	360.5	357.8	355.1	352.9
70°	333.4	332.3	331.0	329.8	328.6	326.6	323.9	321.1	318.4	315.7	313.5
72.5°	291.9	290.7	289.4	288.3	287.0	285.5	283.8	282.0	280.3	278.5	276.3
75°	229.6	229.0	228.4	227.7	227.1	226.0	224.5	223.0	221.5	220.0	218.2
77.5°	173.8	172.8	171.7	170.8	169.7	168.9	168.3	167.6	167.0	166.5	165.5
80°	136.7	136.3	136.1	135.7	135.5	135.0	134.4	133.8	133.1	132.6	131.6
82.5°	101.7	101.7	101.6	101.5	101.4	101.2	100.9	100.5	100.1	99.8	98.6
85°	56.0	55.7	55.5	55.1	54.8	54.5	54.2	53.9	53.6	53.3	52.3
87.5°	19.9	20.1	20.2	20.3	20.4	20.8	21.5	22.1	22.7	23.4	22.6
90°	1.2	4.3	7.3	10.4	13.5	17.8	23.5	29.2	34.8	40.5	39.9
92.5°	20.6	22.8	25.1	27.4	29.6	31.4	32.7	34.1	35.4	36.7	36.8
95°	60.1	62.7	65.3	67.9	70.4	72.0	72.5	72.9	73.5	74.0	74.0
97.5°	109.9	112.1	114.4	116.6	118.9	120.5	121.5	122.4	123.4	124.4	124.4
100°	146.9	148.9	151.0	153.0	155.1	156.5	157.2	158.0	158.8	159.5	159.5
102.5°	185.7	187.3	189.0	190.6	192.3	193.6	194.6	195.6	196.5	197.5	197.7
105°	248.6	249.3	250.1	250.9	251.6	252.4	252.8	253.3	253.9	254.4	254.9
107.5°	311.9	313.1	314.2	315.3	316.5	317.0	317.0	317.0	317.0	317.0	317.3
110°	352.7	354.2	355.7	357.3	358.8	359.6	359.6	359.6	359.6	359.6	359.6



TEST NUMBER: P331608-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	397.1	398.6	400.1	401.7	403.2	403.9	403.7	403.5	403.2	403.1	402.4
115°	462.5	464.0	465.6	467.1	468.7	469.1	468.7	468.1	467.6	467.1	466.9
117.5°	527.7	529.8	531.8	533.9	535.9	536.3	534.8	533.3	531.9	530.5	529.9
120°	571.1	573.2	575.3	577.4	579.4	579.4	577.4	575.3	573.2	571.1	571.1
122.5°	610.9	613.4	615.9	618.3	620.8	621.3	619.9	618.5	617.0	615.5	614.9
125°	672.9	675.2	677.5	679.8	682.2	683.0	682.2	681.4	680.6	679.8	679.1
127.5°	733.3	736.2	739.1	742.1	745.0	746.0	745.1	744.1	743.2	742.3	741.4
130°	771.2	774.5	777.9	781.2	784.5	786.0	785.5	785.0	784.4	783.9	783.4
132.5°	813.8	816.5	819.2	821.9	824.7	826.1	826.2	826.3	826.3	826.4	825.4
135°	870.7	873.4	876.3	879.1	882.0	883.6	884.1	884.7	885.2	885.6	885.4
137.5°	930.5	932.8	935.1	937.5	939.8	941.3	941.9	942.6	943.3	944.0	943.8
140°	966.6	968.9	971.3	973.6	975.9	977.7	978.9	980.3	981.5	982.8	982.8
142.5°	1003.6	1005.9	1008.3	1010.6	1012.9	1014.4	1015.3	1016.2	1017.1	1018.0	1018.2
145°	1056.8	1058.6	1060.4	1062.2	1064.0	1065.7	1067.2	1068.7	1070.3	1071.8	1072.1
147.5°	1104.2	1106.3	1108.5	1110.7	1112.9	1114.5	1115.4	1116.5	1117.5	1118.6	1119.1
150°	1136.6	1138.1	1139.7	1141.2	1142.7	1144.1	1145.0	1146.1	1147.1	1148.2	1148.9
152.5°	1165.3	1166.8	1168.3	1169.8	1171.4	1172.8	1174.0	1175.3	1176.5	1177.8	1178.8
155°	1208.3	1209.1	1209.8	1210.6	1211.4	1212.1	1212.9	1213.6	1214.4	1215.2	1216.5
157.5°	1245.0	1245.5	1246.1	1246.6	1247.1	1247.6	1248.0	1248.5	1248.9	1249.5	1251.2
160°	1267.2	1267.7	1268.3	1268.8	1269.3	1269.7	1269.9	1270.2	1270.4	1270.7	1272.2
162.5°	1287.5	1287.7	1287.8	1287.9	1288.0	1288.2	1288.4	1288.7	1289.0	1289.2	1290.9
165°	1314.6	1314.4	1314.1	1313.8	1313.6	1313.5	1313.5	1313.5	1313.5	1313.5	1315.3
167.5°	1337.3	1336.5	1335.8	1335.0	1334.2	1333.8	1333.7	1333.7	1333.6	1333.6	1335.4
170°	1349.3	1348.5	1347.8	1347.0	1346.2	1345.8	1345.5	1345.2	1345.0	1344.7	1346.5
172.5°	1357.6	1356.9	1356.1	1355.3	1354.6	1354.1	1353.8	1353.5	1353.3	1353.0	1354.9
175°	1367.8	1367.1	1366.3	1365.5	1364.8	1364.1	1363.6	1363.1	1362.5	1362.0	1363.9
177.5°	1372.0	1371.4	1370.7	1370.1	1369.5	1369.0	1368.6	1368.2	1367.8	1367.3	1368.6
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331608-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2	1421.2
2.5°	1415.1	1417.6	1420.0	1421.0	1420.5	1420.0	1419.5	1419.1
5°	1405.6	1408.0	1410.4	1411.4	1410.8	1410.2	1409.5	1408.9
7.5°	1389.7	1392.1	1394.6	1395.5	1394.8	1394.2	1393.5	1392.9
10°	1375.6	1378.0	1380.4	1381.2	1380.3	1379.3	1378.4	1377.5
12.5°	1358.8	1360.5	1362.2	1362.7	1362.0	1361.4	1360.7	1360.0
15°	1329.4	1330.6	1331.8	1331.7	1330.2	1328.6	1327.1	1325.6
17.5°	1294.5	1295.9	1297.3	1297.3	1295.7	1294.3	1292.9	1291.4
20°	1267.3	1268.2	1269.1	1268.9	1267.7	1266.5	1265.3	1264.1
22.5°	1238.5	1238.7	1238.9	1238.6	1237.9	1237.2	1236.4	1235.6
25°	1191.5	1192.1	1192.8	1192.8	1192.1	1191.5	1190.9	1190.3
27.5°	1145.3	1144.3	1143.4	1142.3	1140.9	1139.3	1137.9	1136.5
30°	1109.2	1108.3	1107.4	1106.3	1105.1	1103.8	1102.7	1101.4
32.5°	1073.9	1072.2	1070.6	1069.2	1067.9	1066.8	1065.5	1064.3
35°	1017.2	1015.4	1013.5	1011.9	1010.4	1008.9	1007.3	1005.8
37.5°	960.3	958.1	955.8	954.0	952.5	951.0	949.6	948.2
40°	921.0	918.4	915.6	913.6	912.4	911.2	910.0	908.7
42.5°	882.3	879.3	876.4	874.1	872.4	870.7	869.0	867.2
45°	822.9	819.5	816.2	813.9	812.6	811.5	810.2	809.0
47.5°	761.0	757.4	753.9	751.3	749.5	747.8	746.0	744.2
50°	721.2	717.0	712.7	709.9	708.4	706.9	705.3	703.8
52.5°	680.1	676.5	673.1	670.3	668.2	666.3	664.2	662.3
55°	618.6	614.9	611.4	608.8	607.3	605.7	604.2	602.6
57.5°	554.7	551.2	547.6	545.2	544.1	543.0	541.8	540.6
60°	512.6	509.3	506.0	503.8	502.9	502.0	501.1	500.2
62.5°	472.7	469.6	466.5	464.3	463.2	462.0	460.8	459.7
65°	411.3	408.6	405.9	403.8	402.3	400.7	399.2	397.7
67.5°	350.8	348.7	346.5	344.8	343.7	342.4	341.3	340.0
70°	311.4	309.3	307.2	305.5	304.3	303.1	301.8	300.7
72.5°	274.3	272.2	270.0	268.5	267.5	266.5	265.6	264.6
75°	216.4	214.5	212.8	212.1	212.8	213.3	213.9	214.5
77.5°	164.6	163.7	162.8	161.9	161.0	160.2	159.3	158.5
80°	130.7	129.8	128.9	128.1	127.5	127.0	126.4	125.7
82.5°	97.5	96.3	95.1	94.5	94.3	94.3	94.2	94.0
85°	51.5	50.6	49.7	49.0	48.8	48.4	48.2	47.8
87.5°	21.8	20.9	20.1	19.5	19.4	19.2	19.0	18.8
90°	39.4	39.0	38.4	38.3	38.5	38.8	39.1	39.3
92.5°	37.0	37.1	37.2	37.3	37.3	37.4	37.5	37.5
95°	74.0	74.0	74.0	73.7	73.2	72.7	72.2	71.7
97.5°	124.4	124.4	124.4	124.4	124.3	124.3	124.2	124.2
100°	159.5	159.5	159.5	159.4	159.2	158.9	158.6	158.4
102.5°	197.9	198.1	198.3	198.3	198.0	197.8	197.5	197.2
105°	255.4	255.9	256.5	256.7	256.7	256.7	256.7	256.7
107.5°	317.4	317.6	317.9	317.4	316.2	315.0	313.8	312.6
110°	359.6	359.6	359.6	359.2	358.5	357.7	356.9	356.1



TEST NUMBER: P331608-940

CATALOG NUMBER: S122DIW-S1005D1240U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	401.8	401.2	400.6	400.0	399.4	398.9	398.3	397.7
115°	466.6	466.4	466.1	465.6	464.8	464.0	463.2	462.5
117.5°	529.2	528.6	528.0	527.4	526.6	525.8	525.0	524.2
120°	571.1	571.1	571.1	570.8	570.0	569.3	568.5	567.8
122.5°	614.4	613.8	613.1	612.5	612.0	611.4	610.8	610.3
125°	678.3	677.5	676.8	676.3	676.0	675.7	675.5	675.2
127.5°	740.5	739.5	738.6	737.7	736.9	736.1	735.3	734.4
130°	782.9	782.4	781.9	781.1	780.1	779.1	778.0	776.9
132.5°	824.2	823.0	822.0	821.0	820.2	819.3	818.5	817.7
135°	885.2	884.9	884.7	884.1	883.3	882.6	881.8	881.0
137.5°	943.5	943.3	943.2	942.5	941.5	940.5	939.4	938.4
140°	982.8	982.8	982.8	982.3	981.2	980.3	979.2	978.2
142.5°	1018.3	1018.6	1018.8	1018.3	1017.4	1016.3	1015.3	1014.2
145°	1072.4	1072.6	1072.8	1072.5	1071.5	1070.4	1069.4	1068.4
147.5°	1119.6	1120.3	1120.8	1120.6	1119.6	1118.7	1117.7	1116.7
150°	1149.7	1150.5	1151.2	1151.2	1150.5	1149.7	1148.9	1148.2
152.5°	1179.7	1180.6	1181.6	1181.6	1180.6	1179.7	1178.8	1177.8
155°	1217.8	1219.1	1220.3	1220.6	1219.9	1219.1	1218.3	1217.5
157.5°	1252.9	1254.6	1256.4	1256.7	1255.4	1254.2	1252.9	1251.7
160°	1273.8	1275.3	1276.8	1277.1	1276.1	1275.1	1274.1	1273.0
162.5°	1292.7	1294.4	1296.2	1296.5	1295.2	1294.0	1292.7	1291.6
165°	1317.1	1318.8	1320.7	1320.9	1319.6	1318.4	1317.1	1315.8
167.5°	1337.2	1339.0	1340.8	1341.0	1339.7	1338.4	1337.0	1335.7
170°	1348.3	1350.1	1351.9	1352.0	1350.5	1349.0	1347.4	1345.9
172.5°	1356.6	1358.4	1360.2	1360.3	1358.8	1357.3	1355.8	1354.2
175°	1365.7	1367.4	1369.2	1369.4	1367.8	1366.3	1364.8	1363.2
177.5°	1369.8	1371.1	1372.3	1372.3	1371.1	1369.8	1368.6	1367.3
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1

(END OF REPORT)