

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331808

Luminaire Tested: **S122RDIW-S675D435U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331808
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D435U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3823.4 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331808

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331808

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66
1	101	97	93	89	94	91	87	84	79	77	75	69	67	65	59	58	57
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49
3	85	75	68	62	79	71	64	59	62	57	53	55	51	48	47	45	42
4	78	67	59	53	72	63	56	51	56	50	46	49	45	41	43	40	37
5	72	60	52	46	67	57	50	44	50	45	40	44	40	36	39	35	33
6	66	54	46	41	62	51	44	39	46	40	35	40	36	32	35	32	29
7	61	49	41	36	57	47	39	34	42	36	32	37	32	29	33	29	26
8	57	45	37	32	53	43	36	31	38	32	28	34	29	26	30	26	23
9	53	41	34	29	50	39	32	28	35	29	26	31	27	23	28	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	25	21	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18213	18213	18213
5°	18282	17985	18084
10°	18143	17690	17539
15°	17934	17167	16672
20°	17646	16417	15593
25°	17350	15567	14549
30°	16940	14693	13209
35°	16539	13742	12033
40°	16136	12760	10671
45°	15664	11654	9439
50°	15179	10540	8231
55°	14686	9340	7068
60°	14108	8076	5867
65°	13456	6785	5345
70°	12675	5589	4914
75°	11715	5097	4585
80°	10349	4556	4175
85°	8133	3594	3594



TEST NUMBER: P331808

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.6	2.8
10°-20°	289.9	7.6
20°-30°	407.1	10.6
30°-40°	443.9	11.6
40°-50°	408.2	10.7
50°-60°	320.6	8.4
60°-70°	209.0	5.5
70°-80°	107.8	2.8
80°-90°	30.1	0.8
90°-100°	34.0	0.9
100°-110°	105.7	2.8
110°-120°	180.6	4.7
120°-130°	237.5	6.2
130°-140°	266.6	7.0
140°-150°	261.4	6.8
150°-160°	219.2	5.7
160°-170°	145.4	3.8
170°-180°	50.8	1.3
0°-30°	802.6	21.0
0°-40°	1246.6	32.6
0°-60°	1975.3	51.7
0°-90°	2322.2	60.7
90°-120°	320.3	8.4
90°-150°	1085.7	28.4
90°-180°	1501.0	39.3
0°-180°	3823.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1128	1128	1128	1128	1128	
5°	1128	1122	1110	1118	1116	107
15°	1073	1060	1027	1008	997	302
25°	974	939	874	833	817	448
35°	839	785	697	635	610	525
45°	686	615	510	441	413	529
55°	522	440	332	273	251	466
65°	352	269	178	145	140	349
75°	188	118	82	75	74	199
85°	44	23	19	19	19	52
90°	0	6	16	15	15	3
95°	24	28	29	29	28	27
105°	97	99	100	101	101	103
115°	181	184	183	182	181	179
125°	264	267	266	265	265	236
135°	341	346	347	346	345	263
145°	414	417	420	420	419	259
155°	473	475	476	478	477	218
165°	515	515	515	518	516	145
175°	536	535	534	537	534	51
180°	537	537	537	537	537	



TEST NUMBER: P331808

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0
2.5°	1132.1	1131.2	1130.3	1129.4	1128.5	1127.0	1125.0	1123.0	1121.1	1119.1	1120.9
5°	1128.0	1126.9	1125.8	1124.6	1123.5	1121.5	1118.5	1115.6	1112.6	1109.7	1111.7
7.5°	1116.4	1115.0	1113.6	1112.2	1110.8	1108.3	1104.9	1101.5	1098.0	1094.6	1095.1
10°	1106.6	1105.0	1103.4	1101.8	1100.2	1097.2	1092.6	1088.1	1083.6	1079.0	1078.4
12.5°	1094.3	1092.4	1090.4	1088.5	1086.5	1082.7	1076.9	1071.1	1065.2	1059.4	1058.2
15°	1072.9	1070.4	1067.9	1065.4	1062.9	1057.8	1050.1	1042.4	1034.7	1027.0	1022.7
17.5°	1046.6	1042.8	1039.0	1035.1	1031.3	1024.5	1014.6	1004.7	994.8	984.9	979.8
20°	1027.0	1022.4	1017.9	1013.4	1008.8	1000.9	989.5	978.2	966.9	955.5	949.8
22.5°	1005.7	1000.7	995.6	990.5	985.4	976.5	963.7	950.9	938.1	925.3	918.0
25°	973.9	966.6	959.4	952.1	944.9	933.7	918.8	903.8	888.8	873.8	864.5
27.5°	935.5	927.6	919.7	911.8	903.9	891.5	874.7	857.8	840.9	824.0	813.2
30°	908.6	899.9	891.3	882.7	874.1	860.7	842.5	824.4	806.2	788.1	776.5
32.5°	882.4	872.3	862.3	852.2	842.1	827.8	809.3	790.8	772.3	753.8	740.6
35°	839.1	827.6	816.0	804.4	792.9	777.1	757.1	737.2	717.2	697.2	682.9
37.5°	795.9	783.1	770.4	757.7	745.0	728.0	706.8	685.5	664.2	642.9	627.2
40°	765.6	752.0	738.4	724.8	711.2	693.4	671.4	649.4	627.4	605.4	589.3
42.5°	734.6	720.3	705.9	691.6	677.3	658.7	636.0	613.3	590.5	567.8	551.1
45°	686.0	670.8	655.6	640.4	625.2	605.7	581.9	558.1	534.2	510.4	494.3
47.5°	638.6	622.5	606.4	590.3	574.2	553.9	529.3	504.7	480.1	455.5	439.5
50°	604.3	588.2	572.1	556.0	539.9	519.4	494.4	469.5	444.5	419.6	403.9
52.5°	570.9	554.0	537.2	520.4	503.5	482.9	458.5	434.1	409.7	385.3	370.2
55°	521.7	504.0	486.3	468.6	450.9	429.8	405.3	380.8	356.3	331.8	318.2
57.5°	471.2	453.1	434.9	416.8	398.6	377.8	354.2	330.7	307.1	283.6	271.1
60°	436.9	418.8	400.6	382.5	364.3	343.6	320.2	296.8	273.5	250.1	238.5
62.5°	403.4	385.3	367.1	349.0	330.8	310.6	288.4	266.1	243.8	221.5	210.5
65°	352.2	333.8	315.4	297.1	278.7	259.3	238.9	218.5	198.0	177.6	169.9
67.5°	302.8	284.5	266.3	248.1	229.8	211.5	193.1	174.8	156.4	138.0	134.5
70°	268.5	250.8	233.1	215.4	197.7	181.0	165.4	149.7	134.1	118.4	116.1
72.5°	235.8	218.8	201.9	184.9	167.9	153.2	140.6	128.0	115.5	102.9	101.0
75°	187.8	172.0	156.1	140.2	124.3	112.5	104.8	97.1	89.4	81.7	80.1
77.5°	140.7	126.7	112.8	98.9	85.0	76.1	72.4	68.7	65.0	61.3	60.3
80°	111.3	99.7	88.1	76.6	65.0	58.1	55.8	53.5	51.3	49.0	48.1
82.5°	84.3	75.3	66.3	57.2	48.2	42.9	41.4	39.8	38.3	36.8	36.2
85°	43.9	39.1	34.4	29.6	24.8	22.1	21.4	20.8	20.1	19.4	19.4
87.5°	13.2	11.9	10.7	9.5	8.3	7.9	8.4	8.8	9.3	9.7	9.5
90°	0.5	1.7	2.9	4.1	5.3	7.0	9.2	11.4	13.6	15.9	15.7
92.5°	8.1	9.0	9.8	10.7	11.6	12.3	12.8	13.4	13.9	14.4	14.4
95°	23.6	24.6	25.6	26.6	27.6	28.2	28.4	28.6	28.8	29.0	29.0
97.5°	43.0	43.9	44.8	45.7	46.6	47.2	47.6	48.0	48.4	48.7	48.7
100°	57.5	58.3	59.1	60.0	60.8	61.3	61.6	61.9	62.2	62.5	62.5
102.5°	72.8	73.4	74.0	74.7	75.3	75.9	76.2	76.6	77.0	77.4	77.5
105°	97.4	97.7	98.0	98.3	98.6	98.9	99.1	99.3	99.5	99.7	99.9
107.5°	122.2	122.7	123.1	123.6	124.0	124.2	124.2	124.2	124.2	124.2	124.3
110°	138.2	138.8	139.4	140.0	140.6	140.9	140.9	140.9	140.9	140.9	140.9



TEST NUMBER: P331808

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	155.6	156.2	156.8	157.4	158.0	158.3	158.2	158.1	158.0	157.9	157.7
115°	181.2	181.8	182.4	183.0	183.6	183.8	183.6	183.4	183.2	183.0	182.9
117.5°	206.8	207.6	208.4	209.2	210.0	210.1	209.6	209.0	208.4	207.9	207.6
120°	223.8	224.6	225.4	226.2	227.0	227.0	226.2	225.4	224.6	223.8	223.8
122.5°	239.4	240.4	241.3	242.3	243.3	243.5	242.9	242.3	241.8	241.2	241.0
125°	263.7	264.6	265.5	266.4	267.3	267.6	267.3	267.0	266.7	266.4	266.1
127.5°	287.3	288.5	289.6	290.8	291.9	292.3	292.0	291.6	291.2	290.9	290.5
130°	302.2	303.5	304.8	306.1	307.4	308.0	307.8	307.6	307.4	307.2	307.0
132.5°	318.9	319.9	321.0	322.1	323.1	323.7	323.7	323.8	323.8	323.8	323.4
135°	341.2	342.3	343.4	344.5	345.6	346.2	346.4	346.6	346.8	347.0	346.9
137.5°	364.6	365.5	366.4	367.3	368.2	368.8	369.1	369.4	369.6	369.9	369.8
140°	378.8	379.7	380.6	381.5	382.4	383.1	383.6	384.1	384.6	385.1	385.1
142.5°	393.3	394.2	395.1	396.0	396.9	397.5	397.8	398.2	398.5	398.9	399.0
145°	414.1	414.8	415.5	416.2	416.9	417.6	418.2	418.8	419.4	420.0	420.1
147.5°	432.7	433.5	434.4	435.2	436.1	436.7	437.1	437.5	437.9	438.3	438.5
150°	445.4	446.0	446.6	447.2	447.8	448.3	448.7	449.1	449.5	449.9	450.2
152.5°	456.6	457.2	457.8	458.4	459.0	459.6	460.0	460.5	461.0	461.5	461.9
155°	473.4	473.7	474.0	474.4	474.7	475.0	475.3	475.6	475.9	476.2	476.7
157.5°	487.9	488.1	488.3	488.5	488.7	488.8	489.0	489.2	489.4	489.6	490.3
160°	496.6	496.8	497.0	497.2	497.4	497.5	497.6	497.7	497.8	497.9	498.5
162.5°	504.5	504.6	504.6	504.6	504.7	504.8	504.9	505.0	505.1	505.2	505.8
165°	515.1	515.0	514.9	514.8	514.7	514.7	514.7	514.7	514.7	514.7	515.4
167.5°	524.0	523.7	523.4	523.1	522.8	522.6	522.6	522.6	522.6	522.6	523.3
170°	528.7	528.4	528.1	527.8	527.5	527.3	527.2	527.1	527.0	526.9	527.6
172.5°	532.0	531.7	531.4	531.1	530.8	530.6	530.5	530.4	530.3	530.2	530.9
175°	536.0	535.7	535.4	535.1	534.8	534.5	534.3	534.1	533.9	533.7	534.4
177.5°	537.6	537.4	537.1	536.9	536.6	536.4	536.3	536.1	535.9	535.8	536.3
180°	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9



TEST NUMBER: P331808

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0
2.5°	1122.7	1124.5	1126.3	1127.0	1126.7	1126.3	1126.0	1125.6
5°	1113.7	1115.8	1117.8	1118.5	1117.8	1117.1	1116.5	1115.8
7.5°	1095.7	1096.3	1096.9	1096.6	1095.4	1094.3	1093.1	1091.9
10°	1077.7	1077.0	1076.3	1075.3	1073.9	1072.6	1071.2	1069.8
12.5°	1057.0	1055.8	1054.5	1052.8	1050.5	1048.3	1046.0	1043.7
15°	1018.4	1014.0	1009.7	1006.4	1004.2	1001.9	999.6	997.4
17.5°	974.7	969.5	964.4	959.9	956.0	952.1	948.2	944.3
20°	944.2	938.5	932.8	927.5	922.5	917.5	912.5	907.5
22.5°	910.7	903.4	896.1	890.6	886.8	883.1	879.4	875.7
25°	855.2	845.9	836.6	830.3	826.9	823.5	820.1	816.7
27.5°	802.3	791.5	780.7	772.5	767.1	761.7	756.3	750.9
30°	765.0	753.4	741.8	733.0	726.8	720.7	714.6	708.5
32.5°	727.4	714.2	701.0	691.5	685.7	680.0	674.2	668.5
35°	668.7	654.4	640.1	630.4	625.4	620.4	615.5	610.5
37.5°	611.4	595.7	580.0	569.2	563.5	557.8	552.1	546.4
40°	573.1	557.0	540.9	529.9	524.0	518.1	512.2	506.3
42.5°	534.5	517.8	501.2	490.0	484.3	478.6	472.9	467.1
45°	478.2	462.1	446.0	435.2	429.8	424.3	418.9	413.4
47.5°	423.5	407.5	391.4	381.0	376.0	371.1	366.1	361.2
50°	388.3	372.6	357.0	346.7	342.0	337.2	332.5	327.7
52.5°	355.1	339.9	324.8	315.1	310.7	306.3	301.9	297.5
55°	304.6	290.9	277.3	268.4	264.1	259.7	255.4	251.1
57.5°	258.6	246.2	233.7	225.6	222.0	218.4	214.7	211.1
60°	227.0	215.4	203.8	196.2	192.6	189.0	185.3	181.7
62.5°	199.5	188.4	177.4	170.8	168.6	166.5	164.3	162.1
65°	162.2	154.5	146.8	142.6	141.9	141.2	140.5	139.9
67.5°	130.9	127.4	123.9	121.7	121.0	120.3	119.6	118.8
70°	113.9	111.6	109.3	107.8	106.8	105.9	105.0	104.1
72.5°	99.1	97.2	95.3	94.1	93.5	93.0	92.4	91.9
75°	78.5	76.9	75.3	74.4	74.2	74.0	73.7	73.5
77.5°	59.4	58.5	57.6	57.0	56.6	56.3	55.9	55.5
80°	47.2	46.3	45.4	44.9	44.9	44.9	44.9	44.9
82.5°	35.7	35.1	34.6	34.3	34.3	34.3	34.3	34.3
85°	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4
87.5°	9.3	9.0	8.8	8.7	8.7	8.8	8.8	8.8
90°	15.5	15.3	15.1	15.0	15.1	15.2	15.3	15.4
92.5°	14.5	14.5	14.6	14.6	14.6	14.6	14.7	14.7
95°	29.0	29.0	29.0	28.9	28.7	28.5	28.3	28.1
97.5°	48.7	48.7	48.7	48.7	48.7	48.7	48.7	48.7
100°	62.5	62.5	62.5	62.5	62.4	62.3	62.2	62.1
102.5°	77.5	77.6	77.7	77.7	77.6	77.5	77.4	77.3
105°	100.1	100.3	100.5	100.6	100.6	100.6	100.6	100.6
107.5°	124.4	124.5	124.6	124.4	123.9	123.4	123.0	122.5
110°	140.9	140.9	140.9	140.7	140.4	140.1	139.8	139.5



TEST NUMBER: P331808

CATALOG NUMBER: S122RDIW-S675D435U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	157.5	157.2	157.0	156.7	156.5	156.3	156.1	155.9
115°	182.8	182.7	182.6	182.4	182.1	181.8	181.5	181.2
117.5°	207.4	207.1	206.9	206.6	206.3	206.0	205.7	205.4
120°	223.8	223.8	223.8	223.7	223.4	223.1	222.8	222.5
122.5°	240.7	240.5	240.2	240.0	239.8	239.6	239.3	239.1
125°	265.8	265.5	265.2	265.0	264.9	264.8	264.7	264.6
127.5°	290.1	289.8	289.4	289.1	288.7	288.4	288.1	287.8
130°	306.8	306.6	306.4	306.1	305.7	305.3	304.9	304.5
132.5°	323.0	322.5	322.1	321.7	321.4	321.0	320.7	320.4
135°	346.8	346.7	346.6	346.4	346.1	345.8	345.5	345.2
137.5°	369.7	369.6	369.6	369.3	368.9	368.5	368.1	367.7
140°	385.1	385.1	385.1	384.9	384.5	384.1	383.7	383.3
142.5°	399.0	399.1	399.2	399.0	398.6	398.2	397.8	397.4
145°	420.2	420.3	420.4	420.2	419.8	419.4	419.0	418.6
147.5°	438.7	439.0	439.2	439.1	438.7	438.3	437.9	437.6
150°	450.5	450.8	451.1	451.1	450.8	450.5	450.2	449.9
152.5°	462.2	462.6	463.0	463.0	462.6	462.2	461.9	461.5
155°	477.2	477.7	478.2	478.3	478.0	477.7	477.4	477.1
157.5°	490.9	491.6	492.3	492.4	491.9	491.4	491.0	490.5
160°	499.1	499.7	500.3	500.4	500.0	499.6	499.2	498.8
162.5°	506.5	507.2	507.9	508.0	507.5	507.0	506.5	506.1
165°	516.1	516.8	517.5	517.6	517.1	516.6	516.1	515.6
167.5°	524.0	524.7	525.4	525.5	524.9	524.4	523.9	523.4
170°	528.3	529.0	529.7	529.8	529.2	528.6	528.0	527.4
172.5°	531.6	532.3	533.0	533.0	532.4	531.8	531.2	530.6
175°	535.1	535.8	536.5	536.6	536.0	535.4	534.8	534.2
177.5°	536.8	537.2	537.7	537.7	537.2	536.8	536.3	535.8
180°	536.9	536.9	536.9	536.9	536.9	536.9	536.9	536.9

(END OF REPORT)