

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331585-940

Luminaire Tested: **S122DIW-S1005D435U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331585-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S1005D435U940-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 435 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5467.8 lumens  
Efficiency: N/A  
Efficacy: 104.3 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 52.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331585-940

CATALOG NUMBER: S122DIW-S1005D435U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331585-940

CATALOG NUMBER: S122DIW-S1005D435U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	72
1	103	99	95	92	98	94	91	88	85	82	80	76	74	73	68	67	66	62
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	61	59	56	53
3	87	78	70	65	82	74	67	62	67	62	58	61	57	53	55	52	49	46
4	80	69	61	55	76	66	59	53	60	54	50	55	50	46	49	46	43	40
5	74	62	54	48	70	59	52	47	54	48	44	49	44	41	45	41	38	35
6	68	56	48	42	65	54	46	41	49	43	38	45	40	36	41	37	34	31
7	63	51	43	38	60	49	42	36	45	39	34	41	36	32	38	33	30	28
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	30	27	25
9	55	43	35	30	52	41	34	29	38	32	28	35	30	26	32	28	25	23
10	52	40	32	27	49	38	31	27	35	29	25	33	28	24	30	26	23	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	28709	28709	28709	28709
5°	32185	28896	25606	28896
10°	36882	28658	22161	28658
15°	40802	28134	19579	28134
20°	40180	27569	17849	27569
25°	36230	26820	16751	26820
30°	29940	25620	15951	25620
35°	21821	24366	15382	24366
40°	17428	22885	15066	22885
45°	15230	21174	14636	21174
50°	14315	19515	14350	19515
55°	13196	17833	13965	17833
60°	12093	16043	13372	16043
65°	11018	14437	12791	14437
70°	10003	12873	11939	12873
75°	8865	11123	10574	11123
80°	7624	9214	8517	9214
85°	6836	6836	5076	6836



TEST NUMBER: P331585-940

CATALOG NUMBER: S122DIW-S1005D435U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	169.3	3.1
10°-20°	492.3	9.0
20°-30°	714.5	13.1
30°-40°	754.0	13.8
40°-50°	667.6	12.2
50°-60°	532.7	9.7
60°-70°	362.1	6.6
70°-80°	185.6	3.4
80°-90°	46.1	0.8
90°-100°	17.6	0.3
100°-110°	64.4	1.2
110°-120°	172.2	3.1
120°-130°	284.3	5.2
130°-140°	302.4	5.5
140°-150°	281.0	5.1
150°-160°	225.9	4.1
160°-170°	145.6	2.7
170°-180°	50.1	0.9
0°-30°	1376.1	25.2
0°-40°	2130.1	39.0
0°-60°	3330.4	60.9
0°-90°	3924.2	71.8
90°-120°	254.2	4.6
90°-150°	1121.9	20.5
90°-180°	1544.0	28.2
0°-180°	5467.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1778	1778	1778	1778	1778	
5°	1986	1783	1580	1783	1986	198
15°	2441	1683	1171	1683	2441	674
25°	2034	1506	940	1506	2034	919
35°	1107	1236	780	1236	1107	720
45°	667	927	641	927	667	524
55°	469	634	496	634	469	420
65°	288	378	335	378	288	287
75°	142	178	170	178	142	152
85°	37	37	27	37	37	41
90°	10	0	10	0	10	6
95°	16	25	16	25	16	15
105°	29	116	29	116	29	30
115°	31	219	31	219	31	78
125°	326	310	326	310	326	282
135°	396	383	396	383	396	305
145°	452	445	452	445	452	282
155°	490	490	490	490	490	226
165°	515	516	515	516	515	145
175°	525	528	525	528	525	50
180°	527	527	527	527	527	



TEST NUMBER: P331585-940

CATALOG NUMBER: S122DIW-S1005D435U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1860.1	1860.6	1861.7	1853.0	1851.9	1851.9	1844.2	1837.7	1830.1	1819.6	1820.8
5°	1985.8	1993.3	1996.1	1987.9	1975.6	1974.2	1962.7	1943.5	1925.7	1911.4	1901.1
7.5°	2135.9	2138.9	2132.3	2121.5	2112.3	2095.9	2074.3	2053.1	2023.5	1996.3	1976.0
10°	2249.6	2253.7	2242.1	2226.4	2213.4	2194.3	2162.8	2130.7	2091.8	2054.2	2024.1
12.5°	2336.0	2346.1	2331.2	2329.1	2306.9	2280.6	2243.2	2227.0	2172.1	2119.8	2087.6
15°	2441.0	2440.3	2441.7	2428.7	2412.3	2408.2	2368.6	2325.5	2248.3	2217.5	2164.2
17.5°	2410.7	2421.0	2425.8	2425.6	2425.3	2422.7	2409.9	2382.7	2344.0	2294.2	2232.7
20°	2338.5	2352.2	2354.2	2369.9	2378.8	2390.4	2395.2	2387.6	2363.7	2322.1	2268.8
22.5°	2227.0	2230.8	2237.2	2261.6	2280.9	2310.1	2325.2	2350.5	2341.4	2320.9	2276.4
25°	2033.7	2026.9	2050.8	2063.1	2107.5	2153.9	2187.5	2224.4	2257.2	2277.0	2264.0
27.5°	1801.6	1791.4	1827.2	1859.8	1896.0	1946.2	1998.4	2060.0	2111.3	2175.4	2197.4
30°	1605.9	1612.0	1646.2	1681.1	1735.7	1806.8	1865.5	1933.2	2006.3	2078.1	2128.0
32.5°	1394.9	1418.5	1440.1	1493.5	1541.7	1621.0	1707.0	1791.6	1882.8	1964.4	2041.7
35°	1107.1	1134.3	1164.5	1203.4	1271.0	1349.6	1433.7	1547.8	1672.2	1783.6	1875.2
37.5°	931.8	927.5	944.7	972.9	1027.6	1091.1	1187.8	1300.6	1447.0	1577.9	1707.0
40°	826.9	824.1	836.4	862.4	904.1	950.6	1035.3	1134.3	1270.3	1430.3	1584.0
42.5°	754.7	756.3	763.2	781.5	810.0	848.3	911.8	996.0	1120.6	1271.2	1436.5
45°	667.0	671.7	679.3	688.1	704.5	736.0	771.5	831.7	930.1	1055.8	1218.4
47.5°	603.8	604.0	611.6	619.4	629.1	646.8	675.8	713.5	783.0	885.4	1025.2
50°	569.9	565.2	570.6	576.8	587.0	599.3	618.4	654.0	700.4	783.1	900.0
52.5°	528.3	528.5	533.4	535.7	544.9	557.2	574.7	599.3	641.4	706.1	802.1
55°	468.8	472.2	474.9	479.0	487.2	496.1	509.8	526.2	559.0	607.5	678.6
57.5°	412.8	413.8	416.6	424.4	429.5	437.7	450.8	465.7	487.0	522.9	576.3
60°	374.5	374.5	380.0	383.3	390.2	398.4	408.7	423.0	442.1	471.5	514.6
62.5°	339.5	338.9	341.2	346.7	352.0	359.6	369.8	382.0	400.0	426.1	461.5
65°	288.4	287.0	291.1	292.5	297.9	305.5	313.7	326.6	341.0	360.2	391.6
67.5°	239.2	240.9	243.0	245.6	248.6	256.5	262.0	271.2	283.3	299.2	320.5
70°	211.9	211.9	211.9	213.9	218.0	222.1	227.6	235.1	246.7	260.4	279.5
72.5°	181.2	183.4	185.6	184.4	189.6	192.0	198.6	202.9	213.9	222.7	239.6
75°	142.1	142.1	142.1	145.5	147.6	149.6	153.7	157.8	163.4	174.2	183.2
77.5°	106.0	105.8	106.5	107.3	109.5	111.9	113.2	116.8	121.9	127.0	134.5
80°	82.0	83.4	84.1	85.4	85.4	86.8	87.5	92.3	95.7	99.1	103.9
82.5°	63.4	63.7	63.8	64.1	64.6	65.5	67.2	68.8	70.0	72.9	76.5
85°	36.9	36.2	36.2	37.5	36.9	36.9	38.3	39.6	39.6	40.3	42.4
87.5°	16.2	16.2	16.8	16.1	16.1	16.6	16.5	15.9	16.4	16.9	17.2
90°	10.3	10.2	10.0	9.8	9.6	9.3	8.9	8.5	8.0	7.6	7.0
92.5°	10.3	10.2	10.1	10.0	9.9	9.7	9.5	9.3	9.1	8.8	8.5
95°	16.4	16.5	16.6	16.7	16.8	16.6	16.1	15.7	15.2	14.9	14.3
97.5°	21.8	21.8	21.7	21.6	21.5	21.2	21.0	20.6	20.2	19.9	18.5
100°	25.5	25.3	25.2	25.1	24.9	24.4	23.7	23.1	22.4	21.8	20.2
102.5°	27.4	27.1	26.9	26.7	26.4	25.9	25.0	24.1	23.2	22.3	34.4
105°	29.0	28.6	28.3	27.9	27.6	27.0	26.0	25.1	24.2	23.3	46.4
107.5°	29.8	29.4	29.2	28.8	28.4	28.7	29.7	30.7	31.6	32.5	60.3
110°	30.1	29.8	29.4	29.1	28.7	32.8	41.3	49.8	58.2	66.7	91.1



TEST NUMBER: P331585-940

CATALOG NUMBER: S122DIW-S1005D435U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	30.4	30.1	29.9	29.6	29.3	44.7	75.5	106.5	137.3	168.3	174.2
115°	31.2	37.4	43.4	49.6	55.6	78.3	117.5	156.8	195.9	235.1	233.0
117.5°	127.6	147.7	167.6	187.7	207.8	222.5	232.0	241.5	251.0	260.5	259.0
120°	232.5	243.9	255.4	266.8	278.2	283.5	282.4	281.4	280.4	279.4	277.9
122.5°	290.1	292.3	294.5	296.8	299.0	299.8	299.2	298.5	298.0	297.4	295.7
125°	325.8	325.7	325.4	325.1	324.9	324.4	323.9	323.2	322.6	322.1	320.5
127.5°	348.4	348.4	348.3	348.3	348.2	347.8	346.9	346.1	345.2	344.3	343.1
130°	362.5	362.6	362.7	362.7	362.8	362.4	361.4	360.5	359.5	358.6	357.8
132.5°	376.2	376.3	376.3	376.4	376.5	376.1	375.3	374.6	373.8	373.0	372.0
135°	396.0	396.2	396.4	396.5	396.6	396.4	395.5	394.7	393.8	393.0	392.2
137.5°	414.0	414.4	414.6	414.9	415.2	414.9	414.1	413.3	412.4	411.6	410.7
140°	425.3	425.8	426.1	426.6	427.0	426.9	426.1	425.3	424.5	423.8	422.8
142.5°	436.3	436.8	437.2	437.6	438.0	437.9	437.2	436.5	435.8	435.1	434.0
145°	451.7	452.1	452.5	452.9	453.3	453.3	452.6	452.1	451.5	450.8	449.4
147.5°	465.1	465.5	465.8	466.2	466.5	466.5	466.1	465.7	465.2	464.8	463.3
150°	473.4	473.8	474.2	474.7	475.1	475.0	474.5	474.0	473.5	473.0	471.6
152.5°	480.4	480.9	481.5	482.1	482.6	482.7	482.1	481.6	481.1	480.6	479.3
155°	490.2	490.8	491.5	492.1	492.8	492.9	492.4	492.0	491.4	490.9	489.9
157.5°	499.1	499.7	500.3	501.1	501.7	501.8	501.1	500.6	500.0	499.4	498.7
160°	504.3	504.8	505.4	506.0	506.6	506.7	506.1	505.6	505.2	504.6	504.1
162.5°	508.5	509.3	510.0	510.7	511.4	511.5	511.0	510.3	509.8	509.2	508.7
165°	514.9	515.5	516.1	516.7	517.3	517.3	516.7	516.1	515.5	514.9	514.7
167.5°	519.0	519.7	520.5	521.2	522.0	522.1	521.5	520.9	520.3	519.7	519.5
170°	521.4	522.2	522.9	523.7	524.4	524.5	524.0	523.3	522.7	522.2	522.0
172.5°	523.3	524.0	524.8	525.5	526.3	526.4	525.8	525.1	524.6	524.0	523.8
175°	524.9	525.7	526.6	527.4	528.2	528.3	527.7	527.2	526.6	525.9	525.8
177.5°	525.8	526.4	527.0	527.6	528.2	528.3	527.8	527.4	526.9	526.4	526.4
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331585-940

CATALOG NUMBER: S122DIW-S1005D435U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1824.6	1820.2	1817.5	1807.7	1798.8	1790.1	1787.4	1788.5	1776.5	1765.0	1760.1
5°	1895.7	1882.0	1869.0	1850.6	1828.7	1804.7	1792.4	1782.9	1759.0	1733.0	1718.0
7.5°	1959.4	1939.8	1914.8	1880.1	1848.2	1810.6	1786.7	1765.5	1730.5	1693.9	1671.5
10°	1998.1	1971.5	1939.4	1897.0	1858.1	1812.3	1780.1	1748.0	1707.0	1663.3	1635.9
12.5°	2031.5	1995.6	1964.0	1909.6	1863.5	1806.2	1768.2	1722.9	1679.7	1627.7	1601.0
15°	2110.9	2044.6	1984.5	1923.0	1866.3	1786.3	1743.9	1683.1	1626.4	1562.2	1531.4
17.5°	2172.3	2097.7	2003.0	1924.9	1858.8	1770.2	1708.0	1635.1	1568.1	1494.7	1452.9
20°	2207.3	2121.8	2020.0	1927.1	1847.8	1746.7	1679.0	1604.5	1526.0	1443.2	1398.2
22.5°	2228.0	2138.2	2037.6	1918.9	1826.0	1727.5	1642.4	1560.8	1481.1	1391.9	1344.6
25°	2234.6	2152.6	2046.0	1912.1	1798.6	1687.2	1584.7	1505.5	1409.1	1325.7	1256.7
27.5°	2202.1	2143.3	2040.8	1899.2	1767.0	1636.8	1522.5	1432.7	1331.1	1240.5	1171.2
30°	2162.1	2128.0	2028.2	1886.1	1741.9	1601.8	1476.0	1374.2	1273.1	1181.5	1110.4
32.5°	2100.4	2093.0	2005.3	1867.5	1715.1	1557.6	1427.5	1324.5	1212.5	1122.5	1054.7
35°	1979.1	2011.8	1956.5	1826.0	1664.6	1494.5	1353.7	1236.2	1120.1	1033.9	970.4
37.5°	1816.4	1897.8	1883.4	1765.1	1596.6	1425.9	1270.5	1147.6	1037.0	950.0	887.7
40°	1704.3	1808.2	1823.2	1718.7	1548.5	1372.9	1208.2	1085.8	977.9	898.7	835.7
42.5°	1584.0	1705.4	1746.7	1662.9	1496.0	1317.1	1152.4	1025.7	918.8	841.8	786.0
45°	1382.4	1543.0	1617.6	1569.7	1408.5	1225.3	1055.8	927.3	830.3	757.9	714.8
47.5°	1194.0	1369.5	1469.6	1452.7	1311.0	1129.6	962.1	838.7	744.3	686.5	648.0
50°	1060.6	1241.0	1361.9	1367.4	1241.0	1061.2	893.1	776.9	690.2	636.2	604.8
52.5°	944.7	1116.9	1248.8	1277.7	1162.8	990.2	831.3	715.8	639.4	589.8	561.6
55°	793.4	939.0	1085.2	1138.4	1046.2	882.3	735.3	633.5	561.7	527.5	502.9
57.5°	659.6	781.0	916.0	974.9	918.0	777.7	639.9	551.4	493.3	463.3	444.4
60°	589.1	684.7	805.0	875.4	826.2	701.2	580.9	496.8	449.0	422.3	404.6
62.5°	523.4	608.2	709.9	774.3	747.4	629.5	521.8	447.6	406.4	381.3	368.5
65°	431.9	498.8	577.5	636.9	619.1	529.6	441.5	377.9	345.1	325.3	315.0
67.5°	355.6	404.0	458.5	510.6	496.2	432.8	362.0	312.5	288.1	271.0	264.8
70°	307.6	344.4	393.0	434.6	423.0	371.0	315.0	272.7	251.5	237.1	231.0
72.5°	261.6	291.9	329.0	363.0	355.2	312.0	265.3	233.3	217.0	203.8	198.8
75°	197.5	220.7	243.3	265.8	263.8	230.3	203.0	178.3	165.4	155.2	153.1
77.5°	145.8	158.8	174.2	187.5	183.8	164.7	143.2	129.1	119.6	112.7	111.6
80°	111.4	118.9	129.8	139.4	134.6	126.4	109.3	99.1	92.3	85.4	82.7
82.5°	80.8	88.3	94.9	100.0	96.4	88.7	78.2	71.2	67.1	62.4	61.3
85°	42.4	46.5	49.2	50.6	49.2	44.4	39.6	36.9	33.5	31.5	30.8
87.5°	17.7	17.5	17.4	18.3	16.5	16.3	13.9	12.1	11.8	11.4	10.4
90°	6.2	5.6	4.9	4.1	3.2	2.2	1.3	0.4	1.3	2.2	3.2
92.5°	8.2	7.8	7.5	7.4	7.4	7.5	7.6	7.7	7.6	7.5	7.4
95°	13.6	13.1	12.5	13.6	16.4	19.2	21.9	24.8	21.9	19.2	16.4
97.5°	17.1	15.8	14.4	17.7	25.5	33.4	41.3	49.1	41.3	33.4	25.5
100°	18.8	17.4	16.0	21.0	32.6	44.2	55.8	67.5	55.8	44.2	32.6
102.5°	46.5	58.5	70.5	77.8	80.3	82.7	85.2	87.6	85.2	82.7	80.3
105°	69.5	92.6	115.7	126.0	123.5	120.9	118.4	115.8	118.4	120.9	123.5
107.5°	88.0	115.7	143.5	156.3	154.3	152.2	150.2	148.1	150.2	152.2	154.3
110°	115.7	140.1	164.6	175.9	174.2	172.4	170.6	168.8	170.6	172.4	174.2





TEST NUMBER: P331585-940

CATALOG NUMBER: S122DIW-S1005D435U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	180.3	186.4	192.4	194.7	193.1	191.5	189.9	188.3	189.9	191.5	193.1
115°	231.0	228.8	226.7	224.9	223.5	222.0	220.6	219.2	220.6	222.0	223.5
117.5°	257.5	256.1	254.7	253.1	251.5	249.9	248.3	246.6	248.3	249.9	251.5
120°	276.3	274.8	273.3	271.9	270.6	269.3	268.0	266.8	268.0	269.3	270.6
122.5°	294.0	292.4	290.7	289.2	287.8	286.5	285.2	283.8	285.2	286.5	287.8
125°	318.9	317.3	315.6	314.2	313.2	312.1	310.9	309.9	310.9	312.1	313.2
127.5°	341.9	340.7	339.5	338.3	337.1	335.8	334.7	333.4	334.7	335.8	337.1
130°	356.8	355.9	354.9	353.7	352.4	351.1	349.7	348.4	349.7	351.1	352.4
132.5°	371.1	370.1	369.3	368.2	367.0	365.9	364.7	363.6	364.7	365.9	367.0
135°	391.5	390.7	389.9	388.9	387.4	386.1	384.8	383.4	384.8	386.1	387.4
137.5°	409.9	409.0	408.1	407.2	406.4	405.4	404.4	403.5	404.4	405.4	406.4
140°	422.0	421.1	420.1	419.3	418.6	417.9	417.2	416.6	417.2	417.9	418.6
142.5°	432.9	431.9	430.9	430.0	429.4	428.7	428.2	427.6	428.2	428.7	429.4
145°	448.0	446.6	445.1	444.4	444.5	444.6	444.7	444.8	444.7	444.6	444.5
147.5°	461.9	460.5	459.1	458.5	458.9	459.1	459.5	459.8	459.5	459.1	458.9
150°	470.3	469.0	467.5	467.2	467.8	468.3	469.0	469.6	469.0	468.3	467.8
152.5°	478.0	476.7	475.5	475.1	475.8	476.4	477.2	477.8	477.2	476.4	475.8
155°	488.8	487.9	486.9	486.7	487.5	488.2	489.0	489.7	489.0	488.2	487.5
157.5°	498.0	497.3	496.6	496.6	497.2	497.8	498.5	499.1	498.5	497.8	497.2
160°	503.6	503.1	502.6	502.6	503.1	503.6	504.1	504.6	504.1	503.6	503.1
162.5°	508.3	507.8	507.5	507.5	508.0	508.5	509.0	509.5	509.0	508.5	508.0
165°	514.4	514.2	513.9	514.0	514.5	515.1	515.6	516.0	515.6	515.1	514.5
167.5°	519.2	519.0	518.8	518.9	519.4	520.0	520.4	520.9	520.4	520.0	519.4
170°	521.8	521.7	521.5	521.7	522.2	522.6	523.2	523.7	523.2	522.6	522.2
172.5°	523.6	523.4	523.3	523.4	524.0	524.5	525.0	525.5	525.0	524.5	524.0
175°	525.7	525.5	525.3	525.5	526.1	526.6	527.3	527.9	527.3	526.6	526.1
177.5°	526.3	526.2	526.1	526.4	526.8	527.3	527.8	528.2	527.8	527.3	526.8
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331585-940

CATALOG NUMBER: S122DIW-S1005D435U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1754.6	1751.3	1739.8	1733.8	1724.0	1714.7	1708.7	1711.5	1713.6	1712.5	1710.8
5°	1704.3	1691.3	1671.5	1654.4	1642.1	1619.6	1610.0	1605.3	1601.2	1596.3	1591.5
7.5°	1644.4	1624.0	1595.5	1571.2	1548.2	1520.2	1504.2	1494.7	1484.8	1474.0	1464.5
10°	1601.8	1573.1	1543.0	1508.9	1481.6	1456.3	1433.7	1418.6	1405.0	1392.0	1382.4
12.5°	1557.0	1523.9	1486.7	1440.0	1409.9	1373.7	1370.3	1343.8	1322.4	1314.4	1303.1
15°	1485.6	1439.1	1392.0	1336.7	1312.8	1280.0	1259.5	1238.9	1220.5	1207.5	1204.1
17.5°	1404.6	1344.4	1297.5	1257.8	1218.6	1185.0	1166.1	1149.7	1134.5	1117.1	1114.8
20°	1342.8	1290.8	1239.7	1204.8	1164.5	1130.2	1107.1	1090.7	1077.6	1067.4	1058.5
22.5°	1284.3	1227.4	1180.5	1142.5	1102.7	1075.0	1056.8	1040.9	1030.1	1018.8	1010.4
25°	1190.4	1146.0	1094.8	1051.7	1018.9	1001.1	986.1	972.4	965.6	958.1	948.5
27.5°	1108.3	1058.9	1010.9	977.6	948.8	933.1	922.4	913.1	906.7	902.3	896.9
30°	1050.3	1000.4	962.9	930.1	906.2	890.5	883.6	878.2	870.6	867.9	865.1
32.5°	994.5	949.6	917.5	889.0	866.2	856.0	849.7	844.8	838.9	836.2	830.7
35°	915.7	878.2	846.7	831.0	812.5	803.6	798.9	792.0	786.6	783.8	783.1
37.5°	841.5	808.9	788.2	767.9	760.2	754.7	748.1	743.5	741.9	741.5	740.7
40°	793.4	766.7	748.3	731.9	728.4	720.2	714.8	710.7	710.7	711.4	710.7
42.5°	749.7	725.8	709.4	695.3	691.3	686.3	680.9	680.6	681.7	684.0	681.7
45°	683.4	666.3	654.7	647.8	640.3	635.5	634.8	636.9	637.6	638.3	640.3
47.5°	622.4	611.1	600.6	593.0	589.8	588.9	588.1	591.7	594.9	596.2	599.3
50°	586.3	573.4	564.5	559.6	557.0	555.5	557.0	561.1	563.7	567.2	569.3
52.5°	545.9	536.7	530.6	526.9	525.8	526.6	526.9	531.5	535.9	537.2	538.1
55°	490.0	483.1	481.8	475.6	478.3	477.7	481.1	483.8	487.9	492.0	492.7
57.5°	434.2	428.7	425.1	425.6	426.4	429.4	432.3	437.1	441.5	445.9	446.2
60°	397.1	394.3	392.3	392.3	393.6	397.7	401.1	405.9	408.7	411.3	413.4
62.5°	363.1	360.4	358.4	359.4	363.0	365.4	369.4	372.0	374.8	377.5	378.4
65°	309.6	308.2	310.2	311.7	312.3	315.8	320.5	322.5	325.3	326.6	331.4
67.5°	260.2	260.5	260.2	262.2	266.1	266.9	271.4	276.3	276.8	279.4	282.5
70°	226.9	228.3	229.6	231.0	234.4	235.8	239.2	241.2	244.0	246.0	248.1
72.5°	196.3	196.5	197.9	197.6	200.5	203.5	206.3	208.4	211.2	213.7	215.8
75°	151.1	151.1	152.4	153.1	156.5	159.9	159.3	160.6	163.4	166.0	167.5
77.5°	110.3	108.8	110.3	111.0	112.1	114.9	115.5	117.4	120.6	119.6	121.1
80°	84.1	82.0	84.1	84.7	84.7	88.2	88.2	89.5	91.6	89.5	91.6
82.5°	60.0	59.0	60.5	60.7	61.8	61.9	63.0	63.3	65.4	64.4	65.4
85°	30.1	29.4	30.1	29.4	30.1	30.8	30.8	30.1	30.1	31.5	29.4
87.5°	10.1	9.7	9.3	9.5	9.0	8.6	8.2	8.3	8.4	7.3	7.4
90°	4.1	4.9	5.6	6.2	7.0	7.6	8.0	8.5	8.9	9.3	9.6
92.5°	7.4	7.5	7.8	8.2	8.5	8.8	9.1	9.3	9.5	9.7	9.9
95°	13.6	12.5	13.1	13.6	14.3	14.9	15.2	15.7	16.1	16.6	16.8
97.5°	17.7	14.4	15.8	17.1	18.5	19.9	20.2	20.6	21.0	21.2	21.5
100°	21.0	16.0	17.4	18.8	20.2	21.8	22.4	23.1	23.7	24.4	24.9
102.5°	77.8	70.5	58.5	46.5	34.4	22.3	23.2	24.1	25.0	25.9	26.4
105°	126.0	115.7	92.6	69.5	46.4	23.3	24.2	25.1	26.0	27.0	27.6
107.5°	156.3	143.5	115.7	88.0	60.3	32.5	31.6	30.7	29.7	28.7	28.4
110°	175.9	164.6	140.1	115.7	91.1	66.7	58.2	49.8	41.3	32.8	28.7



TEST NUMBER: P331585-940

CATALOG NUMBER: S122DIW-S1005D435U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	194.7	192.4	186.4	180.3	174.2	168.3	137.3	106.5	75.5	44.7	29.3
115°	224.9	226.7	228.8	231.0	233.0	235.1	195.9	156.8	117.5	78.3	55.6
117.5°	253.1	254.7	256.1	257.5	259.0	260.5	251.0	241.5	232.0	222.5	207.8
120°	271.9	273.3	274.8	276.3	277.9	279.4	280.4	281.4	282.4	283.5	278.2
122.5°	289.2	290.7	292.4	294.0	295.7	297.4	298.0	298.5	299.2	299.8	299.0
125°	314.2	315.6	317.3	318.9	320.5	322.1	322.6	323.2	323.9	324.4	324.9
127.5°	338.3	339.5	340.7	341.9	343.1	344.3	345.2	346.1	346.9	347.8	348.2
130°	353.7	354.9	355.9	356.8	357.8	358.6	359.5	360.5	361.4	362.4	362.8
132.5°	368.2	369.3	370.1	371.1	372.0	373.0	373.8	374.6	375.3	376.1	376.5
135°	388.9	389.9	390.7	391.5	392.2	393.0	393.8	394.7	395.5	396.4	396.6
137.5°	407.2	408.1	409.0	409.9	410.7	411.6	412.4	413.3	414.1	414.9	415.2
140°	419.3	420.1	421.1	422.0	422.8	423.8	424.5	425.3	426.1	426.9	427.0
142.5°	430.0	430.9	431.9	432.9	434.0	435.1	435.8	436.5	437.2	437.9	438.0
145°	444.4	445.1	446.6	448.0	449.4	450.8	451.5	452.1	452.6	453.3	453.3
147.5°	458.5	459.1	460.5	461.9	463.3	464.8	465.2	465.7	466.1	466.5	466.5
150°	467.2	467.5	469.0	470.3	471.6	473.0	473.5	474.0	474.5	475.0	475.1
152.5°	475.1	475.5	476.7	478.0	479.3	480.6	481.1	481.6	482.1	482.7	482.6
155°	486.7	486.9	487.9	488.8	489.9	490.9	491.4	492.0	492.4	492.9	492.8
157.5°	496.6	496.6	497.3	498.0	498.7	499.4	500.0	500.6	501.1	501.8	501.7
160°	502.6	502.6	503.1	503.6	504.1	504.6	505.2	505.6	506.1	506.7	506.6
162.5°	507.5	507.5	507.8	508.3	508.7	509.2	509.8	510.3	511.0	511.5	511.4
165°	514.0	513.9	514.2	514.4	514.7	514.9	515.5	516.1	516.7	517.3	517.3
167.5°	518.9	518.8	519.0	519.2	519.5	519.7	520.3	520.9	521.5	522.1	522.0
170°	521.7	521.5	521.7	521.8	522.0	522.2	522.7	523.3	524.0	524.5	524.4
172.5°	523.4	523.3	523.4	523.6	523.8	524.0	524.6	525.1	525.8	526.4	526.3
175°	525.5	525.3	525.5	525.7	525.8	525.9	526.6	527.2	527.7	528.3	528.2
177.5°	526.4	526.1	526.2	526.3	526.4	526.4	526.9	527.4	527.8	528.3	528.2
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331585-940

CATALOG NUMBER: S122DIW-S1005D435U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1705.4	1704.3	1704.3	1699.4	1704.3	1704.3	1705.4	1710.8	1712.5	1713.6	1711.5
5°	1582.0	1579.9	1576.5	1579.9	1576.5	1579.9	1582.0	1591.5	1596.3	1601.2	1605.3
7.5°	1459.9	1451.7	1450.5	1442.4	1450.5	1451.7	1459.9	1464.5	1474.0	1484.8	1494.7
10°	1370.8	1365.4	1364.7	1351.7	1364.7	1365.4	1370.8	1382.4	1392.0	1405.0	1418.6
12.5°	1303.1	1289.9	1292.5	1285.0	1292.5	1289.9	1303.1	1303.1	1314.4	1322.4	1343.8
15°	1185.6	1185.6	1182.9	1171.3	1182.9	1185.6	1185.6	1204.1	1207.5	1220.5	1238.9
17.5°	1101.4	1099.9	1093.4	1096.6	1093.4	1099.9	1101.4	1114.8	1117.1	1134.5	1149.7
20°	1051.0	1047.0	1038.8	1038.8	1038.8	1047.0	1051.0	1058.5	1067.4	1077.6	1090.7
22.5°	1003.4	1003.2	994.4	997.2	994.4	1003.2	1003.4	1010.4	1018.8	1030.1	1040.9
25°	947.8	942.4	938.3	940.3	938.3	942.4	947.8	948.5	958.1	965.6	972.4
27.5°	895.1	892.1	891.8	886.2	891.8	892.1	895.1	896.9	902.3	906.7	913.1
30°	864.4	857.6	859.0	855.6	859.0	857.6	864.4	865.1	867.9	870.6	878.2
32.5°	829.5	827.0	825.6	822.8	825.6	827.0	829.5	830.7	836.2	838.9	844.8
35°	781.8	782.5	779.0	780.4	779.0	782.5	781.8	783.1	783.8	786.6	792.0
37.5°	740.1	742.3	740.7	741.0	740.7	742.3	740.1	740.7	741.5	741.9	743.5
40°	712.7	712.7	712.7	714.8	712.7	712.7	712.7	710.7	711.4	710.7	710.7
42.5°	686.5	685.5	684.3	684.2	684.3	685.5	686.5	681.7	684.0	681.7	680.6
45°	641.7	643.7	644.4	641.0	644.4	643.7	641.7	640.3	638.3	637.6	636.9
47.5°	601.1	601.4	601.1	604.1	601.1	601.4	601.1	599.3	596.2	594.9	591.7
50°	572.7	571.3	572.7	571.3	572.7	571.3	572.7	569.3	567.2	563.7	561.1
52.5°	542.6	542.9	542.1	541.8	542.1	542.9	542.6	538.1	537.2	535.9	531.5
55°	495.4	496.8	496.1	496.1	496.1	496.8	495.4	492.7	492.0	487.9	483.8
57.5°	446.7	447.9	448.8	445.9	448.8	447.9	446.7	446.2	445.9	441.5	437.1
60°	412.8	416.2	415.4	414.1	415.4	416.2	412.8	413.4	411.3	408.7	405.9
62.5°	381.6	382.8	382.7	382.5	382.7	382.8	381.6	378.4	377.5	374.8	372.0
65°	333.5	334.8	332.8	334.8	332.8	334.8	333.5	331.4	326.6	325.3	322.5
67.5°	281.7	282.1	283.6	284.5	283.6	282.1	281.7	282.5	279.4	276.8	276.3
70°	249.4	248.8	250.8	252.9	250.8	248.8	249.4	248.1	246.0	244.0	241.2
72.5°	215.5	217.0	216.3	217.8	216.3	217.0	215.5	215.8	213.7	211.2	208.4
75°	166.0	168.1	167.5	169.5	167.5	168.1	166.0	167.5	166.0	163.4	160.6
77.5°	120.0	120.3	120.0	121.1	120.0	120.3	120.0	121.1	119.6	120.6	117.4
80°	91.6	90.2	88.8	91.6	88.8	90.2	91.6	91.6	89.5	91.6	89.5
82.5°	63.7	64.5	63.1	63.1	63.1	64.5	63.7	65.4	64.4	65.4	63.3
85°	29.4	28.7	27.4	27.4	27.4	28.7	29.4	29.4	31.5	30.1	30.1
87.5°	7.4	6.9	7.0	6.4	7.0	6.9	7.4	7.4	7.3	8.4	8.3
90°	9.8	10.0	10.2	10.3	10.2	10.0	9.8	9.6	9.3	8.9	8.5
92.5°	10.0	10.1	10.2	10.3	10.2	10.1	10.0	9.9	9.7	9.5	9.3
95°	16.7	16.6	16.5	16.4	16.5	16.6	16.7	16.8	16.6	16.1	15.7
97.5°	21.6	21.7	21.8	21.8	21.8	21.7	21.6	21.5	21.2	21.0	20.6
100°	25.1	25.2	25.3	25.5	25.3	25.2	25.1	24.9	24.4	23.7	23.1
102.5°	26.7	26.9	27.1	27.4	27.1	26.9	26.7	26.4	25.9	25.0	24.1
105°	27.9	28.3	28.6	29.0	28.6	28.3	27.9	27.6	27.0	26.0	25.1
107.5°	28.8	29.2	29.4	29.8	29.4	29.2	28.8	28.4	28.7	29.7	30.7
110°	29.1	29.4	29.8	30.1	29.8	29.4	29.1	28.7	32.8	41.3	49.8



TEST NUMBER: P331585-940

CATALOG NUMBER: S122DIW-S1005D435U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	29.6	29.9	30.1	30.4	30.1	29.9	29.6	29.3	44.7	75.5	106.5
115°	49.6	43.4	37.4	31.2	37.4	43.4	49.6	55.6	78.3	117.5	156.8
117.5°	187.7	167.6	147.7	127.6	147.7	167.6	187.7	207.8	222.5	232.0	241.5
120°	266.8	255.4	243.9	232.5	243.9	255.4	266.8	278.2	283.5	282.4	281.4
122.5°	296.8	294.5	292.3	290.1	292.3	294.5	296.8	299.0	299.8	299.2	298.5
125°	325.1	325.4	325.7	325.8	325.7	325.4	325.1	324.9	324.4	323.9	323.2
127.5°	348.3	348.3	348.4	348.4	348.4	348.3	348.3	348.2	347.8	346.9	346.1
130°	362.7	362.7	362.6	362.5	362.6	362.7	362.7	362.8	362.4	361.4	360.5
132.5°	376.4	376.3	376.3	376.2	376.3	376.3	376.4	376.5	376.1	375.3	374.6
135°	396.5	396.4	396.2	396.0	396.2	396.4	396.5	396.6	396.4	395.5	394.7
137.5°	414.9	414.6	414.4	414.0	414.4	414.6	414.9	415.2	414.9	414.1	413.3
140°	426.6	426.1	425.8	425.3	425.8	426.1	426.6	427.0	426.9	426.1	425.3
142.5°	437.6	437.2	436.8	436.3	436.8	437.2	437.6	438.0	437.9	437.2	436.5
145°	452.9	452.5	452.1	451.7	452.1	452.5	452.9	453.3	453.3	452.6	452.1
147.5°	466.2	465.8	465.5	465.1	465.5	465.8	466.2	466.5	466.5	466.1	465.7
150°	474.7	474.2	473.8	473.4	473.8	474.2	474.7	475.1	475.0	474.5	474.0
152.5°	482.1	481.5	480.9	480.4	480.9	481.5	482.1	482.6	482.7	482.1	481.6
155°	492.1	491.5	490.8	490.2	490.8	491.5	492.1	492.8	492.9	492.4	492.0
157.5°	501.1	500.3	499.7	499.1	499.7	500.3	501.1	501.7	501.8	501.1	500.6
160°	506.0	505.4	504.8	504.3	504.8	505.4	506.0	506.6	506.7	506.1	505.6
162.5°	510.7	510.0	509.3	508.5	509.3	510.0	510.7	511.4	511.5	511.0	510.3
165°	516.7	516.1	515.5	514.9	515.5	516.1	516.7	517.3	517.3	516.7	516.1
167.5°	521.2	520.5	519.7	519.0	519.7	520.5	521.2	522.0	522.1	521.5	520.9
170°	523.7	522.9	522.2	521.4	522.2	522.9	523.7	524.4	524.5	524.0	523.3
172.5°	525.5	524.8	524.0	523.3	524.0	524.8	525.5	526.3	526.4	525.8	525.1
175°	527.4	526.6	525.7	524.9	525.7	526.6	527.4	528.2	528.3	527.7	527.2
177.5°	527.6	527.0	526.4	525.8	526.4	527.0	527.6	528.2	528.3	527.8	527.4
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331585-940

CATALOG NUMBER: S122DIW-S1005D435U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1708.7	1714.7	1724.0	1733.8	1739.8	1751.3	1754.6	1760.1	1765.0	1776.5	1788.5
5°	1610.0	1619.6	1642.1	1654.4	1671.5	1691.3	1704.3	1718.0	1733.0	1759.0	1782.9
7.5°	1504.2	1520.2	1548.2	1571.2	1595.5	1624.0	1644.4	1671.5	1693.9	1730.5	1765.5
10°	1433.7	1456.3	1481.6	1508.9	1543.0	1573.1	1601.8	1635.9	1663.3	1707.0	1748.0
12.5°	1370.3	1373.7	1409.9	1440.0	1486.7	1523.9	1557.0	1601.0	1627.7	1679.7	1722.9
15°	1259.5	1280.0	1312.8	1336.7	1392.0	1439.1	1485.6	1531.4	1562.2	1626.4	1683.1
17.5°	1166.1	1185.0	1218.6	1257.8	1297.5	1344.4	1404.6	1452.9	1494.7	1568.1	1635.1
20°	1107.1	1130.2	1164.5	1204.8	1239.7	1290.8	1342.8	1398.2	1443.2	1526.0	1604.5
22.5°	1056.8	1075.0	1102.7	1142.5	1180.5	1227.4	1284.3	1344.6	1391.9	1481.1	1560.8
25°	986.1	1001.1	1018.9	1051.7	1094.8	1146.0	1190.4	1256.7	1325.7	1409.1	1505.5
27.5°	922.4	933.1	948.8	977.6	1010.9	1058.9	1108.3	1171.2	1240.5	1331.1	1432.7
30°	883.6	890.5	906.2	930.1	962.9	1000.4	1050.3	1110.4	1181.5	1273.1	1374.2
32.5°	849.7	856.0	866.2	889.0	917.5	949.6	994.5	1054.7	1122.5	1212.5	1324.5
35°	798.9	803.6	812.5	831.0	846.7	878.2	915.7	970.4	1033.9	1120.1	1236.2
37.5°	748.1	754.7	760.2	767.9	788.2	808.9	841.5	887.7	950.0	1037.0	1147.6
40°	714.8	720.2	728.4	731.9	748.3	766.7	793.4	835.7	898.7	977.9	1085.8
42.5°	680.9	686.3	691.3	695.3	709.4	725.8	749.7	786.0	841.8	918.8	1025.7
45°	634.8	635.5	640.3	647.8	654.7	666.3	683.4	714.8	757.9	830.3	927.3
47.5°	588.1	588.9	589.8	593.0	600.6	611.1	622.4	648.0	686.5	744.3	838.7
50°	557.0	555.5	557.0	559.6	564.5	573.4	586.3	604.8	636.2	690.2	776.9
52.5°	526.9	526.6	525.8	526.9	530.6	536.7	545.9	561.6	589.8	639.4	715.8
55°	481.1	477.7	478.3	475.6	481.8	483.1	490.0	502.9	527.5	561.7	633.5
57.5°	432.3	429.4	426.4	425.6	425.1	428.7	434.2	444.4	463.3	493.3	551.4
60°	401.1	397.7	393.6	392.3	392.3	394.3	397.1	404.6	422.3	449.0	496.8
62.5°	369.4	365.4	363.0	359.4	358.4	360.4	363.1	368.5	381.3	406.4	447.6
65°	320.5	315.8	312.3	311.7	310.2	308.2	309.6	315.0	325.3	345.1	377.9
67.5°	271.4	266.9	266.1	262.2	260.2	260.5	260.2	264.8	271.0	288.1	312.5
70°	239.2	235.8	234.4	231.0	229.6	228.3	226.9	231.0	237.1	251.5	272.7
72.5°	206.3	203.5	200.5	197.6	197.9	196.5	196.3	198.8	203.8	217.0	233.3
75°	159.3	159.9	156.5	153.1	152.4	151.1	151.1	153.1	155.2	165.4	178.3
77.5°	115.5	114.9	112.1	111.0	110.3	108.8	110.3	111.6	112.7	119.6	129.1
80°	88.2	88.2	84.7	84.7	84.1	82.0	84.1	82.7	85.4	92.3	99.1
82.5°	63.0	61.9	61.8	60.7	60.5	59.0	60.0	61.3	62.4	67.1	71.2
85°	30.8	30.8	30.1	29.4	30.1	29.4	30.1	30.8	31.5	33.5	36.9
87.5°	8.2	8.6	9.0	9.5	9.3	9.7	10.1	10.4	11.4	11.8	12.1
90°	8.0	7.6	7.0	6.2	5.6	4.9	4.1	3.2	2.2	1.3	0.4
92.5°	9.1	8.8	8.5	8.2	7.8	7.5	7.4	7.4	7.5	7.6	7.7
95°	15.2	14.9	14.3	13.6	13.1	12.5	13.6	16.4	19.2	21.9	24.8
97.5°	20.2	19.9	18.5	17.1	15.8	14.4	17.7	25.5	33.4	41.3	49.1
100°	22.4	21.8	20.2	18.8	17.4	16.0	21.0	32.6	44.2	55.8	67.5
102.5°	23.2	22.3	34.4	46.5	58.5	70.5	77.8	80.3	82.7	85.2	87.6
105°	24.2	23.3	46.4	69.5	92.6	115.7	126.0	123.5	120.9	118.4	115.8
107.5°	31.6	32.5	60.3	88.0	115.7	143.5	156.3	154.3	152.2	150.2	148.1
110°	58.2	66.7	91.1	115.7	140.1	164.6	175.9	174.2	172.4	170.6	168.8



TEST NUMBER: P331585-940

CATALOG NUMBER: S122DIW-S1005D435U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	137.3	168.3	174.2	180.3	186.4	192.4	194.7	193.1	191.5	189.9	188.3
115°	195.9	235.1	233.0	231.0	228.8	226.7	224.9	223.5	222.0	220.6	219.2
117.5°	251.0	260.5	259.0	257.5	256.1	254.7	253.1	251.5	249.9	248.3	246.6
120°	280.4	279.4	277.9	276.3	274.8	273.3	271.9	270.6	269.3	268.0	266.8
122.5°	298.0	297.4	295.7	294.0	292.4	290.7	289.2	287.8	286.5	285.2	283.8
125°	322.6	322.1	320.5	318.9	317.3	315.6	314.2	313.2	312.1	310.9	309.9
127.5°	345.2	344.3	343.1	341.9	340.7	339.5	338.3	337.1	335.8	334.7	333.4
130°	359.5	358.6	357.8	356.8	355.9	354.9	353.7	352.4	351.1	349.7	348.4
132.5°	373.8	373.0	372.0	371.1	370.1	369.3	368.2	367.0	365.9	364.7	363.6
135°	393.8	393.0	392.2	391.5	390.7	389.9	388.9	387.4	386.1	384.8	383.4
137.5°	412.4	411.6	410.7	409.9	409.0	408.1	407.2	406.4	405.4	404.4	403.5
140°	424.5	423.8	422.8	422.0	421.1	420.1	419.3	418.6	417.9	417.2	416.6
142.5°	435.8	435.1	434.0	432.9	431.9	430.9	430.0	429.4	428.7	428.2	427.6
145°	451.5	450.8	449.4	448.0	446.6	445.1	444.4	444.5	444.6	444.7	444.8
147.5°	465.2	464.8	463.3	461.9	460.5	459.1	458.5	458.9	459.1	459.5	459.8
150°	473.5	473.0	471.6	470.3	469.0	467.5	467.2	467.8	468.3	469.0	469.6
152.5°	481.1	480.6	479.3	478.0	476.7	475.5	475.1	475.8	476.4	477.2	477.8
155°	491.4	490.9	489.9	488.8	487.9	486.9	486.7	487.5	488.2	489.0	489.7
157.5°	500.0	499.4	498.7	498.0	497.3	496.6	496.6	497.2	497.8	498.5	499.1
160°	505.2	504.6	504.1	503.6	503.1	502.6	502.6	503.1	503.6	504.1	504.6
162.5°	509.8	509.2	508.7	508.3	507.8	507.5	507.5	508.0	508.5	509.0	509.5
165°	515.5	514.9	514.7	514.4	514.2	513.9	514.0	514.5	515.1	515.6	516.0
167.5°	520.3	519.7	519.5	519.2	519.0	518.8	518.9	519.4	520.0	520.4	520.9
170°	522.7	522.2	522.0	521.8	521.7	521.5	521.7	522.2	522.6	523.2	523.7
172.5°	524.6	524.0	523.8	523.6	523.4	523.3	523.4	524.0	524.5	525.0	525.5
175°	526.6	525.9	525.8	525.7	525.5	525.3	525.5	526.1	526.6	527.3	527.9
177.5°	526.9	526.4	526.4	526.3	526.2	526.1	526.4	526.8	527.3	527.8	528.2
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331585-940

CATALOG NUMBER: S122DIW-S1005D435U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1787.4	1790.1	1798.8	1807.7	1817.5	1820.2	1824.6	1820.8	1819.6	1830.1	1837.7
5°	1792.4	1804.7	1828.7	1850.6	1869.0	1882.0	1895.7	1901.1	1911.4	1925.7	1943.5
7.5°	1786.7	1810.6	1848.2	1880.1	1914.8	1939.8	1959.4	1976.0	1996.3	2023.5	2053.1
10°	1780.1	1812.3	1858.1	1897.0	1939.4	1971.5	1998.1	2024.1	2054.2	2091.8	2130.7
12.5°	1768.2	1806.2	1863.5	1909.6	1964.0	1995.6	2031.5	2087.6	2119.8	2172.1	2227.0
15°	1743.9	1786.3	1866.3	1923.0	1984.5	2044.6	2110.9	2164.2	2217.5	2248.3	2325.5
17.5°	1708.0	1770.2	1858.8	1924.9	2003.0	2097.7	2172.3	2232.7	2294.2	2344.0	2382.7
20°	1679.0	1746.7	1847.8	1927.1	2020.0	2121.8	2207.3	2268.8	2322.1	2363.7	2387.6
22.5°	1642.4	1727.5	1826.0	1918.9	2037.6	2138.2	2228.0	2276.4	2320.9	2341.4	2350.5
25°	1584.7	1687.2	1798.6	1912.1	2046.0	2152.6	2234.6	2264.0	2277.0	2257.2	2224.4
27.5°	1522.5	1636.8	1767.0	1899.2	2040.8	2143.3	2202.1	2197.4	2175.4	2111.3	2060.0
30°	1476.0	1601.8	1741.9	1886.1	2028.2	2128.0	2162.1	2128.0	2078.1	2006.3	1933.2
32.5°	1427.5	1557.6	1715.1	1867.5	2005.3	2093.0	2100.4	2041.7	1964.4	1882.8	1791.6
35°	1353.7	1494.5	1664.6	1826.0	1956.5	2011.8	1979.1	1875.2	1783.6	1672.2	1547.8
37.5°	1270.5	1425.9	1596.6	1765.1	1883.4	1897.8	1816.4	1707.0	1577.9	1447.0	1300.6
40°	1208.2	1372.9	1548.5	1718.7	1823.2	1808.2	1704.3	1584.0	1430.3	1270.3	1134.3
42.5°	1152.4	1317.1	1496.0	1662.9	1746.7	1705.4	1584.0	1436.5	1271.2	1120.6	996.0
45°	1055.8	1225.3	1408.5	1569.7	1617.6	1543.0	1382.4	1218.4	1055.8	930.1	831.7
47.5°	962.1	1129.6	1311.0	1452.7	1469.6	1369.5	1194.0	1025.2	885.4	783.0	713.5
50°	893.1	1061.2	1241.0	1367.4	1361.9	1241.0	1060.6	900.0	783.1	700.4	654.0
52.5°	831.3	990.2	1162.8	1277.7	1248.8	1116.9	944.7	802.1	706.1	641.4	599.3
55°	735.3	882.3	1046.2	1138.4	1085.2	939.0	793.4	678.6	607.5	559.0	526.2
57.5°	639.9	777.7	918.0	974.9	916.0	781.0	659.6	576.3	522.9	487.0	465.7
60°	580.9	701.2	826.2	875.4	805.0	684.7	589.1	514.6	471.5	442.1	423.0
62.5°	521.8	629.5	747.4	774.3	709.9	608.2	523.4	461.5	426.1	400.0	382.0
65°	441.5	529.6	619.1	636.9	577.5	498.8	431.9	391.6	360.2	341.0	326.6
67.5°	362.0	432.8	496.2	510.6	458.5	404.0	355.6	320.5	299.2	283.3	271.2
70°	315.0	371.0	423.0	434.6	393.0	344.4	307.6	279.5	260.4	246.7	235.1
72.5°	265.3	312.0	355.2	363.0	329.0	291.9	261.6	239.6	222.7	213.9	202.9
75°	203.0	230.3	263.8	265.8	243.3	220.7	197.5	183.2	174.2	163.4	157.8
77.5°	143.2	164.7	183.8	187.5	174.2	158.8	145.8	134.5	127.0	121.9	116.8
80°	109.3	126.4	134.6	139.4	129.8	118.9	111.4	103.9	99.1	95.7	92.3
82.5°	78.2	88.7	96.4	100.0	94.9	88.3	80.8	76.5	72.9	70.0	68.8
85°	39.6	44.4	49.2	50.6	49.2	46.5	42.4	42.4	40.3	39.6	39.6
87.5°	13.9	16.3	16.5	18.3	17.4	17.5	17.7	17.2	16.9	16.4	15.9
90°	1.3	2.2	3.2	4.1	4.9	5.6	6.2	7.0	7.6	8.0	8.5
92.5°	7.6	7.5	7.4	7.4	7.5	7.8	8.2	8.5	8.8	9.1	9.3
95°	21.9	19.2	16.4	13.6	12.5	13.1	13.6	14.3	14.9	15.2	15.7
97.5°	41.3	33.4	25.5	17.7	14.4	15.8	17.1	18.5	19.9	20.2	20.6
100°	55.8	44.2	32.6	21.0	16.0	17.4	18.8	20.2	21.8	22.4	23.1
102.5°	85.2	82.7	80.3	77.8	70.5	58.5	46.5	34.4	22.3	23.2	24.1
105°	118.4	120.9	123.5	126.0	115.7	92.6	69.5	46.4	23.3	24.2	25.1
107.5°	150.2	152.2	154.3	156.3	143.5	115.7	88.0	60.3	32.5	31.6	30.7
110°	170.6	172.4	174.2	175.9	164.6	140.1	115.7	91.1	66.7	58.2	49.8





TEST NUMBER: P331585-940

CATALOG NUMBER: S122DIW-S1005D435U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	189.9	191.5	193.1	194.7	192.4	186.4	180.3	174.2	168.3	137.3	106.5
115°	220.6	222.0	223.5	224.9	226.7	228.8	231.0	233.0	235.1	195.9	156.8
117.5°	248.3	249.9	251.5	253.1	254.7	256.1	257.5	259.0	260.5	251.0	241.5
120°	268.0	269.3	270.6	271.9	273.3	274.8	276.3	277.9	279.4	280.4	281.4
122.5°	285.2	286.5	287.8	289.2	290.7	292.4	294.0	295.7	297.4	298.0	298.5
125°	310.9	312.1	313.2	314.2	315.6	317.3	318.9	320.5	322.1	322.6	323.2
127.5°	334.7	335.8	337.1	338.3	339.5	340.7	341.9	343.1	344.3	345.2	346.1
130°	349.7	351.1	352.4	353.7	354.9	355.9	356.8	357.8	358.6	359.5	360.5
132.5°	364.7	365.9	367.0	368.2	369.3	370.1	371.1	372.0	373.0	373.8	374.6
135°	384.8	386.1	387.4	388.9	389.9	390.7	391.5	392.2	393.0	393.8	394.7
137.5°	404.4	405.4	406.4	407.2	408.1	409.0	409.9	410.7	411.6	412.4	413.3
140°	417.2	417.9	418.6	419.3	420.1	421.1	422.0	422.8	423.8	424.5	425.3
142.5°	428.2	428.7	429.4	430.0	430.9	431.9	432.9	434.0	435.1	435.8	436.5
145°	444.7	444.6	444.5	444.4	445.1	446.6	448.0	449.4	450.8	451.5	452.1
147.5°	459.5	459.1	458.9	458.5	459.1	460.5	461.9	463.3	464.8	465.2	465.7
150°	469.0	468.3	467.8	467.2	467.5	469.0	470.3	471.6	473.0	473.5	474.0
152.5°	477.2	476.4	475.8	475.1	475.5	476.7	478.0	479.3	480.6	481.1	481.6
155°	489.0	488.2	487.5	486.7	486.9	487.9	488.8	489.9	490.9	491.4	492.0
157.5°	498.5	497.8	497.2	496.6	496.6	497.3	498.0	498.7	499.4	500.0	500.6
160°	504.1	503.6	503.1	502.6	502.6	503.1	503.6	504.1	504.6	505.2	505.6
162.5°	509.0	508.5	508.0	507.5	507.5	507.8	508.3	508.7	509.2	509.8	510.3
165°	515.6	515.1	514.5	514.0	513.9	514.2	514.4	514.7	514.9	515.5	516.1
167.5°	520.4	520.0	519.4	518.9	518.8	519.0	519.2	519.5	519.7	520.3	520.9
170°	523.2	522.6	522.2	521.7	521.5	521.7	521.8	522.0	522.2	522.7	523.3
172.5°	525.0	524.5	524.0	523.4	523.3	523.4	523.6	523.8	524.0	524.6	525.1
175°	527.3	526.6	526.1	525.5	525.3	525.5	525.7	525.8	525.9	526.6	527.2
177.5°	527.8	527.3	526.8	526.4	526.1	526.2	526.3	526.4	526.4	526.9	527.4
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331585-940

CATALOG NUMBER: S122DIW-S1005D435U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1844.2	1851.9	1851.9	1853.0	1861.7	1860.6	1860.1
5°	1962.7	1974.2	1975.6	1987.9	1996.1	1993.3	1985.8
7.5°	2074.3	2095.9	2112.3	2121.5	2132.3	2138.9	2135.9
10°	2162.8	2194.3	2213.4	2226.4	2242.1	2253.7	2249.6
12.5°	2243.2	2280.6	2306.9	2329.1	2331.2	2346.1	2336.0
15°	2368.6	2408.2	2412.3	2428.7	2441.7	2440.3	2441.0
17.5°	2409.9	2422.7	2425.3	2425.6	2425.8	2421.0	2410.7
20°	2395.2	2390.4	2378.8	2369.9	2354.2	2352.2	2338.5
22.5°	2325.2	2310.1	2280.9	2261.6	2237.2	2230.8	2227.0
25°	2187.5	2153.9	2107.5	2063.1	2050.8	2026.9	2033.7
27.5°	1998.4	1946.2	1896.0	1859.8	1827.2	1791.4	1801.6
30°	1865.5	1806.8	1735.7	1681.1	1646.2	1612.0	1605.9
32.5°	1707.0	1621.0	1541.7	1493.5	1440.1	1418.5	1394.9
35°	1433.7	1349.6	1271.0	1203.4	1164.5	1134.3	1107.1
37.5°	1187.8	1091.1	1027.6	972.9	944.7	927.5	931.8
40°	1035.3	950.6	904.1	862.4	836.4	824.1	826.9
42.5°	911.8	848.3	810.0	781.5	763.2	756.3	754.7
45°	771.5	736.0	704.5	688.1	679.3	671.7	667.0
47.5°	675.8	646.8	629.1	619.4	611.6	604.0	603.8
50°	618.4	599.3	587.0	576.8	570.6	565.2	569.9
52.5°	574.7	557.2	544.9	535.7	533.4	528.5	528.3
55°	509.8	496.1	487.2	479.0	474.9	472.2	468.8
57.5°	450.8	437.7	429.5	424.4	416.6	413.8	412.8
60°	408.7	398.4	390.2	383.3	380.0	374.5	374.5
62.5°	369.8	359.6	352.0	346.7	341.2	338.9	339.5
65°	313.7	305.5	297.9	292.5	291.1	287.0	288.4
67.5°	262.0	256.5	248.6	245.6	243.0	240.9	239.2
70°	227.6	222.1	218.0	213.9	211.9	211.9	211.9
72.5°	198.6	192.0	189.6	184.4	185.6	183.4	181.2
75°	153.7	149.6	147.6	145.5	142.1	142.1	142.1
77.5°	113.2	111.9	109.5	107.3	106.5	105.8	106.0
80°	87.5	86.8	85.4	85.4	84.1	83.4	82.0
82.5°	67.2	65.5	64.6	64.1	63.8	63.7	63.4
85°	38.3	36.9	36.9	37.5	36.2	36.2	36.9
87.5°	16.5	16.6	16.1	16.1	16.8	16.2	16.2
90°	8.9	9.3	9.6	9.8	10.0	10.2	10.3
92.5°	9.5	9.7	9.9	10.0	10.1	10.2	10.3
95°	16.1	16.6	16.8	16.7	16.6	16.5	16.4
97.5°	21.0	21.2	21.5	21.6	21.7	21.8	21.8
100°	23.7	24.4	24.9	25.1	25.2	25.3	25.5
102.5°	25.0	25.9	26.4	26.7	26.9	27.1	27.4
105°	26.0	27.0	27.6	27.9	28.3	28.6	29.0
107.5°	29.7	28.7	28.4	28.8	29.2	29.4	29.8
110°	41.3	32.8	28.7	29.1	29.4	29.8	30.1



TEST NUMBER: P331585-940

CATALOG NUMBER: S122DIW-S1005D435U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	75.5	44.7	29.3	29.6	29.9	30.1	30.4
115°	117.5	78.3	55.6	49.6	43.4	37.4	31.2
117.5°	232.0	222.5	207.8	187.7	167.6	147.7	127.6
120°	282.4	283.5	278.2	266.8	255.4	243.9	232.5
122.5°	299.2	299.8	299.0	296.8	294.5	292.3	290.1
125°	323.9	324.4	324.9	325.1	325.4	325.7	325.8
127.5°	346.9	347.8	348.2	348.3	348.3	348.4	348.4
130°	361.4	362.4	362.8	362.7	362.7	362.6	362.5
132.5°	375.3	376.1	376.5	376.4	376.3	376.3	376.2
135°	395.5	396.4	396.6	396.5	396.4	396.2	396.0
137.5°	414.1	414.9	415.2	414.9	414.6	414.4	414.0
140°	426.1	426.9	427.0	426.6	426.1	425.8	425.3
142.5°	437.2	437.9	438.0	437.6	437.2	436.8	436.3
145°	452.6	453.3	453.3	452.9	452.5	452.1	451.7
147.5°	466.1	466.5	466.5	466.2	465.8	465.5	465.1
150°	474.5	475.0	475.1	474.7	474.2	473.8	473.4
152.5°	482.1	482.7	482.6	482.1	481.5	480.9	480.4
155°	492.4	492.9	492.8	492.1	491.5	490.8	490.2
157.5°	501.1	501.8	501.7	501.1	500.3	499.7	499.1
160°	506.1	506.7	506.6	506.0	505.4	504.8	504.3
162.5°	511.0	511.5	511.4	510.7	510.0	509.3	508.5
165°	516.7	517.3	517.3	516.7	516.1	515.5	514.9
167.5°	521.5	522.1	522.0	521.2	520.5	519.7	519.0
170°	524.0	524.5	524.4	523.7	522.9	522.2	521.4
172.5°	525.8	526.4	526.3	525.5	524.8	524.0	523.3
175°	527.7	528.3	528.2	527.4	526.6	525.7	524.9
177.5°	527.8	528.3	528.2	527.6	527.0	526.4	525.8
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7

(END OF REPORT)