

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331815

Luminaire Tested: **S122RDIW-S675D970U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331815
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D970U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6193.2 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331815

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331815

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	38	38	38	32	32	32	28		
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32	32	32	28	28	28	24		
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33	28	28	28	24	24	24	21		
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	24	24	24	21	21	21	18		
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21	21	21	18	18	18	16		
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	18	18	18	16	16	16	15		
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16	16	16	15	15	15	13		
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15	15	15	13	13	13	12		
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	16	13	13	13	12	12	12	11		
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14	12	12	12	11	11	11	11		
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11	11	11	10	10	10	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18213	18213	18213
5°	18282	17985	18084
10°	18143	17690	17539
15°	17934	17167	16672
20°	17646	16417	15593
25°	17350	15567	14549
30°	16940	14693	13209
35°	16539	13742	12033
40°	16136	12760	10671
45°	15664	11654	9439
50°	15179	10540	8231
55°	14686	9340	7068
60°	14108	8076	5867
65°	13456	6785	5345
70°	12675	5589	4914
75°	11715	5097	4585
80°	10349	4556	4175
85°	8133	3594	3594



TEST NUMBER: P331815

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.6	1.7
10°-20°	289.9	4.7
20°-30°	407.1	6.6
30°-40°	443.9	7.2
40°-50°	408.2	6.6
50°-60°	320.6	5.2
60°-70°	209.0	3.4
70°-80°	107.8	1.7
80°-90°	31.2	0.5
90°-100°	44.1	0.7
100°-110°	161.5	2.6
110°-120°	431.8	7.0
120°-130°	712.8	11.5
130°-140°	758.0	12.2
140°-150°	704.6	11.4
150°-160°	566.5	9.1
160°-170°	365.0	5.9
170°-180°	125.6	2.0
0°-30°	802.6	13.0
0°-40°	1246.6	20.1
0°-60°	1975.3	31.9
0°-90°	2323.3	37.5
90°-120°	637.4	10.3
90°-150°	2812.8	45.4
90°-180°	3870.0	62.5
0°-180°	6193.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1128	1128	1128	1128	1128	
5°	1128	1122	1110	1118	1116	107
15°	1073	1060	1027	1008	997	302
25°	974	939	874	833	817	448
35°	839	785	697	635	610	525
45°	686	615	510	441	413	529
55°	522	440	332	273	251	466
65°	352	269	178	145	140	349
75°	188	118	82	75	74	199
85°	44	23	19	19	19	52
90°	1	11	19	24	26	5
95°	62	33	37	42	41	76
105°	290	303	58	68	73	310
115°	549	566	590	168	78	541
125°	777	790	807	814	817	692
135°	961	976	985	994	993	742
145°	1115	1115	1130	1136	1132	697
155°	1228	1220	1231	1236	1229	566
165°	1294	1289	1291	1297	1291	365
175°	1323	1317	1319	1324	1316	126
180°	1320	1320	1320	1320	1320	



TEST NUMBER: P331815

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0
2.5°	1132.1	1131.2	1130.3	1129.4	1128.5	1127.0	1125.0	1123.0	1121.1	1119.1	1120.9
5°	1128.0	1126.9	1125.8	1124.6	1123.5	1121.5	1118.5	1115.6	1112.6	1109.7	1111.7
7.5°	1116.4	1115.0	1113.6	1112.2	1110.8	1108.3	1104.9	1101.5	1098.0	1094.6	1095.1
10°	1106.6	1105.0	1103.4	1101.8	1100.2	1097.2	1092.6	1088.1	1083.6	1079.0	1078.4
12.5°	1094.3	1092.4	1090.4	1088.5	1086.5	1082.7	1076.9	1071.1	1065.2	1059.4	1058.2
15°	1072.9	1070.4	1067.9	1065.4	1062.9	1057.8	1050.1	1042.4	1034.7	1027.0	1022.7
17.5°	1046.6	1042.8	1039.0	1035.1	1031.3	1024.5	1014.6	1004.7	994.8	984.9	979.8
20°	1027.0	1022.4	1017.9	1013.4	1008.8	1000.9	989.5	978.2	966.9	955.5	949.8
22.5°	1005.7	1000.7	995.6	990.5	985.4	976.5	963.7	950.9	938.1	925.3	918.0
25°	973.9	966.6	959.4	952.1	944.9	933.7	918.8	903.8	888.8	873.8	864.5
27.5°	935.5	927.6	919.7	911.8	903.9	891.5	874.7	857.8	840.9	824.0	813.2
30°	908.6	899.9	891.3	882.7	874.1	860.7	842.5	824.4	806.2	788.1	776.5
32.5°	882.4	872.3	862.3	852.2	842.1	827.8	809.3	790.8	772.3	753.8	740.6
35°	839.1	827.6	816.0	804.4	792.9	777.1	757.1	737.2	717.2	697.2	682.9
37.5°	795.9	783.1	770.4	757.7	745.0	728.0	706.8	685.5	664.2	642.9	627.2
40°	765.6	752.0	738.4	724.8	711.2	693.4	671.4	649.4	627.4	605.4	589.3
42.5°	734.6	720.3	705.9	691.6	677.3	658.7	636.0	613.3	590.5	567.8	551.1
45°	686.0	670.8	655.6	640.4	625.2	605.7	581.9	558.1	534.2	510.4	494.3
47.5°	638.6	622.5	606.4	590.3	574.2	553.9	529.3	504.7	480.1	455.5	439.5
50°	604.3	588.2	572.1	556.0	539.9	519.4	494.4	469.5	444.5	419.6	403.9
52.5°	570.9	554.0	537.2	520.4	503.5	482.9	458.5	434.1	409.7	385.3	370.2
55°	521.7	504.0	486.3	468.6	450.9	429.8	405.3	380.8	356.3	331.8	318.2
57.5°	471.2	453.1	434.9	416.8	398.6	377.8	354.2	330.7	307.1	283.6	271.1
60°	436.9	418.8	400.6	382.5	364.3	343.6	320.2	296.8	273.5	250.1	238.5
62.5°	403.4	385.3	367.1	349.0	330.8	310.6	288.4	266.1	243.8	221.5	210.5
65°	352.2	333.8	315.4	297.1	278.7	259.3	238.9	218.5	198.0	177.6	169.9
67.5°	302.8	284.5	266.3	248.1	229.8	211.5	193.1	174.8	156.4	138.0	134.5
70°	268.5	250.8	233.1	215.4	197.7	181.0	165.4	149.7	134.1	118.4	116.1
72.5°	235.8	218.8	201.9	184.9	167.9	153.2	140.6	128.0	115.5	102.9	101.0
75°	187.8	172.0	156.1	140.2	124.3	112.5	104.8	97.1	89.4	81.7	80.1
77.5°	140.7	126.7	112.8	98.9	85.0	76.1	72.4	68.7	65.0	61.3	60.3
80°	111.3	99.7	88.1	76.6	65.0	58.1	55.8	53.5	51.3	49.0	48.1
82.5°	84.3	75.3	66.3	57.2	48.2	42.9	41.4	39.8	38.3	36.8	36.2
85°	43.9	39.1	34.4	29.6	24.8	22.1	21.4	20.8	20.1	19.4	19.4
87.5°	13.3	12.3	11.3	10.3	9.3	9.0	9.3	9.7	10.0	10.4	10.4
90°	1.0	3.3	5.6	8.0	10.3	12.3	14.0	15.7	17.4	19.1	20.2
92.5°	19.3	19.1	18.9	18.7	18.5	18.8	19.6	20.5	21.3	22.2	22.7
95°	62.1	55.1	48.1	41.1	34.1	31.3	32.8	34.3	35.8	37.3	38.3
97.5°	123.3	103.5	83.8	64.0	44.3	36.1	39.6	43.0	46.4	49.9	50.7
100°	169.1	140.0	110.9	81.9	52.8	40.0	43.6	47.2	50.9	54.5	56.2
102.5°	219.6	213.4	207.3	201.1	194.9	176.8	146.6	116.4	86.2	56.0	58.2
105°	290.5	296.9	303.2	309.6	316.0	290.2	232.2	174.2	116.3	58.3	60.6
107.5°	371.3	376.5	381.6	386.7	391.9	359.7	290.2	220.6	151.1	81.6	79.2
110°	423.3	427.8	432.2	436.7	441.1	412.7	351.3	290.0	228.6	167.2	146.0



TEST NUMBER: P331815

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	472.2	476.2	480.1	484.1	488.0	482.4	467.3	452.1	436.9	421.8	344.3
115°	549.4	553.0	556.7	560.3	563.9	568.3	573.6	578.9	584.3	589.6	491.2
117.5°	618.4	622.5	626.5	630.5	634.6	638.4	642.1	645.7	649.4	653.0	629.2
120°	668.9	672.1	675.2	678.4	681.6	685.1	688.9	692.8	696.6	700.4	703.0
122.5°	711.7	715.0	718.4	721.7	725.1	728.9	733.0	737.2	741.3	745.5	747.0
125°	776.8	779.6	782.4	785.1	787.9	791.3	795.3	799.4	803.4	807.4	808.9
127.5°	835.9	839.0	842.0	845.1	848.1	851.2	854.2	857.2	860.2	863.2	865.4
130°	873.4	876.8	880.2	883.5	886.9	889.8	892.1	894.5	896.8	899.2	901.5
132.5°	911.6	914.5	917.4	920.2	923.1	925.7	928.1	930.4	932.7	935.1	937.1
135°	961.3	964.7	968.1	971.5	974.9	977.5	979.4	981.3	983.2	985.2	987.3
137.5°	1011.5	1013.9	1016.3	1018.7	1021.0	1023.3	1025.5	1027.6	1029.8	1032.0	1034.1
140°	1044.4	1046.1	1047.8	1049.5	1051.2	1053.2	1055.5	1057.9	1060.2	1062.6	1064.5
142.5°	1071.9	1073.4	1075.0	1076.5	1078.0	1080.1	1082.8	1085.5	1088.2	1090.8	1092.6
145°	1115.1	1114.9	1114.7	1114.5	1114.3	1116.0	1119.6	1123.2	1126.8	1130.4	1131.9
147.5°	1152.8	1151.9	1151.1	1150.3	1149.5	1150.9	1154.5	1158.0	1161.6	1165.2	1166.3
150°	1177.2	1175.7	1174.2	1172.8	1171.3	1172.2	1175.6	1179.0	1182.4	1185.8	1187.1
152.5°	1197.9	1196.2	1194.5	1192.9	1191.2	1192.0	1195.2	1198.5	1201.7	1204.9	1206.2
155°	1227.9	1225.9	1224.0	1222.1	1220.2	1220.5	1223.1	1225.6	1228.2	1230.7	1232.0
157.5°	1251.4	1249.8	1248.1	1246.5	1244.9	1245.0	1246.8	1248.6	1250.3	1252.1	1253.6
160°	1265.1	1263.9	1262.6	1261.3	1260.0	1260.0	1261.3	1262.6	1263.9	1265.1	1266.4
162.5°	1277.4	1276.1	1274.8	1273.5	1272.3	1272.2	1273.3	1274.4	1275.5	1276.6	1278.0
165°	1293.8	1292.5	1291.2	1290.0	1288.7	1288.4	1289.0	1289.6	1290.3	1290.9	1292.4
167.5°	1306.0	1304.7	1303.5	1302.2	1300.9	1300.6	1301.2	1301.8	1302.4	1303.0	1304.4
170°	1312.9	1311.6	1310.4	1309.1	1307.8	1307.4	1307.8	1308.2	1308.7	1309.1	1310.6
172.5°	1317.5	1316.2	1314.9	1313.7	1312.4	1312.0	1312.4	1312.8	1313.2	1313.7	1315.2
175°	1323.4	1321.9	1320.4	1319.0	1317.5	1316.9	1317.4	1317.8	1318.2	1318.6	1320.1
177.5°	1324.4	1323.2	1322.0	1320.8	1319.6	1319.1	1319.3	1319.4	1319.6	1319.8	1321.0
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P331815

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0
2.5°	1122.7	1124.5	1126.3	1127.0	1126.7	1126.3	1126.0	1125.6
5°	1113.7	1115.8	1117.8	1118.5	1117.8	1117.1	1116.5	1115.8
7.5°	1095.7	1096.3	1096.9	1096.6	1095.4	1094.3	1093.1	1091.9
10°	1077.7	1077.0	1076.3	1075.3	1073.9	1072.6	1071.2	1069.8
12.5°	1057.0	1055.8	1054.5	1052.8	1050.5	1048.3	1046.0	1043.7
15°	1018.4	1014.0	1009.7	1006.4	1004.2	1001.9	999.6	997.4
17.5°	974.7	969.5	964.4	959.9	956.0	952.1	948.2	944.3
20°	944.2	938.5	932.8	927.5	922.5	917.5	912.5	907.5
22.5°	910.7	903.4	896.1	890.6	886.8	883.1	879.4	875.7
25°	855.2	845.9	836.6	830.3	826.9	823.5	820.1	816.7
27.5°	802.3	791.5	780.7	772.5	767.1	761.7	756.3	750.9
30°	765.0	753.4	741.8	733.0	726.8	720.7	714.6	708.5
32.5°	727.4	714.2	701.0	691.5	685.7	680.0	674.2	668.5
35°	668.7	654.4	640.1	630.4	625.4	620.4	615.5	610.5
37.5°	611.4	595.7	580.0	569.2	563.5	557.8	552.1	546.4
40°	573.1	557.0	540.9	529.9	524.0	518.1	512.2	506.3
42.5°	534.5	517.8	501.2	490.0	484.3	478.6	472.9	467.1
45°	478.2	462.1	446.0	435.2	429.8	424.3	418.9	413.4
47.5°	423.5	407.5	391.4	381.0	376.0	371.1	366.1	361.2
50°	388.3	372.6	357.0	346.7	342.0	337.2	332.5	327.7
52.5°	355.1	339.9	324.8	315.1	310.7	306.3	301.9	297.5
55°	304.6	290.9	277.3	268.4	264.1	259.7	255.4	251.1
57.5°	258.6	246.2	233.7	225.6	222.0	218.4	214.7	211.1
60°	227.0	215.4	203.8	196.2	192.6	189.0	185.3	181.7
62.5°	199.5	188.4	177.4	170.8	168.6	166.5	164.3	162.1
65°	162.2	154.5	146.8	142.6	141.9	141.2	140.5	139.9
67.5°	130.9	127.4	123.9	121.7	121.0	120.3	119.6	118.8
70°	113.9	111.6	109.3	107.8	106.8	105.9	105.0	104.1
72.5°	99.1	97.2	95.3	94.1	93.5	93.0	92.4	91.9
75°	78.5	76.9	75.3	74.4	74.2	74.0	73.7	73.5
77.5°	59.4	58.5	57.6	57.0	56.6	56.3	55.9	55.5
80°	47.2	46.3	45.4	44.9	44.9	44.9	44.9	44.9
82.5°	35.7	35.1	34.6	34.3	34.3	34.3	34.3	34.3
85°	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4
87.5°	10.4	10.4	10.5	10.5	10.6	10.7	10.8	10.9
90°	21.2	22.3	23.4	24.1	24.5	24.9	25.4	25.8
92.5°	23.3	23.8	24.4	24.8	25.0	25.3	25.5	25.8
95°	39.4	40.5	41.5	41.9	41.7	41.5	41.3	41.1
97.5°	51.6	52.4	53.3	53.8	54.1	54.3	54.6	54.8
100°	57.9	59.6	61.3	62.3	62.7	63.2	63.6	64.0
102.5°	60.4	62.6	64.8	66.2	66.8	67.4	68.0	68.6
105°	63.0	65.3	67.6	69.2	70.1	70.9	71.8	72.6
107.5°	76.8	74.5	72.1	71.3	72.2	73.0	73.9	74.7
110°	124.7	103.5	82.3	72.1	72.9	73.8	74.6	75.5



TEST NUMBER: P331815

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	266.8	189.4	111.9	73.5	74.2	74.9	75.6	76.3
115°	392.9	294.6	196.3	139.5	124.2	108.9	93.6	78.4
117.5°	605.4	581.7	557.9	520.9	470.6	420.4	370.2	319.9
120°	705.5	708.0	710.6	697.5	668.9	640.2	611.5	582.9
122.5°	748.6	750.1	751.6	749.6	744.0	738.5	732.9	727.4
125°	810.4	811.9	813.4	814.4	815.1	815.7	816.3	817.0
127.5°	867.6	869.7	871.9	873.0	873.2	873.3	873.4	873.5
130°	903.8	906.2	908.5	909.6	909.3	909.1	908.9	908.7
132.5°	939.1	941.1	943.1	944.0	943.7	943.5	943.3	943.1
135°	989.4	991.5	993.6	994.5	994.1	993.6	993.2	992.8
137.5°	1036.1	1038.2	1040.3	1041.0	1040.3	1039.5	1038.8	1038.1
140°	1066.4	1068.3	1070.2	1070.6	1069.6	1068.5	1067.4	1066.4
142.5°	1094.3	1096.1	1097.8	1098.1	1097.1	1096.0	1095.0	1093.9
145°	1133.4	1134.9	1136.3	1136.6	1135.5	1134.4	1133.4	1132.3
147.5°	1167.4	1168.5	1169.6	1169.7	1168.8	1167.9	1167.0	1166.1
150°	1188.4	1189.6	1190.9	1191.0	1190.0	1188.9	1187.8	1186.8
152.5°	1207.5	1208.7	1210.0	1210.0	1208.6	1207.2	1205.8	1204.4
155°	1233.3	1234.5	1235.8	1235.6	1233.9	1232.2	1230.5	1228.8
157.5°	1255.0	1256.5	1257.9	1257.8	1256.1	1254.5	1252.8	1251.2
160°	1267.7	1268.9	1270.2	1270.1	1268.6	1267.1	1265.7	1264.2
162.5°	1279.5	1280.9	1282.4	1282.2	1280.3	1278.5	1276.7	1274.9
165°	1293.9	1295.4	1296.9	1296.9	1295.4	1293.9	1292.4	1290.9
167.5°	1305.9	1307.4	1308.9	1308.7	1306.8	1304.9	1303.0	1301.1
170°	1312.1	1313.5	1315.0	1314.8	1312.9	1311.0	1309.1	1307.2
172.5°	1316.6	1318.1	1319.6	1319.4	1317.5	1315.6	1313.7	1311.8
175°	1321.6	1323.1	1324.6	1324.3	1322.1	1320.0	1317.9	1315.8
177.5°	1322.2	1323.3	1324.5	1324.4	1322.8	1321.3	1319.8	1318.3
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5

(END OF REPORT)