

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331591-940

Luminaire Tested: **S122DIW-S1005D710U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331591-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D710U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6453.2 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331591-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331591-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	97	93	90	94	91	87	84	79	77	75	69	67	66	59	58	57	52
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49	45
3	85	75	68	62	79	71	65	59	62	58	54	55	51	48	47	45	42	39
4	78	67	59	53	73	63	56	51	56	50	46	49	45	41	43	40	37	34
5	72	60	52	46	67	57	50	44	50	45	40	44	40	36	39	35	33	30
6	66	54	46	41	62	51	44	39	46	40	36	40	36	32	35	32	29	26
7	61	49	41	36	57	47	40	34	42	36	32	37	32	29	33	29	26	24
8	57	45	37	32	54	43	36	31	38	32	28	34	29	26	30	26	24	21
9	53	41	34	29	50	39	32	28	35	30	26	31	27	23	28	24	21	19
10	50	38	31	26	47	36	30	25	33	27	23	29	25	21	26	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	28709	28709	28709	28709
5°	32185	28896	25606	28896
10°	36882	28658	22161	28658
15°	40802	28134	19579	28134
20°	40180	27569	17849	27569
25°	36230	26820	16751	26820
30°	29940	25620	15951	25620
35°	21821	24366	15382	24366
40°	17428	22885	15066	22885
45°	15230	21174	14636	21174
50°	14315	19515	14350	19515
55°	13196	17833	13965	17833
60°	12093	16043	13372	16043
65°	11018	14437	12791	14437
70°	10003	12873	11939	12873
75°	8865	11123	10574	11123
80°	7624	9214	8517	9214
85°	6836	6836	5076	6836



TEST NUMBER: P331591-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.3	2.6
10°-20°	492.3	7.6
20°-30°	714.5	11.1
30°-40°	754.0	11.7
40°-50°	667.6	10.3
50°-60°	532.7	8.3
60°-70°	362.1	5.6
70°-80°	185.6	2.9
80°-90°	46.9	0.7
90°-100°	28.8	0.4
100°-110°	105.5	1.6
110°-120°	282.1	4.4
120°-130°	465.6	7.2
130°-140°	495.2	7.7
140°-150°	460.3	7.1
150°-160°	370.1	5.7
160°-170°	238.5	3.7
170°-180°	82.1	1.3
0°-30°	1376.1	21.3
0°-40°	2130.1	33.0
0°-60°	3330.4	51.6
0°-90°	3925.0	60.8
90°-120°	416.4	6.5
90°-150°	1837.6	28.5
90°-180°	2528.0	39.2
0°-180°	6453.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1778	1778	1778	1778	1778	
5°	1986	1783	1580	1783	1986	198
15°	2441	1683	1171	1683	2441	674
25°	2034	1506	940	1506	2034	919
35°	1107	1236	780	1236	1107	720
45°	667	927	641	927	667	524
55°	469	634	496	634	469	420
65°	288	378	335	378	288	287
75°	142	178	170	178	142	152
85°	37	37	27	37	37	41
90°	17	1	17	1	17	9
95°	27	41	27	41	27	25
105°	47	190	47	190	47	49
115°	51	359	51	359	51	128
125°	534	508	534	508	534	462
135°	649	628	649	628	649	500
145°	740	728	740	728	740	463
155°	803	802	803	802	803	370
165°	843	845	843	845	843	238
175°	860	865	860	865	860	82
180°	863	863	863	863	863	



TEST NUMBER: P331591-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1860.1	1860.6	1861.7	1853.0	1851.9	1851.9	1844.2	1837.7	1830.1	1819.6	1820.8
5°	1985.8	1993.3	1996.1	1987.9	1975.6	1974.2	1962.7	1943.5	1925.7	1911.4	1901.1
7.5°	2135.9	2138.9	2132.3	2121.5	2112.3	2095.9	2074.3	2053.1	2023.5	1996.3	1976.0
10°	2249.6	2253.7	2242.1	2226.4	2213.4	2194.3	2162.8	2130.7	2091.8	2054.2	2024.1
12.5°	2336.0	2346.1	2331.2	2329.1	2306.9	2280.6	2243.2	2227.0	2172.1	2119.8	2087.6
15°	2441.0	2440.3	2441.7	2428.7	2412.3	2408.2	2368.6	2325.5	2248.3	2217.5	2164.2
17.5°	2410.7	2421.0	2425.8	2425.6	2425.3	2422.7	2409.9	2382.7	2344.0	2294.2	2232.7
20°	2338.5	2352.2	2354.2	2369.9	2378.8	2390.4	2395.2	2387.6	2363.7	2322.1	2268.8
22.5°	2227.0	2230.8	2237.2	2261.6	2280.9	2310.1	2325.2	2350.5	2341.4	2320.9	2276.4
25°	2033.7	2026.9	2050.8	2063.1	2107.5	2153.9	2187.5	2224.4	2257.2	2277.0	2264.0
27.5°	1801.6	1791.4	1827.2	1859.8	1896.0	1946.2	1998.4	2060.0	2111.3	2175.4	2197.4
30°	1605.9	1612.0	1646.2	1681.1	1735.7	1806.8	1865.5	1933.2	2006.3	2078.1	2128.0
32.5°	1394.9	1418.5	1440.1	1493.5	1541.7	1621.0	1707.0	1791.6	1882.8	1964.4	2041.7
35°	1107.1	1134.3	1164.5	1203.4	1271.0	1349.6	1433.7	1547.8	1672.2	1783.6	1875.2
37.5°	931.8	927.5	944.7	972.9	1027.6	1091.1	1187.8	1300.6	1447.0	1577.9	1707.0
40°	826.9	824.1	836.4	862.4	904.1	950.6	1035.3	1134.3	1270.3	1430.3	1584.0
42.5°	754.7	756.3	763.2	781.5	810.0	848.3	911.8	996.0	1120.6	1271.2	1436.5
45°	667.0	671.7	679.3	688.1	704.5	736.0	771.5	831.7	930.1	1055.8	1218.4
47.5°	603.8	604.0	611.6	619.4	629.1	646.8	675.8	713.5	783.0	885.4	1025.2
50°	569.9	565.2	570.6	576.8	587.0	599.3	618.4	654.0	700.4	783.1	900.0
52.5°	528.3	528.5	533.4	535.7	544.9	557.2	574.7	599.3	641.4	706.1	802.1
55°	468.8	472.2	474.9	479.0	487.2	496.1	509.8	526.2	559.0	607.5	678.6
57.5°	412.8	413.8	416.6	424.4	429.5	437.7	450.8	465.7	487.0	522.9	576.3
60°	374.5	374.5	380.0	383.3	390.2	398.4	408.7	423.0	442.1	471.5	514.6
62.5°	339.5	338.9	341.2	346.7	352.0	359.6	369.8	382.0	400.0	426.1	461.5
65°	288.4	287.0	291.1	292.5	297.9	305.5	313.7	326.6	341.0	360.2	391.6
67.5°	239.2	240.9	243.0	245.6	248.6	256.5	262.0	271.2	283.3	299.2	320.5
70°	211.9	211.9	211.9	213.9	218.0	222.1	227.6	235.1	246.7	260.4	279.5
72.5°	181.2	183.4	185.6	184.4	189.6	192.0	198.6	202.9	213.9	222.7	239.6
75°	142.1	142.1	142.1	145.5	147.6	149.6	153.7	157.8	163.4	174.2	183.2
77.5°	106.0	105.8	106.5	107.3	109.5	111.9	113.2	116.8	121.9	127.0	134.5
80°	82.0	83.4	84.1	85.4	85.4	86.8	87.5	92.3	95.7	99.1	103.9
82.5°	63.4	63.7	63.8	64.1	64.6	65.5	67.2	68.8	70.0	72.9	76.5
85°	36.9	36.2	36.2	37.5	36.9	36.9	38.3	39.6	39.6	40.3	42.4
87.5°	17.6	17.6	18.0	17.4	17.4	17.8	17.7	17.0	17.4	17.8	18.1
90°	16.9	16.6	16.3	16.1	15.8	15.2	14.5	13.9	13.2	12.5	11.4
92.5°	16.9	16.7	16.5	16.3	16.2	16.0	15.6	15.2	14.8	14.4	13.9
95°	26.8	27.0	27.1	27.3	27.4	27.1	26.4	25.8	25.1	24.3	23.4
97.5°	35.8	35.7	35.5	35.3	35.1	34.8	34.2	33.7	33.2	32.5	30.3
100°	41.8	41.6	41.3	41.0	40.8	40.0	38.9	37.8	36.6	35.6	33.3
102.5°	44.9	44.4	44.1	43.7	43.2	42.4	40.9	39.5	38.0	36.6	56.3
105°	47.4	46.9	46.4	45.7	45.2	44.1	42.6	41.1	39.6	38.1	76.0
107.5°	48.8	48.2	47.7	47.2	46.6	47.1	48.7	50.2	51.7	53.3	98.7
110°	49.3	48.8	48.2	47.6	47.1	53.8	67.6	81.5	95.4	109.2	149.4



TEST NUMBER: P331591-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	49.8	49.4	49.0	48.5	48.1	73.1	123.8	174.3	225.0	275.5	285.4
115°	51.2	61.2	71.2	81.1	91.1	128.2	192.4	256.7	320.9	385.1	381.7
117.5°	209.0	241.8	274.6	307.5	340.3	364.4	380.0	395.6	411.1	426.6	424.2
120°	380.8	399.5	418.2	436.9	455.7	464.2	462.5	460.9	459.2	457.5	455.0
122.5°	475.2	478.8	482.4	486.1	489.7	491.1	490.0	489.0	488.0	487.1	484.3
125°	533.7	533.3	532.9	532.4	532.1	531.4	530.4	529.4	528.4	527.4	524.9
127.5°	570.7	570.6	570.5	570.4	570.3	569.6	568.2	566.8	565.3	563.9	562.0
130°	593.7	593.8	594.0	594.1	594.2	593.5	592.0	590.5	589.0	587.5	585.9
132.5°	616.2	616.3	616.4	616.5	616.7	616.1	614.8	613.5	612.2	610.9	609.4
135°	648.6	648.9	649.2	649.4	649.7	649.2	647.7	646.4	645.0	643.6	642.4
137.5°	678.1	678.7	679.1	679.6	680.1	679.7	678.2	676.9	675.6	674.2	672.8
140°	696.7	697.3	698.0	698.7	699.5	699.2	697.9	696.7	695.4	694.2	692.6
142.5°	714.6	715.3	716.0	716.8	717.4	717.2	716.0	714.9	713.8	712.7	710.9
145°	739.8	740.4	741.1	741.8	742.5	742.3	741.4	740.4	739.5	738.5	736.1
147.5°	761.8	762.4	763.0	763.6	764.2	764.1	763.4	762.7	762.0	761.2	758.8
150°	775.3	776.0	776.7	777.4	778.1	778.0	777.2	776.3	775.5	774.7	772.5
152.5°	786.8	787.7	788.6	789.5	790.5	790.5	789.7	788.8	788.0	787.2	785.1
155°	802.8	803.9	805.0	806.1	807.2	807.4	806.6	805.7	804.9	804.1	802.4
157.5°	817.3	818.5	819.6	820.6	821.7	821.8	820.8	819.9	818.9	818.0	816.8
160°	825.9	826.9	827.8	828.8	829.7	829.8	829.0	828.1	827.3	826.5	825.6
162.5°	832.9	834.0	835.3	836.4	837.7	837.8	836.8	835.9	834.9	834.0	833.3
165°	843.4	844.4	845.3	846.2	847.2	847.2	846.2	845.3	844.4	843.4	842.9
167.5°	850.0	851.2	852.5	853.7	855.0	855.1	854.2	853.2	852.2	851.2	850.9
170°	854.0	855.2	856.5	857.7	859.0	859.1	858.1	857.2	856.2	855.2	855.0
172.5°	856.9	858.2	859.4	860.7	861.9	862.1	861.1	860.1	859.2	858.2	857.9
175°	859.6	860.9	862.4	863.7	865.1	865.3	864.3	863.4	862.5	861.5	861.2
177.5°	861.2	862.2	863.2	864.2	865.2	865.3	864.5	863.8	863.0	862.2	862.1
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331591-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1824.6	1820.2	1817.5	1807.7	1798.8	1790.1	1787.4	1788.5	1776.5	1765.0	1760.1
5°	1895.7	1882.0	1869.0	1850.6	1828.7	1804.7	1792.4	1782.9	1759.0	1733.0	1718.0
7.5°	1959.4	1939.8	1914.8	1880.1	1848.2	1810.6	1786.7	1765.5	1730.5	1693.9	1671.5
10°	1998.1	1971.5	1939.4	1897.0	1858.1	1812.3	1780.1	1748.0	1707.0	1663.3	1635.9
12.5°	2031.5	1995.6	1964.0	1909.6	1863.5	1806.2	1768.2	1722.9	1679.7	1627.7	1601.0
15°	2110.9	2044.6	1984.5	1923.0	1866.3	1786.3	1743.9	1683.1	1626.4	1562.2	1531.4
17.5°	2172.3	2097.7	2003.0	1924.9	1858.8	1770.2	1708.0	1635.1	1568.1	1494.7	1452.9
20°	2207.3	2121.8	2020.0	1927.1	1847.8	1746.7	1679.0	1604.5	1526.0	1443.2	1398.2
22.5°	2228.0	2138.2	2037.6	1918.9	1826.0	1727.5	1642.4	1560.8	1481.1	1391.9	1344.6
25°	2234.6	2152.6	2046.0	1912.1	1798.6	1687.2	1584.7	1505.5	1409.1	1325.7	1256.7
27.5°	2202.1	2143.3	2040.8	1899.2	1767.0	1636.8	1522.5	1432.7	1331.1	1240.5	1171.2
30°	2162.1	2128.0	2028.2	1886.1	1741.9	1601.8	1476.0	1374.2	1273.1	1181.5	1110.4
32.5°	2100.4	2093.0	2005.3	1867.5	1715.1	1557.6	1427.5	1324.5	1212.5	1122.5	1054.7
35°	1979.1	2011.8	1956.5	1826.0	1664.6	1494.5	1353.7	1236.2	1120.1	1033.9	970.4
37.5°	1816.4	1897.8	1883.4	1765.1	1596.6	1425.9	1270.5	1147.6	1037.0	950.0	887.7
40°	1704.3	1808.2	1823.2	1718.7	1548.5	1372.9	1208.2	1085.8	977.9	898.7	835.7
42.5°	1584.0	1705.4	1746.7	1662.9	1496.0	1317.1	1152.4	1025.7	918.8	841.8	786.0
45°	1382.4	1543.0	1617.6	1569.7	1408.5	1225.3	1055.8	927.3	830.3	757.9	714.8
47.5°	1194.0	1369.5	1469.6	1452.7	1311.0	1129.6	962.1	838.7	744.3	686.5	648.0
50°	1060.6	1241.0	1361.9	1367.4	1241.0	1061.2	893.1	776.9	690.2	636.2	604.8
52.5°	944.7	1116.9	1248.8	1277.7	1162.8	990.2	831.3	715.8	639.4	589.8	561.6
55°	793.4	939.0	1085.2	1138.4	1046.2	882.3	735.3	633.5	561.7	527.5	502.9
57.5°	659.6	781.0	916.0	974.9	918.0	777.7	639.9	551.4	493.3	463.3	444.4
60°	589.1	684.7	805.0	875.4	826.2	701.2	580.9	496.8	449.0	422.3	404.6
62.5°	523.4	608.2	709.9	774.3	747.4	629.5	521.8	447.6	406.4	381.3	368.5
65°	431.9	498.8	577.5	636.9	619.1	529.6	441.5	377.9	345.1	325.3	315.0
67.5°	355.6	404.0	458.5	510.6	496.2	432.8	362.0	312.5	288.1	271.0	264.8
70°	307.6	344.4	393.0	434.6	423.0	371.0	315.0	272.7	251.5	237.1	231.0
72.5°	261.6	291.9	329.0	363.0	355.2	312.0	265.3	233.3	217.0	203.8	198.8
75°	197.5	220.7	243.3	265.8	263.8	230.3	203.0	178.3	165.4	155.2	153.1
77.5°	145.8	158.8	174.2	187.5	183.8	164.7	143.2	129.1	119.6	112.7	111.6
80°	111.4	118.9	129.8	139.4	134.6	126.4	109.3	99.1	92.3	85.4	82.7
82.5°	80.8	88.3	94.9	100.0	96.4	88.7	78.2	71.2	67.1	62.4	61.3
85°	42.4	46.5	49.2	50.6	49.2	44.4	39.6	36.9	33.5	31.5	30.8
87.5°	18.5	18.2	18.0	18.8	16.9	16.6	14.1	12.1	11.9	11.7	10.9
90°	10.3	9.2	8.0	6.7	5.2	3.7	2.1	0.6	2.1	3.7	5.2
92.5°	13.4	12.8	12.3	12.0	12.2	12.3	12.5	12.6	12.5	12.3	12.2
95°	22.4	21.4	20.4	22.3	26.8	31.4	36.0	40.6	36.0	31.4	26.8
97.5°	28.1	25.9	23.6	28.9	41.8	54.8	67.6	80.5	67.6	54.8	41.8
100°	30.9	28.5	26.1	34.5	53.5	72.5	91.5	110.5	91.5	72.5	53.5
102.5°	76.1	95.8	115.5	127.3	131.3	135.4	139.5	143.5	139.5	135.4	131.3
105°	113.8	151.7	189.6	206.4	202.2	198.1	193.9	189.8	193.9	198.1	202.2
107.5°	144.2	189.6	235.0	256.0	252.6	249.3	245.9	242.5	245.9	249.3	252.6
110°	189.4	229.5	269.6	288.2	285.3	282.4	279.5	276.5	279.5	282.4	285.3



TEST NUMBER: P331591-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	295.3	305.2	315.1	318.8	316.2	313.7	311.1	308.5	311.1	313.7	316.2
115°	378.3	374.8	371.3	368.4	366.0	363.6	361.3	358.9	361.3	363.6	366.0
117.5°	421.9	419.5	417.1	414.6	411.9	409.3	406.6	404.0	406.6	409.3	411.9
120°	452.5	450.0	447.5	445.3	443.2	441.1	439.1	436.9	439.1	441.1	443.2
122.5°	481.6	478.8	476.2	473.7	471.5	469.3	467.2	464.9	467.2	469.3	471.5
125°	522.2	519.6	516.9	514.7	512.9	511.1	509.3	507.5	509.3	511.1	512.9
127.5°	560.0	558.0	556.1	554.1	552.1	550.1	548.0	546.1	548.0	550.1	552.1
130°	584.3	582.8	581.3	579.4	577.2	575.0	572.7	570.5	572.7	575.0	577.2
132.5°	607.8	606.3	604.8	603.1	601.2	599.3	597.4	595.6	597.4	599.3	601.2
135°	641.1	639.9	638.6	636.9	634.6	632.4	630.2	628.0	630.2	632.4	634.6
137.5°	671.4	669.9	668.5	667.0	665.5	664.0	662.4	660.8	662.4	664.0	665.5
140°	691.1	689.6	688.0	686.7	685.6	684.5	683.4	682.3	683.4	684.5	685.6
142.5°	709.2	707.4	705.6	704.3	703.3	702.3	701.2	700.3	701.2	702.3	703.3
145°	733.8	731.4	729.1	727.9	728.1	728.3	728.3	728.5	728.3	728.3	728.1
147.5°	756.5	754.2	751.9	751.0	751.5	752.1	752.6	753.0	752.6	752.1	751.5
150°	770.3	768.0	765.8	765.2	766.2	767.1	768.1	769.1	768.1	767.1	766.2
152.5°	782.9	780.9	778.7	778.2	779.3	780.4	781.5	782.6	781.5	780.4	779.3
155°	800.7	799.1	797.4	797.2	798.4	799.7	800.9	802.2	800.9	799.7	798.4
157.5°	815.6	814.5	813.3	813.3	814.3	815.4	816.5	817.5	816.5	815.4	814.3
160°	824.8	824.0	823.1	823.1	824.0	824.8	825.6	826.5	825.6	824.8	824.0
162.5°	832.6	831.8	831.1	831.2	832.0	832.9	833.7	834.5	833.7	832.9	832.0
165°	842.5	842.1	841.7	841.9	842.8	843.6	844.4	845.3	844.4	843.6	842.8
167.5°	850.4	850.1	849.7	849.9	850.7	851.6	852.4	853.2	852.4	851.6	850.7
170°	854.7	854.3	854.1	854.3	855.2	856.0	856.8	857.7	856.8	856.0	855.2
172.5°	857.6	857.4	857.1	857.4	858.2	859.1	859.9	860.7	859.9	859.1	858.2
175°	860.9	860.6	860.3	860.7	861.7	862.6	863.6	864.6	863.6	862.6	861.7
177.5°	862.0	861.8	861.7	862.1	862.9	863.6	864.4	865.2	864.4	863.6	862.9
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331591-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1754.6	1751.3	1739.8	1733.8	1724.0	1714.7	1708.7	1711.5	1713.6	1712.5	1710.8
5°	1704.3	1691.3	1671.5	1654.4	1642.1	1619.6	1610.0	1605.3	1601.2	1596.3	1591.5
7.5°	1644.4	1624.0	1595.5	1571.2	1548.2	1520.2	1504.2	1494.7	1484.8	1474.0	1464.5
10°	1601.8	1573.1	1543.0	1508.9	1481.6	1456.3	1433.7	1418.6	1405.0	1392.0	1382.4
12.5°	1557.0	1523.9	1486.7	1440.0	1409.9	1373.7	1370.3	1343.8	1322.4	1314.4	1303.1
15°	1485.6	1439.1	1392.0	1336.7	1312.8	1280.0	1259.5	1238.9	1220.5	1207.5	1204.1
17.5°	1404.6	1344.4	1297.5	1257.8	1218.6	1185.0	1166.1	1149.7	1134.5	1117.1	1114.8
20°	1342.8	1290.8	1239.7	1204.8	1164.5	1130.2	1107.1	1090.7	1077.6	1067.4	1058.5
22.5°	1284.3	1227.4	1180.5	1142.5	1102.7	1075.0	1056.8	1040.9	1030.1	1018.8	1010.4
25°	1190.4	1146.0	1094.8	1051.7	1018.9	1001.1	986.1	972.4	965.6	958.1	948.5
27.5°	1108.3	1058.9	1010.9	977.6	948.8	933.1	922.4	913.1	906.7	902.3	896.9
30°	1050.3	1000.4	962.9	930.1	906.2	890.5	883.6	878.2	870.6	867.9	865.1
32.5°	994.5	949.6	917.5	889.0	866.2	856.0	849.7	844.8	838.9	836.2	830.7
35°	915.7	878.2	846.7	831.0	812.5	803.6	798.9	792.0	786.6	783.8	783.1
37.5°	841.5	808.9	788.2	767.9	760.2	754.7	748.1	743.5	741.9	741.5	740.7
40°	793.4	766.7	748.3	731.9	728.4	720.2	714.8	710.7	710.7	711.4	710.7
42.5°	749.7	725.8	709.4	695.3	691.3	686.3	680.9	680.6	681.7	684.0	681.7
45°	683.4	666.3	654.7	647.8	640.3	635.5	634.8	636.9	637.6	638.3	640.3
47.5°	622.4	611.1	600.6	593.0	589.8	588.9	588.1	591.7	594.9	596.2	599.3
50°	586.3	573.4	564.5	559.6	557.0	555.5	557.0	561.1	563.7	567.2	569.3
52.5°	545.9	536.7	530.6	526.9	525.8	526.6	526.9	531.5	535.9	537.2	538.1
55°	490.0	483.1	481.8	475.6	478.3	477.7	481.1	483.8	487.9	492.0	492.7
57.5°	434.2	428.7	425.1	425.6	426.4	429.4	432.3	437.1	441.5	445.9	446.2
60°	397.1	394.3	392.3	392.3	393.6	397.7	401.1	405.9	408.7	411.3	413.4
62.5°	363.1	360.4	358.4	359.4	363.0	365.4	369.4	372.0	374.8	377.5	378.4
65°	309.6	308.2	310.2	311.7	312.3	315.8	320.5	322.5	325.3	326.6	331.4
67.5°	260.2	260.5	260.2	262.2	266.1	266.9	271.4	276.3	276.8	279.4	282.5
70°	226.9	228.3	229.6	231.0	234.4	235.8	239.2	241.2	244.0	246.0	248.1
72.5°	196.3	196.5	197.9	197.6	200.5	203.5	206.3	208.4	211.2	213.7	215.8
75°	151.1	151.1	152.4	153.1	156.5	159.9	159.3	160.6	163.4	166.0	167.5
77.5°	110.3	108.8	110.3	111.0	112.1	114.9	115.5	117.4	120.6	119.6	121.1
80°	84.1	82.0	84.1	84.7	84.7	88.2	88.2	89.5	91.6	89.5	91.6
82.5°	60.0	59.0	60.5	60.7	61.8	61.9	63.0	63.3	65.4	64.4	65.4
85°	30.1	29.4	30.1	29.4	30.1	30.8	30.8	30.1	30.1	31.5	29.4
87.5°	10.6	10.3	10.0	10.3	9.9	9.6	9.2	9.4	9.5	8.6	8.6
90°	6.7	8.0	9.2	10.3	11.4	12.5	13.2	13.9	14.5	15.2	15.8
92.5°	12.0	12.3	12.8	13.4	13.9	14.4	14.8	15.2	15.6	16.0	16.2
95°	22.3	20.4	21.4	22.4	23.4	24.3	25.1	25.8	26.4	27.1	27.4
97.5°	28.9	23.6	25.9	28.1	30.3	32.5	33.2	33.7	34.2	34.8	35.1
100°	34.5	26.1	28.5	30.9	33.3	35.6	36.6	37.8	38.9	40.0	40.8
102.5°	127.3	115.5	95.8	76.1	56.3	36.6	38.0	39.5	40.9	42.4	43.2
105°	206.4	189.6	151.7	113.8	76.0	38.1	39.6	41.1	42.6	44.1	45.2
107.5°	256.0	235.0	189.6	144.2	98.7	53.3	51.7	50.2	48.7	47.1	46.6
110°	288.2	269.6	229.5	189.4	149.4	109.2	95.4	81.5	67.6	53.8	47.1



TEST NUMBER: P331591-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	318.8	315.1	305.2	295.3	285.4	275.5	225.0	174.3	123.8	73.1	48.1
115°	368.4	371.3	374.8	378.3	381.7	385.1	320.9	256.7	192.4	128.2	91.1
117.5°	414.6	417.1	419.5	421.9	424.2	426.6	411.1	395.6	380.0	364.4	340.3
120°	445.3	447.5	450.0	452.5	455.0	457.5	459.2	460.9	462.5	464.2	455.7
122.5°	473.7	476.2	478.8	481.6	484.3	487.1	488.0	489.0	490.0	491.1	489.7
125°	514.7	516.9	519.6	522.2	524.9	527.4	528.4	529.4	530.4	531.4	532.1
127.5°	554.1	556.1	558.0	560.0	562.0	563.9	565.3	566.8	568.2	569.6	570.3
130°	579.4	581.3	582.8	584.3	585.9	587.5	589.0	590.5	592.0	593.5	594.2
132.5°	603.1	604.8	606.3	607.8	609.4	610.9	612.2	613.5	614.8	616.1	616.7
135°	636.9	638.6	639.9	641.1	642.4	643.6	645.0	646.4	647.7	649.2	649.7
137.5°	667.0	668.5	669.9	671.4	672.8	674.2	675.6	676.9	678.2	679.7	680.1
140°	686.7	688.0	689.6	691.1	692.6	694.2	695.4	696.7	697.9	699.2	699.5
142.5°	704.3	705.6	707.4	709.2	710.9	712.7	713.8	714.9	716.0	717.2	717.4
145°	727.9	729.1	731.4	733.8	736.1	738.5	739.5	740.4	741.4	742.3	742.5
147.5°	751.0	751.9	754.2	756.5	758.8	761.2	762.0	762.7	763.4	764.1	764.2
150°	765.2	765.8	768.0	770.3	772.5	774.7	775.5	776.3	777.2	778.0	778.1
152.5°	778.2	778.7	780.9	782.9	785.1	787.2	788.0	788.8	789.7	790.5	790.5
155°	797.2	797.4	799.1	800.7	802.4	804.1	804.9	805.7	806.6	807.4	807.2
157.5°	813.3	813.3	814.5	815.6	816.8	818.0	818.9	819.9	820.8	821.8	821.7
160°	823.1	823.1	824.0	824.8	825.6	826.5	827.3	828.1	829.0	829.8	829.7
162.5°	831.2	831.1	831.8	832.6	833.3	834.0	834.9	835.9	836.8	837.8	837.7
165°	841.9	841.7	842.1	842.5	842.9	843.4	844.4	845.3	846.2	847.2	847.2
167.5°	849.9	849.7	850.1	850.4	850.9	851.2	852.2	853.2	854.2	855.1	855.0
170°	854.3	854.1	854.3	854.7	855.0	855.2	856.2	857.2	858.1	859.1	859.0
172.5°	857.4	857.1	857.4	857.6	857.9	858.2	859.2	860.1	861.1	862.1	861.9
175°	860.7	860.3	860.6	860.9	861.2	861.5	862.5	863.4	864.3	865.3	865.1
177.5°	862.1	861.7	861.8	862.0	862.1	862.2	863.0	863.8	864.5	865.3	865.2
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331591-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1705.4	1704.3	1704.3	1699.4	1704.3	1704.3	1705.4	1710.8	1712.5	1713.6	1711.5
5°	1582.0	1579.9	1576.5	1579.9	1576.5	1579.9	1582.0	1591.5	1596.3	1601.2	1605.3
7.5°	1459.9	1451.7	1450.5	1442.4	1450.5	1451.7	1459.9	1464.5	1474.0	1484.8	1494.7
10°	1370.8	1365.4	1364.7	1351.7	1364.7	1365.4	1370.8	1382.4	1392.0	1405.0	1418.6
12.5°	1303.1	1289.9	1292.5	1285.0	1292.5	1289.9	1303.1	1303.1	1314.4	1322.4	1343.8
15°	1185.6	1185.6	1182.9	1171.3	1182.9	1185.6	1185.6	1204.1	1207.5	1220.5	1238.9
17.5°	1101.4	1099.9	1093.4	1096.6	1093.4	1099.9	1101.4	1114.8	1117.1	1134.5	1149.7
20°	1051.0	1047.0	1038.8	1038.8	1038.8	1047.0	1051.0	1058.5	1067.4	1077.6	1090.7
22.5°	1003.4	1003.2	994.4	997.2	994.4	1003.2	1003.4	1010.4	1018.8	1030.1	1040.9
25°	947.8	942.4	938.3	940.3	938.3	942.4	947.8	948.5	958.1	965.6	972.4
27.5°	895.1	892.1	891.8	886.2	891.8	892.1	895.1	896.9	902.3	906.7	913.1
30°	864.4	857.6	859.0	855.6	859.0	857.6	864.4	865.1	867.9	870.6	878.2
32.5°	829.5	827.0	825.6	822.8	825.6	827.0	829.5	830.7	836.2	838.9	844.8
35°	781.8	782.5	779.0	780.4	779.0	782.5	781.8	783.1	783.8	786.6	792.0
37.5°	740.1	742.3	740.7	741.0	740.7	742.3	740.1	740.7	741.5	741.9	743.5
40°	712.7	712.7	712.7	714.8	712.7	712.7	712.7	710.7	711.4	710.7	710.7
42.5°	686.5	685.5	684.3	684.2	684.3	685.5	686.5	681.7	684.0	681.7	680.6
45°	641.7	643.7	644.4	641.0	644.4	643.7	641.7	640.3	638.3	637.6	636.9
47.5°	601.1	601.4	601.1	604.1	601.1	601.4	601.1	599.3	596.2	594.9	591.7
50°	572.7	571.3	572.7	571.3	572.7	571.3	572.7	569.3	567.2	563.7	561.1
52.5°	542.6	542.9	542.1	541.8	542.1	542.9	542.6	538.1	537.2	535.9	531.5
55°	495.4	496.8	496.1	496.1	496.1	496.8	495.4	492.7	492.0	487.9	483.8
57.5°	446.7	447.9	448.8	445.9	448.8	447.9	446.7	446.2	445.9	441.5	437.1
60°	412.8	416.2	415.4	414.1	415.4	416.2	412.8	413.4	411.3	408.7	405.9
62.5°	381.6	382.8	382.7	382.5	382.7	382.8	381.6	378.4	377.5	374.8	372.0
65°	333.5	334.8	332.8	334.8	332.8	334.8	333.5	331.4	326.6	325.3	322.5
67.5°	281.7	282.1	283.6	284.5	283.6	282.1	281.7	282.5	279.4	276.8	276.3
70°	249.4	248.8	250.8	252.9	250.8	248.8	249.4	248.1	246.0	244.0	241.2
72.5°	215.5	217.0	216.3	217.8	216.3	217.0	215.5	215.8	213.7	211.2	208.4
75°	166.0	168.1	167.5	169.5	167.5	168.1	166.0	167.5	166.0	163.4	160.6
77.5°	120.0	120.3	120.0	121.1	120.0	120.3	120.0	121.1	119.6	120.6	117.4
80°	91.6	90.2	88.8	91.6	88.8	90.2	91.6	91.6	89.5	91.6	89.5
82.5°	63.7	64.5	63.1	63.1	63.1	64.5	63.7	65.4	64.4	65.4	63.3
85°	29.4	28.7	27.4	27.4	27.4	28.7	29.4	29.4	31.5	30.1	30.1
87.5°	8.6	8.2	8.2	7.8	8.2	8.2	8.6	8.6	8.6	9.5	9.4
90°	16.1	16.3	16.6	16.9	16.6	16.3	16.1	15.8	15.2	14.5	13.9
92.5°	16.3	16.5	16.7	16.9	16.7	16.5	16.3	16.2	16.0	15.6	15.2
95°	27.3	27.1	27.0	26.8	27.0	27.1	27.3	27.4	27.1	26.4	25.8
97.5°	35.3	35.5	35.7	35.8	35.7	35.5	35.3	35.1	34.8	34.2	33.7
100°	41.0	41.3	41.6	41.8	41.6	41.3	41.0	40.8	40.0	38.9	37.8
102.5°	43.7	44.1	44.4	44.9	44.4	44.1	43.7	43.2	42.4	40.9	39.5
105°	45.7	46.4	46.9	47.4	46.9	46.4	45.7	45.2	44.1	42.6	41.1
107.5°	47.2	47.7	48.2	48.8	48.2	47.7	47.2	46.6	47.1	48.7	50.2
110°	47.6	48.2	48.8	49.3	48.8	48.2	47.6	47.1	53.8	67.6	81.5



TEST NUMBER: P331591-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	48.5	49.0	49.4	49.8	49.4	49.0	48.5	48.1	73.1	123.8	174.3
115°	81.1	71.2	61.2	51.2	61.2	71.2	81.1	91.1	128.2	192.4	256.7
117.5°	307.5	274.6	241.8	209.0	241.8	274.6	307.5	340.3	364.4	380.0	395.6
120°	436.9	418.2	399.5	380.8	399.5	418.2	436.9	455.7	464.2	462.5	460.9
122.5°	486.1	482.4	478.8	475.2	478.8	482.4	486.1	489.7	491.1	490.0	489.0
125°	532.4	532.9	533.3	533.7	533.3	532.9	532.4	532.1	531.4	530.4	529.4
127.5°	570.4	570.5	570.6	570.7	570.6	570.5	570.4	570.3	569.6	568.2	566.8
130°	594.1	594.0	593.8	593.7	593.8	594.0	594.1	594.2	593.5	592.0	590.5
132.5°	616.5	616.4	616.3	616.2	616.3	616.4	616.5	616.7	616.1	614.8	613.5
135°	649.4	649.2	648.9	648.6	648.9	649.2	649.4	649.7	649.2	647.7	646.4
137.5°	679.6	679.1	678.7	678.1	678.7	679.1	679.6	680.1	679.7	678.2	676.9
140°	698.7	698.0	697.3	696.7	697.3	698.0	698.7	699.5	699.2	697.9	696.7
142.5°	716.8	716.0	715.3	714.6	715.3	716.0	716.8	717.4	717.2	716.0	714.9
145°	741.8	741.1	740.4	739.8	740.4	741.1	741.8	742.5	742.3	741.4	740.4
147.5°	763.6	763.0	762.4	761.8	762.4	763.0	763.6	764.2	764.1	763.4	762.7
150°	777.4	776.7	776.0	775.3	776.0	776.7	777.4	778.1	778.0	777.2	776.3
152.5°	789.5	788.6	787.7	786.8	787.7	788.6	789.5	790.5	790.5	789.7	788.8
155°	806.1	805.0	803.9	802.8	803.9	805.0	806.1	807.2	807.4	806.6	805.7
157.5°	820.6	819.6	818.5	817.3	818.5	819.6	820.6	821.7	821.8	820.8	819.9
160°	828.8	827.8	826.9	825.9	826.9	827.8	828.8	829.7	829.8	829.0	828.1
162.5°	836.4	835.3	834.0	832.9	834.0	835.3	836.4	837.7	837.8	836.8	835.9
165°	846.2	845.3	844.4	843.4	844.4	845.3	846.2	847.2	847.2	846.2	845.3
167.5°	853.7	852.5	851.2	850.0	851.2	852.5	853.7	855.0	855.1	854.2	853.2
170°	857.7	856.5	855.2	854.0	855.2	856.5	857.7	859.0	859.1	858.1	857.2
172.5°	860.7	859.4	858.2	856.9	858.2	859.4	860.7	861.9	862.1	861.1	860.1
175°	863.7	862.4	860.9	859.6	860.9	862.4	863.7	865.1	865.3	864.3	863.4
177.5°	864.2	863.2	862.2	861.2	862.2	863.2	864.2	865.2	865.3	864.5	863.8
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331591-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1708.7	1714.7	1724.0	1733.8	1739.8	1751.3	1754.6	1760.1	1765.0	1776.5	1788.5
5°	1610.0	1619.6	1642.1	1654.4	1671.5	1691.3	1704.3	1718.0	1733.0	1759.0	1782.9
7.5°	1504.2	1520.2	1548.2	1571.2	1595.5	1624.0	1644.4	1671.5	1693.9	1730.5	1765.5
10°	1433.7	1456.3	1481.6	1508.9	1543.0	1573.1	1601.8	1635.9	1663.3	1707.0	1748.0
12.5°	1370.3	1373.7	1409.9	1440.0	1486.7	1523.9	1557.0	1601.0	1627.7	1679.7	1722.9
15°	1259.5	1280.0	1312.8	1336.7	1392.0	1439.1	1485.6	1531.4	1562.2	1626.4	1683.1
17.5°	1166.1	1185.0	1218.6	1257.8	1297.5	1344.4	1404.6	1452.9	1494.7	1568.1	1635.1
20°	1107.1	1130.2	1164.5	1204.8	1239.7	1290.8	1342.8	1398.2	1443.2	1526.0	1604.5
22.5°	1056.8	1075.0	1102.7	1142.5	1180.5	1227.4	1284.3	1344.6	1391.9	1481.1	1560.8
25°	986.1	1001.1	1018.9	1051.7	1094.8	1146.0	1190.4	1256.7	1325.7	1409.1	1505.5
27.5°	922.4	933.1	948.8	977.6	1010.9	1058.9	1108.3	1171.2	1240.5	1331.1	1432.7
30°	883.6	890.5	906.2	930.1	962.9	1000.4	1050.3	1110.4	1181.5	1273.1	1374.2
32.5°	849.7	856.0	866.2	889.0	917.5	949.6	994.5	1054.7	1122.5	1212.5	1324.5
35°	798.9	803.6	812.5	831.0	846.7	878.2	915.7	970.4	1033.9	1120.1	1236.2
37.5°	748.1	754.7	760.2	767.9	788.2	808.9	841.5	887.7	950.0	1037.0	1147.6
40°	714.8	720.2	728.4	731.9	748.3	766.7	793.4	835.7	898.7	977.9	1085.8
42.5°	680.9	686.3	691.3	695.3	709.4	725.8	749.7	786.0	841.8	918.8	1025.7
45°	634.8	635.5	640.3	647.8	654.7	666.3	683.4	714.8	757.9	830.3	927.3
47.5°	588.1	588.9	589.8	593.0	600.6	611.1	622.4	648.0	686.5	744.3	838.7
50°	557.0	555.5	557.0	559.6	564.5	573.4	586.3	604.8	636.2	690.2	776.9
52.5°	526.9	526.6	525.8	526.9	530.6	536.7	545.9	561.6	589.8	639.4	715.8
55°	481.1	477.7	478.3	475.6	481.8	483.1	490.0	502.9	527.5	561.7	633.5
57.5°	432.3	429.4	426.4	425.6	425.1	428.7	434.2	444.4	463.3	493.3	551.4
60°	401.1	397.7	393.6	392.3	392.3	394.3	397.1	404.6	422.3	449.0	496.8
62.5°	369.4	365.4	363.0	359.4	358.4	360.4	363.1	368.5	381.3	406.4	447.6
65°	320.5	315.8	312.3	311.7	310.2	308.2	309.6	315.0	325.3	345.1	377.9
67.5°	271.4	266.9	266.1	262.2	260.2	260.5	260.2	264.8	271.0	288.1	312.5
70°	239.2	235.8	234.4	231.0	229.6	228.3	226.9	231.0	237.1	251.5	272.7
72.5°	206.3	203.5	200.5	197.6	197.9	196.5	196.3	198.8	203.8	217.0	233.3
75°	159.3	159.9	156.5	153.1	152.4	151.1	151.1	153.1	155.2	165.4	178.3
77.5°	115.5	114.9	112.1	111.0	110.3	108.8	110.3	111.6	112.7	119.6	129.1
80°	88.2	88.2	84.7	84.7	84.1	82.0	84.1	82.7	85.4	92.3	99.1
82.5°	63.0	61.9	61.8	60.7	60.5	59.0	60.0	61.3	62.4	67.1	71.2
85°	30.8	30.8	30.1	29.4	30.1	29.4	30.1	30.8	31.5	33.5	36.9
87.5°	9.2	9.6	9.9	10.3	10.0	10.3	10.6	10.9	11.7	11.9	12.1
90°	13.2	12.5	11.4	10.3	9.2	8.0	6.7	5.2	3.7	2.1	0.6
92.5°	14.8	14.4	13.9	13.4	12.8	12.3	12.0	12.2	12.3	12.5	12.6
95°	25.1	24.3	23.4	22.4	21.4	20.4	22.3	26.8	31.4	36.0	40.6
97.5°	33.2	32.5	30.3	28.1	25.9	23.6	28.9	41.8	54.8	67.6	80.5
100°	36.6	35.6	33.3	30.9	28.5	26.1	34.5	53.5	72.5	91.5	110.5
102.5°	38.0	36.6	56.3	76.1	95.8	115.5	127.3	131.3	135.4	139.5	143.5
105°	39.6	38.1	76.0	113.8	151.7	189.6	206.4	202.2	198.1	193.9	189.8
107.5°	51.7	53.3	98.7	144.2	189.6	235.0	256.0	252.6	249.3	245.9	242.5
110°	95.4	109.2	149.4	189.4	229.5	269.6	288.2	285.3	282.4	279.5	276.5



TEST NUMBER: P331591-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	225.0	275.5	285.4	295.3	305.2	315.1	318.8	316.2	313.7	311.1	308.5
115°	320.9	385.1	381.7	378.3	374.8	371.3	368.4	366.0	363.6	361.3	358.9
117.5°	411.1	426.6	424.2	421.9	419.5	417.1	414.6	411.9	409.3	406.6	404.0
120°	459.2	457.5	455.0	452.5	450.0	447.5	445.3	443.2	441.1	439.1	436.9
122.5°	488.0	487.1	484.3	481.6	478.8	476.2	473.7	471.5	469.3	467.2	464.9
125°	528.4	527.4	524.9	522.2	519.6	516.9	514.7	512.9	511.1	509.3	507.5
127.5°	565.3	563.9	562.0	560.0	558.0	556.1	554.1	552.1	550.1	548.0	546.1
130°	589.0	587.5	585.9	584.3	582.8	581.3	579.4	577.2	575.0	572.7	570.5
132.5°	612.2	610.9	609.4	607.8	606.3	604.8	603.1	601.2	599.3	597.4	595.6
135°	645.0	643.6	642.4	641.1	639.9	638.6	636.9	634.6	632.4	630.2	628.0
137.5°	675.6	674.2	672.8	671.4	669.9	668.5	667.0	665.5	664.0	662.4	660.8
140°	695.4	694.2	692.6	691.1	689.6	688.0	686.7	685.6	684.5	683.4	682.3
142.5°	713.8	712.7	710.9	709.2	707.4	705.6	704.3	703.3	702.3	701.2	700.3
145°	739.5	738.5	736.1	733.8	731.4	729.1	727.9	728.1	728.3	728.3	728.5
147.5°	762.0	761.2	758.8	756.5	754.2	751.9	751.0	751.5	752.1	752.6	753.0
150°	775.5	774.7	772.5	770.3	768.0	765.8	765.2	766.2	767.1	768.1	769.1
152.5°	788.0	787.2	785.1	782.9	780.9	778.7	778.2	779.3	780.4	781.5	782.6
155°	804.9	804.1	802.4	800.7	799.1	797.4	797.2	798.4	799.7	800.9	802.2
157.5°	818.9	818.0	816.8	815.6	814.5	813.3	813.3	814.3	815.4	816.5	817.5
160°	827.3	826.5	825.6	824.8	824.0	823.1	823.1	824.0	824.8	825.6	826.5
162.5°	834.9	834.0	833.3	832.6	831.8	831.1	831.2	832.0	832.9	833.7	834.5
165°	844.4	843.4	842.9	842.5	842.1	841.7	841.9	842.8	843.6	844.4	845.3
167.5°	852.2	851.2	850.9	850.4	850.1	849.7	849.9	850.7	851.6	852.4	853.2
170°	856.2	855.2	855.0	854.7	854.3	854.1	854.3	855.2	856.0	856.8	857.7
172.5°	859.2	858.2	857.9	857.6	857.4	857.1	857.4	858.2	859.1	859.9	860.7
175°	862.5	861.5	861.2	860.9	860.6	860.3	860.7	861.7	862.6	863.6	864.6
177.5°	863.0	862.2	862.1	862.0	861.8	861.7	862.1	862.9	863.6	864.4	865.2
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331591-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1787.4	1790.1	1798.8	1807.7	1817.5	1820.2	1824.6	1820.8	1819.6	1830.1	1837.7
5°	1792.4	1804.7	1828.7	1850.6	1869.0	1882.0	1895.7	1901.1	1911.4	1925.7	1943.5
7.5°	1786.7	1810.6	1848.2	1880.1	1914.8	1939.8	1959.4	1976.0	1996.3	2023.5	2053.1
10°	1780.1	1812.3	1858.1	1897.0	1939.4	1971.5	1998.1	2024.1	2054.2	2091.8	2130.7
12.5°	1768.2	1806.2	1863.5	1909.6	1964.0	1995.6	2031.5	2087.6	2119.8	2172.1	2227.0
15°	1743.9	1786.3	1866.3	1923.0	1984.5	2044.6	2110.9	2164.2	2217.5	2248.3	2325.5
17.5°	1708.0	1770.2	1858.8	1924.9	2003.0	2097.7	2172.3	2232.7	2294.2	2344.0	2382.7
20°	1679.0	1746.7	1847.8	1927.1	2020.0	2121.8	2207.3	2268.8	2322.1	2363.7	2387.6
22.5°	1642.4	1727.5	1826.0	1918.9	2037.6	2138.2	2228.0	2276.4	2320.9	2341.4	2350.5
25°	1584.7	1687.2	1798.6	1912.1	2046.0	2152.6	2234.6	2264.0	2277.0	2257.2	2224.4
27.5°	1522.5	1636.8	1767.0	1899.2	2040.8	2143.3	2202.1	2197.4	2175.4	2111.3	2060.0
30°	1476.0	1601.8	1741.9	1886.1	2028.2	2128.0	2162.1	2128.0	2078.1	2006.3	1933.2
32.5°	1427.5	1557.6	1715.1	1867.5	2005.3	2093.0	2100.4	2041.7	1964.4	1882.8	1791.6
35°	1353.7	1494.5	1664.6	1826.0	1956.5	2011.8	1979.1	1875.2	1783.6	1672.2	1547.8
37.5°	1270.5	1425.9	1596.6	1765.1	1883.4	1897.8	1816.4	1707.0	1577.9	1447.0	1300.6
40°	1208.2	1372.9	1548.5	1718.7	1823.2	1808.2	1704.3	1584.0	1430.3	1270.3	1134.3
42.5°	1152.4	1317.1	1496.0	1662.9	1746.7	1705.4	1584.0	1436.5	1271.2	1120.6	996.0
45°	1055.8	1225.3	1408.5	1569.7	1617.6	1543.0	1382.4	1218.4	1055.8	930.1	831.7
47.5°	962.1	1129.6	1311.0	1452.7	1469.6	1369.5	1194.0	1025.2	885.4	783.0	713.5
50°	893.1	1061.2	1241.0	1367.4	1361.9	1241.0	1060.6	900.0	783.1	700.4	654.0
52.5°	831.3	990.2	1162.8	1277.7	1248.8	1116.9	944.7	802.1	706.1	641.4	599.3
55°	735.3	882.3	1046.2	1138.4	1085.2	939.0	793.4	678.6	607.5	559.0	526.2
57.5°	639.9	777.7	918.0	974.9	916.0	781.0	659.6	576.3	522.9	487.0	465.7
60°	580.9	701.2	826.2	875.4	805.0	684.7	589.1	514.6	471.5	442.1	423.0
62.5°	521.8	629.5	747.4	774.3	709.9	608.2	523.4	461.5	426.1	400.0	382.0
65°	441.5	529.6	619.1	636.9	577.5	498.8	431.9	391.6	360.2	341.0	326.6
67.5°	362.0	432.8	496.2	510.6	458.5	404.0	355.6	320.5	299.2	283.3	271.2
70°	315.0	371.0	423.0	434.6	393.0	344.4	307.6	279.5	260.4	246.7	235.1
72.5°	265.3	312.0	355.2	363.0	329.0	291.9	261.6	239.6	222.7	213.9	202.9
75°	203.0	230.3	263.8	265.8	243.3	220.7	197.5	183.2	174.2	163.4	157.8
77.5°	143.2	164.7	183.8	187.5	174.2	158.8	145.8	134.5	127.0	121.9	116.8
80°	109.3	126.4	134.6	139.4	129.8	118.9	111.4	103.9	99.1	95.7	92.3
82.5°	78.2	88.7	96.4	100.0	94.9	88.3	80.8	76.5	72.9	70.0	68.8
85°	39.6	44.4	49.2	50.6	49.2	46.5	42.4	42.4	40.3	39.6	39.6
87.5°	14.1	16.6	16.9	18.8	18.0	18.2	18.5	18.1	17.8	17.4	17.0
90°	2.1	3.7	5.2	6.7	8.0	9.2	10.3	11.4	12.5	13.2	13.9
92.5°	12.5	12.3	12.2	12.0	12.3	12.8	13.4	13.9	14.4	14.8	15.2
95°	36.0	31.4	26.8	22.3	20.4	21.4	22.4	23.4	24.3	25.1	25.8
97.5°	67.6	54.8	41.8	28.9	23.6	25.9	28.1	30.3	32.5	33.2	33.7
100°	91.5	72.5	53.5	34.5	26.1	28.5	30.9	33.3	35.6	36.6	37.8
102.5°	139.5	135.4	131.3	127.3	115.5	95.8	76.1	56.3	36.6	38.0	39.5
105°	193.9	198.1	202.2	206.4	189.6	151.7	113.8	76.0	38.1	39.6	41.1
107.5°	245.9	249.3	252.6	256.0	235.0	189.6	144.2	98.7	53.3	51.7	50.2
110°	279.5	282.4	285.3	288.2	269.6	229.5	189.4	149.4	109.2	95.4	81.5



TEST NUMBER: P331591-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	311.1	313.7	316.2	318.8	315.1	305.2	295.3	285.4	275.5	225.0	174.3
115°	361.3	363.6	366.0	368.4	371.3	374.8	378.3	381.7	385.1	320.9	256.7
117.5°	406.6	409.3	411.9	414.6	417.1	419.5	421.9	424.2	426.6	411.1	395.6
120°	439.1	441.1	443.2	445.3	447.5	450.0	452.5	455.0	457.5	459.2	460.9
122.5°	467.2	469.3	471.5	473.7	476.2	478.8	481.6	484.3	487.1	488.0	489.0
125°	509.3	511.1	512.9	514.7	516.9	519.6	522.2	524.9	527.4	528.4	529.4
127.5°	548.0	550.1	552.1	554.1	556.1	558.0	560.0	562.0	563.9	565.3	566.8
130°	572.7	575.0	577.2	579.4	581.3	582.8	584.3	585.9	587.5	589.0	590.5
132.5°	597.4	599.3	601.2	603.1	604.8	606.3	607.8	609.4	610.9	612.2	613.5
135°	630.2	632.4	634.6	636.9	638.6	639.9	641.1	642.4	643.6	645.0	646.4
137.5°	662.4	664.0	665.5	667.0	668.5	669.9	671.4	672.8	674.2	675.6	676.9
140°	683.4	684.5	685.6	686.7	688.0	689.6	691.1	692.6	694.2	695.4	696.7
142.5°	701.2	702.3	703.3	704.3	705.6	707.4	709.2	710.9	712.7	713.8	714.9
145°	728.3	728.3	728.1	727.9	729.1	731.4	733.8	736.1	738.5	739.5	740.4
147.5°	752.6	752.1	751.5	751.0	751.9	754.2	756.5	758.8	761.2	762.0	762.7
150°	768.1	767.1	766.2	765.2	765.8	768.0	770.3	772.5	774.7	775.5	776.3
152.5°	781.5	780.4	779.3	778.2	778.7	780.9	782.9	785.1	787.2	788.0	788.8
155°	800.9	799.7	798.4	797.2	797.4	799.1	800.7	802.4	804.1	804.9	805.7
157.5°	816.5	815.4	814.3	813.3	813.3	814.5	815.6	816.8	818.0	818.9	819.9
160°	825.6	824.8	824.0	823.1	823.1	824.0	824.8	825.6	826.5	827.3	828.1
162.5°	833.7	832.9	832.0	831.2	831.1	831.8	832.6	833.3	834.0	834.9	835.9
165°	844.4	843.6	842.8	841.9	841.7	842.1	842.5	842.9	843.4	844.4	845.3
167.5°	852.4	851.6	850.7	849.9	849.7	850.1	850.4	850.9	851.2	852.2	853.2
170°	856.8	856.0	855.2	854.3	854.1	854.3	854.7	855.0	855.2	856.2	857.2
172.5°	859.9	859.1	858.2	857.4	857.1	857.4	857.6	857.9	858.2	859.2	860.1
175°	863.6	862.6	861.7	860.7	860.3	860.6	860.9	861.2	861.5	862.5	863.4
177.5°	864.4	863.6	862.9	862.1	861.7	861.8	862.0	862.1	862.2	863.0	863.8
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331591-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1844.2	1851.9	1851.9	1853.0	1861.7	1860.6	1860.1
5°	1962.7	1974.2	1975.6	1987.9	1996.1	1993.3	1985.8
7.5°	2074.3	2095.9	2112.3	2121.5	2132.3	2138.9	2135.9
10°	2162.8	2194.3	2213.4	2226.4	2242.1	2253.7	2249.6
12.5°	2243.2	2280.6	2306.9	2329.1	2331.2	2346.1	2336.0
15°	2368.6	2408.2	2412.3	2428.7	2441.7	2440.3	2441.0
17.5°	2409.9	2422.7	2425.3	2425.6	2425.8	2421.0	2410.7
20°	2395.2	2390.4	2378.8	2369.9	2354.2	2352.2	2338.5
22.5°	2325.2	2310.1	2280.9	2261.6	2237.2	2230.8	2227.0
25°	2187.5	2153.9	2107.5	2063.1	2050.8	2026.9	2033.7
27.5°	1998.4	1946.2	1896.0	1859.8	1827.2	1791.4	1801.6
30°	1865.5	1806.8	1735.7	1681.1	1646.2	1612.0	1605.9
32.5°	1707.0	1621.0	1541.7	1493.5	1440.1	1418.5	1394.9
35°	1433.7	1349.6	1271.0	1203.4	1164.5	1134.3	1107.1
37.5°	1187.8	1091.1	1027.6	972.9	944.7	927.5	931.8
40°	1035.3	950.6	904.1	862.4	836.4	824.1	826.9
42.5°	911.8	848.3	810.0	781.5	763.2	756.3	754.7
45°	771.5	736.0	704.5	688.1	679.3	671.7	667.0
47.5°	675.8	646.8	629.1	619.4	611.6	604.0	603.8
50°	618.4	599.3	587.0	576.8	570.6	565.2	569.9
52.5°	574.7	557.2	544.9	535.7	533.4	528.5	528.3
55°	509.8	496.1	487.2	479.0	474.9	472.2	468.8
57.5°	450.8	437.7	429.5	424.4	416.6	413.8	412.8
60°	408.7	398.4	390.2	383.3	380.0	374.5	374.5
62.5°	369.8	359.6	352.0	346.7	341.2	338.9	339.5
65°	313.7	305.5	297.9	292.5	291.1	287.0	288.4
67.5°	262.0	256.5	248.6	245.6	243.0	240.9	239.2
70°	227.6	222.1	218.0	213.9	211.9	211.9	211.9
72.5°	198.6	192.0	189.6	184.4	185.6	183.4	181.2
75°	153.7	149.6	147.6	145.5	142.1	142.1	142.1
77.5°	113.2	111.9	109.5	107.3	106.5	105.8	106.0
80°	87.5	86.8	85.4	85.4	84.1	83.4	82.0
82.5°	67.2	65.5	64.6	64.1	63.8	63.7	63.4
85°	38.3	36.9	36.9	37.5	36.2	36.2	36.9
87.5°	17.7	17.8	17.4	17.4	18.0	17.6	17.6
90°	14.5	15.2	15.8	16.1	16.3	16.6	16.9
92.5°	15.6	16.0	16.2	16.3	16.5	16.7	16.9
95°	26.4	27.1	27.4	27.3	27.1	27.0	26.8
97.5°	34.2	34.8	35.1	35.3	35.5	35.7	35.8
100°	38.9	40.0	40.8	41.0	41.3	41.6	41.8
102.5°	40.9	42.4	43.2	43.7	44.1	44.4	44.9
105°	42.6	44.1	45.2	45.7	46.4	46.9	47.4
107.5°	48.7	47.1	46.6	47.2	47.7	48.2	48.8
110°	67.6	53.8	47.1	47.6	48.2	48.8	49.3



TEST NUMBER: P331591-940

CATALOG NUMBER: S122DIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	123.8	73.1	48.1	48.5	49.0	49.4	49.8
115°	192.4	128.2	91.1	81.1	71.2	61.2	51.2
117.5°	380.0	364.4	340.3	307.5	274.6	241.8	209.0
120°	462.5	464.2	455.7	436.9	418.2	399.5	380.8
122.5°	490.0	491.1	489.7	486.1	482.4	478.8	475.2
125°	530.4	531.4	532.1	532.4	532.9	533.3	533.7
127.5°	568.2	569.6	570.3	570.4	570.5	570.6	570.7
130°	592.0	593.5	594.2	594.1	594.0	593.8	593.7
132.5°	614.8	616.1	616.7	616.5	616.4	616.3	616.2
135°	647.7	649.2	649.7	649.4	649.2	648.9	648.6
137.5°	678.2	679.7	680.1	679.6	679.1	678.7	678.1
140°	697.9	699.2	699.5	698.7	698.0	697.3	696.7
142.5°	716.0	717.2	717.4	716.8	716.0	715.3	714.6
145°	741.4	742.3	742.5	741.8	741.1	740.4	739.8
147.5°	763.4	764.1	764.2	763.6	763.0	762.4	761.8
150°	777.2	778.0	778.1	777.4	776.7	776.0	775.3
152.5°	789.7	790.5	790.5	789.5	788.6	787.7	786.8
155°	806.6	807.4	807.2	806.1	805.0	803.9	802.8
157.5°	820.8	821.8	821.7	820.6	819.6	818.5	817.3
160°	829.0	829.8	829.7	828.8	827.8	826.9	825.9
162.5°	836.8	837.8	837.7	836.4	835.3	834.0	832.9
165°	846.2	847.2	847.2	846.2	845.3	844.4	843.4
167.5°	854.2	855.1	855.0	853.7	852.5	851.2	850.0
170°	858.1	859.1	859.0	857.7	856.5	855.2	854.0
172.5°	861.1	862.1	861.9	860.7	859.4	858.2	856.9
175°	864.3	865.3	865.1	863.7	862.4	860.9	859.6
177.5°	864.5	865.3	865.2	864.2	863.2	862.2	861.2
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7

(END OF REPORT)