

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331816

Luminaire Tested: **S122RDIW-S675D970U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331816
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D970U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5680.9 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331816

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331816

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41								
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41	35								
2	88	81	75	70	80	74	69	65	61	57	54	49	47	45	38	37	35	30								
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26								
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26	23								
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20								
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18								
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	19	16								
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	21	19	17	14								
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13								
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	18	16	14	12								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18213	18213	18213
5°	18282	17985	18084
10°	18143	17690	17539
15°	17934	17167	16672
20°	17646	16417	15593
25°	17350	15567	14549
30°	16940	14693	13209
35°	16539	13742	12033
40°	16136	12760	10671
45°	15664	11654	9439
50°	15179	10540	8231
55°	14686	9340	7068
60°	14108	8076	5867
65°	13456	6785	5345
70°	12675	5589	4914
75°	11715	5097	4585
80°	10349	4556	4175
85°	8133	3594	3594



TEST NUMBER: P331816

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.6	1.9
10°-20°	289.9	5.1
20°-30°	407.1	7.2
30°-40°	443.9	7.8
40°-50°	408.2	7.2
50°-60°	320.6	5.6
60°-70°	209.0	3.7
70°-80°	107.8	1.9
80°-90°	32.7	0.6
90°-100°	76.0	1.3
100°-110°	236.2	4.2
110°-120°	403.8	7.1
120°-130°	531.0	9.3
130°-140°	595.9	10.5
140°-150°	584.3	10.3
150°-160°	490.1	8.6
160°-170°	325.1	5.7
170°-180°	113.6	2.0
0°-30°	802.6	14.1
0°-40°	1246.6	21.9
0°-60°	1975.3	34.8
0°-90°	2324.9	40.9
90°-120°	716.0	12.6
90°-150°	2427.3	42.7
90°-180°	3356.0	59.1
0°-180°	5680.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1128	1128	1128	1128	1128	
5°	1128	1122	1110	1118	1116	107
15°	1073	1060	1027	1008	997	302
25°	974	939	874	833	817	448
35°	839	785	697	635	610	525
45°	686	615	510	441	413	529
55°	522	440	332	273	251	466
65°	352	269	178	145	140	349
75°	188	118	82	75	74	199
85°	44	23	19	19	19	52
90°	1	14	35	34	34	5
95°	53	62	65	65	63	60
105°	218	221	223	225	225	230
115°	405	411	409	408	405	401
125°	590	598	596	593	592	527
135°	763	773	776	775	772	589
145°	926	933	939	940	936	578
155°	1058	1061	1064	1069	1066	487
165°	1152	1151	1151	1157	1153	325
175°	1198	1195	1193	1200	1194	114
180°	1200	1200	1200	1200	1200	



TEST NUMBER: P331816

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0
2.5°	1132.1	1131.2	1130.3	1129.4	1128.5	1127.0	1125.0	1123.0	1121.1	1119.1	1120.9
5°	1128.0	1126.9	1125.8	1124.6	1123.5	1121.5	1118.5	1115.6	1112.6	1109.7	1111.7
7.5°	1116.4	1115.0	1113.6	1112.2	1110.8	1108.3	1104.9	1101.5	1098.0	1094.6	1095.1
10°	1106.6	1105.0	1103.4	1101.8	1100.2	1097.2	1092.6	1088.1	1083.6	1079.0	1078.4
12.5°	1094.3	1092.4	1090.4	1088.5	1086.5	1082.7	1076.9	1071.1	1065.2	1059.4	1058.2
15°	1072.9	1070.4	1067.9	1065.4	1062.9	1057.8	1050.1	1042.4	1034.7	1027.0	1022.7
17.5°	1046.6	1042.8	1039.0	1035.1	1031.3	1024.5	1014.6	1004.7	994.8	984.9	979.8
20°	1027.0	1022.4	1017.9	1013.4	1008.8	1000.9	989.5	978.2	966.9	955.5	949.8
22.5°	1005.7	1000.7	995.6	990.5	985.4	976.5	963.7	950.9	938.1	925.3	918.0
25°	973.9	966.6	959.4	952.1	944.9	933.7	918.8	903.8	888.8	873.8	864.5
27.5°	935.5	927.6	919.7	911.8	903.9	891.5	874.7	857.8	840.9	824.0	813.2
30°	908.6	899.9	891.3	882.7	874.1	860.7	842.5	824.4	806.2	788.1	776.5
32.5°	882.4	872.3	862.3	852.2	842.1	827.8	809.3	790.8	772.3	753.8	740.6
35°	839.1	827.6	816.0	804.4	792.9	777.1	757.1	737.2	717.2	697.2	682.9
37.5°	795.9	783.1	770.4	757.7	745.0	728.0	706.8	685.5	664.2	642.9	627.2
40°	765.6	752.0	738.4	724.8	711.2	693.4	671.4	649.4	627.4	605.4	589.3
42.5°	734.6	720.3	705.9	691.6	677.3	658.7	636.0	613.3	590.5	567.8	551.1
45°	686.0	670.8	655.6	640.4	625.2	605.7	581.9	558.1	534.2	510.4	494.3
47.5°	638.6	622.5	606.4	590.3	574.2	553.9	529.3	504.7	480.1	455.5	439.5
50°	604.3	588.2	572.1	556.0	539.9	519.4	494.4	469.5	444.5	419.6	403.9
52.5°	570.9	554.0	537.2	520.4	503.5	482.9	458.5	434.1	409.7	385.3	370.2
55°	521.7	504.0	486.3	468.6	450.9	429.8	405.3	380.8	356.3	331.8	318.2
57.5°	471.2	453.1	434.9	416.8	398.6	377.8	354.2	330.7	307.1	283.6	271.1
60°	436.9	418.8	400.6	382.5	364.3	343.6	320.2	296.8	273.5	250.1	238.5
62.5°	403.4	385.3	367.1	349.0	330.8	310.6	288.4	266.1	243.8	221.5	210.5
65°	352.2	333.8	315.4	297.1	278.7	259.3	238.9	218.5	198.0	177.6	169.9
67.5°	302.8	284.5	266.3	248.1	229.8	211.5	193.1	174.8	156.4	138.0	134.5
70°	268.5	250.8	233.1	215.4	197.7	181.0	165.4	149.7	134.1	118.4	116.1
72.5°	235.8	218.8	201.9	184.9	167.9	153.2	140.6	128.0	115.5	102.9	101.0
75°	187.8	172.0	156.1	140.2	124.3	112.5	104.8	97.1	89.4	81.7	80.1
77.5°	140.7	126.7	112.8	98.9	85.0	76.1	72.4	68.7	65.0	61.3	60.3
80°	111.3	99.7	88.1	76.6	65.0	58.1	55.8	53.5	51.3	49.0	48.1
82.5°	84.3	75.3	66.3	57.2	48.2	42.9	41.4	39.8	38.3	36.8	36.2
85°	43.9	39.1	34.4	29.6	24.8	22.1	21.4	20.8	20.1	19.4	19.4
87.5°	13.3	12.4	11.4	10.5	9.6	9.7	10.7	11.6	12.6	13.6	13.4
90°	1.0	3.7	6.4	9.1	11.8	15.6	20.6	25.5	30.5	35.4	35.0
92.5°	18.0	20.0	22.0	24.0	26.0	27.5	28.7	29.9	31.0	32.2	32.3
95°	52.7	54.9	57.2	59.4	61.7	63.0	63.5	63.9	64.4	64.8	64.8
97.5°	96.2	98.2	100.2	102.2	104.1	105.6	106.4	107.3	108.1	109.0	109.0
100°	128.6	130.4	132.2	134.0	135.8	137.1	137.7	138.4	139.1	139.8	139.8
102.5°	162.7	164.1	165.5	167.0	168.4	169.6	170.4	171.3	172.1	173.0	173.2
105°	217.8	218.4	219.1	219.8	220.5	221.0	221.5	221.9	222.4	222.8	223.3
107.5°	273.3	274.3	275.2	276.2	277.2	277.7	277.7	277.7	277.7	277.7	277.9
110°	308.9	310.3	311.6	313.0	314.3	315.0	315.0	315.0	315.0	315.0	315.0



TEST NUMBER: P331816

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	347.8	349.2	350.5	351.9	353.2	353.8	353.6	353.4	353.3	353.1	352.5
115°	405.1	406.5	407.8	409.2	410.5	411.0	410.5	410.1	409.6	409.2	409.0
117.5°	462.3	464.1	465.9	467.7	469.5	469.7	468.5	467.2	466.0	464.7	464.2
120°	500.4	502.2	504.0	505.8	507.6	507.6	505.8	504.0	502.2	500.4	500.4
122.5°	535.2	537.4	539.5	541.7	543.8	544.3	543.0	541.8	540.5	539.2	538.7
125°	589.5	591.5	593.5	595.6	597.6	598.3	597.6	596.9	596.2	595.6	594.9
127.5°	642.4	644.9	647.5	650.1	652.6	653.5	652.7	651.9	651.1	650.3	649.4
130°	675.6	678.5	681.4	684.4	687.3	688.5	688.1	687.6	687.2	686.7	686.3
132.5°	712.8	715.2	717.6	720.0	722.4	723.6	723.7	723.8	723.9	724.0	723.0
135°	762.7	765.2	767.6	770.1	772.6	774.0	774.5	774.9	775.4	775.8	775.6
137.5°	815.1	817.2	819.2	821.2	823.2	824.6	825.1	825.7	826.3	826.9	826.7
140°	846.7	848.8	850.8	852.8	854.8	856.4	857.6	858.7	859.8	860.9	860.9
142.5°	879.2	881.2	883.2	885.2	887.3	888.7	889.4	890.2	891.0	891.7	891.9
145°	925.7	927.3	928.9	930.5	932.1	933.5	934.9	936.2	937.6	938.9	939.1
147.5°	967.3	969.2	971.1	972.9	974.8	976.2	977.1	978.0	978.9	979.8	980.3
150°	995.6	997.0	998.3	999.7	1001.0	1002.2	1003.1	1004.0	1004.9	1005.8	1006.4
152.5°	1020.8	1022.1	1023.5	1024.8	1026.2	1027.4	1028.5	1029.5	1030.6	1031.7	1032.5
155°	1058.4	1059.1	1059.8	1060.5	1061.1	1061.8	1062.5	1063.2	1063.8	1064.5	1065.6
157.5°	1090.6	1091.1	1091.5	1092.0	1092.4	1092.9	1093.3	1093.7	1094.1	1094.5	1096.0
160°	1110.1	1110.5	1111.0	1111.4	1111.9	1112.2	1112.5	1112.7	1112.9	1113.1	1114.5
162.5°	1127.9	1128.0	1128.1	1128.2	1128.3	1128.4	1128.7	1128.9	1129.1	1129.3	1130.9
165°	1151.6	1151.4	1151.2	1150.9	1150.7	1150.6	1150.6	1150.6	1150.6	1150.6	1152.2
167.5°	1171.5	1170.8	1170.1	1169.4	1168.8	1168.4	1168.4	1168.3	1168.3	1168.2	1169.8
170°	1182.0	1181.3	1180.7	1180.0	1179.3	1178.9	1178.6	1178.4	1178.2	1178.0	1179.5
172.5°	1189.3	1188.6	1187.9	1187.3	1186.6	1186.1	1185.9	1185.7	1185.5	1185.2	1186.8
175°	1198.2	1197.5	1196.9	1196.2	1195.5	1194.9	1194.5	1194.0	1193.6	1193.1	1194.7
177.5°	1201.9	1201.3	1200.8	1200.2	1199.7	1199.2	1198.9	1198.5	1198.2	1197.8	1198.9
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331816

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0
2.5°	1122.7	1124.5	1126.3	1127.0	1126.7	1126.3	1126.0	1125.6
5°	1113.7	1115.8	1117.8	1118.5	1117.8	1117.1	1116.5	1115.8
7.5°	1095.7	1096.3	1096.9	1096.6	1095.4	1094.3	1093.1	1091.9
10°	1077.7	1077.0	1076.3	1075.3	1073.9	1072.6	1071.2	1069.8
12.5°	1057.0	1055.8	1054.5	1052.8	1050.5	1048.3	1046.0	1043.7
15°	1018.4	1014.0	1009.7	1006.4	1004.2	1001.9	999.6	997.4
17.5°	974.7	969.5	964.4	959.9	956.0	952.1	948.2	944.3
20°	944.2	938.5	932.8	927.5	922.5	917.5	912.5	907.5
22.5°	910.7	903.4	896.1	890.6	886.8	883.1	879.4	875.7
25°	855.2	845.9	836.6	830.3	826.9	823.5	820.1	816.7
27.5°	802.3	791.5	780.7	772.5	767.1	761.7	756.3	750.9
30°	765.0	753.4	741.8	733.0	726.8	720.7	714.6	708.5
32.5°	727.4	714.2	701.0	691.5	685.7	680.0	674.2	668.5
35°	668.7	654.4	640.1	630.4	625.4	620.4	615.5	610.5
37.5°	611.4	595.7	580.0	569.2	563.5	557.8	552.1	546.4
40°	573.1	557.0	540.9	529.9	524.0	518.1	512.2	506.3
42.5°	534.5	517.8	501.2	490.0	484.3	478.6	472.9	467.1
45°	478.2	462.1	446.0	435.2	429.8	424.3	418.9	413.4
47.5°	423.5	407.5	391.4	381.0	376.0	371.1	366.1	361.2
50°	388.3	372.6	357.0	346.7	342.0	337.2	332.5	327.7
52.5°	355.1	339.9	324.8	315.1	310.7	306.3	301.9	297.5
55°	304.6	290.9	277.3	268.4	264.1	259.7	255.4	251.1
57.5°	258.6	246.2	233.7	225.6	222.0	218.4	214.7	211.1
60°	227.0	215.4	203.8	196.2	192.6	189.0	185.3	181.7
62.5°	199.5	188.4	177.4	170.8	168.6	166.5	164.3	162.1
65°	162.2	154.5	146.8	142.6	141.9	141.2	140.5	139.9
67.5°	130.9	127.4	123.9	121.7	121.0	120.3	119.6	118.8
70°	113.9	111.6	109.3	107.8	106.8	105.9	105.0	104.1
72.5°	99.1	97.2	95.3	94.1	93.5	93.0	92.4	91.9
75°	78.5	76.9	75.3	74.4	74.2	74.0	73.7	73.5
77.5°	59.4	58.5	57.6	57.0	56.6	56.3	55.9	55.5
80°	47.2	46.3	45.4	44.9	44.9	44.9	44.9	44.9
82.5°	35.7	35.1	34.6	34.3	34.3	34.3	34.3	34.3
85°	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4
87.5°	13.1	12.8	12.5	12.4	12.5	12.5	12.6	12.6
90°	34.5	34.1	33.6	33.5	33.8	34.0	34.2	34.4
92.5°	32.4	32.5	32.6	32.6	32.7	32.7	32.8	32.8
95°	64.8	64.8	64.8	64.6	64.1	63.7	63.2	62.8
97.5°	109.0	109.0	109.0	109.0	108.9	108.9	108.8	108.8
100°	139.8	139.8	139.8	139.7	139.4	139.2	139.0	138.8
102.5°	173.4	173.5	173.7	173.7	173.5	173.2	173.0	172.8
105°	223.7	224.2	224.6	224.9	224.9	224.9	224.9	224.9
107.5°	278.1	278.3	278.4	278.0	277.0	275.9	274.9	273.9
110°	315.0	315.0	315.0	314.7	314.0	313.3	312.6	312.0



TEST NUMBER: P331816

CATALOG NUMBER: S122RDIW-S675D970U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	352.0	351.5	350.9	350.4	349.9	349.4	348.9	348.4
115°	408.7	408.5	408.3	407.8	407.2	406.5	405.8	405.1
117.5°	463.6	463.1	462.5	461.9	461.3	460.6	459.9	459.2
120°	500.4	500.4	500.4	500.0	499.3	498.7	498.0	497.3
122.5°	538.2	537.6	537.1	536.6	536.1	535.6	535.1	534.6
125°	594.2	593.5	592.9	592.4	592.2	592.0	591.7	591.5
127.5°	648.6	647.8	647.0	646.2	645.5	644.8	644.1	643.4
130°	685.8	685.4	684.9	684.2	683.3	682.4	681.5	680.6
132.5°	722.0	721.0	720.0	719.2	718.5	717.7	717.0	716.3
135°	775.4	775.2	774.9	774.5	773.8	773.1	772.5	771.8
137.5°	826.5	826.4	826.2	825.6	824.7	823.8	822.9	822.0
140°	860.9	860.9	860.9	860.5	859.6	858.7	857.8	856.9
142.5°	892.1	892.3	892.4	892.1	891.2	890.3	889.4	888.5
145°	939.4	939.6	939.8	939.5	938.6	937.7	936.8	935.9
147.5°	980.8	981.3	981.8	981.6	980.8	979.9	979.1	978.2
150°	1007.1	1007.8	1008.5	1008.5	1007.8	1007.1	1006.4	1005.8
152.5°	1033.4	1034.3	1035.1	1035.1	1034.3	1033.4	1032.5	1031.7
155°	1066.8	1067.9	1069.0	1069.2	1068.6	1067.9	1067.2	1066.5
157.5°	1097.6	1099.1	1100.6	1100.8	1099.8	1098.7	1097.6	1096.5
160°	1115.8	1117.2	1118.5	1118.8	1117.9	1117.0	1116.1	1115.2
162.5°	1132.4	1133.9	1135.5	1135.7	1134.6	1133.5	1132.4	1131.4
165°	1153.8	1155.3	1156.9	1157.1	1156.0	1154.9	1153.8	1152.6
167.5°	1171.4	1173.0	1174.5	1174.7	1173.6	1172.4	1171.2	1170.1
170°	1181.1	1182.7	1184.3	1184.4	1183.0	1181.7	1180.3	1179.0
172.5°	1188.4	1190.0	1191.5	1191.7	1190.3	1189.0	1187.6	1186.3
175°	1196.3	1197.9	1199.4	1199.6	1198.2	1196.9	1195.5	1194.2
177.5°	1200.0	1201.0	1202.1	1202.1	1201.0	1200.0	1198.9	1197.8
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2

(END OF REPORT)