

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331841

Luminaire Tested: **S122RDIW-S865D1440U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331841
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S865D1440U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9065.1 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331841

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331841

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36					36			
1	95	91	88	84	86	83	80	77	67	65	63	53	51	50	39	39	38	32					32			
2	87	80	75	70	79	73	68	64	60	56	53	47	45	43	35	34	33	28					28			
3	80	71	64	59	72	65	59	54	53	49	45	42	39	37	32	30	29	24					24			
4	73	63	56	50	66	58	52	47	48	43	39	38	35	32	29	27	25	21					21			
5	68	57	49	43	61	52	45	40	43	38	34	34	31	28	26	24	22	19					19			
6	62	51	43	38	57	47	40	35	39	34	30	31	28	25	24	22	20	17					17			
7	58	46	39	33	52	42	36	31	35	30	27	29	25	22	22	20	18	15					15			
8	54	42	35	30	49	39	32	28	32	27	24	26	23	20	21	18	16	14					14			
9	50	39	31	27	46	36	29	25	30	25	22	24	21	18	19	17	15	13					13			
10	47	35	29	24	43	33	27	23	27	23	20	23	19	17	18	16	14	12					12			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30832	30832	30832	30832
5°	34434	31024	27509	31024
10°	38203	30808	23845	30808
15°	40082	30355	18788	30355
20°	34749	29687	16258	29687
25°	22789	28771	14516	28771
30°	15340	27660	13136	27660
35°	12423	26260	11848	26260
40°	11049	24738	10964	24738
45°	9999	22952	9787	22952
50°	9100	21182	9065	21182
55°	8555	19220	8442	19220
60°	7156	17418	7072	17418
65°	6032	15817	6842	15817
70°	5575	14124	6453	14124
75°	5215	12296	5958	12296
80°	4816	10116	5309	10116
85°	4428	7984	4668	7984



TEST NUMBER: P331841

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	2.0
10°-20°	504.4	5.6
20°-30°	650.0	7.2
30°-40°	617.7	6.8
40°-50°	529.1	5.8
50°-60°	402.9	4.4
60°-70°	254.7	2.8
70°-80°	127.2	1.4
80°-90°	38.0	0.4
90°-100°	65.6	0.7
100°-110°	240.4	2.7
110°-120°	642.7	7.1
120°-130°	1060.9	11.7
130°-140°	1128.3	12.4
140°-150°	1048.7	11.6
150°-160°	843.1	9.3
160°-170°	543.3	6.0
170°-180°	187.0	2.1
0°-30°	1335.4	14.7
0°-40°	1953.1	21.5
0°-60°	2885.1	31.8
0°-90°	3305.0	36.5
90°-120°	948.7	10.5
90°-150°	4186.6	46.2
90°-180°	5760.0	63.5
0°-180°	9065.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1910	1910	1910	1910	1910	
5°	2125	1914	1697	1914	2125	210
15°	2398	1816	1124	1816	2398	647
25°	1279	1615	815	1615	1279	607
35°	630	1332	601	1332	630	403
45°	438	1005	429	1005	438	339
55°	304	683	300	683	304	267
65°	158	414	179	414	158	161
75°	84	197	96	197	84	89
85°	24	43	25	43	24	27
90°	38	1	38	1	38	18
95°	61	92	61	92	61	57
105°	108	432	108	432	108	112
115°	117	818	117	818	117	292
125°	1216	1156	1216	1156	1216	1052
135°	1478	1431	1478	1431	1478	1139
145°	1685	1660	1685	1660	1685	1054
155°	1829	1828	1829	1828	1829	844
165°	1921	1926	1921	1926	1921	542
175°	1958	1970	1958	1970	1958	187
180°	1966	1966	1966	1966	1966	



TEST NUMBER: P331841

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1987.1	1988.7	1990.3	1986.5	1986.5	1983.4	1976.5	1971.2	1956.3	1954.2	1954.2
5°	2124.6	2123.2	2125.9	2117.3	2105.3	2102.7	2090.1	2073.5	2056.2	2037.0	2033.0
7.5°	2261.2	2259.2	2253.9	2252.5	2243.3	2223.3	2203.0	2181.4	2152.7	2124.7	2110.6
10°	2330.2	2352.1	2338.9	2315.6	2320.3	2289.1	2272.5	2244.0	2220.1	2178.3	2169.0
12.5°	2398.2	2406.8	2402.6	2389.4	2383.5	2361.8	2339.4	2314.6	2270.5	2233.0	2200.3
15°	2397.9	2410.5	2413.8	2409.9	2413.2	2411.9	2399.9	2379.3	2340.9	2299.7	2263.9
17.5°	2220.9	2229.7	2251.4	2266.1	2284.7	2324.0	2343.4	2350.9	2345.2	2321.7	2296.5
20°	2022.4	2007.8	2068.8	2100.0	2126.5	2192.9	2250.0	2271.9	2307.0	2306.4	2299.7
22.5°	1741.0	1744.5	1802.4	1839.4	1916.9	1983.2	2048.3	2130.7	2198.7	2243.7	2270.0
25°	1279.2	1304.5	1362.2	1412.6	1498.9	1622.3	1734.4	1864.5	1987.2	2084.1	2176.3
27.5°	960.8	962.6	1008.4	1055.0	1106.2	1207.3	1348.5	1503.8	1678.8	1823.2	1989.3
30°	822.8	818.8	838.0	866.5	910.3	988.6	1094.8	1247.4	1421.9	1639.5	1833.3
32.5°	725.1	725.3	739.8	760.9	797.3	850.1	922.8	1046.8	1211.7	1425.6	1652.8
35°	630.3	629.7	640.3	655.5	670.8	704.6	754.4	819.4	932.9	1132.6	1364.8
37.5°	562.4	565.3	570.5	580.0	596.9	615.7	645.6	689.3	770.1	888.2	1083.4
40°	524.2	525.5	532.8	540.8	550.7	565.3	589.9	625.0	684.1	778.3	920.9
42.5°	489.1	490.5	495.6	503.1	510.9	525.5	545.8	576.2	624.1	697.6	815.3
45°	437.9	437.9	442.6	445.9	454.5	467.8	484.4	509.6	542.7	597.2	675.5
47.5°	389.9	390.0	393.1	398.8	404.2	414.6	430.9	451.5	475.6	517.7	584.6
50°	362.3	362.9	364.9	369.6	372.9	382.2	394.8	412.7	437.9	470.4	526.2
52.5°	340.0	339.6	342.1	344.1	346.4	353.0	362.4	378.2	400.8	429.0	475.2
55°	303.9	301.2	305.2	308.5	310.5	313.2	318.5	328.4	347.7	371.6	406.1
57.5°	258.8	257.7	260.5	263.5	269.8	276.9	281.5	287.8	297.8	314.9	349.1
60°	221.6	221.6	227.6	229.6	236.9	246.2	255.5	260.8	270.7	282.0	307.2
62.5°	188.7	189.2	192.0	194.0	198.1	209.5	222.5	234.2	243.6	254.4	271.1
65°	157.9	159.2	159.2	160.6	163.2	165.9	171.2	180.5	197.1	212.3	224.9
67.5°	134.0	134.4	134.8	136.2	136.8	139.7	141.9	146.0	149.8	164.3	179.9
70°	118.1	120.1	119.4	120.8	121.4	122.7	125.4	127.4	133.4	136.7	146.0
72.5°	103.2	104.7	104.6	105.4	107.1	107.4	109.5	111.5	115.3	118.1	123.1
75°	83.6	82.9	83.6	84.9	85.6	86.3	86.3	88.9	90.9	93.6	96.9
77.5°	64.5	65.2	65.0	65.2	65.3	66.5	66.4	67.5	69.5	70.9	72.5
80°	51.8	52.4	51.8	52.4	53.1	53.7	53.1	53.7	55.7	57.1	57.1
82.5°	40.1	40.2	40.6	40.7	40.9	41.0	41.9	42.1	43.5	43.3	43.8
85°	23.9	23.2	23.2	23.2	23.9	24.5	23.9	23.9	24.5	24.5	24.5
87.5°	16.2	16.6	16.5	16.3	16.2	16.0	15.7	15.9	15.0	15.2	14.2
90°	38.4	37.8	37.1	36.5	35.9	34.8	33.2	31.6	30.0	28.4	25.9
92.5°	38.4	38.0	37.6	37.3	36.9	36.3	35.5	34.6	33.8	33.0	31.7
95°	61.2	61.5	61.8	62.1	62.4	61.8	60.2	58.6	57.0	55.5	53.3
97.5°	81.6	81.3	80.9	80.5	80.1	79.3	78.0	76.8	75.5	74.2	69.1
100°	95.3	94.7	94.0	93.4	92.8	91.2	88.7	86.1	83.6	81.1	75.7
102.5°	102.1	101.2	100.3	99.5	98.6	96.5	93.2	89.9	86.6	83.3	128.3
105°	108.1	106.8	105.6	104.3	103.0	100.7	97.2	93.7	90.2	86.8	173.0
107.5°	111.2	110.0	108.7	107.4	106.2	107.3	110.8	114.4	117.9	121.5	224.9
110°	112.4	111.1	109.8	108.6	107.3	122.5	154.1	185.7	217.3	248.9	340.2



TEST NUMBER: P331841

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	113.5	112.5	111.5	110.5	109.4	166.6	281.9	397.2	512.5	627.8	650.3
115°	116.6	139.4	162.1	184.9	207.6	292.2	438.5	584.9	731.2	877.5	869.6
117.5°	476.2	550.9	625.7	700.5	775.3	830.4	865.8	901.2	936.6	972.0	966.5
120°	867.6	910.2	952.9	995.6	1038.2	1057.7	1053.9	1050.1	1046.3	1042.5	1036.8
122.5°	1082.6	1090.9	1099.2	1107.4	1115.7	1118.7	1116.5	1114.2	1111.9	1109.6	1103.4
125°	1216.0	1215.1	1214.1	1213.2	1212.2	1210.6	1208.4	1206.2	1204.0	1201.8	1195.8
127.5°	1300.2	1300.0	1299.8	1299.6	1299.5	1297.7	1294.5	1291.3	1288.1	1284.9	1280.4
130°	1352.5	1352.9	1353.2	1353.5	1353.8	1352.2	1348.8	1345.3	1341.8	1338.3	1334.8
132.5°	1403.7	1404.1	1404.4	1404.7	1405.0	1403.7	1400.7	1397.7	1394.8	1391.8	1388.3
135°	1477.7	1478.3	1479.0	1479.6	1480.2	1479.0	1475.8	1472.6	1469.5	1466.3	1463.5
137.5°	1545.1	1546.2	1547.3	1548.3	1549.4	1548.4	1545.3	1542.2	1539.1	1536.0	1532.8
140°	1587.2	1588.8	1590.4	1592.0	1593.5	1592.9	1590.1	1587.2	1584.4	1581.5	1578.1
142.5°	1628.2	1629.8	1631.3	1632.9	1634.5	1634.0	1631.4	1628.8	1626.2	1623.6	1619.6
145°	1685.4	1686.9	1688.5	1690.1	1691.7	1691.4	1689.1	1686.9	1684.7	1682.5	1677.1
147.5°	1735.7	1737.0	1738.4	1739.7	1741.0	1740.9	1739.2	1737.6	1735.9	1734.3	1729.0
150°	1766.4	1768.0	1769.6	1771.2	1772.7	1772.6	1770.7	1768.8	1766.9	1765.0	1759.9
152.5°	1792.6	1794.7	1796.8	1798.8	1800.9	1801.0	1799.1	1797.2	1795.3	1793.4	1788.6
155°	1829.0	1831.5	1834.1	1836.6	1839.1	1839.4	1837.5	1835.6	1833.7	1831.8	1828.1
157.5°	1862.3	1864.7	1867.2	1869.7	1872.1	1872.3	1870.1	1868.0	1865.9	1863.7	1861.0
160°	1881.6	1883.8	1886.0	1888.3	1890.5	1890.6	1888.7	1886.8	1884.9	1883.0	1881.1
162.5°	1897.6	1900.3	1903.0	1905.7	1908.4	1908.7	1906.6	1904.4	1902.3	1900.1	1898.5
165°	1921.4	1923.7	1925.9	1928.1	1930.3	1930.3	1928.1	1925.9	1923.7	1921.4	1920.5
167.5°	1936.5	1939.4	1942.2	1945.1	1947.9	1948.2	1946.0	1943.8	1941.6	1939.4	1938.5
170°	1945.6	1948.5	1951.3	1954.2	1957.0	1957.3	1955.1	1952.9	1950.7	1948.5	1947.8
172.5°	1952.4	1955.3	1958.1	1961.0	1963.8	1964.1	1961.9	1959.7	1957.5	1955.3	1954.7
175°	1958.4	1961.6	1964.7	1967.9	1971.1	1971.5	1969.3	1967.1	1964.9	1962.7	1962.1
177.5°	1962.1	1964.4	1966.7	1968.9	1971.2	1971.5	1969.7	1967.9	1966.2	1964.4	1964.1
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5



TEST NUMBER: P331841

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1955.2	1951.0	1947.3	1937.7	1932.9	1922.3	1920.7	1920.2	1906.4	1893.1	1889.4
5°	2022.4	2011.8	1995.8	1977.3	1958.0	1938.1	1924.8	1914.2	1887.7	1862.5	1847.9
7.5°	2090.1	2067.2	2039.8	2004.6	1975.3	1942.4	1917.9	1896.0	1858.4	1822.3	1798.0
10°	2140.5	2103.3	2066.8	2018.4	1980.6	1943.4	1908.9	1879.1	1836.6	1788.8	1755.0
12.5°	2171.8	2130.9	2080.6	2033.3	1984.3	1937.0	1890.9	1852.5	1802.6	1753.3	1713.0
15°	2214.1	2170.3	2109.3	2041.6	1978.6	1916.9	1863.8	1816.0	1751.0	1691.9	1642.8
17.5°	2248.8	2188.5	2123.0	2044.7	1971.7	1893.3	1824.9	1763.9	1691.5	1620.3	1562.4
20°	2259.9	2200.2	2124.6	2046.3	1960.0	1867.8	1794.1	1727.8	1650.1	1572.5	1506.2
22.5°	2253.0	2206.6	2122.4	2028.7	1940.4	1843.9	1760.7	1683.7	1597.6	1518.4	1441.4
25°	2206.2	2190.2	2110.6	2008.4	1907.6	1795.5	1699.2	1615.0	1516.8	1431.9	1348.2
27.5°	2097.0	2131.3	2082.0	1973.1	1861.0	1740.8	1632.6	1536.7	1434.8	1339.2	1255.9
30°	1991.9	2070.8	2049.6	1948.7	1823.3	1705.2	1583.8	1483.6	1374.8	1276.6	1194.3
32.5°	1848.0	1978.4	1999.2	1914.8	1785.1	1655.3	1528.1	1428.4	1314.8	1211.3	1131.1
35°	1619.0	1814.0	1903.6	1849.9	1719.8	1579.8	1448.4	1332.3	1218.2	1116.0	1036.4
37.5°	1345.7	1611.4	1760.7	1764.5	1645.1	1499.5	1356.5	1241.2	1124.4	1024.1	937.9
40°	1168.4	1456.4	1650.8	1693.9	1593.1	1435.8	1291.2	1173.7	1059.6	961.4	862.6
42.5°	1009.2	1296.1	1535.1	1610.1	1529.9	1373.7	1228.6	1105.8	994.9	902.0	801.0
45°	816.1	1066.9	1330.3	1464.4	1419.9	1275.3	1122.0	1005.2	901.0	820.8	723.9
47.5°	688.5	865.2	1120.1	1301.4	1300.6	1168.6	1017.8	906.0	809.3	734.1	655.7
50°	615.7	769.7	985.3	1191.0	1208.2	1097.4	954.1	843.3	753.1	674.1	611.1
52.5°	550.4	677.3	871.2	1068.4	1117.5	1021.5	882.5	780.2	692.6	620.0	566.0
55°	465.1	563.3	710.6	895.1	969.4	901.7	778.3	682.8	611.8	550.7	504.3
57.5°	393.5	467.1	585.3	733.8	820.4	777.8	676.0	598.4	537.6	482.4	445.7
60°	348.3	408.7	508.9	633.0	728.5	698.7	611.8	539.4	487.7	439.9	405.4
62.5°	305.9	357.8	443.6	544.3	631.9	619.6	548.6	487.9	442.6	399.0	369.8
65°	246.2	284.0	351.0	430.0	500.3	506.3	455.2	414.0	373.6	339.1	313.2
67.5°	196.0	220.7	267.9	334.4	387.1	405.9	374.7	343.3	311.2	284.5	262.1
70°	165.2	185.1	219.6	273.4	321.8	341.7	323.8	299.2	271.4	249.5	230.2
72.5°	133.9	153.3	178.7	218.2	259.7	281.2	275.0	257.3	234.7	216.6	198.4
75°	100.9	106.8	124.1	150.6	183.1	201.7	206.4	197.1	179.1	165.2	154.6
77.5°	74.6	78.2	86.4	100.3	121.6	138.1	144.9	143.8	131.5	123.4	113.5
80°	59.7	61.7	65.7	71.7	87.6	104.2	108.8	108.8	100.2	96.9	86.9
82.5°	45.4	46.8	49.2	52.5	60.0	74.4	79.6	80.7	75.2	70.9	63.0
85°	25.9	25.2	26.5	28.5	29.9	33.8	41.8	43.1	41.8	36.5	34.5
87.5°	13.7	13.7	13.2	12.1	11.9	11.8	13.7	15.7	14.2	13.4	13.0
90°	23.4	20.9	18.3	15.3	11.9	8.4	4.9	1.4	4.9	8.4	11.9
92.5°	30.5	29.2	27.9	27.5	27.8	28.1	28.4	28.7	28.4	28.1	27.8
95°	51.0	48.8	46.6	50.7	61.2	71.6	82.0	92.4	82.0	71.6	61.2
97.5°	64.0	58.9	53.8	65.9	95.3	124.7	154.1	183.5	154.1	124.7	95.3
100°	70.3	64.9	59.6	78.5	121.8	165.1	208.4	251.7	208.4	165.1	121.8
102.5°	173.2	218.2	263.1	290.2	299.3	308.5	317.7	326.8	317.7	308.5	299.3
105°	259.3	345.6	431.9	470.3	460.8	451.3	441.8	432.4	441.8	451.3	460.8
107.5°	328.4	431.9	535.4	583.3	575.6	568.0	560.3	552.7	560.3	568.0	575.6
110°	431.6	522.9	614.2	656.6	650.0	643.3	636.7	630.1	636.7	643.3	650.0



TEST NUMBER: P331841

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	672.9	695.5	718.0	726.4	720.5	714.6	708.7	702.9	708.7	714.6	720.5
115°	861.7	853.8	845.9	839.3	833.9	828.5	823.2	817.8	823.2	828.5	833.9
117.5°	961.1	955.6	950.2	944.5	938.5	932.5	926.5	920.5	926.5	932.5	938.5
120°	1031.1	1025.4	1019.7	1014.5	1009.8	1005.0	1000.3	995.6	1000.3	1005.0	1009.8
122.5°	1097.2	1091.0	1084.9	1079.3	1074.3	1069.3	1064.3	1059.3	1064.3	1069.3	1074.3
125°	1189.8	1183.8	1177.8	1172.7	1168.6	1164.5	1160.4	1156.3	1160.4	1164.5	1168.6
127.5°	1275.9	1271.4	1266.9	1262.4	1257.8	1253.3	1248.7	1244.2	1248.7	1253.3	1257.8
130°	1331.4	1327.9	1324.4	1320.2	1315.1	1310.0	1305.0	1299.9	1305.0	1310.0	1315.1
132.5°	1384.8	1381.4	1377.9	1374.0	1369.7	1365.4	1361.1	1356.8	1361.1	1365.4	1369.7
135°	1460.6	1457.8	1454.9	1451.0	1445.9	1440.9	1435.8	1430.8	1435.8	1440.9	1445.9
137.5°	1529.6	1526.3	1523.1	1519.7	1516.2	1512.7	1509.1	1505.6	1509.1	1512.7	1516.2
140°	1574.6	1571.1	1567.6	1564.6	1562.1	1559.6	1557.0	1554.5	1557.0	1559.6	1562.1
142.5°	1615.7	1611.7	1607.7	1604.6	1602.3	1600.0	1597.7	1595.5	1597.7	1600.0	1602.3
145°	1671.8	1666.4	1661.0	1658.5	1658.8	1659.1	1659.4	1659.8	1659.4	1659.1	1658.8
147.5°	1723.7	1718.3	1713.0	1711.0	1712.2	1713.4	1714.6	1715.8	1714.6	1713.4	1712.2
150°	1754.9	1749.8	1744.8	1743.3	1745.6	1747.8	1750.0	1752.2	1750.0	1747.8	1745.6
152.5°	1783.8	1779.0	1774.2	1773.1	1775.5	1778.0	1780.5	1782.9	1780.5	1778.0	1775.5
155°	1824.3	1820.5	1816.7	1816.2	1819.0	1821.9	1824.7	1827.6	1824.7	1821.9	1819.0
157.5°	1858.4	1855.7	1853.1	1853.0	1855.4	1857.8	1860.2	1862.6	1860.2	1857.8	1855.4
160°	1879.3	1877.4	1875.5	1875.5	1877.4	1879.3	1881.1	1883.0	1881.1	1879.3	1877.4
162.5°	1896.8	1895.2	1893.5	1893.7	1895.6	1897.5	1899.4	1901.2	1899.4	1897.5	1895.6
165°	1919.5	1918.6	1917.7	1918.1	1920.0	1921.9	1923.8	1925.7	1923.8	1921.9	1920.0
167.5°	1937.6	1936.7	1935.8	1936.3	1938.2	1940.1	1942.0	1943.9	1942.0	1940.1	1938.2
170°	1947.2	1946.6	1945.9	1946.6	1948.5	1950.4	1952.3	1954.2	1952.3	1950.4	1948.5
172.5°	1954.0	1953.4	1952.8	1953.4	1955.3	1957.2	1959.1	1961.0	1959.1	1957.2	1955.3
175°	1961.4	1960.8	1960.2	1961.0	1963.2	1965.4	1967.6	1969.8	1967.6	1965.4	1963.2
177.5°	1963.9	1963.6	1963.4	1964.1	1965.9	1967.7	1969.5	1971.2	1969.5	1967.7	1965.9
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5



TEST NUMBER: P331841

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1882.5	1878.8	1871.9	1861.3	1854.9	1843.8	1836.3	1840.6	1841.6	1840.6	1839.5
5°	1831.9	1818.0	1798.8	1780.2	1762.9	1744.4	1733.7	1729.1	1719.8	1714.5	1711.9
7.5°	1770.8	1746.8	1719.5	1687.2	1659.7	1630.9	1616.2	1608.9	1589.9	1579.5	1570.5
10°	1725.1	1687.3	1660.1	1617.6	1591.8	1553.9	1528.1	1528.7	1502.8	1488.2	1477.6
12.5°	1674.7	1633.2	1587.9	1549.7	1513.7	1483.3	1452.2	1439.5	1412.1	1398.0	1369.3
15°	1591.1	1542.7	1494.9	1443.1	1406.6	1359.5	1314.4	1259.3	1214.9	1176.4	1165.8
17.5°	1499.8	1439.8	1391.9	1331.1	1268.6	1189.4	1137.1	1105.1	1078.3	1058.0	1042.9
20°	1437.2	1376.1	1325.0	1233.5	1149.2	1095.5	1057.0	1032.4	1004.6	982.7	970.7
22.5°	1371.3	1307.6	1238.0	1135.8	1070.1	1027.0	992.7	964.5	945.6	928.5	917.6
25°	1277.9	1208.2	1093.5	1023.1	970.0	924.9	901.0	883.8	863.9	840.7	830.0
27.5°	1179.2	1068.4	986.0	933.7	883.0	853.7	832.2	806.4	788.6	778.2	767.1
30°	1105.4	994.6	930.2	873.2	837.3	804.8	779.6	765.0	747.8	729.9	722.6
32.5°	1023.1	934.6	872.9	825.4	789.0	761.3	741.4	717.8	705.3	694.3	679.0
35°	920.9	853.9	797.5	759.1	724.6	702.0	678.8	664.8	642.3	633.0	627.0
37.5°	834.4	776.3	734.2	693.6	666.3	641.3	627.1	605.0	595.2	582.3	569.7
40°	785.6	728.5	688.1	654.9	624.4	605.8	587.9	570.0	555.4	549.4	534.1
42.5°	735.7	689.3	648.8	612.4	592.0	572.3	549.7	536.5	521.4	511.7	502.3
45°	666.8	625.7	591.2	561.3	538.8	518.2	503.6	481.7	473.1	453.8	445.9
47.5°	606.3	568.1	535.2	506.8	484.8	471.4	450.0	432.9	419.1	407.3	397.0
50°	563.3	531.5	499.6	474.4	454.5	435.3	413.4	404.7	383.5	377.5	371.6
52.5°	524.0	493.8	464.6	439.9	420.0	401.3	382.0	370.8	356.4	350.5	346.1
55°	469.1	439.9	412.0	390.1	370.2	351.0	339.1	325.1	318.5	313.8	308.5
57.5°	413.9	387.6	366.3	344.1	324.1	308.8	295.0	286.6	279.7	273.6	267.3
60°	378.9	353.6	334.4	313.8	293.3	280.7	270.0	260.1	252.1	242.8	240.2
62.5°	341.7	319.7	302.0	282.0	264.1	252.5	242.4	233.0	223.5	209.9	206.2
65°	290.6	273.4	254.8	238.2	222.3	211.0	196.4	185.8	181.8	180.5	179.8
67.5°	244.4	228.1	212.2	195.2	180.7	170.3	162.8	161.2	158.4	157.6	155.8
70°	213.6	198.4	182.5	166.5	152.6	150.6	148.0	145.3	142.0	140.7	139.3
72.5°	186.0	170.3	154.3	141.6	135.6	133.1	130.4	127.8	125.5	124.2	123.4
75°	142.7	128.1	117.4	112.8	109.5	107.5	103.5	101.5	100.2	98.2	97.5
77.5°	102.7	94.5	89.6	86.7	83.2	81.1	78.8	76.8	75.4	75.0	73.9
80°	78.3	74.3	71.0	67.0	65.7	63.0	62.4	60.4	61.0	59.1	59.1
82.5°	60.8	55.7	52.9	51.1	49.8	47.6	47.0	46.0	46.2	44.7	44.7
85°	31.2	29.9	28.5	27.2	27.2	25.2	25.9	25.2	25.2	23.9	23.2
87.5°	13.2	13.2	12.7	13.2	13.7	13.7	14.0	13.8	14.1	14.4	14.1
90°	15.3	18.3	20.9	23.4	25.9	28.4	30.0	31.6	33.2	34.8	35.9
92.5°	27.5	27.9	29.2	30.5	31.7	33.0	33.8	34.6	35.5	36.3	36.9
95°	50.7	46.6	48.8	51.0	53.3	55.5	57.0	58.6	60.2	61.8	62.4
97.5°	65.9	53.8	58.9	64.0	69.1	74.2	75.5	76.8	78.0	79.3	80.1
100°	78.5	59.6	64.9	70.3	75.7	81.1	83.6	86.1	88.7	91.2	92.8
102.5°	290.2	263.1	218.2	173.2	128.3	83.3	86.6	89.9	93.2	96.5	98.6
105°	470.3	431.9	345.6	259.3	173.0	86.8	90.2	93.7	97.2	100.7	103.0
107.5°	583.3	535.4	431.9	328.4	224.9	121.5	117.9	114.4	110.8	107.3	106.2
110°	656.6	614.2	522.9	431.6	340.2	248.9	217.3	185.7	154.1	122.5	107.3



TEST NUMBER: P331841

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	726.4	718.0	695.5	672.9	650.3	627.8	512.5	397.2	281.9	166.6	109.4
115°	839.3	845.9	853.8	861.7	869.6	877.5	731.2	584.9	438.5	292.2	207.6
117.5°	944.5	950.2	955.6	961.1	966.5	972.0	936.6	901.2	865.8	830.4	775.3
120°	1014.5	1019.7	1025.4	1031.1	1036.8	1042.5	1046.3	1050.1	1053.9	1057.7	1038.2
122.5°	1079.3	1084.9	1091.0	1097.2	1103.4	1109.6	1111.9	1114.2	1116.5	1118.7	1115.7
125°	1172.7	1177.8	1183.8	1189.8	1195.8	1201.8	1204.0	1206.2	1208.4	1210.6	1212.2
127.5°	1262.4	1266.9	1271.4	1275.9	1280.4	1284.9	1288.1	1291.3	1294.5	1297.7	1299.5
130°	1320.2	1324.4	1327.9	1331.4	1334.8	1338.3	1341.8	1345.3	1348.8	1352.2	1353.8
132.5°	1374.0	1377.9	1381.4	1384.8	1388.3	1391.8	1394.8	1397.7	1400.7	1403.7	1405.0
135°	1451.0	1454.9	1457.8	1460.6	1463.5	1466.3	1469.5	1472.6	1475.8	1479.0	1480.2
137.5°	1519.7	1523.1	1526.3	1529.6	1532.8	1536.0	1539.1	1542.2	1545.3	1548.4	1549.4
140°	1564.6	1567.6	1571.1	1574.6	1578.1	1581.5	1584.4	1587.2	1590.1	1592.9	1593.5
142.5°	1604.6	1607.7	1611.7	1615.7	1619.6	1623.6	1626.2	1628.8	1631.4	1634.0	1634.5
145°	1658.5	1661.0	1666.4	1671.8	1677.1	1682.5	1684.7	1686.9	1689.1	1691.4	1691.7
147.5°	1711.0	1713.0	1718.3	1723.7	1729.0	1734.3	1735.9	1737.6	1739.2	1740.9	1741.0
150°	1743.3	1744.8	1749.8	1754.9	1759.9	1765.0	1766.9	1768.8	1770.7	1772.6	1772.7
152.5°	1773.1	1774.2	1779.0	1783.8	1788.6	1793.4	1795.3	1797.2	1799.1	1801.0	1800.9
155°	1816.2	1816.7	1820.5	1824.3	1828.1	1831.8	1833.7	1835.6	1837.5	1839.4	1839.1
157.5°	1853.0	1853.1	1855.7	1858.4	1861.0	1863.7	1865.9	1868.0	1870.1	1872.3	1872.1
160°	1875.5	1875.5	1877.4	1879.3	1881.1	1883.0	1884.9	1886.8	1888.7	1890.6	1890.5
162.5°	1893.7	1893.5	1895.2	1896.8	1898.5	1900.1	1902.3	1904.4	1906.6	1908.7	1908.4
165°	1918.1	1917.7	1918.6	1919.5	1920.5	1921.4	1923.7	1925.9	1928.1	1930.3	1930.3
167.5°	1936.3	1935.8	1936.7	1937.6	1938.5	1939.4	1941.6	1943.8	1946.0	1948.2	1947.9
170°	1946.6	1945.9	1946.6	1947.2	1947.8	1948.5	1950.7	1952.9	1955.1	1957.3	1957.0
172.5°	1953.4	1952.8	1953.4	1954.0	1954.7	1955.3	1957.5	1959.7	1961.9	1964.1	1963.8
175°	1961.0	1960.2	1960.8	1961.4	1962.1	1962.7	1964.9	1967.1	1969.3	1971.5	1971.1
177.5°	1964.1	1963.4	1963.6	1963.9	1964.1	1964.4	1966.2	1967.9	1969.7	1971.5	1971.2
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5



TEST NUMBER: P331841

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1833.7	1834.7	1833.1	1834.2	1833.1	1834.7	1833.7	1839.5	1840.6	1841.6	1840.6
5°	1708.5	1700.6	1699.2	1697.3	1699.2	1700.6	1708.5	1711.9	1714.5	1719.8	1729.1
7.5°	1559.1	1557.9	1554.6	1550.0	1554.6	1557.9	1559.1	1570.5	1579.5	1589.9	1608.9
10°	1463.0	1459.7	1459.1	1454.4	1459.1	1459.7	1463.0	1477.6	1488.2	1502.8	1528.7
12.5°	1350.5	1329.1	1326.9	1315.3	1326.9	1329.1	1350.5	1369.3	1398.0	1412.1	1439.5
15°	1149.9	1145.9	1132.6	1124.0	1132.6	1145.9	1149.9	1165.8	1176.4	1214.9	1259.3
17.5°	1035.2	1022.2	1018.1	1016.2	1018.1	1022.2	1035.2	1042.9	1058.0	1078.3	1105.1
20°	961.4	949.5	947.5	946.2	947.5	949.5	961.4	970.7	982.7	1004.6	1032.4
22.5°	910.5	898.0	892.8	888.8	892.8	898.0	910.5	917.6	928.5	945.6	964.5
25°	823.4	818.8	816.1	814.8	816.1	818.8	823.4	830.0	840.7	863.9	883.8
27.5°	755.3	745.1	743.1	739.7	743.1	745.1	755.3	767.1	778.2	788.6	806.4
30°	716.6	713.3	708.6	704.6	708.6	713.3	716.6	722.6	729.9	747.8	765.0
32.5°	670.9	668.2	664.0	662.2	664.0	668.2	670.9	679.0	694.3	705.3	717.8
35°	620.4	611.1	607.1	601.1	607.1	611.1	620.4	627.0	633.0	642.3	664.8
37.5°	566.9	562.0	556.4	558.4	556.4	562.0	566.9	569.7	582.3	595.2	605.0
40°	525.5	522.2	520.9	520.2	520.9	522.2	525.5	534.1	549.4	555.4	570.0
42.5°	492.6	483.4	480.0	479.8	480.0	483.4	492.6	502.3	511.7	521.4	536.5
45°	442.6	433.9	428.0	428.6	428.0	433.9	442.6	445.9	453.8	473.1	481.7
47.5°	391.3	391.1	387.4	388.6	387.4	391.1	391.3	397.0	407.3	419.1	432.9
50°	366.9	362.9	360.3	360.9	360.3	362.9	366.9	371.6	377.5	383.5	404.7
52.5°	343.6	340.1	338.0	340.8	338.0	340.1	343.6	346.1	350.5	356.4	370.8
55°	305.2	301.2	300.6	299.9	300.6	301.2	305.2	308.5	313.8	318.5	325.1
57.5°	262.4	259.7	255.7	254.0	255.7	259.7	262.4	267.3	273.6	279.7	286.6
60°	231.6	226.3	219.6	219.0	219.6	226.3	231.6	240.2	242.8	252.1	260.1
62.5°	203.4	202.4	201.0	200.9	201.0	202.4	203.4	206.2	209.9	223.5	233.0
65°	178.5	177.8	178.5	179.1	178.5	177.8	178.5	179.8	180.5	181.8	185.8
67.5°	155.5	154.3	153.1	153.7	153.1	154.3	155.5	155.8	157.6	158.4	161.2
70°	138.0	137.3	136.7	136.7	136.7	137.3	138.0	139.3	140.7	142.0	145.3
72.5°	121.0	120.9	120.2	119.7	120.2	120.9	121.0	123.4	124.2	125.5	127.8
75°	96.9	95.5	95.5	95.5	95.5	95.5	96.9	97.5	98.2	100.2	101.5
77.5°	73.8	73.1	72.5	71.9	72.5	73.1	73.8	73.9	75.0	75.4	76.8
80°	58.4	57.7	57.1	57.1	57.1	57.7	58.4	59.1	59.1	61.0	60.4
82.5°	44.6	43.9	43.8	43.3	43.8	43.9	44.6	44.7	44.7	46.2	46.0
85°	23.9	24.5	23.9	25.2	23.9	24.5	23.9	23.2	23.9	25.2	25.2
87.5°	14.2	13.8	14.5	14.0	14.5	13.8	14.2	14.1	14.4	14.1	13.8
90°	36.5	37.1	37.8	38.4	37.8	37.1	36.5	35.9	34.8	33.2	31.6
92.5°	37.3	37.6	38.0	38.4	38.0	37.6	37.3	36.9	36.3	35.5	34.6
95°	62.1	61.8	61.5	61.2	61.5	61.8	62.1	62.4	61.8	60.2	58.6
97.5°	80.5	80.9	81.3	81.6	81.3	80.9	80.5	80.1	79.3	78.0	76.8
100°	93.4	94.0	94.7	95.3	94.7	94.0	93.4	92.8	91.2	88.7	86.1
102.5°	99.5	100.3	101.2	102.1	101.2	100.3	99.5	98.6	96.5	93.2	89.9
105°	104.3	105.6	106.8	108.1	106.8	105.6	104.3	103.0	100.7	97.2	93.7
107.5°	107.4	108.7	110.0	111.2	110.0	108.7	107.4	106.2	107.3	110.8	114.4
110°	108.6	109.8	111.1	112.4	111.1	109.8	108.6	107.3	122.5	154.1	185.7



TEST NUMBER: P331841

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	110.5	111.5	112.5	113.5	112.5	111.5	110.5	109.4	166.6	281.9	397.2
115°	184.9	162.1	139.4	116.6	139.4	162.1	184.9	207.6	292.2	438.5	584.9
117.5°	700.5	625.7	550.9	476.2	550.9	625.7	700.5	775.3	830.4	865.8	901.2
120°	995.6	952.9	910.2	867.6	910.2	952.9	995.6	1038.2	1057.7	1053.9	1050.1
122.5°	1107.4	1099.2	1090.9	1082.6	1090.9	1099.2	1107.4	1115.7	1118.7	1116.5	1114.2
125°	1213.2	1214.1	1215.1	1216.0	1215.1	1214.1	1213.2	1212.2	1210.6	1208.4	1206.2
127.5°	1299.6	1299.8	1300.0	1300.2	1300.0	1299.8	1299.6	1299.5	1297.7	1294.5	1291.3
130°	1353.5	1353.2	1352.9	1352.5	1352.9	1353.2	1353.5	1353.8	1352.2	1348.8	1345.3
132.5°	1404.7	1404.4	1404.1	1403.7	1404.1	1404.4	1404.7	1405.0	1403.7	1400.7	1397.7
135°	1479.6	1479.0	1478.3	1477.7	1478.3	1479.0	1479.6	1480.2	1479.0	1475.8	1472.6
137.5°	1548.3	1547.3	1546.2	1545.1	1546.2	1547.3	1548.3	1549.4	1548.4	1545.3	1542.2
140°	1592.0	1590.4	1588.8	1587.2	1588.8	1590.4	1592.0	1593.5	1592.9	1590.1	1587.2
142.5°	1632.9	1631.3	1629.8	1628.2	1629.8	1631.3	1632.9	1634.5	1634.0	1631.4	1628.8
145°	1690.1	1688.5	1686.9	1685.4	1686.9	1688.5	1690.1	1691.7	1691.4	1689.1	1686.9
147.5°	1739.7	1738.4	1737.0	1735.7	1737.0	1738.4	1739.7	1741.0	1740.9	1739.2	1737.6
150°	1771.2	1769.6	1768.0	1766.4	1768.0	1769.6	1771.2	1772.7	1772.6	1770.7	1768.8
152.5°	1798.8	1796.8	1794.7	1792.6	1794.7	1796.8	1798.8	1800.9	1801.0	1799.1	1797.2
155°	1836.6	1834.1	1831.5	1829.0	1831.5	1834.1	1836.6	1839.1	1839.4	1837.5	1835.6
157.5°	1869.7	1867.2	1864.7	1862.3	1864.7	1867.2	1869.7	1872.1	1872.3	1870.1	1868.0
160°	1888.3	1886.0	1883.8	1881.6	1883.8	1886.0	1888.3	1890.5	1890.6	1888.7	1886.8
162.5°	1905.7	1903.0	1900.3	1897.6	1900.3	1903.0	1905.7	1908.4	1908.7	1906.6	1904.4
165°	1928.1	1925.9	1923.7	1921.4	1923.7	1925.9	1928.1	1930.3	1930.3	1928.1	1925.9
167.5°	1945.1	1942.2	1939.4	1936.5	1939.4	1942.2	1945.1	1947.9	1948.2	1946.0	1943.8
170°	1954.2	1951.3	1948.5	1945.6	1948.5	1951.3	1954.2	1957.0	1957.3	1955.1	1952.9
172.5°	1961.0	1958.1	1955.3	1952.4	1955.3	1958.1	1961.0	1963.8	1964.1	1961.9	1959.7
175°	1967.9	1964.7	1961.6	1958.4	1961.6	1964.7	1967.9	1971.1	1971.5	1969.3	1967.1
177.5°	1968.9	1966.7	1964.4	1962.1	1964.4	1966.7	1968.9	1971.2	1971.5	1969.7	1967.9
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5



TEST NUMBER: P331841

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1836.3	1843.8	1854.9	1861.3	1871.9	1878.8	1882.5	1889.4	1893.1	1906.4	1920.2
5°	1733.7	1744.4	1762.9	1780.2	1798.8	1818.0	1831.9	1847.9	1862.5	1887.7	1914.2
7.5°	1616.2	1630.9	1659.7	1687.2	1719.5	1746.8	1770.8	1798.0	1822.3	1858.4	1896.0
10°	1528.1	1553.9	1591.8	1617.6	1660.1	1687.3	1725.1	1755.0	1788.8	1836.6	1879.1
12.5°	1452.2	1483.3	1513.7	1549.7	1587.9	1633.2	1674.7	1713.0	1753.3	1802.6	1852.5
15°	1314.4	1359.5	1406.6	1443.1	1494.9	1542.7	1591.1	1642.8	1691.9	1751.0	1816.0
17.5°	1137.1	1189.4	1268.6	1331.1	1391.9	1439.8	1499.8	1562.4	1620.3	1691.5	1763.9
20°	1057.0	1095.5	1149.2	1233.5	1325.0	1376.1	1437.2	1506.2	1572.5	1650.1	1727.8
22.5°	992.7	1027.0	1070.1	1135.8	1238.0	1307.6	1371.3	1441.4	1518.4	1597.6	1683.7
25°	901.0	924.9	970.0	1023.1	1093.5	1208.2	1277.9	1348.2	1431.9	1516.8	1615.0
27.5°	832.2	853.7	883.0	933.7	986.0	1068.4	1179.2	1255.9	1339.2	1434.8	1536.7
30°	779.6	804.8	837.3	873.2	930.2	994.6	1105.4	1194.3	1276.6	1374.8	1483.6
32.5°	741.4	761.3	789.0	825.4	872.9	934.6	1023.1	1131.1	1211.3	1314.8	1428.4
35°	678.8	702.0	724.6	759.1	797.5	853.9	920.9	1036.4	1116.0	1218.2	1332.3
37.5°	627.1	641.3	666.3	693.6	734.2	776.3	834.4	937.9	1024.1	1124.4	1241.2
40°	587.9	605.8	624.4	654.9	688.1	728.5	785.6	862.6	961.4	1059.6	1173.7
42.5°	549.7	572.3	592.0	612.4	648.8	689.3	735.7	801.0	902.0	994.9	1105.8
45°	503.6	518.2	538.8	561.3	591.2	625.7	666.8	723.9	820.8	901.0	1005.2
47.5°	450.0	471.4	484.8	506.8	535.2	568.1	606.3	655.7	734.1	809.3	906.0
50°	413.4	435.3	454.5	474.4	499.6	531.5	563.3	611.1	674.1	753.1	843.3
52.5°	382.0	401.3	420.0	439.9	464.6	493.8	524.0	566.0	620.0	692.6	780.2
55°	339.1	351.0	370.2	390.1	412.0	439.9	469.1	504.3	550.7	611.8	682.8
57.5°	295.0	308.8	324.1	344.1	366.3	387.6	413.9	445.7	482.4	537.6	598.4
60°	270.0	280.7	293.3	313.8	334.4	353.6	378.9	405.4	439.9	487.7	539.4
62.5°	242.4	252.5	264.1	282.0	302.0	319.7	341.7	369.8	399.0	442.6	487.9
65°	196.4	211.0	222.3	238.2	254.8	273.4	290.6	313.2	339.1	373.6	414.0
67.5°	162.8	170.3	180.7	195.2	212.2	228.1	244.4	262.1	284.5	311.2	343.3
70°	148.0	150.6	152.6	166.5	182.5	198.4	213.6	230.2	249.5	271.4	299.2
72.5°	130.4	133.1	135.6	141.6	154.3	170.3	186.0	198.4	216.6	234.7	257.3
75°	103.5	107.5	109.5	112.8	117.4	128.1	142.7	154.6	165.2	179.1	197.1
77.5°	78.8	81.1	83.2	86.7	89.6	94.5	102.7	113.5	123.4	131.5	143.8
80°	62.4	63.0	65.7	67.0	71.0	74.3	78.3	86.9	96.9	100.2	108.8
82.5°	47.0	47.6	49.8	51.1	52.9	55.7	60.8	63.0	70.9	75.2	80.7
85°	25.9	25.2	27.2	27.2	28.5	29.9	31.2	34.5	36.5	41.8	43.1
87.5°	14.0	13.7	13.7	13.2	12.7	13.2	13.2	13.0	13.4	14.2	15.7
90°	30.0	28.4	25.9	23.4	20.9	18.3	15.3	11.9	8.4	4.9	1.4
92.5°	33.8	33.0	31.7	30.5	29.2	27.9	27.5	27.8	28.1	28.4	28.7
95°	57.0	55.5	53.3	51.0	48.8	46.6	50.7	61.2	71.6	82.0	92.4
97.5°	75.5	74.2	69.1	64.0	58.9	53.8	65.9	95.3	124.7	154.1	183.5
100°	83.6	81.1	75.7	70.3	64.9	59.6	78.5	121.8	165.1	208.4	251.7
102.5°	86.6	83.3	128.3	173.2	218.2	263.1	290.2	299.3	308.5	317.7	326.8
105°	90.2	86.8	173.0	259.3	345.6	431.9	470.3	460.8	451.3	441.8	432.4
107.5°	117.9	121.5	224.9	328.4	431.9	535.4	583.3	575.6	568.0	560.3	552.7
110°	217.3	248.9	340.2	431.6	522.9	614.2	656.6	650.0	643.3	636.7	630.1



TEST NUMBER: P331841

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	512.5	627.8	650.3	672.9	695.5	718.0	726.4	720.5	714.6	708.7	702.9
115°	731.2	877.5	869.6	861.7	853.8	845.9	839.3	833.9	828.5	823.2	817.8
117.5°	936.6	972.0	966.5	961.1	955.6	950.2	944.5	938.5	932.5	926.5	920.5
120°	1046.3	1042.5	1036.8	1031.1	1025.4	1019.7	1014.5	1009.8	1005.0	1000.3	995.6
122.5°	1111.9	1109.6	1103.4	1097.2	1091.0	1084.9	1079.3	1074.3	1069.3	1064.3	1059.3
125°	1204.0	1201.8	1195.8	1189.8	1183.8	1177.8	1172.7	1168.6	1164.5	1160.4	1156.3
127.5°	1288.1	1284.9	1280.4	1275.9	1271.4	1266.9	1262.4	1257.8	1253.3	1248.7	1244.2
130°	1341.8	1338.3	1334.8	1331.4	1327.9	1324.4	1320.2	1315.1	1310.0	1305.0	1299.9
132.5°	1394.8	1391.8	1388.3	1384.8	1381.4	1377.9	1374.0	1369.7	1365.4	1361.1	1356.8
135°	1469.5	1466.3	1463.5	1460.6	1457.8	1454.9	1451.0	1445.9	1440.9	1435.8	1430.8
137.5°	1539.1	1536.0	1532.8	1529.6	1526.3	1523.1	1519.7	1516.2	1512.7	1509.1	1505.6
140°	1584.4	1581.5	1578.1	1574.6	1571.1	1567.6	1564.6	1562.1	1559.6	1557.0	1554.5
142.5°	1626.2	1623.6	1619.6	1615.7	1611.7	1607.7	1604.6	1602.3	1600.0	1597.7	1595.5
145°	1684.7	1682.5	1677.1	1671.8	1666.4	1661.0	1658.5	1658.8	1659.1	1659.4	1659.8
147.5°	1735.9	1734.3	1729.0	1723.7	1718.3	1713.0	1711.0	1712.2	1713.4	1714.6	1715.8
150°	1766.9	1765.0	1759.9	1754.9	1749.8	1744.8	1743.3	1745.6	1747.8	1750.0	1752.2
152.5°	1795.3	1793.4	1788.6	1783.8	1779.0	1774.2	1773.1	1775.5	1778.0	1780.5	1782.9
155°	1833.7	1831.8	1828.1	1824.3	1820.5	1816.7	1816.2	1819.0	1821.9	1824.7	1827.6
157.5°	1865.9	1863.7	1861.0	1858.4	1855.7	1853.1	1853.0	1855.4	1857.8	1860.2	1862.6
160°	1884.9	1883.0	1881.1	1879.3	1877.4	1875.5	1875.5	1877.4	1879.3	1881.1	1883.0
162.5°	1902.3	1900.1	1898.5	1896.8	1895.2	1893.5	1893.7	1895.6	1897.5	1899.4	1901.2
165°	1923.7	1921.4	1920.5	1919.5	1918.6	1917.7	1918.1	1920.0	1921.9	1923.8	1925.7
167.5°	1941.6	1939.4	1938.5	1937.6	1936.7	1935.8	1936.3	1938.2	1940.1	1942.0	1943.9
170°	1950.7	1948.5	1947.8	1947.2	1946.6	1945.9	1946.6	1948.5	1950.4	1952.3	1954.2
172.5°	1957.5	1955.3	1954.7	1954.0	1953.4	1952.8	1953.4	1955.3	1957.2	1959.1	1961.0
175°	1964.9	1962.7	1962.1	1961.4	1960.8	1960.2	1961.0	1963.2	1965.4	1967.6	1969.8
177.5°	1966.2	1964.4	1964.1	1963.9	1963.6	1963.4	1964.1	1965.9	1967.7	1969.5	1971.2
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5



TEST NUMBER: P331841

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1920.7	1922.3	1932.9	1937.7	1947.3	1951.0	1955.2	1954.2	1954.2	1956.3	1971.2
5°	1924.8	1938.1	1958.0	1977.3	1995.8	2011.8	2022.4	2033.0	2037.0	2056.2	2073.5
7.5°	1917.9	1942.4	1975.3	2004.6	2039.8	2067.2	2090.1	2110.6	2124.7	2152.7	2181.4
10°	1908.9	1943.4	1980.6	2018.4	2066.8	2103.3	2140.5	2169.0	2178.3	2220.1	2244.0
12.5°	1890.9	1937.0	1984.3	2033.3	2080.6	2130.9	2171.8	2200.3	2233.0	2270.5	2314.6
15°	1863.8	1916.9	1978.6	2041.6	2109.3	2170.3	2214.1	2263.9	2299.7	2340.9	2379.3
17.5°	1824.9	1893.3	1971.7	2044.7	2123.0	2188.5	2248.8	2296.5	2321.7	2345.2	2350.9
20°	1794.1	1867.8	1960.0	2046.3	2124.6	2200.2	2259.9	2299.7	2306.4	2307.0	2271.9
22.5°	1760.7	1843.9	1940.4	2028.7	2122.4	2206.6	2253.0	2270.0	2243.7	2198.7	2130.7
25°	1699.2	1795.5	1907.6	2008.4	2110.6	2190.2	2206.2	2176.3	2084.1	1987.2	1864.5
27.5°	1632.6	1740.8	1861.0	1973.1	2082.0	2131.3	2097.0	1989.3	1823.2	1678.8	1503.8
30°	1583.8	1705.2	1823.3	1948.7	2049.6	2070.8	1991.9	1833.3	1639.5	1421.9	1247.4
32.5°	1528.1	1655.3	1785.1	1914.8	1999.2	1978.4	1848.0	1652.8	1425.6	1211.7	1046.8
35°	1448.4	1579.8	1719.8	1849.9	1903.6	1814.0	1619.0	1364.8	1132.6	932.9	819.4
37.5°	1356.5	1499.5	1645.1	1764.5	1760.7	1611.4	1345.7	1083.4	888.2	770.1	689.3
40°	1291.2	1435.8	1593.1	1693.9	1650.8	1456.4	1168.4	920.9	778.3	684.1	625.0
42.5°	1228.6	1373.7	1529.9	1610.1	1535.1	1296.1	1009.2	815.3	697.6	624.1	576.2
45°	1122.0	1275.3	1419.9	1464.4	1330.3	1066.9	816.1	675.5	597.2	542.7	509.6
47.5°	1017.8	1168.6	1300.6	1301.4	1120.1	865.2	688.5	584.6	517.7	475.6	451.5
50°	954.1	1097.4	1208.2	1191.0	985.3	769.7	615.7	526.2	470.4	437.9	412.7
52.5°	882.5	1021.5	1117.5	1068.4	871.2	677.3	550.4	475.2	429.0	400.8	378.2
55°	778.3	901.7	969.4	895.1	710.6	563.3	465.1	406.1	371.6	347.7	328.4
57.5°	676.0	777.8	820.4	733.8	585.3	467.1	393.5	349.1	314.9	297.8	287.8
60°	611.8	698.7	728.5	633.0	508.9	408.7	348.3	307.2	282.0	270.7	260.8
62.5°	548.6	619.6	631.9	544.3	443.6	357.8	305.9	271.1	254.4	243.6	234.2
65°	455.2	506.3	500.3	430.0	351.0	284.0	246.2	224.9	212.3	197.1	180.5
67.5°	374.7	405.9	387.1	334.4	267.9	220.7	196.0	179.9	164.3	149.8	146.0
70°	323.8	341.7	321.8	273.4	219.6	185.1	165.2	146.0	136.7	133.4	127.4
72.5°	275.0	281.2	259.7	218.2	178.7	153.3	133.9	123.1	118.1	115.3	111.5
75°	206.4	201.7	183.1	150.6	124.1	106.8	100.9	96.9	93.6	90.9	88.9
77.5°	144.9	138.1	121.6	100.3	86.4	78.2	74.6	72.5	70.9	69.5	67.5
80°	108.8	104.2	87.6	71.7	65.7	61.7	59.7	57.1	57.1	55.7	53.7
82.5°	79.6	74.4	60.0	52.5	49.2	46.8	45.4	43.8	43.3	43.5	42.1
85°	41.8	33.8	29.9	28.5	26.5	25.2	25.9	24.5	24.5	24.5	23.9
87.5°	13.7	11.8	11.9	12.1	13.2	13.7	13.7	14.2	15.2	15.0	15.9
90°	4.9	8.4	11.9	15.3	18.3	20.9	23.4	25.9	28.4	30.0	31.6
92.5°	28.4	28.1	27.8	27.5	27.9	29.2	30.5	31.7	33.0	33.8	34.6
95°	82.0	71.6	61.2	50.7	46.6	48.8	51.0	53.3	55.5	57.0	58.6
97.5°	154.1	124.7	95.3	65.9	53.8	58.9	64.0	69.1	74.2	75.5	76.8
100°	208.4	165.1	121.8	78.5	59.6	64.9	70.3	75.7	81.1	83.6	86.1
102.5°	317.7	308.5	299.3	290.2	263.1	218.2	173.2	128.3	83.3	86.6	89.9
105°	441.8	451.3	460.8	470.3	431.9	345.6	259.3	173.0	86.8	90.2	93.7
107.5°	560.3	568.0	575.6	583.3	535.4	431.9	328.4	224.9	121.5	117.9	114.4
110°	636.7	643.3	650.0	656.6	614.2	522.9	431.6	340.2	248.9	217.3	185.7



TEST NUMBER: P331841

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	708.7	714.6	720.5	726.4	718.0	695.5	672.9	650.3	627.8	512.5	397.2
115°	823.2	828.5	833.9	839.3	845.9	853.8	861.7	869.6	877.5	731.2	584.9
117.5°	926.5	932.5	938.5	944.5	950.2	955.6	961.1	966.5	972.0	936.6	901.2
120°	1000.3	1005.0	1009.8	1014.5	1019.7	1025.4	1031.1	1036.8	1042.5	1046.3	1050.1
122.5°	1064.3	1069.3	1074.3	1079.3	1084.9	1091.0	1097.2	1103.4	1109.6	1111.9	1114.2
125°	1160.4	1164.5	1168.6	1172.7	1177.8	1183.8	1189.8	1195.8	1201.8	1204.0	1206.2
127.5°	1248.7	1253.3	1257.8	1262.4	1266.9	1271.4	1275.9	1280.4	1284.9	1288.1	1291.3
130°	1305.0	1310.0	1315.1	1320.2	1324.4	1327.9	1331.4	1334.8	1338.3	1341.8	1345.3
132.5°	1361.1	1365.4	1369.7	1374.0	1377.9	1381.4	1384.8	1388.3	1391.8	1394.8	1397.7
135°	1435.8	1440.9	1445.9	1451.0	1454.9	1457.8	1460.6	1463.5	1466.3	1469.5	1472.6
137.5°	1509.1	1512.7	1516.2	1519.7	1523.1	1526.3	1529.6	1532.8	1536.0	1539.1	1542.2
140°	1557.0	1559.6	1562.1	1564.6	1567.6	1571.1	1574.6	1578.1	1581.5	1584.4	1587.2
142.5°	1597.7	1600.0	1602.3	1604.6	1607.7	1611.7	1615.7	1619.6	1623.6	1626.2	1628.8
145°	1659.4	1659.1	1658.8	1658.5	1661.0	1666.4	1671.8	1677.1	1682.5	1684.7	1686.9
147.5°	1714.6	1713.4	1712.2	1711.0	1713.0	1718.3	1723.7	1729.0	1734.3	1735.9	1737.6
150°	1750.0	1747.8	1745.6	1743.3	1744.8	1749.8	1754.9	1759.9	1765.0	1766.9	1768.8
152.5°	1780.5	1778.0	1775.5	1773.1	1774.2	1779.0	1783.8	1788.6	1793.4	1795.3	1797.2
155°	1824.7	1821.9	1819.0	1816.2	1816.7	1820.5	1824.3	1828.1	1831.8	1833.7	1835.6
157.5°	1860.2	1857.8	1855.4	1853.0	1853.1	1855.7	1858.4	1861.0	1863.7	1865.9	1868.0
160°	1881.1	1879.3	1877.4	1875.5	1875.5	1877.4	1879.3	1881.1	1883.0	1884.9	1886.8
162.5°	1899.4	1897.5	1895.6	1893.7	1893.5	1895.2	1896.8	1898.5	1900.1	1902.3	1904.4
165°	1923.8	1921.9	1920.0	1918.1	1917.7	1918.6	1919.5	1920.5	1921.4	1923.7	1925.9
167.5°	1942.0	1940.1	1938.2	1936.3	1935.8	1936.7	1937.6	1938.5	1939.4	1941.6	1943.8
170°	1952.3	1950.4	1948.5	1946.6	1945.9	1946.6	1947.2	1947.8	1948.5	1950.7	1952.9
172.5°	1959.1	1957.2	1955.3	1953.4	1952.8	1953.4	1954.0	1954.7	1955.3	1957.5	1959.7
175°	1967.6	1965.4	1963.2	1961.0	1960.2	1960.8	1961.4	1962.1	1962.7	1964.9	1967.1
177.5°	1969.5	1967.7	1965.9	1964.1	1963.4	1963.6	1963.9	1964.1	1964.4	1966.2	1967.9
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5



TEST NUMBER: P331841

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1976.5	1983.4	1986.5	1986.5	1990.3	1988.7	1987.1
5°	2090.1	2102.7	2105.3	2117.3	2125.9	2123.2	2124.6
7.5°	2203.0	2223.3	2243.3	2252.5	2253.9	2259.2	2261.2
10°	2272.5	2289.1	2320.3	2315.6	2338.9	2352.1	2330.2
12.5°	2339.4	2361.8	2383.5	2389.4	2402.6	2406.8	2398.2
15°	2399.9	2411.9	2413.2	2409.9	2413.8	2410.5	2397.9
17.5°	2343.4	2324.0	2284.7	2266.1	2251.4	2229.7	2220.9
20°	2250.0	2192.9	2126.5	2100.0	2068.8	2007.8	2022.4
22.5°	2048.3	1983.2	1916.9	1839.4	1802.4	1744.5	1741.0
25°	1734.4	1622.3	1498.9	1412.6	1362.2	1304.5	1279.2
27.5°	1348.5	1207.3	1106.2	1055.0	1008.4	962.6	960.8
30°	1094.8	988.6	910.3	866.5	838.0	818.8	822.8
32.5°	922.8	850.1	797.3	760.9	739.8	725.3	725.1
35°	754.4	704.6	670.8	655.5	640.3	629.7	630.3
37.5°	645.6	615.7	596.9	580.0	570.5	565.3	562.4
40°	589.9	565.3	550.7	540.8	532.8	525.5	524.2
42.5°	545.8	525.5	510.9	503.1	495.6	490.5	489.1
45°	484.4	467.8	454.5	445.9	442.6	437.9	437.9
47.5°	430.9	414.6	404.2	398.8	393.1	390.0	389.9
50°	394.8	382.2	372.9	369.6	364.9	362.9	362.3
52.5°	362.4	353.0	346.4	344.1	342.1	339.6	340.0
55°	318.5	313.2	310.5	308.5	305.2	301.2	303.9
57.5°	281.5	276.9	269.8	263.5	260.5	257.7	258.8
60°	255.5	246.2	236.9	229.6	227.6	221.6	221.6
62.5°	222.5	209.5	198.1	194.0	192.0	189.2	188.7
65°	171.2	165.9	163.2	160.6	159.2	159.2	157.9
67.5°	141.9	139.7	136.8	136.2	134.8	134.4	134.0
70°	125.4	122.7	121.4	120.8	119.4	120.1	118.1
72.5°	109.5	107.4	107.1	105.4	104.6	104.7	103.2
75°	86.3	86.3	85.6	84.9	83.6	82.9	83.6
77.5°	66.4	66.5	65.3	65.2	65.0	65.2	64.5
80°	53.1	53.7	53.1	52.4	51.8	52.4	51.8
82.5°	41.9	41.0	40.9	40.7	40.6	40.2	40.1
85°	23.9	24.5	23.9	23.2	23.2	23.2	23.9
87.5°	15.7	16.0	16.2	16.3	16.5	16.6	16.2
90°	33.2	34.8	35.9	36.5	37.1	37.8	38.4
92.5°	35.5	36.3	36.9	37.3	37.6	38.0	38.4
95°	60.2	61.8	62.4	62.1	61.8	61.5	61.2
97.5°	78.0	79.3	80.1	80.5	80.9	81.3	81.6
100°	88.7	91.2	92.8	93.4	94.0	94.7	95.3
102.5°	93.2	96.5	98.6	99.5	100.3	101.2	102.1
105°	97.2	100.7	103.0	104.3	105.6	106.8	108.1
107.5°	110.8	107.3	106.2	107.4	108.7	110.0	111.2
110°	154.1	122.5	107.3	108.6	109.8	111.1	112.4



TEST NUMBER: P331841

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	281.9	166.6	109.4	110.5	111.5	112.5	113.5
115°	438.5	292.2	207.6	184.9	162.1	139.4	116.6
117.5°	865.8	830.4	775.3	700.5	625.7	550.9	476.2
120°	1053.9	1057.7	1038.2	995.6	952.9	910.2	867.6
122.5°	1116.5	1118.7	1115.7	1107.4	1099.2	1090.9	1082.6
125°	1208.4	1210.6	1212.2	1213.2	1214.1	1215.1	1216.0
127.5°	1294.5	1297.7	1299.5	1299.6	1299.8	1300.0	1300.2
130°	1348.8	1352.2	1353.8	1353.5	1353.2	1352.9	1352.5
132.5°	1400.7	1403.7	1405.0	1404.7	1404.4	1404.1	1403.7
135°	1475.8	1479.0	1480.2	1479.6	1479.0	1478.3	1477.7
137.5°	1545.3	1548.4	1549.4	1548.3	1547.3	1546.2	1545.1
140°	1590.1	1592.9	1593.5	1592.0	1590.4	1588.8	1587.2
142.5°	1631.4	1634.0	1634.5	1632.9	1631.3	1629.8	1628.2
145°	1689.1	1691.4	1691.7	1690.1	1688.5	1686.9	1685.4
147.5°	1739.2	1740.9	1741.0	1739.7	1738.4	1737.0	1735.7
150°	1770.7	1772.6	1772.7	1771.2	1769.6	1768.0	1766.4
152.5°	1799.1	1801.0	1800.9	1798.8	1796.8	1794.7	1792.6
155°	1837.5	1839.4	1839.1	1836.6	1834.1	1831.5	1829.0
157.5°	1870.1	1872.3	1872.1	1869.7	1867.2	1864.7	1862.3
160°	1888.7	1890.6	1890.5	1888.3	1886.0	1883.8	1881.6
162.5°	1906.6	1908.7	1908.4	1905.7	1903.0	1900.3	1897.6
165°	1928.1	1930.3	1930.3	1928.1	1925.9	1923.7	1921.4
167.5°	1946.0	1948.2	1947.9	1945.1	1942.2	1939.4	1936.5
170°	1955.1	1957.3	1957.0	1954.2	1951.3	1948.5	1945.6
172.5°	1961.9	1964.1	1963.8	1961.0	1958.1	1955.3	1952.4
175°	1969.3	1971.5	1971.1	1967.9	1964.7	1961.6	1958.4
177.5°	1969.7	1971.5	1971.2	1968.9	1966.7	1964.4	1962.1
180°	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5	1965.5

(END OF REPORT)