

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331483-940

Luminaire Tested: **S122DIW-S290D1240U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331483-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S290D1240U940-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1240 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5584.2 lumens  
Efficiency: N/A  
Efficacy: 119.8 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331483-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331483-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29	21
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	18
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	23	22	21	15
3	76	67	60	55	67	60	54	50	46	42	39	33	30	28	21	20	18	13
4	70	60	52	47	61	53	47	42	41	36	33	29	27	24	19	17	16	12
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	15	14	12	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	12	11	8
8	50	39	31	26	44	35	28	24	27	22	19	20	17	15	13	11	10	7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	21	38	29	23	19	23	18	15	17	14	12	11	9	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8510	8510	8510	8510
5°	9540	8566	7590	8566
10°	10932	8496	6568	8496
15°	12094	8339	5804	8339
20°	11911	8172	5290	8172
25°	10739	7949	4965	7949
30°	8874	7594	4728	7594
35°	6467	7222	4559	7222
40°	5166	6785	4466	6785
45°	4514	6277	4338	6277
50°	4245	5785	4253	5785
55°	3910	5286	4138	5286
60°	3584	4753	3965	4753
65°	3266	4279	3790	4279
70°	2965	3814	3541	3814
75°	2633	3300	3132	3300
80°	2259	2724	2520	2724
85°	2038	2038	1501	2038



TEST NUMBER: P331483-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.2	0.9
10°-20°	145.9	2.6
20°-30°	211.8	3.8
30°-40°	223.5	4.0
40°-50°	197.9	3.5
50°-60°	157.9	2.8
60°-70°	107.3	1.9
70°-80°	55.0	1.0
80°-90°	17.0	0.3
90°-100°	50.3	0.9
100°-110°	184.4	3.3
110°-120°	492.9	8.8
120°-130°	813.7	14.6
130°-140°	865.3	15.5
140°-150°	804.3	14.4
150°-160°	646.7	11.6
160°-170°	416.7	7.5
170°-180°	143.4	2.6
0°-30°	407.9	7.3
0°-40°	631.4	11.3
0°-60°	987.2	17.7
0°-90°	1166.5	20.9
90°-120°	727.6	13.0
90°-150°	3210.9	57.5
90°-180°	4418.0	79.1
0°-180°	5584.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	527	527	527	527	527	
5°	589	528	468	528	589	59
15°	724	499	347	499	724	200
25°	603	446	279	446	603	272
35°	328	366	231	366	328	213
45°	198	275	190	275	198	155
55°	139	188	147	188	139	125
65°	86	112	99	112	86	85
75°	42	53	50	53	42	45
85°	11	11	8	11	11	13
90°	29	1	29	1	29	13
95°	47	71	47	71	47	44
105°	83	332	83	332	83	86
115°	89	627	89	627	89	224
125°	933	887	933	887	933	807
135°	1133	1097	1133	1097	1133	874
145°	1293	1273	1293	1273	1293	808
155°	1403	1402	1403	1402	1403	647
165°	1474	1477	1474	1477	1474	416
175°	1502	1511	1502	1511	1502	143
180°	1507	1507	1507	1507	1507	



TEST NUMBER: P331483-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	551.3	551.5	551.9	549.3	548.9	548.9	546.7	544.7	542.4	539.4	539.8
5°	588.6	590.8	591.7	589.2	585.6	585.2	581.8	576.1	570.8	566.6	563.6
7.5°	633.1	634.0	632.0	628.8	626.2	621.3	614.8	608.6	599.8	591.7	585.8
10°	666.8	668.1	664.6	660.0	656.1	650.4	641.1	631.6	620.1	608.9	600.0
12.5°	692.4	695.4	691.0	690.5	683.9	676.0	664.9	660.1	643.9	628.4	618.8
15°	723.5	723.4	723.8	719.9	715.1	713.8	702.1	689.3	666.5	657.3	641.5
17.5°	714.5	717.6	719.1	719.0	718.9	718.1	714.3	706.3	694.8	680.0	661.8
20°	693.2	697.2	697.9	702.5	705.2	708.6	710.0	707.8	700.7	688.3	672.5
22.5°	660.1	661.3	663.2	670.4	676.1	684.7	689.2	696.8	694.0	688.0	674.8
25°	602.8	600.8	607.9	611.5	624.7	638.5	648.5	659.3	669.1	674.9	671.1
27.5°	534.0	531.0	541.6	551.3	562.0	576.9	592.4	610.6	625.8	644.9	651.4
30°	476.0	477.9	487.9	498.3	514.5	535.6	553.0	573.0	594.8	616.0	630.8
32.5°	413.5	420.4	426.9	442.7	457.0	480.5	506.0	531.1	558.1	582.3	605.2
35°	328.1	336.3	345.2	356.7	376.7	400.0	425.0	458.8	495.7	528.7	555.8
37.5°	276.3	274.9	280.0	288.4	304.6	323.4	352.1	385.5	428.9	467.7	506.0
40°	245.1	244.3	247.9	255.7	268.0	281.8	306.9	336.3	376.6	424.0	469.6
42.5°	223.7	224.2	226.2	231.7	240.1	251.5	270.3	295.2	332.2	376.8	425.8
45°	197.7	199.1	201.3	204.0	208.8	218.2	228.7	246.6	275.7	313.0	361.1
47.5°	179.0	179.1	181.3	183.6	186.5	191.7	200.4	211.5	232.1	262.4	303.9
50°	169.0	167.6	169.2	170.9	174.0	177.6	183.3	193.9	207.6	232.1	266.8
52.5°	156.6	156.7	158.1	158.8	161.5	165.1	170.3	177.6	190.1	209.3	237.7
55°	138.9	140.0	140.8	142.0	144.5	147.0	151.1	156.0	165.7	180.0	201.2
57.5°	122.3	122.7	123.5	125.8	127.3	129.7	133.6	138.0	144.4	155.0	170.9
60°	111.0	111.0	112.6	113.6	115.7	118.1	121.1	125.4	131.1	139.7	152.6
62.5°	100.7	100.5	101.1	102.8	104.3	106.6	109.6	113.2	118.6	126.4	136.8
65°	85.5	85.1	86.3	86.7	88.3	90.5	93.0	96.8	101.1	106.7	116.1
67.5°	70.9	71.4	72.1	72.8	73.7	76.1	77.7	80.3	84.0	88.7	95.0
70°	62.8	62.8	62.8	63.4	64.6	65.8	67.4	69.6	73.1	77.1	82.8
72.5°	53.7	54.4	55.0	54.7	56.2	56.9	58.9	60.1	63.4	66.0	71.0
75°	42.2	42.2	42.2	43.2	43.8	44.3	45.6	46.8	48.4	51.6	54.3
77.5°	31.5	31.4	31.6	31.8	32.5	33.2	33.5	34.6	36.1	37.6	39.9
80°	24.3	24.7	24.9	25.3	25.3	25.7	25.9	27.4	28.4	29.3	30.8
82.5°	18.8	18.9	18.9	19.0	19.2	19.4	20.0	20.4	20.8	21.6	22.6
85°	11.0	10.7	10.7	11.1	11.0	11.0	11.3	11.8	11.8	11.9	12.6
87.5°	10.1	10.0	10.1	9.8	9.7	9.7	9.5	9.1	9.0	8.9	8.6
90°	29.4	29.0	28.4	28.0	27.6	26.7	25.4	24.3	23.0	21.8	19.9
92.5°	29.4	29.2	28.9	28.5	28.3	27.8	27.2	26.6	25.9	25.3	24.3
95°	46.9	47.2	47.3	47.6	47.9	47.3	46.2	44.9	43.8	42.5	40.8
97.5°	62.6	62.3	62.1	61.7	61.4	60.8	59.8	58.9	57.9	57.0	53.1
100°	73.1	72.6	72.1	71.6	71.2	69.9	67.9	66.1	64.1	62.2	58.1
102.5°	78.3	77.7	77.0	76.2	75.6	74.0	71.5	68.9	66.4	63.9	98.4
105°	82.9	81.9	81.0	80.0	79.0	77.2	74.5	71.9	69.2	66.5	132.7
107.5°	85.3	84.4	83.4	82.4	81.4	82.3	85.0	87.7	90.4	93.2	172.5
110°	86.1	85.2	84.3	83.3	82.3	93.9	118.2	142.4	166.7	190.9	260.9



TEST NUMBER: P331483-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	87.0	86.2	85.5	84.7	83.9	127.8	216.2	304.6	393.1	481.4	498.8
115°	89.4	106.9	124.4	141.8	159.3	224.1	336.4	448.5	560.8	673.1	667.0
117.5°	365.2	422.6	479.9	537.3	594.6	636.9	664.0	691.2	718.3	745.5	741.3
120°	665.4	698.1	730.8	763.6	796.3	811.2	808.2	805.4	802.5	799.5	795.2
122.5°	830.3	836.7	843.0	849.4	855.7	858.0	856.3	854.5	852.7	851.0	846.3
125°	932.6	931.9	931.2	930.4	929.7	928.5	926.8	925.1	923.5	921.8	917.1
127.5°	997.2	997.0	996.9	996.8	996.7	995.3	992.8	990.3	987.9	985.4	982.0
130°	1037.3	1037.6	1037.9	1038.0	1038.3	1037.1	1034.5	1031.8	1029.1	1026.4	1023.8
132.5°	1076.7	1076.8	1077.1	1077.4	1077.5	1076.6	1074.2	1072.0	1069.7	1067.5	1064.8
135°	1133.4	1133.8	1134.3	1134.8	1135.2	1134.3	1131.8	1129.4	1127.0	1124.6	1122.4
137.5°	1185.0	1185.9	1186.7	1187.5	1188.3	1187.6	1185.2	1182.8	1180.4	1178.0	1175.5
140°	1217.4	1218.5	1219.8	1220.9	1222.2	1221.7	1219.5	1217.4	1215.1	1213.0	1210.3
142.5°	1248.8	1249.9	1251.2	1252.4	1253.6	1253.2	1251.2	1249.2	1247.2	1245.3	1242.2
145°	1292.6	1293.8	1295.0	1296.2	1297.4	1297.2	1295.5	1293.8	1292.1	1290.4	1286.3
147.5°	1331.2	1332.2	1333.2	1334.3	1335.2	1335.2	1333.9	1332.7	1331.4	1330.1	1326.1
150°	1354.8	1355.9	1357.2	1358.4	1359.6	1359.5	1358.1	1356.6	1355.1	1353.7	1349.8
152.5°	1374.8	1376.4	1378.0	1379.7	1381.3	1381.3	1379.8	1378.4	1377.0	1375.5	1371.8
155°	1402.8	1404.7	1406.7	1408.5	1410.5	1410.8	1409.3	1407.8	1406.4	1405.0	1402.0
157.5°	1428.3	1430.2	1432.1	1434.0	1435.8	1436.0	1434.3	1432.7	1431.0	1429.4	1427.4
160°	1443.1	1444.8	1446.5	1448.2	1449.9	1450.0	1448.6	1447.2	1445.6	1444.2	1442.8
162.5°	1455.4	1457.4	1459.5	1461.6	1463.7	1463.9	1462.2	1460.6	1458.9	1457.3	1456.1
165°	1473.6	1475.3	1477.0	1478.7	1480.4	1480.4	1478.7	1477.0	1475.3	1473.6	1472.9
167.5°	1485.2	1487.4	1489.6	1491.7	1494.0	1494.2	1492.5	1490.8	1489.1	1487.4	1486.7
170°	1492.2	1494.4	1496.6	1498.8	1500.9	1501.2	1499.5	1497.8	1496.1	1494.4	1493.9
172.5°	1497.4	1499.6	1501.8	1504.0	1506.2	1506.4	1504.7	1503.0	1501.3	1499.6	1499.1
175°	1502.0	1504.4	1506.9	1509.3	1511.7	1512.1	1510.4	1508.7	1507.0	1505.3	1504.9
177.5°	1504.9	1506.6	1508.3	1510.1	1511.8	1512.1	1510.6	1509.3	1508.0	1506.6	1506.4
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331483-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	540.8	539.6	538.8	535.8	533.2	530.7	529.9	530.1	526.6	523.2	521.7
5°	562.0	557.9	554.0	548.6	542.1	534.9	531.4	528.5	521.4	513.7	509.3
7.5°	580.8	575.0	567.6	557.3	547.9	536.7	529.6	523.3	513.0	502.1	495.4
10°	592.3	584.4	574.9	562.3	550.8	537.2	527.7	518.2	506.0	493.0	484.9
12.5°	602.2	591.6	582.2	566.1	552.4	535.4	524.1	510.7	497.9	482.5	474.6
15°	625.7	606.1	588.3	570.0	553.2	529.5	516.9	498.9	482.1	463.1	454.0
17.5°	643.9	621.8	593.8	570.6	551.0	524.7	506.3	484.7	464.8	443.1	430.7
20°	654.2	628.9	598.8	571.2	547.8	517.7	497.7	475.6	452.4	427.8	414.5
22.5°	660.4	633.8	604.0	568.8	541.3	512.1	486.9	462.6	439.1	412.6	398.6
25°	662.4	638.1	606.5	566.8	533.2	500.2	469.8	446.2	417.7	393.0	372.6
27.5°	652.7	635.3	604.9	562.9	523.8	485.2	451.3	424.7	394.6	367.7	347.1
30°	640.9	630.8	601.2	559.1	516.3	474.8	437.6	407.3	377.4	350.3	329.1
32.5°	622.6	620.5	594.4	553.6	508.4	461.7	423.1	392.6	359.4	332.7	312.6
35°	586.7	596.4	580.0	541.3	493.5	443.0	401.3	366.4	332.0	306.5	287.7
37.5°	538.4	562.6	558.3	523.3	473.2	422.7	376.6	340.2	307.4	281.6	263.1
40°	505.2	536.0	540.5	509.4	459.1	407.0	358.1	321.9	289.9	266.4	247.7
42.5°	469.6	505.5	517.7	492.9	443.4	390.4	341.6	304.1	272.3	249.5	233.0
45°	409.8	457.4	479.5	465.3	417.5	363.2	313.0	274.9	246.1	224.6	211.9
47.5°	353.9	405.9	435.6	430.6	388.6	334.8	285.2	248.6	220.6	203.5	192.1
50°	314.4	367.8	403.7	405.4	367.8	314.6	264.7	230.3	204.6	188.6	179.2
52.5°	280.0	331.1	370.1	378.8	344.6	293.6	246.5	212.1	189.5	174.8	166.5
55°	235.1	278.3	321.6	337.5	310.1	261.5	217.9	187.8	166.5	156.4	149.1
57.5°	195.6	231.5	271.5	289.0	272.2	230.5	189.7	163.5	146.2	137.3	131.7
60°	174.6	203.0	238.6	259.5	244.9	207.9	172.2	147.2	133.0	125.2	119.9
62.5°	155.2	180.3	210.4	229.5	221.6	186.6	154.7	132.7	120.5	113.1	109.2
65°	128.0	147.8	171.2	188.8	183.5	157.0	130.8	112.0	102.3	96.4	93.4
67.5°	105.4	119.8	135.9	151.3	147.1	128.3	107.4	92.6	85.4	80.3	78.5
70°	91.1	102.1	116.5	128.9	125.4	110.0	93.4	80.8	74.5	70.3	68.5
72.5°	77.6	86.5	97.6	107.6	105.3	92.5	78.6	69.2	64.3	60.4	58.9
75°	58.6	65.5	72.1	78.8	78.2	68.3	60.2	52.9	49.0	46.0	45.4
77.5°	43.2	47.1	51.6	55.6	54.5	48.8	42.4	38.3	35.5	33.4	33.1
80°	33.0	35.2	38.5	41.3	39.9	37.5	32.4	29.3	27.4	25.3	24.5
82.5°	24.0	26.1	28.1	29.7	28.5	26.3	23.2	21.1	19.9	18.5	18.2
85°	12.6	13.7	14.6	15.0	14.6	13.2	11.8	11.0	9.9	9.3	9.1
87.5°	8.5	8.0	7.7	7.6	6.5	6.0	4.8	3.7	4.2	4.5	4.7
90°	17.9	16.0	14.1	11.8	9.1	6.4	3.7	1.1	3.7	6.4	9.1
92.5°	23.4	22.4	21.4	21.0	21.3	21.6	21.8	22.0	21.8	21.6	21.3
95°	39.1	37.5	35.8	38.9	46.9	54.9	62.9	70.9	62.9	54.9	46.9
97.5°	49.0	45.1	41.2	50.6	73.1	95.6	118.2	140.7	118.2	95.6	73.1
100°	53.9	49.8	45.7	60.3	93.5	126.6	159.9	193.1	159.9	126.6	93.5
102.5°	132.9	167.3	201.8	222.6	229.6	236.6	243.6	250.7	243.6	236.6	229.6
105°	198.9	265.1	331.3	360.7	353.4	346.2	338.9	331.6	338.9	346.2	353.4
107.5°	251.9	331.3	410.6	447.4	441.5	435.6	429.7	423.9	429.7	435.6	441.5
110°	331.0	401.1	471.1	503.5	498.5	493.4	488.3	483.2	488.3	493.4	498.5





TEST NUMBER: P331483-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	516.1	533.4	550.7	557.1	552.6	548.0	543.6	539.0	543.6	548.0	552.6
115°	660.9	654.9	648.8	643.7	639.5	635.4	631.3	627.2	631.3	635.4	639.5
117.5°	737.1	732.9	728.8	724.4	719.8	715.2	710.6	706.0	710.6	715.2	719.8
120°	790.9	786.5	782.1	778.1	774.5	770.8	767.2	763.6	767.2	770.8	774.5
122.5°	841.5	836.8	832.1	827.8	823.9	820.1	816.3	812.4	816.3	820.1	823.9
125°	912.5	907.9	903.3	899.4	896.3	893.1	889.9	886.8	889.9	893.1	896.3
127.5°	978.6	975.1	971.7	968.2	964.7	961.2	957.7	954.2	957.7	961.2	964.7
130°	1021.1	1018.4	1015.7	1012.5	1008.6	1004.8	1000.9	997.0	1000.9	1004.8	1008.6
132.5°	1062.1	1059.4	1056.8	1053.8	1050.5	1047.2	1043.9	1040.6	1043.9	1047.2	1050.5
135°	1120.3	1118.0	1115.9	1112.9	1108.9	1105.1	1101.2	1097.3	1101.2	1105.1	1108.9
137.5°	1173.1	1170.6	1168.1	1165.6	1162.9	1160.1	1157.4	1154.7	1157.4	1160.1	1162.9
140°	1207.6	1205.0	1202.3	1200.0	1198.0	1196.1	1194.2	1192.2	1194.2	1196.1	1198.0
142.5°	1239.1	1236.1	1233.1	1230.7	1228.9	1227.2	1225.4	1223.7	1225.4	1227.2	1228.9
145°	1282.2	1278.1	1273.9	1272.0	1272.2	1272.5	1272.7	1272.9	1272.7	1272.5	1272.2
147.5°	1322.0	1317.9	1313.8	1312.2	1313.1	1314.1	1315.0	1315.9	1315.0	1314.1	1313.1
150°	1345.9	1342.0	1338.2	1337.0	1338.7	1340.5	1342.2	1343.9	1342.2	1340.5	1338.7
152.5°	1368.2	1364.4	1360.8	1359.9	1361.7	1363.6	1365.6	1367.4	1365.6	1363.6	1361.7
155°	1399.1	1396.2	1393.3	1392.9	1395.1	1397.3	1399.5	1401.7	1399.5	1397.3	1395.1
157.5°	1425.3	1423.3	1421.2	1421.1	1423.0	1424.8	1426.6	1428.5	1426.6	1424.8	1423.0
160°	1441.3	1439.8	1438.4	1438.4	1439.8	1441.3	1442.8	1444.2	1442.8	1441.3	1439.8
162.5°	1454.7	1453.5	1452.2	1452.3	1453.8	1455.3	1456.7	1458.2	1456.7	1455.3	1453.8
165°	1472.2	1471.5	1470.8	1471.1	1472.6	1474.0	1475.5	1476.9	1475.5	1474.0	1472.6
167.5°	1486.0	1485.4	1484.7	1485.1	1486.6	1488.0	1489.4	1490.9	1489.4	1488.0	1486.6
170°	1493.4	1492.9	1492.5	1492.9	1494.4	1495.8	1497.3	1498.8	1497.3	1495.8	1494.4
172.5°	1498.6	1498.2	1497.7	1498.2	1499.6	1501.1	1502.5	1504.0	1502.5	1501.1	1499.6
175°	1504.3	1503.9	1503.3	1504.0	1505.7	1507.3	1509.0	1510.7	1509.0	1507.3	1505.7
177.5°	1506.2	1506.0	1505.8	1506.4	1507.8	1509.1	1510.5	1511.8	1510.5	1509.1	1507.8
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331483-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	520.1	519.2	515.8	514.0	511.0	508.3	506.5	507.3	507.9	507.7	507.1
5°	505.2	501.3	495.4	490.4	486.8	480.1	477.2	475.8	474.6	473.2	471.8
7.5°	487.4	481.3	473.0	465.7	459.0	450.6	445.9	443.1	440.1	436.9	434.1
10°	474.8	466.3	457.4	447.3	439.2	431.7	425.0	420.5	416.4	412.6	409.8
12.5°	461.5	451.7	440.7	426.9	417.9	407.2	406.2	398.3	392.0	389.6	386.3
15°	440.4	426.6	412.6	396.2	389.1	379.4	373.4	367.2	361.8	357.9	357.0
17.5°	416.3	398.5	384.6	372.8	361.2	351.2	345.6	340.8	336.3	331.2	330.5
20°	398.1	382.6	367.5	357.1	345.2	335.0	328.1	323.3	319.4	316.4	313.8
22.5°	380.7	363.8	349.9	338.7	326.9	318.7	313.3	308.5	305.3	302.0	299.5
25°	352.8	339.7	324.5	311.7	302.0	296.8	292.3	288.3	286.2	284.0	281.2
27.5°	328.5	313.9	299.7	289.8	281.2	276.6	273.4	270.6	268.8	267.4	265.8
30°	311.4	296.6	285.4	275.7	268.6	263.9	261.9	260.3	258.1	257.3	256.5
32.5°	294.8	281.5	272.0	263.5	256.8	253.7	251.9	250.4	248.7	247.9	246.2
35°	271.4	260.3	251.0	246.3	240.9	238.2	236.8	234.8	233.2	232.4	232.1
37.5°	249.4	239.8	233.6	227.7	225.3	223.7	221.8	220.4	219.9	219.8	219.5
40°	235.1	227.3	221.8	217.0	216.0	213.5	211.9	210.7	210.7	210.9	210.7
42.5°	222.2	215.1	210.3	206.1	204.9	203.5	201.8	201.8	202.1	202.8	202.1
45°	202.6	197.5	194.0	192.1	189.8	188.4	188.2	188.8	189.0	189.2	189.8
47.5°	184.5	181.1	178.0	175.8	174.8	174.6	174.3	175.4	176.4	176.7	177.6
50°	173.8	170.0	167.3	165.9	165.1	164.7	165.1	166.3	167.1	168.1	168.7
52.5°	161.8	159.1	157.3	156.1	155.9	156.1	156.1	157.6	158.8	159.3	159.5
55°	145.3	143.2	142.9	141.0	141.8	141.6	142.6	143.4	144.6	145.9	146.1
57.5°	128.7	127.1	126.0	126.2	126.4	127.3	128.1	129.6	130.8	132.2	132.2
60°	117.7	116.9	116.3	116.3	116.6	117.9	118.9	120.3	121.1	122.0	122.5
62.5°	107.6	106.8	106.2	106.6	107.6	108.3	109.5	110.3	111.1	111.9	112.2
65°	91.8	91.4	91.9	92.4	92.6	93.5	95.0	95.6	96.4	96.8	98.3
67.5°	77.1	77.2	77.1	77.7	78.9	79.1	80.4	81.9	82.0	82.8	83.7
70°	67.2	67.7	68.0	68.5	69.5	69.9	70.9	71.5	72.3	72.9	73.6
72.5°	58.1	58.2	58.7	58.6	59.5	60.3	61.2	61.8	62.6	63.4	63.9
75°	44.8	44.8	45.2	45.4	46.4	47.4	47.2	47.6	48.4	49.2	49.7
77.5°	32.7	32.3	32.7	32.9	33.3	34.1	34.2	34.8	35.8	35.5	35.9
80°	24.9	24.3	24.9	25.1	25.1	26.1	26.1	26.6	27.1	26.6	27.1
82.5°	17.7	17.5	17.9	18.0	18.3	18.4	18.6	18.7	19.4	19.1	19.4
85°	8.9	8.7	8.9	8.7	8.9	9.1	9.1	8.9	8.9	9.3	8.7
87.5°	5.1	5.4	5.6	6.0	6.2	6.5	6.5	6.8	7.0	7.0	7.1
90°	11.8	14.1	16.0	17.9	19.9	21.8	23.0	24.3	25.4	26.7	27.6
92.5°	21.0	21.4	22.4	23.4	24.3	25.3	25.9	26.6	27.2	27.8	28.3
95°	38.9	35.8	37.5	39.1	40.8	42.5	43.8	44.9	46.2	47.3	47.9
97.5°	50.6	41.2	45.1	49.0	53.1	57.0	57.9	58.9	59.8	60.8	61.4
100°	60.3	45.7	49.8	53.9	58.1	62.2	64.1	66.1	67.9	69.9	71.2
102.5°	222.6	201.8	167.3	132.9	98.4	63.9	66.4	68.9	71.5	74.0	75.6
105°	360.7	331.3	265.1	198.9	132.7	66.5	69.2	71.9	74.5	77.2	79.0
107.5°	447.4	410.6	331.3	251.9	172.5	93.2	90.4	87.7	85.0	82.3	81.4
110°	503.5	471.1	401.1	331.0	260.9	190.9	166.7	142.4	118.2	93.9	82.3



TEST NUMBER: P331483-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	557.1	550.7	533.4	516.1	498.8	481.4	393.1	304.6	216.2	127.8	83.9
115°	643.7	648.8	654.9	660.9	667.0	673.1	560.8	448.5	336.4	224.1	159.3
117.5°	724.4	728.8	732.9	737.1	741.3	745.5	718.3	691.2	664.0	636.9	594.6
120°	778.1	782.1	786.5	790.9	795.2	799.5	802.5	805.4	808.2	811.2	796.3
122.5°	827.8	832.1	836.8	841.5	846.3	851.0	852.7	854.5	856.3	858.0	855.7
125°	899.4	903.3	907.9	912.5	917.1	921.8	923.5	925.1	926.8	928.5	929.7
127.5°	968.2	971.7	975.1	978.6	982.0	985.4	987.9	990.3	992.8	995.3	996.7
130°	1012.5	1015.7	1018.4	1021.1	1023.8	1026.4	1029.1	1031.8	1034.5	1037.1	1038.3
132.5°	1053.8	1056.8	1059.4	1062.1	1064.8	1067.5	1069.7	1072.0	1074.2	1076.6	1077.5
135°	1112.9	1115.9	1118.0	1120.3	1122.4	1124.6	1127.0	1129.4	1131.8	1134.3	1135.2
137.5°	1165.6	1168.1	1170.6	1173.1	1175.5	1178.0	1180.4	1182.8	1185.2	1187.6	1188.3
140°	1200.0	1202.3	1205.0	1207.6	1210.3	1213.0	1215.1	1217.4	1219.5	1221.7	1222.2
142.5°	1230.7	1233.1	1236.1	1239.1	1242.2	1245.3	1247.2	1249.2	1251.2	1253.2	1253.6
145°	1272.0	1273.9	1278.1	1282.2	1286.3	1290.4	1292.1	1293.8	1295.5	1297.2	1297.4
147.5°	1312.2	1313.8	1317.9	1322.0	1326.1	1330.1	1331.4	1332.7	1333.9	1335.2	1335.2
150°	1337.0	1338.2	1342.0	1345.9	1349.8	1353.7	1355.1	1356.6	1358.1	1359.5	1359.6
152.5°	1359.9	1360.8	1364.4	1368.2	1371.8	1375.5	1377.0	1378.4	1379.8	1381.3	1381.3
155°	1392.9	1393.3	1396.2	1399.1	1402.0	1405.0	1406.4	1407.8	1409.3	1410.8	1410.5
157.5°	1421.1	1421.2	1423.3	1425.3	1427.4	1429.4	1431.0	1432.7	1434.3	1436.0	1435.8
160°	1438.4	1438.4	1439.8	1441.3	1442.8	1444.2	1445.6	1447.2	1448.6	1450.0	1449.9
162.5°	1452.3	1452.2	1453.5	1454.7	1456.1	1457.3	1458.9	1460.6	1462.2	1463.9	1463.7
165°	1471.1	1470.8	1471.5	1472.2	1472.9	1473.6	1475.3	1477.0	1478.7	1480.4	1480.4
167.5°	1485.1	1484.7	1485.4	1486.0	1486.7	1487.4	1489.1	1490.8	1492.5	1494.2	1494.0
170°	1492.9	1492.5	1492.9	1493.4	1493.9	1494.4	1496.1	1497.8	1499.5	1501.2	1500.9
172.5°	1498.2	1497.7	1498.2	1498.6	1499.1	1499.6	1501.3	1503.0	1504.7	1506.4	1506.2
175°	1504.0	1503.3	1503.9	1504.3	1504.9	1505.3	1507.0	1508.7	1510.4	1512.1	1511.7
177.5°	1506.4	1505.8	1506.0	1506.2	1506.4	1506.6	1508.0	1509.3	1510.6	1512.1	1511.8
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331483-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	505.5	505.2	505.2	503.7	505.2	505.2	505.5	507.1	507.7	507.9	507.3
5°	469.0	468.3	467.3	468.3	467.3	468.3	469.0	471.8	473.2	474.6	475.8
7.5°	432.7	430.3	430.0	427.6	430.0	430.3	432.7	434.1	436.9	440.1	443.1
10°	406.4	404.7	404.5	400.6	404.5	404.7	406.4	409.8	412.6	416.4	420.5
12.5°	386.3	382.4	383.2	380.9	383.2	382.4	386.3	386.3	389.6	392.0	398.3
15°	351.4	351.4	350.6	347.2	350.6	351.4	351.4	357.0	357.9	361.8	367.2
17.5°	326.5	326.0	324.1	325.1	324.1	326.0	326.5	330.5	331.2	336.3	340.8
20°	311.6	310.3	307.9	307.9	307.9	310.3	311.6	313.8	316.4	319.4	323.3
22.5°	297.5	297.4	294.8	295.6	294.8	297.4	297.5	299.5	302.0	305.3	308.5
25°	281.0	279.4	278.1	278.7	278.1	279.4	281.0	281.2	284.0	286.2	288.3
27.5°	265.3	264.4	264.3	262.7	264.3	264.4	265.3	265.8	267.4	268.8	270.6
30°	256.3	254.2	254.6	253.6	254.6	254.2	256.3	256.5	257.3	258.1	260.3
32.5°	245.8	245.1	244.8	243.9	244.8	245.1	245.8	246.2	247.9	248.7	250.4
35°	231.8	231.9	231.0	231.3	231.0	231.9	231.8	232.1	232.4	233.2	234.8
37.5°	219.4	220.0	219.5	219.6	219.5	220.0	219.4	219.5	219.8	219.9	220.4
40°	211.2	211.2	211.2	211.9	211.2	211.2	211.2	210.7	210.9	210.7	210.7
42.5°	203.5	203.1	202.9	202.8	202.9	203.1	203.5	202.1	202.8	202.1	201.8
45°	190.2	190.8	191.0	190.0	191.0	190.8	190.2	189.8	189.2	189.0	188.8
47.5°	178.2	178.3	178.2	179.1	178.2	178.3	178.2	177.6	176.7	176.4	175.4
50°	169.8	169.3	169.8	169.3	169.8	169.3	169.8	168.7	168.1	167.1	166.3
52.5°	160.9	161.0	160.7	160.6	160.7	161.0	160.9	159.5	159.3	158.8	157.6
55°	146.9	147.2	147.0	147.0	147.0	147.2	146.9	146.1	145.9	144.6	143.4
57.5°	132.4	132.8	133.0	132.2	133.0	132.8	132.4	132.2	132.2	130.8	129.6
60°	122.3	123.3	123.1	122.8	123.1	123.3	122.3	122.5	122.0	121.1	120.3
62.5°	113.1	113.5	113.4	113.3	113.4	113.5	113.1	112.2	111.9	111.1	110.3
65°	98.9	99.2	98.6	99.2	98.6	99.2	98.9	98.3	96.8	96.4	95.6
67.5°	83.5	83.6	84.1	84.4	84.1	83.6	83.5	83.7	82.8	82.0	81.9
70°	73.9	73.7	74.4	75.0	74.4	73.7	73.9	73.6	72.9	72.3	71.5
72.5°	63.8	64.3	64.1	64.6	64.1	64.3	63.8	63.9	63.4	62.6	61.8
75°	49.2	49.8	49.7	50.2	49.7	49.8	49.2	49.7	49.2	48.4	47.6
77.5°	35.6	35.7	35.6	35.9	35.6	35.7	35.6	35.9	35.5	35.8	34.8
80°	27.1	26.8	26.3	27.1	26.3	26.8	27.1	27.1	26.6	27.1	26.6
82.5°	18.9	19.1	18.7	18.7	18.7	19.1	18.9	19.4	19.1	19.4	18.7
85°	8.7	8.5	8.1	8.1	8.1	8.5	8.7	8.7	9.3	8.9	8.9
87.5°	7.2	7.1	7.2	7.2	7.2	7.1	7.2	7.1	7.0	7.0	6.8
90°	28.0	28.4	29.0	29.4	29.0	28.4	28.0	27.6	26.7	25.4	24.3
92.5°	28.5	28.9	29.2	29.4	29.2	28.9	28.5	28.3	27.8	27.2	26.6
95°	47.6	47.3	47.2	46.9	47.2	47.3	47.6	47.9	47.3	46.2	44.9
97.5°	61.7	62.1	62.3	62.6	62.3	62.1	61.7	61.4	60.8	59.8	58.9
100°	71.6	72.1	72.6	73.1	72.6	72.1	71.6	71.2	69.9	67.9	66.1
102.5°	76.2	77.0	77.7	78.3	77.7	77.0	76.2	75.6	74.0	71.5	68.9
105°	80.0	81.0	81.9	82.9	81.9	81.0	80.0	79.0	77.2	74.5	71.9
107.5°	82.4	83.4	84.4	85.3	84.4	83.4	82.4	81.4	82.3	85.0	87.7
110°	83.3	84.3	85.2	86.1	85.2	84.3	83.3	82.3	93.9	118.2	142.4



TEST NUMBER: P331483-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	84.7	85.5	86.2	87.0	86.2	85.5	84.7	83.9	127.8	216.2	304.6
115°	141.8	124.4	106.9	89.4	106.9	124.4	141.8	159.3	224.1	336.4	448.5
117.5°	537.3	479.9	422.6	365.2	422.6	479.9	537.3	594.6	636.9	664.0	691.2
120°	763.6	730.8	698.1	665.4	698.1	730.8	763.6	796.3	811.2	808.2	805.4
122.5°	849.4	843.0	836.7	830.3	836.7	843.0	849.4	855.7	858.0	856.3	854.5
125°	930.4	931.2	931.9	932.6	931.9	931.2	930.4	929.7	928.5	926.8	925.1
127.5°	996.8	996.9	997.0	997.2	997.0	996.9	996.8	996.7	995.3	992.8	990.3
130°	1038.0	1037.9	1037.6	1037.3	1037.6	1037.9	1038.0	1038.3	1037.1	1034.5	1031.8
132.5°	1077.4	1077.1	1076.8	1076.7	1076.8	1077.1	1077.4	1077.5	1076.6	1074.2	1072.0
135°	1134.8	1134.3	1133.8	1133.4	1133.8	1134.3	1134.8	1135.2	1134.3	1131.8	1129.4
137.5°	1187.5	1186.7	1185.9	1185.0	1185.9	1186.7	1187.5	1188.3	1187.6	1185.2	1182.8
140°	1220.9	1219.8	1218.5	1217.4	1218.5	1219.8	1220.9	1222.2	1221.7	1219.5	1217.4
142.5°	1252.4	1251.2	1249.9	1248.8	1249.9	1251.2	1252.4	1253.6	1253.2	1251.2	1249.2
145°	1296.2	1295.0	1293.8	1292.6	1293.8	1295.0	1296.2	1297.4	1297.2	1295.5	1293.8
147.5°	1334.3	1333.2	1332.2	1331.2	1332.2	1333.2	1334.3	1335.2	1335.2	1333.9	1332.7
150°	1358.4	1357.2	1355.9	1354.8	1355.9	1357.2	1358.4	1359.6	1359.5	1358.1	1356.6
152.5°	1379.7	1378.0	1376.4	1374.8	1376.4	1378.0	1379.7	1381.3	1381.3	1379.8	1378.4
155°	1408.5	1406.7	1404.7	1402.8	1404.7	1406.7	1408.5	1410.5	1410.8	1409.3	1407.8
157.5°	1434.0	1432.1	1430.2	1428.3	1430.2	1432.1	1434.0	1435.8	1436.0	1434.3	1432.7
160°	1448.2	1446.5	1444.8	1443.1	1444.8	1446.5	1448.2	1449.9	1450.0	1448.6	1447.2
162.5°	1461.6	1459.5	1457.4	1455.4	1457.4	1459.5	1461.6	1463.7	1463.9	1462.2	1460.6
165°	1478.7	1477.0	1475.3	1473.6	1475.3	1477.0	1478.7	1480.4	1480.4	1478.7	1477.0
167.5°	1491.7	1489.6	1487.4	1485.2	1487.4	1489.6	1491.7	1494.0	1494.2	1492.5	1490.8
170°	1498.8	1496.6	1494.4	1492.2	1494.4	1496.6	1498.8	1500.9	1501.2	1499.5	1497.8
172.5°	1504.0	1501.8	1499.6	1497.4	1499.6	1501.8	1504.0	1506.2	1506.4	1504.7	1503.0
175°	1509.3	1506.9	1504.4	1502.0	1504.4	1506.9	1509.3	1511.7	1512.1	1510.4	1508.7
177.5°	1510.1	1508.3	1506.6	1504.9	1506.6	1508.3	1510.1	1511.8	1512.1	1510.6	1509.3
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331483-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	506.5	508.3	511.0	514.0	515.8	519.2	520.1	521.7	523.2	526.6	530.1
5°	477.2	480.1	486.8	490.4	495.4	501.3	505.2	509.3	513.7	521.4	528.5
7.5°	445.9	450.6	459.0	465.7	473.0	481.3	487.4	495.4	502.1	513.0	523.3
10°	425.0	431.7	439.2	447.3	457.4	466.3	474.8	484.9	493.0	506.0	518.2
12.5°	406.2	407.2	417.9	426.9	440.7	451.7	461.5	474.6	482.5	497.9	510.7
15°	373.4	379.4	389.1	396.2	412.6	426.6	440.4	454.0	463.1	482.1	498.9
17.5°	345.6	351.2	361.2	372.8	384.6	398.5	416.3	430.7	443.1	464.8	484.7
20°	328.1	335.0	345.2	357.1	367.5	382.6	398.1	414.5	427.8	452.4	475.6
22.5°	313.3	318.7	326.9	338.7	349.9	363.8	380.7	398.6	412.6	439.1	462.6
25°	292.3	296.8	302.0	311.7	324.5	339.7	352.8	372.6	393.0	417.7	446.2
27.5°	273.4	276.6	281.2	289.8	299.7	313.9	328.5	347.1	367.7	394.6	424.7
30°	261.9	263.9	268.6	275.7	285.4	296.6	311.4	329.1	350.3	377.4	407.3
32.5°	251.9	253.7	256.8	263.5	272.0	281.5	294.8	312.6	332.7	359.4	392.6
35°	236.8	238.2	240.9	246.3	251.0	260.3	271.4	287.7	306.5	332.0	366.4
37.5°	221.8	223.7	225.3	227.7	233.6	239.8	249.4	263.1	281.6	307.4	340.2
40°	211.9	213.5	216.0	217.0	221.8	227.3	235.1	247.7	266.4	289.9	321.9
42.5°	201.8	203.5	204.9	206.1	210.3	215.1	222.2	233.0	249.5	272.3	304.1
45°	188.2	188.4	189.8	192.1	194.0	197.5	202.6	211.9	224.6	246.1	274.9
47.5°	174.3	174.6	174.8	175.8	178.0	181.1	184.5	192.1	203.5	220.6	248.6
50°	165.1	164.7	165.1	165.9	167.3	170.0	173.8	179.2	188.6	204.6	230.3
52.5°	156.1	156.1	155.9	156.1	157.3	159.1	161.8	166.5	174.8	189.5	212.1
55°	142.6	141.6	141.8	141.0	142.9	143.2	145.3	149.1	156.4	166.5	187.8
57.5°	128.1	127.3	126.4	126.2	126.0	127.1	128.7	131.7	137.3	146.2	163.5
60°	118.9	117.9	116.6	116.3	116.3	116.9	117.7	119.9	125.2	133.0	147.2
62.5°	109.5	108.3	107.6	106.6	106.2	106.8	107.6	109.2	113.1	120.5	132.7
65°	95.0	93.5	92.6	92.4	91.9	91.4	91.8	93.4	96.4	102.3	112.0
67.5°	80.4	79.1	78.9	77.7	77.1	77.2	77.1	78.5	80.3	85.4	92.6
70°	70.9	69.9	69.5	68.5	68.0	67.7	67.2	68.5	70.3	74.5	80.8
72.5°	61.2	60.3	59.5	58.6	58.7	58.2	58.1	58.9	60.4	64.3	69.2
75°	47.2	47.4	46.4	45.4	45.2	44.8	44.8	45.4	46.0	49.0	52.9
77.5°	34.2	34.1	33.3	32.9	32.7	32.3	32.7	33.1	33.4	35.5	38.3
80°	26.1	26.1	25.1	25.1	24.9	24.3	24.9	24.5	25.3	27.4	29.3
82.5°	18.6	18.4	18.3	18.0	17.9	17.5	17.7	18.2	18.5	19.9	21.1
85°	9.1	9.1	8.9	8.7	8.9	8.7	8.9	9.1	9.3	9.9	11.0
87.5°	6.5	6.5	6.2	6.0	5.6	5.4	5.1	4.7	4.5	4.2	3.7
90°	23.0	21.8	19.9	17.9	16.0	14.1	11.8	9.1	6.4	3.7	1.1
92.5°	25.9	25.3	24.3	23.4	22.4	21.4	21.0	21.3	21.6	21.8	22.0
95°	43.8	42.5	40.8	39.1	37.5	35.8	38.9	46.9	54.9	62.9	70.9
97.5°	57.9	57.0	53.1	49.0	45.1	41.2	50.6	73.1	95.6	118.2	140.7
100°	64.1	62.2	58.1	53.9	49.8	45.7	60.3	93.5	126.6	159.9	193.1
102.5°	66.4	63.9	98.4	132.9	167.3	201.8	222.6	229.6	236.6	243.6	250.7
105°	69.2	66.5	132.7	198.9	265.1	331.3	360.7	353.4	346.2	338.9	331.6
107.5°	90.4	93.2	172.5	251.9	331.3	410.6	447.4	441.5	435.6	429.7	423.9
110°	166.7	190.9	260.9	331.0	401.1	471.1	503.5	498.5	493.4	488.3	483.2



TEST NUMBER: P331483-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	393.1	481.4	498.8	516.1	533.4	550.7	557.1	552.6	548.0	543.6	539.0
115°	560.8	673.1	667.0	660.9	654.9	648.8	643.7	639.5	635.4	631.3	627.2
117.5°	718.3	745.5	741.3	737.1	732.9	728.8	724.4	719.8	715.2	710.6	706.0
120°	802.5	799.5	795.2	790.9	786.5	782.1	778.1	774.5	770.8	767.2	763.6
122.5°	852.7	851.0	846.3	841.5	836.8	832.1	827.8	823.9	820.1	816.3	812.4
125°	923.5	921.8	917.1	912.5	907.9	903.3	899.4	896.3	893.1	889.9	886.8
127.5°	987.9	985.4	982.0	978.6	975.1	971.7	968.2	964.7	961.2	957.7	954.2
130°	1029.1	1026.4	1023.8	1021.1	1018.4	1015.7	1012.5	1008.6	1004.8	1000.9	997.0
132.5°	1069.7	1067.5	1064.8	1062.1	1059.4	1056.8	1053.8	1050.5	1047.2	1043.9	1040.6
135°	1127.0	1124.6	1122.4	1120.3	1118.0	1115.9	1112.9	1108.9	1105.1	1101.2	1097.3
137.5°	1180.4	1178.0	1175.5	1173.1	1170.6	1168.1	1165.6	1162.9	1160.1	1157.4	1154.7
140°	1215.1	1213.0	1210.3	1207.6	1205.0	1202.3	1200.0	1198.0	1196.1	1194.2	1192.2
142.5°	1247.2	1245.3	1242.2	1239.1	1236.1	1233.1	1230.7	1228.9	1227.2	1225.4	1223.7
145°	1292.1	1290.4	1286.3	1282.2	1278.1	1273.9	1272.0	1272.2	1272.5	1272.7	1272.9
147.5°	1331.4	1330.1	1326.1	1322.0	1317.9	1313.8	1312.2	1313.1	1314.1	1315.0	1315.9
150°	1355.1	1353.7	1349.8	1345.9	1342.0	1338.2	1337.0	1338.7	1340.5	1342.2	1343.9
152.5°	1377.0	1375.5	1371.8	1368.2	1364.4	1360.8	1359.9	1361.7	1363.6	1365.6	1367.4
155°	1406.4	1405.0	1402.0	1399.1	1396.2	1393.3	1392.9	1395.1	1397.3	1399.5	1401.7
157.5°	1431.0	1429.4	1427.4	1425.3	1423.3	1421.2	1421.1	1423.0	1424.8	1426.6	1428.5
160°	1445.6	1444.2	1442.8	1441.3	1439.8	1438.4	1438.4	1439.8	1441.3	1442.8	1444.2
162.5°	1458.9	1457.3	1456.1	1454.7	1453.5	1452.2	1452.3	1453.8	1455.3	1456.7	1458.2
165°	1475.3	1473.6	1472.9	1472.2	1471.5	1470.8	1471.1	1472.6	1474.0	1475.5	1476.9
167.5°	1489.1	1487.4	1486.7	1486.0	1485.4	1484.7	1485.1	1486.6	1488.0	1489.4	1490.9
170°	1496.1	1494.4	1493.9	1493.4	1492.9	1492.5	1492.9	1494.4	1495.8	1497.3	1498.8
172.5°	1501.3	1499.6	1499.1	1498.6	1498.2	1497.7	1498.2	1499.6	1501.1	1502.5	1504.0
175°	1507.0	1505.3	1504.9	1504.3	1503.9	1503.3	1504.0	1505.7	1507.3	1509.0	1510.7
177.5°	1508.0	1506.6	1506.4	1506.2	1506.0	1505.8	1506.4	1507.8	1509.1	1510.5	1511.8
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331483-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	529.9	530.7	533.2	535.8	538.8	539.6	540.8	539.8	539.4	542.4	544.7
5°	531.4	534.9	542.1	548.6	554.0	557.9	562.0	563.6	566.6	570.8	576.1
7.5°	529.6	536.7	547.9	557.3	567.6	575.0	580.8	585.8	591.7	599.8	608.6
10°	527.7	537.2	550.8	562.3	574.9	584.4	592.3	600.0	608.9	620.1	631.6
12.5°	524.1	535.4	552.4	566.1	582.2	591.6	602.2	618.8	628.4	643.9	660.1
15°	516.9	529.5	553.2	570.0	588.3	606.1	625.7	641.5	657.3	666.5	689.3
17.5°	506.3	524.7	551.0	570.6	593.8	621.8	643.9	661.8	680.0	694.8	706.3
20°	497.7	517.7	547.8	571.2	598.8	628.9	654.2	672.5	688.3	700.7	707.8
22.5°	486.9	512.1	541.3	568.8	604.0	633.8	660.4	674.8	688.0	694.0	696.8
25°	469.8	500.2	533.2	566.8	606.5	638.1	662.4	671.1	674.9	669.1	659.3
27.5°	451.3	485.2	523.8	562.9	604.9	635.3	652.7	651.4	644.9	625.8	610.6
30°	437.6	474.8	516.3	559.1	601.2	630.8	640.9	630.8	616.0	594.8	573.0
32.5°	423.1	461.7	508.4	553.6	594.4	620.5	622.6	605.2	582.3	558.1	531.1
35°	401.3	443.0	493.5	541.3	580.0	596.4	586.7	555.8	528.7	495.7	458.8
37.5°	376.6	422.7	473.2	523.3	558.3	562.6	538.4	506.0	467.7	428.9	385.5
40°	358.1	407.0	459.1	509.4	540.5	536.0	505.2	469.6	424.0	376.6	336.3
42.5°	341.6	390.4	443.4	492.9	517.7	505.5	469.6	425.8	376.8	332.2	295.2
45°	313.0	363.2	417.5	465.3	479.5	457.4	409.8	361.1	313.0	275.7	246.6
47.5°	285.2	334.8	388.6	430.6	435.6	405.9	353.9	303.9	262.4	232.1	211.5
50°	264.7	314.6	367.8	405.4	403.7	367.8	314.4	266.8	232.1	207.6	193.9
52.5°	246.5	293.6	344.6	378.8	370.1	331.1	280.0	237.7	209.3	190.1	177.6
55°	217.9	261.5	310.1	337.5	321.6	278.3	235.1	201.2	180.0	165.7	156.0
57.5°	189.7	230.5	272.2	289.0	271.5	231.5	195.6	170.9	155.0	144.4	138.0
60°	172.2	207.9	244.9	259.5	238.6	203.0	174.6	152.6	139.7	131.1	125.4
62.5°	154.7	186.6	221.6	229.5	210.4	180.3	155.2	136.8	126.4	118.6	113.2
65°	130.8	157.0	183.5	188.8	171.2	147.8	128.0	116.1	106.7	101.1	96.8
67.5°	107.4	128.3	147.1	151.3	135.9	119.8	105.4	95.0	88.7	84.0	80.3
70°	93.4	110.0	125.4	128.9	116.5	102.1	91.1	82.8	77.1	73.1	69.6
72.5°	78.6	92.5	105.3	107.6	97.6	86.5	77.6	71.0	66.0	63.4	60.1
75°	60.2	68.3	78.2	78.8	72.1	65.5	58.6	54.3	51.6	48.4	46.8
77.5°	42.4	48.8	54.5	55.6	51.6	47.1	43.2	39.9	37.6	36.1	34.6
80°	32.4	37.5	39.9	41.3	38.5	35.2	33.0	30.8	29.3	28.4	27.4
82.5°	23.2	26.3	28.5	29.7	28.1	26.1	24.0	22.6	21.6	20.8	20.4
85°	11.8	13.2	14.6	15.0	14.6	13.7	12.6	12.6	11.9	11.8	11.8
87.5°	4.8	6.0	6.5	7.6	7.7	8.0	8.5	8.6	8.9	9.0	9.1
90°	3.7	6.4	9.1	11.8	14.1	16.0	17.9	19.9	21.8	23.0	24.3
92.5°	21.8	21.6	21.3	21.0	21.4	22.4	23.4	24.3	25.3	25.9	26.6
95°	62.9	54.9	46.9	38.9	35.8	37.5	39.1	40.8	42.5	43.8	44.9
97.5°	118.2	95.6	73.1	50.6	41.2	45.1	49.0	53.1	57.0	57.9	58.9
100°	159.9	126.6	93.5	60.3	45.7	49.8	53.9	58.1	62.2	64.1	66.1
102.5°	243.6	236.6	229.6	222.6	201.8	167.3	132.9	98.4	63.9	66.4	68.9
105°	338.9	346.2	353.4	360.7	331.3	265.1	198.9	132.7	66.5	69.2	71.9
107.5°	429.7	435.6	441.5	447.4	410.6	331.3	251.9	172.5	93.2	90.4	87.7
110°	488.3	493.4	498.5	503.5	471.1	401.1	331.0	260.9	190.9	166.7	142.4





TEST NUMBER: P331483-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	543.6	548.0	552.6	557.1	550.7	533.4	516.1	498.8	481.4	393.1	304.6
115°	631.3	635.4	639.5	643.7	648.8	654.9	660.9	667.0	673.1	560.8	448.5
117.5°	710.6	715.2	719.8	724.4	728.8	732.9	737.1	741.3	745.5	718.3	691.2
120°	767.2	770.8	774.5	778.1	782.1	786.5	790.9	795.2	799.5	802.5	805.4
122.5°	816.3	820.1	823.9	827.8	832.1	836.8	841.5	846.3	851.0	852.7	854.5
125°	889.9	893.1	896.3	899.4	903.3	907.9	912.5	917.1	921.8	923.5	925.1
127.5°	957.7	961.2	964.7	968.2	971.7	975.1	978.6	982.0	985.4	987.9	990.3
130°	1000.9	1004.8	1008.6	1012.5	1015.7	1018.4	1021.1	1023.8	1026.4	1029.1	1031.8
132.5°	1043.9	1047.2	1050.5	1053.8	1056.8	1059.4	1062.1	1064.8	1067.5	1069.7	1072.0
135°	1101.2	1105.1	1108.9	1112.9	1115.9	1118.0	1120.3	1122.4	1124.6	1127.0	1129.4
137.5°	1157.4	1160.1	1162.9	1165.6	1168.1	1170.6	1173.1	1175.5	1178.0	1180.4	1182.8
140°	1194.2	1196.1	1198.0	1200.0	1202.3	1205.0	1207.6	1210.3	1213.0	1215.1	1217.4
142.5°	1225.4	1227.2	1228.9	1230.7	1233.1	1236.1	1239.1	1242.2	1245.3	1247.2	1249.2
145°	1272.7	1272.5	1272.2	1272.0	1273.9	1278.1	1282.2	1286.3	1290.4	1292.1	1293.8
147.5°	1315.0	1314.1	1313.1	1312.2	1313.8	1317.9	1322.0	1326.1	1330.1	1331.4	1332.7
150°	1342.2	1340.5	1338.7	1337.0	1338.2	1342.0	1345.9	1349.8	1353.7	1355.1	1356.6
152.5°	1365.6	1363.6	1361.7	1359.9	1360.8	1364.4	1368.2	1371.8	1375.5	1377.0	1378.4
155°	1399.5	1397.3	1395.1	1392.9	1393.3	1396.2	1399.1	1402.0	1405.0	1406.4	1407.8
157.5°	1426.6	1424.8	1423.0	1421.1	1421.2	1423.3	1425.3	1427.4	1429.4	1431.0	1432.7
160°	1442.8	1441.3	1439.8	1438.4	1438.4	1439.8	1441.3	1442.8	1444.2	1445.6	1447.2
162.5°	1456.7	1455.3	1453.8	1452.3	1452.2	1453.5	1454.7	1456.1	1457.3	1458.9	1460.6
165°	1475.5	1474.0	1472.6	1471.1	1470.8	1471.5	1472.2	1472.9	1473.6	1475.3	1477.0
167.5°	1489.4	1488.0	1486.6	1485.1	1484.7	1485.4	1486.0	1486.7	1487.4	1489.1	1490.8
170°	1497.3	1495.8	1494.4	1492.9	1492.5	1492.9	1493.4	1493.9	1494.4	1496.1	1497.8
172.5°	1502.5	1501.1	1499.6	1498.2	1497.7	1498.2	1498.6	1499.1	1499.6	1501.3	1503.0
175°	1509.0	1507.3	1505.7	1504.0	1503.3	1503.9	1504.3	1504.9	1505.3	1507.0	1508.7
177.5°	1510.5	1509.1	1507.8	1506.4	1505.8	1506.0	1506.2	1506.4	1506.6	1508.0	1509.3
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331483-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	546.7	548.9	548.9	549.3	551.9	551.5	551.3
5°	581.8	585.2	585.6	589.2	591.7	590.8	588.6
7.5°	614.8	621.3	626.2	628.8	632.0	634.0	633.1
10°	641.1	650.4	656.1	660.0	664.6	668.1	666.8
12.5°	664.9	676.0	683.9	690.5	691.0	695.4	692.4
15°	702.1	713.8	715.1	719.9	723.8	723.4	723.5
17.5°	714.3	718.1	718.9	719.0	719.1	717.6	714.5
20°	710.0	708.6	705.2	702.5	697.9	697.2	693.2
22.5°	689.2	684.7	676.1	670.4	663.2	661.3	660.1
25°	648.5	638.5	624.7	611.5	607.9	600.8	602.8
27.5°	592.4	576.9	562.0	551.3	541.6	531.0	534.0
30°	553.0	535.6	514.5	498.3	487.9	477.9	476.0
32.5°	506.0	480.5	457.0	442.7	426.9	420.4	413.5
35°	425.0	400.0	376.7	356.7	345.2	336.3	328.1
37.5°	352.1	323.4	304.6	288.4	280.0	274.9	276.3
40°	306.9	281.8	268.0	255.7	247.9	244.3	245.1
42.5°	270.3	251.5	240.1	231.7	226.2	224.2	223.7
45°	228.7	218.2	208.8	204.0	201.3	199.1	197.7
47.5°	200.4	191.7	186.5	183.6	181.3	179.1	179.0
50°	183.3	177.6	174.0	170.9	169.2	167.6	169.0
52.5°	170.3	165.1	161.5	158.8	158.1	156.7	156.6
55°	151.1	147.0	144.5	142.0	140.8	140.0	138.9
57.5°	133.6	129.7	127.3	125.8	123.5	122.7	122.3
60°	121.1	118.1	115.7	113.6	112.6	111.0	111.0
62.5°	109.6	106.6	104.3	102.8	101.1	100.5	100.7
65°	93.0	90.5	88.3	86.7	86.3	85.1	85.5
67.5°	77.7	76.1	73.7	72.8	72.1	71.4	70.9
70°	67.4	65.8	64.6	63.4	62.8	62.8	62.8
72.5°	58.9	56.9	56.2	54.7	55.0	54.4	53.7
75°	45.6	44.3	43.8	43.2	42.2	42.2	42.2
77.5°	33.5	33.2	32.5	31.8	31.6	31.4	31.5
80°	25.9	25.7	25.3	25.3	24.9	24.7	24.3
82.5°	20.0	19.4	19.2	19.0	18.9	18.9	18.8
85°	11.3	11.0	11.0	11.1	10.7	10.7	11.0
87.5°	9.5	9.7	9.7	9.8	10.1	10.0	10.1
90°	25.4	26.7	27.6	28.0	28.4	29.0	29.4
92.5°	27.2	27.8	28.3	28.5	28.9	29.2	29.4
95°	46.2	47.3	47.9	47.6	47.3	47.2	46.9
97.5°	59.8	60.8	61.4	61.7	62.1	62.3	62.6
100°	67.9	69.9	71.2	71.6	72.1	72.6	73.1
102.5°	71.5	74.0	75.6	76.2	77.0	77.7	78.3
105°	74.5	77.2	79.0	80.0	81.0	81.9	82.9
107.5°	85.0	82.3	81.4	82.4	83.4	84.4	85.3
110°	118.2	93.9	82.3	83.3	84.3	85.2	86.1



TEST NUMBER: P331483-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	216.2	127.8	83.9	84.7	85.5	86.2	87.0
115°	336.4	224.1	159.3	141.8	124.4	106.9	89.4
117.5°	664.0	636.9	594.6	537.3	479.9	422.6	365.2
120°	808.2	811.2	796.3	763.6	730.8	698.1	665.4
122.5°	856.3	858.0	855.7	849.4	843.0	836.7	830.3
125°	926.8	928.5	929.7	930.4	931.2	931.9	932.6
127.5°	992.8	995.3	996.7	996.8	996.9	997.0	997.2
130°	1034.5	1037.1	1038.3	1038.0	1037.9	1037.6	1037.3
132.5°	1074.2	1076.6	1077.5	1077.4	1077.1	1076.8	1076.7
135°	1131.8	1134.3	1135.2	1134.8	1134.3	1133.8	1133.4
137.5°	1185.2	1187.6	1188.3	1187.5	1186.7	1185.9	1185.0
140°	1219.5	1221.7	1222.2	1220.9	1219.8	1218.5	1217.4
142.5°	1251.2	1253.2	1253.6	1252.4	1251.2	1249.9	1248.8
145°	1295.5	1297.2	1297.4	1296.2	1295.0	1293.8	1292.6
147.5°	1333.9	1335.2	1335.2	1334.3	1333.2	1332.2	1331.2
150°	1358.1	1359.5	1359.6	1358.4	1357.2	1355.9	1354.8
152.5°	1379.8	1381.3	1381.3	1379.7	1378.0	1376.4	1374.8
155°	1409.3	1410.8	1410.5	1408.5	1406.7	1404.7	1402.8
157.5°	1434.3	1436.0	1435.8	1434.0	1432.1	1430.2	1428.3
160°	1448.6	1450.0	1449.9	1448.2	1446.5	1444.8	1443.1
162.5°	1462.2	1463.9	1463.7	1461.6	1459.5	1457.4	1455.4
165°	1478.7	1480.4	1480.4	1478.7	1477.0	1475.3	1473.6
167.5°	1492.5	1494.2	1494.0	1491.7	1489.6	1487.4	1485.2
170°	1499.5	1501.2	1500.9	1498.8	1496.6	1494.4	1492.2
172.5°	1504.7	1506.4	1506.2	1504.0	1501.8	1499.6	1497.4
175°	1510.4	1512.1	1511.7	1509.3	1506.9	1504.4	1502.0
177.5°	1510.6	1512.1	1511.8	1510.1	1508.3	1506.6	1504.9
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4

(END OF REPORT)