

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331842

Luminaire Tested: **S122RDIW-S865D1440U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331842
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S865D1440U835-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8302.5 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331842

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331842

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	37	35	30
3	81	72	65	60	73	66	60	55	55	50	47	44	41	39	34	32	31	26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	24	22	19
7	59	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19	17
8	54	43	35	30	50	40	33	29	33	28	25	28	24	21	22	20	18	15
9	51	39	32	27	46	36	30	26	31	26	22	26	22	19	21	18	16	14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30832	30832	30832	30832
5°	34434	31024	27509	31024
10°	38203	30808	23845	30808
15°	40082	30355	18788	30355
20°	34749	29687	16258	29687
25°	22789	28771	14516	28771
30°	15340	27660	13136	27660
35°	12423	26260	11848	26260
40°	11049	24738	10964	24738
45°	9999	22952	9787	22952
50°	9100	21182	9065	21182
55°	8555	19220	8442	19220
60°	7156	17418	7072	17418
65°	6032	15817	6842	15817
70°	5575	14124	6453	14124
75°	5215	12296	5958	12296
80°	4816	10116	5309	10116
85°	4428	7984	4668	7984



TEST NUMBER: P331842

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	2.2
10°-20°	504.4	6.1
20°-30°	650.0	7.8
30°-40°	617.7	7.4
40°-50°	529.1	6.4
50°-60°	402.9	4.9
60°-70°	254.7	3.1
70°-80°	127.2	1.5
80°-90°	40.2	0.5
90°-100°	113.2	1.4
100°-110°	351.6	4.2
110°-120°	601.0	7.2
120°-130°	790.3	9.5
130°-140°	887.0	10.7
140°-150°	869.7	10.5
150°-160°	729.5	8.8
160°-170°	483.8	5.8
170°-180°	169.1	2.0
0°-30°	1335.4	16.1
0°-40°	1953.1	23.5
0°-60°	2885.1	34.8
0°-90°	3307.3	39.8
90°-120°	1065.7	12.8
90°-150°	3612.8	43.5
90°-180°	4995.0	60.2
0°-180°	8302.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1910	1910	1910	1910	1910	
5°	2125	1914	1697	1914	2125	210
15°	2398	1816	1124	1816	2398	647
25°	1279	1615	815	1615	1279	607
35°	630	1332	601	1332	630	403
45°	438	1005	429	1005	438	339
55°	304	683	300	683	304	267
65°	158	414	179	414	158	161
75°	84	197	96	197	84	89
85°	24	43	25	43	24	27
90°	51	2	51	2	51	23
95°	94	78	94	78	94	104
105°	335	324	335	324	335	352
115°	603	603	603	603	603	596
125°	880	877	880	877	880	785
135°	1149	1135	1149	1135	1149	884
145°	1393	1378	1393	1378	1393	870
155°	1588	1575	1588	1575	1588	731
165°	1716	1714	1716	1714	1716	484
175°	1777	1783	1777	1783	1777	169
180°	1786	1786	1786	1786	1786	



TEST NUMBER: P331842

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1987.1	1988.7	1990.3	1986.5	1986.5	1983.4	1976.5	1971.2	1956.3	1954.2	1954.2
5°	2124.6	2123.2	2125.9	2117.3	2105.3	2102.7	2090.1	2073.5	2056.2	2037.0	2033.0
7.5°	2261.2	2259.2	2253.9	2252.5	2243.3	2223.3	2203.0	2181.4	2152.7	2124.7	2110.6
10°	2330.2	2352.1	2338.9	2315.6	2320.3	2289.1	2272.5	2244.0	2220.1	2178.3	2169.0
12.5°	2398.2	2406.8	2402.6	2389.4	2383.5	2361.8	2339.4	2314.6	2270.5	2233.0	2200.3
15°	2397.9	2410.5	2413.8	2409.9	2413.2	2411.9	2399.9	2379.3	2340.9	2299.7	2263.9
17.5°	2220.9	2229.7	2251.4	2266.1	2284.7	2324.0	2343.4	2350.9	2345.2	2321.7	2296.5
20°	2022.4	2007.8	2068.8	2100.0	2126.5	2192.9	2250.0	2271.9	2307.0	2306.4	2299.7
22.5°	1741.0	1744.5	1802.4	1839.4	1916.9	1983.2	2048.3	2130.7	2198.7	2243.7	2270.0
25°	1279.2	1304.5	1362.2	1412.6	1498.9	1622.3	1734.4	1864.5	1987.2	2084.1	2176.3
27.5°	960.8	962.6	1008.4	1055.0	1106.2	1207.3	1348.5	1503.8	1678.8	1823.2	1989.3
30°	822.8	818.8	838.0	866.5	910.3	988.6	1094.8	1247.4	1421.9	1639.5	1833.3
32.5°	725.1	725.3	739.8	760.9	797.3	850.1	922.8	1046.8	1211.7	1425.6	1652.8
35°	630.3	629.7	640.3	655.5	670.8	704.6	754.4	819.4	932.9	1132.6	1364.8
37.5°	562.4	565.3	570.5	580.0	596.9	615.7	645.6	689.3	770.1	888.2	1083.4
40°	524.2	525.5	532.8	540.8	550.7	565.3	589.9	625.0	684.1	778.3	920.9
42.5°	489.1	490.5	495.6	503.1	510.9	525.5	545.8	576.2	624.1	697.6	815.3
45°	437.9	437.9	442.6	445.9	454.5	467.8	484.4	509.6	542.7	597.2	675.5
47.5°	389.9	390.0	393.1	398.8	404.2	414.6	430.9	451.5	475.6	517.7	584.6
50°	362.3	362.9	364.9	369.6	372.9	382.2	394.8	412.7	437.9	470.4	526.2
52.5°	340.0	339.6	342.1	344.1	346.4	353.0	362.4	378.2	400.8	429.0	475.2
55°	303.9	301.2	305.2	308.5	310.5	313.2	318.5	328.4	347.7	371.6	406.1
57.5°	258.8	257.7	260.5	263.5	269.8	276.9	281.5	287.8	297.8	314.9	349.1
60°	221.6	221.6	227.6	229.6	236.9	246.2	255.5	260.8	270.7	282.0	307.2
62.5°	188.7	189.2	192.0	194.0	198.1	209.5	222.5	234.2	243.6	254.4	271.1
65°	157.9	159.2	159.2	160.6	163.2	165.9	171.2	180.5	197.1	212.3	224.9
67.5°	134.0	134.4	134.8	136.2	136.8	139.7	141.9	146.0	149.8	164.3	179.9
70°	118.1	120.1	119.4	120.8	121.4	122.7	125.4	127.4	133.4	136.7	146.0
72.5°	103.2	104.7	104.6	105.4	107.1	107.4	109.5	111.5	115.3	118.1	123.1
75°	83.6	82.9	83.6	84.9	85.6	86.3	86.3	88.9	90.9	93.6	96.9
77.5°	64.5	65.2	65.0	65.2	65.3	66.5	66.4	67.5	69.5	70.9	72.5
80°	51.8	52.4	51.8	52.4	53.1	53.7	53.1	53.7	55.7	57.1	57.1
82.5°	40.1	40.2	40.6	40.7	40.9	41.0	41.9	42.1	43.5	43.3	43.8
85°	23.9	23.2	23.2	23.2	23.9	24.5	23.9	23.9	24.5	24.5	24.5
87.5°	18.7	19.2	19.1	19.1	19.0	19.0	19.2	19.8	19.4	20.1	18.1
90°	51.3	50.9	50.6	50.3	49.9	50.1	50.8	51.4	52.1	52.8	45.4
92.5°	48.8	48.8	48.7	48.6	48.6	48.5	48.3	48.2	48.1	47.9	46.2
95°	93.5	94.1	94.8	95.5	96.1	96.5	96.5	96.5	96.5	96.5	95.8
97.5°	161.9	162.0	162.0	162.1	162.2	162.2	162.2	162.2	162.2	162.2	160.9
100°	206.5	206.9	207.2	207.5	207.9	208.0	208.0	208.0	208.0	208.0	207.0
102.5°	257.2	257.5	257.9	258.2	258.5	258.6	258.3	258.0	257.8	257.5	256.2
105°	334.7	334.7	334.7	334.7	334.7	334.3	333.7	333.0	332.3	331.7	331.0
107.5°	407.6	409.2	410.7	412.3	413.8	414.4	414.2	413.9	413.6	413.4	413.4
110°	464.3	465.3	466.3	467.3	468.3	468.9	468.9	468.9	468.9	468.9	468.9



TEST NUMBER: P331842

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	518.6	519.3	520.1	520.8	521.5	522.3	523.1	523.9	524.7	525.5	525.8
115°	603.0	604.0	605.0	606.0	607.0	607.7	608.0	608.4	608.7	609.1	609.7
117.5°	683.5	684.5	685.5	686.5	687.5	688.5	689.3	690.1	690.9	691.7	693.5
120°	740.2	741.2	742.2	743.2	744.2	744.7	744.7	744.7	744.7	744.7	747.4
122.5°	795.7	796.4	797.2	797.9	798.6	799.4	800.2	801.0	801.8	802.6	804.5
125°	880.4	880.8	881.1	881.4	881.8	882.4	883.4	884.4	885.4	886.4	887.5
127.5°	957.6	958.7	959.7	960.8	961.9	963.0	964.2	965.4	966.6	967.9	969.1
130°	1013.1	1014.4	1015.8	1017.1	1018.4	1019.4	1020.1	1020.8	1021.5	1022.1	1022.8
132.5°	1066.1	1067.2	1068.3	1069.4	1070.4	1071.7	1073.2	1074.7	1076.1	1077.6	1077.5
135°	1148.8	1149.8	1150.8	1151.8	1152.8	1153.5	1153.8	1154.1	1154.5	1154.8	1154.1
137.5°	1223.5	1224.9	1226.2	1227.6	1228.9	1229.7	1230.0	1230.2	1230.5	1230.8	1229.9
140°	1275.4	1276.7	1278.1	1279.4	1280.8	1281.4	1281.4	1281.4	1281.4	1281.4	1279.8
142.5°	1322.4	1323.8	1325.1	1326.5	1327.8	1328.3	1328.1	1327.8	1327.5	1327.3	1326.1
145°	1393.0	1394.3	1395.7	1397.0	1398.3	1398.8	1398.5	1398.2	1397.8	1397.5	1395.5
147.5°	1456.0	1457.3	1458.5	1459.8	1461.1	1461.4	1460.6	1459.9	1459.2	1458.4	1457.1
150°	1497.0	1498.0	1499.0	1500.0	1501.0	1501.0	1500.0	1499.0	1498.0	1497.0	1495.7
152.5°	1535.6	1536.9	1538.1	1539.4	1540.7	1540.7	1539.4	1538.1	1536.9	1535.6	1534.0
155°	1587.5	1588.5	1589.5	1590.5	1591.5	1591.1	1589.5	1587.8	1586.1	1584.4	1583.4
157.5°	1632.1	1633.7	1635.3	1636.9	1638.5	1638.2	1635.9	1633.6	1631.3	1629.1	1628.5
160°	1659.8	1661.2	1662.5	1663.8	1665.2	1664.8	1662.8	1660.8	1658.8	1656.8	1656.5
162.5°	1683.9	1685.6	1687.2	1688.8	1690.4	1690.0	1687.8	1685.5	1683.2	1680.9	1680.6
165°	1715.6	1717.3	1719.0	1720.6	1722.3	1722.0	1719.6	1717.3	1714.9	1712.6	1712.6
167.5°	1741.5	1743.3	1745.0	1746.8	1748.5	1748.2	1745.9	1743.5	1741.2	1738.8	1738.9
170°	1754.8	1756.8	1758.8	1760.8	1762.8	1762.7	1760.3	1758.0	1755.6	1753.3	1753.6
172.5°	1765.7	1767.7	1769.7	1771.7	1773.7	1773.5	1771.2	1768.8	1766.5	1764.1	1764.5
175°	1777.4	1779.4	1781.4	1783.4	1785.5	1785.3	1782.9	1780.6	1778.3	1775.9	1776.6
177.5°	1782.8	1784.4	1786.1	1787.7	1789.3	1789.3	1787.7	1786.1	1784.4	1782.8	1783.4
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331842

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1955.2	1951.0	1947.3	1937.7	1932.9	1922.3	1920.7	1920.2	1906.4	1893.1	1889.4
5°	2022.4	2011.8	1995.8	1977.3	1958.0	1938.1	1924.8	1914.2	1887.7	1862.5	1847.9
7.5°	2090.1	2067.2	2039.8	2004.6	1975.3	1942.4	1917.9	1896.0	1858.4	1822.3	1798.0
10°	2140.5	2103.3	2066.8	2018.4	1980.6	1943.4	1908.9	1879.1	1836.6	1788.8	1755.0
12.5°	2171.8	2130.9	2080.6	2033.3	1984.3	1937.0	1890.9	1852.5	1802.6	1753.3	1713.0
15°	2214.1	2170.3	2109.3	2041.6	1978.6	1916.9	1863.8	1816.0	1751.0	1691.9	1642.8
17.5°	2248.8	2188.5	2123.0	2044.7	1971.7	1893.3	1824.9	1763.9	1691.5	1620.3	1562.4
20°	2259.9	2200.2	2124.6	2046.3	1960.0	1867.8	1794.1	1727.8	1650.1	1572.5	1506.2
22.5°	2253.0	2206.6	2122.4	2028.7	1940.4	1843.9	1760.7	1683.7	1597.6	1518.4	1441.4
25°	2206.2	2190.2	2110.6	2008.4	1907.6	1795.5	1699.2	1615.0	1516.8	1431.9	1348.2
27.5°	2097.0	2131.3	2082.0	1973.1	1861.0	1740.8	1632.6	1536.7	1434.8	1339.2	1255.9
30°	1991.9	2070.8	2049.6	1948.7	1823.3	1705.2	1583.8	1483.6	1374.8	1276.6	1194.3
32.5°	1848.0	1978.4	1999.2	1914.8	1785.1	1655.3	1528.1	1428.4	1314.8	1211.3	1131.1
35°	1619.0	1814.0	1903.6	1849.9	1719.8	1579.8	1448.4	1332.3	1218.2	1116.0	1036.4
37.5°	1345.7	1611.4	1760.7	1764.5	1645.1	1499.5	1356.5	1241.2	1124.4	1024.1	937.9
40°	1168.4	1456.4	1650.8	1693.9	1593.1	1435.8	1291.2	1173.7	1059.6	961.4	862.6
42.5°	1009.2	1296.1	1535.1	1610.1	1529.9	1373.7	1228.6	1105.8	994.9	902.0	801.0
45°	816.1	1066.9	1330.3	1464.4	1419.9	1275.3	1122.0	1005.2	901.0	820.8	723.9
47.5°	688.5	865.2	1120.1	1301.4	1300.6	1168.6	1017.8	906.0	809.3	734.1	655.7
50°	615.7	769.7	985.3	1191.0	1208.2	1097.4	954.1	843.3	753.1	674.1	611.1
52.5°	550.4	677.3	871.2	1068.4	1117.5	1021.5	882.5	780.2	692.6	620.0	566.0
55°	465.1	563.3	710.6	895.1	969.4	901.7	778.3	682.8	611.8	550.7	504.3
57.5°	393.5	467.1	585.3	733.8	820.4	777.8	676.0	598.4	537.6	482.4	445.7
60°	348.3	408.7	508.9	633.0	728.5	698.7	611.8	539.4	487.7	439.9	405.4
62.5°	305.9	357.8	443.6	544.3	631.9	619.6	548.6	487.9	442.6	399.0	369.8
65°	246.2	284.0	351.0	430.0	500.3	506.3	455.2	414.0	373.6	339.1	313.2
67.5°	196.0	220.7	267.9	334.4	387.1	405.9	374.7	343.3	311.2	284.5	262.1
70°	165.2	185.1	219.6	273.4	321.8	341.7	323.8	299.2	271.4	249.5	230.2
72.5°	133.9	153.3	178.7	218.2	259.7	281.2	275.0	257.3	234.7	216.6	198.4
75°	100.9	106.8	124.1	150.6	183.1	201.7	206.4	197.1	179.1	165.2	154.6
77.5°	74.6	78.2	86.4	100.3	121.6	138.1	144.9	143.8	131.5	123.4	113.5
80°	59.7	61.7	65.7	71.7	87.6	104.2	108.8	108.8	100.2	96.9	86.9
82.5°	45.4	46.8	49.2	52.5	60.0	74.4	79.6	80.7	75.2	70.9	63.0
85°	25.9	25.2	26.5	28.5	29.9	33.8	41.8	43.1	41.8	36.5	34.5
87.5°	16.6	15.7	14.2	12.5	12.3	12.0	13.8	15.7	14.4	13.6	13.3
90°	38.0	30.7	23.3	17.6	13.6	9.5	5.5	1.5	5.5	9.5	13.6
92.5°	44.5	42.7	41.0	38.6	35.7	32.7	29.8	26.8	29.8	32.7	35.7
95°	95.1	94.5	93.8	91.8	88.4	85.1	81.7	78.4	81.7	85.1	88.4
97.5°	159.7	158.4	157.1	155.0	152.1	149.1	146.2	143.2	146.2	149.1	152.1
100°	206.0	205.0	204.0	202.2	199.5	196.8	194.1	191.5	194.1	196.8	199.5
102.5°	254.9	253.7	252.4	250.7	248.5	246.4	244.3	242.1	244.3	246.4	248.5
105°	330.3	329.7	329.0	328.1	327.1	326.1	325.1	324.1	325.1	326.1	327.1
107.5°	413.4	413.4	413.4	412.6	411.2	409.7	408.2	406.7	408.2	409.7	411.2
110°	468.9	468.9	468.9	467.8	465.8	463.8	461.8	459.8	461.8	463.8	465.8



TEST NUMBER: P331842

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	526.1	526.3	526.6	525.7	523.7	521.7	519.7	517.7	519.7	521.7	523.7
115°	610.4	611.1	611.7	611.1	609.1	607.0	605.0	603.0	605.0	607.0	609.1
117.5°	695.4	697.3	699.2	698.8	696.1	693.4	690.7	688.1	690.7	693.4	696.1
120°	750.1	752.8	755.5	755.5	752.8	750.1	747.4	744.7	747.4	750.1	752.8
122.5°	806.4	808.3	810.1	809.5	806.2	803.0	799.8	796.6	799.8	803.0	806.2
125°	888.5	889.5	890.5	889.5	886.4	883.4	880.4	877.4	880.4	883.4	886.4
127.5°	970.3	971.5	972.7	971.4	967.6	963.7	959.9	956.1	959.9	963.7	967.6
130°	1023.5	1024.1	1024.8	1023.0	1018.6	1014.3	1009.9	1005.5	1009.9	1014.3	1018.6
132.5°	1077.3	1077.2	1077.1	1075.2	1071.7	1068.1	1064.6	1061.0	1064.6	1068.1	1071.7
135°	1153.5	1152.8	1152.1	1149.9	1146.2	1142.6	1138.9	1135.2	1138.9	1142.6	1146.2
137.5°	1229.0	1228.2	1227.3	1225.3	1222.3	1219.3	1216.3	1213.3	1216.3	1219.3	1222.3
140°	1278.1	1276.4	1274.7	1272.4	1269.4	1266.4	1263.3	1260.3	1263.3	1266.4	1269.4
142.5°	1325.0	1323.8	1322.7	1320.6	1317.6	1314.6	1311.6	1308.6	1311.6	1314.6	1317.6
145°	1393.5	1391.5	1389.5	1387.3	1384.9	1382.6	1380.3	1377.9	1380.3	1382.6	1384.9
147.5°	1455.7	1454.4	1453.1	1451.0	1448.2	1445.3	1442.5	1439.7	1442.5	1445.3	1448.2
150°	1494.3	1493.0	1491.6	1490.0	1488.0	1486.0	1483.9	1481.9	1483.9	1486.0	1488.0
152.5°	1532.4	1530.8	1529.2	1527.4	1525.3	1523.3	1521.3	1519.3	1521.3	1523.3	1525.3
155°	1582.4	1581.4	1580.4	1579.4	1578.4	1577.4	1576.4	1575.4	1576.4	1577.4	1578.4
157.5°	1627.9	1627.3	1626.7	1626.0	1625.4	1624.7	1624.0	1623.3	1624.0	1624.7	1625.4
160°	1656.1	1655.8	1655.5	1655.0	1654.3	1653.6	1653.0	1652.3	1653.0	1653.6	1654.3
162.5°	1680.3	1679.9	1679.6	1679.4	1679.2	1679.1	1679.0	1678.8	1679.0	1679.1	1679.2
165°	1712.6	1712.6	1712.6	1712.8	1713.1	1713.4	1713.8	1714.1	1713.8	1713.4	1713.1
167.5°	1739.0	1739.0	1739.1	1739.6	1740.6	1741.6	1742.6	1743.6	1742.6	1741.6	1740.6
170°	1754.0	1754.3	1754.6	1755.3	1756.3	1757.3	1758.3	1759.3	1758.3	1757.3	1756.3
172.5°	1764.8	1765.2	1765.5	1766.2	1767.2	1768.2	1769.2	1770.2	1769.2	1768.2	1767.2
175°	1777.2	1777.9	1778.6	1779.4	1780.4	1781.4	1782.4	1783.4	1782.4	1781.4	1780.4
177.5°	1783.9	1784.4	1785.0	1785.7	1786.5	1787.3	1788.1	1788.9	1788.1	1787.3	1786.5
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331842

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1882.5	1878.8	1871.9	1861.3	1854.9	1843.8	1836.3	1840.6	1841.6	1840.6	1839.5
5°	1831.9	1818.0	1798.8	1780.2	1762.9	1744.4	1733.7	1729.1	1719.8	1714.5	1711.9
7.5°	1770.8	1746.8	1719.5	1687.2	1659.7	1630.9	1616.2	1608.9	1589.9	1579.5	1570.5
10°	1725.1	1687.3	1660.1	1617.6	1591.8	1553.9	1528.1	1528.7	1502.8	1488.2	1477.6
12.5°	1674.7	1633.2	1587.9	1549.7	1513.7	1483.3	1452.2	1439.5	1412.1	1398.0	1369.3
15°	1591.1	1542.7	1494.9	1443.1	1406.6	1359.5	1314.4	1259.3	1214.9	1176.4	1165.8
17.5°	1499.8	1439.8	1391.9	1331.1	1268.6	1189.4	1137.1	1105.1	1078.3	1058.0	1042.9
20°	1437.2	1376.1	1325.0	1233.5	1149.2	1095.5	1057.0	1032.4	1004.6	982.7	970.7
22.5°	1371.3	1307.6	1238.0	1135.8	1070.1	1027.0	992.7	964.5	945.6	928.5	917.6
25°	1277.9	1208.2	1093.5	1023.1	970.0	924.9	901.0	883.8	863.9	840.7	830.0
27.5°	1179.2	1068.4	986.0	933.7	883.0	853.7	832.2	806.4	788.6	778.2	767.1
30°	1105.4	994.6	930.2	873.2	837.3	804.8	779.6	765.0	747.8	729.9	722.6
32.5°	1023.1	934.6	872.9	825.4	789.0	761.3	741.4	717.8	705.3	694.3	679.0
35°	920.9	853.9	797.5	759.1	724.6	702.0	678.8	664.8	642.3	633.0	627.0
37.5°	834.4	776.3	734.2	693.6	666.3	641.3	627.1	605.0	595.2	582.3	569.7
40°	785.6	728.5	688.1	654.9	624.4	605.8	587.9	570.0	555.4	549.4	534.1
42.5°	735.7	689.3	648.8	612.4	592.0	572.3	549.7	536.5	521.4	511.7	502.3
45°	666.8	625.7	591.2	561.3	538.8	518.2	503.6	481.7	473.1	453.8	445.9
47.5°	606.3	568.1	535.2	506.8	484.8	471.4	450.0	432.9	419.1	407.3	397.0
50°	563.3	531.5	499.6	474.4	454.5	435.3	413.4	404.7	383.5	377.5	371.6
52.5°	524.0	493.8	464.6	439.9	420.0	401.3	382.0	370.8	356.4	350.5	346.1
55°	469.1	439.9	412.0	390.1	370.2	351.0	339.1	325.1	318.5	313.8	308.5
57.5°	413.9	387.6	366.3	344.1	324.1	308.8	295.0	286.6	279.7	273.6	267.3
60°	378.9	353.6	334.4	313.8	293.3	280.7	270.0	260.1	252.1	242.8	240.2
62.5°	341.7	319.7	302.0	282.0	264.1	252.5	242.4	233.0	223.5	209.9	206.2
65°	290.6	273.4	254.8	238.2	222.3	211.0	196.4	185.8	181.8	180.5	179.8
67.5°	244.4	228.1	212.2	195.2	180.7	170.3	162.8	161.2	158.4	157.6	155.8
70°	213.6	198.4	182.5	166.5	152.6	150.6	148.0	145.3	142.0	140.7	139.3
72.5°	186.0	170.3	154.3	141.6	135.6	133.1	130.4	127.8	125.5	124.2	123.4
75°	142.7	128.1	117.4	112.8	109.5	107.5	103.5	101.5	100.2	98.2	97.5
77.5°	102.7	94.5	89.6	86.7	83.2	81.1	78.8	76.8	75.4	75.0	73.9
80°	78.3	74.3	71.0	67.0	65.7	63.0	62.4	60.4	61.0	59.1	59.1
82.5°	60.8	55.7	52.9	51.1	49.8	47.6	47.0	46.0	46.2	44.7	44.7
85°	31.2	29.9	28.5	27.2	27.2	25.2	25.9	25.2	25.2	23.9	23.2
87.5°	13.6	14.2	14.6	16.1	17.6	18.5	18.4	17.7	17.6	17.4	16.9
90°	17.6	23.3	30.7	38.0	45.4	52.8	52.1	51.4	50.8	50.1	49.9
92.5°	38.6	41.0	42.7	44.5	46.2	47.9	48.1	48.2	48.3	48.5	48.6
95°	91.8	93.8	94.5	95.1	95.8	96.5	96.5	96.5	96.5	96.5	96.1
97.5°	155.0	157.1	158.4	159.7	160.9	162.2	162.2	162.2	162.2	162.2	162.2
100°	202.2	204.0	205.0	206.0	207.0	208.0	208.0	208.0	208.0	208.0	207.9
102.5°	250.7	252.4	253.7	254.9	256.2	257.5	257.8	258.0	258.3	258.6	258.5
105°	328.1	329.0	329.7	330.3	331.0	331.7	332.3	333.0	333.7	334.3	334.7
107.5°	412.6	413.4	413.4	413.4	413.4	413.4	413.6	413.9	414.2	414.4	413.8
110°	467.8	468.9	468.9	468.9	468.9	468.9	468.9	468.9	468.9	468.9	468.3



TEST NUMBER: P331842

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	525.7	526.6	526.3	526.1	525.8	525.5	524.7	523.9	523.1	522.3	521.5
115°	611.1	611.7	611.1	610.4	609.7	609.1	608.7	608.4	608.0	607.7	607.0
117.5°	698.8	699.2	697.3	695.4	693.5	691.7	690.9	690.1	689.3	688.5	687.5
120°	755.5	755.5	752.8	750.1	747.4	744.7	744.7	744.7	744.7	744.7	744.2
122.5°	809.5	810.1	808.3	806.4	804.5	802.6	801.8	801.0	800.2	799.4	798.6
125°	889.5	890.5	889.5	888.5	887.5	886.4	885.4	884.4	883.4	882.4	881.8
127.5°	971.4	972.7	971.5	970.3	969.1	967.9	966.6	965.4	964.2	963.0	961.9
130°	1023.0	1024.8	1024.1	1023.5	1022.8	1022.1	1021.5	1020.8	1020.1	1019.4	1018.4
132.5°	1075.2	1077.1	1077.2	1077.3	1077.5	1077.6	1076.1	1074.7	1073.2	1071.7	1070.4
135°	1149.9	1152.1	1152.8	1153.5	1154.1	1154.8	1154.5	1154.1	1153.8	1153.5	1152.8
137.5°	1225.3	1227.3	1228.2	1229.0	1229.9	1230.8	1230.5	1230.2	1230.0	1229.7	1228.9
140°	1272.4	1274.7	1276.4	1278.1	1279.8	1281.4	1281.4	1281.4	1281.4	1281.4	1280.8
142.5°	1320.6	1322.7	1323.8	1325.0	1326.1	1327.3	1327.5	1327.8	1328.1	1328.3	1327.8
145°	1387.3	1389.5	1391.5	1393.5	1395.5	1397.5	1397.8	1398.2	1398.5	1398.8	1398.3
147.5°	1451.0	1453.1	1454.4	1455.7	1457.1	1458.4	1459.2	1459.9	1460.6	1461.4	1461.1
150°	1490.0	1491.6	1493.0	1494.3	1495.7	1497.0	1498.0	1499.0	1500.0	1501.0	1501.0
152.5°	1527.4	1529.2	1530.8	1532.4	1534.0	1535.6	1536.9	1538.1	1539.4	1540.7	1540.7
155°	1579.4	1580.4	1581.4	1582.4	1583.4	1584.4	1586.1	1587.8	1589.5	1591.1	1591.5
157.5°	1626.0	1626.7	1627.3	1627.9	1628.5	1629.1	1631.3	1633.6	1635.9	1638.2	1638.5
160°	1655.0	1655.5	1655.8	1656.1	1656.5	1656.8	1658.8	1660.8	1662.8	1664.8	1665.2
162.5°	1679.4	1679.6	1679.9	1680.3	1680.6	1680.9	1683.2	1685.5	1687.8	1690.0	1690.4
165°	1712.8	1712.6	1712.6	1712.6	1712.6	1712.6	1714.9	1717.3	1719.6	1722.0	1722.3
167.5°	1739.6	1739.1	1739.0	1739.0	1738.9	1738.8	1741.2	1743.5	1745.9	1748.2	1748.5
170°	1755.3	1754.6	1754.3	1754.0	1753.6	1753.3	1755.6	1758.0	1760.3	1762.7	1762.8
172.5°	1766.2	1765.5	1765.2	1764.8	1764.5	1764.1	1766.5	1768.8	1771.2	1773.5	1773.7
175°	1779.4	1778.6	1777.9	1777.2	1776.6	1775.9	1778.3	1780.6	1782.9	1785.3	1785.5
177.5°	1785.7	1785.0	1784.4	1783.9	1783.4	1782.8	1784.4	1786.1	1787.7	1789.3	1789.3
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331842

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1833.7	1834.7	1833.1	1834.2	1833.1	1834.7	1833.7	1839.5	1840.6	1841.6	1840.6
5°	1708.5	1700.6	1699.2	1697.3	1699.2	1700.6	1708.5	1711.9	1714.5	1719.8	1729.1
7.5°	1559.1	1557.9	1554.6	1550.0	1554.6	1557.9	1559.1	1570.5	1579.5	1589.9	1608.9
10°	1463.0	1459.7	1459.1	1454.4	1459.1	1459.7	1463.0	1477.6	1488.2	1502.8	1528.7
12.5°	1350.5	1329.1	1326.9	1315.3	1326.9	1329.1	1350.5	1369.3	1398.0	1412.1	1439.5
15°	1149.9	1145.9	1132.6	1124.0	1132.6	1145.9	1149.9	1165.8	1176.4	1214.9	1259.3
17.5°	1035.2	1022.2	1018.1	1016.2	1018.1	1022.2	1035.2	1042.9	1058.0	1078.3	1105.1
20°	961.4	949.5	947.5	946.2	947.5	949.5	961.4	970.7	982.7	1004.6	1032.4
22.5°	910.5	898.0	892.8	888.8	892.8	898.0	910.5	917.6	928.5	945.6	964.5
25°	823.4	818.8	816.1	814.8	816.1	818.8	823.4	830.0	840.7	863.9	883.8
27.5°	755.3	745.1	743.1	739.7	743.1	745.1	755.3	767.1	778.2	788.6	806.4
30°	716.6	713.3	708.6	704.6	708.6	713.3	716.6	722.6	729.9	747.8	765.0
32.5°	670.9	668.2	664.0	662.2	664.0	668.2	670.9	679.0	694.3	705.3	717.8
35°	620.4	611.1	607.1	601.1	607.1	611.1	620.4	627.0	633.0	642.3	664.8
37.5°	566.9	562.0	556.4	558.4	556.4	562.0	566.9	569.7	582.3	595.2	605.0
40°	525.5	522.2	520.9	520.2	520.9	522.2	525.5	534.1	549.4	555.4	570.0
42.5°	492.6	483.4	480.0	479.8	480.0	483.4	492.6	502.3	511.7	521.4	536.5
45°	442.6	433.9	428.0	428.6	428.0	433.9	442.6	445.9	453.8	473.1	481.7
47.5°	391.3	391.1	387.4	388.6	387.4	391.1	391.3	397.0	407.3	419.1	432.9
50°	366.9	362.9	360.3	360.9	360.3	362.9	366.9	371.6	377.5	383.5	404.7
52.5°	343.6	340.1	338.0	340.8	338.0	340.1	343.6	346.1	350.5	356.4	370.8
55°	305.2	301.2	300.6	299.9	300.6	301.2	305.2	308.5	313.8	318.5	325.1
57.5°	262.4	259.7	255.7	254.0	255.7	259.7	262.4	267.3	273.6	279.7	286.6
60°	231.6	226.3	219.6	219.0	219.6	226.3	231.6	240.2	242.8	252.1	260.1
62.5°	203.4	202.4	201.0	200.9	201.0	202.4	203.4	206.2	209.9	223.5	233.0
65°	178.5	177.8	178.5	179.1	178.5	177.8	178.5	179.8	180.5	181.8	185.8
67.5°	155.5	154.3	153.1	153.7	153.1	154.3	155.5	155.8	157.6	158.4	161.2
70°	138.0	137.3	136.7	136.7	136.7	137.3	138.0	139.3	140.7	142.0	145.3
72.5°	121.0	120.9	120.2	119.7	120.2	120.9	121.0	123.4	124.2	125.5	127.8
75°	96.9	95.5	95.5	95.5	95.5	95.5	96.9	97.5	98.2	100.2	101.5
77.5°	73.8	73.1	72.5	71.9	72.5	73.1	73.8	73.9	75.0	75.4	76.8
80°	58.4	57.7	57.1	57.1	57.1	57.7	58.4	59.1	59.1	61.0	60.4
82.5°	44.6	43.9	43.8	43.3	43.8	43.9	44.6	44.7	44.7	46.2	46.0
85°	23.9	24.5	23.9	25.2	23.9	24.5	23.9	23.2	23.9	25.2	25.2
87.5°	17.0	16.5	17.1	16.6	17.1	16.5	17.0	16.9	17.4	17.6	17.7
90°	50.3	50.6	50.9	51.3	50.9	50.6	50.3	49.9	50.1	50.8	51.4
92.5°	48.6	48.7	48.8	48.8	48.8	48.7	48.6	48.6	48.5	48.3	48.2
95°	95.5	94.8	94.1	93.5	94.1	94.8	95.5	96.1	96.5	96.5	96.5
97.5°	162.1	162.0	162.0	161.9	162.0	162.0	162.1	162.2	162.2	162.2	162.2
100°	207.5	207.2	206.9	206.5	206.9	207.2	207.5	207.9	208.0	208.0	208.0
102.5°	258.2	257.9	257.5	257.2	257.5	257.9	258.2	258.5	258.6	258.3	258.0
105°	334.7	334.7	334.7	334.7	334.7	334.7	334.7	334.7	334.3	333.7	333.0
107.5°	412.3	410.7	409.2	407.6	409.2	410.7	412.3	413.8	414.4	414.2	413.9
110°	467.3	466.3	465.3	464.3	465.3	466.3	467.3	468.3	468.9	468.9	468.9



TEST NUMBER: P331842

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	520.8	520.1	519.3	518.6	519.3	520.1	520.8	521.5	522.3	523.1	523.9
115°	606.0	605.0	604.0	603.0	604.0	605.0	606.0	607.0	607.7	608.0	608.4
117.5°	686.5	685.5	684.5	683.5	684.5	685.5	686.5	687.5	688.5	689.3	690.1
120°	743.2	742.2	741.2	740.2	741.2	742.2	743.2	744.2	744.7	744.7	744.7
122.5°	797.9	797.2	796.4	795.7	796.4	797.2	797.9	798.6	799.4	800.2	801.0
125°	881.4	881.1	880.8	880.4	880.8	881.1	881.4	881.8	882.4	883.4	884.4
127.5°	960.8	959.7	958.7	957.6	958.7	959.7	960.8	961.9	963.0	964.2	965.4
130°	1017.1	1015.8	1014.4	1013.1	1014.4	1015.8	1017.1	1018.4	1019.4	1020.1	1020.8
132.5°	1069.4	1068.3	1067.2	1066.1	1067.2	1068.3	1069.4	1070.4	1071.7	1073.2	1074.7
135°	1151.8	1150.8	1149.8	1148.8	1149.8	1150.8	1151.8	1152.8	1153.5	1153.8	1154.1
137.5°	1227.6	1226.2	1224.9	1223.5	1224.9	1226.2	1227.6	1228.9	1229.7	1230.0	1230.2
140°	1279.4	1278.1	1276.7	1275.4	1276.7	1278.1	1279.4	1280.8	1281.4	1281.4	1281.4
142.5°	1326.5	1325.1	1323.8	1322.4	1323.8	1325.1	1326.5	1327.8	1328.3	1328.1	1327.8
145°	1397.0	1395.7	1394.3	1393.0	1394.3	1395.7	1397.0	1398.3	1398.8	1398.5	1398.2
147.5°	1459.8	1458.5	1457.3	1456.0	1457.3	1458.5	1459.8	1461.1	1461.4	1460.6	1459.9
150°	1500.0	1499.0	1498.0	1497.0	1498.0	1499.0	1500.0	1501.0	1501.0	1500.0	1499.0
152.5°	1539.4	1538.1	1536.9	1535.6	1536.9	1538.1	1539.4	1540.7	1540.7	1539.4	1538.1
155°	1590.5	1589.5	1588.5	1587.5	1588.5	1589.5	1590.5	1591.5	1591.1	1589.5	1587.8
157.5°	1636.9	1635.3	1633.7	1632.1	1633.7	1635.3	1636.9	1638.5	1638.2	1635.9	1633.6
160°	1663.8	1662.5	1661.2	1659.8	1661.2	1662.5	1663.8	1665.2	1664.8	1662.8	1660.8
162.5°	1688.8	1687.2	1685.6	1683.9	1685.6	1687.2	1688.8	1690.4	1690.0	1687.8	1685.5
165°	1720.6	1719.0	1717.3	1715.6	1717.3	1719.0	1720.6	1722.3	1722.0	1719.6	1717.3
167.5°	1746.8	1745.0	1743.3	1741.5	1743.3	1745.0	1746.8	1748.5	1748.2	1745.9	1743.5
170°	1760.8	1758.8	1756.8	1754.8	1756.8	1758.8	1760.8	1762.8	1762.7	1760.3	1758.0
172.5°	1771.7	1769.7	1767.7	1765.7	1767.7	1769.7	1771.7	1773.7	1773.5	1771.2	1768.8
175°	1783.4	1781.4	1779.4	1777.4	1779.4	1781.4	1783.4	1785.5	1785.3	1782.9	1780.6
177.5°	1787.7	1786.1	1784.4	1782.8	1784.4	1786.1	1787.7	1789.3	1789.3	1787.7	1786.1
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331842

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1836.3	1843.8	1854.9	1861.3	1871.9	1878.8	1882.5	1889.4	1893.1	1906.4	1920.2
5°	1733.7	1744.4	1762.9	1780.2	1798.8	1818.0	1831.9	1847.9	1862.5	1887.7	1914.2
7.5°	1616.2	1630.9	1659.7	1687.2	1719.5	1746.8	1770.8	1798.0	1822.3	1858.4	1896.0
10°	1528.1	1553.9	1591.8	1617.6	1660.1	1687.3	1725.1	1755.0	1788.8	1836.6	1879.1
12.5°	1452.2	1483.3	1513.7	1549.7	1587.9	1633.2	1674.7	1713.0	1753.3	1802.6	1852.5
15°	1314.4	1359.5	1406.6	1443.1	1494.9	1542.7	1591.1	1642.8	1691.9	1751.0	1816.0
17.5°	1137.1	1189.4	1268.6	1331.1	1391.9	1439.8	1499.8	1562.4	1620.3	1691.5	1763.9
20°	1057.0	1095.5	1149.2	1233.5	1325.0	1376.1	1437.2	1506.2	1572.5	1650.1	1727.8
22.5°	992.7	1027.0	1070.1	1135.8	1238.0	1307.6	1371.3	1441.4	1518.4	1597.6	1683.7
25°	901.0	924.9	970.0	1023.1	1093.5	1208.2	1277.9	1348.2	1431.9	1516.8	1615.0
27.5°	832.2	853.7	883.0	933.7	986.0	1068.4	1179.2	1255.9	1339.2	1434.8	1536.7
30°	779.6	804.8	837.3	873.2	930.2	994.6	1105.4	1194.3	1276.6	1374.8	1483.6
32.5°	741.4	761.3	789.0	825.4	872.9	934.6	1023.1	1131.1	1211.3	1314.8	1428.4
35°	678.8	702.0	724.6	759.1	797.5	853.9	920.9	1036.4	1116.0	1218.2	1332.3
37.5°	627.1	641.3	666.3	693.6	734.2	776.3	834.4	937.9	1024.1	1124.4	1241.2
40°	587.9	605.8	624.4	654.9	688.1	728.5	785.6	862.6	961.4	1059.6	1173.7
42.5°	549.7	572.3	592.0	612.4	648.8	689.3	735.7	801.0	902.0	994.9	1105.8
45°	503.6	518.2	538.8	561.3	591.2	625.7	666.8	723.9	820.8	901.0	1005.2
47.5°	450.0	471.4	484.8	506.8	535.2	568.1	606.3	655.7	734.1	809.3	906.0
50°	413.4	435.3	454.5	474.4	499.6	531.5	563.3	611.1	674.1	753.1	843.3
52.5°	382.0	401.3	420.0	439.9	464.6	493.8	524.0	566.0	620.0	692.6	780.2
55°	339.1	351.0	370.2	390.1	412.0	439.9	469.1	504.3	550.7	611.8	682.8
57.5°	295.0	308.8	324.1	344.1	366.3	387.6	413.9	445.7	482.4	537.6	598.4
60°	270.0	280.7	293.3	313.8	334.4	353.6	378.9	405.4	439.9	487.7	539.4
62.5°	242.4	252.5	264.1	282.0	302.0	319.7	341.7	369.8	399.0	442.6	487.9
65°	196.4	211.0	222.3	238.2	254.8	273.4	290.6	313.2	339.1	373.6	414.0
67.5°	162.8	170.3	180.7	195.2	212.2	228.1	244.4	262.1	284.5	311.2	343.3
70°	148.0	150.6	152.6	166.5	182.5	198.4	213.6	230.2	249.5	271.4	299.2
72.5°	130.4	133.1	135.6	141.6	154.3	170.3	186.0	198.4	216.6	234.7	257.3
75°	103.5	107.5	109.5	112.8	117.4	128.1	142.7	154.6	165.2	179.1	197.1
77.5°	78.8	81.1	83.2	86.7	89.6	94.5	102.7	113.5	123.4	131.5	143.8
80°	62.4	63.0	65.7	67.0	71.0	74.3	78.3	86.9	96.9	100.2	108.8
82.5°	47.0	47.6	49.8	51.1	52.9	55.7	60.8	63.0	70.9	75.2	80.7
85°	25.9	25.2	27.2	27.2	28.5	29.9	31.2	34.5	36.5	41.8	43.1
87.5°	18.4	18.5	17.6	16.1	14.6	14.2	13.6	13.3	13.6	14.4	15.7
90°	52.1	52.8	45.4	38.0	30.7	23.3	17.6	13.6	9.5	5.5	1.5
92.5°	48.1	47.9	46.2	44.5	42.7	41.0	38.6	35.7	32.7	29.8	26.8
95°	96.5	96.5	95.8	95.1	94.5	93.8	91.8	88.4	85.1	81.7	78.4
97.5°	162.2	162.2	160.9	159.7	158.4	157.1	155.0	152.1	149.1	146.2	143.2
100°	208.0	208.0	207.0	206.0	205.0	204.0	202.2	199.5	196.8	194.1	191.5
102.5°	257.8	257.5	256.2	254.9	253.7	252.4	250.7	248.5	246.4	244.3	242.1
105°	332.3	331.7	331.0	330.3	329.7	329.0	328.1	327.1	326.1	325.1	324.1
107.5°	413.6	413.4	413.4	413.4	413.4	413.4	412.6	411.2	409.7	408.2	406.7
110°	468.9	468.9	468.9	468.9	468.9	468.9	467.8	465.8	463.8	461.8	459.8



TEST NUMBER: P331842

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	524.7	525.5	525.8	526.1	526.3	526.6	525.7	523.7	521.7	519.7	517.7
115°	608.7	609.1	609.7	610.4	611.1	611.7	611.1	609.1	607.0	605.0	603.0
117.5°	690.9	691.7	693.5	695.4	697.3	699.2	698.8	696.1	693.4	690.7	688.1
120°	744.7	744.7	747.4	750.1	752.8	755.5	755.5	752.8	750.1	747.4	744.7
122.5°	801.8	802.6	804.5	806.4	808.3	810.1	809.5	806.2	803.0	799.8	796.6
125°	885.4	886.4	887.5	888.5	889.5	890.5	889.5	886.4	883.4	880.4	877.4
127.5°	966.6	967.9	969.1	970.3	971.5	972.7	971.4	967.6	963.7	959.9	956.1
130°	1021.5	1022.1	1022.8	1023.5	1024.1	1024.8	1023.0	1018.6	1014.3	1009.9	1005.5
132.5°	1076.1	1077.6	1077.5	1077.3	1077.2	1077.1	1075.2	1071.7	1068.1	1064.6	1061.0
135°	1154.5	1154.8	1154.1	1153.5	1152.8	1152.1	1149.9	1146.2	1142.6	1138.9	1135.2
137.5°	1230.5	1230.8	1229.9	1229.0	1228.2	1227.3	1225.3	1222.3	1219.3	1216.3	1213.3
140°	1281.4	1281.4	1279.8	1278.1	1276.4	1274.7	1272.4	1269.4	1266.4	1263.3	1260.3
142.5°	1327.5	1327.3	1326.1	1325.0	1323.8	1322.7	1320.6	1317.6	1314.6	1311.6	1308.6
145°	1397.8	1397.5	1395.5	1393.5	1391.5	1389.5	1387.3	1384.9	1382.6	1380.3	1377.9
147.5°	1459.2	1458.4	1457.1	1455.7	1454.4	1453.1	1451.0	1448.2	1445.3	1442.5	1439.7
150°	1498.0	1497.0	1495.7	1494.3	1493.0	1491.6	1490.0	1488.0	1486.0	1483.9	1481.9
152.5°	1536.9	1535.6	1534.0	1532.4	1530.8	1529.2	1527.4	1525.3	1523.3	1521.3	1519.3
155°	1586.1	1584.4	1583.4	1582.4	1581.4	1580.4	1579.4	1578.4	1577.4	1576.4	1575.4
157.5°	1631.3	1629.1	1628.5	1627.9	1627.3	1626.7	1626.0	1625.4	1624.7	1624.0	1623.3
160°	1658.8	1656.8	1656.5	1656.1	1655.8	1655.5	1655.0	1654.3	1653.6	1653.0	1652.3
162.5°	1683.2	1680.9	1680.6	1680.3	1679.9	1679.6	1679.4	1679.2	1679.1	1679.0	1678.8
165°	1714.9	1712.6	1712.6	1712.6	1712.6	1712.6	1712.8	1713.1	1713.4	1713.8	1714.1
167.5°	1741.2	1738.8	1738.9	1739.0	1739.0	1739.1	1739.6	1740.6	1741.6	1742.6	1743.6
170°	1755.6	1753.3	1753.6	1754.0	1754.3	1754.6	1755.3	1756.3	1757.3	1758.3	1759.3
172.5°	1766.5	1764.1	1764.5	1764.8	1765.2	1765.5	1766.2	1767.2	1768.2	1769.2	1770.2
175°	1778.3	1775.9	1776.6	1777.2	1777.9	1778.6	1779.4	1780.4	1781.4	1782.4	1783.4
177.5°	1784.4	1782.8	1783.4	1783.9	1784.4	1785.0	1785.7	1786.5	1787.3	1788.1	1788.9
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331842

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1920.7	1922.3	1932.9	1937.7	1947.3	1951.0	1955.2	1954.2	1954.2	1956.3	1971.2
5°	1924.8	1938.1	1958.0	1977.3	1995.8	2011.8	2022.4	2033.0	2037.0	2056.2	2073.5
7.5°	1917.9	1942.4	1975.3	2004.6	2039.8	2067.2	2090.1	2110.6	2124.7	2152.7	2181.4
10°	1908.9	1943.4	1980.6	2018.4	2066.8	2103.3	2140.5	2169.0	2178.3	2220.1	2244.0
12.5°	1890.9	1937.0	1984.3	2033.3	2080.6	2130.9	2171.8	2200.3	2233.0	2270.5	2314.6
15°	1863.8	1916.9	1978.6	2041.6	2109.3	2170.3	2214.1	2263.9	2299.7	2340.9	2379.3
17.5°	1824.9	1893.3	1971.7	2044.7	2123.0	2188.5	2248.8	2296.5	2321.7	2345.2	2350.9
20°	1794.1	1867.8	1960.0	2046.3	2124.6	2200.2	2259.9	2299.7	2306.4	2307.0	2271.9
22.5°	1760.7	1843.9	1940.4	2028.7	2122.4	2206.6	2253.0	2270.0	2243.7	2198.7	2130.7
25°	1699.2	1795.5	1907.6	2008.4	2110.6	2190.2	2206.2	2176.3	2084.1	1987.2	1864.5
27.5°	1632.6	1740.8	1861.0	1973.1	2082.0	2131.3	2097.0	1989.3	1823.2	1678.8	1503.8
30°	1583.8	1705.2	1823.3	1948.7	2049.6	2070.8	1991.9	1833.3	1639.5	1421.9	1247.4
32.5°	1528.1	1655.3	1785.1	1914.8	1999.2	1978.4	1848.0	1652.8	1425.6	1211.7	1046.8
35°	1448.4	1579.8	1719.8	1849.9	1903.6	1814.0	1619.0	1364.8	1132.6	932.9	819.4
37.5°	1356.5	1499.5	1645.1	1764.5	1760.7	1611.4	1345.7	1083.4	888.2	770.1	689.3
40°	1291.2	1435.8	1593.1	1693.9	1650.8	1456.4	1168.4	920.9	778.3	684.1	625.0
42.5°	1228.6	1373.7	1529.9	1610.1	1535.1	1296.1	1009.2	815.3	697.6	624.1	576.2
45°	1122.0	1275.3	1419.9	1464.4	1330.3	1066.9	816.1	675.5	597.2	542.7	509.6
47.5°	1017.8	1168.6	1300.6	1301.4	1120.1	865.2	688.5	584.6	517.7	475.6	451.5
50°	954.1	1097.4	1208.2	1191.0	985.3	769.7	615.7	526.2	470.4	437.9	412.7
52.5°	882.5	1021.5	1117.5	1068.4	871.2	677.3	550.4	475.2	429.0	400.8	378.2
55°	778.3	901.7	969.4	895.1	710.6	563.3	465.1	406.1	371.6	347.7	328.4
57.5°	676.0	777.8	820.4	733.8	585.3	467.1	393.5	349.1	314.9	297.8	287.8
60°	611.8	698.7	728.5	633.0	508.9	408.7	348.3	307.2	282.0	270.7	260.8
62.5°	548.6	619.6	631.9	544.3	443.6	357.8	305.9	271.1	254.4	243.6	234.2
65°	455.2	506.3	500.3	430.0	351.0	284.0	246.2	224.9	212.3	197.1	180.5
67.5°	374.7	405.9	387.1	334.4	267.9	220.7	196.0	179.9	164.3	149.8	146.0
70°	323.8	341.7	321.8	273.4	219.6	185.1	165.2	146.0	136.7	133.4	127.4
72.5°	275.0	281.2	259.7	218.2	178.7	153.3	133.9	123.1	118.1	115.3	111.5
75°	206.4	201.7	183.1	150.6	124.1	106.8	100.9	96.9	93.6	90.9	88.9
77.5°	144.9	138.1	121.6	100.3	86.4	78.2	74.6	72.5	70.9	69.5	67.5
80°	108.8	104.2	87.6	71.7	65.7	61.7	59.7	57.1	57.1	55.7	53.7
82.5°	79.6	74.4	60.0	52.5	49.2	46.8	45.4	43.8	43.3	43.5	42.1
85°	41.8	33.8	29.9	28.5	26.5	25.2	25.9	24.5	24.5	24.5	23.9
87.5°	13.8	12.0	12.3	12.5	14.2	15.7	16.6	18.1	20.1	19.4	19.8
90°	5.5	9.5	13.6	17.6	23.3	30.7	38.0	45.4	52.8	52.1	51.4
92.5°	29.8	32.7	35.7	38.6	41.0	42.7	44.5	46.2	47.9	48.1	48.2
95°	81.7	85.1	88.4	91.8	93.8	94.5	95.1	95.8	96.5	96.5	96.5
97.5°	146.2	149.1	152.1	155.0	157.1	158.4	159.7	160.9	162.2	162.2	162.2
100°	194.1	196.8	199.5	202.2	204.0	205.0	206.0	207.0	208.0	208.0	208.0
102.5°	244.3	246.4	248.5	250.7	252.4	253.7	254.9	256.2	257.5	257.8	258.0
105°	325.1	326.1	327.1	328.1	329.0	329.7	330.3	331.0	331.7	332.3	333.0
107.5°	408.2	409.7	411.2	412.6	413.4	413.4	413.4	413.4	413.4	413.6	413.9
110°	461.8	463.8	465.8	467.8	468.9	468.9	468.9	468.9	468.9	468.9	468.9



TEST NUMBER: P331842

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	519.7	521.7	523.7	525.7	526.6	526.3	526.1	525.8	525.5	524.7	523.9
115°	605.0	607.0	609.1	611.1	611.7	611.1	610.4	609.7	609.1	608.7	608.4
117.5°	690.7	693.4	696.1	698.8	699.2	697.3	695.4	693.5	691.7	690.9	690.1
120°	747.4	750.1	752.8	755.5	755.5	752.8	750.1	747.4	744.7	744.7	744.7
122.5°	799.8	803.0	806.2	809.5	810.1	808.3	806.4	804.5	802.6	801.8	801.0
125°	880.4	883.4	886.4	889.5	890.5	889.5	888.5	887.5	886.4	885.4	884.4
127.5°	959.9	963.7	967.6	971.4	972.7	971.5	970.3	969.1	967.9	966.6	965.4
130°	1009.9	1014.3	1018.6	1023.0	1024.8	1024.1	1023.5	1022.8	1022.1	1021.5	1020.8
132.5°	1064.6	1068.1	1071.7	1075.2	1077.1	1077.2	1077.3	1077.5	1077.6	1076.1	1074.7
135°	1138.9	1142.6	1146.2	1149.9	1152.1	1152.8	1153.5	1154.1	1154.8	1154.5	1154.1
137.5°	1216.3	1219.3	1222.3	1225.3	1227.3	1228.2	1229.0	1229.9	1230.8	1230.5	1230.2
140°	1263.3	1266.4	1269.4	1272.4	1274.7	1276.4	1278.1	1279.8	1281.4	1281.4	1281.4
142.5°	1311.6	1314.6	1317.6	1320.6	1322.7	1323.8	1325.0	1326.1	1327.3	1327.5	1327.8
145°	1380.3	1382.6	1384.9	1387.3	1389.5	1391.5	1393.5	1395.5	1397.5	1397.8	1398.2
147.5°	1442.5	1445.3	1448.2	1451.0	1453.1	1454.4	1455.7	1457.1	1458.4	1459.2	1459.9
150°	1483.9	1486.0	1488.0	1490.0	1491.6	1493.0	1494.3	1495.7	1497.0	1498.0	1499.0
152.5°	1521.3	1523.3	1525.3	1527.4	1529.2	1530.8	1532.4	1534.0	1535.6	1536.9	1538.1
155°	1576.4	1577.4	1578.4	1579.4	1580.4	1581.4	1582.4	1583.4	1584.4	1586.1	1587.8
157.5°	1624.0	1624.7	1625.4	1626.0	1626.7	1627.3	1627.9	1628.5	1629.1	1631.3	1633.6
160°	1653.0	1653.6	1654.3	1655.0	1655.5	1655.8	1656.1	1656.5	1656.8	1658.8	1660.8
162.5°	1679.0	1679.1	1679.2	1679.4	1679.6	1679.9	1680.3	1680.6	1680.9	1683.2	1685.5
165°	1713.8	1713.4	1713.1	1712.8	1712.6	1712.6	1712.6	1712.6	1712.6	1714.9	1717.3
167.5°	1742.6	1741.6	1740.6	1739.6	1739.1	1739.0	1739.0	1738.9	1738.8	1741.2	1743.5
170°	1758.3	1757.3	1756.3	1755.3	1754.6	1754.3	1754.0	1753.6	1753.3	1755.6	1758.0
172.5°	1769.2	1768.2	1767.2	1766.2	1765.5	1765.2	1764.8	1764.5	1764.1	1766.5	1768.8
175°	1782.4	1781.4	1780.4	1779.4	1778.6	1777.9	1777.2	1776.6	1775.9	1778.3	1780.6
177.5°	1788.1	1787.3	1786.5	1785.7	1785.0	1784.4	1783.9	1783.4	1782.8	1784.4	1786.1
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331842

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1976.5	1983.4	1986.5	1986.5	1990.3	1988.7	1987.1
5°	2090.1	2102.7	2105.3	2117.3	2125.9	2123.2	2124.6
7.5°	2203.0	2223.3	2243.3	2252.5	2253.9	2259.2	2261.2
10°	2272.5	2289.1	2320.3	2315.6	2338.9	2352.1	2330.2
12.5°	2339.4	2361.8	2383.5	2389.4	2402.6	2406.8	2398.2
15°	2399.9	2411.9	2413.2	2409.9	2413.8	2410.5	2397.9
17.5°	2343.4	2324.0	2284.7	2266.1	2251.4	2229.7	2220.9
20°	2250.0	2192.9	2126.5	2100.0	2068.8	2007.8	2022.4
22.5°	2048.3	1983.2	1916.9	1839.4	1802.4	1744.5	1741.0
25°	1734.4	1622.3	1498.9	1412.6	1362.2	1304.5	1279.2
27.5°	1348.5	1207.3	1106.2	1055.0	1008.4	962.6	960.8
30°	1094.8	988.6	910.3	866.5	838.0	818.8	822.8
32.5°	922.8	850.1	797.3	760.9	739.8	725.3	725.1
35°	754.4	704.6	670.8	655.5	640.3	629.7	630.3
37.5°	645.6	615.7	596.9	580.0	570.5	565.3	562.4
40°	589.9	565.3	550.7	540.8	532.8	525.5	524.2
42.5°	545.8	525.5	510.9	503.1	495.6	490.5	489.1
45°	484.4	467.8	454.5	445.9	442.6	437.9	437.9
47.5°	430.9	414.6	404.2	398.8	393.1	390.0	389.9
50°	394.8	382.2	372.9	369.6	364.9	362.9	362.3
52.5°	362.4	353.0	346.4	344.1	342.1	339.6	340.0
55°	318.5	313.2	310.5	308.5	305.2	301.2	303.9
57.5°	281.5	276.9	269.8	263.5	260.5	257.7	258.8
60°	255.5	246.2	236.9	229.6	227.6	221.6	221.6
62.5°	222.5	209.5	198.1	194.0	192.0	189.2	188.7
65°	171.2	165.9	163.2	160.6	159.2	159.2	157.9
67.5°	141.9	139.7	136.8	136.2	134.8	134.4	134.0
70°	125.4	122.7	121.4	120.8	119.4	120.1	118.1
72.5°	109.5	107.4	107.1	105.4	104.6	104.7	103.2
75°	86.3	86.3	85.6	84.9	83.6	82.9	83.6
77.5°	66.4	66.5	65.3	65.2	65.0	65.2	64.5
80°	53.1	53.7	53.1	52.4	51.8	52.4	51.8
82.5°	41.9	41.0	40.9	40.7	40.6	40.2	40.1
85°	23.9	24.5	23.9	23.2	23.2	23.2	23.9
87.5°	19.2	19.0	19.0	19.1	19.1	19.2	18.7
90°	50.8	50.1	49.9	50.3	50.6	50.9	51.3
92.5°	48.3	48.5	48.6	48.6	48.7	48.8	48.8
95°	96.5	96.5	96.1	95.5	94.8	94.1	93.5
97.5°	162.2	162.2	162.2	162.1	162.0	162.0	161.9
100°	208.0	208.0	207.9	207.5	207.2	206.9	206.5
102.5°	258.3	258.6	258.5	258.2	257.9	257.5	257.2
105°	333.7	334.3	334.7	334.7	334.7	334.7	334.7
107.5°	414.2	414.4	413.8	412.3	410.7	409.2	407.6
110°	468.9	468.9	468.3	467.3	466.3	465.3	464.3



TEST NUMBER: P331842

CATALOG NUMBER: S122RDIW-S865D1440U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	523.1	522.3	521.5	520.8	520.1	519.3	518.6
115°	608.0	607.7	607.0	606.0	605.0	604.0	603.0
117.5°	689.3	688.5	687.5	686.5	685.5	684.5	683.5
120°	744.7	744.7	744.2	743.2	742.2	741.2	740.2
122.5°	800.2	799.4	798.6	797.9	797.2	796.4	795.7
125°	883.4	882.4	881.8	881.4	881.1	880.8	880.4
127.5°	964.2	963.0	961.9	960.8	959.7	958.7	957.6
130°	1020.1	1019.4	1018.4	1017.1	1015.8	1014.4	1013.1
132.5°	1073.2	1071.7	1070.4	1069.4	1068.3	1067.2	1066.1
135°	1153.8	1153.5	1152.8	1151.8	1150.8	1149.8	1148.8
137.5°	1230.0	1229.7	1228.9	1227.6	1226.2	1224.9	1223.5
140°	1281.4	1281.4	1280.8	1279.4	1278.1	1276.7	1275.4
142.5°	1328.1	1328.3	1327.8	1326.5	1325.1	1323.8	1322.4
145°	1398.5	1398.8	1398.3	1397.0	1395.7	1394.3	1393.0
147.5°	1460.6	1461.4	1461.1	1459.8	1458.5	1457.3	1456.0
150°	1500.0	1501.0	1501.0	1500.0	1499.0	1498.0	1497.0
152.5°	1539.4	1540.7	1540.7	1539.4	1538.1	1536.9	1535.6
155°	1589.5	1591.1	1591.5	1590.5	1589.5	1588.5	1587.5
157.5°	1635.9	1638.2	1638.5	1636.9	1635.3	1633.7	1632.1
160°	1662.8	1664.8	1665.2	1663.8	1662.5	1661.2	1659.8
162.5°	1687.8	1690.0	1690.4	1688.8	1687.2	1685.6	1683.9
165°	1719.6	1722.0	1722.3	1720.6	1719.0	1717.3	1715.6
167.5°	1745.9	1748.2	1748.5	1746.8	1745.0	1743.3	1741.5
170°	1760.3	1762.7	1762.8	1760.8	1758.8	1756.8	1754.8
172.5°	1771.2	1773.5	1773.7	1771.7	1769.7	1767.7	1765.7
175°	1782.9	1785.3	1785.5	1783.4	1781.4	1779.4	1777.4
177.5°	1787.7	1789.3	1789.3	1787.7	1786.1	1784.4	1782.8
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5

(END OF REPORT)