

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331487-940

Luminaire Tested: **S122DIW-S290D1240U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331487-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D1240U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5493.2 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331487-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331487-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	20
1	91	87	83	80	80	77	74	71	58	56	54	41	40	38	25	24	24	16
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14
3	75	66	60	54	66	59	53	48	45	41	38	32	29	27	19	18	17	12
4	69	59	51	46	61	52	46	41	40	35	32	28	25	23	17	16	15	10
5	63	52	44	39	55	46	40	35	35	31	27	25	22	20	15	14	13	9
6	58	47	39	33	51	41	35	30	32	27	24	23	20	17	14	12	11	8
7	53	42	34	29	47	37	31	26	29	24	21	20	17	15	13	11	10	7
8	49	38	30	25	44	34	27	23	26	21	18	19	16	13	12	10	9	6
9	46	34	27	22	40	31	24	20	24	19	16	17	14	12	11	9	8	5
10	43	31	24	20	38	28	22	18	22	17	14	16	13	11	10	8	7	5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6801	6801	6801
5°	6827	6729	6770
10°	6787	6661	6694
15°	6703	6574	6569
20°	6584	6445	6438
25°	6465	6285	6285
30°	6315	6139	6087
35°	6173	5964	5876
40°	5994	5788	5678
45°	5818	5613	5476
50°	5627	5433	5242
55°	5427	5225	5027
60°	5205	4970	4789
65°	4967	4722	4504
70°	4664	4414	4206
75°	4242	4067	3968
80°	3766	3654	3468
85°	3075	2927	2631



TEST NUMBER: P331487-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.6	0.7
10°-20°	111.5	2.0
20°-30°	163.8	3.0
30°-40°	190.3	3.5
40°-50°	190.1	3.5
50°-60°	165.8	3.0
60°-70°	122.6	2.2
70°-80°	69.4	1.3
80°-90°	22.4	0.4
90°-100°	50.3	0.9
100°-110°	184.4	3.4
110°-120°	492.9	9.0
120°-130°	813.7	14.8
130°-140°	865.3	15.8
140°-150°	804.3	14.6
150°-160°	646.7	11.8
160°-170°	416.7	7.6
170°-180°	143.4	2.6
0°-30°	314.9	5.7
0°-40°	505.2	9.2
0°-60°	861.1	15.7
0°-90°	1075.5	19.6
90°-120°	727.6	13.2
90°-150°	3210.9	58.5
90°-180°	4418.0	80.4
0°-180°	5493.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	421	421	421	421	421	
5°	421	420	415	418	418	40
15°	401	398	393	395	393	113
25°	363	360	353	354	353	167
35°	313	309	303	300	298	195
45°	255	252	246	242	240	197
55°	193	190	186	181	179	172
65°	130	128	124	120	118	129
75°	68	67	65	63	64	73
85°	17	16	16	15	14	19
90°	1	13	22	27	29	4
95°	71	37	42	48	47	87
105°	332	346	66	78	83	354
115°	627	646	673	192	89	617
125°	887	901	922	929	933	790
135°	1097	1114	1125	1135	1133	847
145°	1273	1273	1290	1297	1293	796
155°	1402	1393	1405	1411	1403	646
165°	1477	1471	1474	1480	1474	417
175°	1511	1504	1505	1512	1502	144
180°	1507	1507	1507	1507	1507	



TEST NUMBER: P331487-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2
2.5°	423.2	422.8	422.5	422.1	421.8	421.2	420.4	419.6	418.8	418.0	418.7
5°	421.2	420.9	420.5	420.2	419.8	419.2	418.2	417.2	416.2	415.2	415.9
7.5°	417.6	417.0	416.4	415.9	415.4	414.6	413.6	412.5	411.5	410.5	411.3
10°	414.0	413.4	412.8	412.1	411.4	410.6	409.6	408.5	407.4	406.3	407.0
12.5°	409.1	408.6	408.0	407.4	406.9	406.1	405.0	403.9	402.9	401.8	402.3
15°	401.0	400.5	399.9	399.4	398.9	398.1	396.8	395.7	394.5	393.3	393.7
17.5°	390.7	390.1	389.6	389.1	388.5	387.6	386.5	385.2	384.1	382.9	383.3
20°	383.2	382.6	382.1	381.6	381.0	380.1	378.9	377.6	376.4	375.1	375.4
22.5°	375.8	375.0	374.3	373.4	372.7	371.8	370.6	369.3	368.2	367.0	367.0
25°	362.9	362.2	361.5	360.8	360.1	358.9	357.4	355.9	354.4	352.8	353.0
27.5°	348.4	347.8	347.1	346.4	345.8	344.8	343.7	342.4	341.3	340.0	339.7
30°	338.7	338.0	337.2	336.5	335.7	334.7	333.4	332.1	330.6	329.3	329.0
32.5°	328.2	327.7	327.2	326.5	326.0	324.9	323.5	322.2	320.7	319.3	318.8
35°	313.2	312.2	311.3	310.4	309.5	308.4	306.9	305.5	304.1	302.6	302.0
37.5°	296.0	295.2	294.4	293.6	292.8	291.8	290.3	288.9	287.4	286.0	285.3
40°	284.4	283.7	282.9	282.2	281.5	280.4	278.9	277.5	276.1	274.6	273.8
42.5°	273.0	272.3	271.6	270.9	270.2	269.0	267.6	266.2	264.7	263.3	262.4
45°	254.8	254.1	253.5	252.9	252.3	251.3	249.9	248.6	247.3	245.8	244.9
47.5°	236.7	236.0	235.5	234.9	234.3	233.3	231.8	230.5	229.1	227.7	226.6
50°	224.0	223.6	223.1	222.7	222.2	221.3	220.1	218.8	217.6	216.3	215.1
52.5°	211.7	211.1	210.5	209.9	209.3	208.4	207.2	206.1	204.8	203.7	202.6
55°	192.8	192.3	191.7	191.2	190.6	189.8	188.8	187.7	186.6	185.6	184.4
57.5°	173.9	173.4	173.0	172.5	172.1	171.3	170.1	169.0	167.7	166.6	165.5
60°	161.2	160.9	160.5	160.2	159.8	159.0	157.7	156.5	155.2	153.9	152.9
62.5°	148.9	148.3	147.8	147.2	146.6	145.8	144.8	143.9	142.9	142.0	141.0
65°	130.0	129.5	128.9	128.4	127.9	127.2	126.3	125.4	124.5	123.6	122.7
67.5°	110.8	110.4	109.9	109.5	109.1	108.5	107.6	106.8	106.0	105.2	104.6
70°	98.8	98.4	98.1	97.7	97.4	96.8	96.0	95.2	94.3	93.5	92.9
72.5°	86.5	86.1	85.8	85.4	85.1	84.6	84.1	83.6	83.1	82.6	81.9
75°	68.0	67.9	67.7	67.5	67.3	67.1	66.6	66.1	65.6	65.2	64.6
77.5°	51.5	51.2	50.9	50.6	50.3	50.0	49.8	49.7	49.5	49.3	49.0
80°	40.5	40.4	40.3	40.2	40.1	40.0	39.9	39.7	39.5	39.3	39.1
82.5°	30.1	30.1	30.1	30.1	30.1	30.0	29.9	29.8	29.7	29.6	29.2
85°	16.6	16.5	16.4	16.3	16.2	16.1	16.1	16.0	15.9	15.8	15.5
87.5°	6.1	6.4	6.9	7.2	7.6	7.9	8.2	8.4	8.6	8.9	8.9
90°	1.1	3.7	6.4	9.1	11.8	14.1	16.0	17.9	19.9	21.8	23.0
92.5°	22.0	21.8	21.6	21.3	21.0	21.4	22.4	23.4	24.3	25.3	25.9
95°	70.9	62.9	54.9	46.9	38.9	35.8	37.5	39.1	40.8	42.5	43.8
97.5°	140.7	118.2	95.6	73.1	50.6	41.2	45.1	49.0	53.1	57.0	57.9
100°	193.1	159.9	126.6	93.5	60.3	45.7	49.8	53.9	58.1	62.2	64.1
102.5°	250.7	243.6	236.6	229.6	222.6	201.8	167.3	132.9	98.4	63.9	66.4
105°	331.6	338.9	346.2	353.4	360.7	331.3	265.1	198.9	132.7	66.5	69.2
107.5°	423.9	429.7	435.6	441.5	447.4	410.6	331.3	251.9	172.5	93.2	90.4
110°	483.2	488.3	493.4	498.5	503.5	471.1	401.1	331.0	260.9	190.9	166.7



TEST NUMBER: P331487-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	539.0	543.6	548.0	552.6	557.1	550.7	533.4	516.1	498.8	481.4	393.1
115°	627.2	631.3	635.4	639.5	643.7	648.8	654.9	660.9	667.0	673.1	560.8
117.5°	706.0	710.6	715.2	719.8	724.4	728.8	732.9	737.1	741.3	745.5	718.3
120°	763.6	767.2	770.8	774.5	778.1	782.1	786.5	790.9	795.2	799.5	802.5
122.5°	812.4	816.3	820.1	823.9	827.8	832.1	836.8	841.5	846.3	851.0	852.7
125°	886.8	889.9	893.1	896.3	899.4	903.3	907.9	912.5	917.1	921.8	923.5
127.5°	954.2	957.7	961.2	964.7	968.2	971.7	975.1	978.6	982.0	985.4	987.9
130°	997.0	1000.9	1004.8	1008.6	1012.5	1015.7	1018.4	1021.1	1023.8	1026.4	1029.1
132.5°	1040.6	1043.9	1047.2	1050.5	1053.8	1056.8	1059.4	1062.1	1064.8	1067.5	1069.7
135°	1097.3	1101.2	1105.1	1108.9	1112.9	1115.9	1118.0	1120.3	1122.4	1124.6	1127.0
137.5°	1154.7	1157.4	1160.1	1162.9	1165.6	1168.1	1170.6	1173.1	1175.5	1178.0	1180.4
140°	1192.2	1194.2	1196.1	1198.0	1200.0	1202.3	1205.0	1207.6	1210.3	1213.0	1215.1
142.5°	1223.7	1225.4	1227.2	1228.9	1230.7	1233.1	1236.1	1239.1	1242.2	1245.3	1247.2
145°	1272.9	1272.7	1272.5	1272.2	1272.0	1273.9	1278.1	1282.2	1286.3	1290.4	1292.1
147.5°	1315.9	1315.0	1314.1	1313.1	1312.2	1313.8	1317.9	1322.0	1326.1	1330.1	1331.4
150°	1343.9	1342.2	1340.5	1338.7	1337.0	1338.2	1342.0	1345.9	1349.8	1353.7	1355.1
152.5°	1367.4	1365.6	1363.6	1361.7	1359.9	1360.8	1364.4	1368.2	1371.8	1375.5	1377.0
155°	1401.7	1399.5	1397.3	1395.1	1392.9	1393.3	1396.2	1399.1	1402.0	1405.0	1406.4
157.5°	1428.5	1426.6	1424.8	1423.0	1421.1	1421.2	1423.3	1425.3	1427.4	1429.4	1431.0
160°	1444.2	1442.8	1441.3	1439.8	1438.4	1438.4	1439.8	1441.3	1442.8	1444.2	1445.6
162.5°	1458.2	1456.7	1455.3	1453.8	1452.3	1452.2	1453.5	1454.7	1456.1	1457.3	1458.9
165°	1476.9	1475.5	1474.0	1472.6	1471.1	1470.8	1471.5	1472.2	1472.9	1473.6	1475.3
167.5°	1490.9	1489.4	1488.0	1486.6	1485.1	1484.7	1485.4	1486.0	1486.7	1487.4	1489.1
170°	1498.8	1497.3	1495.8	1494.4	1492.9	1492.5	1492.9	1493.4	1493.9	1494.4	1496.1
172.5°	1504.0	1502.5	1501.1	1499.6	1498.2	1497.7	1498.2	1498.6	1499.1	1499.6	1501.3
175°	1510.7	1509.0	1507.3	1505.7	1504.0	1503.3	1503.9	1504.3	1504.9	1505.3	1507.0
177.5°	1511.8	1510.5	1509.1	1507.8	1506.4	1505.8	1506.0	1506.2	1506.4	1506.6	1508.0
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331487-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2
2.5°	419.5	420.2	420.9	421.2	421.1	420.9	420.8	420.6
5°	416.7	417.4	418.1	418.4	418.2	418.0	417.9	417.7
7.5°	412.0	412.7	413.4	413.7	413.5	413.2	413.0	412.9
10°	407.8	408.5	409.2	409.4	409.1	408.8	408.6	408.3
12.5°	402.8	403.2	403.8	403.9	403.8	403.5	403.3	403.1
15°	394.0	394.4	394.8	394.8	394.3	393.9	393.4	393.0
17.5°	383.7	384.1	384.5	384.5	384.1	383.7	383.3	382.8
20°	375.7	375.9	376.2	376.1	375.8	375.4	375.1	374.7
22.5°	367.1	367.2	367.2	367.1	366.9	366.7	366.5	366.3
25°	353.2	353.4	353.6	353.6	353.4	353.2	353.0	352.8
27.5°	339.5	339.2	338.9	338.6	338.1	337.7	337.3	336.9
30°	328.8	328.5	328.2	328.0	327.6	327.3	326.9	326.5
32.5°	318.3	317.8	317.4	316.9	316.6	316.2	315.8	315.5
35°	301.5	301.0	300.4	300.0	299.5	299.1	298.6	298.1
37.5°	284.6	284.0	283.3	282.8	282.3	281.9	281.5	281.1
40°	273.0	272.2	271.4	270.8	270.5	270.1	269.7	269.4
42.5°	261.5	260.6	259.8	259.0	258.6	258.1	257.6	257.1
45°	243.9	242.9	241.9	241.2	240.9	240.5	240.1	239.8
47.5°	225.6	224.5	223.5	222.7	222.2	221.7	221.1	220.6
50°	213.8	212.5	211.2	210.4	210.0	209.6	209.1	208.7
52.5°	201.6	200.5	199.5	198.7	198.0	197.5	196.9	196.3
55°	183.3	182.3	181.2	180.5	180.0	179.5	179.1	178.6
57.5°	164.4	163.4	162.3	161.6	161.3	161.0	160.6	160.2
60°	151.9	151.0	150.0	149.4	149.1	148.8	148.6	148.3
62.5°	140.1	139.2	138.3	137.7	137.3	137.0	136.6	136.3
65°	121.9	121.1	120.3	119.7	119.2	118.8	118.3	117.9
67.5°	104.0	103.3	102.7	102.2	101.8	101.5	101.1	100.8
70°	92.3	91.7	91.0	90.6	90.2	89.8	89.4	89.1
72.5°	81.3	80.7	80.1	79.5	79.3	79.0	78.7	78.4
75°	64.1	63.6	63.0	62.9	63.0	63.2	63.4	63.6
77.5°	48.8	48.5	48.2	48.0	47.7	47.5	47.3	47.0
80°	38.8	38.5	38.3	38.0	37.8	37.6	37.5	37.3
82.5°	28.9	28.5	28.2	28.0	28.0	27.9	27.9	27.9
85°	15.2	15.0	14.7	14.5	14.4	14.4	14.3	14.2
87.5°	8.9	9.0	9.0	9.0	9.1	9.1	9.1	9.1
90°	24.3	25.4	26.7	27.6	28.0	28.4	29.0	29.4
92.5°	26.6	27.2	27.8	28.3	28.5	28.9	29.2	29.4
95°	44.9	46.2	47.3	47.9	47.6	47.3	47.2	46.9
97.5°	58.9	59.8	60.8	61.4	61.7	62.1	62.3	62.6
100°	66.1	67.9	69.9	71.2	71.6	72.1	72.6	73.1
102.5°	68.9	71.5	74.0	75.6	76.2	77.0	77.7	78.3
105°	71.9	74.5	77.2	79.0	80.0	81.0	81.9	82.9
107.5°	87.7	85.0	82.3	81.4	82.4	83.4	84.4	85.3
110°	142.4	118.2	93.9	82.3	83.3	84.3	85.2	86.1



TEST NUMBER: P331487-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	304.6	216.2	127.8	83.9	84.7	85.5	86.2	87.0
115°	448.5	336.4	224.1	159.3	141.8	124.4	106.9	89.4
117.5°	691.2	664.0	636.9	594.6	537.3	479.9	422.6	365.2
120°	805.4	808.2	811.2	796.3	763.6	730.8	698.1	665.4
122.5°	854.5	856.3	858.0	855.7	849.4	843.0	836.7	830.3
125°	925.1	926.8	928.5	929.7	930.4	931.2	931.9	932.6
127.5°	990.3	992.8	995.3	996.7	996.8	996.9	997.0	997.2
130°	1031.8	1034.5	1037.1	1038.3	1038.0	1037.9	1037.6	1037.3
132.5°	1072.0	1074.2	1076.6	1077.5	1077.4	1077.1	1076.8	1076.7
135°	1129.4	1131.8	1134.3	1135.2	1134.8	1134.3	1133.8	1133.4
137.5°	1182.8	1185.2	1187.6	1188.3	1187.5	1186.7	1185.9	1185.0
140°	1217.4	1219.5	1221.7	1222.2	1220.9	1219.8	1218.5	1217.4
142.5°	1249.2	1251.2	1253.2	1253.6	1252.4	1251.2	1249.9	1248.8
145°	1293.8	1295.5	1297.2	1297.4	1296.2	1295.0	1293.8	1292.6
147.5°	1332.7	1333.9	1335.2	1335.2	1334.3	1333.2	1332.2	1331.2
150°	1356.6	1358.1	1359.5	1359.6	1358.4	1357.2	1355.9	1354.8
152.5°	1378.4	1379.8	1381.3	1381.3	1379.7	1378.0	1376.4	1374.8
155°	1407.8	1409.3	1410.8	1410.5	1408.5	1406.7	1404.7	1402.8
157.5°	1432.7	1434.3	1436.0	1435.8	1434.0	1432.1	1430.2	1428.3
160°	1447.2	1448.6	1450.0	1449.9	1448.2	1446.5	1444.8	1443.1
162.5°	1460.6	1462.2	1463.9	1463.7	1461.6	1459.5	1457.4	1455.4
165°	1477.0	1478.7	1480.4	1480.4	1478.7	1477.0	1475.3	1473.6
167.5°	1490.8	1492.5	1494.2	1494.0	1491.7	1489.6	1487.4	1485.2
170°	1497.8	1499.5	1501.2	1500.9	1498.8	1496.6	1494.4	1492.2
172.5°	1503.0	1504.7	1506.4	1506.2	1504.0	1501.8	1499.6	1497.4
175°	1508.7	1510.4	1512.1	1511.7	1509.3	1506.9	1504.4	1502.0
177.5°	1509.3	1510.6	1512.1	1511.8	1510.1	1508.3	1506.6	1504.9
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4

(END OF REPORT)