

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331829

Luminaire Tested: **S122RDIW-S865D710U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331829
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S865D710U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6137.8 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331829

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331829

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54
1	99	95	92	89	92	89	86	83	76	74	72	65	63	62	54	53	52	47
2	91	84	79	74	85	79	74	69	68	64	61	58	55	53	49	47	45	41
3	84	75	68	63	78	70	64	59	61	56	52	52	49	46	44	42	39	36
4	77	67	60	54	72	63	56	51	55	49	45	47	43	40	40	37	35	31
5	71	60	53	47	66	56	50	45	49	44	40	43	39	35	36	33	31	28
6	66	55	47	41	61	51	44	39	45	39	35	39	35	32	33	30	28	25
7	61	50	42	37	57	47	40	35	41	36	32	36	32	28	31	28	25	23
8	57	45	38	33	53	43	36	31	38	32	29	33	29	26	29	25	23	21
9	53	42	34	30	50	39	33	28	35	30	26	31	26	23	27	23	21	19
10	50	38	32	27	47	36	30	26	32	27	24	29	24	21	25	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30832	30832	30832	30832
5°	34434	31024	27509	31024
10°	38203	30808	23845	30808
15°	40082	30355	18788	30355
20°	34749	29687	16258	29687
25°	22789	28771	14516	28771
30°	15340	27660	13136	27660
35°	12423	26260	11848	26260
40°	11049	24738	10964	24738
45°	9999	22952	9787	22952
50°	9100	21182	9065	21182
55°	8555	19220	8442	19220
60°	7156	17418	7072	17418
65°	6032	15817	6842	15817
70°	5575	14124	6453	14124
75°	5215	12296	5958	12296
80°	4816	10116	5309	10116
85°	4428	7984	4668	7984



TEST NUMBER: P331829

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	2.9
10°-20°	504.4	8.2
20°-30°	650.0	10.6
30°-40°	617.7	10.1
40°-50°	529.1	8.6
50°-60°	402.9	6.6
60°-70°	254.7	4.2
70°-80°	127.2	2.1
80°-90°	35.5	0.6
90°-100°	32.3	0.5
100°-110°	118.3	1.9
110°-120°	316.3	5.2
120°-130°	522.2	8.5
130°-140°	555.4	9.0
140°-150°	516.2	8.4
150°-160°	415.0	6.8
160°-170°	267.4	4.4
170°-180°	92.1	1.5
0°-30°	1335.4	21.8
0°-40°	1953.1	31.8
0°-60°	2885.1	47.0
0°-90°	3302.6	53.8
90°-120°	467.0	7.6
90°-150°	2060.7	33.6
90°-180°	2835.0	46.2
0°-180°	6137.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1910	1910	1910	1910	1910	
5°	2125	1914	1697	1914	2125	210
15°	2398	1816	1124	1816	2398	647
25°	1279	1615	815	1615	1279	607
35°	630	1332	601	1332	630	403
45°	438	1005	429	1005	438	339
55°	304	683	300	683	304	267
65°	158	414	179	414	158	161
75°	84	197	96	197	84	89
85°	24	43	25	43	24	26
90°	19	1	19	1	19	9
95°	30	46	30	46	30	28
105°	53	213	53	213	53	55
115°	57	402	57	402	57	144
125°	598	569	598	569	598	518
135°	727	704	727	704	727	561
145°	830	817	830	817	830	519
155°	900	900	900	900	900	415
165°	946	948	946	948	946	267
175°	964	970	964	970	964	92
180°	968	968	968	968	968	



TEST NUMBER: P331829

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1987.1	1988.7	1990.3	1986.5	1986.5	1983.4	1976.5	1971.2	1956.3	1954.2	1954.2
5°	2124.6	2123.2	2125.9	2117.3	2105.3	2102.7	2090.1	2073.5	2056.2	2037.0	2033.0
7.5°	2261.2	2259.2	2253.9	2252.5	2243.3	2223.3	2203.0	2181.4	2152.7	2124.7	2110.6
10°	2330.2	2352.1	2338.9	2315.6	2320.3	2289.1	2272.5	2244.0	2220.1	2178.3	2169.0
12.5°	2398.2	2406.8	2402.6	2389.4	2383.5	2361.8	2339.4	2314.6	2270.5	2233.0	2200.3
15°	2397.9	2410.5	2413.8	2409.9	2413.2	2411.9	2399.9	2379.3	2340.9	2299.7	2263.9
17.5°	2220.9	2229.7	2251.4	2266.1	2284.7	2324.0	2343.4	2350.9	2345.2	2321.7	2296.5
20°	2022.4	2007.8	2068.8	2100.0	2126.5	2192.9	2250.0	2271.9	2307.0	2306.4	2299.7
22.5°	1741.0	1744.5	1802.4	1839.4	1916.9	1983.2	2048.3	2130.7	2198.7	2243.7	2270.0
25°	1279.2	1304.5	1362.2	1412.6	1498.9	1622.3	1734.4	1864.5	1987.2	2084.1	2176.3
27.5°	960.8	962.6	1008.4	1055.0	1106.2	1207.3	1348.5	1503.8	1678.8	1823.2	1989.3
30°	822.8	818.8	838.0	866.5	910.3	988.6	1094.8	1247.4	1421.9	1639.5	1833.3
32.5°	725.1	725.3	739.8	760.9	797.3	850.1	922.8	1046.8	1211.7	1425.6	1652.8
35°	630.3	629.7	640.3	655.5	670.8	704.6	754.4	819.4	932.9	1132.6	1364.8
37.5°	562.4	565.3	570.5	580.0	596.9	615.7	645.6	689.3	770.1	888.2	1083.4
40°	524.2	525.5	532.8	540.8	550.7	565.3	589.9	625.0	684.1	778.3	920.9
42.5°	489.1	490.5	495.6	503.1	510.9	525.5	545.8	576.2	624.1	697.6	815.3
45°	437.9	437.9	442.6	445.9	454.5	467.8	484.4	509.6	542.7	597.2	675.5
47.5°	389.9	390.0	393.1	398.8	404.2	414.6	430.9	451.5	475.6	517.7	584.6
50°	362.3	362.9	364.9	369.6	372.9	382.2	394.8	412.7	437.9	470.4	526.2
52.5°	340.0	339.6	342.1	344.1	346.4	353.0	362.4	378.2	400.8	429.0	475.2
55°	303.9	301.2	305.2	308.5	310.5	313.2	318.5	328.4	347.7	371.6	406.1
57.5°	258.8	257.7	260.5	263.5	269.8	276.9	281.5	287.8	297.8	314.9	349.1
60°	221.6	221.6	227.6	229.6	236.9	246.2	255.5	260.8	270.7	282.0	307.2
62.5°	188.7	189.2	192.0	194.0	198.1	209.5	222.5	234.2	243.6	254.4	271.1
65°	157.9	159.2	159.2	160.6	163.2	165.9	171.2	180.5	197.1	212.3	224.9
67.5°	134.0	134.4	134.8	136.2	136.8	139.7	141.9	146.0	149.8	164.3	179.9
70°	118.1	120.1	119.4	120.8	121.4	122.7	125.4	127.4	133.4	136.7	146.0
72.5°	103.2	104.7	104.6	105.4	107.1	107.4	109.5	111.5	115.3	118.1	123.1
75°	83.6	82.9	83.6	84.9	85.6	86.3	86.3	88.9	90.9	93.6	96.9
77.5°	64.5	65.2	65.0	65.2	65.3	66.5	66.4	67.5	69.5	70.9	72.5
80°	51.8	52.4	51.8	52.4	53.1	53.7	53.1	53.7	55.7	57.1	57.1
82.5°	40.1	40.2	40.6	40.7	40.9	41.0	41.9	42.1	43.5	43.3	43.8
85°	23.9	23.2	23.2	23.2	23.9	24.5	23.9	23.9	24.5	24.5	24.5
87.5°	12.3	12.7	12.7	12.6	12.6	12.4	12.3	12.7	12.0	12.4	11.6
90°	18.9	18.6	18.3	18.0	17.7	17.1	16.3	15.6	14.8	14.0	12.8
92.5°	18.9	18.7	18.5	18.3	18.2	17.9	17.5	17.1	16.6	16.2	15.6
95°	30.1	30.3	30.4	30.6	30.7	30.4	29.6	28.9	28.1	27.3	26.2
97.5°	40.2	40.0	39.8	39.6	39.4	39.0	38.4	37.8	37.2	36.5	34.0
100°	46.9	46.6	46.3	46.0	45.7	44.9	43.6	42.4	41.1	39.9	37.3
102.5°	50.3	49.8	49.4	49.0	48.5	47.5	45.9	44.3	42.6	41.0	63.1
105°	53.2	52.6	52.0	51.3	50.7	49.5	47.8	46.1	44.4	42.7	85.2
107.5°	54.7	54.1	53.5	52.9	52.3	52.8	54.6	56.3	58.0	59.8	110.7
110°	55.3	54.7	54.1	53.4	52.8	60.3	75.8	91.4	107.0	122.5	167.5



TEST NUMBER: P331829

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	55.9	55.4	54.9	54.4	53.9	82.0	138.8	195.5	252.3	309.0	320.1
115°	57.4	68.6	79.8	91.0	102.2	143.8	215.8	287.9	359.9	431.9	428.0
117.5°	234.4	271.2	308.0	344.8	381.6	408.7	426.1	443.6	461.0	478.4	475.7
120°	427.0	448.0	469.0	490.0	511.0	520.6	518.7	516.9	515.0	513.1	510.3
122.5°	532.9	537.0	541.0	545.1	549.2	550.7	549.5	548.4	547.3	546.2	543.1
125°	598.5	598.1	597.6	597.1	596.7	595.9	594.8	593.7	592.6	591.5	588.6
127.5°	640.0	639.9	639.8	639.7	639.6	638.8	637.2	635.6	634.0	632.4	630.2
130°	665.8	665.9	666.1	666.2	666.4	665.6	663.9	662.2	660.5	658.8	657.0
132.5°	691.0	691.1	691.3	691.4	691.6	690.9	689.5	688.0	686.5	685.1	683.4
135°	727.4	727.7	728.0	728.3	728.6	728.0	726.4	724.9	723.3	721.8	720.4
137.5°	760.5	761.1	761.6	762.1	762.7	762.2	760.6	759.1	757.6	756.1	754.5
140°	781.3	782.0	782.8	783.6	784.4	784.1	782.7	781.3	779.9	778.5	776.7
142.5°	801.4	802.2	803.0	803.8	804.5	804.3	803.0	801.7	800.5	799.2	797.2
145°	829.6	830.3	831.1	831.9	832.7	832.5	831.4	830.3	829.3	828.2	825.5
147.5°	854.3	855.0	855.7	856.3	857.0	856.9	856.1	855.3	854.5	853.6	851.0
150°	869.5	870.2	871.0	871.8	872.6	872.5	871.6	870.6	869.7	868.8	866.3
152.5°	882.3	883.4	884.4	885.4	886.5	886.5	885.6	884.6	883.7	882.8	880.4
155°	900.3	901.5	902.8	904.0	905.2	905.4	904.5	903.5	902.6	901.7	899.8
157.5°	916.6	917.9	919.1	920.3	921.5	921.6	920.5	919.5	918.4	917.3	916.0
160°	926.2	927.3	928.3	929.4	930.5	930.6	929.7	928.7	927.8	926.9	925.9
162.5°	934.0	935.3	936.7	938.0	939.4	939.5	938.4	937.4	936.3	935.3	934.5
165°	945.8	946.9	948.0	949.0	950.1	950.1	949.0	948.0	946.9	945.8	945.3
167.5°	953.2	954.6	956.0	957.4	958.8	958.9	957.9	956.8	955.7	954.6	954.2
170°	957.7	959.1	960.5	961.9	963.3	963.4	962.3	961.3	960.2	959.1	958.8
172.5°	961.0	962.4	963.8	965.2	966.6	966.8	965.7	964.6	963.5	962.4	962.1
175°	964.0	965.5	967.1	968.6	970.2	970.4	969.3	968.3	967.2	966.1	965.8
177.5°	965.8	966.9	968.0	969.2	970.3	970.4	969.5	968.7	967.8	966.9	966.8
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331829

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1955.2	1951.0	1947.3	1937.7	1932.9	1922.3	1920.7	1920.2	1906.4	1893.1	1889.4
5°	2022.4	2011.8	1995.8	1977.3	1958.0	1938.1	1924.8	1914.2	1887.7	1862.5	1847.9
7.5°	2090.1	2067.2	2039.8	2004.6	1975.3	1942.4	1917.9	1896.0	1858.4	1822.3	1798.0
10°	2140.5	2103.3	2066.8	2018.4	1980.6	1943.4	1908.9	1879.1	1836.6	1788.8	1755.0
12.5°	2171.8	2130.9	2080.6	2033.3	1984.3	1937.0	1890.9	1852.5	1802.6	1753.3	1713.0
15°	2214.1	2170.3	2109.3	2041.6	1978.6	1916.9	1863.8	1816.0	1751.0	1691.9	1642.8
17.5°	2248.8	2188.5	2123.0	2044.7	1971.7	1893.3	1824.9	1763.9	1691.5	1620.3	1562.4
20°	2259.9	2200.2	2124.6	2046.3	1960.0	1867.8	1794.1	1727.8	1650.1	1572.5	1506.2
22.5°	2253.0	2206.6	2122.4	2028.7	1940.4	1843.9	1760.7	1683.7	1597.6	1518.4	1441.4
25°	2206.2	2190.2	2110.6	2008.4	1907.6	1795.5	1699.2	1615.0	1516.8	1431.9	1348.2
27.5°	2097.0	2131.3	2082.0	1973.1	1861.0	1740.8	1632.6	1536.7	1434.8	1339.2	1255.9
30°	1991.9	2070.8	2049.6	1948.7	1823.3	1705.2	1583.8	1483.6	1374.8	1276.6	1194.3
32.5°	1848.0	1978.4	1999.2	1914.8	1785.1	1655.3	1528.1	1428.4	1314.8	1211.3	1131.1
35°	1619.0	1814.0	1903.6	1849.9	1719.8	1579.8	1448.4	1332.3	1218.2	1116.0	1036.4
37.5°	1345.7	1611.4	1760.7	1764.5	1645.1	1499.5	1356.5	1241.2	1124.4	1024.1	937.9
40°	1168.4	1456.4	1650.8	1693.9	1593.1	1435.8	1291.2	1173.7	1059.6	961.4	862.6
42.5°	1009.2	1296.1	1535.1	1610.1	1529.9	1373.7	1228.6	1105.8	994.9	902.0	801.0
45°	816.1	1066.9	1330.3	1464.4	1419.9	1275.3	1122.0	1005.2	901.0	820.8	723.9
47.5°	688.5	865.2	1120.1	1301.4	1300.6	1168.6	1017.8	906.0	809.3	734.1	655.7
50°	615.7	769.7	985.3	1191.0	1208.2	1097.4	954.1	843.3	753.1	674.1	611.1
52.5°	550.4	677.3	871.2	1068.4	1117.5	1021.5	882.5	780.2	692.6	620.0	566.0
55°	465.1	563.3	710.6	895.1	969.4	901.7	778.3	682.8	611.8	550.7	504.3
57.5°	393.5	467.1	585.3	733.8	820.4	777.8	676.0	598.4	537.6	482.4	445.7
60°	348.3	408.7	508.9	633.0	728.5	698.7	611.8	539.4	487.7	439.9	405.4
62.5°	305.9	357.8	443.6	544.3	631.9	619.6	548.6	487.9	442.6	399.0	369.8
65°	246.2	284.0	351.0	430.0	500.3	506.3	455.2	414.0	373.6	339.1	313.2
67.5°	196.0	220.7	267.9	334.4	387.1	405.9	374.7	343.3	311.2	284.5	262.1
70°	165.2	185.1	219.6	273.4	321.8	341.7	323.8	299.2	271.4	249.5	230.2
72.5°	133.9	153.3	178.7	218.2	259.7	281.2	275.0	257.3	234.7	216.6	198.4
75°	100.9	106.8	124.1	150.6	183.1	201.7	206.4	197.1	179.1	165.2	154.6
77.5°	74.6	78.2	86.4	100.3	121.6	138.1	144.9	143.8	131.5	123.4	113.5
80°	59.7	61.7	65.7	71.7	87.6	104.2	108.8	108.8	100.2	96.9	86.9
82.5°	45.4	46.8	49.2	52.5	60.0	74.4	79.6	80.7	75.2	70.9	63.0
85°	25.9	25.2	26.5	28.5	29.9	33.8	41.8	43.1	41.8	36.5	34.5
87.5°	11.3	11.6	11.4	10.5	10.7	10.9	13.2	15.5	13.8	12.5	11.8
90°	11.5	10.3	9.0	7.5	5.8	4.1	2.4	0.7	2.4	4.1	5.8
92.5°	15.0	14.4	13.8	13.5	13.7	13.8	14.0	14.1	14.0	13.8	13.7
95°	25.1	24.0	22.9	25.0	30.1	35.2	40.4	45.5	40.4	35.2	30.1
97.5°	31.5	29.0	26.5	32.4	46.9	61.4	75.8	90.3	75.8	61.4	46.9
100°	34.6	32.0	29.3	38.7	60.0	81.3	102.6	123.9	102.6	81.3	60.0
102.5°	85.3	107.4	129.5	142.8	147.3	151.8	156.4	160.9	156.4	151.8	147.3
105°	127.6	170.1	212.6	231.5	226.8	222.2	217.5	212.8	217.5	222.2	226.8
107.5°	161.7	212.6	263.5	287.1	283.3	279.6	275.8	272.0	275.8	279.6	283.3
110°	212.4	257.4	302.3	323.2	319.9	316.7	313.4	310.1	313.4	316.7	319.9



TEST NUMBER: P331829

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	331.2	342.3	353.4	357.5	354.6	351.8	348.9	346.0	348.9	351.8	354.6
115°	424.2	420.3	416.4	413.1	410.5	407.8	405.2	402.5	405.2	407.8	410.5
117.5°	473.1	470.4	467.7	464.9	461.9	459.0	456.0	453.1	456.0	459.0	461.9
120°	507.5	504.7	501.9	499.4	497.0	494.7	492.4	490.0	492.4	494.7	497.0
122.5°	540.1	537.0	534.0	531.2	528.8	526.3	523.9	521.4	523.9	526.3	528.8
125°	585.6	582.7	579.7	577.2	575.2	573.2	571.2	569.1	571.2	573.2	575.2
127.5°	628.0	625.8	623.6	621.4	619.1	616.9	614.6	612.4	614.6	616.9	619.1
130°	655.3	653.6	651.9	649.8	647.3	644.8	642.3	639.8	642.3	644.8	647.3
132.5°	681.6	679.9	678.2	676.3	674.2	672.1	670.0	667.9	670.0	672.1	674.2
135°	719.0	717.6	716.2	714.2	711.7	709.2	706.7	704.3	706.7	709.2	711.7
137.5°	752.9	751.3	749.7	748.0	746.3	744.6	742.8	741.1	742.8	744.6	746.3
140°	775.0	773.3	771.6	770.1	768.9	767.6	766.4	765.2	766.4	767.6	768.9
142.5°	795.3	793.3	791.3	789.8	788.7	787.6	786.4	785.3	786.4	787.6	788.7
145°	822.9	820.2	817.6	816.3	816.5	816.7	816.8	817.0	816.8	816.7	816.5
147.5°	848.4	845.8	843.2	842.2	842.8	843.4	844.0	844.5	844.0	843.4	842.8
150°	863.8	861.3	858.8	858.1	859.2	860.3	861.4	862.5	861.4	860.3	859.2
152.5°	878.0	875.7	873.3	872.7	873.9	875.2	876.4	877.6	876.4	875.2	873.9
155°	897.9	896.1	894.2	894.0	895.4	896.8	898.2	899.6	898.2	896.8	895.4
157.5°	914.7	913.4	912.1	912.1	913.2	914.4	915.6	916.8	915.6	914.4	913.2
160°	925.0	924.1	923.1	923.1	924.1	925.0	925.9	926.9	925.9	925.0	924.1
162.5°	933.7	932.8	932.0	932.1	933.0	934.0	934.9	935.8	934.9	934.0	933.0
165°	944.8	944.4	943.9	944.1	945.1	946.0	946.9	947.9	946.9	946.0	945.1
167.5°	953.7	953.3	952.9	953.1	954.0	955.0	955.9	956.8	955.9	955.0	954.0
170°	958.5	958.1	957.8	958.1	959.1	960.0	960.9	961.9	960.9	960.0	959.1
172.5°	961.8	961.5	961.2	961.5	962.4	963.4	964.3	965.2	964.3	963.4	962.4
175°	965.5	965.1	964.8	965.2	966.3	967.4	968.5	969.6	968.5	967.4	966.3
177.5°	966.7	966.5	966.4	966.8	967.7	968.5	969.4	970.3	969.4	968.5	967.7
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331829

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1882.5	1878.8	1871.9	1861.3	1854.9	1843.8	1836.3	1840.6	1841.6	1840.6	1839.5
5°	1831.9	1818.0	1798.8	1780.2	1762.9	1744.4	1733.7	1729.1	1719.8	1714.5	1711.9
7.5°	1770.8	1746.8	1719.5	1687.2	1659.7	1630.9	1616.2	1608.9	1589.9	1579.5	1570.5
10°	1725.1	1687.3	1660.1	1617.6	1591.8	1553.9	1528.1	1528.7	1502.8	1488.2	1477.6
12.5°	1674.7	1633.2	1587.9	1549.7	1513.7	1483.3	1452.2	1439.5	1412.1	1398.0	1369.3
15°	1591.1	1542.7	1494.9	1443.1	1406.6	1359.5	1314.4	1259.3	1214.9	1176.4	1165.8
17.5°	1499.8	1439.8	1391.9	1331.1	1268.6	1189.4	1137.1	1105.1	1078.3	1058.0	1042.9
20°	1437.2	1376.1	1325.0	1233.5	1149.2	1095.5	1057.0	1032.4	1004.6	982.7	970.7
22.5°	1371.3	1307.6	1238.0	1135.8	1070.1	1027.0	992.7	964.5	945.6	928.5	917.6
25°	1277.9	1208.2	1093.5	1023.1	970.0	924.9	901.0	883.8	863.9	840.7	830.0
27.5°	1179.2	1068.4	986.0	933.7	883.0	853.7	832.2	806.4	788.6	778.2	767.1
30°	1105.4	994.6	930.2	873.2	837.3	804.8	779.6	765.0	747.8	729.9	722.6
32.5°	1023.1	934.6	872.9	825.4	789.0	761.3	741.4	717.8	705.3	694.3	679.0
35°	920.9	853.9	797.5	759.1	724.6	702.0	678.8	664.8	642.3	633.0	627.0
37.5°	834.4	776.3	734.2	693.6	666.3	641.3	627.1	605.0	595.2	582.3	569.7
40°	785.6	728.5	688.1	654.9	624.4	605.8	587.9	570.0	555.4	549.4	534.1
42.5°	735.7	689.3	648.8	612.4	592.0	572.3	549.7	536.5	521.4	511.7	502.3
45°	666.8	625.7	591.2	561.3	538.8	518.2	503.6	481.7	473.1	453.8	445.9
47.5°	606.3	568.1	535.2	506.8	484.8	471.4	450.0	432.9	419.1	407.3	397.0
50°	563.3	531.5	499.6	474.4	454.5	435.3	413.4	404.7	383.5	377.5	371.6
52.5°	524.0	493.8	464.6	439.9	420.0	401.3	382.0	370.8	356.4	350.5	346.1
55°	469.1	439.9	412.0	390.1	370.2	351.0	339.1	325.1	318.5	313.8	308.5
57.5°	413.9	387.6	366.3	344.1	324.1	308.8	295.0	286.6	279.7	273.6	267.3
60°	378.9	353.6	334.4	313.8	293.3	280.7	270.0	260.1	252.1	242.8	240.2
62.5°	341.7	319.7	302.0	282.0	264.1	252.5	242.4	233.0	223.5	209.9	206.2
65°	290.6	273.4	254.8	238.2	222.3	211.0	196.4	185.8	181.8	180.5	179.8
67.5°	244.4	228.1	212.2	195.2	180.7	170.3	162.8	161.2	158.4	157.6	155.8
70°	213.6	198.4	182.5	166.5	152.6	150.6	148.0	145.3	142.0	140.7	139.3
72.5°	186.0	170.3	154.3	141.6	135.6	133.1	130.4	127.8	125.5	124.2	123.4
75°	142.7	128.1	117.4	112.8	109.5	107.5	103.5	101.5	100.2	98.2	97.5
77.5°	102.7	94.5	89.6	86.7	83.2	81.1	78.8	76.8	75.4	75.0	73.9
80°	78.3	74.3	71.0	67.0	65.7	63.0	62.4	60.4	61.0	59.1	59.1
82.5°	60.8	55.7	52.9	51.1	49.8	47.6	47.0	46.0	46.2	44.7	44.7
85°	31.2	29.9	28.5	27.2	27.2	25.2	25.9	25.2	25.2	23.9	23.2
87.5°	11.6	11.4	10.5	10.8	11.0	10.8	10.9	10.5	10.7	10.9	10.4
90°	7.5	9.0	10.3	11.5	12.8	14.0	14.8	15.6	16.3	17.1	17.7
92.5°	13.5	13.8	14.4	15.0	15.6	16.2	16.6	17.1	17.5	17.9	18.2
95°	25.0	22.9	24.0	25.1	26.2	27.3	28.1	28.9	29.6	30.4	30.7
97.5°	32.4	26.5	29.0	31.5	34.0	36.5	37.2	37.8	38.4	39.0	39.4
100°	38.7	29.3	32.0	34.6	37.3	39.9	41.1	42.4	43.6	44.9	45.7
102.5°	142.8	129.5	107.4	85.3	63.1	41.0	42.6	44.3	45.9	47.5	48.5
105°	231.5	212.6	170.1	127.6	85.2	42.7	44.4	46.1	47.8	49.5	50.7
107.5°	287.1	263.5	212.6	161.7	110.7	59.8	58.0	56.3	54.6	52.8	52.3
110°	323.2	302.3	257.4	212.4	167.5	122.5	107.0	91.4	75.8	60.3	52.8



TEST NUMBER: P331829

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	357.5	353.4	342.3	331.2	320.1	309.0	252.3	195.5	138.8	82.0	53.9
115°	413.1	416.4	420.3	424.2	428.0	431.9	359.9	287.9	215.8	143.8	102.2
117.5°	464.9	467.7	470.4	473.1	475.7	478.4	461.0	443.6	426.1	408.7	381.6
120°	499.4	501.9	504.7	507.5	510.3	513.1	515.0	516.9	518.7	520.6	511.0
122.5°	531.2	534.0	537.0	540.1	543.1	546.2	547.3	548.4	549.5	550.7	549.2
125°	577.2	579.7	582.7	585.6	588.6	591.5	592.6	593.7	594.8	595.9	596.7
127.5°	621.4	623.6	625.8	628.0	630.2	632.4	634.0	635.6	637.2	638.8	639.6
130°	649.8	651.9	653.6	655.3	657.0	658.8	660.5	662.2	663.9	665.6	666.4
132.5°	676.3	678.2	679.9	681.6	683.4	685.1	686.5	688.0	689.5	690.9	691.6
135°	714.2	716.2	717.6	719.0	720.4	721.8	723.3	724.9	726.4	728.0	728.6
137.5°	748.0	749.7	751.3	752.9	754.5	756.1	757.6	759.1	760.6	762.2	762.7
140°	770.1	771.6	773.3	775.0	776.7	778.5	779.9	781.3	782.7	784.1	784.4
142.5°	789.8	791.3	793.3	795.3	797.2	799.2	800.5	801.7	803.0	804.3	804.5
145°	816.3	817.6	820.2	822.9	825.5	828.2	829.3	830.3	831.4	832.5	832.7
147.5°	842.2	843.2	845.8	848.4	851.0	853.6	854.5	855.3	856.1	856.9	857.0
150°	858.1	858.8	861.3	863.8	866.3	868.8	869.7	870.6	871.6	872.5	872.6
152.5°	872.7	873.3	875.7	878.0	880.4	882.8	883.7	884.6	885.6	886.5	886.5
155°	894.0	894.2	896.1	897.9	899.8	901.7	902.6	903.5	904.5	905.4	905.2
157.5°	912.1	912.1	913.4	914.7	916.0	917.3	918.4	919.5	920.5	921.6	921.5
160°	923.1	923.1	924.1	925.0	925.9	926.9	927.8	928.7	929.7	930.6	930.5
162.5°	932.1	932.0	932.8	933.7	934.5	935.3	936.3	937.4	938.4	939.5	939.4
165°	944.1	943.9	944.4	944.8	945.3	945.8	946.9	948.0	949.0	950.1	950.1
167.5°	953.1	952.9	953.3	953.7	954.2	954.6	955.7	956.8	957.9	958.9	958.8
170°	958.1	957.8	958.1	958.5	958.8	959.1	960.2	961.3	962.3	963.4	963.3
172.5°	961.5	961.2	961.5	961.8	962.1	962.4	963.5	964.6	965.7	966.8	966.6
175°	965.2	964.8	965.1	965.5	965.8	966.1	967.2	968.3	969.3	970.4	970.2
177.5°	966.8	966.4	966.5	966.7	966.8	966.9	967.8	968.7	969.5	970.4	970.3
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331829

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1833.7	1834.7	1833.1	1834.2	1833.1	1834.7	1833.7	1839.5	1840.6	1841.6	1840.6
5°	1708.5	1700.6	1699.2	1697.3	1699.2	1700.6	1708.5	1711.9	1714.5	1719.8	1729.1
7.5°	1559.1	1557.9	1554.6	1550.0	1554.6	1557.9	1559.1	1570.5	1579.5	1589.9	1608.9
10°	1463.0	1459.7	1459.1	1454.4	1459.1	1459.7	1463.0	1477.6	1488.2	1502.8	1528.7
12.5°	1350.5	1329.1	1326.9	1315.3	1326.9	1329.1	1350.5	1369.3	1398.0	1412.1	1439.5
15°	1149.9	1145.9	1132.6	1124.0	1132.6	1145.9	1149.9	1165.8	1176.4	1214.9	1259.3
17.5°	1035.2	1022.2	1018.1	1016.2	1018.1	1022.2	1035.2	1042.9	1058.0	1078.3	1105.1
20°	961.4	949.5	947.5	946.2	947.5	949.5	961.4	970.7	982.7	1004.6	1032.4
22.5°	910.5	898.0	892.8	888.8	892.8	898.0	910.5	917.6	928.5	945.6	964.5
25°	823.4	818.8	816.1	814.8	816.1	818.8	823.4	830.0	840.7	863.9	883.8
27.5°	755.3	745.1	743.1	739.7	743.1	745.1	755.3	767.1	778.2	788.6	806.4
30°	716.6	713.3	708.6	704.6	708.6	713.3	716.6	722.6	729.9	747.8	765.0
32.5°	670.9	668.2	664.0	662.2	664.0	668.2	670.9	679.0	694.3	705.3	717.8
35°	620.4	611.1	607.1	601.1	607.1	611.1	620.4	627.0	633.0	642.3	664.8
37.5°	566.9	562.0	556.4	558.4	556.4	562.0	566.9	569.7	582.3	595.2	605.0
40°	525.5	522.2	520.9	520.2	520.9	522.2	525.5	534.1	549.4	555.4	570.0
42.5°	492.6	483.4	480.0	479.8	480.0	483.4	492.6	502.3	511.7	521.4	536.5
45°	442.6	433.9	428.0	428.6	428.0	433.9	442.6	445.9	453.8	473.1	481.7
47.5°	391.3	391.1	387.4	388.6	387.4	391.1	391.3	397.0	407.3	419.1	432.9
50°	366.9	362.9	360.3	360.9	360.3	362.9	366.9	371.6	377.5	383.5	404.7
52.5°	343.6	340.1	338.0	340.8	338.0	340.1	343.6	346.1	350.5	356.4	370.8
55°	305.2	301.2	300.6	299.9	300.6	301.2	305.2	308.5	313.8	318.5	325.1
57.5°	262.4	259.7	255.7	254.0	255.7	259.7	262.4	267.3	273.6	279.7	286.6
60°	231.6	226.3	219.6	219.0	219.6	226.3	231.6	240.2	242.8	252.1	260.1
62.5°	203.4	202.4	201.0	200.9	201.0	202.4	203.4	206.2	209.9	223.5	233.0
65°	178.5	177.8	178.5	179.1	178.5	177.8	178.5	179.8	180.5	181.8	185.8
67.5°	155.5	154.3	153.1	153.7	153.1	154.3	155.5	155.8	157.6	158.4	161.2
70°	138.0	137.3	136.7	136.7	136.7	137.3	138.0	139.3	140.7	142.0	145.3
72.5°	121.0	120.9	120.2	119.7	120.2	120.9	121.0	123.4	124.2	125.5	127.8
75°	96.9	95.5	95.5	95.5	95.5	95.5	96.9	97.5	98.2	100.2	101.5
77.5°	73.8	73.1	72.5	71.9	72.5	73.1	73.8	73.9	75.0	75.4	76.8
80°	58.4	57.7	57.1	57.1	57.1	57.7	58.4	59.1	59.1	61.0	60.4
82.5°	44.6	43.9	43.8	43.3	43.8	43.9	44.6	44.7	44.7	46.2	46.0
85°	23.9	24.5	23.9	25.2	23.9	24.5	23.9	23.2	23.9	25.2	25.2
87.5°	10.5	10.0	10.6	10.1	10.6	10.0	10.5	10.4	10.9	10.7	10.5
90°	18.0	18.3	18.6	18.9	18.6	18.3	18.0	17.7	17.1	16.3	15.6
92.5°	18.3	18.5	18.7	18.9	18.7	18.5	18.3	18.2	17.9	17.5	17.1
95°	30.6	30.4	30.3	30.1	30.3	30.4	30.6	30.7	30.4	29.6	28.9
97.5°	39.6	39.8	40.0	40.2	40.0	39.8	39.6	39.4	39.0	38.4	37.8
100°	46.0	46.3	46.6	46.9	46.6	46.3	46.0	45.7	44.9	43.6	42.4
102.5°	49.0	49.4	49.8	50.3	49.8	49.4	49.0	48.5	47.5	45.9	44.3
105°	51.3	52.0	52.6	53.2	52.6	52.0	51.3	50.7	49.5	47.8	46.1
107.5°	52.9	53.5	54.1	54.7	54.1	53.5	52.9	52.3	52.8	54.6	56.3
110°	53.4	54.1	54.7	55.3	54.7	54.1	53.4	52.8	60.3	75.8	91.4



TEST NUMBER: P331829

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	54.4	54.9	55.4	55.9	55.4	54.9	54.4	53.9	82.0	138.8	195.5
115°	91.0	79.8	68.6	57.4	68.6	79.8	91.0	102.2	143.8	215.8	287.9
117.5°	344.8	308.0	271.2	234.4	271.2	308.0	344.8	381.6	408.7	426.1	443.6
120°	490.0	469.0	448.0	427.0	448.0	469.0	490.0	511.0	520.6	518.7	516.9
122.5°	545.1	541.0	537.0	532.9	537.0	541.0	545.1	549.2	550.7	549.5	548.4
125°	597.1	597.6	598.1	598.5	598.1	597.6	597.1	596.7	595.9	594.8	593.7
127.5°	639.7	639.8	639.9	640.0	639.9	639.8	639.7	639.6	638.8	637.2	635.6
130°	666.2	666.1	665.9	665.8	665.9	666.1	666.2	666.4	665.6	663.9	662.2
132.5°	691.4	691.3	691.1	691.0	691.1	691.3	691.4	691.6	690.9	689.5	688.0
135°	728.3	728.0	727.7	727.4	727.7	728.0	728.3	728.6	728.0	726.4	724.9
137.5°	762.1	761.6	761.1	760.5	761.1	761.6	762.1	762.7	762.2	760.6	759.1
140°	783.6	782.8	782.0	781.3	782.0	782.8	783.6	784.4	784.1	782.7	781.3
142.5°	803.8	803.0	802.2	801.4	802.2	803.0	803.8	804.5	804.3	803.0	801.7
145°	831.9	831.1	830.3	829.6	830.3	831.1	831.9	832.7	832.5	831.4	830.3
147.5°	856.3	855.7	855.0	854.3	855.0	855.7	856.3	857.0	856.9	856.1	855.3
150°	871.8	871.0	870.2	869.5	870.2	871.0	871.8	872.6	872.5	871.6	870.6
152.5°	885.4	884.4	883.4	882.3	883.4	884.4	885.4	886.5	886.5	885.6	884.6
155°	904.0	902.8	901.5	900.3	901.5	902.8	904.0	905.2	905.4	904.5	903.5
157.5°	920.3	919.1	917.9	916.6	917.9	919.1	920.3	921.5	921.6	920.5	919.5
160°	929.4	928.3	927.3	926.2	927.3	928.3	929.4	930.5	930.6	929.7	928.7
162.5°	938.0	936.7	935.3	934.0	935.3	936.7	938.0	939.4	939.5	938.4	937.4
165°	949.0	948.0	946.9	945.8	946.9	948.0	949.0	950.1	950.1	949.0	948.0
167.5°	957.4	956.0	954.6	953.2	954.6	956.0	957.4	958.8	958.9	957.9	956.8
170°	961.9	960.5	959.1	957.7	959.1	960.5	961.9	963.3	963.4	962.3	961.3
172.5°	965.2	963.8	962.4	961.0	962.4	963.8	965.2	966.6	966.8	965.7	964.6
175°	968.6	967.1	965.5	964.0	965.5	967.1	968.6	970.2	970.4	969.3	968.3
177.5°	969.2	968.0	966.9	965.8	966.9	968.0	969.2	970.3	970.4	969.5	968.7
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331829

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1836.3	1843.8	1854.9	1861.3	1871.9	1878.8	1882.5	1889.4	1893.1	1906.4	1920.2
5°	1733.7	1744.4	1762.9	1780.2	1798.8	1818.0	1831.9	1847.9	1862.5	1887.7	1914.2
7.5°	1616.2	1630.9	1659.7	1687.2	1719.5	1746.8	1770.8	1798.0	1822.3	1858.4	1896.0
10°	1528.1	1553.9	1591.8	1617.6	1660.1	1687.3	1725.1	1755.0	1788.8	1836.6	1879.1
12.5°	1452.2	1483.3	1513.7	1549.7	1587.9	1633.2	1674.7	1713.0	1753.3	1802.6	1852.5
15°	1314.4	1359.5	1406.6	1443.1	1494.9	1542.7	1591.1	1642.8	1691.9	1751.0	1816.0
17.5°	1137.1	1189.4	1268.6	1331.1	1391.9	1439.8	1499.8	1562.4	1620.3	1691.5	1763.9
20°	1057.0	1095.5	1149.2	1233.5	1325.0	1376.1	1437.2	1506.2	1572.5	1650.1	1727.8
22.5°	992.7	1027.0	1070.1	1135.8	1238.0	1307.6	1371.3	1441.4	1518.4	1597.6	1683.7
25°	901.0	924.9	970.0	1023.1	1093.5	1208.2	1277.9	1348.2	1431.9	1516.8	1615.0
27.5°	832.2	853.7	883.0	933.7	986.0	1068.4	1179.2	1255.9	1339.2	1434.8	1536.7
30°	779.6	804.8	837.3	873.2	930.2	994.6	1105.4	1194.3	1276.6	1374.8	1483.6
32.5°	741.4	761.3	789.0	825.4	872.9	934.6	1023.1	1131.1	1211.3	1314.8	1428.4
35°	678.8	702.0	724.6	759.1	797.5	853.9	920.9	1036.4	1116.0	1218.2	1332.3
37.5°	627.1	641.3	666.3	693.6	734.2	776.3	834.4	937.9	1024.1	1124.4	1241.2
40°	587.9	605.8	624.4	654.9	688.1	728.5	785.6	862.6	961.4	1059.6	1173.7
42.5°	549.7	572.3	592.0	612.4	648.8	689.3	735.7	801.0	902.0	994.9	1105.8
45°	503.6	518.2	538.8	561.3	591.2	625.7	666.8	723.9	820.8	901.0	1005.2
47.5°	450.0	471.4	484.8	506.8	535.2	568.1	606.3	655.7	734.1	809.3	906.0
50°	413.4	435.3	454.5	474.4	499.6	531.5	563.3	611.1	674.1	753.1	843.3
52.5°	382.0	401.3	420.0	439.9	464.6	493.8	524.0	566.0	620.0	692.6	780.2
55°	339.1	351.0	370.2	390.1	412.0	439.9	469.1	504.3	550.7	611.8	682.8
57.5°	295.0	308.8	324.1	344.1	366.3	387.6	413.9	445.7	482.4	537.6	598.4
60°	270.0	280.7	293.3	313.8	334.4	353.6	378.9	405.4	439.9	487.7	539.4
62.5°	242.4	252.5	264.1	282.0	302.0	319.7	341.7	369.8	399.0	442.6	487.9
65°	196.4	211.0	222.3	238.2	254.8	273.4	290.6	313.2	339.1	373.6	414.0
67.5°	162.8	170.3	180.7	195.2	212.2	228.1	244.4	262.1	284.5	311.2	343.3
70°	148.0	150.6	152.6	166.5	182.5	198.4	213.6	230.2	249.5	271.4	299.2
72.5°	130.4	133.1	135.6	141.6	154.3	170.3	186.0	198.4	216.6	234.7	257.3
75°	103.5	107.5	109.5	112.8	117.4	128.1	142.7	154.6	165.2	179.1	197.1
77.5°	78.8	81.1	83.2	86.7	89.6	94.5	102.7	113.5	123.4	131.5	143.8
80°	62.4	63.0	65.7	67.0	71.0	74.3	78.3	86.9	96.9	100.2	108.8
82.5°	47.0	47.6	49.8	51.1	52.9	55.7	60.8	63.0	70.9	75.2	80.7
85°	25.9	25.2	27.2	27.2	28.5	29.9	31.2	34.5	36.5	41.8	43.1
87.5°	10.9	10.8	11.0	10.8	10.5	11.4	11.6	11.8	12.5	13.8	15.5
90°	14.8	14.0	12.8	11.5	10.3	9.0	7.5	5.8	4.1	2.4	0.7
92.5°	16.6	16.2	15.6	15.0	14.4	13.8	13.5	13.7	13.8	14.0	14.1
95°	28.1	27.3	26.2	25.1	24.0	22.9	25.0	30.1	35.2	40.4	45.5
97.5°	37.2	36.5	34.0	31.5	29.0	26.5	32.4	46.9	61.4	75.8	90.3
100°	41.1	39.9	37.3	34.6	32.0	29.3	38.7	60.0	81.3	102.6	123.9
102.5°	42.6	41.0	63.1	85.3	107.4	129.5	142.8	147.3	151.8	156.4	160.9
105°	44.4	42.7	85.2	127.6	170.1	212.6	231.5	226.8	222.2	217.5	212.8
107.5°	58.0	59.8	110.7	161.7	212.6	263.5	287.1	283.3	279.6	275.8	272.0
110°	107.0	122.5	167.5	212.4	257.4	302.3	323.2	319.9	316.7	313.4	310.1



TEST NUMBER: P331829

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	252.3	309.0	320.1	331.2	342.3	353.4	357.5	354.6	351.8	348.9	346.0
115°	359.9	431.9	428.0	424.2	420.3	416.4	413.1	410.5	407.8	405.2	402.5
117.5°	461.0	478.4	475.7	473.1	470.4	467.7	464.9	461.9	459.0	456.0	453.1
120°	515.0	513.1	510.3	507.5	504.7	501.9	499.4	497.0	494.7	492.4	490.0
122.5°	547.3	546.2	543.1	540.1	537.0	534.0	531.2	528.8	526.3	523.9	521.4
125°	592.6	591.5	588.6	585.6	582.7	579.7	577.2	575.2	573.2	571.2	569.1
127.5°	634.0	632.4	630.2	628.0	625.8	623.6	621.4	619.1	616.9	614.6	612.4
130°	660.5	658.8	657.0	655.3	653.6	651.9	649.8	647.3	644.8	642.3	639.8
132.5°	686.5	685.1	683.4	681.6	679.9	678.2	676.3	674.2	672.1	670.0	667.9
135°	723.3	721.8	720.4	719.0	717.6	716.2	714.2	711.7	709.2	706.7	704.3
137.5°	757.6	756.1	754.5	752.9	751.3	749.7	748.0	746.3	744.6	742.8	741.1
140°	779.9	778.5	776.7	775.0	773.3	771.6	770.1	768.9	767.6	766.4	765.2
142.5°	800.5	799.2	797.2	795.3	793.3	791.3	789.8	788.7	787.6	786.4	785.3
145°	829.3	828.2	825.5	822.9	820.2	817.6	816.3	816.5	816.7	816.8	817.0
147.5°	854.5	853.6	851.0	848.4	845.8	843.2	842.2	842.8	843.4	844.0	844.5
150°	869.7	868.8	866.3	863.8	861.3	858.8	858.1	859.2	860.3	861.4	862.5
152.5°	883.7	882.8	880.4	878.0	875.7	873.3	872.7	873.9	875.2	876.4	877.6
155°	902.6	901.7	899.8	897.9	896.1	894.2	894.0	895.4	896.8	898.2	899.6
157.5°	918.4	917.3	916.0	914.7	913.4	912.1	912.1	913.2	914.4	915.6	916.8
160°	927.8	926.9	925.9	925.0	924.1	923.1	923.1	924.1	925.0	925.9	926.9
162.5°	936.3	935.3	934.5	933.7	932.8	932.0	932.1	933.0	934.0	934.9	935.8
165°	946.9	945.8	945.3	944.8	944.4	943.9	944.1	945.1	946.0	946.9	947.9
167.5°	955.7	954.6	954.2	953.7	953.3	952.9	953.1	954.0	955.0	955.9	956.8
170°	960.2	959.1	958.8	958.5	958.1	957.8	958.1	959.1	960.0	960.9	961.9
172.5°	963.5	962.4	962.1	961.8	961.5	961.2	961.5	962.4	963.4	964.3	965.2
175°	967.2	966.1	965.8	965.5	965.1	964.8	965.2	966.3	967.4	968.5	969.6
177.5°	967.8	966.9	966.8	966.7	966.5	966.4	966.8	967.7	968.5	969.4	970.3
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331829

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1920.7	1922.3	1932.9	1937.7	1947.3	1951.0	1955.2	1954.2	1954.2	1956.3	1971.2
5°	1924.8	1938.1	1958.0	1977.3	1995.8	2011.8	2022.4	2033.0	2037.0	2056.2	2073.5
7.5°	1917.9	1942.4	1975.3	2004.6	2039.8	2067.2	2090.1	2110.6	2124.7	2152.7	2181.4
10°	1908.9	1943.4	1980.6	2018.4	2066.8	2103.3	2140.5	2169.0	2178.3	2220.1	2244.0
12.5°	1890.9	1937.0	1984.3	2033.3	2080.6	2130.9	2171.8	2200.3	2233.0	2270.5	2314.6
15°	1863.8	1916.9	1978.6	2041.6	2109.3	2170.3	2214.1	2263.9	2299.7	2340.9	2379.3
17.5°	1824.9	1893.3	1971.7	2044.7	2123.0	2188.5	2248.8	2296.5	2321.7	2345.2	2350.9
20°	1794.1	1867.8	1960.0	2046.3	2124.6	2200.2	2259.9	2299.7	2306.4	2307.0	2271.9
22.5°	1760.7	1843.9	1940.4	2028.7	2122.4	2206.6	2253.0	2270.0	2243.7	2198.7	2130.7
25°	1699.2	1795.5	1907.6	2008.4	2110.6	2190.2	2206.2	2176.3	2084.1	1987.2	1864.5
27.5°	1632.6	1740.8	1861.0	1973.1	2082.0	2131.3	2097.0	1989.3	1823.2	1678.8	1503.8
30°	1583.8	1705.2	1823.3	1948.7	2049.6	2070.8	1991.9	1833.3	1639.5	1421.9	1247.4
32.5°	1528.1	1655.3	1785.1	1914.8	1999.2	1978.4	1848.0	1652.8	1425.6	1211.7	1046.8
35°	1448.4	1579.8	1719.8	1849.9	1903.6	1814.0	1619.0	1364.8	1132.6	932.9	819.4
37.5°	1356.5	1499.5	1645.1	1764.5	1760.7	1611.4	1345.7	1083.4	888.2	770.1	689.3
40°	1291.2	1435.8	1593.1	1693.9	1650.8	1456.4	1168.4	920.9	778.3	684.1	625.0
42.5°	1228.6	1373.7	1529.9	1610.1	1535.1	1296.1	1009.2	815.3	697.6	624.1	576.2
45°	1122.0	1275.3	1419.9	1464.4	1330.3	1066.9	816.1	675.5	597.2	542.7	509.6
47.5°	1017.8	1168.6	1300.6	1301.4	1120.1	865.2	688.5	584.6	517.7	475.6	451.5
50°	954.1	1097.4	1208.2	1191.0	985.3	769.7	615.7	526.2	470.4	437.9	412.7
52.5°	882.5	1021.5	1117.5	1068.4	871.2	677.3	550.4	475.2	429.0	400.8	378.2
55°	778.3	901.7	969.4	895.1	710.6	563.3	465.1	406.1	371.6	347.7	328.4
57.5°	676.0	777.8	820.4	733.8	585.3	467.1	393.5	349.1	314.9	297.8	287.8
60°	611.8	698.7	728.5	633.0	508.9	408.7	348.3	307.2	282.0	270.7	260.8
62.5°	548.6	619.6	631.9	544.3	443.6	357.8	305.9	271.1	254.4	243.6	234.2
65°	455.2	506.3	500.3	430.0	351.0	284.0	246.2	224.9	212.3	197.1	180.5
67.5°	374.7	405.9	387.1	334.4	267.9	220.7	196.0	179.9	164.3	149.8	146.0
70°	323.8	341.7	321.8	273.4	219.6	185.1	165.2	146.0	136.7	133.4	127.4
72.5°	275.0	281.2	259.7	218.2	178.7	153.3	133.9	123.1	118.1	115.3	111.5
75°	206.4	201.7	183.1	150.6	124.1	106.8	100.9	96.9	93.6	90.9	88.9
77.5°	144.9	138.1	121.6	100.3	86.4	78.2	74.6	72.5	70.9	69.5	67.5
80°	108.8	104.2	87.6	71.7	65.7	61.7	59.7	57.1	57.1	55.7	53.7
82.5°	79.6	74.4	60.0	52.5	49.2	46.8	45.4	43.8	43.3	43.5	42.1
85°	41.8	33.8	29.9	28.5	26.5	25.2	25.9	24.5	24.5	24.5	23.9
87.5°	13.2	10.9	10.7	10.5	11.4	11.6	11.3	11.6	12.4	12.0	12.7
90°	2.4	4.1	5.8	7.5	9.0	10.3	11.5	12.8	14.0	14.8	15.6
92.5°	14.0	13.8	13.7	13.5	13.8	14.4	15.0	15.6	16.2	16.6	17.1
95°	40.4	35.2	30.1	25.0	22.9	24.0	25.1	26.2	27.3	28.1	28.9
97.5°	75.8	61.4	46.9	32.4	26.5	29.0	31.5	34.0	36.5	37.2	37.8
100°	102.6	81.3	60.0	38.7	29.3	32.0	34.6	37.3	39.9	41.1	42.4
102.5°	156.4	151.8	147.3	142.8	129.5	107.4	85.3	63.1	41.0	42.6	44.3
105°	217.5	222.2	226.8	231.5	212.6	170.1	127.6	85.2	42.7	44.4	46.1
107.5°	275.8	279.6	283.3	287.1	263.5	212.6	161.7	110.7	59.8	58.0	56.3
110°	313.4	316.7	319.9	323.2	302.3	257.4	212.4	167.5	122.5	107.0	91.4



TEST NUMBER: P331829

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	348.9	351.8	354.6	357.5	353.4	342.3	331.2	320.1	309.0	252.3	195.5
115°	405.2	407.8	410.5	413.1	416.4	420.3	424.2	428.0	431.9	359.9	287.9
117.5°	456.0	459.0	461.9	464.9	467.7	470.4	473.1	475.7	478.4	461.0	443.6
120°	492.4	494.7	497.0	499.4	501.9	504.7	507.5	510.3	513.1	515.0	516.9
122.5°	523.9	526.3	528.8	531.2	534.0	537.0	540.1	543.1	546.2	547.3	548.4
125°	571.2	573.2	575.2	577.2	579.7	582.7	585.6	588.6	591.5	592.6	593.7
127.5°	614.6	616.9	619.1	621.4	623.6	625.8	628.0	630.2	632.4	634.0	635.6
130°	642.3	644.8	647.3	649.8	651.9	653.6	655.3	657.0	658.8	660.5	662.2
132.5°	670.0	672.1	674.2	676.3	678.2	679.9	681.6	683.4	685.1	686.5	688.0
135°	706.7	709.2	711.7	714.2	716.2	717.6	719.0	720.4	721.8	723.3	724.9
137.5°	742.8	744.6	746.3	748.0	749.7	751.3	752.9	754.5	756.1	757.6	759.1
140°	766.4	767.6	768.9	770.1	771.6	773.3	775.0	776.7	778.5	779.9	781.3
142.5°	786.4	787.6	788.7	789.8	791.3	793.3	795.3	797.2	799.2	800.5	801.7
145°	816.8	816.7	816.5	816.3	817.6	820.2	822.9	825.5	828.2	829.3	830.3
147.5°	844.0	843.4	842.8	842.2	843.2	845.8	848.4	851.0	853.6	854.5	855.3
150°	861.4	860.3	859.2	858.1	858.8	861.3	863.8	866.3	868.8	869.7	870.6
152.5°	876.4	875.2	873.9	872.7	873.3	875.7	878.0	880.4	882.8	883.7	884.6
155°	898.2	896.8	895.4	894.0	894.2	896.1	897.9	899.8	901.7	902.6	903.5
157.5°	915.6	914.4	913.2	912.1	912.1	913.4	914.7	916.0	917.3	918.4	919.5
160°	925.9	925.0	924.1	923.1	923.1	924.1	925.0	925.9	926.9	927.8	928.7
162.5°	934.9	934.0	933.0	932.1	932.0	932.8	933.7	934.5	935.3	936.3	937.4
165°	946.9	946.0	945.1	944.1	943.9	944.4	944.8	945.3	945.8	946.9	948.0
167.5°	955.9	955.0	954.0	953.1	952.9	953.3	953.7	954.2	954.6	955.7	956.8
170°	960.9	960.0	959.1	958.1	957.8	958.1	958.5	958.8	959.1	960.2	961.3
172.5°	964.3	963.4	962.4	961.5	961.2	961.5	961.8	962.1	962.4	963.5	964.6
175°	968.5	967.4	966.3	965.2	964.8	965.1	965.5	965.8	966.1	967.2	968.3
177.5°	969.4	968.5	967.7	966.8	966.4	966.5	966.7	966.8	966.9	967.8	968.7
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331829

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1976.5	1983.4	1986.5	1986.5	1990.3	1988.7	1987.1
5°	2090.1	2102.7	2105.3	2117.3	2125.9	2123.2	2124.6
7.5°	2203.0	2223.3	2243.3	2252.5	2253.9	2259.2	2261.2
10°	2272.5	2289.1	2320.3	2315.6	2338.9	2352.1	2330.2
12.5°	2339.4	2361.8	2383.5	2389.4	2402.6	2406.8	2398.2
15°	2399.9	2411.9	2413.2	2409.9	2413.8	2410.5	2397.9
17.5°	2343.4	2324.0	2284.7	2266.1	2251.4	2229.7	2220.9
20°	2250.0	2192.9	2126.5	2100.0	2068.8	2007.8	2022.4
22.5°	2048.3	1983.2	1916.9	1839.4	1802.4	1744.5	1741.0
25°	1734.4	1622.3	1498.9	1412.6	1362.2	1304.5	1279.2
27.5°	1348.5	1207.3	1106.2	1055.0	1008.4	962.6	960.8
30°	1094.8	988.6	910.3	866.5	838.0	818.8	822.8
32.5°	922.8	850.1	797.3	760.9	739.8	725.3	725.1
35°	754.4	704.6	670.8	655.5	640.3	629.7	630.3
37.5°	645.6	615.7	596.9	580.0	570.5	565.3	562.4
40°	589.9	565.3	550.7	540.8	532.8	525.5	524.2
42.5°	545.8	525.5	510.9	503.1	495.6	490.5	489.1
45°	484.4	467.8	454.5	445.9	442.6	437.9	437.9
47.5°	430.9	414.6	404.2	398.8	393.1	390.0	389.9
50°	394.8	382.2	372.9	369.6	364.9	362.9	362.3
52.5°	362.4	353.0	346.4	344.1	342.1	339.6	340.0
55°	318.5	313.2	310.5	308.5	305.2	301.2	303.9
57.5°	281.5	276.9	269.8	263.5	260.5	257.7	258.8
60°	255.5	246.2	236.9	229.6	227.6	221.6	221.6
62.5°	222.5	209.5	198.1	194.0	192.0	189.2	188.7
65°	171.2	165.9	163.2	160.6	159.2	159.2	157.9
67.5°	141.9	139.7	136.8	136.2	134.8	134.4	134.0
70°	125.4	122.7	121.4	120.8	119.4	120.1	118.1
72.5°	109.5	107.4	107.1	105.4	104.6	104.7	103.2
75°	86.3	86.3	85.6	84.9	83.6	82.9	83.6
77.5°	66.4	66.5	65.3	65.2	65.0	65.2	64.5
80°	53.1	53.7	53.1	52.4	51.8	52.4	51.8
82.5°	41.9	41.0	40.9	40.7	40.6	40.2	40.1
85°	23.9	24.5	23.9	23.2	23.2	23.2	23.9
87.5°	12.3	12.4	12.6	12.6	12.7	12.7	12.3
90°	16.3	17.1	17.7	18.0	18.3	18.6	18.9
92.5°	17.5	17.9	18.2	18.3	18.5	18.7	18.9
95°	29.6	30.4	30.7	30.6	30.4	30.3	30.1
97.5°	38.4	39.0	39.4	39.6	39.8	40.0	40.2
100°	43.6	44.9	45.7	46.0	46.3	46.6	46.9
102.5°	45.9	47.5	48.5	49.0	49.4	49.8	50.3
105°	47.8	49.5	50.7	51.3	52.0	52.6	53.2
107.5°	54.6	52.8	52.3	52.9	53.5	54.1	54.7
110°	75.8	60.3	52.8	53.4	54.1	54.7	55.3



TEST NUMBER: P331829

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	138.8	82.0	53.9	54.4	54.9	55.4	55.9
115°	215.8	143.8	102.2	91.0	79.8	68.6	57.4
117.5°	426.1	408.7	381.6	344.8	308.0	271.2	234.4
120°	518.7	520.6	511.0	490.0	469.0	448.0	427.0
122.5°	549.5	550.7	549.2	545.1	541.0	537.0	532.9
125°	594.8	595.9	596.7	597.1	597.6	598.1	598.5
127.5°	637.2	638.8	639.6	639.7	639.8	639.9	640.0
130°	663.9	665.6	666.4	666.2	666.1	665.9	665.8
132.5°	689.5	690.9	691.6	691.4	691.3	691.1	691.0
135°	726.4	728.0	728.6	728.3	728.0	727.7	727.4
137.5°	760.6	762.2	762.7	762.1	761.6	761.1	760.5
140°	782.7	784.1	784.4	783.6	782.8	782.0	781.3
142.5°	803.0	804.3	804.5	803.8	803.0	802.2	801.4
145°	831.4	832.5	832.7	831.9	831.1	830.3	829.6
147.5°	856.1	856.9	857.0	856.3	855.7	855.0	854.3
150°	871.6	872.5	872.6	871.8	871.0	870.2	869.5
152.5°	885.6	886.5	886.5	885.4	884.4	883.4	882.3
155°	904.5	905.4	905.2	904.0	902.8	901.5	900.3
157.5°	920.5	921.6	921.5	920.3	919.1	917.9	916.6
160°	929.7	930.6	930.5	929.4	928.3	927.3	926.2
162.5°	938.4	939.5	939.4	938.0	936.7	935.3	934.0
165°	949.0	950.1	950.1	949.0	948.0	946.9	945.8
167.5°	957.9	958.9	958.8	957.4	956.0	954.6	953.2
170°	962.3	963.4	963.3	961.9	960.5	959.1	957.7
172.5°	965.7	966.8	966.6	965.2	963.8	962.4	961.0
175°	969.3	970.4	970.2	968.6	967.1	965.5	964.0
177.5°	969.5	970.4	970.3	969.2	968.0	966.9	965.8
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5

(END OF REPORT)