

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331489-940

Luminaire Tested: **S122DIW-S290D1440U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331489-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D1440U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6303.4 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331489-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331489-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	27	27	27	19
1	91	87	83	80	80	77	74	71	58	56	54	40	39	38	24	24	23	16
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14
3	76	67	60	55	66	59	54	49	45	41	38	32	29	27	19	18	17	12
4	69	59	52	46	61	52	46	41	40	36	32	28	26	23	17	16	15	10
5	63	53	45	39	56	47	40	35	36	31	28	25	22	20	16	14	13	9
6	58	47	39	34	51	42	35	31	32	27	24	23	20	18	14	13	11	8
7	54	42	35	30	47	38	31	27	29	24	21	21	18	16	13	11	10	7
8	50	38	31	26	44	34	28	24	26	22	19	19	16	14	12	10	9	6
9	46	35	28	23	41	31	25	21	24	20	17	17	14	12	11	9	8	6
10	43	32	25	20	38	28	22	19	22	18	15	16	13	11	10	9	7	5

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8510	8510	8510	8510
5°	9540	8566	7590	8566
10°	10932	8496	6568	8496
15°	12094	8339	5804	8339
20°	11911	8172	5290	8172
25°	10739	7949	4965	7949
30°	8874	7594	4728	7594
35°	6467	7222	4559	7222
40°	5166	6785	4466	6785
45°	4514	6277	4338	6277
50°	4245	5785	4253	5785
55°	3910	5286	4138	5286
60°	3584	4753	3965	4753
65°	3266	4279	3790	4279
70°	2965	3814	3541	3814
75°	2633	3300	3132	3300
80°	2259	2724	2520	2724
85°	2038	2038	1501	2038



TEST NUMBER: P331489-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.2	0.8
10°-20°	145.9	2.3
20°-30°	211.8	3.4
30°-40°	223.5	3.5
40°-50°	197.9	3.1
50°-60°	157.9	2.5
60°-70°	107.3	1.7
70°-80°	55.0	0.9
80°-90°	17.6	0.3
90°-100°	58.5	0.9
100°-110°	214.4	3.4
110°-120°	573.1	9.1
120°-130°	946.0	15.0
130°-140°	1006.1	16.0
140°-150°	935.1	14.8
150°-160°	751.8	11.9
160°-170°	484.5	7.7
170°-180°	166.8	2.6
0°-30°	407.9	6.5
0°-40°	631.4	10.0
0°-60°	987.2	15.7
0°-90°	1167.1	18.5
90°-120°	846.0	13.4
90°-150°	3733.2	59.2
90°-180°	5136.0	81.5
0°-180°	6303.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	527	527	527	527	527	
5°	589	528	468	528	589	59
15°	724	499	347	499	724	200
25°	603	446	279	446	603	272
35°	328	366	231	366	328	213
45°	198	275	190	275	198	155
55°	139	188	147	188	139	125
65°	86	112	99	112	86	85
75°	42	53	50	53	42	45
85°	11	11	8	11	11	13
90°	34	1	34	1	34	16
95°	55	82	55	82	55	51
105°	96	386	96	386	96	100
115°	104	729	104	729	104	260
125°	1084	1031	1084	1031	1084	938
135°	1318	1276	1318	1276	1318	1016
145°	1503	1480	1503	1480	1503	940
155°	1631	1630	1631	1630	1631	753
165°	1713	1717	1713	1717	1713	484
175°	1746	1756	1746	1756	1746	166
180°	1753	1753	1753	1753	1753	



TEST NUMBER: P331489-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	551.3	551.5	551.9	549.3	548.9	548.9	546.7	544.7	542.4	539.4	539.8
5°	588.6	590.8	591.7	589.2	585.6	585.2	581.8	576.1	570.8	566.6	563.6
7.5°	633.1	634.0	632.0	628.8	626.2	621.3	614.8	608.6	599.8	591.7	585.8
10°	666.8	668.1	664.6	660.0	656.1	650.4	641.1	631.6	620.1	608.9	600.0
12.5°	692.4	695.4	691.0	690.5	683.9	676.0	664.9	660.1	643.9	628.4	618.8
15°	723.5	723.4	723.8	719.9	715.1	713.8	702.1	689.3	666.5	657.3	641.5
17.5°	714.5	717.6	719.1	719.0	718.9	718.1	714.3	706.3	694.8	680.0	661.8
20°	693.2	697.2	697.9	702.5	705.2	708.6	710.0	707.8	700.7	688.3	672.5
22.5°	660.1	661.3	663.2	670.4	676.1	684.7	689.2	696.8	694.0	688.0	674.8
25°	602.8	600.8	607.9	611.5	624.7	638.5	648.5	659.3	669.1	674.9	671.1
27.5°	534.0	531.0	541.6	551.3	562.0	576.9	592.4	610.6	625.8	644.9	651.4
30°	476.0	477.9	487.9	498.3	514.5	535.6	553.0	573.0	594.8	616.0	630.8
32.5°	413.5	420.4	426.9	442.7	457.0	480.5	506.0	531.1	558.1	582.3	605.2
35°	328.1	336.3	345.2	356.7	376.7	400.0	425.0	458.8	495.7	528.7	555.8
37.5°	276.3	274.9	280.0	288.4	304.6	323.4	352.1	385.5	428.9	467.7	506.0
40°	245.1	244.3	247.9	255.7	268.0	281.8	306.9	336.3	376.6	424.0	469.6
42.5°	223.7	224.2	226.2	231.7	240.1	251.5	270.3	295.2	332.2	376.8	425.8
45°	197.7	199.1	201.3	204.0	208.8	218.2	228.7	246.6	275.7	313.0	361.1
47.5°	179.0	179.1	181.3	183.6	186.5	191.7	200.4	211.5	232.1	262.4	303.9
50°	169.0	167.6	169.2	170.9	174.0	177.6	183.3	193.9	207.6	232.1	266.8
52.5°	156.6	156.7	158.1	158.8	161.5	165.1	170.3	177.6	190.1	209.3	237.7
55°	138.9	140.0	140.8	142.0	144.5	147.0	151.1	156.0	165.7	180.0	201.2
57.5°	122.3	122.7	123.5	125.8	127.3	129.7	133.6	138.0	144.4	155.0	170.9
60°	111.0	111.0	112.6	113.6	115.7	118.1	121.1	125.4	131.1	139.7	152.6
62.5°	100.7	100.5	101.1	102.8	104.3	106.6	109.6	113.2	118.6	126.4	136.8
65°	85.5	85.1	86.3	86.7	88.3	90.5	93.0	96.8	101.1	106.7	116.1
67.5°	70.9	71.4	72.1	72.8	73.7	76.1	77.7	80.3	84.0	88.7	95.0
70°	62.8	62.8	62.8	63.4	64.6	65.8	67.4	69.6	73.1	77.1	82.8
72.5°	53.7	54.4	55.0	54.7	56.2	56.9	58.9	60.1	63.4	66.0	71.0
75°	42.2	42.2	42.2	43.2	43.8	44.3	45.6	46.8	48.4	51.6	54.3
77.5°	31.5	31.4	31.6	31.8	32.5	33.2	33.5	34.6	36.1	37.6	39.9
80°	24.3	24.7	24.9	25.3	25.3	25.7	25.9	27.4	28.4	29.3	30.8
82.5°	18.8	18.9	18.9	19.0	19.2	19.4	20.0	20.4	20.8	21.6	22.6
85°	11.0	10.7	10.7	11.1	11.0	11.0	11.3	11.8	11.8	11.9	12.6
87.5°	11.1	11.0	11.0	10.7	10.6	10.6	10.3	9.8	9.7	9.6	9.4
90°	34.2	33.7	33.1	32.5	32.0	31.0	29.6	28.2	26.8	25.3	23.1
92.5°	34.2	33.9	33.5	33.3	32.9	32.4	31.7	30.9	30.1	29.4	28.3
95°	54.6	54.8	55.1	55.4	55.6	55.1	53.7	52.3	50.8	49.5	47.5
97.5°	72.8	72.5	72.1	71.8	71.4	70.7	69.6	68.5	67.3	66.2	61.6
100°	85.0	84.4	83.8	83.3	82.8	81.3	79.1	76.8	74.5	72.3	67.5
102.5°	91.0	90.2	89.4	88.7	87.9	86.1	83.1	80.2	77.2	74.3	114.4
105°	96.4	95.2	94.2	93.0	91.8	89.8	86.7	83.6	80.4	77.4	154.3
107.5°	99.2	98.1	96.9	95.8	94.7	95.7	98.8	102.0	105.1	108.3	200.5
110°	100.2	99.1	97.9	96.8	95.7	109.2	137.4	165.6	193.8	221.9	303.4



TEST NUMBER: P331489-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	101.2	100.3	99.4	98.5	97.6	148.6	251.4	354.2	457.0	559.8	579.9
115°	104.0	124.3	144.5	164.9	185.1	260.6	391.0	521.6	652.0	782.5	775.4
117.5°	424.6	491.2	557.9	624.6	691.3	740.5	772.0	803.6	835.2	866.7	861.8
120°	773.6	811.6	849.7	887.8	925.8	943.2	939.8	936.4	933.0	929.6	924.5
122.5°	965.4	972.8	980.2	987.5	994.9	997.6	995.6	993.5	991.5	989.4	983.9
125°	1084.3	1083.5	1082.6	1081.8	1080.9	1079.5	1077.5	1075.6	1073.6	1071.7	1066.3
127.5°	1159.4	1159.2	1159.0	1158.9	1158.8	1157.2	1154.3	1151.5	1148.6	1145.8	1141.7
130°	1206.0	1206.4	1206.7	1206.9	1207.2	1205.8	1202.7	1199.6	1196.5	1193.4	1190.3
132.5°	1251.7	1252.1	1252.3	1252.6	1252.9	1251.7	1249.0	1246.3	1243.8	1241.1	1238.0
135°	1317.7	1318.2	1318.8	1319.4	1319.9	1318.8	1316.0	1313.1	1310.4	1307.5	1305.0
137.5°	1377.8	1378.8	1379.7	1380.6	1381.6	1380.7	1378.0	1375.2	1372.4	1369.7	1366.8
140°	1415.3	1416.8	1418.2	1419.6	1420.9	1420.4	1417.9	1415.3	1412.8	1410.2	1407.2
142.5°	1451.9	1453.3	1454.6	1456.1	1457.5	1457.1	1454.7	1452.4	1450.1	1447.8	1444.2
145°	1502.9	1504.2	1505.7	1507.1	1508.5	1508.2	1506.2	1504.2	1502.3	1500.3	1495.5
147.5°	1547.7	1548.9	1550.2	1551.3	1552.5	1552.4	1550.9	1549.4	1547.9	1546.5	1541.8
150°	1575.1	1576.5	1578.0	1579.4	1580.7	1580.6	1579.0	1577.3	1575.6	1573.9	1569.3
152.5°	1598.5	1600.4	1602.2	1604.0	1605.9	1606.0	1604.3	1602.6	1600.9	1599.2	1594.9
155°	1630.9	1633.2	1635.5	1637.7	1639.9	1640.2	1638.5	1636.8	1635.1	1633.4	1630.1
157.5°	1660.6	1662.8	1665.0	1667.2	1669.4	1669.6	1667.6	1665.7	1663.8	1661.9	1659.5
160°	1677.8	1679.8	1681.8	1683.8	1685.8	1685.9	1684.2	1682.5	1680.8	1679.1	1677.4
162.5°	1692.1	1694.5	1696.9	1699.3	1701.7	1702.0	1700.1	1698.2	1696.3	1694.3	1692.9
165°	1713.3	1715.4	1717.3	1719.3	1721.3	1721.3	1719.3	1717.3	1715.4	1713.3	1712.5
167.5°	1726.8	1729.4	1731.9	1734.5	1737.0	1737.2	1735.3	1733.3	1731.3	1729.4	1728.6
170°	1734.9	1737.5	1740.0	1742.6	1745.1	1745.3	1743.4	1741.4	1739.5	1737.5	1736.9
172.5°	1741.0	1743.6	1746.1	1748.6	1751.1	1751.4	1749.4	1747.5	1745.5	1743.6	1743.0
175°	1746.3	1749.2	1751.9	1754.8	1757.7	1758.0	1756.0	1754.1	1752.1	1750.2	1749.6
177.5°	1749.6	1751.7	1753.7	1755.7	1757.7	1758.0	1756.4	1754.8	1753.3	1751.7	1751.4
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331489-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	540.8	539.6	538.8	535.8	533.2	530.7	529.9	530.1	526.6	523.2	521.7
5°	562.0	557.9	554.0	548.6	542.1	534.9	531.4	528.5	521.4	513.7	509.3
7.5°	580.8	575.0	567.6	557.3	547.9	536.7	529.6	523.3	513.0	502.1	495.4
10°	592.3	584.4	574.9	562.3	550.8	537.2	527.7	518.2	506.0	493.0	484.9
12.5°	602.2	591.6	582.2	566.1	552.4	535.4	524.1	510.7	497.9	482.5	474.6
15°	625.7	606.1	588.3	570.0	553.2	529.5	516.9	498.9	482.1	463.1	454.0
17.5°	643.9	621.8	593.8	570.6	551.0	524.7	506.3	484.7	464.8	443.1	430.7
20°	654.2	628.9	598.8	571.2	547.8	517.7	497.7	475.6	452.4	427.8	414.5
22.5°	660.4	633.8	604.0	568.8	541.3	512.1	486.9	462.6	439.1	412.6	398.6
25°	662.4	638.1	606.5	566.8	533.2	500.2	469.8	446.2	417.7	393.0	372.6
27.5°	652.7	635.3	604.9	562.9	523.8	485.2	451.3	424.7	394.6	367.7	347.1
30°	640.9	630.8	601.2	559.1	516.3	474.8	437.6	407.3	377.4	350.3	329.1
32.5°	622.6	620.5	594.4	553.6	508.4	461.7	423.1	392.6	359.4	332.7	312.6
35°	586.7	596.4	580.0	541.3	493.5	443.0	401.3	366.4	332.0	306.5	287.7
37.5°	538.4	562.6	558.3	523.3	473.2	422.7	376.6	340.2	307.4	281.6	263.1
40°	505.2	536.0	540.5	509.4	459.1	407.0	358.1	321.9	289.9	266.4	247.7
42.5°	469.6	505.5	517.7	492.9	443.4	390.4	341.6	304.1	272.3	249.5	233.0
45°	409.8	457.4	479.5	465.3	417.5	363.2	313.0	274.9	246.1	224.6	211.9
47.5°	353.9	405.9	435.6	430.6	388.6	334.8	285.2	248.6	220.6	203.5	192.1
50°	314.4	367.8	403.7	405.4	367.8	314.6	264.7	230.3	204.6	188.6	179.2
52.5°	280.0	331.1	370.1	378.8	344.6	293.6	246.5	212.1	189.5	174.8	166.5
55°	235.1	278.3	321.6	337.5	310.1	261.5	217.9	187.8	166.5	156.4	149.1
57.5°	195.6	231.5	271.5	289.0	272.2	230.5	189.7	163.5	146.2	137.3	131.7
60°	174.6	203.0	238.6	259.5	244.9	207.9	172.2	147.2	133.0	125.2	119.9
62.5°	155.2	180.3	210.4	229.5	221.6	186.6	154.7	132.7	120.5	113.1	109.2
65°	128.0	147.8	171.2	188.8	183.5	157.0	130.8	112.0	102.3	96.4	93.4
67.5°	105.4	119.8	135.9	151.3	147.1	128.3	107.4	92.6	85.4	80.3	78.5
70°	91.1	102.1	116.5	128.9	125.4	110.0	93.4	80.8	74.5	70.3	68.5
72.5°	77.6	86.5	97.6	107.6	105.3	92.5	78.6	69.2	64.3	60.4	58.9
75°	58.6	65.5	72.1	78.8	78.2	68.3	60.2	52.9	49.0	46.0	45.4
77.5°	43.2	47.1	51.6	55.6	54.5	48.8	42.4	38.3	35.5	33.4	33.1
80°	33.0	35.2	38.5	41.3	39.9	37.5	32.4	29.3	27.4	25.3	24.5
82.5°	24.0	26.1	28.1	29.7	28.5	26.3	23.2	21.1	19.9	18.5	18.2
85°	12.6	13.7	14.6	15.0	14.6	13.2	11.8	11.0	9.9	9.3	9.1
87.5°	9.0	8.6	8.1	7.9	6.8	6.2	4.9	3.8	4.3	4.7	5.0
90°	20.9	18.6	16.3	13.6	10.6	7.5	4.4	1.2	4.4	7.5	10.6
92.5°	27.2	26.0	24.9	24.5	24.8	25.1	25.3	25.6	25.3	25.1	24.8
95°	45.5	43.5	41.6	45.2	54.6	63.8	73.1	82.4	73.1	63.8	54.6
97.5°	57.1	52.5	48.0	58.8	85.0	111.2	137.4	163.6	137.4	111.2	85.0
100°	62.7	57.9	53.1	70.0	108.6	147.2	185.8	224.4	185.8	147.2	108.6
102.5°	154.4	194.6	234.6	258.8	266.9	275.1	283.3	291.4	283.3	275.1	266.9
105°	231.2	308.2	385.1	419.4	410.9	402.4	394.0	385.6	394.0	402.4	410.9
107.5°	292.8	385.1	477.4	520.1	513.3	506.5	499.6	492.8	499.6	506.5	513.3
110°	384.9	466.3	547.7	585.5	579.6	573.6	567.8	561.9	567.8	573.6	579.6



TEST NUMBER: P331489-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	600.0	620.2	640.2	647.7	642.5	637.2	632.0	626.8	632.0	637.2	642.5
115°	768.4	761.3	754.3	748.4	743.6	738.8	734.1	729.2	734.1	738.8	743.6
117.5°	857.0	852.1	847.3	842.2	836.9	831.5	826.2	820.8	826.2	831.5	836.9
120°	919.4	914.4	909.3	904.6	900.4	896.2	892.0	887.8	892.0	896.2	900.4
122.5°	978.4	972.9	967.4	962.4	958.0	953.5	949.0	944.6	949.0	953.5	958.0
125°	1061.0	1055.6	1050.3	1045.7	1042.1	1038.4	1034.7	1031.1	1034.7	1038.4	1042.1
127.5°	1137.7	1133.7	1129.7	1125.7	1121.6	1117.6	1113.5	1109.5	1113.5	1117.6	1121.6
130°	1187.2	1184.1	1181.0	1177.2	1172.7	1168.1	1163.7	1159.1	1163.7	1168.1	1172.7
132.5°	1234.8	1231.8	1228.7	1225.2	1221.4	1217.5	1213.7	1209.9	1213.7	1217.5	1221.4
135°	1302.4	1299.9	1297.4	1293.9	1289.3	1284.9	1280.3	1275.9	1280.3	1284.9	1289.3
137.5°	1364.0	1361.0	1358.2	1355.1	1352.0	1348.9	1345.7	1342.6	1345.7	1348.9	1352.0
140°	1404.1	1401.0	1397.8	1395.2	1392.9	1390.7	1388.4	1386.2	1388.4	1390.7	1392.9
142.5°	1440.7	1437.2	1433.6	1430.8	1428.8	1426.7	1424.7	1422.7	1424.7	1426.7	1428.8
145°	1490.8	1485.9	1481.1	1478.9	1479.2	1479.4	1479.7	1480.1	1479.7	1479.4	1479.2
147.5°	1537.0	1532.2	1527.5	1525.7	1526.8	1527.9	1528.9	1530.0	1528.9	1527.9	1526.8
150°	1564.9	1560.3	1555.9	1554.5	1556.6	1558.5	1560.5	1562.5	1560.5	1558.5	1556.6
152.5°	1590.6	1586.4	1582.1	1581.1	1583.2	1585.5	1587.7	1589.8	1587.7	1585.5	1583.2
155°	1626.7	1623.4	1620.0	1619.5	1622.0	1624.6	1627.1	1629.7	1627.1	1624.6	1622.0
157.5°	1657.2	1654.7	1652.4	1652.3	1654.5	1656.6	1658.8	1660.9	1658.8	1656.6	1654.5
160°	1675.8	1674.1	1672.4	1672.4	1674.1	1675.8	1677.4	1679.1	1677.4	1675.8	1674.1
162.5°	1691.4	1690.0	1688.5	1688.6	1690.3	1692.0	1693.7	1695.3	1693.7	1692.0	1690.3
165°	1711.6	1710.8	1710.0	1710.4	1712.1	1713.8	1715.5	1717.2	1715.5	1713.8	1712.1
167.5°	1727.8	1727.0	1726.2	1726.6	1728.3	1730.0	1731.7	1733.4	1731.7	1730.0	1728.3
170°	1736.3	1735.8	1735.2	1735.8	1737.5	1739.2	1740.9	1742.6	1740.9	1739.2	1737.5
172.5°	1742.4	1741.9	1741.3	1741.9	1743.6	1745.3	1747.0	1748.6	1747.0	1745.3	1743.6
175°	1749.0	1748.5	1747.9	1748.6	1750.6	1752.6	1754.5	1756.5	1754.5	1752.6	1750.6
177.5°	1751.2	1751.0	1750.8	1751.4	1753.0	1754.6	1756.2	1757.7	1756.2	1754.6	1753.0
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331489-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	520.1	519.2	515.8	514.0	511.0	508.3	506.5	507.3	507.9	507.7	507.1
5°	505.2	501.3	495.4	490.4	486.8	480.1	477.2	475.8	474.6	473.2	471.8
7.5°	487.4	481.3	473.0	465.7	459.0	450.6	445.9	443.1	440.1	436.9	434.1
10°	474.8	466.3	457.4	447.3	439.2	431.7	425.0	420.5	416.4	412.6	409.8
12.5°	461.5	451.7	440.7	426.9	417.9	407.2	406.2	398.3	392.0	389.6	386.3
15°	440.4	426.6	412.6	396.2	389.1	379.4	373.4	367.2	361.8	357.9	357.0
17.5°	416.3	398.5	384.6	372.8	361.2	351.2	345.6	340.8	336.3	331.2	330.5
20°	398.1	382.6	367.5	357.1	345.2	335.0	328.1	323.3	319.4	316.4	313.8
22.5°	380.7	363.8	349.9	338.7	326.9	318.7	313.3	308.5	305.3	302.0	299.5
25°	352.8	339.7	324.5	311.7	302.0	296.8	292.3	288.3	286.2	284.0	281.2
27.5°	328.5	313.9	299.7	289.8	281.2	276.6	273.4	270.6	268.8	267.4	265.8
30°	311.4	296.6	285.4	275.7	268.6	263.9	261.9	260.3	258.1	257.3	256.5
32.5°	294.8	281.5	272.0	263.5	256.8	253.7	251.9	250.4	248.7	247.9	246.2
35°	271.4	260.3	251.0	246.3	240.9	238.2	236.8	234.8	233.2	232.4	232.1
37.5°	249.4	239.8	233.6	227.7	225.3	223.7	221.8	220.4	219.9	219.8	219.5
40°	235.1	227.3	221.8	217.0	216.0	213.5	211.9	210.7	210.7	210.9	210.7
42.5°	222.2	215.1	210.3	206.1	204.9	203.5	201.8	201.8	202.1	202.8	202.1
45°	202.6	197.5	194.0	192.1	189.8	188.4	188.2	188.8	189.0	189.2	189.8
47.5°	184.5	181.1	178.0	175.8	174.8	174.6	174.3	175.4	176.4	176.7	177.6
50°	173.8	170.0	167.3	165.9	165.1	164.7	165.1	166.3	167.1	168.1	168.7
52.5°	161.8	159.1	157.3	156.1	155.9	156.1	156.1	157.6	158.8	159.3	159.5
55°	145.3	143.2	142.9	141.0	141.8	141.6	142.6	143.4	144.6	145.9	146.1
57.5°	128.7	127.1	126.0	126.2	126.4	127.3	128.1	129.6	130.8	132.2	132.2
60°	117.7	116.9	116.3	116.3	116.6	117.9	118.9	120.3	121.1	122.0	122.5
62.5°	107.6	106.8	106.2	106.6	107.6	108.3	109.5	110.3	111.1	111.9	112.2
65°	91.8	91.4	91.9	92.4	92.6	93.5	95.0	95.6	96.4	96.8	98.3
67.5°	77.1	77.2	77.1	77.7	78.9	79.1	80.4	81.9	82.0	82.8	83.7
70°	67.2	67.7	68.0	68.5	69.5	69.9	70.9	71.5	72.3	72.9	73.6
72.5°	58.1	58.2	58.7	58.6	59.5	60.3	61.2	61.8	62.6	63.4	63.9
75°	44.8	44.8	45.2	45.4	46.4	47.4	47.2	47.6	48.4	49.2	49.7
77.5°	32.7	32.3	32.7	32.9	33.3	34.1	34.2	34.8	35.8	35.5	35.9
80°	24.9	24.3	24.9	25.1	25.1	26.1	26.1	26.6	27.1	26.6	27.1
82.5°	17.7	17.5	17.9	18.0	18.3	18.4	18.6	18.7	19.4	19.1	19.4
85°	8.9	8.7	8.9	8.7	8.9	9.1	9.1	8.9	8.9	9.3	8.7
87.5°	5.5	5.9	6.2	6.6	6.9	7.2	7.3	7.6	7.8	7.8	8.0
90°	13.6	16.3	18.6	20.9	23.1	25.3	26.8	28.2	29.6	31.0	32.0
92.5°	24.5	24.9	26.0	27.2	28.3	29.4	30.1	30.9	31.7	32.4	32.9
95°	45.2	41.6	43.5	45.5	47.5	49.5	50.8	52.3	53.7	55.1	55.6
97.5°	58.8	48.0	52.5	57.1	61.6	66.2	67.3	68.5	69.6	70.7	71.4
100°	70.0	53.1	57.9	62.7	67.5	72.3	74.5	76.8	79.1	81.3	82.8
102.5°	258.8	234.6	194.6	154.4	114.4	74.3	77.2	80.2	83.1	86.1	87.9
105°	419.4	385.1	308.2	231.2	154.3	77.4	80.4	83.6	86.7	89.8	91.8
107.5°	520.1	477.4	385.1	292.8	200.5	108.3	105.1	102.0	98.8	95.7	94.7
110°	585.5	547.7	466.3	384.9	303.4	221.9	193.8	165.6	137.4	109.2	95.7



TEST NUMBER: P331489-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	647.7	640.2	620.2	600.0	579.9	559.8	457.0	354.2	251.4	148.6	97.6
115°	748.4	754.3	761.3	768.4	775.4	782.5	652.0	521.6	391.0	260.6	185.1
117.5°	842.2	847.3	852.1	857.0	861.8	866.7	835.2	803.6	772.0	740.5	691.3
120°	904.6	909.3	914.4	919.4	924.5	929.6	933.0	936.4	939.8	943.2	925.8
122.5°	962.4	967.4	972.9	978.4	983.9	989.4	991.5	993.5	995.6	997.6	994.9
125°	1045.7	1050.3	1055.6	1061.0	1066.3	1071.7	1073.6	1075.6	1077.5	1079.5	1080.9
127.5°	1125.7	1129.7	1133.7	1137.7	1141.7	1145.8	1148.6	1151.5	1154.3	1157.2	1158.8
130°	1177.2	1181.0	1184.1	1187.2	1190.3	1193.4	1196.5	1199.6	1202.7	1205.8	1207.2
132.5°	1225.2	1228.7	1231.8	1234.8	1238.0	1241.1	1243.8	1246.3	1249.0	1251.7	1252.9
135°	1293.9	1297.4	1299.9	1302.4	1305.0	1307.5	1310.4	1313.1	1316.0	1318.8	1319.9
137.5°	1355.1	1358.2	1361.0	1364.0	1366.8	1369.7	1372.4	1375.2	1378.0	1380.7	1381.6
140°	1395.2	1397.8	1401.0	1404.1	1407.2	1410.2	1412.8	1415.3	1417.9	1420.4	1420.9
142.5°	1430.8	1433.6	1437.2	1440.7	1444.2	1447.8	1450.1	1452.4	1454.7	1457.1	1457.5
145°	1478.9	1481.1	1485.9	1490.8	1495.5	1500.3	1502.3	1504.2	1506.2	1508.2	1508.5
147.5°	1525.7	1527.5	1532.2	1537.0	1541.8	1546.5	1547.9	1549.4	1550.9	1552.4	1552.5
150°	1554.5	1555.9	1560.3	1564.9	1569.3	1573.9	1575.6	1577.3	1579.0	1580.6	1580.7
152.5°	1581.1	1582.1	1586.4	1590.6	1594.9	1599.2	1600.9	1602.6	1604.3	1606.0	1605.9
155°	1619.5	1620.0	1623.4	1626.7	1630.1	1633.4	1635.1	1636.8	1638.5	1640.2	1639.9
157.5°	1652.3	1652.4	1654.7	1657.2	1659.5	1661.9	1663.8	1665.7	1667.6	1669.6	1669.4
160°	1672.4	1672.4	1674.1	1675.8	1677.4	1679.1	1680.8	1682.5	1684.2	1685.9	1685.8
162.5°	1688.6	1688.5	1690.0	1691.4	1692.9	1694.3	1696.3	1698.2	1700.1	1702.0	1701.7
165°	1710.4	1710.0	1710.8	1711.6	1712.5	1713.3	1715.4	1717.3	1719.3	1721.3	1721.3
167.5°	1726.6	1726.2	1727.0	1727.8	1728.6	1729.4	1731.3	1733.3	1735.3	1737.2	1737.0
170°	1735.8	1735.2	1735.8	1736.3	1736.9	1737.5	1739.5	1741.4	1743.4	1745.3	1745.1
172.5°	1741.9	1741.3	1741.9	1742.4	1743.0	1743.6	1745.5	1747.5	1749.4	1751.4	1751.1
175°	1748.6	1747.9	1748.5	1749.0	1749.6	1750.2	1752.1	1754.1	1756.0	1758.0	1757.7
177.5°	1751.4	1750.8	1751.0	1751.2	1751.4	1751.7	1753.3	1754.8	1756.4	1758.0	1757.7
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331489-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	505.5	505.2	505.2	503.7	505.2	505.2	505.5	507.1	507.7	507.9	507.3
5°	469.0	468.3	467.3	468.3	467.3	468.3	469.0	471.8	473.2	474.6	475.8
7.5°	432.7	430.3	430.0	427.6	430.0	430.3	432.7	434.1	436.9	440.1	443.1
10°	406.4	404.7	404.5	400.6	404.5	404.7	406.4	409.8	412.6	416.4	420.5
12.5°	386.3	382.4	383.2	380.9	383.2	382.4	386.3	386.3	389.6	392.0	398.3
15°	351.4	351.4	350.6	347.2	350.6	351.4	351.4	357.0	357.9	361.8	367.2
17.5°	326.5	326.0	324.1	325.1	324.1	326.0	326.5	330.5	331.2	336.3	340.8
20°	311.6	310.3	307.9	307.9	307.9	310.3	311.6	313.8	316.4	319.4	323.3
22.5°	297.5	297.4	294.8	295.6	294.8	297.4	297.5	299.5	302.0	305.3	308.5
25°	281.0	279.4	278.1	278.7	278.1	279.4	281.0	281.2	284.0	286.2	288.3
27.5°	265.3	264.4	264.3	262.7	264.3	264.4	265.3	265.8	267.4	268.8	270.6
30°	256.3	254.2	254.6	253.6	254.6	254.2	256.3	256.5	257.3	258.1	260.3
32.5°	245.8	245.1	244.8	243.9	244.8	245.1	245.8	246.2	247.9	248.7	250.4
35°	231.8	231.9	231.0	231.3	231.0	231.9	231.8	232.1	232.4	233.2	234.8
37.5°	219.4	220.0	219.5	219.6	219.5	220.0	219.4	219.5	219.8	219.9	220.4
40°	211.2	211.2	211.2	211.9	211.2	211.2	211.2	210.7	210.9	210.7	210.7
42.5°	203.5	203.1	202.9	202.8	202.9	203.1	203.5	202.1	202.8	202.1	201.8
45°	190.2	190.8	191.0	190.0	191.0	190.8	190.2	189.8	189.2	189.0	188.8
47.5°	178.2	178.3	178.2	179.1	178.2	178.3	178.2	177.6	176.7	176.4	175.4
50°	169.8	169.3	169.8	169.3	169.8	169.3	169.8	168.7	168.1	167.1	166.3
52.5°	160.9	161.0	160.7	160.6	160.7	161.0	160.9	159.5	159.3	158.8	157.6
55°	146.9	147.2	147.0	147.0	147.0	147.2	146.9	146.1	145.9	144.6	143.4
57.5°	132.4	132.8	133.0	132.2	133.0	132.8	132.4	132.2	132.2	130.8	129.6
60°	122.3	123.3	123.1	122.8	123.1	123.3	122.3	122.5	122.0	121.1	120.3
62.5°	113.1	113.5	113.4	113.3	113.4	113.5	113.1	112.2	111.9	111.1	110.3
65°	98.9	99.2	98.6	99.2	98.6	99.2	98.9	98.3	96.8	96.4	95.6
67.5°	83.5	83.6	84.1	84.4	84.1	83.6	83.5	83.7	82.8	82.0	81.9
70°	73.9	73.7	74.4	75.0	74.4	73.7	73.9	73.6	72.9	72.3	71.5
72.5°	63.8	64.3	64.1	64.6	64.1	64.3	63.8	63.9	63.4	62.6	61.8
75°	49.2	49.8	49.7	50.2	49.7	49.8	49.2	49.7	49.2	48.4	47.6
77.5°	35.6	35.7	35.6	35.9	35.6	35.7	35.6	35.9	35.5	35.8	34.8
80°	27.1	26.8	26.3	27.1	26.3	26.8	27.1	27.1	26.6	27.1	26.6
82.5°	18.9	19.1	18.7	18.7	18.7	19.1	18.9	19.4	19.1	19.4	18.7
85°	8.7	8.5	8.1	8.1	8.1	8.5	8.7	8.7	9.3	8.9	8.9
87.5°	8.1	8.1	8.2	8.1	8.2	8.1	8.1	8.0	7.8	7.8	7.6
90°	32.5	33.1	33.7	34.2	33.7	33.1	32.5	32.0	31.0	29.6	28.2
92.5°	33.3	33.5	33.9	34.2	33.9	33.5	33.3	32.9	32.4	31.7	30.9
95°	55.4	55.1	54.8	54.6	54.8	55.1	55.4	55.6	55.1	53.7	52.3
97.5°	71.8	72.1	72.5	72.8	72.5	72.1	71.8	71.4	70.7	69.6	68.5
100°	83.3	83.8	84.4	85.0	84.4	83.8	83.3	82.8	81.3	79.1	76.8
102.5°	88.7	89.4	90.2	91.0	90.2	89.4	88.7	87.9	86.1	83.1	80.2
105°	93.0	94.2	95.2	96.4	95.2	94.2	93.0	91.8	89.8	86.7	83.6
107.5°	95.8	96.9	98.1	99.2	98.1	96.9	95.8	94.7	95.7	98.8	102.0
110°	96.8	97.9	99.1	100.2	99.1	97.9	96.8	95.7	109.2	137.4	165.6



TEST NUMBER: P331489-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	98.5	99.4	100.3	101.2	100.3	99.4	98.5	97.6	148.6	251.4	354.2
115°	164.9	144.5	124.3	104.0	124.3	144.5	164.9	185.1	260.6	391.0	521.6
117.5°	624.6	557.9	491.2	424.6	491.2	557.9	624.6	691.3	740.5	772.0	803.6
120°	887.8	849.7	811.6	773.6	811.6	849.7	887.8	925.8	943.2	939.8	936.4
122.5°	987.5	980.2	972.8	965.4	972.8	980.2	987.5	994.9	997.6	995.6	993.5
125°	1081.8	1082.6	1083.5	1084.3	1083.5	1082.6	1081.8	1080.9	1079.5	1077.5	1075.6
127.5°	1158.9	1159.0	1159.2	1159.4	1159.2	1159.0	1158.9	1158.8	1157.2	1154.3	1151.5
130°	1206.9	1206.7	1206.4	1206.0	1206.4	1206.7	1206.9	1207.2	1205.8	1202.7	1199.6
132.5°	1252.6	1252.3	1252.1	1251.7	1252.1	1252.3	1252.6	1252.9	1251.7	1249.0	1246.3
135°	1319.4	1318.8	1318.2	1317.7	1318.2	1318.8	1319.4	1319.9	1318.8	1316.0	1313.1
137.5°	1380.6	1379.7	1378.8	1377.8	1378.8	1379.7	1380.6	1381.6	1380.7	1378.0	1375.2
140°	1419.6	1418.2	1416.8	1415.3	1416.8	1418.2	1419.6	1420.9	1420.4	1417.9	1415.3
142.5°	1456.1	1454.6	1453.3	1451.9	1453.3	1454.6	1456.1	1457.5	1457.1	1454.7	1452.4
145°	1507.1	1505.7	1504.2	1502.9	1504.2	1505.7	1507.1	1508.5	1508.2	1506.2	1504.2
147.5°	1551.3	1550.2	1548.9	1547.7	1548.9	1550.2	1551.3	1552.5	1552.4	1550.9	1549.4
150°	1579.4	1578.0	1576.5	1575.1	1576.5	1578.0	1579.4	1580.7	1580.6	1579.0	1577.3
152.5°	1604.0	1602.2	1600.4	1598.5	1600.4	1602.2	1604.0	1605.9	1606.0	1604.3	1602.6
155°	1637.7	1635.5	1633.2	1630.9	1633.2	1635.5	1637.7	1639.9	1640.2	1638.5	1636.8
157.5°	1667.2	1665.0	1662.8	1660.6	1662.8	1665.0	1667.2	1669.4	1669.6	1667.6	1665.7
160°	1683.8	1681.8	1679.8	1677.8	1679.8	1681.8	1683.8	1685.8	1685.9	1684.2	1682.5
162.5°	1699.3	1696.9	1694.5	1692.1	1694.5	1696.9	1699.3	1701.7	1702.0	1700.1	1698.2
165°	1719.3	1717.3	1715.4	1713.3	1715.4	1717.3	1719.3	1721.3	1721.3	1719.3	1717.3
167.5°	1734.5	1731.9	1729.4	1726.8	1729.4	1731.9	1734.5	1737.0	1737.2	1735.3	1733.3
170°	1742.6	1740.0	1737.5	1734.9	1737.5	1740.0	1742.6	1745.1	1745.3	1743.4	1741.4
172.5°	1748.6	1746.1	1743.6	1741.0	1743.6	1746.1	1748.6	1751.1	1751.4	1749.4	1747.5
175°	1754.8	1751.9	1749.2	1746.3	1749.2	1751.9	1754.8	1757.7	1758.0	1756.0	1754.1
177.5°	1755.7	1753.7	1751.7	1749.6	1751.7	1753.7	1755.7	1757.7	1758.0	1756.4	1754.8
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331489-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	506.5	508.3	511.0	514.0	515.8	519.2	520.1	521.7	523.2	526.6	530.1
5°	477.2	480.1	486.8	490.4	495.4	501.3	505.2	509.3	513.7	521.4	528.5
7.5°	445.9	450.6	459.0	465.7	473.0	481.3	487.4	495.4	502.1	513.0	523.3
10°	425.0	431.7	439.2	447.3	457.4	466.3	474.8	484.9	493.0	506.0	518.2
12.5°	406.2	407.2	417.9	426.9	440.7	451.7	461.5	474.6	482.5	497.9	510.7
15°	373.4	379.4	389.1	396.2	412.6	426.6	440.4	454.0	463.1	482.1	498.9
17.5°	345.6	351.2	361.2	372.8	384.6	398.5	416.3	430.7	443.1	464.8	484.7
20°	328.1	335.0	345.2	357.1	367.5	382.6	398.1	414.5	427.8	452.4	475.6
22.5°	313.3	318.7	326.9	338.7	349.9	363.8	380.7	398.6	412.6	439.1	462.6
25°	292.3	296.8	302.0	311.7	324.5	339.7	352.8	372.6	393.0	417.7	446.2
27.5°	273.4	276.6	281.2	289.8	299.7	313.9	328.5	347.1	367.7	394.6	424.7
30°	261.9	263.9	268.6	275.7	285.4	296.6	311.4	329.1	350.3	377.4	407.3
32.5°	251.9	253.7	256.8	263.5	272.0	281.5	294.8	312.6	332.7	359.4	392.6
35°	236.8	238.2	240.9	246.3	251.0	260.3	271.4	287.7	306.5	332.0	366.4
37.5°	221.8	223.7	225.3	227.7	233.6	239.8	249.4	263.1	281.6	307.4	340.2
40°	211.9	213.5	216.0	217.0	221.8	227.3	235.1	247.7	266.4	289.9	321.9
42.5°	201.8	203.5	204.9	206.1	210.3	215.1	222.2	233.0	249.5	272.3	304.1
45°	188.2	188.4	189.8	192.1	194.0	197.5	202.6	211.9	224.6	246.1	274.9
47.5°	174.3	174.6	174.8	175.8	178.0	181.1	184.5	192.1	203.5	220.6	248.6
50°	165.1	164.7	165.1	165.9	167.3	170.0	173.8	179.2	188.6	204.6	230.3
52.5°	156.1	156.1	155.9	156.1	157.3	159.1	161.8	166.5	174.8	189.5	212.1
55°	142.6	141.6	141.8	141.0	142.9	143.2	145.3	149.1	156.4	166.5	187.8
57.5°	128.1	127.3	126.4	126.2	126.0	127.1	128.7	131.7	137.3	146.2	163.5
60°	118.9	117.9	116.6	116.3	116.3	116.9	117.7	119.9	125.2	133.0	147.2
62.5°	109.5	108.3	107.6	106.6	106.2	106.8	107.6	109.2	113.1	120.5	132.7
65°	95.0	93.5	92.6	92.4	91.9	91.4	91.8	93.4	96.4	102.3	112.0
67.5°	80.4	79.1	78.9	77.7	77.1	77.2	77.1	78.5	80.3	85.4	92.6
70°	70.9	69.9	69.5	68.5	68.0	67.7	67.2	68.5	70.3	74.5	80.8
72.5°	61.2	60.3	59.5	58.6	58.7	58.2	58.1	58.9	60.4	64.3	69.2
75°	47.2	47.4	46.4	45.4	45.2	44.8	44.8	45.4	46.0	49.0	52.9
77.5°	34.2	34.1	33.3	32.9	32.7	32.3	32.7	33.1	33.4	35.5	38.3
80°	26.1	26.1	25.1	25.1	24.9	24.3	24.9	24.5	25.3	27.4	29.3
82.5°	18.6	18.4	18.3	18.0	17.9	17.5	17.7	18.2	18.5	19.9	21.1
85°	9.1	9.1	8.9	8.7	8.9	8.7	8.9	9.1	9.3	9.9	11.0
87.5°	7.3	7.2	6.9	6.6	6.2	5.9	5.5	5.0	4.7	4.3	3.8
90°	26.8	25.3	23.1	20.9	18.6	16.3	13.6	10.6	7.5	4.4	1.2
92.5°	30.1	29.4	28.3	27.2	26.0	24.9	24.5	24.8	25.1	25.3	25.6
95°	50.8	49.5	47.5	45.5	43.5	41.6	45.2	54.6	63.8	73.1	82.4
97.5°	67.3	66.2	61.6	57.1	52.5	48.0	58.8	85.0	111.2	137.4	163.6
100°	74.5	72.3	67.5	62.7	57.9	53.1	70.0	108.6	147.2	185.8	224.4
102.5°	77.2	74.3	114.4	154.4	194.6	234.6	258.8	266.9	275.1	283.3	291.4
105°	80.4	77.4	154.3	231.2	308.2	385.1	419.4	410.9	402.4	394.0	385.6
107.5°	105.1	108.3	200.5	292.8	385.1	477.4	520.1	513.3	506.5	499.6	492.8
110°	193.8	221.9	303.4	384.9	466.3	547.7	585.5	579.6	573.6	567.8	561.9



TEST NUMBER: P331489-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	457.0	559.8	579.9	600.0	620.2	640.2	647.7	642.5	637.2	632.0	626.8
115°	652.0	782.5	775.4	768.4	761.3	754.3	748.4	743.6	738.8	734.1	729.2
117.5°	835.2	866.7	861.8	857.0	852.1	847.3	842.2	836.9	831.5	826.2	820.8
120°	933.0	929.6	924.5	919.4	914.4	909.3	904.6	900.4	896.2	892.0	887.8
122.5°	991.5	989.4	983.9	978.4	972.9	967.4	962.4	958.0	953.5	949.0	944.6
125°	1073.6	1071.7	1066.3	1061.0	1055.6	1050.3	1045.7	1042.1	1038.4	1034.7	1031.1
127.5°	1148.6	1145.8	1141.7	1137.7	1133.7	1129.7	1125.7	1121.6	1117.6	1113.5	1109.5
130°	1196.5	1193.4	1190.3	1187.2	1184.1	1181.0	1177.2	1172.7	1168.1	1163.7	1159.1
132.5°	1243.8	1241.1	1238.0	1234.8	1231.8	1228.7	1225.2	1221.4	1217.5	1213.7	1209.9
135°	1310.4	1307.5	1305.0	1302.4	1299.9	1297.4	1293.9	1289.3	1284.9	1280.3	1275.9
137.5°	1372.4	1369.7	1366.8	1364.0	1361.0	1358.2	1355.1	1352.0	1348.9	1345.7	1342.6
140°	1412.8	1410.2	1407.2	1404.1	1401.0	1397.8	1395.2	1392.9	1390.7	1388.4	1386.2
142.5°	1450.1	1447.8	1444.2	1440.7	1437.2	1433.6	1430.8	1428.8	1426.7	1424.7	1422.7
145°	1502.3	1500.3	1495.5	1490.8	1485.9	1481.1	1478.9	1479.2	1479.4	1479.7	1480.1
147.5°	1547.9	1546.5	1541.8	1537.0	1532.2	1527.5	1525.7	1526.8	1527.9	1528.9	1530.0
150°	1575.6	1573.9	1569.3	1564.9	1560.3	1555.9	1554.5	1556.6	1558.5	1560.5	1562.5
152.5°	1600.9	1599.2	1594.9	1590.6	1586.4	1582.1	1581.1	1583.2	1585.5	1587.7	1589.8
155°	1635.1	1633.4	1630.1	1626.7	1623.4	1620.0	1619.5	1622.0	1624.6	1627.1	1629.7
157.5°	1663.8	1661.9	1659.5	1657.2	1654.7	1652.4	1652.3	1654.5	1656.6	1658.8	1660.9
160°	1680.8	1679.1	1677.4	1675.8	1674.1	1672.4	1672.4	1674.1	1675.8	1677.4	1679.1
162.5°	1696.3	1694.3	1692.9	1691.4	1690.0	1688.5	1688.6	1690.3	1692.0	1693.7	1695.3
165°	1715.4	1713.3	1712.5	1711.6	1710.8	1710.0	1710.4	1712.1	1713.8	1715.5	1717.2
167.5°	1731.3	1729.4	1728.6	1727.8	1727.0	1726.2	1726.6	1728.3	1730.0	1731.7	1733.4
170°	1739.5	1737.5	1736.9	1736.3	1735.8	1735.2	1735.8	1737.5	1739.2	1740.9	1742.6
172.5°	1745.5	1743.6	1743.0	1742.4	1741.9	1741.3	1741.9	1743.6	1745.3	1747.0	1748.6
175°	1752.1	1750.2	1749.6	1749.0	1748.5	1747.9	1748.6	1750.6	1752.6	1754.5	1756.5
177.5°	1753.3	1751.7	1751.4	1751.2	1751.0	1750.8	1751.4	1753.0	1754.6	1756.2	1757.7
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331489-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	529.9	530.7	533.2	535.8	538.8	539.6	540.8	539.8	539.4	542.4	544.7
5°	531.4	534.9	542.1	548.6	554.0	557.9	562.0	563.6	566.6	570.8	576.1
7.5°	529.6	536.7	547.9	557.3	567.6	575.0	580.8	585.8	591.7	599.8	608.6
10°	527.7	537.2	550.8	562.3	574.9	584.4	592.3	600.0	608.9	620.1	631.6
12.5°	524.1	535.4	552.4	566.1	582.2	591.6	602.2	618.8	628.4	643.9	660.1
15°	516.9	529.5	553.2	570.0	588.3	606.1	625.7	641.5	657.3	666.5	689.3
17.5°	506.3	524.7	551.0	570.6	593.8	621.8	643.9	661.8	680.0	694.8	706.3
20°	497.7	517.7	547.8	571.2	598.8	628.9	654.2	672.5	688.3	700.7	707.8
22.5°	486.9	512.1	541.3	568.8	604.0	633.8	660.4	674.8	688.0	694.0	696.8
25°	469.8	500.2	533.2	566.8	606.5	638.1	662.4	671.1	674.9	669.1	659.3
27.5°	451.3	485.2	523.8	562.9	604.9	635.3	652.7	651.4	644.9	625.8	610.6
30°	437.6	474.8	516.3	559.1	601.2	630.8	640.9	630.8	616.0	594.8	573.0
32.5°	423.1	461.7	508.4	553.6	594.4	620.5	622.6	605.2	582.3	558.1	531.1
35°	401.3	443.0	493.5	541.3	580.0	596.4	586.7	555.8	528.7	495.7	458.8
37.5°	376.6	422.7	473.2	523.3	558.3	562.6	538.4	506.0	467.7	428.9	385.5
40°	358.1	407.0	459.1	509.4	540.5	536.0	505.2	469.6	424.0	376.6	336.3
42.5°	341.6	390.4	443.4	492.9	517.7	505.5	469.6	425.8	376.8	332.2	295.2
45°	313.0	363.2	417.5	465.3	479.5	457.4	409.8	361.1	313.0	275.7	246.6
47.5°	285.2	334.8	388.6	430.6	435.6	405.9	353.9	303.9	262.4	232.1	211.5
50°	264.7	314.6	367.8	405.4	403.7	367.8	314.4	266.8	232.1	207.6	193.9
52.5°	246.5	293.6	344.6	378.8	370.1	331.1	280.0	237.7	209.3	190.1	177.6
55°	217.9	261.5	310.1	337.5	321.6	278.3	235.1	201.2	180.0	165.7	156.0
57.5°	189.7	230.5	272.2	289.0	271.5	231.5	195.6	170.9	155.0	144.4	138.0
60°	172.2	207.9	244.9	259.5	238.6	203.0	174.6	152.6	139.7	131.1	125.4
62.5°	154.7	186.6	221.6	229.5	210.4	180.3	155.2	136.8	126.4	118.6	113.2
65°	130.8	157.0	183.5	188.8	171.2	147.8	128.0	116.1	106.7	101.1	96.8
67.5°	107.4	128.3	147.1	151.3	135.9	119.8	105.4	95.0	88.7	84.0	80.3
70°	93.4	110.0	125.4	128.9	116.5	102.1	91.1	82.8	77.1	73.1	69.6
72.5°	78.6	92.5	105.3	107.6	97.6	86.5	77.6	71.0	66.0	63.4	60.1
75°	60.2	68.3	78.2	78.8	72.1	65.5	58.6	54.3	51.6	48.4	46.8
77.5°	42.4	48.8	54.5	55.6	51.6	47.1	43.2	39.9	37.6	36.1	34.6
80°	32.4	37.5	39.9	41.3	38.5	35.2	33.0	30.8	29.3	28.4	27.4
82.5°	23.2	26.3	28.5	29.7	28.1	26.1	24.0	22.6	21.6	20.8	20.4
85°	11.8	13.2	14.6	15.0	14.6	13.7	12.6	12.6	11.9	11.8	11.8
87.5°	4.9	6.2	6.8	7.9	8.1	8.6	9.0	9.4	9.6	9.7	9.8
90°	4.4	7.5	10.6	13.6	16.3	18.6	20.9	23.1	25.3	26.8	28.2
92.5°	25.3	25.1	24.8	24.5	24.9	26.0	27.2	28.3	29.4	30.1	30.9
95°	73.1	63.8	54.6	45.2	41.6	43.5	45.5	47.5	49.5	50.8	52.3
97.5°	137.4	111.2	85.0	58.8	48.0	52.5	57.1	61.6	66.2	67.3	68.5
100°	185.8	147.2	108.6	70.0	53.1	57.9	62.7	67.5	72.3	74.5	76.8
102.5°	283.3	275.1	266.9	258.8	234.6	194.6	154.4	114.4	74.3	77.2	80.2
105°	394.0	402.4	410.9	419.4	385.1	308.2	231.2	154.3	77.4	80.4	83.6
107.5°	499.6	506.5	513.3	520.1	477.4	385.1	292.8	200.5	108.3	105.1	102.0
110°	567.8	573.6	579.6	585.5	547.7	466.3	384.9	303.4	221.9	193.8	165.6



TEST NUMBER: P331489-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	632.0	637.2	642.5	647.7	640.2	620.2	600.0	579.9	559.8	457.0	354.2
115°	734.1	738.8	743.6	748.4	754.3	761.3	768.4	775.4	782.5	652.0	521.6
117.5°	826.2	831.5	836.9	842.2	847.3	852.1	857.0	861.8	866.7	835.2	803.6
120°	892.0	896.2	900.4	904.6	909.3	914.4	919.4	924.5	929.6	933.0	936.4
122.5°	949.0	953.5	958.0	962.4	967.4	972.9	978.4	983.9	989.4	991.5	993.5
125°	1034.7	1038.4	1042.1	1045.7	1050.3	1055.6	1061.0	1066.3	1071.7	1073.6	1075.6
127.5°	1113.5	1117.6	1121.6	1125.7	1129.7	1133.7	1137.7	1141.7	1145.8	1148.6	1151.5
130°	1163.7	1168.1	1172.7	1177.2	1181.0	1184.1	1187.2	1190.3	1193.4	1196.5	1199.6
132.5°	1213.7	1217.5	1221.4	1225.2	1228.7	1231.8	1234.8	1238.0	1241.1	1243.8	1246.3
135°	1280.3	1284.9	1289.3	1293.9	1297.4	1299.9	1302.4	1305.0	1307.5	1310.4	1313.1
137.5°	1345.7	1348.9	1352.0	1355.1	1358.2	1361.0	1364.0	1366.8	1369.7	1372.4	1375.2
140°	1388.4	1390.7	1392.9	1395.2	1397.8	1401.0	1404.1	1407.2	1410.2	1412.8	1415.3
142.5°	1424.7	1426.7	1428.8	1430.8	1433.6	1437.2	1440.7	1444.2	1447.8	1450.1	1452.4
145°	1479.7	1479.4	1479.2	1478.9	1481.1	1485.9	1490.8	1495.5	1500.3	1502.3	1504.2
147.5°	1528.9	1527.9	1526.8	1525.7	1527.5	1532.2	1537.0	1541.8	1546.5	1547.9	1549.4
150°	1560.5	1558.5	1556.6	1554.5	1555.9	1560.3	1564.9	1569.3	1573.9	1575.6	1577.3
152.5°	1587.7	1585.5	1583.2	1581.1	1582.1	1586.4	1590.6	1594.9	1599.2	1600.9	1602.6
155°	1627.1	1624.6	1622.0	1619.5	1620.0	1623.4	1626.7	1630.1	1633.4	1635.1	1636.8
157.5°	1658.8	1656.6	1654.5	1652.3	1652.4	1654.7	1657.2	1659.5	1661.9	1663.8	1665.7
160°	1677.4	1675.8	1674.1	1672.4	1672.4	1674.1	1675.8	1677.4	1679.1	1680.8	1682.5
162.5°	1693.7	1692.0	1690.3	1688.6	1688.5	1690.0	1691.4	1692.9	1694.3	1696.3	1698.2
165°	1715.5	1713.8	1712.1	1710.4	1710.0	1710.8	1711.6	1712.5	1713.3	1715.4	1717.3
167.5°	1731.7	1730.0	1728.3	1726.6	1726.2	1727.0	1727.8	1728.6	1729.4	1731.3	1733.3
170°	1740.9	1739.2	1737.5	1735.8	1735.2	1735.8	1736.3	1736.9	1737.5	1739.5	1741.4
172.5°	1747.0	1745.3	1743.6	1741.9	1741.3	1741.9	1742.4	1743.0	1743.6	1745.5	1747.5
175°	1754.5	1752.6	1750.6	1748.6	1747.9	1748.5	1749.0	1749.6	1750.2	1752.1	1754.1
177.5°	1756.2	1754.6	1753.0	1751.4	1750.8	1751.0	1751.2	1751.4	1751.7	1753.3	1754.8
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331489-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	546.7	548.9	548.9	549.3	551.9	551.5	551.3
5°	581.8	585.2	585.6	589.2	591.7	590.8	588.6
7.5°	614.8	621.3	626.2	628.8	632.0	634.0	633.1
10°	641.1	650.4	656.1	660.0	664.6	668.1	666.8
12.5°	664.9	676.0	683.9	690.5	691.0	695.4	692.4
15°	702.1	713.8	715.1	719.9	723.8	723.4	723.5
17.5°	714.3	718.1	718.9	719.0	719.1	717.6	714.5
20°	710.0	708.6	705.2	702.5	697.9	697.2	693.2
22.5°	689.2	684.7	676.1	670.4	663.2	661.3	660.1
25°	648.5	638.5	624.7	611.5	607.9	600.8	602.8
27.5°	592.4	576.9	562.0	551.3	541.6	531.0	534.0
30°	553.0	535.6	514.5	498.3	487.9	477.9	476.0
32.5°	506.0	480.5	457.0	442.7	426.9	420.4	413.5
35°	425.0	400.0	376.7	356.7	345.2	336.3	328.1
37.5°	352.1	323.4	304.6	288.4	280.0	274.9	276.3
40°	306.9	281.8	268.0	255.7	247.9	244.3	245.1
42.5°	270.3	251.5	240.1	231.7	226.2	224.2	223.7
45°	228.7	218.2	208.8	204.0	201.3	199.1	197.7
47.5°	200.4	191.7	186.5	183.6	181.3	179.1	179.0
50°	183.3	177.6	174.0	170.9	169.2	167.6	169.0
52.5°	170.3	165.1	161.5	158.8	158.1	156.7	156.6
55°	151.1	147.0	144.5	142.0	140.8	140.0	138.9
57.5°	133.6	129.7	127.3	125.8	123.5	122.7	122.3
60°	121.1	118.1	115.7	113.6	112.6	111.0	111.0
62.5°	109.6	106.6	104.3	102.8	101.1	100.5	100.7
65°	93.0	90.5	88.3	86.7	86.3	85.1	85.5
67.5°	77.7	76.1	73.7	72.8	72.1	71.4	70.9
70°	67.4	65.8	64.6	63.4	62.8	62.8	62.8
72.5°	58.9	56.9	56.2	54.7	55.0	54.4	53.7
75°	45.6	44.3	43.8	43.2	42.2	42.2	42.2
77.5°	33.5	33.2	32.5	31.8	31.6	31.4	31.5
80°	25.9	25.7	25.3	25.3	24.9	24.7	24.3
82.5°	20.0	19.4	19.2	19.0	18.9	18.9	18.8
85°	11.3	11.0	11.0	11.1	10.7	10.7	11.0
87.5°	10.3	10.6	10.6	10.7	11.0	11.0	11.1
90°	29.6	31.0	32.0	32.5	33.1	33.7	34.2
92.5°	31.7	32.4	32.9	33.3	33.5	33.9	34.2
95°	53.7	55.1	55.6	55.4	55.1	54.8	54.6
97.5°	69.6	70.7	71.4	71.8	72.1	72.5	72.8
100°	79.1	81.3	82.8	83.3	83.8	84.4	85.0
102.5°	83.1	86.1	87.9	88.7	89.4	90.2	91.0
105°	86.7	89.8	91.8	93.0	94.2	95.2	96.4
107.5°	98.8	95.7	94.7	95.8	96.9	98.1	99.2
110°	137.4	109.2	95.7	96.8	97.9	99.1	100.2



TEST NUMBER: P331489-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	251.4	148.6	97.6	98.5	99.4	100.3	101.2
115°	391.0	260.6	185.1	164.9	144.5	124.3	104.0
117.5°	772.0	740.5	691.3	624.6	557.9	491.2	424.6
120°	939.8	943.2	925.8	887.8	849.7	811.6	773.6
122.5°	995.6	997.6	994.9	987.5	980.2	972.8	965.4
125°	1077.5	1079.5	1080.9	1081.8	1082.6	1083.5	1084.3
127.5°	1154.3	1157.2	1158.8	1158.9	1159.0	1159.2	1159.4
130°	1202.7	1205.8	1207.2	1206.9	1206.7	1206.4	1206.0
132.5°	1249.0	1251.7	1252.9	1252.6	1252.3	1252.1	1251.7
135°	1316.0	1318.8	1319.9	1319.4	1318.8	1318.2	1317.7
137.5°	1378.0	1380.7	1381.6	1380.6	1379.7	1378.8	1377.8
140°	1417.9	1420.4	1420.9	1419.6	1418.2	1416.8	1415.3
142.5°	1454.7	1457.1	1457.5	1456.1	1454.6	1453.3	1451.9
145°	1506.2	1508.2	1508.5	1507.1	1505.7	1504.2	1502.9
147.5°	1550.9	1552.4	1552.5	1551.3	1550.2	1548.9	1547.7
150°	1579.0	1580.6	1580.7	1579.4	1578.0	1576.5	1575.1
152.5°	1604.3	1606.0	1605.9	1604.0	1602.2	1600.4	1598.5
155°	1638.5	1640.2	1639.9	1637.7	1635.5	1633.2	1630.9
157.5°	1667.6	1669.6	1669.4	1667.2	1665.0	1662.8	1660.6
160°	1684.2	1685.9	1685.8	1683.8	1681.8	1679.8	1677.8
162.5°	1700.1	1702.0	1701.7	1699.3	1696.9	1694.5	1692.1
165°	1719.3	1721.3	1721.3	1719.3	1717.3	1715.4	1713.3
167.5°	1735.3	1737.2	1737.0	1734.5	1731.9	1729.4	1726.8
170°	1743.4	1745.3	1745.1	1742.6	1740.0	1737.5	1734.9
172.5°	1749.4	1751.4	1751.1	1748.6	1746.1	1743.6	1741.0
175°	1756.0	1758.0	1757.7	1754.8	1751.9	1749.2	1746.3
177.5°	1756.4	1758.0	1757.7	1755.7	1753.7	1751.7	1749.6
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7

(END OF REPORT)