

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331477-940

Luminaire Tested: **S122DIW-S290D970U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331477-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D970U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4616.6 lumens
Efficiency: N/A
Efficacy: 121.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331477-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331477-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33	25
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29	22
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	25	24	19
3	77	68	61	56	68	61	55	51	48	44	40	35	33	31	24	22	21	16
4	71	60	53	47	63	54	48	43	42	38	35	31	29	26	21	20	18	14
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	17	16	12
6	60	48	40	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	25	28	23	20	21	18	16	15	13	11	9
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8510	8510	8510	8510
5°	9540	8566	7590	8566
10°	10932	8496	6568	8496
15°	12094	8339	5804	8339
20°	11911	8172	5290	8172
25°	10739	7949	4965	7949
30°	8874	7594	4728	7594
35°	6467	7222	4559	7222
40°	5166	6785	4466	6785
45°	4514	6277	4338	6277
50°	4245	5785	4253	5785
55°	3910	5286	4138	5286
60°	3584	4753	3965	4753
65°	3266	4279	3790	4279
70°	2965	3814	3541	3814
75°	2633	3300	3132	3300
80°	2259	2724	2520	2724
85°	2038	2038	1501	2038



TEST NUMBER: P331477-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.2	1.1
10°-20°	145.9	3.2
20°-30°	211.8	4.6
30°-40°	223.5	4.8
40°-50°	197.9	4.3
50°-60°	157.9	3.4
60°-70°	107.3	2.3
70°-80°	55.0	1.2
80°-90°	16.2	0.4
90°-100°	39.3	0.9
100°-110°	144.0	3.1
110°-120°	385.0	8.3
120°-130°	635.6	13.8
130°-140°	675.9	14.6
140°-150°	628.3	13.6
150°-160°	505.1	10.9
160°-170°	325.5	7.1
170°-180°	112.0	2.4
0°-30°	407.9	8.8
0°-40°	631.4	13.7
0°-60°	987.2	21.4
0°-90°	1165.7	25.3
90°-120°	568.4	12.3
90°-150°	2508.2	54.3
90°-180°	3451.0	74.8
0°-180°	4616.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	527	527	527	527	527	
5°	589	528	468	528	589	59
15°	724	499	347	499	724	200
25°	603	446	279	446	603	272
35°	328	366	231	366	328	213
45°	198	275	190	275	198	155
55°	139	188	147	188	139	125
65°	86	112	99	112	86	85
75°	42	53	50	53	42	45
85°	11	11	8	11	11	13
90°	23	1	23	1	23	11
95°	37	55	37	55	37	34
105°	65	259	65	259	65	67
115°	70	490	70	490	70	175
125°	728	693	728	693	728	630
135°	885	857	885	857	885	682
145°	1010	994	1010	994	1010	631
155°	1096	1095	1096	1095	1096	506
165°	1151	1154	1151	1154	1151	325
175°	1173	1180	1173	1180	1173	112
180°	1178	1178	1178	1178	1178	



TEST NUMBER: P331477-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	551.3	551.5	551.9	549.3	548.9	548.9	546.7	544.7	542.4	539.4	539.8
5°	588.6	590.8	591.7	589.2	585.6	585.2	581.8	576.1	570.8	566.6	563.6
7.5°	633.1	634.0	632.0	628.8	626.2	621.3	614.8	608.6	599.8	591.7	585.8
10°	666.8	668.1	664.6	660.0	656.1	650.4	641.1	631.6	620.1	608.9	600.0
12.5°	692.4	695.4	691.0	690.5	683.9	676.0	664.9	660.1	643.9	628.4	618.8
15°	723.5	723.4	723.8	719.9	715.1	713.8	702.1	689.3	666.5	657.3	641.5
17.5°	714.5	717.6	719.1	719.0	718.9	718.1	714.3	706.3	694.8	680.0	661.8
20°	693.2	697.2	697.9	702.5	705.2	708.6	710.0	707.8	700.7	688.3	672.5
22.5°	660.1	661.3	663.2	670.4	676.1	684.7	689.2	696.8	694.0	688.0	674.8
25°	602.8	600.8	607.9	611.5	624.7	638.5	648.5	659.3	669.1	674.9	671.1
27.5°	534.0	531.0	541.6	551.3	562.0	576.9	592.4	610.6	625.8	644.9	651.4
30°	476.0	477.9	487.9	498.3	514.5	535.6	553.0	573.0	594.8	616.0	630.8
32.5°	413.5	420.4	426.9	442.7	457.0	480.5	506.0	531.1	558.1	582.3	605.2
35°	328.1	336.3	345.2	356.7	376.7	400.0	425.0	458.8	495.7	528.7	555.8
37.5°	276.3	274.9	280.0	288.4	304.6	323.4	352.1	385.5	428.9	467.7	506.0
40°	245.1	244.3	247.9	255.7	268.0	281.8	306.9	336.3	376.6	424.0	469.6
42.5°	223.7	224.2	226.2	231.7	240.1	251.5	270.3	295.2	332.2	376.8	425.8
45°	197.7	199.1	201.3	204.0	208.8	218.2	228.7	246.6	275.7	313.0	361.1
47.5°	179.0	179.1	181.3	183.6	186.5	191.7	200.4	211.5	232.1	262.4	303.9
50°	169.0	167.6	169.2	170.9	174.0	177.6	183.3	193.9	207.6	232.1	266.8
52.5°	156.6	156.7	158.1	158.8	161.5	165.1	170.3	177.6	190.1	209.3	237.7
55°	138.9	140.0	140.8	142.0	144.5	147.0	151.1	156.0	165.7	180.0	201.2
57.5°	122.3	122.7	123.5	125.8	127.3	129.7	133.6	138.0	144.4	155.0	170.9
60°	111.0	111.0	112.6	113.6	115.7	118.1	121.1	125.4	131.1	139.7	152.6
62.5°	100.7	100.5	101.1	102.8	104.3	106.6	109.6	113.2	118.6	126.4	136.8
65°	85.5	85.1	86.3	86.7	88.3	90.5	93.0	96.8	101.1	106.7	116.1
67.5°	70.9	71.4	72.1	72.8	73.7	76.1	77.7	80.3	84.0	88.7	95.0
70°	62.8	62.8	62.8	63.4	64.6	65.8	67.4	69.6	73.1	77.1	82.8
72.5°	53.7	54.4	55.0	54.7	56.2	56.9	58.9	60.1	63.4	66.0	71.0
75°	42.2	42.2	42.2	43.2	43.8	44.3	45.6	46.8	48.4	51.6	54.3
77.5°	31.5	31.4	31.6	31.8	32.5	33.2	33.5	34.6	36.1	37.6	39.9
80°	24.3	24.7	24.9	25.3	25.3	25.7	25.9	27.4	28.4	29.3	30.8
82.5°	18.8	18.9	18.9	19.0	19.2	19.4	20.0	20.4	20.8	21.6	22.6
85°	11.0	10.7	10.7	11.1	11.0	11.0	11.3	11.8	11.8	11.9	12.6
87.5°	8.8	8.7	8.8	8.6	8.5	8.6	8.4	8.0	7.9	7.9	7.8
90°	23.0	22.6	22.2	21.8	21.5	20.9	19.9	18.9	18.0	17.0	15.5
92.5°	23.0	22.7	22.6	22.3	22.1	21.8	21.2	20.8	20.2	19.8	19.0
95°	36.6	36.8	37.0	37.2	37.4	37.0	36.1	35.1	34.2	33.3	31.9
97.5°	48.9	48.7	48.4	48.2	48.0	47.5	46.7	46.0	45.2	44.5	41.4
100°	57.1	56.7	56.4	55.9	55.6	54.7	53.1	51.6	50.1	48.6	45.4
102.5°	61.2	60.6	60.1	59.6	59.0	57.8	55.8	53.9	51.9	49.9	46.9
105°	64.7	64.0	63.2	62.5	61.7	60.3	58.2	56.2	54.0	52.0	49.7
107.5°	66.6	65.9	65.1	64.4	63.6	64.3	66.4	68.5	70.6	72.8	75.1
110°	67.3	66.5	65.8	65.0	64.3	73.4	92.3	111.2	130.2	149.1	203.8



TEST NUMBER: P331477-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	68.0	67.4	66.8	66.2	65.5	99.8	168.9	237.9	307.0	376.1	389.6
115°	69.9	83.5	97.1	110.8	124.4	175.0	262.7	350.4	438.0	525.8	521.0
117.5°	285.3	330.1	374.9	419.6	464.5	497.5	518.7	539.8	561.1	582.3	579.1
120°	519.8	545.3	570.9	596.5	622.0	633.6	631.3	629.1	626.9	624.6	621.2
122.5°	648.6	653.5	658.5	663.4	668.4	670.2	668.9	667.5	666.1	664.8	661.0
125°	728.5	727.9	727.4	726.8	726.2	725.3	724.0	722.6	721.3	720.0	716.4
127.5°	778.9	778.8	778.7	778.6	778.5	777.5	775.5	773.6	771.7	769.7	767.0
130°	810.3	810.5	810.7	810.8	811.1	810.1	808.1	805.9	803.9	801.8	799.7
132.5°	841.0	841.2	841.3	841.5	841.8	841.0	839.2	837.4	835.6	833.8	831.7
135°	885.3	885.6	886.0	886.4	886.8	886.0	884.1	882.3	880.4	878.5	876.7
137.5°	925.7	926.3	926.9	927.6	928.3	927.6	925.8	923.9	922.1	920.2	918.3
140°	950.9	951.8	952.8	953.8	954.7	954.3	952.6	950.9	949.2	947.5	945.4
142.5°	975.4	976.4	977.3	978.3	979.2	978.9	977.4	975.8	974.3	972.7	970.4
145°	1009.7	1010.7	1011.6	1012.5	1013.5	1013.3	1012.0	1010.7	1009.3	1008.0	1004.8
147.5°	1039.8	1040.6	1041.4	1042.2	1043.0	1042.9	1042.0	1041.0	1040.0	1039.0	1035.8
150°	1058.3	1059.2	1060.2	1061.1	1062.0	1061.9	1060.8	1059.7	1058.5	1057.4	1054.4
152.5°	1074.0	1075.2	1076.5	1077.7	1079.0	1079.0	1077.8	1076.7	1075.6	1074.4	1071.6
155°	1095.7	1097.3	1098.8	1100.3	1101.8	1102.0	1100.8	1099.7	1098.6	1097.4	1095.2
157.5°	1115.7	1117.1	1118.7	1120.1	1121.6	1121.7	1120.4	1119.1	1117.8	1116.5	1114.9
160°	1127.3	1128.6	1129.9	1131.2	1132.6	1132.7	1131.5	1130.4	1129.3	1128.1	1127.0
162.5°	1136.8	1138.4	1140.1	1141.7	1143.4	1143.5	1142.2	1140.9	1139.6	1138.4	1137.4
165°	1151.1	1152.4	1153.8	1155.1	1156.5	1156.5	1155.1	1153.8	1152.4	1151.1	1150.6
167.5°	1160.2	1161.9	1163.6	1165.3	1167.0	1167.2	1165.8	1164.5	1163.1	1161.9	1161.4
170°	1165.6	1167.3	1169.0	1170.7	1172.4	1172.6	1171.3	1170.0	1168.7	1167.3	1167.0
172.5°	1169.7	1171.4	1173.1	1174.8	1176.5	1176.7	1175.4	1174.0	1172.8	1171.4	1171.0
175°	1173.3	1175.2	1177.1	1178.9	1180.9	1181.2	1179.8	1178.5	1177.1	1175.8	1175.5
177.5°	1175.5	1176.9	1178.2	1179.6	1181.0	1181.1	1180.0	1179.0	1177.9	1176.9	1176.7
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331477-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	540.8	539.6	538.8	535.8	533.2	530.7	529.9	530.1	526.6	523.2	521.7
5°	562.0	557.9	554.0	548.6	542.1	534.9	531.4	528.5	521.4	513.7	509.3
7.5°	580.8	575.0	567.6	557.3	547.9	536.7	529.6	523.3	513.0	502.1	495.4
10°	592.3	584.4	574.9	562.3	550.8	537.2	527.7	518.2	506.0	493.0	484.9
12.5°	602.2	591.6	582.2	566.1	552.4	535.4	524.1	510.7	497.9	482.5	474.6
15°	625.7	606.1	588.3	570.0	553.2	529.5	516.9	498.9	482.1	463.1	454.0
17.5°	643.9	621.8	593.8	570.6	551.0	524.7	506.3	484.7	464.8	443.1	430.7
20°	654.2	628.9	598.8	571.2	547.8	517.7	497.7	475.6	452.4	427.8	414.5
22.5°	660.4	633.8	604.0	568.8	541.3	512.1	486.9	462.6	439.1	412.6	398.6
25°	662.4	638.1	606.5	566.8	533.2	500.2	469.8	446.2	417.7	393.0	372.6
27.5°	652.7	635.3	604.9	562.9	523.8	485.2	451.3	424.7	394.6	367.7	347.1
30°	640.9	630.8	601.2	559.1	516.3	474.8	437.6	407.3	377.4	350.3	329.1
32.5°	622.6	620.5	594.4	553.6	508.4	461.7	423.1	392.6	359.4	332.7	312.6
35°	586.7	596.4	580.0	541.3	493.5	443.0	401.3	366.4	332.0	306.5	287.7
37.5°	538.4	562.6	558.3	523.3	473.2	422.7	376.6	340.2	307.4	281.6	263.1
40°	505.2	536.0	540.5	509.4	459.1	407.0	358.1	321.9	289.9	266.4	247.7
42.5°	469.6	505.5	517.7	492.9	443.4	390.4	341.6	304.1	272.3	249.5	233.0
45°	409.8	457.4	479.5	465.3	417.5	363.2	313.0	274.9	246.1	224.6	211.9
47.5°	353.9	405.9	435.6	430.6	388.6	334.8	285.2	248.6	220.6	203.5	192.1
50°	314.4	367.8	403.7	405.4	367.8	314.6	264.7	230.3	204.6	188.6	179.2
52.5°	280.0	331.1	370.1	378.8	344.6	293.6	246.5	212.1	189.5	174.8	166.5
55°	235.1	278.3	321.6	337.5	310.1	261.5	217.9	187.8	166.5	156.4	149.1
57.5°	195.6	231.5	271.5	289.0	272.2	230.5	189.7	163.5	146.2	137.3	131.7
60°	174.6	203.0	238.6	259.5	244.9	207.9	172.2	147.2	133.0	125.2	119.9
62.5°	155.2	180.3	210.4	229.5	221.6	186.6	154.7	132.7	120.5	113.1	109.2
65°	128.0	147.8	171.2	188.8	183.5	157.0	130.8	112.0	102.3	96.4	93.4
67.5°	105.4	119.8	135.9	151.3	147.1	128.3	107.4	92.6	85.4	80.3	78.5
70°	91.1	102.1	116.5	128.9	125.4	110.0	93.4	80.8	74.5	70.3	68.5
72.5°	77.6	86.5	97.6	107.6	105.3	92.5	78.6	69.2	64.3	60.4	58.9
75°	58.6	65.5	72.1	78.8	78.2	68.3	60.2	52.9	49.0	46.0	45.4
77.5°	43.2	47.1	51.6	55.6	54.5	48.8	42.4	38.3	35.5	33.4	33.1
80°	33.0	35.2	38.5	41.3	39.9	37.5	32.4	29.3	27.4	25.3	24.5
82.5°	24.0	26.1	28.1	29.7	28.5	26.3	23.2	21.1	19.9	18.5	18.2
85°	12.6	13.7	14.6	15.0	14.6	13.2	11.8	11.0	9.9	9.3	9.1
87.5°	7.7	7.4	7.0	7.0	6.2	5.7	4.6	3.7	4.0	4.3	4.4
90°	14.0	12.5	11.0	9.2	7.1	5.0	2.9	0.9	2.9	5.0	7.1
92.5°	18.3	17.5	16.8	16.5	16.7	16.9	17.0	17.2	17.0	16.9	16.7
95°	30.6	29.2	27.9	30.4	36.6	42.9	49.1	55.4	49.1	42.9	36.6
97.5°	38.3	35.3	32.2	39.5	57.1	74.7	92.3	109.9	92.3	74.7	57.1
100°	42.1	38.9	35.7	47.1	73.0	98.9	124.8	150.8	124.8	98.9	73.0
102.5°	103.8	130.7	157.7	173.8	179.3	184.9	190.3	195.8	190.3	184.9	179.3
105°	155.3	207.1	258.8	281.8	276.1	270.4	264.7	259.0	264.7	270.4	276.1
107.5°	196.7	258.8	320.7	349.5	344.8	340.3	335.7	331.1	335.7	340.3	344.8
110°	258.6	313.3	368.0	393.3	389.4	385.4	381.5	377.5	381.5	385.4	389.4



TEST NUMBER: P331477-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	403.1	416.7	430.2	435.2	431.7	428.1	424.6	421.1	424.6	428.1	431.7
115°	516.2	511.5	506.8	502.8	499.6	496.4	493.1	489.9	493.1	496.4	499.6
117.5°	575.8	572.6	569.3	565.9	562.2	558.7	555.1	551.4	555.1	558.7	562.2
120°	617.8	614.3	610.9	607.8	604.9	602.1	599.3	596.5	599.3	602.1	604.9
122.5°	657.4	653.6	650.0	646.6	643.5	640.6	637.6	634.6	637.6	640.6	643.5
125°	712.8	709.2	705.6	702.6	700.1	697.7	695.2	692.7	695.2	697.7	700.1
127.5°	764.4	761.7	759.0	756.3	753.6	750.8	748.1	745.4	748.1	750.8	753.6
130°	797.6	795.5	793.4	790.9	787.8	784.9	781.9	778.8	781.9	784.9	787.8
132.5°	829.6	827.6	825.5	823.1	820.6	818.1	815.5	812.9	815.5	818.1	820.6
135°	875.0	873.3	871.6	869.3	866.3	863.3	860.2	857.2	860.2	863.3	866.3
137.5°	916.3	914.4	912.5	910.4	908.4	906.2	904.1	902.0	904.1	906.2	908.4
140°	943.3	941.2	939.1	937.4	935.9	934.3	932.8	931.3	932.8	934.3	935.9
142.5°	968.0	965.5	963.1	961.3	959.9	958.6	957.2	955.8	957.2	958.6	959.9
145°	1001.6	998.4	995.1	993.6	993.8	994.0	994.2	994.3	994.2	994.0	993.8
147.5°	1032.6	1029.5	1026.3	1025.0	1025.7	1026.4	1027.2	1028.0	1027.2	1026.4	1025.7
150°	1051.3	1048.3	1045.3	1044.5	1045.8	1047.0	1048.4	1049.7	1048.4	1047.0	1045.8
152.5°	1068.7	1065.8	1062.9	1062.2	1063.7	1065.1	1066.7	1068.2	1066.7	1065.1	1063.7
155°	1092.9	1090.7	1088.3	1088.1	1089.8	1091.5	1093.1	1094.9	1093.1	1091.5	1089.8
157.5°	1113.4	1111.8	1110.2	1110.1	1111.5	1112.9	1114.5	1115.9	1114.5	1112.9	1111.5
160°	1125.9	1124.7	1123.6	1123.6	1124.7	1125.9	1127.0	1128.1	1127.0	1125.9	1124.7
162.5°	1136.4	1135.4	1134.4	1134.5	1135.6	1136.8	1137.9	1139.1	1137.9	1136.8	1135.6
165°	1150.0	1149.4	1148.9	1149.1	1150.3	1151.4	1152.5	1153.7	1152.5	1151.4	1150.3
167.5°	1160.8	1160.3	1159.8	1160.0	1161.2	1162.3	1163.4	1164.6	1163.4	1162.3	1161.2
170°	1166.5	1166.2	1165.8	1166.2	1167.3	1168.5	1169.6	1170.7	1169.6	1168.5	1167.3
172.5°	1170.6	1170.3	1169.9	1170.3	1171.4	1172.5	1173.7	1174.8	1173.7	1172.5	1171.4
175°	1175.1	1174.7	1174.3	1174.8	1176.2	1177.4	1178.8	1180.1	1178.8	1177.4	1176.2
177.5°	1176.5	1176.4	1176.3	1176.7	1177.8	1178.8	1179.9	1181.0	1179.9	1178.8	1177.8
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331477-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	520.1	519.2	515.8	514.0	511.0	508.3	506.5	507.3	507.9	507.7	507.1
5°	505.2	501.3	495.4	490.4	486.8	480.1	477.2	475.8	474.6	473.2	471.8
7.5°	487.4	481.3	473.0	465.7	459.0	450.6	445.9	443.1	440.1	436.9	434.1
10°	474.8	466.3	457.4	447.3	439.2	431.7	425.0	420.5	416.4	412.6	409.8
12.5°	461.5	451.7	440.7	426.9	417.9	407.2	406.2	398.3	392.0	389.6	386.3
15°	440.4	426.6	412.6	396.2	389.1	379.4	373.4	367.2	361.8	357.9	357.0
17.5°	416.3	398.5	384.6	372.8	361.2	351.2	345.6	340.8	336.3	331.2	330.5
20°	398.1	382.6	367.5	357.1	345.2	335.0	328.1	323.3	319.4	316.4	313.8
22.5°	380.7	363.8	349.9	338.7	326.9	318.7	313.3	308.5	305.3	302.0	299.5
25°	352.8	339.7	324.5	311.7	302.0	296.8	292.3	288.3	286.2	284.0	281.2
27.5°	328.5	313.9	299.7	289.8	281.2	276.6	273.4	270.6	268.8	267.4	265.8
30°	311.4	296.6	285.4	275.7	268.6	263.9	261.9	260.3	258.1	257.3	256.5
32.5°	294.8	281.5	272.0	263.5	256.8	253.7	251.9	250.4	248.7	247.9	246.2
35°	271.4	260.3	251.0	246.3	240.9	238.2	236.8	234.8	233.2	232.4	232.1
37.5°	249.4	239.8	233.6	227.7	225.3	223.7	221.8	220.4	219.9	219.8	219.5
40°	235.1	227.3	221.8	217.0	216.0	213.5	211.9	210.7	210.7	210.9	210.7
42.5°	222.2	215.1	210.3	206.1	204.9	203.5	201.8	201.8	202.1	202.8	202.1
45°	202.6	197.5	194.0	192.1	189.8	188.4	188.2	188.8	189.0	189.2	189.8
47.5°	184.5	181.1	178.0	175.8	174.8	174.6	174.3	175.4	176.4	176.7	177.6
50°	173.8	170.0	167.3	165.9	165.1	164.7	165.1	166.3	167.1	168.1	168.7
52.5°	161.8	159.1	157.3	156.1	155.9	156.1	156.1	157.6	158.8	159.3	159.5
55°	145.3	143.2	142.9	141.0	141.8	141.6	142.6	143.4	144.6	145.9	146.1
57.5°	128.7	127.1	126.0	126.2	126.4	127.3	128.1	129.6	130.8	132.2	132.2
60°	117.7	116.9	116.3	116.3	116.6	117.9	118.9	120.3	121.1	122.0	122.5
62.5°	107.6	106.8	106.2	106.6	107.6	108.3	109.5	110.3	111.1	111.9	112.2
65°	91.8	91.4	91.9	92.4	92.6	93.5	95.0	95.6	96.4	96.8	98.3
67.5°	77.1	77.2	77.1	77.7	78.9	79.1	80.4	81.9	82.0	82.8	83.7
70°	67.2	67.7	68.0	68.5	69.5	69.9	70.9	71.5	72.3	72.9	73.6
72.5°	58.1	58.2	58.7	58.6	59.5	60.3	61.2	61.8	62.6	63.4	63.9
75°	44.8	44.8	45.2	45.4	46.4	47.4	47.2	47.6	48.4	49.2	49.7
77.5°	32.7	32.3	32.7	32.9	33.3	34.1	34.2	34.8	35.8	35.5	35.9
80°	24.9	24.3	24.9	25.1	25.1	26.1	26.1	26.6	27.1	26.6	27.1
82.5°	17.7	17.5	17.9	18.0	18.3	18.4	18.6	18.7	19.4	19.1	19.4
85°	8.9	8.7	8.9	8.7	8.9	9.1	9.1	8.9	8.9	9.3	8.7
87.5°	4.5	4.8	4.9	5.3	5.4	5.5	5.5	5.7	5.9	5.8	5.9
90°	9.2	11.0	12.5	14.0	15.5	17.0	18.0	18.9	19.9	20.9	21.5
92.5°	16.5	16.8	17.5	18.3	19.0	19.8	20.2	20.8	21.2	21.8	22.1
95°	30.4	27.9	29.2	30.6	31.9	33.3	34.2	35.1	36.1	37.0	37.4
97.5°	39.5	32.2	35.3	38.3	41.4	44.5	45.2	46.0	46.7	47.5	48.0
100°	47.1	35.7	38.9	42.1	45.4	48.6	50.1	51.6	53.1	54.7	55.6
102.5°	173.8	157.7	130.7	103.8	76.9	49.9	51.9	53.9	55.8	57.8	59.0
105°	281.8	258.8	207.1	155.3	103.7	52.0	54.0	56.2	58.2	60.3	61.7
107.5°	349.5	320.7	258.8	196.7	134.7	72.8	70.6	68.5	66.4	64.3	63.6
110°	393.3	368.0	313.3	258.6	203.8	149.1	130.2	111.2	92.3	73.4	64.3



TEST NUMBER: P331477-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	435.2	430.2	416.7	403.1	389.6	376.1	307.0	237.9	168.9	99.8	65.5
115°	502.8	506.8	511.5	516.2	521.0	525.8	438.0	350.4	262.7	175.0	124.4
117.5°	565.9	569.3	572.6	575.8	579.1	582.3	561.1	539.8	518.7	497.5	464.5
120°	607.8	610.9	614.3	617.8	621.2	624.6	626.9	629.1	631.3	633.6	622.0
122.5°	646.6	650.0	653.6	657.4	661.0	664.8	666.1	667.5	668.9	670.2	668.4
125°	702.6	705.6	709.2	712.8	716.4	720.0	721.3	722.6	724.0	725.3	726.2
127.5°	756.3	759.0	761.7	764.4	767.0	769.7	771.7	773.6	775.5	777.5	778.5
130°	790.9	793.4	795.5	797.6	799.7	801.8	803.9	805.9	808.1	810.1	811.1
132.5°	823.1	825.5	827.6	829.6	831.7	833.8	835.6	837.4	839.2	841.0	841.8
135°	869.3	871.6	873.3	875.0	876.7	878.5	880.4	882.3	884.1	886.0	886.8
137.5°	910.4	912.5	914.4	916.3	918.3	920.2	922.1	923.9	925.8	927.6	928.3
140°	937.4	939.1	941.2	943.3	945.4	947.5	949.2	950.9	952.6	954.3	954.7
142.5°	961.3	963.1	965.5	968.0	970.4	972.7	974.3	975.8	977.4	978.9	979.2
145°	993.6	995.1	998.4	1001.6	1004.8	1008.0	1009.3	1010.7	1012.0	1013.3	1013.5
147.5°	1025.0	1026.3	1029.5	1032.6	1035.8	1039.0	1040.0	1041.0	1042.0	1042.9	1043.0
150°	1044.5	1045.3	1048.3	1051.3	1054.4	1057.4	1058.5	1059.7	1060.8	1061.9	1062.0
152.5°	1062.2	1062.9	1065.8	1068.7	1071.6	1074.4	1075.6	1076.7	1077.8	1079.0	1079.0
155°	1088.1	1088.3	1090.7	1092.9	1095.2	1097.4	1098.6	1099.7	1100.8	1102.0	1101.8
157.5°	1110.1	1110.2	1111.8	1113.4	1114.9	1116.5	1117.8	1119.1	1120.4	1121.7	1121.6
160°	1123.6	1123.6	1124.7	1125.9	1127.0	1128.1	1129.3	1130.4	1131.5	1132.7	1132.6
162.5°	1134.5	1134.4	1135.4	1136.4	1137.4	1138.4	1139.6	1140.9	1142.2	1143.5	1143.4
165°	1149.1	1148.9	1149.4	1150.0	1150.6	1151.1	1152.4	1153.8	1155.1	1156.5	1156.5
167.5°	1160.0	1159.8	1160.3	1160.8	1161.4	1161.9	1163.1	1164.5	1165.8	1167.2	1167.0
170°	1166.2	1165.8	1166.2	1166.5	1167.0	1167.3	1168.7	1170.0	1171.3	1172.6	1172.4
172.5°	1170.3	1169.9	1170.3	1170.6	1171.0	1171.4	1172.8	1174.0	1175.4	1176.7	1176.5
175°	1174.8	1174.3	1174.7	1175.1	1175.5	1175.8	1177.1	1178.5	1179.8	1181.2	1180.9
177.5°	1176.7	1176.3	1176.4	1176.5	1176.7	1176.9	1177.9	1179.0	1180.0	1181.1	1181.0
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331477-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	505.5	505.2	505.2	503.7	505.2	505.2	505.5	507.1	507.7	507.9	507.3
5°	469.0	468.3	467.3	468.3	467.3	468.3	469.0	471.8	473.2	474.6	475.8
7.5°	432.7	430.3	430.0	427.6	430.0	430.3	432.7	434.1	436.9	440.1	443.1
10°	406.4	404.7	404.5	400.6	404.5	404.7	406.4	409.8	412.6	416.4	420.5
12.5°	386.3	382.4	383.2	380.9	383.2	382.4	386.3	386.3	389.6	392.0	398.3
15°	351.4	351.4	350.6	347.2	350.6	351.4	351.4	357.0	357.9	361.8	367.2
17.5°	326.5	326.0	324.1	325.1	324.1	326.0	326.5	330.5	331.2	336.3	340.8
20°	311.6	310.3	307.9	307.9	307.9	310.3	311.6	313.8	316.4	319.4	323.3
22.5°	297.5	297.4	294.8	295.6	294.8	297.4	297.5	299.5	302.0	305.3	308.5
25°	281.0	279.4	278.1	278.7	278.1	279.4	281.0	281.2	284.0	286.2	288.3
27.5°	265.3	264.4	264.3	262.7	264.3	264.4	265.3	265.8	267.4	268.8	270.6
30°	256.3	254.2	254.6	253.6	254.6	254.2	256.3	256.5	257.3	258.1	260.3
32.5°	245.8	245.1	244.8	243.9	244.8	245.1	245.8	246.2	247.9	248.7	250.4
35°	231.8	231.9	231.0	231.3	231.0	231.9	231.8	232.1	232.4	233.2	234.8
37.5°	219.4	220.0	219.5	219.6	219.5	220.0	219.4	219.5	219.8	219.9	220.4
40°	211.2	211.2	211.2	211.9	211.2	211.2	211.2	210.7	210.9	210.7	210.7
42.5°	203.5	203.1	202.9	202.8	202.9	203.1	203.5	202.1	202.8	202.1	201.8
45°	190.2	190.8	191.0	190.0	191.0	190.8	190.2	189.8	189.2	189.0	188.8
47.5°	178.2	178.3	178.2	179.1	178.2	178.3	178.2	177.6	176.7	176.4	175.4
50°	169.8	169.3	169.8	169.3	169.8	169.3	169.8	168.7	168.1	167.1	166.3
52.5°	160.9	161.0	160.7	160.6	160.7	161.0	160.9	159.5	159.3	158.8	157.6
55°	146.9	147.2	147.0	147.0	147.0	147.2	146.9	146.1	145.9	144.6	143.4
57.5°	132.4	132.8	133.0	132.2	133.0	132.8	132.4	132.2	132.2	130.8	129.6
60°	122.3	123.3	123.1	122.8	123.1	123.3	122.3	122.5	122.0	121.1	120.3
62.5°	113.1	113.5	113.4	113.3	113.4	113.5	113.1	112.2	111.9	111.1	110.3
65°	98.9	99.2	98.6	99.2	98.6	99.2	98.9	98.3	96.8	96.4	95.6
67.5°	83.5	83.6	84.1	84.4	84.1	83.6	83.5	83.7	82.8	82.0	81.9
70°	73.9	73.7	74.4	75.0	74.4	73.7	73.9	73.6	72.9	72.3	71.5
72.5°	63.8	64.3	64.1	64.6	64.1	64.3	63.8	63.9	63.4	62.6	61.8
75°	49.2	49.8	49.7	50.2	49.7	49.8	49.2	49.7	49.2	48.4	47.6
77.5°	35.6	35.7	35.6	35.9	35.6	35.7	35.6	35.9	35.5	35.8	34.8
80°	27.1	26.8	26.3	27.1	26.3	26.8	27.1	27.1	26.6	27.1	26.6
82.5°	18.9	19.1	18.7	18.7	18.7	19.1	18.9	19.4	19.1	19.4	18.7
85°	8.7	8.5	8.1	8.1	8.1	8.5	8.7	8.7	9.3	8.9	8.9
87.5°	6.0	5.9	6.0	5.9	6.0	5.9	6.0	5.9	5.8	5.9	5.7
90°	21.8	22.2	22.6	23.0	22.6	22.2	21.8	21.5	20.9	19.9	18.9
92.5°	22.3	22.6	22.7	23.0	22.7	22.6	22.3	22.1	21.8	21.2	20.8
95°	37.2	37.0	36.8	36.6	36.8	37.0	37.2	37.4	37.0	36.1	35.1
97.5°	48.2	48.4	48.7	48.9	48.7	48.4	48.2	48.0	47.5	46.7	46.0
100°	55.9	56.4	56.7	57.1	56.7	56.4	55.9	55.6	54.7	53.1	51.6
102.5°	59.6	60.1	60.6	61.2	60.6	60.1	59.6	59.0	57.8	55.8	53.9
105°	62.5	63.2	64.0	64.7	64.0	63.2	62.5	61.7	60.3	58.2	56.2
107.5°	64.4	65.1	65.9	66.6	65.9	65.1	64.4	63.6	64.3	66.4	68.5
110°	65.0	65.8	66.5	67.3	66.5	65.8	65.0	64.3	73.4	92.3	111.2



TEST NUMBER: P331477-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	66.2	66.8	67.4	68.0	67.4	66.8	66.2	65.5	99.8	168.9	237.9
115°	110.8	97.1	83.5	69.9	83.5	97.1	110.8	124.4	175.0	262.7	350.4
117.5°	419.6	374.9	330.1	285.3	330.1	374.9	419.6	464.5	497.5	518.7	539.8
120°	596.5	570.9	545.3	519.8	545.3	570.9	596.5	622.0	633.6	631.3	629.1
122.5°	663.4	658.5	653.5	648.6	653.5	658.5	663.4	668.4	670.2	668.9	667.5
125°	726.8	727.4	727.9	728.5	727.9	727.4	726.8	726.2	725.3	724.0	722.6
127.5°	778.6	778.7	778.8	778.9	778.8	778.7	778.6	778.5	777.5	775.5	773.6
130°	810.8	810.7	810.5	810.3	810.5	810.7	810.8	811.1	810.1	808.1	805.9
132.5°	841.5	841.3	841.2	841.0	841.2	841.3	841.5	841.8	841.0	839.2	837.4
135°	886.4	886.0	885.6	885.3	885.6	886.0	886.4	886.8	886.0	884.1	882.3
137.5°	927.6	926.9	926.3	925.7	926.3	926.9	927.6	928.3	927.6	925.8	923.9
140°	953.8	952.8	951.8	950.9	951.8	952.8	953.8	954.7	954.3	952.6	950.9
142.5°	978.3	977.3	976.4	975.4	976.4	977.3	978.3	979.2	978.9	977.4	975.8
145°	1012.5	1011.6	1010.7	1009.7	1010.7	1011.6	1012.5	1013.5	1013.3	1012.0	1010.7
147.5°	1042.2	1041.4	1040.6	1039.8	1040.6	1041.4	1042.2	1043.0	1042.9	1042.0	1041.0
150°	1061.1	1060.2	1059.2	1058.3	1059.2	1060.2	1061.1	1062.0	1061.9	1060.8	1059.7
152.5°	1077.7	1076.5	1075.2	1074.0	1075.2	1076.5	1077.7	1079.0	1079.0	1077.8	1076.7
155°	1100.3	1098.8	1097.3	1095.7	1097.3	1098.8	1100.3	1101.8	1102.0	1100.8	1099.7
157.5°	1120.1	1118.7	1117.1	1115.7	1117.1	1118.7	1120.1	1121.6	1121.7	1120.4	1119.1
160°	1131.2	1129.9	1128.6	1127.3	1128.6	1129.9	1131.2	1132.6	1132.7	1131.5	1130.4
162.5°	1141.7	1140.1	1138.4	1136.8	1138.4	1140.1	1141.7	1143.4	1143.5	1142.2	1140.9
165°	1155.1	1153.8	1152.4	1151.1	1152.4	1153.8	1155.1	1156.5	1156.5	1155.1	1153.8
167.5°	1165.3	1163.6	1161.9	1160.2	1161.9	1163.6	1165.3	1167.0	1167.2	1165.8	1164.5
170°	1170.7	1169.0	1167.3	1165.6	1167.3	1169.0	1170.7	1172.4	1172.6	1171.3	1170.0
172.5°	1174.8	1173.1	1171.4	1169.7	1171.4	1173.1	1174.8	1176.5	1176.7	1175.4	1174.0
175°	1178.9	1177.1	1175.2	1173.3	1175.2	1177.1	1178.9	1180.9	1181.2	1179.8	1178.5
177.5°	1179.6	1178.2	1176.9	1175.5	1176.9	1178.2	1179.6	1181.0	1181.1	1180.0	1179.0
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331477-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	506.5	508.3	511.0	514.0	515.8	519.2	520.1	521.7	523.2	526.6	530.1
5°	477.2	480.1	486.8	490.4	495.4	501.3	505.2	509.3	513.7	521.4	528.5
7.5°	445.9	450.6	459.0	465.7	473.0	481.3	487.4	495.4	502.1	513.0	523.3
10°	425.0	431.7	439.2	447.3	457.4	466.3	474.8	484.9	493.0	506.0	518.2
12.5°	406.2	407.2	417.9	426.9	440.7	451.7	461.5	474.6	482.5	497.9	510.7
15°	373.4	379.4	389.1	396.2	412.6	426.6	440.4	454.0	463.1	482.1	498.9
17.5°	345.6	351.2	361.2	372.8	384.6	398.5	416.3	430.7	443.1	464.8	484.7
20°	328.1	335.0	345.2	357.1	367.5	382.6	398.1	414.5	427.8	452.4	475.6
22.5°	313.3	318.7	326.9	338.7	349.9	363.8	380.7	398.6	412.6	439.1	462.6
25°	292.3	296.8	302.0	311.7	324.5	339.7	352.8	372.6	393.0	417.7	446.2
27.5°	273.4	276.6	281.2	289.8	299.7	313.9	328.5	347.1	367.7	394.6	424.7
30°	261.9	263.9	268.6	275.7	285.4	296.6	311.4	329.1	350.3	377.4	407.3
32.5°	251.9	253.7	256.8	263.5	272.0	281.5	294.8	312.6	332.7	359.4	392.6
35°	236.8	238.2	240.9	246.3	251.0	260.3	271.4	287.7	306.5	332.0	366.4
37.5°	221.8	223.7	225.3	227.7	233.6	239.8	249.4	263.1	281.6	307.4	340.2
40°	211.9	213.5	216.0	217.0	221.8	227.3	235.1	247.7	266.4	289.9	321.9
42.5°	201.8	203.5	204.9	206.1	210.3	215.1	222.2	233.0	249.5	272.3	304.1
45°	188.2	188.4	189.8	192.1	194.0	197.5	202.6	211.9	224.6	246.1	274.9
47.5°	174.3	174.6	174.8	175.8	178.0	181.1	184.5	192.1	203.5	220.6	248.6
50°	165.1	164.7	165.1	165.9	167.3	170.0	173.8	179.2	188.6	204.6	230.3
52.5°	156.1	156.1	155.9	156.1	157.3	159.1	161.8	166.5	174.8	189.5	212.1
55°	142.6	141.6	141.8	141.0	142.9	143.2	145.3	149.1	156.4	166.5	187.8
57.5°	128.1	127.3	126.4	126.2	126.0	127.1	128.7	131.7	137.3	146.2	163.5
60°	118.9	117.9	116.6	116.3	116.3	116.9	117.7	119.9	125.2	133.0	147.2
62.5°	109.5	108.3	107.6	106.6	106.2	106.8	107.6	109.2	113.1	120.5	132.7
65°	95.0	93.5	92.6	92.4	91.9	91.4	91.8	93.4	96.4	102.3	112.0
67.5°	80.4	79.1	78.9	77.7	77.1	77.2	77.1	78.5	80.3	85.4	92.6
70°	70.9	69.9	69.5	68.5	68.0	67.7	67.2	68.5	70.3	74.5	80.8
72.5°	61.2	60.3	59.5	58.6	58.7	58.2	58.1	58.9	60.4	64.3	69.2
75°	47.2	47.4	46.4	45.4	45.2	44.8	44.8	45.4	46.0	49.0	52.9
77.5°	34.2	34.1	33.3	32.9	32.7	32.3	32.7	33.1	33.4	35.5	38.3
80°	26.1	26.1	25.1	25.1	24.9	24.3	24.9	24.5	25.3	27.4	29.3
82.5°	18.6	18.4	18.3	18.0	17.9	17.5	17.7	18.2	18.5	19.9	21.1
85°	9.1	9.1	8.9	8.7	8.9	8.7	8.9	9.1	9.3	9.9	11.0
87.5°	5.5	5.5	5.4	5.3	4.9	4.8	4.5	4.4	4.3	4.0	3.7
90°	18.0	17.0	15.5	14.0	12.5	11.0	9.2	7.1	5.0	2.9	0.9
92.5°	20.2	19.8	19.0	18.3	17.5	16.8	16.5	16.7	16.9	17.0	17.2
95°	34.2	33.3	31.9	30.6	29.2	27.9	30.4	36.6	42.9	49.1	55.4
97.5°	45.2	44.5	41.4	38.3	35.3	32.2	39.5	57.1	74.7	92.3	109.9
100°	50.1	48.6	45.4	42.1	38.9	35.7	47.1	73.0	98.9	124.8	150.8
102.5°	51.9	49.9	76.9	103.8	130.7	157.7	173.8	179.3	184.9	190.3	195.8
105°	54.0	52.0	103.7	155.3	207.1	258.8	281.8	276.1	270.4	264.7	259.0
107.5°	70.6	72.8	134.7	196.7	258.8	320.7	349.5	344.8	340.3	335.7	331.1
110°	130.2	149.1	203.8	258.6	313.3	368.0	393.3	389.4	385.4	381.5	377.5



TEST NUMBER: P331477-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	307.0	376.1	389.6	403.1	416.7	430.2	435.2	431.7	428.1	424.6	421.1
115°	438.0	525.8	521.0	516.2	511.5	506.8	502.8	499.6	496.4	493.1	489.9
117.5°	561.1	582.3	579.1	575.8	572.6	569.3	565.9	562.2	558.7	555.1	551.4
120°	626.9	624.6	621.2	617.8	614.3	610.9	607.8	604.9	602.1	599.3	596.5
122.5°	666.1	664.8	661.0	657.4	653.6	650.0	646.6	643.5	640.6	637.6	634.6
125°	721.3	720.0	716.4	712.8	709.2	705.6	702.6	700.1	697.7	695.2	692.7
127.5°	771.7	769.7	767.0	764.4	761.7	759.0	756.3	753.6	750.8	748.1	745.4
130°	803.9	801.8	799.7	797.6	795.5	793.4	790.9	787.8	784.9	781.9	778.8
132.5°	835.6	833.8	831.7	829.6	827.6	825.5	823.1	820.6	818.1	815.5	812.9
135°	880.4	878.5	876.7	875.0	873.3	871.6	869.3	866.3	863.3	860.2	857.2
137.5°	922.1	920.2	918.3	916.3	914.4	912.5	910.4	908.4	906.2	904.1	902.0
140°	949.2	947.5	945.4	943.3	941.2	939.1	937.4	935.9	934.3	932.8	931.3
142.5°	974.3	972.7	970.4	968.0	965.5	963.1	961.3	959.9	958.6	957.2	955.8
145°	1009.3	1008.0	1004.8	1001.6	998.4	995.1	993.6	993.8	994.0	994.2	994.3
147.5°	1040.0	1039.0	1035.8	1032.6	1029.5	1026.3	1025.0	1025.7	1026.4	1027.2	1028.0
150°	1058.5	1057.4	1054.4	1051.3	1048.3	1045.3	1044.5	1045.8	1047.0	1048.4	1049.7
152.5°	1075.6	1074.4	1071.6	1068.7	1065.8	1062.9	1062.2	1063.7	1065.1	1066.7	1068.2
155°	1098.6	1097.4	1095.2	1092.9	1090.7	1088.3	1088.1	1089.8	1091.5	1093.1	1094.9
157.5°	1117.8	1116.5	1114.9	1113.4	1111.8	1110.2	1110.1	1111.5	1112.9	1114.5	1115.9
160°	1129.3	1128.1	1127.0	1125.9	1124.7	1123.6	1123.6	1124.7	1125.9	1127.0	1128.1
162.5°	1139.6	1138.4	1137.4	1136.4	1135.4	1134.4	1134.5	1135.6	1136.8	1137.9	1139.1
165°	1152.4	1151.1	1150.6	1150.0	1149.4	1148.9	1149.1	1150.3	1151.4	1152.5	1153.7
167.5°	1163.1	1161.9	1161.4	1160.8	1160.3	1159.8	1160.0	1161.2	1162.3	1163.4	1164.6
170°	1168.7	1167.3	1167.0	1166.5	1166.2	1165.8	1166.2	1167.3	1168.5	1169.6	1170.7
172.5°	1172.8	1171.4	1171.0	1170.6	1170.3	1169.9	1170.3	1171.4	1172.5	1173.7	1174.8
175°	1177.1	1175.8	1175.5	1175.1	1174.7	1174.3	1174.8	1176.2	1177.4	1178.8	1180.1
177.5°	1177.9	1176.9	1176.7	1176.5	1176.4	1176.3	1176.7	1177.8	1178.8	1179.9	1181.0
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331477-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	529.9	530.7	533.2	535.8	538.8	539.6	540.8	539.8	539.4	542.4	544.7
5°	531.4	534.9	542.1	548.6	554.0	557.9	562.0	563.6	566.6	570.8	576.1
7.5°	529.6	536.7	547.9	557.3	567.6	575.0	580.8	585.8	591.7	599.8	608.6
10°	527.7	537.2	550.8	562.3	574.9	584.4	592.3	600.0	608.9	620.1	631.6
12.5°	524.1	535.4	552.4	566.1	582.2	591.6	602.2	618.8	628.4	643.9	660.1
15°	516.9	529.5	553.2	570.0	588.3	606.1	625.7	641.5	657.3	666.5	689.3
17.5°	506.3	524.7	551.0	570.6	593.8	621.8	643.9	661.8	680.0	694.8	706.3
20°	497.7	517.7	547.8	571.2	598.8	628.9	654.2	672.5	688.3	700.7	707.8
22.5°	486.9	512.1	541.3	568.8	604.0	633.8	660.4	674.8	688.0	694.0	696.8
25°	469.8	500.2	533.2	566.8	606.5	638.1	662.4	671.1	674.9	669.1	659.3
27.5°	451.3	485.2	523.8	562.9	604.9	635.3	652.7	651.4	644.9	625.8	610.6
30°	437.6	474.8	516.3	559.1	601.2	630.8	640.9	630.8	616.0	594.8	573.0
32.5°	423.1	461.7	508.4	553.6	594.4	620.5	622.6	605.2	582.3	558.1	531.1
35°	401.3	443.0	493.5	541.3	580.0	596.4	586.7	555.8	528.7	495.7	458.8
37.5°	376.6	422.7	473.2	523.3	558.3	562.6	538.4	506.0	467.7	428.9	385.5
40°	358.1	407.0	459.1	509.4	540.5	536.0	505.2	469.6	424.0	376.6	336.3
42.5°	341.6	390.4	443.4	492.9	517.7	505.5	469.6	425.8	376.8	332.2	295.2
45°	313.0	363.2	417.5	465.3	479.5	457.4	409.8	361.1	313.0	275.7	246.6
47.5°	285.2	334.8	388.6	430.6	435.6	405.9	353.9	303.9	262.4	232.1	211.5
50°	264.7	314.6	367.8	405.4	403.7	367.8	314.4	266.8	232.1	207.6	193.9
52.5°	246.5	293.6	344.6	378.8	370.1	331.1	280.0	237.7	209.3	190.1	177.6
55°	217.9	261.5	310.1	337.5	321.6	278.3	235.1	201.2	180.0	165.7	156.0
57.5°	189.7	230.5	272.2	289.0	271.5	231.5	195.6	170.9	155.0	144.4	138.0
60°	172.2	207.9	244.9	259.5	238.6	203.0	174.6	152.6	139.7	131.1	125.4
62.5°	154.7	186.6	221.6	229.5	210.4	180.3	155.2	136.8	126.4	118.6	113.2
65°	130.8	157.0	183.5	188.8	171.2	147.8	128.0	116.1	106.7	101.1	96.8
67.5°	107.4	128.3	147.1	151.3	135.9	119.8	105.4	95.0	88.7	84.0	80.3
70°	93.4	110.0	125.4	128.9	116.5	102.1	91.1	82.8	77.1	73.1	69.6
72.5°	78.6	92.5	105.3	107.6	97.6	86.5	77.6	71.0	66.0	63.4	60.1
75°	60.2	68.3	78.2	78.8	72.1	65.5	58.6	54.3	51.6	48.4	46.8
77.5°	42.4	48.8	54.5	55.6	51.6	47.1	43.2	39.9	37.6	36.1	34.6
80°	32.4	37.5	39.9	41.3	38.5	35.2	33.0	30.8	29.3	28.4	27.4
82.5°	23.2	26.3	28.5	29.7	28.1	26.1	24.0	22.6	21.6	20.8	20.4
85°	11.8	13.2	14.6	15.0	14.6	13.7	12.6	12.6	11.9	11.8	11.8
87.5°	4.6	5.7	6.2	7.0	7.0	7.4	7.7	7.8	7.9	7.9	8.0
90°	2.9	5.0	7.1	9.2	11.0	12.5	14.0	15.5	17.0	18.0	18.9
92.5°	17.0	16.9	16.7	16.5	16.8	17.5	18.3	19.0	19.8	20.2	20.8
95°	49.1	42.9	36.6	30.4	27.9	29.2	30.6	31.9	33.3	34.2	35.1
97.5°	92.3	74.7	57.1	39.5	32.2	35.3	38.3	41.4	44.5	45.2	46.0
100°	124.8	98.9	73.0	47.1	35.7	38.9	42.1	45.4	48.6	50.1	51.6
102.5°	190.3	184.9	179.3	173.8	157.7	130.7	103.8	76.9	49.9	51.9	53.9
105°	264.7	270.4	276.1	281.8	258.8	207.1	155.3	103.7	52.0	54.0	56.2
107.5°	335.7	340.3	344.8	349.5	320.7	258.8	196.7	134.7	72.8	70.6	68.5
110°	381.5	385.4	389.4	393.3	368.0	313.3	258.6	203.8	149.1	130.2	111.2



TEST NUMBER: P331477-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	424.6	428.1	431.7	435.2	430.2	416.7	403.1	389.6	376.1	307.0	237.9
115°	493.1	496.4	499.6	502.8	506.8	511.5	516.2	521.0	525.8	438.0	350.4
117.5°	555.1	558.7	562.2	565.9	569.3	572.6	575.8	579.1	582.3	561.1	539.8
120°	599.3	602.1	604.9	607.8	610.9	614.3	617.8	621.2	624.6	626.9	629.1
122.5°	637.6	640.6	643.5	646.6	650.0	653.6	657.4	661.0	664.8	666.1	667.5
125°	695.2	697.7	700.1	702.6	705.6	709.2	712.8	716.4	720.0	721.3	722.6
127.5°	748.1	750.8	753.6	756.3	759.0	761.7	764.4	767.0	769.7	771.7	773.6
130°	781.9	784.9	787.8	790.9	793.4	795.5	797.6	799.7	801.8	803.9	805.9
132.5°	815.5	818.1	820.6	823.1	825.5	827.6	829.6	831.7	833.8	835.6	837.4
135°	860.2	863.3	866.3	869.3	871.6	873.3	875.0	876.7	878.5	880.4	882.3
137.5°	904.1	906.2	908.4	910.4	912.5	914.4	916.3	918.3	920.2	922.1	923.9
140°	932.8	934.3	935.9	937.4	939.1	941.2	943.3	945.4	947.5	949.2	950.9
142.5°	957.2	958.6	959.9	961.3	963.1	965.5	968.0	970.4	972.7	974.3	975.8
145°	994.2	994.0	993.8	993.6	995.1	998.4	1001.6	1004.8	1008.0	1009.3	1010.7
147.5°	1027.2	1026.4	1025.7	1025.0	1026.3	1029.5	1032.6	1035.8	1039.0	1040.0	1041.0
150°	1048.4	1047.0	1045.8	1044.5	1045.3	1048.3	1051.3	1054.4	1057.4	1058.5	1059.7
152.5°	1066.7	1065.1	1063.7	1062.2	1062.9	1065.8	1068.7	1071.6	1074.4	1075.6	1076.7
155°	1093.1	1091.5	1089.8	1088.1	1088.3	1090.7	1092.9	1095.2	1097.4	1098.6	1099.7
157.5°	1114.5	1112.9	1111.5	1110.1	1110.2	1111.8	1113.4	1114.9	1116.5	1117.8	1119.1
160°	1127.0	1125.9	1124.7	1123.6	1123.6	1124.7	1125.9	1127.0	1128.1	1129.3	1130.4
162.5°	1137.9	1136.8	1135.6	1134.5	1134.4	1135.4	1136.4	1137.4	1138.4	1139.6	1140.9
165°	1152.5	1151.4	1150.3	1149.1	1148.9	1149.4	1150.0	1150.6	1151.1	1152.4	1153.8
167.5°	1163.4	1162.3	1161.2	1160.0	1159.8	1160.3	1160.8	1161.4	1161.9	1163.1	1164.5
170°	1169.6	1168.5	1167.3	1166.2	1165.8	1166.2	1166.5	1167.0	1167.3	1168.7	1170.0
172.5°	1173.7	1172.5	1171.4	1170.3	1169.9	1170.3	1170.6	1171.0	1171.4	1172.8	1174.0
175°	1178.8	1177.4	1176.2	1174.8	1174.3	1174.7	1175.1	1175.5	1175.8	1177.1	1178.5
177.5°	1179.9	1178.8	1177.8	1176.7	1176.3	1176.4	1176.5	1176.7	1176.9	1177.9	1179.0
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331477-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	546.7	548.9	548.9	549.3	551.9	551.5	551.3
5°	581.8	585.2	585.6	589.2	591.7	590.8	588.6
7.5°	614.8	621.3	626.2	628.8	632.0	634.0	633.1
10°	641.1	650.4	656.1	660.0	664.6	668.1	666.8
12.5°	664.9	676.0	683.9	690.5	691.0	695.4	692.4
15°	702.1	713.8	715.1	719.9	723.8	723.4	723.5
17.5°	714.3	718.1	718.9	719.0	719.1	717.6	714.5
20°	710.0	708.6	705.2	702.5	697.9	697.2	693.2
22.5°	689.2	684.7	676.1	670.4	663.2	661.3	660.1
25°	648.5	638.5	624.7	611.5	607.9	600.8	602.8
27.5°	592.4	576.9	562.0	551.3	541.6	531.0	534.0
30°	553.0	535.6	514.5	498.3	487.9	477.9	476.0
32.5°	506.0	480.5	457.0	442.7	426.9	420.4	413.5
35°	425.0	400.0	376.7	356.7	345.2	336.3	328.1
37.5°	352.1	323.4	304.6	288.4	280.0	274.9	276.3
40°	306.9	281.8	268.0	255.7	247.9	244.3	245.1
42.5°	270.3	251.5	240.1	231.7	226.2	224.2	223.7
45°	228.7	218.2	208.8	204.0	201.3	199.1	197.7
47.5°	200.4	191.7	186.5	183.6	181.3	179.1	179.0
50°	183.3	177.6	174.0	170.9	169.2	167.6	169.0
52.5°	170.3	165.1	161.5	158.8	158.1	156.7	156.6
55°	151.1	147.0	144.5	142.0	140.8	140.0	138.9
57.5°	133.6	129.7	127.3	125.8	123.5	122.7	122.3
60°	121.1	118.1	115.7	113.6	112.6	111.0	111.0
62.5°	109.6	106.6	104.3	102.8	101.1	100.5	100.7
65°	93.0	90.5	88.3	86.7	86.3	85.1	85.5
67.5°	77.7	76.1	73.7	72.8	72.1	71.4	70.9
70°	67.4	65.8	64.6	63.4	62.8	62.8	62.8
72.5°	58.9	56.9	56.2	54.7	55.0	54.4	53.7
75°	45.6	44.3	43.8	43.2	42.2	42.2	42.2
77.5°	33.5	33.2	32.5	31.8	31.6	31.4	31.5
80°	25.9	25.7	25.3	25.3	24.9	24.7	24.3
82.5°	20.0	19.4	19.2	19.0	18.9	18.9	18.8
85°	11.3	11.0	11.0	11.1	10.7	10.7	11.0
87.5°	8.4	8.6	8.5	8.6	8.8	8.7	8.8
90°	19.9	20.9	21.5	21.8	22.2	22.6	23.0
92.5°	21.2	21.8	22.1	22.3	22.6	22.7	23.0
95°	36.1	37.0	37.4	37.2	37.0	36.8	36.6
97.5°	46.7	47.5	48.0	48.2	48.4	48.7	48.9
100°	53.1	54.7	55.6	55.9	56.4	56.7	57.1
102.5°	55.8	57.8	59.0	59.6	60.1	60.6	61.2
105°	58.2	60.3	61.7	62.5	63.2	64.0	64.7
107.5°	66.4	64.3	63.6	64.4	65.1	65.9	66.6
110°	92.3	73.4	64.3	65.0	65.8	66.5	67.3



TEST NUMBER: P331477-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	168.9	99.8	65.5	66.2	66.8	67.4	68.0
115°	262.7	175.0	124.4	110.8	97.1	83.5	69.9
117.5°	518.7	497.5	464.5	419.6	374.9	330.1	285.3
120°	631.3	633.6	622.0	596.5	570.9	545.3	519.8
122.5°	668.9	670.2	668.4	663.4	658.5	653.5	648.6
125°	724.0	725.3	726.2	726.8	727.4	727.9	728.5
127.5°	775.5	777.5	778.5	778.6	778.7	778.8	778.9
130°	808.1	810.1	811.1	810.8	810.7	810.5	810.3
132.5°	839.2	841.0	841.8	841.5	841.3	841.2	841.0
135°	884.1	886.0	886.8	886.4	886.0	885.6	885.3
137.5°	925.8	927.6	928.3	927.6	926.9	926.3	925.7
140°	952.6	954.3	954.7	953.8	952.8	951.8	950.9
142.5°	977.4	978.9	979.2	978.3	977.3	976.4	975.4
145°	1012.0	1013.3	1013.5	1012.5	1011.6	1010.7	1009.7
147.5°	1042.0	1042.9	1043.0	1042.2	1041.4	1040.6	1039.8
150°	1060.8	1061.9	1062.0	1061.1	1060.2	1059.2	1058.3
152.5°	1077.8	1079.0	1079.0	1077.7	1076.5	1075.2	1074.0
155°	1100.8	1102.0	1101.8	1100.3	1098.8	1097.3	1095.7
157.5°	1120.4	1121.7	1121.6	1120.1	1118.7	1117.1	1115.7
160°	1131.5	1132.7	1132.6	1131.2	1129.9	1128.6	1127.3
162.5°	1142.2	1143.5	1143.4	1141.7	1140.1	1138.4	1136.8
165°	1155.1	1156.5	1156.5	1155.1	1153.8	1152.4	1151.1
167.5°	1165.8	1167.2	1167.0	1165.3	1163.6	1161.9	1160.2
170°	1171.3	1172.6	1172.4	1170.7	1169.0	1167.3	1165.6
172.5°	1175.4	1176.7	1176.5	1174.8	1173.1	1171.4	1169.7
175°	1179.8	1181.2	1180.9	1178.9	1177.1	1175.2	1173.3
177.5°	1180.0	1181.1	1181.0	1179.6	1178.2	1176.9	1175.5
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5

(END OF REPORT)