

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331831

Luminaire Tested: **S122RDIW-S865D710U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331831
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S865D710U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5853.3 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331831

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331831

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	44
2	90	83	77	72	83	77	72	68	66	62	59	56	53	50	46	44	42	38
3	83	73	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37	33
4	76	65	58	52	70	61	54	49	52	47	43	45	41	38	37	34	32	29
5	70	58	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28	25
6	64	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	23	20
8	56	43	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20	18
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	19	16
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23675	23675	23675
5°	23765	23378	23506
10°	23582	22996	22799
15°	23311	22313	21670
20°	22936	21340	20270
25°	22552	20236	18912
30°	22018	19099	17169
35°	21498	17864	15640
40°	20976	16585	13873
45°	20361	15150	12271
50°	19733	13700	10698
55°	19088	12141	9188
60°	18338	10498	7627
65°	17490	8821	6946
70°	16475	7265	6387
75°	15234	6625	5958
80°	13445	5923	5430
85°	10578	4668	4668



TEST NUMBER: P331831

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.2	2.3
10°-20°	376.8	6.4
20°-30°	529.2	9.0
30°-40°	577.1	9.9
40°-50°	530.6	9.1
50°-60°	416.7	7.1
60°-70°	271.7	4.6
70°-80°	140.1	2.4
80°-90°	38.7	0.7
90°-100°	32.3	0.6
100°-110°	118.3	2.0
110°-120°	316.3	5.4
120°-130°	522.2	8.9
130°-140°	555.4	9.5
140°-150°	516.2	8.8
150°-160°	415.0	7.1
160°-170°	267.4	4.6
170°-180°	92.1	1.6
0°-30°	1043.3	17.8
0°-40°	1620.3	27.7
0°-60°	2567.6	43.9
0°-90°	3018.1	51.6
90°-120°	467.0	8.0
90°-150°	2060.7	35.2
90°-180°	2835.0	48.4
0°-180°	5853.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1466	1466	1466	1466	1466	
5°	1466	1459	1442	1453	1450	139
15°	1395	1378	1335	1310	1296	393
25°	1266	1221	1136	1083	1062	582
35°	1091	1020	906	826	794	682
45°	892	800	664	573	537	688
55°	678	572	431	355	326	606
65°	458	350	231	188	182	454
75°	244	154	106	97	96	258
85°	57	31	25	25	25	67
90°	1	8	14	17	19	4
95°	46	24	27	31	30	56
105°	213	222	43	50	53	227
115°	402	415	432	123	57	396
125°	569	578	592	596	598	507
135°	704	715	722	728	727	544
145°	817	817	828	833	830	511
155°	900	894	902	905	900	414
165°	948	944	946	950	946	268
175°	970	965	966	970	964	92
180°	968	968	968	968	968	



TEST NUMBER: P331831

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3
2.5°	1471.6	1470.4	1469.2	1468.0	1466.9	1465.0	1462.4	1459.8	1457.2	1454.6	1457.0
5°	1466.3	1464.8	1463.3	1461.8	1460.4	1457.7	1453.9	1450.1	1446.2	1442.4	1445.0
7.5°	1451.1	1449.3	1447.5	1445.7	1443.8	1440.7	1436.2	1431.7	1427.2	1422.7	1423.5
10°	1438.4	1436.3	1434.3	1432.2	1430.1	1426.2	1420.3	1414.4	1408.5	1402.6	1401.7
12.5°	1422.5	1419.9	1417.4	1414.9	1412.3	1407.3	1399.7	1392.2	1384.6	1377.1	1375.5
15°	1394.6	1391.4	1388.1	1384.9	1381.6	1375.0	1365.0	1355.0	1344.9	1334.9	1329.3
17.5°	1360.4	1355.4	1350.5	1345.5	1340.6	1331.7	1318.8	1305.9	1293.1	1280.2	1273.6
20°	1334.9	1329.0	1323.1	1317.2	1311.3	1301.0	1286.2	1271.5	1256.8	1242.0	1234.6
22.5°	1307.3	1300.7	1294.1	1287.5	1280.9	1269.3	1252.6	1236.0	1219.4	1202.7	1193.2
25°	1265.9	1256.5	1247.0	1237.6	1228.2	1213.7	1194.2	1174.8	1155.3	1135.9	1123.8
27.5°	1216.0	1205.7	1195.5	1185.2	1175.0	1158.9	1136.9	1115.0	1093.0	1071.1	1057.0
30°	1181.0	1169.8	1158.6	1147.4	1136.2	1118.8	1095.2	1071.6	1048.0	1024.4	1009.4
32.5°	1147.0	1133.9	1120.8	1107.7	1094.6	1076.1	1052.0	1027.9	1003.9	979.8	962.7
35°	1090.7	1075.7	1060.7	1045.6	1030.6	1010.1	984.1	958.2	932.3	906.3	887.7
37.5°	1034.5	1018.0	1001.5	984.9	968.4	946.3	918.7	891.0	863.4	835.7	815.2
40°	995.2	977.5	959.8	942.1	924.4	901.3	872.7	844.1	815.5	786.9	765.9
42.5°	954.9	936.2	917.6	899.0	880.3	856.2	826.7	797.1	767.6	738.0	716.4
45°	891.7	871.9	852.2	832.4	812.7	787.3	756.4	725.4	694.4	663.5	642.5
47.5°	830.1	809.2	788.3	767.3	746.4	719.9	688.0	656.0	624.0	592.1	571.3
50°	785.6	764.6	743.7	722.7	701.8	675.1	642.7	610.2	577.8	545.4	525.0
52.5°	742.0	720.1	698.3	676.4	654.5	627.7	596.0	564.2	532.5	500.8	481.1
55°	678.1	655.1	632.1	609.1	586.1	558.6	526.8	494.9	463.1	431.3	413.6
57.5°	612.5	588.9	565.3	541.7	518.2	491.1	460.4	429.8	399.2	368.6	352.4
60°	567.9	544.3	520.8	497.2	473.6	446.6	416.2	385.8	355.5	325.1	310.1
62.5°	524.4	500.8	477.2	453.6	430.0	403.8	374.8	345.9	316.9	287.9	273.6
65°	457.8	433.9	410.0	386.1	362.3	337.0	310.5	284.0	257.4	230.9	220.9
67.5°	393.6	369.9	346.2	322.4	298.7	274.9	251.1	227.2	203.3	179.4	174.8
70°	349.0	326.0	303.0	280.0	257.0	235.3	215.0	194.6	174.3	153.9	151.0
72.5°	306.5	284.5	262.4	240.4	218.3	199.1	182.8	166.4	150.1	133.8	131.3
75°	244.2	223.5	202.9	182.2	161.6	146.3	136.2	126.2	116.2	106.2	104.1
77.5°	182.9	164.7	146.6	128.5	110.4	99.0	94.1	89.3	84.5	79.6	78.4
80°	144.6	129.6	114.6	99.5	84.5	75.5	72.5	69.6	66.6	63.7	62.5
82.5°	109.6	97.9	86.1	74.4	62.7	55.8	53.8	51.8	49.8	47.8	47.1
85°	57.1	50.9	44.7	38.5	32.3	28.8	27.9	27.0	26.1	25.2	25.2
87.5°	17.1	15.6	14.0	12.5	10.9	10.3	10.5	10.8	11.0	11.3	11.2
90°	0.7	2.4	4.1	5.8	7.5	9.0	10.3	11.5	12.8	14.0	14.8
92.5°	14.1	14.0	13.8	13.7	13.5	13.8	14.4	15.0	15.6	16.2	16.6
95°	45.5	40.4	35.2	30.1	25.0	22.9	24.0	25.1	26.2	27.3	28.1
97.5°	90.3	75.8	61.4	46.9	32.4	26.5	29.0	31.5	34.0	36.5	37.2
100°	123.9	102.6	81.3	60.0	38.7	29.3	32.0	34.6	37.3	39.9	41.1
102.5°	160.9	156.4	151.8	147.3	142.8	129.5	107.4	85.3	63.1	41.0	42.6
105°	212.8	217.5	222.2	226.8	231.5	212.6	170.1	127.6	85.2	42.7	44.4
107.5°	272.0	275.8	279.6	283.3	287.1	263.5	212.6	161.7	110.7	59.8	58.0
110°	310.1	313.4	316.7	319.9	323.2	302.3	257.4	212.4	167.5	122.5	107.0



TEST NUMBER: P331831

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	346.0	348.9	351.8	354.6	357.5	353.4	342.3	331.2	320.1	309.0	252.3
115°	402.5	405.2	407.8	410.5	413.1	416.4	420.3	424.2	428.0	431.9	359.9
117.5°	453.1	456.0	459.0	461.9	464.9	467.7	470.4	473.1	475.7	478.4	461.0
120°	490.0	492.4	494.7	497.0	499.4	501.9	504.7	507.5	510.3	513.1	515.0
122.5°	521.4	523.9	526.3	528.8	531.2	534.0	537.0	540.1	543.1	546.2	547.3
125°	569.1	571.2	573.2	575.2	577.2	579.7	582.7	585.6	588.6	591.5	592.6
127.5°	612.4	614.6	616.9	619.1	621.4	623.6	625.8	628.0	630.2	632.4	634.0
130°	639.8	642.3	644.8	647.3	649.8	651.9	653.6	655.3	657.0	658.8	660.5
132.5°	667.9	670.0	672.1	674.2	676.3	678.2	679.9	681.6	683.4	685.1	686.5
135°	704.3	706.7	709.2	711.7	714.2	716.2	717.6	719.0	720.4	721.8	723.3
137.5°	741.1	742.8	744.6	746.3	748.0	749.7	751.3	752.9	754.5	756.1	757.6
140°	765.2	766.4	767.6	768.9	770.1	771.6	773.3	775.0	776.7	778.5	779.9
142.5°	785.3	786.4	787.6	788.7	789.8	791.3	793.3	795.3	797.2	799.2	800.5
145°	817.0	816.8	816.7	816.5	816.3	817.6	820.2	822.9	825.5	828.2	829.3
147.5°	844.5	844.0	843.4	842.8	842.2	843.2	845.8	848.4	851.0	853.6	854.5
150°	862.5	861.4	860.3	859.2	858.1	858.8	861.3	863.8	866.3	868.8	869.7
152.5°	877.6	876.4	875.2	873.9	872.7	873.3	875.7	878.0	880.4	882.8	883.7
155°	899.6	898.2	896.8	895.4	894.0	894.2	896.1	897.9	899.8	901.7	902.6
157.5°	916.8	915.6	914.4	913.2	912.1	912.1	913.4	914.7	916.0	917.3	918.4
160°	926.9	925.9	925.0	924.1	923.1	923.1	924.1	925.0	925.9	926.9	927.8
162.5°	935.8	934.9	934.0	933.0	932.1	932.0	932.8	933.7	934.5	935.3	936.3
165°	947.9	946.9	946.0	945.1	944.1	943.9	944.4	944.8	945.3	945.8	946.9
167.5°	956.8	955.9	955.0	954.0	953.1	952.9	953.3	953.7	954.2	954.6	955.7
170°	961.9	960.9	960.0	959.1	958.1	957.8	958.1	958.5	958.8	959.1	960.2
172.5°	965.2	964.3	963.4	962.4	961.5	961.2	961.5	961.8	962.1	962.4	963.5
175°	969.6	968.5	967.4	966.3	965.2	964.8	965.1	965.5	965.8	966.1	967.2
177.5°	970.3	969.4	968.5	967.7	966.8	966.4	966.5	966.7	966.8	966.9	967.8
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331831

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3
2.5°	1459.3	1461.7	1464.0	1465.0	1464.5	1464.0	1463.6	1463.1
5°	1447.7	1450.3	1453.0	1453.9	1453.0	1452.1	1451.2	1450.3
7.5°	1424.3	1425.0	1425.8	1425.4	1423.9	1422.4	1420.8	1419.3
10°	1400.8	1399.9	1399.0	1397.7	1395.9	1394.2	1392.4	1390.6
12.5°	1373.9	1372.3	1370.7	1368.5	1365.5	1362.6	1359.6	1356.7
15°	1323.7	1318.1	1312.5	1308.2	1305.3	1302.3	1299.4	1296.4
17.5°	1266.9	1260.2	1253.6	1247.7	1242.6	1237.6	1232.5	1227.4
20°	1227.3	1219.9	1212.5	1205.6	1199.1	1192.6	1186.1	1179.7
22.5°	1183.8	1174.3	1164.8	1157.6	1152.8	1147.9	1143.1	1138.3
25°	1111.7	1099.6	1087.5	1079.2	1074.8	1070.4	1066.0	1061.6
27.5°	1042.9	1028.8	1014.7	1004.2	997.2	990.1	983.1	976.1
30°	994.3	979.3	964.2	952.7	944.8	936.8	928.9	920.9
32.5°	945.5	928.3	911.2	898.8	891.4	883.9	876.4	868.9
35°	869.1	850.6	832.0	819.5	813.0	806.5	800.0	793.5
37.5°	794.8	774.3	753.9	739.9	732.5	725.0	717.6	710.2
40°	745.0	724.1	703.1	688.8	681.2	673.5	665.8	658.2
42.5°	694.8	673.1	651.5	636.9	629.5	622.1	614.6	607.2
45°	621.6	600.7	579.7	565.7	558.6	551.6	544.5	537.4
47.5°	550.4	529.6	508.8	495.2	488.8	482.3	475.9	469.5
50°	504.7	484.3	464.0	450.7	444.5	438.3	432.1	425.9
52.5°	461.5	441.9	422.2	409.6	403.8	398.1	392.4	386.7
55°	395.9	378.2	360.5	348.8	343.2	337.6	332.0	326.4
57.5°	336.2	320.0	303.8	293.3	288.6	283.8	279.1	274.4
60°	295.0	280.0	264.9	255.1	250.3	245.6	240.9	236.2
62.5°	259.3	245.0	230.6	222.0	219.2	216.4	213.5	210.7
65°	210.8	200.8	190.8	185.3	184.4	183.6	182.7	181.8
67.5°	170.2	165.6	161.0	158.2	157.3	156.3	155.4	154.5
70°	148.0	145.1	142.1	140.1	138.9	137.7	136.5	135.3
72.5°	128.8	126.3	123.8	122.3	121.5	120.8	120.1	119.4
75°	102.0	100.0	97.9	96.7	96.4	96.1	95.8	95.5
77.5°	77.3	76.1	74.9	74.1	73.6	73.1	72.7	72.2
80°	61.3	60.2	59.0	58.4	58.4	58.4	58.4	58.4
82.5°	46.4	45.6	44.9	44.6	44.6	44.6	44.6	44.6
85°	25.2	25.2	25.2	25.2	25.2	25.2	25.2	25.2
87.5°	11.1	11.1	11.0	11.0	11.0	11.1	11.1	11.2
90°	15.6	16.3	17.1	17.7	18.0	18.3	18.6	18.9
92.5°	17.1	17.5	17.9	18.2	18.3	18.5	18.7	18.9
95°	28.9	29.6	30.4	30.7	30.6	30.4	30.3	30.1
97.5°	37.8	38.4	39.0	39.4	39.6	39.8	40.0	40.2
100°	42.4	43.6	44.9	45.7	46.0	46.3	46.6	46.9
102.5°	44.3	45.9	47.5	48.5	49.0	49.4	49.8	50.3
105°	46.1	47.8	49.5	50.7	51.3	52.0	52.6	53.2
107.5°	56.3	54.6	52.8	52.3	52.9	53.5	54.1	54.7
110°	91.4	75.8	60.3	52.8	53.4	54.1	54.7	55.3



TEST NUMBER: P331831

CATALOG NUMBER: S122RDIW-S865D710U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	195.5	138.8	82.0	53.9	54.4	54.9	55.4	55.9
115°	287.9	215.8	143.8	102.2	91.0	79.8	68.6	57.4
117.5°	443.6	426.1	408.7	381.6	344.8	308.0	271.2	234.4
120°	516.9	518.7	520.6	511.0	490.0	469.0	448.0	427.0
122.5°	548.4	549.5	550.7	549.2	545.1	541.0	537.0	532.9
125°	593.7	594.8	595.9	596.7	597.1	597.6	598.1	598.5
127.5°	635.6	637.2	638.8	639.6	639.7	639.8	639.9	640.0
130°	662.2	663.9	665.6	666.4	666.2	666.1	665.9	665.8
132.5°	688.0	689.5	690.9	691.6	691.4	691.3	691.1	691.0
135°	724.9	726.4	728.0	728.6	728.3	728.0	727.7	727.4
137.5°	759.1	760.6	762.2	762.7	762.1	761.6	761.1	760.5
140°	781.3	782.7	784.1	784.4	783.6	782.8	782.0	781.3
142.5°	801.7	803.0	804.3	804.5	803.8	803.0	802.2	801.4
145°	830.3	831.4	832.5	832.7	831.9	831.1	830.3	829.6
147.5°	855.3	856.1	856.9	857.0	856.3	855.7	855.0	854.3
150°	870.6	871.6	872.5	872.6	871.8	871.0	870.2	869.5
152.5°	884.6	885.6	886.5	886.5	885.4	884.4	883.4	882.3
155°	903.5	904.5	905.4	905.2	904.0	902.8	901.5	900.3
157.5°	919.5	920.5	921.6	921.5	920.3	919.1	917.9	916.6
160°	928.7	929.7	930.6	930.5	929.4	928.3	927.3	926.2
162.5°	937.4	938.4	939.5	939.4	938.0	936.7	935.3	934.0
165°	948.0	949.0	950.1	950.1	949.0	948.0	946.9	945.8
167.5°	956.8	957.9	958.9	958.8	957.4	956.0	954.6	953.2
170°	961.3	962.3	963.4	963.3	961.9	960.5	959.1	957.7
172.5°	964.6	965.7	966.8	966.6	965.2	963.8	962.4	961.0
175°	968.3	969.3	970.4	970.2	968.6	967.1	965.5	964.0
177.5°	968.7	969.5	970.4	970.3	969.2	968.0	966.9	965.8
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5

(END OF REPORT)