

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331481-940

Luminaire Tested: **S122DIW-S290D970U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331481-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D970U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4525.5 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331481-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331481-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	72	60	58	56	43	42	41	28	28	27	20
2	84	77	71	66	74	68	63	59	53	49	46	38	36	34	25	24	23	17
3	76	67	60	55	67	60	54	49	46	42	39	34	31	29	22	21	19	14
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	12
5	64	53	45	39	56	47	41	36	37	32	28	27	24	21	18	16	14	11
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13	9
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	15	13	11	8
8	50	38	31	26	44	34	28	23	27	22	19	20	17	14	13	11	10	7
9	46	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	20	38	29	23	18	23	18	15	17	14	12	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6801	6801	6801
5°	6827	6729	6770
10°	6787	6661	6694
15°	6703	6574	6569
20°	6584	6445	6438
25°	6465	6285	6285
30°	6315	6139	6087
35°	6173	5964	5876
40°	5994	5788	5678
45°	5818	5613	5476
50°	5627	5433	5242
55°	5427	5225	5027
60°	5205	4970	4789
65°	4967	4722	4504
70°	4664	4414	4206
75°	4242	4067	3968
80°	3766	3654	3468
85°	3075	2927	2631



TEST NUMBER: P331481-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.6	0.9
10°-20°	111.5	2.5
20°-30°	163.8	3.6
30°-40°	190.3	4.2
40°-50°	190.1	4.2
50°-60°	165.8	3.7
60°-70°	122.6	2.7
70°-80°	69.4	1.5
80°-90°	21.6	0.5
90°-100°	39.3	0.9
100°-110°	144.0	3.2
110°-120°	385.0	8.5
120°-130°	635.6	14.0
130°-140°	675.9	14.9
140°-150°	628.3	13.9
150°-160°	505.1	11.2
160°-170°	325.5	7.2
170°-180°	112.0	2.5
0°-30°	314.9	7.0
0°-40°	505.2	11.2
0°-60°	861.1	19.0
0°-90°	1074.7	23.7
90°-120°	568.4	12.6
90°-150°	2508.2	55.4
90°-180°	3451.0	76.3
0°-180°	4525.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	421	421	421	421	421	
5°	421	420	415	418	418	40
15°	401	398	393	395	393	113
25°	363	360	353	354	353	167
35°	313	309	303	300	298	195
45°	255	252	246	242	240	197
55°	193	190	186	181	179	172
65°	130	128	124	120	118	129
75°	68	67	65	63	64	73
85°	17	16	16	15	14	19
90°	1	10	17	21	23	3
95°	55	29	33	37	37	68
105°	259	270	52	61	65	277
115°	490	505	526	150	70	482
125°	693	704	720	726	728	617
135°	857	870	878	886	885	662
145°	994	994	1008	1013	1010	622
155°	1095	1088	1097	1102	1096	504
165°	1154	1149	1151	1156	1151	326
175°	1180	1175	1176	1181	1173	112
180°	1178	1178	1178	1178	1178	



TEST NUMBER: P331481-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2
2.5°	423.2	422.8	422.5	422.1	421.8	421.2	420.4	419.6	418.8	418.0	418.7
5°	421.2	420.9	420.5	420.2	419.8	419.2	418.2	417.2	416.2	415.2	415.9
7.5°	417.6	417.0	416.4	415.9	415.4	414.6	413.6	412.5	411.5	410.5	411.3
10°	414.0	413.4	412.8	412.1	411.4	410.6	409.6	408.5	407.4	406.3	407.0
12.5°	409.1	408.6	408.0	407.4	406.9	406.1	405.0	403.9	402.9	401.8	402.3
15°	401.0	400.5	399.9	399.4	398.9	398.1	396.8	395.7	394.5	393.3	393.7
17.5°	390.7	390.1	389.6	389.1	388.5	387.6	386.5	385.2	384.1	382.9	383.3
20°	383.2	382.6	382.1	381.6	381.0	380.1	378.9	377.6	376.4	375.1	375.4
22.5°	375.8	375.0	374.3	373.4	372.7	371.8	370.6	369.3	368.2	367.0	367.0
25°	362.9	362.2	361.5	360.8	360.1	358.9	357.4	355.9	354.4	352.8	353.0
27.5°	348.4	347.8	347.1	346.4	345.8	344.8	343.7	342.4	341.3	340.0	339.7
30°	338.7	338.0	337.2	336.5	335.7	334.7	333.4	332.1	330.6	329.3	329.0
32.5°	328.2	327.7	327.2	326.5	326.0	324.9	323.5	322.2	320.7	319.3	318.8
35°	313.2	312.2	311.3	310.4	309.5	308.4	306.9	305.5	304.1	302.6	302.0
37.5°	296.0	295.2	294.4	293.6	292.8	291.8	290.3	288.9	287.4	286.0	285.3
40°	284.4	283.7	282.9	282.2	281.5	280.4	278.9	277.5	276.1	274.6	273.8
42.5°	273.0	272.3	271.6	270.9	270.2	269.0	267.6	266.2	264.7	263.3	262.4
45°	254.8	254.1	253.5	252.9	252.3	251.3	249.9	248.6	247.3	245.8	244.9
47.5°	236.7	236.0	235.5	234.9	234.3	233.3	231.8	230.5	229.1	227.7	226.6
50°	224.0	223.6	223.1	222.7	222.2	221.3	220.1	218.8	217.6	216.3	215.1
52.5°	211.7	211.1	210.5	209.9	209.3	208.4	207.2	206.1	204.8	203.7	202.6
55°	192.8	192.3	191.7	191.2	190.6	189.8	188.8	187.7	186.6	185.6	184.4
57.5°	173.9	173.4	173.0	172.5	172.1	171.3	170.1	169.0	167.7	166.6	165.5
60°	161.2	160.9	160.5	160.2	159.8	159.0	157.7	156.5	155.2	153.9	152.9
62.5°	148.9	148.3	147.8	147.2	146.6	145.8	144.8	143.9	142.9	142.0	141.0
65°	130.0	129.5	128.9	128.4	127.9	127.2	126.3	125.4	124.5	123.6	122.7
67.5°	110.8	110.4	109.9	109.5	109.1	108.5	107.6	106.8	106.0	105.2	104.6
70°	98.8	98.4	98.1	97.7	97.4	96.8	96.0	95.2	94.3	93.5	92.9
72.5°	86.5	86.1	85.8	85.4	85.1	84.6	84.1	83.6	83.1	82.6	81.9
75°	68.0	67.9	67.7	67.5	67.3	67.1	66.6	66.1	65.6	65.2	64.6
77.5°	51.5	51.2	50.9	50.6	50.3	50.0	49.8	49.7	49.5	49.3	49.0
80°	40.5	40.4	40.3	40.2	40.1	40.0	39.9	39.7	39.5	39.3	39.1
82.5°	30.1	30.1	30.1	30.1	30.1	30.0	29.9	29.8	29.7	29.6	29.2
85°	16.6	16.5	16.4	16.3	16.2	16.1	16.1	16.0	15.9	15.8	15.5
87.5°	6.0	6.2	6.5	6.8	7.1	7.3	7.5	7.7	7.8	7.9	7.9
90°	0.9	2.9	5.0	7.1	9.2	11.0	12.5	14.0	15.5	17.0	18.0
92.5°	17.2	17.0	16.9	16.7	16.5	16.8	17.5	18.3	19.0	19.8	20.2
95°	55.4	49.1	42.9	36.6	30.4	27.9	29.2	30.6	31.9	33.3	34.2
97.5°	109.9	92.3	74.7	57.1	39.5	32.2	35.3	38.3	41.4	44.5	45.2
100°	150.8	124.8	98.9	73.0	47.1	35.7	38.9	42.1	45.4	48.6	50.1
102.5°	195.8	190.3	184.9	179.3	173.8	157.7	130.7	103.8	76.9	49.9	51.9
105°	259.0	264.7	270.4	276.1	281.8	258.8	207.1	155.3	103.7	52.0	54.0
107.5°	331.1	335.7	340.3	344.8	349.5	320.7	258.8	196.7	134.7	72.8	70.6
110°	377.5	381.5	385.4	389.4	393.3	368.0	313.3	258.6	203.8	149.1	130.2



TEST NUMBER: P331481-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	421.1	424.6	428.1	431.7	435.2	430.2	416.7	403.1	389.6	376.1	307.0
115°	489.9	493.1	496.4	499.6	502.8	506.8	511.5	516.2	521.0	525.8	438.0
117.5°	551.4	555.1	558.7	562.2	565.9	569.3	572.6	575.8	579.1	582.3	561.1
120°	596.5	599.3	602.1	604.9	607.8	610.9	614.3	617.8	621.2	624.6	626.9
122.5°	634.6	637.6	640.6	643.5	646.6	650.0	653.6	657.4	661.0	664.8	666.1
125°	692.7	695.2	697.7	700.1	702.6	705.6	709.2	712.8	716.4	720.0	721.3
127.5°	745.4	748.1	750.8	753.6	756.3	759.0	761.7	764.4	767.0	769.7	771.7
130°	778.8	781.9	784.9	787.8	790.9	793.4	795.5	797.6	799.7	801.8	803.9
132.5°	812.9	815.5	818.1	820.6	823.1	825.5	827.6	829.6	831.7	833.8	835.6
135°	857.2	860.2	863.3	866.3	869.3	871.6	873.3	875.0	876.7	878.5	880.4
137.5°	902.0	904.1	906.2	908.4	910.4	912.5	914.4	916.3	918.3	920.2	922.1
140°	931.3	932.8	934.3	935.9	937.4	939.1	941.2	943.3	945.4	947.5	949.2
142.5°	955.8	957.2	958.6	959.9	961.3	963.1	965.5	968.0	970.4	972.7	974.3
145°	994.3	994.2	994.0	993.8	993.6	995.1	998.4	1001.6	1004.8	1008.0	1009.3
147.5°	1028.0	1027.2	1026.4	1025.7	1025.0	1026.3	1029.5	1032.6	1035.8	1039.0	1040.0
150°	1049.7	1048.4	1047.0	1045.8	1044.5	1045.3	1048.3	1051.3	1054.4	1057.4	1058.5
152.5°	1068.2	1066.7	1065.1	1063.7	1062.2	1062.9	1065.8	1068.7	1071.6	1074.4	1075.6
155°	1094.9	1093.1	1091.5	1089.8	1088.1	1088.3	1090.7	1092.9	1095.2	1097.4	1098.6
157.5°	1115.9	1114.5	1112.9	1111.5	1110.1	1110.2	1111.8	1113.4	1114.9	1116.5	1117.8
160°	1128.1	1127.0	1125.9	1124.7	1123.6	1123.6	1124.7	1125.9	1127.0	1128.1	1129.3
162.5°	1139.1	1137.9	1136.8	1135.6	1134.5	1134.4	1135.4	1136.4	1137.4	1138.4	1139.6
165°	1153.7	1152.5	1151.4	1150.3	1149.1	1148.9	1149.4	1150.0	1150.6	1151.1	1152.4
167.5°	1164.6	1163.4	1162.3	1161.2	1160.0	1159.8	1160.3	1160.8	1161.4	1161.9	1163.1
170°	1170.7	1169.6	1168.5	1167.3	1166.2	1165.8	1166.2	1166.5	1167.0	1167.3	1168.7
172.5°	1174.8	1173.7	1172.5	1171.4	1170.3	1169.9	1170.3	1170.6	1171.0	1171.4	1172.8
175°	1180.1	1178.8	1177.4	1176.2	1174.8	1174.3	1174.7	1175.1	1175.5	1175.8	1177.1
177.5°	1181.0	1179.9	1178.8	1177.8	1176.7	1176.3	1176.4	1176.5	1176.7	1176.9	1177.9
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331481-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	421.2	421.2	421.2	421.2	421.2	421.2	421.2	421.2
2.5°	419.5	420.2	420.9	421.2	421.1	420.9	420.8	420.6
5°	416.7	417.4	418.1	418.4	418.2	418.0	417.9	417.7
7.5°	412.0	412.7	413.4	413.7	413.5	413.2	413.0	412.9
10°	407.8	408.5	409.2	409.4	409.1	408.8	408.6	408.3
12.5°	402.8	403.2	403.8	403.9	403.8	403.5	403.3	403.1
15°	394.0	394.4	394.8	394.8	394.3	393.9	393.4	393.0
17.5°	383.7	384.1	384.5	384.5	384.1	383.7	383.3	382.8
20°	375.7	375.9	376.2	376.1	375.8	375.4	375.1	374.7
22.5°	367.1	367.2	367.2	367.1	366.9	366.7	366.5	366.3
25°	353.2	353.4	353.6	353.6	353.4	353.2	353.0	352.8
27.5°	339.5	339.2	338.9	338.6	338.1	337.7	337.3	336.9
30°	328.8	328.5	328.2	328.0	327.6	327.3	326.9	326.5
32.5°	318.3	317.8	317.4	316.9	316.6	316.2	315.8	315.5
35°	301.5	301.0	300.4	300.0	299.5	299.1	298.6	298.1
37.5°	284.6	284.0	283.3	282.8	282.3	281.9	281.5	281.1
40°	273.0	272.2	271.4	270.8	270.5	270.1	269.7	269.4
42.5°	261.5	260.6	259.8	259.0	258.6	258.1	257.6	257.1
45°	243.9	242.9	241.9	241.2	240.9	240.5	240.1	239.8
47.5°	225.6	224.5	223.5	222.7	222.2	221.7	221.1	220.6
50°	213.8	212.5	211.2	210.4	210.0	209.6	209.1	208.7
52.5°	201.6	200.5	199.5	198.7	198.0	197.5	196.9	196.3
55°	183.3	182.3	181.2	180.5	180.0	179.5	179.1	178.6
57.5°	164.4	163.4	162.3	161.6	161.3	161.0	160.6	160.2
60°	151.9	151.0	150.0	149.4	149.1	148.8	148.6	148.3
62.5°	140.1	139.2	138.3	137.7	137.3	137.0	136.6	136.3
65°	121.9	121.1	120.3	119.7	119.2	118.8	118.3	117.9
67.5°	104.0	103.3	102.7	102.2	101.8	101.5	101.1	100.8
70°	92.3	91.7	91.0	90.6	90.2	89.8	89.4	89.1
72.5°	81.3	80.7	80.1	79.5	79.3	79.0	78.7	78.4
75°	64.1	63.6	63.0	62.9	63.0	63.2	63.4	63.6
77.5°	48.8	48.5	48.2	48.0	47.7	47.5	47.3	47.0
80°	38.8	38.5	38.3	38.0	37.8	37.6	37.5	37.3
82.5°	28.9	28.5	28.2	28.0	28.0	27.9	27.9	27.9
85°	15.2	15.0	14.7	14.5	14.4	14.4	14.3	14.2
87.5°	7.9	7.8	7.8	7.8	7.8	7.8	7.8	7.8
90°	18.9	19.9	20.9	21.5	21.8	22.2	22.6	23.0
92.5°	20.8	21.2	21.8	22.1	22.3	22.6	22.7	23.0
95°	35.1	36.1	37.0	37.4	37.2	37.0	36.8	36.6
97.5°	46.0	46.7	47.5	48.0	48.2	48.4	48.7	48.9
100°	51.6	53.1	54.7	55.6	55.9	56.4	56.7	57.1
102.5°	53.9	55.8	57.8	59.0	59.6	60.1	60.6	61.2
105°	56.2	58.2	60.3	61.7	62.5	63.2	64.0	64.7
107.5°	68.5	66.4	64.3	63.6	64.4	65.1	65.9	66.6
110°	111.2	92.3	73.4	64.3	65.0	65.8	66.5	67.3



TEST NUMBER: P331481-940

CATALOG NUMBER: S122DIW-S290D970U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	237.9	168.9	99.8	65.5	66.2	66.8	67.4	68.0
115°	350.4	262.7	175.0	124.4	110.8	97.1	83.5	69.9
117.5°	539.8	518.7	497.5	464.5	419.6	374.9	330.1	285.3
120°	629.1	631.3	633.6	622.0	596.5	570.9	545.3	519.8
122.5°	667.5	668.9	670.2	668.4	663.4	658.5	653.5	648.6
125°	722.6	724.0	725.3	726.2	726.8	727.4	727.9	728.5
127.5°	773.6	775.5	777.5	778.5	778.6	778.7	778.8	778.9
130°	805.9	808.1	810.1	811.1	810.8	810.7	810.5	810.3
132.5°	837.4	839.2	841.0	841.8	841.5	841.3	841.2	841.0
135°	882.3	884.1	886.0	886.8	886.4	886.0	885.6	885.3
137.5°	923.9	925.8	927.6	928.3	927.6	926.9	926.3	925.7
140°	950.9	952.6	954.3	954.7	953.8	952.8	951.8	950.9
142.5°	975.8	977.4	978.9	979.2	978.3	977.3	976.4	975.4
145°	1010.7	1012.0	1013.3	1013.5	1012.5	1011.6	1010.7	1009.7
147.5°	1041.0	1042.0	1042.9	1043.0	1042.2	1041.4	1040.6	1039.8
150°	1059.7	1060.8	1061.9	1062.0	1061.1	1060.2	1059.2	1058.3
152.5°	1076.7	1077.8	1079.0	1079.0	1077.7	1076.5	1075.2	1074.0
155°	1099.7	1100.8	1102.0	1101.8	1100.3	1098.8	1097.3	1095.7
157.5°	1119.1	1120.4	1121.7	1121.6	1120.1	1118.7	1117.1	1115.7
160°	1130.4	1131.5	1132.7	1132.6	1131.2	1129.9	1128.6	1127.3
162.5°	1140.9	1142.2	1143.5	1143.4	1141.7	1140.1	1138.4	1136.8
165°	1153.8	1155.1	1156.5	1156.5	1155.1	1153.8	1152.4	1151.1
167.5°	1164.5	1165.8	1167.2	1167.0	1165.3	1163.6	1161.9	1160.2
170°	1170.0	1171.3	1172.6	1172.4	1170.7	1169.0	1167.3	1165.6
172.5°	1174.0	1175.4	1176.7	1176.5	1174.8	1173.1	1171.4	1169.7
175°	1178.5	1179.8	1181.2	1180.9	1178.9	1177.1	1175.2	1173.3
177.5°	1179.0	1180.0	1181.1	1181.0	1179.6	1178.2	1176.9	1175.5
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5

(END OF REPORT)