

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331514-940

Luminaire Tested: **S122DIW-S485D1240U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331514-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D1240U940-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5748.3 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331514-940

CATALOG NUMBER: S122DIW-S485D1240U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331514-940

CATALOG NUMBER: S122DIW-S485D1240U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	37	36	35	29
2	86	79	73	68	77	72	67	63	58	54	51	45	42	40	32	31	30	25
3	79	70	63	57	71	63	57	53	51	47	43	40	37	34	29	27	26	21
4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	23	18
5	66	55	47	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16
6	61	50	42	36	55	45	38	34	37	32	28	29	25	23	22	19	18	14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	17	16	13
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13990	13990	13990	13990
5°	15686	14083	12478	14083
10°	17974	13967	10799	13967
15°	19883	13710	9541	13710
20°	19581	13435	8698	13435
25°	17655	13069	8165	13069
30°	14590	12486	7774	12486
35°	10634	11874	7496	11874
40°	8494	11152	7341	11152
45°	7421	10319	7133	10319
50°	6978	9510	6993	9510
55°	6432	8690	6804	8690
60°	5893	7818	6516	7818
65°	5368	7033	6235	7033
70°	4877	6274	5816	6274
75°	4323	5421	5153	5421
80°	3710	4491	4147	4491
85°	3335	3335	2464	3335



TEST NUMBER: P331514-940

CATALOG NUMBER: S122DIW-S485D1240U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.5	1.4
10°-20°	239.9	4.2
20°-30°	348.2	6.1
30°-40°	367.4	6.4
40°-50°	325.3	5.7
50°-60°	259.6	4.5
60°-70°	176.5	3.1
70°-80°	90.5	1.6
80°-90°	27.3	0.5
90°-100°	86.8	1.5
100°-110°	269.6	4.7
110°-120°	460.9	8.0
120°-130°	606.1	10.5
130°-140°	680.3	11.8
140°-150°	667.1	11.6
150°-160°	559.5	9.7
160°-170°	371.1	6.5
170°-180°	129.7	2.3
0°-30°	670.6	11.7
0°-40°	1038.0	18.1
0°-60°	1623.0	28.2
0°-90°	1917.2	33.4
90°-120°	817.4	14.2
90°-150°	2770.9	48.2
90°-180°	3831.0	66.6
0°-180°	5748.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	866	866	866	866	866	
5°	968	869	770	869	968	97
15°	1190	820	571	820	1190	328
25°	991	734	458	734	991	448
35°	540	602	380	602	540	351
45°	325	452	312	452	325	256
55°	228	309	242	309	228	205
65°	140	184	163	184	140	140
75°	69	87	83	87	69	74
85°	18	18	13	18	18	21
90°	39	1	39	1	39	18
95°	72	60	72	60	72	80
105°	257	249	257	249	257	270
115°	462	462	462	462	462	457
125°	675	673	675	673	675	602
135°	881	871	881	871	881	678
145°	1068	1057	1068	1057	1068	667
155°	1218	1208	1218	1208	1218	560
165°	1316	1315	1316	1315	1316	371
175°	1363	1368	1363	1368	1363	130
180°	1370	1370	1370	1370	1370	



TEST NUMBER: P331514-940

CATALOG NUMBER: S122DIW-S485D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	906.5	906.8	907.2	903.0	902.5	902.5	898.8	895.5	891.8	886.7	887.3
5°	967.8	971.4	972.8	968.8	962.8	962.1	956.4	947.1	938.4	931.5	926.5
7.5°	1040.9	1042.3	1039.1	1033.8	1029.4	1021.4	1010.8	1000.5	986.1	972.8	963.0
10°	1096.3	1098.3	1092.6	1084.9	1078.6	1069.3	1054.0	1038.3	1019.4	1001.0	986.4
12.5°	1138.4	1143.4	1136.0	1135.1	1124.2	1111.4	1093.1	1085.2	1058.5	1033.0	1017.3
15°	1189.5	1189.2	1189.9	1183.6	1175.5	1173.6	1154.2	1133.3	1095.6	1080.7	1054.6
17.5°	1174.7	1179.8	1182.1	1182.1	1181.9	1180.6	1174.4	1161.2	1142.3	1118.0	1088.1
20°	1139.6	1146.2	1147.3	1154.9	1159.2	1164.9	1167.2	1163.6	1151.9	1131.6	1105.6
22.5°	1085.2	1087.1	1090.2	1102.2	1111.5	1125.7	1133.1	1145.4	1140.9	1131.0	1109.4
25°	991.0	987.7	999.3	1005.4	1027.0	1049.6	1066.0	1084.0	1099.9	1109.6	1103.3
27.5°	878.0	873.0	890.5	906.3	923.9	948.4	973.8	1003.9	1028.9	1060.2	1070.9
30°	782.6	785.6	802.3	819.2	845.9	880.5	909.1	942.1	977.8	1012.7	1037.0
32.5°	679.8	691.3	701.8	727.8	751.3	789.9	831.9	873.1	917.6	957.3	994.9
35°	539.5	552.8	567.5	586.5	619.4	657.7	698.7	754.3	814.9	869.2	913.8
37.5°	454.1	452.0	460.4	474.1	500.8	531.7	578.8	633.8	705.2	768.9	831.9
40°	403.0	401.6	407.6	420.3	440.6	463.2	504.5	552.8	619.1	697.0	772.0
42.5°	367.7	368.5	371.9	380.8	394.8	413.4	444.3	485.4	546.1	619.5	700.0
45°	325.0	327.3	331.0	335.4	343.3	358.6	375.9	405.3	453.3	514.5	593.8
47.5°	294.3	294.4	298.0	301.8	306.6	315.2	329.4	347.8	381.6	431.5	499.6
50°	277.8	275.4	278.0	281.1	286.1	292.0	301.4	318.7	341.3	381.7	438.5
52.5°	257.5	257.5	259.9	261.1	265.6	271.5	280.1	292.0	312.5	344.1	390.9
55°	228.5	230.2	231.5	233.4	237.5	241.7	248.4	256.5	272.4	296.0	330.6
57.5°	201.2	201.7	203.0	206.8	209.4	213.3	219.6	226.9	237.3	254.9	280.9
60°	182.5	182.5	185.1	186.8	190.1	194.1	199.1	206.2	215.4	229.8	250.7
62.5°	165.4	165.1	166.2	169.0	171.5	175.2	180.2	186.2	194.9	207.7	224.9
65°	140.5	139.9	141.9	142.5	145.2	148.8	152.8	159.2	166.2	175.5	190.8
67.5°	116.5	117.3	118.4	119.7	121.2	125.0	127.7	132.2	138.0	145.8	156.2
70°	103.3	103.3	103.3	104.2	106.2	108.3	110.9	114.6	120.2	126.9	136.2
72.5°	88.3	89.3	90.4	89.9	92.4	93.5	96.8	98.8	104.2	108.5	116.7
75°	69.3	69.3	69.3	70.9	72.0	72.9	74.9	77.0	79.6	84.9	89.3
77.5°	51.7	51.5	51.9	52.3	53.3	54.6	55.1	57.0	59.4	61.9	65.5
80°	39.9	40.7	40.9	41.6	41.6	42.3	42.6	44.9	46.6	48.3	50.6
82.5°	30.9	31.0	31.1	31.2	31.5	31.9	32.7	33.5	34.1	35.5	37.3
85°	18.0	17.7	17.7	18.3	18.0	18.0	18.6	19.4	19.4	19.6	20.7
87.5°	14.8	14.7	15.0	14.6	14.6	14.9	15.0	14.8	15.2	15.5	14.7
90°	39.3	39.1	38.8	38.5	38.3	38.4	39.0	39.4	39.9	40.5	34.8
92.5°	37.5	37.5	37.4	37.3	37.3	37.2	37.1	37.0	36.8	36.7	35.4
95°	71.7	72.2	72.7	73.2	73.7	74.0	74.0	74.0	74.0	74.0	73.5
97.5°	124.2	124.2	124.3	124.3	124.4	124.4	124.4	124.4	124.4	124.4	123.4
100°	158.4	158.6	158.9	159.2	159.4	159.5	159.5	159.5	159.5	159.5	158.8
102.5°	197.2	197.5	197.8	198.0	198.3	198.3	198.1	197.9	197.7	197.5	196.5
105°	256.7	256.7	256.7	256.7	256.7	256.5	255.9	255.4	254.9	254.4	253.9
107.5°	312.6	313.8	315.0	316.2	317.4	317.9	317.6	317.4	317.3	317.0	317.0
110°	356.1	356.9	357.7	358.5	359.2	359.6	359.6	359.6	359.6	359.6	359.6



TEST NUMBER: P331514-940

CATALOG NUMBER: S122DIW-S485D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	397.7	398.3	398.9	399.4	400.0	400.6	401.2	401.8	402.4	403.1	403.2
115°	462.5	463.2	464.0	464.8	465.6	466.1	466.4	466.6	466.9	467.1	467.6
117.5°	524.2	525.0	525.8	526.6	527.4	528.0	528.6	529.2	529.9	530.5	531.9
120°	567.8	568.5	569.3	570.0	570.8	571.1	571.1	571.1	571.1	571.1	573.2
122.5°	610.3	610.8	611.4	612.0	612.5	613.1	613.8	614.4	614.9	615.5	617.0
125°	675.2	675.5	675.7	676.0	676.3	676.8	677.5	678.3	679.1	679.8	680.6
127.5°	734.4	735.3	736.1	736.9	737.7	738.6	739.5	740.5	741.4	742.3	743.2
130°	776.9	778.0	779.1	780.1	781.1	781.9	782.4	782.9	783.4	783.9	784.4
132.5°	817.7	818.5	819.3	820.2	821.0	822.0	823.0	824.2	825.4	826.4	826.3
135°	881.0	881.8	882.6	883.3	884.1	884.7	884.9	885.2	885.4	885.6	885.2
137.5°	938.4	939.4	940.5	941.5	942.5	943.2	943.3	943.5	943.8	944.0	943.3
140°	978.2	979.2	980.3	981.2	982.3	982.8	982.8	982.8	982.8	982.8	981.5
142.5°	1014.2	1015.3	1016.3	1017.4	1018.3	1018.8	1018.6	1018.3	1018.2	1018.0	1017.1
145°	1068.4	1069.4	1070.4	1071.5	1072.5	1072.8	1072.6	1072.4	1072.1	1071.8	1070.3
147.5°	1116.7	1117.7	1118.7	1119.6	1120.6	1120.8	1120.3	1119.6	1119.1	1118.6	1117.5
150°	1148.2	1148.9	1149.7	1150.5	1151.2	1151.2	1150.5	1149.7	1148.9	1148.2	1147.1
152.5°	1177.8	1178.8	1179.7	1180.6	1181.6	1181.6	1180.6	1179.7	1178.8	1177.8	1176.5
155°	1217.5	1218.3	1219.1	1219.9	1220.6	1220.3	1219.1	1217.8	1216.5	1215.2	1214.4
157.5°	1251.7	1252.9	1254.2	1255.4	1256.7	1256.4	1254.6	1252.9	1251.2	1249.5	1248.9
160°	1273.0	1274.1	1275.1	1276.1	1277.1	1276.8	1275.3	1273.8	1272.2	1270.7	1270.4
162.5°	1291.6	1292.7	1294.0	1295.2	1296.5	1296.2	1294.4	1292.7	1290.9	1289.2	1289.0
165°	1315.8	1317.1	1318.4	1319.6	1320.9	1320.7	1318.8	1317.1	1315.3	1313.5	1313.5
167.5°	1335.7	1337.0	1338.4	1339.7	1341.0	1340.8	1339.0	1337.2	1335.4	1333.6	1333.6
170°	1345.9	1347.4	1349.0	1350.5	1352.0	1351.9	1350.1	1348.3	1346.5	1344.7	1345.0
172.5°	1354.2	1355.8	1357.3	1358.8	1360.3	1360.2	1358.4	1356.6	1354.9	1353.0	1353.3
175°	1363.2	1364.8	1366.3	1367.8	1369.4	1369.2	1367.4	1365.7	1363.9	1362.0	1362.5
177.5°	1367.3	1368.6	1369.8	1371.1	1372.3	1372.3	1371.1	1369.8	1368.6	1367.3	1367.8
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331514-940

CATALOG NUMBER: S122DIW-S485D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	889.1	887.0	885.6	880.9	876.6	872.4	871.0	871.6	865.7	860.1	857.7
5°	923.8	917.1	910.8	901.8	891.2	879.5	873.5	868.9	857.2	844.5	837.2
7.5°	954.8	945.3	933.1	916.2	900.7	882.3	870.7	860.4	843.3	825.5	814.6
10°	973.7	960.7	945.1	924.4	905.4	883.2	867.5	851.9	831.9	810.6	797.3
12.5°	990.0	972.5	957.1	930.6	908.1	880.2	861.7	839.6	818.6	793.3	780.2
15°	1028.7	996.4	967.1	937.1	909.5	870.5	849.9	820.2	792.6	761.3	746.3
17.5°	1058.5	1022.3	976.2	938.1	905.8	862.6	832.3	796.8	764.1	728.3	708.0
20°	1075.7	1034.0	984.4	939.1	900.4	851.2	818.2	781.9	743.6	703.3	681.4
22.5°	1085.7	1042.1	992.9	935.1	889.8	841.9	800.4	760.6	721.8	678.3	655.2
25°	1089.0	1049.0	997.0	931.7	876.5	822.2	772.2	733.6	686.7	646.0	612.4
27.5°	1073.1	1044.5	994.5	925.5	861.1	797.6	742.0	698.2	648.6	604.6	570.7
30°	1053.6	1037.0	988.4	919.1	848.8	780.6	719.3	669.7	620.5	575.8	541.2
32.5°	1023.6	1019.9	977.2	910.1	835.8	759.0	695.6	645.4	590.8	547.0	514.0
35°	964.4	980.4	953.4	889.8	811.2	728.3	659.7	602.4	545.8	503.8	472.9
37.5°	885.2	924.9	917.8	860.1	778.0	694.9	619.1	559.3	505.3	463.0	432.6
40°	830.5	881.2	888.5	837.5	754.7	669.1	588.8	529.1	476.5	437.9	407.2
42.5°	772.0	831.1	851.2	810.4	729.1	641.9	561.6	499.9	447.8	410.2	383.1
45°	673.7	752.0	788.3	764.9	686.3	597.1	514.5	451.9	404.7	369.3	348.3
47.5°	581.8	667.4	716.2	707.9	638.8	550.5	468.9	408.8	362.7	334.6	315.8
50°	516.8	604.8	663.7	666.4	604.8	517.2	435.2	378.6	336.4	310.0	294.7
52.5°	460.4	544.3	608.6	622.7	566.7	482.5	405.1	348.8	311.6	287.4	273.7
55°	386.6	457.5	528.9	554.8	509.9	429.9	358.3	308.7	273.8	257.1	245.1
57.5°	321.5	380.6	446.4	475.1	447.4	379.0	311.8	268.8	240.4	225.8	216.6
60°	287.0	333.7	392.3	426.6	402.6	341.7	283.0	242.1	218.8	205.8	197.2
62.5°	255.1	296.4	345.9	377.3	364.3	306.7	254.3	218.1	198.0	185.8	179.6
65°	210.4	243.1	281.4	310.4	301.8	258.1	215.2	184.1	168.2	158.5	153.6
67.5°	173.3	196.9	223.5	248.8	241.8	210.9	176.5	152.3	140.4	132.1	129.1
70°	149.9	167.8	191.5	211.8	206.2	180.8	153.6	132.9	122.5	115.6	112.5
72.5°	127.5	142.2	160.3	176.9	173.1	152.0	129.3	113.7	105.8	99.3	96.8
75°	96.2	107.5	118.6	129.6	128.6	112.3	98.9	86.9	80.6	75.6	74.6
77.5°	71.1	77.4	84.9	91.4	89.6	80.3	69.8	63.0	58.3	54.9	54.4
80°	54.3	58.0	63.3	67.9	65.6	61.6	53.3	48.3	44.9	41.6	40.3
82.5°	39.3	43.1	46.2	48.8	47.0	43.2	38.1	34.7	32.7	30.4	29.9
85°	20.7	22.6	24.0	24.6	24.0	21.7	19.4	18.0	16.3	15.3	15.0
87.5°	13.8	12.7	11.6	11.2	9.8	9.2	7.5	6.1	6.4	6.8	6.9
90°	29.2	23.5	17.8	13.5	10.4	7.3	4.3	1.2	4.3	7.3	10.4
92.5°	34.1	32.7	31.4	29.6	27.4	25.1	22.8	20.6	22.8	25.1	27.4
95°	72.9	72.5	72.0	70.4	67.9	65.3	62.7	60.1	62.7	65.3	67.9
97.5°	122.4	121.5	120.5	118.9	116.6	114.4	112.1	109.9	112.1	114.4	116.6
100°	158.0	157.2	156.5	155.1	153.0	151.0	148.9	146.9	148.9	151.0	153.0
102.5°	195.6	194.6	193.6	192.3	190.6	189.0	187.3	185.7	187.3	189.0	190.6
105°	253.3	252.8	252.4	251.6	250.9	250.1	249.3	248.6	249.3	250.1	250.9
107.5°	317.0	317.0	317.0	316.5	315.3	314.2	313.1	311.9	313.1	314.2	315.3
110°	359.6	359.6	359.6	358.8	357.3	355.7	354.2	352.7	354.2	355.7	357.3



TEST NUMBER: P331514-940

CATALOG NUMBER: S122DIW-S485D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	403.5	403.7	403.9	403.2	401.7	400.1	398.6	397.1	398.6	400.1	401.7
115°	468.1	468.7	469.1	468.7	467.1	465.6	464.0	462.5	464.0	465.6	467.1
117.5°	533.3	534.8	536.3	535.9	533.9	531.8	529.8	527.7	529.8	531.8	533.9
120°	575.3	577.4	579.4	579.4	577.4	575.3	573.2	571.1	573.2	575.3	577.4
122.5°	618.5	619.9	621.3	620.8	618.3	615.9	613.4	610.9	613.4	615.9	618.3
125°	681.4	682.2	683.0	682.2	679.8	677.5	675.2	672.9	675.2	677.5	679.8
127.5°	744.1	745.1	746.0	745.0	742.1	739.1	736.2	733.3	736.2	739.1	742.1
130°	785.0	785.5	786.0	784.5	781.2	777.9	774.5	771.2	774.5	777.9	781.2
132.5°	826.3	826.2	826.1	824.7	821.9	819.2	816.5	813.8	816.5	819.2	821.9
135°	884.7	884.1	883.6	882.0	879.1	876.3	873.4	870.7	873.4	876.3	879.1
137.5°	942.6	941.9	941.3	939.8	937.5	935.1	932.8	930.5	932.8	935.1	937.5
140°	980.3	978.9	977.7	975.9	973.6	971.3	968.9	966.6	968.9	971.3	973.6
142.5°	1016.2	1015.3	1014.4	1012.9	1010.6	1008.3	1005.9	1003.6	1005.9	1008.3	1010.6
145°	1068.7	1067.2	1065.7	1064.0	1062.2	1060.4	1058.6	1056.8	1058.6	1060.4	1062.2
147.5°	1116.5	1115.4	1114.5	1112.9	1110.7	1108.5	1106.3	1104.2	1106.3	1108.5	1110.7
150°	1146.1	1145.0	1144.1	1142.7	1141.2	1139.7	1138.1	1136.6	1138.1	1139.7	1141.2
152.5°	1175.3	1174.0	1172.8	1171.4	1169.8	1168.3	1166.8	1165.3	1166.8	1168.3	1169.8
155°	1213.6	1212.9	1212.1	1211.4	1210.6	1209.8	1209.1	1208.3	1209.1	1209.8	1210.6
157.5°	1248.5	1248.0	1247.6	1247.1	1246.6	1246.1	1245.5	1245.0	1245.5	1246.1	1246.6
160°	1270.2	1269.9	1269.7	1269.3	1268.8	1268.3	1267.7	1267.2	1267.7	1268.3	1268.8
162.5°	1288.7	1288.4	1288.2	1288.0	1287.9	1287.8	1287.7	1287.5	1287.7	1287.8	1287.9
165°	1313.5	1313.5	1313.5	1313.6	1313.8	1314.1	1314.4	1314.6	1314.4	1314.1	1313.8
167.5°	1333.7	1333.7	1333.8	1334.2	1335.0	1335.8	1336.5	1337.3	1336.5	1335.8	1335.0
170°	1345.2	1345.5	1345.8	1346.2	1347.0	1347.8	1348.5	1349.3	1348.5	1347.8	1347.0
172.5°	1353.5	1353.8	1354.1	1354.6	1355.3	1356.1	1356.9	1357.6	1356.9	1356.1	1355.3
175°	1363.1	1363.6	1364.1	1364.8	1365.5	1366.3	1367.1	1367.8	1367.1	1366.3	1365.5
177.5°	1368.2	1368.6	1369.0	1369.5	1370.1	1370.7	1371.4	1372.0	1371.4	1370.7	1370.1
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331514-940

CATALOG NUMBER: S122DIW-S485D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	855.1	853.5	847.8	844.9	840.2	835.6	832.7	834.0	835.1	834.6	833.7
5°	830.5	824.2	814.6	806.2	800.2	789.3	784.6	782.3	780.2	777.9	775.6
7.5°	801.4	791.4	777.6	765.7	754.5	740.8	733.1	728.3	723.5	718.3	713.6
10°	780.6	766.6	752.0	735.3	722.0	709.6	698.7	691.3	684.7	678.3	673.7
12.5°	758.8	742.6	724.5	701.8	687.1	669.4	667.8	654.9	644.4	640.5	635.1
15°	724.0	701.3	678.3	651.4	639.7	623.8	613.8	603.8	594.8	588.4	586.7
17.5°	684.5	655.1	632.3	613.0	593.9	577.5	568.3	560.3	552.9	544.4	543.3
20°	654.3	629.1	604.1	587.1	567.5	550.8	539.5	531.5	525.1	520.1	515.9
22.5°	625.9	598.2	575.3	556.7	537.3	523.9	515.0	507.3	502.0	496.5	492.4
25°	580.1	558.5	533.5	512.6	496.5	487.9	480.5	473.9	470.6	466.9	462.3
27.5°	540.1	516.0	492.7	476.4	462.4	454.7	449.5	445.0	441.8	439.7	437.0
30°	511.8	487.5	469.2	453.3	441.6	433.9	430.6	427.9	424.3	422.9	421.6
32.5°	484.6	462.8	447.1	433.3	422.1	417.1	414.1	411.7	408.8	407.5	404.8
35°	446.2	427.9	412.6	404.9	395.9	391.6	389.3	385.9	383.3	382.0	381.7
37.5°	410.1	394.1	384.1	374.3	370.4	367.7	364.6	362.3	361.5	361.3	361.0
40°	386.6	373.6	364.6	356.7	355.0	351.0	348.3	346.3	346.3	346.7	346.3
42.5°	365.3	353.7	345.7	338.9	336.9	334.5	331.8	331.7	332.3	333.3	332.3
45°	333.1	324.7	319.1	315.7	312.0	309.7	309.3	310.4	310.7	311.0	312.0
47.5°	303.3	297.7	292.7	289.0	287.4	287.0	286.6	288.3	289.9	290.5	292.0
50°	285.7	279.4	275.1	272.8	271.4	270.7	271.4	273.4	274.7	276.4	277.4
52.5°	266.0	261.5	258.6	256.7	256.2	256.6	256.7	259.0	261.2	261.7	262.3
55°	238.8	235.4	234.8	231.8	233.1	232.7	234.4	235.8	237.7	239.8	240.1
57.5°	211.6	208.9	207.1	207.4	207.8	209.3	210.6	213.0	215.2	217.2	217.5
60°	193.5	192.2	191.2	191.2	191.8	193.9	195.5	197.8	199.1	200.5	201.4
62.5°	177.0	175.7	174.6	175.1	176.9	178.1	180.0	181.3	182.6	184.0	184.4
65°	150.9	150.2	151.2	151.9	152.2	153.8	156.2	157.2	158.5	159.2	161.5
67.5°	126.8	127.0	126.8	127.8	129.7	130.1	132.2	134.6	134.9	136.2	137.7
70°	110.6	111.2	111.9	112.5	114.2	114.9	116.5	117.5	118.9	119.8	120.9
72.5°	95.7	95.8	96.5	96.3	97.7	99.2	100.6	101.6	102.9	104.2	105.1
75°	73.6	73.6	74.3	74.6	76.2	77.9	77.6	78.3	79.6	81.0	81.6
77.5°	53.8	53.1	53.8	54.0	54.6	56.0	56.3	57.2	58.8	58.3	59.0
80°	40.9	39.9	40.9	41.3	41.3	43.0	43.0	43.6	44.6	43.6	44.6
82.5°	29.2	28.8	29.5	29.6	30.1	30.1	30.7	30.9	31.8	31.4	31.8
85°	14.6	14.4	14.6	14.4	14.6	15.0	15.0	14.6	14.6	15.3	14.4
87.5°	7.2	7.8	8.7	9.8	10.7	11.6	11.1	11.1	11.0	10.3	10.3
90°	13.5	17.8	23.5	29.2	34.8	40.5	39.9	39.4	39.0	38.4	38.3
92.5°	29.6	31.4	32.7	34.1	35.4	36.7	36.8	37.0	37.1	37.2	37.3
95°	70.4	72.0	72.5	72.9	73.5	74.0	74.0	74.0	74.0	74.0	73.7
97.5°	118.9	120.5	121.5	122.4	123.4	124.4	124.4	124.4	124.4	124.4	124.4
100°	155.1	156.5	157.2	158.0	158.8	159.5	159.5	159.5	159.5	159.5	159.4
102.5°	192.3	193.6	194.6	195.6	196.5	197.5	197.7	197.9	198.1	198.3	198.3
105°	251.6	252.4	252.8	253.3	253.9	254.4	254.9	255.4	255.9	256.5	256.7
107.5°	316.5	317.0	317.0	317.0	317.0	317.0	317.3	317.4	317.6	317.9	317.4
110°	358.8	359.6	359.6	359.6	359.6	359.6	359.6	359.6	359.6	359.6	359.2



TEST NUMBER: P331514-940

CATALOG NUMBER: S122DIW-S485D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	403.2	403.9	403.7	403.5	403.2	403.1	402.4	401.8	401.2	400.6	400.0
115°	468.7	469.1	468.7	468.1	467.6	467.1	466.9	466.6	466.4	466.1	465.6
117.5°	535.9	536.3	534.8	533.3	531.9	530.5	529.9	529.2	528.6	528.0	527.4
120°	579.4	579.4	577.4	575.3	573.2	571.1	571.1	571.1	571.1	571.1	570.8
122.5°	620.8	621.3	619.9	618.5	617.0	615.5	614.9	614.4	613.8	613.1	612.5
125°	682.2	683.0	682.2	681.4	680.6	679.8	679.1	678.3	677.5	676.8	676.3
127.5°	745.0	746.0	745.1	744.1	743.2	742.3	741.4	740.5	739.5	738.6	737.7
130°	784.5	786.0	785.5	785.0	784.4	783.9	783.4	782.9	782.4	781.9	781.1
132.5°	824.7	826.1	826.2	826.3	826.3	826.4	825.4	824.2	823.0	822.0	821.0
135°	882.0	883.6	884.1	884.7	885.2	885.6	885.4	885.2	884.9	884.7	884.1
137.5°	939.8	941.3	941.9	942.6	943.3	944.0	943.8	943.5	943.3	943.2	942.5
140°	975.9	977.7	978.9	980.3	981.5	982.8	982.8	982.8	982.8	982.8	982.3
142.5°	1012.9	1014.4	1015.3	1016.2	1017.1	1018.0	1018.2	1018.3	1018.6	1018.8	1018.3
145°	1064.0	1065.7	1067.2	1068.7	1070.3	1071.8	1072.1	1072.4	1072.6	1072.8	1072.5
147.5°	1112.9	1114.5	1115.4	1116.5	1117.5	1118.6	1119.1	1119.6	1120.3	1120.8	1120.6
150°	1142.7	1144.1	1145.0	1146.1	1147.1	1148.2	1148.9	1149.7	1150.5	1151.2	1151.2
152.5°	1171.4	1172.8	1174.0	1175.3	1176.5	1177.8	1178.8	1179.7	1180.6	1181.6	1181.6
155°	1211.4	1212.1	1212.9	1213.6	1214.4	1215.2	1216.5	1217.8	1219.1	1220.3	1220.6
157.5°	1247.1	1247.6	1248.0	1248.5	1248.9	1249.5	1251.2	1252.9	1254.6	1256.4	1256.7
160°	1269.3	1269.7	1269.9	1270.2	1270.4	1270.7	1272.2	1273.8	1275.3	1276.8	1277.1
162.5°	1288.0	1288.2	1288.4	1288.7	1289.0	1289.2	1290.9	1292.7	1294.4	1296.2	1296.5
165°	1313.6	1313.5	1313.5	1313.5	1313.5	1313.5	1315.3	1317.1	1318.8	1320.7	1320.9
167.5°	1334.2	1333.8	1333.7	1333.7	1333.6	1333.6	1335.4	1337.2	1339.0	1340.8	1341.0
170°	1346.2	1345.8	1345.5	1345.2	1345.0	1344.7	1346.5	1348.3	1350.1	1351.9	1352.0
172.5°	1354.6	1354.1	1353.8	1353.5	1353.3	1353.0	1354.9	1356.6	1358.4	1360.2	1360.3
175°	1364.8	1364.1	1363.6	1363.1	1362.5	1362.0	1363.9	1365.7	1367.4	1369.2	1369.4
177.5°	1369.5	1369.0	1368.6	1368.2	1367.8	1367.3	1368.6	1369.8	1371.1	1372.3	1372.3
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331514-940

CATALOG NUMBER: S122DIW-S485D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	831.1	830.5	830.5	828.1	830.5	830.5	831.1	833.7	834.6	835.1	834.0
5°	771.0	769.9	768.3	769.9	768.3	769.9	771.0	775.6	777.9	780.2	782.3
7.5°	711.5	707.5	706.9	702.9	706.9	707.5	711.5	713.6	718.3	723.5	728.3
10°	668.1	665.4	665.0	658.7	665.0	665.4	668.1	673.7	678.3	684.7	691.3
12.5°	635.0	628.6	629.9	626.2	629.9	628.6	635.0	635.1	640.5	644.4	654.9
15°	577.7	577.7	576.5	570.8	576.5	577.7	577.7	586.7	588.4	594.8	603.8
17.5°	536.7	536.0	532.8	534.4	532.8	536.0	536.7	543.3	544.4	552.9	560.3
20°	512.2	510.1	506.2	506.2	506.2	510.1	512.2	515.9	520.1	525.1	531.5
22.5°	489.0	488.8	484.6	486.0	484.6	488.8	489.0	492.4	496.5	502.0	507.3
25°	461.9	459.2	457.3	458.3	457.3	459.2	461.9	462.3	466.9	470.6	473.9
27.5°	436.2	434.7	434.6	431.9	434.6	434.7	436.2	437.0	439.7	441.8	445.0
30°	421.2	417.9	418.6	417.0	418.6	417.9	421.2	421.6	422.9	424.3	427.9
32.5°	404.2	403.1	402.3	400.9	402.3	403.1	404.2	404.8	407.5	408.8	411.7
35°	380.9	381.3	379.6	380.3	379.6	381.3	380.9	381.7	382.0	383.3	385.9
37.5°	360.7	361.8	361.0	361.1	361.0	361.8	360.7	361.0	361.3	361.5	362.3
40°	347.3	347.3	347.3	348.3	347.3	347.3	347.3	346.3	346.7	346.3	346.3
42.5°	334.6	334.0	333.5	333.4	333.5	334.0	334.6	332.3	333.3	332.3	331.7
45°	312.7	313.7	314.1	312.4	314.1	313.7	312.7	312.0	311.0	310.7	310.4
47.5°	292.9	293.0	292.9	294.4	292.9	293.0	292.9	292.0	290.5	289.9	288.3
50°	279.1	278.4	279.1	278.4	279.1	278.4	279.1	277.4	276.4	274.7	273.4
52.5°	264.4	264.6	264.1	264.0	264.1	264.6	264.4	262.3	261.7	261.2	259.0
55°	241.5	242.1	241.7	241.7	241.7	242.1	241.5	240.1	239.8	237.7	235.8
57.5°	217.7	218.3	218.7	217.2	218.7	218.3	217.7	217.5	217.2	215.2	213.0
60°	201.2	202.8	202.5	201.8	202.5	202.8	201.2	201.4	200.5	199.1	197.8
62.5°	185.9	186.5	186.5	186.4	186.5	186.5	185.9	184.4	184.0	182.6	181.3
65°	162.5	163.2	162.2	163.2	162.2	163.2	162.5	161.5	159.2	158.5	157.2
67.5°	137.2	137.5	138.2	138.7	138.2	137.5	137.2	137.7	136.2	134.9	134.6
70°	121.5	121.2	122.3	123.2	122.3	121.2	121.5	120.9	119.8	118.9	117.5
72.5°	105.0	105.8	105.4	106.2	105.4	105.8	105.0	105.1	104.2	102.9	101.6
75°	81.0	81.9	81.6	82.6	81.6	81.9	81.0	81.6	81.0	79.6	78.3
77.5°	58.5	58.6	58.5	59.0	58.5	58.6	58.5	59.0	58.3	58.8	57.2
80°	44.6	44.0	43.2	44.6	43.2	44.0	44.6	44.6	43.6	44.6	43.6
82.5°	31.0	31.5	30.8	30.8	30.8	31.5	31.0	31.8	31.4	31.8	30.9
85°	14.4	14.0	13.3	13.3	13.3	14.0	14.4	14.4	15.3	14.6	14.6
87.5°	10.3	10.2	10.2	10.0	10.2	10.2	10.3	10.3	10.3	11.0	11.1
90°	38.5	38.8	39.1	39.3	39.1	38.8	38.5	38.3	38.4	39.0	39.4
92.5°	37.3	37.4	37.5	37.5	37.5	37.4	37.3	37.3	37.2	37.1	37.0
95°	73.2	72.7	72.2	71.7	72.2	72.7	73.2	73.7	74.0	74.0	74.0
97.5°	124.3	124.3	124.2	124.2	124.2	124.3	124.3	124.4	124.4	124.4	124.4
100°	159.2	158.9	158.6	158.4	158.6	158.9	159.2	159.4	159.5	159.5	159.5
102.5°	198.0	197.8	197.5	197.2	197.5	197.8	198.0	198.3	198.3	198.1	197.9
105°	256.7	256.7	256.7	256.7	256.7	256.7	256.7	256.7	256.5	255.9	255.4
107.5°	316.2	315.0	313.8	312.6	313.8	315.0	316.2	317.4	317.9	317.6	317.4
110°	358.5	357.7	356.9	356.1	356.9	357.7	358.5	359.2	359.6	359.6	359.6



TEST NUMBER: P331514-940

CATALOG NUMBER: S122DIW-S485D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	399.4	398.9	398.3	397.7	398.3	398.9	399.4	400.0	400.6	401.2	401.8
115°	464.8	464.0	463.2	462.5	463.2	464.0	464.8	465.6	466.1	466.4	466.6
117.5°	526.6	525.8	525.0	524.2	525.0	525.8	526.6	527.4	528.0	528.6	529.2
120°	570.0	569.3	568.5	567.8	568.5	569.3	570.0	570.8	571.1	571.1	571.1
122.5°	612.0	611.4	610.8	610.3	610.8	611.4	612.0	612.5	613.1	613.8	614.4
125°	676.0	675.7	675.5	675.2	675.5	675.7	676.0	676.3	676.8	677.5	678.3
127.5°	736.9	736.1	735.3	734.4	735.3	736.1	736.9	737.7	738.6	739.5	740.5
130°	780.1	779.1	778.0	776.9	778.0	779.1	780.1	781.1	781.9	782.4	782.9
132.5°	820.2	819.3	818.5	817.7	818.5	819.3	820.2	821.0	822.0	823.0	824.2
135°	883.3	882.6	881.8	881.0	881.8	882.6	883.3	884.1	884.7	884.9	885.2
137.5°	941.5	940.5	939.4	938.4	939.4	940.5	941.5	942.5	943.2	943.3	943.5
140°	981.2	980.3	979.2	978.2	979.2	980.3	981.2	982.3	982.8	982.8	982.8
142.5°	1017.4	1016.3	1015.3	1014.2	1015.3	1016.3	1017.4	1018.3	1018.8	1018.6	1018.3
145°	1071.5	1070.4	1069.4	1068.4	1069.4	1070.4	1071.5	1072.5	1072.8	1072.6	1072.4
147.5°	1119.6	1118.7	1117.7	1116.7	1117.7	1118.7	1119.6	1120.6	1120.8	1120.3	1119.6
150°	1150.5	1149.7	1148.9	1148.2	1148.9	1149.7	1150.5	1151.2	1151.2	1150.5	1149.7
152.5°	1180.6	1179.7	1178.8	1177.8	1178.8	1179.7	1180.6	1181.6	1181.6	1180.6	1179.7
155°	1219.9	1219.1	1218.3	1217.5	1218.3	1219.1	1219.9	1220.6	1220.3	1219.1	1217.8
157.5°	1255.4	1254.2	1252.9	1251.7	1252.9	1254.2	1255.4	1256.7	1256.4	1254.6	1252.9
160°	1276.1	1275.1	1274.1	1273.0	1274.1	1275.1	1276.1	1277.1	1276.8	1275.3	1273.8
162.5°	1295.2	1294.0	1292.7	1291.6	1292.7	1294.0	1295.2	1296.5	1296.2	1294.4	1292.7
165°	1319.6	1318.4	1317.1	1315.8	1317.1	1318.4	1319.6	1320.9	1320.7	1318.8	1317.1
167.5°	1339.7	1338.4	1337.0	1335.7	1337.0	1338.4	1339.7	1341.0	1340.8	1339.0	1337.2
170°	1350.5	1349.0	1347.4	1345.9	1347.4	1349.0	1350.5	1352.0	1351.9	1350.1	1348.3
172.5°	1358.8	1357.3	1355.8	1354.2	1355.8	1357.3	1358.8	1360.3	1360.2	1358.4	1356.6
175°	1367.8	1366.3	1364.8	1363.2	1364.8	1366.3	1367.8	1369.4	1369.2	1367.4	1365.7
177.5°	1371.1	1369.8	1368.6	1367.3	1368.6	1369.8	1371.1	1372.3	1372.3	1371.1	1369.8
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331514-940

CATALOG NUMBER: S122DIW-S485D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	832.7	835.6	840.2	844.9	847.8	853.5	855.1	857.7	860.1	865.7	871.6
5°	784.6	789.3	800.2	806.2	814.6	824.2	830.5	837.2	844.5	857.2	868.9
7.5°	733.1	740.8	754.5	765.7	777.6	791.4	801.4	814.6	825.5	843.3	860.4
10°	698.7	709.6	722.0	735.3	752.0	766.6	780.6	797.3	810.6	831.9	851.9
12.5°	667.8	669.4	687.1	701.8	724.5	742.6	758.8	780.2	793.3	818.6	839.6
15°	613.8	623.8	639.7	651.4	678.3	701.3	724.0	746.3	761.3	792.6	820.2
17.5°	568.3	577.5	593.9	613.0	632.3	655.1	684.5	708.0	728.3	764.1	796.8
20°	539.5	550.8	567.5	587.1	604.1	629.1	654.3	681.4	703.3	743.6	781.9
22.5°	515.0	523.9	537.3	556.7	575.3	598.2	625.9	655.2	678.3	721.8	760.6
25°	480.5	487.9	496.5	512.6	533.5	558.5	580.1	612.4	646.0	686.7	733.6
27.5°	449.5	454.7	462.4	476.4	492.7	516.0	540.1	570.7	604.6	648.6	698.2
30°	430.6	433.9	441.6	453.3	469.2	487.5	511.8	541.2	575.8	620.5	669.7
32.5°	414.1	417.1	422.1	433.3	447.1	462.8	484.6	514.0	547.0	590.8	645.4
35°	389.3	391.6	395.9	404.9	412.6	427.9	446.2	472.9	503.8	545.8	602.4
37.5°	364.6	367.7	370.4	374.3	384.1	394.1	410.1	432.6	463.0	505.3	559.3
40°	348.3	351.0	355.0	356.7	364.6	373.6	386.6	407.2	437.9	476.5	529.1
42.5°	331.8	334.5	336.9	338.9	345.7	353.7	365.3	383.1	410.2	447.8	499.9
45°	309.3	309.7	312.0	315.7	319.1	324.7	333.1	348.3	369.3	404.7	451.9
47.5°	286.6	287.0	287.4	289.0	292.7	297.7	303.3	315.8	334.6	362.7	408.8
50°	271.4	270.7	271.4	272.8	275.1	279.4	285.7	294.7	310.0	336.4	378.6
52.5°	256.7	256.6	256.2	256.7	258.6	261.5	266.0	273.7	287.4	311.6	348.8
55°	234.4	232.7	233.1	231.8	234.8	235.4	238.8	245.1	257.1	273.8	308.7
57.5°	210.6	209.3	207.8	207.4	207.1	208.9	211.6	216.6	225.8	240.4	268.8
60°	195.5	193.9	191.8	191.2	191.2	192.2	193.5	197.2	205.8	218.8	242.1
62.5°	180.0	178.1	176.9	175.1	174.6	175.7	177.0	179.6	185.8	198.0	218.1
65°	156.2	153.8	152.2	151.9	151.2	150.2	150.9	153.6	158.5	168.2	184.1
67.5°	132.2	130.1	129.7	127.8	126.8	127.0	126.8	129.1	132.1	140.4	152.3
70°	116.5	114.9	114.2	112.5	111.9	111.2	110.6	112.5	115.6	122.5	132.9
72.5°	100.6	99.2	97.7	96.3	96.5	95.8	95.7	96.8	99.3	105.8	113.7
75°	77.6	77.9	76.2	74.6	74.3	73.6	73.6	74.6	75.6	80.6	86.9
77.5°	56.3	56.0	54.6	54.0	53.8	53.1	53.8	54.4	54.9	58.3	63.0
80°	43.0	43.0	41.3	41.3	40.9	39.9	40.9	40.3	41.6	44.9	48.3
82.5°	30.7	30.1	30.1	29.6	29.5	28.8	29.2	29.9	30.4	32.7	34.7
85°	15.0	15.0	14.6	14.4	14.6	14.4	14.6	15.0	15.3	16.3	18.0
87.5°	11.1	11.6	10.7	9.8	8.7	7.8	7.2	6.9	6.8	6.4	6.1
90°	39.9	40.5	34.8	29.2	23.5	17.8	13.5	10.4	7.3	4.3	1.2
92.5°	36.8	36.7	35.4	34.1	32.7	31.4	29.6	27.4	25.1	22.8	20.6
95°	74.0	74.0	73.5	72.9	72.5	72.0	70.4	67.9	65.3	62.7	60.1
97.5°	124.4	124.4	123.4	122.4	121.5	120.5	118.9	116.6	114.4	112.1	109.9
100°	159.5	159.5	158.8	158.0	157.2	156.5	155.1	153.0	151.0	148.9	146.9
102.5°	197.7	197.5	196.5	195.6	194.6	193.6	192.3	190.6	189.0	187.3	185.7
105°	254.9	254.4	253.9	253.3	252.8	252.4	251.6	250.9	250.1	249.3	248.6
107.5°	317.3	317.0	317.0	317.0	317.0	317.0	316.5	315.3	314.2	313.1	311.9
110°	359.6	359.6	359.6	359.6	359.6	359.6	358.8	357.3	355.7	354.2	352.7



TEST NUMBER: P331514-940

CATALOG NUMBER: S122DIW-S485D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	402.4	403.1	403.2	403.5	403.7	403.9	403.2	401.7	400.1	398.6	397.1
115°	466.9	467.1	467.6	468.1	468.7	469.1	468.7	467.1	465.6	464.0	462.5
117.5°	529.9	530.5	531.9	533.3	534.8	536.3	535.9	533.9	531.8	529.8	527.7
120°	571.1	571.1	573.2	575.3	577.4	579.4	579.4	577.4	575.3	573.2	571.1
122.5°	614.9	615.5	617.0	618.5	619.9	621.3	620.8	618.3	615.9	613.4	610.9
125°	679.1	679.8	680.6	681.4	682.2	683.0	682.2	679.8	677.5	675.2	672.9
127.5°	741.4	742.3	743.2	744.1	745.1	746.0	745.0	742.1	739.1	736.2	733.3
130°	783.4	783.9	784.4	785.0	785.5	786.0	784.5	781.2	777.9	774.5	771.2
132.5°	825.4	826.4	826.3	826.3	826.2	826.1	824.7	821.9	819.2	816.5	813.8
135°	885.4	885.6	885.2	884.7	884.1	883.6	882.0	879.1	876.3	873.4	870.7
137.5°	943.8	944.0	943.3	942.6	941.9	941.3	939.8	937.5	935.1	932.8	930.5
140°	982.8	982.8	981.5	980.3	978.9	977.7	975.9	973.6	971.3	968.9	966.6
142.5°	1018.2	1018.0	1017.1	1016.2	1015.3	1014.4	1012.9	1010.6	1008.3	1005.9	1003.6
145°	1072.1	1071.8	1070.3	1068.7	1067.2	1065.7	1064.0	1062.2	1060.4	1058.6	1056.8
147.5°	1119.1	1118.6	1117.5	1116.5	1115.4	1114.5	1112.9	1110.7	1108.5	1106.3	1104.2
150°	1148.9	1148.2	1147.1	1146.1	1145.0	1144.1	1142.7	1141.2	1139.7	1138.1	1136.6
152.5°	1178.8	1177.8	1176.5	1175.3	1174.0	1172.8	1171.4	1169.8	1168.3	1166.8	1165.3
155°	1216.5	1215.2	1214.4	1213.6	1212.9	1212.1	1211.4	1210.6	1209.8	1209.1	1208.3
157.5°	1251.2	1249.5	1248.9	1248.5	1248.0	1247.6	1247.1	1246.6	1246.1	1245.5	1245.0
160°	1272.2	1270.7	1270.4	1270.2	1269.9	1269.7	1269.3	1268.8	1268.3	1267.7	1267.2
162.5°	1290.9	1289.2	1289.0	1288.7	1288.4	1288.2	1288.0	1287.9	1287.8	1287.7	1287.5
165°	1315.3	1313.5	1313.5	1313.5	1313.5	1313.5	1313.6	1313.8	1314.1	1314.4	1314.6
167.5°	1335.4	1333.6	1333.6	1333.7	1333.7	1333.8	1334.2	1335.0	1335.8	1336.5	1337.3
170°	1346.5	1344.7	1345.0	1345.2	1345.5	1345.8	1346.2	1347.0	1347.8	1348.5	1349.3
172.5°	1354.9	1353.0	1353.3	1353.5	1353.8	1354.1	1354.6	1355.3	1356.1	1356.9	1357.6
175°	1363.9	1362.0	1362.5	1363.1	1363.6	1364.1	1364.8	1365.5	1366.3	1367.1	1367.8
177.5°	1368.6	1367.3	1367.8	1368.2	1368.6	1369.0	1369.5	1370.1	1370.7	1371.4	1372.0
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331514-940

CATALOG NUMBER: S122DIW-S485D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	871.0	872.4	876.6	880.9	885.6	887.0	889.1	887.3	886.7	891.8	895.5
5°	873.5	879.5	891.2	901.8	910.8	917.1	923.8	926.5	931.5	938.4	947.1
7.5°	870.7	882.3	900.7	916.2	933.1	945.3	954.8	963.0	972.8	986.1	1000.5
10°	867.5	883.2	905.4	924.4	945.1	960.7	973.7	986.4	1001.0	1019.4	1038.3
12.5°	861.7	880.2	908.1	930.6	957.1	972.5	990.0	1017.3	1033.0	1058.5	1085.2
15°	849.9	870.5	909.5	937.1	967.1	996.4	1028.7	1054.6	1080.7	1095.6	1133.3
17.5°	832.3	862.6	905.8	938.1	976.2	1022.3	1058.5	1088.1	1118.0	1142.3	1161.2
20°	818.2	851.2	900.4	939.1	984.4	1034.0	1075.7	1105.6	1131.6	1151.9	1163.6
22.5°	800.4	841.9	889.8	935.1	992.9	1042.1	1085.7	1109.4	1131.0	1140.9	1145.4
25°	772.2	822.2	876.5	931.7	997.0	1049.0	1089.0	1103.3	1109.6	1099.9	1084.0
27.5°	742.0	797.6	861.1	925.5	994.5	1044.5	1073.1	1070.9	1060.2	1028.9	1003.9
30°	719.3	780.6	848.8	919.1	988.4	1037.0	1053.6	1037.0	1012.7	977.8	942.1
32.5°	695.6	759.0	835.8	910.1	977.2	1019.9	1023.6	994.9	957.3	917.6	873.1
35°	659.7	728.3	811.2	889.8	953.4	980.4	964.4	913.8	869.2	814.9	754.3
37.5°	619.1	694.9	778.0	860.1	917.8	924.9	885.2	831.9	768.9	705.2	633.8
40°	588.8	669.1	754.7	837.5	888.5	881.2	830.5	772.0	697.0	619.1	552.8
42.5°	561.6	641.9	729.1	810.4	851.2	831.1	772.0	700.0	619.5	546.1	485.4
45°	514.5	597.1	686.3	764.9	788.3	752.0	673.7	593.8	514.5	453.3	405.3
47.5°	468.9	550.5	638.8	707.9	716.2	667.4	581.8	499.6	431.5	381.6	347.8
50°	435.2	517.2	604.8	666.4	663.7	604.8	516.8	438.5	381.7	341.3	318.7
52.5°	405.1	482.5	566.7	622.7	608.6	544.3	460.4	390.9	344.1	312.5	292.0
55°	358.3	429.9	509.9	554.8	528.9	457.5	386.6	330.6	296.0	272.4	256.5
57.5°	311.8	379.0	447.4	475.1	446.4	380.6	321.5	280.9	254.9	237.3	226.9
60°	283.0	341.7	402.6	426.6	392.3	333.7	287.0	250.7	229.8	215.4	206.2
62.5°	254.3	306.7	364.3	377.3	345.9	296.4	255.1	224.9	207.7	194.9	186.2
65°	215.2	258.1	301.8	310.4	281.4	243.1	210.4	190.8	175.5	166.2	159.2
67.5°	176.5	210.9	241.8	248.8	223.5	196.9	173.3	156.2	145.8	138.0	132.2
70°	153.6	180.8	206.2	211.8	191.5	167.8	149.9	136.2	126.9	120.2	114.6
72.5°	129.3	152.0	173.1	176.9	160.3	142.2	127.5	116.7	108.5	104.2	98.8
75°	98.9	112.3	128.6	129.6	118.6	107.5	96.2	89.3	84.9	79.6	77.0
77.5°	69.8	80.3	89.6	91.4	84.9	77.4	71.1	65.5	61.9	59.4	57.0
80°	53.3	61.6	65.6	67.9	63.3	58.0	54.3	50.6	48.3	46.6	44.9
82.5°	38.1	43.2	47.0	48.8	46.2	43.1	39.3	37.3	35.5	34.1	33.5
85°	19.4	21.7	24.0	24.6	24.0	22.6	20.7	20.7	19.6	19.4	19.4
87.5°	7.5	9.2	9.8	11.2	11.6	12.7	13.8	14.7	15.5	15.2	14.8
90°	4.3	7.3	10.4	13.5	17.8	23.5	29.2	34.8	40.5	39.9	39.4
92.5°	22.8	25.1	27.4	29.6	31.4	32.7	34.1	35.4	36.7	36.8	37.0
95°	62.7	65.3	67.9	70.4	72.0	72.5	72.9	73.5	74.0	74.0	74.0
97.5°	112.1	114.4	116.6	118.9	120.5	121.5	122.4	123.4	124.4	124.4	124.4
100°	148.9	151.0	153.0	155.1	156.5	157.2	158.0	158.8	159.5	159.5	159.5
102.5°	187.3	189.0	190.6	192.3	193.6	194.6	195.6	196.5	197.5	197.7	197.9
105°	249.3	250.1	250.9	251.6	252.4	252.8	253.3	253.9	254.4	254.9	255.4
107.5°	313.1	314.2	315.3	316.5	317.0	317.0	317.0	317.0	317.0	317.3	317.4
110°	354.2	355.7	357.3	358.8	359.6	359.6	359.6	359.6	359.6	359.6	359.6



TEST NUMBER: P331514-940

CATALOG NUMBER: S122DIW-S485D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	398.6	400.1	401.7	403.2	403.9	403.7	403.5	403.2	403.1	402.4	401.8
115°	464.0	465.6	467.1	468.7	469.1	468.7	468.1	467.6	467.1	466.9	466.6
117.5°	529.8	531.8	533.9	535.9	536.3	534.8	533.3	531.9	530.5	529.9	529.2
120°	573.2	575.3	577.4	579.4	579.4	577.4	575.3	573.2	571.1	571.1	571.1
122.5°	613.4	615.9	618.3	620.8	621.3	619.9	618.5	617.0	615.5	614.9	614.4
125°	675.2	677.5	679.8	682.2	683.0	682.2	681.4	680.6	679.8	679.1	678.3
127.5°	736.2	739.1	742.1	745.0	746.0	745.1	744.1	743.2	742.3	741.4	740.5
130°	774.5	777.9	781.2	784.5	786.0	785.5	785.0	784.4	783.9	783.4	782.9
132.5°	816.5	819.2	821.9	824.7	826.1	826.2	826.3	826.3	826.4	825.4	824.2
135°	873.4	876.3	879.1	882.0	883.6	884.1	884.7	885.2	885.6	885.4	885.2
137.5°	932.8	935.1	937.5	939.8	941.3	941.9	942.6	943.3	944.0	943.8	943.5
140°	968.9	971.3	973.6	975.9	977.7	978.9	980.3	981.5	982.8	982.8	982.8
142.5°	1005.9	1008.3	1010.6	1012.9	1014.4	1015.3	1016.2	1017.1	1018.0	1018.2	1018.3
145°	1058.6	1060.4	1062.2	1064.0	1065.7	1067.2	1068.7	1070.3	1071.8	1072.1	1072.4
147.5°	1106.3	1108.5	1110.7	1112.9	1114.5	1115.4	1116.5	1117.5	1118.6	1119.1	1119.6
150°	1138.1	1139.7	1141.2	1142.7	1144.1	1145.0	1146.1	1147.1	1148.2	1148.9	1149.7
152.5°	1166.8	1168.3	1169.8	1171.4	1172.8	1174.0	1175.3	1176.5	1177.8	1178.8	1179.7
155°	1209.1	1209.8	1210.6	1211.4	1212.1	1212.9	1213.6	1214.4	1215.2	1216.5	1217.8
157.5°	1245.5	1246.1	1246.6	1247.1	1247.6	1248.0	1248.5	1248.9	1249.5	1251.2	1252.9
160°	1267.7	1268.3	1268.8	1269.3	1269.7	1269.9	1270.2	1270.4	1270.7	1272.2	1273.8
162.5°	1287.7	1287.8	1287.9	1288.0	1288.2	1288.4	1288.7	1289.0	1289.2	1290.9	1292.7
165°	1314.4	1314.1	1313.8	1313.6	1313.5	1313.5	1313.5	1313.5	1313.5	1315.3	1317.1
167.5°	1336.5	1335.8	1335.0	1334.2	1333.8	1333.7	1333.7	1333.6	1333.6	1335.4	1337.2
170°	1348.5	1347.8	1347.0	1346.2	1345.8	1345.5	1345.2	1345.0	1344.7	1346.5	1348.3
172.5°	1356.9	1356.1	1355.3	1354.6	1354.1	1353.8	1353.5	1353.3	1353.0	1354.9	1356.6
175°	1367.1	1366.3	1365.5	1364.8	1364.1	1363.6	1363.1	1362.5	1362.0	1363.9	1365.7
177.5°	1371.4	1370.7	1370.1	1369.5	1369.0	1368.6	1368.2	1367.8	1367.3	1368.6	1369.8
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331514-940

CATALOG NUMBER: S122DIW-S485D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	898.8	902.5	902.5	903.0	907.2	906.8	906.5
5°	956.4	962.1	962.8	968.8	972.8	971.4	967.8
7.5°	1010.8	1021.4	1029.4	1033.8	1039.1	1042.3	1040.9
10°	1054.0	1069.3	1078.6	1084.9	1092.6	1098.3	1096.3
12.5°	1093.1	1111.4	1124.2	1135.1	1136.0	1143.4	1138.4
15°	1154.2	1173.6	1175.5	1183.6	1189.9	1189.2	1189.5
17.5°	1174.4	1180.6	1181.9	1182.1	1182.1	1179.8	1174.7
20°	1167.2	1164.9	1159.2	1154.9	1147.3	1146.2	1139.6
22.5°	1133.1	1125.7	1111.5	1102.2	1090.2	1087.1	1085.2
25°	1066.0	1049.6	1027.0	1005.4	999.3	987.7	991.0
27.5°	973.8	948.4	923.9	906.3	890.5	873.0	878.0
30°	909.1	880.5	845.9	819.2	802.3	785.6	782.6
32.5°	831.9	789.9	751.3	727.8	701.8	691.3	679.8
35°	698.7	657.7	619.4	586.5	567.5	552.8	539.5
37.5°	578.8	531.7	500.8	474.1	460.4	452.0	454.1
40°	504.5	463.2	440.6	420.3	407.6	401.6	403.0
42.5°	444.3	413.4	394.8	380.8	371.9	368.5	367.7
45°	375.9	358.6	343.3	335.4	331.0	327.3	325.0
47.5°	329.4	315.2	306.6	301.8	298.0	294.4	294.3
50°	301.4	292.0	286.1	281.1	278.0	275.4	277.8
52.5°	280.1	271.5	265.6	261.1	259.9	257.5	257.5
55°	248.4	241.7	237.5	233.4	231.5	230.2	228.5
57.5°	219.6	213.3	209.4	206.8	203.0	201.7	201.2
60°	199.1	194.1	190.1	186.8	185.1	182.5	182.5
62.5°	180.2	175.2	171.5	169.0	166.2	165.1	165.4
65°	152.8	148.8	145.2	142.5	141.9	139.9	140.5
67.5°	127.7	125.0	121.2	119.7	118.4	117.3	116.5
70°	110.9	108.3	106.2	104.2	103.3	103.3	103.3
72.5°	96.8	93.5	92.4	89.9	90.4	89.3	88.3
75°	74.9	72.9	72.0	70.9	69.3	69.3	69.3
77.5°	55.1	54.6	53.3	52.3	51.9	51.5	51.7
80°	42.6	42.3	41.6	41.6	40.9	40.7	39.9
82.5°	32.7	31.9	31.5	31.2	31.1	31.0	30.9
85°	18.6	18.0	18.0	18.3	17.7	17.7	18.0
87.5°	15.0	14.9	14.6	14.6	15.0	14.7	14.8
90°	39.0	38.4	38.3	38.5	38.8	39.1	39.3
92.5°	37.1	37.2	37.3	37.3	37.4	37.5	37.5
95°	74.0	74.0	73.7	73.2	72.7	72.2	71.7
97.5°	124.4	124.4	124.4	124.3	124.3	124.2	124.2
100°	159.5	159.5	159.4	159.2	158.9	158.6	158.4
102.5°	198.1	198.3	198.3	198.0	197.8	197.5	197.2
105°	255.9	256.5	256.7	256.7	256.7	256.7	256.7
107.5°	317.6	317.9	317.4	316.2	315.0	313.8	312.6
110°	359.6	359.6	359.2	358.5	357.7	356.9	356.1



TEST NUMBER: P331514-940

CATALOG NUMBER: S122DIW-S485D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	401.2	400.6	400.0	399.4	398.9	398.3	397.7
115°	466.4	466.1	465.6	464.8	464.0	463.2	462.5
117.5°	528.6	528.0	527.4	526.6	525.8	525.0	524.2
120°	571.1	571.1	570.8	570.0	569.3	568.5	567.8
122.5°	613.8	613.1	612.5	612.0	611.4	610.8	610.3
125°	677.5	676.8	676.3	676.0	675.7	675.5	675.2
127.5°	739.5	738.6	737.7	736.9	736.1	735.3	734.4
130°	782.4	781.9	781.1	780.1	779.1	778.0	776.9
132.5°	823.0	822.0	821.0	820.2	819.3	818.5	817.7
135°	884.9	884.7	884.1	883.3	882.6	881.8	881.0
137.5°	943.3	943.2	942.5	941.5	940.5	939.4	938.4
140°	982.8	982.8	982.3	981.2	980.3	979.2	978.2
142.5°	1018.6	1018.8	1018.3	1017.4	1016.3	1015.3	1014.2
145°	1072.6	1072.8	1072.5	1071.5	1070.4	1069.4	1068.4
147.5°	1120.3	1120.8	1120.6	1119.6	1118.7	1117.7	1116.7
150°	1150.5	1151.2	1151.2	1150.5	1149.7	1148.9	1148.2
152.5°	1180.6	1181.6	1181.6	1180.6	1179.7	1178.8	1177.8
155°	1219.1	1220.3	1220.6	1219.9	1219.1	1218.3	1217.5
157.5°	1254.6	1256.4	1256.7	1255.4	1254.2	1252.9	1251.7
160°	1275.3	1276.8	1277.1	1276.1	1275.1	1274.1	1273.0
162.5°	1294.4	1296.2	1296.5	1295.2	1294.0	1292.7	1291.6
165°	1318.8	1320.7	1320.9	1319.6	1318.4	1317.1	1315.8
167.5°	1339.0	1340.8	1341.0	1339.7	1338.4	1337.0	1335.7
170°	1350.1	1351.9	1352.0	1350.5	1349.0	1347.4	1345.9
172.5°	1358.4	1360.2	1360.3	1358.8	1357.3	1355.8	1354.2
175°	1367.4	1369.2	1369.4	1367.8	1366.3	1364.8	1363.2
177.5°	1371.1	1372.3	1372.3	1371.1	1369.8	1368.6	1367.3
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1

(END OF REPORT)