

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331836

Luminaire Tested: **S122RDIW-S865D970U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331836
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S865D970U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6376.6 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331836

CATALOG NUMBER: S122RDIW-S865D970U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331836

CATALOG NUMBER: S122RDIW-S865D970U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	38	36	34	30
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	35	32	30	26
5	69	58	50	44	63	54	47	41	46	40	36	38	34	31	31	29	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	23	20
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	17
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23675	23675	23675
5°	23765	23378	23506
10°	23582	22996	22799
15°	23311	22313	21670
20°	22936	21340	20270
25°	22552	20236	18912
30°	22018	19099	17169
35°	21498	17864	15640
40°	20976	16585	13873
45°	20361	15150	12271
50°	19733	13700	10698
55°	19088	12141	9188
60°	18338	10498	7627
65°	17490	8821	6946
70°	16475	7265	6387
75°	15234	6625	5958
80°	13445	5923	5430
85°	10578	4668	4668



TEST NUMBER: P331836

CATALOG NUMBER: S122RDIW-S865D970U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.2	2.2
10°-20°	376.8	5.9
20°-30°	529.2	8.3
30°-40°	577.1	9.0
40°-50°	530.6	8.3
50°-60°	416.7	6.5
60°-70°	271.7	4.3
70°-80°	140.1	2.2
80°-90°	41.1	0.6
90°-100°	76.0	1.2
100°-110°	236.2	3.7
110°-120°	403.8	6.3
120°-130°	531.0	8.3
130°-140°	595.9	9.3
140°-150°	584.3	9.2
150°-160°	490.1	7.7
160°-170°	325.1	5.1
170°-180°	113.6	1.8
0°-30°	1043.3	16.4
0°-40°	1620.3	25.4
0°-60°	2567.6	40.3
0°-90°	3020.5	47.4
90°-120°	716.0	11.2
90°-150°	2427.3	38.1
90°-180°	3356.0	52.6
0°-180°	6376.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1466	1466	1466	1466	1466	
5°	1466	1459	1442	1453	1450	139
15°	1395	1378	1335	1310	1296	393
25°	1266	1221	1136	1083	1062	582
35°	1091	1020	906	826	794	682
45°	892	800	664	573	537	688
55°	678	572	431	355	326	606
65°	458	350	231	188	182	454
75°	244	154	106	97	96	258
85°	57	31	25	25	25	67
90°	1	14	35	34	34	5
95°	53	62	65	65	63	60
105°	218	221	223	225	225	230
115°	405	411	409	408	405	401
125°	590	598	596	593	592	527
135°	763	773	776	775	772	589
145°	926	933	939	940	936	578
155°	1058	1061	1064	1069	1066	487
165°	1152	1151	1151	1157	1153	325
175°	1198	1195	1193	1200	1194	114
180°	1200	1200	1200	1200	1200	



TEST NUMBER: P331836

CATALOG NUMBER: S122RDIW-S865D970U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3
2.5°	1471.6	1470.4	1469.2	1468.0	1466.9	1465.0	1462.4	1459.8	1457.2	1454.6	1457.0
5°	1466.3	1464.8	1463.3	1461.8	1460.4	1457.7	1453.9	1450.1	1446.2	1442.4	1445.0
7.5°	1451.1	1449.3	1447.5	1445.7	1443.8	1440.7	1436.2	1431.7	1427.2	1422.7	1423.5
10°	1438.4	1436.3	1434.3	1432.2	1430.1	1426.2	1420.3	1414.4	1408.5	1402.6	1401.7
12.5°	1422.5	1419.9	1417.4	1414.9	1412.3	1407.3	1399.7	1392.2	1384.6	1377.1	1375.5
15°	1394.6	1391.4	1388.1	1384.9	1381.6	1375.0	1365.0	1355.0	1344.9	1334.9	1329.3
17.5°	1360.4	1355.4	1350.5	1345.5	1340.6	1331.7	1318.8	1305.9	1293.1	1280.2	1273.6
20°	1334.9	1329.0	1323.1	1317.2	1311.3	1301.0	1286.2	1271.5	1256.8	1242.0	1234.6
22.5°	1307.3	1300.7	1294.1	1287.5	1280.9	1269.3	1252.6	1236.0	1219.4	1202.7	1193.2
25°	1265.9	1256.5	1247.0	1237.6	1228.2	1213.7	1194.2	1174.8	1155.3	1135.9	1123.8
27.5°	1216.0	1205.7	1195.5	1185.2	1175.0	1158.9	1136.9	1115.0	1093.0	1071.1	1057.0
30°	1181.0	1169.8	1158.6	1147.4	1136.2	1118.8	1095.2	1071.6	1048.0	1024.4	1009.4
32.5°	1147.0	1133.9	1120.8	1107.7	1094.6	1076.1	1052.0	1027.9	1003.9	979.8	962.7
35°	1090.7	1075.7	1060.7	1045.6	1030.6	1010.1	984.1	958.2	932.3	906.3	887.7
37.5°	1034.5	1018.0	1001.5	984.9	968.4	946.3	918.7	891.0	863.4	835.7	815.2
40°	995.2	977.5	959.8	942.1	924.4	901.3	872.7	844.1	815.5	786.9	765.9
42.5°	954.9	936.2	917.6	899.0	880.3	856.2	826.7	797.1	767.6	738.0	716.4
45°	891.7	871.9	852.2	832.4	812.7	787.3	756.4	725.4	694.4	663.5	642.5
47.5°	830.1	809.2	788.3	767.3	746.4	719.9	688.0	656.0	624.0	592.1	571.3
50°	785.6	764.6	743.7	722.7	701.8	675.1	642.7	610.2	577.8	545.4	525.0
52.5°	742.0	720.1	698.3	676.4	654.5	627.7	596.0	564.2	532.5	500.8	481.1
55°	678.1	655.1	632.1	609.1	586.1	558.6	526.8	494.9	463.1	431.3	413.6
57.5°	612.5	588.9	565.3	541.7	518.2	491.1	460.4	429.8	399.2	368.6	352.4
60°	567.9	544.3	520.8	497.2	473.6	446.6	416.2	385.8	355.5	325.1	310.1
62.5°	524.4	500.8	477.2	453.6	430.0	403.8	374.8	345.9	316.9	287.9	273.6
65°	457.8	433.9	410.0	386.1	362.3	337.0	310.5	284.0	257.4	230.9	220.9
67.5°	393.6	369.9	346.2	322.4	298.7	274.9	251.1	227.2	203.3	179.4	174.8
70°	349.0	326.0	303.0	280.0	257.0	235.3	215.0	194.6	174.3	153.9	151.0
72.5°	306.5	284.5	262.4	240.4	218.3	199.1	182.8	166.4	150.1	133.8	131.3
75°	244.2	223.5	202.9	182.2	161.6	146.3	136.2	126.2	116.2	106.2	104.1
77.5°	182.9	164.7	146.6	128.5	110.4	99.0	94.1	89.3	84.5	79.6	78.4
80°	144.6	129.6	114.6	99.5	84.5	75.5	72.5	69.6	66.6	63.7	62.5
82.5°	109.6	97.9	86.1	74.4	62.7	55.8	53.8	51.8	49.8	47.8	47.1
85°	57.1	50.9	44.7	38.5	32.3	28.8	27.9	27.0	26.1	25.2	25.2
87.5°	17.2	15.8	14.5	13.1	11.8	11.6	12.6	13.6	14.6	15.6	15.3
90°	1.0	3.7	6.4	9.1	11.8	15.6	20.6	25.5	30.5	35.4	35.0
92.5°	18.0	20.0	22.0	24.0	26.0	27.5	28.7	29.9	31.0	32.2	32.3
95°	52.7	54.9	57.2	59.4	61.7	63.0	63.5	63.9	64.4	64.8	64.8
97.5°	96.2	98.2	100.2	102.2	104.1	105.6	106.4	107.3	108.1	109.0	109.0
100°	128.6	130.4	132.2	134.0	135.8	137.1	137.7	138.4	139.1	139.8	139.8
102.5°	162.7	164.1	165.5	167.0	168.4	169.6	170.4	171.3	172.1	173.0	173.2
105°	217.8	218.4	219.1	219.8	220.5	221.0	221.5	221.9	222.4	222.8	223.3
107.5°	273.3	274.3	275.2	276.2	277.2	277.7	277.7	277.7	277.7	277.7	277.9
110°	308.9	310.3	311.6	313.0	314.3	315.0	315.0	315.0	315.0	315.0	315.0



TEST NUMBER: P331836

CATALOG NUMBER: S122RDIW-S865D970U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	347.8	349.2	350.5	351.9	353.2	353.8	353.6	353.4	353.3	353.1	352.5
115°	405.1	406.5	407.8	409.2	410.5	411.0	410.5	410.1	409.6	409.2	409.0
117.5°	462.3	464.1	465.9	467.7	469.5	469.7	468.5	467.2	466.0	464.7	464.2
120°	500.4	502.2	504.0	505.8	507.6	507.6	505.8	504.0	502.2	500.4	500.4
122.5°	535.2	537.4	539.5	541.7	543.8	544.3	543.0	541.8	540.5	539.2	538.7
125°	589.5	591.5	593.5	595.6	597.6	598.3	597.6	596.9	596.2	595.6	594.9
127.5°	642.4	644.9	647.5	650.1	652.6	653.5	652.7	651.9	651.1	650.3	649.4
130°	675.6	678.5	681.4	684.4	687.3	688.5	688.1	687.6	687.2	686.7	686.3
132.5°	712.8	715.2	717.6	720.0	722.4	723.6	723.7	723.8	723.9	724.0	723.0
135°	762.7	765.2	767.6	770.1	772.6	774.0	774.5	774.9	775.4	775.8	775.6
137.5°	815.1	817.2	819.2	821.2	823.2	824.6	825.1	825.7	826.3	826.9	826.7
140°	846.7	848.8	850.8	852.8	854.8	856.4	857.6	858.7	859.8	860.9	860.9
142.5°	879.2	881.2	883.2	885.2	887.3	888.7	889.4	890.2	891.0	891.7	891.9
145°	925.7	927.3	928.9	930.5	932.1	933.5	934.9	936.2	937.6	938.9	939.1
147.5°	967.3	969.2	971.1	972.9	974.8	976.2	977.1	978.0	978.9	979.8	980.3
150°	995.6	997.0	998.3	999.7	1001.0	1002.2	1003.1	1004.0	1004.9	1005.8	1006.4
152.5°	1020.8	1022.1	1023.5	1024.8	1026.2	1027.4	1028.5	1029.5	1030.6	1031.7	1032.5
155°	1058.4	1059.1	1059.8	1060.5	1061.1	1061.8	1062.5	1063.2	1063.8	1064.5	1065.6
157.5°	1090.6	1091.1	1091.5	1092.0	1092.4	1092.9	1093.3	1093.7	1094.1	1094.5	1096.0
160°	1110.1	1110.5	1111.0	1111.4	1111.9	1112.2	1112.5	1112.7	1112.9	1113.1	1114.5
162.5°	1127.9	1128.0	1128.1	1128.2	1128.3	1128.4	1128.7	1128.9	1129.1	1129.3	1130.9
165°	1151.6	1151.4	1151.2	1150.9	1150.7	1150.6	1150.6	1150.6	1150.6	1150.6	1152.2
167.5°	1171.5	1170.8	1170.1	1169.4	1168.8	1168.4	1168.4	1168.3	1168.3	1168.2	1169.8
170°	1182.0	1181.3	1180.7	1180.0	1179.3	1178.9	1178.6	1178.4	1178.2	1178.0	1179.5
172.5°	1189.3	1188.6	1187.9	1187.3	1186.6	1186.1	1185.9	1185.7	1185.5	1185.2	1186.8
175°	1198.2	1197.5	1196.9	1196.2	1195.5	1194.9	1194.5	1194.0	1193.6	1193.1	1194.7
177.5°	1201.9	1201.3	1200.8	1200.2	1199.7	1199.2	1198.9	1198.5	1198.2	1197.8	1198.9
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331836

CATALOG NUMBER: S122RDIW-S865D970U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3
2.5°	1459.3	1461.7	1464.0	1465.0	1464.5	1464.0	1463.6	1463.1
5°	1447.7	1450.3	1453.0	1453.9	1453.0	1452.1	1451.2	1450.3
7.5°	1424.3	1425.0	1425.8	1425.4	1423.9	1422.4	1420.8	1419.3
10°	1400.8	1399.9	1399.0	1397.7	1395.9	1394.2	1392.4	1390.6
12.5°	1373.9	1372.3	1370.7	1368.5	1365.5	1362.6	1359.6	1356.7
15°	1323.7	1318.1	1312.5	1308.2	1305.3	1302.3	1299.4	1296.4
17.5°	1266.9	1260.2	1253.6	1247.7	1242.6	1237.6	1232.5	1227.4
20°	1227.3	1219.9	1212.5	1205.6	1199.1	1192.6	1186.1	1179.7
22.5°	1183.8	1174.3	1164.8	1157.6	1152.8	1147.9	1143.1	1138.3
25°	1111.7	1099.6	1087.5	1079.2	1074.8	1070.4	1066.0	1061.6
27.5°	1042.9	1028.8	1014.7	1004.2	997.2	990.1	983.1	976.1
30°	994.3	979.3	964.2	952.7	944.8	936.8	928.9	920.9
32.5°	945.5	928.3	911.2	898.8	891.4	883.9	876.4	868.9
35°	869.1	850.6	832.0	819.5	813.0	806.5	800.0	793.5
37.5°	794.8	774.3	753.9	739.9	732.5	725.0	717.6	710.2
40°	745.0	724.1	703.1	688.8	681.2	673.5	665.8	658.2
42.5°	694.8	673.1	651.5	636.9	629.5	622.1	614.6	607.2
45°	621.6	600.7	579.7	565.7	558.6	551.6	544.5	537.4
47.5°	550.4	529.6	508.8	495.2	488.8	482.3	475.9	469.5
50°	504.7	484.3	464.0	450.7	444.5	438.3	432.1	425.9
52.5°	461.5	441.9	422.2	409.6	403.8	398.1	392.4	386.7
55°	395.9	378.2	360.5	348.8	343.2	337.6	332.0	326.4
57.5°	336.2	320.0	303.8	293.3	288.6	283.8	279.1	274.4
60°	295.0	280.0	264.9	255.1	250.3	245.6	240.9	236.2
62.5°	259.3	245.0	230.6	222.0	219.2	216.4	213.5	210.7
65°	210.8	200.8	190.8	185.3	184.4	183.6	182.7	181.8
67.5°	170.2	165.6	161.0	158.2	157.3	156.3	155.4	154.5
70°	148.0	145.1	142.1	140.1	138.9	137.7	136.5	135.3
72.5°	128.8	126.3	123.8	122.3	121.5	120.8	120.1	119.4
75°	102.0	100.0	97.9	96.7	96.4	96.1	95.8	95.5
77.5°	77.3	76.1	74.9	74.1	73.6	73.1	72.7	72.2
80°	61.3	60.2	59.0	58.4	58.4	58.4	58.4	58.4
82.5°	46.4	45.6	44.9	44.6	44.6	44.6	44.6	44.6
85°	25.2	25.2	25.2	25.2	25.2	25.2	25.2	25.2
87.5°	14.9	14.6	14.3	14.1	14.2	14.2	14.3	14.3
90°	34.5	34.1	33.6	33.5	33.8	34.0	34.2	34.4
92.5°	32.4	32.5	32.6	32.6	32.7	32.7	32.8	32.8
95°	64.8	64.8	64.8	64.6	64.1	63.7	63.2	62.8
97.5°	109.0	109.0	109.0	109.0	108.9	108.9	108.8	108.8
100°	139.8	139.8	139.8	139.7	139.4	139.2	139.0	138.8
102.5°	173.4	173.5	173.7	173.7	173.5	173.2	173.0	172.8
105°	223.7	224.2	224.6	224.9	224.9	224.9	224.9	224.9
107.5°	278.1	278.3	278.4	278.0	277.0	275.9	274.9	273.9
110°	315.0	315.0	315.0	314.7	314.0	313.3	312.6	312.0



TEST NUMBER: P331836

CATALOG NUMBER: S122RDIW-S865D970U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	352.0	351.5	350.9	350.4	349.9	349.4	348.9	348.4
115°	408.7	408.5	408.3	407.8	407.2	406.5	405.8	405.1
117.5°	463.6	463.1	462.5	461.9	461.3	460.6	459.9	459.2
120°	500.4	500.4	500.4	500.0	499.3	498.7	498.0	497.3
122.5°	538.2	537.6	537.1	536.6	536.1	535.6	535.1	534.6
125°	594.2	593.5	592.9	592.4	592.2	592.0	591.7	591.5
127.5°	648.6	647.8	647.0	646.2	645.5	644.8	644.1	643.4
130°	685.8	685.4	684.9	684.2	683.3	682.4	681.5	680.6
132.5°	722.0	721.0	720.0	719.2	718.5	717.7	717.0	716.3
135°	775.4	775.2	774.9	774.5	773.8	773.1	772.5	771.8
137.5°	826.5	826.4	826.2	825.6	824.7	823.8	822.9	822.0
140°	860.9	860.9	860.9	860.5	859.6	858.7	857.8	856.9
142.5°	892.1	892.3	892.4	892.1	891.2	890.3	889.4	888.5
145°	939.4	939.6	939.8	939.5	938.6	937.7	936.8	935.9
147.5°	980.8	981.3	981.8	981.6	980.8	979.9	979.1	978.2
150°	1007.1	1007.8	1008.5	1008.5	1007.8	1007.1	1006.4	1005.8
152.5°	1033.4	1034.3	1035.1	1035.1	1034.3	1033.4	1032.5	1031.7
155°	1066.8	1067.9	1069.0	1069.2	1068.6	1067.9	1067.2	1066.5
157.5°	1097.6	1099.1	1100.6	1100.8	1099.8	1098.7	1097.6	1096.5
160°	1115.8	1117.2	1118.5	1118.8	1117.9	1117.0	1116.1	1115.2
162.5°	1132.4	1133.9	1135.5	1135.7	1134.6	1133.5	1132.4	1131.4
165°	1153.8	1155.3	1156.9	1157.1	1156.0	1154.9	1153.8	1152.6
167.5°	1171.4	1173.0	1174.5	1174.7	1173.6	1172.4	1171.2	1170.1
170°	1181.1	1182.7	1184.3	1184.4	1183.0	1181.7	1180.3	1179.0
172.5°	1188.4	1190.0	1191.5	1191.7	1190.3	1189.0	1187.6	1186.3
175°	1196.3	1197.9	1199.4	1199.6	1198.2	1196.9	1195.5	1194.2
177.5°	1200.0	1201.0	1202.1	1202.1	1201.0	1200.0	1198.9	1197.8
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2

(END OF REPORT)