

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331610-935

Luminaire Tested: **S122DIW-S1005D1440U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331610-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S1005D1440U935-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8094.8 lumens  
Efficiency: N/A  
Efficacy: 97.6 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331610-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331610-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39	35
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	57	51	69	60	53	48	51	46	42	42	38	36	34	32	30	26
5	69	58	50	44	63	53	47	41	45	40	36	38	34	31	31	28	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	28	26	23	20
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	27719	27719	27719	27719
5°	31076	27901	24725	27901
10°	35611	27671	21397	27671
15°	39397	27164	18903	27164
20°	38797	26620	17234	26620
25°	34983	25896	16174	25896
30°	28909	24738	15401	24738
35°	21068	23526	14852	23526
40°	16828	22097	14547	22097
45°	14705	20445	14132	20445
50°	13823	18844	13855	18844
55°	12740	17219	13486	17219
60°	11677	15490	12910	15490
65°	10636	13941	12351	13941
70°	9659	12430	11528	12430
75°	8559	10742	10212	10742
80°	7364	8898	8219	8898
85°	6595	6595	4891	6595



TEST NUMBER: P331610-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	163.5	2.0
10°-20°	475.3	5.9
20°-30°	689.9	8.5
30°-40°	728.0	9.0
40°-50°	644.6	8.0
50°-60°	514.4	6.4
60°-70°	349.6	4.3
70°-80°	179.3	2.2
80°-90°	49.4	0.6
90°-100°	97.5	1.2
100°-110°	302.7	3.7
110°-120°	517.4	6.4
120°-130°	680.4	8.4
130°-140°	763.7	9.4
140°-150°	748.8	9.3
150°-160°	628.1	7.8
160°-170°	416.6	5.1
170°-180°	145.6	1.8
0°-30°	1328.7	16.4
0°-40°	2056.7	25.4
0°-60°	3215.7	39.7
0°-90°	3793.9	46.9
90°-120°	917.6	11.3
90°-150°	3110.6	38.4
90°-180°	4301.0	53.1
0°-180°	8094.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1717	1717	1717	1717	1717	
5°	1917	1722	1526	1722	1917	191
15°	2357	1625	1131	1625	2357	650
25°	1964	1454	908	1454	1964	888
35°	1069	1194	754	1194	1069	695
45°	644	895	619	895	644	506
55°	453	612	479	612	453	406
65°	278	365	323	365	278	277
75°	137	172	164	172	137	147
85°	36	36	26	36	36	40
90°	44	1	44	1	44	21
95°	80	68	80	68	80	90
105°	288	279	288	279	288	303
115°	519	519	519	519	519	513
125°	758	755	758	755	758	676
135°	989	977	989	977	989	761
145°	1199	1186	1199	1186	1199	749
155°	1367	1356	1367	1356	1367	629
165°	1477	1476	1477	1476	1477	417
175°	1530	1536	1530	1536	1530	145
180°	1538	1538	1538	1538	1538	



TEST NUMBER: P331610-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1796.0	1796.6	1797.6	1789.2	1788.1	1788.1	1780.7	1774.4	1767.0	1757.0	1758.1
5°	1917.4	1924.7	1927.3	1919.4	1907.5	1906.3	1895.1	1876.5	1859.4	1845.6	1835.7
7.5°	2062.4	2065.3	2058.8	2048.4	2039.5	2023.7	2002.9	1982.4	1953.8	1927.5	1908.0
10°	2172.1	2176.1	2164.9	2149.7	2137.2	2118.7	2088.4	2057.4	2019.7	1983.5	1954.4
12.5°	2255.6	2265.3	2250.9	2248.9	2227.5	2202.1	2165.9	2150.3	2097.3	2046.8	2015.7
15°	2356.9	2356.2	2357.6	2345.0	2329.2	2325.2	2287.0	2245.4	2170.8	2141.1	2089.6
17.5°	2327.6	2337.6	2342.3	2342.1	2341.7	2339.3	2326.9	2300.7	2263.3	2215.2	2155.8
20°	2258.0	2271.1	2273.1	2288.3	2296.9	2308.1	2312.7	2305.4	2282.3	2242.1	2190.6
22.5°	2150.3	2154.0	2160.2	2183.8	2202.4	2230.5	2245.1	2269.5	2260.7	2241.0	2198.0
25°	1963.7	1957.1	1980.1	1992.0	2034.9	2079.7	2112.1	2147.8	2179.4	2198.6	2186.0
27.5°	1739.6	1729.7	1764.3	1795.8	1830.7	1879.2	1929.6	1989.1	2038.6	2100.5	2121.8
30°	1550.6	1556.5	1589.5	1623.2	1675.9	1744.6	1801.3	1866.6	1937.2	2006.6	2054.7
32.5°	1346.9	1369.7	1390.5	1442.1	1488.6	1565.1	1648.2	1729.9	1818.0	1896.8	1971.3
35°	1068.9	1095.3	1124.4	1161.9	1227.3	1303.1	1384.3	1494.5	1614.6	1722.2	1810.6
37.5°	899.7	895.5	912.1	939.4	992.2	1053.5	1146.9	1255.8	1397.1	1523.5	1648.2
40°	798.4	795.7	807.6	832.7	873.0	917.8	999.6	1095.3	1226.6	1381.0	1529.5
42.5°	728.8	730.3	736.9	754.6	782.1	819.1	880.4	961.7	1082.0	1227.4	1387.0
45°	644.0	648.6	655.9	664.4	680.3	710.7	744.9	803.1	898.0	1019.4	1176.5
47.5°	583.0	583.2	590.6	598.1	607.4	624.6	652.6	689.0	756.0	854.9	989.9
50°	550.3	545.7	551.0	556.9	566.8	578.7	597.1	631.5	676.3	756.1	869.0
52.5°	510.1	510.3	515.1	517.3	526.2	538.0	554.9	578.7	619.3	681.7	774.5
55°	452.6	455.9	458.6	462.5	470.5	479.1	492.2	508.1	539.8	586.6	655.2
57.5°	398.6	399.6	402.3	409.7	414.7	422.7	435.2	449.6	470.2	504.9	556.5
60°	361.6	361.6	366.9	370.1	376.8	384.7	394.6	408.5	426.9	455.3	496.9
62.5°	327.8	327.3	329.4	334.8	339.8	347.2	357.1	368.9	386.2	411.5	445.7
65°	278.4	277.2	281.1	282.4	287.7	295.0	302.9	315.4	329.2	347.8	378.1
67.5°	230.9	232.6	234.6	237.1	240.0	247.7	253.0	261.8	273.5	288.9	309.4
70°	204.6	204.6	204.6	206.6	210.5	214.5	219.7	227.0	238.2	251.4	269.8
72.5°	175.0	177.1	179.2	178.1	183.0	185.4	191.7	195.9	206.6	215.0	231.4
75°	137.2	137.2	137.2	140.5	142.5	144.5	148.4	152.4	157.7	168.2	176.8
77.5°	102.4	102.1	102.8	103.6	105.7	108.1	109.3	112.8	117.7	122.6	129.8
80°	79.2	80.5	81.2	82.5	82.5	83.8	84.5	89.1	92.4	95.7	100.3
82.5°	61.2	61.5	61.6	61.9	62.4	63.2	64.9	66.4	67.6	70.3	73.9
85°	35.6	35.0	35.0	36.2	35.6	35.6	36.9	38.2	38.2	38.9	40.9
87.5°	22.6	22.5	23.0	22.4	22.3	22.9	23.0	22.6	23.2	23.8	23.2
90°	44.2	43.8	43.6	43.3	43.0	43.1	43.7	44.3	44.9	45.5	39.1
92.5°	42.0	42.0	41.9	41.8	41.8	41.8	41.6	41.5	41.4	41.2	39.8
95°	80.5	81.0	81.6	82.2	82.7	83.1	83.1	83.1	83.1	83.1	82.5
97.5°	139.4	139.5	139.5	139.6	139.7	139.7	139.7	139.7	139.7	139.7	138.5
100°	177.8	178.1	178.4	178.7	179.0	179.1	179.1	179.1	179.1	179.1	178.2
102.5°	221.4	221.7	222.1	222.3	222.6	222.7	222.4	222.1	222.0	221.7	220.6
105°	288.2	288.2	288.2	288.2	288.2	287.8	287.3	286.7	286.1	285.6	285.0
107.5°	350.9	352.3	353.6	355.0	356.3	356.8	356.6	356.4	356.1	355.9	355.9
110°	399.8	400.6	401.5	402.3	403.2	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P331610-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.5	447.1	447.8	448.4	449.0	449.7	450.4	451.1	451.8	452.5	452.7
115°	519.2	520.0	520.9	521.8	522.6	523.2	523.5	523.8	524.1	524.4	525.0
117.5°	588.5	589.4	590.2	591.1	591.9	592.8	593.5	594.2	594.9	595.6	597.1
120°	637.3	638.2	639.0	639.9	640.8	641.2	641.2	641.2	641.2	641.2	643.5
122.5°	685.1	685.7	686.4	687.0	687.6	688.3	689.0	689.7	690.3	691.0	692.7
125°	758.0	758.4	758.6	758.9	759.2	759.7	760.6	761.5	762.3	763.2	764.1
127.5°	824.5	825.4	826.3	827.2	828.2	829.1	830.2	831.2	832.2	833.4	834.4
130°	872.3	873.4	874.6	875.7	876.8	877.7	878.3	878.9	879.5	880.0	880.6
132.5°	917.9	918.9	919.8	920.8	921.6	922.7	924.0	925.3	926.5	927.8	927.7
135°	989.1	990.0	990.8	991.7	992.6	993.2	993.4	993.7	994.0	994.3	993.7
137.5°	1053.4	1054.6	1055.8	1057.0	1058.1	1058.8	1059.0	1059.2	1059.5	1059.7	1058.9
140°	1098.1	1099.2	1100.4	1101.6	1102.8	1103.3	1103.3	1103.3	1103.3	1103.3	1101.9
142.5°	1138.6	1139.8	1140.9	1142.1	1143.2	1143.7	1143.5	1143.2	1143.0	1142.8	1141.8
145°	1199.4	1200.5	1201.7	1202.8	1203.9	1204.4	1204.1	1203.9	1203.5	1203.2	1201.5
147.5°	1253.6	1254.7	1255.8	1256.9	1258.0	1258.3	1257.6	1257.0	1256.4	1255.7	1254.6
150°	1288.9	1289.8	1290.6	1291.5	1292.4	1292.4	1291.5	1290.6	1289.8	1288.9	1287.8
152.5°	1322.2	1323.3	1324.3	1325.4	1326.5	1326.5	1325.4	1324.3	1323.3	1322.2	1320.8
155°	1366.8	1367.7	1368.6	1369.4	1370.3	1369.9	1368.6	1367.1	1365.6	1364.2	1363.3
157.5°	1405.2	1406.6	1408.0	1409.4	1410.7	1410.5	1408.5	1406.5	1404.5	1402.7	1402.1
160°	1429.1	1430.3	1431.4	1432.5	1433.7	1433.4	1431.7	1429.9	1428.2	1426.5	1426.2
162.5°	1449.8	1451.3	1452.7	1454.1	1455.4	1455.1	1453.2	1451.2	1449.2	1447.3	1447.0
165°	1477.1	1478.6	1480.1	1481.4	1482.9	1482.6	1480.6	1478.6	1476.5	1474.5	1474.5
167.5°	1499.4	1501.0	1502.4	1504.0	1505.5	1505.2	1503.2	1501.2	1499.2	1497.1	1497.2
170°	1510.9	1512.6	1514.3	1516.0	1517.8	1517.7	1515.6	1513.6	1511.6	1509.6	1509.8
172.5°	1520.3	1522.0	1523.7	1525.4	1527.2	1527.0	1525.0	1522.9	1521.0	1518.9	1519.2
175°	1530.3	1532.1	1533.8	1535.5	1537.3	1537.1	1535.1	1533.1	1531.1	1529.0	1529.7
177.5°	1535.0	1536.4	1537.8	1539.2	1540.6	1540.6	1539.2	1537.8	1536.4	1535.0	1535.5
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331610-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1761.8	1757.6	1754.9	1745.4	1736.9	1728.5	1725.9	1726.9	1715.3	1704.2	1699.4
5°	1830.4	1817.1	1804.7	1786.8	1765.7	1742.6	1730.7	1721.5	1698.4	1673.4	1658.8
7.5°	1891.9	1873.0	1848.8	1815.3	1784.6	1748.3	1725.2	1704.7	1670.9	1635.6	1613.9
10°	1929.3	1903.6	1872.6	1831.7	1794.1	1749.9	1718.8	1687.8	1648.2	1606.0	1579.6
12.5°	1961.5	1926.8	1896.4	1843.8	1799.3	1744.0	1707.3	1663.5	1621.9	1571.7	1545.8
15°	2038.2	1974.2	1916.2	1856.7	1802.0	1724.8	1683.9	1625.1	1570.4	1508.4	1478.7
17.5°	2097.5	2025.5	1934.1	1858.6	1794.8	1709.3	1649.2	1578.8	1514.1	1443.2	1402.8
20°	2131.2	2048.7	1950.4	1860.7	1784.2	1686.5	1621.2	1549.3	1473.4	1393.5	1350.0
22.5°	2151.3	2064.6	1967.4	1852.8	1763.1	1668.0	1585.8	1507.0	1430.1	1343.9	1298.3
25°	2157.7	2078.5	1975.6	1846.2	1736.6	1629.1	1530.2	1453.6	1360.6	1280.0	1213.4
27.5°	2126.2	2069.5	1970.5	1833.8	1706.2	1580.5	1470.1	1383.4	1285.2	1197.8	1130.8
30°	2087.7	2054.7	1958.3	1821.1	1681.9	1546.6	1425.2	1326.9	1229.2	1140.8	1072.2
32.5°	2028.1	2020.9	1936.2	1803.2	1656.0	1503.9	1378.3	1278.8	1170.7	1083.8	1018.4
35°	1910.9	1942.5	1889.1	1763.1	1607.3	1443.0	1307.1	1193.6	1081.5	998.3	936.9
37.5°	1753.9	1832.5	1818.5	1704.3	1541.6	1376.8	1226.8	1108.1	1001.3	917.3	857.1
40°	1645.6	1745.9	1760.4	1659.5	1495.2	1325.6	1166.6	1048.4	944.2	867.7	806.9
42.5°	1529.5	1646.7	1686.5	1605.6	1444.5	1271.8	1112.8	990.4	887.2	812.8	759.0
45°	1334.8	1489.9	1561.9	1515.6	1359.9	1183.1	1019.4	895.4	801.7	731.8	690.2
47.5°	1152.9	1322.3	1419.0	1402.7	1265.8	1090.7	928.9	809.9	718.7	662.9	625.7
50°	1024.1	1198.3	1315.0	1320.3	1198.3	1024.7	862.4	750.2	666.4	614.3	583.9
52.5°	912.1	1078.4	1205.7	1233.7	1122.7	956.1	802.7	691.1	617.3	569.5	542.3
55°	766.0	906.6	1047.8	1099.2	1010.2	851.9	710.0	611.7	542.3	509.4	485.6
57.5°	636.9	754.1	884.4	941.3	886.4	750.9	617.9	532.4	476.3	447.4	429.1
60°	568.8	661.2	777.3	845.2	797.7	677.0	560.9	479.7	433.5	407.8	390.6
62.5°	505.4	587.3	685.4	747.6	721.7	607.9	503.9	432.2	392.4	368.2	355.8
65°	417.0	481.6	557.6	614.9	597.8	511.3	426.3	364.9	333.2	314.1	304.2
67.5°	343.4	390.1	442.7	493.0	479.1	417.9	349.6	301.8	278.2	261.7	255.7
70°	297.0	332.5	379.4	419.7	408.5	358.3	304.2	263.3	242.8	228.9	223.0
72.5°	252.6	281.9	317.6	350.5	342.9	301.3	256.1	225.2	209.6	196.7	191.9
75°	190.7	213.1	234.9	256.7	254.7	222.4	196.0	172.2	159.7	149.8	147.8
77.5°	140.8	153.3	168.2	181.1	177.5	159.0	138.3	124.7	115.5	108.8	107.8
80°	107.5	114.8	125.4	134.6	130.0	122.1	105.6	95.7	89.1	82.5	79.8
82.5°	78.0	85.2	91.6	96.6	93.1	85.7	75.5	68.8	64.8	60.3	59.2
85°	40.9	44.9	47.5	48.8	47.5	42.9	38.2	35.6	32.4	30.4	29.7
87.5°	22.4	21.1	19.8	19.9	17.7	17.0	14.1	11.9	12.1	12.2	11.8
90°	32.7	26.4	20.1	15.2	11.7	8.2	4.7	1.3	4.7	8.2	11.7
92.5°	38.3	36.8	35.3	33.2	30.7	28.2	25.7	23.1	25.7	28.2	30.7
95°	81.9	81.4	80.8	79.0	76.1	73.3	70.3	67.5	70.3	73.3	76.1
97.5°	137.5	136.4	135.3	133.5	131.0	128.4	125.9	123.3	125.9	128.4	131.0
100°	177.4	176.5	175.6	174.1	171.8	169.4	167.1	164.9	167.1	169.4	171.8
102.5°	219.5	218.4	217.3	215.9	214.0	212.2	210.3	208.4	210.3	212.2	214.0
105°	284.4	283.9	283.3	282.5	281.6	280.8	279.9	279.1	279.9	280.8	281.6
107.5°	355.9	355.9	355.9	355.2	354.0	352.8	351.5	350.2	351.5	352.8	354.0
110°	403.7	403.7	403.7	402.8	401.1	399.3	397.6	395.9	397.6	399.3	401.1





TEST NUMBER: P331610-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	453.0	453.1	453.4	452.6	450.9	449.2	447.5	445.7	447.5	449.2	450.9
115°	525.6	526.2	526.7	526.2	524.4	522.6	520.9	519.2	520.9	522.6	524.4
117.5°	598.7	600.4	602.0	601.7	599.3	597.0	594.7	592.5	594.7	597.0	599.3
120°	645.8	648.2	650.5	650.5	648.2	645.8	643.5	641.2	643.5	645.8	648.2
122.5°	694.3	695.9	697.5	697.0	694.1	691.4	688.6	685.9	688.6	691.4	694.1
125°	765.0	765.9	766.7	765.9	763.2	760.6	758.0	755.4	758.0	760.6	763.2
127.5°	835.4	836.5	837.5	836.4	833.1	829.7	826.5	823.2	826.5	829.7	833.1
130°	881.2	881.8	882.4	880.8	877.0	873.3	869.5	865.7	869.5	873.3	877.0
132.5°	927.6	927.5	927.4	925.7	922.7	919.6	916.6	913.5	916.6	919.6	922.7
135°	993.2	992.6	992.0	990.1	986.9	983.8	980.6	977.4	980.6	983.8	986.9
137.5°	1058.2	1057.5	1056.7	1055.0	1052.4	1049.8	1047.2	1044.7	1047.2	1049.8	1052.4
140°	1100.4	1099.0	1097.5	1095.5	1093.0	1090.4	1087.7	1085.1	1087.7	1090.4	1093.0
142.5°	1140.8	1139.8	1138.8	1137.0	1134.5	1131.9	1129.3	1126.7	1129.3	1131.9	1134.5
145°	1199.8	1198.1	1196.4	1194.5	1192.4	1190.4	1188.4	1186.4	1188.4	1190.4	1192.4
147.5°	1253.4	1252.2	1251.1	1249.3	1246.9	1244.4	1242.0	1239.6	1242.0	1244.4	1246.9
150°	1286.6	1285.5	1284.3	1282.9	1281.2	1279.4	1277.6	1275.9	1277.6	1279.4	1281.2
152.5°	1319.4	1318.0	1316.6	1315.1	1313.3	1311.6	1309.8	1308.1	1309.8	1311.6	1313.3
155°	1362.4	1361.6	1360.7	1359.9	1359.0	1358.1	1357.3	1356.4	1357.3	1358.1	1359.0
157.5°	1401.6	1401.1	1400.6	1400.0	1399.5	1398.9	1398.3	1397.7	1398.3	1398.9	1399.5
160°	1425.9	1425.6	1425.4	1425.0	1424.4	1423.7	1423.2	1422.6	1423.2	1423.7	1424.4
162.5°	1446.7	1446.4	1446.1	1446.0	1445.8	1445.7	1445.6	1445.4	1445.6	1445.7	1445.8
165°	1474.5	1474.5	1474.5	1474.7	1475.0	1475.2	1475.6	1475.8	1475.6	1475.2	1475.0
167.5°	1497.3	1497.3	1497.4	1497.8	1498.7	1499.5	1500.4	1501.2	1500.4	1499.5	1498.7
170°	1510.2	1510.5	1510.7	1511.3	1512.2	1513.0	1513.9	1514.8	1513.9	1513.0	1512.2
172.5°	1519.5	1519.8	1520.1	1520.7	1521.6	1522.4	1523.3	1524.1	1523.3	1522.4	1521.6
175°	1530.2	1530.8	1531.4	1532.1	1532.9	1533.8	1534.6	1535.5	1534.6	1533.8	1532.9
177.5°	1535.9	1536.4	1536.9	1537.5	1538.2	1538.9	1539.6	1540.2	1539.6	1538.9	1538.2
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331610-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1694.2	1691.0	1679.9	1674.1	1664.7	1655.6	1649.8	1652.5	1654.6	1653.6	1651.9
5°	1645.6	1633.1	1613.9	1597.4	1585.5	1563.8	1554.5	1550.0	1546.0	1541.4	1536.7
7.5°	1587.8	1568.1	1540.6	1517.1	1494.9	1467.8	1452.4	1443.2	1433.7	1423.2	1414.0
10°	1546.6	1518.9	1489.9	1456.9	1430.6	1406.1	1384.3	1369.8	1356.6	1344.1	1334.8
12.5°	1503.4	1471.4	1435.5	1390.4	1361.3	1326.4	1323.1	1297.5	1276.9	1269.1	1258.3
15°	1434.4	1389.6	1344.1	1290.6	1267.6	1235.9	1216.1	1196.3	1178.5	1165.9	1162.6
17.5°	1356.2	1298.1	1252.8	1214.4	1176.6	1144.2	1125.9	1110.1	1095.5	1078.7	1076.4
20°	1296.6	1246.4	1197.0	1163.3	1124.4	1091.3	1068.9	1053.1	1040.5	1030.6	1022.1
22.5°	1240.1	1185.2	1139.9	1103.1	1064.7	1038.0	1020.4	1005.0	994.6	983.7	975.6
25°	1149.4	1106.6	1057.0	1015.5	983.8	966.6	952.1	938.9	932.4	925.1	915.8
27.5°	1070.1	1022.4	976.1	943.9	916.1	901.0	890.6	881.7	875.5	871.2	866.0
30°	1014.2	966.0	929.7	898.0	874.9	859.8	853.2	847.9	840.6	838.0	835.3
32.5°	960.3	916.9	885.9	858.4	836.4	826.5	820.4	815.7	810.0	807.4	802.1
35°	884.2	847.9	817.5	802.4	784.5	775.9	771.4	764.7	759.5	756.8	756.1
37.5°	812.5	781.0	761.0	741.5	734.0	728.8	722.4	717.9	716.4	715.9	715.2
40°	766.0	740.3	722.6	706.7	703.4	695.4	690.2	686.2	686.2	686.9	686.2
42.5°	723.8	700.8	685.0	671.3	667.4	662.7	657.5	657.2	658.2	660.5	658.2
45°	659.9	643.3	632.1	625.5	618.3	613.6	612.9	614.9	615.6	616.3	618.3
47.5°	601.0	590.0	579.9	572.6	569.5	568.6	567.8	571.3	574.5	575.7	578.7
50°	566.1	553.6	545.0	540.4	537.8	536.4	537.8	541.7	544.3	547.7	549.7
52.5°	527.1	518.2	512.3	508.8	507.6	508.5	508.8	513.2	517.5	518.7	519.5
55°	473.1	466.5	465.2	459.3	461.8	461.2	464.5	467.2	471.1	475.1	475.7
57.5°	419.2	414.0	410.4	411.0	411.7	414.7	417.4	422.1	426.3	430.5	430.8
60°	383.4	380.7	378.8	378.8	380.0	384.0	387.3	391.9	394.6	397.2	399.2
62.5°	350.6	348.0	346.0	347.1	350.5	352.8	356.7	359.2	361.9	364.5	365.4
65°	298.9	297.6	299.5	300.9	301.5	304.9	309.4	311.4	314.1	315.4	320.0
67.5°	251.2	251.5	251.2	253.1	256.9	257.7	262.1	266.7	267.3	269.8	272.8
70°	219.0	220.4	221.7	223.0	226.4	227.6	230.9	232.9	235.6	237.5	239.5
72.5°	189.5	189.8	191.1	190.8	193.6	196.5	199.2	201.2	203.9	206.4	208.4
75°	145.9	145.9	147.1	147.8	151.1	154.4	153.8	155.1	157.7	160.3	161.7
77.5°	106.5	105.0	106.5	107.2	108.2	111.0	111.5	113.4	116.4	115.5	116.9
80°	81.2	79.2	81.2	81.8	81.8	85.2	85.2	86.4	88.4	86.4	88.4
82.5°	57.9	57.0	58.5	58.6	59.7	59.8	60.9	61.1	63.1	62.2	63.1
85°	29.0	28.4	29.0	28.4	29.0	29.7	29.7	29.0	29.0	30.4	28.4
87.5°	12.0	12.5	13.2	14.5	15.2	15.9	15.3	15.2	15.1	13.9	13.9
90°	15.2	20.1	26.4	32.7	39.1	45.5	44.9	44.3	43.7	43.1	43.0
92.5°	33.2	35.3	36.8	38.3	39.8	41.2	41.4	41.5	41.6	41.8	41.8
95°	79.0	80.8	81.4	81.9	82.5	83.1	83.1	83.1	83.1	83.1	82.7
97.5°	133.5	135.3	136.4	137.5	138.5	139.7	139.7	139.7	139.7	139.7	139.7
100°	174.1	175.6	176.5	177.4	178.2	179.1	179.1	179.1	179.1	179.1	179.0
102.5°	215.9	217.3	218.4	219.5	220.6	221.7	222.0	222.1	222.4	222.7	222.6
105°	282.5	283.3	283.9	284.4	285.0	285.6	286.1	286.7	287.3	287.8	288.2
107.5°	355.2	355.9	355.9	355.9	355.9	355.9	356.1	356.4	356.6	356.8	356.3
110°	402.8	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.2



TEST NUMBER: P331610-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	452.6	453.4	453.1	453.0	452.7	452.5	451.8	451.1	450.4	449.7	449.0
115°	526.2	526.7	526.2	525.6	525.0	524.4	524.1	523.8	523.5	523.2	522.6
117.5°	601.7	602.0	600.4	598.7	597.1	595.6	594.9	594.2	593.5	592.8	591.9
120°	650.5	650.5	648.2	645.8	643.5	641.2	641.2	641.2	641.2	641.2	640.8
122.5°	697.0	697.5	695.9	694.3	692.7	691.0	690.3	689.7	689.0	688.3	687.6
125°	765.9	766.7	765.9	765.0	764.1	763.2	762.3	761.5	760.6	759.7	759.2
127.5°	836.4	837.5	836.5	835.4	834.4	833.4	832.2	831.2	830.2	829.1	828.2
130°	880.8	882.4	881.8	881.2	880.6	880.0	879.5	878.9	878.3	877.7	876.8
132.5°	925.7	927.4	927.5	927.6	927.7	927.8	926.5	925.3	924.0	922.7	921.6
135°	990.1	992.0	992.6	993.2	993.7	994.3	994.0	993.7	993.4	993.2	992.6
137.5°	1055.0	1056.7	1057.5	1058.2	1058.9	1059.7	1059.5	1059.2	1059.0	1058.8	1058.1
140°	1095.5	1097.5	1099.0	1100.4	1101.9	1103.3	1103.3	1103.3	1103.3	1103.3	1102.8
142.5°	1137.0	1138.8	1139.8	1140.8	1141.8	1142.8	1143.0	1143.2	1143.5	1143.7	1143.2
145°	1194.5	1196.4	1198.1	1199.8	1201.5	1203.2	1203.5	1203.9	1204.1	1204.4	1203.9
147.5°	1249.3	1251.1	1252.2	1253.4	1254.6	1255.7	1256.4	1257.0	1257.6	1258.3	1258.0
150°	1282.9	1284.3	1285.5	1286.6	1287.8	1288.9	1289.8	1290.6	1291.5	1292.4	1292.4
152.5°	1315.1	1316.6	1318.0	1319.4	1320.8	1322.2	1323.3	1324.3	1325.4	1326.5	1326.5
155°	1359.9	1360.7	1361.6	1362.4	1363.3	1364.2	1365.6	1367.1	1368.6	1369.9	1370.3
157.5°	1400.0	1400.6	1401.1	1401.6	1402.1	1402.7	1404.5	1406.5	1408.5	1410.5	1410.7
160°	1425.0	1425.4	1425.6	1425.9	1426.2	1426.5	1428.2	1429.9	1431.7	1433.4	1433.7
162.5°	1446.0	1446.1	1446.4	1446.7	1447.0	1447.3	1449.2	1451.2	1453.2	1455.1	1455.4
165°	1474.7	1474.5	1474.5	1474.5	1474.5	1474.5	1476.5	1478.6	1480.6	1482.6	1482.9
167.5°	1497.8	1497.4	1497.3	1497.3	1497.2	1497.1	1499.2	1501.2	1503.2	1505.2	1505.5
170°	1511.3	1510.7	1510.5	1510.2	1509.8	1509.6	1511.6	1513.6	1515.6	1517.7	1517.8
172.5°	1520.7	1520.1	1519.8	1519.5	1519.2	1518.9	1521.0	1522.9	1525.0	1527.0	1527.2
175°	1532.1	1531.4	1530.8	1530.2	1529.7	1529.0	1531.1	1533.1	1535.1	1537.1	1537.3
177.5°	1537.5	1536.9	1536.4	1535.9	1535.5	1535.0	1536.4	1537.8	1539.2	1540.6	1540.6
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331610-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1646.7	1645.6	1645.6	1640.9	1645.6	1645.6	1646.7	1651.9	1653.6	1654.6	1652.5
5°	1527.5	1525.5	1522.2	1525.5	1522.2	1525.5	1527.5	1536.7	1541.4	1546.0	1550.0
7.5°	1409.6	1401.7	1400.6	1392.8	1400.6	1401.7	1409.6	1414.0	1423.2	1433.7	1443.2
10°	1323.6	1318.4	1317.7	1305.1	1317.7	1318.4	1323.6	1334.8	1344.1	1356.6	1369.8
12.5°	1258.2	1245.5	1248.0	1240.7	1248.0	1245.5	1258.2	1258.3	1269.1	1276.9	1297.5
15°	1144.8	1144.8	1142.2	1130.9	1142.2	1144.8	1144.8	1162.6	1165.9	1178.5	1196.3
17.5°	1063.4	1062.0	1055.8	1058.9	1055.8	1062.0	1063.4	1076.4	1078.7	1095.5	1110.1
20°	1014.8	1010.9	1003.0	1003.0	1003.0	1010.9	1014.8	1022.1	1030.6	1040.5	1053.1
22.5°	968.9	968.6	960.2	962.9	960.2	968.6	968.9	975.6	983.7	994.6	1005.0
25°	915.2	909.9	905.9	907.9	905.9	909.9	915.2	915.8	925.1	932.4	938.9
27.5°	864.3	861.3	861.1	855.7	861.1	861.3	864.3	866.0	871.2	875.5	881.7
30°	834.7	828.1	829.4	826.1	829.4	828.1	834.7	835.3	838.0	840.6	847.9
32.5°	800.9	798.5	797.2	794.4	797.2	798.5	800.9	802.1	807.4	810.0	815.7
35°	754.8	755.5	752.2	753.5	752.2	755.5	754.8	756.1	756.8	759.5	764.7
37.5°	714.6	716.7	715.1	715.5	715.1	716.7	714.6	715.2	715.9	716.4	717.9
40°	688.2	688.2	688.2	690.2	688.2	688.2	688.2	686.2	686.9	686.2	686.2
42.5°	662.9	661.9	660.7	660.6	660.7	661.9	662.9	658.2	660.5	658.2	657.2
45°	619.6	621.6	622.2	618.9	622.2	621.6	619.6	618.3	616.3	615.6	614.9
47.5°	580.4	580.7	580.4	583.3	580.4	580.7	580.4	578.7	575.7	574.5	571.3
50°	552.9	551.6	552.9	551.6	552.9	551.6	552.9	549.7	547.7	544.3	541.7
52.5°	523.9	524.2	523.4	523.1	523.4	524.2	523.9	519.5	518.7	517.5	513.2
55°	478.4	479.7	479.1	479.1	479.1	479.7	478.4	475.7	475.1	471.1	467.2
57.5°	431.3	432.5	433.3	430.5	433.3	432.5	431.3	430.8	430.5	426.3	422.1
60°	398.6	401.8	401.1	399.8	401.1	401.8	398.6	399.2	397.2	394.6	391.9
62.5°	368.4	369.6	369.5	369.3	369.5	369.6	368.4	365.4	364.5	361.9	359.2
65°	322.0	323.3	321.3	323.3	321.3	323.3	322.0	320.0	315.4	314.1	311.4
67.5°	272.0	272.4	273.8	274.7	273.8	272.4	272.0	272.8	269.8	267.3	266.7
70°	240.8	240.2	242.2	244.2	242.2	240.2	240.8	239.5	237.5	235.6	232.9
72.5°	208.1	209.6	208.9	210.3	208.9	209.6	208.1	208.4	206.4	203.9	201.2
75°	160.3	162.3	161.7	163.7	161.7	162.3	160.3	161.7	160.3	157.7	155.1
77.5°	115.9	116.1	115.9	116.9	115.9	116.1	115.9	116.9	115.5	116.4	113.4
80°	88.4	87.1	85.8	88.4	85.8	87.1	88.4	88.4	86.4	88.4	86.4
82.5°	61.5	62.3	61.0	61.0	61.0	62.3	61.5	63.1	62.2	63.1	61.1
85°	28.4	27.7	26.4	26.4	26.4	27.7	28.4	28.4	30.4	29.0	29.0
87.5°	13.9	13.4	13.5	13.1	13.5	13.4	13.9	13.9	13.9	15.1	15.2
90°	43.3	43.6	43.8	44.2	43.8	43.6	43.3	43.0	43.1	43.7	44.3
92.5°	41.8	41.9	42.0	42.0	42.0	41.9	41.8	41.8	41.8	41.6	41.5
95°	82.2	81.6	81.0	80.5	81.0	81.6	82.2	82.7	83.1	83.1	83.1
97.5°	139.6	139.5	139.5	139.4	139.5	139.5	139.6	139.7	139.7	139.7	139.7
100°	178.7	178.4	178.1	177.8	178.1	178.4	178.7	179.0	179.1	179.1	179.1
102.5°	222.3	222.1	221.7	221.4	221.7	222.1	222.3	222.6	222.7	222.4	222.1
105°	288.2	288.2	288.2	288.2	288.2	288.2	288.2	288.2	287.8	287.3	286.7
107.5°	355.0	353.6	352.3	350.9	352.3	353.6	355.0	356.3	356.8	356.6	356.4
110°	402.3	401.5	400.6	399.8	400.6	401.5	402.3	403.2	403.7	403.7	403.7



TEST NUMBER: P331610-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	448.4	447.8	447.1	446.5	447.1	447.8	448.4	449.0	449.7	450.4	451.1
115°	521.8	520.9	520.0	519.2	520.0	520.9	521.8	522.6	523.2	523.5	523.8
117.5°	591.1	590.2	589.4	588.5	589.4	590.2	591.1	591.9	592.8	593.5	594.2
120°	639.9	639.0	638.2	637.3	638.2	639.0	639.9	640.8	641.2	641.2	641.2
122.5°	687.0	686.4	685.7	685.1	685.7	686.4	687.0	687.6	688.3	689.0	689.7
125°	758.9	758.6	758.4	758.0	758.4	758.6	758.9	759.2	759.7	760.6	761.5
127.5°	827.2	826.3	825.4	824.5	825.4	826.3	827.2	828.2	829.1	830.2	831.2
130°	875.7	874.6	873.4	872.3	873.4	874.6	875.7	876.8	877.7	878.3	878.9
132.5°	920.8	919.8	918.9	917.9	918.9	919.8	920.8	921.6	922.7	924.0	925.3
135°	991.7	990.8	990.0	989.1	990.0	990.8	991.7	992.6	993.2	993.4	993.7
137.5°	1057.0	1055.8	1054.6	1053.4	1054.6	1055.8	1057.0	1058.1	1058.8	1059.0	1059.2
140°	1101.6	1100.4	1099.2	1098.1	1099.2	1100.4	1101.6	1102.8	1103.3	1103.3	1103.3
142.5°	1142.1	1140.9	1139.8	1138.6	1139.8	1140.9	1142.1	1143.2	1143.7	1143.5	1143.2
145°	1202.8	1201.7	1200.5	1199.4	1200.5	1201.7	1202.8	1203.9	1204.4	1204.1	1203.9
147.5°	1256.9	1255.8	1254.7	1253.6	1254.7	1255.8	1256.9	1258.0	1258.3	1257.6	1257.0
150°	1291.5	1290.6	1289.8	1288.9	1289.8	1290.6	1291.5	1292.4	1292.4	1291.5	1290.6
152.5°	1325.4	1324.3	1323.3	1322.2	1323.3	1324.3	1325.4	1326.5	1326.5	1325.4	1324.3
155°	1369.4	1368.6	1367.7	1366.8	1367.7	1368.6	1369.4	1370.3	1369.9	1368.6	1367.1
157.5°	1409.4	1408.0	1406.6	1405.2	1406.6	1408.0	1409.4	1410.7	1410.5	1408.5	1406.5
160°	1432.5	1431.4	1430.3	1429.1	1430.3	1431.4	1432.5	1433.7	1433.4	1431.7	1429.9
162.5°	1454.1	1452.7	1451.3	1449.8	1451.3	1452.7	1454.1	1455.4	1455.1	1453.2	1451.2
165°	1481.4	1480.1	1478.6	1477.1	1478.6	1480.1	1481.4	1482.9	1482.6	1480.6	1478.6
167.5°	1504.0	1502.4	1501.0	1499.4	1501.0	1502.4	1504.0	1505.5	1505.2	1503.2	1501.2
170°	1516.0	1514.3	1512.6	1510.9	1512.6	1514.3	1516.0	1517.8	1517.7	1515.6	1513.6
172.5°	1525.4	1523.7	1522.0	1520.3	1522.0	1523.7	1525.4	1527.2	1527.0	1525.0	1522.9
175°	1535.5	1533.8	1532.1	1530.3	1532.1	1533.8	1535.5	1537.3	1537.1	1535.1	1533.1
177.5°	1539.2	1537.8	1536.4	1535.0	1536.4	1537.8	1539.2	1540.6	1540.6	1539.2	1537.8
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331610-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1649.8	1655.6	1664.7	1674.1	1679.9	1691.0	1694.2	1699.4	1704.2	1715.3	1726.9
5°	1554.5	1563.8	1585.5	1597.4	1613.9	1633.1	1645.6	1658.8	1673.4	1698.4	1721.5
7.5°	1452.4	1467.8	1494.9	1517.1	1540.6	1568.1	1587.8	1613.9	1635.6	1670.9	1704.7
10°	1384.3	1406.1	1430.6	1456.9	1489.9	1518.9	1546.6	1579.6	1606.0	1648.2	1687.8
12.5°	1323.1	1326.4	1361.3	1390.4	1435.5	1471.4	1503.4	1545.8	1571.7	1621.9	1663.5
15°	1216.1	1235.9	1267.6	1290.6	1344.1	1389.6	1434.4	1478.7	1508.4	1570.4	1625.1
17.5°	1125.9	1144.2	1176.6	1214.4	1252.8	1298.1	1356.2	1402.8	1443.2	1514.1	1578.8
20°	1068.9	1091.3	1124.4	1163.3	1197.0	1246.4	1296.6	1350.0	1393.5	1473.4	1549.3
22.5°	1020.4	1038.0	1064.7	1103.1	1139.9	1185.2	1240.1	1298.3	1343.9	1430.1	1507.0
25°	952.1	966.6	983.8	1015.5	1057.0	1106.6	1149.4	1213.4	1280.0	1360.6	1453.6
27.5°	890.6	901.0	916.1	943.9	976.1	1022.4	1070.1	1130.8	1197.8	1285.2	1383.4
30°	853.2	859.8	874.9	898.0	929.7	966.0	1014.2	1072.2	1140.8	1229.2	1326.9
32.5°	820.4	826.5	836.4	858.4	885.9	916.9	960.3	1018.4	1083.8	1170.7	1278.8
35°	771.4	775.9	784.5	802.4	817.5	847.9	884.2	936.9	998.3	1081.5	1193.6
37.5°	722.4	728.8	734.0	741.5	761.0	781.0	812.5	857.1	917.3	1001.3	1108.1
40°	690.2	695.4	703.4	706.7	722.6	740.3	766.0	806.9	867.7	944.2	1048.4
42.5°	657.5	662.7	667.4	671.3	685.0	700.8	723.8	759.0	812.8	887.2	990.4
45°	612.9	613.6	618.3	625.5	632.1	643.3	659.9	690.2	731.8	801.7	895.4
47.5°	567.8	568.6	569.5	572.6	579.9	590.0	601.0	625.7	662.9	718.7	809.9
50°	537.8	536.4	537.8	540.4	545.0	553.6	566.1	583.9	614.3	666.4	750.2
52.5°	508.8	508.5	507.6	508.8	512.3	518.2	527.1	542.3	569.5	617.3	691.1
55°	464.5	461.2	461.8	459.3	465.2	466.5	473.1	485.6	509.4	542.3	611.7
57.5°	417.4	414.7	411.7	411.0	410.4	414.0	419.2	429.1	447.4	476.3	532.4
60°	387.3	384.0	380.0	378.8	378.8	380.7	383.4	390.6	407.8	433.5	479.7
62.5°	356.7	352.8	350.5	347.1	346.0	348.0	350.6	355.8	368.2	392.4	432.2
65°	309.4	304.9	301.5	300.9	299.5	297.6	298.9	304.2	314.1	333.2	364.9
67.5°	262.1	257.7	256.9	253.1	251.2	251.5	251.2	255.7	261.7	278.2	301.8
70°	230.9	227.6	226.4	223.0	221.7	220.4	219.0	223.0	228.9	242.8	263.3
72.5°	199.2	196.5	193.6	190.8	191.1	189.8	189.5	191.9	196.7	209.6	225.2
75°	153.8	154.4	151.1	147.8	147.1	145.9	145.9	147.8	149.8	159.7	172.2
77.5°	111.5	111.0	108.2	107.2	106.5	105.0	106.5	107.8	108.8	115.5	124.7
80°	85.2	85.2	81.8	81.8	81.2	79.2	81.2	79.8	82.5	89.1	95.7
82.5°	60.9	59.8	59.7	58.6	58.5	57.0	57.9	59.2	60.3	64.8	68.8
85°	29.7	29.7	29.0	28.4	29.0	28.4	29.0	29.7	30.4	32.4	35.6
87.5°	15.3	15.9	15.2	14.5	13.2	12.5	12.0	11.8	12.2	12.1	11.9
90°	44.9	45.5	39.1	32.7	26.4	20.1	15.2	11.7	8.2	4.7	1.3
92.5°	41.4	41.2	39.8	38.3	36.8	35.3	33.2	30.7	28.2	25.7	23.1
95°	83.1	83.1	82.5	81.9	81.4	80.8	79.0	76.1	73.3	70.3	67.5
97.5°	139.7	139.7	138.5	137.5	136.4	135.3	133.5	131.0	128.4	125.9	123.3
100°	179.1	179.1	178.2	177.4	176.5	175.6	174.1	171.8	169.4	167.1	164.9
102.5°	222.0	221.7	220.6	219.5	218.4	217.3	215.9	214.0	212.2	210.3	208.4
105°	286.1	285.6	285.0	284.4	283.9	283.3	282.5	281.6	280.8	279.9	279.1
107.5°	356.1	355.9	355.9	355.9	355.9	355.9	355.2	354.0	352.8	351.5	350.2
110°	403.7	403.7	403.7	403.7	403.7	403.7	402.8	401.1	399.3	397.6	395.9



TEST NUMBER: P331610-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	451.8	452.5	452.7	453.0	453.1	453.4	452.6	450.9	449.2	447.5	445.7
115°	524.1	524.4	525.0	525.6	526.2	526.7	526.2	524.4	522.6	520.9	519.2
117.5°	594.9	595.6	597.1	598.7	600.4	602.0	601.7	599.3	597.0	594.7	592.5
120°	641.2	641.2	643.5	645.8	648.2	650.5	650.5	648.2	645.8	643.5	641.2
122.5°	690.3	691.0	692.7	694.3	695.9	697.5	697.0	694.1	691.4	688.6	685.9
125°	762.3	763.2	764.1	765.0	765.9	766.7	765.9	763.2	760.6	758.0	755.4
127.5°	832.2	833.4	834.4	835.4	836.5	837.5	836.4	833.1	829.7	826.5	823.2
130°	879.5	880.0	880.6	881.2	881.8	882.4	880.8	877.0	873.3	869.5	865.7
132.5°	926.5	927.8	927.7	927.6	927.5	927.4	925.7	922.7	919.6	916.6	913.5
135°	994.0	994.3	993.7	993.2	992.6	992.0	990.1	986.9	983.8	980.6	977.4
137.5°	1059.5	1059.7	1058.9	1058.2	1057.5	1056.7	1055.0	1052.4	1049.8	1047.2	1044.7
140°	1103.3	1103.3	1101.9	1100.4	1099.0	1097.5	1095.5	1093.0	1090.4	1087.7	1085.1
142.5°	1143.0	1142.8	1141.8	1140.8	1139.8	1138.8	1137.0	1134.5	1131.9	1129.3	1126.7
145°	1203.5	1203.2	1201.5	1199.8	1198.1	1196.4	1194.5	1192.4	1190.4	1188.4	1186.4
147.5°	1256.4	1255.7	1254.6	1253.4	1252.2	1251.1	1249.3	1246.9	1244.4	1242.0	1239.6
150°	1289.8	1288.9	1287.8	1286.6	1285.5	1284.3	1282.9	1281.2	1279.4	1277.6	1275.9
152.5°	1323.3	1322.2	1320.8	1319.4	1318.0	1316.6	1315.1	1313.3	1311.6	1309.8	1308.1
155°	1365.6	1364.2	1363.3	1362.4	1361.6	1360.7	1359.9	1359.0	1358.1	1357.3	1356.4
157.5°	1404.5	1402.7	1402.1	1401.6	1401.1	1400.6	1400.0	1399.5	1398.9	1398.3	1397.7
160°	1428.2	1426.5	1426.2	1425.9	1425.6	1425.4	1425.0	1424.4	1423.7	1423.2	1422.6
162.5°	1449.2	1447.3	1447.0	1446.7	1446.4	1446.1	1446.0	1445.8	1445.7	1445.6	1445.4
165°	1476.5	1474.5	1474.5	1474.5	1474.5	1474.5	1474.7	1475.0	1475.2	1475.6	1475.8
167.5°	1499.2	1497.1	1497.2	1497.3	1497.3	1497.4	1497.8	1498.7	1499.5	1500.4	1501.2
170°	1511.6	1509.6	1509.8	1510.2	1510.5	1510.7	1511.3	1512.2	1513.0	1513.9	1514.8
172.5°	1521.0	1518.9	1519.2	1519.5	1519.8	1520.1	1520.7	1521.6	1522.4	1523.3	1524.1
175°	1531.1	1529.0	1529.7	1530.2	1530.8	1531.4	1532.1	1532.9	1533.8	1534.6	1535.5
177.5°	1536.4	1535.0	1535.5	1535.9	1536.4	1536.9	1537.5	1538.2	1538.9	1539.6	1540.2
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331610-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1725.9	1728.5	1736.9	1745.4	1754.9	1757.6	1761.8	1758.1	1757.0	1767.0	1774.4
5°	1730.7	1742.6	1765.7	1786.8	1804.7	1817.1	1830.4	1835.7	1845.6	1859.4	1876.5
7.5°	1725.2	1748.3	1784.6	1815.3	1848.8	1873.0	1891.9	1908.0	1927.5	1953.8	1982.4
10°	1718.8	1749.9	1794.1	1831.7	1872.6	1903.6	1929.3	1954.4	1983.5	2019.7	2057.4
12.5°	1707.3	1744.0	1799.3	1843.8	1896.4	1926.8	1961.5	2015.7	2046.8	2097.3	2150.3
15°	1683.9	1724.8	1802.0	1856.7	1916.2	1974.2	2038.2	2089.6	2141.1	2170.8	2245.4
17.5°	1649.2	1709.3	1794.8	1858.6	1934.1	2025.5	2097.5	2155.8	2215.2	2263.3	2300.7
20°	1621.2	1686.5	1784.2	1860.7	1950.4	2048.7	2131.2	2190.6	2242.1	2282.3	2305.4
22.5°	1585.8	1668.0	1763.1	1852.8	1967.4	2064.6	2151.3	2198.0	2241.0	2260.7	2269.5
25°	1530.2	1629.1	1736.6	1846.2	1975.6	2078.5	2157.7	2186.0	2198.6	2179.4	2147.8
27.5°	1470.1	1580.5	1706.2	1833.8	1970.5	2069.5	2126.2	2121.8	2100.5	2038.6	1989.1
30°	1425.2	1546.6	1681.9	1821.1	1958.3	2054.7	2087.7	2054.7	2006.6	1937.2	1866.6
32.5°	1378.3	1503.9	1656.0	1803.2	1936.2	2020.9	2028.1	1971.3	1896.8	1818.0	1729.9
35°	1307.1	1443.0	1607.3	1763.1	1889.1	1942.5	1910.9	1810.6	1722.2	1614.6	1494.5
37.5°	1226.8	1376.8	1541.6	1704.3	1818.5	1832.5	1753.9	1648.2	1523.5	1397.1	1255.8
40°	1166.6	1325.6	1495.2	1659.5	1760.4	1745.9	1645.6	1529.5	1381.0	1226.6	1095.3
42.5°	1112.8	1271.8	1444.5	1605.6	1686.5	1646.7	1529.5	1387.0	1227.4	1082.0	961.7
45°	1019.4	1183.1	1359.9	1515.6	1561.9	1489.9	1334.8	1176.5	1019.4	898.0	803.1
47.5°	928.9	1090.7	1265.8	1402.7	1419.0	1322.3	1152.9	989.9	854.9	756.0	689.0
50°	862.4	1024.7	1198.3	1320.3	1315.0	1198.3	1024.1	869.0	756.1	676.3	631.5
52.5°	802.7	956.1	1122.7	1233.7	1205.7	1078.4	912.1	774.5	681.7	619.3	578.7
55°	710.0	851.9	1010.2	1099.2	1047.8	906.6	766.0	655.2	586.6	539.8	508.1
57.5°	617.9	750.9	886.4	941.3	884.4	754.1	636.9	556.5	504.9	470.2	449.6
60°	560.9	677.0	797.7	845.2	777.3	661.2	568.8	496.9	455.3	426.9	408.5
62.5°	503.9	607.9	721.7	747.6	685.4	587.3	505.4	445.7	411.5	386.2	368.9
65°	426.3	511.3	597.8	614.9	557.6	481.6	417.0	378.1	347.8	329.2	315.4
67.5°	349.6	417.9	479.1	493.0	442.7	390.1	343.4	309.4	288.9	273.5	261.8
70°	304.2	358.3	408.5	419.7	379.4	332.5	297.0	269.8	251.4	238.2	227.0
72.5°	256.1	301.3	342.9	350.5	317.6	281.9	252.6	231.4	215.0	206.6	195.9
75°	196.0	222.4	254.7	256.7	234.9	213.1	190.7	176.8	168.2	157.7	152.4
77.5°	138.3	159.0	177.5	181.1	168.2	153.3	140.8	129.8	122.6	117.7	112.8
80°	105.6	122.1	130.0	134.6	125.4	114.8	107.5	100.3	95.7	92.4	89.1
82.5°	75.5	85.7	93.1	96.6	91.6	85.2	78.0	73.9	70.3	67.6	66.4
85°	38.2	42.9	47.5	48.8	47.5	44.9	40.9	40.9	38.9	38.2	38.2
87.5°	14.1	17.0	17.7	19.9	19.8	21.1	22.4	23.2	23.8	23.2	22.6
90°	4.7	8.2	11.7	15.2	20.1	26.4	32.7	39.1	45.5	44.9	44.3
92.5°	25.7	28.2	30.7	33.2	35.3	36.8	38.3	39.8	41.2	41.4	41.5
95°	70.3	73.3	76.1	79.0	80.8	81.4	81.9	82.5	83.1	83.1	83.1
97.5°	125.9	128.4	131.0	133.5	135.3	136.4	137.5	138.5	139.7	139.7	139.7
100°	167.1	169.4	171.8	174.1	175.6	176.5	177.4	178.2	179.1	179.1	179.1
102.5°	210.3	212.2	214.0	215.9	217.3	218.4	219.5	220.6	221.7	222.0	222.1
105°	279.9	280.8	281.6	282.5	283.3	283.9	284.4	285.0	285.6	286.1	286.7
107.5°	351.5	352.8	354.0	355.2	355.9	355.9	355.9	355.9	355.9	356.1	356.4
110°	397.6	399.3	401.1	402.8	403.7	403.7	403.7	403.7	403.7	403.7	403.7





TEST NUMBER: P331610-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	447.5	449.2	450.9	452.6	453.4	453.1	453.0	452.7	452.5	451.8	451.1
115°	520.9	522.6	524.4	526.2	526.7	526.2	525.6	525.0	524.4	524.1	523.8
117.5°	594.7	597.0	599.3	601.7	602.0	600.4	598.7	597.1	595.6	594.9	594.2
120°	643.5	645.8	648.2	650.5	650.5	648.2	645.8	643.5	641.2	641.2	641.2
122.5°	688.6	691.4	694.1	697.0	697.5	695.9	694.3	692.7	691.0	690.3	689.7
125°	758.0	760.6	763.2	765.9	766.7	765.9	765.0	764.1	763.2	762.3	761.5
127.5°	826.5	829.7	833.1	836.4	837.5	836.5	835.4	834.4	833.4	832.2	831.2
130°	869.5	873.3	877.0	880.8	882.4	881.8	881.2	880.6	880.0	879.5	878.9
132.5°	916.6	919.6	922.7	925.7	927.4	927.5	927.6	927.7	927.8	926.5	925.3
135°	980.6	983.8	986.9	990.1	992.0	992.6	993.2	993.7	994.3	994.0	993.7
137.5°	1047.2	1049.8	1052.4	1055.0	1056.7	1057.5	1058.2	1058.9	1059.7	1059.5	1059.2
140°	1087.7	1090.4	1093.0	1095.5	1097.5	1099.0	1100.4	1101.9	1103.3	1103.3	1103.3
142.5°	1129.3	1131.9	1134.5	1137.0	1138.8	1139.8	1140.8	1141.8	1142.8	1143.0	1143.2
145°	1188.4	1190.4	1192.4	1194.5	1196.4	1198.1	1199.8	1201.5	1203.2	1203.5	1203.9
147.5°	1242.0	1244.4	1246.9	1249.3	1251.1	1252.2	1253.4	1254.6	1255.7	1256.4	1257.0
150°	1277.6	1279.4	1281.2	1282.9	1284.3	1285.5	1286.6	1287.8	1288.9	1289.8	1290.6
152.5°	1309.8	1311.6	1313.3	1315.1	1316.6	1318.0	1319.4	1320.8	1322.2	1323.3	1324.3
155°	1357.3	1358.1	1359.0	1359.9	1360.7	1361.6	1362.4	1363.3	1364.2	1365.6	1367.1
157.5°	1398.3	1398.9	1399.5	1400.0	1400.6	1401.1	1401.6	1402.1	1402.7	1404.5	1406.5
160°	1423.2	1423.7	1424.4	1425.0	1425.4	1425.6	1425.9	1426.2	1426.5	1428.2	1429.9
162.5°	1445.6	1445.7	1445.8	1446.0	1446.1	1446.4	1446.7	1447.0	1447.3	1449.2	1451.2
165°	1475.6	1475.2	1475.0	1474.7	1474.5	1474.5	1474.5	1474.5	1474.5	1476.5	1478.6
167.5°	1500.4	1499.5	1498.7	1497.8	1497.4	1497.3	1497.3	1497.2	1497.1	1499.2	1501.2
170°	1513.9	1513.0	1512.2	1511.3	1510.7	1510.5	1510.2	1509.8	1509.6	1511.6	1513.6
172.5°	1523.3	1522.4	1521.6	1520.7	1520.1	1519.8	1519.5	1519.2	1518.9	1521.0	1522.9
175°	1534.6	1533.8	1532.9	1532.1	1531.4	1530.8	1530.2	1529.7	1529.0	1531.1	1533.1
177.5°	1539.6	1538.9	1538.2	1537.5	1536.9	1536.4	1535.9	1535.5	1535.0	1536.4	1537.8
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331610-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1780.7	1788.1	1788.1	1789.2	1797.6	1796.6	1796.0
5°	1895.1	1906.3	1907.5	1919.4	1927.3	1924.7	1917.4
7.5°	2002.9	2023.7	2039.5	2048.4	2058.8	2065.3	2062.4
10°	2088.4	2118.7	2137.2	2149.7	2164.9	2176.1	2172.1
12.5°	2165.9	2202.1	2227.5	2248.9	2250.9	2265.3	2255.6
15°	2287.0	2325.2	2329.2	2345.0	2357.6	2356.2	2356.9
17.5°	2326.9	2339.3	2341.7	2342.1	2342.3	2337.6	2327.6
20°	2312.7	2308.1	2296.9	2288.3	2273.1	2271.1	2258.0
22.5°	2245.1	2230.5	2202.4	2183.8	2160.2	2154.0	2150.3
25°	2112.1	2079.7	2034.9	1992.0	1980.1	1957.1	1963.7
27.5°	1929.6	1879.2	1830.7	1795.8	1764.3	1729.7	1739.6
30°	1801.3	1744.6	1675.9	1623.2	1589.5	1556.5	1550.6
32.5°	1648.2	1565.1	1488.6	1442.1	1390.5	1369.7	1346.9
35°	1384.3	1303.1	1227.3	1161.9	1124.4	1095.3	1068.9
37.5°	1146.9	1053.5	992.2	939.4	912.1	895.5	899.7
40°	999.6	917.8	873.0	832.7	807.6	795.7	798.4
42.5°	880.4	819.1	782.1	754.6	736.9	730.3	728.8
45°	744.9	710.7	680.3	664.4	655.9	648.6	644.0
47.5°	652.6	624.6	607.4	598.1	590.6	583.2	583.0
50°	597.1	578.7	566.8	556.9	551.0	545.7	550.3
52.5°	554.9	538.0	526.2	517.3	515.1	510.3	510.1
55°	492.2	479.1	470.5	462.5	458.6	455.9	452.6
57.5°	435.2	422.7	414.7	409.7	402.3	399.6	398.6
60°	394.6	384.7	376.8	370.1	366.9	361.6	361.6
62.5°	357.1	347.2	339.8	334.8	329.4	327.3	327.8
65°	302.9	295.0	287.7	282.4	281.1	277.2	278.4
67.5°	253.0	247.7	240.0	237.1	234.6	232.6	230.9
70°	219.7	214.5	210.5	206.6	204.6	204.6	204.6
72.5°	191.7	185.4	183.0	178.1	179.2	177.1	175.0
75°	148.4	144.5	142.5	140.5	137.2	137.2	137.2
77.5°	109.3	108.1	105.7	103.6	102.8	102.1	102.4
80°	84.5	83.8	82.5	82.5	81.2	80.5	79.2
82.5°	64.9	63.2	62.4	61.9	61.6	61.5	61.2
85°	36.9	35.6	35.6	36.2	35.0	35.0	35.6
87.5°	23.0	22.9	22.3	22.4	23.0	22.5	22.6
90°	43.7	43.1	43.0	43.3	43.6	43.8	44.2
92.5°	41.6	41.8	41.8	41.8	41.9	42.0	42.0
95°	83.1	83.1	82.7	82.2	81.6	81.0	80.5
97.5°	139.7	139.7	139.7	139.6	139.5	139.5	139.4
100°	179.1	179.1	179.0	178.7	178.4	178.1	177.8
102.5°	222.4	222.7	222.6	222.3	222.1	221.7	221.4
105°	287.3	287.8	288.2	288.2	288.2	288.2	288.2
107.5°	356.6	356.8	356.3	355.0	353.6	352.3	350.9
110°	403.7	403.7	403.2	402.3	401.5	400.6	399.8



TEST NUMBER: P331610-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	450.4	449.7	449.0	448.4	447.8	447.1	446.5
115°	523.5	523.2	522.6	521.8	520.9	520.0	519.2
117.5°	593.5	592.8	591.9	591.1	590.2	589.4	588.5
120°	641.2	641.2	640.8	639.9	639.0	638.2	637.3
122.5°	689.0	688.3	687.6	687.0	686.4	685.7	685.1
125°	760.6	759.7	759.2	758.9	758.6	758.4	758.0
127.5°	830.2	829.1	828.2	827.2	826.3	825.4	824.5
130°	878.3	877.7	876.8	875.7	874.6	873.4	872.3
132.5°	924.0	922.7	921.6	920.8	919.8	918.9	917.9
135°	993.4	993.2	992.6	991.7	990.8	990.0	989.1
137.5°	1059.0	1058.8	1058.1	1057.0	1055.8	1054.6	1053.4
140°	1103.3	1103.3	1102.8	1101.6	1100.4	1099.2	1098.1
142.5°	1143.5	1143.7	1143.2	1142.1	1140.9	1139.8	1138.6
145°	1204.1	1204.4	1203.9	1202.8	1201.7	1200.5	1199.4
147.5°	1257.6	1258.3	1258.0	1256.9	1255.8	1254.7	1253.6
150°	1291.5	1292.4	1292.4	1291.5	1290.6	1289.8	1288.9
152.5°	1325.4	1326.5	1326.5	1325.4	1324.3	1323.3	1322.2
155°	1368.6	1369.9	1370.3	1369.4	1368.6	1367.7	1366.8
157.5°	1408.5	1410.5	1410.7	1409.4	1408.0	1406.6	1405.2
160°	1431.7	1433.4	1433.7	1432.5	1431.4	1430.3	1429.1
162.5°	1453.2	1455.1	1455.4	1454.1	1452.7	1451.3	1449.8
165°	1480.6	1482.6	1482.9	1481.4	1480.1	1478.6	1477.1
167.5°	1503.2	1505.2	1505.5	1504.0	1502.4	1501.0	1499.4
170°	1515.6	1517.7	1517.8	1516.0	1514.3	1512.6	1510.9
172.5°	1525.0	1527.0	1527.2	1525.4	1523.7	1522.0	1520.3
175°	1535.1	1537.1	1537.3	1535.5	1533.8	1532.1	1530.3
177.5°	1539.2	1540.6	1540.6	1539.2	1537.8	1536.4	1535.0
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2

(END OF REPORT)