

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331496-940

Luminaire Tested: **S122DIW-S485D435U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331496-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S485D435U940-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3252.2 lumens  
Efficiency: N/A  
Efficacy: 107.7 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 30.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331496-940

CATALOG NUMBER: S122DIW-S485D435U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331496-940

CATALOG NUMBER: S122DIW-S485D435U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59				
1	100	96	92	89	93	90	87	84	78	76	74	68	66	64	58	56	55	51				
2	92	85	79	74	85	79	74	70	69	65	62	60	57	55	51	49	47	43				
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41	37				
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	38	36	33				
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32	29				
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	34	31	28	25				
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23				
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21				
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	23	21	19				
10	50	38	31	26	46	36	29	25	32	27	23	29	24	21	25	22	19	17				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13990	13990	13990	13990
5°	15686	14083	12478	14083
10°	17974	13967	10799	13967
15°	19883	13710	9541	13710
20°	19581	13435	8698	13435
25°	17655	13069	8165	13069
30°	14590	12486	7774	12486
35°	10634	11874	7496	11874
40°	8494	11152	7341	11152
45°	7421	10319	7133	10319
50°	6978	9510	6993	9510
55°	6432	8690	6804	8690
60°	5893	7818	6516	7818
65°	5368	7033	6235	7033
70°	4877	6274	5816	6274
75°	4323	5421	5153	5421
80°	3710	4491	4147	4491
85°	3335	3335	2464	3335



TEST NUMBER: P331496-940

CATALOG NUMBER: S122DIW-S485D435U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	82.5	2.5
10°-20°	239.9	7.4
20°-30°	348.2	10.7
30°-40°	367.4	11.3
40°-50°	325.3	10.0
50°-60°	259.6	8.0
60°-70°	176.5	5.4
70°-80°	90.5	2.8
80°-90°	23.7	0.7
90°-100°	30.3	0.9
100°-110°	94.2	2.9
110°-120°	161.0	5.0
120°-130°	211.8	6.5
130°-140°	237.7	7.3
140°-150°	233.1	7.2
150°-160°	195.5	6.0
160°-170°	129.7	4.0
170°-180°	45.3	1.4
0°-30°	670.6	20.6
0°-40°	1038.0	31.9
0°-60°	1623.0	49.9
0°-90°	1913.6	58.8
90°-120°	285.6	8.8
90°-150°	968.1	29.8
90°-180°	1339.0	41.2
0°-180°	3252.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	866	866	866	866	866	
5°	968	869	770	869	968	97
15°	1190	820	571	820	1190	328
25°	991	734	458	734	991	448
35°	540	602	380	602	540	351
45°	325	452	312	452	325	256
55°	228	309	242	309	228	205
65°	140	184	163	184	140	140
75°	69	87	83	87	69	74
85°	18	18	13	18	18	20
90°	14	0	14	0	14	7
95°	25	21	25	21	25	28
105°	90	87	90	87	90	94
115°	162	162	162	162	162	160
125°	236	235	236	235	236	210
135°	308	304	308	304	308	237
145°	373	369	373	369	373	233
155°	425	422	425	422	425	196
165°	460	459	460	459	460	130
175°	476	478	476	478	476	45
180°	479	479	479	479	479	



TEST NUMBER: P331496-940

CATALOG NUMBER: S122DIW-S485D435U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	906.5	906.8	907.2	903.0	902.5	902.5	898.8	895.5	891.8	886.7	887.3
5°	967.8	971.4	972.8	968.8	962.8	962.1	956.4	947.1	938.4	931.5	926.5
7.5°	1040.9	1042.3	1039.1	1033.8	1029.4	1021.4	1010.8	1000.5	986.1	972.8	963.0
10°	1096.3	1098.3	1092.6	1084.9	1078.6	1069.3	1054.0	1038.3	1019.4	1001.0	986.4
12.5°	1138.4	1143.4	1136.0	1135.1	1124.2	1111.4	1093.1	1085.2	1058.5	1033.0	1017.3
15°	1189.5	1189.2	1189.9	1183.6	1175.5	1173.6	1154.2	1133.3	1095.6	1080.7	1054.6
17.5°	1174.7	1179.8	1182.1	1182.1	1181.9	1180.6	1174.4	1161.2	1142.3	1118.0	1088.1
20°	1139.6	1146.2	1147.3	1154.9	1159.2	1164.9	1167.2	1163.6	1151.9	1131.6	1105.6
22.5°	1085.2	1087.1	1090.2	1102.2	1111.5	1125.7	1133.1	1145.4	1140.9	1131.0	1109.4
25°	991.0	987.7	999.3	1005.4	1027.0	1049.6	1066.0	1084.0	1099.9	1109.6	1103.3
27.5°	878.0	873.0	890.5	906.3	923.9	948.4	973.8	1003.9	1028.9	1060.2	1070.9
30°	782.6	785.6	802.3	819.2	845.9	880.5	909.1	942.1	977.8	1012.7	1037.0
32.5°	679.8	691.3	701.8	727.8	751.3	789.9	831.9	873.1	917.6	957.3	994.9
35°	539.5	552.8	567.5	586.5	619.4	657.7	698.7	754.3	814.9	869.2	913.8
37.5°	454.1	452.0	460.4	474.1	500.8	531.7	578.8	633.8	705.2	768.9	831.9
40°	403.0	401.6	407.6	420.3	440.6	463.2	504.5	552.8	619.1	697.0	772.0
42.5°	367.7	368.5	371.9	380.8	394.8	413.4	444.3	485.4	546.1	619.5	700.0
45°	325.0	327.3	331.0	335.4	343.3	358.6	375.9	405.3	453.3	514.5	593.8
47.5°	294.3	294.4	298.0	301.8	306.6	315.2	329.4	347.8	381.6	431.5	499.6
50°	277.8	275.4	278.0	281.1	286.1	292.0	301.4	318.7	341.3	381.7	438.5
52.5°	257.5	257.5	259.9	261.1	265.6	271.5	280.1	292.0	312.5	344.1	390.9
55°	228.5	230.2	231.5	233.4	237.5	241.7	248.4	256.5	272.4	296.0	330.6
57.5°	201.2	201.7	203.0	206.8	209.4	213.3	219.6	226.9	237.3	254.9	280.9
60°	182.5	182.5	185.1	186.8	190.1	194.1	199.1	206.2	215.4	229.8	250.7
62.5°	165.4	165.1	166.2	169.0	171.5	175.2	180.2	186.2	194.9	207.7	224.9
65°	140.5	139.9	141.9	142.5	145.2	148.8	152.8	159.2	166.2	175.5	190.8
67.5°	116.5	117.3	118.4	119.7	121.2	125.0	127.7	132.2	138.0	145.8	156.2
70°	103.3	103.3	103.3	104.2	106.2	108.3	110.9	114.6	120.2	126.9	136.2
72.5°	88.3	89.3	90.4	89.9	92.4	93.5	96.8	98.8	104.2	108.5	116.7
75°	69.3	69.3	69.3	70.9	72.0	72.9	74.9	77.0	79.6	84.9	89.3
77.5°	51.7	51.5	51.9	52.3	53.3	54.6	55.1	57.0	59.4	61.9	65.5
80°	39.9	40.7	40.9	41.6	41.6	42.3	42.6	44.9	46.6	48.3	50.6
82.5°	30.9	31.0	31.1	31.2	31.5	31.9	32.7	33.5	34.1	35.5	37.3
85°	18.0	17.7	17.7	18.3	18.0	18.0	18.6	19.4	19.4	19.6	20.7
87.5°	9.6	9.6	9.9	9.6	9.6	9.9	9.9	9.7	10.0	10.3	10.2
90°	13.7	13.6	13.6	13.5	13.4	13.5	13.6	13.8	14.0	14.2	12.1
92.5°	13.1	13.1	13.0	13.0	13.0	13.0	12.9	12.9	12.8	12.8	12.4
95°	25.1	25.2	25.4	25.6	25.8	25.9	25.9	25.9	25.9	25.9	25.7
97.5°	43.4	43.4	43.4	43.4	43.4	43.4	43.4	43.4	43.4	43.4	43.2
100°	55.4	55.5	55.6	55.6	55.7	55.7	55.7	55.7	55.7	55.7	55.5
102.5°	68.9	69.0	69.1	69.2	69.3	69.3	69.2	69.1	69.1	69.0	68.7
105°	89.7	89.7	89.7	89.7	89.7	89.6	89.4	89.3	89.1	88.9	88.7
107.5°	109.2	109.7	110.0	110.5	110.9	111.1	111.0	110.9	110.8	110.8	110.8
110°	124.4	124.7	124.9	125.2	125.5	125.6	125.6	125.6	125.6	125.6	125.6



TEST NUMBER: P331496-940

CATALOG NUMBER: S122DIW-S485D435U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	139.0	139.2	139.4	139.6	139.7	140.0	140.2	140.4	140.6	140.8	140.9
115°	161.6	161.8	162.1	162.4	162.6	162.8	162.9	163.0	163.1	163.2	163.4
117.5°	183.2	183.4	183.7	184.0	184.2	184.5	184.7	184.9	185.1	185.4	185.8
120°	198.4	198.7	198.9	199.2	199.5	199.6	199.6	199.6	199.6	199.6	200.3
122.5°	213.2	213.4	213.7	213.8	214.0	214.2	214.5	214.6	214.9	215.1	215.6
125°	235.9	236.0	236.1	236.2	236.3	236.5	236.7	237.0	237.3	237.6	237.8
127.5°	256.6	256.9	257.2	257.4	257.8	258.1	258.4	258.7	259.0	259.4	259.7
130°	271.5	271.9	272.2	272.6	273.0	273.2	273.4	273.6	273.8	273.9	274.1
132.5°	285.7	286.0	286.2	286.6	286.9	287.2	287.6	288.0	288.4	288.7	288.7
135°	307.8	308.1	308.4	308.6	308.9	309.1	309.2	309.2	309.3	309.4	309.2
137.5°	327.9	328.2	328.6	329.0	329.3	329.6	329.6	329.7	329.8	329.8	329.6
140°	341.8	342.1	342.5	342.9	343.2	343.4	343.4	343.4	343.4	343.4	343.0
142.5°	354.4	354.7	355.1	355.4	355.8	356.0	355.9	355.8	355.8	355.7	355.3
145°	373.3	373.6	374.0	374.3	374.7	374.9	374.8	374.7	374.6	374.5	374.0
147.5°	390.2	390.5	390.8	391.2	391.6	391.6	391.5	391.2	391.0	390.8	390.5
150°	401.2	401.4	401.7	402.0	402.3	402.3	402.0	401.7	401.4	401.2	400.8
152.5°	411.5	411.9	412.1	412.5	412.9	412.9	412.5	412.1	411.9	411.5	411.1
155°	425.4	425.7	426.0	426.2	426.5	426.4	426.0	425.5	425.1	424.6	424.4
157.5°	437.4	437.8	438.2	438.6	439.1	439.0	438.4	437.7	437.2	436.6	436.4
160°	444.8	445.1	445.5	445.9	446.2	446.1	445.6	445.1	444.5	444.0	443.9
162.5°	451.3	451.7	452.1	452.5	453.0	452.9	452.3	451.7	451.0	450.5	450.4
165°	459.8	460.2	460.7	461.1	461.5	461.5	460.8	460.2	459.6	459.0	459.0
167.5°	466.7	467.2	467.6	468.1	468.6	468.5	467.9	467.3	466.6	466.0	466.0
170°	470.3	470.8	471.4	471.9	472.4	472.3	471.7	471.1	470.5	469.8	469.9
172.5°	473.1	473.7	474.2	474.7	475.3	475.3	474.7	474.0	473.4	472.8	472.9
175°	476.4	476.9	477.4	478.0	478.5	478.4	477.8	477.2	476.5	475.9	476.1
177.5°	477.8	478.2	478.7	479.0	479.5	479.5	479.0	478.7	478.2	477.8	477.9
180°	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8



TEST NUMBER: P331496-940

CATALOG NUMBER: S122DIW-S485D435U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	889.1	887.0	885.6	880.9	876.6	872.4	871.0	871.6	865.7	860.1	857.7
5°	923.8	917.1	910.8	901.8	891.2	879.5	873.5	868.9	857.2	844.5	837.2
7.5°	954.8	945.3	933.1	916.2	900.7	882.3	870.7	860.4	843.3	825.5	814.6
10°	973.7	960.7	945.1	924.4	905.4	883.2	867.5	851.9	831.9	810.6	797.3
12.5°	990.0	972.5	957.1	930.6	908.1	880.2	861.7	839.6	818.6	793.3	780.2
15°	1028.7	996.4	967.1	937.1	909.5	870.5	849.9	820.2	792.6	761.3	746.3
17.5°	1058.5	1022.3	976.2	938.1	905.8	862.6	832.3	796.8	764.1	728.3	708.0
20°	1075.7	1034.0	984.4	939.1	900.4	851.2	818.2	781.9	743.6	703.3	681.4
22.5°	1085.7	1042.1	992.9	935.1	889.8	841.9	800.4	760.6	721.8	678.3	655.2
25°	1089.0	1049.0	997.0	931.7	876.5	822.2	772.2	733.6	686.7	646.0	612.4
27.5°	1073.1	1044.5	994.5	925.5	861.1	797.6	742.0	698.2	648.6	604.6	570.7
30°	1053.6	1037.0	988.4	919.1	848.8	780.6	719.3	669.7	620.5	575.8	541.2
32.5°	1023.6	1019.9	977.2	910.1	835.8	759.0	695.6	645.4	590.8	547.0	514.0
35°	964.4	980.4	953.4	889.8	811.2	728.3	659.7	602.4	545.8	503.8	472.9
37.5°	885.2	924.9	917.8	860.1	778.0	694.9	619.1	559.3	505.3	463.0	432.6
40°	830.5	881.2	888.5	837.5	754.7	669.1	588.8	529.1	476.5	437.9	407.2
42.5°	772.0	831.1	851.2	810.4	729.1	641.9	561.6	499.9	447.8	410.2	383.1
45°	673.7	752.0	788.3	764.9	686.3	597.1	514.5	451.9	404.7	369.3	348.3
47.5°	581.8	667.4	716.2	707.9	638.8	550.5	468.9	408.8	362.7	334.6	315.8
50°	516.8	604.8	663.7	666.4	604.8	517.2	435.2	378.6	336.4	310.0	294.7
52.5°	460.4	544.3	608.6	622.7	566.7	482.5	405.1	348.8	311.6	287.4	273.7
55°	386.6	457.5	528.9	554.8	509.9	429.9	358.3	308.7	273.8	257.1	245.1
57.5°	321.5	380.6	446.4	475.1	447.4	379.0	311.8	268.8	240.4	225.8	216.6
60°	287.0	333.7	392.3	426.6	402.6	341.7	283.0	242.1	218.8	205.8	197.2
62.5°	255.1	296.4	345.9	377.3	364.3	306.7	254.3	218.1	198.0	185.8	179.6
65°	210.4	243.1	281.4	310.4	301.8	258.1	215.2	184.1	168.2	158.5	153.6
67.5°	173.3	196.9	223.5	248.8	241.8	210.9	176.5	152.3	140.4	132.1	129.1
70°	149.9	167.8	191.5	211.8	206.2	180.8	153.6	132.9	122.5	115.6	112.5
72.5°	127.5	142.2	160.3	176.9	173.1	152.0	129.3	113.7	105.8	99.3	96.8
75°	96.2	107.5	118.6	129.6	128.6	112.3	98.9	86.9	80.6	75.6	74.6
77.5°	71.1	77.4	84.9	91.4	89.6	80.3	69.8	63.0	58.3	54.9	54.4
80°	54.3	58.0	63.3	67.9	65.6	61.6	53.3	48.3	44.9	41.6	40.3
82.5°	39.3	43.1	46.2	48.8	47.0	43.2	38.1	34.7	32.7	30.4	29.9
85°	20.7	22.6	24.0	24.6	24.0	21.7	19.4	18.0	16.3	15.3	15.0
87.5°	10.0	9.6	9.3	9.5	8.5	8.2	7.0	6.0	5.9	5.8	5.5
90°	10.2	8.2	6.2	4.7	3.7	2.6	1.5	0.4	1.5	2.6	3.7
92.5°	11.9	11.4	11.0	10.3	9.5	8.7	8.0	7.2	8.0	8.7	9.5
95°	25.5	25.3	25.1	24.6	23.7	22.8	21.9	21.0	21.9	22.8	23.7
97.5°	42.8	42.4	42.1	41.6	40.8	39.9	39.1	38.3	39.1	39.9	40.8
100°	55.2	54.9	54.7	54.2	53.5	52.7	52.0	51.3	52.0	52.7	53.5
102.5°	68.3	67.9	67.7	67.1	66.6	66.0	65.5	64.9	65.5	66.0	66.6
105°	88.5	88.4	88.2	87.9	87.7	87.4	87.1	86.9	87.1	87.4	87.7
107.5°	110.8	110.8	110.8	110.6	110.2	109.8	109.4	109.0	109.4	109.8	110.2
110°	125.6	125.6	125.6	125.4	124.8	124.3	123.8	123.2	123.8	124.3	124.8





TEST NUMBER: P331496-940

CATALOG NUMBER: S122DIW-S485D435U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	141.0	141.1	141.2	140.9	140.4	139.8	139.3	138.8	139.3	139.8	140.4
115°	163.5	163.7	163.9	163.7	163.2	162.6	162.1	161.6	162.1	162.6	163.2
117.5°	186.4	186.9	187.3	187.3	186.5	185.8	185.1	184.4	185.1	185.8	186.5
120°	201.0	201.7	202.4	202.4	201.7	201.0	200.3	199.6	200.3	201.0	201.7
122.5°	216.1	216.6	217.1	217.0	216.1	215.2	214.4	213.5	214.4	215.2	216.1
125°	238.1	238.4	238.6	238.4	237.6	236.7	235.9	235.1	235.9	236.7	237.6
127.5°	260.0	260.4	260.6	260.3	259.3	258.2	257.3	256.2	257.3	258.2	259.3
130°	274.3	274.5	274.6	274.1	273.0	271.8	270.6	269.5	270.6	271.8	273.0
132.5°	288.7	288.6	288.6	288.1	287.2	286.2	285.3	284.4	285.3	286.2	287.2
135°	309.1	308.9	308.7	308.2	307.2	306.2	305.2	304.3	305.2	306.2	307.2
137.5°	329.4	329.1	328.9	328.3	327.5	326.7	325.9	325.1	325.9	326.7	327.5
140°	342.5	342.1	341.6	341.0	340.2	339.4	338.6	337.8	338.6	339.4	340.2
142.5°	355.1	354.7	354.5	353.9	353.1	352.3	351.5	350.7	351.5	352.3	353.1
145°	373.4	372.9	372.4	371.8	371.1	370.5	369.9	369.3	369.9	370.5	371.1
147.5°	390.1	389.8	389.4	388.9	388.1	387.4	386.6	385.8	386.6	387.4	388.1
150°	400.5	400.1	399.8	399.3	398.8	398.2	397.7	397.2	397.7	398.2	398.8
152.5°	410.6	410.2	409.8	409.3	408.8	408.2	407.7	407.2	407.7	408.2	408.8
155°	424.1	423.8	423.6	423.3	423.0	422.7	422.4	422.1	422.4	422.7	423.0
157.5°	436.2	436.0	435.9	435.8	435.6	435.4	435.2	435.1	435.2	435.4	435.6
160°	443.8	443.7	443.6	443.5	443.4	443.2	443.0	442.8	443.0	443.2	443.4
162.5°	450.3	450.2	450.1	450.0	450.0	450.0	450.0	449.9	450.0	450.0	450.0
165°	459.0	459.0	459.0	459.0	459.1	459.1	459.2	459.3	459.2	459.1	459.1
167.5°	466.0	466.0	466.0	466.2	466.5	466.7	467.0	467.3	467.0	466.7	466.5
170°	470.0	470.1	470.2	470.4	470.6	470.9	471.2	471.4	471.2	470.9	470.6
172.5°	473.0	473.1	473.1	473.3	473.6	473.9	474.1	474.4	474.1	473.9	473.6
175°	476.3	476.4	476.6	476.9	477.2	477.4	477.7	478.0	477.7	477.4	477.2
177.5°	478.0	478.2	478.3	478.5	478.8	478.9	479.2	479.4	479.2	478.9	478.8
180°	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8



TEST NUMBER: P331496-940

CATALOG NUMBER: S122DIW-S485D435U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	855.1	853.5	847.8	844.9	840.2	835.6	832.7	834.0	835.1	834.6	833.7
5°	830.5	824.2	814.6	806.2	800.2	789.3	784.6	782.3	780.2	777.9	775.6
7.5°	801.4	791.4	777.6	765.7	754.5	740.8	733.1	728.3	723.5	718.3	713.6
10°	780.6	766.6	752.0	735.3	722.0	709.6	698.7	691.3	684.7	678.3	673.7
12.5°	758.8	742.6	724.5	701.8	687.1	669.4	667.8	654.9	644.4	640.5	635.1
15°	724.0	701.3	678.3	651.4	639.7	623.8	613.8	603.8	594.8	588.4	586.7
17.5°	684.5	655.1	632.3	613.0	593.9	577.5	568.3	560.3	552.9	544.4	543.3
20°	654.3	629.1	604.1	587.1	567.5	550.8	539.5	531.5	525.1	520.1	515.9
22.5°	625.9	598.2	575.3	556.7	537.3	523.9	515.0	507.3	502.0	496.5	492.4
25°	580.1	558.5	533.5	512.6	496.5	487.9	480.5	473.9	470.6	466.9	462.3
27.5°	540.1	516.0	492.7	476.4	462.4	454.7	449.5	445.0	441.8	439.7	437.0
30°	511.8	487.5	469.2	453.3	441.6	433.9	430.6	427.9	424.3	422.9	421.6
32.5°	484.6	462.8	447.1	433.3	422.1	417.1	414.1	411.7	408.8	407.5	404.8
35°	446.2	427.9	412.6	404.9	395.9	391.6	389.3	385.9	383.3	382.0	381.7
37.5°	410.1	394.1	384.1	374.3	370.4	367.7	364.6	362.3	361.5	361.3	361.0
40°	386.6	373.6	364.6	356.7	355.0	351.0	348.3	346.3	346.3	346.7	346.3
42.5°	365.3	353.7	345.7	338.9	336.9	334.5	331.8	331.7	332.3	333.3	332.3
45°	333.1	324.7	319.1	315.7	312.0	309.7	309.3	310.4	310.7	311.0	312.0
47.5°	303.3	297.7	292.7	289.0	287.4	287.0	286.6	288.3	289.9	290.5	292.0
50°	285.7	279.4	275.1	272.8	271.4	270.7	271.4	273.4	274.7	276.4	277.4
52.5°	266.0	261.5	258.6	256.7	256.2	256.6	256.7	259.0	261.2	261.7	262.3
55°	238.8	235.4	234.8	231.8	233.1	232.7	234.4	235.8	237.7	239.8	240.1
57.5°	211.6	208.9	207.1	207.4	207.8	209.3	210.6	213.0	215.2	217.2	217.5
60°	193.5	192.2	191.2	191.2	191.8	193.9	195.5	197.8	199.1	200.5	201.4
62.5°	177.0	175.7	174.6	175.1	176.9	178.1	180.0	181.3	182.6	184.0	184.4
65°	150.9	150.2	151.2	151.9	152.2	153.8	156.2	157.2	158.5	159.2	161.5
67.5°	126.8	127.0	126.8	127.8	129.7	130.1	132.2	134.6	134.9	136.2	137.7
70°	110.6	111.2	111.9	112.5	114.2	114.9	116.5	117.5	118.9	119.8	120.9
72.5°	95.7	95.8	96.5	96.3	97.7	99.2	100.6	101.6	102.9	104.2	105.1
75°	73.6	73.6	74.3	74.6	76.2	77.9	77.6	78.3	79.6	81.0	81.6
77.5°	53.8	53.1	53.8	54.0	54.6	56.0	56.3	57.2	58.8	58.3	59.0
80°	40.9	39.9	40.9	41.3	41.3	43.0	43.0	43.6	44.6	43.6	44.6
82.5°	29.2	28.8	29.5	29.6	30.1	30.1	30.7	30.9	31.8	31.4	31.8
85°	14.6	14.4	14.6	14.4	14.6	15.0	15.0	14.6	14.6	15.3	14.4
87.5°	5.4	5.5	5.6	6.1	6.2	6.3	6.0	6.0	5.9	5.4	5.4
90°	4.7	6.2	8.2	10.2	12.1	14.2	14.0	13.8	13.6	13.5	13.4
92.5°	10.3	11.0	11.4	11.9	12.4	12.8	12.8	12.9	12.9	13.0	13.0
95°	24.6	25.1	25.3	25.5	25.7	25.9	25.9	25.9	25.9	25.9	25.8
97.5°	41.6	42.1	42.4	42.8	43.2	43.4	43.4	43.4	43.4	43.4	43.4
100°	54.2	54.7	54.9	55.2	55.5	55.7	55.7	55.7	55.7	55.7	55.7
102.5°	67.1	67.7	67.9	68.3	68.7	69.0	69.1	69.1	69.2	69.3	69.3
105°	87.9	88.2	88.4	88.5	88.7	88.9	89.1	89.3	89.4	89.6	89.7
107.5°	110.6	110.8	110.8	110.8	110.8	110.8	110.8	110.9	111.0	111.1	110.9
110°	125.4	125.6	125.6	125.6	125.6	125.6	125.6	125.6	125.6	125.6	125.5



TEST NUMBER: P331496-940

CATALOG NUMBER: S122DIW-S485D435U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	140.9	141.2	141.1	141.0	140.9	140.8	140.6	140.4	140.2	140.0	139.7
115°	163.7	163.9	163.7	163.5	163.4	163.2	163.1	163.0	162.9	162.8	162.6
117.5°	187.3	187.3	186.9	186.4	185.8	185.4	185.1	184.9	184.7	184.5	184.2
120°	202.4	202.4	201.7	201.0	200.3	199.6	199.6	199.6	199.6	199.6	199.5
122.5°	217.0	217.1	216.6	216.1	215.6	215.1	214.9	214.6	214.5	214.2	214.0
125°	238.4	238.6	238.4	238.1	237.8	237.6	237.3	237.0	236.7	236.5	236.3
127.5°	260.3	260.6	260.4	260.0	259.7	259.4	259.0	258.7	258.4	258.1	257.8
130°	274.1	274.6	274.5	274.3	274.1	273.9	273.8	273.6	273.4	273.2	273.0
132.5°	288.1	288.6	288.6	288.7	288.7	288.7	288.4	288.0	287.6	287.2	286.9
135°	308.2	308.7	308.9	309.1	309.2	309.4	309.3	309.2	309.2	309.1	308.9
137.5°	328.3	328.9	329.1	329.4	329.6	329.8	329.8	329.7	329.6	329.6	329.3
140°	341.0	341.6	342.1	342.5	343.0	343.4	343.4	343.4	343.4	343.4	343.2
142.5°	353.9	354.5	354.7	355.1	355.3	355.7	355.8	355.8	355.9	356.0	355.8
145°	371.8	372.4	372.9	373.4	374.0	374.5	374.6	374.7	374.8	374.9	374.7
147.5°	388.9	389.4	389.8	390.1	390.5	390.8	391.0	391.2	391.5	391.6	391.6
150°	399.3	399.8	400.1	400.5	400.8	401.2	401.4	401.7	402.0	402.3	402.3
152.5°	409.3	409.8	410.2	410.6	411.1	411.5	411.9	412.1	412.5	412.9	412.9
155°	423.3	423.6	423.8	424.1	424.4	424.6	425.1	425.5	426.0	426.4	426.5
157.5°	435.8	435.9	436.0	436.2	436.4	436.6	437.2	437.7	438.4	439.0	439.1
160°	443.5	443.6	443.7	443.8	443.9	444.0	444.5	445.1	445.6	446.1	446.2
162.5°	450.0	450.1	450.2	450.3	450.4	450.5	451.0	451.7	452.3	452.9	453.0
165°	459.0	459.0	459.0	459.0	459.0	459.0	459.6	460.2	460.8	461.5	461.5
167.5°	466.2	466.0	466.0	466.0	466.0	466.0	466.6	467.3	467.9	468.5	468.6
170°	470.4	470.2	470.1	470.0	469.9	469.8	470.5	471.1	471.7	472.3	472.4
172.5°	473.3	473.1	473.1	473.0	472.9	472.8	473.4	474.0	474.7	475.3	475.3
175°	476.9	476.6	476.4	476.3	476.1	475.9	476.5	477.2	477.8	478.4	478.5
177.5°	478.5	478.3	478.2	478.0	477.9	477.8	478.2	478.7	479.0	479.5	479.5
180°	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8



TEST NUMBER: P331496-940

CATALOG NUMBER: S122DIW-S485D435U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	831.1	830.5	830.5	828.1	830.5	830.5	831.1	833.7	834.6	835.1	834.0
5°	771.0	769.9	768.3	769.9	768.3	769.9	771.0	775.6	777.9	780.2	782.3
7.5°	711.5	707.5	706.9	702.9	706.9	707.5	711.5	713.6	718.3	723.5	728.3
10°	668.1	665.4	665.0	658.7	665.0	665.4	668.1	673.7	678.3	684.7	691.3
12.5°	635.0	628.6	629.9	626.2	629.9	628.6	635.0	635.1	640.5	644.4	654.9
15°	577.7	577.7	576.5	570.8	576.5	577.7	577.7	586.7	588.4	594.8	603.8
17.5°	536.7	536.0	532.8	534.4	532.8	536.0	536.7	543.3	544.4	552.9	560.3
20°	512.2	510.1	506.2	506.2	506.2	510.1	512.2	515.9	520.1	525.1	531.5
22.5°	489.0	488.8	484.6	486.0	484.6	488.8	489.0	492.4	496.5	502.0	507.3
25°	461.9	459.2	457.3	458.3	457.3	459.2	461.9	462.3	466.9	470.6	473.9
27.5°	436.2	434.7	434.6	431.9	434.6	434.7	436.2	437.0	439.7	441.8	445.0
30°	421.2	417.9	418.6	417.0	418.6	417.9	421.2	421.6	422.9	424.3	427.9
32.5°	404.2	403.1	402.3	400.9	402.3	403.1	404.2	404.8	407.5	408.8	411.7
35°	380.9	381.3	379.6	380.3	379.6	381.3	380.9	381.7	382.0	383.3	385.9
37.5°	360.7	361.8	361.0	361.1	361.0	361.8	360.7	361.0	361.3	361.5	362.3
40°	347.3	347.3	347.3	348.3	347.3	347.3	347.3	346.3	346.7	346.3	346.3
42.5°	334.6	334.0	333.5	333.4	333.5	334.0	334.6	332.3	333.3	332.3	331.7
45°	312.7	313.7	314.1	312.4	314.1	313.7	312.7	312.0	311.0	310.7	310.4
47.5°	292.9	293.0	292.9	294.4	292.9	293.0	292.9	292.0	290.5	289.9	288.3
50°	279.1	278.4	279.1	278.4	279.1	278.4	279.1	277.4	276.4	274.7	273.4
52.5°	264.4	264.6	264.1	264.0	264.1	264.6	264.4	262.3	261.7	261.2	259.0
55°	241.5	242.1	241.7	241.7	241.7	242.1	241.5	240.1	239.8	237.7	235.8
57.5°	217.7	218.3	218.7	217.2	218.7	218.3	217.7	217.5	217.2	215.2	213.0
60°	201.2	202.8	202.5	201.8	202.5	202.8	201.2	201.4	200.5	199.1	197.8
62.5°	185.9	186.5	186.5	186.4	186.5	186.5	185.9	184.4	184.0	182.6	181.3
65°	162.5	163.2	162.2	163.2	162.2	163.2	162.5	161.5	159.2	158.5	157.2
67.5°	137.2	137.5	138.2	138.7	138.2	137.5	137.2	137.7	136.2	134.9	134.6
70°	121.5	121.2	122.3	123.2	122.3	121.2	121.5	120.9	119.8	118.9	117.5
72.5°	105.0	105.8	105.4	106.2	105.4	105.8	105.0	105.1	104.2	102.9	101.6
75°	81.0	81.9	81.6	82.6	81.6	81.9	81.0	81.6	81.0	79.6	78.3
77.5°	58.5	58.6	58.5	59.0	58.5	58.6	58.5	59.0	58.3	58.8	57.2
80°	44.6	44.0	43.2	44.6	43.2	44.0	44.6	44.6	43.6	44.6	43.6
82.5°	31.0	31.5	30.8	30.8	30.8	31.5	31.0	31.8	31.4	31.8	30.9
85°	14.4	14.0	13.3	13.3	13.3	14.0	14.4	14.4	15.3	14.6	14.6
87.5°	5.4	5.1	5.1	4.9	5.1	5.1	5.4	5.4	5.4	5.9	6.0
90°	13.5	13.6	13.6	13.7	13.6	13.6	13.5	13.4	13.5	13.6	13.8
92.5°	13.0	13.0	13.1	13.1	13.1	13.0	13.0	13.0	13.0	12.9	12.9
95°	25.6	25.4	25.2	25.1	25.2	25.4	25.6	25.8	25.9	25.9	25.9
97.5°	43.4	43.4	43.4	43.4	43.4	43.4	43.4	43.4	43.4	43.4	43.4
100°	55.6	55.6	55.5	55.4	55.5	55.6	55.6	55.7	55.7	55.7	55.7
102.5°	69.2	69.1	69.0	68.9	69.0	69.1	69.2	69.3	69.3	69.2	69.1
105°	89.7	89.7	89.7	89.7	89.7	89.7	89.7	89.7	89.6	89.4	89.3
107.5°	110.5	110.0	109.7	109.2	109.7	110.0	110.5	110.9	111.1	111.0	110.9
110°	125.2	124.9	124.7	124.4	124.7	124.9	125.2	125.5	125.6	125.6	125.6



TEST NUMBER: P331496-940

CATALOG NUMBER: S122DIW-S485D435U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	139.6	139.4	139.2	139.0	139.2	139.4	139.6	139.7	140.0	140.2	140.4
115°	162.4	162.1	161.8	161.6	161.8	162.1	162.4	162.6	162.8	162.9	163.0
117.5°	184.0	183.7	183.4	183.2	183.4	183.7	184.0	184.2	184.5	184.7	184.9
120°	199.2	198.9	198.7	198.4	198.7	198.9	199.2	199.5	199.6	199.6	199.6
122.5°	213.8	213.7	213.4	213.2	213.4	213.7	213.8	214.0	214.2	214.5	214.6
125°	236.2	236.1	236.0	235.9	236.0	236.1	236.2	236.3	236.5	236.7	237.0
127.5°	257.4	257.2	256.9	256.6	256.9	257.2	257.4	257.8	258.1	258.4	258.7
130°	272.6	272.2	271.9	271.5	271.9	272.2	272.6	273.0	273.2	273.4	273.6
132.5°	286.6	286.2	286.0	285.7	286.0	286.2	286.6	286.9	287.2	287.6	288.0
135°	308.6	308.4	308.1	307.8	308.1	308.4	308.6	308.9	309.1	309.2	309.2
137.5°	329.0	328.6	328.2	327.9	328.2	328.6	329.0	329.3	329.6	329.6	329.7
140°	342.9	342.5	342.1	341.8	342.1	342.5	342.9	343.2	343.4	343.4	343.4
142.5°	355.4	355.1	354.7	354.4	354.7	355.1	355.4	355.8	356.0	355.9	355.8
145°	374.3	374.0	373.6	373.3	373.6	374.0	374.3	374.7	374.9	374.8	374.7
147.5°	391.2	390.8	390.5	390.2	390.5	390.8	391.2	391.6	391.6	391.5	391.2
150°	402.0	401.7	401.4	401.2	401.4	401.7	402.0	402.3	402.3	402.0	401.7
152.5°	412.5	412.1	411.9	411.5	411.9	412.1	412.5	412.9	412.9	412.5	412.1
155°	426.2	426.0	425.7	425.4	425.7	426.0	426.2	426.5	426.4	426.0	425.5
157.5°	438.6	438.2	437.8	437.4	437.8	438.2	438.6	439.1	439.0	438.4	437.7
160°	445.9	445.5	445.1	444.8	445.1	445.5	445.9	446.2	446.1	445.6	445.1
162.5°	452.5	452.1	451.7	451.3	451.7	452.1	452.5	453.0	452.9	452.3	451.7
165°	461.1	460.7	460.2	459.8	460.2	460.7	461.1	461.5	461.5	460.8	460.2
167.5°	468.1	467.6	467.2	466.7	467.2	467.6	468.1	468.6	468.5	467.9	467.3
170°	471.9	471.4	470.8	470.3	470.8	471.4	471.9	472.4	472.3	471.7	471.1
172.5°	474.7	474.2	473.7	473.1	473.7	474.2	474.7	475.3	475.3	474.7	474.0
175°	478.0	477.4	476.9	476.4	476.9	477.4	478.0	478.5	478.4	477.8	477.2
177.5°	479.0	478.7	478.2	477.8	478.2	478.7	479.0	479.5	479.5	479.0	478.7
180°	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8



TEST NUMBER: P331496-940

CATALOG NUMBER: S122DIW-S485D435U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	832.7	835.6	840.2	844.9	847.8	853.5	855.1	857.7	860.1	865.7	871.6
5°	784.6	789.3	800.2	806.2	814.6	824.2	830.5	837.2	844.5	857.2	868.9
7.5°	733.1	740.8	754.5	765.7	777.6	791.4	801.4	814.6	825.5	843.3	860.4
10°	698.7	709.6	722.0	735.3	752.0	766.6	780.6	797.3	810.6	831.9	851.9
12.5°	667.8	669.4	687.1	701.8	724.5	742.6	758.8	780.2	793.3	818.6	839.6
15°	613.8	623.8	639.7	651.4	678.3	701.3	724.0	746.3	761.3	792.6	820.2
17.5°	568.3	577.5	593.9	613.0	632.3	655.1	684.5	708.0	728.3	764.1	796.8
20°	539.5	550.8	567.5	587.1	604.1	629.1	654.3	681.4	703.3	743.6	781.9
22.5°	515.0	523.9	537.3	556.7	575.3	598.2	625.9	655.2	678.3	721.8	760.6
25°	480.5	487.9	496.5	512.6	533.5	558.5	580.1	612.4	646.0	686.7	733.6
27.5°	449.5	454.7	462.4	476.4	492.7	516.0	540.1	570.7	604.6	648.6	698.2
30°	430.6	433.9	441.6	453.3	469.2	487.5	511.8	541.2	575.8	620.5	669.7
32.5°	414.1	417.1	422.1	433.3	447.1	462.8	484.6	514.0	547.0	590.8	645.4
35°	389.3	391.6	395.9	404.9	412.6	427.9	446.2	472.9	503.8	545.8	602.4
37.5°	364.6	367.7	370.4	374.3	384.1	394.1	410.1	432.6	463.0	505.3	559.3
40°	348.3	351.0	355.0	356.7	364.6	373.6	386.6	407.2	437.9	476.5	529.1
42.5°	331.8	334.5	336.9	338.9	345.7	353.7	365.3	383.1	410.2	447.8	499.9
45°	309.3	309.7	312.0	315.7	319.1	324.7	333.1	348.3	369.3	404.7	451.9
47.5°	286.6	287.0	287.4	289.0	292.7	297.7	303.3	315.8	334.6	362.7	408.8
50°	271.4	270.7	271.4	272.8	275.1	279.4	285.7	294.7	310.0	336.4	378.6
52.5°	256.7	256.6	256.2	256.7	258.6	261.5	266.0	273.7	287.4	311.6	348.8
55°	234.4	232.7	233.1	231.8	234.8	235.4	238.8	245.1	257.1	273.8	308.7
57.5°	210.6	209.3	207.8	207.4	207.1	208.9	211.6	216.6	225.8	240.4	268.8
60°	195.5	193.9	191.8	191.2	191.2	192.2	193.5	197.2	205.8	218.8	242.1
62.5°	180.0	178.1	176.9	175.1	174.6	175.7	177.0	179.6	185.8	198.0	218.1
65°	156.2	153.8	152.2	151.9	151.2	150.2	150.9	153.6	158.5	168.2	184.1
67.5°	132.2	130.1	129.7	127.8	126.8	127.0	126.8	129.1	132.1	140.4	152.3
70°	116.5	114.9	114.2	112.5	111.9	111.2	110.6	112.5	115.6	122.5	132.9
72.5°	100.6	99.2	97.7	96.3	96.5	95.8	95.7	96.8	99.3	105.8	113.7
75°	77.6	77.9	76.2	74.6	74.3	73.6	73.6	74.6	75.6	80.6	86.9
77.5°	56.3	56.0	54.6	54.0	53.8	53.1	53.8	54.4	54.9	58.3	63.0
80°	43.0	43.0	41.3	41.3	40.9	39.9	40.9	40.3	41.6	44.9	48.3
82.5°	30.7	30.1	30.1	29.6	29.5	28.8	29.2	29.9	30.4	32.7	34.7
85°	15.0	15.0	14.6	14.4	14.6	14.4	14.6	15.0	15.3	16.3	18.0
87.5°	6.0	6.3	6.2	6.1	5.6	5.5	5.4	5.5	5.8	5.9	6.0
90°	14.0	14.2	12.1	10.2	8.2	6.2	4.7	3.7	2.6	1.5	0.4
92.5°	12.8	12.8	12.4	11.9	11.4	11.0	10.3	9.5	8.7	8.0	7.2
95°	25.9	25.9	25.7	25.5	25.3	25.1	24.6	23.7	22.8	21.9	21.0
97.5°	43.4	43.4	43.2	42.8	42.4	42.1	41.6	40.8	39.9	39.1	38.3
100°	55.7	55.7	55.5	55.2	54.9	54.7	54.2	53.5	52.7	52.0	51.3
102.5°	69.1	69.0	68.7	68.3	67.9	67.7	67.1	66.6	66.0	65.5	64.9
105°	89.1	88.9	88.7	88.5	88.4	88.2	87.9	87.7	87.4	87.1	86.9
107.5°	110.8	110.8	110.8	110.8	110.8	110.8	110.6	110.2	109.8	109.4	109.0
110°	125.6	125.6	125.6	125.6	125.6	125.6	125.4	124.8	124.3	123.8	123.2



TEST NUMBER: P331496-940

CATALOG NUMBER: S122DIW-S485D435U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	140.6	140.8	140.9	141.0	141.1	141.2	140.9	140.4	139.8	139.3	138.8
115°	163.1	163.2	163.4	163.5	163.7	163.9	163.7	163.2	162.6	162.1	161.6
117.5°	185.1	185.4	185.8	186.4	186.9	187.3	187.3	186.5	185.8	185.1	184.4
120°	199.6	199.6	200.3	201.0	201.7	202.4	202.4	201.7	201.0	200.3	199.6
122.5°	214.9	215.1	215.6	216.1	216.6	217.1	217.0	216.1	215.2	214.4	213.5
125°	237.3	237.6	237.8	238.1	238.4	238.6	238.4	237.6	236.7	235.9	235.1
127.5°	259.0	259.4	259.7	260.0	260.4	260.6	260.3	259.3	258.2	257.3	256.2
130°	273.8	273.9	274.1	274.3	274.5	274.6	274.1	273.0	271.8	270.6	269.5
132.5°	288.4	288.7	288.7	288.7	288.6	288.6	288.1	287.2	286.2	285.3	284.4
135°	309.3	309.4	309.2	309.1	308.9	308.7	308.2	307.2	306.2	305.2	304.3
137.5°	329.8	329.8	329.6	329.4	329.1	328.9	328.3	327.5	326.7	325.9	325.1
140°	343.4	343.4	343.0	342.5	342.1	341.6	341.0	340.2	339.4	338.6	337.8
142.5°	355.8	355.7	355.3	355.1	354.7	354.5	353.9	353.1	352.3	351.5	350.7
145°	374.6	374.5	374.0	373.4	372.9	372.4	371.8	371.1	370.5	369.9	369.3
147.5°	391.0	390.8	390.5	390.1	389.8	389.4	388.9	388.1	387.4	386.6	385.8
150°	401.4	401.2	400.8	400.5	400.1	399.8	399.3	398.8	398.2	397.7	397.2
152.5°	411.9	411.5	411.1	410.6	410.2	409.8	409.3	408.8	408.2	407.7	407.2
155°	425.1	424.6	424.4	424.1	423.8	423.6	423.3	423.0	422.7	422.4	422.1
157.5°	437.2	436.6	436.4	436.2	436.0	435.9	435.8	435.6	435.4	435.2	435.1
160°	444.5	444.0	443.9	443.8	443.7	443.6	443.5	443.4	443.2	443.0	442.8
162.5°	451.0	450.5	450.4	450.3	450.2	450.1	450.0	450.0	450.0	450.0	449.9
165°	459.6	459.0	459.0	459.0	459.0	459.0	459.0	459.1	459.1	459.2	459.3
167.5°	466.6	466.0	466.0	466.0	466.0	466.0	466.2	466.5	466.7	467.0	467.3
170°	470.5	469.8	469.9	470.0	470.1	470.2	470.4	470.6	470.9	471.2	471.4
172.5°	473.4	472.8	472.9	473.0	473.1	473.1	473.3	473.6	473.9	474.1	474.4
175°	476.5	475.9	476.1	476.3	476.4	476.6	476.9	477.2	477.4	477.7	478.0
177.5°	478.2	477.8	477.9	478.0	478.2	478.3	478.5	478.8	478.9	479.2	479.4
180°	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8



TEST NUMBER: P331496-940

CATALOG NUMBER: S122DIW-S485D435U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	871.0	872.4	876.6	880.9	885.6	887.0	889.1	887.3	886.7	891.8	895.5
5°	873.5	879.5	891.2	901.8	910.8	917.1	923.8	926.5	931.5	938.4	947.1
7.5°	870.7	882.3	900.7	916.2	933.1	945.3	954.8	963.0	972.8	986.1	1000.5
10°	867.5	883.2	905.4	924.4	945.1	960.7	973.7	986.4	1001.0	1019.4	1038.3
12.5°	861.7	880.2	908.1	930.6	957.1	972.5	990.0	1017.3	1033.0	1058.5	1085.2
15°	849.9	870.5	909.5	937.1	967.1	996.4	1028.7	1054.6	1080.7	1095.6	1133.3
17.5°	832.3	862.6	905.8	938.1	976.2	1022.3	1058.5	1088.1	1118.0	1142.3	1161.2
20°	818.2	851.2	900.4	939.1	984.4	1034.0	1075.7	1105.6	1131.6	1151.9	1163.6
22.5°	800.4	841.9	889.8	935.1	992.9	1042.1	1085.7	1109.4	1131.0	1140.9	1145.4
25°	772.2	822.2	876.5	931.7	997.0	1049.0	1089.0	1103.3	1109.6	1099.9	1084.0
27.5°	742.0	797.6	861.1	925.5	994.5	1044.5	1073.1	1070.9	1060.2	1028.9	1003.9
30°	719.3	780.6	848.8	919.1	988.4	1037.0	1053.6	1037.0	1012.7	977.8	942.1
32.5°	695.6	759.0	835.8	910.1	977.2	1019.9	1023.6	994.9	957.3	917.6	873.1
35°	659.7	728.3	811.2	889.8	953.4	980.4	964.4	913.8	869.2	814.9	754.3
37.5°	619.1	694.9	778.0	860.1	917.8	924.9	885.2	831.9	768.9	705.2	633.8
40°	588.8	669.1	754.7	837.5	888.5	881.2	830.5	772.0	697.0	619.1	552.8
42.5°	561.6	641.9	729.1	810.4	851.2	831.1	772.0	700.0	619.5	546.1	485.4
45°	514.5	597.1	686.3	764.9	788.3	752.0	673.7	593.8	514.5	453.3	405.3
47.5°	468.9	550.5	638.8	707.9	716.2	667.4	581.8	499.6	431.5	381.6	347.8
50°	435.2	517.2	604.8	666.4	663.7	604.8	516.8	438.5	381.7	341.3	318.7
52.5°	405.1	482.5	566.7	622.7	608.6	544.3	460.4	390.9	344.1	312.5	292.0
55°	358.3	429.9	509.9	554.8	528.9	457.5	386.6	330.6	296.0	272.4	256.5
57.5°	311.8	379.0	447.4	475.1	446.4	380.6	321.5	280.9	254.9	237.3	226.9
60°	283.0	341.7	402.6	426.6	392.3	333.7	287.0	250.7	229.8	215.4	206.2
62.5°	254.3	306.7	364.3	377.3	345.9	296.4	255.1	224.9	207.7	194.9	186.2
65°	215.2	258.1	301.8	310.4	281.4	243.1	210.4	190.8	175.5	166.2	159.2
67.5°	176.5	210.9	241.8	248.8	223.5	196.9	173.3	156.2	145.8	138.0	132.2
70°	153.6	180.8	206.2	211.8	191.5	167.8	149.9	136.2	126.9	120.2	114.6
72.5°	129.3	152.0	173.1	176.9	160.3	142.2	127.5	116.7	108.5	104.2	98.8
75°	98.9	112.3	128.6	129.6	118.6	107.5	96.2	89.3	84.9	79.6	77.0
77.5°	69.8	80.3	89.6	91.4	84.9	77.4	71.1	65.5	61.9	59.4	57.0
80°	53.3	61.6	65.6	67.9	63.3	58.0	54.3	50.6	48.3	46.6	44.9
82.5°	38.1	43.2	47.0	48.8	46.2	43.1	39.3	37.3	35.5	34.1	33.5
85°	19.4	21.7	24.0	24.6	24.0	22.6	20.7	20.7	19.6	19.4	19.4
87.5°	7.0	8.2	8.5	9.5	9.3	9.6	10.0	10.2	10.3	10.0	9.7
90°	1.5	2.6	3.7	4.7	6.2	8.2	10.2	12.1	14.2	14.0	13.8
92.5°	8.0	8.7	9.5	10.3	11.0	11.4	11.9	12.4	12.8	12.8	12.9
95°	21.9	22.8	23.7	24.6	25.1	25.3	25.5	25.7	25.9	25.9	25.9
97.5°	39.1	39.9	40.8	41.6	42.1	42.4	42.8	43.2	43.4	43.4	43.4
100°	52.0	52.7	53.5	54.2	54.7	54.9	55.2	55.5	55.7	55.7	55.7
102.5°	65.5	66.0	66.6	67.1	67.7	67.9	68.3	68.7	69.0	69.1	69.1
105°	87.1	87.4	87.7	87.9	88.2	88.4	88.5	88.7	88.9	89.1	89.3
107.5°	109.4	109.8	110.2	110.6	110.8	110.8	110.8	110.8	110.8	110.8	110.9
110°	123.8	124.3	124.8	125.4	125.6	125.6	125.6	125.6	125.6	125.6	125.6





TEST NUMBER: P331496-940

CATALOG NUMBER: S122DIW-S485D435U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	139.3	139.8	140.4	140.9	141.2	141.1	141.0	140.9	140.8	140.6	140.4
115°	162.1	162.6	163.2	163.7	163.9	163.7	163.5	163.4	163.2	163.1	163.0
117.5°	185.1	185.8	186.5	187.3	187.3	186.9	186.4	185.8	185.4	185.1	184.9
120°	200.3	201.0	201.7	202.4	202.4	201.7	201.0	200.3	199.6	199.6	199.6
122.5°	214.4	215.2	216.1	217.0	217.1	216.6	216.1	215.6	215.1	214.9	214.6
125°	235.9	236.7	237.6	238.4	238.6	238.4	238.1	237.8	237.6	237.3	237.0
127.5°	257.3	258.2	259.3	260.3	260.6	260.4	260.0	259.7	259.4	259.0	258.7
130°	270.6	271.8	273.0	274.1	274.6	274.5	274.3	274.1	273.9	273.8	273.6
132.5°	285.3	286.2	287.2	288.1	288.6	288.6	288.7	288.7	288.7	288.4	288.0
135°	305.2	306.2	307.2	308.2	308.7	308.9	309.1	309.2	309.4	309.3	309.2
137.5°	325.9	326.7	327.5	328.3	328.9	329.1	329.4	329.6	329.8	329.8	329.7
140°	338.6	339.4	340.2	341.0	341.6	342.1	342.5	343.0	343.4	343.4	343.4
142.5°	351.5	352.3	353.1	353.9	354.5	354.7	355.1	355.3	355.7	355.8	355.8
145°	369.9	370.5	371.1	371.8	372.4	372.9	373.4	374.0	374.5	374.6	374.7
147.5°	386.6	387.4	388.1	388.9	389.4	389.8	390.1	390.5	390.8	391.0	391.2
150°	397.7	398.2	398.8	399.3	399.8	400.1	400.5	400.8	401.2	401.4	401.7
152.5°	407.7	408.2	408.8	409.3	409.8	410.2	410.6	411.1	411.5	411.9	412.1
155°	422.4	422.7	423.0	423.3	423.6	423.8	424.1	424.4	424.6	425.1	425.5
157.5°	435.2	435.4	435.6	435.8	435.9	436.0	436.2	436.4	436.6	437.2	437.7
160°	443.0	443.2	443.4	443.5	443.6	443.7	443.8	443.9	444.0	444.5	445.1
162.5°	450.0	450.0	450.0	450.0	450.1	450.2	450.3	450.4	450.5	451.0	451.7
165°	459.2	459.1	459.1	459.0	459.0	459.0	459.0	459.0	459.0	459.6	460.2
167.5°	467.0	466.7	466.5	466.2	466.0	466.0	466.0	466.0	466.0	466.6	467.3
170°	471.2	470.9	470.6	470.4	470.2	470.1	470.0	469.9	469.8	470.5	471.1
172.5°	474.1	473.9	473.6	473.3	473.1	473.1	473.0	472.9	472.8	473.4	474.0
175°	477.7	477.4	477.2	476.9	476.6	476.4	476.3	476.1	475.9	476.5	477.2
177.5°	479.2	478.9	478.8	478.5	478.3	478.2	478.0	477.9	477.8	478.2	478.7
180°	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8



TEST NUMBER: P331496-940

CATALOG NUMBER: S122DIW-S485D435U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	898.8	902.5	902.5	903.0	907.2	906.8	906.5
5°	956.4	962.1	962.8	968.8	972.8	971.4	967.8
7.5°	1010.8	1021.4	1029.4	1033.8	1039.1	1042.3	1040.9
10°	1054.0	1069.3	1078.6	1084.9	1092.6	1098.3	1096.3
12.5°	1093.1	1111.4	1124.2	1135.1	1136.0	1143.4	1138.4
15°	1154.2	1173.6	1175.5	1183.6	1189.9	1189.2	1189.5
17.5°	1174.4	1180.6	1181.9	1182.1	1182.1	1179.8	1174.7
20°	1167.2	1164.9	1159.2	1154.9	1147.3	1146.2	1139.6
22.5°	1133.1	1125.7	1111.5	1102.2	1090.2	1087.1	1085.2
25°	1066.0	1049.6	1027.0	1005.4	999.3	987.7	991.0
27.5°	973.8	948.4	923.9	906.3	890.5	873.0	878.0
30°	909.1	880.5	845.9	819.2	802.3	785.6	782.6
32.5°	831.9	789.9	751.3	727.8	701.8	691.3	679.8
35°	698.7	657.7	619.4	586.5	567.5	552.8	539.5
37.5°	578.8	531.7	500.8	474.1	460.4	452.0	454.1
40°	504.5	463.2	440.6	420.3	407.6	401.6	403.0
42.5°	444.3	413.4	394.8	380.8	371.9	368.5	367.7
45°	375.9	358.6	343.3	335.4	331.0	327.3	325.0
47.5°	329.4	315.2	306.6	301.8	298.0	294.4	294.3
50°	301.4	292.0	286.1	281.1	278.0	275.4	277.8
52.5°	280.1	271.5	265.6	261.1	259.9	257.5	257.5
55°	248.4	241.7	237.5	233.4	231.5	230.2	228.5
57.5°	219.6	213.3	209.4	206.8	203.0	201.7	201.2
60°	199.1	194.1	190.1	186.8	185.1	182.5	182.5
62.5°	180.2	175.2	171.5	169.0	166.2	165.1	165.4
65°	152.8	148.8	145.2	142.5	141.9	139.9	140.5
67.5°	127.7	125.0	121.2	119.7	118.4	117.3	116.5
70°	110.9	108.3	106.2	104.2	103.3	103.3	103.3
72.5°	96.8	93.5	92.4	89.9	90.4	89.3	88.3
75°	74.9	72.9	72.0	70.9	69.3	69.3	69.3
77.5°	55.1	54.6	53.3	52.3	51.9	51.5	51.7
80°	42.6	42.3	41.6	41.6	40.9	40.7	39.9
82.5°	32.7	31.9	31.5	31.2	31.1	31.0	30.9
85°	18.6	18.0	18.0	18.3	17.7	17.7	18.0
87.5°	9.9	9.9	9.6	9.6	9.9	9.6	9.6
90°	13.6	13.5	13.4	13.5	13.6	13.6	13.7
92.5°	12.9	13.0	13.0	13.0	13.0	13.1	13.1
95°	25.9	25.9	25.8	25.6	25.4	25.2	25.1
97.5°	43.4	43.4	43.4	43.4	43.4	43.4	43.4
100°	55.7	55.7	55.7	55.6	55.6	55.5	55.4
102.5°	69.2	69.3	69.3	69.2	69.1	69.0	68.9
105°	89.4	89.6	89.7	89.7	89.7	89.7	89.7
107.5°	111.0	111.1	110.9	110.5	110.0	109.7	109.2
110°	125.6	125.6	125.5	125.2	124.9	124.7	124.4



TEST NUMBER: P331496-940

CATALOG NUMBER: S122DIW-S485D435U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	140.2	140.0	139.7	139.6	139.4	139.2	139.0
115°	162.9	162.8	162.6	162.4	162.1	161.8	161.6
117.5°	184.7	184.5	184.2	184.0	183.7	183.4	183.2
120°	199.6	199.6	199.5	199.2	198.9	198.7	198.4
122.5°	214.5	214.2	214.0	213.8	213.7	213.4	213.2
125°	236.7	236.5	236.3	236.2	236.1	236.0	235.9
127.5°	258.4	258.1	257.8	257.4	257.2	256.9	256.6
130°	273.4	273.2	273.0	272.6	272.2	271.9	271.5
132.5°	287.6	287.2	286.9	286.6	286.2	286.0	285.7
135°	309.2	309.1	308.9	308.6	308.4	308.1	307.8
137.5°	329.6	329.6	329.3	329.0	328.6	328.2	327.9
140°	343.4	343.4	343.2	342.9	342.5	342.1	341.8
142.5°	355.9	356.0	355.8	355.4	355.1	354.7	354.4
145°	374.8	374.9	374.7	374.3	374.0	373.6	373.3
147.5°	391.5	391.6	391.6	391.2	390.8	390.5	390.2
150°	402.0	402.3	402.3	402.0	401.7	401.4	401.2
152.5°	412.5	412.9	412.9	412.5	412.1	411.9	411.5
155°	426.0	426.4	426.5	426.2	426.0	425.7	425.4
157.5°	438.4	439.0	439.1	438.6	438.2	437.8	437.4
160°	445.6	446.1	446.2	445.9	445.5	445.1	444.8
162.5°	452.3	452.9	453.0	452.5	452.1	451.7	451.3
165°	460.8	461.5	461.5	461.1	460.7	460.2	459.8
167.5°	467.9	468.5	468.6	468.1	467.6	467.2	466.7
170°	471.7	472.3	472.4	471.9	471.4	470.8	470.3
172.5°	474.7	475.3	475.3	474.7	474.2	473.7	473.1
175°	477.8	478.4	478.5	478.0	477.4	476.9	476.4
177.5°	479.0	479.5	479.5	479.0	478.7	478.2	477.8
180°	478.8	478.8	478.8	478.8	478.8	478.8	478.8

(END OF REPORT)