

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331501-940

Luminaire Tested: **S122DIW-S485D710U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331501-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S485D710U940-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 710 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4442.0 lumens  
Efficiency: N/A  
Efficacy: 118.1 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331501-940

CATALOG NUMBER: S122DIW-S485D710U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331501-940

CATALOG NUMBER: S122DIW-S485D710U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43									43																			
1	97	93	89	85	88	85	82	79	70	68	66	57	55	54	45	44	43	37									37																			
2	88	81	75	70	81	75	70	65	62	58	55	50	48	46	40	38	37	32									32																			
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	33	32	27									27																			
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24									24																			
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	26	24	21									21																			
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22	19									19																			
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17									17																			
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	20	17	15									15																			
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14									14																			
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13									13																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13990	13990	13990	13990
5°	15686	14083	12478	14083
10°	17974	13967	10799	13967
15°	19883	13710	9541	13710
20°	19581	13435	8698	13435
25°	17655	13069	8165	13069
30°	14590	12486	7774	12486
35°	10634	11874	7496	11874
40°	8494	11152	7341	11152
45°	7421	10319	7133	10319
50°	6978	9510	6993	9510
55°	6432	8690	6804	8690
60°	5893	7818	6516	7818
65°	5368	7033	6235	7033
70°	4877	6274	5816	6274
75°	4323	5421	5153	5421
80°	3710	4491	4147	4491
85°	3335	3335	2464	3335



TEST NUMBER: P331501-940

CATALOG NUMBER: S122DIW-S485D710U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	82.5	1.9
10°-20°	239.9	5.4
20°-30°	348.2	7.8
30°-40°	367.4	8.3
40°-50°	325.3	7.3
50°-60°	259.6	5.8
60°-70°	176.5	4.0
70°-80°	90.5	2.0
80°-90°	23.9	0.5
90°-100°	28.8	0.6
100°-110°	105.5	2.4
110°-120°	282.1	6.4
120°-130°	465.6	10.5
130°-140°	495.2	11.1
140°-150°	460.3	10.4
150°-160°	370.1	8.3
160°-170°	238.5	5.4
170°-180°	82.1	1.8
0°-30°	670.6	15.1
0°-40°	1038.0	23.4
0°-60°	1623.0	36.5
0°-90°	1913.8	43.1
90°-120°	416.4	9.4
90°-150°	1837.6	41.4
90°-180°	2528.0	56.9
0°-180°	4442.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	866	866	866	866	866	
5°	968	869	770	869	968	97
15°	1190	820	571	820	1190	328
25°	991	734	458	734	991	448
35°	540	602	380	602	540	351
45°	325	452	312	452	325	256
55°	228	309	242	309	228	205
65°	140	184	163	184	140	140
75°	69	87	83	87	69	74
85°	18	18	13	18	18	20
90°	17	1	17	1	17	8
95°	27	41	27	41	27	25
105°	47	190	47	190	47	49
115°	51	359	51	359	51	128
125°	534	508	534	508	534	462
135°	649	628	649	628	649	500
145°	740	728	740	728	740	463
155°	803	802	803	802	803	370
165°	843	845	843	845	843	238
175°	860	865	860	865	860	82
180°	863	863	863	863	863	



TEST NUMBER: P331501-940

CATALOG NUMBER: S122DIW-S485D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	906.5	906.8	907.2	903.0	902.5	902.5	898.8	895.5	891.8	886.7	887.3
5°	967.8	971.4	972.8	968.8	962.8	962.1	956.4	947.1	938.4	931.5	926.5
7.5°	1040.9	1042.3	1039.1	1033.8	1029.4	1021.4	1010.8	1000.5	986.1	972.8	963.0
10°	1096.3	1098.3	1092.6	1084.9	1078.6	1069.3	1054.0	1038.3	1019.4	1001.0	986.4
12.5°	1138.4	1143.4	1136.0	1135.1	1124.2	1111.4	1093.1	1085.2	1058.5	1033.0	1017.3
15°	1189.5	1189.2	1189.9	1183.6	1175.5	1173.6	1154.2	1133.3	1095.6	1080.7	1054.6
17.5°	1174.7	1179.8	1182.1	1182.1	1181.9	1180.6	1174.4	1161.2	1142.3	1118.0	1088.1
20°	1139.6	1146.2	1147.3	1154.9	1159.2	1164.9	1167.2	1163.6	1151.9	1131.6	1105.6
22.5°	1085.2	1087.1	1090.2	1102.2	1111.5	1125.7	1133.1	1145.4	1140.9	1131.0	1109.4
25°	991.0	987.7	999.3	1005.4	1027.0	1049.6	1066.0	1084.0	1099.9	1109.6	1103.3
27.5°	878.0	873.0	890.5	906.3	923.9	948.4	973.8	1003.9	1028.9	1060.2	1070.9
30°	782.6	785.6	802.3	819.2	845.9	880.5	909.1	942.1	977.8	1012.7	1037.0
32.5°	679.8	691.3	701.8	727.8	751.3	789.9	831.9	873.1	917.6	957.3	994.9
35°	539.5	552.8	567.5	586.5	619.4	657.7	698.7	754.3	814.9	869.2	913.8
37.5°	454.1	452.0	460.4	474.1	500.8	531.7	578.8	633.8	705.2	768.9	831.9
40°	403.0	401.6	407.6	420.3	440.6	463.2	504.5	552.8	619.1	697.0	772.0
42.5°	367.7	368.5	371.9	380.8	394.8	413.4	444.3	485.4	546.1	619.5	700.0
45°	325.0	327.3	331.0	335.4	343.3	358.6	375.9	405.3	453.3	514.5	593.8
47.5°	294.3	294.4	298.0	301.8	306.6	315.2	329.4	347.8	381.6	431.5	499.6
50°	277.8	275.4	278.0	281.1	286.1	292.0	301.4	318.7	341.3	381.7	438.5
52.5°	257.5	257.5	259.9	261.1	265.6	271.5	280.1	292.0	312.5	344.1	390.9
55°	228.5	230.2	231.5	233.4	237.5	241.7	248.4	256.5	272.4	296.0	330.6
57.5°	201.2	201.7	203.0	206.8	209.4	213.3	219.6	226.9	237.3	254.9	280.9
60°	182.5	182.5	185.1	186.8	190.1	194.1	199.1	206.2	215.4	229.8	250.7
62.5°	165.4	165.1	166.2	169.0	171.5	175.2	180.2	186.2	194.9	207.7	224.9
65°	140.5	139.9	141.9	142.5	145.2	148.8	152.8	159.2	166.2	175.5	190.8
67.5°	116.5	117.3	118.4	119.7	121.2	125.0	127.7	132.2	138.0	145.8	156.2
70°	103.3	103.3	103.3	104.2	106.2	108.3	110.9	114.6	120.2	126.9	136.2
72.5°	88.3	89.3	90.4	89.9	92.4	93.5	96.8	98.8	104.2	108.5	116.7
75°	69.3	69.3	69.3	70.9	72.0	72.9	74.9	77.0	79.6	84.9	89.3
77.5°	51.7	51.5	51.9	52.3	53.3	54.6	55.1	57.0	59.4	61.9	65.5
80°	39.9	40.7	40.9	41.6	41.6	42.3	42.6	44.9	46.6	48.3	50.6
82.5°	30.9	31.0	31.1	31.2	31.5	31.9	32.7	33.5	34.1	35.5	37.3
85°	18.0	17.7	17.7	18.3	18.0	18.0	18.6	19.4	19.4	19.6	20.7
87.5°	10.3	10.3	10.4	10.2	10.1	10.3	10.1	9.7	9.8	10.0	10.0
90°	16.9	16.6	16.3	16.1	15.8	15.2	14.5	13.9	13.2	12.5	11.4
92.5°	16.9	16.7	16.5	16.3	16.2	16.0	15.6	15.2	14.8	14.4	13.9
95°	26.8	27.0	27.1	27.3	27.4	27.1	26.4	25.8	25.1	24.3	23.4
97.5°	35.8	35.7	35.5	35.3	35.1	34.8	34.2	33.7	33.2	32.5	30.3
100°	41.8	41.6	41.3	41.0	40.8	40.0	38.9	37.8	36.6	35.6	33.3
102.5°	44.9	44.4	44.1	43.7	43.2	42.4	40.9	39.5	38.0	36.6	56.3
105°	47.4	46.9	46.4	45.7	45.2	44.1	42.6	41.1	39.6	38.1	76.0
107.5°	48.8	48.2	47.7	47.2	46.6	47.1	48.7	50.2	51.7	53.3	98.7
110°	49.3	48.8	48.2	47.6	47.1	53.8	67.6	81.5	95.4	109.2	149.4



TEST NUMBER: P331501-940

CATALOG NUMBER: S122DIW-S485D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	49.8	49.4	49.0	48.5	48.1	73.1	123.8	174.3	225.0	275.5	285.4
115°	51.2	61.2	71.2	81.1	91.1	128.2	192.4	256.7	320.9	385.1	381.7
117.5°	209.0	241.8	274.6	307.5	340.3	364.4	380.0	395.6	411.1	426.6	424.2
120°	380.8	399.5	418.2	436.9	455.7	464.2	462.5	460.9	459.2	457.5	455.0
122.5°	475.2	478.8	482.4	486.1	489.7	491.1	490.0	489.0	488.0	487.1	484.3
125°	533.7	533.3	532.9	532.4	532.1	531.4	530.4	529.4	528.4	527.4	524.9
127.5°	570.7	570.6	570.5	570.4	570.3	569.6	568.2	566.8	565.3	563.9	562.0
130°	593.7	593.8	594.0	594.1	594.2	593.5	592.0	590.5	589.0	587.5	585.9
132.5°	616.2	616.3	616.4	616.5	616.7	616.1	614.8	613.5	612.2	610.9	609.4
135°	648.6	648.9	649.2	649.4	649.7	649.2	647.7	646.4	645.0	643.6	642.4
137.5°	678.1	678.7	679.1	679.6	680.1	679.7	678.2	676.9	675.6	674.2	672.8
140°	696.7	697.3	698.0	698.7	699.5	699.2	697.9	696.7	695.4	694.2	692.6
142.5°	714.6	715.3	716.0	716.8	717.4	717.2	716.0	714.9	713.8	712.7	710.9
145°	739.8	740.4	741.1	741.8	742.5	742.3	741.4	740.4	739.5	738.5	736.1
147.5°	761.8	762.4	763.0	763.6	764.2	764.1	763.4	762.7	762.0	761.2	758.8
150°	775.3	776.0	776.7	777.4	778.1	778.0	777.2	776.3	775.5	774.7	772.5
152.5°	786.8	787.7	788.6	789.5	790.5	790.5	789.7	788.8	788.0	787.2	785.1
155°	802.8	803.9	805.0	806.1	807.2	807.4	806.6	805.7	804.9	804.1	802.4
157.5°	817.3	818.5	819.6	820.6	821.7	821.8	820.8	819.9	818.9	818.0	816.8
160°	825.9	826.9	827.8	828.8	829.7	829.8	829.0	828.1	827.3	826.5	825.6
162.5°	832.9	834.0	835.3	836.4	837.7	837.8	836.8	835.9	834.9	834.0	833.3
165°	843.4	844.4	845.3	846.2	847.2	847.2	846.2	845.3	844.4	843.4	842.9
167.5°	850.0	851.2	852.5	853.7	855.0	855.1	854.2	853.2	852.2	851.2	850.9
170°	854.0	855.2	856.5	857.7	859.0	859.1	858.1	857.2	856.2	855.2	855.0
172.5°	856.9	858.2	859.4	860.7	861.9	862.1	861.1	860.1	859.2	858.2	857.9
175°	859.6	860.9	862.4	863.7	865.1	865.3	864.3	863.4	862.5	861.5	861.2
177.5°	861.2	862.2	863.2	864.2	865.2	865.3	864.5	863.8	863.0	862.2	862.1
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331501-940

CATALOG NUMBER: S122DIW-S485D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	889.1	887.0	885.6	880.9	876.6	872.4	871.0	871.6	865.7	860.1	857.7
5°	923.8	917.1	910.8	901.8	891.2	879.5	873.5	868.9	857.2	844.5	837.2
7.5°	954.8	945.3	933.1	916.2	900.7	882.3	870.7	860.4	843.3	825.5	814.6
10°	973.7	960.7	945.1	924.4	905.4	883.2	867.5	851.9	831.9	810.6	797.3
12.5°	990.0	972.5	957.1	930.6	908.1	880.2	861.7	839.6	818.6	793.3	780.2
15°	1028.7	996.4	967.1	937.1	909.5	870.5	849.9	820.2	792.6	761.3	746.3
17.5°	1058.5	1022.3	976.2	938.1	905.8	862.6	832.3	796.8	764.1	728.3	708.0
20°	1075.7	1034.0	984.4	939.1	900.4	851.2	818.2	781.9	743.6	703.3	681.4
22.5°	1085.7	1042.1	992.9	935.1	889.8	841.9	800.4	760.6	721.8	678.3	655.2
25°	1089.0	1049.0	997.0	931.7	876.5	822.2	772.2	733.6	686.7	646.0	612.4
27.5°	1073.1	1044.5	994.5	925.5	861.1	797.6	742.0	698.2	648.6	604.6	570.7
30°	1053.6	1037.0	988.4	919.1	848.8	780.6	719.3	669.7	620.5	575.8	541.2
32.5°	1023.6	1019.9	977.2	910.1	835.8	759.0	695.6	645.4	590.8	547.0	514.0
35°	964.4	980.4	953.4	889.8	811.2	728.3	659.7	602.4	545.8	503.8	472.9
37.5°	885.2	924.9	917.8	860.1	778.0	694.9	619.1	559.3	505.3	463.0	432.6
40°	830.5	881.2	888.5	837.5	754.7	669.1	588.8	529.1	476.5	437.9	407.2
42.5°	772.0	831.1	851.2	810.4	729.1	641.9	561.6	499.9	447.8	410.2	383.1
45°	673.7	752.0	788.3	764.9	686.3	597.1	514.5	451.9	404.7	369.3	348.3
47.5°	581.8	667.4	716.2	707.9	638.8	550.5	468.9	408.8	362.7	334.6	315.8
50°	516.8	604.8	663.7	666.4	604.8	517.2	435.2	378.6	336.4	310.0	294.7
52.5°	460.4	544.3	608.6	622.7	566.7	482.5	405.1	348.8	311.6	287.4	273.7
55°	386.6	457.5	528.9	554.8	509.9	429.9	358.3	308.7	273.8	257.1	245.1
57.5°	321.5	380.6	446.4	475.1	447.4	379.0	311.8	268.8	240.4	225.8	216.6
60°	287.0	333.7	392.3	426.6	402.6	341.7	283.0	242.1	218.8	205.8	197.2
62.5°	255.1	296.4	345.9	377.3	364.3	306.7	254.3	218.1	198.0	185.8	179.6
65°	210.4	243.1	281.4	310.4	301.8	258.1	215.2	184.1	168.2	158.5	153.6
67.5°	173.3	196.9	223.5	248.8	241.8	210.9	176.5	152.3	140.4	132.1	129.1
70°	149.9	167.8	191.5	211.8	206.2	180.8	153.6	132.9	122.5	115.6	112.5
72.5°	127.5	142.2	160.3	176.9	173.1	152.0	129.3	113.7	105.8	99.3	96.8
75°	96.2	107.5	118.6	129.6	128.6	112.3	98.9	86.9	80.6	75.6	74.6
77.5°	71.1	77.4	84.9	91.4	89.6	80.3	69.8	63.0	58.3	54.9	54.4
80°	54.3	58.0	63.3	67.9	65.6	61.6	53.3	48.3	44.9	41.6	40.3
82.5°	39.3	43.1	46.2	48.8	47.0	43.2	38.1	34.7	32.7	30.4	29.9
85°	20.7	22.6	24.0	24.6	24.0	21.7	19.4	18.0	16.3	15.3	15.0
87.5°	10.1	9.8	9.6	9.9	8.7	8.5	7.1	6.0	6.1	6.1	5.8
90°	10.3	9.2	8.0	6.7	5.2	3.7	2.1	0.6	2.1	3.7	5.2
92.5°	13.4	12.8	12.3	12.0	12.2	12.3	12.5	12.6	12.5	12.3	12.2
95°	22.4	21.4	20.4	22.3	26.8	31.4	36.0	40.6	36.0	31.4	26.8
97.5°	28.1	25.9	23.6	28.9	41.8	54.8	67.6	80.5	67.6	54.8	41.8
100°	30.9	28.5	26.1	34.5	53.5	72.5	91.5	110.5	91.5	72.5	53.5
102.5°	76.1	95.8	115.5	127.3	131.3	135.4	139.5	143.5	139.5	135.4	131.3
105°	113.8	151.7	189.6	206.4	202.2	198.1	193.9	189.8	193.9	198.1	202.2
107.5°	144.2	189.6	235.0	256.0	252.6	249.3	245.9	242.5	245.9	249.3	252.6
110°	189.4	229.5	269.6	288.2	285.3	282.4	279.5	276.5	279.5	282.4	285.3





TEST NUMBER: P331501-940

CATALOG NUMBER: S122DIW-S485D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	295.3	305.2	315.1	318.8	316.2	313.7	311.1	308.5	311.1	313.7	316.2
115°	378.3	374.8	371.3	368.4	366.0	363.6	361.3	358.9	361.3	363.6	366.0
117.5°	421.9	419.5	417.1	414.6	411.9	409.3	406.6	404.0	406.6	409.3	411.9
120°	452.5	450.0	447.5	445.3	443.2	441.1	439.1	436.9	439.1	441.1	443.2
122.5°	481.6	478.8	476.2	473.7	471.5	469.3	467.2	464.9	467.2	469.3	471.5
125°	522.2	519.6	516.9	514.7	512.9	511.1	509.3	507.5	509.3	511.1	512.9
127.5°	560.0	558.0	556.1	554.1	552.1	550.1	548.0	546.1	548.0	550.1	552.1
130°	584.3	582.8	581.3	579.4	577.2	575.0	572.7	570.5	572.7	575.0	577.2
132.5°	607.8	606.3	604.8	603.1	601.2	599.3	597.4	595.6	597.4	599.3	601.2
135°	641.1	639.9	638.6	636.9	634.6	632.4	630.2	628.0	630.2	632.4	634.6
137.5°	671.4	669.9	668.5	667.0	665.5	664.0	662.4	660.8	662.4	664.0	665.5
140°	691.1	689.6	688.0	686.7	685.6	684.5	683.4	682.3	683.4	684.5	685.6
142.5°	709.2	707.4	705.6	704.3	703.3	702.3	701.2	700.3	701.2	702.3	703.3
145°	733.8	731.4	729.1	727.9	728.1	728.3	728.3	728.5	728.3	728.3	728.1
147.5°	756.5	754.2	751.9	751.0	751.5	752.1	752.6	753.0	752.6	752.1	751.5
150°	770.3	768.0	765.8	765.2	766.2	767.1	768.1	769.1	768.1	767.1	766.2
152.5°	782.9	780.9	778.7	778.2	779.3	780.4	781.5	782.6	781.5	780.4	779.3
155°	800.7	799.1	797.4	797.2	798.4	799.7	800.9	802.2	800.9	799.7	798.4
157.5°	815.6	814.5	813.3	813.3	814.3	815.4	816.5	817.5	816.5	815.4	814.3
160°	824.8	824.0	823.1	823.1	824.0	824.8	825.6	826.5	825.6	824.8	824.0
162.5°	832.6	831.8	831.1	831.2	832.0	832.9	833.7	834.5	833.7	832.9	832.0
165°	842.5	842.1	841.7	841.9	842.8	843.6	844.4	845.3	844.4	843.6	842.8
167.5°	850.4	850.1	849.7	849.9	850.7	851.6	852.4	853.2	852.4	851.6	850.7
170°	854.7	854.3	854.1	854.3	855.2	856.0	856.8	857.7	856.8	856.0	855.2
172.5°	857.6	857.4	857.1	857.4	858.2	859.1	859.9	860.7	859.9	859.1	858.2
175°	860.9	860.6	860.3	860.7	861.7	862.6	863.6	864.6	863.6	862.6	861.7
177.5°	862.0	861.8	861.7	862.1	862.9	863.6	864.4	865.2	864.4	863.6	862.9
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331501-940

CATALOG NUMBER: S122DIW-S485D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	855.1	853.5	847.8	844.9	840.2	835.6	832.7	834.0	835.1	834.6	833.7
5°	830.5	824.2	814.6	806.2	800.2	789.3	784.6	782.3	780.2	777.9	775.6
7.5°	801.4	791.4	777.6	765.7	754.5	740.8	733.1	728.3	723.5	718.3	713.6
10°	780.6	766.6	752.0	735.3	722.0	709.6	698.7	691.3	684.7	678.3	673.7
12.5°	758.8	742.6	724.5	701.8	687.1	669.4	667.8	654.9	644.4	640.5	635.1
15°	724.0	701.3	678.3	651.4	639.7	623.8	613.8	603.8	594.8	588.4	586.7
17.5°	684.5	655.1	632.3	613.0	593.9	577.5	568.3	560.3	552.9	544.4	543.3
20°	654.3	629.1	604.1	587.1	567.5	550.8	539.5	531.5	525.1	520.1	515.9
22.5°	625.9	598.2	575.3	556.7	537.3	523.9	515.0	507.3	502.0	496.5	492.4
25°	580.1	558.5	533.5	512.6	496.5	487.9	480.5	473.9	470.6	466.9	462.3
27.5°	540.1	516.0	492.7	476.4	462.4	454.7	449.5	445.0	441.8	439.7	437.0
30°	511.8	487.5	469.2	453.3	441.6	433.9	430.6	427.9	424.3	422.9	421.6
32.5°	484.6	462.8	447.1	433.3	422.1	417.1	414.1	411.7	408.8	407.5	404.8
35°	446.2	427.9	412.6	404.9	395.9	391.6	389.3	385.9	383.3	382.0	381.7
37.5°	410.1	394.1	384.1	374.3	370.4	367.7	364.6	362.3	361.5	361.3	361.0
40°	386.6	373.6	364.6	356.7	355.0	351.0	348.3	346.3	346.3	346.7	346.3
42.5°	365.3	353.7	345.7	338.9	336.9	334.5	331.8	331.7	332.3	333.3	332.3
45°	333.1	324.7	319.1	315.7	312.0	309.7	309.3	310.4	310.7	311.0	312.0
47.5°	303.3	297.7	292.7	289.0	287.4	287.0	286.6	288.3	289.9	290.5	292.0
50°	285.7	279.4	275.1	272.8	271.4	270.7	271.4	273.4	274.7	276.4	277.4
52.5°	266.0	261.5	258.6	256.7	256.2	256.6	256.7	259.0	261.2	261.7	262.3
55°	238.8	235.4	234.8	231.8	233.1	232.7	234.4	235.8	237.7	239.8	240.1
57.5°	211.6	208.9	207.1	207.4	207.8	209.3	210.6	213.0	215.2	217.2	217.5
60°	193.5	192.2	191.2	191.2	191.8	193.9	195.5	197.8	199.1	200.5	201.4
62.5°	177.0	175.7	174.6	175.1	176.9	178.1	180.0	181.3	182.6	184.0	184.4
65°	150.9	150.2	151.2	151.9	152.2	153.8	156.2	157.2	158.5	159.2	161.5
67.5°	126.8	127.0	126.8	127.8	129.7	130.1	132.2	134.6	134.9	136.2	137.7
70°	110.6	111.2	111.9	112.5	114.2	114.9	116.5	117.5	118.9	119.8	120.9
72.5°	95.7	95.8	96.5	96.3	97.7	99.2	100.6	101.6	102.9	104.2	105.1
75°	73.6	73.6	74.3	74.6	76.2	77.9	77.6	78.3	79.6	81.0	81.6
77.5°	53.8	53.1	53.8	54.0	54.6	56.0	56.3	57.2	58.8	58.3	59.0
80°	40.9	39.9	40.9	41.3	41.3	43.0	43.0	43.6	44.6	43.6	44.6
82.5°	29.2	28.8	29.5	29.6	30.1	30.1	30.7	30.9	31.8	31.4	31.8
85°	14.6	14.4	14.6	14.4	14.6	15.0	15.0	14.6	14.6	15.3	14.4
87.5°	5.9	5.9	5.8	6.1	6.0	6.0	5.8	6.0	6.2	5.7	5.8
90°	6.7	8.0	9.2	10.3	11.4	12.5	13.2	13.9	14.5	15.2	15.8
92.5°	12.0	12.3	12.8	13.4	13.9	14.4	14.8	15.2	15.6	16.0	16.2
95°	22.3	20.4	21.4	22.4	23.4	24.3	25.1	25.8	26.4	27.1	27.4
97.5°	28.9	23.6	25.9	28.1	30.3	32.5	33.2	33.7	34.2	34.8	35.1
100°	34.5	26.1	28.5	30.9	33.3	35.6	36.6	37.8	38.9	40.0	40.8
102.5°	127.3	115.5	95.8	76.1	56.3	36.6	38.0	39.5	40.9	42.4	43.2
105°	206.4	189.6	151.7	113.8	76.0	38.1	39.6	41.1	42.6	44.1	45.2
107.5°	256.0	235.0	189.6	144.2	98.7	53.3	51.7	50.2	48.7	47.1	46.6
110°	288.2	269.6	229.5	189.4	149.4	109.2	95.4	81.5	67.6	53.8	47.1



TEST NUMBER: P331501-940

CATALOG NUMBER: S122DIW-S485D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	318.8	315.1	305.2	295.3	285.4	275.5	225.0	174.3	123.8	73.1	48.1
115°	368.4	371.3	374.8	378.3	381.7	385.1	320.9	256.7	192.4	128.2	91.1
117.5°	414.6	417.1	419.5	421.9	424.2	426.6	411.1	395.6	380.0	364.4	340.3
120°	445.3	447.5	450.0	452.5	455.0	457.5	459.2	460.9	462.5	464.2	455.7
122.5°	473.7	476.2	478.8	481.6	484.3	487.1	488.0	489.0	490.0	491.1	489.7
125°	514.7	516.9	519.6	522.2	524.9	527.4	528.4	529.4	530.4	531.4	532.1
127.5°	554.1	556.1	558.0	560.0	562.0	563.9	565.3	566.8	568.2	569.6	570.3
130°	579.4	581.3	582.8	584.3	585.9	587.5	589.0	590.5	592.0	593.5	594.2
132.5°	603.1	604.8	606.3	607.8	609.4	610.9	612.2	613.5	614.8	616.1	616.7
135°	636.9	638.6	639.9	641.1	642.4	643.6	645.0	646.4	647.7	649.2	649.7
137.5°	667.0	668.5	669.9	671.4	672.8	674.2	675.6	676.9	678.2	679.7	680.1
140°	686.7	688.0	689.6	691.1	692.6	694.2	695.4	696.7	697.9	699.2	699.5
142.5°	704.3	705.6	707.4	709.2	710.9	712.7	713.8	714.9	716.0	717.2	717.4
145°	727.9	729.1	731.4	733.8	736.1	738.5	739.5	740.4	741.4	742.3	742.5
147.5°	751.0	751.9	754.2	756.5	758.8	761.2	762.0	762.7	763.4	764.1	764.2
150°	765.2	765.8	768.0	770.3	772.5	774.7	775.5	776.3	777.2	778.0	778.1
152.5°	778.2	778.7	780.9	782.9	785.1	787.2	788.0	788.8	789.7	790.5	790.5
155°	797.2	797.4	799.1	800.7	802.4	804.1	804.9	805.7	806.6	807.4	807.2
157.5°	813.3	813.3	814.5	815.6	816.8	818.0	818.9	819.9	820.8	821.8	821.7
160°	823.1	823.1	824.0	824.8	825.6	826.5	827.3	828.1	829.0	829.8	829.7
162.5°	831.2	831.1	831.8	832.6	833.3	834.0	834.9	835.9	836.8	837.8	837.7
165°	841.9	841.7	842.1	842.5	842.9	843.4	844.4	845.3	846.2	847.2	847.2
167.5°	849.9	849.7	850.1	850.4	850.9	851.2	852.2	853.2	854.2	855.1	855.0
170°	854.3	854.1	854.3	854.7	855.0	855.2	856.2	857.2	858.1	859.1	859.0
172.5°	857.4	857.1	857.4	857.6	857.9	858.2	859.2	860.1	861.1	862.1	861.9
175°	860.7	860.3	860.6	860.9	861.2	861.5	862.5	863.4	864.3	865.3	865.1
177.5°	862.1	861.7	861.8	862.0	862.1	862.2	863.0	863.8	864.5	865.3	865.2
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331501-940

CATALOG NUMBER: S122DIW-S485D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	831.1	830.5	830.5	828.1	830.5	830.5	831.1	833.7	834.6	835.1	834.0
5°	771.0	769.9	768.3	769.9	768.3	769.9	771.0	775.6	777.9	780.2	782.3
7.5°	711.5	707.5	706.9	702.9	706.9	707.5	711.5	713.6	718.3	723.5	728.3
10°	668.1	665.4	665.0	658.7	665.0	665.4	668.1	673.7	678.3	684.7	691.3
12.5°	635.0	628.6	629.9	626.2	629.9	628.6	635.0	635.1	640.5	644.4	654.9
15°	577.7	577.7	576.5	570.8	576.5	577.7	577.7	586.7	588.4	594.8	603.8
17.5°	536.7	536.0	532.8	534.4	532.8	536.0	536.7	543.3	544.4	552.9	560.3
20°	512.2	510.1	506.2	506.2	506.2	510.1	512.2	515.9	520.1	525.1	531.5
22.5°	489.0	488.8	484.6	486.0	484.6	488.8	489.0	492.4	496.5	502.0	507.3
25°	461.9	459.2	457.3	458.3	457.3	459.2	461.9	462.3	466.9	470.6	473.9
27.5°	436.2	434.7	434.6	431.9	434.6	434.7	436.2	437.0	439.7	441.8	445.0
30°	421.2	417.9	418.6	417.0	418.6	417.9	421.2	421.6	422.9	424.3	427.9
32.5°	404.2	403.1	402.3	400.9	402.3	403.1	404.2	404.8	407.5	408.8	411.7
35°	380.9	381.3	379.6	380.3	379.6	381.3	380.9	381.7	382.0	383.3	385.9
37.5°	360.7	361.8	361.0	361.1	361.0	361.8	360.7	361.0	361.3	361.5	362.3
40°	347.3	347.3	347.3	348.3	347.3	347.3	347.3	346.3	346.7	346.3	346.3
42.5°	334.6	334.0	333.5	333.4	333.5	334.0	334.6	332.3	333.3	332.3	331.7
45°	312.7	313.7	314.1	312.4	314.1	313.7	312.7	312.0	311.0	310.7	310.4
47.5°	292.9	293.0	292.9	294.4	292.9	293.0	292.9	292.0	290.5	289.9	288.3
50°	279.1	278.4	279.1	278.4	279.1	278.4	279.1	277.4	276.4	274.7	273.4
52.5°	264.4	264.6	264.1	264.0	264.1	264.6	264.4	262.3	261.7	261.2	259.0
55°	241.5	242.1	241.7	241.7	241.7	242.1	241.5	240.1	239.8	237.7	235.8
57.5°	217.7	218.3	218.7	217.2	218.7	218.3	217.7	217.5	217.2	215.2	213.0
60°	201.2	202.8	202.5	201.8	202.5	202.8	201.2	201.4	200.5	199.1	197.8
62.5°	185.9	186.5	186.5	186.4	186.5	186.5	185.9	184.4	184.0	182.6	181.3
65°	162.5	163.2	162.2	163.2	162.2	163.2	162.5	161.5	159.2	158.5	157.2
67.5°	137.2	137.5	138.2	138.7	138.2	137.5	137.2	137.7	136.2	134.9	134.6
70°	121.5	121.2	122.3	123.2	122.3	121.2	121.5	120.9	119.8	118.9	117.5
72.5°	105.0	105.8	105.4	106.2	105.4	105.8	105.0	105.1	104.2	102.9	101.6
75°	81.0	81.9	81.6	82.6	81.6	81.9	81.0	81.6	81.0	79.6	78.3
77.5°	58.5	58.6	58.5	59.0	58.5	58.6	58.5	59.0	58.3	58.8	57.2
80°	44.6	44.0	43.2	44.6	43.2	44.0	44.6	44.6	43.6	44.6	43.6
82.5°	31.0	31.5	30.8	30.8	30.8	31.5	31.0	31.8	31.4	31.8	30.9
85°	14.4	14.0	13.3	13.3	13.3	14.0	14.4	14.4	15.3	14.6	14.6
87.5°	5.9	5.6	5.7	5.5	5.7	5.6	5.9	5.8	5.7	6.2	6.0
90°	16.1	16.3	16.6	16.9	16.6	16.3	16.1	15.8	15.2	14.5	13.9
92.5°	16.3	16.5	16.7	16.9	16.7	16.5	16.3	16.2	16.0	15.6	15.2
95°	27.3	27.1	27.0	26.8	27.0	27.1	27.3	27.4	27.1	26.4	25.8
97.5°	35.3	35.5	35.7	35.8	35.7	35.5	35.3	35.1	34.8	34.2	33.7
100°	41.0	41.3	41.6	41.8	41.6	41.3	41.0	40.8	40.0	38.9	37.8
102.5°	43.7	44.1	44.4	44.9	44.4	44.1	43.7	43.2	42.4	40.9	39.5
105°	45.7	46.4	46.9	47.4	46.9	46.4	45.7	45.2	44.1	42.6	41.1
107.5°	47.2	47.7	48.2	48.8	48.2	47.7	47.2	46.6	47.1	48.7	50.2
110°	47.6	48.2	48.8	49.3	48.8	48.2	47.6	47.1	53.8	67.6	81.5



TEST NUMBER: P331501-940

CATALOG NUMBER: S122DIW-S485D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	48.5	49.0	49.4	49.8	49.4	49.0	48.5	48.1	73.1	123.8	174.3
115°	81.1	71.2	61.2	51.2	61.2	71.2	81.1	91.1	128.2	192.4	256.7
117.5°	307.5	274.6	241.8	209.0	241.8	274.6	307.5	340.3	364.4	380.0	395.6
120°	436.9	418.2	399.5	380.8	399.5	418.2	436.9	455.7	464.2	462.5	460.9
122.5°	486.1	482.4	478.8	475.2	478.8	482.4	486.1	489.7	491.1	490.0	489.0
125°	532.4	532.9	533.3	533.7	533.3	532.9	532.4	532.1	531.4	530.4	529.4
127.5°	570.4	570.5	570.6	570.7	570.6	570.5	570.4	570.3	569.6	568.2	566.8
130°	594.1	594.0	593.8	593.7	593.8	594.0	594.1	594.2	593.5	592.0	590.5
132.5°	616.5	616.4	616.3	616.2	616.3	616.4	616.5	616.7	616.1	614.8	613.5
135°	649.4	649.2	648.9	648.6	648.9	649.2	649.4	649.7	649.2	647.7	646.4
137.5°	679.6	679.1	678.7	678.1	678.7	679.1	679.6	680.1	679.7	678.2	676.9
140°	698.7	698.0	697.3	696.7	697.3	698.0	698.7	699.5	699.2	697.9	696.7
142.5°	716.8	716.0	715.3	714.6	715.3	716.0	716.8	717.4	717.2	716.0	714.9
145°	741.8	741.1	740.4	739.8	740.4	741.1	741.8	742.5	742.3	741.4	740.4
147.5°	763.6	763.0	762.4	761.8	762.4	763.0	763.6	764.2	764.1	763.4	762.7
150°	777.4	776.7	776.0	775.3	776.0	776.7	777.4	778.1	778.0	777.2	776.3
152.5°	789.5	788.6	787.7	786.8	787.7	788.6	789.5	790.5	790.5	789.7	788.8
155°	806.1	805.0	803.9	802.8	803.9	805.0	806.1	807.2	807.4	806.6	805.7
157.5°	820.6	819.6	818.5	817.3	818.5	819.6	820.6	821.7	821.8	820.8	819.9
160°	828.8	827.8	826.9	825.9	826.9	827.8	828.8	829.7	829.8	829.0	828.1
162.5°	836.4	835.3	834.0	832.9	834.0	835.3	836.4	837.7	837.8	836.8	835.9
165°	846.2	845.3	844.4	843.4	844.4	845.3	846.2	847.2	847.2	846.2	845.3
167.5°	853.7	852.5	851.2	850.0	851.2	852.5	853.7	855.0	855.1	854.2	853.2
170°	857.7	856.5	855.2	854.0	855.2	856.5	857.7	859.0	859.1	858.1	857.2
172.5°	860.7	859.4	858.2	856.9	858.2	859.4	860.7	861.9	862.1	861.1	860.1
175°	863.7	862.4	860.9	859.6	860.9	862.4	863.7	865.1	865.3	864.3	863.4
177.5°	864.2	863.2	862.2	861.2	862.2	863.2	864.2	865.2	865.3	864.5	863.8
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331501-940

CATALOG NUMBER: S122DIW-S485D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	832.7	835.6	840.2	844.9	847.8	853.5	855.1	857.7	860.1	865.7	871.6
5°	784.6	789.3	800.2	806.2	814.6	824.2	830.5	837.2	844.5	857.2	868.9
7.5°	733.1	740.8	754.5	765.7	777.6	791.4	801.4	814.6	825.5	843.3	860.4
10°	698.7	709.6	722.0	735.3	752.0	766.6	780.6	797.3	810.6	831.9	851.9
12.5°	667.8	669.4	687.1	701.8	724.5	742.6	758.8	780.2	793.3	818.6	839.6
15°	613.8	623.8	639.7	651.4	678.3	701.3	724.0	746.3	761.3	792.6	820.2
17.5°	568.3	577.5	593.9	613.0	632.3	655.1	684.5	708.0	728.3	764.1	796.8
20°	539.5	550.8	567.5	587.1	604.1	629.1	654.3	681.4	703.3	743.6	781.9
22.5°	515.0	523.9	537.3	556.7	575.3	598.2	625.9	655.2	678.3	721.8	760.6
25°	480.5	487.9	496.5	512.6	533.5	558.5	580.1	612.4	646.0	686.7	733.6
27.5°	449.5	454.7	462.4	476.4	492.7	516.0	540.1	570.7	604.6	648.6	698.2
30°	430.6	433.9	441.6	453.3	469.2	487.5	511.8	541.2	575.8	620.5	669.7
32.5°	414.1	417.1	422.1	433.3	447.1	462.8	484.6	514.0	547.0	590.8	645.4
35°	389.3	391.6	395.9	404.9	412.6	427.9	446.2	472.9	503.8	545.8	602.4
37.5°	364.6	367.7	370.4	374.3	384.1	394.1	410.1	432.6	463.0	505.3	559.3
40°	348.3	351.0	355.0	356.7	364.6	373.6	386.6	407.2	437.9	476.5	529.1
42.5°	331.8	334.5	336.9	338.9	345.7	353.7	365.3	383.1	410.2	447.8	499.9
45°	309.3	309.7	312.0	315.7	319.1	324.7	333.1	348.3	369.3	404.7	451.9
47.5°	286.6	287.0	287.4	289.0	292.7	297.7	303.3	315.8	334.6	362.7	408.8
50°	271.4	270.7	271.4	272.8	275.1	279.4	285.7	294.7	310.0	336.4	378.6
52.5°	256.7	256.6	256.2	256.7	258.6	261.5	266.0	273.7	287.4	311.6	348.8
55°	234.4	232.7	233.1	231.8	234.8	235.4	238.8	245.1	257.1	273.8	308.7
57.5°	210.6	209.3	207.8	207.4	207.1	208.9	211.6	216.6	225.8	240.4	268.8
60°	195.5	193.9	191.8	191.2	191.2	192.2	193.5	197.2	205.8	218.8	242.1
62.5°	180.0	178.1	176.9	175.1	174.6	175.7	177.0	179.6	185.8	198.0	218.1
65°	156.2	153.8	152.2	151.9	151.2	150.2	150.9	153.6	158.5	168.2	184.1
67.5°	132.2	130.1	129.7	127.8	126.8	127.0	126.8	129.1	132.1	140.4	152.3
70°	116.5	114.9	114.2	112.5	111.9	111.2	110.6	112.5	115.6	122.5	132.9
72.5°	100.6	99.2	97.7	96.3	96.5	95.8	95.7	96.8	99.3	105.8	113.7
75°	77.6	77.9	76.2	74.6	74.3	73.6	73.6	74.6	75.6	80.6	86.9
77.5°	56.3	56.0	54.6	54.0	53.8	53.1	53.8	54.4	54.9	58.3	63.0
80°	43.0	43.0	41.3	41.3	40.9	39.9	40.9	40.3	41.6	44.9	48.3
82.5°	30.7	30.1	30.1	29.6	29.5	28.8	29.2	29.9	30.4	32.7	34.7
85°	15.0	15.0	14.6	14.4	14.6	14.4	14.6	15.0	15.3	16.3	18.0
87.5°	5.8	6.0	6.0	6.1	5.8	5.9	5.9	5.8	6.1	6.1	6.0
90°	13.2	12.5	11.4	10.3	9.2	8.0	6.7	5.2	3.7	2.1	0.6
92.5°	14.8	14.4	13.9	13.4	12.8	12.3	12.0	12.2	12.3	12.5	12.6
95°	25.1	24.3	23.4	22.4	21.4	20.4	22.3	26.8	31.4	36.0	40.6
97.5°	33.2	32.5	30.3	28.1	25.9	23.6	28.9	41.8	54.8	67.6	80.5
100°	36.6	35.6	33.3	30.9	28.5	26.1	34.5	53.5	72.5	91.5	110.5
102.5°	38.0	36.6	56.3	76.1	95.8	115.5	127.3	131.3	135.4	139.5	143.5
105°	39.6	38.1	76.0	113.8	151.7	189.6	206.4	202.2	198.1	193.9	189.8
107.5°	51.7	53.3	98.7	144.2	189.6	235.0	256.0	252.6	249.3	245.9	242.5
110°	95.4	109.2	149.4	189.4	229.5	269.6	288.2	285.3	282.4	279.5	276.5



TEST NUMBER: P331501-940

CATALOG NUMBER: S122DIW-S485D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	225.0	275.5	285.4	295.3	305.2	315.1	318.8	316.2	313.7	311.1	308.5
115°	320.9	385.1	381.7	378.3	374.8	371.3	368.4	366.0	363.6	361.3	358.9
117.5°	411.1	426.6	424.2	421.9	419.5	417.1	414.6	411.9	409.3	406.6	404.0
120°	459.2	457.5	455.0	452.5	450.0	447.5	445.3	443.2	441.1	439.1	436.9
122.5°	488.0	487.1	484.3	481.6	478.8	476.2	473.7	471.5	469.3	467.2	464.9
125°	528.4	527.4	524.9	522.2	519.6	516.9	514.7	512.9	511.1	509.3	507.5
127.5°	565.3	563.9	562.0	560.0	558.0	556.1	554.1	552.1	550.1	548.0	546.1
130°	589.0	587.5	585.9	584.3	582.8	581.3	579.4	577.2	575.0	572.7	570.5
132.5°	612.2	610.9	609.4	607.8	606.3	604.8	603.1	601.2	599.3	597.4	595.6
135°	645.0	643.6	642.4	641.1	639.9	638.6	636.9	634.6	632.4	630.2	628.0
137.5°	675.6	674.2	672.8	671.4	669.9	668.5	667.0	665.5	664.0	662.4	660.8
140°	695.4	694.2	692.6	691.1	689.6	688.0	686.7	685.6	684.5	683.4	682.3
142.5°	713.8	712.7	710.9	709.2	707.4	705.6	704.3	703.3	702.3	701.2	700.3
145°	739.5	738.5	736.1	733.8	731.4	729.1	727.9	728.1	728.3	728.3	728.5
147.5°	762.0	761.2	758.8	756.5	754.2	751.9	751.0	751.5	752.1	752.6	753.0
150°	775.5	774.7	772.5	770.3	768.0	765.8	765.2	766.2	767.1	768.1	769.1
152.5°	788.0	787.2	785.1	782.9	780.9	778.7	778.2	779.3	780.4	781.5	782.6
155°	804.9	804.1	802.4	800.7	799.1	797.4	797.2	798.4	799.7	800.9	802.2
157.5°	818.9	818.0	816.8	815.6	814.5	813.3	813.3	814.3	815.4	816.5	817.5
160°	827.3	826.5	825.6	824.8	824.0	823.1	823.1	824.0	824.8	825.6	826.5
162.5°	834.9	834.0	833.3	832.6	831.8	831.1	831.2	832.0	832.9	833.7	834.5
165°	844.4	843.4	842.9	842.5	842.1	841.7	841.9	842.8	843.6	844.4	845.3
167.5°	852.2	851.2	850.9	850.4	850.1	849.7	849.9	850.7	851.6	852.4	853.2
170°	856.2	855.2	855.0	854.7	854.3	854.1	854.3	855.2	856.0	856.8	857.7
172.5°	859.2	858.2	857.9	857.6	857.4	857.1	857.4	858.2	859.1	859.9	860.7
175°	862.5	861.5	861.2	860.9	860.6	860.3	860.7	861.7	862.6	863.6	864.6
177.5°	863.0	862.2	862.1	862.0	861.8	861.7	862.1	862.9	863.6	864.4	865.2
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331501-940

CATALOG NUMBER: S122DIW-S485D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	871.0	872.4	876.6	880.9	885.6	887.0	889.1	887.3	886.7	891.8	895.5
5°	873.5	879.5	891.2	901.8	910.8	917.1	923.8	926.5	931.5	938.4	947.1
7.5°	870.7	882.3	900.7	916.2	933.1	945.3	954.8	963.0	972.8	986.1	1000.5
10°	867.5	883.2	905.4	924.4	945.1	960.7	973.7	986.4	1001.0	1019.4	1038.3
12.5°	861.7	880.2	908.1	930.6	957.1	972.5	990.0	1017.3	1033.0	1058.5	1085.2
15°	849.9	870.5	909.5	937.1	967.1	996.4	1028.7	1054.6	1080.7	1095.6	1133.3
17.5°	832.3	862.6	905.8	938.1	976.2	1022.3	1058.5	1088.1	1118.0	1142.3	1161.2
20°	818.2	851.2	900.4	939.1	984.4	1034.0	1075.7	1105.6	1131.6	1151.9	1163.6
22.5°	800.4	841.9	889.8	935.1	992.9	1042.1	1085.7	1109.4	1131.0	1140.9	1145.4
25°	772.2	822.2	876.5	931.7	997.0	1049.0	1089.0	1103.3	1109.6	1099.9	1084.0
27.5°	742.0	797.6	861.1	925.5	994.5	1044.5	1073.1	1070.9	1060.2	1028.9	1003.9
30°	719.3	780.6	848.8	919.1	988.4	1037.0	1053.6	1037.0	1012.7	977.8	942.1
32.5°	695.6	759.0	835.8	910.1	977.2	1019.9	1023.6	994.9	957.3	917.6	873.1
35°	659.7	728.3	811.2	889.8	953.4	980.4	964.4	913.8	869.2	814.9	754.3
37.5°	619.1	694.9	778.0	860.1	917.8	924.9	885.2	831.9	768.9	705.2	633.8
40°	588.8	669.1	754.7	837.5	888.5	881.2	830.5	772.0	697.0	619.1	552.8
42.5°	561.6	641.9	729.1	810.4	851.2	831.1	772.0	700.0	619.5	546.1	485.4
45°	514.5	597.1	686.3	764.9	788.3	752.0	673.7	593.8	514.5	453.3	405.3
47.5°	468.9	550.5	638.8	707.9	716.2	667.4	581.8	499.6	431.5	381.6	347.8
50°	435.2	517.2	604.8	666.4	663.7	604.8	516.8	438.5	381.7	341.3	318.7
52.5°	405.1	482.5	566.7	622.7	608.6	544.3	460.4	390.9	344.1	312.5	292.0
55°	358.3	429.9	509.9	554.8	528.9	457.5	386.6	330.6	296.0	272.4	256.5
57.5°	311.8	379.0	447.4	475.1	446.4	380.6	321.5	280.9	254.9	237.3	226.9
60°	283.0	341.7	402.6	426.6	392.3	333.7	287.0	250.7	229.8	215.4	206.2
62.5°	254.3	306.7	364.3	377.3	345.9	296.4	255.1	224.9	207.7	194.9	186.2
65°	215.2	258.1	301.8	310.4	281.4	243.1	210.4	190.8	175.5	166.2	159.2
67.5°	176.5	210.9	241.8	248.8	223.5	196.9	173.3	156.2	145.8	138.0	132.2
70°	153.6	180.8	206.2	211.8	191.5	167.8	149.9	136.2	126.9	120.2	114.6
72.5°	129.3	152.0	173.1	176.9	160.3	142.2	127.5	116.7	108.5	104.2	98.8
75°	98.9	112.3	128.6	129.6	118.6	107.5	96.2	89.3	84.9	79.6	77.0
77.5°	69.8	80.3	89.6	91.4	84.9	77.4	71.1	65.5	61.9	59.4	57.0
80°	53.3	61.6	65.6	67.9	63.3	58.0	54.3	50.6	48.3	46.6	44.9
82.5°	38.1	43.2	47.0	48.8	46.2	43.1	39.3	37.3	35.5	34.1	33.5
85°	19.4	21.7	24.0	24.6	24.0	22.6	20.7	20.7	19.6	19.4	19.4
87.5°	7.1	8.5	8.7	9.9	9.6	9.8	10.1	10.0	10.0	9.8	9.7
90°	2.1	3.7	5.2	6.7	8.0	9.2	10.3	11.4	12.5	13.2	13.9
92.5°	12.5	12.3	12.2	12.0	12.3	12.8	13.4	13.9	14.4	14.8	15.2
95°	36.0	31.4	26.8	22.3	20.4	21.4	22.4	23.4	24.3	25.1	25.8
97.5°	67.6	54.8	41.8	28.9	23.6	25.9	28.1	30.3	32.5	33.2	33.7
100°	91.5	72.5	53.5	34.5	26.1	28.5	30.9	33.3	35.6	36.6	37.8
102.5°	139.5	135.4	131.3	127.3	115.5	95.8	76.1	56.3	36.6	38.0	39.5
105°	193.9	198.1	202.2	206.4	189.6	151.7	113.8	76.0	38.1	39.6	41.1
107.5°	245.9	249.3	252.6	256.0	235.0	189.6	144.2	98.7	53.3	51.7	50.2
110°	279.5	282.4	285.3	288.2	269.6	229.5	189.4	149.4	109.2	95.4	81.5





TEST NUMBER: P331501-940

CATALOG NUMBER: S122DIW-S485D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	311.1	313.7	316.2	318.8	315.1	305.2	295.3	285.4	275.5	225.0	174.3
115°	361.3	363.6	366.0	368.4	371.3	374.8	378.3	381.7	385.1	320.9	256.7
117.5°	406.6	409.3	411.9	414.6	417.1	419.5	421.9	424.2	426.6	411.1	395.6
120°	439.1	441.1	443.2	445.3	447.5	450.0	452.5	455.0	457.5	459.2	460.9
122.5°	467.2	469.3	471.5	473.7	476.2	478.8	481.6	484.3	487.1	488.0	489.0
125°	509.3	511.1	512.9	514.7	516.9	519.6	522.2	524.9	527.4	528.4	529.4
127.5°	548.0	550.1	552.1	554.1	556.1	558.0	560.0	562.0	563.9	565.3	566.8
130°	572.7	575.0	577.2	579.4	581.3	582.8	584.3	585.9	587.5	589.0	590.5
132.5°	597.4	599.3	601.2	603.1	604.8	606.3	607.8	609.4	610.9	612.2	613.5
135°	630.2	632.4	634.6	636.9	638.6	639.9	641.1	642.4	643.6	645.0	646.4
137.5°	662.4	664.0	665.5	667.0	668.5	669.9	671.4	672.8	674.2	675.6	676.9
140°	683.4	684.5	685.6	686.7	688.0	689.6	691.1	692.6	694.2	695.4	696.7
142.5°	701.2	702.3	703.3	704.3	705.6	707.4	709.2	710.9	712.7	713.8	714.9
145°	728.3	728.3	728.1	727.9	729.1	731.4	733.8	736.1	738.5	739.5	740.4
147.5°	752.6	752.1	751.5	751.0	751.9	754.2	756.5	758.8	761.2	762.0	762.7
150°	768.1	767.1	766.2	765.2	765.8	768.0	770.3	772.5	774.7	775.5	776.3
152.5°	781.5	780.4	779.3	778.2	778.7	780.9	782.9	785.1	787.2	788.0	788.8
155°	800.9	799.7	798.4	797.2	797.4	799.1	800.7	802.4	804.1	804.9	805.7
157.5°	816.5	815.4	814.3	813.3	813.3	814.5	815.6	816.8	818.0	818.9	819.9
160°	825.6	824.8	824.0	823.1	823.1	824.0	824.8	825.6	826.5	827.3	828.1
162.5°	833.7	832.9	832.0	831.2	831.1	831.8	832.6	833.3	834.0	834.9	835.9
165°	844.4	843.6	842.8	841.9	841.7	842.1	842.5	842.9	843.4	844.4	845.3
167.5°	852.4	851.6	850.7	849.9	849.7	850.1	850.4	850.9	851.2	852.2	853.2
170°	856.8	856.0	855.2	854.3	854.1	854.3	854.7	855.0	855.2	856.2	857.2
172.5°	859.9	859.1	858.2	857.4	857.1	857.4	857.6	857.9	858.2	859.2	860.1
175°	863.6	862.6	861.7	860.7	860.3	860.6	860.9	861.2	861.5	862.5	863.4
177.5°	864.4	863.6	862.9	862.1	861.7	861.8	862.0	862.1	862.2	863.0	863.8
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331501-940

CATALOG NUMBER: S122DIW-S485D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	898.8	902.5	902.5	903.0	907.2	906.8	906.5
5°	956.4	962.1	962.8	968.8	972.8	971.4	967.8
7.5°	1010.8	1021.4	1029.4	1033.8	1039.1	1042.3	1040.9
10°	1054.0	1069.3	1078.6	1084.9	1092.6	1098.3	1096.3
12.5°	1093.1	1111.4	1124.2	1135.1	1136.0	1143.4	1138.4
15°	1154.2	1173.6	1175.5	1183.6	1189.9	1189.2	1189.5
17.5°	1174.4	1180.6	1181.9	1182.1	1182.1	1179.8	1174.7
20°	1167.2	1164.9	1159.2	1154.9	1147.3	1146.2	1139.6
22.5°	1133.1	1125.7	1111.5	1102.2	1090.2	1087.1	1085.2
25°	1066.0	1049.6	1027.0	1005.4	999.3	987.7	991.0
27.5°	973.8	948.4	923.9	906.3	890.5	873.0	878.0
30°	909.1	880.5	845.9	819.2	802.3	785.6	782.6
32.5°	831.9	789.9	751.3	727.8	701.8	691.3	679.8
35°	698.7	657.7	619.4	586.5	567.5	552.8	539.5
37.5°	578.8	531.7	500.8	474.1	460.4	452.0	454.1
40°	504.5	463.2	440.6	420.3	407.6	401.6	403.0
42.5°	444.3	413.4	394.8	380.8	371.9	368.5	367.7
45°	375.9	358.6	343.3	335.4	331.0	327.3	325.0
47.5°	329.4	315.2	306.6	301.8	298.0	294.4	294.3
50°	301.4	292.0	286.1	281.1	278.0	275.4	277.8
52.5°	280.1	271.5	265.6	261.1	259.9	257.5	257.5
55°	248.4	241.7	237.5	233.4	231.5	230.2	228.5
57.5°	219.6	213.3	209.4	206.8	203.0	201.7	201.2
60°	199.1	194.1	190.1	186.8	185.1	182.5	182.5
62.5°	180.2	175.2	171.5	169.0	166.2	165.1	165.4
65°	152.8	148.8	145.2	142.5	141.9	139.9	140.5
67.5°	127.7	125.0	121.2	119.7	118.4	117.3	116.5
70°	110.9	108.3	106.2	104.2	103.3	103.3	103.3
72.5°	96.8	93.5	92.4	89.9	90.4	89.3	88.3
75°	74.9	72.9	72.0	70.9	69.3	69.3	69.3
77.5°	55.1	54.6	53.3	52.3	51.9	51.5	51.7
80°	42.6	42.3	41.6	41.6	40.9	40.7	39.9
82.5°	32.7	31.9	31.5	31.2	31.1	31.0	30.9
85°	18.6	18.0	18.0	18.3	17.7	17.7	18.0
87.5°	10.1	10.3	10.1	10.2	10.4	10.3	10.3
90°	14.5	15.2	15.8	16.1	16.3	16.6	16.9
92.5°	15.6	16.0	16.2	16.3	16.5	16.7	16.9
95°	26.4	27.1	27.4	27.3	27.1	27.0	26.8
97.5°	34.2	34.8	35.1	35.3	35.5	35.7	35.8
100°	38.9	40.0	40.8	41.0	41.3	41.6	41.8
102.5°	40.9	42.4	43.2	43.7	44.1	44.4	44.9
105°	42.6	44.1	45.2	45.7	46.4	46.9	47.4
107.5°	48.7	47.1	46.6	47.2	47.7	48.2	48.8
110°	67.6	53.8	47.1	47.6	48.2	48.8	49.3



TEST NUMBER: P331501-940

CATALOG NUMBER: S122DIW-S485D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	123.8	73.1	48.1	48.5	49.0	49.4	49.8
115°	192.4	128.2	91.1	81.1	71.2	61.2	51.2
117.5°	380.0	364.4	340.3	307.5	274.6	241.8	209.0
120°	462.5	464.2	455.7	436.9	418.2	399.5	380.8
122.5°	490.0	491.1	489.7	486.1	482.4	478.8	475.2
125°	530.4	531.4	532.1	532.4	532.9	533.3	533.7
127.5°	568.2	569.6	570.3	570.4	570.5	570.6	570.7
130°	592.0	593.5	594.2	594.1	594.0	593.8	593.7
132.5°	614.8	616.1	616.7	616.5	616.4	616.3	616.2
135°	647.7	649.2	649.7	649.4	649.2	648.9	648.6
137.5°	678.2	679.7	680.1	679.6	679.1	678.7	678.1
140°	697.9	699.2	699.5	698.7	698.0	697.3	696.7
142.5°	716.0	717.2	717.4	716.8	716.0	715.3	714.6
145°	741.4	742.3	742.5	741.8	741.1	740.4	739.8
147.5°	763.4	764.1	764.2	763.6	763.0	762.4	761.8
150°	777.2	778.0	778.1	777.4	776.7	776.0	775.3
152.5°	789.7	790.5	790.5	789.5	788.6	787.7	786.8
155°	806.6	807.4	807.2	806.1	805.0	803.9	802.8
157.5°	820.8	821.8	821.7	820.6	819.6	818.5	817.3
160°	829.0	829.8	829.7	828.8	827.8	826.9	825.9
162.5°	836.8	837.8	837.7	836.4	835.3	834.0	832.9
165°	846.2	847.2	847.2	846.2	845.3	844.4	843.4
167.5°	854.2	855.1	855.0	853.7	852.5	851.2	850.0
170°	858.1	859.1	859.0	857.7	856.5	855.2	854.0
172.5°	861.1	862.1	861.9	860.7	859.4	858.2	856.9
175°	864.3	865.3	865.1	863.7	862.4	860.9	859.6
177.5°	864.5	865.3	865.2	864.2	863.2	862.2	861.2
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7

(END OF REPORT)