

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331614-935

Luminaire Tested: **S122DIW-S1005D1440U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331614-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D1440U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7798.4 lumens
Efficiency: N/A
Efficacy: 94.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331614-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331614-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	32
3	80	71	64	58	73	65	59	54	54	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	28	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22157	22157	22157
5°	22242	21921	22049
10°	22109	21697	21807
15°	21835	21417	21396
20°	21448	20993	20972
25°	21063	20475	20475
30°	20566	19999	19827
35°	20103	19429	19141
40°	19524	18858	18493
45°	18952	18287	17838
50°	18329	17698	17071
55°	17681	17011	16380
60°	16956	16191	15594
65°	16180	15373	14670
70°	15196	14389	13704
75°	13830	13250	12926
80°	12273	11901	11288
85°	10022	9541	8540



TEST NUMBER: P331614-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.0	1.7
10°-20°	363.1	4.7
20°-30°	533.7	6.8
30°-40°	619.9	7.9
40°-50°	619.3	7.9
50°-60°	540.0	6.9
60°-70°	399.3	5.1
70°-80°	226.2	2.9
80°-90°	67.0	0.9
90°-100°	97.5	1.2
100°-110°	302.7	3.9
110°-120°	517.4	6.6
120°-130°	680.4	8.7
130°-140°	763.7	9.8
140°-150°	748.8	9.6
150°-160°	628.1	8.1
160°-170°	416.6	5.3
170°-180°	145.6	1.9
0°-30°	1025.8	13.2
0°-40°	1645.7	21.1
0°-60°	2805.0	36.0
0°-90°	3497.4	44.8
90°-120°	917.6	11.8
90°-150°	3110.6	39.9
90°-180°	4301.0	55.2
0°-180°	7798.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1372	1366	1352	1362	1360	130
15°	1306	1298	1281	1286	1280	368
25°	1182	1171	1149	1152	1149	544
35°	1020	1006	986	978	971	637
45°	830	820	801	787	781	640
55°	628	620	604	589	582	561
65°	424	415	402	391	384	419
75°	222	219	212	205	207	237
85°	54	53	52	48	46	62
90°	1	18	46	43	44	6
95°	68	80	83	83	80	77
105°	279	283	286	288	288	295
115°	519	526	524	523	519	513
125°	755	766	763	759	758	675
135°	977	991	994	993	989	755
145°	1186	1195	1203	1204	1199	741
155°	1356	1360	1364	1370	1367	624
165°	1476	1475	1474	1483	1477	416
175°	1536	1532	1529	1537	1530	146
180°	1538	1538	1538	1538	1538	



TEST NUMBER: P331614-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3
2.5°	1378.6	1377.4	1376.3	1375.1	1373.9	1372.1	1369.5	1366.9	1364.3	1361.8	1364.1
5°	1372.3	1371.1	1369.9	1368.7	1367.6	1365.4	1362.2	1358.9	1355.7	1352.5	1354.9
7.5°	1360.1	1358.3	1356.5	1354.7	1352.9	1350.3	1347.0	1343.8	1340.5	1337.2	1339.5
10°	1348.5	1346.5	1344.5	1342.4	1340.3	1337.6	1334.0	1330.5	1327.0	1323.4	1325.9
12.5°	1332.7	1330.8	1329.0	1327.2	1325.4	1322.8	1319.2	1315.7	1312.3	1308.7	1310.4
15°	1306.3	1304.6	1302.8	1301.1	1299.2	1296.5	1292.7	1288.8	1285.0	1281.3	1282.5
17.5°	1272.6	1270.7	1269.0	1267.2	1265.5	1262.7	1258.8	1254.9	1251.0	1247.2	1248.5
20°	1248.3	1246.5	1244.7	1242.9	1241.2	1238.3	1234.2	1230.1	1226.0	1221.8	1222.7
22.5°	1224.0	1221.5	1219.1	1216.6	1214.1	1211.0	1207.1	1203.2	1199.4	1195.5	1195.7
25°	1182.3	1179.9	1177.6	1175.3	1172.9	1169.2	1164.2	1159.3	1154.3	1149.3	1149.9
27.5°	1134.8	1132.6	1130.6	1128.4	1126.4	1123.3	1119.4	1115.4	1111.6	1107.6	1106.7
30°	1103.1	1100.8	1098.4	1096.1	1093.7	1090.4	1086.0	1081.6	1077.2	1072.7	1071.9
32.5°	1069.4	1067.5	1065.6	1063.7	1061.8	1058.6	1054.0	1049.3	1044.7	1040.0	1038.5
35°	1019.9	1017.0	1014.1	1011.2	1008.2	1004.4	999.7	995.1	990.4	985.7	984.0
37.5°	964.3	961.7	959.2	956.6	954.0	950.4	945.6	941.0	936.3	931.6	929.4
40°	926.3	923.9	921.6	919.3	916.9	913.4	908.7	904.0	899.3	894.7	892.0
42.5°	889.3	887.0	884.7	882.4	879.9	876.4	871.8	867.0	862.4	857.6	854.8
45°	830.0	827.9	825.9	823.8	821.7	818.6	814.2	809.8	805.4	800.9	797.7
47.5°	770.9	769.0	767.0	765.1	763.1	759.8	755.3	750.7	746.1	741.6	738.1
50°	729.7	728.2	726.8	725.3	723.8	721.0	717.0	712.8	708.7	704.6	700.5
52.5°	689.6	687.7	685.7	683.8	681.8	678.9	675.0	671.1	667.4	663.5	660.0
55°	628.1	626.3	624.6	622.8	621.0	618.4	614.9	611.4	607.9	604.3	600.8
57.5°	566.4	564.9	563.5	562.1	560.7	558.1	554.2	550.4	546.5	542.6	539.2
60°	525.1	524.0	522.8	521.7	520.5	517.8	513.8	509.6	505.5	501.4	498.2
62.5°	485.1	483.2	481.3	479.4	477.5	475.0	471.8	468.7	465.5	462.4	459.3
65°	423.5	421.8	420.1	418.3	416.6	414.1	411.2	408.3	405.4	402.4	399.8
67.5°	361.0	359.6	358.2	356.8	355.4	353.4	350.7	348.1	345.4	342.9	340.8
70°	321.9	320.8	319.6	318.5	317.3	315.4	312.7	310.0	307.5	304.8	302.7
72.5°	281.8	280.7	279.5	278.4	277.2	275.7	274.1	272.3	270.6	268.9	266.8
75°	221.7	221.1	220.5	219.9	219.3	218.3	216.8	215.3	213.9	212.4	210.7
77.5°	167.8	166.9	165.8	164.9	163.8	163.1	162.5	161.9	161.3	160.7	159.8
80°	132.0	131.6	131.4	131.0	130.8	130.4	129.8	129.2	128.5	128.0	127.1
82.5°	98.2	98.2	98.1	98.0	97.9	97.7	97.4	97.0	96.7	96.3	95.2
85°	54.1	53.8	53.6	53.2	53.0	52.6	52.3	52.0	51.7	51.5	50.5
87.5°	19.3	19.5	19.7	19.9	20.1	20.7	21.4	22.3	23.1	23.8	23.1
90°	1.3	4.7	8.2	11.7	15.2	20.1	26.4	32.7	39.1	45.5	44.9
92.5°	23.1	25.7	28.2	30.7	33.2	35.3	36.8	38.3	39.8	41.2	41.4
95°	67.5	70.3	73.3	76.1	79.0	80.8	81.4	81.9	82.5	83.1	83.1
97.5°	123.3	125.9	128.4	131.0	133.5	135.3	136.4	137.5	138.5	139.7	139.7
100°	164.9	167.1	169.4	171.8	174.1	175.6	176.5	177.4	178.2	179.1	179.1
102.5°	208.4	210.3	212.2	214.0	215.9	217.3	218.4	219.5	220.6	221.7	222.0
105°	279.1	279.9	280.8	281.6	282.5	283.3	283.9	284.4	285.0	285.6	286.1
107.5°	350.2	351.5	352.8	354.0	355.2	355.9	355.9	355.9	355.9	355.9	356.1
110°	395.9	397.6	399.3	401.1	402.8	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P331614-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	445.7	447.5	449.2	450.9	452.6	453.4	453.1	453.0	452.7	452.5	451.8
115°	519.2	520.9	522.6	524.4	526.2	526.7	526.2	525.6	525.0	524.4	524.1
117.5°	592.5	594.7	597.0	599.3	601.7	602.0	600.4	598.7	597.1	595.6	594.9
120°	641.2	643.5	645.8	648.2	650.5	650.5	648.2	645.8	643.5	641.2	641.2
122.5°	685.9	688.6	691.4	694.1	697.0	697.5	695.9	694.3	692.7	691.0	690.3
125°	755.4	758.0	760.6	763.2	765.9	766.7	765.9	765.0	764.1	763.2	762.3
127.5°	823.2	826.5	829.7	833.1	836.4	837.5	836.5	835.4	834.4	833.4	832.2
130°	865.7	869.5	873.3	877.0	880.8	882.4	881.8	881.2	880.6	880.0	879.5
132.5°	913.5	916.6	919.6	922.7	925.7	927.4	927.5	927.6	927.7	927.8	926.5
135°	977.4	980.6	983.8	986.9	990.1	992.0	992.6	993.2	993.7	994.3	994.0
137.5°	1044.7	1047.2	1049.8	1052.4	1055.0	1056.7	1057.5	1058.2	1058.9	1059.7	1059.5
140°	1085.1	1087.7	1090.4	1093.0	1095.5	1097.5	1099.0	1100.4	1101.9	1103.3	1103.3
142.5°	1126.7	1129.3	1131.9	1134.5	1137.0	1138.8	1139.8	1140.8	1141.8	1142.8	1143.0
145°	1186.4	1188.4	1190.4	1192.4	1194.5	1196.4	1198.1	1199.8	1201.5	1203.2	1203.5
147.5°	1239.6	1242.0	1244.4	1246.9	1249.3	1251.1	1252.2	1253.4	1254.6	1255.7	1256.4
150°	1275.9	1277.6	1279.4	1281.2	1282.9	1284.3	1285.5	1286.6	1287.8	1288.9	1289.8
152.5°	1308.1	1309.8	1311.6	1313.3	1315.1	1316.6	1318.0	1319.4	1320.8	1322.2	1323.3
155°	1356.4	1357.3	1358.1	1359.0	1359.9	1360.7	1361.6	1362.4	1363.3	1364.2	1365.6
157.5°	1397.7	1398.3	1398.9	1399.5	1400.0	1400.6	1401.1	1401.6	1402.1	1402.7	1404.5
160°	1422.6	1423.2	1423.7	1424.4	1425.0	1425.4	1425.6	1425.9	1426.2	1426.5	1428.2
162.5°	1445.4	1445.6	1445.7	1445.8	1446.0	1446.1	1446.4	1446.7	1447.0	1447.3	1449.2
165°	1475.8	1475.6	1475.2	1475.0	1474.7	1474.5	1474.5	1474.5	1474.5	1474.5	1476.5
167.5°	1501.2	1500.4	1499.5	1498.7	1497.8	1497.4	1497.3	1497.3	1497.2	1497.1	1499.2
170°	1514.8	1513.9	1513.0	1512.2	1511.3	1510.7	1510.5	1510.2	1509.8	1509.6	1511.6
172.5°	1524.1	1523.3	1522.4	1521.6	1520.7	1520.1	1519.8	1519.5	1519.2	1518.9	1521.0
175°	1535.5	1534.6	1533.8	1532.9	1532.1	1531.4	1530.8	1530.2	1529.7	1529.0	1531.1
177.5°	1540.2	1539.6	1538.9	1538.2	1537.5	1536.9	1536.4	1535.9	1535.5	1535.0	1536.4
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331614-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3
2.5°	1366.4	1368.7	1371.1	1372.1	1371.6	1371.1	1370.6	1370.2
5°	1357.2	1359.5	1361.8	1362.8	1362.2	1361.6	1361.0	1360.4
7.5°	1341.9	1344.2	1346.6	1347.5	1346.8	1346.2	1345.5	1344.9
10°	1328.2	1330.5	1332.8	1333.6	1332.7	1331.8	1330.9	1330.1
12.5°	1312.0	1313.6	1315.3	1315.8	1315.1	1314.5	1313.8	1313.2
15°	1283.6	1284.8	1285.9	1285.8	1284.4	1282.9	1281.4	1280.0
17.5°	1249.9	1251.3	1252.6	1252.6	1251.1	1249.7	1248.4	1246.9
20°	1223.7	1224.5	1225.4	1225.2	1224.1	1222.9	1221.8	1220.6
22.5°	1195.8	1196.0	1196.2	1195.9	1195.2	1194.6	1193.8	1193.1
25°	1150.5	1151.1	1151.7	1151.7	1151.1	1150.5	1149.9	1149.3
27.5°	1105.9	1104.9	1104.1	1102.9	1101.6	1100.1	1098.7	1097.3
30°	1071.0	1070.1	1069.3	1068.2	1067.0	1065.8	1064.7	1063.5
32.5°	1036.9	1035.3	1033.7	1032.3	1031.1	1030.0	1028.8	1027.6
35°	982.1	980.4	978.6	977.1	975.6	974.1	972.6	971.1
37.5°	927.2	925.1	922.9	921.1	919.7	918.3	916.9	915.5
40°	889.3	886.7	884.1	882.2	881.0	879.9	878.7	877.4
42.5°	852.0	849.0	846.2	844.0	842.3	840.7	839.0	837.3
45°	794.5	791.3	788.1	785.8	784.6	783.5	782.3	781.2
47.5°	734.8	731.3	728.0	725.4	723.7	722.0	720.3	718.6
50°	696.4	692.3	688.2	685.4	684.0	682.5	681.1	679.6
52.5°	656.7	653.2	649.9	647.2	645.2	643.3	641.4	639.5
55°	597.3	593.7	590.3	587.8	586.3	584.9	583.4	581.9
57.5°	535.6	532.2	528.7	526.4	525.4	524.3	523.1	522.0
60°	495.0	491.7	488.5	486.5	485.6	484.7	483.8	482.9
62.5°	456.4	453.4	450.4	448.3	447.2	446.1	445.0	443.8
65°	397.2	394.5	391.9	389.9	388.4	386.9	385.5	384.0
67.5°	338.7	336.7	334.6	332.9	331.8	330.6	329.5	328.3
70°	300.7	298.7	296.6	295.0	293.8	292.7	291.4	290.3
72.5°	264.8	262.8	260.7	259.2	258.3	257.4	256.4	255.5
75°	209.0	207.2	205.4	204.8	205.4	206.0	206.6	207.2
77.5°	158.9	158.1	157.2	156.4	155.5	154.7	153.9	153.1
80°	126.2	125.4	124.5	123.7	123.1	122.6	122.0	121.4
82.5°	94.1	93.0	91.9	91.3	91.1	91.0	90.9	90.7
85°	49.7	48.8	48.0	47.4	47.1	46.8	46.5	46.1
87.5°	22.2	21.4	20.6	20.1	19.9	19.7	19.5	19.4
90°	44.3	43.7	43.1	43.0	43.3	43.6	43.8	44.2
92.5°	41.5	41.6	41.8	41.8	41.8	41.9	42.0	42.0
95°	83.1	83.1	83.1	82.7	82.2	81.6	81.0	80.5
97.5°	139.7	139.7	139.7	139.7	139.6	139.5	139.5	139.4
100°	179.1	179.1	179.1	179.0	178.7	178.4	178.1	177.8
102.5°	222.1	222.4	222.7	222.6	222.3	222.1	221.7	221.4
105°	286.7	287.3	287.8	288.2	288.2	288.2	288.2	288.2
107.5°	356.4	356.6	356.8	356.3	355.0	353.6	352.3	350.9
110°	403.7	403.7	403.7	403.2	402.3	401.5	400.6	399.8



TEST NUMBER: P331614-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	451.1	450.4	449.7	449.0	448.4	447.8	447.1	446.5
115°	523.8	523.5	523.2	522.6	521.8	520.9	520.0	519.2
117.5°	594.2	593.5	592.8	591.9	591.1	590.2	589.4	588.5
120°	641.2	641.2	641.2	640.8	639.9	639.0	638.2	637.3
122.5°	689.7	689.0	688.3	687.6	687.0	686.4	685.7	685.1
125°	761.5	760.6	759.7	759.2	758.9	758.6	758.4	758.0
127.5°	831.2	830.2	829.1	828.2	827.2	826.3	825.4	824.5
130°	878.9	878.3	877.7	876.8	875.7	874.6	873.4	872.3
132.5°	925.3	924.0	922.7	921.6	920.8	919.8	918.9	917.9
135°	993.7	993.4	993.2	992.6	991.7	990.8	990.0	989.1
137.5°	1059.2	1059.0	1058.8	1058.1	1057.0	1055.8	1054.6	1053.4
140°	1103.3	1103.3	1103.3	1102.8	1101.6	1100.4	1099.2	1098.1
142.5°	1143.2	1143.5	1143.7	1143.2	1142.1	1140.9	1139.8	1138.6
145°	1203.9	1204.1	1204.4	1203.9	1202.8	1201.7	1200.5	1199.4
147.5°	1257.0	1257.6	1258.3	1258.0	1256.9	1255.8	1254.7	1253.6
150°	1290.6	1291.5	1292.4	1292.4	1291.5	1290.6	1289.8	1288.9
152.5°	1324.3	1325.4	1326.5	1326.5	1325.4	1324.3	1323.3	1322.2
155°	1367.1	1368.6	1369.9	1370.3	1369.4	1368.6	1367.7	1366.8
157.5°	1406.5	1408.5	1410.5	1410.7	1409.4	1408.0	1406.6	1405.2
160°	1429.9	1431.7	1433.4	1433.7	1432.5	1431.4	1430.3	1429.1
162.5°	1451.2	1453.2	1455.1	1455.4	1454.1	1452.7	1451.3	1449.8
165°	1478.6	1480.6	1482.6	1482.9	1481.4	1480.1	1478.6	1477.1
167.5°	1501.2	1503.2	1505.2	1505.5	1504.0	1502.4	1501.0	1499.4
170°	1513.6	1515.6	1517.7	1517.8	1516.0	1514.3	1512.6	1510.9
172.5°	1522.9	1525.0	1527.0	1527.2	1525.4	1523.7	1522.0	1520.3
175°	1533.1	1535.1	1537.1	1537.3	1535.5	1533.8	1532.1	1530.3
177.5°	1537.8	1539.2	1540.6	1540.6	1539.2	1537.8	1536.4	1535.0
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2

(END OF REPORT)