

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331589-935

Luminaire Tested: **S122DIW-S1005D435U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331589-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D435U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4983.0 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331589-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331589-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	75	75	75	70
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	64	63	59
2	93	85	79	74	88	81	75	71	73	68	64	65	62	59	58	55	53	49
3	85	75	68	62	80	71	65	59	64	59	54	58	53	50	51	48	45	42
4	78	67	58	52	73	63	56	50	57	51	46	51	47	43	46	42	39	36
5	72	60	51	45	67	57	49	43	51	45	40	46	41	37	42	37	34	31
6	66	54	45	39	62	51	43	38	46	40	35	42	37	33	38	33	30	27
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27	24
8	57	44	36	31	54	42	35	30	38	32	28	35	30	26	32	27	24	22
9	53	40	33	27	50	39	32	27	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22157	22157	22157
5°	22242	21921	22049
10°	22109	21697	21807
15°	21835	21417	21396
20°	21448	20993	20972
25°	21063	20475	20475
30°	20566	19999	19827
35°	20103	19429	19141
40°	19524	18858	18493
45°	18952	18287	17838
50°	18329	17698	17071
55°	17681	17011	16380
60°	16956	16191	15594
65°	16180	15373	14670
70°	15196	14389	13704
75°	13830	13250	12926
80°	12273	11901	11288
85°	10022	9541	8540



TEST NUMBER: P331589-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.0	2.6
10°-20°	363.1	7.3
20°-30°	533.7	10.7
30°-40°	619.9	12.4
40°-50°	619.3	12.4
50°-60°	540.0	10.8
60°-70°	399.3	8.0
70°-80°	226.2	4.5
80°-90°	62.1	1.2
90°-100°	17.0	0.3
100°-110°	62.2	1.2
110°-120°	166.3	3.3
120°-130°	274.5	5.5
130°-140°	291.9	5.9
140°-150°	271.3	5.4
150°-160°	218.2	4.4
160°-170°	140.6	2.8
170°-180°	48.4	1.0
0°-30°	1025.8	20.6
0°-40°	1645.7	33.0
0°-60°	2805.0	56.3
0°-90°	3492.6	70.1
90°-120°	245.5	4.9
90°-150°	1083.3	21.7
90°-180°	1490.0	29.9
0°-180°	4983.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1372	1366	1352	1362	1360	130
15°	1306	1298	1281	1286	1280	368
25°	1182	1171	1149	1152	1149	544
35°	1020	1006	986	978	971	637
45°	830	820	801	787	781	640
55°	628	620	604	589	582	561
65°	424	415	402	391	384	419
75°	222	219	212	205	207	237
85°	54	53	52	48	46	62
90°	0	4	7	9	10	4
95°	24	13	14	16	16	29
105°	112	117	22	26	28	120
115°	212	218	227	65	30	208
125°	299	304	311	313	315	267
135°	370	376	379	383	382	286
145°	430	429	435	438	436	269
155°	473	470	474	476	473	218
165°	498	496	497	500	497	141
175°	510	507	508	510	507	48
180°	509	509	509	509	509	



TEST NUMBER: P331589-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3
2.5°	1378.6	1377.4	1376.3	1375.1	1373.9	1372.1	1369.5	1366.9	1364.3	1361.8	1364.1
5°	1372.3	1371.1	1369.9	1368.7	1367.6	1365.4	1362.2	1358.9	1355.7	1352.5	1354.9
7.5°	1360.1	1358.3	1356.5	1354.7	1352.9	1350.3	1347.0	1343.8	1340.5	1337.2	1339.5
10°	1348.5	1346.5	1344.5	1342.4	1340.3	1337.6	1334.0	1330.5	1327.0	1323.4	1325.9
12.5°	1332.7	1330.8	1329.0	1327.2	1325.4	1322.8	1319.2	1315.7	1312.3	1308.7	1310.4
15°	1306.3	1304.6	1302.8	1301.1	1299.2	1296.5	1292.7	1288.8	1285.0	1281.3	1282.5
17.5°	1272.6	1270.7	1269.0	1267.2	1265.5	1262.7	1258.8	1254.9	1251.0	1247.2	1248.5
20°	1248.3	1246.5	1244.7	1242.9	1241.2	1238.3	1234.2	1230.1	1226.0	1221.8	1222.7
22.5°	1224.0	1221.5	1219.1	1216.6	1214.1	1211.0	1207.1	1203.2	1199.4	1195.5	1195.7
25°	1182.3	1179.9	1177.6	1175.3	1172.9	1169.2	1164.2	1159.3	1154.3	1149.3	1149.9
27.5°	1134.8	1132.6	1130.6	1128.4	1126.4	1123.3	1119.4	1115.4	1111.6	1107.6	1106.7
30°	1103.1	1100.8	1098.4	1096.1	1093.7	1090.4	1086.0	1081.6	1077.2	1072.7	1071.9
32.5°	1069.4	1067.5	1065.6	1063.7	1061.8	1058.6	1054.0	1049.3	1044.7	1040.0	1038.5
35°	1019.9	1017.0	1014.1	1011.2	1008.2	1004.4	999.7	995.1	990.4	985.7	984.0
37.5°	964.3	961.7	959.2	956.6	954.0	950.4	945.6	941.0	936.3	931.6	929.4
40°	926.3	923.9	921.6	919.3	916.9	913.4	908.7	904.0	899.3	894.7	892.0
42.5°	889.3	887.0	884.7	882.4	879.9	876.4	871.8	867.0	862.4	857.6	854.8
45°	830.0	827.9	825.9	823.8	821.7	818.6	814.2	809.8	805.4	800.9	797.7
47.5°	770.9	769.0	767.0	765.1	763.1	759.8	755.3	750.7	746.1	741.6	738.1
50°	729.7	728.2	726.8	725.3	723.8	721.0	717.0	712.8	708.7	704.6	700.5
52.5°	689.6	687.7	685.7	683.8	681.8	678.9	675.0	671.1	667.4	663.5	660.0
55°	628.1	626.3	624.6	622.8	621.0	618.4	614.9	611.4	607.9	604.3	600.8
57.5°	566.4	564.9	563.5	562.1	560.7	558.1	554.2	550.4	546.5	542.6	539.2
60°	525.1	524.0	522.8	521.7	520.5	517.8	513.8	509.6	505.5	501.4	498.2
62.5°	485.1	483.2	481.3	479.4	477.5	475.0	471.8	468.7	465.5	462.4	459.3
65°	423.5	421.8	420.1	418.3	416.6	414.1	411.2	408.3	405.4	402.4	399.8
67.5°	361.0	359.6	358.2	356.8	355.4	353.4	350.7	348.1	345.4	342.9	340.8
70°	321.9	320.8	319.6	318.5	317.3	315.4	312.7	310.0	307.5	304.8	302.7
72.5°	281.8	280.7	279.5	278.4	277.2	275.7	274.1	272.3	270.6	268.9	266.8
75°	221.7	221.1	220.5	219.9	219.3	218.3	216.8	215.3	213.9	212.4	210.7
77.5°	167.8	166.9	165.8	164.9	163.8	163.1	162.5	161.9	161.3	160.7	159.8
80°	132.0	131.6	131.4	131.0	130.8	130.4	129.8	129.2	128.5	128.0	127.1
82.5°	98.2	98.2	98.1	98.0	97.9	97.7	97.4	97.0	96.7	96.3	95.2
85°	54.1	53.8	53.6	53.2	53.0	52.6	52.3	52.0	51.7	51.5	50.5
87.5°	19.1	18.8	18.5	18.2	17.9	17.6	17.3	17.0	16.6	16.3	15.7
90°	0.3	1.3	2.2	3.1	4.0	4.7	5.4	6.0	6.7	7.3	7.7
92.5°	7.4	7.3	7.2	7.1	7.1	7.2	7.6	7.9	8.2	8.5	8.8
95°	23.9	21.2	18.5	15.8	13.1	12.1	12.7	13.2	13.8	14.4	14.7
97.5°	47.4	39.9	32.3	24.6	17.0	13.9	15.2	16.5	17.9	19.2	19.5
100°	65.2	53.9	42.7	31.5	20.3	15.4	16.8	18.2	19.5	21.0	21.6
102.5°	84.6	82.2	79.8	77.5	75.1	68.1	56.5	44.9	33.2	21.5	22.4
105°	111.8	114.3	116.8	119.2	121.7	111.8	89.5	67.1	44.8	22.5	23.3
107.5°	143.0	145.0	147.0	149.0	150.9	138.5	111.8	85.0	58.2	31.4	30.5
110°	163.0	164.7	166.4	168.2	169.9	158.9	135.3	111.7	88.0	64.4	56.2



TEST NUMBER: P331589-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	181.8	183.4	184.9	186.4	188.0	185.8	179.9	174.1	168.2	162.5	132.6
115°	211.6	213.0	214.4	215.8	217.1	218.9	220.9	223.0	225.0	227.0	189.2
117.5°	238.2	239.7	241.3	242.8	244.4	245.9	247.3	248.7	250.1	251.5	242.4
120°	257.6	258.8	260.0	261.3	262.5	263.9	265.4	266.8	268.3	269.8	270.7
122.5°	274.1	275.3	276.6	277.9	279.2	280.7	282.3	283.9	285.5	287.1	287.7
125°	299.2	300.2	301.4	302.4	303.4	304.7	306.3	307.9	309.4	311.0	311.5
127.5°	321.9	323.1	324.3	325.5	326.7	327.8	329.0	330.1	331.3	332.4	333.3
130°	336.4	337.7	339.0	340.3	341.6	342.7	343.6	344.5	345.4	346.3	347.2
132.5°	351.1	352.1	353.3	354.4	355.5	356.5	357.4	358.3	359.2	360.2	360.9
135°	370.2	371.5	372.8	374.1	375.5	376.4	377.2	378.0	378.7	379.4	380.2
137.5°	389.6	390.5	391.4	392.4	393.2	394.1	394.9	395.8	396.6	397.4	398.2
140°	402.3	402.9	403.6	404.2	404.8	405.6	406.6	407.4	408.3	409.2	409.9
142.5°	412.8	413.5	414.0	414.6	415.2	416.0	417.0	418.0	419.0	420.1	420.8
145°	429.5	429.4	429.3	429.2	429.1	429.8	431.2	432.6	433.9	435.3	435.9
147.5°	443.9	443.7	443.3	443.1	442.7	443.2	444.6	446.0	447.4	448.8	449.2
150°	453.4	452.8	452.2	451.7	451.1	451.4	452.8	454.1	455.4	456.7	457.2
152.5°	461.3	460.7	460.0	459.4	458.7	459.1	460.3	461.6	462.8	464.1	464.5
155°	472.9	472.2	471.4	470.7	469.9	470.1	471.1	472.0	473.0	474.0	474.5
157.5°	481.9	481.3	480.7	480.1	479.5	479.5	480.2	480.9	481.6	482.2	482.8
160°	487.2	486.7	486.3	485.8	485.3	485.3	485.8	486.3	486.7	487.2	487.8
162.5°	492.0	491.5	490.9	490.5	490.0	490.0	490.3	490.8	491.2	491.6	492.2
165°	498.3	497.8	497.3	496.8	496.3	496.2	496.5	496.7	497.0	497.1	497.7
167.5°	503.0	502.5	502.0	501.5	501.0	500.9	501.1	501.4	501.6	501.8	502.4
170°	505.7	505.1	504.6	504.2	503.7	503.5	503.7	503.9	504.0	504.2	504.7
172.5°	507.4	507.0	506.4	505.9	505.4	505.3	505.4	505.6	505.8	505.9	506.5
175°	509.7	509.1	508.5	508.0	507.4	507.2	507.4	507.6	507.6	507.8	508.4
177.5°	510.1	509.6	509.1	508.7	508.2	508.0	508.1	508.2	508.2	508.2	508.8
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331589-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3
2.5°	1366.4	1368.7	1371.1	1372.1	1371.6	1371.1	1370.6	1370.2
5°	1357.2	1359.5	1361.8	1362.8	1362.2	1361.6	1361.0	1360.4
7.5°	1341.9	1344.2	1346.6	1347.5	1346.8	1346.2	1345.5	1344.9
10°	1328.2	1330.5	1332.8	1333.6	1332.7	1331.8	1330.9	1330.1
12.5°	1312.0	1313.6	1315.3	1315.8	1315.1	1314.5	1313.8	1313.2
15°	1283.6	1284.8	1285.9	1285.8	1284.4	1282.9	1281.4	1280.0
17.5°	1249.9	1251.3	1252.6	1252.6	1251.1	1249.7	1248.4	1246.9
20°	1223.7	1224.5	1225.4	1225.2	1224.1	1222.9	1221.8	1220.6
22.5°	1195.8	1196.0	1196.2	1195.9	1195.2	1194.6	1193.8	1193.1
25°	1150.5	1151.1	1151.7	1151.7	1151.1	1150.5	1149.9	1149.3
27.5°	1105.9	1104.9	1104.1	1102.9	1101.6	1100.1	1098.7	1097.3
30°	1071.0	1070.1	1069.3	1068.2	1067.0	1065.8	1064.7	1063.5
32.5°	1036.9	1035.3	1033.7	1032.3	1031.1	1030.0	1028.8	1027.6
35°	982.1	980.4	978.6	977.1	975.6	974.1	972.6	971.1
37.5°	927.2	925.1	922.9	921.1	919.7	918.3	916.9	915.5
40°	889.3	886.7	884.1	882.2	881.0	879.9	878.7	877.4
42.5°	852.0	849.0	846.2	844.0	842.3	840.7	839.0	837.3
45°	794.5	791.3	788.1	785.8	784.6	783.5	782.3	781.2
47.5°	734.8	731.3	728.0	725.4	723.7	722.0	720.3	718.6
50°	696.4	692.3	688.2	685.4	684.0	682.5	681.1	679.6
52.5°	656.7	653.2	649.9	647.2	645.2	643.3	641.4	639.5
55°	597.3	593.7	590.3	587.8	586.3	584.9	583.4	581.9
57.5°	535.6	532.2	528.7	526.4	525.4	524.3	523.1	522.0
60°	495.0	491.7	488.5	486.5	485.6	484.7	483.8	482.9
62.5°	456.4	453.4	450.4	448.3	447.2	446.1	445.0	443.8
65°	397.2	394.5	391.9	389.9	388.4	386.9	385.5	384.0
67.5°	338.7	336.7	334.6	332.9	331.8	330.6	329.5	328.3
70°	300.7	298.7	296.6	295.0	293.8	292.7	291.4	290.3
72.5°	264.8	262.8	260.7	259.2	258.3	257.4	256.4	255.5
75°	209.0	207.2	205.4	204.8	205.4	206.0	206.6	207.2
77.5°	158.9	158.1	157.2	156.4	155.5	154.7	153.9	153.1
80°	126.2	125.4	124.5	123.7	123.1	122.6	122.0	121.4
82.5°	94.1	93.0	91.9	91.3	91.1	91.0	90.9	90.7
85°	49.7	48.8	48.0	47.4	47.1	46.8	46.5	46.1
87.5°	15.0	14.4	13.8	13.3	13.2	12.9	12.7	12.6
90°	8.2	8.6	9.0	9.3	9.5	9.6	9.8	9.9
92.5°	9.0	9.2	9.4	9.6	9.6	9.7	9.8	9.9
95°	15.2	15.6	16.0	16.2	16.1	16.0	15.9	15.8
97.5°	19.9	20.2	20.5	20.8	20.8	20.9	21.0	21.1
100°	22.3	22.9	23.6	24.0	24.2	24.4	24.5	24.6
102.5°	23.2	24.1	25.0	25.5	25.7	26.0	26.2	26.4
105°	24.3	25.1	26.1	26.7	26.9	27.3	27.6	28.0
107.5°	29.6	28.7	27.7	27.5	27.8	28.2	28.4	28.8
110°	48.0	39.9	31.7	27.7	28.1	28.4	28.8	29.1



TEST NUMBER: P331589-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	102.8	72.9	43.1	28.3	28.6	28.8	29.1	29.4
115°	151.4	113.5	75.6	53.7	47.9	41.9	36.1	30.1
117.5°	233.2	224.0	214.8	200.6	181.2	161.9	142.6	123.2
120°	271.7	272.7	273.7	268.6	257.6	246.6	235.5	224.5
122.5°	288.3	288.9	289.5	288.7	286.5	284.4	282.2	280.1
125°	312.1	312.7	313.2	313.7	313.9	314.2	314.4	314.6
127.5°	334.2	334.9	335.8	336.2	336.3	336.3	336.4	336.4
130°	348.1	349.0	349.9	350.3	350.3	350.2	350.1	350.0
132.5°	361.7	362.4	363.2	363.5	363.4	363.3	363.3	363.3
135°	381.1	381.9	382.7	383.0	382.9	382.7	382.5	382.4
137.5°	399.1	399.8	400.6	400.9	400.6	400.4	400.1	399.8
140°	410.7	411.5	412.2	412.3	411.9	411.5	411.1	410.7
142.5°	421.5	422.1	422.8	422.9	422.5	422.1	421.7	421.3
145°	436.5	437.0	437.6	437.7	437.3	436.9	436.5	436.1
147.5°	449.6	450.0	450.5	450.5	450.1	449.8	449.4	449.1
150°	457.7	458.1	458.7	458.7	458.3	457.9	457.4	457.1
152.5°	465.0	465.5	466.1	466.0	465.5	464.9	464.3	463.8
155°	475.0	475.4	476.0	475.9	475.2	474.6	473.9	473.3
157.5°	483.4	483.9	484.5	484.4	483.8	483.1	482.5	481.9
160°	488.2	488.7	489.2	489.1	488.6	488.0	487.4	486.9
162.5°	492.8	493.4	493.9	493.8	493.1	492.4	491.7	491.0
165°	498.3	498.9	499.5	499.5	498.9	498.3	497.7	497.1
167.5°	503.0	503.5	504.1	504.0	503.3	502.6	501.8	501.1
170°	505.3	505.9	506.4	506.4	505.7	504.9	504.2	503.4
172.5°	507.0	507.6	508.2	508.2	507.4	506.7	505.9	505.2
175°	509.0	509.5	510.1	510.1	509.2	508.4	507.6	506.8
177.5°	509.2	509.6	510.1	510.1	509.5	508.9	508.2	507.7
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6

(END OF REPORT)