

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331554-940

Luminaire Tested: **S122DIW-S675D1440U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331554-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D1440U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6869.3 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331554-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331554-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	94	90	86	83	85	82	78	76	66	63	61	51	50	48	37	37	36	30
2	86	79	73	68	77	71	66	62	58	54	51	45	42	40	33	31	30	25
3	78	69	62	56	71	63	57	52	51	46	43	40	37	34	29	27	26	21
4	72	61	53	48	64	56	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	41	59	49	43	37	40	35	31	32	28	25	23	21	19	16
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15285	15285	15285
5°	15344	15123	15211
10°	15252	14969	15044
15°	15064	14775	14760
20°	14795	14483	14467
25°	14530	14125	14125
30°	14188	13798	13679
35°	13868	13403	13204
40°	13468	13009	12760
45°	13075	12618	12305
50°	12645	12210	11776
55°	12197	11738	11299
60°	11699	11170	10756
65°	11163	10609	10120
70°	10485	9928	9456
75°	9538	9145	8914
80°	8461	8210	7782
85°	6928	6576	5891



TEST NUMBER: P331554-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.0	1.3
10°-20°	250.5	3.6
20°-30°	368.2	5.4
30°-40°	427.7	6.2
40°-50°	427.2	6.2
50°-60°	372.6	5.4
60°-70°	275.5	4.0
70°-80°	156.0	2.3
80°-90°	48.3	0.7
90°-100°	100.9	1.5
100°-110°	313.5	4.6
110°-120°	535.9	7.8
120°-130°	704.7	10.3
130°-140°	791.0	11.5
140°-150°	775.6	11.3
150°-160°	650.5	9.5
160°-170°	431.5	6.3
170°-180°	150.8	2.2
0°-30°	707.7	10.3
0°-40°	1135.4	16.5
0°-60°	1935.1	28.2
0°-90°	2415.0	35.2
90°-120°	950.3	13.8
90°-150°	3221.6	46.9
90°-180°	4454.0	64.8
0°-180°	6869.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	947	947	947	947	947	
5°	947	943	933	940	938	90
15°	901	895	884	887	883	254
25°	816	808	793	794	793	375
35°	704	694	680	675	670	439
45°	573	566	553	543	539	442
55°	433	428	417	406	401	387
65°	292	286	278	270	265	289
75°	153	151	147	142	143	163
85°	37	36	36	33	32	43
90°	1	18	47	45	46	5
95°	70	83	86	86	83	80
105°	289	293	296	298	298	305
115°	538	545	543	542	538	532
125°	782	794	790	787	785	699
135°	1012	1026	1030	1028	1024	782
145°	1229	1238	1246	1247	1242	767
155°	1405	1409	1413	1419	1416	646
165°	1528	1527	1527	1536	1530	431
175°	1590	1586	1584	1592	1585	151
180°	1593	1593	1593	1593	1593	



TEST NUMBER: P331554-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7
2.5°	951.1	950.3	949.5	948.7	947.9	946.6	944.8	943.0	941.2	939.4	941.0
5°	946.7	945.9	945.1	944.3	943.5	942.0	939.8	937.5	935.3	933.1	934.7
7.5°	938.3	937.1	935.9	934.6	933.4	931.6	929.3	927.0	924.8	922.5	924.1
10°	930.3	928.9	927.5	926.0	924.7	922.7	920.3	917.9	915.4	913.0	914.6
12.5°	919.4	918.2	916.9	915.6	914.4	912.6	910.1	907.7	905.3	902.9	904.0
15°	901.2	900.0	898.8	897.6	896.3	894.4	891.8	889.1	886.5	883.9	884.8
17.5°	877.9	876.6	875.5	874.2	873.1	871.1	868.4	865.8	863.1	860.4	861.4
20°	861.1	860.0	858.7	857.5	856.3	854.3	851.4	848.6	845.8	842.9	843.6
22.5°	844.4	842.7	841.0	839.3	837.6	835.4	832.8	830.1	827.4	824.7	824.8
25°	815.6	814.0	812.4	810.7	809.1	806.6	803.2	799.8	796.3	792.9	793.3
27.5°	782.8	781.4	780.0	778.5	777.0	775.0	772.2	769.5	766.8	764.1	763.5
30°	761.0	759.4	757.8	756.2	754.6	752.2	749.2	746.2	743.2	740.1	739.5
32.5°	737.7	736.4	735.1	733.8	732.5	730.3	727.1	723.9	720.7	717.5	716.4
35°	703.6	701.7	699.6	697.6	695.5	692.9	689.7	686.4	683.2	680.0	678.8
37.5°	665.2	663.4	661.6	659.9	658.2	655.6	652.4	649.2	646.0	642.7	641.1
40°	639.0	637.4	635.8	634.2	632.6	630.2	626.9	623.7	620.5	617.2	615.4
42.5°	613.6	611.9	610.3	608.7	607.1	604.7	601.4	598.2	594.9	591.7	589.7
45°	572.6	571.1	569.7	568.4	566.9	564.7	561.7	558.7	555.6	552.6	550.4
47.5°	531.8	530.5	529.1	527.8	526.5	524.2	521.0	517.9	514.8	511.6	509.3
50°	503.4	502.4	501.4	500.3	499.4	497.4	494.6	491.8	488.9	486.1	483.3
52.5°	475.7	474.4	473.1	471.7	470.4	468.4	465.7	463.1	460.4	457.7	455.4
55°	433.3	432.1	430.9	429.6	428.5	426.6	424.2	421.8	419.4	417.0	414.5
57.5°	390.7	389.8	388.8	387.8	386.8	385.0	382.4	379.7	377.0	374.3	371.9
60°	362.3	361.5	360.7	359.9	359.1	357.2	354.5	351.6	348.7	345.9	343.7
62.5°	334.7	333.3	332.1	330.7	329.5	327.7	325.6	323.3	321.2	319.0	316.9
65°	292.2	291.0	289.8	288.6	287.3	285.7	283.7	281.7	279.6	277.7	275.8
67.5°	249.1	248.1	247.1	246.1	245.1	243.8	241.9	240.1	238.4	236.5	235.1
70°	222.1	221.3	220.5	219.7	218.9	217.6	215.7	213.9	212.1	210.3	208.8
72.5°	194.5	193.6	192.8	192.0	191.2	190.2	189.0	187.9	186.7	185.5	184.1
75°	152.9	152.5	152.1	151.7	151.3	150.6	149.6	148.6	147.6	146.6	145.3
77.5°	115.8	115.1	114.4	113.7	113.1	112.5	112.1	111.6	111.3	110.8	110.3
80°	91.0	90.9	90.6	90.4	90.2	89.9	89.5	89.1	88.7	88.3	87.7
82.5°	67.8	67.7	67.7	67.6	67.6	67.4	67.1	67.0	66.7	66.4	65.7
85°	37.4	37.1	36.9	36.7	36.5	36.3	36.1	35.9	35.7	35.5	34.9
87.5°	13.4	13.7	14.2	14.5	15.0	15.6	16.7	17.7	18.6	19.6	19.0
90°	1.3	4.9	8.5	12.1	15.7	20.8	27.4	33.9	40.5	47.1	46.5
92.5°	23.9	26.6	29.2	31.8	34.4	36.6	38.1	39.7	41.2	42.7	42.9
95°	69.9	72.9	75.9	78.8	81.9	83.6	84.3	84.8	85.4	86.1	86.1
97.5°	127.7	130.4	133.0	135.6	138.2	140.1	141.2	142.4	143.5	144.6	144.6
100°	170.8	173.1	175.5	177.9	180.3	181.9	182.8	183.7	184.6	185.5	185.5
102.5°	215.9	217.8	219.7	221.6	223.6	225.1	226.2	227.3	228.5	229.6	229.9
105°	289.0	289.9	290.8	291.7	292.6	293.4	294.0	294.5	295.2	295.8	296.3
107.5°	362.7	364.0	365.3	366.7	367.9	368.6	368.6	368.6	368.6	368.6	368.8
110°	410.0	411.8	413.6	415.4	417.1	418.1	418.1	418.1	418.1	418.1	418.1



TEST NUMBER: P331554-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	461.6	463.4	465.2	467.0	468.8	469.6	469.3	469.1	468.9	468.6	467.9
115°	537.7	539.5	541.3	543.1	544.9	545.5	544.9	544.3	543.7	543.1	542.8
117.5°	613.6	615.9	618.3	620.7	623.1	623.5	621.8	620.1	618.4	616.8	616.1
120°	664.1	666.5	668.9	671.3	673.7	673.7	671.3	668.9	666.5	664.1	664.1
122.5°	710.3	713.2	716.0	718.9	721.8	722.4	720.8	719.1	717.4	715.7	715.0
125°	782.4	785.1	787.7	790.4	793.2	794.1	793.2	792.3	791.4	790.4	789.5
127.5°	852.6	856.0	859.3	862.8	866.2	867.4	866.3	865.2	864.2	863.1	861.9
130°	896.6	900.5	904.5	908.3	912.2	913.8	913.2	912.7	912.0	911.4	910.9
132.5°	946.1	949.3	952.4	955.6	958.8	960.5	960.6	960.6	960.8	960.9	959.6
135°	1012.3	1015.6	1018.9	1022.1	1025.4	1027.3	1028.0	1028.6	1029.1	1029.7	1029.5
137.5°	1081.9	1084.6	1087.3	1089.9	1092.6	1094.4	1095.2	1095.9	1096.7	1097.5	1097.3
140°	1123.8	1126.5	1129.3	1131.9	1134.6	1136.7	1138.2	1139.7	1141.2	1142.6	1142.6
142.5°	1166.9	1169.6	1172.2	1174.9	1177.6	1179.5	1180.4	1181.5	1182.5	1183.6	1183.7
145°	1228.7	1230.8	1232.9	1234.9	1237.1	1239.0	1240.8	1242.6	1244.4	1246.2	1246.4
147.5°	1283.8	1286.3	1288.8	1291.4	1293.9	1295.7	1296.9	1298.1	1299.3	1300.5	1301.2
150°	1321.4	1323.2	1325.1	1326.9	1328.6	1330.1	1331.3	1332.5	1333.7	1334.9	1335.8
152.5°	1354.8	1356.6	1358.3	1360.1	1362.0	1363.6	1365.0	1366.5	1367.9	1369.3	1370.5
155°	1404.8	1405.7	1406.6	1407.5	1408.4	1409.3	1410.2	1411.0	1411.9	1412.8	1414.3
157.5°	1447.5	1448.1	1448.8	1449.4	1449.9	1450.5	1451.1	1451.6	1452.2	1452.7	1454.6
160°	1473.4	1474.0	1474.5	1475.2	1475.8	1476.2	1476.5	1476.8	1477.1	1477.4	1479.2
162.5°	1497.0	1497.2	1497.3	1497.4	1497.5	1497.7	1498.0	1498.3	1498.6	1498.9	1500.9
165°	1528.5	1528.2	1527.9	1527.6	1527.3	1527.1	1527.1	1527.1	1527.1	1527.1	1529.2
167.5°	1554.8	1553.9	1553.0	1552.1	1551.2	1550.8	1550.7	1550.7	1550.6	1550.5	1552.6
170°	1568.8	1567.9	1567.0	1566.1	1565.2	1564.6	1564.3	1564.1	1563.7	1563.4	1565.5
172.5°	1578.5	1577.6	1576.7	1575.8	1574.9	1574.3	1574.0	1573.7	1573.4	1573.1	1575.2
175°	1590.3	1589.4	1588.5	1587.6	1586.7	1586.0	1585.4	1584.7	1584.2	1583.6	1585.7
177.5°	1595.2	1594.5	1593.8	1593.0	1592.3	1591.7	1591.2	1590.7	1590.3	1589.7	1591.2
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331554-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7
2.5°	942.6	944.3	945.9	946.6	946.2	945.9	945.6	945.3
5°	936.3	937.9	939.5	940.1	939.8	939.3	939.0	938.5
7.5°	925.8	927.4	929.0	929.5	929.1	928.7	928.3	927.8
10°	916.2	917.9	919.5	920.0	919.4	918.8	918.2	917.6
12.5°	905.1	906.2	907.4	907.7	907.2	906.9	906.4	906.0
15°	885.6	886.4	887.2	887.1	886.0	885.0	884.0	883.0
17.5°	862.3	863.2	864.2	864.2	863.2	862.2	861.2	860.2
20°	844.2	844.8	845.3	845.3	844.5	843.6	842.8	842.0
22.5°	825.0	825.1	825.2	825.0	824.6	824.0	823.6	823.1
25°	793.7	794.1	794.5	794.5	794.1	793.7	793.3	792.9
27.5°	762.9	762.3	761.7	760.9	759.9	758.9	758.0	757.0
30°	738.9	738.2	737.6	736.9	736.1	735.3	734.5	733.7
32.5°	715.3	714.3	713.1	712.2	711.4	710.6	709.7	708.9
35°	677.6	676.4	675.1	674.0	673.1	672.0	671.0	669.9
37.5°	639.7	638.2	636.7	635.4	634.5	633.5	632.6	631.6
40°	613.6	611.7	609.9	608.6	607.8	607.0	606.2	605.4
42.5°	587.7	585.8	583.8	582.2	581.0	580.0	578.8	577.7
45°	548.1	545.9	543.7	542.2	541.4	540.6	539.8	538.9
47.5°	506.9	504.5	502.2	500.4	499.3	498.1	497.0	495.8
50°	480.5	477.6	474.7	472.9	471.8	470.8	469.8	468.8
52.5°	453.0	450.7	448.4	446.5	445.1	443.8	442.5	441.1
55°	412.1	409.7	407.2	405.5	404.5	403.5	402.4	401.4
57.5°	369.5	367.1	364.8	363.2	362.4	361.7	360.9	360.1
60°	341.4	339.2	337.0	335.6	335.0	334.4	333.8	333.1
62.5°	314.9	312.8	310.8	309.3	308.5	307.7	307.0	306.2
65°	274.0	272.2	270.4	268.9	268.0	266.9	265.9	264.9
67.5°	233.6	232.3	230.9	229.7	228.9	228.1	227.3	226.5
70°	207.4	206.1	204.6	203.5	202.7	201.9	201.1	200.3
72.5°	182.7	181.3	179.9	178.8	178.2	177.5	176.9	176.2
75°	144.1	142.9	141.7	141.3	141.7	142.1	142.5	142.9
77.5°	109.7	109.1	108.4	107.9	107.3	106.7	106.2	105.6
80°	87.1	86.5	85.9	85.3	85.0	84.5	84.2	83.7
82.5°	64.9	64.1	63.4	63.0	62.9	62.8	62.7	62.6
85°	34.3	33.7	33.1	32.6	32.5	32.3	32.1	31.8
87.5°	18.4	17.8	17.2	16.9	16.8	16.6	16.5	16.4
90°	45.8	45.3	44.7	44.5	44.9	45.1	45.4	45.7
92.5°	43.0	43.1	43.2	43.3	43.3	43.4	43.5	43.5
95°	86.1	86.1	86.1	85.7	85.2	84.5	83.9	83.4
97.5°	144.6	144.6	144.6	144.6	144.5	144.5	144.5	144.4
100°	185.5	185.5	185.5	185.4	185.0	184.8	184.5	184.1
102.5°	230.1	230.3	230.6	230.5	230.2	230.0	229.6	229.3
105°	296.9	297.6	298.1	298.5	298.5	298.5	298.5	298.5
107.5°	369.1	369.3	369.5	369.0	367.7	366.2	364.9	363.5
110°	418.1	418.1	418.1	417.6	416.7	415.8	414.9	414.0



TEST NUMBER: P331554-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	467.2	466.5	465.7	465.0	464.4	463.8	463.1	462.4
115°	542.5	542.2	541.9	541.3	540.4	539.5	538.6	537.7
117.5°	615.4	614.7	613.9	613.1	612.2	611.3	610.4	609.5
120°	664.1	664.1	664.1	663.6	662.7	661.8	660.9	660.0
122.5°	714.3	713.5	712.8	712.1	711.5	710.9	710.2	709.5
125°	788.6	787.7	786.8	786.3	786.0	785.7	785.4	785.1
127.5°	860.9	859.8	858.7	857.7	856.8	855.8	854.9	853.9
130°	910.3	909.6	909.0	908.1	907.0	905.8	904.6	903.4
132.5°	958.3	957.0	955.6	954.5	953.6	952.6	951.6	950.7
135°	1029.1	1028.9	1028.6	1028.0	1027.1	1026.2	1025.3	1024.4
137.5°	1097.0	1096.8	1096.5	1095.8	1094.7	1093.4	1092.3	1091.0
140°	1142.6	1142.6	1142.6	1142.1	1140.9	1139.7	1138.4	1137.3
142.5°	1184.0	1184.3	1184.5	1184.0	1182.9	1181.6	1180.4	1179.2
145°	1246.8	1247.1	1247.3	1246.9	1245.7	1244.6	1243.3	1242.2
147.5°	1301.8	1302.4	1303.1	1302.9	1301.7	1300.6	1299.5	1298.3
150°	1336.7	1337.6	1338.5	1338.5	1337.6	1336.7	1335.8	1334.9
152.5°	1371.5	1372.7	1373.9	1373.9	1372.7	1371.5	1370.5	1369.3
155°	1415.9	1417.4	1418.8	1419.2	1418.3	1417.4	1416.5	1415.6
157.5°	1456.7	1458.7	1460.8	1461.1	1459.6	1458.2	1456.8	1455.4
160°	1481.0	1482.7	1484.5	1484.9	1483.6	1482.5	1481.3	1480.1
162.5°	1503.0	1505.0	1507.0	1507.3	1505.9	1504.5	1503.1	1501.6
165°	1531.3	1533.4	1535.5	1535.8	1534.3	1532.9	1531.3	1529.8
167.5°	1554.7	1556.8	1558.9	1559.2	1557.6	1556.0	1554.5	1552.9
170°	1567.6	1569.7	1571.8	1571.9	1570.1	1568.3	1566.6	1564.8
172.5°	1577.3	1579.4	1581.4	1581.6	1579.8	1578.1	1576.3	1574.5
175°	1587.8	1589.8	1592.0	1592.1	1590.3	1588.5	1586.7	1584.9
177.5°	1592.7	1594.1	1595.5	1595.5	1594.1	1592.7	1591.2	1589.7
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0

(END OF REPORT)