

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331536-940

Luminaire Tested: **S122DIW-S675D710U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331536-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D710U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4604.2 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331536-940

CATALOG NUMBER: S122DIW-S675D710U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331536-940

CATALOG NUMBER: S122DIW-S675D710U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	52	50	49	44
2	90	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	41	37
3	82	72	65	59	75	67	61	55	57	52	48	48	45	42	40	38	35	31
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30	27
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	27	23
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23	20
7	58	46	38	33	54	43	36	31	37	32	27	32	27	24	27	23	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	17	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15285	15285	15285
5°	15344	15123	15211
10°	15252	14969	15044
15°	15064	14775	14760
20°	14795	14483	14467
25°	14530	14125	14125
30°	14188	13798	13679
35°	13868	13403	13204
40°	13468	13009	12760
45°	13075	12618	12305
50°	12645	12210	11776
55°	12197	11738	11299
60°	11699	11170	10756
65°	11163	10609	10120
70°	10485	9928	9456
75°	9538	9145	8914
80°	8461	8210	7782
85°	6928	6576	5891



TEST NUMBER: P331536-940

CATALOG NUMBER: S122DIW-S675D710U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.0	1.9
10°-20°	250.5	5.4
20°-30°	368.2	8.0
30°-40°	427.7	9.3
40°-50°	427.2	9.3
50°-60°	372.6	8.1
60°-70°	275.5	6.0
70°-80°	156.0	3.4
80°-90°	45.1	1.0
90°-100°	49.7	1.1
100°-110°	154.3	3.4
110°-120°	263.8	5.7
120°-130°	346.9	7.5
130°-140°	389.3	8.5
140°-150°	381.7	8.3
150°-160°	320.2	7.0
160°-170°	212.4	4.6
170°-180°	74.2	1.6
0°-30°	707.7	15.4
0°-40°	1135.4	24.7
0°-60°	1935.1	42.0
0°-90°	2411.7	52.4
90°-120°	467.8	10.2
90°-150°	1585.7	34.4
90°-180°	2193.0	47.6
0°-180°	4604.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	947	947	947	947	947	
5°	947	943	933	940	938	90
15°	901	895	884	887	883	254
25°	816	808	793	794	793	375
35°	704	694	680	675	670	439
45°	573	566	553	543	539	442
55°	433	428	417	406	401	387
65°	292	286	278	270	265	289
75°	153	151	147	142	143	163
85°	37	36	36	33	32	43
90°	1	9	23	22	22	4
95°	34	41	42	42	41	39
105°	142	144	146	147	147	150
115°	265	268	267	267	265	262
125°	385	391	389	387	386	344
135°	498	505	507	506	504	385
145°	605	609	613	614	611	378
155°	691	693	695	698	697	318
165°	752	752	752	756	753	212
175°	783	781	779	784	780	74
180°	784	784	784	784	784	



TEST NUMBER: P331536-940

CATALOG NUMBER: S122DIW-S675D710U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7
2.5°	951.1	950.3	949.5	948.7	947.9	946.6	944.8	943.0	941.2	939.4	941.0
5°	946.7	945.9	945.1	944.3	943.5	942.0	939.8	937.5	935.3	933.1	934.7
7.5°	938.3	937.1	935.9	934.6	933.4	931.6	929.3	927.0	924.8	922.5	924.1
10°	930.3	928.9	927.5	926.0	924.7	922.7	920.3	917.9	915.4	913.0	914.6
12.5°	919.4	918.2	916.9	915.6	914.4	912.6	910.1	907.7	905.3	902.9	904.0
15°	901.2	900.0	898.8	897.6	896.3	894.4	891.8	889.1	886.5	883.9	884.8
17.5°	877.9	876.6	875.5	874.2	873.1	871.1	868.4	865.8	863.1	860.4	861.4
20°	861.1	860.0	858.7	857.5	856.3	854.3	851.4	848.6	845.8	842.9	843.6
22.5°	844.4	842.7	841.0	839.3	837.6	835.4	832.8	830.1	827.4	824.7	824.8
25°	815.6	814.0	812.4	810.7	809.1	806.6	803.2	799.8	796.3	792.9	793.3
27.5°	782.8	781.4	780.0	778.5	777.0	775.0	772.2	769.5	766.8	764.1	763.5
30°	761.0	759.4	757.8	756.2	754.6	752.2	749.2	746.2	743.2	740.1	739.5
32.5°	737.7	736.4	735.1	733.8	732.5	730.3	727.1	723.9	720.7	717.5	716.4
35°	703.6	701.7	699.6	697.6	695.5	692.9	689.7	686.4	683.2	680.0	678.8
37.5°	665.2	663.4	661.6	659.9	658.2	655.6	652.4	649.2	646.0	642.7	641.1
40°	639.0	637.4	635.8	634.2	632.6	630.2	626.9	623.7	620.5	617.2	615.4
42.5°	613.6	611.9	610.3	608.7	607.1	604.7	601.4	598.2	594.9	591.7	589.7
45°	572.6	571.1	569.7	568.4	566.9	564.7	561.7	558.7	555.6	552.6	550.4
47.5°	531.8	530.5	529.1	527.8	526.5	524.2	521.0	517.9	514.8	511.6	509.3
50°	503.4	502.4	501.4	500.3	499.4	497.4	494.6	491.8	488.9	486.1	483.3
52.5°	475.7	474.4	473.1	471.7	470.4	468.4	465.7	463.1	460.4	457.7	455.4
55°	433.3	432.1	430.9	429.6	428.5	426.6	424.2	421.8	419.4	417.0	414.5
57.5°	390.7	389.8	388.8	387.8	386.8	385.0	382.4	379.7	377.0	374.3	371.9
60°	362.3	361.5	360.7	359.9	359.1	357.2	354.5	351.6	348.7	345.9	343.7
62.5°	334.7	333.3	332.1	330.7	329.5	327.7	325.6	323.3	321.2	319.0	316.9
65°	292.2	291.0	289.8	288.6	287.3	285.7	283.7	281.7	279.6	277.7	275.8
67.5°	249.1	248.1	247.1	246.1	245.1	243.8	241.9	240.1	238.4	236.5	235.1
70°	222.1	221.3	220.5	219.7	218.9	217.6	215.7	213.9	212.1	210.3	208.8
72.5°	194.5	193.6	192.8	192.0	191.2	190.2	189.0	187.9	186.7	185.5	184.1
75°	152.9	152.5	152.1	151.7	151.3	150.6	149.6	148.6	147.6	146.6	145.3
77.5°	115.8	115.1	114.4	113.7	113.1	112.5	112.1	111.6	111.3	110.8	110.3
80°	91.0	90.9	90.6	90.4	90.2	89.9	89.5	89.1	88.7	88.3	87.7
82.5°	67.8	67.7	67.7	67.6	67.6	67.4	67.1	67.0	66.7	66.4	65.7
85°	37.4	37.1	36.9	36.7	36.5	36.3	36.1	35.9	35.7	35.5	34.9
87.5°	13.2	13.3	13.3	13.3	13.4	13.6	13.8	14.2	14.5	14.8	14.3
90°	0.6	2.4	4.2	6.0	7.8	10.3	13.5	16.7	19.9	23.2	22.8
92.5°	11.8	13.1	14.4	15.7	16.9	18.0	18.7	19.5	20.2	21.0	21.1
95°	34.4	35.8	37.4	38.8	40.3	41.2	41.5	41.7	42.1	42.4	42.4
97.5°	62.9	64.1	65.5	66.7	68.0	68.9	69.6	70.1	70.6	71.2	71.2
100°	84.0	85.2	86.4	87.6	88.7	89.5	90.0	90.4	90.9	91.3	91.3
102.5°	106.3	107.2	108.2	109.1	110.0	110.8	111.4	111.9	112.4	113.0	113.2
105°	142.2	142.7	143.1	143.6	144.0	144.4	144.7	145.0	145.3	145.6	145.9
107.5°	178.5	179.1	179.9	180.5	181.1	181.5	181.5	181.5	181.5	181.5	181.6
110°	201.8	202.7	203.6	204.5	205.4	205.8	205.8	205.8	205.8	205.8	205.8



TEST NUMBER: P331536-940

CATALOG NUMBER: S122DIW-S675D710U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	227.2	228.1	229.0	229.9	230.8	231.1	231.0	230.9	230.8	230.7	230.3
115°	264.7	265.6	266.4	267.3	268.2	268.5	268.2	267.9	267.6	267.3	267.2
117.5°	302.0	303.2	304.3	305.5	306.7	306.8	306.0	305.2	304.4	303.6	303.3
120°	326.9	328.1	329.2	330.4	331.5	331.5	330.4	329.2	328.1	326.9	326.9
122.5°	349.6	351.1	352.5	353.8	355.3	355.6	354.7	353.9	353.1	352.3	352.0
125°	385.1	386.5	387.7	389.1	390.4	390.8	390.4	389.9	389.5	389.1	388.6
127.5°	419.6	421.3	423.0	424.6	426.3	427.0	426.4	425.9	425.3	424.8	424.3
130°	441.3	443.3	445.1	447.1	449.0	449.8	449.5	449.2	448.9	448.6	448.4
132.5°	465.7	467.3	468.9	470.4	471.9	472.8	472.8	472.9	473.0	473.0	472.3
135°	498.3	499.9	501.5	503.1	504.7	505.7	506.0	506.3	506.6	506.8	506.7
137.5°	532.5	533.9	535.2	536.5	537.8	538.7	539.0	539.5	539.8	540.2	540.1
140°	553.2	554.5	555.8	557.1	558.5	559.5	560.3	561.0	561.7	562.4	562.4
142.5°	574.4	575.7	577.0	578.4	579.6	580.6	581.0	581.6	582.0	582.6	582.6
145°	604.8	605.8	606.8	607.9	608.9	609.8	610.7	611.6	612.5	613.4	613.5
147.5°	632.0	633.1	634.4	635.6	636.9	637.8	638.4	638.9	639.5	640.2	640.4
150°	650.4	651.3	652.2	653.1	654.0	654.7	655.3	655.9	656.5	657.1	657.5
152.5°	666.8	667.7	668.6	669.5	670.4	671.2	671.9	672.6	673.3	674.0	674.6
155°	691.4	691.9	692.3	692.8	693.2	693.7	694.1	694.6	695.0	695.4	696.2
157.5°	712.5	712.8	713.1	713.4	713.7	714.0	714.3	714.5	714.8	715.1	716.0
160°	725.2	725.5	725.8	726.1	726.4	726.7	726.7	726.9	727.0	727.2	728.1
162.5°	736.8	736.9	737.0	737.0	737.1	737.2	737.4	737.5	737.6	737.8	738.8
165°	752.3	752.2	752.1	751.9	751.8	751.7	751.7	751.7	751.7	751.7	752.7
167.5°	765.4	764.9	764.5	764.0	763.6	763.3	763.3	763.2	763.2	763.2	764.2
170°	772.2	771.8	771.3	770.9	770.4	770.2	770.0	769.8	769.7	769.5	770.6
172.5°	776.9	776.5	776.1	775.6	775.2	774.9	774.7	774.6	774.5	774.3	775.3
175°	782.7	782.4	781.9	781.5	781.0	780.7	780.3	780.1	779.8	779.4	780.5
177.5°	785.2	784.8	784.4	784.1	783.7	783.5	783.2	783.0	782.7	782.5	783.2
180°	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1



TEST NUMBER: P331536-940

CATALOG NUMBER: S122DIW-S675D710U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7
2.5°	942.6	944.3	945.9	946.6	946.2	945.9	945.6	945.3
5°	936.3	937.9	939.5	940.1	939.8	939.3	939.0	938.5
7.5°	925.8	927.4	929.0	929.5	929.1	928.7	928.3	927.8
10°	916.2	917.9	919.5	920.0	919.4	918.8	918.2	917.6
12.5°	905.1	906.2	907.4	907.7	907.2	906.9	906.4	906.0
15°	885.6	886.4	887.2	887.1	886.0	885.0	884.0	883.0
17.5°	862.3	863.2	864.2	864.2	863.2	862.2	861.2	860.2
20°	844.2	844.8	845.3	845.3	844.5	843.6	842.8	842.0
22.5°	825.0	825.1	825.2	825.0	824.6	824.0	823.6	823.1
25°	793.7	794.1	794.5	794.5	794.1	793.7	793.3	792.9
27.5°	762.9	762.3	761.7	760.9	759.9	758.9	758.0	757.0
30°	738.9	738.2	737.6	736.9	736.1	735.3	734.5	733.7
32.5°	715.3	714.3	713.1	712.2	711.4	710.6	709.7	708.9
35°	677.6	676.4	675.1	674.0	673.1	672.0	671.0	669.9
37.5°	639.7	638.2	636.7	635.4	634.5	633.5	632.6	631.6
40°	613.6	611.7	609.9	608.6	607.8	607.0	606.2	605.4
42.5°	587.7	585.8	583.8	582.2	581.0	580.0	578.8	577.7
45°	548.1	545.9	543.7	542.2	541.4	540.6	539.8	538.9
47.5°	506.9	504.5	502.2	500.4	499.3	498.1	497.0	495.8
50°	480.5	477.6	474.7	472.9	471.8	470.8	469.8	468.8
52.5°	453.0	450.7	448.4	446.5	445.1	443.8	442.5	441.1
55°	412.1	409.7	407.2	405.5	404.5	403.5	402.4	401.4
57.5°	369.5	367.1	364.8	363.2	362.4	361.7	360.9	360.1
60°	341.4	339.2	337.0	335.6	335.0	334.4	333.8	333.1
62.5°	314.9	312.8	310.8	309.3	308.5	307.7	307.0	306.2
65°	274.0	272.2	270.4	268.9	268.0	266.9	265.9	264.9
67.5°	233.6	232.3	230.9	229.7	228.9	228.1	227.3	226.5
70°	207.4	206.1	204.6	203.5	202.7	201.9	201.1	200.3
72.5°	182.7	181.3	179.9	178.8	178.2	177.5	176.9	176.2
75°	144.1	142.9	141.7	141.3	141.7	142.1	142.5	142.9
77.5°	109.7	109.1	108.4	107.9	107.3	106.7	106.2	105.6
80°	87.1	86.5	85.9	85.3	85.0	84.5	84.2	83.7
82.5°	64.9	64.1	63.4	63.0	62.9	62.8	62.7	62.6
85°	34.3	33.7	33.1	32.6	32.5	32.3	32.1	31.8
87.5°	13.7	13.2	12.7	12.3	12.2	12.0	11.9	11.8
90°	22.6	22.3	22.0	21.9	22.0	22.2	22.4	22.5
92.5°	21.1	21.2	21.3	21.3	21.3	21.4	21.4	21.4
95°	42.4	42.4	42.4	42.2	41.9	41.6	41.3	41.0
97.5°	71.2	71.2	71.2	71.2	71.2	71.2	71.1	71.1
100°	91.3	91.3	91.3	91.2	91.1	91.0	90.8	90.7
102.5°	113.2	113.3	113.5	113.5	113.3	113.2	113.1	112.9
105°	146.2	146.4	146.8	146.9	146.9	146.9	146.9	146.9
107.5°	181.6	181.8	181.9	181.6	180.9	180.3	179.6	179.0
110°	205.8	205.8	205.8	205.5	205.1	204.6	204.2	203.8



TEST NUMBER: P331536-940

CATALOG NUMBER: S122DIW-S675D710U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	230.0	229.6	229.3	228.9	228.6	228.3	227.9	227.7
115°	267.1	266.9	266.7	266.4	266.0	265.6	265.1	264.7
117.5°	302.9	302.6	302.2	301.8	301.3	300.9	300.4	300.0
120°	326.9	326.9	326.9	326.6	326.2	325.7	325.3	324.9
122.5°	351.6	351.2	350.9	350.5	350.2	349.9	349.6	349.3
125°	388.2	387.7	387.3	387.0	386.9	386.7	386.6	386.5
127.5°	423.7	423.2	422.7	422.2	421.7	421.2	420.8	420.4
130°	448.1	447.7	447.5	447.0	446.4	445.9	445.2	444.7
132.5°	471.7	471.0	470.4	469.8	469.4	468.9	468.4	468.0
135°	506.6	506.4	506.3	506.0	505.5	505.1	504.6	504.2
137.5°	539.9	539.8	539.8	539.4	538.8	538.2	537.6	537.0
140°	562.4	562.4	562.4	562.1	561.6	561.0	560.4	559.8
142.5°	582.8	582.9	583.0	582.8	582.2	581.6	581.0	580.4
145°	613.7	613.9	613.9	613.8	613.1	612.6	612.0	611.4
147.5°	640.8	641.1	641.4	641.3	640.8	640.2	639.6	639.1
150°	657.9	658.4	658.8	658.8	658.4	657.9	657.5	657.1
152.5°	675.1	675.6	676.3	676.3	675.6	675.1	674.6	674.0
155°	696.9	697.7	698.4	698.6	698.1	697.7	697.2	696.8
157.5°	717.0	718.0	719.0	719.2	718.5	717.7	717.0	716.3
160°	729.0	729.9	730.8	730.8	730.3	729.7	729.2	728.5
162.5°	739.8	740.8	741.8	741.9	741.2	740.6	739.9	739.1
165°	753.8	754.7	755.8	756.0	755.2	754.5	753.8	753.0
167.5°	765.3	766.2	767.3	767.4	766.7	765.9	765.2	764.4
170°	771.6	772.7	773.6	773.7	772.8	772.0	771.1	770.2
172.5°	776.4	777.4	778.5	778.5	777.7	776.8	775.9	775.0
175°	781.5	782.6	783.6	783.6	782.7	781.9	781.0	780.2
177.5°	783.9	784.6	785.3	785.3	784.6	783.9	783.2	782.5
180°	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1

(END OF REPORT)