

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331590-935

Luminaire Tested: **S122DIW-S1005D435U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331590-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D435U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4785.7 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331590-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331590-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	98	94	90	87	84	82	79	76	74	72	68	67	65	61
2	94	86	80	74	89	82	76	71	74	70	66	67	63	60	60	57	55	52
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	44
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	40	37
5	72	60	51	45	68	57	50	44	52	46	41	47	42	38	43	39	35	33
6	67	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31	29
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25
8	57	45	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	38	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22157	22157	22157
5°	22242	21921	22049
10°	22109	21697	21807
15°	21835	21417	21396
20°	21448	20993	20972
25°	21063	20475	20475
30°	20566	19999	19827
35°	20103	19429	19141
40°	19524	18858	18493
45°	18952	18287	17838
50°	18329	17698	17071
55°	17681	17011	16380
60°	16956	16191	15594
65°	16180	15373	14670
70°	15196	14389	13704
75°	13830	13250	12926
80°	12273	11901	11288
85°	10022	9541	8540



TEST NUMBER: P331590-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.0	2.7
10°-20°	363.1	7.6
20°-30°	533.7	11.2
30°-40°	619.9	13.0
40°-50°	619.3	12.9
50°-60°	540.0	11.3
60°-70°	399.3	8.3
70°-80°	226.2	4.7
80°-90°	62.7	1.3
90°-100°	29.3	0.6
100°-110°	91.0	1.9
110°-120°	155.5	3.2
120°-130°	204.5	4.3
130°-140°	229.5	4.8
140°-150°	225.0	4.7
150°-160°	188.8	3.9
160°-170°	125.2	2.6
170°-180°	43.8	0.9
0°-30°	1025.8	21.4
0°-40°	1645.7	34.4
0°-60°	2805.0	58.6
0°-90°	3493.2	73.0
90°-120°	275.7	5.8
90°-150°	934.8	19.5
90°-180°	1293.0	27.0
0°-180°	4785.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1372	1366	1352	1362	1360	130
15°	1306	1298	1281	1286	1280	368
25°	1182	1171	1149	1152	1149	544
35°	1020	1006	986	978	971	637
45°	830	820	801	787	781	640
55°	628	620	604	589	582	561
65°	424	415	402	391	384	419
75°	222	219	212	205	207	237
85°	54	53	52	48	46	62
90°	0	5	14	13	13	4
95°	20	24	25	25	24	23
105°	84	85	86	87	87	89
115°	156	158	158	157	156	154
125°	227	230	229	228	228	203
135°	294	298	299	298	297	227
145°	356	359	362	362	360	223
155°	408	409	410	412	411	188
165°	444	443	443	446	444	125
175°	462	460	460	462	460	44
180°	462	462	462	462	462	



TEST NUMBER: P331590-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3
2.5°	1378.6	1377.4	1376.3	1375.1	1373.9	1372.1	1369.5	1366.9	1364.3	1361.8	1364.1
5°	1372.3	1371.1	1369.9	1368.7	1367.6	1365.4	1362.2	1358.9	1355.7	1352.5	1354.9
7.5°	1360.1	1358.3	1356.5	1354.7	1352.9	1350.3	1347.0	1343.8	1340.5	1337.2	1339.5
10°	1348.5	1346.5	1344.5	1342.4	1340.3	1337.6	1334.0	1330.5	1327.0	1323.4	1325.9
12.5°	1332.7	1330.8	1329.0	1327.2	1325.4	1322.8	1319.2	1315.7	1312.3	1308.7	1310.4
15°	1306.3	1304.6	1302.8	1301.1	1299.2	1296.5	1292.7	1288.8	1285.0	1281.3	1282.5
17.5°	1272.6	1270.7	1269.0	1267.2	1265.5	1262.7	1258.8	1254.9	1251.0	1247.2	1248.5
20°	1248.3	1246.5	1244.7	1242.9	1241.2	1238.3	1234.2	1230.1	1226.0	1221.8	1222.7
22.5°	1224.0	1221.5	1219.1	1216.6	1214.1	1211.0	1207.1	1203.2	1199.4	1195.5	1195.7
25°	1182.3	1179.9	1177.6	1175.3	1172.9	1169.2	1164.2	1159.3	1154.3	1149.3	1149.9
27.5°	1134.8	1132.6	1130.6	1128.4	1126.4	1123.3	1119.4	1115.4	1111.6	1107.6	1106.7
30°	1103.1	1100.8	1098.4	1096.1	1093.7	1090.4	1086.0	1081.6	1077.2	1072.7	1071.9
32.5°	1069.4	1067.5	1065.6	1063.7	1061.8	1058.6	1054.0	1049.3	1044.7	1040.0	1038.5
35°	1019.9	1017.0	1014.1	1011.2	1008.2	1004.4	999.7	995.1	990.4	985.7	984.0
37.5°	964.3	961.7	959.2	956.6	954.0	950.4	945.6	941.0	936.3	931.6	929.4
40°	926.3	923.9	921.6	919.3	916.9	913.4	908.7	904.0	899.3	894.7	892.0
42.5°	889.3	887.0	884.7	882.4	879.9	876.4	871.8	867.0	862.4	857.6	854.8
45°	830.0	827.9	825.9	823.8	821.7	818.6	814.2	809.8	805.4	800.9	797.7
47.5°	770.9	769.0	767.0	765.1	763.1	759.8	755.3	750.7	746.1	741.6	738.1
50°	729.7	728.2	726.8	725.3	723.8	721.0	717.0	712.8	708.7	704.6	700.5
52.5°	689.6	687.7	685.7	683.8	681.8	678.9	675.0	671.1	667.4	663.5	660.0
55°	628.1	626.3	624.6	622.8	621.0	618.4	614.9	611.4	607.9	604.3	600.8
57.5°	566.4	564.9	563.5	562.1	560.7	558.1	554.2	550.4	546.5	542.6	539.2
60°	525.1	524.0	522.8	521.7	520.5	517.8	513.8	509.6	505.5	501.4	498.2
62.5°	485.1	483.2	481.3	479.4	477.5	475.0	471.8	468.7	465.5	462.4	459.3
65°	423.5	421.8	420.1	418.3	416.6	414.1	411.2	408.3	405.4	402.4	399.8
67.5°	361.0	359.6	358.2	356.8	355.4	353.4	350.7	348.1	345.4	342.9	340.8
70°	321.9	320.8	319.6	318.5	317.3	315.4	312.7	310.0	307.5	304.8	302.7
72.5°	281.8	280.7	279.5	278.4	277.2	275.7	274.1	272.3	270.6	268.9	266.8
75°	221.7	221.1	220.5	219.9	219.3	218.3	216.8	215.3	213.9	212.4	210.7
77.5°	167.8	166.9	165.8	164.9	163.8	163.1	162.5	161.9	161.3	160.7	159.8
80°	132.0	131.6	131.4	131.0	130.8	130.4	129.8	129.2	128.5	128.0	127.1
82.5°	98.2	98.2	98.1	98.0	97.9	97.7	97.4	97.0	96.7	96.3	95.2
85°	54.1	53.8	53.6	53.2	53.0	52.6	52.3	52.0	51.7	51.5	50.5
87.5°	19.1	18.9	18.6	18.3	18.0	17.8	17.7	17.7	17.6	17.5	16.8
90°	0.4	1.5	2.5	3.5	4.6	6.0	7.9	9.8	11.7	13.7	13.5
92.5°	7.0	7.7	8.4	9.2	10.0	10.6	11.0	11.5	12.0	12.4	12.4
95°	20.3	21.2	22.0	22.9	23.8	24.3	24.5	24.6	24.8	25.0	25.0
97.5°	37.0	37.8	38.6	39.3	40.1	40.6	41.0	41.3	41.7	41.9	41.9
100°	49.5	50.2	50.9	51.7	52.3	52.8	53.0	53.3	53.6	53.8	53.8
102.5°	62.7	63.2	63.7	64.3	64.8	65.3	65.6	66.0	66.3	66.6	66.7
105°	83.9	84.1	84.4	84.6	84.9	85.2	85.3	85.5	85.7	85.8	86.0
107.5°	105.2	105.6	106.0	106.4	106.8	106.9	106.9	106.9	106.9	106.9	107.0
110°	119.0	119.5	120.0	120.5	121.1	121.3	121.3	121.3	121.3	121.3	121.3



TEST NUMBER: P331590-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	134.0	134.5	135.0	135.5	136.0	136.3	136.2	136.1	136.0	136.0	135.8
115°	156.0	156.5	157.0	157.6	158.1	158.3	158.1	157.9	157.7	157.6	157.5
117.5°	178.1	178.7	179.4	180.1	180.8	180.9	180.5	179.9	179.4	179.0	178.7
120°	192.7	193.4	194.1	194.8	195.4	195.4	194.8	194.1	193.4	192.7	192.7
122.5°	206.1	207.0	207.8	208.6	209.5	209.7	209.1	208.6	208.2	207.7	207.5
125°	227.0	227.8	228.6	229.4	230.1	230.4	230.1	229.9	229.6	229.4	229.1
127.5°	247.4	248.4	249.3	250.4	251.3	251.7	251.4	251.1	250.7	250.5	250.1
130°	260.2	261.3	262.4	263.6	264.7	265.2	265.0	264.8	264.7	264.5	264.3
132.5°	274.6	275.4	276.4	277.3	278.2	278.7	278.7	278.8	278.8	278.8	278.4
135°	293.8	294.7	295.7	296.6	297.6	298.1	298.3	298.4	298.6	298.8	298.7
137.5°	313.9	314.7	315.5	316.2	317.0	317.5	317.8	318.1	318.2	318.5	318.4
140°	326.1	326.9	327.7	328.5	329.2	329.8	330.3	330.7	331.1	331.6	331.6
142.5°	338.6	339.4	340.2	341.0	341.7	342.2	342.5	342.9	343.1	343.5	343.5
145°	356.5	357.1	357.7	358.3	359.0	359.6	360.1	360.6	361.1	361.6	361.7
147.5°	372.6	373.2	374.0	374.7	375.5	376.0	376.3	376.7	377.0	377.4	377.5
150°	383.5	384.0	384.5	385.0	385.6	386.0	386.3	386.7	387.0	387.4	387.6
152.5°	393.1	393.6	394.2	394.7	395.2	395.7	396.1	396.5	396.9	397.4	397.7
155°	407.6	407.9	408.1	408.5	408.7	409.0	409.2	409.5	409.7	410.0	410.4
157.5°	420.1	420.3	420.4	420.6	420.8	420.9	421.0	421.2	421.4	421.5	422.1
160°	427.6	427.7	427.9	428.1	428.3	428.3	428.4	428.5	428.6	428.7	429.2
162.5°	434.4	434.5	434.5	434.5	434.5	434.6	434.7	434.8	434.9	435.0	435.5
165°	443.5	443.4	443.3	443.2	443.2	443.2	443.2	443.2	443.2	443.2	443.8
167.5°	451.2	450.9	450.6	450.4	450.1	450.0	450.0	450.0	450.0	450.0	450.6
170°	455.2	455.0	454.7	454.4	454.2	454.0	453.9	453.8	453.7	453.7	454.3
172.5°	458.1	457.8	457.5	457.3	457.0	456.8	456.8	456.7	456.6	456.5	457.1
175°	461.5	461.2	461.0	460.7	460.5	460.2	460.0	459.9	459.7	459.5	460.1
177.5°	462.9	462.7	462.4	462.3	462.0	461.8	461.8	461.6	461.4	461.3	461.8
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3



TEST NUMBER: P331590-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3
2.5°	1366.4	1368.7	1371.1	1372.1	1371.6	1371.1	1370.6	1370.2
5°	1357.2	1359.5	1361.8	1362.8	1362.2	1361.6	1361.0	1360.4
7.5°	1341.9	1344.2	1346.6	1347.5	1346.8	1346.2	1345.5	1344.9
10°	1328.2	1330.5	1332.8	1333.6	1332.7	1331.8	1330.9	1330.1
12.5°	1312.0	1313.6	1315.3	1315.8	1315.1	1314.5	1313.8	1313.2
15°	1283.6	1284.8	1285.9	1285.8	1284.4	1282.9	1281.4	1280.0
17.5°	1249.9	1251.3	1252.6	1252.6	1251.1	1249.7	1248.4	1246.9
20°	1223.7	1224.5	1225.4	1225.2	1224.1	1222.9	1221.8	1220.6
22.5°	1195.8	1196.0	1196.2	1195.9	1195.2	1194.6	1193.8	1193.1
25°	1150.5	1151.1	1151.7	1151.7	1151.1	1150.5	1149.9	1149.3
27.5°	1105.9	1104.9	1104.1	1102.9	1101.6	1100.1	1098.7	1097.3
30°	1071.0	1070.1	1069.3	1068.2	1067.0	1065.8	1064.7	1063.5
32.5°	1036.9	1035.3	1033.7	1032.3	1031.1	1030.0	1028.8	1027.6
35°	982.1	980.4	978.6	977.1	975.6	974.1	972.6	971.1
37.5°	927.2	925.1	922.9	921.1	919.7	918.3	916.9	915.5
40°	889.3	886.7	884.1	882.2	881.0	879.9	878.7	877.4
42.5°	852.0	849.0	846.2	844.0	842.3	840.7	839.0	837.3
45°	794.5	791.3	788.1	785.8	784.6	783.5	782.3	781.2
47.5°	734.8	731.3	728.0	725.4	723.7	722.0	720.3	718.6
50°	696.4	692.3	688.2	685.4	684.0	682.5	681.1	679.6
52.5°	656.7	653.2	649.9	647.2	645.2	643.3	641.4	639.5
55°	597.3	593.7	590.3	587.8	586.3	584.9	583.4	581.9
57.5°	535.6	532.2	528.7	526.4	525.4	524.3	523.1	522.0
60°	495.0	491.7	488.5	486.5	485.6	484.7	483.8	482.9
62.5°	456.4	453.4	450.4	448.3	447.2	446.1	445.0	443.8
65°	397.2	394.5	391.9	389.9	388.4	386.9	385.5	384.0
67.5°	338.7	336.7	334.6	332.9	331.8	330.6	329.5	328.3
70°	300.7	298.7	296.6	295.0	293.8	292.7	291.4	290.3
72.5°	264.8	262.8	260.7	259.2	258.3	257.4	256.4	255.5
75°	209.0	207.2	205.4	204.8	205.4	206.0	206.6	207.2
77.5°	158.9	158.1	157.2	156.4	155.5	154.7	153.9	153.1
80°	126.2	125.4	124.5	123.7	123.1	122.6	122.0	121.4
82.5°	94.1	93.0	91.9	91.3	91.1	91.0	90.9	90.7
85°	49.7	48.8	48.0	47.4	47.1	46.8	46.5	46.1
87.5°	16.0	15.3	14.6	14.1	13.9	13.6	13.4	13.2
90°	13.3	13.2	13.0	12.9	13.0	13.1	13.2	13.3
92.5°	12.5	12.5	12.6	12.6	12.6	12.6	12.7	12.7
95°	25.0	25.0	25.0	24.9	24.7	24.5	24.4	24.2
97.5°	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9
100°	53.8	53.8	53.8	53.8	53.7	53.6	53.6	53.5
102.5°	66.7	66.8	66.9	66.9	66.8	66.7	66.6	66.6
105°	86.2	86.4	86.5	86.6	86.6	86.6	86.6	86.6
107.5°	107.1	107.2	107.3	107.1	106.7	106.2	105.9	105.5
110°	121.3	121.3	121.3	121.1	120.9	120.6	120.4	120.1



TEST NUMBER: P331590-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	135.6	135.3	135.2	134.9	134.7	134.6	134.4	134.2
115°	157.4	157.3	157.2	157.0	156.8	156.5	156.3	156.0
117.5°	178.6	178.3	178.1	177.9	177.6	177.4	177.1	176.8
120°	192.7	192.7	192.7	192.6	192.3	192.1	191.8	191.6
122.5°	207.2	207.1	206.8	206.6	206.5	206.3	206.0	205.9
125°	228.9	228.6	228.3	228.2	228.1	228.0	227.9	227.8
127.5°	249.8	249.5	249.2	248.9	248.6	248.3	248.1	247.8
130°	264.2	264.0	263.8	263.6	263.2	262.9	262.5	262.2
132.5°	278.1	277.7	277.3	277.0	276.7	276.4	276.1	275.9
135°	298.6	298.5	298.4	298.3	298.0	297.7	297.5	297.2
137.5°	318.3	318.2	318.2	318.0	317.6	317.3	316.9	316.6
140°	331.6	331.6	331.6	331.4	331.1	330.7	330.4	330.0
142.5°	343.5	343.6	343.7	343.5	343.2	342.9	342.5	342.2
145°	361.8	361.9	362.0	361.8	361.4	361.1	360.8	360.4
147.5°	377.7	378.0	378.2	378.1	377.7	377.4	377.0	376.8
150°	387.9	388.1	388.4	388.4	388.1	387.9	387.6	387.4
152.5°	398.0	398.3	398.6	398.6	398.3	398.0	397.7	397.4
155°	410.9	411.3	411.7	411.8	411.6	411.3	411.0	410.8
157.5°	422.7	423.3	423.9	424.0	423.5	423.1	422.8	422.3
160°	429.7	430.2	430.8	430.8	430.5	430.2	429.8	429.5
162.5°	436.1	436.7	437.3	437.4	437.0	436.5	436.1	435.8
165°	444.4	445.0	445.6	445.7	445.2	444.8	444.4	443.9
167.5°	451.2	451.8	452.4	452.5	451.9	451.5	451.1	450.6
170°	454.9	455.5	456.1	456.2	455.6	455.1	454.6	454.1
172.5°	457.7	458.3	458.9	458.9	458.4	457.9	457.4	456.8
175°	460.7	461.3	461.9	462.0	461.5	461.0	460.5	459.9
177.5°	462.2	462.5	463.0	463.0	462.5	462.2	461.8	461.3
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3

(END OF REPORT)