

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331595-935

Luminaire Tested: **S122DIW-S1005D710U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331595-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D710U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5934.5 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331595-935

CATALOG NUMBER: S122DIW-S1005D710U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331595-935

CATALOG NUMBER: S122DIW-S1005D710U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54	50
2	91	83	77	72	84	78	72	68	68	64	60	59	55	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39	35
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	36	34	30
5	70	58	50	44	65	54	47	41	48	42	37	42	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22157	22157	22157
5°	22242	21921	22049
10°	22109	21697	21807
15°	21835	21417	21396
20°	21448	20993	20972
25°	21063	20475	20475
30°	20566	19999	19827
35°	20103	19429	19141
40°	19524	18858	18493
45°	18952	18287	17838
50°	18329	17698	17071
55°	17681	17011	16380
60°	16956	16191	15594
65°	16180	15373	14670
70°	15196	14389	13704
75°	13830	13250	12926
80°	12273	11901	11288
85°	10022	9541	8540



TEST NUMBER: P331595-935

CATALOG NUMBER: S122DIW-S1005D710U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.0	2.2
10°-20°	363.1	6.1
20°-30°	533.7	9.0
30°-40°	619.9	10.4
40°-50°	619.3	10.4
50°-60°	540.0	9.1
60°-70°	399.3	6.7
70°-80°	226.2	3.8
80°-90°	62.9	1.1
90°-100°	27.8	0.5
100°-110°	101.9	1.7
110°-120°	272.4	4.6
120°-130°	449.6	7.6
130°-140°	478.2	8.1
140°-150°	444.4	7.5
150°-160°	357.3	6.0
160°-170°	230.3	3.9
170°-180°	79.3	1.3
0°-30°	1025.8	17.3
0°-40°	1645.7	27.7
0°-60°	2805.0	47.3
0°-90°	3493.4	58.9
90°-120°	402.1	6.8
90°-150°	1774.3	29.9
90°-180°	2441.0	41.1
0°-180°	5934.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1372	1366	1352	1362	1360	130
15°	1306	1298	1281	1286	1280	368
25°	1182	1171	1149	1152	1149	544
35°	1020	1006	986	978	971	637
45°	830	820	801	787	781	640
55°	628	620	604	589	582	561
65°	424	415	402	391	384	419
75°	222	219	212	205	207	237
85°	54	53	52	48	46	62
90°	1	7	12	15	16	4
95°	39	21	24	26	26	48
105°	183	191	37	43	46	196
115°	347	357	372	106	49	341
125°	490	498	509	513	515	437
135°	606	616	622	627	626	468
145°	703	703	713	717	714	440
155°	775	770	776	779	775	357
165°	816	813	814	818	814	230
175°	835	831	832	835	830	79
180°	833	833	833	833	833	



TEST NUMBER: P331595-935

CATALOG NUMBER: S122DIW-S1005D710U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3
2.5°	1378.6	1377.4	1376.3	1375.1	1373.9	1372.1	1369.5	1366.9	1364.3	1361.8	1364.1
5°	1372.3	1371.1	1369.9	1368.7	1367.6	1365.4	1362.2	1358.9	1355.7	1352.5	1354.9
7.5°	1360.1	1358.3	1356.5	1354.7	1352.9	1350.3	1347.0	1343.8	1340.5	1337.2	1339.5
10°	1348.5	1346.5	1344.5	1342.4	1340.3	1337.6	1334.0	1330.5	1327.0	1323.4	1325.9
12.5°	1332.7	1330.8	1329.0	1327.2	1325.4	1322.8	1319.2	1315.7	1312.3	1308.7	1310.4
15°	1306.3	1304.6	1302.8	1301.1	1299.2	1296.5	1292.7	1288.8	1285.0	1281.3	1282.5
17.5°	1272.6	1270.7	1269.0	1267.2	1265.5	1262.7	1258.8	1254.9	1251.0	1247.2	1248.5
20°	1248.3	1246.5	1244.7	1242.9	1241.2	1238.3	1234.2	1230.1	1226.0	1221.8	1222.7
22.5°	1224.0	1221.5	1219.1	1216.6	1214.1	1211.0	1207.1	1203.2	1199.4	1195.5	1195.7
25°	1182.3	1179.9	1177.6	1175.3	1172.9	1169.2	1164.2	1159.3	1154.3	1149.3	1149.9
27.5°	1134.8	1132.6	1130.6	1128.4	1126.4	1123.3	1119.4	1115.4	1111.6	1107.6	1106.7
30°	1103.1	1100.8	1098.4	1096.1	1093.7	1090.4	1086.0	1081.6	1077.2	1072.7	1071.9
32.5°	1069.4	1067.5	1065.6	1063.7	1061.8	1058.6	1054.0	1049.3	1044.7	1040.0	1038.5
35°	1019.9	1017.0	1014.1	1011.2	1008.2	1004.4	999.7	995.1	990.4	985.7	984.0
37.5°	964.3	961.7	959.2	956.6	954.0	950.4	945.6	941.0	936.3	931.6	929.4
40°	926.3	923.9	921.6	919.3	916.9	913.4	908.7	904.0	899.3	894.7	892.0
42.5°	889.3	887.0	884.7	882.4	879.9	876.4	871.8	867.0	862.4	857.6	854.8
45°	830.0	827.9	825.9	823.8	821.7	818.6	814.2	809.8	805.4	800.9	797.7
47.5°	770.9	769.0	767.0	765.1	763.1	759.8	755.3	750.7	746.1	741.6	738.1
50°	729.7	728.2	726.8	725.3	723.8	721.0	717.0	712.8	708.7	704.6	700.5
52.5°	689.6	687.7	685.7	683.8	681.8	678.9	675.0	671.1	667.4	663.5	660.0
55°	628.1	626.3	624.6	622.8	621.0	618.4	614.9	611.4	607.9	604.3	600.8
57.5°	566.4	564.9	563.5	562.1	560.7	558.1	554.2	550.4	546.5	542.6	539.2
60°	525.1	524.0	522.8	521.7	520.5	517.8	513.8	509.6	505.5	501.4	498.2
62.5°	485.1	483.2	481.3	479.4	477.5	475.0	471.8	468.7	465.5	462.4	459.3
65°	423.5	421.8	420.1	418.3	416.6	414.1	411.2	408.3	405.4	402.4	399.8
67.5°	361.0	359.6	358.2	356.8	355.4	353.4	350.7	348.1	345.4	342.9	340.8
70°	321.9	320.8	319.6	318.5	317.3	315.4	312.7	310.0	307.5	304.8	302.7
72.5°	281.8	280.7	279.5	278.4	277.2	275.7	274.1	272.3	270.6	268.9	266.8
75°	221.7	221.1	220.5	219.9	219.3	218.3	216.8	215.3	213.9	212.4	210.7
77.5°	167.8	166.9	165.8	164.9	163.8	163.1	162.5	161.9	161.3	160.7	159.8
80°	132.0	131.6	131.4	131.0	130.8	130.4	129.8	129.2	128.5	128.0	127.1
82.5°	98.2	98.2	98.1	98.0	97.9	97.7	97.4	97.0	96.7	96.3	95.2
85°	54.1	53.8	53.6	53.2	53.0	52.6	52.3	52.0	51.7	51.5	50.5
87.5°	19.1	18.9	18.8	18.6	18.4	18.2	18.0	17.7	17.5	17.2	16.6
90°	0.6	2.1	3.5	5.0	6.5	7.7	8.9	9.9	11.0	12.1	12.7
92.5°	12.1	12.1	11.9	11.8	11.6	11.9	12.4	12.9	13.4	13.9	14.3
95°	39.2	34.8	30.3	25.9	21.5	19.7	20.7	21.6	22.6	23.5	24.2
97.5°	77.7	65.3	52.9	40.4	27.9	22.8	25.0	27.1	29.3	31.4	32.0
100°	106.7	88.3	70.0	51.7	33.3	25.2	27.6	29.8	32.1	34.4	35.4
102.5°	138.5	134.7	130.7	126.8	123.0	111.5	92.5	73.4	54.3	35.3	36.7
105°	183.2	187.3	191.3	195.3	199.3	183.0	146.5	109.9	73.4	36.8	38.2
107.5°	234.2	237.5	240.7	243.9	247.2	226.9	183.0	139.2	95.3	51.5	49.9
110°	267.0	269.8	272.7	275.4	278.3	260.3	221.6	182.9	144.2	105.5	92.1



TEST NUMBER: P331595-935

CATALOG NUMBER: S122DIW-S1005D710U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	297.9	300.4	302.9	305.3	307.8	304.3	294.7	285.2	275.6	266.0	217.2
115°	346.6	348.9	351.1	353.4	355.7	358.5	361.9	365.2	368.5	371.9	309.9
117.5°	390.1	392.6	395.2	397.7	400.3	402.7	405.0	407.3	409.6	411.9	396.9
120°	421.9	424.0	425.9	427.9	430.0	432.1	434.5	437.0	439.4	441.8	443.4
122.5°	448.9	451.1	453.1	455.3	457.4	459.8	462.4	465.0	467.6	470.3	471.2
125°	490.0	491.8	493.5	495.2	497.0	499.1	501.7	504.2	506.8	509.3	510.2
127.5°	527.3	529.2	531.2	533.0	535.0	536.9	538.8	540.7	542.6	544.5	545.9
130°	550.9	553.0	555.2	557.3	559.5	561.3	562.7	564.2	565.7	567.2	568.7
132.5°	575.1	576.9	578.7	580.5	582.3	583.9	585.4	586.9	588.4	589.9	591.1
135°	606.4	608.5	610.6	612.8	614.9	616.6	617.9	619.1	620.3	621.5	622.8
137.5°	638.1	639.6	641.1	642.6	644.0	645.5	646.9	648.2	649.6	651.0	652.3
140°	658.8	659.9	660.9	662.0	663.1	664.3	665.8	667.3	668.7	670.3	671.5
142.5°	676.1	677.1	678.1	679.1	680.0	681.3	683.0	684.8	686.4	688.1	689.2
145°	703.4	703.3	703.2	703.0	702.8	704.0	706.2	708.5	710.8	713.1	714.0
147.5°	727.1	726.7	726.2	725.7	725.1	726.0	728.2	730.5	732.7	734.9	735.7
150°	742.6	741.7	740.7	739.8	738.8	739.4	741.6	743.7	745.9	748.0	748.8
152.5°	755.6	754.6	753.5	752.4	751.4	751.9	754.0	756.0	758.0	760.1	760.9
155°	774.6	773.4	772.1	770.9	769.7	769.9	771.5	773.1	774.7	776.4	777.1
157.5°	789.4	788.3	787.3	786.3	785.3	785.3	786.4	787.6	788.7	789.8	790.7
160°	798.1	797.2	796.4	795.7	794.8	794.8	795.7	796.4	797.2	798.1	798.8
162.5°	805.7	804.9	804.2	803.3	802.5	802.5	803.1	803.9	804.6	805.3	806.2
165°	816.1	815.3	814.5	813.7	812.9	812.7	813.1	813.5	813.9	814.3	815.3
167.5°	823.8	823.0	822.3	821.4	820.6	820.4	820.8	821.1	821.6	821.9	822.9
170°	828.2	827.3	826.6	825.8	824.9	824.7	824.9	825.3	825.5	825.8	826.7
172.5°	831.0	830.3	829.5	828.6	827.9	827.6	827.9	828.1	828.4	828.6	829.6
175°	834.8	833.9	832.9	832.0	831.0	830.7	831.0	831.3	831.6	831.8	832.8
177.5°	835.4	834.7	833.9	833.2	832.4	832.1	832.2	832.3	832.4	832.5	833.3
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331595-935

CATALOG NUMBER: S122DIW-S1005D710U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3
2.5°	1366.4	1368.7	1371.1	1372.1	1371.6	1371.1	1370.6	1370.2
5°	1357.2	1359.5	1361.8	1362.8	1362.2	1361.6	1361.0	1360.4
7.5°	1341.9	1344.2	1346.6	1347.5	1346.8	1346.2	1345.5	1344.9
10°	1328.2	1330.5	1332.8	1333.6	1332.7	1331.8	1330.9	1330.1
12.5°	1312.0	1313.6	1315.3	1315.8	1315.1	1314.5	1313.8	1313.2
15°	1283.6	1284.8	1285.9	1285.8	1284.4	1282.9	1281.4	1280.0
17.5°	1249.9	1251.3	1252.6	1252.6	1251.1	1249.7	1248.4	1246.9
20°	1223.7	1224.5	1225.4	1225.2	1224.1	1222.9	1221.8	1220.6
22.5°	1195.8	1196.0	1196.2	1195.9	1195.2	1194.6	1193.8	1193.1
25°	1150.5	1151.1	1151.7	1151.7	1151.1	1150.5	1149.9	1149.3
27.5°	1105.9	1104.9	1104.1	1102.9	1101.6	1100.1	1098.7	1097.3
30°	1071.0	1070.1	1069.3	1068.2	1067.0	1065.8	1064.7	1063.5
32.5°	1036.9	1035.3	1033.7	1032.3	1031.1	1030.0	1028.8	1027.6
35°	982.1	980.4	978.6	977.1	975.6	974.1	972.6	971.1
37.5°	927.2	925.1	922.9	921.1	919.7	918.3	916.9	915.5
40°	889.3	886.7	884.1	882.2	881.0	879.9	878.7	877.4
42.5°	852.0	849.0	846.2	844.0	842.3	840.7	839.0	837.3
45°	794.5	791.3	788.1	785.8	784.6	783.5	782.3	781.2
47.5°	734.8	731.3	728.0	725.4	723.7	722.0	720.3	718.6
50°	696.4	692.3	688.2	685.4	684.0	682.5	681.1	679.6
52.5°	656.7	653.2	649.9	647.2	645.2	643.3	641.4	639.5
55°	597.3	593.7	590.3	587.8	586.3	584.9	583.4	581.9
57.5°	535.6	532.2	528.7	526.4	525.4	524.3	523.1	522.0
60°	495.0	491.7	488.5	486.5	485.6	484.7	483.8	482.9
62.5°	456.4	453.4	450.4	448.3	447.2	446.1	445.0	443.8
65°	397.2	394.5	391.9	389.9	388.4	386.9	385.5	384.0
67.5°	338.7	336.7	334.6	332.9	331.8	330.6	329.5	328.3
70°	300.7	298.7	296.6	295.0	293.8	292.7	291.4	290.3
72.5°	264.8	262.8	260.7	259.2	258.3	257.4	256.4	255.5
75°	209.0	207.2	205.4	204.8	205.4	206.0	206.6	207.2
77.5°	158.9	158.1	157.2	156.4	155.5	154.7	153.9	153.1
80°	126.2	125.4	124.5	123.7	123.1	122.6	122.0	121.4
82.5°	94.1	93.0	91.9	91.3	91.1	91.0	90.9	90.7
85°	49.7	48.8	48.0	47.4	47.1	46.8	46.5	46.1
87.5°	16.0	15.5	14.9	14.6	14.4	14.2	14.0	13.8
90°	13.4	14.0	14.7	15.2	15.5	15.8	16.0	16.3
92.5°	14.7	15.1	15.4	15.7	15.8	15.9	16.1	16.3
95°	24.9	25.5	26.2	26.4	26.3	26.2	26.1	25.9
97.5°	32.5	33.1	33.6	33.9	34.1	34.3	34.4	34.6
100°	36.5	37.5	38.7	39.3	39.6	39.9	40.1	40.4
102.5°	38.1	39.5	40.9	41.8	42.2	42.5	42.9	43.3
105°	39.7	41.2	42.6	43.7	44.2	44.8	45.3	45.8
107.5°	48.5	47.0	45.5	45.0	45.5	46.1	46.6	47.1
110°	78.7	65.3	51.9	45.5	46.0	46.6	47.1	47.6



TEST NUMBER: P331595-935

CATALOG NUMBER: S122DIW-S1005D710U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	168.3	119.5	70.6	46.4	46.8	47.3	47.7	48.1
115°	247.9	185.8	123.8	88.0	78.4	68.7	59.1	49.4
117.5°	381.9	366.9	351.9	328.6	296.9	265.2	233.5	201.8
120°	445.1	446.6	448.2	440.0	421.9	403.8	385.7	367.6
122.5°	472.2	473.1	474.2	472.9	469.3	465.8	462.4	458.8
125°	511.2	512.1	513.1	513.8	514.1	514.5	515.0	515.3
127.5°	547.3	548.6	550.0	550.7	550.8	550.9	551.0	551.0
130°	570.2	571.6	573.1	573.8	573.6	573.5	573.3	573.3
132.5°	592.4	593.7	594.9	595.5	595.3	595.2	595.0	595.0
135°	624.1	625.4	626.8	627.3	627.1	626.8	626.5	626.3
137.5°	653.6	654.9	656.3	656.7	656.2	655.7	655.3	654.8
140°	672.7	673.9	675.1	675.4	674.7	674.0	673.3	672.7
142.5°	690.3	691.4	692.5	692.7	692.1	691.4	690.7	690.0
145°	714.9	715.8	716.8	717.0	716.3	715.6	714.9	714.3
147.5°	736.4	737.1	737.8	737.9	737.3	736.8	736.2	735.6
150°	749.6	750.4	751.2	751.3	750.6	749.9	749.2	748.6
152.5°	761.6	762.5	763.3	763.3	762.3	761.5	760.6	759.7
155°	777.9	778.8	779.5	779.4	778.3	777.3	776.2	775.2
157.5°	791.7	792.6	793.5	793.4	792.4	791.3	790.3	789.2
160°	799.6	800.5	801.2	801.2	800.2	799.3	798.4	797.5
162.5°	807.1	808.0	808.9	808.8	807.6	806.5	805.3	804.2
165°	816.2	817.1	818.0	818.0	817.1	816.2	815.3	814.3
167.5°	823.8	824.8	825.6	825.5	824.3	823.1	821.9	820.7
170°	827.7	828.5	829.5	829.4	828.2	827.0	825.8	824.6
172.5°	830.5	831.5	832.4	832.2	831.0	829.8	828.6	827.4
175°	833.7	834.6	835.5	835.3	834.0	832.7	831.3	830.0
177.5°	834.1	834.7	835.5	835.4	834.5	833.4	832.5	831.6
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0

(END OF REPORT)