

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331577-940

Luminaire Tested: **S122DIW-S865D1240U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331577-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D1240U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7552.2 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331577-940

CATALOG NUMBER: S122DIW-S865D1240U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331577-940

CATALOG NUMBER: S122DIW-S865D1240U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	84	87	84	80	77	69	67	64	55	54	52	43	42	41	35
2	87	80	74	69	79	73	68	64	60	57	53	48	46	44	38	36	34	29
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25	21
5	67	55	47	41	61	51	44	39	42	37	33	34	30	27	27	24	22	18
6	61	50	42	36	56	46	39	33	38	33	29	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19869	19869	19869
5°	19945	19656	19772
10°	19825	19457	19556
15°	19580	19206	19184
20°	19234	18826	18806
25°	18887	18360	18360
30°	18442	17935	17780
35°	18027	17422	17164
40°	17506	16910	16583
45°	16993	16401	15995
50°	16435	15872	15307
55°	15854	15254	14688
60°	15206	14518	13986
65°	14514	13788	13154
70°	13629	12902	12288
75°	12402	11884	11584
80°	11000	10674	10126
85°	8985	8559	7669



TEST NUMBER: P331577-940

CATALOG NUMBER: S122DIW-S865D1240U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.7	1.5
10°-20°	325.6	4.3
20°-30°	478.6	6.3
30°-40°	555.9	7.4
40°-50°	555.3	7.4
50°-60°	484.3	6.4
60°-70°	358.1	4.7
70°-80°	202.8	2.7
80°-90°	58.2	0.8
90°-100°	50.3	0.7
100°-110°	184.4	2.4
110°-120°	492.9	6.5
120°-130°	813.7	10.8
130°-140°	865.3	11.5
140°-150°	804.3	10.6
150°-160°	646.7	8.6
160°-170°	416.7	5.5
170°-180°	143.4	1.9
0°-30°	919.9	12.2
0°-40°	1475.8	19.5
0°-60°	2515.4	33.3
0°-90°	3134.5	41.5
90°-120°	727.6	9.6
90°-150°	3210.9	42.5
90°-180°	4418.0	58.5
0°-180°	7552.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1231	1231	1231	1231	1231	
5°	1231	1225	1213	1222	1220	117
15°	1171	1164	1149	1153	1148	330
25°	1060	1050	1031	1033	1031	488
35°	915	902	884	877	871	571
45°	744	735	718	706	700	574
55°	563	556	542	528	522	503
65°	380	372	361	350	344	376
75°	199	196	190	184	186	212
85°	48	47	46	43	41	56
90°	1	13	22	27	29	6
95°	71	37	42	48	47	87
105°	332	346	66	78	83	354
115°	627	646	673	192	89	617
125°	887	901	922	929	933	790
135°	1097	1114	1125	1135	1133	847
145°	1273	1273	1290	1297	1293	796
155°	1402	1393	1405	1411	1403	646
165°	1477	1471	1474	1480	1474	417
175°	1511	1504	1505	1512	1502	144
180°	1507	1507	1507	1507	1507	



TEST NUMBER: P331577-940

CATALOG NUMBER: S122DIW-S865D1240U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1236.3	1235.2	1234.1	1233.1	1232.1	1230.4	1228.1	1225.7	1223.4	1221.1	1223.2
5°	1230.6	1229.5	1228.5	1227.4	1226.4	1224.4	1221.6	1218.6	1215.8	1212.8	1215.0
7.5°	1219.7	1218.1	1216.5	1214.8	1213.2	1210.9	1207.9	1205.0	1202.0	1199.1	1201.2
10°	1209.2	1207.5	1205.6	1203.7	1201.9	1199.4	1196.2	1193.1	1190.0	1186.8	1188.9
12.5°	1195.1	1193.5	1191.9	1190.2	1188.6	1186.2	1183.0	1179.8	1176.7	1173.6	1175.0
15°	1171.4	1169.8	1168.2	1166.7	1165.1	1162.6	1159.2	1155.7	1152.4	1149.0	1150.0
17.5°	1141.1	1139.5	1138.0	1136.4	1134.8	1132.3	1128.8	1125.3	1121.9	1118.4	1119.6
20°	1119.4	1117.8	1116.2	1114.6	1113.0	1110.4	1106.7	1103.0	1099.4	1095.7	1096.4
22.5°	1097.6	1095.4	1093.1	1090.9	1088.8	1085.9	1082.4	1079.0	1075.5	1072.0	1072.2
25°	1060.2	1058.1	1056.0	1053.9	1051.8	1048.5	1044.0	1039.6	1035.1	1030.6	1031.2
27.5°	1017.6	1015.7	1013.8	1011.9	1010.0	1007.3	1003.8	1000.2	996.8	993.2	992.5
30°	989.2	987.1	985.0	982.9	980.8	977.8	973.8	969.9	965.9	962.0	961.2
32.5°	958.9	957.3	955.6	953.9	952.2	949.2	945.1	940.9	936.8	932.6	931.2
35°	914.6	912.0	909.4	906.8	904.1	900.7	896.5	892.3	888.1	883.9	882.3
37.5°	864.7	862.4	860.1	857.7	855.5	852.2	848.0	843.8	839.5	835.4	833.4
40°	830.6	828.6	826.4	824.3	822.2	819.0	814.8	810.7	806.5	802.3	799.9
42.5°	797.5	795.4	793.3	791.2	789.1	786.0	781.8	777.6	773.3	769.1	766.5
45°	744.2	742.4	740.6	738.8	736.9	734.0	730.0	726.1	722.2	718.3	715.3
47.5°	691.3	689.6	687.8	686.1	684.3	681.4	677.3	673.2	669.1	664.9	661.9
50°	654.3	653.0	651.8	650.4	649.1	646.6	642.9	639.2	635.5	631.9	628.2
52.5°	618.4	616.6	614.9	613.1	611.4	608.9	605.4	601.9	598.4	594.9	591.9
55°	563.2	561.7	560.1	558.5	556.9	554.6	551.4	548.2	545.1	541.9	538.8
57.5°	507.8	506.6	505.3	504.1	502.8	500.4	497.0	493.5	490.0	486.5	483.5
60°	470.9	469.8	468.9	467.8	466.7	464.4	460.7	457.0	453.3	449.6	446.7
62.5°	435.0	433.3	431.6	429.9	428.2	426.0	423.1	420.3	417.4	414.6	412.0
65°	379.9	378.3	376.7	375.1	373.5	371.4	368.8	366.1	363.6	360.9	358.6
67.5°	323.8	322.4	321.2	319.9	318.7	316.9	314.5	312.1	309.8	307.4	305.6
70°	288.7	287.7	286.6	285.5	284.5	282.8	280.4	278.0	275.7	273.3	271.5
72.5°	252.7	251.7	250.7	249.6	248.5	247.3	245.8	244.2	242.6	241.1	239.3
75°	198.8	198.2	197.7	197.2	196.7	195.7	194.5	193.1	191.8	190.5	189.0
77.5°	150.5	149.6	148.7	147.8	147.0	146.2	145.7	145.2	144.6	144.1	143.3
80°	118.3	118.1	117.8	117.5	117.3	116.9	116.4	115.8	115.3	114.8	114.0
82.5°	88.0	88.0	87.9	87.8	87.8	87.7	87.3	87.0	86.7	86.4	85.3
85°	48.5	48.2	48.0	47.7	47.4	47.2	46.9	46.6	46.4	46.2	45.4
87.5°	17.3	17.4	17.5	17.6	17.7	17.7	17.7	17.7	17.7	17.7	17.2
90°	1.1	3.7	6.4	9.1	11.8	14.1	16.0	17.9	19.9	21.8	23.0
92.5°	22.0	21.8	21.6	21.3	21.0	21.4	22.4	23.4	24.3	25.3	25.9
95°	70.9	62.9	54.9	46.9	38.9	35.8	37.5	39.1	40.8	42.5	43.8
97.5°	140.7	118.2	95.6	73.1	50.6	41.2	45.1	49.0	53.1	57.0	57.9
100°	193.1	159.9	126.6	93.5	60.3	45.7	49.8	53.9	58.1	62.2	64.1
102.5°	250.7	243.6	236.6	229.6	222.6	201.8	167.3	132.9	98.4	63.9	66.4
105°	331.6	338.9	346.2	353.4	360.7	331.3	265.1	198.9	132.7	66.5	69.2
107.5°	423.9	429.7	435.6	441.5	447.4	410.6	331.3	251.9	172.5	93.2	90.4
110°	483.2	488.3	493.4	498.5	503.5	471.1	401.1	331.0	260.9	190.9	166.7



TEST NUMBER: P331577-940

CATALOG NUMBER: S122DIW-S865D1240U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	539.0	543.6	548.0	552.6	557.1	550.7	533.4	516.1	498.8	481.4	393.1
115°	627.2	631.3	635.4	639.5	643.7	648.8	654.9	660.9	667.0	673.1	560.8
117.5°	706.0	710.6	715.2	719.8	724.4	728.8	732.9	737.1	741.3	745.5	718.3
120°	763.6	767.2	770.8	774.5	778.1	782.1	786.5	790.9	795.2	799.5	802.5
122.5°	812.4	816.3	820.1	823.9	827.8	832.1	836.8	841.5	846.3	851.0	852.7
125°	886.8	889.9	893.1	896.3	899.4	903.3	907.9	912.5	917.1	921.8	923.5
127.5°	954.2	957.7	961.2	964.7	968.2	971.7	975.1	978.6	982.0	985.4	987.9
130°	997.0	1000.9	1004.8	1008.6	1012.5	1015.7	1018.4	1021.1	1023.8	1026.4	1029.1
132.5°	1040.6	1043.9	1047.2	1050.5	1053.8	1056.8	1059.4	1062.1	1064.8	1067.5	1069.7
135°	1097.3	1101.2	1105.1	1108.9	1112.9	1115.9	1118.0	1120.3	1122.4	1124.6	1127.0
137.5°	1154.7	1157.4	1160.1	1162.9	1165.6	1168.1	1170.6	1173.1	1175.5	1178.0	1180.4
140°	1192.2	1194.2	1196.1	1198.0	1200.0	1202.3	1205.0	1207.6	1210.3	1213.0	1215.1
142.5°	1223.7	1225.4	1227.2	1228.9	1230.7	1233.1	1236.1	1239.1	1242.2	1245.3	1247.2
145°	1272.9	1272.7	1272.5	1272.2	1272.0	1273.9	1278.1	1282.2	1286.3	1290.4	1292.1
147.5°	1315.9	1315.0	1314.1	1313.1	1312.2	1313.8	1317.9	1322.0	1326.1	1330.1	1331.4
150°	1343.9	1342.2	1340.5	1338.7	1337.0	1338.2	1342.0	1345.9	1349.8	1353.7	1355.1
152.5°	1367.4	1365.6	1363.6	1361.7	1359.9	1360.8	1364.4	1368.2	1371.8	1375.5	1377.0
155°	1401.7	1399.5	1397.3	1395.1	1392.9	1393.3	1396.2	1399.1	1402.0	1405.0	1406.4
157.5°	1428.5	1426.6	1424.8	1423.0	1421.1	1421.2	1423.3	1425.3	1427.4	1429.4	1431.0
160°	1444.2	1442.8	1441.3	1439.8	1438.4	1438.4	1439.8	1441.3	1442.8	1444.2	1445.6
162.5°	1458.2	1456.7	1455.3	1453.8	1452.3	1452.2	1453.5	1454.7	1456.1	1457.3	1458.9
165°	1476.9	1475.5	1474.0	1472.6	1471.1	1470.8	1471.5	1472.2	1472.9	1473.6	1475.3
167.5°	1490.9	1489.4	1488.0	1486.6	1485.1	1484.7	1485.4	1486.0	1486.7	1487.4	1489.1
170°	1498.8	1497.3	1495.8	1494.4	1492.9	1492.5	1492.9	1493.4	1493.9	1494.4	1496.1
172.5°	1504.0	1502.5	1501.1	1499.6	1498.2	1497.7	1498.2	1498.6	1499.1	1499.6	1501.3
175°	1510.7	1509.0	1507.3	1505.7	1504.0	1503.3	1503.9	1504.3	1504.9	1505.3	1507.0
177.5°	1511.8	1510.5	1509.1	1507.8	1506.4	1505.8	1506.0	1506.2	1506.4	1506.6	1508.0
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331577-940

CATALOG NUMBER: S122DIW-S865D1240U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1225.3	1227.4	1229.5	1230.4	1229.9	1229.5	1229.1	1228.7
5°	1217.0	1219.1	1221.3	1222.0	1221.6	1221.0	1220.5	1219.9
7.5°	1203.3	1205.4	1207.6	1208.3	1207.7	1207.1	1206.6	1205.9
10°	1191.0	1193.1	1195.2	1195.9	1195.1	1194.3	1193.5	1192.8
12.5°	1176.5	1177.9	1179.5	1179.9	1179.3	1178.8	1178.1	1177.6
15°	1151.0	1152.1	1153.2	1153.0	1151.7	1150.4	1149.1	1147.7
17.5°	1120.8	1122.0	1123.3	1123.2	1122.0	1120.7	1119.5	1118.2
20°	1097.3	1098.1	1098.9	1098.7	1097.7	1096.6	1095.6	1094.5
22.5°	1072.4	1072.5	1072.6	1072.5	1071.7	1071.1	1070.5	1069.9
25°	1031.7	1032.2	1032.7	1032.7	1032.2	1031.7	1031.2	1030.6
27.5°	991.7	990.9	990.1	989.1	987.7	986.5	985.3	984.0
30°	960.4	959.7	958.9	957.9	956.9	955.8	954.8	953.7
32.5°	929.8	928.4	926.9	925.7	924.7	923.6	922.6	921.5
35°	880.7	879.1	877.6	876.1	874.9	873.5	872.2	870.8
37.5°	831.5	829.6	827.6	826.0	824.7	823.5	822.2	820.9
40°	797.5	795.1	792.8	791.0	790.1	789.0	787.9	786.8
42.5°	763.9	761.3	758.8	756.8	755.3	753.9	752.3	750.9
45°	712.5	709.5	706.7	704.7	703.6	702.6	701.5	700.5
47.5°	658.9	655.9	652.8	650.5	649.0	647.5	646.0	644.4
50°	624.5	620.8	617.2	614.7	613.3	612.0	610.7	609.4
52.5°	588.8	585.8	582.7	580.3	578.6	576.8	575.2	573.4
55°	535.7	532.4	529.3	527.1	525.8	524.4	523.2	521.8
57.5°	480.4	477.2	474.1	472.1	471.1	470.1	469.1	468.1
60°	443.9	441.0	438.1	436.2	435.4	434.6	433.8	433.1
62.5°	409.2	406.5	403.9	402.1	401.0	400.0	399.0	398.1
65°	356.1	353.8	351.4	349.6	348.3	347.0	345.6	344.3
67.5°	303.7	301.8	300.1	298.6	297.6	296.5	295.4	294.4
70°	269.7	267.8	266.0	264.5	263.5	262.4	261.4	260.3
72.5°	237.5	235.6	233.8	232.5	231.6	230.8	229.9	229.1
75°	187.3	185.7	184.2	183.7	184.2	184.8	185.2	185.7
77.5°	142.6	141.8	141.0	140.2	139.5	138.8	138.0	137.2
80°	113.2	112.4	111.6	110.9	110.4	109.9	109.4	108.9
82.5°	84.4	83.4	82.4	81.9	81.7	81.6	81.5	81.4
85°	44.6	43.8	43.0	42.4	42.2	41.9	41.6	41.4
87.5°	16.9	16.4	16.1	15.8	15.7	15.6	15.4	15.3
90°	24.3	25.4	26.7	27.6	28.0	28.4	29.0	29.4
92.5°	26.6	27.2	27.8	28.3	28.5	28.9	29.2	29.4
95°	44.9	46.2	47.3	47.9	47.6	47.3	47.2	46.9
97.5°	58.9	59.8	60.8	61.4	61.7	62.1	62.3	62.6
100°	66.1	67.9	69.9	71.2	71.6	72.1	72.6	73.1
102.5°	68.9	71.5	74.0	75.6	76.2	77.0	77.7	78.3
105°	71.9	74.5	77.2	79.0	80.0	81.0	81.9	82.9
107.5°	87.7	85.0	82.3	81.4	82.4	83.4	84.4	85.3
110°	142.4	118.2	93.9	82.3	83.3	84.3	85.2	86.1



TEST NUMBER: P331577-940

CATALOG NUMBER: S122DIW-S865D1240U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	304.6	216.2	127.8	83.9	84.7	85.5	86.2	87.0
115°	448.5	336.4	224.1	159.3	141.8	124.4	106.9	89.4
117.5°	691.2	664.0	636.9	594.6	537.3	479.9	422.6	365.2
120°	805.4	808.2	811.2	796.3	763.6	730.8	698.1	665.4
122.5°	854.5	856.3	858.0	855.7	849.4	843.0	836.7	830.3
125°	925.1	926.8	928.5	929.7	930.4	931.2	931.9	932.6
127.5°	990.3	992.8	995.3	996.7	996.8	996.9	997.0	997.2
130°	1031.8	1034.5	1037.1	1038.3	1038.0	1037.9	1037.6	1037.3
132.5°	1072.0	1074.2	1076.6	1077.5	1077.4	1077.1	1076.8	1076.7
135°	1129.4	1131.8	1134.3	1135.2	1134.8	1134.3	1133.8	1133.4
137.5°	1182.8	1185.2	1187.6	1188.3	1187.5	1186.7	1185.9	1185.0
140°	1217.4	1219.5	1221.7	1222.2	1220.9	1219.8	1218.5	1217.4
142.5°	1249.2	1251.2	1253.2	1253.6	1252.4	1251.2	1249.9	1248.8
145°	1293.8	1295.5	1297.2	1297.4	1296.2	1295.0	1293.8	1292.6
147.5°	1332.7	1333.9	1335.2	1335.2	1334.3	1333.2	1332.2	1331.2
150°	1356.6	1358.1	1359.5	1359.6	1358.4	1357.2	1355.9	1354.8
152.5°	1378.4	1379.8	1381.3	1381.3	1379.7	1378.0	1376.4	1374.8
155°	1407.8	1409.3	1410.8	1410.5	1408.5	1406.7	1404.7	1402.8
157.5°	1432.7	1434.3	1436.0	1435.8	1434.0	1432.1	1430.2	1428.3
160°	1447.2	1448.6	1450.0	1449.9	1448.2	1446.5	1444.8	1443.1
162.5°	1460.6	1462.2	1463.9	1463.7	1461.6	1459.5	1457.4	1455.4
165°	1477.0	1478.7	1480.4	1480.4	1478.7	1477.0	1475.3	1473.6
167.5°	1490.8	1492.5	1494.2	1494.0	1491.7	1489.6	1487.4	1485.2
170°	1497.8	1499.5	1501.2	1500.9	1498.8	1496.6	1494.4	1492.2
172.5°	1503.0	1504.7	1506.4	1506.2	1504.0	1501.8	1499.6	1497.4
175°	1508.7	1510.4	1512.1	1511.7	1509.3	1506.9	1504.4	1502.0
177.5°	1509.3	1510.6	1512.1	1511.8	1510.1	1508.3	1506.6	1504.9
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4

(END OF REPORT)