

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331596-935

Luminaire Tested: **S122DIW-S1005D710U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331596-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D710U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5611.3 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331596-935

CATALOG NUMBER: S122DIW-S1005D710U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331596-935

CATALOG NUMBER: S122DIW-S1005D710U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57	52
2	92	84	78	72	86	79	73	69	69	65	61	61	57	55	52	50	48	44
3	84	74	66	60	78	69	63	57	61	56	52	54	50	46	46	43	41	37
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	37	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	24
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	32	28	24	29	25	22	19
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	26	22	20	17
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22157	22157	22157
5°	22242	21921	22049
10°	22109	21697	21807
15°	21835	21417	21396
20°	21448	20993	20972
25°	21063	20475	20475
30°	20566	19999	19827
35°	20103	19429	19141
40°	19524	18858	18493
45°	18952	18287	17838
50°	18329	17698	17071
55°	17681	17011	16380
60°	16956	16191	15594
65°	16180	15373	14670
70°	15196	14389	13704
75°	13830	13250	12926
80°	12273	11901	11288
85°	10022	9541	8540



TEST NUMBER: P331596-935

CATALOG NUMBER: S122DIW-S1005D710U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.0	2.3
10°-20°	363.1	6.5
20°-30°	533.7	9.5
30°-40°	619.9	11.0
40°-50°	619.3	11.0
50°-60°	540.0	9.6
60°-70°	399.3	7.1
70°-80°	226.2	4.0
80°-90°	63.8	1.1
90°-100°	48.0	0.9
100°-110°	149.0	2.7
110°-120°	254.7	4.5
120°-130°	334.9	6.0
130°-140°	375.9	6.7
140°-150°	368.6	6.6
150°-160°	309.2	5.5
160°-170°	205.1	3.7
170°-180°	71.7	1.3
0°-30°	1025.8	18.3
0°-40°	1645.7	29.3
0°-60°	2805.0	50.0
0°-90°	3494.3	62.3
90°-120°	451.7	8.0
90°-150°	1531.1	27.3
90°-180°	2117.0	37.7
0°-180°	5611.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1372	1366	1352	1362	1360	130
15°	1306	1298	1281	1286	1280	368
25°	1182	1171	1149	1152	1149	544
35°	1020	1006	986	978	971	637
45°	830	820	801	787	781	640
55°	628	620	604	589	582	561
65°	424	415	402	391	384	419
75°	222	219	212	205	207	237
85°	54	53	52	48	46	62
90°	1	9	22	21	22	4
95°	33	39	41	41	40	38
105°	137	139	141	142	142	145
115°	256	259	258	257	256	253
125°	372	377	376	374	373	332
135°	481	488	489	489	487	372
145°	584	588	592	593	590	365
155°	668	670	672	674	673	307
165°	726	726	726	730	727	205
175°	756	754	753	757	753	72
180°	757	757	757	757	757	



TEST NUMBER: P331596-935

CATALOG NUMBER: S122DIW-S1005D710U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3
2.5°	1378.6	1377.4	1376.3	1375.1	1373.9	1372.1	1369.5	1366.9	1364.3	1361.8	1364.1
5°	1372.3	1371.1	1369.9	1368.7	1367.6	1365.4	1362.2	1358.9	1355.7	1352.5	1354.9
7.5°	1360.1	1358.3	1356.5	1354.7	1352.9	1350.3	1347.0	1343.8	1340.5	1337.2	1339.5
10°	1348.5	1346.5	1344.5	1342.4	1340.3	1337.6	1334.0	1330.5	1327.0	1323.4	1325.9
12.5°	1332.7	1330.8	1329.0	1327.2	1325.4	1322.8	1319.2	1315.7	1312.3	1308.7	1310.4
15°	1306.3	1304.6	1302.8	1301.1	1299.2	1296.5	1292.7	1288.8	1285.0	1281.3	1282.5
17.5°	1272.6	1270.7	1269.0	1267.2	1265.5	1262.7	1258.8	1254.9	1251.0	1247.2	1248.5
20°	1248.3	1246.5	1244.7	1242.9	1241.2	1238.3	1234.2	1230.1	1226.0	1221.8	1222.7
22.5°	1224.0	1221.5	1219.1	1216.6	1214.1	1211.0	1207.1	1203.2	1199.4	1195.5	1195.7
25°	1182.3	1179.9	1177.6	1175.3	1172.9	1169.2	1164.2	1159.3	1154.3	1149.3	1149.9
27.5°	1134.8	1132.6	1130.6	1128.4	1126.4	1123.3	1119.4	1115.4	1111.6	1107.6	1106.7
30°	1103.1	1100.8	1098.4	1096.1	1093.7	1090.4	1086.0	1081.6	1077.2	1072.7	1071.9
32.5°	1069.4	1067.5	1065.6	1063.7	1061.8	1058.6	1054.0	1049.3	1044.7	1040.0	1038.5
35°	1019.9	1017.0	1014.1	1011.2	1008.2	1004.4	999.7	995.1	990.4	985.7	984.0
37.5°	964.3	961.7	959.2	956.6	954.0	950.4	945.6	941.0	936.3	931.6	929.4
40°	926.3	923.9	921.6	919.3	916.9	913.4	908.7	904.0	899.3	894.7	892.0
42.5°	889.3	887.0	884.7	882.4	879.9	876.4	871.8	867.0	862.4	857.6	854.8
45°	830.0	827.9	825.9	823.8	821.7	818.6	814.2	809.8	805.4	800.9	797.7
47.5°	770.9	769.0	767.0	765.1	763.1	759.8	755.3	750.7	746.1	741.6	738.1
50°	729.7	728.2	726.8	725.3	723.8	721.0	717.0	712.8	708.7	704.6	700.5
52.5°	689.6	687.7	685.7	683.8	681.8	678.9	675.0	671.1	667.4	663.5	660.0
55°	628.1	626.3	624.6	622.8	621.0	618.4	614.9	611.4	607.9	604.3	600.8
57.5°	566.4	564.9	563.5	562.1	560.7	558.1	554.2	550.4	546.5	542.6	539.2
60°	525.1	524.0	522.8	521.7	520.5	517.8	513.8	509.6	505.5	501.4	498.2
62.5°	485.1	483.2	481.3	479.4	477.5	475.0	471.8	468.7	465.5	462.4	459.3
65°	423.5	421.8	420.1	418.3	416.6	414.1	411.2	408.3	405.4	402.4	399.8
67.5°	361.0	359.6	358.2	356.8	355.4	353.4	350.7	348.1	345.4	342.9	340.8
70°	321.9	320.8	319.6	318.5	317.3	315.4	312.7	310.0	307.5	304.8	302.7
72.5°	281.8	280.7	279.5	278.4	277.2	275.7	274.1	272.3	270.6	268.9	266.8
75°	221.7	221.1	220.5	219.9	219.3	218.3	216.8	215.3	213.9	212.4	210.7
77.5°	167.8	166.9	165.8	164.9	163.8	163.1	162.5	161.9	161.3	160.7	159.8
80°	132.0	131.6	131.4	131.0	130.8	130.4	129.8	129.2	128.5	128.0	127.1
82.5°	98.2	98.2	98.1	98.0	97.9	97.7	97.4	97.0	96.7	96.3	95.2
85°	54.1	53.8	53.6	53.2	53.0	52.6	52.3	52.0	51.7	51.5	50.5
87.5°	19.1	19.0	18.9	18.8	18.6	18.6	18.8	18.9	19.1	19.3	18.5
90°	0.6	2.3	4.0	5.8	7.5	9.9	13.0	16.1	19.2	22.4	22.0
92.5°	11.4	12.7	13.9	15.2	16.4	17.4	18.1	18.9	19.5	20.3	20.4
95°	33.2	34.6	36.1	37.5	38.9	39.8	40.0	40.3	40.6	40.9	40.9
97.5°	60.7	61.9	63.2	64.4	65.7	66.6	67.2	67.7	68.2	68.7	68.7
100°	81.1	82.3	83.4	84.6	85.7	86.4	86.9	87.3	87.7	88.2	88.2
102.5°	102.6	103.5	104.4	105.3	106.2	106.9	107.5	108.1	108.6	109.1	109.3
105°	137.3	137.8	138.2	138.6	139.1	139.4	139.7	140.0	140.3	140.6	140.9
107.5°	172.4	173.0	173.7	174.3	174.9	175.2	175.2	175.2	175.2	175.2	175.3
110°	194.8	195.7	196.6	197.4	198.3	198.7	198.7	198.7	198.7	198.7	198.7



TEST NUMBER: P331596-935

CATALOG NUMBER: S122DIW-S1005D710U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.4	220.2	221.1	222.0	222.8	223.2	223.1	222.9	222.8	222.7	222.4
115°	255.5	256.4	257.3	258.1	259.0	259.2	259.0	258.6	258.4	258.1	258.0
117.5°	291.6	292.7	293.9	295.0	296.1	296.3	295.5	294.7	293.9	293.2	292.8
120°	315.6	316.8	317.9	319.0	320.1	320.1	319.0	317.9	316.8	315.6	315.6
122.5°	337.6	339.0	340.4	341.6	343.0	343.4	342.5	341.7	341.0	340.2	339.8
125°	371.9	373.2	374.4	375.7	376.9	377.4	376.9	376.5	376.1	375.7	375.2
127.5°	405.2	406.8	408.5	410.0	411.6	412.2	411.7	411.2	410.7	410.2	409.7
130°	426.1	428.0	429.8	431.7	433.5	434.3	434.0	433.8	433.4	433.2	432.9
132.5°	449.7	451.2	452.7	454.2	455.6	456.5	456.5	456.6	456.7	456.7	456.1
135°	481.1	482.7	484.2	485.8	487.3	488.3	488.5	488.9	489.1	489.4	489.2
137.5°	514.2	515.5	516.8	518.1	519.3	520.1	520.5	520.9	521.2	521.6	521.5
140°	534.2	535.4	536.7	538.0	539.2	540.2	541.0	541.7	542.3	543.0	543.0
142.5°	554.6	555.9	557.2	558.4	559.6	560.6	561.0	561.5	562.0	562.5	562.6
145°	583.9	585.0	585.9	586.9	588.0	588.8	589.7	590.6	591.4	592.3	592.4
147.5°	610.2	611.3	612.5	613.7	614.9	615.8	616.4	616.9	617.5	618.1	618.4
150°	628.0	628.9	629.7	630.6	631.5	632.1	632.7	633.3	633.9	634.5	634.9
152.5°	643.9	644.7	645.6	646.4	647.3	648.1	648.8	649.5	650.1	650.8	651.3
155°	667.6	668.0	668.5	668.9	669.3	669.8	670.2	670.6	671.1	671.5	672.2
157.5°	687.9	688.3	688.5	688.8	689.1	689.4	689.7	689.9	690.2	690.4	691.4
160°	700.3	700.5	700.8	701.1	701.4	701.6	701.7	701.9	702.0	702.1	703.0
162.5°	711.4	711.5	711.6	711.6	711.7	711.8	712.0	712.1	712.2	712.4	713.3
165°	726.4	726.3	726.2	726.0	725.9	725.8	725.8	725.8	725.8	725.8	726.8
167.5°	739.0	738.6	738.1	737.7	737.3	737.0	737.0	736.9	736.9	736.9	737.9
170°	745.6	745.2	744.8	744.3	743.9	743.6	743.5	743.3	743.2	743.0	744.1
172.5°	750.2	749.8	749.3	748.9	748.5	748.2	748.0	748.0	747.8	747.6	748.6
175°	755.8	755.4	755.0	754.6	754.1	753.8	753.5	753.2	752.9	752.6	753.6
177.5°	758.1	757.8	757.4	757.1	756.7	756.5	756.2	756.0	755.8	755.5	756.2
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1



TEST NUMBER: P331596-935

CATALOG NUMBER: S122DIW-S1005D710U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3
2.5°	1366.4	1368.7	1371.1	1372.1	1371.6	1371.1	1370.6	1370.2
5°	1357.2	1359.5	1361.8	1362.8	1362.2	1361.6	1361.0	1360.4
7.5°	1341.9	1344.2	1346.6	1347.5	1346.8	1346.2	1345.5	1344.9
10°	1328.2	1330.5	1332.8	1333.6	1332.7	1331.8	1330.9	1330.1
12.5°	1312.0	1313.6	1315.3	1315.8	1315.1	1314.5	1313.8	1313.2
15°	1283.6	1284.8	1285.9	1285.8	1284.4	1282.9	1281.4	1280.0
17.5°	1249.9	1251.3	1252.6	1252.6	1251.1	1249.7	1248.4	1246.9
20°	1223.7	1224.5	1225.4	1225.2	1224.1	1222.9	1221.8	1220.6
22.5°	1195.8	1196.0	1196.2	1195.9	1195.2	1194.6	1193.8	1193.1
25°	1150.5	1151.1	1151.7	1151.7	1151.1	1150.5	1149.9	1149.3
27.5°	1105.9	1104.9	1104.1	1102.9	1101.6	1100.1	1098.7	1097.3
30°	1071.0	1070.1	1069.3	1068.2	1067.0	1065.8	1064.7	1063.5
32.5°	1036.9	1035.3	1033.7	1032.3	1031.1	1030.0	1028.8	1027.6
35°	982.1	980.4	978.6	977.1	975.6	974.1	972.6	971.1
37.5°	927.2	925.1	922.9	921.1	919.7	918.3	916.9	915.5
40°	889.3	886.7	884.1	882.2	881.0	879.9	878.7	877.4
42.5°	852.0	849.0	846.2	844.0	842.3	840.7	839.0	837.3
45°	794.5	791.3	788.1	785.8	784.6	783.5	782.3	781.2
47.5°	734.8	731.3	728.0	725.4	723.7	722.0	720.3	718.6
50°	696.4	692.3	688.2	685.4	684.0	682.5	681.1	679.6
52.5°	656.7	653.2	649.9	647.2	645.2	643.3	641.4	639.5
55°	597.3	593.7	590.3	587.8	586.3	584.9	583.4	581.9
57.5°	535.6	532.2	528.7	526.4	525.4	524.3	523.1	522.0
60°	495.0	491.7	488.5	486.5	485.6	484.7	483.8	482.9
62.5°	456.4	453.4	450.4	448.3	447.2	446.1	445.0	443.8
65°	397.2	394.5	391.9	389.9	388.4	386.9	385.5	384.0
67.5°	338.7	336.7	334.6	332.9	331.8	330.6	329.5	328.3
70°	300.7	298.7	296.6	295.0	293.8	292.7	291.4	290.3
72.5°	264.8	262.8	260.7	259.2	258.3	257.4	256.4	255.5
75°	209.0	207.2	205.4	204.8	205.4	206.0	206.6	207.2
77.5°	158.9	158.1	157.2	156.4	155.5	154.7	153.9	153.1
80°	126.2	125.4	124.5	123.7	123.1	122.6	122.0	121.4
82.5°	94.1	93.0	91.9	91.3	91.1	91.0	90.9	90.7
85°	49.7	48.8	48.0	47.4	47.1	46.8	46.5	46.1
87.5°	17.7	17.0	16.2	15.8	15.5	15.3	15.1	14.9
90°	21.8	21.5	21.3	21.2	21.3	21.4	21.6	21.7
92.5°	20.4	20.5	20.6	20.6	20.6	20.7	20.7	20.7
95°	40.9	40.9	40.9	40.7	40.5	40.2	39.9	39.6
97.5°	68.7	68.7	68.7	68.7	68.7	68.7	68.6	68.6
100°	88.2	88.2	88.2	88.1	88.0	87.8	87.6	87.6
102.5°	109.3	109.4	109.6	109.6	109.4	109.3	109.2	109.0
105°	141.1	141.4	141.7	141.8	141.8	141.8	141.8	141.8
107.5°	175.4	175.6	175.6	175.4	174.7	174.1	173.4	172.8
110°	198.7	198.7	198.7	198.5	198.0	197.6	197.2	196.8



TEST NUMBER: P331596-935

CATALOG NUMBER: S122DIW-S1005D710U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	222.1	221.7	221.4	221.0	220.8	220.4	220.1	219.8
115°	257.9	257.7	257.5	257.3	256.8	256.4	256.0	255.5
117.5°	292.5	292.1	291.8	291.4	290.9	290.5	290.1	289.6
120°	315.6	315.6	315.6	315.4	315.0	314.5	314.1	313.7
122.5°	339.5	339.1	338.8	338.5	338.1	337.9	337.5	337.3
125°	374.8	374.4	373.9	373.7	373.6	373.4	373.2	373.2
127.5°	409.1	408.6	408.1	407.7	407.2	406.7	406.3	405.9
130°	432.7	432.3	432.0	431.6	431.0	430.5	429.9	429.4
132.5°	455.5	454.8	454.2	453.7	453.2	452.7	452.3	451.9
135°	489.1	489.0	488.9	488.5	488.1	487.7	487.2	486.8
137.5°	521.3	521.2	521.2	520.8	520.2	519.7	519.1	518.5
140°	543.0	543.0	543.0	542.8	542.3	541.7	541.1	540.5
142.5°	562.7	562.8	562.9	562.7	562.1	561.5	561.0	560.4
145°	592.5	592.7	592.8	592.6	592.0	591.5	590.9	590.4
147.5°	618.7	619.0	619.3	619.2	618.7	618.1	617.6	617.1
150°	635.2	635.7	636.1	636.1	635.7	635.2	634.9	634.5
152.5°	651.9	652.4	653.0	653.0	652.4	651.9	651.3	650.8
155°	672.9	673.6	674.3	674.5	674.1	673.6	673.2	672.8
157.5°	692.3	693.3	694.2	694.4	693.7	693.0	692.3	691.6
160°	703.9	704.7	705.6	705.7	705.2	704.6	704.0	703.4
162.5°	714.3	715.3	716.3	716.4	715.7	715.1	714.4	713.7
165°	727.8	728.8	729.8	730.0	729.2	728.5	727.8	727.1
167.5°	738.9	739.9	740.9	741.0	740.3	739.5	738.8	738.0
170°	745.0	746.1	747.0	747.1	746.2	745.4	744.5	743.6
172.5°	749.7	750.6	751.7	751.7	750.9	750.0	749.2	748.3
175°	754.6	755.6	756.6	756.6	755.8	755.0	754.1	753.3
177.5°	756.9	757.6	758.3	758.3	757.6	756.9	756.2	755.5
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1

(END OF REPORT)