

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331579-940

Luminaire Tested: **S122DIW-S865D1440U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331579-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D1440U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8537.2 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331579-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331579-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	85	87	84	81	78	69	66	64	55	53	52	42	41	40	34
2	88	81	75	70	80	74	69	64	61	57	54	48	46	44	37	36	34	29
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	33	31	30	25
4	73	63	56	50	67	58	51	46	48	43	39	39	35	33	30	28	26	22
5	68	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20	17
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	15
8	53	42	34	29	49	38	32	27	32	27	24	26	23	20	21	18	16	14
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	19	17	15	13
10	47	35	28	23	42	32	26	22	27	22	19	23	19	16	18	15	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	24857	24857	24857	24857
5°	27869	25020	22172	25020
10°	31936	24815	19189	24815
15°	35328	24359	16951	24359
20°	34790	23871	15454	23871
25°	31370	23222	14503	23222
30°	25922	22184	13811	22184
35°	18892	21098	13318	21098
40°	15091	19816	13044	19816
45°	13186	18333	12673	18333
50°	12396	16900	12424	16900
55°	11426	15440	12090	15440
60°	10469	13892	11580	13892
65°	9540	12500	11075	12500
70°	8658	11146	10334	11146
75°	7679	9632	9158	9632
80°	6602	7978	7373	7978
85°	5910	5910	4372	5910



TEST NUMBER: P331579-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.6	1.7
10°-20°	426.3	5.0
20°-30°	618.6	7.2
30°-40°	652.8	7.6
40°-50°	578.0	6.8
50°-60°	461.3	5.4
60°-70°	313.5	3.7
70°-80°	160.7	1.9
80°-90°	43.1	0.5
90°-100°	58.5	0.7
100°-110°	214.4	2.5
110°-120°	573.1	6.7
120°-130°	946.0	11.1
130°-140°	1006.1	11.8
140°-150°	935.1	11.0
150°-160°	751.8	8.8
160°-170°	484.5	5.7
170°-180°	166.8	2.0
0°-30°	1191.5	14.0
0°-40°	1844.3	21.6
0°-60°	2883.6	33.8
0°-90°	3400.9	39.8
90°-120°	846.0	9.9
90°-150°	3733.2	43.7
90°-180°	5136.0	60.2
0°-180°	8537.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1540	1540	1540	1540	1540	
5°	1720	1544	1368	1544	1720	172
15°	2114	1457	1014	1457	2114	583
25°	1761	1304	814	1304	1761	796
35°	958	1070	676	1070	958	623
45°	578	803	555	803	578	454
55°	406	548	430	548	406	364
65°	250	327	290	327	250	248
75°	123	154	147	154	123	132
85°	32	32	24	32	32	36
90°	34	1	34	1	34	17
95°	55	82	55	82	55	51
105°	96	386	96	386	96	100
115°	104	729	104	729	104	260
125°	1084	1031	1084	1031	1084	938
135°	1318	1276	1318	1276	1318	1016
145°	1503	1480	1503	1480	1503	940
155°	1631	1630	1631	1630	1631	753
165°	1713	1717	1713	1717	1713	484
175°	1746	1756	1746	1756	1746	166
180°	1753	1753	1753	1753	1753	



TEST NUMBER: P331579-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1610.6	1611.1	1612.0	1604.5	1603.5	1603.5	1596.9	1591.2	1584.6	1575.6	1576.5
5°	1719.5	1726.0	1728.3	1721.3	1710.6	1709.4	1699.3	1682.7	1667.4	1654.9	1646.1
7.5°	1849.4	1852.0	1846.2	1836.8	1828.9	1814.7	1796.0	1777.7	1752.0	1728.5	1710.9
10°	1947.9	1951.4	1941.3	1927.7	1916.5	1899.9	1872.7	1844.9	1811.2	1778.6	1752.6
12.5°	2022.7	2031.4	2018.5	2016.7	1997.4	1974.7	1942.3	1928.2	1880.8	1835.4	1807.5
15°	2113.5	2112.9	2114.2	2102.8	2088.7	2085.1	2050.8	2013.6	1946.7	1920.0	1873.9
17.5°	2087.2	2096.2	2100.4	2100.2	2099.9	2097.7	2086.7	2063.2	2029.6	1986.5	1933.1
20°	2024.8	2036.6	2038.4	2052.0	2059.7	2069.7	2073.9	2067.3	2046.7	2010.5	1964.4
22.5°	1928.2	1931.5	1937.1	1958.3	1975.0	2000.2	2013.3	2035.2	2027.2	2009.6	1971.0
25°	1760.9	1755.0	1775.7	1786.3	1824.8	1865.0	1894.0	1925.9	1954.4	1971.5	1960.2
27.5°	1560.0	1551.0	1582.1	1610.3	1641.6	1685.2	1730.4	1783.7	1828.1	1883.6	1902.6
30°	1390.4	1395.8	1425.4	1455.5	1502.9	1564.4	1615.3	1673.9	1737.2	1799.3	1842.5
32.5°	1207.7	1228.2	1247.0	1293.2	1334.9	1403.5	1478.0	1551.3	1630.2	1700.8	1767.7
35°	958.5	982.2	1008.3	1042.0	1100.5	1168.6	1241.4	1340.2	1447.9	1544.4	1623.6
37.5°	806.8	803.1	818.0	842.3	889.7	944.7	1028.5	1126.1	1252.9	1366.2	1478.0
40°	716.0	713.5	724.2	746.7	782.8	823.0	896.4	982.2	1099.9	1238.4	1371.5
42.5°	653.4	654.9	660.8	676.6	701.4	734.5	789.4	862.5	970.3	1100.6	1243.8
45°	577.5	581.7	588.2	595.8	610.0	637.2	668.0	720.1	805.3	914.2	1055.0
47.5°	522.8	522.9	529.6	536.3	544.7	560.1	585.1	617.9	678.0	766.6	887.7
50°	493.5	489.4	494.1	499.4	508.3	518.9	535.5	566.2	606.5	678.1	779.3
52.5°	457.5	457.6	461.9	463.9	471.8	482.5	497.6	518.9	555.4	611.4	694.6
55°	405.9	408.8	411.3	414.7	421.9	429.5	441.4	455.6	484.0	526.0	587.5
57.5°	357.4	358.3	360.7	367.5	371.9	379.1	390.3	403.1	421.6	452.7	499.0
60°	324.2	324.2	329.0	331.9	337.9	344.9	353.8	366.2	382.8	408.2	445.6
62.5°	294.0	293.5	295.3	300.2	304.7	311.4	320.2	330.7	346.3	369.0	399.7
65°	249.7	248.5	252.1	253.2	258.0	264.5	271.6	282.9	295.2	311.8	339.0
67.5°	207.1	208.5	210.4	212.7	215.3	222.1	226.9	234.8	245.3	259.0	277.5
70°	183.4	183.4	183.4	185.2	188.8	192.3	197.1	203.6	213.6	225.4	242.0
72.5°	156.9	158.8	160.7	159.6	164.2	166.3	171.9	175.6	185.2	192.8	207.4
75°	123.1	123.1	123.1	126.0	127.8	129.6	133.1	136.7	141.4	150.9	158.5
77.5°	91.8	91.6	92.2	92.9	94.8	96.9	98.0	101.2	105.6	109.9	116.5
80°	71.0	72.2	72.8	73.9	73.9	75.2	75.7	79.9	82.8	85.8	90.0
82.5°	54.9	55.1	55.3	55.5	56.0	56.7	58.2	59.6	60.5	63.0	66.3
85°	31.9	31.4	31.4	32.5	31.9	31.9	33.2	34.3	34.3	34.9	36.6
87.5°	19.2	19.1	19.4	18.8	18.7	19.0	18.7	17.9	18.1	18.4	18.4
90°	34.2	33.7	33.1	32.5	32.0	31.0	29.6	28.2	26.8	25.3	23.1
92.5°	34.2	33.9	33.5	33.3	32.9	32.4	31.7	30.9	30.1	29.4	28.3
95°	54.6	54.8	55.1	55.4	55.6	55.1	53.7	52.3	50.8	49.5	47.5
97.5°	72.8	72.5	72.1	71.8	71.4	70.7	69.6	68.5	67.3	66.2	61.6
100°	85.0	84.4	83.8	83.3	82.8	81.3	79.1	76.8	74.5	72.3	67.5
102.5°	91.0	90.2	89.4	88.7	87.9	86.1	83.1	80.2	77.2	74.3	114.4
105°	96.4	95.2	94.2	93.0	91.8	89.8	86.7	83.6	80.4	77.4	154.3
107.5°	99.2	98.1	96.9	95.8	94.7	95.7	98.8	102.0	105.1	108.3	200.5
110°	100.2	99.1	97.9	96.8	95.7	109.2	137.4	165.6	193.8	221.9	303.4



TEST NUMBER: P331579-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	101.2	100.3	99.4	98.5	97.6	148.6	251.4	354.2	457.0	559.8	579.9
115°	104.0	124.3	144.5	164.9	185.1	260.6	391.0	521.6	652.0	782.5	775.4
117.5°	424.6	491.2	557.9	624.6	691.3	740.5	772.0	803.6	835.2	866.7	861.8
120°	773.6	811.6	849.7	887.8	925.8	943.2	939.8	936.4	933.0	929.6	924.5
122.5°	965.4	972.8	980.2	987.5	994.9	997.6	995.6	993.5	991.5	989.4	983.9
125°	1084.3	1083.5	1082.6	1081.8	1080.9	1079.5	1077.5	1075.6	1073.6	1071.7	1066.3
127.5°	1159.4	1159.2	1159.0	1158.9	1158.8	1157.2	1154.3	1151.5	1148.6	1145.8	1141.7
130°	1206.0	1206.4	1206.7	1206.9	1207.2	1205.8	1202.7	1199.6	1196.5	1193.4	1190.3
132.5°	1251.7	1252.1	1252.3	1252.6	1252.9	1251.7	1249.0	1246.3	1243.8	1241.1	1238.0
135°	1317.7	1318.2	1318.8	1319.4	1319.9	1318.8	1316.0	1313.1	1310.4	1307.5	1305.0
137.5°	1377.8	1378.8	1379.7	1380.6	1381.6	1380.7	1378.0	1375.2	1372.4	1369.7	1366.8
140°	1415.3	1416.8	1418.2	1419.6	1420.9	1420.4	1417.9	1415.3	1412.8	1410.2	1407.2
142.5°	1451.9	1453.3	1454.6	1456.1	1457.5	1457.1	1454.7	1452.4	1450.1	1447.8	1444.2
145°	1502.9	1504.2	1505.7	1507.1	1508.5	1508.2	1506.2	1504.2	1502.3	1500.3	1495.5
147.5°	1547.7	1548.9	1550.2	1551.3	1552.5	1552.4	1550.9	1549.4	1547.9	1546.5	1541.8
150°	1575.1	1576.5	1578.0	1579.4	1580.7	1580.6	1579.0	1577.3	1575.6	1573.9	1569.3
152.5°	1598.5	1600.4	1602.2	1604.0	1605.9	1606.0	1604.3	1602.6	1600.9	1599.2	1594.9
155°	1630.9	1633.2	1635.5	1637.7	1639.9	1640.2	1638.5	1636.8	1635.1	1633.4	1630.1
157.5°	1660.6	1662.8	1665.0	1667.2	1669.4	1669.6	1667.6	1665.7	1663.8	1661.9	1659.5
160°	1677.8	1679.8	1681.8	1683.8	1685.8	1685.9	1684.2	1682.5	1680.8	1679.1	1677.4
162.5°	1692.1	1694.5	1696.9	1699.3	1701.7	1702.0	1700.1	1698.2	1696.3	1694.3	1692.9
165°	1713.3	1715.4	1717.3	1719.3	1721.3	1721.3	1719.3	1717.3	1715.4	1713.3	1712.5
167.5°	1726.8	1729.4	1731.9	1734.5	1737.0	1737.2	1735.3	1733.3	1731.3	1729.4	1728.6
170°	1734.9	1737.5	1740.0	1742.6	1745.1	1745.3	1743.4	1741.4	1739.5	1737.5	1736.9
172.5°	1741.0	1743.6	1746.1	1748.6	1751.1	1751.4	1749.4	1747.5	1745.5	1743.6	1743.0
175°	1746.3	1749.2	1751.9	1754.8	1757.7	1758.0	1756.0	1754.1	1752.1	1750.2	1749.6
177.5°	1749.6	1751.7	1753.7	1755.7	1757.7	1758.0	1756.4	1754.8	1753.3	1751.7	1751.4
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331579-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1579.8	1576.0	1573.7	1565.1	1557.6	1550.0	1547.7	1548.5	1538.2	1528.2	1523.9
5°	1641.4	1629.5	1618.3	1602.3	1583.4	1562.6	1552.0	1543.7	1523.0	1500.6	1487.6
7.5°	1696.5	1679.5	1658.0	1627.9	1600.3	1567.7	1547.0	1528.7	1498.4	1466.7	1447.2
10°	1730.1	1707.0	1679.2	1642.5	1608.8	1569.1	1541.3	1513.6	1478.0	1440.2	1416.5
12.5°	1759.0	1727.9	1700.5	1653.4	1613.6	1564.0	1531.0	1491.7	1454.4	1409.4	1386.3
15°	1827.7	1770.3	1718.2	1665.0	1615.9	1546.7	1510.0	1457.3	1408.2	1352.6	1326.0
17.5°	1880.9	1816.4	1734.4	1666.7	1609.4	1532.8	1478.9	1415.8	1357.7	1294.1	1257.9
20°	1911.2	1837.2	1749.0	1668.6	1599.9	1512.3	1453.8	1389.3	1321.2	1249.6	1210.6
22.5°	1929.1	1851.4	1764.2	1661.4	1581.0	1495.8	1422.1	1351.4	1282.5	1205.1	1164.2
25°	1934.8	1863.9	1771.6	1655.6	1557.4	1460.9	1372.2	1303.5	1220.0	1147.9	1088.2
27.5°	1906.7	1855.7	1767.0	1644.4	1530.0	1417.2	1318.3	1240.5	1152.5	1074.2	1014.1
30°	1872.1	1842.5	1756.1	1633.1	1508.2	1387.0	1278.1	1189.9	1102.3	1023.1	961.5
32.5°	1818.6	1812.2	1736.3	1616.9	1485.1	1348.6	1235.9	1146.8	1049.8	971.9	913.2
35°	1713.5	1742.0	1694.0	1581.0	1441.4	1294.1	1172.2	1070.4	969.8	895.2	840.2
37.5°	1572.7	1643.2	1630.7	1528.3	1382.4	1234.7	1100.1	993.7	897.9	822.6	768.6
40°	1475.7	1565.6	1578.6	1488.1	1340.8	1188.7	1046.2	940.2	846.7	778.1	723.6
42.5°	1371.5	1476.6	1512.3	1439.8	1295.3	1140.4	997.8	888.1	795.6	728.9	680.6
45°	1197.0	1336.1	1400.5	1359.1	1219.5	1060.9	914.2	802.9	718.9	656.2	618.9
47.5°	1033.8	1185.7	1272.5	1257.8	1135.1	978.0	832.9	726.2	644.4	594.4	561.1
50°	918.3	1074.5	1179.2	1184.0	1074.5	918.9	773.4	672.8	597.6	550.9	523.6
52.5°	818.0	967.1	1081.3	1106.3	1006.8	857.4	719.9	619.7	553.6	510.6	486.2
55°	687.0	813.0	939.6	985.8	905.9	763.8	636.7	548.5	486.3	456.8	435.5
57.5°	571.1	676.2	793.1	844.1	794.9	673.3	554.0	477.5	427.0	401.2	384.9
60°	510.1	592.9	697.1	758.0	715.3	607.1	502.9	430.2	388.8	365.7	350.3
62.5°	453.3	526.6	614.7	670.4	647.2	545.1	451.8	387.5	351.8	330.2	319.1
65°	374.0	431.9	500.0	551.4	536.1	458.5	382.3	327.2	298.8	281.6	272.8
67.5°	307.9	349.8	397.0	442.1	429.7	374.8	313.4	270.6	249.5	234.7	229.3
70°	266.3	298.2	340.2	376.3	366.2	321.3	272.8	236.1	217.8	205.4	200.0
72.5°	226.5	252.8	284.8	314.3	307.6	270.2	229.7	202.0	187.9	176.5	172.1
75°	171.0	191.1	210.6	230.2	228.4	199.4	175.8	154.4	143.2	134.3	132.5
77.5°	126.3	137.5	150.8	162.4	159.2	142.6	124.0	111.8	103.5	97.6	96.7
80°	96.5	103.0	112.4	120.7	116.5	109.5	94.7	85.8	79.9	73.9	71.6
82.5°	69.9	76.4	82.1	86.6	83.5	76.8	67.7	61.6	58.1	54.0	53.1
85°	36.6	40.2	42.6	43.8	42.6	38.4	34.3	31.9	29.0	27.2	26.7
87.5°	18.4	17.9	17.5	17.9	15.9	15.2	12.8	10.7	10.8	11.0	10.6
90°	20.9	18.6	16.3	13.6	10.6	7.5	4.4	1.2	4.4	7.5	10.6
92.5°	27.2	26.0	24.9	24.5	24.8	25.1	25.3	25.6	25.3	25.1	24.8
95°	45.5	43.5	41.6	45.2	54.6	63.8	73.1	82.4	73.1	63.8	54.6
97.5°	57.1	52.5	48.0	58.8	85.0	111.2	137.4	163.6	137.4	111.2	85.0
100°	62.7	57.9	53.1	70.0	108.6	147.2	185.8	224.4	185.8	147.2	108.6
102.5°	154.4	194.6	234.6	258.8	266.9	275.1	283.3	291.4	283.3	275.1	266.9
105°	231.2	308.2	385.1	419.4	410.9	402.4	394.0	385.6	394.0	402.4	410.9
107.5°	292.8	385.1	477.4	520.1	513.3	506.5	499.6	492.8	499.6	506.5	513.3
110°	384.9	466.3	547.7	585.5	579.6	573.6	567.8	561.9	567.8	573.6	579.6



TEST NUMBER: P331579-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	600.0	620.2	640.2	647.7	642.5	637.2	632.0	626.8	632.0	637.2	642.5
115°	768.4	761.3	754.3	748.4	743.6	738.8	734.1	729.2	734.1	738.8	743.6
117.5°	857.0	852.1	847.3	842.2	836.9	831.5	826.2	820.8	826.2	831.5	836.9
120°	919.4	914.4	909.3	904.6	900.4	896.2	892.0	887.8	892.0	896.2	900.4
122.5°	978.4	972.9	967.4	962.4	958.0	953.5	949.0	944.6	949.0	953.5	958.0
125°	1061.0	1055.6	1050.3	1045.7	1042.1	1038.4	1034.7	1031.1	1034.7	1038.4	1042.1
127.5°	1137.7	1133.7	1129.7	1125.7	1121.6	1117.6	1113.5	1109.5	1113.5	1117.6	1121.6
130°	1187.2	1184.1	1181.0	1177.2	1172.7	1168.1	1163.7	1159.1	1163.7	1168.1	1172.7
132.5°	1234.8	1231.8	1228.7	1225.2	1221.4	1217.5	1213.7	1209.9	1213.7	1217.5	1221.4
135°	1302.4	1299.9	1297.4	1293.9	1289.3	1284.9	1280.3	1275.9	1280.3	1284.9	1289.3
137.5°	1364.0	1361.0	1358.2	1355.1	1352.0	1348.9	1345.7	1342.6	1345.7	1348.9	1352.0
140°	1404.1	1401.0	1397.8	1395.2	1392.9	1390.7	1388.4	1386.2	1388.4	1390.7	1392.9
142.5°	1440.7	1437.2	1433.6	1430.8	1428.8	1426.7	1424.7	1422.7	1424.7	1426.7	1428.8
145°	1490.8	1485.9	1481.1	1478.9	1479.2	1479.4	1479.7	1480.1	1479.7	1479.4	1479.2
147.5°	1537.0	1532.2	1527.5	1525.7	1526.8	1527.9	1528.9	1530.0	1528.9	1527.9	1526.8
150°	1564.9	1560.3	1555.9	1554.5	1556.6	1558.5	1560.5	1562.5	1560.5	1558.5	1556.6
152.5°	1590.6	1586.4	1582.1	1581.1	1583.2	1585.5	1587.7	1589.8	1587.7	1585.5	1583.2
155°	1626.7	1623.4	1620.0	1619.5	1622.0	1624.6	1627.1	1629.7	1627.1	1624.6	1622.0
157.5°	1657.2	1654.7	1652.4	1652.3	1654.5	1656.6	1658.8	1660.9	1658.8	1656.6	1654.5
160°	1675.8	1674.1	1672.4	1672.4	1674.1	1675.8	1677.4	1679.1	1677.4	1675.8	1674.1
162.5°	1691.4	1690.0	1688.5	1688.6	1690.3	1692.0	1693.7	1695.3	1693.7	1692.0	1690.3
165°	1711.6	1710.8	1710.0	1710.4	1712.1	1713.8	1715.5	1717.2	1715.5	1713.8	1712.1
167.5°	1727.8	1727.0	1726.2	1726.6	1728.3	1730.0	1731.7	1733.4	1731.7	1730.0	1728.3
170°	1736.3	1735.8	1735.2	1735.8	1737.5	1739.2	1740.9	1742.6	1740.9	1739.2	1737.5
172.5°	1742.4	1741.9	1741.3	1741.9	1743.6	1745.3	1747.0	1748.6	1747.0	1745.3	1743.6
175°	1749.0	1748.5	1747.9	1748.6	1750.6	1752.6	1754.5	1756.5	1754.5	1752.6	1750.6
177.5°	1751.2	1751.0	1750.8	1751.4	1753.0	1754.6	1756.2	1757.7	1756.2	1754.6	1753.0
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331579-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1519.2	1516.4	1506.5	1501.3	1492.7	1484.7	1479.4	1481.8	1483.7	1482.7	1481.4
5°	1475.7	1464.5	1447.2	1432.4	1421.8	1402.3	1394.0	1389.9	1386.3	1382.2	1378.0
7.5°	1423.9	1406.1	1381.4	1360.4	1340.5	1316.3	1302.4	1294.1	1285.7	1276.3	1268.0
10°	1387.0	1362.1	1336.1	1306.4	1282.8	1260.9	1241.4	1228.3	1216.6	1205.2	1197.0
12.5°	1348.1	1319.5	1287.3	1246.8	1220.8	1189.5	1186.4	1163.5	1145.0	1138.1	1128.4
15°	1286.4	1246.1	1205.2	1157.4	1136.7	1108.2	1090.5	1072.7	1056.8	1045.5	1042.6
17.5°	1216.2	1164.1	1123.5	1089.0	1055.1	1026.0	1009.7	995.5	982.3	967.3	965.3
20°	1162.7	1117.7	1073.4	1043.1	1008.3	978.7	958.5	944.3	933.1	924.3	916.5
22.5°	1112.1	1062.8	1022.2	989.2	954.8	930.9	915.0	901.3	891.9	882.1	874.9
25°	1030.7	992.3	947.9	910.6	882.2	866.8	853.8	842.0	836.1	829.6	821.3
27.5°	959.6	916.9	875.4	846.5	821.5	807.9	798.7	790.6	785.1	781.2	776.5
30°	909.5	866.2	833.7	805.3	784.6	771.0	765.1	760.4	753.9	751.4	749.1
32.5°	861.1	822.2	794.4	769.8	750.0	741.2	735.8	731.5	726.4	724.0	719.3
35°	792.9	760.4	733.1	719.5	703.6	695.8	691.7	685.8	681.0	678.7	678.1
37.5°	728.6	700.3	682.4	664.9	658.2	653.4	647.8	643.7	642.3	641.9	641.4
40°	687.0	663.9	647.9	633.7	630.7	623.7	618.9	615.4	615.4	616.0	615.4
42.5°	649.1	628.4	614.3	602.0	598.5	594.3	589.6	589.3	590.3	592.3	590.3
45°	591.7	576.9	566.9	560.9	554.4	550.3	549.7	551.4	552.1	552.7	554.4
47.5°	539.0	529.1	520.0	513.4	510.6	509.9	509.2	512.3	515.1	516.2	518.9
50°	507.7	496.4	488.7	484.6	482.2	481.1	482.2	485.8	488.1	491.1	492.8
52.5°	472.6	464.7	459.4	456.2	455.2	455.9	456.2	460.2	464.0	465.0	465.9
55°	424.3	418.3	417.1	411.8	414.2	413.6	416.5	418.9	422.5	426.1	426.6
57.5°	375.9	371.2	368.0	368.5	369.3	371.8	374.3	378.4	382.3	386.0	386.4
60°	343.8	341.4	339.7	339.7	340.8	344.4	347.3	351.4	353.8	356.2	357.9
62.5°	314.4	312.1	310.3	311.2	314.3	316.5	319.9	322.1	324.5	326.8	327.7
65°	268.0	266.9	268.7	269.8	270.4	273.4	277.5	279.3	281.6	282.9	287.0
67.5°	225.3	225.5	225.3	226.9	230.4	231.1	235.1	239.2	239.6	241.9	244.6
70°	196.4	197.6	198.9	200.0	203.0	204.1	207.1	208.8	211.2	213.0	214.8
72.5°	170.0	170.1	171.4	171.1	173.6	176.2	178.7	180.5	182.8	185.1	186.8
75°	130.7	130.7	132.0	132.5	135.5	138.5	137.9	139.0	141.4	143.7	145.0
77.5°	95.5	94.2	95.5	96.1	97.0	99.5	100.0	101.7	104.3	103.5	104.9
80°	72.8	71.0	72.8	73.4	73.4	76.3	76.3	77.5	79.3	77.5	79.3
82.5°	52.0	51.1	52.4	52.5	53.5	53.6	54.6	54.8	56.5	55.7	56.5
85°	26.0	25.4	26.0	25.4	26.0	26.7	26.7	26.0	26.0	27.2	25.4
87.5°	10.8	10.9	10.8	11.2	11.2	11.2	11.1	11.3	11.6	11.0	11.1
90°	13.6	16.3	18.6	20.9	23.1	25.3	26.8	28.2	29.6	31.0	32.0
92.5°	24.5	24.9	26.0	27.2	28.3	29.4	30.1	30.9	31.7	32.4	32.9
95°	45.2	41.6	43.5	45.5	47.5	49.5	50.8	52.3	53.7	55.1	55.6
97.5°	58.8	48.0	52.5	57.1	61.6	66.2	67.3	68.5	69.6	70.7	71.4
100°	70.0	53.1	57.9	62.7	67.5	72.3	74.5	76.8	79.1	81.3	82.8
102.5°	258.8	234.6	194.6	154.4	114.4	74.3	77.2	80.2	83.1	86.1	87.9
105°	419.4	385.1	308.2	231.2	154.3	77.4	80.4	83.6	86.7	89.8	91.8
107.5°	520.1	477.4	385.1	292.8	200.5	108.3	105.1	102.0	98.8	95.7	94.7
110°	585.5	547.7	466.3	384.9	303.4	221.9	193.8	165.6	137.4	109.2	95.7



TEST NUMBER: P331579-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	647.7	640.2	620.2	600.0	579.9	559.8	457.0	354.2	251.4	148.6	97.6
115°	748.4	754.3	761.3	768.4	775.4	782.5	652.0	521.6	391.0	260.6	185.1
117.5°	842.2	847.3	852.1	857.0	861.8	866.7	835.2	803.6	772.0	740.5	691.3
120°	904.6	909.3	914.4	919.4	924.5	929.6	933.0	936.4	939.8	943.2	925.8
122.5°	962.4	967.4	972.9	978.4	983.9	989.4	991.5	993.5	995.6	997.6	994.9
125°	1045.7	1050.3	1055.6	1061.0	1066.3	1071.7	1073.6	1075.6	1077.5	1079.5	1080.9
127.5°	1125.7	1129.7	1133.7	1137.7	1141.7	1145.8	1148.6	1151.5	1154.3	1157.2	1158.8
130°	1177.2	1181.0	1184.1	1187.2	1190.3	1193.4	1196.5	1199.6	1202.7	1205.8	1207.2
132.5°	1225.2	1228.7	1231.8	1234.8	1238.0	1241.1	1243.8	1246.3	1249.0	1251.7	1252.9
135°	1293.9	1297.4	1299.9	1302.4	1305.0	1307.5	1310.4	1313.1	1316.0	1318.8	1319.9
137.5°	1355.1	1358.2	1361.0	1364.0	1366.8	1369.7	1372.4	1375.2	1378.0	1380.7	1381.6
140°	1395.2	1397.8	1401.0	1404.1	1407.2	1410.2	1412.8	1415.3	1417.9	1420.4	1420.9
142.5°	1430.8	1433.6	1437.2	1440.7	1444.2	1447.8	1450.1	1452.4	1454.7	1457.1	1457.5
145°	1478.9	1481.1	1485.9	1490.8	1495.5	1500.3	1502.3	1504.2	1506.2	1508.2	1508.5
147.5°	1525.7	1527.5	1532.2	1537.0	1541.8	1546.5	1547.9	1549.4	1550.9	1552.4	1552.5
150°	1554.5	1555.9	1560.3	1564.9	1569.3	1573.9	1575.6	1577.3	1579.0	1580.6	1580.7
152.5°	1581.1	1582.1	1586.4	1590.6	1594.9	1599.2	1600.9	1602.6	1604.3	1606.0	1605.9
155°	1619.5	1620.0	1623.4	1626.7	1630.1	1633.4	1635.1	1636.8	1638.5	1640.2	1639.9
157.5°	1652.3	1652.4	1654.7	1657.2	1659.5	1661.9	1663.8	1665.7	1667.6	1669.6	1669.4
160°	1672.4	1672.4	1674.1	1675.8	1677.4	1679.1	1680.8	1682.5	1684.2	1685.9	1685.8
162.5°	1688.6	1688.5	1690.0	1691.4	1692.9	1694.3	1696.3	1698.2	1700.1	1702.0	1701.7
165°	1710.4	1710.0	1710.8	1711.6	1712.5	1713.3	1715.4	1717.3	1719.3	1721.3	1721.3
167.5°	1726.6	1726.2	1727.0	1727.8	1728.6	1729.4	1731.3	1733.3	1735.3	1737.2	1737.0
170°	1735.8	1735.2	1735.8	1736.3	1736.9	1737.5	1739.5	1741.4	1743.4	1745.3	1745.1
172.5°	1741.9	1741.3	1741.9	1742.4	1743.0	1743.6	1745.5	1747.5	1749.4	1751.4	1751.1
175°	1748.6	1747.9	1748.5	1749.0	1749.6	1750.2	1752.1	1754.1	1756.0	1758.0	1757.7
177.5°	1751.4	1750.8	1751.0	1751.2	1751.4	1751.7	1753.3	1754.8	1756.4	1758.0	1757.7
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331579-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1476.6	1475.7	1475.7	1471.4	1475.7	1475.7	1476.6	1481.4	1482.7	1483.7	1481.8
5°	1369.8	1368.0	1365.0	1368.0	1365.0	1368.0	1369.8	1378.0	1382.2	1386.3	1389.9
7.5°	1264.1	1257.0	1255.9	1248.9	1255.9	1257.0	1264.1	1268.0	1276.3	1285.7	1294.1
10°	1187.0	1182.2	1181.6	1170.4	1181.6	1182.2	1187.0	1197.0	1205.2	1216.6	1228.3
12.5°	1128.3	1116.9	1119.1	1112.6	1119.1	1116.9	1128.3	1128.4	1138.1	1145.0	1163.5
15°	1026.6	1026.6	1024.2	1014.1	1024.2	1026.6	1026.6	1042.6	1045.5	1056.8	1072.7
17.5°	953.6	952.3	946.7	949.6	946.7	952.3	953.6	965.3	967.3	982.3	995.5
20°	910.0	906.5	899.4	899.4	899.4	906.5	910.0	916.5	924.3	933.1	944.3
22.5°	868.9	868.6	861.0	863.4	861.0	868.6	868.9	874.9	882.1	891.9	901.3
25°	820.6	815.9	812.4	814.1	812.4	815.9	820.6	821.3	829.6	836.1	842.0
27.5°	775.0	772.4	772.1	767.3	772.1	772.4	775.0	776.5	781.2	785.1	790.6
30°	748.5	742.6	743.8	740.8	743.8	742.6	748.5	749.1	751.4	753.9	760.4
32.5°	718.2	716.0	714.9	712.4	714.9	716.0	718.2	719.3	724.0	726.4	731.5
35°	676.9	677.5	674.5	675.7	674.5	677.5	676.9	678.1	678.7	681.0	685.8
37.5°	640.8	642.7	641.3	641.7	641.3	642.7	640.8	641.4	641.9	642.3	643.7
40°	617.2	617.2	617.2	618.9	617.2	617.2	617.2	615.4	616.0	615.4	615.4
42.5°	594.4	593.4	592.5	592.4	592.5	593.4	594.4	590.3	592.3	590.3	589.3
45°	555.6	557.4	557.9	555.0	557.9	557.4	555.6	554.4	552.7	552.1	551.4
47.5°	520.5	520.7	520.5	523.1	520.5	520.7	520.5	518.9	516.2	515.1	512.3
50°	495.9	494.6	495.9	494.6	495.9	494.6	495.9	492.8	491.1	488.1	485.8
52.5°	469.8	470.0	469.3	469.1	469.3	470.0	469.8	465.9	465.0	464.0	460.2
55°	429.0	430.2	429.5	429.5	429.5	430.2	429.0	426.6	426.1	422.5	418.9
57.5°	386.7	387.8	388.6	386.0	388.6	387.8	386.7	386.4	386.0	382.3	378.4
60°	357.4	360.3	359.7	358.6	359.7	360.3	357.4	357.9	356.2	353.8	351.4
62.5°	330.4	331.4	331.4	331.1	331.4	331.4	330.4	327.7	326.8	324.5	322.1
65°	288.7	289.9	288.1	289.9	288.1	289.9	288.7	287.0	282.9	281.6	279.3
67.5°	243.9	244.2	245.6	246.4	245.6	244.2	243.9	244.6	241.9	239.6	239.2
70°	216.0	215.3	217.1	218.9	217.1	215.3	216.0	214.8	213.0	211.2	208.8
72.5°	186.6	187.9	187.3	188.6	187.3	187.9	186.6	186.8	185.1	182.8	180.5
75°	143.7	145.5	145.0	146.8	145.0	145.5	143.7	145.0	143.7	141.4	139.0
77.5°	103.9	104.2	103.9	104.9	103.9	104.2	103.9	104.9	103.5	104.3	101.7
80°	79.3	78.1	77.0	79.3	77.0	78.1	79.3	79.3	77.5	79.3	77.5
82.5°	55.1	55.8	54.7	54.7	54.7	55.8	55.1	56.5	55.7	56.5	54.8
85°	25.4	24.9	23.6	23.6	23.6	24.9	25.4	25.4	27.2	26.0	26.0
87.5°	11.2	10.9	11.0	10.6	11.0	10.9	11.2	11.1	11.0	11.6	11.3
90°	32.5	33.1	33.7	34.2	33.7	33.1	32.5	32.0	31.0	29.6	28.2
92.5°	33.3	33.5	33.9	34.2	33.9	33.5	33.3	32.9	32.4	31.7	30.9
95°	55.4	55.1	54.8	54.6	54.8	55.1	55.4	55.6	55.1	53.7	52.3
97.5°	71.8	72.1	72.5	72.8	72.5	72.1	71.8	71.4	70.7	69.6	68.5
100°	83.3	83.8	84.4	85.0	84.4	83.8	83.3	82.8	81.3	79.1	76.8
102.5°	88.7	89.4	90.2	91.0	90.2	89.4	88.7	87.9	86.1	83.1	80.2
105°	93.0	94.2	95.2	96.4	95.2	94.2	93.0	91.8	89.8	86.7	83.6
107.5°	95.8	96.9	98.1	99.2	98.1	96.9	95.8	94.7	95.7	98.8	102.0
110°	96.8	97.9	99.1	100.2	99.1	97.9	96.8	95.7	109.2	137.4	165.6



TEST NUMBER: P331579-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	98.5	99.4	100.3	101.2	100.3	99.4	98.5	97.6	148.6	251.4	354.2
115°	164.9	144.5	124.3	104.0	124.3	144.5	164.9	185.1	260.6	391.0	521.6
117.5°	624.6	557.9	491.2	424.6	491.2	557.9	624.6	691.3	740.5	772.0	803.6
120°	887.8	849.7	811.6	773.6	811.6	849.7	887.8	925.8	943.2	939.8	936.4
122.5°	987.5	980.2	972.8	965.4	972.8	980.2	987.5	994.9	997.6	995.6	993.5
125°	1081.8	1082.6	1083.5	1084.3	1083.5	1082.6	1081.8	1080.9	1079.5	1077.5	1075.6
127.5°	1158.9	1159.0	1159.2	1159.4	1159.2	1159.0	1158.9	1158.8	1157.2	1154.3	1151.5
130°	1206.9	1206.7	1206.4	1206.0	1206.4	1206.7	1206.9	1207.2	1205.8	1202.7	1199.6
132.5°	1252.6	1252.3	1252.1	1251.7	1252.1	1252.3	1252.6	1252.9	1251.7	1249.0	1246.3
135°	1319.4	1318.8	1318.2	1317.7	1318.2	1318.8	1319.4	1319.9	1318.8	1316.0	1313.1
137.5°	1380.6	1379.7	1378.8	1377.8	1378.8	1379.7	1380.6	1381.6	1380.7	1378.0	1375.2
140°	1419.6	1418.2	1416.8	1415.3	1416.8	1418.2	1419.6	1420.9	1420.4	1417.9	1415.3
142.5°	1456.1	1454.6	1453.3	1451.9	1453.3	1454.6	1456.1	1457.5	1457.1	1454.7	1452.4
145°	1507.1	1505.7	1504.2	1502.9	1504.2	1505.7	1507.1	1508.5	1508.2	1506.2	1504.2
147.5°	1551.3	1550.2	1548.9	1547.7	1548.9	1550.2	1551.3	1552.5	1552.4	1550.9	1549.4
150°	1579.4	1578.0	1576.5	1575.1	1576.5	1578.0	1579.4	1580.7	1580.6	1579.0	1577.3
152.5°	1604.0	1602.2	1600.4	1598.5	1600.4	1602.2	1604.0	1605.9	1606.0	1604.3	1602.6
155°	1637.7	1635.5	1633.2	1630.9	1633.2	1635.5	1637.7	1639.9	1640.2	1638.5	1636.8
157.5°	1667.2	1665.0	1662.8	1660.6	1662.8	1665.0	1667.2	1669.4	1669.6	1667.6	1665.7
160°	1683.8	1681.8	1679.8	1677.8	1679.8	1681.8	1683.8	1685.8	1685.9	1684.2	1682.5
162.5°	1699.3	1696.9	1694.5	1692.1	1694.5	1696.9	1699.3	1701.7	1702.0	1700.1	1698.2
165°	1719.3	1717.3	1715.4	1713.3	1715.4	1717.3	1719.3	1721.3	1721.3	1719.3	1717.3
167.5°	1734.5	1731.9	1729.4	1726.8	1729.4	1731.9	1734.5	1737.0	1737.2	1735.3	1733.3
170°	1742.6	1740.0	1737.5	1734.9	1737.5	1740.0	1742.6	1745.1	1745.3	1743.4	1741.4
172.5°	1748.6	1746.1	1743.6	1741.0	1743.6	1746.1	1748.6	1751.1	1751.4	1749.4	1747.5
175°	1754.8	1751.9	1749.2	1746.3	1749.2	1751.9	1754.8	1757.7	1758.0	1756.0	1754.1
177.5°	1755.7	1753.7	1751.7	1749.6	1751.7	1753.7	1755.7	1757.7	1758.0	1756.4	1754.8
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331579-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1479.4	1484.7	1492.7	1501.3	1506.5	1516.4	1519.2	1523.9	1528.2	1538.2	1548.5
5°	1394.0	1402.3	1421.8	1432.4	1447.2	1464.5	1475.7	1487.6	1500.6	1523.0	1543.7
7.5°	1302.4	1316.3	1340.5	1360.4	1381.4	1406.1	1423.9	1447.2	1466.7	1498.4	1528.7
10°	1241.4	1260.9	1282.8	1306.4	1336.1	1362.1	1387.0	1416.5	1440.2	1478.0	1513.6
12.5°	1186.4	1189.5	1220.8	1246.8	1287.3	1319.5	1348.1	1386.3	1409.4	1454.4	1491.7
15°	1090.5	1108.2	1136.7	1157.4	1205.2	1246.1	1286.4	1326.0	1352.6	1408.2	1457.3
17.5°	1009.7	1026.0	1055.1	1089.0	1123.5	1164.1	1216.2	1257.9	1294.1	1357.7	1415.8
20°	958.5	978.7	1008.3	1043.1	1073.4	1117.7	1162.7	1210.6	1249.6	1321.2	1389.3
22.5°	915.0	930.9	954.8	989.2	1022.2	1062.8	1112.1	1164.2	1205.1	1282.5	1351.4
25°	853.8	866.8	882.2	910.6	947.9	992.3	1030.7	1088.2	1147.9	1220.0	1303.5
27.5°	798.7	807.9	821.5	846.5	875.4	916.9	959.6	1014.1	1074.2	1152.5	1240.5
30°	765.1	771.0	784.6	805.3	833.7	866.2	909.5	961.5	1023.1	1102.3	1189.9
32.5°	735.8	741.2	750.0	769.8	794.4	822.2	861.1	913.2	971.9	1049.8	1146.8
35°	691.7	695.8	703.6	719.5	733.1	760.4	792.9	840.2	895.2	969.8	1070.4
37.5°	647.8	653.4	658.2	664.9	682.4	700.3	728.6	768.6	822.6	897.9	993.7
40°	618.9	623.7	630.7	633.7	647.9	663.9	687.0	723.6	778.1	846.7	940.2
42.5°	589.6	594.3	598.5	602.0	614.3	628.4	649.1	680.6	728.9	795.6	888.1
45°	549.7	550.3	554.4	560.9	566.9	576.9	591.7	618.9	656.2	718.9	802.9
47.5°	509.2	509.9	510.6	513.4	520.0	529.1	539.0	561.1	594.4	644.4	726.2
50°	482.2	481.1	482.2	484.6	488.7	496.4	507.7	523.6	550.9	597.6	672.8
52.5°	456.2	455.9	455.2	456.2	459.4	464.7	472.6	486.2	510.6	553.6	619.7
55°	416.5	413.6	414.2	411.8	417.1	418.3	424.3	435.5	456.8	486.3	548.5
57.5°	374.3	371.8	369.3	368.5	368.0	371.2	375.9	384.9	401.2	427.0	477.5
60°	347.3	344.4	340.8	339.7	339.7	341.4	343.8	350.3	365.7	388.8	430.2
62.5°	319.9	316.5	314.3	311.2	310.3	312.1	314.4	319.1	330.2	351.8	387.5
65°	277.5	273.4	270.4	269.8	268.7	266.9	268.0	272.8	281.6	298.8	327.2
67.5°	235.1	231.1	230.4	226.9	225.3	225.5	225.3	229.3	234.7	249.5	270.6
70°	207.1	204.1	203.0	200.0	198.9	197.6	196.4	200.0	205.4	217.8	236.1
72.5°	178.7	176.2	173.6	171.1	171.4	170.1	170.0	172.1	176.5	187.9	202.0
75°	137.9	138.5	135.5	132.5	132.0	130.7	130.7	132.5	134.3	143.2	154.4
77.5°	100.0	99.5	97.0	96.1	95.5	94.2	95.5	96.7	97.6	103.5	111.8
80°	76.3	76.3	73.4	73.4	72.8	71.0	72.8	71.6	73.9	79.9	85.8
82.5°	54.6	53.6	53.5	52.5	52.4	51.1	52.0	53.1	54.0	58.1	61.6
85°	26.7	26.7	26.0	25.4	26.0	25.4	26.0	26.7	27.2	29.0	31.9
87.5°	11.1	11.2	11.2	11.2	10.8	10.9	10.8	10.6	11.0	10.8	10.7
90°	26.8	25.3	23.1	20.9	18.6	16.3	13.6	10.6	7.5	4.4	1.2
92.5°	30.1	29.4	28.3	27.2	26.0	24.9	24.5	24.8	25.1	25.3	25.6
95°	50.8	49.5	47.5	45.5	43.5	41.6	45.2	54.6	63.8	73.1	82.4
97.5°	67.3	66.2	61.6	57.1	52.5	48.0	58.8	85.0	111.2	137.4	163.6
100°	74.5	72.3	67.5	62.7	57.9	53.1	70.0	108.6	147.2	185.8	224.4
102.5°	77.2	74.3	114.4	154.4	194.6	234.6	258.8	266.9	275.1	283.3	291.4
105°	80.4	77.4	154.3	231.2	308.2	385.1	419.4	410.9	402.4	394.0	385.6
107.5°	105.1	108.3	200.5	292.8	385.1	477.4	520.1	513.3	506.5	499.6	492.8
110°	193.8	221.9	303.4	384.9	466.3	547.7	585.5	579.6	573.6	567.8	561.9



TEST NUMBER: P331579-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	457.0	559.8	579.9	600.0	620.2	640.2	647.7	642.5	637.2	632.0	626.8
115°	652.0	782.5	775.4	768.4	761.3	754.3	748.4	743.6	738.8	734.1	729.2
117.5°	835.2	866.7	861.8	857.0	852.1	847.3	842.2	836.9	831.5	826.2	820.8
120°	933.0	929.6	924.5	919.4	914.4	909.3	904.6	900.4	896.2	892.0	887.8
122.5°	991.5	989.4	983.9	978.4	972.9	967.4	962.4	958.0	953.5	949.0	944.6
125°	1073.6	1071.7	1066.3	1061.0	1055.6	1050.3	1045.7	1042.1	1038.4	1034.7	1031.1
127.5°	1148.6	1145.8	1141.7	1137.7	1133.7	1129.7	1125.7	1121.6	1117.6	1113.5	1109.5
130°	1196.5	1193.4	1190.3	1187.2	1184.1	1181.0	1177.2	1172.7	1168.1	1163.7	1159.1
132.5°	1243.8	1241.1	1238.0	1234.8	1231.8	1228.7	1225.2	1221.4	1217.5	1213.7	1209.9
135°	1310.4	1307.5	1305.0	1302.4	1299.9	1297.4	1293.9	1289.3	1284.9	1280.3	1275.9
137.5°	1372.4	1369.7	1366.8	1364.0	1361.0	1358.2	1355.1	1352.0	1348.9	1345.7	1342.6
140°	1412.8	1410.2	1407.2	1404.1	1401.0	1397.8	1395.2	1392.9	1390.7	1388.4	1386.2
142.5°	1450.1	1447.8	1444.2	1440.7	1437.2	1433.6	1430.8	1428.8	1426.7	1424.7	1422.7
145°	1502.3	1500.3	1495.5	1490.8	1485.9	1481.1	1478.9	1479.2	1479.4	1479.7	1480.1
147.5°	1547.9	1546.5	1541.8	1537.0	1532.2	1527.5	1525.7	1526.8	1527.9	1528.9	1530.0
150°	1575.6	1573.9	1569.3	1564.9	1560.3	1555.9	1554.5	1556.6	1558.5	1560.5	1562.5
152.5°	1600.9	1599.2	1594.9	1590.6	1586.4	1582.1	1581.1	1583.2	1585.5	1587.7	1589.8
155°	1635.1	1633.4	1630.1	1626.7	1623.4	1620.0	1619.5	1622.0	1624.6	1627.1	1629.7
157.5°	1663.8	1661.9	1659.5	1657.2	1654.7	1652.4	1652.3	1654.5	1656.6	1658.8	1660.9
160°	1680.8	1679.1	1677.4	1675.8	1674.1	1672.4	1672.4	1674.1	1675.8	1677.4	1679.1
162.5°	1696.3	1694.3	1692.9	1691.4	1690.0	1688.5	1688.6	1690.3	1692.0	1693.7	1695.3
165°	1715.4	1713.3	1712.5	1711.6	1710.8	1710.0	1710.4	1712.1	1713.8	1715.5	1717.2
167.5°	1731.3	1729.4	1728.6	1727.8	1727.0	1726.2	1726.6	1728.3	1730.0	1731.7	1733.4
170°	1739.5	1737.5	1736.9	1736.3	1735.8	1735.2	1735.8	1737.5	1739.2	1740.9	1742.6
172.5°	1745.5	1743.6	1743.0	1742.4	1741.9	1741.3	1741.9	1743.6	1745.3	1747.0	1748.6
175°	1752.1	1750.2	1749.6	1749.0	1748.5	1747.9	1748.6	1750.6	1752.6	1754.5	1756.5
177.5°	1753.3	1751.7	1751.4	1751.2	1751.0	1750.8	1751.4	1753.0	1754.6	1756.2	1757.7
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331579-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1547.7	1550.0	1557.6	1565.1	1573.7	1576.0	1579.8	1576.5	1575.6	1584.6	1591.2
5°	1552.0	1562.6	1583.4	1602.3	1618.3	1629.5	1641.4	1646.1	1654.9	1667.4	1682.7
7.5°	1547.0	1567.7	1600.3	1627.9	1658.0	1679.5	1696.5	1710.9	1728.5	1752.0	1777.7
10°	1541.3	1569.1	1608.8	1642.5	1679.2	1707.0	1730.1	1752.6	1778.6	1811.2	1844.9
12.5°	1531.0	1564.0	1613.6	1653.4	1700.5	1727.9	1759.0	1807.5	1835.4	1880.8	1928.2
15°	1510.0	1546.7	1615.9	1665.0	1718.2	1770.3	1827.7	1873.9	1920.0	1946.7	2013.6
17.5°	1478.9	1532.8	1609.4	1666.7	1734.4	1816.4	1880.9	1933.1	1986.5	2029.6	2063.2
20°	1453.8	1512.3	1599.9	1668.6	1749.0	1837.2	1911.2	1964.4	2010.5	2046.7	2067.3
22.5°	1422.1	1495.8	1581.0	1661.4	1764.2	1851.4	1929.1	1971.0	2009.6	2027.2	2035.2
25°	1372.2	1460.9	1557.4	1655.6	1771.6	1863.9	1934.8	1960.2	1971.5	1954.4	1925.9
27.5°	1318.3	1417.2	1530.0	1644.4	1767.0	1855.7	1906.7	1902.6	1883.6	1828.1	1783.7
30°	1278.1	1387.0	1508.2	1633.1	1756.1	1842.5	1872.1	1842.5	1799.3	1737.2	1673.9
32.5°	1235.9	1348.6	1485.1	1616.9	1736.3	1812.2	1818.6	1767.7	1700.8	1630.2	1551.3
35°	1172.2	1294.1	1441.4	1581.0	1694.0	1742.0	1713.5	1623.6	1544.4	1447.9	1340.2
37.5°	1100.1	1234.7	1382.4	1528.3	1630.7	1643.2	1572.7	1478.0	1366.2	1252.9	1126.1
40°	1046.2	1188.7	1340.8	1488.1	1578.6	1565.6	1475.7	1371.5	1238.4	1099.9	982.2
42.5°	997.8	1140.4	1295.3	1439.8	1512.3	1476.6	1371.5	1243.8	1100.6	970.3	862.5
45°	914.2	1060.9	1219.5	1359.1	1400.5	1336.1	1197.0	1055.0	914.2	805.3	720.1
47.5°	832.9	978.0	1135.1	1257.8	1272.5	1185.7	1033.8	887.7	766.6	678.0	617.9
50°	773.4	918.9	1074.5	1184.0	1179.2	1074.5	918.3	779.3	678.1	606.5	566.2
52.5°	719.9	857.4	1006.8	1106.3	1081.3	967.1	818.0	694.6	611.4	555.4	518.9
55°	636.7	763.8	905.9	985.8	939.6	813.0	687.0	587.5	526.0	484.0	455.6
57.5°	554.0	673.3	794.9	844.1	793.1	676.2	571.1	499.0	452.7	421.6	403.1
60°	502.9	607.1	715.3	758.0	697.1	592.9	510.1	445.6	408.2	382.8	366.2
62.5°	451.8	545.1	647.2	670.4	614.7	526.6	453.3	399.7	369.0	346.3	330.7
65°	382.3	458.5	536.1	551.4	500.0	431.9	374.0	339.0	311.8	295.2	282.9
67.5°	313.4	374.8	429.7	442.1	397.0	349.8	307.9	277.5	259.0	245.3	234.8
70°	272.8	321.3	366.2	376.3	340.2	298.2	266.3	242.0	225.4	213.6	203.6
72.5°	229.7	270.2	307.6	314.3	284.8	252.8	226.5	207.4	192.8	185.2	175.6
75°	175.8	199.4	228.4	230.2	210.6	191.1	171.0	158.5	150.9	141.4	136.7
77.5°	124.0	142.6	159.2	162.4	150.8	137.5	126.3	116.5	109.9	105.6	101.2
80°	94.7	109.5	116.5	120.7	112.4	103.0	96.5	90.0	85.8	82.8	79.9
82.5°	67.7	76.8	83.5	86.6	82.1	76.4	69.9	66.3	63.0	60.5	59.6
85°	34.3	38.4	42.6	43.8	42.6	40.2	36.6	36.6	34.9	34.3	34.3
87.5°	12.8	15.2	15.9	17.9	17.5	17.9	18.4	18.4	18.4	18.1	17.9
90°	4.4	7.5	10.6	13.6	16.3	18.6	20.9	23.1	25.3	26.8	28.2
92.5°	25.3	25.1	24.8	24.5	24.9	26.0	27.2	28.3	29.4	30.1	30.9
95°	73.1	63.8	54.6	45.2	41.6	43.5	45.5	47.5	49.5	50.8	52.3
97.5°	137.4	111.2	85.0	58.8	48.0	52.5	57.1	61.6	66.2	67.3	68.5
100°	185.8	147.2	108.6	70.0	53.1	57.9	62.7	67.5	72.3	74.5	76.8
102.5°	283.3	275.1	266.9	258.8	234.6	194.6	154.4	114.4	74.3	77.2	80.2
105°	394.0	402.4	410.9	419.4	385.1	308.2	231.2	154.3	77.4	80.4	83.6
107.5°	499.6	506.5	513.3	520.1	477.4	385.1	292.8	200.5	108.3	105.1	102.0
110°	567.8	573.6	579.6	585.5	547.7	466.3	384.9	303.4	221.9	193.8	165.6



TEST NUMBER: P331579-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	632.0	637.2	642.5	647.7	640.2	620.2	600.0	579.9	559.8	457.0	354.2
115°	734.1	738.8	743.6	748.4	754.3	761.3	768.4	775.4	782.5	652.0	521.6
117.5°	826.2	831.5	836.9	842.2	847.3	852.1	857.0	861.8	866.7	835.2	803.6
120°	892.0	896.2	900.4	904.6	909.3	914.4	919.4	924.5	929.6	933.0	936.4
122.5°	949.0	953.5	958.0	962.4	967.4	972.9	978.4	983.9	989.4	991.5	993.5
125°	1034.7	1038.4	1042.1	1045.7	1050.3	1055.6	1061.0	1066.3	1071.7	1073.6	1075.6
127.5°	1113.5	1117.6	1121.6	1125.7	1129.7	1133.7	1137.7	1141.7	1145.8	1148.6	1151.5
130°	1163.7	1168.1	1172.7	1177.2	1181.0	1184.1	1187.2	1190.3	1193.4	1196.5	1199.6
132.5°	1213.7	1217.5	1221.4	1225.2	1228.7	1231.8	1234.8	1238.0	1241.1	1243.8	1246.3
135°	1280.3	1284.9	1289.3	1293.9	1297.4	1299.9	1302.4	1305.0	1307.5	1310.4	1313.1
137.5°	1345.7	1348.9	1352.0	1355.1	1358.2	1361.0	1364.0	1366.8	1369.7	1372.4	1375.2
140°	1388.4	1390.7	1392.9	1395.2	1397.8	1401.0	1404.1	1407.2	1410.2	1412.8	1415.3
142.5°	1424.7	1426.7	1428.8	1430.8	1433.6	1437.2	1440.7	1444.2	1447.8	1450.1	1452.4
145°	1479.7	1479.4	1479.2	1478.9	1481.1	1485.9	1490.8	1495.5	1500.3	1502.3	1504.2
147.5°	1528.9	1527.9	1526.8	1525.7	1527.5	1532.2	1537.0	1541.8	1546.5	1547.9	1549.4
150°	1560.5	1558.5	1556.6	1554.5	1555.9	1560.3	1564.9	1569.3	1573.9	1575.6	1577.3
152.5°	1587.7	1585.5	1583.2	1581.1	1582.1	1586.4	1590.6	1594.9	1599.2	1600.9	1602.6
155°	1627.1	1624.6	1622.0	1619.5	1620.0	1623.4	1626.7	1630.1	1633.4	1635.1	1636.8
157.5°	1658.8	1656.6	1654.5	1652.3	1652.4	1654.7	1657.2	1659.5	1661.9	1663.8	1665.7
160°	1677.4	1675.8	1674.1	1672.4	1672.4	1674.1	1675.8	1677.4	1679.1	1680.8	1682.5
162.5°	1693.7	1692.0	1690.3	1688.6	1688.5	1690.0	1691.4	1692.9	1694.3	1696.3	1698.2
165°	1715.5	1713.8	1712.1	1710.4	1710.0	1710.8	1711.6	1712.5	1713.3	1715.4	1717.3
167.5°	1731.7	1730.0	1728.3	1726.6	1726.2	1727.0	1727.8	1728.6	1729.4	1731.3	1733.3
170°	1740.9	1739.2	1737.5	1735.8	1735.2	1735.8	1736.3	1736.9	1737.5	1739.5	1741.4
172.5°	1747.0	1745.3	1743.6	1741.9	1741.3	1741.9	1742.4	1743.0	1743.6	1745.5	1747.5
175°	1754.5	1752.6	1750.6	1748.6	1747.9	1748.5	1749.0	1749.6	1750.2	1752.1	1754.1
177.5°	1756.2	1754.6	1753.0	1751.4	1750.8	1751.0	1751.2	1751.4	1751.7	1753.3	1754.8
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331579-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1596.9	1603.5	1603.5	1604.5	1612.0	1611.1	1610.6
5°	1699.3	1709.4	1710.6	1721.3	1728.3	1726.0	1719.5
7.5°	1796.0	1814.7	1828.9	1836.8	1846.2	1852.0	1849.4
10°	1872.7	1899.9	1916.5	1927.7	1941.3	1951.4	1947.9
12.5°	1942.3	1974.7	1997.4	2016.7	2018.5	2031.4	2022.7
15°	2050.8	2085.1	2088.7	2102.8	2114.2	2112.9	2113.5
17.5°	2086.7	2097.7	2099.9	2100.2	2100.4	2096.2	2087.2
20°	2073.9	2069.7	2059.7	2052.0	2038.4	2036.6	2024.8
22.5°	2013.3	2000.2	1975.0	1958.3	1937.1	1931.5	1928.2
25°	1894.0	1865.0	1824.8	1786.3	1775.7	1755.0	1760.9
27.5°	1730.4	1685.2	1641.6	1610.3	1582.1	1551.0	1560.0
30°	1615.3	1564.4	1502.9	1455.5	1425.4	1395.8	1390.4
32.5°	1478.0	1403.5	1334.9	1293.2	1247.0	1228.2	1207.7
35°	1241.4	1168.6	1100.5	1042.0	1008.3	982.2	958.5
37.5°	1028.5	944.7	889.7	842.3	818.0	803.1	806.8
40°	896.4	823.0	782.8	746.7	724.2	713.5	716.0
42.5°	789.4	734.5	701.4	676.6	660.8	654.9	653.4
45°	668.0	637.2	610.0	595.8	588.2	581.7	577.5
47.5°	585.1	560.1	544.7	536.3	529.6	522.9	522.8
50°	535.5	518.9	508.3	499.4	494.1	489.4	493.5
52.5°	497.6	482.5	471.8	463.9	461.9	457.6	457.5
55°	441.4	429.5	421.9	414.7	411.3	408.8	405.9
57.5°	390.3	379.1	371.9	367.5	360.7	358.3	357.4
60°	353.8	344.9	337.9	331.9	329.0	324.2	324.2
62.5°	320.2	311.4	304.7	300.2	295.3	293.5	294.0
65°	271.6	264.5	258.0	253.2	252.1	248.5	249.7
67.5°	226.9	222.1	215.3	212.7	210.4	208.5	207.1
70°	197.1	192.3	188.8	185.2	183.4	183.4	183.4
72.5°	171.9	166.3	164.2	159.6	160.7	158.8	156.9
75°	133.1	129.6	127.8	126.0	123.1	123.1	123.1
77.5°	98.0	96.9	94.8	92.9	92.2	91.6	91.8
80°	75.7	75.2	73.9	73.9	72.8	72.2	71.0
82.5°	58.2	56.7	56.0	55.5	55.3	55.1	54.9
85°	33.2	31.9	31.9	32.5	31.4	31.4	31.9
87.5°	18.7	19.0	18.7	18.8	19.4	19.1	19.2
90°	29.6	31.0	32.0	32.5	33.1	33.7	34.2
92.5°	31.7	32.4	32.9	33.3	33.5	33.9	34.2
95°	53.7	55.1	55.6	55.4	55.1	54.8	54.6
97.5°	69.6	70.7	71.4	71.8	72.1	72.5	72.8
100°	79.1	81.3	82.8	83.3	83.8	84.4	85.0
102.5°	83.1	86.1	87.9	88.7	89.4	90.2	91.0
105°	86.7	89.8	91.8	93.0	94.2	95.2	96.4
107.5°	98.8	95.7	94.7	95.8	96.9	98.1	99.2
110°	137.4	109.2	95.7	96.8	97.9	99.1	100.2



TEST NUMBER: P331579-940

CATALOG NUMBER: S122DIW-S865D1440U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	251.4	148.6	97.6	98.5	99.4	100.3	101.2
115°	391.0	260.6	185.1	164.9	144.5	124.3	104.0
117.5°	772.0	740.5	691.3	624.6	557.9	491.2	424.6
120°	939.8	943.2	925.8	887.8	849.7	811.6	773.6
122.5°	995.6	997.6	994.9	987.5	980.2	972.8	965.4
125°	1077.5	1079.5	1080.9	1081.8	1082.6	1083.5	1084.3
127.5°	1154.3	1157.2	1158.8	1158.9	1159.0	1159.2	1159.4
130°	1202.7	1205.8	1207.2	1206.9	1206.7	1206.4	1206.0
132.5°	1249.0	1251.7	1252.9	1252.6	1252.3	1252.1	1251.7
135°	1316.0	1318.8	1319.9	1319.4	1318.8	1318.2	1317.7
137.5°	1378.0	1380.7	1381.6	1380.6	1379.7	1378.8	1377.8
140°	1417.9	1420.4	1420.9	1419.6	1418.2	1416.8	1415.3
142.5°	1454.7	1457.1	1457.5	1456.1	1454.6	1453.3	1451.9
145°	1506.2	1508.2	1508.5	1507.1	1505.7	1504.2	1502.9
147.5°	1550.9	1552.4	1552.5	1551.3	1550.2	1548.9	1547.7
150°	1579.0	1580.6	1580.7	1579.4	1578.0	1576.5	1575.1
152.5°	1604.3	1606.0	1605.9	1604.0	1602.2	1600.4	1598.5
155°	1638.5	1640.2	1639.9	1637.7	1635.5	1633.2	1630.9
157.5°	1667.6	1669.6	1669.4	1667.2	1665.0	1662.8	1660.6
160°	1684.2	1685.9	1685.8	1683.8	1681.8	1679.8	1677.8
162.5°	1700.1	1702.0	1701.7	1699.3	1696.9	1694.5	1692.1
165°	1719.3	1721.3	1721.3	1719.3	1717.3	1715.4	1713.3
167.5°	1735.3	1737.2	1737.0	1734.5	1731.9	1729.4	1726.8
170°	1743.4	1745.3	1745.1	1742.6	1740.0	1737.5	1734.9
172.5°	1749.4	1751.4	1751.1	1748.6	1746.1	1743.6	1741.0
175°	1756.0	1758.0	1757.7	1754.8	1751.9	1749.2	1746.3
177.5°	1756.4	1758.0	1757.7	1755.7	1753.7	1751.7	1749.6
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7

(END OF REPORT)