

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331559-940

Luminaire Tested: **S122DIW-S865D435U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331559-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D435U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4675.6 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331559-940

CATALOG NUMBER: S122DIW-S865D435U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331559-940

CATALOG NUMBER: S122DIW-S865D435U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	97	93	90	96	92	88	85	81	79	76	72	70	68	63	62	61	56
2	93	85	79	73	87	80	75	70	71	67	63	63	60	57	56	53	51	47
3	84	75	67	61	79	71	64	58	63	58	53	56	52	48	49	46	43	40
4	77	66	58	52	73	63	55	50	56	50	45	50	45	41	44	41	37	34
5	71	59	51	45	67	56	48	43	50	44	39	45	40	36	40	36	33	30
6	66	53	45	39	62	50	43	37	45	39	34	41	36	32	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23
8	56	44	36	30	53	42	34	29	38	32	27	34	29	25	30	26	23	21
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21	19
10	49	37	29	24	46	35	28	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19869	19869	19869
5°	19945	19656	19772
10°	19825	19457	19556
15°	19580	19206	19184
20°	19234	18826	18806
25°	18887	18360	18360
30°	18442	17935	17780
35°	18027	17422	17164
40°	17506	16910	16583
45°	16993	16401	15995
50°	16435	15872	15307
55°	15854	15254	14688
60°	15206	14518	13986
65°	14514	13788	13154
70°	13629	12902	12288
75°	12402	11884	11584
80°	11000	10674	10126
85°	8985	8559	7669



TEST NUMBER: P331559-940

CATALOG NUMBER: S122DIW-S865D435U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.7	2.5
10°-20°	325.6	7.0
20°-30°	478.6	10.2
30°-40°	555.9	11.9
40°-50°	555.3	11.9
50°-60°	484.3	10.4
60°-70°	358.1	7.7
70°-80°	202.8	4.3
80°-90°	55.8	1.2
90°-100°	17.6	0.4
100°-110°	64.4	1.4
110°-120°	172.2	3.7
120°-130°	284.3	6.1
130°-140°	302.4	6.5
140°-150°	281.0	6.0
150°-160°	225.9	4.8
160°-170°	145.6	3.1
170°-180°	50.1	1.1
0°-30°	919.9	19.7
0°-40°	1475.8	31.6
0°-60°	2515.4	53.8
0°-90°	3132.1	67.0
90°-120°	254.2	5.4
90°-150°	1121.9	24.0
90°-180°	1544.0	33.0
0°-180°	4675.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1231	1231	1231	1231	1231	
5°	1231	1225	1213	1222	1220	117
15°	1171	1164	1149	1153	1148	330
25°	1060	1050	1031	1033	1031	488
35°	915	902	884	877	871	571
45°	744	735	718	706	700	574
55°	563	556	542	528	522	503
65°	380	372	361	350	344	376
75°	199	196	190	184	186	212
85°	48	47	46	43	41	56
90°	0	4	8	9	10	4
95°	25	13	15	17	16	30
105°	116	121	23	27	29	124
115°	219	226	235	67	31	216
125°	310	315	322	325	326	276
135°	383	389	393	396	396	296
145°	445	445	451	453	452	278
155°	490	487	491	493	490	226
165°	516	514	515	517	515	146
175°	528	525	526	528	525	50
180°	527	527	527	527	527	



TEST NUMBER: P331559-940

CATALOG NUMBER: S122DIW-S865D435U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1236.3	1235.2	1234.1	1233.1	1232.1	1230.4	1228.1	1225.7	1223.4	1221.1	1223.2
5°	1230.6	1229.5	1228.5	1227.4	1226.4	1224.4	1221.6	1218.6	1215.8	1212.8	1215.0
7.5°	1219.7	1218.1	1216.5	1214.8	1213.2	1210.9	1207.9	1205.0	1202.0	1199.1	1201.2
10°	1209.2	1207.5	1205.6	1203.7	1201.9	1199.4	1196.2	1193.1	1190.0	1186.8	1188.9
12.5°	1195.1	1193.5	1191.9	1190.2	1188.6	1186.2	1183.0	1179.8	1176.7	1173.6	1175.0
15°	1171.4	1169.8	1168.2	1166.7	1165.1	1162.6	1159.2	1155.7	1152.4	1149.0	1150.0
17.5°	1141.1	1139.5	1138.0	1136.4	1134.8	1132.3	1128.8	1125.3	1121.9	1118.4	1119.6
20°	1119.4	1117.8	1116.2	1114.6	1113.0	1110.4	1106.7	1103.0	1099.4	1095.7	1096.4
22.5°	1097.6	1095.4	1093.1	1090.9	1088.8	1085.9	1082.4	1079.0	1075.5	1072.0	1072.2
25°	1060.2	1058.1	1056.0	1053.9	1051.8	1048.5	1044.0	1039.6	1035.1	1030.6	1031.2
27.5°	1017.6	1015.7	1013.8	1011.9	1010.0	1007.3	1003.8	1000.2	996.8	993.2	992.5
30°	989.2	987.1	985.0	982.9	980.8	977.8	973.8	969.9	965.9	962.0	961.2
32.5°	958.9	957.3	955.6	953.9	952.2	949.2	945.1	940.9	936.8	932.6	931.2
35°	914.6	912.0	909.4	906.8	904.1	900.7	896.5	892.3	888.1	883.9	882.3
37.5°	864.7	862.4	860.1	857.7	855.5	852.2	848.0	843.8	839.5	835.4	833.4
40°	830.6	828.6	826.4	824.3	822.2	819.0	814.8	810.7	806.5	802.3	799.9
42.5°	797.5	795.4	793.3	791.2	789.1	786.0	781.8	777.6	773.3	769.1	766.5
45°	744.2	742.4	740.6	738.8	736.9	734.0	730.0	726.1	722.2	718.3	715.3
47.5°	691.3	689.6	687.8	686.1	684.3	681.4	677.3	673.2	669.1	664.9	661.9
50°	654.3	653.0	651.8	650.4	649.1	646.6	642.9	639.2	635.5	631.9	628.2
52.5°	618.4	616.6	614.9	613.1	611.4	608.9	605.4	601.9	598.4	594.9	591.9
55°	563.2	561.7	560.1	558.5	556.9	554.6	551.4	548.2	545.1	541.9	538.8
57.5°	507.8	506.6	505.3	504.1	502.8	500.4	497.0	493.5	490.0	486.5	483.5
60°	470.9	469.8	468.9	467.8	466.7	464.4	460.7	457.0	453.3	449.6	446.7
62.5°	435.0	433.3	431.6	429.9	428.2	426.0	423.1	420.3	417.4	414.6	412.0
65°	379.9	378.3	376.7	375.1	373.5	371.4	368.8	366.1	363.6	360.9	358.6
67.5°	323.8	322.4	321.2	319.9	318.7	316.9	314.5	312.1	309.8	307.4	305.6
70°	288.7	287.7	286.6	285.5	284.5	282.8	280.4	278.0	275.7	273.3	271.5
72.5°	252.7	251.7	250.7	249.6	248.5	247.3	245.8	244.2	242.6	241.1	239.3
75°	198.8	198.2	197.7	197.2	196.7	195.7	194.5	193.1	191.8	190.5	189.0
77.5°	150.5	149.6	148.7	147.8	147.0	146.2	145.7	145.2	144.6	144.1	143.3
80°	118.3	118.1	117.8	117.5	117.3	116.9	116.4	115.8	115.3	114.8	114.0
82.5°	88.0	88.0	87.9	87.8	87.8	87.7	87.3	87.0	86.7	86.4	85.3
85°	48.5	48.2	48.0	47.7	47.4	47.2	46.9	46.6	46.4	46.2	45.4
87.5°	17.1	16.9	16.7	16.4	16.1	16.0	15.6	15.3	15.1	14.8	14.3
90°	0.4	1.3	2.2	3.2	4.1	4.9	5.6	6.2	7.0	7.6	8.0
92.5°	7.7	7.6	7.5	7.4	7.4	7.5	7.8	8.2	8.5	8.8	9.1
95°	24.8	21.9	19.2	16.4	13.6	12.5	13.1	13.6	14.3	14.9	15.2
97.5°	49.1	41.3	33.4	25.5	17.7	14.4	15.8	17.1	18.5	19.9	20.2
100°	67.5	55.8	44.2	32.6	21.0	16.0	17.4	18.8	20.2	21.8	22.4
102.5°	87.6	85.2	82.7	80.3	77.8	70.5	58.5	46.5	34.4	22.3	23.2
105°	115.8	118.4	120.9	123.5	126.0	115.7	92.6	69.5	46.4	23.3	24.2
107.5°	148.1	150.2	152.2	154.3	156.3	143.5	115.7	88.0	60.3	32.5	31.6
110°	168.8	170.6	172.4	174.2	175.9	164.6	140.1	115.7	91.1	66.7	58.2



TEST NUMBER: P331559-940

CATALOG NUMBER: S122DIW-S865D435U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	188.3	189.9	191.5	193.1	194.7	192.4	186.4	180.3	174.2	168.3	137.3
115°	219.2	220.6	222.0	223.5	224.9	226.7	228.8	231.0	233.0	235.1	195.9
117.5°	246.6	248.3	249.9	251.5	253.1	254.7	256.1	257.5	259.0	260.5	251.0
120°	266.8	268.0	269.3	270.6	271.9	273.3	274.8	276.3	277.9	279.4	280.4
122.5°	283.8	285.2	286.5	287.8	289.2	290.7	292.4	294.0	295.7	297.4	298.0
125°	309.9	310.9	312.1	313.2	314.2	315.6	317.3	318.9	320.5	322.1	322.6
127.5°	333.4	334.7	335.8	337.1	338.3	339.5	340.7	341.9	343.1	344.3	345.2
130°	348.4	349.7	351.1	352.4	353.7	354.9	355.9	356.8	357.8	358.6	359.5
132.5°	363.6	364.7	365.9	367.0	368.2	369.3	370.1	371.1	372.0	373.0	373.8
135°	383.4	384.8	386.1	387.4	388.9	389.9	390.7	391.5	392.2	393.0	393.8
137.5°	403.5	404.4	405.4	406.4	407.2	408.1	409.0	409.9	410.7	411.6	412.4
140°	416.6	417.2	417.9	418.6	419.3	420.1	421.1	422.0	422.8	423.8	424.5
142.5°	427.6	428.2	428.7	429.4	430.0	430.9	431.9	432.9	434.0	435.1	435.8
145°	444.8	444.7	444.6	444.5	444.4	445.1	446.6	448.0	449.4	450.8	451.5
147.5°	459.8	459.5	459.1	458.9	458.5	459.1	460.5	461.9	463.3	464.8	465.2
150°	469.6	469.0	468.3	467.8	467.2	467.5	469.0	470.3	471.6	473.0	473.5
152.5°	477.8	477.2	476.4	475.8	475.1	475.5	476.7	478.0	479.3	480.6	481.1
155°	489.7	489.0	488.2	487.5	486.7	486.9	487.9	488.8	489.9	490.9	491.4
157.5°	499.1	498.5	497.8	497.2	496.6	496.6	497.3	498.0	498.7	499.4	500.0
160°	504.6	504.1	503.6	503.1	502.6	502.6	503.1	503.6	504.1	504.6	505.2
162.5°	509.5	509.0	508.5	508.0	507.5	507.5	507.8	508.3	508.7	509.2	509.8
165°	516.0	515.6	515.1	514.5	514.0	513.9	514.2	514.4	514.7	514.9	515.5
167.5°	520.9	520.4	520.0	519.4	518.9	518.8	519.0	519.2	519.5	519.7	520.3
170°	523.7	523.2	522.6	522.2	521.7	521.5	521.7	521.8	522.0	522.2	522.7
172.5°	525.5	525.0	524.5	524.0	523.4	523.3	523.4	523.6	523.8	524.0	524.6
175°	527.9	527.3	526.6	526.1	525.5	525.3	525.5	525.7	525.8	525.9	526.6
177.5°	528.2	527.8	527.3	526.8	526.4	526.1	526.2	526.3	526.4	526.4	526.9
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331559-940

CATALOG NUMBER: S122DIW-S865D435U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1225.3	1227.4	1229.5	1230.4	1229.9	1229.5	1229.1	1228.7
5°	1217.0	1219.1	1221.3	1222.0	1221.6	1221.0	1220.5	1219.9
7.5°	1203.3	1205.4	1207.6	1208.3	1207.7	1207.1	1206.6	1205.9
10°	1191.0	1193.1	1195.2	1195.9	1195.1	1194.3	1193.5	1192.8
12.5°	1176.5	1177.9	1179.5	1179.9	1179.3	1178.8	1178.1	1177.6
15°	1151.0	1152.1	1153.2	1153.0	1151.7	1150.4	1149.1	1147.7
17.5°	1120.8	1122.0	1123.3	1123.2	1122.0	1120.7	1119.5	1118.2
20°	1097.3	1098.1	1098.9	1098.7	1097.7	1096.6	1095.6	1094.5
22.5°	1072.4	1072.5	1072.6	1072.5	1071.7	1071.1	1070.5	1069.9
25°	1031.7	1032.2	1032.7	1032.7	1032.2	1031.7	1031.2	1030.6
27.5°	991.7	990.9	990.1	989.1	987.7	986.5	985.3	984.0
30°	960.4	959.7	958.9	957.9	956.9	955.8	954.8	953.7
32.5°	929.8	928.4	926.9	925.7	924.7	923.6	922.6	921.5
35°	880.7	879.1	877.6	876.1	874.9	873.5	872.2	870.8
37.5°	831.5	829.6	827.6	826.0	824.7	823.5	822.2	820.9
40°	797.5	795.1	792.8	791.0	790.1	789.0	787.9	786.8
42.5°	763.9	761.3	758.8	756.8	755.3	753.9	752.3	750.9
45°	712.5	709.5	706.7	704.7	703.6	702.6	701.5	700.5
47.5°	658.9	655.9	652.8	650.5	649.0	647.5	646.0	644.4
50°	624.5	620.8	617.2	614.7	613.3	612.0	610.7	609.4
52.5°	588.8	585.8	582.7	580.3	578.6	576.8	575.2	573.4
55°	535.7	532.4	529.3	527.1	525.8	524.4	523.2	521.8
57.5°	480.4	477.2	474.1	472.1	471.1	470.1	469.1	468.1
60°	443.9	441.0	438.1	436.2	435.4	434.6	433.8	433.1
62.5°	409.2	406.5	403.9	402.1	401.0	400.0	399.0	398.1
65°	356.1	353.8	351.4	349.6	348.3	347.0	345.6	344.3
67.5°	303.7	301.8	300.1	298.6	297.6	296.5	295.4	294.4
70°	269.7	267.8	266.0	264.5	263.5	262.4	261.4	260.3
72.5°	237.5	235.6	233.8	232.5	231.6	230.8	229.9	229.1
75°	187.3	185.7	184.2	183.7	184.2	184.8	185.2	185.7
77.5°	142.6	141.8	141.0	140.2	139.5	138.8	138.0	137.2
80°	113.2	112.4	111.6	110.9	110.4	109.9	109.4	108.9
82.5°	84.4	83.4	82.4	81.9	81.7	81.6	81.5	81.4
85°	44.6	43.8	43.0	42.4	42.2	41.9	41.6	41.4
87.5°	13.6	13.1	12.6	12.2	12.0	11.9	11.7	11.5
90°	8.5	8.9	9.3	9.6	9.8	10.0	10.2	10.3
92.5°	9.3	9.5	9.7	9.9	10.0	10.1	10.2	10.3
95°	15.7	16.1	16.6	16.8	16.7	16.6	16.5	16.4
97.5°	20.6	21.0	21.2	21.5	21.6	21.7	21.8	21.8
100°	23.1	23.7	24.4	24.9	25.1	25.2	25.3	25.5
102.5°	24.1	25.0	25.9	26.4	26.7	26.9	27.1	27.4
105°	25.1	26.0	27.0	27.6	27.9	28.3	28.6	29.0
107.5°	30.7	29.7	28.7	28.4	28.8	29.2	29.4	29.8
110°	49.8	41.3	32.8	28.7	29.1	29.4	29.8	30.1



TEST NUMBER: P331559-940

CATALOG NUMBER: S122DIW-S865D435U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	106.5	75.5	44.7	29.3	29.6	29.9	30.1	30.4
115°	156.8	117.5	78.3	55.6	49.6	43.4	37.4	31.2
117.5°	241.5	232.0	222.5	207.8	187.7	167.6	147.7	127.6
120°	281.4	282.4	283.5	278.2	266.8	255.4	243.9	232.5
122.5°	298.5	299.2	299.8	299.0	296.8	294.5	292.3	290.1
125°	323.2	323.9	324.4	324.9	325.1	325.4	325.7	325.8
127.5°	346.1	346.9	347.8	348.2	348.3	348.3	348.4	348.4
130°	360.5	361.4	362.4	362.8	362.7	362.7	362.6	362.5
132.5°	374.6	375.3	376.1	376.5	376.4	376.3	376.3	376.2
135°	394.7	395.5	396.4	396.6	396.5	396.4	396.2	396.0
137.5°	413.3	414.1	414.9	415.2	414.9	414.6	414.4	414.0
140°	425.3	426.1	426.9	427.0	426.6	426.1	425.8	425.3
142.5°	436.5	437.2	437.9	438.0	437.6	437.2	436.8	436.3
145°	452.1	452.6	453.3	453.3	452.9	452.5	452.1	451.7
147.5°	465.7	466.1	466.5	466.5	466.2	465.8	465.5	465.1
150°	474.0	474.5	475.0	475.1	474.7	474.2	473.8	473.4
152.5°	481.6	482.1	482.7	482.6	482.1	481.5	480.9	480.4
155°	492.0	492.4	492.9	492.8	492.1	491.5	490.8	490.2
157.5°	500.6	501.1	501.8	501.7	501.1	500.3	499.7	499.1
160°	505.6	506.1	506.7	506.6	506.0	505.4	504.8	504.3
162.5°	510.3	511.0	511.5	511.4	510.7	510.0	509.3	508.5
165°	516.1	516.7	517.3	517.3	516.7	516.1	515.5	514.9
167.5°	520.9	521.5	522.1	522.0	521.2	520.5	519.7	519.0
170°	523.3	524.0	524.5	524.4	523.7	522.9	522.2	521.4
172.5°	525.1	525.8	526.4	526.3	525.5	524.8	524.0	523.3
175°	527.2	527.7	528.3	528.2	527.4	526.6	525.7	524.9
177.5°	527.4	527.8	528.3	528.2	527.6	527.0	526.4	525.8
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7

(END OF REPORT)