

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331601-935

Luminaire Tested: **S122DIW-S1005D970U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331601-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D970U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6826.1 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331601-935

CATALOG NUMBER: S122DIW-S1005D970U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331601-935

CATALOG NUMBER: S122DIW-S1005D970U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	44	42	41	36
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	26	47	36	29	24	31	25	22	27	22	19	22	19	17	14
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22157	22157	22157
5°	22242	21921	22049
10°	22109	21697	21807
15°	21835	21417	21396
20°	21448	20993	20972
25°	21063	20475	20475
30°	20566	19999	19827
35°	20103	19429	19141
40°	19524	18858	18493
45°	18952	18287	17838
50°	18329	17698	17071
55°	17681	17011	16380
60°	16956	16191	15594
65°	16180	15373	14670
70°	15196	14389	13704
75°	13830	13250	12926
80°	12273	11901	11288
85°	10022	9541	8540



TEST NUMBER: P331601-935

CATALOG NUMBER: S122DIW-S1005D970U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.0	1.9
10°-20°	363.1	5.3
20°-30°	533.7	7.8
30°-40°	619.9	9.1
40°-50°	619.3	9.1
50°-60°	540.0	7.9
60°-70°	399.3	5.8
70°-80°	226.2	3.3
80°-90°	63.6	0.9
90°-100°	37.9	0.6
100°-110°	139.1	2.0
110°-120°	371.8	5.4
120°-130°	613.7	9.0
130°-140°	652.7	9.6
140°-150°	606.6	8.9
150°-160°	487.7	7.1
160°-170°	314.3	4.6
170°-180°	108.2	1.6
0°-30°	1025.8	15.0
0°-40°	1645.7	24.1
0°-60°	2805.0	41.1
0°-90°	3494.1	51.2
90°-120°	548.8	8.0
90°-150°	2421.8	35.5
90°-180°	3332.0	48.8
0°-180°	6826.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1372	1366	1352	1362	1360	130
15°	1306	1298	1281	1286	1280	368
25°	1182	1171	1149	1152	1149	544
35°	1020	1006	986	978	971	637
45°	830	820	801	787	781	640
55°	628	620	604	589	582	561
65°	424	415	402	391	384	419
75°	222	219	212	205	207	237
85°	54	53	52	48	46	62
90°	1	10	16	20	22	5
95°	54	28	32	36	35	65
105°	250	261	50	59	62	267
115°	473	487	508	145	68	466
125°	669	680	695	701	703	596
135°	828	840	848	856	855	639
145°	960	960	973	978	975	600
155°	1057	1051	1060	1064	1058	487
165°	1114	1109	1112	1117	1112	315
175°	1139	1134	1135	1140	1133	108
180°	1137	1137	1137	1137	1137	



TEST NUMBER: P331601-935

CATALOG NUMBER: S122DIW-S1005D970U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3
2.5°	1378.6	1377.4	1376.3	1375.1	1373.9	1372.1	1369.5	1366.9	1364.3	1361.8	1364.1
5°	1372.3	1371.1	1369.9	1368.7	1367.6	1365.4	1362.2	1358.9	1355.7	1352.5	1354.9
7.5°	1360.1	1358.3	1356.5	1354.7	1352.9	1350.3	1347.0	1343.8	1340.5	1337.2	1339.5
10°	1348.5	1346.5	1344.5	1342.4	1340.3	1337.6	1334.0	1330.5	1327.0	1323.4	1325.9
12.5°	1332.7	1330.8	1329.0	1327.2	1325.4	1322.8	1319.2	1315.7	1312.3	1308.7	1310.4
15°	1306.3	1304.6	1302.8	1301.1	1299.2	1296.5	1292.7	1288.8	1285.0	1281.3	1282.5
17.5°	1272.6	1270.7	1269.0	1267.2	1265.5	1262.7	1258.8	1254.9	1251.0	1247.2	1248.5
20°	1248.3	1246.5	1244.7	1242.9	1241.2	1238.3	1234.2	1230.1	1226.0	1221.8	1222.7
22.5°	1224.0	1221.5	1219.1	1216.6	1214.1	1211.0	1207.1	1203.2	1199.4	1195.5	1195.7
25°	1182.3	1179.9	1177.6	1175.3	1172.9	1169.2	1164.2	1159.3	1154.3	1149.3	1149.9
27.5°	1134.8	1132.6	1130.6	1128.4	1126.4	1123.3	1119.4	1115.4	1111.6	1107.6	1106.7
30°	1103.1	1100.8	1098.4	1096.1	1093.7	1090.4	1086.0	1081.6	1077.2	1072.7	1071.9
32.5°	1069.4	1067.5	1065.6	1063.7	1061.8	1058.6	1054.0	1049.3	1044.7	1040.0	1038.5
35°	1019.9	1017.0	1014.1	1011.2	1008.2	1004.4	999.7	995.1	990.4	985.7	984.0
37.5°	964.3	961.7	959.2	956.6	954.0	950.4	945.6	941.0	936.3	931.6	929.4
40°	926.3	923.9	921.6	919.3	916.9	913.4	908.7	904.0	899.3	894.7	892.0
42.5°	889.3	887.0	884.7	882.4	879.9	876.4	871.8	867.0	862.4	857.6	854.8
45°	830.0	827.9	825.9	823.8	821.7	818.6	814.2	809.8	805.4	800.9	797.7
47.5°	770.9	769.0	767.0	765.1	763.1	759.8	755.3	750.7	746.1	741.6	738.1
50°	729.7	728.2	726.8	725.3	723.8	721.0	717.0	712.8	708.7	704.6	700.5
52.5°	689.6	687.7	685.7	683.8	681.8	678.9	675.0	671.1	667.4	663.5	660.0
55°	628.1	626.3	624.6	622.8	621.0	618.4	614.9	611.4	607.9	604.3	600.8
57.5°	566.4	564.9	563.5	562.1	560.7	558.1	554.2	550.4	546.5	542.6	539.2
60°	525.1	524.0	522.8	521.7	520.5	517.8	513.8	509.6	505.5	501.4	498.2
62.5°	485.1	483.2	481.3	479.4	477.5	475.0	471.8	468.7	465.5	462.4	459.3
65°	423.5	421.8	420.1	418.3	416.6	414.1	411.2	408.3	405.4	402.4	399.8
67.5°	361.0	359.6	358.2	356.8	355.4	353.4	350.7	348.1	345.4	342.9	340.8
70°	321.9	320.8	319.6	318.5	317.3	315.4	312.7	310.0	307.5	304.8	302.7
72.5°	281.8	280.7	279.5	278.4	277.2	275.7	274.1	272.3	270.6	268.9	266.8
75°	221.7	221.1	220.5	219.9	219.3	218.3	216.8	215.3	213.9	212.4	210.7
77.5°	167.8	166.9	165.8	164.9	163.8	163.1	162.5	161.9	161.3	160.7	159.8
80°	132.0	131.6	131.4	131.0	130.8	130.4	129.8	129.2	128.5	128.0	127.1
82.5°	98.2	98.2	98.1	98.0	97.9	97.7	97.4	97.0	96.7	96.3	95.2
85°	54.1	53.8	53.6	53.2	53.0	52.6	52.3	52.0	51.7	51.5	50.5
87.5°	19.2	19.1	19.0	18.9	18.9	18.8	18.6	18.4	18.3	18.1	17.6
90°	0.9	2.8	4.8	6.9	8.9	10.6	12.1	13.5	15.0	16.4	17.4
92.5°	16.6	16.4	16.3	16.1	15.9	16.2	16.9	17.7	18.3	19.1	19.5
95°	53.5	47.4	41.4	35.4	29.4	26.9	28.2	29.5	30.8	32.1	33.0
97.5°	106.2	89.1	72.2	55.1	38.1	31.1	34.1	37.0	40.0	43.0	43.7
100°	145.6	120.5	95.5	70.5	45.5	34.4	37.5	40.6	43.8	46.9	48.4
102.5°	189.1	183.7	178.5	173.1	167.8	152.2	126.2	100.2	74.2	48.2	50.1
105°	250.1	255.6	261.1	266.6	272.1	249.9	199.9	150.0	100.1	50.2	52.2
107.5°	319.7	324.2	328.6	332.9	337.4	309.7	249.9	189.9	130.1	70.3	68.2
110°	364.5	368.3	372.1	376.0	379.8	355.3	302.5	249.7	196.8	144.0	125.7



TEST NUMBER: P331601-935

CATALOG NUMBER: S122DIW-S1005D970U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	406.6	410.0	413.4	416.8	420.2	415.3	402.3	389.3	376.2	363.2	296.4
115°	473.0	476.1	479.3	482.4	485.5	489.3	493.9	498.4	503.1	507.6	422.9
117.5°	532.4	536.0	539.4	542.9	546.4	549.7	552.8	555.9	559.1	562.2	541.7
120°	575.9	578.7	581.3	584.1	586.9	589.9	593.1	596.5	599.8	603.0	605.3
122.5°	612.8	615.6	618.5	621.4	624.3	627.6	631.1	634.7	638.3	641.9	643.2
125°	668.8	671.2	673.6	676.0	678.4	681.3	684.8	688.3	691.7	695.2	696.5
127.5°	719.7	722.4	725.0	727.6	730.2	732.9	735.5	738.0	740.6	743.2	745.1
130°	752.0	754.9	757.9	760.7	763.6	766.1	768.1	770.2	772.1	774.2	776.2
132.5°	784.9	787.4	789.9	792.3	794.8	797.0	799.1	801.1	803.1	805.1	806.8
135°	827.7	830.6	833.5	836.5	839.4	841.6	843.3	844.9	846.5	848.3	850.1
137.5°	870.9	873.0	875.0	877.1	879.1	881.1	883.0	884.8	886.7	888.6	890.4
140°	899.2	900.7	902.2	903.6	905.1	906.8	908.8	910.9	912.8	914.9	916.5
142.5°	922.9	924.2	925.6	926.9	928.2	930.0	932.3	934.6	936.9	939.2	940.7
145°	960.1	959.9	959.8	959.6	959.4	960.9	964.0	967.1	970.2	973.3	974.6
147.5°	992.6	991.8	991.1	990.4	989.7	990.9	994.0	997.0	1000.1	1003.2	1004.2
150°	1013.6	1012.3	1011.0	1009.8	1008.5	1009.3	1012.2	1015.1	1018.0	1021.0	1022.1
152.5°	1031.4	1029.9	1028.5	1027.1	1025.6	1026.3	1029.1	1031.9	1034.7	1037.4	1038.5
155°	1057.2	1055.5	1053.9	1052.2	1050.6	1050.9	1053.1	1055.2	1057.5	1059.6	1060.8
157.5°	1077.5	1076.1	1074.6	1073.2	1071.9	1071.9	1073.5	1075.0	1076.5	1078.1	1079.3
160°	1089.3	1088.2	1087.1	1086.0	1084.9	1084.9	1086.0	1087.1	1088.2	1089.3	1090.4
162.5°	1099.8	1098.7	1097.6	1096.5	1095.5	1095.4	1096.3	1097.3	1098.2	1099.2	1100.4
165°	1114.0	1112.8	1111.7	1110.7	1109.6	1109.3	1109.8	1110.3	1110.9	1111.5	1112.8
167.5°	1124.5	1123.3	1122.3	1121.2	1120.1	1119.8	1120.3	1120.8	1121.4	1121.9	1123.1
170°	1130.4	1129.3	1128.3	1127.1	1126.0	1125.7	1126.0	1126.4	1126.8	1127.1	1128.4
172.5°	1134.4	1133.2	1132.1	1131.1	1130.0	1129.6	1130.0	1130.3	1130.7	1131.1	1132.4
175°	1139.4	1138.2	1136.9	1135.7	1134.4	1133.9	1134.3	1134.6	1135.0	1135.3	1136.6
177.5°	1140.3	1139.3	1138.2	1137.2	1136.2	1135.7	1135.9	1136.0	1136.2	1136.3	1137.4
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331601-935

CATALOG NUMBER: S122DIW-S1005D970U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3
2.5°	1366.4	1368.7	1371.1	1372.1	1371.6	1371.1	1370.6	1370.2
5°	1357.2	1359.5	1361.8	1362.8	1362.2	1361.6	1361.0	1360.4
7.5°	1341.9	1344.2	1346.6	1347.5	1346.8	1346.2	1345.5	1344.9
10°	1328.2	1330.5	1332.8	1333.6	1332.7	1331.8	1330.9	1330.1
12.5°	1312.0	1313.6	1315.3	1315.8	1315.1	1314.5	1313.8	1313.2
15°	1283.6	1284.8	1285.9	1285.8	1284.4	1282.9	1281.4	1280.0
17.5°	1249.9	1251.3	1252.6	1252.6	1251.1	1249.7	1248.4	1246.9
20°	1223.7	1224.5	1225.4	1225.2	1224.1	1222.9	1221.8	1220.6
22.5°	1195.8	1196.0	1196.2	1195.9	1195.2	1194.6	1193.8	1193.1
25°	1150.5	1151.1	1151.7	1151.7	1151.1	1150.5	1149.9	1149.3
27.5°	1105.9	1104.9	1104.1	1102.9	1101.6	1100.1	1098.7	1097.3
30°	1071.0	1070.1	1069.3	1068.2	1067.0	1065.8	1064.7	1063.5
32.5°	1036.9	1035.3	1033.7	1032.3	1031.1	1030.0	1028.8	1027.6
35°	982.1	980.4	978.6	977.1	975.6	974.1	972.6	971.1
37.5°	927.2	925.1	922.9	921.1	919.7	918.3	916.9	915.5
40°	889.3	886.7	884.1	882.2	881.0	879.9	878.7	877.4
42.5°	852.0	849.0	846.2	844.0	842.3	840.7	839.0	837.3
45°	794.5	791.3	788.1	785.8	784.6	783.5	782.3	781.2
47.5°	734.8	731.3	728.0	725.4	723.7	722.0	720.3	718.6
50°	696.4	692.3	688.2	685.4	684.0	682.5	681.1	679.6
52.5°	656.7	653.2	649.9	647.2	645.2	643.3	641.4	639.5
55°	597.3	593.7	590.3	587.8	586.3	584.9	583.4	581.9
57.5°	535.6	532.2	528.7	526.4	525.4	524.3	523.1	522.0
60°	495.0	491.7	488.5	486.5	485.6	484.7	483.8	482.9
62.5°	456.4	453.4	450.4	448.3	447.2	446.1	445.0	443.8
65°	397.2	394.5	391.9	389.9	388.4	386.9	385.5	384.0
67.5°	338.7	336.7	334.6	332.9	331.8	330.6	329.5	328.3
70°	300.7	298.7	296.6	295.0	293.8	292.7	291.4	290.3
72.5°	264.8	262.8	260.7	259.2	258.3	257.4	256.4	255.5
75°	209.0	207.2	205.4	204.8	205.4	206.0	206.6	207.2
77.5°	158.9	158.1	157.2	156.4	155.5	154.7	153.9	153.1
80°	126.2	125.4	124.5	123.7	123.1	122.6	122.0	121.4
82.5°	94.1	93.0	91.9	91.3	91.1	91.0	90.9	90.7
85°	49.7	48.8	48.0	47.4	47.1	46.8	46.5	46.1
87.5°	17.0	16.5	16.0	15.7	15.5	15.3	15.2	15.0
90°	18.3	19.2	20.1	20.8	21.1	21.4	21.9	22.2
92.5°	20.1	20.5	21.0	21.4	21.5	21.8	22.0	22.2
95°	33.9	34.9	35.7	36.1	35.9	35.7	35.6	35.4
97.5°	44.4	45.1	45.9	46.3	46.6	46.8	47.0	47.2
100°	49.9	51.3	52.8	53.6	54.0	54.4	54.8	55.1
102.5°	52.0	53.9	55.8	57.0	57.5	58.0	58.5	59.1
105°	54.2	56.2	58.2	59.6	60.4	61.0	61.8	62.5
107.5°	66.1	64.1	62.1	61.4	62.2	62.9	63.6	64.3
110°	107.4	89.1	70.9	62.1	62.8	63.5	64.2	65.0



TEST NUMBER: P331601-935

CATALOG NUMBER: S122DIW-S1005D970U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	229.7	163.1	96.3	63.3	63.9	64.5	65.1	65.7
115°	338.3	253.7	169.0	120.1	106.9	93.8	80.6	67.5
117.5°	521.2	500.8	480.4	448.5	405.2	362.0	318.7	275.4
120°	607.4	609.6	611.8	600.5	575.9	551.2	526.5	501.9
122.5°	644.5	645.8	647.1	645.4	640.6	635.8	631.0	626.3
125°	697.8	699.0	700.3	701.2	701.8	702.3	702.8	703.4
127.5°	747.0	748.8	750.7	751.7	751.8	751.9	752.0	752.1
130°	778.2	780.2	782.2	783.2	782.9	782.7	782.6	782.4
132.5°	808.6	810.3	812.0	812.8	812.5	812.4	812.2	812.0
135°	851.9	853.7	855.5	856.3	855.9	855.5	855.1	854.8
137.5°	892.1	893.9	895.7	896.3	895.7	895.0	894.4	893.8
140°	918.2	919.8	921.4	921.8	920.9	920.0	919.0	918.2
142.5°	942.2	943.7	945.2	945.5	944.6	943.7	942.8	941.8
145°	975.9	977.1	978.4	978.6	977.7	976.7	975.9	974.9
147.5°	1005.1	1006.1	1007.0	1007.1	1006.3	1005.6	1004.8	1004.0
150°	1023.2	1024.2	1025.4	1025.5	1024.6	1023.6	1022.7	1021.8
152.5°	1039.7	1040.7	1041.8	1041.8	1040.6	1039.4	1038.2	1037.0
155°	1061.9	1062.9	1064.0	1063.9	1062.4	1060.9	1059.5	1058.0
157.5°	1080.6	1081.8	1083.1	1083.0	1081.5	1080.1	1078.7	1077.3
160°	1091.5	1092.5	1093.6	1093.6	1092.3	1091.0	1089.8	1088.5
162.5°	1101.6	1102.9	1104.1	1104.0	1102.3	1100.8	1099.2	1097.7
165°	1114.0	1115.3	1116.6	1116.6	1115.3	1114.0	1112.8	1111.5
167.5°	1124.4	1125.7	1127.0	1126.8	1125.2	1123.5	1121.9	1120.2
170°	1129.7	1130.9	1132.2	1132.0	1130.4	1128.8	1127.1	1125.5
172.5°	1133.6	1134.9	1136.2	1136.0	1134.4	1132.7	1131.1	1129.5
175°	1137.9	1139.2	1140.5	1140.2	1138.3	1136.5	1134.7	1132.9
177.5°	1138.4	1139.4	1140.4	1140.3	1138.9	1137.6	1136.3	1135.1
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0

(END OF REPORT)