

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331602-935

Luminaire Tested: **S122DIW-S1005D970U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331602-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D970U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6385.0 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331602-935

CATALOG NUMBER: S122DIW-S1005D970U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331602-935

CATALOG NUMBER: S122DIW-S1005D970U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	99	94	91	87	92	88	84	81	75	73	71	64	62	61	53	52	51	46
2	90	83	76	71	83	77	71	67	66	62	58	56	53	51	47	45	43	39
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28	24
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	30	27	24	21
7	59	46	38	33	54	44	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22157	22157	22157
5°	22242	21921	22049
10°	22109	21697	21807
15°	21835	21417	21396
20°	21448	20993	20972
25°	21063	20475	20475
30°	20566	19999	19827
35°	20103	19429	19141
40°	19524	18858	18493
45°	18952	18287	17838
50°	18329	17698	17071
55°	17681	17011	16380
60°	16956	16191	15594
65°	16180	15373	14670
70°	15196	14389	13704
75°	13830	13250	12926
80°	12273	11901	11288
85°	10022	9541	8540



TEST NUMBER: P331602-935

CATALOG NUMBER: S122DIW-S1005D970U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.0	2.0
10°-20°	363.1	5.7
20°-30°	533.7	8.4
30°-40°	619.9	9.7
40°-50°	619.3	9.7
50°-60°	540.0	8.5
60°-70°	399.3	6.3
70°-80°	226.2	3.5
80°-90°	64.9	1.0
90°-100°	65.5	1.0
100°-110°	203.4	3.2
110°-120°	347.6	5.4
120°-130°	457.2	7.2
130°-140°	513.1	8.0
140°-150°	503.1	7.9
150°-160°	422.0	6.6
160°-170°	279.9	4.4
170°-180°	97.8	1.5
0°-30°	1025.8	16.1
0°-40°	1645.7	25.8
0°-60°	2805.0	43.9
0°-90°	3495.4	54.7
90°-120°	616.5	9.7
90°-150°	2089.9	32.7
90°-180°	2890.0	45.3
0°-180°	6385.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1372	1366	1352	1362	1360	130
15°	1306	1298	1281	1286	1280	368
25°	1182	1171	1149	1152	1149	544
35°	1020	1006	986	978	971	637
45°	830	820	801	787	781	640
55°	628	620	604	589	582	561
65°	424	415	402	391	384	419
75°	222	219	212	205	207	237
85°	54	53	52	48	46	62
90°	1	12	30	29	30	5
95°	45	54	56	56	54	52
105°	188	190	192	194	194	198
115°	349	354	352	351	349	345
125°	508	515	513	510	509	453
135°	657	666	668	667	664	507
145°	797	803	808	809	806	498
155°	911	914	916	920	918	419
165°	992	991	991	996	992	280
175°	1032	1029	1027	1033	1028	98
180°	1033	1033	1033	1033	1033	



TEST NUMBER: P331602-935

CATALOG NUMBER: S122DIW-S1005D970U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3
2.5°	1378.6	1377.4	1376.3	1375.1	1373.9	1372.1	1369.5	1366.9	1364.3	1361.8	1364.1
5°	1372.3	1371.1	1369.9	1368.7	1367.6	1365.4	1362.2	1358.9	1355.7	1352.5	1354.9
7.5°	1360.1	1358.3	1356.5	1354.7	1352.9	1350.3	1347.0	1343.8	1340.5	1337.2	1339.5
10°	1348.5	1346.5	1344.5	1342.4	1340.3	1337.6	1334.0	1330.5	1327.0	1323.4	1325.9
12.5°	1332.7	1330.8	1329.0	1327.2	1325.4	1322.8	1319.2	1315.7	1312.3	1308.7	1310.4
15°	1306.3	1304.6	1302.8	1301.1	1299.2	1296.5	1292.7	1288.8	1285.0	1281.3	1282.5
17.5°	1272.6	1270.7	1269.0	1267.2	1265.5	1262.7	1258.8	1254.9	1251.0	1247.2	1248.5
20°	1248.3	1246.5	1244.7	1242.9	1241.2	1238.3	1234.2	1230.1	1226.0	1221.8	1222.7
22.5°	1224.0	1221.5	1219.1	1216.6	1214.1	1211.0	1207.1	1203.2	1199.4	1195.5	1195.7
25°	1182.3	1179.9	1177.6	1175.3	1172.9	1169.2	1164.2	1159.3	1154.3	1149.3	1149.9
27.5°	1134.8	1132.6	1130.6	1128.4	1126.4	1123.3	1119.4	1115.4	1111.6	1107.6	1106.7
30°	1103.1	1100.8	1098.4	1096.1	1093.7	1090.4	1086.0	1081.6	1077.2	1072.7	1071.9
32.5°	1069.4	1067.5	1065.6	1063.7	1061.8	1058.6	1054.0	1049.3	1044.7	1040.0	1038.5
35°	1019.9	1017.0	1014.1	1011.2	1008.2	1004.4	999.7	995.1	990.4	985.7	984.0
37.5°	964.3	961.7	959.2	956.6	954.0	950.4	945.6	941.0	936.3	931.6	929.4
40°	926.3	923.9	921.6	919.3	916.9	913.4	908.7	904.0	899.3	894.7	892.0
42.5°	889.3	887.0	884.7	882.4	879.9	876.4	871.8	867.0	862.4	857.6	854.8
45°	830.0	827.9	825.9	823.8	821.7	818.6	814.2	809.8	805.4	800.9	797.7
47.5°	770.9	769.0	767.0	765.1	763.1	759.8	755.3	750.7	746.1	741.6	738.1
50°	729.7	728.2	726.8	725.3	723.8	721.0	717.0	712.8	708.7	704.6	700.5
52.5°	689.6	687.7	685.7	683.8	681.8	678.9	675.0	671.1	667.4	663.5	660.0
55°	628.1	626.3	624.6	622.8	621.0	618.4	614.9	611.4	607.9	604.3	600.8
57.5°	566.4	564.9	563.5	562.1	560.7	558.1	554.2	550.4	546.5	542.6	539.2
60°	525.1	524.0	522.8	521.7	520.5	517.8	513.8	509.6	505.5	501.4	498.2
62.5°	485.1	483.2	481.3	479.4	477.5	475.0	471.8	468.7	465.5	462.4	459.3
65°	423.5	421.8	420.1	418.3	416.6	414.1	411.2	408.3	405.4	402.4	399.8
67.5°	361.0	359.6	358.2	356.8	355.4	353.4	350.7	348.1	345.4	342.9	340.8
70°	321.9	320.8	319.6	318.5	317.3	315.4	312.7	310.0	307.5	304.8	302.7
72.5°	281.8	280.7	279.5	278.4	277.2	275.7	274.1	272.3	270.6	268.9	266.8
75°	221.7	221.1	220.5	219.9	219.3	218.3	216.8	215.3	213.9	212.4	210.7
77.5°	167.8	166.9	165.8	164.9	163.8	163.1	162.5	161.9	161.3	160.7	159.8
80°	132.0	131.6	131.4	131.0	130.8	130.4	129.8	129.2	128.5	128.0	127.1
82.5°	98.2	98.2	98.1	98.0	97.9	97.7	97.4	97.0	96.7	96.3	95.2
85°	54.1	53.8	53.6	53.2	53.0	52.6	52.3	52.0	51.7	51.5	50.5
87.5°	19.2	19.2	19.2	19.2	19.2	19.4	19.7	20.1	20.5	20.9	20.1
90°	0.9	3.2	5.5	7.8	10.2	13.4	17.7	22.0	26.3	30.5	30.1
92.5°	15.5	17.2	18.9	20.7	22.4	23.7	24.7	25.7	26.7	27.7	27.8
95°	45.4	47.3	49.2	51.1	53.1	54.2	54.7	55.0	55.4	55.8	55.8
97.5°	82.8	84.6	86.3	88.0	89.6	90.9	91.6	92.4	93.1	93.8	93.8
100°	110.7	112.3	113.8	115.4	116.9	118.0	118.6	119.2	119.8	120.4	120.4
102.5°	140.1	141.3	142.5	143.8	145.0	146.0	146.7	147.5	148.2	149.0	149.1
105°	187.5	188.0	188.6	189.2	189.9	190.3	190.7	191.1	191.5	191.8	192.3
107.5°	235.3	236.2	236.9	237.8	238.7	239.1	239.1	239.1	239.1	239.1	239.3
110°	266.0	267.2	268.3	269.5	270.6	271.2	271.2	271.2	271.2	271.2	271.2



TEST NUMBER: P331602-935

CATALOG NUMBER: S122DIW-S1005D970U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	299.5	300.7	301.8	303.0	304.1	304.6	304.4	304.3	304.2	304.0	303.5
115°	348.8	350.0	351.1	352.3	353.4	353.9	353.4	353.1	352.7	352.3	352.1
117.5°	398.0	399.6	401.1	402.7	404.2	404.4	403.4	402.3	401.2	400.1	399.7
120°	430.8	432.4	433.9	435.5	437.0	437.0	435.5	433.9	432.4	430.8	430.8
122.5°	460.8	462.7	464.5	466.4	468.2	468.6	467.5	466.5	465.4	464.3	463.8
125°	507.6	509.3	511.0	512.8	514.5	515.1	514.5	513.9	513.3	512.8	512.2
127.5°	553.1	555.3	557.5	559.7	561.9	562.7	562.0	561.3	560.6	559.9	559.1
130°	581.7	584.2	586.7	589.3	591.8	592.8	592.5	592.0	591.7	591.2	590.9
132.5°	613.7	615.8	617.9	619.9	622.0	623.0	623.1	623.2	623.3	623.4	622.5
135°	656.7	658.8	660.9	663.1	665.2	666.4	666.8	667.2	667.6	668.0	667.8
137.5°	701.8	703.6	705.3	707.1	708.8	710.0	710.4	710.9	711.4	712.0	711.8
140°	729.0	730.8	732.5	734.3	736.0	737.4	738.4	739.3	740.3	741.2	741.2
142.5°	757.0	758.7	760.4	762.2	764.0	765.2	765.8	766.5	767.2	767.8	767.9
145°	797.0	798.4	799.8	801.2	802.5	803.7	804.9	806.1	807.3	808.4	808.6
147.5°	832.8	834.5	836.1	837.7	839.3	840.5	841.3	842.1	842.8	843.6	844.0
150°	857.2	858.4	859.5	860.7	861.9	862.9	863.7	864.4	865.2	866.0	866.5
152.5°	878.9	880.0	881.2	882.4	883.6	884.6	885.5	886.4	887.3	888.3	889.0
155°	911.3	911.9	912.5	913.1	913.6	914.2	914.8	915.4	915.9	916.5	917.5
157.5°	939.0	939.4	939.8	940.2	940.6	941.0	941.3	941.7	942.0	942.4	943.7
160°	955.8	956.1	956.6	956.9	957.3	957.6	957.9	958.0	958.2	958.4	959.6
162.5°	971.1	971.2	971.3	971.4	971.5	971.6	971.8	972.0	972.2	972.3	973.7
165°	991.5	991.4	991.2	990.9	990.8	990.7	990.7	990.7	990.7	990.7	992.0
167.5°	1008.7	1008.1	1007.5	1006.9	1006.3	1006.0	1006.0	1005.9	1005.9	1005.8	1007.2
170°	1017.7	1017.1	1016.6	1016.0	1015.4	1015.0	1014.8	1014.6	1014.4	1014.3	1015.5
172.5°	1024.0	1023.4	1022.8	1022.3	1021.7	1021.2	1021.1	1020.9	1020.7	1020.5	1021.8
175°	1031.7	1031.0	1030.5	1029.9	1029.3	1028.8	1028.5	1028.0	1027.7	1027.3	1028.6
177.5°	1034.8	1034.3	1033.9	1033.4	1032.9	1032.5	1032.3	1031.9	1031.7	1031.3	1032.3
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4



TEST NUMBER: P331602-935

CATALOG NUMBER: S122DIW-S1005D970U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3
2.5°	1366.4	1368.7	1371.1	1372.1	1371.6	1371.1	1370.6	1370.2
5°	1357.2	1359.5	1361.8	1362.8	1362.2	1361.6	1361.0	1360.4
7.5°	1341.9	1344.2	1346.6	1347.5	1346.8	1346.2	1345.5	1344.9
10°	1328.2	1330.5	1332.8	1333.6	1332.7	1331.8	1330.9	1330.1
12.5°	1312.0	1313.6	1315.3	1315.8	1315.1	1314.5	1313.8	1313.2
15°	1283.6	1284.8	1285.9	1285.8	1284.4	1282.9	1281.4	1280.0
17.5°	1249.9	1251.3	1252.6	1252.6	1251.1	1249.7	1248.4	1246.9
20°	1223.7	1224.5	1225.4	1225.2	1224.1	1222.9	1221.8	1220.6
22.5°	1195.8	1196.0	1196.2	1195.9	1195.2	1194.6	1193.8	1193.1
25°	1150.5	1151.1	1151.7	1151.7	1151.1	1150.5	1149.9	1149.3
27.5°	1105.9	1104.9	1104.1	1102.9	1101.6	1100.1	1098.7	1097.3
30°	1071.0	1070.1	1069.3	1068.2	1067.0	1065.8	1064.7	1063.5
32.5°	1036.9	1035.3	1033.7	1032.3	1031.1	1030.0	1028.8	1027.6
35°	982.1	980.4	978.6	977.1	975.6	974.1	972.6	971.1
37.5°	927.2	925.1	922.9	921.1	919.7	918.3	916.9	915.5
40°	889.3	886.7	884.1	882.2	881.0	879.9	878.7	877.4
42.5°	852.0	849.0	846.2	844.0	842.3	840.7	839.0	837.3
45°	794.5	791.3	788.1	785.8	784.6	783.5	782.3	781.2
47.5°	734.8	731.3	728.0	725.4	723.7	722.0	720.3	718.6
50°	696.4	692.3	688.2	685.4	684.0	682.5	681.1	679.6
52.5°	656.7	653.2	649.9	647.2	645.2	643.3	641.4	639.5
55°	597.3	593.7	590.3	587.8	586.3	584.9	583.4	581.9
57.5°	535.6	532.2	528.7	526.4	525.4	524.3	523.1	522.0
60°	495.0	491.7	488.5	486.5	485.6	484.7	483.8	482.9
62.5°	456.4	453.4	450.4	448.3	447.2	446.1	445.0	443.8
65°	397.2	394.5	391.9	389.9	388.4	386.9	385.5	384.0
67.5°	338.7	336.7	334.6	332.9	331.8	330.6	329.5	328.3
70°	300.7	298.7	296.6	295.0	293.8	292.7	291.4	290.3
72.5°	264.8	262.8	260.7	259.2	258.3	257.4	256.4	255.5
75°	209.0	207.2	205.4	204.8	205.4	206.0	206.6	207.2
77.5°	158.9	158.1	157.2	156.4	155.5	154.7	153.9	153.1
80°	126.2	125.4	124.5	123.7	123.1	122.6	122.0	121.4
82.5°	94.1	93.0	91.9	91.3	91.1	91.0	90.9	90.7
85°	49.7	48.8	48.0	47.4	47.1	46.8	46.5	46.1
87.5°	19.3	18.5	17.7	17.3	17.0	16.9	16.7	16.4
90°	29.7	29.4	28.9	28.8	29.1	29.3	29.4	29.6
92.5°	27.9	28.0	28.1	28.1	28.2	28.2	28.2	28.2
95°	55.8	55.8	55.8	55.6	55.2	54.8	54.4	54.1
97.5°	93.8	93.8	93.8	93.8	93.8	93.8	93.7	93.7
100°	120.4	120.4	120.4	120.3	120.0	119.9	119.7	119.5
102.5°	149.3	149.4	149.6	149.6	149.4	149.1	149.0	148.8
105°	192.6	193.0	193.4	193.6	193.6	193.6	193.6	193.6
107.5°	239.4	239.6	239.7	239.4	238.5	237.5	236.7	235.8
110°	271.2	271.2	271.2	271.0	270.4	269.8	269.1	268.6



TEST NUMBER: P331602-935

CATALOG NUMBER: S122DIW-S1005D970U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	303.1	302.6	302.1	301.7	301.3	300.8	300.4	300.0
115°	351.9	351.7	351.5	351.1	350.6	350.0	349.4	348.8
117.5°	399.2	398.7	398.2	397.7	397.2	396.6	396.0	395.4
120°	430.8	430.8	430.8	430.5	429.9	429.4	428.8	428.2
122.5°	463.4	462.9	462.4	462.0	461.6	461.2	460.7	460.3
125°	511.6	511.0	510.5	510.1	509.9	509.7	509.5	509.3
127.5°	558.4	557.8	557.1	556.4	555.8	555.2	554.6	554.0
130°	590.5	590.1	589.7	589.1	588.3	587.5	586.8	586.0
132.5°	621.6	620.8	619.9	619.2	618.6	617.9	617.3	616.7
135°	667.6	667.4	667.2	666.8	666.2	665.6	665.1	664.5
137.5°	711.6	711.5	711.4	710.8	710.1	709.3	708.5	707.7
140°	741.2	741.2	741.2	740.9	740.1	739.3	738.6	737.8
142.5°	768.1	768.3	768.4	768.1	767.3	766.5	765.8	765.0
145°	808.8	809.0	809.2	808.9	808.1	807.4	806.6	805.8
147.5°	844.5	844.9	845.3	845.2	844.5	843.7	843.0	842.2
150°	867.1	867.7	868.3	868.3	867.7	867.1	866.5	866.0
152.5°	889.8	890.5	891.2	891.2	890.5	889.8	889.0	888.3
155°	918.5	919.5	920.4	920.6	920.1	919.5	918.9	918.3
157.5°	945.0	946.3	947.6	947.8	946.9	946.0	945.0	944.1
160°	960.7	961.9	963.0	963.3	962.5	961.7	961.0	960.2
162.5°	975.0	976.3	977.7	977.8	976.9	975.9	975.0	974.1
165°	993.4	994.7	996.1	996.3	995.3	994.4	993.4	992.4
167.5°	1008.6	1010.0	1011.2	1011.4	1010.5	1009.4	1008.4	1007.5
170°	1016.9	1018.3	1019.7	1019.8	1018.6	1017.4	1016.2	1015.1
172.5°	1023.2	1024.6	1025.9	1026.1	1024.8	1023.7	1022.5	1021.4
175°	1030.0	1031.4	1032.7	1032.9	1031.7	1030.5	1029.3	1028.2
177.5°	1033.2	1034.1	1035.0	1035.0	1034.1	1033.2	1032.3	1031.3
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4

(END OF REPORT)