

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331572-940

Luminaire Tested: **S122DIW-S865D970U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331572-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S865D970U940-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6127.7 lumens  
Efficiency: N/A  
Efficacy: 100.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 61.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331572-940

CATALOG NUMBER: S122DIW-S865D970U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331572-940

CATALOG NUMBER: S122DIW-S865D970U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	44	42	41	36
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23	20
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	26	47	36	29	24	31	25	22	27	22	19	22	19	16	14
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19869	19869	19869
5°	19945	19656	19772
10°	19825	19457	19556
15°	19580	19206	19184
20°	19234	18826	18806
25°	18887	18360	18360
30°	18442	17935	17780
35°	18027	17422	17164
40°	17506	16910	16583
45°	16993	16401	15995
50°	16435	15872	15307
55°	15854	15254	14688
60°	15206	14518	13986
65°	14514	13788	13154
70°	13629	12902	12288
75°	12402	11884	11584
80°	11000	10674	10126
85°	8985	8559	7669



TEST NUMBER: P331572-940

CATALOG NUMBER: S122DIW-S865D970U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	115.7	1.9
10°-20°	325.6	5.3
20°-30°	478.6	7.8
30°-40°	555.9	9.1
40°-50°	555.3	9.1
50°-60°	484.3	7.9
60°-70°	358.1	5.8
70°-80°	202.8	3.3
80°-90°	58.8	1.0
90°-100°	67.8	1.1
100°-110°	210.6	3.4
110°-120°	360.0	5.9
120°-130°	473.5	7.7
130°-140°	531.4	8.7
140°-150°	521.1	8.5
150°-160°	437.0	7.1
160°-170°	289.9	4.7
170°-180°	101.3	1.7
0°-30°	919.9	15.0
0°-40°	1475.8	24.1
0°-60°	2515.4	41.0
0°-90°	3135.0	51.2
90°-120°	638.5	10.4
90°-150°	2164.4	35.3
90°-180°	2993.0	48.8
0°-180°	6127.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1231	1231	1231	1231	1231	
5°	1231	1225	1213	1222	1220	117
15°	1171	1164	1149	1153	1148	330
25°	1060	1050	1031	1033	1031	488
35°	915	902	884	877	871	571
45°	744	735	718	706	700	574
55°	563	556	542	528	522	503
65°	380	372	361	350	344	376
75°	199	196	190	184	186	212
85°	48	47	46	43	41	56
90°	1	12	32	30	31	5
95°	47	56	58	58	56	54
105°	194	197	199	200	200	205
115°	361	366	365	364	361	357
125°	526	533	531	528	527	470
135°	680	690	692	691	688	525
145°	826	832	837	838	835	515
155°	944	946	949	953	951	434
165°	1027	1026	1026	1032	1028	289
175°	1068	1066	1064	1070	1065	101
180°	1070	1070	1070	1070	1070	



TEST NUMBER: P331572-940

CATALOG NUMBER: S122DIW-S865D970U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1236.3	1235.2	1234.1	1233.1	1232.1	1230.4	1228.1	1225.7	1223.4	1221.1	1223.2
5°	1230.6	1229.5	1228.5	1227.4	1226.4	1224.4	1221.6	1218.6	1215.8	1212.8	1215.0
7.5°	1219.7	1218.1	1216.5	1214.8	1213.2	1210.9	1207.9	1205.0	1202.0	1199.1	1201.2
10°	1209.2	1207.5	1205.6	1203.7	1201.9	1199.4	1196.2	1193.1	1190.0	1186.8	1188.9
12.5°	1195.1	1193.5	1191.9	1190.2	1188.6	1186.2	1183.0	1179.8	1176.7	1173.6	1175.0
15°	1171.4	1169.8	1168.2	1166.7	1165.1	1162.6	1159.2	1155.7	1152.4	1149.0	1150.0
17.5°	1141.1	1139.5	1138.0	1136.4	1134.8	1132.3	1128.8	1125.3	1121.9	1118.4	1119.6
20°	1119.4	1117.8	1116.2	1114.6	1113.0	1110.4	1106.7	1103.0	1099.4	1095.7	1096.4
22.5°	1097.6	1095.4	1093.1	1090.9	1088.8	1085.9	1082.4	1079.0	1075.5	1072.0	1072.2
25°	1060.2	1058.1	1056.0	1053.9	1051.8	1048.5	1044.0	1039.6	1035.1	1030.6	1031.2
27.5°	1017.6	1015.7	1013.8	1011.9	1010.0	1007.3	1003.8	1000.2	996.8	993.2	992.5
30°	989.2	987.1	985.0	982.9	980.8	977.8	973.8	969.9	965.9	962.0	961.2
32.5°	958.9	957.3	955.6	953.9	952.2	949.2	945.1	940.9	936.8	932.6	931.2
35°	914.6	912.0	909.4	906.8	904.1	900.7	896.5	892.3	888.1	883.9	882.3
37.5°	864.7	862.4	860.1	857.7	855.5	852.2	848.0	843.8	839.5	835.4	833.4
40°	830.6	828.6	826.4	824.3	822.2	819.0	814.8	810.7	806.5	802.3	799.9
42.5°	797.5	795.4	793.3	791.2	789.1	786.0	781.8	777.6	773.3	769.1	766.5
45°	744.2	742.4	740.6	738.8	736.9	734.0	730.0	726.1	722.2	718.3	715.3
47.5°	691.3	689.6	687.8	686.1	684.3	681.4	677.3	673.2	669.1	664.9	661.9
50°	654.3	653.0	651.8	650.4	649.1	646.6	642.9	639.2	635.5	631.9	628.2
52.5°	618.4	616.6	614.9	613.1	611.4	608.9	605.4	601.9	598.4	594.9	591.9
55°	563.2	561.7	560.1	558.5	556.9	554.6	551.4	548.2	545.1	541.9	538.8
57.5°	507.8	506.6	505.3	504.1	502.8	500.4	497.0	493.5	490.0	486.5	483.5
60°	470.9	469.8	468.9	467.8	466.7	464.4	460.7	457.0	453.3	449.6	446.7
62.5°	435.0	433.3	431.6	429.9	428.2	426.0	423.1	420.3	417.4	414.6	412.0
65°	379.9	378.3	376.7	375.1	373.5	371.4	368.8	366.1	363.6	360.9	358.6
67.5°	323.8	322.4	321.2	319.9	318.7	316.9	314.5	312.1	309.8	307.4	305.6
70°	288.7	287.7	286.6	285.5	284.5	282.8	280.4	278.0	275.7	273.3	271.5
72.5°	252.7	251.7	250.7	249.6	248.5	247.3	245.8	244.2	242.6	241.1	239.3
75°	198.8	198.2	197.7	197.2	196.7	195.7	194.5	193.1	191.8	190.5	189.0
77.5°	150.5	149.6	148.7	147.8	147.0	146.2	145.7	145.2	144.6	144.1	143.3
80°	118.3	118.1	117.8	117.5	117.3	116.9	116.4	115.8	115.3	114.8	114.0
82.5°	88.0	88.0	87.9	87.8	87.8	87.7	87.3	87.0	86.7	86.4	85.3
85°	48.5	48.2	48.0	47.7	47.4	47.2	46.9	46.6	46.4	46.2	45.4
87.5°	17.2	17.3	17.3	17.4	17.5	17.7	18.2	18.6	19.1	19.6	18.9
90°	0.9	3.3	5.7	8.1	10.5	13.9	18.4	22.7	27.2	31.6	31.2
92.5°	16.1	17.8	19.6	21.4	23.2	24.5	25.6	26.7	27.6	28.7	28.8
95°	47.0	49.0	51.0	53.0	55.0	56.2	56.6	57.0	57.4	57.8	57.8
97.5°	85.8	87.6	89.3	91.1	92.8	94.2	94.9	95.7	96.4	97.2	97.2
100°	114.7	116.3	117.9	119.5	121.1	122.3	122.8	123.4	124.0	124.7	124.7
102.5°	145.1	146.3	147.6	148.9	150.2	151.2	151.9	152.8	153.5	154.3	154.4
105°	194.2	194.7	195.4	196.0	196.6	197.1	197.5	197.9	198.3	198.7	199.1
107.5°	243.7	244.6	245.4	246.3	247.2	247.6	247.6	247.6	247.6	247.6	247.8
110°	275.4	276.7	277.9	279.1	280.3	280.9	280.9	280.9	280.9	280.9	280.9



TEST NUMBER: P331572-940

CATALOG NUMBER: S122DIW-S865D970U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	310.1	311.4	312.5	313.8	315.0	315.5	315.3	315.1	315.0	314.9	314.3
115°	361.2	362.5	363.6	364.9	366.0	366.5	366.0	365.7	365.2	364.9	364.7
117.5°	412.2	413.8	415.4	417.1	418.7	418.8	417.8	416.6	415.5	414.4	413.9
120°	446.2	447.8	449.4	451.0	452.6	452.6	451.0	449.4	447.8	446.2	446.2
122.5°	477.2	479.2	481.1	483.0	484.9	485.4	484.2	483.1	482.0	480.8	480.4
125°	525.7	527.4	529.2	531.1	532.9	533.5	532.9	532.3	531.6	531.1	530.5
127.5°	572.8	575.1	577.4	579.7	581.9	582.7	582.0	581.3	580.6	579.9	579.1
130°	602.4	605.0	607.6	610.3	612.9	613.9	613.6	613.1	612.8	612.3	612.0
132.5°	635.6	637.8	639.9	642.0	644.2	645.2	645.3	645.4	645.5	645.6	644.7
135°	680.1	682.3	684.5	686.7	688.9	690.2	690.6	691.0	691.4	691.8	691.6
137.5°	726.8	728.7	730.5	732.3	734.1	735.3	735.8	736.3	736.8	737.4	737.2
140°	755.0	756.9	758.7	760.5	762.2	763.7	764.7	765.7	766.7	767.7	767.7
142.5°	784.0	785.8	787.6	789.3	791.2	792.5	793.1	793.8	794.5	795.1	795.3
145°	825.5	826.9	828.3	829.7	831.2	832.4	833.7	834.8	836.1	837.2	837.4
147.5°	862.6	864.2	865.9	867.5	869.2	870.5	871.3	872.1	872.9	873.7	874.1
150°	887.8	889.0	890.2	891.4	892.6	893.7	894.5	895.3	896.1	896.9	897.4
152.5°	910.3	911.4	912.7	913.8	915.1	916.1	917.1	918.0	919.0	920.0	920.7
155°	943.8	944.4	945.0	945.7	946.2	946.8	947.4	948.1	948.6	949.2	950.2
157.5°	972.5	972.9	973.3	973.7	974.1	974.6	974.9	975.3	975.6	976.0	977.3
160°	989.9	990.2	990.7	991.0	991.5	991.8	992.0	992.2	992.4	992.6	993.8
162.5°	1005.8	1005.8	1005.9	1006.0	1006.1	1006.2	1006.5	1006.7	1006.8	1007.0	1008.4
165°	1026.9	1026.7	1026.5	1026.3	1026.1	1026.0	1026.0	1026.0	1026.0	1026.0	1027.4
167.5°	1044.6	1044.0	1043.4	1042.8	1042.2	1041.9	1041.9	1041.8	1041.8	1041.7	1043.1
170°	1054.0	1053.4	1052.8	1052.2	1051.6	1051.2	1051.0	1050.8	1050.6	1050.4	1051.8
172.5°	1060.5	1059.9	1059.3	1058.7	1058.1	1057.7	1057.5	1057.3	1057.1	1056.9	1058.3
175°	1068.4	1067.8	1067.3	1066.7	1066.0	1065.5	1065.1	1064.7	1064.3	1063.9	1065.3
177.5°	1071.7	1071.2	1070.8	1070.2	1069.8	1069.3	1069.1	1068.7	1068.4	1068.1	1069.1
180°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2



TEST NUMBER: P331572-940

CATALOG NUMBER: S122DIW-S865D970U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1225.3	1227.4	1229.5	1230.4	1229.9	1229.5	1229.1	1228.7
5°	1217.0	1219.1	1221.3	1222.0	1221.6	1221.0	1220.5	1219.9
7.5°	1203.3	1205.4	1207.6	1208.3	1207.7	1207.1	1206.6	1205.9
10°	1191.0	1193.1	1195.2	1195.9	1195.1	1194.3	1193.5	1192.8
12.5°	1176.5	1177.9	1179.5	1179.9	1179.3	1178.8	1178.1	1177.6
15°	1151.0	1152.1	1153.2	1153.0	1151.7	1150.4	1149.1	1147.7
17.5°	1120.8	1122.0	1123.3	1123.2	1122.0	1120.7	1119.5	1118.2
20°	1097.3	1098.1	1098.9	1098.7	1097.7	1096.6	1095.6	1094.5
22.5°	1072.4	1072.5	1072.6	1072.5	1071.7	1071.1	1070.5	1069.9
25°	1031.7	1032.2	1032.7	1032.7	1032.2	1031.7	1031.2	1030.6
27.5°	991.7	990.9	990.1	989.1	987.7	986.5	985.3	984.0
30°	960.4	959.7	958.9	957.9	956.9	955.8	954.8	953.7
32.5°	929.8	928.4	926.9	925.7	924.7	923.6	922.6	921.5
35°	880.7	879.1	877.6	876.1	874.9	873.5	872.2	870.8
37.5°	831.5	829.6	827.6	826.0	824.7	823.5	822.2	820.9
40°	797.5	795.1	792.8	791.0	790.1	789.0	787.9	786.8
42.5°	763.9	761.3	758.8	756.8	755.3	753.9	752.3	750.9
45°	712.5	709.5	706.7	704.7	703.6	702.6	701.5	700.5
47.5°	658.9	655.9	652.8	650.5	649.0	647.5	646.0	644.4
50°	624.5	620.8	617.2	614.7	613.3	612.0	610.7	609.4
52.5°	588.8	585.8	582.7	580.3	578.6	576.8	575.2	573.4
55°	535.7	532.4	529.3	527.1	525.8	524.4	523.2	521.8
57.5°	480.4	477.2	474.1	472.1	471.1	470.1	469.1	468.1
60°	443.9	441.0	438.1	436.2	435.4	434.6	433.8	433.1
62.5°	409.2	406.5	403.9	402.1	401.0	400.0	399.0	398.1
65°	356.1	353.8	351.4	349.6	348.3	347.0	345.6	344.3
67.5°	303.7	301.8	300.1	298.6	297.6	296.5	295.4	294.4
70°	269.7	267.8	266.0	264.5	263.5	262.4	261.4	260.3
72.5°	237.5	235.6	233.8	232.5	231.6	230.8	229.9	229.1
75°	187.3	185.7	184.2	183.7	184.2	184.8	185.2	185.7
77.5°	142.6	141.8	141.0	140.2	139.5	138.8	138.0	137.2
80°	113.2	112.4	111.6	110.9	110.4	109.9	109.4	108.9
82.5°	84.4	83.4	82.4	81.9	81.7	81.6	81.5	81.4
85°	44.6	43.8	43.0	42.4	42.2	41.9	41.6	41.4
87.5°	18.2	17.5	16.8	16.3	16.1	16.0	15.8	15.6
90°	30.8	30.4	30.0	29.9	30.1	30.3	30.5	30.7
92.5°	28.9	29.0	29.1	29.1	29.2	29.2	29.2	29.2
95°	57.8	57.8	57.8	57.6	57.2	56.8	56.4	56.0
97.5°	97.2	97.2	97.2	97.2	97.1	97.1	97.0	97.0
100°	124.7	124.7	124.7	124.6	124.3	124.1	123.9	123.8
102.5°	154.6	154.7	154.9	154.9	154.7	154.4	154.3	154.1
105°	199.5	199.9	200.3	200.5	200.5	200.5	200.5	200.5
107.5°	248.0	248.2	248.3	247.9	247.0	246.0	245.1	244.2
110°	280.9	280.9	280.9	280.6	280.0	279.4	278.7	278.2





TEST NUMBER: P331572-940

CATALOG NUMBER: S122DIW-S865D970U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	313.9	313.4	312.9	312.5	312.0	311.6	311.1	310.7
115°	364.4	364.3	364.1	363.6	363.1	362.5	361.9	361.2
117.5°	413.4	413.0	412.4	411.9	411.3	410.7	410.1	409.5
120°	446.2	446.2	446.2	445.9	445.2	444.7	444.1	443.4
122.5°	479.9	479.4	478.9	478.5	478.0	477.6	477.2	476.7
125°	529.9	529.2	528.7	528.2	528.1	527.9	527.6	527.4
127.5°	578.4	577.7	576.9	576.2	575.6	575.0	574.4	573.7
130°	611.5	611.2	610.7	610.1	609.3	608.5	607.7	606.9
132.5°	643.8	642.9	642.0	641.3	640.7	640.0	639.4	638.7
135°	691.4	691.3	691.0	690.6	690.0	689.4	688.8	688.2
137.5°	737.0	736.9	736.7	736.2	735.4	734.6	733.8	733.0
140°	767.7	767.7	767.7	767.3	766.5	765.7	764.9	764.1
142.5°	795.5	795.7	795.8	795.5	794.7	793.9	793.1	792.3
145°	837.7	837.9	838.0	837.8	837.0	836.2	835.4	834.6
147.5°	874.6	875.0	875.5	875.3	874.6	873.8	873.1	872.3
150°	898.0	898.7	899.3	899.3	898.7	898.0	897.4	896.9
152.5°	921.5	922.3	923.0	923.0	922.3	921.5	920.7	920.0
155°	951.3	952.3	953.2	953.4	952.9	952.3	951.6	951.0
157.5°	978.7	980.1	981.4	981.6	980.7	979.7	978.7	977.8
160°	995.0	996.2	997.4	997.6	996.8	996.0	995.2	994.4
162.5°	1009.8	1011.1	1012.5	1012.7	1011.7	1010.8	1009.8	1008.9
165°	1028.9	1030.2	1031.6	1031.8	1030.8	1029.8	1028.9	1027.8
167.5°	1044.6	1046.0	1047.3	1047.5	1046.5	1045.4	1044.4	1043.4
170°	1053.2	1054.6	1056.1	1056.1	1054.9	1053.7	1052.5	1051.3
172.5°	1059.7	1061.1	1062.5	1062.7	1061.4	1060.2	1059.0	1057.8
175°	1066.8	1068.2	1069.5	1069.7	1068.4	1067.3	1066.0	1064.9
177.5°	1070.1	1070.9	1071.9	1071.9	1070.9	1070.1	1069.1	1068.1
180°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2

(END OF REPORT)