

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331862-940

Luminaire Tested: **S122RDIW-S1005D1440U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331862-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D1440U940-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7859.4 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331862-940

CATALOG NUMBER: S122RDIW-S1005D1440U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331862-940

CATALOG NUMBER: S122RDIW-S1005D1440U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	97	93	89	86	89	85	82	79	71	69	67	57	56	55	45	44	43	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	81	73	66	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29
4	75	65	57	52	68	60	53	48	50	46	42	41	38	35	33	31	29	25
5	69	58	50	45	63	54	47	42	45	40	36	38	34	31	30	28	26	23
6	64	52	45	39	58	49	42	37	41	36	32	34	31	28	28	25	23	20
7	59	48	40	35	54	44	37	33	38	32	29	31	28	25	26	23	21	18
8	55	43	36	31	51	40	34	29	34	29	26	29	25	22	24	21	19	17
9	51	40	33	28	47	37	31	26	32	27	23	27	23	20	22	19	17	15
10	48	37	30	25	44	34	28	24	29	25	21	25	21	19	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	31752	31752	31752	31752
5°	35462	31951	28329	31951
10°	39346	31727	24556	31727
15°	41279	31263	19348	31263
20°	35787	30574	16744	30574
25°	23469	29630	14949	29630
30°	15797	28486	13530	28486
35°	12796	27045	12203	27045
40°	11377	25478	11291	25478
45°	10298	23640	10079	23640
50°	9372	21815	9339	21815
55°	8811	19792	8695	19792
60°	7369	17938	7282	17938
65°	6212	16290	7049	16290
70°	5740	14549	6647	14549
75°	5371	12664	6138	12664
80°	4956	10423	5467	10423
85°	4557	8225	4798	8225



TEST NUMBER: P331862-940

CATALOG NUMBER: S122RDIW-S1005D1440U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.4	2.4
10°-20°	519.5	6.6
20°-30°	669.4	8.5
30°-40°	636.1	8.1
40°-50°	544.9	6.9
50°-60°	415.0	5.3
60°-70°	262.3	3.3
70°-80°	131.0	1.7
80°-90°	40.5	0.5
90°-100°	100.9	1.3
100°-110°	313.5	4.0
110°-120°	535.9	6.8
120°-130°	704.7	9.0
130°-140°	791.0	10.1
140°-150°	775.6	9.9
150°-160°	650.5	8.3
160°-170°	431.5	5.5
170°-180°	150.8	1.9
0°-30°	1375.3	17.5
0°-40°	2011.4	25.6
0°-60°	2971.3	37.8
0°-90°	3405.1	43.3
90°-120°	950.3	12.1
90°-150°	3221.6	41.0
90°-180°	4454.0	56.7
0°-180°	7859.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1967	1967	1967	1967	1967	
5°	2188	1971	1748	1971	2188	216
15°	2470	1870	1158	1870	2470	666
25°	1317	1663	839	1663	1317	625
35°	649	1372	619	1372	649	415
45°	451	1035	441	1035	451	349
55°	313	703	309	703	313	275
65°	163	426	184	426	163	166
75°	86	203	98	203	86	91
85°	25	44	26	44	25	28
90°	46	1	46	1	46	21
95°	83	70	83	70	83	93
105°	298	289	298	289	298	314
115°	538	538	538	538	538	531
125°	785	782	785	782	785	700
135°	1024	1012	1024	1012	1024	789
145°	1242	1229	1242	1229	1242	776
155°	1416	1405	1416	1405	1416	651
165°	1530	1528	1530	1528	1530	431
175°	1585	1590	1585	1590	1585	151
180°	1593	1593	1593	1593	1593	



TEST NUMBER: P331862-940

CATALOG NUMBER: S122RDIW-S1005D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	2046.4	2048.1	2049.7	2045.9	2045.9	2042.6	2035.5	2030.0	2014.7	2012.5	2012.5
5°	2188.0	2186.7	2189.3	2180.5	2168.2	2165.4	2152.5	2135.4	2117.6	2097.8	2093.7
7.5°	2328.8	2326.7	2321.2	2319.8	2310.3	2289.6	2268.8	2246.5	2217.0	2188.2	2173.6
10°	2399.9	2422.4	2408.7	2384.8	2389.6	2357.5	2340.4	2311.0	2286.4	2243.4	2233.8
12.5°	2469.8	2478.7	2474.3	2460.8	2454.6	2432.3	2409.2	2383.7	2338.3	2299.6	2266.0
15°	2469.5	2482.5	2485.9	2481.8	2485.3	2483.9	2471.6	2450.4	2410.7	2368.4	2331.5
17.5°	2287.2	2296.2	2318.6	2333.8	2353.0	2393.4	2413.3	2421.2	2415.3	2391.1	2365.1
20°	2082.8	2067.7	2130.6	2162.8	2190.0	2258.3	2317.1	2339.7	2375.9	2375.3	2368.4
22.5°	1793.1	1796.6	1856.2	1894.4	1974.2	2042.5	2109.4	2194.3	2264.4	2310.7	2337.8
25°	1317.4	1343.5	1402.8	1454.8	1543.6	1670.7	1786.2	1920.1	2046.6	2146.3	2241.3
27.5°	989.4	991.4	1038.5	1086.5	1139.2	1243.4	1388.8	1548.7	1728.9	1877.7	2048.7
30°	847.3	843.2	863.0	892.4	937.5	1018.2	1127.5	1284.7	1464.4	1688.5	1888.0
32.5°	746.7	747.0	761.9	783.6	821.1	875.5	950.4	1078.0	1247.9	1468.2	1702.2
35°	649.2	648.5	659.4	675.1	690.8	725.7	776.9	843.9	960.7	1166.4	1405.6
37.5°	579.2	582.2	587.5	597.4	614.7	634.1	664.9	709.8	793.1	914.7	1115.7
40°	539.8	541.2	548.7	556.9	567.1	582.2	607.4	643.7	704.5	801.6	948.4
42.5°	503.7	505.2	510.4	518.1	526.2	541.2	562.1	593.4	642.7	718.5	839.6
45°	451.0	451.0	455.8	459.2	468.1	481.7	498.8	524.8	558.9	615.0	695.6
47.5°	401.5	401.6	404.8	410.7	416.3	427.0	443.7	464.9	489.8	533.2	602.0
50°	373.1	373.8	375.9	380.6	384.1	393.6	406.6	425.0	451.0	484.5	541.9
52.5°	350.2	349.7	352.3	354.4	356.7	363.6	373.3	389.5	412.7	441.8	489.4
55°	313.0	310.2	314.3	317.7	319.8	322.5	328.0	338.2	358.0	382.6	418.2
57.5°	266.5	265.4	268.3	271.4	277.9	285.3	289.9	296.4	306.7	324.3	359.5
60°	228.2	228.2	234.3	236.4	244.0	253.5	263.1	268.6	278.8	290.4	316.4
62.5°	194.3	194.9	197.8	199.8	204.0	215.8	229.2	241.2	250.9	262.0	279.2
65°	162.6	164.0	164.0	165.3	168.1	170.9	176.3	185.8	203.0	218.6	231.7
67.5°	138.0	138.5	138.8	140.2	140.9	143.9	146.1	150.3	154.3	169.2	185.3
70°	121.6	123.7	123.0	124.4	125.0	126.4	129.1	131.2	137.3	140.8	150.3
72.5°	106.3	107.8	107.7	108.5	110.3	110.6	112.7	114.8	118.8	121.6	126.8
75°	86.1	85.4	86.1	87.5	88.2	88.8	88.8	91.6	93.6	96.3	99.8
77.5°	66.4	67.1	67.0	67.1	67.2	68.5	68.3	69.6	71.6	72.9	74.6
80°	53.3	53.9	53.3	53.9	54.7	55.4	54.7	55.4	57.4	58.8	58.8
82.5°	41.3	41.4	41.8	42.0	42.1	42.3	43.2	43.3	44.9	44.6	45.1
85°	24.6	23.9	23.9	23.9	24.6	25.3	24.6	24.6	25.3	25.3	25.3
87.5°	17.9	18.4	18.3	18.3	18.2	18.2	18.4	19.0	18.5	19.3	17.4
90°	45.7	45.4	45.1	44.9	44.5	44.7	45.3	45.8	46.5	47.1	40.5
92.5°	43.5	43.5	43.4	43.3	43.3	43.2	43.1	43.0	42.9	42.7	41.2
95°	83.4	83.9	84.5	85.2	85.7	86.1	86.1	86.1	86.1	86.1	85.4
97.5°	144.4	144.5	144.5	144.5	144.6	144.6	144.6	144.6	144.6	144.6	143.5
100°	184.1	184.5	184.8	185.0	185.4	185.5	185.5	185.5	185.5	185.5	184.6
102.5°	229.3	229.6	230.0	230.2	230.5	230.6	230.3	230.1	229.9	229.6	228.5
105°	298.5	298.5	298.5	298.5	298.5	298.1	297.6	296.9	296.3	295.8	295.2
107.5°	363.5	364.9	366.2	367.7	369.0	369.5	369.3	369.1	368.8	368.6	368.6
110°	414.0	414.9	415.8	416.7	417.6	418.1	418.1	418.1	418.1	418.1	418.1



TEST NUMBER: P331862-940

CATALOG NUMBER: S122RDIW-S1005D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	462.4	463.1	463.8	464.4	465.0	465.7	466.5	467.2	467.9	468.6	468.9
115°	537.7	538.6	539.5	540.4	541.3	541.9	542.2	542.5	542.8	543.1	543.7
117.5°	609.5	610.4	611.3	612.2	613.1	613.9	614.7	615.4	616.1	616.8	618.4
120°	660.0	660.9	661.8	662.7	663.6	664.1	664.1	664.1	664.1	664.1	666.5
122.5°	709.5	710.2	710.9	711.5	712.1	712.8	713.5	714.3	715.0	715.7	717.4
125°	785.1	785.4	785.7	786.0	786.3	786.8	787.7	788.6	789.5	790.4	791.4
127.5°	853.9	854.9	855.8	856.8	857.7	858.7	859.8	860.9	861.9	863.1	864.2
130°	903.4	904.6	905.8	907.0	908.1	909.0	909.6	910.3	910.9	911.4	912.0
132.5°	950.7	951.6	952.6	953.6	954.5	955.6	957.0	958.3	959.6	960.9	960.8
135°	1024.4	1025.3	1026.2	1027.1	1028.0	1028.6	1028.9	1029.1	1029.5	1029.7	1029.1
137.5°	1091.0	1092.3	1093.4	1094.7	1095.8	1096.5	1096.8	1097.0	1097.3	1097.5	1096.7
140°	1137.3	1138.4	1139.7	1140.9	1142.1	1142.6	1142.6	1142.6	1142.6	1142.6	1141.2
142.5°	1179.2	1180.4	1181.6	1182.9	1184.0	1184.5	1184.3	1184.0	1183.7	1183.6	1182.5
145°	1242.2	1243.3	1244.6	1245.7	1246.9	1247.3	1247.1	1246.8	1246.4	1246.2	1244.4
147.5°	1298.3	1299.5	1300.6	1301.7	1302.9	1303.1	1302.4	1301.8	1301.2	1300.5	1299.3
150°	1334.9	1335.8	1336.7	1337.6	1338.5	1338.5	1337.6	1336.7	1335.8	1334.9	1333.7
152.5°	1369.3	1370.5	1371.5	1372.7	1373.9	1373.9	1372.7	1371.5	1370.5	1369.3	1367.9
155°	1415.6	1416.5	1417.4	1418.3	1419.2	1418.8	1417.4	1415.9	1414.3	1412.8	1411.9
157.5°	1455.4	1456.8	1458.2	1459.6	1461.1	1460.8	1458.7	1456.7	1454.6	1452.7	1452.2
160°	1480.1	1481.3	1482.5	1483.6	1484.9	1484.5	1482.7	1481.0	1479.2	1477.4	1477.1
162.5°	1501.6	1503.1	1504.5	1505.9	1507.3	1507.0	1505.0	1503.0	1500.9	1498.9	1498.6
165°	1529.8	1531.3	1532.9	1534.3	1535.8	1535.5	1533.4	1531.3	1529.2	1527.1	1527.1
167.5°	1552.9	1554.5	1556.0	1557.6	1559.2	1558.9	1556.8	1554.7	1552.6	1550.5	1550.6
170°	1564.8	1566.6	1568.3	1570.1	1571.9	1571.8	1569.7	1567.6	1565.5	1563.4	1563.7
172.5°	1574.5	1576.3	1578.1	1579.8	1581.6	1581.4	1579.4	1577.3	1575.2	1573.1	1573.4
175°	1584.9	1586.7	1588.5	1590.3	1592.1	1592.0	1589.8	1587.8	1585.7	1583.6	1584.2
177.5°	1589.7	1591.2	1592.7	1594.1	1595.5	1595.5	1594.1	1592.7	1591.2	1589.7	1590.3
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331862-940

CATALOG NUMBER: S122RDIW-S1005D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	2013.7	2009.2	2005.5	1995.6	1990.7	1979.7	1978.1	1977.5	1963.4	1949.6	1945.8
5°	2082.8	2071.8	2055.5	2036.3	2016.5	1996.0	1982.4	1971.4	1944.0	1918.1	1903.1
7.5°	2152.5	2129.0	2100.7	2064.5	2034.3	2000.4	1975.2	1952.7	1913.9	1876.7	1851.6
10°	2204.4	2166.1	2128.5	2078.7	2039.7	2001.4	1966.0	1935.2	1891.4	1842.3	1807.4
12.5°	2236.7	2194.6	2142.8	2094.0	2043.5	1994.9	1947.3	1907.8	1856.5	1805.6	1764.2
15°	2280.3	2235.2	2172.3	2102.6	2037.6	1974.2	1919.5	1870.3	1803.3	1742.5	1691.9
17.5°	2316.0	2253.9	2186.4	2105.8	2030.6	1949.8	1879.5	1816.6	1742.0	1668.7	1609.1
20°	2327.4	2265.9	2188.0	2107.4	2018.6	1923.6	1847.7	1779.4	1699.4	1619.4	1551.1
22.5°	2320.3	2272.4	2185.9	2089.4	1998.3	1899.0	1813.3	1734.0	1645.3	1563.7	1484.4
25°	2272.1	2255.7	2173.6	2068.4	1964.5	1849.1	1750.0	1663.2	1562.1	1474.6	1388.5
27.5°	2159.5	2194.9	2144.1	2032.0	1916.6	1792.8	1681.4	1582.6	1477.7	1379.2	1293.4
30°	2051.4	2132.6	2110.8	2006.9	1877.8	1756.1	1631.1	1527.9	1415.9	1314.7	1230.0
32.5°	1903.2	2037.6	2058.9	1971.9	1838.4	1704.8	1573.7	1471.1	1354.1	1247.5	1164.9
35°	1667.3	1868.2	1960.4	1905.1	1771.2	1627.0	1491.7	1372.1	1254.5	1149.3	1067.4
37.5°	1385.9	1659.6	1813.3	1817.2	1694.3	1544.4	1397.0	1278.3	1158.0	1054.6	966.0
40°	1203.4	1499.9	1700.1	1744.5	1640.7	1478.7	1329.7	1208.8	1091.3	990.2	888.3
42.5°	1039.4	1334.8	1580.9	1658.1	1575.7	1414.8	1265.2	1138.8	1024.6	928.9	824.9
45°	840.5	1098.8	1370.0	1508.1	1462.3	1313.3	1155.5	1035.3	927.9	845.3	745.5
47.5°	709.0	891.1	1153.6	1340.2	1339.4	1203.5	1048.2	933.0	833.5	756.0	675.3
50°	634.1	792.6	1014.8	1226.5	1244.3	1130.2	982.6	868.5	775.6	694.3	629.4
52.5°	566.9	697.5	897.2	1100.3	1150.8	1052.0	908.8	803.4	713.3	638.5	582.9
55°	479.0	580.1	731.8	921.8	998.4	928.6	801.6	703.1	630.0	567.1	519.3
57.5°	405.2	481.1	602.8	755.7	844.9	801.0	696.2	616.3	553.7	496.8	459.1
60°	358.7	420.9	524.1	651.9	750.3	719.5	630.0	555.5	502.2	453.1	417.5
62.5°	315.0	368.5	456.9	560.6	650.8	638.1	565.0	502.5	455.8	411.0	380.8
65°	253.5	292.5	361.5	442.8	515.2	521.4	468.8	426.4	384.7	349.2	322.5
67.5°	201.9	227.3	275.9	344.4	398.7	418.0	385.9	353.6	320.5	293.0	269.9
70°	170.1	190.6	226.1	281.5	331.4	351.9	333.5	308.2	279.5	256.9	237.1
72.5°	137.9	157.8	184.0	224.7	267.4	289.6	283.2	265.0	241.7	223.0	204.3
75°	103.9	110.0	127.8	155.2	188.6	207.8	212.5	203.0	184.5	170.1	159.2
77.5°	76.8	80.5	89.0	103.3	125.2	142.2	149.3	148.1	135.5	127.1	116.8
80°	61.5	63.6	67.7	73.8	90.2	107.3	112.1	112.1	103.2	99.8	89.5
82.5°	46.7	48.2	50.7	54.1	61.8	76.7	82.0	83.1	77.5	72.9	64.9
85°	26.7	25.9	27.4	29.4	30.8	34.9	43.1	44.4	43.1	37.5	35.5
87.5°	16.1	15.3	14.0	12.4	12.2	12.1	14.1	16.1	14.6	13.7	13.4
90°	33.9	27.4	20.8	15.7	12.1	8.5	4.9	1.3	4.9	8.5	12.1
92.5°	39.7	38.1	36.6	34.4	31.8	29.2	26.6	23.9	26.6	29.2	31.8
95°	84.8	84.3	83.6	81.9	78.8	75.9	72.9	69.9	72.9	75.9	78.8
97.5°	142.4	141.2	140.1	138.2	135.6	133.0	130.4	127.7	130.4	133.0	135.6
100°	183.7	182.8	181.9	180.3	177.9	175.5	173.1	170.8	173.1	175.5	177.9
102.5°	227.3	226.2	225.1	223.6	221.6	219.7	217.8	215.9	217.8	219.7	221.6
105°	294.5	294.0	293.4	292.6	291.7	290.8	289.9	289.0	289.9	290.8	291.7
107.5°	368.6	368.6	368.6	367.9	366.7	365.3	364.0	362.7	364.0	365.3	366.7
110°	418.1	418.1	418.1	417.1	415.4	413.6	411.8	410.0	411.8	413.6	415.4



TEST NUMBER: P331862-940

CATALOG NUMBER: S122RDIW-S1005D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	469.1	469.3	469.6	468.8	467.0	465.2	463.4	461.6	463.4	465.2	467.0
115°	544.3	544.9	545.5	544.9	543.1	541.3	539.5	537.7	539.5	541.3	543.1
117.5°	620.1	621.8	623.5	623.1	620.7	618.3	615.9	613.6	615.9	618.3	620.7
120°	668.9	671.3	673.7	673.7	671.3	668.9	666.5	664.1	666.5	668.9	671.3
122.5°	719.1	720.8	722.4	721.8	718.9	716.0	713.2	710.3	713.2	716.0	718.9
125°	792.3	793.2	794.1	793.2	790.4	787.7	785.1	782.4	785.1	787.7	790.4
127.5°	865.2	866.3	867.4	866.2	862.8	859.3	856.0	852.6	856.0	859.3	862.8
130°	912.7	913.2	913.8	912.2	908.3	904.5	900.5	896.6	900.5	904.5	908.3
132.5°	960.6	960.6	960.5	958.8	955.6	952.4	949.3	946.1	949.3	952.4	955.6
135°	1028.6	1028.0	1027.3	1025.4	1022.1	1018.9	1015.6	1012.3	1015.6	1018.9	1022.1
137.5°	1095.9	1095.2	1094.4	1092.6	1089.9	1087.3	1084.6	1081.9	1084.6	1087.3	1089.9
140°	1139.7	1138.2	1136.7	1134.6	1131.9	1129.3	1126.5	1123.8	1126.5	1129.3	1131.9
142.5°	1181.5	1180.4	1179.5	1177.6	1174.9	1172.2	1169.6	1166.9	1169.6	1172.2	1174.9
145°	1242.6	1240.8	1239.0	1237.1	1234.9	1232.9	1230.8	1228.7	1230.8	1232.9	1234.9
147.5°	1298.1	1296.9	1295.7	1293.9	1291.4	1288.8	1286.3	1283.8	1286.3	1288.8	1291.4
150°	1332.5	1331.3	1330.1	1328.6	1326.9	1325.1	1323.2	1321.4	1323.2	1325.1	1326.9
152.5°	1366.5	1365.0	1363.6	1362.0	1360.1	1358.3	1356.6	1354.8	1356.6	1358.3	1360.1
155°	1411.0	1410.2	1409.3	1408.4	1407.5	1406.6	1405.7	1404.8	1405.7	1406.6	1407.5
157.5°	1451.6	1451.1	1450.5	1449.9	1449.4	1448.8	1448.1	1447.5	1448.1	1448.8	1449.4
160°	1476.8	1476.5	1476.2	1475.8	1475.2	1474.5	1474.0	1473.4	1474.0	1474.5	1475.2
162.5°	1498.3	1498.0	1497.7	1497.5	1497.4	1497.3	1497.2	1497.0	1497.2	1497.3	1497.4
165°	1527.1	1527.1	1527.1	1527.3	1527.6	1527.9	1528.2	1528.5	1528.2	1527.9	1527.6
167.5°	1550.7	1550.7	1550.8	1551.2	1552.1	1553.0	1553.9	1554.8	1553.9	1553.0	1552.1
170°	1564.1	1564.3	1564.6	1565.2	1566.1	1567.0	1567.9	1568.8	1567.9	1567.0	1566.1
172.5°	1573.7	1574.0	1574.3	1574.9	1575.8	1576.7	1577.6	1578.5	1577.6	1576.7	1575.8
175°	1584.7	1585.4	1586.0	1586.7	1587.6	1588.5	1589.4	1590.3	1589.4	1588.5	1587.6
177.5°	1590.7	1591.2	1591.7	1592.3	1593.0	1593.8	1594.5	1595.2	1594.5	1593.8	1593.0
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331862-940

CATALOG NUMBER: S122RDIW-S1005D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	1938.8	1934.9	1927.8	1916.8	1910.3	1898.8	1891.1	1895.5	1896.7	1895.5	1894.4
5°	1886.7	1872.3	1852.5	1833.4	1815.6	1796.4	1785.6	1780.7	1771.2	1765.7	1763.0
7.5°	1823.6	1798.9	1770.9	1737.6	1709.2	1679.6	1664.5	1656.9	1637.4	1626.7	1617.4
10°	1776.6	1737.7	1709.7	1666.0	1639.3	1600.4	1573.7	1574.4	1547.7	1532.7	1521.8
12.5°	1724.7	1681.9	1635.3	1596.0	1559.0	1527.7	1495.5	1482.6	1454.3	1439.8	1410.2
15°	1638.6	1588.8	1539.5	1486.2	1448.7	1400.2	1353.7	1297.0	1251.2	1211.6	1200.6
17.5°	1544.6	1482.8	1433.5	1370.9	1306.5	1224.9	1171.1	1138.2	1110.5	1089.7	1074.1
20°	1480.1	1417.2	1364.6	1270.3	1183.5	1128.2	1088.5	1063.3	1034.6	1012.0	999.7
22.5°	1412.3	1346.7	1275.0	1169.7	1102.1	1057.7	1022.3	993.3	973.8	956.3	945.0
25°	1316.1	1244.3	1126.1	1053.6	999.0	952.5	927.9	910.2	889.7	865.8	854.9
27.5°	1214.4	1100.3	1015.4	961.5	909.4	879.1	857.0	830.5	812.2	801.4	790.1
30°	1138.4	1024.3	958.1	899.3	862.4	828.8	802.9	787.9	770.1	751.6	744.1
32.5°	1053.6	962.5	899.0	850.1	812.6	784.1	763.6	739.2	726.4	715.1	699.3
35°	948.4	879.4	821.4	781.8	746.2	723.0	699.0	684.7	661.5	651.9	645.8
37.5°	859.3	799.5	756.2	714.3	686.2	660.5	645.9	623.0	613.0	599.7	586.7
40°	809.0	750.3	708.6	674.4	643.0	623.8	605.4	587.0	571.9	565.8	550.1
42.5°	757.7	709.8	668.2	630.7	609.7	589.4	566.1	552.5	537.0	527.0	517.3
45°	686.7	644.4	608.9	578.1	554.8	533.7	518.6	496.1	487.2	467.4	459.2
47.5°	624.5	585.1	551.2	521.9	499.3	485.4	463.4	445.8	431.6	419.5	408.9
50°	580.1	547.3	514.5	488.6	468.1	448.3	425.7	416.8	394.9	388.8	382.6
52.5°	539.7	508.5	478.5	453.1	432.6	413.3	393.4	381.8	367.1	361.0	356.4
55°	483.1	453.1	424.4	401.8	381.3	361.5	349.2	334.8	328.0	323.2	317.7
57.5°	426.2	399.2	377.2	354.4	333.8	318.0	303.8	295.2	288.1	281.8	275.3
60°	390.2	364.2	344.4	323.2	302.0	289.0	278.1	267.9	259.7	250.1	247.4
62.5°	351.9	329.2	311.0	290.4	272.0	260.1	249.7	240.0	230.2	216.2	212.4
65°	299.3	281.5	262.4	245.3	228.9	217.3	202.2	191.4	187.3	185.8	185.2
67.5°	251.7	235.0	218.6	201.0	186.1	175.3	167.7	166.0	163.2	162.4	160.4
70°	220.1	204.3	187.9	171.5	157.2	155.2	152.4	149.6	146.2	144.9	143.5
72.5°	191.6	175.3	158.9	145.8	139.6	137.1	134.4	131.6	129.3	128.0	127.1
75°	147.0	131.9	120.9	116.2	112.7	110.7	106.6	104.5	103.2	101.1	100.4
77.5°	105.8	97.3	92.3	89.3	85.7	83.5	81.1	79.1	77.7	77.2	76.2
80°	80.6	76.5	73.1	69.0	67.7	64.9	64.2	62.2	62.9	60.8	60.8
82.5°	62.6	57.4	54.6	52.6	51.3	49.0	48.4	47.4	47.5	46.0	46.0
85°	32.1	30.8	29.4	28.0	28.0	25.9	26.7	25.9	25.9	24.6	23.9
87.5°	13.6	14.0	14.2	15.5	16.9	17.6	17.5	16.9	16.7	16.6	16.1
90°	15.7	20.8	27.4	33.9	40.5	47.1	46.5	45.8	45.3	44.7	44.5
92.5°	34.4	36.6	38.1	39.7	41.2	42.7	42.9	43.0	43.1	43.2	43.3
95°	81.9	83.6	84.3	84.8	85.4	86.1	86.1	86.1	86.1	86.1	85.7
97.5°	138.2	140.1	141.2	142.4	143.5	144.6	144.6	144.6	144.6	144.6	144.6
100°	180.3	181.9	182.8	183.7	184.6	185.5	185.5	185.5	185.5	185.5	185.4
102.5°	223.6	225.1	226.2	227.3	228.5	229.6	229.9	230.1	230.3	230.6	230.5
105°	292.6	293.4	294.0	294.5	295.2	295.8	296.3	296.9	297.6	298.1	298.5
107.5°	367.9	368.6	368.6	368.6	368.6	368.6	368.8	369.1	369.3	369.5	369.0
110°	417.1	418.1	418.1	418.1	418.1	418.1	418.1	418.1	418.1	418.1	417.6



TEST NUMBER: P331862-940

CATALOG NUMBER: S122RDIW-S1005D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	468.8	469.6	469.3	469.1	468.9	468.6	467.9	467.2	466.5	465.7	465.0
115°	544.9	545.5	544.9	544.3	543.7	543.1	542.8	542.5	542.2	541.9	541.3
117.5°	623.1	623.5	621.8	620.1	618.4	616.8	616.1	615.4	614.7	613.9	613.1
120°	673.7	673.7	671.3	668.9	666.5	664.1	664.1	664.1	664.1	664.1	663.6
122.5°	721.8	722.4	720.8	719.1	717.4	715.7	715.0	714.3	713.5	712.8	712.1
125°	793.2	794.1	793.2	792.3	791.4	790.4	789.5	788.6	787.7	786.8	786.3
127.5°	866.2	867.4	866.3	865.2	864.2	863.1	861.9	860.9	859.8	858.7	857.7
130°	912.2	913.8	913.2	912.7	912.0	911.4	910.9	910.3	909.6	909.0	908.1
132.5°	958.8	960.5	960.6	960.6	960.8	960.9	959.6	958.3	957.0	955.6	954.5
135°	1025.4	1027.3	1028.0	1028.6	1029.1	1029.7	1029.5	1029.1	1028.9	1028.6	1028.0
137.5°	1092.6	1094.4	1095.2	1095.9	1096.7	1097.5	1097.3	1097.0	1096.8	1096.5	1095.8
140°	1134.6	1136.7	1138.2	1139.7	1141.2	1142.6	1142.6	1142.6	1142.6	1142.6	1142.1
142.5°	1177.6	1179.5	1180.4	1181.5	1182.5	1183.6	1183.7	1184.0	1184.3	1184.5	1184.0
145°	1237.1	1239.0	1240.8	1242.6	1244.4	1246.2	1246.4	1246.8	1247.1	1247.3	1246.9
147.5°	1293.9	1295.7	1296.9	1298.1	1299.3	1300.5	1301.2	1301.8	1302.4	1303.1	1302.9
150°	1328.6	1330.1	1331.3	1332.5	1333.7	1334.9	1335.8	1336.7	1337.6	1338.5	1338.5
152.5°	1362.0	1363.6	1365.0	1366.5	1367.9	1369.3	1370.5	1371.5	1372.7	1373.9	1373.9
155°	1408.4	1409.3	1410.2	1411.0	1411.9	1412.8	1414.3	1415.9	1417.4	1418.8	1419.2
157.5°	1449.9	1450.5	1451.1	1451.6	1452.2	1452.7	1454.6	1456.7	1458.7	1460.8	1461.1
160°	1475.8	1476.2	1476.5	1476.8	1477.1	1477.4	1479.2	1481.0	1482.7	1484.5	1484.9
162.5°	1497.5	1497.7	1498.0	1498.3	1498.6	1498.9	1500.9	1503.0	1505.0	1507.0	1507.3
165°	1527.3	1527.1	1527.1	1527.1	1527.1	1527.1	1529.2	1531.3	1533.4	1535.5	1535.8
167.5°	1551.2	1550.8	1550.7	1550.7	1550.6	1550.5	1552.6	1554.7	1556.8	1558.9	1559.2
170°	1565.2	1564.6	1564.3	1564.1	1563.7	1563.4	1565.5	1567.6	1569.7	1571.8	1571.9
172.5°	1574.9	1574.3	1574.0	1573.7	1573.4	1573.1	1575.2	1577.3	1579.4	1581.4	1581.6
175°	1586.7	1586.0	1585.4	1584.7	1584.2	1583.6	1585.7	1587.8	1589.8	1592.0	1592.1
177.5°	1592.3	1591.7	1591.2	1590.7	1590.3	1589.7	1591.2	1592.7	1594.1	1595.5	1595.5
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331862-940

CATALOG NUMBER: S122RDIW-S1005D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	1888.5	1889.5	1887.9	1889.0	1887.9	1889.5	1888.5	1894.4	1895.5	1896.7	1895.5
5°	1759.5	1751.3	1750.0	1747.9	1750.0	1751.3	1759.5	1763.0	1765.7	1771.2	1780.7
7.5°	1605.7	1604.5	1601.1	1596.3	1601.1	1604.5	1605.7	1617.4	1626.7	1637.4	1656.9
10°	1506.7	1503.3	1502.6	1497.8	1502.6	1503.3	1506.7	1521.8	1532.7	1547.7	1574.4
12.5°	1390.8	1368.9	1366.5	1354.6	1366.5	1368.9	1390.8	1410.2	1439.8	1454.3	1482.6
15°	1184.2	1180.1	1166.4	1157.5	1166.4	1180.1	1184.2	1200.6	1211.6	1251.2	1297.0
17.5°	1066.1	1052.8	1048.5	1046.6	1048.5	1052.8	1066.1	1074.1	1089.7	1110.5	1138.2
20°	990.2	977.9	975.8	974.5	975.8	977.9	990.2	999.7	1012.0	1034.6	1063.3
22.5°	937.6	924.8	919.4	915.3	919.4	924.8	937.6	945.0	956.3	973.8	993.3
25°	848.0	843.2	840.5	839.1	840.5	843.2	848.0	854.9	865.8	889.7	910.2
27.5°	777.9	767.4	765.4	761.8	765.4	767.4	777.9	790.1	801.4	812.2	830.5
30°	738.0	734.6	729.8	725.7	729.8	734.6	738.0	744.1	751.6	770.1	787.9
32.5°	691.0	688.1	683.9	682.0	683.9	688.1	691.0	699.3	715.1	726.4	739.2
35°	638.9	629.4	625.3	619.1	625.3	629.4	638.9	645.8	651.9	661.5	684.7
37.5°	583.8	578.8	573.0	575.1	573.0	578.8	583.8	586.7	599.7	613.0	623.0
40°	541.2	537.8	536.5	535.7	536.5	537.8	541.2	550.1	565.8	571.9	587.0
42.5°	507.3	497.8	494.3	494.2	494.3	497.8	507.3	517.3	527.0	537.0	552.5
45°	455.8	446.9	440.8	441.4	440.8	446.9	455.8	459.2	467.4	487.2	496.1
47.5°	403.1	402.8	399.0	400.1	399.0	402.8	403.1	408.9	419.5	431.6	445.8
50°	377.9	373.8	371.0	371.8	371.0	373.8	377.9	382.6	388.8	394.9	416.8
52.5°	353.8	350.3	348.1	351.0	348.1	350.3	353.8	356.4	361.0	367.1	381.8
55°	314.3	310.2	309.5	308.9	309.5	310.2	314.3	317.7	323.2	328.0	334.8
57.5°	270.2	267.4	263.3	261.5	263.3	267.4	270.2	275.3	281.8	288.1	295.2
60°	238.4	233.0	226.1	225.5	226.1	233.0	238.4	247.4	250.1	259.7	267.9
62.5°	209.5	208.4	207.1	206.9	207.1	208.4	209.5	212.4	216.2	230.2	240.0
65°	183.8	183.2	183.8	184.5	183.8	183.2	183.8	185.2	185.8	187.3	191.4
67.5°	160.2	158.9	157.7	158.3	157.7	158.9	160.2	160.4	162.4	163.2	166.0
70°	142.1	141.4	140.8	140.8	140.8	141.4	142.1	143.5	144.9	146.2	149.6
72.5°	124.7	124.5	123.9	123.2	123.9	124.5	124.7	127.1	128.0	129.3	131.6
75°	99.8	98.4	98.4	98.4	98.4	98.4	99.8	100.4	101.1	103.2	104.5
77.5°	76.0	75.3	74.6	74.1	74.6	75.3	76.0	76.2	77.2	77.7	79.1
80°	60.1	59.5	58.8	58.8	58.8	59.5	60.1	60.8	60.8	62.9	62.2
82.5°	45.9	45.2	45.1	44.6	45.1	45.2	45.9	46.0	46.0	47.5	47.4
85°	24.6	25.3	24.6	25.9	24.6	25.3	24.6	23.9	24.6	25.9	25.9
87.5°	16.1	15.6	16.2	15.7	16.2	15.6	16.1	16.1	16.6	16.7	16.9
90°	44.9	45.1	45.4	45.7	45.4	45.1	44.9	44.5	44.7	45.3	45.8
92.5°	43.3	43.4	43.5	43.5	43.5	43.4	43.3	43.3	43.2	43.1	43.0
95°	85.2	84.5	83.9	83.4	83.9	84.5	85.2	85.7	86.1	86.1	86.1
97.5°	144.5	144.5	144.5	144.4	144.5	144.5	144.5	144.6	144.6	144.6	144.6
100°	185.0	184.8	184.5	184.1	184.5	184.8	185.0	185.4	185.5	185.5	185.5
102.5°	230.2	230.0	229.6	229.3	229.6	230.0	230.2	230.5	230.6	230.3	230.1
105°	298.5	298.5	298.5	298.5	298.5	298.5	298.5	298.5	298.1	297.6	296.9
107.5°	367.7	366.2	364.9	363.5	364.9	366.2	367.7	369.0	369.5	369.3	369.1
110°	416.7	415.8	414.9	414.0	414.9	415.8	416.7	417.6	418.1	418.1	418.1



TEST NUMBER: P331862-940

CATALOG NUMBER: S122RDIW-S1005D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	464.4	463.8	463.1	462.4	463.1	463.8	464.4	465.0	465.7	466.5	467.2
115°	540.4	539.5	538.6	537.7	538.6	539.5	540.4	541.3	541.9	542.2	542.5
117.5°	612.2	611.3	610.4	609.5	610.4	611.3	612.2	613.1	613.9	614.7	615.4
120°	662.7	661.8	660.9	660.0	660.9	661.8	662.7	663.6	664.1	664.1	664.1
122.5°	711.5	710.9	710.2	709.5	710.2	710.9	711.5	712.1	712.8	713.5	714.3
125°	786.0	785.7	785.4	785.1	785.4	785.7	786.0	786.3	786.8	787.7	788.6
127.5°	856.8	855.8	854.9	853.9	854.9	855.8	856.8	857.7	858.7	859.8	860.9
130°	907.0	905.8	904.6	903.4	904.6	905.8	907.0	908.1	909.0	909.6	910.3
132.5°	953.6	952.6	951.6	950.7	951.6	952.6	953.6	954.5	955.6	957.0	958.3
135°	1027.1	1026.2	1025.3	1024.4	1025.3	1026.2	1027.1	1028.0	1028.6	1028.9	1029.1
137.5°	1094.7	1093.4	1092.3	1091.0	1092.3	1093.4	1094.7	1095.8	1096.5	1096.8	1097.0
140°	1140.9	1139.7	1138.4	1137.3	1138.4	1139.7	1140.9	1142.1	1142.6	1142.6	1142.6
142.5°	1182.9	1181.6	1180.4	1179.2	1180.4	1181.6	1182.9	1184.0	1184.5	1184.3	1184.0
145°	1245.7	1244.6	1243.3	1242.2	1243.3	1244.6	1245.7	1246.9	1247.3	1247.1	1246.8
147.5°	1301.7	1300.6	1299.5	1298.3	1299.5	1300.6	1301.7	1302.9	1303.1	1302.4	1301.8
150°	1337.6	1336.7	1335.8	1334.9	1335.8	1336.7	1337.6	1338.5	1338.5	1337.6	1336.7
152.5°	1372.7	1371.5	1370.5	1369.3	1370.5	1371.5	1372.7	1373.9	1373.9	1372.7	1371.5
155°	1418.3	1417.4	1416.5	1415.6	1416.5	1417.4	1418.3	1419.2	1418.8	1417.4	1415.9
157.5°	1459.6	1458.2	1456.8	1455.4	1456.8	1458.2	1459.6	1461.1	1460.8	1458.7	1456.7
160°	1483.6	1482.5	1481.3	1480.1	1481.3	1482.5	1483.6	1484.9	1484.5	1482.7	1481.0
162.5°	1505.9	1504.5	1503.1	1501.6	1503.1	1504.5	1505.9	1507.3	1507.0	1505.0	1503.0
165°	1534.3	1532.9	1531.3	1529.8	1531.3	1532.9	1534.3	1535.8	1535.5	1533.4	1531.3
167.5°	1557.6	1556.0	1554.5	1552.9	1554.5	1556.0	1557.6	1559.2	1558.9	1556.8	1554.7
170°	1570.1	1568.3	1566.6	1564.8	1566.6	1568.3	1570.1	1571.9	1571.8	1569.7	1567.6
172.5°	1579.8	1578.1	1576.3	1574.5	1576.3	1578.1	1579.8	1581.6	1581.4	1579.4	1577.3
175°	1590.3	1588.5	1586.7	1584.9	1586.7	1588.5	1590.3	1592.1	1592.0	1589.8	1587.8
177.5°	1594.1	1592.7	1591.2	1589.7	1591.2	1592.7	1594.1	1595.5	1595.5	1594.1	1592.7
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331862-940

CATALOG NUMBER: S122RDIW-S1005D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	1891.1	1898.8	1910.3	1916.8	1927.8	1934.9	1938.8	1945.8	1949.6	1963.4	1977.5
5°	1785.6	1796.4	1815.6	1833.4	1852.5	1872.3	1886.7	1903.1	1918.1	1944.0	1971.4
7.5°	1664.5	1679.6	1709.2	1737.6	1770.9	1798.9	1823.6	1851.6	1876.7	1913.9	1952.7
10°	1573.7	1600.4	1639.3	1666.0	1709.7	1737.7	1776.6	1807.4	1842.3	1891.4	1935.2
12.5°	1495.5	1527.7	1559.0	1596.0	1635.3	1681.9	1724.7	1764.2	1805.6	1856.5	1907.8
15°	1353.7	1400.2	1448.7	1486.2	1539.5	1588.8	1638.6	1691.9	1742.5	1803.3	1870.3
17.5°	1171.1	1224.9	1306.5	1370.9	1433.5	1482.8	1544.6	1609.1	1668.7	1742.0	1816.6
20°	1088.5	1128.2	1183.5	1270.3	1364.6	1417.2	1480.1	1551.1	1619.4	1699.4	1779.4
22.5°	1022.3	1057.7	1102.1	1169.7	1275.0	1346.7	1412.3	1484.4	1563.7	1645.3	1734.0
25°	927.9	952.5	999.0	1053.6	1126.1	1244.3	1316.1	1388.5	1474.6	1562.1	1663.2
27.5°	857.0	879.1	909.4	961.5	1015.4	1100.3	1214.4	1293.4	1379.2	1477.7	1582.6
30°	802.9	828.8	862.4	899.3	958.1	1024.3	1138.4	1230.0	1314.7	1415.9	1527.9
32.5°	763.6	784.1	812.6	850.1	899.0	962.5	1053.6	1164.9	1247.5	1354.1	1471.1
35°	699.0	723.0	746.2	781.8	821.4	879.4	948.4	1067.4	1149.3	1254.5	1372.1
37.5°	645.9	660.5	686.2	714.3	756.2	799.5	859.3	966.0	1054.6	1158.0	1278.3
40°	605.4	623.8	643.0	674.4	708.6	750.3	809.0	888.3	990.2	1091.3	1208.8
42.5°	566.1	589.4	609.7	630.7	668.2	709.8	757.7	824.9	928.9	1024.6	1138.8
45°	518.6	533.7	554.8	578.1	608.9	644.4	686.7	745.5	845.3	927.9	1035.3
47.5°	463.4	485.4	499.3	521.9	551.2	585.1	624.5	675.3	756.0	833.5	933.0
50°	425.7	448.3	468.1	488.6	514.5	547.3	580.1	629.4	694.3	775.6	868.5
52.5°	393.4	413.3	432.6	453.1	478.5	508.5	539.7	582.9	638.5	713.3	803.4
55°	349.2	361.5	381.3	401.8	424.4	453.1	483.1	519.3	567.1	630.0	703.1
57.5°	303.8	318.0	333.8	354.4	377.2	399.2	426.2	459.1	496.8	553.7	616.3
60°	278.1	289.0	302.0	323.2	344.4	364.2	390.2	417.5	453.1	502.2	555.5
62.5°	249.7	260.1	272.0	290.4	311.0	329.2	351.9	380.8	411.0	455.8	502.5
65°	202.2	217.3	228.9	245.3	262.4	281.5	299.3	322.5	349.2	384.7	426.4
67.5°	167.7	175.3	186.1	201.0	218.6	235.0	251.7	269.9	293.0	320.5	353.6
70°	152.4	155.2	157.2	171.5	187.9	204.3	220.1	237.1	256.9	279.5	308.2
72.5°	134.4	137.1	139.6	145.8	158.9	175.3	191.6	204.3	223.0	241.7	265.0
75°	106.6	110.7	112.7	116.2	120.9	131.9	147.0	159.2	170.1	184.5	203.0
77.5°	81.1	83.5	85.7	89.3	92.3	97.3	105.8	116.8	127.1	135.5	148.1
80°	64.2	64.9	67.7	69.0	73.1	76.5	80.6	89.5	99.8	103.2	112.1
82.5°	48.4	49.0	51.3	52.6	54.6	57.4	62.6	64.9	72.9	77.5	83.1
85°	26.7	25.9	28.0	28.0	29.4	30.8	32.1	35.5	37.5	43.1	44.4
87.5°	17.5	17.6	16.9	15.5	14.2	14.0	13.6	13.4	13.7	14.6	16.1
90°	46.5	47.1	40.5	33.9	27.4	20.8	15.7	12.1	8.5	4.9	1.3
92.5°	42.9	42.7	41.2	39.7	38.1	36.6	34.4	31.8	29.2	26.6	23.9
95°	86.1	86.1	85.4	84.8	84.3	83.6	81.9	78.8	75.9	72.9	69.9
97.5°	144.6	144.6	143.5	142.4	141.2	140.1	138.2	135.6	133.0	130.4	127.7
100°	185.5	185.5	184.6	183.7	182.8	181.9	180.3	177.9	175.5	173.1	170.8
102.5°	229.9	229.6	228.5	227.3	226.2	225.1	223.6	221.6	219.7	217.8	215.9
105°	296.3	295.8	295.2	294.5	294.0	293.4	292.6	291.7	290.8	289.9	289.0
107.5°	368.8	368.6	368.6	368.6	368.6	368.6	367.9	366.7	365.3	364.0	362.7
110°	418.1	418.1	418.1	418.1	418.1	418.1	417.1	415.4	413.6	411.8	410.0



TEST NUMBER: P331862-940

CATALOG NUMBER: S122RDIW-S1005D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	467.9	468.6	468.9	469.1	469.3	469.6	468.8	467.0	465.2	463.4	461.6
115°	542.8	543.1	543.7	544.3	544.9	545.5	544.9	543.1	541.3	539.5	537.7
117.5°	616.1	616.8	618.4	620.1	621.8	623.5	623.1	620.7	618.3	615.9	613.6
120°	664.1	664.1	666.5	668.9	671.3	673.7	673.7	671.3	668.9	666.5	664.1
122.5°	715.0	715.7	717.4	719.1	720.8	722.4	721.8	718.9	716.0	713.2	710.3
125°	789.5	790.4	791.4	792.3	793.2	794.1	793.2	790.4	787.7	785.1	782.4
127.5°	861.9	863.1	864.2	865.2	866.3	867.4	866.2	862.8	859.3	856.0	852.6
130°	910.9	911.4	912.0	912.7	913.2	913.8	912.2	908.3	904.5	900.5	896.6
132.5°	959.6	960.9	960.8	960.6	960.6	960.5	958.8	955.6	952.4	949.3	946.1
135°	1029.5	1029.7	1029.1	1028.6	1028.0	1027.3	1025.4	1022.1	1018.9	1015.6	1012.3
137.5°	1097.3	1097.5	1096.7	1095.9	1095.2	1094.4	1092.6	1089.9	1087.3	1084.6	1081.9
140°	1142.6	1142.6	1141.2	1139.7	1138.2	1136.7	1134.6	1131.9	1129.3	1126.5	1123.8
142.5°	1183.7	1183.6	1182.5	1181.5	1180.4	1179.5	1177.6	1174.9	1172.2	1169.6	1166.9
145°	1246.4	1246.2	1244.4	1242.6	1240.8	1239.0	1237.1	1234.9	1232.9	1230.8	1228.7
147.5°	1301.2	1300.5	1299.3	1298.1	1296.9	1295.7	1293.9	1291.4	1288.8	1286.3	1283.8
150°	1335.8	1334.9	1333.7	1332.5	1331.3	1330.1	1328.6	1326.9	1325.1	1323.2	1321.4
152.5°	1370.5	1369.3	1367.9	1366.5	1365.0	1363.6	1362.0	1360.1	1358.3	1356.6	1354.8
155°	1414.3	1412.8	1411.9	1411.0	1410.2	1409.3	1408.4	1407.5	1406.6	1405.7	1404.8
157.5°	1454.6	1452.7	1452.2	1451.6	1451.1	1450.5	1449.9	1449.4	1448.8	1448.1	1447.5
160°	1479.2	1477.4	1477.1	1476.8	1476.5	1476.2	1475.8	1475.2	1474.5	1474.0	1473.4
162.5°	1500.9	1498.9	1498.6	1498.3	1498.0	1497.7	1497.5	1497.4	1497.3	1497.2	1497.0
165°	1529.2	1527.1	1527.1	1527.1	1527.1	1527.1	1527.3	1527.6	1527.9	1528.2	1528.5
167.5°	1552.6	1550.5	1550.6	1550.7	1550.7	1550.8	1551.2	1552.1	1553.0	1553.9	1554.8
170°	1565.5	1563.4	1563.7	1564.1	1564.3	1564.6	1565.2	1566.1	1567.0	1567.9	1568.8
172.5°	1575.2	1573.1	1573.4	1573.7	1574.0	1574.3	1574.9	1575.8	1576.7	1577.6	1578.5
175°	1585.7	1583.6	1584.2	1584.7	1585.4	1586.0	1586.7	1587.6	1588.5	1589.4	1590.3
177.5°	1591.2	1589.7	1590.3	1590.7	1591.2	1591.7	1592.3	1593.0	1593.8	1594.5	1595.2
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331862-940

CATALOG NUMBER: S122RDIW-S1005D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	1978.1	1979.7	1990.7	1995.6	2005.5	2009.2	2013.7	2012.5	2012.5	2014.7	2030.0
5°	1982.4	1996.0	2016.5	2036.3	2055.5	2071.8	2082.8	2093.7	2097.8	2117.6	2135.4
7.5°	1975.2	2000.4	2034.3	2064.5	2100.7	2129.0	2152.5	2173.6	2188.2	2217.0	2246.5
10°	1966.0	2001.4	2039.7	2078.7	2128.5	2166.1	2204.4	2233.8	2243.4	2286.4	2311.0
12.5°	1947.3	1994.9	2043.5	2094.0	2142.8	2194.6	2236.7	2266.0	2299.6	2338.3	2383.7
15°	1919.5	1974.2	2037.6	2102.6	2172.3	2235.2	2280.3	2331.5	2368.4	2410.7	2450.4
17.5°	1879.5	1949.8	2030.6	2105.8	2186.4	2253.9	2316.0	2365.1	2391.1	2415.3	2421.2
20°	1847.7	1923.6	2018.6	2107.4	2188.0	2265.9	2327.4	2368.4	2375.3	2375.9	2339.7
22.5°	1813.3	1899.0	1998.3	2089.4	2185.9	2272.4	2320.3	2337.8	2310.7	2264.4	2194.3
25°	1750.0	1849.1	1964.5	2068.4	2173.6	2255.7	2272.1	2241.3	2146.3	2046.6	1920.1
27.5°	1681.4	1792.8	1916.6	2032.0	2144.1	2194.9	2159.5	2048.7	1877.7	1728.9	1548.7
30°	1631.1	1756.1	1877.8	2006.9	2110.8	2132.6	2051.4	1888.0	1688.5	1464.4	1284.7
32.5°	1573.7	1704.8	1838.4	1971.9	2058.9	2037.6	1903.2	1702.2	1468.2	1247.9	1078.0
35°	1491.7	1627.0	1771.2	1905.1	1960.4	1868.2	1667.3	1405.6	1166.4	960.7	843.9
37.5°	1397.0	1544.4	1694.3	1817.2	1813.3	1659.6	1385.9	1115.7	914.7	793.1	709.8
40°	1329.7	1478.7	1640.7	1744.5	1700.1	1499.9	1203.4	948.4	801.6	704.5	643.7
42.5°	1265.2	1414.8	1575.7	1658.1	1580.9	1334.8	1039.4	839.6	718.5	642.7	593.4
45°	1155.5	1313.3	1462.3	1508.1	1370.0	1098.8	840.5	695.6	615.0	558.9	524.8
47.5°	1048.2	1203.5	1339.4	1340.2	1153.6	891.1	709.0	602.0	533.2	489.8	464.9
50°	982.6	1130.2	1244.3	1226.5	1014.8	792.6	634.1	541.9	484.5	451.0	425.0
52.5°	908.8	1052.0	1150.8	1100.3	897.2	697.5	566.9	489.4	441.8	412.7	389.5
55°	801.6	928.6	998.4	921.8	731.8	580.1	479.0	418.2	382.6	358.0	338.2
57.5°	696.2	801.0	844.9	755.7	602.8	481.1	405.2	359.5	324.3	306.7	296.4
60°	630.0	719.5	750.3	651.9	524.1	420.9	358.7	316.4	290.4	278.8	268.6
62.5°	565.0	638.1	650.8	560.6	456.9	368.5	315.0	279.2	262.0	250.9	241.2
65°	468.8	521.4	515.2	442.8	361.5	292.5	253.5	231.7	218.6	203.0	185.8
67.5°	385.9	418.0	398.7	344.4	275.9	227.3	201.9	185.3	169.2	154.3	150.3
70°	333.5	351.9	331.4	281.5	226.1	190.6	170.1	150.3	140.8	137.3	131.2
72.5°	283.2	289.6	267.4	224.7	184.0	157.8	137.9	126.8	121.6	118.8	114.8
75°	212.5	207.8	188.6	155.2	127.8	110.0	103.9	99.8	96.3	93.6	91.6
77.5°	149.3	142.2	125.2	103.3	89.0	80.5	76.8	74.6	72.9	71.6	69.6
80°	112.1	107.3	90.2	73.8	67.7	63.6	61.5	58.8	58.8	57.4	55.4
82.5°	82.0	76.7	61.8	54.1	50.7	48.2	46.7	45.1	44.6	44.9	43.3
85°	43.1	34.9	30.8	29.4	27.4	25.9	26.7	25.3	25.3	25.3	24.6
87.5°	14.1	12.1	12.2	12.4	14.0	15.3	16.1	17.4	19.3	18.5	19.0
90°	4.9	8.5	12.1	15.7	20.8	27.4	33.9	40.5	47.1	46.5	45.8
92.5°	26.6	29.2	31.8	34.4	36.6	38.1	39.7	41.2	42.7	42.9	43.0
95°	72.9	75.9	78.8	81.9	83.6	84.3	84.8	85.4	86.1	86.1	86.1
97.5°	130.4	133.0	135.6	138.2	140.1	141.2	142.4	143.5	144.6	144.6	144.6
100°	173.1	175.5	177.9	180.3	181.9	182.8	183.7	184.6	185.5	185.5	185.5
102.5°	217.8	219.7	221.6	223.6	225.1	226.2	227.3	228.5	229.6	229.9	230.1
105°	289.9	290.8	291.7	292.6	293.4	294.0	294.5	295.2	295.8	296.3	296.9
107.5°	364.0	365.3	366.7	367.9	368.6	368.6	368.6	368.6	368.6	368.8	369.1
110°	411.8	413.6	415.4	417.1	418.1	418.1	418.1	418.1	418.1	418.1	418.1



TEST NUMBER: P331862-940

CATALOG NUMBER: S122RDIW-S1005D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	463.4	465.2	467.0	468.8	469.6	469.3	469.1	468.9	468.6	467.9	467.2
115°	539.5	541.3	543.1	544.9	545.5	544.9	544.3	543.7	543.1	542.8	542.5
117.5°	615.9	618.3	620.7	623.1	623.5	621.8	620.1	618.4	616.8	616.1	615.4
120°	666.5	668.9	671.3	673.7	673.7	671.3	668.9	666.5	664.1	664.1	664.1
122.5°	713.2	716.0	718.9	721.8	722.4	720.8	719.1	717.4	715.7	715.0	714.3
125°	785.1	787.7	790.4	793.2	794.1	793.2	792.3	791.4	790.4	789.5	788.6
127.5°	856.0	859.3	862.8	866.2	867.4	866.3	865.2	864.2	863.1	861.9	860.9
130°	900.5	904.5	908.3	912.2	913.8	913.2	912.7	912.0	911.4	910.9	910.3
132.5°	949.3	952.4	955.6	958.8	960.5	960.6	960.6	960.8	960.9	959.6	958.3
135°	1015.6	1018.9	1022.1	1025.4	1027.3	1028.0	1028.6	1029.1	1029.7	1029.5	1029.1
137.5°	1084.6	1087.3	1089.9	1092.6	1094.4	1095.2	1095.9	1096.7	1097.5	1097.3	1097.0
140°	1126.5	1129.3	1131.9	1134.6	1136.7	1138.2	1139.7	1141.2	1142.6	1142.6	1142.6
142.5°	1169.6	1172.2	1174.9	1177.6	1179.5	1180.4	1181.5	1182.5	1183.6	1183.7	1184.0
145°	1230.8	1232.9	1234.9	1237.1	1239.0	1240.8	1242.6	1244.4	1246.2	1246.4	1246.8
147.5°	1286.3	1288.8	1291.4	1293.9	1295.7	1296.9	1298.1	1299.3	1300.5	1301.2	1301.8
150°	1323.2	1325.1	1326.9	1328.6	1330.1	1331.3	1332.5	1333.7	1334.9	1335.8	1336.7
152.5°	1356.6	1358.3	1360.1	1362.0	1363.6	1365.0	1366.5	1367.9	1369.3	1370.5	1371.5
155°	1405.7	1406.6	1407.5	1408.4	1409.3	1410.2	1411.0	1411.9	1412.8	1414.3	1415.9
157.5°	1448.1	1448.8	1449.4	1449.9	1450.5	1451.1	1451.6	1452.2	1452.7	1454.6	1456.7
160°	1474.0	1474.5	1475.2	1475.8	1476.2	1476.5	1476.8	1477.1	1477.4	1479.2	1481.0
162.5°	1497.2	1497.3	1497.4	1497.5	1497.7	1498.0	1498.3	1498.6	1498.9	1500.9	1503.0
165°	1528.2	1527.9	1527.6	1527.3	1527.1	1527.1	1527.1	1527.1	1527.1	1529.2	1531.3
167.5°	1553.9	1553.0	1552.1	1551.2	1550.8	1550.7	1550.7	1550.6	1550.5	1552.6	1554.7
170°	1567.9	1567.0	1566.1	1565.2	1564.6	1564.3	1564.1	1563.7	1563.4	1565.5	1567.6
172.5°	1577.6	1576.7	1575.8	1574.9	1574.3	1574.0	1573.7	1573.4	1573.1	1575.2	1577.3
175°	1589.4	1588.5	1587.6	1586.7	1586.0	1585.4	1584.7	1584.2	1583.6	1585.7	1587.8
177.5°	1594.5	1593.8	1593.0	1592.3	1591.7	1591.2	1590.7	1590.3	1589.7	1591.2	1592.7
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331862-940

CATALOG NUMBER: S122RDIW-S1005D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	2035.5	2042.6	2045.9	2045.9	2049.7	2048.1	2046.4
5°	2152.5	2165.4	2168.2	2180.5	2189.3	2186.7	2188.0
7.5°	2268.8	2289.6	2310.3	2319.8	2321.2	2326.7	2328.8
10°	2340.4	2357.5	2389.6	2384.8	2408.7	2422.4	2399.9
12.5°	2409.2	2432.3	2454.6	2460.8	2474.3	2478.7	2469.8
15°	2471.6	2483.9	2485.3	2481.8	2485.9	2482.5	2469.5
17.5°	2413.3	2393.4	2353.0	2333.8	2318.6	2296.2	2287.2
20°	2317.1	2258.3	2190.0	2162.8	2130.6	2067.7	2082.8
22.5°	2109.4	2042.5	1974.2	1894.4	1856.2	1796.6	1793.1
25°	1786.2	1670.7	1543.6	1454.8	1402.8	1343.5	1317.4
27.5°	1388.8	1243.4	1139.2	1086.5	1038.5	991.4	989.4
30°	1127.5	1018.2	937.5	892.4	863.0	843.2	847.3
32.5°	950.4	875.5	821.1	783.6	761.9	747.0	746.7
35°	776.9	725.7	690.8	675.1	659.4	648.5	649.2
37.5°	664.9	634.1	614.7	597.4	587.5	582.2	579.2
40°	607.4	582.2	567.1	556.9	548.7	541.2	539.8
42.5°	562.1	541.2	526.2	518.1	510.4	505.2	503.7
45°	498.8	481.7	468.1	459.2	455.8	451.0	451.0
47.5°	443.7	427.0	416.3	410.7	404.8	401.6	401.5
50°	406.6	393.6	384.1	380.6	375.9	373.8	373.1
52.5°	373.3	363.6	356.7	354.4	352.3	349.7	350.2
55°	328.0	322.5	319.8	317.7	314.3	310.2	313.0
57.5°	289.9	285.3	277.9	271.4	268.3	265.4	266.5
60°	263.1	253.5	244.0	236.4	234.3	228.2	228.2
62.5°	229.2	215.8	204.0	199.8	197.8	194.9	194.3
65°	176.3	170.9	168.1	165.3	164.0	164.0	162.6
67.5°	146.1	143.9	140.9	140.2	138.8	138.5	138.0
70°	129.1	126.4	125.0	124.4	123.0	123.7	121.6
72.5°	112.7	110.6	110.3	108.5	107.7	107.8	106.3
75°	88.8	88.8	88.2	87.5	86.1	85.4	86.1
77.5°	68.3	68.5	67.2	67.1	67.0	67.1	66.4
80°	54.7	55.4	54.7	53.9	53.3	53.9	53.3
82.5°	43.2	42.3	42.1	42.0	41.8	41.4	41.3
85°	24.6	25.3	24.6	23.9	23.9	23.9	24.6
87.5°	18.4	18.2	18.2	18.3	18.3	18.4	17.9
90°	45.3	44.7	44.5	44.9	45.1	45.4	45.7
92.5°	43.1	43.2	43.3	43.3	43.4	43.5	43.5
95°	86.1	86.1	85.7	85.2	84.5	83.9	83.4
97.5°	144.6	144.6	144.6	144.5	144.5	144.5	144.4
100°	185.5	185.5	185.4	185.0	184.8	184.5	184.1
102.5°	230.3	230.6	230.5	230.2	230.0	229.6	229.3
105°	297.6	298.1	298.5	298.5	298.5	298.5	298.5
107.5°	369.3	369.5	369.0	367.7	366.2	364.9	363.5
110°	418.1	418.1	417.6	416.7	415.8	414.9	414.0



TEST NUMBER: P331862-940

CATALOG NUMBER: S122RDIW-S1005D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	466.5	465.7	465.0	464.4	463.8	463.1	462.4
115°	542.2	541.9	541.3	540.4	539.5	538.6	537.7
117.5°	614.7	613.9	613.1	612.2	611.3	610.4	609.5
120°	664.1	664.1	663.6	662.7	661.8	660.9	660.0
122.5°	713.5	712.8	712.1	711.5	710.9	710.2	709.5
125°	787.7	786.8	786.3	786.0	785.7	785.4	785.1
127.5°	859.8	858.7	857.7	856.8	855.8	854.9	853.9
130°	909.6	909.0	908.1	907.0	905.8	904.6	903.4
132.5°	957.0	955.6	954.5	953.6	952.6	951.6	950.7
135°	1028.9	1028.6	1028.0	1027.1	1026.2	1025.3	1024.4
137.5°	1096.8	1096.5	1095.8	1094.7	1093.4	1092.3	1091.0
140°	1142.6	1142.6	1142.1	1140.9	1139.7	1138.4	1137.3
142.5°	1184.3	1184.5	1184.0	1182.9	1181.6	1180.4	1179.2
145°	1247.1	1247.3	1246.9	1245.7	1244.6	1243.3	1242.2
147.5°	1302.4	1303.1	1302.9	1301.7	1300.6	1299.5	1298.3
150°	1337.6	1338.5	1338.5	1337.6	1336.7	1335.8	1334.9
152.5°	1372.7	1373.9	1373.9	1372.7	1371.5	1370.5	1369.3
155°	1417.4	1418.8	1419.2	1418.3	1417.4	1416.5	1415.6
157.5°	1458.7	1460.8	1461.1	1459.6	1458.2	1456.8	1455.4
160°	1482.7	1484.5	1484.9	1483.6	1482.5	1481.3	1480.1
162.5°	1505.0	1507.0	1507.3	1505.9	1504.5	1503.1	1501.6
165°	1533.4	1535.5	1535.8	1534.3	1532.9	1531.3	1529.8
167.5°	1556.8	1558.9	1559.2	1557.6	1556.0	1554.5	1552.9
170°	1569.7	1571.8	1571.9	1570.1	1568.3	1566.6	1564.8
172.5°	1579.4	1581.4	1581.6	1579.8	1578.1	1576.3	1574.5
175°	1589.8	1592.0	1592.1	1590.3	1588.5	1586.7	1584.9
177.5°	1594.1	1595.5	1595.5	1594.1	1592.7	1591.2	1589.7
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0

(END OF REPORT)