

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331483-935

Luminaire Tested: **S122DIW-S290D1240U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331483-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D1240U935-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5392.0 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331483-935

CATALOG NUMBER: S122DIW-S290D1240U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331483-935

CATALOG NUMBER: S122DIW-S290D1240U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29	21				
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	18				
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	23	22	21	15				
3	76	67	60	55	67	60	54	50	46	42	39	33	30	28	21	20	18	13				
4	70	60	52	47	61	53	47	42	41	36	33	29	27	24	19	17	16	12				
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	10				
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	15	14	12	9				
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	12	11	8				
8	50	39	31	26	44	35	28	24	27	22	19	20	17	15	13	11	10	7				
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7				
10	43	32	25	21	38	29	23	19	23	18	15	17	14	12	11	9	8	6				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8217	8217	8217	8217
5°	9211	8271	7329	8271
10°	10557	8202	6342	8202
15°	11677	8052	5605	8052
20°	11500	7892	5108	7892
25°	10368	7675	4794	7675
30°	8569	7333	4566	7333
35°	6244	6974	4401	6974
40°	4989	6551	4312	6551
45°	4359	6060	4190	6060
50°	4099	5586	4107	5586
55°	3775	5103	3997	5103
60°	3462	4592	3830	4592
65°	3156	4130	3660	4130
70°	2861	3682	3418	3682
75°	2539	3188	3026	3188
80°	2185	2631	2436	2631
85°	1964	1964	1445	1964



TEST NUMBER: P331483-935

CATALOG NUMBER: S122DIW-S290D1240U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.5	0.9
10°-20°	140.9	2.6
20°-30°	204.5	3.8
30°-40°	215.8	4.0
40°-50°	191.1	3.5
50°-60°	152.5	2.8
60°-70°	103.6	1.9
70°-80°	53.1	1.0
80°-90°	16.4	0.3
90°-100°	48.6	0.9
100°-110°	178.1	3.3
110°-120°	476.0	8.8
120°-130°	785.7	14.6
130°-140°	835.5	15.5
140°-150°	776.6	14.4
150°-160°	624.4	11.6
160°-170°	402.3	7.5
170°-180°	138.5	2.6
0°-30°	393.9	7.3
0°-40°	609.7	11.3
0°-60°	953.2	17.7
0°-90°	1126.4	20.9
90°-120°	702.6	13.0
90°-150°	3100.4	57.5
90°-180°	4266.0	79.1
0°-180°	5392.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	568	510	452	510	568	57
15°	699	482	335	482	699	193
25°	582	431	269	431	582	263
35°	317	354	223	354	317	206
45°	191	265	184	265	191	150
55°	134	181	142	181	134	120
65°	83	108	96	108	83	82
75°	41	51	48	51	41	43
85°	11	11	8	11	11	12
90°	28	1	28	1	28	13
95°	45	68	45	68	45	42
105°	80	320	80	320	80	83
115°	86	606	86	606	86	216
125°	900	856	900	856	900	779
135°	1094	1060	1094	1060	1094	843
145°	1248	1229	1248	1229	1248	781
155°	1354	1353	1354	1353	1354	625
165°	1423	1426	1423	1426	1423	402
175°	1450	1459	1450	1459	1450	138
180°	1456	1456	1456	1456	1456	



TEST NUMBER: P331483-935

CATALOG NUMBER: S122DIW-S290D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	532.4	532.5	532.9	530.4	530.0	530.0	527.9	526.0	523.7	520.8	521.2
5°	568.3	570.5	571.3	568.9	565.4	565.1	561.7	556.3	551.1	547.1	544.2
7.5°	611.3	612.2	610.3	607.2	604.6	599.9	593.7	587.6	579.1	571.4	565.6
10°	643.9	645.1	641.7	637.2	633.5	628.0	619.1	609.8	598.7	588.0	579.4
12.5°	668.6	671.5	667.2	666.7	660.3	652.7	642.0	637.4	621.7	606.7	597.4
15°	698.6	698.4	698.9	695.1	690.4	689.2	678.0	665.6	643.5	634.6	619.4
17.5°	689.9	692.9	694.3	694.2	694.1	693.4	689.7	682.0	670.9	656.6	639.0
20°	669.3	673.2	673.8	678.3	680.9	684.2	685.5	683.4	676.6	664.6	649.4
22.5°	637.4	638.5	640.3	647.3	652.8	661.2	665.5	672.8	670.1	664.3	651.5
25°	582.0	580.1	586.9	590.5	603.2	616.5	626.1	636.6	646.0	651.7	648.0
27.5°	515.7	512.7	523.0	532.4	542.6	557.1	572.0	589.6	604.2	622.7	629.0
30°	459.6	461.4	471.1	481.1	496.8	517.1	534.0	553.3	574.3	594.8	609.1
32.5°	399.2	406.0	412.2	427.5	441.3	463.9	488.6	512.8	538.9	562.2	584.4
35°	316.8	324.7	333.3	344.4	363.8	386.2	410.4	443.0	478.6	510.5	536.7
37.5°	266.7	265.4	270.4	278.4	294.1	312.3	340.0	372.2	414.1	451.6	488.6
40°	236.7	235.9	239.4	246.8	258.7	272.1	296.4	324.7	363.6	409.4	453.4
42.5°	216.0	216.5	218.4	223.7	231.9	242.8	261.0	285.1	320.7	363.9	411.1
45°	190.9	192.3	194.4	197.0	201.6	210.7	220.8	238.1	266.2	302.2	348.7
47.5°	172.8	172.9	175.0	177.3	180.0	185.1	193.5	204.2	224.1	253.4	293.4
50°	163.2	161.8	163.3	165.1	168.0	171.5	177.0	187.2	200.4	224.1	257.6
52.5°	151.2	151.3	152.7	153.3	155.9	159.5	164.5	171.5	183.6	202.1	229.5
55°	134.1	135.2	136.0	137.1	139.5	142.0	145.9	150.6	160.0	173.8	194.2
57.5°	118.1	118.5	119.2	121.5	123.0	125.3	129.0	133.3	139.4	149.6	165.0
60°	107.2	107.2	108.7	109.7	111.7	114.0	116.9	121.1	126.6	134.9	147.3
62.5°	97.2	97.0	97.6	99.3	100.7	102.9	105.8	109.3	114.5	122.0	132.1
65°	82.6	82.1	83.3	83.7	85.2	87.4	89.8	93.5	97.6	103.1	112.1
67.5°	68.4	69.0	69.6	70.3	71.1	73.4	75.0	77.6	81.1	85.7	91.7
70°	60.6	60.6	60.6	61.2	62.4	63.5	65.1	67.2	70.6	74.5	80.0
72.5°	51.8	52.5	53.1	52.8	54.2	54.9	56.8	58.0	61.2	63.7	68.5
75°	40.7	40.7	40.7	41.7	42.3	42.8	44.0	45.2	46.8	49.9	52.4
77.5°	30.4	30.3	30.5	30.7	31.3	32.0	32.4	33.4	34.9	36.3	38.5
80°	23.5	23.8	24.0	24.5	24.5	24.8	25.1	26.4	27.4	28.3	29.7
82.5°	18.2	18.3	18.3	18.3	18.5	18.8	19.3	19.7	20.1	20.8	21.9
85°	10.6	10.3	10.3	10.8	10.6	10.6	10.9	11.4	11.4	11.5	12.1
87.5°	9.7	9.6	9.7	9.5	9.4	9.4	9.1	8.8	8.7	8.6	8.4
90°	28.4	28.0	27.5	27.0	26.6	25.7	24.5	23.4	22.2	21.1	19.2
92.5°	28.4	28.2	27.9	27.6	27.3	26.9	26.3	25.7	25.1	24.5	23.5
95°	45.3	45.5	45.7	46.0	46.2	45.7	44.6	43.4	42.3	41.1	39.4
97.5°	60.4	60.2	59.9	59.6	59.3	58.7	57.8	56.8	55.9	55.0	51.2
100°	70.6	70.1	69.7	69.1	68.7	67.5	65.6	63.8	61.9	60.0	56.1
102.5°	75.6	75.0	74.3	73.6	73.0	71.5	69.1	66.6	64.1	61.7	59.0
105°	80.1	79.1	78.2	77.2	76.3	74.6	72.0	69.4	66.8	64.2	61.1
107.5°	82.4	81.5	80.5	79.6	78.6	79.5	82.1	84.7	87.3	90.0	93.0
110°	83.2	82.3	81.4	80.4	79.5	90.7	114.1	137.5	160.9	184.3	215.9



TEST NUMBER: P331483-935

CATALOG NUMBER: S122DIW-S290D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	84.0	83.3	82.6	81.8	81.0	123.4	208.8	294.1	379.5	464.9	481.6
115°	86.4	103.2	120.1	136.9	153.8	216.4	324.8	433.1	541.5	649.9	644.0
117.5°	352.6	408.0	463.4	518.8	574.1	614.9	641.1	667.4	693.5	719.8	715.7
120°	642.5	674.1	705.7	737.3	768.9	783.3	780.4	777.7	774.8	772.0	767.8
122.5°	801.7	807.9	814.0	820.1	826.2	828.5	826.8	825.1	823.4	821.7	817.2
125°	900.5	899.8	899.1	898.4	897.7	896.6	894.9	893.3	891.7	890.0	885.5
127.5°	962.9	962.7	962.6	962.4	962.3	961.0	958.6	956.2	953.9	951.5	948.1
130°	1001.6	1001.9	1002.1	1002.3	1002.5	1001.3	998.8	996.3	993.7	991.1	988.5
132.5°	1039.6	1039.7	1040.0	1040.3	1040.4	1039.5	1037.2	1035.1	1032.9	1030.7	1028.1
135°	1094.3	1094.8	1095.3	1095.7	1096.1	1095.3	1092.9	1090.5	1088.2	1085.9	1083.7
137.5°	1144.2	1145.0	1145.8	1146.6	1147.4	1146.7	1144.4	1142.0	1139.8	1137.5	1135.1
140°	1175.4	1176.6	1177.8	1178.9	1180.1	1179.7	1177.5	1175.4	1173.3	1171.2	1168.6
142.5°	1205.7	1206.9	1208.1	1209.3	1210.4	1210.0	1208.2	1206.2	1204.3	1202.4	1199.4
145°	1248.1	1249.2	1250.4	1251.5	1252.8	1252.5	1250.9	1249.2	1247.6	1246.0	1242.0
147.5°	1285.4	1286.3	1287.3	1288.3	1289.3	1289.2	1288.0	1286.8	1285.6	1284.3	1280.4
150°	1308.1	1309.2	1310.4	1311.6	1312.8	1312.7	1311.3	1309.8	1308.5	1307.1	1303.3
152.5°	1327.5	1329.0	1330.6	1332.1	1333.7	1333.8	1332.3	1330.9	1329.6	1328.1	1324.6
155°	1354.4	1356.3	1358.2	1360.0	1361.9	1362.2	1360.8	1359.3	1358.0	1356.6	1353.8
157.5°	1379.1	1381.0	1382.8	1384.6	1386.4	1386.6	1384.9	1383.4	1381.7	1380.2	1378.2
160°	1393.4	1395.1	1396.7	1398.4	1400.0	1400.1	1398.7	1397.3	1395.9	1394.5	1393.1
162.5°	1405.2	1407.2	1409.2	1411.3	1413.2	1413.5	1411.9	1410.3	1408.7	1407.1	1405.9
165°	1422.9	1424.5	1426.2	1427.8	1429.4	1429.4	1427.8	1426.2	1424.5	1422.9	1422.2
167.5°	1434.1	1436.1	1438.3	1440.4	1442.5	1442.7	1441.1	1439.4	1437.8	1436.1	1435.5
170°	1440.8	1442.9	1445.0	1447.2	1449.2	1449.5	1447.9	1446.2	1444.6	1442.9	1442.4
172.5°	1445.9	1447.9	1450.1	1452.2	1454.3	1454.5	1452.9	1451.2	1449.6	1447.9	1447.5
175°	1450.3	1452.6	1455.0	1457.3	1459.7	1460.0	1458.4	1456.7	1455.1	1453.5	1453.0
177.5°	1453.0	1454.7	1456.4	1458.1	1459.7	1460.0	1458.6	1457.3	1456.0	1454.7	1454.5
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331483-935

CATALOG NUMBER: S122DIW-S290D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	522.2	521.0	520.2	517.4	514.9	512.4	511.6	511.9	508.4	505.1	503.8
5°	542.6	538.6	534.9	529.7	523.4	516.5	513.1	510.3	503.4	496.0	491.7
7.5°	560.8	555.2	548.0	538.1	529.0	518.2	511.3	505.3	495.3	484.8	478.4
10°	571.9	564.3	555.1	542.9	531.8	518.7	509.5	500.3	488.6	476.0	468.2
12.5°	581.4	571.2	562.1	546.6	533.4	516.9	506.1	493.1	480.8	465.9	458.2
15°	604.2	585.2	568.0	550.4	534.2	511.3	499.1	481.7	465.5	447.1	438.3
17.5°	621.7	600.4	573.3	551.0	532.0	506.6	488.9	468.0	448.8	427.8	415.9
20°	631.7	607.3	578.2	551.6	528.9	499.9	480.5	459.3	436.8	413.1	400.2
22.5°	637.7	612.0	583.2	549.2	522.6	494.5	470.1	446.7	424.0	398.4	384.9
25°	639.6	616.1	585.6	547.3	514.8	482.9	453.6	430.8	403.3	379.4	359.7
27.5°	630.3	613.5	584.1	543.5	505.8	468.5	435.8	410.1	381.0	355.1	335.2
30°	618.8	609.1	580.5	539.8	498.5	458.5	422.5	393.3	364.4	338.2	317.8
32.5°	601.2	599.1	573.9	534.5	490.9	445.8	408.5	379.1	347.0	321.2	301.9
35°	566.5	575.8	560.0	522.6	476.5	427.7	387.4	353.8	320.6	295.9	277.8
37.5°	519.9	543.2	539.1	505.2	456.9	408.1	363.6	328.5	296.8	271.9	254.1
40°	487.8	517.5	521.9	491.9	443.2	393.0	345.8	310.8	279.9	257.2	239.2
42.5°	453.4	488.1	499.9	476.0	428.2	376.9	329.8	293.6	262.9	240.9	225.0
45°	395.7	441.6	463.0	449.3	403.1	350.7	302.2	265.4	237.6	216.9	204.6
47.5°	341.7	391.9	420.6	415.8	375.2	323.3	275.3	240.0	213.0	196.5	185.5
50°	303.6	355.2	389.8	391.4	355.2	303.8	255.6	222.4	197.5	182.1	173.1
52.5°	270.4	319.7	357.4	365.8	332.8	283.4	238.0	204.8	183.0	168.8	160.7
55°	227.0	268.7	310.6	325.9	299.5	252.5	210.4	181.3	160.7	151.0	144.0
57.5°	188.8	223.5	262.2	279.1	262.8	222.6	183.1	157.8	141.2	132.6	127.2
60°	168.6	196.0	230.4	250.6	236.4	200.7	166.3	142.2	128.5	120.9	115.8
62.5°	149.8	174.1	203.2	221.6	214.0	180.2	149.4	128.1	116.3	109.2	105.5
65°	123.6	142.8	165.3	182.3	177.2	151.6	126.3	108.1	98.8	93.1	90.1
67.5°	101.8	115.6	131.2	146.1	142.1	123.9	103.7	89.5	82.5	77.6	75.8
70°	88.0	98.6	112.4	124.4	121.1	106.2	90.1	78.0	72.0	67.8	66.1
72.5°	74.9	83.5	94.2	103.9	101.7	89.3	75.9	66.8	62.1	58.3	56.9
75°	56.6	63.2	69.7	76.1	75.5	66.0	58.1	51.1	47.4	44.4	43.8
77.5°	41.8	45.5	49.9	53.6	52.6	47.1	41.0	36.9	34.3	32.3	31.9
80°	31.9	34.0	37.2	39.9	38.6	36.2	31.3	28.3	26.4	24.5	23.7
82.5°	23.2	25.2	27.1	28.7	27.6	25.4	22.4	20.4	19.2	17.9	17.6
85°	12.1	13.3	14.1	14.5	14.1	12.7	11.4	10.6	9.6	9.0	8.8
87.5°	8.2	7.7	7.4	7.3	6.3	5.8	4.6	3.6	4.0	4.4	4.6
90°	17.3	15.4	13.6	11.4	8.8	6.2	3.6	1.0	3.6	6.2	8.8
92.5°	22.6	21.6	20.7	20.3	20.6	20.8	21.0	21.3	21.0	20.8	20.6
95°	37.8	36.2	34.5	37.5	45.3	53.0	60.7	68.4	60.7	53.0	45.3
97.5°	47.4	43.6	39.8	48.8	70.6	92.3	114.1	135.9	114.1	92.3	70.6
100°	52.1	48.1	44.1	58.2	90.2	122.3	154.4	186.4	154.4	122.3	90.2
102.5°	128.3	161.5	194.8	214.9	221.7	228.4	235.2	242.0	235.2	228.4	221.7
105°	192.0	256.0	319.9	348.3	341.2	334.2	327.2	320.2	327.2	334.2	341.2
107.5°	243.2	319.9	396.5	432.0	426.3	420.6	414.9	409.3	414.9	420.6	426.3
110°	319.6	387.3	454.9	486.2	481.3	476.4	471.5	466.6	471.5	476.4	481.3



TEST NUMBER: P331483-935

CATALOG NUMBER: S122DIW-S290D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	498.3	515.1	531.8	538.0	533.6	529.2	524.9	520.5	524.9	529.2	533.6
115°	638.2	632.3	626.5	621.6	617.5	613.5	609.6	605.6	609.6	613.5	617.5
117.5°	711.7	707.7	703.7	699.5	695.0	690.5	686.1	681.7	686.1	690.5	695.0
120°	763.6	759.4	755.2	751.3	747.8	744.2	740.8	737.3	740.8	744.2	747.8
122.5°	812.5	808.0	803.4	799.3	795.6	791.9	788.2	784.5	788.2	791.9	795.6
125°	881.1	876.7	872.2	868.4	865.4	862.4	859.3	856.3	859.3	862.4	865.4
127.5°	944.9	941.5	938.2	934.9	931.5	928.1	924.7	921.4	924.7	928.1	931.5
130°	985.9	983.3	980.8	977.7	973.9	970.2	966.4	962.7	966.4	970.2	973.9
132.5°	1025.5	1023.0	1020.4	1017.5	1014.3	1011.2	1008.0	1004.8	1008.0	1011.2	1014.3
135°	1081.7	1079.5	1077.5	1074.5	1070.7	1067.0	1063.2	1059.5	1063.2	1067.0	1070.7
137.5°	1132.7	1130.3	1127.9	1125.4	1122.8	1120.2	1117.6	1114.9	1117.6	1120.2	1122.8
140°	1166.1	1163.5	1160.9	1158.6	1156.8	1154.9	1153.1	1151.2	1153.1	1154.9	1156.8
142.5°	1196.4	1193.5	1190.6	1188.3	1186.5	1184.9	1183.2	1181.6	1183.2	1184.9	1186.5
145°	1238.0	1234.1	1230.0	1228.2	1228.4	1228.6	1228.9	1229.1	1228.9	1228.6	1228.4
147.5°	1276.4	1272.5	1268.6	1267.0	1267.9	1268.9	1269.7	1270.6	1269.7	1268.9	1267.9
150°	1299.6	1295.8	1292.1	1291.0	1292.6	1294.3	1296.0	1297.6	1296.0	1294.3	1292.6
152.5°	1321.0	1317.4	1313.9	1313.0	1314.8	1316.6	1318.5	1320.3	1318.5	1316.6	1314.8
155°	1350.9	1348.2	1345.3	1345.0	1347.0	1349.2	1351.3	1353.4	1351.3	1349.2	1347.0
157.5°	1376.2	1374.2	1372.3	1372.2	1374.0	1375.7	1377.5	1379.3	1377.5	1375.7	1374.0
160°	1391.6	1390.3	1388.9	1388.9	1390.3	1391.6	1393.1	1394.5	1393.1	1391.6	1390.3
162.5°	1404.6	1403.4	1402.2	1402.3	1403.8	1405.2	1406.5	1408.0	1406.5	1405.2	1403.8
165°	1421.5	1420.8	1420.1	1420.5	1421.9	1423.2	1424.7	1426.1	1424.7	1423.2	1421.9
167.5°	1434.9	1434.3	1433.6	1433.9	1435.4	1436.8	1438.1	1439.6	1438.1	1436.8	1435.4
170°	1442.0	1441.5	1441.1	1441.5	1442.9	1444.3	1445.7	1447.2	1445.7	1444.3	1442.9
172.5°	1447.0	1446.6	1446.1	1446.6	1447.9	1449.4	1450.8	1452.2	1450.8	1449.4	1447.9
175°	1452.5	1452.1	1451.6	1452.2	1453.8	1455.4	1457.1	1458.7	1457.1	1455.4	1453.8
177.5°	1454.3	1454.1	1454.0	1454.5	1455.9	1457.2	1458.4	1459.7	1458.4	1457.2	1455.9
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331483-935

CATALOG NUMBER: S122DIW-S290D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	502.2	501.3	498.0	496.3	493.4	490.8	489.0	489.8	490.4	490.2	489.7
5°	487.8	484.1	478.4	473.6	470.0	463.6	460.8	459.4	458.2	456.9	455.6
7.5°	470.6	464.8	456.7	449.7	443.2	435.1	430.5	427.8	425.0	421.9	419.1
10°	458.5	450.2	441.6	431.9	424.0	416.8	410.4	406.0	402.1	398.4	395.7
12.5°	445.7	436.2	425.5	412.2	403.6	393.1	392.2	384.6	378.5	376.2	373.0
15°	425.2	411.9	398.4	382.5	375.7	366.4	360.5	354.6	349.3	345.6	344.7
17.5°	402.0	384.8	371.3	360.0	348.8	339.1	333.7	329.1	324.7	319.8	319.1
20°	384.4	369.5	354.8	344.8	333.3	323.5	316.8	312.2	308.4	305.5	303.0
22.5°	367.6	351.3	337.9	327.0	315.6	307.7	302.5	297.9	294.8	291.6	289.2
25°	340.7	328.0	313.3	301.0	291.6	286.5	282.2	278.4	276.4	274.2	271.5
27.5°	317.2	303.1	289.4	279.8	271.6	267.1	264.0	261.3	259.5	258.2	256.7
30°	300.7	286.4	275.6	266.2	259.3	254.9	252.9	251.3	249.2	248.4	247.6
32.5°	284.6	271.8	262.6	254.4	248.0	245.0	243.2	241.8	240.1	239.4	237.7
35°	262.1	251.3	242.4	237.8	232.6	230.0	228.7	226.7	225.2	224.4	224.1
37.5°	240.8	231.5	225.6	219.8	217.6	216.0	214.1	212.8	212.3	212.2	212.0
40°	227.0	219.5	214.1	209.5	208.5	206.1	204.6	203.5	203.5	203.6	203.5
42.5°	214.6	207.7	203.0	199.0	197.9	196.5	194.8	194.8	195.1	195.8	195.1
45°	195.6	190.7	187.4	185.5	183.3	181.9	181.7	182.3	182.4	182.7	183.3
47.5°	178.1	174.9	171.9	169.7	168.8	168.6	168.3	169.4	170.3	170.7	171.5
50°	167.8	164.1	161.5	160.1	159.4	159.0	159.4	160.6	161.4	162.3	162.9
52.5°	156.3	153.6	151.9	150.8	150.5	150.8	150.8	152.1	153.3	153.8	154.0
55°	140.3	138.3	137.9	136.1	136.9	136.7	137.7	138.4	139.7	140.9	141.0
57.5°	124.2	122.7	121.7	121.8	122.1	123.0	123.7	125.1	126.3	127.6	127.7
60°	113.7	112.9	112.3	112.3	112.6	113.8	114.8	116.1	116.9	117.8	118.3
62.5°	103.9	103.1	102.5	102.9	103.9	104.6	105.7	106.5	107.3	108.1	108.3
65°	88.6	88.3	88.8	89.2	89.4	90.3	91.7	92.3	93.1	93.5	94.9
67.5°	74.5	74.6	74.5	75.0	76.2	76.4	77.7	79.0	79.2	80.0	80.8
70°	64.9	65.3	65.7	66.1	67.1	67.5	68.4	69.1	69.8	70.4	71.0
72.5°	56.1	56.2	56.7	56.6	57.4	58.2	59.1	59.7	60.4	61.2	61.7
75°	43.2	43.2	43.7	43.8	44.8	45.8	45.5	46.0	46.8	47.5	48.0
77.5°	31.6	31.2	31.6	31.8	32.1	32.9	33.1	33.6	34.5	34.3	34.7
80°	24.0	23.5	24.0	24.3	24.3	25.2	25.2	25.7	26.2	25.7	26.2
82.5°	17.1	16.9	17.3	17.4	17.7	17.7	18.0	18.1	18.7	18.4	18.7
85°	8.6	8.4	8.6	8.4	8.6	8.8	8.8	8.6	8.6	9.0	8.4
87.5°	4.9	5.3	5.4	5.8	6.0	6.3	6.3	6.5	6.8	6.7	6.9
90°	11.4	13.6	15.4	17.3	19.2	21.1	22.2	23.4	24.5	25.7	26.6
92.5°	20.3	20.7	21.6	22.6	23.5	24.5	25.1	25.7	26.3	26.9	27.3
95°	37.5	34.5	36.2	37.8	39.4	41.1	42.3	43.4	44.6	45.7	46.2
97.5°	48.8	39.8	43.6	47.4	51.2	55.0	55.9	56.8	57.8	58.7	59.3
100°	58.2	44.1	48.1	52.1	56.1	60.0	61.9	63.8	65.6	67.5	68.7
102.5°	214.9	194.8	161.5	128.3	95.0	61.7	64.1	66.6	69.1	71.5	73.0
105°	348.3	319.9	256.0	192.0	128.1	64.2	66.8	69.4	72.0	74.6	76.3
107.5°	432.0	396.5	319.9	243.2	166.6	90.0	87.3	84.7	82.1	79.5	78.6
110°	486.2	454.9	387.3	319.6	251.9	184.3	160.9	137.5	114.1	90.7	79.5



TEST NUMBER: P331483-935

CATALOG NUMBER: S122DIW-S290D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	538.0	531.8	515.1	498.3	481.6	464.9	379.5	294.1	208.8	123.4	81.0
115°	621.6	626.5	632.3	638.2	644.0	649.9	541.5	433.1	324.8	216.4	153.8
117.5°	699.5	703.7	707.7	711.7	715.7	719.8	693.5	667.4	641.1	614.9	574.1
120°	751.3	755.2	759.4	763.6	767.8	772.0	774.8	777.7	780.4	783.3	768.9
122.5°	799.3	803.4	808.0	812.5	817.2	821.7	823.4	825.1	826.8	828.5	826.2
125°	868.4	872.2	876.7	881.1	885.5	890.0	891.7	893.3	894.9	896.6	897.7
127.5°	934.9	938.2	941.5	944.9	948.1	951.5	953.9	956.2	958.6	961.0	962.3
130°	977.7	980.8	983.3	985.9	988.5	991.1	993.7	996.3	998.8	1001.3	1002.5
132.5°	1017.5	1020.4	1023.0	1025.5	1028.1	1030.7	1032.9	1035.1	1037.2	1039.5	1040.4
135°	1074.5	1077.5	1079.5	1081.7	1083.7	1085.9	1088.2	1090.5	1092.9	1095.3	1096.1
137.5°	1125.4	1127.9	1130.3	1132.7	1135.1	1137.5	1139.8	1142.0	1144.4	1146.7	1147.4
140°	1158.6	1160.9	1163.5	1166.1	1168.6	1171.2	1173.3	1175.4	1177.5	1179.7	1180.1
142.5°	1188.3	1190.6	1193.5	1196.4	1199.4	1202.4	1204.3	1206.2	1208.2	1210.0	1210.4
145°	1228.2	1230.0	1234.1	1238.0	1242.0	1246.0	1247.6	1249.2	1250.9	1252.5	1252.8
147.5°	1267.0	1268.6	1272.5	1276.4	1280.4	1284.3	1285.6	1286.8	1288.0	1289.2	1289.3
150°	1291.0	1292.1	1295.8	1299.6	1303.3	1307.1	1308.5	1309.8	1311.3	1312.7	1312.8
152.5°	1313.0	1313.9	1317.4	1321.0	1324.6	1328.1	1329.6	1330.9	1332.3	1333.8	1333.7
155°	1345.0	1345.3	1348.2	1350.9	1353.8	1356.6	1358.0	1359.3	1360.8	1362.2	1361.9
157.5°	1372.2	1372.3	1374.2	1376.2	1378.2	1380.2	1381.7	1383.4	1384.9	1386.6	1386.4
160°	1388.9	1388.9	1390.3	1391.6	1393.1	1394.5	1395.9	1397.3	1398.7	1400.1	1400.0
162.5°	1402.3	1402.2	1403.4	1404.6	1405.9	1407.1	1408.7	1410.3	1411.9	1413.5	1413.2
165°	1420.5	1420.1	1420.8	1421.5	1422.2	1422.9	1424.5	1426.2	1427.8	1429.4	1429.4
167.5°	1433.9	1433.6	1434.3	1434.9	1435.5	1436.1	1437.8	1439.4	1441.1	1442.7	1442.5
170°	1441.5	1441.1	1441.5	1442.0	1442.4	1442.9	1444.6	1446.2	1447.9	1449.5	1449.2
172.5°	1446.6	1446.1	1446.6	1447.0	1447.5	1447.9	1449.6	1451.2	1452.9	1454.5	1454.3
175°	1452.2	1451.6	1452.1	1452.5	1453.0	1453.5	1455.1	1456.7	1458.4	1460.0	1459.7
177.5°	1454.5	1454.0	1454.1	1454.3	1454.5	1454.7	1456.0	1457.3	1458.6	1460.0	1459.7
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331483-935

CATALOG NUMBER: S122DIW-S290D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	488.1	487.8	487.8	486.4	487.8	487.8	488.1	489.7	490.2	490.4	489.8
5°	452.8	452.2	451.3	452.2	451.3	452.2	452.8	455.6	456.9	458.2	459.4
7.5°	417.8	415.5	415.2	412.8	415.2	415.5	417.8	419.1	421.9	425.0	427.8
10°	392.4	390.8	390.5	386.8	390.5	390.8	392.4	395.7	398.4	402.1	406.0
12.5°	373.0	369.2	370.0	367.8	370.0	369.2	373.0	373.0	376.2	378.5	384.6
15°	339.3	339.3	338.5	335.3	338.5	339.3	339.3	344.7	345.6	349.3	354.6
17.5°	315.2	314.8	313.0	313.9	313.0	314.8	315.2	319.1	319.8	324.7	329.1
20°	300.8	299.6	297.3	297.3	297.3	299.6	300.8	303.0	305.5	308.4	312.2
22.5°	287.2	287.1	284.6	285.4	284.6	287.1	287.2	289.2	291.6	294.8	297.9
25°	271.3	269.8	268.5	269.1	268.5	269.8	271.3	271.5	274.2	276.4	278.4
27.5°	256.1	255.3	255.2	253.7	255.2	255.3	256.1	256.7	258.2	259.5	261.3
30°	247.5	245.5	245.8	244.9	245.8	245.5	247.5	247.6	248.4	249.2	251.3
32.5°	237.4	236.7	236.3	235.5	236.3	236.7	237.4	237.7	239.4	240.1	241.8
35°	223.8	223.9	223.0	223.3	223.0	223.9	223.8	224.1	224.4	225.2	226.7
37.5°	211.8	212.4	212.0	212.1	212.0	212.4	211.8	212.0	212.2	212.3	212.8
40°	204.0	204.0	204.0	204.6	204.0	204.0	204.0	203.5	203.6	203.5	203.5
42.5°	196.5	196.1	195.9	195.8	195.9	196.1	196.5	195.1	195.8	195.1	194.8
45°	183.7	184.3	184.4	183.5	184.4	184.3	183.7	183.3	182.7	182.4	182.3
47.5°	172.0	172.1	172.0	172.9	172.0	172.1	172.0	171.5	170.7	170.3	169.4
50°	163.9	163.5	163.9	163.5	163.9	163.5	163.9	162.9	162.3	161.4	160.6
52.5°	155.3	155.4	155.2	155.1	155.2	155.4	155.3	154.0	153.8	153.3	152.1
55°	141.8	142.2	142.0	142.0	142.0	142.2	141.8	141.0	140.9	139.7	138.4
57.5°	127.9	128.2	128.5	127.6	128.5	128.2	127.9	127.7	127.6	126.3	125.1
60°	118.1	119.1	118.9	118.6	118.9	119.1	118.1	118.3	117.8	116.9	116.1
62.5°	109.2	109.6	109.5	109.4	109.5	109.6	109.2	108.3	108.1	107.3	106.5
65°	95.5	95.8	95.2	95.8	95.2	95.8	95.5	94.9	93.5	93.1	92.3
67.5°	80.6	80.8	81.2	81.5	81.2	80.8	80.6	80.8	80.0	79.2	79.0
70°	71.4	71.2	71.8	72.4	71.8	71.2	71.4	71.0	70.4	69.8	69.1
72.5°	61.6	62.1	61.9	62.3	61.9	62.1	61.6	61.7	61.2	60.4	59.7
75°	47.5	48.1	48.0	48.5	48.0	48.1	47.5	48.0	47.5	46.8	46.0
77.5°	34.4	34.4	34.4	34.7	34.4	34.4	34.4	34.7	34.3	34.5	33.6
80°	26.2	25.8	25.4	26.2	25.4	25.8	26.2	26.2	25.7	26.2	25.7
82.5°	18.3	18.4	18.1	18.1	18.1	18.4	18.3	18.7	18.4	18.7	18.1
85°	8.4	8.2	7.8	7.8	7.8	8.2	8.4	8.4	9.0	8.6	8.6
87.5°	7.0	6.9	7.0	7.0	7.0	6.9	7.0	6.9	6.7	6.8	6.5
90°	27.0	27.5	28.0	28.4	28.0	27.5	27.0	26.6	25.7	24.5	23.4
92.5°	27.6	27.9	28.2	28.4	28.2	27.9	27.6	27.3	26.9	26.3	25.7
95°	46.0	45.7	45.5	45.3	45.5	45.7	46.0	46.2	45.7	44.6	43.4
97.5°	59.6	59.9	60.2	60.4	60.2	59.9	59.6	59.3	58.7	57.8	56.8
100°	69.1	69.7	70.1	70.6	70.1	69.7	69.1	68.7	67.5	65.6	63.8
102.5°	73.6	74.3	75.0	75.6	75.0	74.3	73.6	73.0	71.5	69.1	66.6
105°	77.2	78.2	79.1	80.1	79.1	78.2	77.2	76.3	74.6	72.0	69.4
107.5°	79.6	80.5	81.5	82.4	81.5	80.5	79.6	78.6	79.5	82.1	84.7
110°	80.4	81.4	82.3	83.2	82.3	81.4	80.4	79.5	90.7	114.1	137.5



TEST NUMBER: P331483-935

CATALOG NUMBER: S122DIW-S290D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	81.8	82.6	83.3	84.0	83.3	82.6	81.8	81.0	123.4	208.8	294.1
115°	136.9	120.1	103.2	86.4	103.2	120.1	136.9	153.8	216.4	324.8	433.1
117.5°	518.8	463.4	408.0	352.6	408.0	463.4	518.8	574.1	614.9	641.1	667.4
120°	737.3	705.7	674.1	642.5	674.1	705.7	737.3	768.9	783.3	780.4	777.7
122.5°	820.1	814.0	807.9	801.7	807.9	814.0	820.1	826.2	828.5	826.8	825.1
125°	898.4	899.1	899.8	900.5	899.8	899.1	898.4	897.7	896.6	894.9	893.3
127.5°	962.4	962.6	962.7	962.9	962.7	962.6	962.4	962.3	961.0	958.6	956.2
130°	1002.3	1002.1	1001.9	1001.6	1001.9	1002.1	1002.3	1002.5	1001.3	998.8	996.3
132.5°	1040.3	1040.0	1039.7	1039.6	1039.7	1040.0	1040.3	1040.4	1039.5	1037.2	1035.1
135°	1095.7	1095.3	1094.8	1094.3	1094.8	1095.3	1095.7	1096.1	1095.3	1092.9	1090.5
137.5°	1146.6	1145.8	1145.0	1144.2	1145.0	1145.8	1146.6	1147.4	1146.7	1144.4	1142.0
140°	1178.9	1177.8	1176.6	1175.4	1176.6	1177.8	1178.9	1180.1	1179.7	1177.5	1175.4
142.5°	1209.3	1208.1	1206.9	1205.7	1206.9	1208.1	1209.3	1210.4	1210.0	1208.2	1206.2
145°	1251.5	1250.4	1249.2	1248.1	1249.2	1250.4	1251.5	1252.8	1252.5	1250.9	1249.2
147.5°	1288.3	1287.3	1286.3	1285.4	1286.3	1287.3	1288.3	1289.3	1289.2	1288.0	1286.8
150°	1311.6	1310.4	1309.2	1308.1	1309.2	1310.4	1311.6	1312.8	1312.7	1311.3	1309.8
152.5°	1332.1	1330.6	1329.0	1327.5	1329.0	1330.6	1332.1	1333.7	1333.8	1332.3	1330.9
155°	1360.0	1358.2	1356.3	1354.4	1356.3	1358.2	1360.0	1361.9	1362.2	1360.8	1359.3
157.5°	1384.6	1382.8	1381.0	1379.1	1381.0	1382.8	1384.6	1386.4	1386.6	1384.9	1383.4
160°	1398.4	1396.7	1395.1	1393.4	1395.1	1396.7	1398.4	1400.0	1400.1	1398.7	1397.3
162.5°	1411.3	1409.2	1407.2	1405.2	1407.2	1409.2	1411.3	1413.2	1413.5	1411.9	1410.3
165°	1427.8	1426.2	1424.5	1422.9	1424.5	1426.2	1427.8	1429.4	1429.4	1427.8	1426.2
167.5°	1440.4	1438.3	1436.1	1434.1	1436.1	1438.3	1440.4	1442.5	1442.7	1441.1	1439.4
170°	1447.2	1445.0	1442.9	1440.8	1442.9	1445.0	1447.2	1449.2	1449.5	1447.9	1446.2
172.5°	1452.2	1450.1	1447.9	1445.9	1447.9	1450.1	1452.2	1454.3	1454.5	1452.9	1451.2
175°	1457.3	1455.0	1452.6	1450.3	1452.6	1455.0	1457.3	1459.7	1460.0	1458.4	1456.7
177.5°	1458.1	1456.4	1454.7	1453.0	1454.7	1456.4	1458.1	1459.7	1460.0	1458.6	1457.3
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331483-935

CATALOG NUMBER: S122DIW-S290D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	489.0	490.8	493.4	496.3	498.0	501.3	502.2	503.8	505.1	508.4	511.9
5°	460.8	463.6	470.0	473.6	478.4	484.1	487.8	491.7	496.0	503.4	510.3
7.5°	430.5	435.1	443.2	449.7	456.7	464.8	470.6	478.4	484.8	495.3	505.3
10°	410.4	416.8	424.0	431.9	441.6	450.2	458.5	468.2	476.0	488.6	500.3
12.5°	392.2	393.1	403.6	412.2	425.5	436.2	445.7	458.2	465.9	480.8	493.1
15°	360.5	366.4	375.7	382.5	398.4	411.9	425.2	438.3	447.1	465.5	481.7
17.5°	333.7	339.1	348.8	360.0	371.3	384.8	402.0	415.9	427.8	448.8	468.0
20°	316.8	323.5	333.3	344.8	354.8	369.5	384.4	400.2	413.1	436.8	459.3
22.5°	302.5	307.7	315.6	327.0	337.9	351.3	367.6	384.9	398.4	424.0	446.7
25°	282.2	286.5	291.6	301.0	313.3	328.0	340.7	359.7	379.4	403.3	430.8
27.5°	264.0	267.1	271.6	279.8	289.4	303.1	317.2	335.2	355.1	381.0	410.1
30°	252.9	254.9	259.3	266.2	275.6	286.4	300.7	317.8	338.2	364.4	393.3
32.5°	243.2	245.0	248.0	254.4	262.6	271.8	284.6	301.9	321.2	347.0	379.1
35°	228.7	230.0	232.6	237.8	242.4	251.3	262.1	277.8	295.9	320.6	353.8
37.5°	214.1	216.0	217.6	219.8	225.6	231.5	240.8	254.1	271.9	296.8	328.5
40°	204.6	206.1	208.5	209.5	214.1	219.5	227.0	239.2	257.2	279.9	310.8
42.5°	194.8	196.5	197.9	199.0	203.0	207.7	214.6	225.0	240.9	262.9	293.6
45°	181.7	181.9	183.3	185.5	187.4	190.7	195.6	204.6	216.9	237.6	265.4
47.5°	168.3	168.6	168.8	169.7	171.9	174.9	178.1	185.5	196.5	213.0	240.0
50°	159.4	159.0	159.4	160.1	161.5	164.1	167.8	173.1	182.1	197.5	222.4
52.5°	150.8	150.8	150.5	150.8	151.9	153.6	156.3	160.7	168.8	183.0	204.8
55°	137.7	136.7	136.9	136.1	137.9	138.3	140.3	144.0	151.0	160.7	181.3
57.5°	123.7	123.0	122.1	121.8	121.7	122.7	124.2	127.2	132.6	141.2	157.8
60°	114.8	113.8	112.6	112.3	112.3	112.9	113.7	115.8	120.9	128.5	142.2
62.5°	105.7	104.6	103.9	102.9	102.5	103.1	103.9	105.5	109.2	116.3	128.1
65°	91.7	90.3	89.4	89.2	88.8	88.3	88.6	90.1	93.1	98.8	108.1
67.5°	77.7	76.4	76.2	75.0	74.5	74.6	74.5	75.8	77.6	82.5	89.5
70°	68.4	67.5	67.1	66.1	65.7	65.3	64.9	66.1	67.8	72.0	78.0
72.5°	59.1	58.2	57.4	56.6	56.7	56.2	56.1	56.9	58.3	62.1	66.8
75°	45.5	45.8	44.8	43.8	43.7	43.2	43.2	43.8	44.4	47.4	51.1
77.5°	33.1	32.9	32.1	31.8	31.6	31.2	31.6	31.9	32.3	34.3	36.9
80°	25.2	25.2	24.3	24.3	24.0	23.5	24.0	23.7	24.5	26.4	28.3
82.5°	18.0	17.7	17.7	17.4	17.3	16.9	17.1	17.6	17.9	19.2	20.4
85°	8.8	8.8	8.6	8.4	8.6	8.4	8.6	8.8	9.0	9.6	10.6
87.5°	6.3	6.3	6.0	5.8	5.4	5.3	4.9	4.6	4.4	4.0	3.6
90°	22.2	21.1	19.2	17.3	15.4	13.6	11.4	8.8	6.2	3.6	1.0
92.5°	25.1	24.5	23.5	22.6	21.6	20.7	20.3	20.6	20.8	21.0	21.3
95°	42.3	41.1	39.4	37.8	36.2	34.5	37.5	45.3	53.0	60.7	68.4
97.5°	55.9	55.0	51.2	47.4	43.6	39.8	48.8	70.6	92.3	114.1	135.9
100°	61.9	60.0	56.1	52.1	48.1	44.1	58.2	90.2	122.3	154.4	186.4
102.5°	64.1	61.7	95.0	128.3	161.5	194.8	214.9	221.7	228.4	235.2	242.0
105°	66.8	64.2	128.1	192.0	256.0	319.9	348.3	341.2	334.2	327.2	320.2
107.5°	87.3	90.0	166.6	243.2	319.9	396.5	432.0	426.3	420.6	414.9	409.3
110°	160.9	184.3	251.9	319.6	387.3	454.9	486.2	481.3	476.4	471.5	466.6



TEST NUMBER: P331483-935

CATALOG NUMBER: S122DIW-S290D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	379.5	464.9	481.6	498.3	515.1	531.8	538.0	533.6	529.2	524.9	520.5
115°	541.5	649.9	644.0	638.2	632.3	626.5	621.6	617.5	613.5	609.6	605.6
117.5°	693.5	719.8	715.7	711.7	707.7	703.7	699.5	695.0	690.5	686.1	681.7
120°	774.8	772.0	767.8	763.6	759.4	755.2	751.3	747.8	744.2	740.8	737.3
122.5°	823.4	821.7	817.2	812.5	808.0	803.4	799.3	795.6	791.9	788.2	784.5
125°	891.7	890.0	885.5	881.1	876.7	872.2	868.4	865.4	862.4	859.3	856.3
127.5°	953.9	951.5	948.1	944.9	941.5	938.2	934.9	931.5	928.1	924.7	921.4
130°	993.7	991.1	988.5	985.9	983.3	980.8	977.7	973.9	970.2	966.4	962.7
132.5°	1032.9	1030.7	1028.1	1025.5	1023.0	1020.4	1017.5	1014.3	1011.2	1008.0	1004.8
135°	1088.2	1085.9	1083.7	1081.7	1079.5	1077.5	1074.5	1070.7	1067.0	1063.2	1059.5
137.5°	1139.8	1137.5	1135.1	1132.7	1130.3	1127.9	1125.4	1122.8	1120.2	1117.6	1114.9
140°	1173.3	1171.2	1168.6	1166.1	1163.5	1160.9	1158.6	1156.8	1154.9	1153.1	1151.2
142.5°	1204.3	1202.4	1199.4	1196.4	1193.5	1190.6	1188.3	1186.5	1184.9	1183.2	1181.6
145°	1247.6	1246.0	1242.0	1238.0	1234.1	1230.0	1228.2	1228.4	1228.6	1228.9	1229.1
147.5°	1285.6	1284.3	1280.4	1276.4	1272.5	1268.6	1267.0	1267.9	1268.9	1269.7	1270.6
150°	1308.5	1307.1	1303.3	1299.6	1295.8	1292.1	1291.0	1292.6	1294.3	1296.0	1297.6
152.5°	1329.6	1328.1	1324.6	1321.0	1317.4	1313.9	1313.0	1314.8	1316.6	1318.5	1320.3
155°	1358.0	1356.6	1353.8	1350.9	1348.2	1345.3	1345.0	1347.0	1349.2	1351.3	1353.4
157.5°	1381.7	1380.2	1378.2	1376.2	1374.2	1372.3	1372.2	1374.0	1375.7	1377.5	1379.3
160°	1395.9	1394.5	1393.1	1391.6	1390.3	1388.9	1388.9	1390.3	1391.6	1393.1	1394.5
162.5°	1408.7	1407.1	1405.9	1404.6	1403.4	1402.2	1402.3	1403.8	1405.2	1406.5	1408.0
165°	1424.5	1422.9	1422.2	1421.5	1420.8	1420.1	1420.5	1421.9	1423.2	1424.7	1426.1
167.5°	1437.8	1436.1	1435.5	1434.9	1434.3	1433.6	1433.9	1435.4	1436.8	1438.1	1439.6
170°	1444.6	1442.9	1442.4	1442.0	1441.5	1441.1	1441.5	1442.9	1444.3	1445.7	1447.2
172.5°	1449.6	1447.9	1447.5	1447.0	1446.6	1446.1	1446.6	1447.9	1449.4	1450.8	1452.2
175°	1455.1	1453.5	1453.0	1452.5	1452.1	1451.6	1452.2	1453.8	1455.4	1457.1	1458.7
177.5°	1456.0	1454.7	1454.5	1454.3	1454.1	1454.0	1454.5	1455.9	1457.2	1458.4	1459.7
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331483-935

CATALOG NUMBER: S122DIW-S290D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	511.6	512.4	514.9	517.4	520.2	521.0	522.2	521.2	520.8	523.7	526.0
5°	513.1	516.5	523.4	529.7	534.9	538.6	542.6	544.2	547.1	551.1	556.3
7.5°	511.3	518.2	529.0	538.1	548.0	555.2	560.8	565.6	571.4	579.1	587.6
10°	509.5	518.7	531.8	542.9	555.1	564.3	571.9	579.4	588.0	598.7	609.8
12.5°	506.1	516.9	533.4	546.6	562.1	571.2	581.4	597.4	606.7	621.7	637.4
15°	499.1	511.3	534.2	550.4	568.0	585.2	604.2	619.4	634.6	643.5	665.6
17.5°	488.9	506.6	532.0	551.0	573.3	600.4	621.7	639.0	656.6	670.9	682.0
20°	480.5	499.9	528.9	551.6	578.2	607.3	631.7	649.4	664.6	676.6	683.4
22.5°	470.1	494.5	522.6	549.2	583.2	612.0	637.7	651.5	664.3	670.1	672.8
25°	453.6	482.9	514.8	547.3	585.6	616.1	639.6	648.0	651.7	646.0	636.6
27.5°	435.8	468.5	505.8	543.5	584.1	613.5	630.3	629.0	622.7	604.2	589.6
30°	422.5	458.5	498.5	539.8	580.5	609.1	618.8	609.1	594.8	574.3	553.3
32.5°	408.5	445.8	490.9	534.5	573.9	599.1	601.2	584.4	562.2	538.9	512.8
35°	387.4	427.7	476.5	522.6	560.0	575.8	566.5	536.7	510.5	478.6	443.0
37.5°	363.6	408.1	456.9	505.2	539.1	543.2	519.9	488.6	451.6	414.1	372.2
40°	345.8	393.0	443.2	491.9	521.9	517.5	487.8	453.4	409.4	363.6	324.7
42.5°	329.8	376.9	428.2	476.0	499.9	488.1	453.4	411.1	363.9	320.7	285.1
45°	302.2	350.7	403.1	449.3	463.0	441.6	395.7	348.7	302.2	266.2	238.1
47.5°	275.3	323.3	375.2	415.8	420.6	391.9	341.7	293.4	253.4	224.1	204.2
50°	255.6	303.8	355.2	391.4	389.8	355.2	303.6	257.6	224.1	200.4	187.2
52.5°	238.0	283.4	332.8	365.8	357.4	319.7	270.4	229.5	202.1	183.6	171.5
55°	210.4	252.5	299.5	325.9	310.6	268.7	227.0	194.2	173.8	160.0	150.6
57.5°	183.1	222.6	262.8	279.1	262.2	223.5	188.8	165.0	149.6	139.4	133.3
60°	166.3	200.7	236.4	250.6	230.4	196.0	168.6	147.3	134.9	126.6	121.1
62.5°	149.4	180.2	214.0	221.6	203.2	174.1	149.8	132.1	122.0	114.5	109.3
65°	126.3	151.6	177.2	182.3	165.3	142.8	123.6	112.1	103.1	97.6	93.5
67.5°	103.7	123.9	142.1	146.1	131.2	115.6	101.8	91.7	85.7	81.1	77.6
70°	90.1	106.2	121.1	124.4	112.4	98.6	88.0	80.0	74.5	70.6	67.2
72.5°	75.9	89.3	101.7	103.9	94.2	83.5	74.9	68.5	63.7	61.2	58.0
75°	58.1	66.0	75.5	76.1	69.7	63.2	56.6	52.4	49.9	46.8	45.2
77.5°	41.0	47.1	52.6	53.6	49.9	45.5	41.8	38.5	36.3	34.9	33.4
80°	31.3	36.2	38.6	39.9	37.2	34.0	31.9	29.7	28.3	27.4	26.4
82.5°	22.4	25.4	27.6	28.7	27.1	25.2	23.2	21.9	20.8	20.1	19.7
85°	11.4	12.7	14.1	14.5	14.1	13.3	12.1	12.1	11.5	11.4	11.4
87.5°	4.6	5.8	6.3	7.3	7.4	7.7	8.2	8.4	8.6	8.7	8.8
90°	3.6	6.2	8.8	11.4	13.6	15.4	17.3	19.2	21.1	22.2	23.4
92.5°	21.0	20.8	20.6	20.3	20.7	21.6	22.6	23.5	24.5	25.1	25.7
95°	60.7	53.0	45.3	37.5	34.5	36.2	37.8	39.4	41.1	42.3	43.4
97.5°	114.1	92.3	70.6	48.8	39.8	43.6	47.4	51.2	55.0	55.9	56.8
100°	154.4	122.3	90.2	58.2	44.1	48.1	52.1	56.1	60.0	61.9	63.8
102.5°	235.2	228.4	221.7	214.9	194.8	161.5	128.3	95.0	61.7	64.1	66.6
105°	327.2	334.2	341.2	348.3	319.9	256.0	192.0	128.1	64.2	66.8	69.4
107.5°	414.9	420.6	426.3	432.0	396.5	319.9	243.2	166.6	90.0	87.3	84.7
110°	471.5	476.4	481.3	486.2	454.9	387.3	319.6	251.9	184.3	160.9	137.5



TEST NUMBER: P331483-935

CATALOG NUMBER: S122DIW-S290D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	524.9	529.2	533.6	538.0	531.8	515.1	498.3	481.6	464.9	379.5	294.1
115°	609.6	613.5	617.5	621.6	626.5	632.3	638.2	644.0	649.9	541.5	433.1
117.5°	686.1	690.5	695.0	699.5	703.7	707.7	711.7	715.7	719.8	693.5	667.4
120°	740.8	744.2	747.8	751.3	755.2	759.4	763.6	767.8	772.0	774.8	777.7
122.5°	788.2	791.9	795.6	799.3	803.4	808.0	812.5	817.2	821.7	823.4	825.1
125°	859.3	862.4	865.4	868.4	872.2	876.7	881.1	885.5	890.0	891.7	893.3
127.5°	924.7	928.1	931.5	934.9	938.2	941.5	944.9	948.1	951.5	953.9	956.2
130°	966.4	970.2	973.9	977.7	980.8	983.3	985.9	988.5	991.1	993.7	996.3
132.5°	1008.0	1011.2	1014.3	1017.5	1020.4	1023.0	1025.5	1028.1	1030.7	1032.9	1035.1
135°	1063.2	1067.0	1070.7	1074.5	1077.5	1079.5	1081.7	1083.7	1085.9	1088.2	1090.5
137.5°	1117.6	1120.2	1122.8	1125.4	1127.9	1130.3	1132.7	1135.1	1137.5	1139.8	1142.0
140°	1153.1	1154.9	1156.8	1158.6	1160.9	1163.5	1166.1	1168.6	1171.2	1173.3	1175.4
142.5°	1183.2	1184.9	1186.5	1188.3	1190.6	1193.5	1196.4	1199.4	1202.4	1204.3	1206.2
145°	1228.9	1228.6	1228.4	1228.2	1230.0	1234.1	1238.0	1242.0	1246.0	1247.6	1249.2
147.5°	1269.7	1268.9	1267.9	1267.0	1268.6	1272.5	1276.4	1280.4	1284.3	1285.6	1286.8
150°	1296.0	1294.3	1292.6	1291.0	1292.1	1295.8	1299.6	1303.3	1307.1	1308.5	1309.8
152.5°	1318.5	1316.6	1314.8	1313.0	1313.9	1317.4	1321.0	1324.6	1328.1	1329.6	1330.9
155°	1351.3	1349.2	1347.0	1345.0	1345.3	1348.2	1350.9	1353.8	1356.6	1358.0	1359.3
157.5°	1377.5	1375.7	1374.0	1372.2	1372.3	1374.2	1376.2	1378.2	1380.2	1381.7	1383.4
160°	1393.1	1391.6	1390.3	1388.9	1388.9	1390.3	1391.6	1393.1	1394.5	1395.9	1397.3
162.5°	1406.5	1405.2	1403.8	1402.3	1402.2	1403.4	1404.6	1405.9	1407.1	1408.7	1410.3
165°	1424.7	1423.2	1421.9	1420.5	1420.1	1420.8	1421.5	1422.2	1422.9	1424.5	1426.2
167.5°	1438.1	1436.8	1435.4	1433.9	1433.6	1434.3	1434.9	1435.5	1436.1	1437.8	1439.4
170°	1445.7	1444.3	1442.9	1441.5	1441.1	1441.5	1442.0	1442.4	1442.9	1444.6	1446.2
172.5°	1450.8	1449.4	1447.9	1446.6	1446.1	1446.6	1447.0	1447.5	1447.9	1449.6	1451.2
175°	1457.1	1455.4	1453.8	1452.2	1451.6	1452.1	1452.5	1453.0	1453.5	1455.1	1456.7
177.5°	1458.4	1457.2	1455.9	1454.5	1454.0	1454.1	1454.3	1454.5	1454.7	1456.0	1457.3
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331483-935

CATALOG NUMBER: S122DIW-S290D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	527.9	530.0	530.0	530.4	532.9	532.5	532.4
5°	561.7	565.1	565.4	568.9	571.3	570.5	568.3
7.5°	593.7	599.9	604.6	607.2	610.3	612.2	611.3
10°	619.1	628.0	633.5	637.2	641.7	645.1	643.9
12.5°	642.0	652.7	660.3	666.7	667.2	671.5	668.6
15°	678.0	689.2	690.4	695.1	698.9	698.4	698.6
17.5°	689.7	693.4	694.1	694.2	694.3	692.9	689.9
20°	685.5	684.2	680.9	678.3	673.8	673.2	669.3
22.5°	665.5	661.2	652.8	647.3	640.3	638.5	637.4
25°	626.1	616.5	603.2	590.5	586.9	580.1	582.0
27.5°	572.0	557.1	542.6	532.4	523.0	512.7	515.7
30°	534.0	517.1	496.8	481.1	471.1	461.4	459.6
32.5°	488.6	463.9	441.3	427.5	412.2	406.0	399.2
35°	410.4	386.2	363.8	344.4	333.3	324.7	316.8
37.5°	340.0	312.3	294.1	278.4	270.4	265.4	266.7
40°	296.4	272.1	258.7	246.8	239.4	235.9	236.7
42.5°	261.0	242.8	231.9	223.7	218.4	216.5	216.0
45°	220.8	210.7	201.6	197.0	194.4	192.3	190.9
47.5°	193.5	185.1	180.0	177.3	175.0	172.9	172.8
50°	177.0	171.5	168.0	165.1	163.3	161.8	163.2
52.5°	164.5	159.5	155.9	153.3	152.7	151.3	151.2
55°	145.9	142.0	139.5	137.1	136.0	135.2	134.1
57.5°	129.0	125.3	123.0	121.5	119.2	118.5	118.1
60°	116.9	114.0	111.7	109.7	108.7	107.2	107.2
62.5°	105.8	102.9	100.7	99.3	97.6	97.0	97.2
65°	89.8	87.4	85.2	83.7	83.3	82.1	82.6
67.5°	75.0	73.4	71.1	70.3	69.6	69.0	68.4
70°	65.1	63.5	62.4	61.2	60.6	60.6	60.6
72.5°	56.8	54.9	54.2	52.8	53.1	52.5	51.8
75°	44.0	42.8	42.3	41.7	40.7	40.7	40.7
77.5°	32.4	32.0	31.3	30.7	30.5	30.3	30.4
80°	25.1	24.8	24.5	24.5	24.0	23.8	23.5
82.5°	19.3	18.8	18.5	18.3	18.3	18.3	18.2
85°	10.9	10.6	10.6	10.8	10.3	10.3	10.6
87.5°	9.1	9.4	9.4	9.5	9.7	9.6	9.7
90°	24.5	25.7	26.6	27.0	27.5	28.0	28.4
92.5°	26.3	26.9	27.3	27.6	27.9	28.2	28.4
95°	44.6	45.7	46.2	46.0	45.7	45.5	45.3
97.5°	57.8	58.7	59.3	59.6	59.9	60.2	60.4
100°	65.6	67.5	68.7	69.1	69.7	70.1	70.6
102.5°	69.1	71.5	73.0	73.6	74.3	75.0	75.6
105°	72.0	74.6	76.3	77.2	78.2	79.1	80.1
107.5°	82.1	79.5	78.6	79.6	80.5	81.5	82.4
110°	114.1	90.7	79.5	80.4	81.4	82.3	83.2



TEST NUMBER: P331483-935

CATALOG NUMBER: S122DIW-S290D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	208.8	123.4	81.0	81.8	82.6	83.3	84.0
115°	324.8	216.4	153.8	136.9	120.1	103.2	86.4
117.5°	641.1	614.9	574.1	518.8	463.4	408.0	352.6
120°	780.4	783.3	768.9	737.3	705.7	674.1	642.5
122.5°	826.8	828.5	826.2	820.1	814.0	807.9	801.7
125°	894.9	896.6	897.7	898.4	899.1	899.8	900.5
127.5°	958.6	961.0	962.3	962.4	962.6	962.7	962.9
130°	998.8	1001.3	1002.5	1002.3	1002.1	1001.9	1001.6
132.5°	1037.2	1039.5	1040.4	1040.3	1040.0	1039.7	1039.6
135°	1092.9	1095.3	1096.1	1095.7	1095.3	1094.8	1094.3
137.5°	1144.4	1146.7	1147.4	1146.6	1145.8	1145.0	1144.2
140°	1177.5	1179.7	1180.1	1178.9	1177.8	1176.6	1175.4
142.5°	1208.2	1210.0	1210.4	1209.3	1208.1	1206.9	1205.7
145°	1250.9	1252.5	1252.8	1251.5	1250.4	1249.2	1248.1
147.5°	1288.0	1289.2	1289.3	1288.3	1287.3	1286.3	1285.4
150°	1311.3	1312.7	1312.8	1311.6	1310.4	1309.2	1308.1
152.5°	1332.3	1333.8	1333.7	1332.1	1330.6	1329.0	1327.5
155°	1360.8	1362.2	1361.9	1360.0	1358.2	1356.3	1354.4
157.5°	1384.9	1386.6	1386.4	1384.6	1382.8	1381.0	1379.1
160°	1398.7	1400.1	1400.0	1398.4	1396.7	1395.1	1393.4
162.5°	1411.9	1413.5	1413.2	1411.3	1409.2	1407.2	1405.2
165°	1427.8	1429.4	1429.4	1427.8	1426.2	1424.5	1422.9
167.5°	1441.1	1442.7	1442.5	1440.4	1438.3	1436.1	1434.1
170°	1447.9	1449.5	1449.2	1447.2	1445.0	1442.9	1440.8
172.5°	1452.9	1454.5	1454.3	1452.2	1450.1	1447.9	1445.9
175°	1458.4	1460.0	1459.7	1457.3	1455.0	1452.6	1450.3
177.5°	1458.6	1460.0	1459.7	1458.1	1456.4	1454.7	1453.0
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5

(END OF REPORT)