

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331481-935

Luminaire Tested: **S122DIW-S290D970U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331481-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D970U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4369.7 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331481-935

CATALOG NUMBER: S122DIW-S290D970U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331481-935

CATALOG NUMBER: S122DIW-S290D970U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	72	60	58	56	43	42	41	28	28	27	20
2	84	77	71	66	74	68	63	59	53	49	46	38	36	34	25	24	23	17
3	76	67	60	55	67	60	54	49	46	42	39	34	31	29	22	21	19	14
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	12
5	64	53	45	39	56	47	41	36	37	32	28	27	24	21	18	16	14	11
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13	9
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	15	13	11	8
8	50	38	31	26	44	34	28	23	27	22	19	20	17	14	13	11	10	7
9	46	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	20	38	29	23	18	23	18	15	17	14	12	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6567	6567	6567
5°	6592	6498	6536
10°	6555	6432	6465
15°	6472	6349	6342
20°	6357	6223	6216
25°	6242	6070	6070
30°	6096	5929	5876
35°	5960	5757	5673
40°	5788	5590	5482
45°	5617	5421	5286
50°	5433	5247	5061
55°	5239	5044	4856
60°	5028	4799	4624
65°	4795	4558	4348
70°	4504	4263	4060
75°	4099	3924	3830
80°	3636	3533	3347
85°	2964	2816	2538



TEST NUMBER: P331481-935

CATALOG NUMBER: S122DIW-S290D970U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	0.9
10°-20°	107.6	2.5
20°-30°	158.2	3.6
30°-40°	183.8	4.2
40°-50°	183.6	4.2
50°-60°	160.1	3.7
60°-70°	118.4	2.7
70°-80°	67.0	1.5
80°-90°	20.8	0.5
90°-100°	37.9	0.9
100°-110°	139.1	3.2
110°-120°	371.8	8.5
120°-130°	613.7	14.0
130°-140°	652.7	14.9
140°-150°	606.6	13.9
150°-160°	487.7	11.2
160°-170°	314.3	7.2
170°-180°	108.2	2.5
0°-30°	304.1	7.0
0°-40°	487.8	11.2
0°-60°	831.5	19.0
0°-90°	1037.7	23.7
90°-120°	548.8	12.6
90°-150°	2421.8	55.4
90°-180°	3332.0	76.3
0°-180°	4369.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	407	407	407	407	407	
5°	407	405	401	404	403	39
15°	387	385	380	381	379	109
25°	350	347	341	341	341	161
35°	302	298	292	290	288	189
45°	246	243	237	233	232	190
55°	186	184	179	175	172	166
65°	126	123	119	116	114	124
75°	66	65	63	61	61	70
85°	16	16	15	14	14	18
90°	1	10	16	20	22	3
95°	54	28	32	36	35	65
105°	250	261	50	59	62	267
115°	473	487	508	145	68	466
125°	669	680	695	701	703	596
135°	828	840	848	856	855	639
145°	960	960	973	978	975	600
155°	1057	1051	1060	1064	1058	487
165°	1114	1109	1112	1117	1112	315
175°	1139	1134	1135	1140	1133	108
180°	1137	1137	1137	1137	1137	



TEST NUMBER: P331481-935

CATALOG NUMBER: S122DIW-S290D970U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7
2.5°	408.6	408.3	407.9	407.6	407.3	406.7	406.0	405.2	404.4	403.6	404.3
5°	406.7	406.4	406.0	405.7	405.4	404.8	403.8	402.9	401.8	400.9	401.6
7.5°	403.2	402.6	402.1	401.6	401.1	400.3	399.3	398.3	397.4	396.4	397.1
10°	399.8	399.2	398.6	398.0	397.3	396.5	395.5	394.4	393.4	392.3	393.0
12.5°	395.0	394.5	394.0	393.4	392.9	392.1	391.1	390.0	389.0	388.0	388.4
15°	387.2	386.7	386.2	385.6	385.1	384.4	383.1	382.0	380.9	379.8	380.1
17.5°	377.2	376.7	376.2	375.7	375.1	374.3	373.2	372.0	370.8	369.7	370.1
20°	370.0	369.5	368.9	368.4	367.9	367.0	365.8	364.6	363.4	362.2	362.5
22.5°	362.8	362.1	361.4	360.6	359.9	359.0	357.8	356.6	355.5	354.4	354.4
25°	350.4	349.7	349.0	348.4	347.7	346.6	345.1	343.6	342.2	340.7	340.9
27.5°	336.4	335.8	335.1	334.5	333.9	332.9	331.8	330.6	329.5	328.3	328.0
30°	327.0	326.3	325.6	324.9	324.2	323.2	321.9	320.6	319.3	318.0	317.7
32.5°	316.9	316.4	315.9	315.3	314.8	313.7	312.4	311.1	309.7	308.3	307.8
35°	302.4	301.4	300.6	299.7	298.9	297.7	296.4	295.0	293.6	292.1	291.6
37.5°	285.9	285.1	284.3	283.5	282.8	281.7	280.3	279.0	277.5	276.1	275.5
40°	274.6	273.9	273.2	272.5	271.8	270.8	269.3	267.9	266.6	265.2	264.4
42.5°	263.6	262.9	262.3	261.6	260.9	259.8	258.4	257.0	255.6	254.3	253.4
45°	246.0	245.4	244.8	244.2	243.6	242.6	241.3	240.0	238.8	237.4	236.4
47.5°	228.5	227.9	227.4	226.8	226.2	225.2	223.9	222.6	221.2	219.8	218.8
50°	216.3	215.9	215.4	215.0	214.6	213.7	212.5	211.3	210.1	208.9	207.7
52.5°	204.4	203.8	203.3	202.7	202.1	201.2	200.1	199.0	197.8	196.7	195.6
55°	186.1	185.6	185.1	184.6	184.1	183.3	182.3	181.2	180.2	179.2	178.1
57.5°	167.9	167.5	167.0	166.6	166.2	165.4	164.3	163.2	162.0	160.8	159.8
60°	155.7	155.3	155.0	154.6	154.3	153.5	152.3	151.1	149.8	148.6	147.7
62.5°	143.8	143.2	142.7	142.2	141.5	140.8	139.8	139.0	138.0	137.1	136.1
65°	125.5	125.0	124.5	124.0	123.5	122.8	121.9	121.1	120.2	119.3	118.5
67.5°	107.0	106.6	106.2	105.7	105.4	104.8	103.9	103.1	102.4	101.6	101.0
70°	95.4	95.1	94.7	94.4	94.0	93.5	92.7	92.0	91.1	90.3	89.7
72.5°	83.5	83.2	82.8	82.5	82.1	81.7	81.2	80.8	80.2	79.7	79.1
75°	65.7	65.5	65.3	65.2	65.0	64.7	64.3	63.8	63.4	62.9	62.4
77.5°	49.8	49.4	49.2	48.9	48.6	48.3	48.1	48.0	47.8	47.6	47.4
80°	39.1	39.0	38.9	38.8	38.7	38.7	38.5	38.3	38.1	38.0	37.7
82.5°	29.1	29.1	29.1	29.0	29.0	28.9	28.8	28.8	28.7	28.6	28.2
85°	16.0	15.9	15.8	15.8	15.7	15.6	15.5	15.4	15.3	15.2	15.0
87.5°	5.8	6.0	6.3	6.5	6.9	7.1	7.2	7.4	7.5	7.7	7.7
90°	0.9	2.8	4.8	6.9	8.9	10.6	12.1	13.5	15.0	16.4	17.4
92.5°	16.6	16.4	16.3	16.1	15.9	16.2	16.9	17.7	18.3	19.1	19.5
95°	53.5	47.4	41.4	35.4	29.4	26.9	28.2	29.5	30.8	32.1	33.0
97.5°	106.2	89.1	72.2	55.1	38.1	31.1	34.1	37.0	40.0	43.0	43.7
100°	145.6	120.5	95.5	70.5	45.5	34.4	37.5	40.6	43.8	46.9	48.4
102.5°	189.1	183.7	178.5	173.1	167.8	152.2	126.2	100.2	74.2	48.2	50.1
105°	250.1	255.6	261.1	266.6	272.1	249.9	199.9	150.0	100.1	50.2	52.2
107.5°	319.7	324.2	328.6	332.9	337.4	309.7	249.9	189.9	130.1	70.3	68.2
110°	364.5	368.3	372.1	376.0	379.8	355.3	302.5	249.7	196.8	144.0	125.7



TEST NUMBER: P331481-935

CATALOG NUMBER: S122DIW-S290D970U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	406.6	410.0	413.4	416.8	420.2	415.3	402.3	389.3	376.2	363.2	296.4
115°	473.0	476.1	479.3	482.4	485.5	489.3	493.9	498.4	503.1	507.6	422.9
117.5°	532.4	536.0	539.4	542.9	546.4	549.7	552.8	555.9	559.1	562.2	541.7
120°	575.9	578.7	581.3	584.1	586.9	589.9	593.1	596.5	599.8	603.0	605.3
122.5°	612.8	615.6	618.5	621.4	624.3	627.6	631.1	634.7	638.3	641.9	643.2
125°	668.8	671.2	673.6	676.0	678.4	681.3	684.8	688.3	691.7	695.2	696.5
127.5°	719.7	722.4	725.0	727.6	730.2	732.9	735.5	738.0	740.6	743.2	745.1
130°	752.0	754.9	757.9	760.7	763.6	766.1	768.1	770.2	772.1	774.2	776.2
132.5°	784.9	787.4	789.9	792.3	794.8	797.0	799.1	801.1	803.1	805.1	806.8
135°	827.7	830.6	833.5	836.5	839.4	841.6	843.3	844.9	846.5	848.3	850.1
137.5°	870.9	873.0	875.0	877.1	879.1	881.1	883.0	884.8	886.7	888.6	890.4
140°	899.2	900.7	902.2	903.6	905.1	906.8	908.8	910.9	912.8	914.9	916.5
142.5°	922.9	924.2	925.6	926.9	928.2	930.0	932.3	934.6	936.9	939.2	940.7
145°	960.1	959.9	959.8	959.6	959.4	960.9	964.0	967.1	970.2	973.3	974.6
147.5°	992.6	991.8	991.1	990.4	989.7	990.9	994.0	997.0	1000.1	1003.2	1004.2
150°	1013.6	1012.3	1011.0	1009.8	1008.5	1009.3	1012.2	1015.1	1018.0	1021.0	1022.1
152.5°	1031.4	1029.9	1028.5	1027.1	1025.6	1026.3	1029.1	1031.9	1034.7	1037.4	1038.5
155°	1057.2	1055.5	1053.9	1052.2	1050.6	1050.9	1053.1	1055.2	1057.5	1059.6	1060.8
157.5°	1077.5	1076.1	1074.6	1073.2	1071.9	1071.9	1073.5	1075.0	1076.5	1078.1	1079.3
160°	1089.3	1088.2	1087.1	1086.0	1084.9	1084.9	1086.0	1087.1	1088.2	1089.3	1090.4
162.5°	1099.8	1098.7	1097.6	1096.5	1095.5	1095.4	1096.3	1097.3	1098.2	1099.2	1100.4
165°	1114.0	1112.8	1111.7	1110.7	1109.6	1109.3	1109.8	1110.3	1110.9	1111.5	1112.8
167.5°	1124.5	1123.3	1122.3	1121.2	1120.1	1119.8	1120.3	1120.8	1121.4	1121.9	1123.1
170°	1130.4	1129.3	1128.3	1127.1	1126.0	1125.7	1126.0	1126.4	1126.8	1127.1	1128.4
172.5°	1134.4	1133.2	1132.1	1131.1	1130.0	1129.6	1130.0	1130.3	1130.7	1131.1	1132.4
175°	1139.4	1138.2	1136.9	1135.7	1134.4	1133.9	1134.3	1134.6	1135.0	1135.3	1136.6
177.5°	1140.3	1139.3	1138.2	1137.2	1136.2	1135.7	1135.9	1136.0	1136.2	1136.3	1137.4
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331481-935

CATALOG NUMBER: S122DIW-S290D970U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7
2.5°	405.0	405.7	406.4	406.7	406.6	406.4	406.3	406.1
5°	402.3	403.0	403.7	404.0	403.8	403.6	403.5	403.3
7.5°	397.8	398.5	399.2	399.4	399.2	399.0	398.8	398.6
10°	393.7	394.4	395.1	395.3	395.0	394.8	394.5	394.3
12.5°	388.9	389.3	389.9	390.0	389.9	389.6	389.4	389.3
15°	380.5	380.8	381.2	381.2	380.7	380.3	379.9	379.4
17.5°	370.5	370.9	371.3	371.3	370.8	370.5	370.1	369.6
20°	362.7	363.0	363.3	363.2	362.8	362.5	362.1	361.8
22.5°	354.5	354.6	354.6	354.5	354.3	354.0	353.9	353.7
25°	341.0	341.2	341.4	341.4	341.2	341.0	340.9	340.7
27.5°	327.8	327.5	327.3	326.9	326.5	326.1	325.7	325.3
30°	317.5	317.2	316.9	316.7	316.3	316.0	315.6	315.2
32.5°	307.4	306.9	306.4	306.0	305.7	305.3	305.0	304.6
35°	291.1	290.6	290.1	289.6	289.2	288.8	288.3	287.8
37.5°	274.8	274.2	273.5	273.0	272.6	272.2	271.8	271.4
40°	263.6	262.9	262.1	261.5	261.1	260.8	260.5	260.1
42.5°	252.5	251.7	250.8	250.1	249.7	249.2	248.7	248.2
45°	235.5	234.5	233.6	232.9	232.6	232.2	231.9	231.5
47.5°	217.8	216.8	215.8	215.0	214.6	214.0	213.5	213.0
50°	206.5	205.2	204.0	203.2	202.8	202.3	201.9	201.5
52.5°	194.7	193.6	192.6	191.8	191.2	190.7	190.1	189.5
55°	177.0	176.0	175.0	174.3	173.8	173.3	172.9	172.5
57.5°	158.8	157.7	156.7	156.0	155.8	155.4	155.1	154.7
60°	146.7	145.8	144.8	144.2	144.0	143.7	143.4	143.2
62.5°	135.3	134.4	133.5	132.9	132.6	132.2	131.9	131.6
65°	117.7	116.9	116.1	115.5	115.1	114.7	114.3	113.8
67.5°	100.4	99.8	99.2	98.7	98.3	98.0	97.6	97.3
70°	89.1	88.5	87.9	87.5	87.1	86.7	86.4	86.0
72.5°	78.5	77.9	77.3	76.8	76.5	76.3	76.0	75.7
75°	61.9	61.4	60.9	60.7	60.9	61.0	61.2	61.4
77.5°	47.1	46.8	46.6	46.3	46.1	45.9	45.6	45.4
80°	37.5	37.2	36.9	36.7	36.5	36.3	36.2	36.0
82.5°	27.9	27.6	27.2	27.0	27.0	26.9	26.9	26.9
85°	14.7	14.5	14.2	14.0	13.9	13.9	13.8	13.7
87.5°	7.7	7.6	7.6	7.6	7.6	7.6	7.6	7.6
90°	18.3	19.2	20.1	20.8	21.1	21.4	21.9	22.2
92.5°	20.1	20.5	21.0	21.4	21.5	21.8	22.0	22.2
95°	33.9	34.9	35.7	36.1	35.9	35.7	35.6	35.4
97.5°	44.4	45.1	45.9	46.3	46.6	46.8	47.0	47.2
100°	49.9	51.3	52.8	53.6	54.0	54.4	54.8	55.1
102.5°	52.0	53.9	55.8	57.0	57.5	58.0	58.5	59.1
105°	54.2	56.2	58.2	59.6	60.4	61.0	61.8	62.5
107.5°	66.1	64.1	62.1	61.4	62.2	62.9	63.6	64.3
110°	107.4	89.1	70.9	62.1	62.8	63.5	64.2	65.0



TEST NUMBER: P331481-935

CATALOG NUMBER: S122DIW-S290D970U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	229.7	163.1	96.3	63.3	63.9	64.5	65.1	65.7
115°	338.3	253.7	169.0	120.1	106.9	93.8	80.6	67.5
117.5°	521.2	500.8	480.4	448.5	405.2	362.0	318.7	275.4
120°	607.4	609.6	611.8	600.5	575.9	551.2	526.5	501.9
122.5°	644.5	645.8	647.1	645.4	640.6	635.8	631.0	626.3
125°	697.8	699.0	700.3	701.2	701.8	702.3	702.8	703.4
127.5°	747.0	748.8	750.7	751.7	751.8	751.9	752.0	752.1
130°	778.2	780.2	782.2	783.2	782.9	782.7	782.6	782.4
132.5°	808.6	810.3	812.0	812.8	812.5	812.4	812.2	812.0
135°	851.9	853.7	855.5	856.3	855.9	855.5	855.1	854.8
137.5°	892.1	893.9	895.7	896.3	895.7	895.0	894.4	893.8
140°	918.2	919.8	921.4	921.8	920.9	920.0	919.0	918.2
142.5°	942.2	943.7	945.2	945.5	944.6	943.7	942.8	941.8
145°	975.9	977.1	978.4	978.6	977.7	976.7	975.9	974.9
147.5°	1005.1	1006.1	1007.0	1007.1	1006.3	1005.6	1004.8	1004.0
150°	1023.2	1024.2	1025.4	1025.5	1024.6	1023.6	1022.7	1021.8
152.5°	1039.7	1040.7	1041.8	1041.8	1040.6	1039.4	1038.2	1037.0
155°	1061.9	1062.9	1064.0	1063.9	1062.4	1060.9	1059.5	1058.0
157.5°	1080.6	1081.8	1083.1	1083.0	1081.5	1080.1	1078.7	1077.3
160°	1091.5	1092.5	1093.6	1093.6	1092.3	1091.0	1089.8	1088.5
162.5°	1101.6	1102.9	1104.1	1104.0	1102.3	1100.8	1099.2	1097.7
165°	1114.0	1115.3	1116.6	1116.6	1115.3	1114.0	1112.8	1111.5
167.5°	1124.4	1125.7	1127.0	1126.8	1125.2	1123.5	1121.9	1120.2
170°	1129.7	1130.9	1132.2	1132.0	1130.4	1128.8	1127.1	1125.5
172.5°	1133.6	1134.9	1136.2	1136.0	1134.4	1132.7	1131.1	1129.5
175°	1137.9	1139.2	1140.5	1140.2	1138.3	1136.5	1134.7	1132.9
177.5°	1138.4	1139.4	1140.4	1140.3	1138.9	1137.6	1136.3	1135.1
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0

(END OF REPORT)