

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331845-940

Luminaire Tested: **S122RDIW-S1005D435U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331845-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D435U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4943.6 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331845-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331845-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69
1	103	99	95	92	97	94	91	88	84	82	79	75	73	71	67	65	64	60
2	95	88	82	77	89	83	78	74	75	71	68	67	64	61	60	58	56	52
3	87	78	71	66	82	74	68	63	67	62	58	60	57	53	54	51	49	46
4	81	70	63	57	76	67	60	55	61	55	51	55	50	47	49	46	43	40
5	75	63	56	50	70	60	53	48	55	49	45	50	45	42	45	41	38	36
6	69	58	50	44	65	55	48	43	50	44	40	46	41	37	41	38	35	32
7	64	53	45	39	61	50	43	38	46	40	36	42	37	34	38	34	31	29
8	60	48	41	35	57	46	39	34	42	37	32	39	34	31	36	32	29	26
9	56	44	37	32	53	43	36	31	39	34	30	36	31	28	33	29	26	24
10	53	41	34	29	50	40	33	29	37	31	27	34	29	26	31	27	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	31752	31752	31752	31752
5°	35462	31951	28329	31951
10°	39346	31727	24556	31727
15°	41279	31263	19348	31263
20°	35787	30574	16744	30574
25°	23469	29630	14949	29630
30°	15797	28486	13530	28486
35°	12796	27045	12203	27045
40°	11377	25478	11291	25478
45°	10298	23640	10079	23640
50°	9372	21815	9339	21815
55°	8811	19792	8695	19792
60°	7369	17938	7282	17938
65°	6212	16290	7049	16290
70°	5740	14549	6647	14549
75°	5371	12664	6138	12664
80°	4956	10423	5467	10423
85°	4557	8225	4798	8225



TEST NUMBER: P331845-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.4	3.8
10°-20°	519.5	10.5
20°-30°	669.4	13.5
30°-40°	636.1	12.9
40°-50°	544.9	11.0
50°-60°	415.0	8.4
60°-70°	262.3	5.3
70°-80°	131.0	2.6
80°-90°	35.4	0.7
90°-100°	17.6	0.4
100°-110°	64.4	1.3
110°-120°	172.2	3.5
120°-130°	284.3	5.8
130°-140°	302.4	6.1
140°-150°	281.0	5.7
150°-160°	225.9	4.6
160°-170°	145.6	2.9
170°-180°	50.1	1.0
0°-30°	1375.3	27.8
0°-40°	2011.4	40.7
0°-60°	2971.3	60.1
0°-90°	3400.0	68.8
90°-120°	254.2	5.1
90°-150°	1121.9	22.7
90°-180°	1544.0	31.2
0°-180°	4943.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1967	1967	1967	1967	1967	
5°	2188	1971	1748	1971	2188	216
15°	2470	1870	1158	1870	2470	666
25°	1317	1663	839	1663	1317	625
35°	649	1372	619	1372	649	415
45°	451	1035	441	1035	451	349
55°	313	703	309	703	313	275
65°	163	426	184	426	163	166
75°	86	203	98	203	86	91
85°	25	44	26	44	25	27
90°	10	0	10	0	10	6
95°	16	25	16	25	16	15
105°	29	116	29	116	29	30
115°	31	219	31	219	31	78
125°	326	310	326	310	326	282
135°	396	383	396	383	396	305
145°	452	445	452	445	452	282
155°	490	490	490	490	490	226
165°	515	516	515	516	515	145
175°	525	528	525	528	525	50
180°	527	527	527	527	527	



TEST NUMBER: P331845-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	2046.4	2048.1	2049.7	2045.9	2045.9	2042.6	2035.5	2030.0	2014.7	2012.5	2012.5
5°	2188.0	2186.7	2189.3	2180.5	2168.2	2165.4	2152.5	2135.4	2117.6	2097.8	2093.7
7.5°	2328.8	2326.7	2321.2	2319.8	2310.3	2289.6	2268.8	2246.5	2217.0	2188.2	2173.6
10°	2399.9	2422.4	2408.7	2384.8	2389.6	2357.5	2340.4	2311.0	2286.4	2243.4	2233.8
12.5°	2469.8	2478.7	2474.3	2460.8	2454.6	2432.3	2409.2	2383.7	2338.3	2299.6	2266.0
15°	2469.5	2482.5	2485.9	2481.8	2485.3	2483.9	2471.6	2450.4	2410.7	2368.4	2331.5
17.5°	2287.2	2296.2	2318.6	2333.8	2353.0	2393.4	2413.3	2421.2	2415.3	2391.1	2365.1
20°	2082.8	2067.7	2130.6	2162.8	2190.0	2258.3	2317.1	2339.7	2375.9	2375.3	2368.4
22.5°	1793.1	1796.6	1856.2	1894.4	1974.2	2042.5	2109.4	2194.3	2264.4	2310.7	2337.8
25°	1317.4	1343.5	1402.8	1454.8	1543.6	1670.7	1786.2	1920.1	2046.6	2146.3	2241.3
27.5°	989.4	991.4	1038.5	1086.5	1139.2	1243.4	1388.8	1548.7	1728.9	1877.7	2048.7
30°	847.3	843.2	863.0	892.4	937.5	1018.2	1127.5	1284.7	1464.4	1688.5	1888.0
32.5°	746.7	747.0	761.9	783.6	821.1	875.5	950.4	1078.0	1247.9	1468.2	1702.2
35°	649.2	648.5	659.4	675.1	690.8	725.7	776.9	843.9	960.7	1166.4	1405.6
37.5°	579.2	582.2	587.5	597.4	614.7	634.1	664.9	709.8	793.1	914.7	1115.7
40°	539.8	541.2	548.7	556.9	567.1	582.2	607.4	643.7	704.5	801.6	948.4
42.5°	503.7	505.2	510.4	518.1	526.2	541.2	562.1	593.4	642.7	718.5	839.6
45°	451.0	451.0	455.8	459.2	468.1	481.7	498.8	524.8	558.9	615.0	695.6
47.5°	401.5	401.6	404.8	410.7	416.3	427.0	443.7	464.9	489.8	533.2	602.0
50°	373.1	373.8	375.9	380.6	384.1	393.6	406.6	425.0	451.0	484.5	541.9
52.5°	350.2	349.7	352.3	354.4	356.7	363.6	373.3	389.5	412.7	441.8	489.4
55°	313.0	310.2	314.3	317.7	319.8	322.5	328.0	338.2	358.0	382.6	418.2
57.5°	266.5	265.4	268.3	271.4	277.9	285.3	289.9	296.4	306.7	324.3	359.5
60°	228.2	228.2	234.3	236.4	244.0	253.5	263.1	268.6	278.8	290.4	316.4
62.5°	194.3	194.9	197.8	199.8	204.0	215.8	229.2	241.2	250.9	262.0	279.2
65°	162.6	164.0	164.0	165.3	168.1	170.9	176.3	185.8	203.0	218.6	231.7
67.5°	138.0	138.5	138.8	140.2	140.9	143.9	146.1	150.3	154.3	169.2	185.3
70°	121.6	123.7	123.0	124.4	125.0	126.4	129.1	131.2	137.3	140.8	150.3
72.5°	106.3	107.8	107.7	108.5	110.3	110.6	112.7	114.8	118.8	121.6	126.8
75°	86.1	85.4	86.1	87.5	88.2	88.8	88.8	91.6	93.6	96.3	99.8
77.5°	66.4	67.1	67.0	67.1	67.2	68.5	68.3	69.6	71.6	72.9	74.6
80°	53.3	53.9	53.3	53.9	54.7	55.4	54.7	55.4	57.4	58.8	58.8
82.5°	41.3	41.4	41.8	42.0	42.1	42.3	43.2	43.3	44.9	44.6	45.1
85°	24.6	23.9	23.9	23.9	24.6	25.3	24.6	24.6	25.3	25.3	25.3
87.5°	10.8	11.3	11.3	11.2	11.2	11.1	11.1	11.5	10.9	11.3	10.7
90°	10.3	10.2	10.0	9.8	9.6	9.3	8.9	8.5	8.0	7.6	7.0
92.5°	10.3	10.2	10.1	10.0	9.9	9.7	9.5	9.3	9.1	8.8	8.5
95°	16.4	16.5	16.6	16.7	16.8	16.6	16.1	15.7	15.2	14.9	14.3
97.5°	21.8	21.8	21.7	21.6	21.5	21.2	21.0	20.6	20.2	19.9	18.5
100°	25.5	25.3	25.2	25.1	24.9	24.4	23.7	23.1	22.4	21.8	20.2
102.5°	27.4	27.1	26.9	26.7	26.4	25.9	25.0	24.1	23.2	22.3	34.4
105°	29.0	28.6	28.3	27.9	27.6	27.0	26.0	25.1	24.2	23.3	46.4
107.5°	29.8	29.4	29.2	28.8	28.4	28.7	29.7	30.7	31.6	32.5	60.3
110°	30.1	29.8	29.4	29.1	28.7	32.8	41.3	49.8	58.2	66.7	91.1



TEST NUMBER: P331845-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	30.4	30.1	29.9	29.6	29.3	44.7	75.5	106.5	137.3	168.3	174.2
115°	31.2	37.4	43.4	49.6	55.6	78.3	117.5	156.8	195.9	235.1	233.0
117.5°	127.6	147.7	167.6	187.7	207.8	222.5	232.0	241.5	251.0	260.5	259.0
120°	232.5	243.9	255.4	266.8	278.2	283.5	282.4	281.4	280.4	279.4	277.9
122.5°	290.1	292.3	294.5	296.8	299.0	299.8	299.2	298.5	298.0	297.4	295.7
125°	325.8	325.7	325.4	325.1	324.9	324.4	323.9	323.2	322.6	322.1	320.5
127.5°	348.4	348.4	348.3	348.3	348.2	347.8	346.9	346.1	345.2	344.3	343.1
130°	362.5	362.6	362.7	362.7	362.8	362.4	361.4	360.5	359.5	358.6	357.8
132.5°	376.2	376.3	376.3	376.4	376.5	376.1	375.3	374.6	373.8	373.0	372.0
135°	396.0	396.2	396.4	396.5	396.6	396.4	395.5	394.7	393.8	393.0	392.2
137.5°	414.0	414.4	414.6	414.9	415.2	414.9	414.1	413.3	412.4	411.6	410.7
140°	425.3	425.8	426.1	426.6	427.0	426.9	426.1	425.3	424.5	423.8	422.8
142.5°	436.3	436.8	437.2	437.6	438.0	437.9	437.2	436.5	435.8	435.1	434.0
145°	451.7	452.1	452.5	452.9	453.3	453.3	452.6	452.1	451.5	450.8	449.4
147.5°	465.1	465.5	465.8	466.2	466.5	466.5	466.1	465.7	465.2	464.8	463.3
150°	473.4	473.8	474.2	474.7	475.1	475.0	474.5	474.0	473.5	473.0	471.6
152.5°	480.4	480.9	481.5	482.1	482.6	482.7	482.1	481.6	481.1	480.6	479.3
155°	490.2	490.8	491.5	492.1	492.8	492.9	492.4	492.0	491.4	490.9	489.9
157.5°	499.1	499.7	500.3	501.1	501.7	501.8	501.1	500.6	500.0	499.4	498.7
160°	504.3	504.8	505.4	506.0	506.6	506.7	506.1	505.6	505.2	504.6	504.1
162.5°	508.5	509.3	510.0	510.7	511.4	511.5	511.0	510.3	509.8	509.2	508.7
165°	514.9	515.5	516.1	516.7	517.3	517.3	516.7	516.1	515.5	514.9	514.7
167.5°	519.0	519.7	520.5	521.2	522.0	522.1	521.5	520.9	520.3	519.7	519.5
170°	521.4	522.2	522.9	523.7	524.4	524.5	524.0	523.3	522.7	522.2	522.0
172.5°	523.3	524.0	524.8	525.5	526.3	526.4	525.8	525.1	524.6	524.0	523.8
175°	524.9	525.7	526.6	527.4	528.2	528.3	527.7	527.2	526.6	525.9	525.8
177.5°	525.8	526.4	527.0	527.6	528.2	528.3	527.8	527.4	526.9	526.4	526.4
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331845-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	2013.7	2009.2	2005.5	1995.6	1990.7	1979.7	1978.1	1977.5	1963.4	1949.6	1945.8
5°	2082.8	2071.8	2055.5	2036.3	2016.5	1996.0	1982.4	1971.4	1944.0	1918.1	1903.1
7.5°	2152.5	2129.0	2100.7	2064.5	2034.3	2000.4	1975.2	1952.7	1913.9	1876.7	1851.6
10°	2204.4	2166.1	2128.5	2078.7	2039.7	2001.4	1966.0	1935.2	1891.4	1842.3	1807.4
12.5°	2236.7	2194.6	2142.8	2094.0	2043.5	1994.9	1947.3	1907.8	1856.5	1805.6	1764.2
15°	2280.3	2235.2	2172.3	2102.6	2037.6	1974.2	1919.5	1870.3	1803.3	1742.5	1691.9
17.5°	2316.0	2253.9	2186.4	2105.8	2030.6	1949.8	1879.5	1816.6	1742.0	1668.7	1609.1
20°	2327.4	2265.9	2188.0	2107.4	2018.6	1923.6	1847.7	1779.4	1699.4	1619.4	1551.1
22.5°	2320.3	2272.4	2185.9	2089.4	1998.3	1899.0	1813.3	1734.0	1645.3	1563.7	1484.4
25°	2272.1	2255.7	2173.6	2068.4	1964.5	1849.1	1750.0	1663.2	1562.1	1474.6	1388.5
27.5°	2159.5	2194.9	2144.1	2032.0	1916.6	1792.8	1681.4	1582.6	1477.7	1379.2	1293.4
30°	2051.4	2132.6	2110.8	2006.9	1877.8	1756.1	1631.1	1527.9	1415.9	1314.7	1230.0
32.5°	1903.2	2037.6	2058.9	1971.9	1838.4	1704.8	1573.7	1471.1	1354.1	1247.5	1164.9
35°	1667.3	1868.2	1960.4	1905.1	1771.2	1627.0	1491.7	1372.1	1254.5	1149.3	1067.4
37.5°	1385.9	1659.6	1813.3	1817.2	1694.3	1544.4	1397.0	1278.3	1158.0	1054.6	966.0
40°	1203.4	1499.9	1700.1	1744.5	1640.7	1478.7	1329.7	1208.8	1091.3	990.2	888.3
42.5°	1039.4	1334.8	1580.9	1658.1	1575.7	1414.8	1265.2	1138.8	1024.6	928.9	824.9
45°	840.5	1098.8	1370.0	1508.1	1462.3	1313.3	1155.5	1035.3	927.9	845.3	745.5
47.5°	709.0	891.1	1153.6	1340.2	1339.4	1203.5	1048.2	933.0	833.5	756.0	675.3
50°	634.1	792.6	1014.8	1226.5	1244.3	1130.2	982.6	868.5	775.6	694.3	629.4
52.5°	566.9	697.5	897.2	1100.3	1150.8	1052.0	908.8	803.4	713.3	638.5	582.9
55°	479.0	580.1	731.8	921.8	998.4	928.6	801.6	703.1	630.0	567.1	519.3
57.5°	405.2	481.1	602.8	755.7	844.9	801.0	696.2	616.3	553.7	496.8	459.1
60°	358.7	420.9	524.1	651.9	750.3	719.5	630.0	555.5	502.2	453.1	417.5
62.5°	315.0	368.5	456.9	560.6	650.8	638.1	565.0	502.5	455.8	411.0	380.8
65°	253.5	292.5	361.5	442.8	515.2	521.4	468.8	426.4	384.7	349.2	322.5
67.5°	201.9	227.3	275.9	344.4	398.7	418.0	385.9	353.6	320.5	293.0	269.9
70°	170.1	190.6	226.1	281.5	331.4	351.9	333.5	308.2	279.5	256.9	237.1
72.5°	137.9	157.8	184.0	224.7	267.4	289.6	283.2	265.0	241.7	223.0	204.3
75°	103.9	110.0	127.8	155.2	188.6	207.8	212.5	203.0	184.5	170.1	159.2
77.5°	76.8	80.5	89.0	103.3	125.2	142.2	149.3	148.1	135.5	127.1	116.8
80°	61.5	63.6	67.7	73.8	90.2	107.3	112.1	112.1	103.2	99.8	89.5
82.5°	46.7	48.2	50.7	54.1	61.8	76.7	82.0	83.1	77.5	72.9	64.9
85°	26.7	25.9	27.4	29.4	30.8	34.9	43.1	44.4	43.1	37.5	35.5
87.5°	10.5	11.0	10.8	10.1	10.4	10.9	13.4	16.0	13.9	12.5	11.6
90°	6.2	5.6	4.9	4.1	3.2	2.2	1.3	0.4	1.3	2.2	3.2
92.5°	8.2	7.8	7.5	7.4	7.4	7.5	7.6	7.7	7.6	7.5	7.4
95°	13.6	13.1	12.5	13.6	16.4	19.2	21.9	24.8	21.9	19.2	16.4
97.5°	17.1	15.8	14.4	17.7	25.5	33.4	41.3	49.1	41.3	33.4	25.5
100°	18.8	17.4	16.0	21.0	32.6	44.2	55.8	67.5	55.8	44.2	32.6
102.5°	46.5	58.5	70.5	77.8	80.3	82.7	85.2	87.6	85.2	82.7	80.3
105°	69.5	92.6	115.7	126.0	123.5	120.9	118.4	115.8	118.4	120.9	123.5
107.5°	88.0	115.7	143.5	156.3	154.3	152.2	150.2	148.1	150.2	152.2	154.3
110°	115.7	140.1	164.6	175.9	174.2	172.4	170.6	168.8	170.6	172.4	174.2



TEST NUMBER: P331845-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	180.3	186.4	192.4	194.7	193.1	191.5	189.9	188.3	189.9	191.5	193.1
115°	231.0	228.8	226.7	224.9	223.5	222.0	220.6	219.2	220.6	222.0	223.5
117.5°	257.5	256.1	254.7	253.1	251.5	249.9	248.3	246.6	248.3	249.9	251.5
120°	276.3	274.8	273.3	271.9	270.6	269.3	268.0	266.8	268.0	269.3	270.6
122.5°	294.0	292.4	290.7	289.2	287.8	286.5	285.2	283.8	285.2	286.5	287.8
125°	318.9	317.3	315.6	314.2	313.2	312.1	310.9	309.9	310.9	312.1	313.2
127.5°	341.9	340.7	339.5	338.3	337.1	335.8	334.7	333.4	334.7	335.8	337.1
130°	356.8	355.9	354.9	353.7	352.4	351.1	349.7	348.4	349.7	351.1	352.4
132.5°	371.1	370.1	369.3	368.2	367.0	365.9	364.7	363.6	364.7	365.9	367.0
135°	391.5	390.7	389.9	388.9	387.4	386.1	384.8	383.4	384.8	386.1	387.4
137.5°	409.9	409.0	408.1	407.2	406.4	405.4	404.4	403.5	404.4	405.4	406.4
140°	422.0	421.1	420.1	419.3	418.6	417.9	417.2	416.6	417.2	417.9	418.6
142.5°	432.9	431.9	430.9	430.0	429.4	428.7	428.2	427.6	428.2	428.7	429.4
145°	448.0	446.6	445.1	444.4	444.5	444.6	444.7	444.8	444.7	444.6	444.5
147.5°	461.9	460.5	459.1	458.5	458.9	459.1	459.5	459.8	459.5	459.1	458.9
150°	470.3	469.0	467.5	467.2	467.8	468.3	469.0	469.6	469.0	468.3	467.8
152.5°	478.0	476.7	475.5	475.1	475.8	476.4	477.2	477.8	477.2	476.4	475.8
155°	488.8	487.9	486.9	486.7	487.5	488.2	489.0	489.7	489.0	488.2	487.5
157.5°	498.0	497.3	496.6	496.6	497.2	497.8	498.5	499.1	498.5	497.8	497.2
160°	503.6	503.1	502.6	502.6	503.1	503.6	504.1	504.6	504.1	503.6	503.1
162.5°	508.3	507.8	507.5	507.5	508.0	508.5	509.0	509.5	509.0	508.5	508.0
165°	514.4	514.2	513.9	514.0	514.5	515.1	515.6	516.0	515.6	515.1	514.5
167.5°	519.2	519.0	518.8	518.9	519.4	520.0	520.4	520.9	520.4	520.0	519.4
170°	521.8	521.7	521.5	521.7	522.2	522.6	523.2	523.7	523.2	522.6	522.2
172.5°	523.6	523.4	523.3	523.4	524.0	524.5	525.0	525.5	525.0	524.5	524.0
175°	525.7	525.5	525.3	525.5	526.1	526.6	527.3	527.9	527.3	526.6	526.1
177.5°	526.3	526.2	526.1	526.4	526.8	527.3	527.8	528.2	527.8	527.3	526.8
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331845-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	1938.8	1934.9	1927.8	1916.8	1910.3	1898.8	1891.1	1895.5	1896.7	1895.5	1894.4
5°	1886.7	1872.3	1852.5	1833.4	1815.6	1796.4	1785.6	1780.7	1771.2	1765.7	1763.0
7.5°	1823.6	1798.9	1770.9	1737.6	1709.2	1679.6	1664.5	1656.9	1637.4	1626.7	1617.4
10°	1776.6	1737.7	1709.7	1666.0	1639.3	1600.4	1573.7	1574.4	1547.7	1532.7	1521.8
12.5°	1724.7	1681.9	1635.3	1596.0	1559.0	1527.7	1495.5	1482.6	1454.3	1439.8	1410.2
15°	1638.6	1588.8	1539.5	1486.2	1448.7	1400.2	1353.7	1297.0	1251.2	1211.6	1200.6
17.5°	1544.6	1482.8	1433.5	1370.9	1306.5	1224.9	1171.1	1138.2	1110.5	1089.7	1074.1
20°	1480.1	1417.2	1364.6	1270.3	1183.5	1128.2	1088.5	1063.3	1034.6	1012.0	999.7
22.5°	1412.3	1346.7	1275.0	1169.7	1102.1	1057.7	1022.3	993.3	973.8	956.3	945.0
25°	1316.1	1244.3	1126.1	1053.6	999.0	952.5	927.9	910.2	889.7	865.8	854.9
27.5°	1214.4	1100.3	1015.4	961.5	909.4	879.1	857.0	830.5	812.2	801.4	790.1
30°	1138.4	1024.3	958.1	899.3	862.4	828.8	802.9	787.9	770.1	751.6	744.1
32.5°	1053.6	962.5	899.0	850.1	812.6	784.1	763.6	739.2	726.4	715.1	699.3
35°	948.4	879.4	821.4	781.8	746.2	723.0	699.0	684.7	661.5	651.9	645.8
37.5°	859.3	799.5	756.2	714.3	686.2	660.5	645.9	623.0	613.0	599.7	586.7
40°	809.0	750.3	708.6	674.4	643.0	623.8	605.4	587.0	571.9	565.8	550.1
42.5°	757.7	709.8	668.2	630.7	609.7	589.4	566.1	552.5	537.0	527.0	517.3
45°	686.7	644.4	608.9	578.1	554.8	533.7	518.6	496.1	487.2	467.4	459.2
47.5°	624.5	585.1	551.2	521.9	499.3	485.4	463.4	445.8	431.6	419.5	408.9
50°	580.1	547.3	514.5	488.6	468.1	448.3	425.7	416.8	394.9	388.8	382.6
52.5°	539.7	508.5	478.5	453.1	432.6	413.3	393.4	381.8	367.1	361.0	356.4
55°	483.1	453.1	424.4	401.8	381.3	361.5	349.2	334.8	328.0	323.2	317.7
57.5°	426.2	399.2	377.2	354.4	333.8	318.0	303.8	295.2	288.1	281.8	275.3
60°	390.2	364.2	344.4	323.2	302.0	289.0	278.1	267.9	259.7	250.1	247.4
62.5°	351.9	329.2	311.0	290.4	272.0	260.1	249.7	240.0	230.2	216.2	212.4
65°	299.3	281.5	262.4	245.3	228.9	217.3	202.2	191.4	187.3	185.8	185.2
67.5°	251.7	235.0	218.6	201.0	186.1	175.3	167.7	166.0	163.2	162.4	160.4
70°	220.1	204.3	187.9	171.5	157.2	155.2	152.4	149.6	146.2	144.9	143.5
72.5°	191.6	175.3	158.9	145.8	139.6	137.1	134.4	131.6	129.3	128.0	127.1
75°	147.0	131.9	120.9	116.2	112.7	110.7	106.6	104.5	103.2	101.1	100.4
77.5°	105.8	97.3	92.3	89.3	85.7	83.5	81.1	79.1	77.7	77.2	76.2
80°	80.6	76.5	73.1	69.0	67.7	64.9	64.2	62.2	62.9	60.8	60.8
82.5°	62.6	57.4	54.6	52.6	51.3	49.0	48.4	47.4	47.5	46.0	46.0
85°	32.1	30.8	29.4	28.0	28.0	25.9	26.7	25.9	25.9	24.6	23.9
87.5°	11.2	10.8	9.9	10.0	10.2	9.7	9.8	9.4	9.5	9.5	9.0
90°	4.1	4.9	5.6	6.2	7.0	7.6	8.0	8.5	8.9	9.3	9.6
92.5°	7.4	7.5	7.8	8.2	8.5	8.8	9.1	9.3	9.5	9.7	9.9
95°	13.6	12.5	13.1	13.6	14.3	14.9	15.2	15.7	16.1	16.6	16.8
97.5°	17.7	14.4	15.8	17.1	18.5	19.9	20.2	20.6	21.0	21.2	21.5
100°	21.0	16.0	17.4	18.8	20.2	21.8	22.4	23.1	23.7	24.4	24.9
102.5°	77.8	70.5	58.5	46.5	34.4	22.3	23.2	24.1	25.0	25.9	26.4
105°	126.0	115.7	92.6	69.5	46.4	23.3	24.2	25.1	26.0	27.0	27.6
107.5°	156.3	143.5	115.7	88.0	60.3	32.5	31.6	30.7	29.7	28.7	28.4
110°	175.9	164.6	140.1	115.7	91.1	66.7	58.2	49.8	41.3	32.8	28.7



TEST NUMBER: P331845-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	194.7	192.4	186.4	180.3	174.2	168.3	137.3	106.5	75.5	44.7	29.3
115°	224.9	226.7	228.8	231.0	233.0	235.1	195.9	156.8	117.5	78.3	55.6
117.5°	253.1	254.7	256.1	257.5	259.0	260.5	251.0	241.5	232.0	222.5	207.8
120°	271.9	273.3	274.8	276.3	277.9	279.4	280.4	281.4	282.4	283.5	278.2
122.5°	289.2	290.7	292.4	294.0	295.7	297.4	298.0	298.5	299.2	299.8	299.0
125°	314.2	315.6	317.3	318.9	320.5	322.1	322.6	323.2	323.9	324.4	324.9
127.5°	338.3	339.5	340.7	341.9	343.1	344.3	345.2	346.1	346.9	347.8	348.2
130°	353.7	354.9	355.9	356.8	357.8	358.6	359.5	360.5	361.4	362.4	362.8
132.5°	368.2	369.3	370.1	371.1	372.0	373.0	373.8	374.6	375.3	376.1	376.5
135°	388.9	389.9	390.7	391.5	392.2	393.0	393.8	394.7	395.5	396.4	396.6
137.5°	407.2	408.1	409.0	409.9	410.7	411.6	412.4	413.3	414.1	414.9	415.2
140°	419.3	420.1	421.1	422.0	422.8	423.8	424.5	425.3	426.1	426.9	427.0
142.5°	430.0	430.9	431.9	432.9	434.0	435.1	435.8	436.5	437.2	437.9	438.0
145°	444.4	445.1	446.6	448.0	449.4	450.8	451.5	452.1	452.6	453.3	453.3
147.5°	458.5	459.1	460.5	461.9	463.3	464.8	465.2	465.7	466.1	466.5	466.5
150°	467.2	467.5	469.0	470.3	471.6	473.0	473.5	474.0	474.5	475.0	475.1
152.5°	475.1	475.5	476.7	478.0	479.3	480.6	481.1	481.6	482.1	482.7	482.6
155°	486.7	486.9	487.9	488.8	489.9	490.9	491.4	492.0	492.4	492.9	492.8
157.5°	496.6	496.6	497.3	498.0	498.7	499.4	500.0	500.6	501.1	501.8	501.7
160°	502.6	502.6	503.1	503.6	504.1	504.6	505.2	505.6	506.1	506.7	506.6
162.5°	507.5	507.5	507.8	508.3	508.7	509.2	509.8	510.3	511.0	511.5	511.4
165°	514.0	513.9	514.2	514.4	514.7	514.9	515.5	516.1	516.7	517.3	517.3
167.5°	518.9	518.8	519.0	519.2	519.5	519.7	520.3	520.9	521.5	522.1	522.0
170°	521.7	521.5	521.7	521.8	522.0	522.2	522.7	523.3	524.0	524.5	524.4
172.5°	523.4	523.3	523.4	523.6	523.8	524.0	524.6	525.1	525.8	526.4	526.3
175°	525.5	525.3	525.5	525.7	525.8	525.9	526.6	527.2	527.7	528.3	528.2
177.5°	526.4	526.1	526.2	526.3	526.4	526.4	526.9	527.4	527.8	528.3	528.2
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331845-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	1888.5	1889.5	1887.9	1889.0	1887.9	1889.5	1888.5	1894.4	1895.5	1896.7	1895.5
5°	1759.5	1751.3	1750.0	1747.9	1750.0	1751.3	1759.5	1763.0	1765.7	1771.2	1780.7
7.5°	1605.7	1604.5	1601.1	1596.3	1601.1	1604.5	1605.7	1617.4	1626.7	1637.4	1656.9
10°	1506.7	1503.3	1502.6	1497.8	1502.6	1503.3	1506.7	1521.8	1532.7	1547.7	1574.4
12.5°	1390.8	1368.9	1366.5	1354.6	1366.5	1368.9	1390.8	1410.2	1439.8	1454.3	1482.6
15°	1184.2	1180.1	1166.4	1157.5	1166.4	1180.1	1184.2	1200.6	1211.6	1251.2	1297.0
17.5°	1066.1	1052.8	1048.5	1046.6	1048.5	1052.8	1066.1	1074.1	1089.7	1110.5	1138.2
20°	990.2	977.9	975.8	974.5	975.8	977.9	990.2	999.7	1012.0	1034.6	1063.3
22.5°	937.6	924.8	919.4	915.3	919.4	924.8	937.6	945.0	956.3	973.8	993.3
25°	848.0	843.2	840.5	839.1	840.5	843.2	848.0	854.9	865.8	889.7	910.2
27.5°	777.9	767.4	765.4	761.8	765.4	767.4	777.9	790.1	801.4	812.2	830.5
30°	738.0	734.6	729.8	725.7	729.8	734.6	738.0	744.1	751.6	770.1	787.9
32.5°	691.0	688.1	683.9	682.0	683.9	688.1	691.0	699.3	715.1	726.4	739.2
35°	638.9	629.4	625.3	619.1	625.3	629.4	638.9	645.8	651.9	661.5	684.7
37.5°	583.8	578.8	573.0	575.1	573.0	578.8	583.8	586.7	599.7	613.0	623.0
40°	541.2	537.8	536.5	535.7	536.5	537.8	541.2	550.1	565.8	571.9	587.0
42.5°	507.3	497.8	494.3	494.2	494.3	497.8	507.3	517.3	527.0	537.0	552.5
45°	455.8	446.9	440.8	441.4	440.8	446.9	455.8	459.2	467.4	487.2	496.1
47.5°	403.1	402.8	399.0	400.1	399.0	402.8	403.1	408.9	419.5	431.6	445.8
50°	377.9	373.8	371.0	371.8	371.0	373.8	377.9	382.6	388.8	394.9	416.8
52.5°	353.8	350.3	348.1	351.0	348.1	350.3	353.8	356.4	361.0	367.1	381.8
55°	314.3	310.2	309.5	308.9	309.5	310.2	314.3	317.7	323.2	328.0	334.8
57.5°	270.2	267.4	263.3	261.5	263.3	267.4	270.2	275.3	281.8	288.1	295.2
60°	238.4	233.0	226.1	225.5	226.1	233.0	238.4	247.4	250.1	259.7	267.9
62.5°	209.5	208.4	207.1	206.9	207.1	208.4	209.5	212.4	216.2	230.2	240.0
65°	183.8	183.2	183.8	184.5	183.8	183.2	183.8	185.2	185.8	187.3	191.4
67.5°	160.2	158.9	157.7	158.3	157.7	158.9	160.2	160.4	162.4	163.2	166.0
70°	142.1	141.4	140.8	140.8	140.8	141.4	142.1	143.5	144.9	146.2	149.6
72.5°	124.7	124.5	123.9	123.2	123.9	124.5	124.7	127.1	128.0	129.3	131.6
75°	99.8	98.4	98.4	98.4	98.4	98.4	99.8	100.4	101.1	103.2	104.5
77.5°	76.0	75.3	74.6	74.1	74.6	75.3	76.0	76.2	77.2	77.7	79.1
80°	60.1	59.5	58.8	58.8	58.8	59.5	60.1	60.8	60.8	62.9	62.2
82.5°	45.9	45.2	45.1	44.6	45.1	45.2	45.9	46.0	46.0	47.5	47.4
85°	24.6	25.3	24.6	25.9	24.6	25.3	24.6	23.9	24.6	25.9	25.9
87.5°	9.1	8.6	9.1	8.6	9.1	8.6	9.1	9.0	9.5	9.5	9.4
90°	9.8	10.0	10.2	10.3	10.2	10.0	9.8	9.6	9.3	8.9	8.5
92.5°	10.0	10.1	10.2	10.3	10.2	10.1	10.0	9.9	9.7	9.5	9.3
95°	16.7	16.6	16.5	16.4	16.5	16.6	16.7	16.8	16.6	16.1	15.7
97.5°	21.6	21.7	21.8	21.8	21.8	21.7	21.6	21.5	21.2	21.0	20.6
100°	25.1	25.2	25.3	25.5	25.3	25.2	25.1	24.9	24.4	23.7	23.1
102.5°	26.7	26.9	27.1	27.4	27.1	26.9	26.7	26.4	25.9	25.0	24.1
105°	27.9	28.3	28.6	29.0	28.6	28.3	27.9	27.6	27.0	26.0	25.1
107.5°	28.8	29.2	29.4	29.8	29.4	29.2	28.8	28.4	28.7	29.7	30.7
110°	29.1	29.4	29.8	30.1	29.8	29.4	29.1	28.7	32.8	41.3	49.8



TEST NUMBER: P331845-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	29.6	29.9	30.1	30.4	30.1	29.9	29.6	29.3	44.7	75.5	106.5
115°	49.6	43.4	37.4	31.2	37.4	43.4	49.6	55.6	78.3	117.5	156.8
117.5°	187.7	167.6	147.7	127.6	147.7	167.6	187.7	207.8	222.5	232.0	241.5
120°	266.8	255.4	243.9	232.5	243.9	255.4	266.8	278.2	283.5	282.4	281.4
122.5°	296.8	294.5	292.3	290.1	292.3	294.5	296.8	299.0	299.8	299.2	298.5
125°	325.1	325.4	325.7	325.8	325.7	325.4	325.1	324.9	324.4	323.9	323.2
127.5°	348.3	348.3	348.4	348.4	348.4	348.3	348.3	348.2	347.8	346.9	346.1
130°	362.7	362.7	362.6	362.5	362.6	362.7	362.7	362.8	362.4	361.4	360.5
132.5°	376.4	376.3	376.3	376.2	376.3	376.3	376.4	376.5	376.1	375.3	374.6
135°	396.5	396.4	396.2	396.0	396.2	396.4	396.5	396.6	396.4	395.5	394.7
137.5°	414.9	414.6	414.4	414.0	414.4	414.6	414.9	415.2	414.9	414.1	413.3
140°	426.6	426.1	425.8	425.3	425.8	426.1	426.6	427.0	426.9	426.1	425.3
142.5°	437.6	437.2	436.8	436.3	436.8	437.2	437.6	438.0	437.9	437.2	436.5
145°	452.9	452.5	452.1	451.7	452.1	452.5	452.9	453.3	453.3	452.6	452.1
147.5°	466.2	465.8	465.5	465.1	465.5	465.8	466.2	466.5	466.5	466.1	465.7
150°	474.7	474.2	473.8	473.4	473.8	474.2	474.7	475.1	475.0	474.5	474.0
152.5°	482.1	481.5	480.9	480.4	480.9	481.5	482.1	482.6	482.7	482.1	481.6
155°	492.1	491.5	490.8	490.2	490.8	491.5	492.1	492.8	492.9	492.4	492.0
157.5°	501.1	500.3	499.7	499.1	499.7	500.3	501.1	501.7	501.8	501.1	500.6
160°	506.0	505.4	504.8	504.3	504.8	505.4	506.0	506.6	506.7	506.1	505.6
162.5°	510.7	510.0	509.3	508.5	509.3	510.0	510.7	511.4	511.5	511.0	510.3
165°	516.7	516.1	515.5	514.9	515.5	516.1	516.7	517.3	517.3	516.7	516.1
167.5°	521.2	520.5	519.7	519.0	519.7	520.5	521.2	522.0	522.1	521.5	520.9
170°	523.7	522.9	522.2	521.4	522.2	522.9	523.7	524.4	524.5	524.0	523.3
172.5°	525.5	524.8	524.0	523.3	524.0	524.8	525.5	526.3	526.4	525.8	525.1
175°	527.4	526.6	525.7	524.9	525.7	526.6	527.4	528.2	528.3	527.7	527.2
177.5°	527.6	527.0	526.4	525.8	526.4	527.0	527.6	528.2	528.3	527.8	527.4
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331845-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	1891.1	1898.8	1910.3	1916.8	1927.8	1934.9	1938.8	1945.8	1949.6	1963.4	1977.5
5°	1785.6	1796.4	1815.6	1833.4	1852.5	1872.3	1886.7	1903.1	1918.1	1944.0	1971.4
7.5°	1664.5	1679.6	1709.2	1737.6	1770.9	1798.9	1823.6	1851.6	1876.7	1913.9	1952.7
10°	1573.7	1600.4	1639.3	1666.0	1709.7	1737.7	1776.6	1807.4	1842.3	1891.4	1935.2
12.5°	1495.5	1527.7	1559.0	1596.0	1635.3	1681.9	1724.7	1764.2	1805.6	1856.5	1907.8
15°	1353.7	1400.2	1448.7	1486.2	1539.5	1588.8	1638.6	1691.9	1742.5	1803.3	1870.3
17.5°	1171.1	1224.9	1306.5	1370.9	1433.5	1482.8	1544.6	1609.1	1668.7	1742.0	1816.6
20°	1088.5	1128.2	1183.5	1270.3	1364.6	1417.2	1480.1	1551.1	1619.4	1699.4	1779.4
22.5°	1022.3	1057.7	1102.1	1169.7	1275.0	1346.7	1412.3	1484.4	1563.7	1645.3	1734.0
25°	927.9	952.5	999.0	1053.6	1126.1	1244.3	1316.1	1388.5	1474.6	1562.1	1663.2
27.5°	857.0	879.1	909.4	961.5	1015.4	1100.3	1214.4	1293.4	1379.2	1477.7	1582.6
30°	802.9	828.8	862.4	899.3	958.1	1024.3	1138.4	1230.0	1314.7	1415.9	1527.9
32.5°	763.6	784.1	812.6	850.1	899.0	962.5	1053.6	1164.9	1247.5	1354.1	1471.1
35°	699.0	723.0	746.2	781.8	821.4	879.4	948.4	1067.4	1149.3	1254.5	1372.1
37.5°	645.9	660.5	686.2	714.3	756.2	799.5	859.3	966.0	1054.6	1158.0	1278.3
40°	605.4	623.8	643.0	674.4	708.6	750.3	809.0	888.3	990.2	1091.3	1208.8
42.5°	566.1	589.4	609.7	630.7	668.2	709.8	757.7	824.9	928.9	1024.6	1138.8
45°	518.6	533.7	554.8	578.1	608.9	644.4	686.7	745.5	845.3	927.9	1035.3
47.5°	463.4	485.4	499.3	521.9	551.2	585.1	624.5	675.3	756.0	833.5	933.0
50°	425.7	448.3	468.1	488.6	514.5	547.3	580.1	629.4	694.3	775.6	868.5
52.5°	393.4	413.3	432.6	453.1	478.5	508.5	539.7	582.9	638.5	713.3	803.4
55°	349.2	361.5	381.3	401.8	424.4	453.1	483.1	519.3	567.1	630.0	703.1
57.5°	303.8	318.0	333.8	354.4	377.2	399.2	426.2	459.1	496.8	553.7	616.3
60°	278.1	289.0	302.0	323.2	344.4	364.2	390.2	417.5	453.1	502.2	555.5
62.5°	249.7	260.1	272.0	290.4	311.0	329.2	351.9	380.8	411.0	455.8	502.5
65°	202.2	217.3	228.9	245.3	262.4	281.5	299.3	322.5	349.2	384.7	426.4
67.5°	167.7	175.3	186.1	201.0	218.6	235.0	251.7	269.9	293.0	320.5	353.6
70°	152.4	155.2	157.2	171.5	187.9	204.3	220.1	237.1	256.9	279.5	308.2
72.5°	134.4	137.1	139.6	145.8	158.9	175.3	191.6	204.3	223.0	241.7	265.0
75°	106.6	110.7	112.7	116.2	120.9	131.9	147.0	159.2	170.1	184.5	203.0
77.5°	81.1	83.5	85.7	89.3	92.3	97.3	105.8	116.8	127.1	135.5	148.1
80°	64.2	64.9	67.7	69.0	73.1	76.5	80.6	89.5	99.8	103.2	112.1
82.5°	48.4	49.0	51.3	52.6	54.6	57.4	62.6	64.9	72.9	77.5	83.1
85°	26.7	25.9	28.0	28.0	29.4	30.8	32.1	35.5	37.5	43.1	44.4
87.5°	9.8	9.7	10.2	10.0	9.9	10.8	11.2	11.6	12.5	13.9	16.0
90°	8.0	7.6	7.0	6.2	5.6	4.9	4.1	3.2	2.2	1.3	0.4
92.5°	9.1	8.8	8.5	8.2	7.8	7.5	7.4	7.4	7.5	7.6	7.7
95°	15.2	14.9	14.3	13.6	13.1	12.5	13.6	16.4	19.2	21.9	24.8
97.5°	20.2	19.9	18.5	17.1	15.8	14.4	17.7	25.5	33.4	41.3	49.1
100°	22.4	21.8	20.2	18.8	17.4	16.0	21.0	32.6	44.2	55.8	67.5
102.5°	23.2	22.3	34.4	46.5	58.5	70.5	77.8	80.3	82.7	85.2	87.6
105°	24.2	23.3	46.4	69.5	92.6	115.7	126.0	123.5	120.9	118.4	115.8
107.5°	31.6	32.5	60.3	88.0	115.7	143.5	156.3	154.3	152.2	150.2	148.1
110°	58.2	66.7	91.1	115.7	140.1	164.6	175.9	174.2	172.4	170.6	168.8



TEST NUMBER: P331845-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	137.3	168.3	174.2	180.3	186.4	192.4	194.7	193.1	191.5	189.9	188.3
115°	195.9	235.1	233.0	231.0	228.8	226.7	224.9	223.5	222.0	220.6	219.2
117.5°	251.0	260.5	259.0	257.5	256.1	254.7	253.1	251.5	249.9	248.3	246.6
120°	280.4	279.4	277.9	276.3	274.8	273.3	271.9	270.6	269.3	268.0	266.8
122.5°	298.0	297.4	295.7	294.0	292.4	290.7	289.2	287.8	286.5	285.2	283.8
125°	322.6	322.1	320.5	318.9	317.3	315.6	314.2	313.2	312.1	310.9	309.9
127.5°	345.2	344.3	343.1	341.9	340.7	339.5	338.3	337.1	335.8	334.7	333.4
130°	359.5	358.6	357.8	356.8	355.9	354.9	353.7	352.4	351.1	349.7	348.4
132.5°	373.8	373.0	372.0	371.1	370.1	369.3	368.2	367.0	365.9	364.7	363.6
135°	393.8	393.0	392.2	391.5	390.7	389.9	388.9	387.4	386.1	384.8	383.4
137.5°	412.4	411.6	410.7	409.9	409.0	408.1	407.2	406.4	405.4	404.4	403.5
140°	424.5	423.8	422.8	422.0	421.1	420.1	419.3	418.6	417.9	417.2	416.6
142.5°	435.8	435.1	434.0	432.9	431.9	430.9	430.0	429.4	428.7	428.2	427.6
145°	451.5	450.8	449.4	448.0	446.6	445.1	444.4	444.5	444.6	444.7	444.8
147.5°	465.2	464.8	463.3	461.9	460.5	459.1	458.5	458.9	459.1	459.5	459.8
150°	473.5	473.0	471.6	470.3	469.0	467.5	467.2	467.8	468.3	469.0	469.6
152.5°	481.1	480.6	479.3	478.0	476.7	475.5	475.1	475.8	476.4	477.2	477.8
155°	491.4	490.9	489.9	488.8	487.9	486.9	486.7	487.5	488.2	489.0	489.7
157.5°	500.0	499.4	498.7	498.0	497.3	496.6	496.6	497.2	497.8	498.5	499.1
160°	505.2	504.6	504.1	503.6	503.1	502.6	502.6	503.1	503.6	504.1	504.6
162.5°	509.8	509.2	508.7	508.3	507.8	507.5	507.5	508.0	508.5	509.0	509.5
165°	515.5	514.9	514.7	514.4	514.2	513.9	514.0	514.5	515.1	515.6	516.0
167.5°	520.3	519.7	519.5	519.2	519.0	518.8	518.9	519.4	520.0	520.4	520.9
170°	522.7	522.2	522.0	521.8	521.7	521.5	521.7	522.2	522.6	523.2	523.7
172.5°	524.6	524.0	523.8	523.6	523.4	523.3	523.4	524.0	524.5	525.0	525.5
175°	526.6	525.9	525.8	525.7	525.5	525.3	525.5	526.1	526.6	527.3	527.9
177.5°	526.9	526.4	526.4	526.3	526.2	526.1	526.4	526.8	527.3	527.8	528.2
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331845-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	1978.1	1979.7	1990.7	1995.6	2005.5	2009.2	2013.7	2012.5	2012.5	2014.7	2030.0
5°	1982.4	1996.0	2016.5	2036.3	2055.5	2071.8	2082.8	2093.7	2097.8	2117.6	2135.4
7.5°	1975.2	2000.4	2034.3	2064.5	2100.7	2129.0	2152.5	2173.6	2188.2	2217.0	2246.5
10°	1966.0	2001.4	2039.7	2078.7	2128.5	2166.1	2204.4	2233.8	2243.4	2286.4	2311.0
12.5°	1947.3	1994.9	2043.5	2094.0	2142.8	2194.6	2236.7	2266.0	2299.6	2338.3	2383.7
15°	1919.5	1974.2	2037.6	2102.6	2172.3	2235.2	2280.3	2331.5	2368.4	2410.7	2450.4
17.5°	1879.5	1949.8	2030.6	2105.8	2186.4	2253.9	2316.0	2365.1	2391.1	2415.3	2421.2
20°	1847.7	1923.6	2018.6	2107.4	2188.0	2265.9	2327.4	2368.4	2375.3	2375.9	2339.7
22.5°	1813.3	1899.0	1998.3	2089.4	2185.9	2272.4	2320.3	2337.8	2310.7	2264.4	2194.3
25°	1750.0	1849.1	1964.5	2068.4	2173.6	2255.7	2272.1	2241.3	2146.3	2046.6	1920.1
27.5°	1681.4	1792.8	1916.6	2032.0	2144.1	2194.9	2159.5	2048.7	1877.7	1728.9	1548.7
30°	1631.1	1756.1	1877.8	2006.9	2110.8	2132.6	2051.4	1888.0	1688.5	1464.4	1284.7
32.5°	1573.7	1704.8	1838.4	1971.9	2058.9	2037.6	1903.2	1702.2	1468.2	1247.9	1078.0
35°	1491.7	1627.0	1771.2	1905.1	1960.4	1868.2	1667.3	1405.6	1166.4	960.7	843.9
37.5°	1397.0	1544.4	1694.3	1817.2	1813.3	1659.6	1385.9	1115.7	914.7	793.1	709.8
40°	1329.7	1478.7	1640.7	1744.5	1700.1	1499.9	1203.4	948.4	801.6	704.5	643.7
42.5°	1265.2	1414.8	1575.7	1658.1	1580.9	1334.8	1039.4	839.6	718.5	642.7	593.4
45°	1155.5	1313.3	1462.3	1508.1	1370.0	1098.8	840.5	695.6	615.0	558.9	524.8
47.5°	1048.2	1203.5	1339.4	1340.2	1153.6	891.1	709.0	602.0	533.2	489.8	464.9
50°	982.6	1130.2	1244.3	1226.5	1014.8	792.6	634.1	541.9	484.5	451.0	425.0
52.5°	908.8	1052.0	1150.8	1100.3	897.2	697.5	566.9	489.4	441.8	412.7	389.5
55°	801.6	928.6	998.4	921.8	731.8	580.1	479.0	418.2	382.6	358.0	338.2
57.5°	696.2	801.0	844.9	755.7	602.8	481.1	405.2	359.5	324.3	306.7	296.4
60°	630.0	719.5	750.3	651.9	524.1	420.9	358.7	316.4	290.4	278.8	268.6
62.5°	565.0	638.1	650.8	560.6	456.9	368.5	315.0	279.2	262.0	250.9	241.2
65°	468.8	521.4	515.2	442.8	361.5	292.5	253.5	231.7	218.6	203.0	185.8
67.5°	385.9	418.0	398.7	344.4	275.9	227.3	201.9	185.3	169.2	154.3	150.3
70°	333.5	351.9	331.4	281.5	226.1	190.6	170.1	150.3	140.8	137.3	131.2
72.5°	283.2	289.6	267.4	224.7	184.0	157.8	137.9	126.8	121.6	118.8	114.8
75°	212.5	207.8	188.6	155.2	127.8	110.0	103.9	99.8	96.3	93.6	91.6
77.5°	149.3	142.2	125.2	103.3	89.0	80.5	76.8	74.6	72.9	71.6	69.6
80°	112.1	107.3	90.2	73.8	67.7	63.6	61.5	58.8	58.8	57.4	55.4
82.5°	82.0	76.7	61.8	54.1	50.7	48.2	46.7	45.1	44.6	44.9	43.3
85°	43.1	34.9	30.8	29.4	27.4	25.9	26.7	25.3	25.3	25.3	24.6
87.5°	13.4	10.9	10.4	10.1	10.8	11.0	10.5	10.7	11.3	10.9	11.5
90°	1.3	2.2	3.2	4.1	4.9	5.6	6.2	7.0	7.6	8.0	8.5
92.5°	7.6	7.5	7.4	7.4	7.5	7.8	8.2	8.5	8.8	9.1	9.3
95°	21.9	19.2	16.4	13.6	12.5	13.1	13.6	14.3	14.9	15.2	15.7
97.5°	41.3	33.4	25.5	17.7	14.4	15.8	17.1	18.5	19.9	20.2	20.6
100°	55.8	44.2	32.6	21.0	16.0	17.4	18.8	20.2	21.8	22.4	23.1
102.5°	85.2	82.7	80.3	77.8	70.5	58.5	46.5	34.4	22.3	23.2	24.1
105°	118.4	120.9	123.5	126.0	115.7	92.6	69.5	46.4	23.3	24.2	25.1
107.5°	150.2	152.2	154.3	156.3	143.5	115.7	88.0	60.3	32.5	31.6	30.7
110°	170.6	172.4	174.2	175.9	164.6	140.1	115.7	91.1	66.7	58.2	49.8



TEST NUMBER: P331845-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	189.9	191.5	193.1	194.7	192.4	186.4	180.3	174.2	168.3	137.3	106.5
115°	220.6	222.0	223.5	224.9	226.7	228.8	231.0	233.0	235.1	195.9	156.8
117.5°	248.3	249.9	251.5	253.1	254.7	256.1	257.5	259.0	260.5	251.0	241.5
120°	268.0	269.3	270.6	271.9	273.3	274.8	276.3	277.9	279.4	280.4	281.4
122.5°	285.2	286.5	287.8	289.2	290.7	292.4	294.0	295.7	297.4	298.0	298.5
125°	310.9	312.1	313.2	314.2	315.6	317.3	318.9	320.5	322.1	322.6	323.2
127.5°	334.7	335.8	337.1	338.3	339.5	340.7	341.9	343.1	344.3	345.2	346.1
130°	349.7	351.1	352.4	353.7	354.9	355.9	356.8	357.8	358.6	359.5	360.5
132.5°	364.7	365.9	367.0	368.2	369.3	370.1	371.1	372.0	373.0	373.8	374.6
135°	384.8	386.1	387.4	388.9	389.9	390.7	391.5	392.2	393.0	393.8	394.7
137.5°	404.4	405.4	406.4	407.2	408.1	409.0	409.9	410.7	411.6	412.4	413.3
140°	417.2	417.9	418.6	419.3	420.1	421.1	422.0	422.8	423.8	424.5	425.3
142.5°	428.2	428.7	429.4	430.0	430.9	431.9	432.9	434.0	435.1	435.8	436.5
145°	444.7	444.6	444.5	444.4	445.1	446.6	448.0	449.4	450.8	451.5	452.1
147.5°	459.5	459.1	458.9	458.5	459.1	460.5	461.9	463.3	464.8	465.2	465.7
150°	469.0	468.3	467.8	467.2	467.5	469.0	470.3	471.6	473.0	473.5	474.0
152.5°	477.2	476.4	475.8	475.1	475.5	476.7	478.0	479.3	480.6	481.1	481.6
155°	489.0	488.2	487.5	486.7	486.9	487.9	488.8	489.9	490.9	491.4	492.0
157.5°	498.5	497.8	497.2	496.6	496.6	497.3	498.0	498.7	499.4	500.0	500.6
160°	504.1	503.6	503.1	502.6	502.6	503.1	503.6	504.1	504.6	505.2	505.6
162.5°	509.0	508.5	508.0	507.5	507.5	507.8	508.3	508.7	509.2	509.8	510.3
165°	515.6	515.1	514.5	514.0	513.9	514.2	514.4	514.7	514.9	515.5	516.1
167.5°	520.4	520.0	519.4	518.9	518.8	519.0	519.2	519.5	519.7	520.3	520.9
170°	523.2	522.6	522.2	521.7	521.5	521.7	521.8	522.0	522.2	522.7	523.3
172.5°	525.0	524.5	524.0	523.4	523.3	523.4	523.6	523.8	524.0	524.6	525.1
175°	527.3	526.6	526.1	525.5	525.3	525.5	525.7	525.8	525.9	526.6	527.2
177.5°	527.8	527.3	526.8	526.4	526.1	526.2	526.3	526.4	526.4	526.9	527.4
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331845-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	2035.5	2042.6	2045.9	2045.9	2049.7	2048.1	2046.4
5°	2152.5	2165.4	2168.2	2180.5	2189.3	2186.7	2188.0
7.5°	2268.8	2289.6	2310.3	2319.8	2321.2	2326.7	2328.8
10°	2340.4	2357.5	2389.6	2384.8	2408.7	2422.4	2399.9
12.5°	2409.2	2432.3	2454.6	2460.8	2474.3	2478.7	2469.8
15°	2471.6	2483.9	2485.3	2481.8	2485.9	2482.5	2469.5
17.5°	2413.3	2393.4	2353.0	2333.8	2318.6	2296.2	2287.2
20°	2317.1	2258.3	2190.0	2162.8	2130.6	2067.7	2082.8
22.5°	2109.4	2042.5	1974.2	1894.4	1856.2	1796.6	1793.1
25°	1786.2	1670.7	1543.6	1454.8	1402.8	1343.5	1317.4
27.5°	1388.8	1243.4	1139.2	1086.5	1038.5	991.4	989.4
30°	1127.5	1018.2	937.5	892.4	863.0	843.2	847.3
32.5°	950.4	875.5	821.1	783.6	761.9	747.0	746.7
35°	776.9	725.7	690.8	675.1	659.4	648.5	649.2
37.5°	664.9	634.1	614.7	597.4	587.5	582.2	579.2
40°	607.4	582.2	567.1	556.9	548.7	541.2	539.8
42.5°	562.1	541.2	526.2	518.1	510.4	505.2	503.7
45°	498.8	481.7	468.1	459.2	455.8	451.0	451.0
47.5°	443.7	427.0	416.3	410.7	404.8	401.6	401.5
50°	406.6	393.6	384.1	380.6	375.9	373.8	373.1
52.5°	373.3	363.6	356.7	354.4	352.3	349.7	350.2
55°	328.0	322.5	319.8	317.7	314.3	310.2	313.0
57.5°	289.9	285.3	277.9	271.4	268.3	265.4	266.5
60°	263.1	253.5	244.0	236.4	234.3	228.2	228.2
62.5°	229.2	215.8	204.0	199.8	197.8	194.9	194.3
65°	176.3	170.9	168.1	165.3	164.0	164.0	162.6
67.5°	146.1	143.9	140.9	140.2	138.8	138.5	138.0
70°	129.1	126.4	125.0	124.4	123.0	123.7	121.6
72.5°	112.7	110.6	110.3	108.5	107.7	107.8	106.3
75°	88.8	88.8	88.2	87.5	86.1	85.4	86.1
77.5°	68.3	68.5	67.2	67.1	67.0	67.1	66.4
80°	54.7	55.4	54.7	53.9	53.3	53.9	53.3
82.5°	43.2	42.3	42.1	42.0	41.8	41.4	41.3
85°	24.6	25.3	24.6	23.9	23.9	23.9	24.6
87.5°	11.1	11.1	11.2	11.2	11.3	11.3	10.8
90°	8.9	9.3	9.6	9.8	10.0	10.2	10.3
92.5°	9.5	9.7	9.9	10.0	10.1	10.2	10.3
95°	16.1	16.6	16.8	16.7	16.6	16.5	16.4
97.5°	21.0	21.2	21.5	21.6	21.7	21.8	21.8
100°	23.7	24.4	24.9	25.1	25.2	25.3	25.5
102.5°	25.0	25.9	26.4	26.7	26.9	27.1	27.4
105°	26.0	27.0	27.6	27.9	28.3	28.6	29.0
107.5°	29.7	28.7	28.4	28.8	29.2	29.4	29.8
110°	41.3	32.8	28.7	29.1	29.4	29.8	30.1



TEST NUMBER: P331845-940

CATALOG NUMBER: S122RDIW-S1005D435U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	75.5	44.7	29.3	29.6	29.9	30.1	30.4
115°	117.5	78.3	55.6	49.6	43.4	37.4	31.2
117.5°	232.0	222.5	207.8	187.7	167.6	147.7	127.6
120°	282.4	283.5	278.2	266.8	255.4	243.9	232.5
122.5°	299.2	299.8	299.0	296.8	294.5	292.3	290.1
125°	323.9	324.4	324.9	325.1	325.4	325.7	325.8
127.5°	346.9	347.8	348.2	348.3	348.3	348.4	348.4
130°	361.4	362.4	362.8	362.7	362.7	362.6	362.5
132.5°	375.3	376.1	376.5	376.4	376.3	376.3	376.2
135°	395.5	396.4	396.6	396.5	396.4	396.2	396.0
137.5°	414.1	414.9	415.2	414.9	414.6	414.4	414.0
140°	426.1	426.9	427.0	426.6	426.1	425.8	425.3
142.5°	437.2	437.9	438.0	437.6	437.2	436.8	436.3
145°	452.6	453.3	453.3	452.9	452.5	452.1	451.7
147.5°	466.1	466.5	466.5	466.2	465.8	465.5	465.1
150°	474.5	475.0	475.1	474.7	474.2	473.8	473.4
152.5°	482.1	482.7	482.6	482.1	481.5	480.9	480.4
155°	492.4	492.9	492.8	492.1	491.5	490.8	490.2
157.5°	501.1	501.8	501.7	501.1	500.3	499.7	499.1
160°	506.1	506.7	506.6	506.0	505.4	504.8	504.3
162.5°	511.0	511.5	511.4	510.7	510.0	509.3	508.5
165°	516.7	517.3	517.3	516.7	516.1	515.5	514.9
167.5°	521.5	522.1	522.0	521.2	520.5	519.7	519.0
170°	524.0	524.5	524.4	523.7	522.9	522.2	521.4
172.5°	525.8	526.4	526.3	525.5	524.8	524.0	523.3
175°	527.7	528.3	528.2	527.4	526.6	525.7	524.9
177.5°	527.8	528.3	528.2	527.6	527.0	526.4	525.8
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7

(END OF REPORT)