

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331517-935

Luminaire Tested: **S122DIW-S485D1240U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331517-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D1240U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5970.6 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331517-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331517-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	29
1	93	89	85	82	83	80	76	74	62	60	58	47	45	44	32	31	31	24
2	85	77	72	67	75	70	65	60	55	51	48	41	39	37	28	27	26	20
3	77	68	61	55	69	61	55	50	48	44	41	36	33	31	25	23	22	17
4	70	60	52	47	63	54	48	43	43	38	34	32	29	27	22	20	19	15
5	65	53	46	40	58	48	41	36	38	33	30	29	26	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	24	20	18	17	14	13	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10797	10797	10797
5°	10838	10682	10746
10°	10775	10575	10627
15°	10641	10437	10425
20°	10452	10232	10220
25°	10265	9978	9978
30°	10023	9747	9661
35°	9798	9469	9329
40°	9514	9190	9012
45°	9236	8912	8690
50°	8932	8626	8317
55°	8617	8290	7983
60°	8263	7892	7598
65°	7885	7492	7148
70°	7407	7010	6680
75°	6744	6457	6301
80°	5979	5793	5504
85°	4872	4650	4168



TEST NUMBER: P331517-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.9	1.1
10°-20°	176.9	3.0
20°-30°	260.1	4.4
30°-40°	302.1	5.1
40°-50°	301.8	5.1
50°-60°	263.2	4.4
60°-70°	194.6	3.3
70°-80°	110.2	1.8
80°-90°	33.2	0.6
90°-100°	48.6	0.8
100°-110°	178.1	3.0
110°-120°	476.0	8.0
120°-130°	785.7	13.2
130°-140°	835.5	14.0
140°-150°	776.6	13.0
150°-160°	624.4	10.5
160°-170°	402.3	6.7
170°-180°	138.5	2.3
0°-30°	499.9	8.4
0°-40°	802.0	13.4
0°-60°	1366.9	22.9
0°-90°	1705.0	28.6
90°-120°	702.6	11.8
90°-150°	3100.4	51.9
90°-180°	4266.0	71.5
0°-180°	5970.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	669	669	669	669	669	
5°	669	666	659	664	663	63
15°	637	632	624	627	624	179
25°	576	571	560	561	560	265
35°	497	490	480	476	473	310
45°	404	400	390	384	381	312
55°	306	302	294	287	284	274
65°	206	202	196	190	187	204
75°	108	107	104	100	101	115
85°	26	26	25	23	22	30
90°	1	12	21	26	28	4
95°	68	36	41	46	45	84
105°	320	334	64	75	80	342
115°	606	624	650	185	86	596
125°	856	870	890	897	900	763
135°	1060	1076	1086	1096	1094	818
145°	1229	1229	1246	1253	1248	768
155°	1353	1345	1357	1362	1354	623
165°	1426	1420	1423	1429	1423	403
175°	1459	1452	1454	1460	1450	139
180°	1456	1456	1456	1456	1456	



TEST NUMBER: P331517-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7
2.5°	671.8	671.2	670.7	670.1	669.5	668.7	667.4	666.2	664.9	663.6	664.8
5°	668.7	668.1	667.6	667.0	666.5	665.4	663.8	662.3	660.6	659.1	660.2
7.5°	662.8	661.9	661.1	660.1	659.3	658.1	656.4	654.9	653.2	651.6	652.8
10°	657.2	656.2	655.1	654.2	653.2	651.8	650.1	648.4	646.7	645.0	646.1
12.5°	649.5	648.6	647.6	646.8	645.9	644.6	642.9	641.2	639.5	637.7	638.5
15°	636.6	635.8	634.9	634.0	633.2	631.8	629.9	628.1	626.2	624.4	624.9
17.5°	620.1	619.3	618.5	617.6	616.7	615.4	613.5	611.6	609.7	607.8	608.5
20°	608.3	607.4	606.6	605.7	604.9	603.5	601.4	599.4	597.4	595.5	595.9
22.5°	596.5	595.3	594.1	592.9	591.7	590.1	588.2	586.3	584.4	582.6	582.6
25°	576.2	575.0	573.9	572.7	571.6	569.8	567.4	564.9	562.5	560.1	560.3
27.5°	553.0	552.0	551.0	549.9	548.9	547.4	545.5	543.5	541.7	539.8	539.3
30°	537.6	536.4	535.3	534.2	533.0	531.3	529.2	527.1	525.0	522.8	522.4
32.5°	521.1	520.2	519.3	518.3	517.5	515.8	513.6	511.3	509.1	506.9	506.1
35°	497.1	495.6	494.2	492.8	491.4	489.5	487.2	484.9	482.6	480.4	479.5
37.5°	469.9	468.6	467.4	466.1	464.9	463.1	460.8	458.6	456.2	454.0	452.9
40°	451.4	450.2	449.1	448.0	446.9	445.1	442.8	440.6	438.2	436.0	434.7
42.5°	433.4	432.2	431.1	430.0	428.9	427.1	424.8	422.6	420.3	417.9	416.6
45°	404.5	403.5	402.4	401.5	400.5	398.9	396.7	394.6	392.4	390.3	388.7
47.5°	375.7	374.7	373.8	372.8	371.9	370.3	368.1	365.8	363.6	361.4	359.7
50°	355.6	354.9	354.1	353.4	352.8	351.4	349.4	347.4	345.3	343.4	341.4
52.5°	336.0	335.1	334.2	333.2	332.3	330.9	329.0	327.1	325.2	323.3	321.7
55°	306.1	305.2	304.4	303.5	302.6	301.4	299.6	297.9	296.2	294.5	292.8
57.5°	276.0	275.3	274.6	274.0	273.3	272.0	270.1	268.2	266.3	264.4	262.7
60°	255.9	255.4	254.8	254.2	253.7	252.4	250.4	248.3	246.3	244.4	242.8
62.5°	236.3	235.5	234.5	233.6	232.7	231.5	230.0	228.4	226.9	225.3	223.9
65°	206.4	205.5	204.7	203.8	203.0	201.8	200.4	199.0	197.5	196.1	194.8
67.5°	175.9	175.2	174.5	173.8	173.1	172.2	170.9	169.6	168.3	167.0	166.1
70°	156.9	156.4	155.8	155.2	154.6	153.7	152.4	151.1	149.8	148.5	147.6
72.5°	137.3	136.8	136.2	135.6	135.1	134.4	133.5	132.7	131.9	131.0	130.0
75°	108.1	107.7	107.5	107.2	106.9	106.4	105.6	105.0	104.3	103.5	102.6
77.5°	81.8	81.3	80.8	80.3	79.8	79.5	79.2	78.9	78.6	78.4	77.9
80°	64.3	64.1	64.1	63.9	63.7	63.5	63.2	62.9	62.7	62.3	61.9
82.5°	47.9	47.8	47.8	47.8	47.7	47.6	47.4	47.3	47.1	46.9	46.4
85°	26.3	26.3	26.1	25.9	25.8	25.7	25.5	25.4	25.2	25.1	24.6
87.5°	9.5	9.7	10.1	10.3	10.6	10.8	10.9	11.1	11.3	11.5	11.3
90°	1.0	3.6	6.2	8.8	11.4	13.6	15.4	17.3	19.2	21.1	22.2
92.5°	21.3	21.0	20.8	20.6	20.3	20.7	21.6	22.6	23.5	24.5	25.1
95°	68.4	60.7	53.0	45.3	37.5	34.5	36.2	37.8	39.4	41.1	42.3
97.5°	135.9	114.1	92.3	70.6	48.8	39.8	43.6	47.4	51.2	55.0	55.9
100°	186.4	154.4	122.3	90.2	58.2	44.1	48.1	52.1	56.1	60.0	61.9
102.5°	242.0	235.2	228.4	221.7	214.9	194.8	161.5	128.3	95.0	61.7	64.1
105°	320.2	327.2	334.2	341.2	348.3	319.9	256.0	192.0	128.1	64.2	66.8
107.5°	409.3	414.9	420.6	426.3	432.0	396.5	319.9	243.2	166.6	90.0	87.3
110°	466.6	471.5	476.4	481.3	486.2	454.9	387.3	319.6	251.9	184.3	160.9



TEST NUMBER: P331517-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	520.5	524.9	529.2	533.6	538.0	531.8	515.1	498.3	481.6	464.9	379.5
115°	605.6	609.6	613.5	617.5	621.6	626.5	632.3	638.2	644.0	649.9	541.5
117.5°	681.7	686.1	690.5	695.0	699.5	703.7	707.7	711.7	715.7	719.8	693.5
120°	737.3	740.8	744.2	747.8	751.3	755.2	759.4	763.6	767.8	772.0	774.8
122.5°	784.5	788.2	791.9	795.6	799.3	803.4	808.0	812.5	817.2	821.7	823.4
125°	856.3	859.3	862.4	865.4	868.4	872.2	876.7	881.1	885.5	890.0	891.7
127.5°	921.4	924.7	928.1	931.5	934.9	938.2	941.5	944.9	948.1	951.5	953.9
130°	962.7	966.4	970.2	973.9	977.7	980.8	983.3	985.9	988.5	991.1	993.7
132.5°	1004.8	1008.0	1011.2	1014.3	1017.5	1020.4	1023.0	1025.5	1028.1	1030.7	1032.9
135°	1059.5	1063.2	1067.0	1070.7	1074.5	1077.5	1079.5	1081.7	1083.7	1085.9	1088.2
137.5°	1114.9	1117.6	1120.2	1122.8	1125.4	1127.9	1130.3	1132.7	1135.1	1137.5	1139.8
140°	1151.2	1153.1	1154.9	1156.8	1158.6	1160.9	1163.5	1166.1	1168.6	1171.2	1173.3
142.5°	1181.6	1183.2	1184.9	1186.5	1188.3	1190.6	1193.5	1196.4	1199.4	1202.4	1204.3
145°	1229.1	1228.9	1228.6	1228.4	1228.2	1230.0	1234.1	1238.0	1242.0	1246.0	1247.6
147.5°	1270.6	1269.7	1268.9	1267.9	1267.0	1268.6	1272.5	1276.4	1280.4	1284.3	1285.6
150°	1297.6	1296.0	1294.3	1292.6	1291.0	1292.1	1295.8	1299.6	1303.3	1307.1	1308.5
152.5°	1320.3	1318.5	1316.6	1314.8	1313.0	1313.9	1317.4	1321.0	1324.6	1328.1	1329.6
155°	1353.4	1351.3	1349.2	1347.0	1345.0	1345.3	1348.2	1350.9	1353.8	1356.6	1358.0
157.5°	1379.3	1377.5	1375.7	1374.0	1372.2	1372.3	1374.2	1376.2	1378.2	1380.2	1381.7
160°	1394.5	1393.1	1391.6	1390.3	1388.9	1388.9	1390.3	1391.6	1393.1	1394.5	1395.9
162.5°	1408.0	1406.5	1405.2	1403.8	1402.3	1402.2	1403.4	1404.6	1405.9	1407.1	1408.7
165°	1426.1	1424.7	1423.2	1421.9	1420.5	1420.1	1420.8	1421.5	1422.2	1422.9	1424.5
167.5°	1439.6	1438.1	1436.8	1435.4	1433.9	1433.6	1434.3	1434.9	1435.5	1436.1	1437.8
170°	1447.2	1445.7	1444.3	1442.9	1441.5	1441.1	1441.5	1442.0	1442.4	1442.9	1444.6
172.5°	1452.2	1450.8	1449.4	1447.9	1446.6	1446.1	1446.6	1447.0	1447.5	1447.9	1449.6
175°	1458.7	1457.1	1455.4	1453.8	1452.2	1451.6	1452.1	1452.5	1453.0	1453.5	1455.1
177.5°	1459.7	1458.4	1457.2	1455.9	1454.5	1454.0	1454.1	1454.3	1454.5	1454.7	1456.0
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331517-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7
2.5°	665.9	667.0	668.1	668.7	668.4	668.1	668.0	667.7
5°	661.4	662.5	663.7	664.1	663.8	663.5	663.2	663.0
7.5°	653.9	655.0	656.3	656.6	656.3	656.0	655.7	655.4
10°	647.2	648.4	649.5	649.9	649.5	649.0	648.6	648.2
12.5°	639.4	640.2	640.9	641.2	640.8	640.6	640.2	639.9
15°	625.5	626.1	626.6	626.5	625.9	625.2	624.5	623.7
17.5°	609.1	609.8	610.4	610.4	609.7	609.1	608.4	607.7
20°	596.3	596.8	597.2	597.1	596.5	595.9	595.4	594.8
22.5°	582.7	582.8	582.9	582.8	582.5	582.1	581.8	581.4
25°	560.7	560.9	561.2	561.2	560.9	560.7	560.3	560.1
27.5°	538.9	538.5	538.0	537.5	536.8	536.1	535.5	534.8
30°	521.9	521.5	521.1	520.6	520.0	519.4	518.8	518.2
32.5°	505.3	504.5	503.8	503.1	502.5	502.0	501.4	500.8
35°	478.6	477.8	476.9	476.1	475.4	474.7	474.0	473.3
37.5°	451.9	450.8	449.8	448.8	448.2	447.5	446.8	446.2
40°	433.4	432.1	430.8	429.9	429.3	428.8	428.2	427.6
42.5°	415.2	413.8	412.3	411.3	410.4	409.7	408.9	408.0
45°	387.2	385.6	384.0	383.0	382.4	381.9	381.3	380.6
47.5°	358.1	356.4	354.7	353.5	352.7	351.9	351.0	350.2
50°	339.4	337.3	335.4	334.0	333.3	332.6	331.8	331.1
52.5°	320.0	318.3	316.7	315.4	314.4	313.5	312.5	311.6
55°	291.1	289.4	287.7	286.5	285.7	285.0	284.3	283.6
57.5°	261.1	259.3	257.7	256.6	256.0	255.5	254.9	254.3
60°	241.2	239.6	238.1	237.0	236.6	236.2	235.7	235.3
62.5°	222.4	220.9	219.5	218.5	217.9	217.4	216.9	216.3
65°	193.6	192.3	191.0	189.9	189.2	188.6	187.9	187.1
67.5°	165.1	164.0	163.1	162.3	161.7	161.1	160.6	160.0
70°	146.5	145.5	144.6	143.8	143.2	142.6	142.1	141.5
72.5°	129.1	128.0	127.1	126.3	125.9	125.4	124.9	124.5
75°	101.8	101.0	100.1	99.8	100.1	100.4	100.7	101.0
77.5°	77.5	77.1	76.6	76.2	75.8	75.4	75.0	74.6
80°	61.5	61.0	60.7	60.3	60.0	59.8	59.4	59.2
82.5°	45.9	45.3	44.8	44.4	44.4	44.3	44.3	44.3
85°	24.2	23.8	23.3	23.1	22.9	22.8	22.6	22.5
87.5°	11.2	11.1	11.0	10.9	10.9	10.8	10.8	10.8
90°	23.4	24.5	25.7	26.6	27.0	27.5	28.0	28.4
92.5°	25.7	26.3	26.9	27.3	27.6	27.9	28.2	28.4
95°	43.4	44.6	45.7	46.2	46.0	45.7	45.5	45.3
97.5°	56.8	57.8	58.7	59.3	59.6	59.9	60.2	60.4
100°	63.8	65.6	67.5	68.7	69.1	69.7	70.1	70.6
102.5°	66.6	69.1	71.5	73.0	73.6	74.3	75.0	75.6
105°	69.4	72.0	74.6	76.3	77.2	78.2	79.1	80.1
107.5°	84.7	82.1	79.5	78.6	79.6	80.5	81.5	82.4
110°	137.5	114.1	90.7	79.5	80.4	81.4	82.3	83.2



TEST NUMBER: P331517-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	294.1	208.8	123.4	81.0	81.8	82.6	83.3	84.0
115°	433.1	324.8	216.4	153.8	136.9	120.1	103.2	86.4
117.5°	667.4	641.1	614.9	574.1	518.8	463.4	408.0	352.6
120°	777.7	780.4	783.3	768.9	737.3	705.7	674.1	642.5
122.5°	825.1	826.8	828.5	826.2	820.1	814.0	807.9	801.7
125°	893.3	894.9	896.6	897.7	898.4	899.1	899.8	900.5
127.5°	956.2	958.6	961.0	962.3	962.4	962.6	962.7	962.9
130°	996.3	998.8	1001.3	1002.5	1002.3	1002.1	1001.9	1001.6
132.5°	1035.1	1037.2	1039.5	1040.4	1040.3	1040.0	1039.7	1039.6
135°	1090.5	1092.9	1095.3	1096.1	1095.7	1095.3	1094.8	1094.3
137.5°	1142.0	1144.4	1146.7	1147.4	1146.6	1145.8	1145.0	1144.2
140°	1175.4	1177.5	1179.7	1180.1	1178.9	1177.8	1176.6	1175.4
142.5°	1206.2	1208.2	1210.0	1210.4	1209.3	1208.1	1206.9	1205.7
145°	1249.2	1250.9	1252.5	1252.8	1251.5	1250.4	1249.2	1248.1
147.5°	1286.8	1288.0	1289.2	1289.3	1288.3	1287.3	1286.3	1285.4
150°	1309.8	1311.3	1312.7	1312.8	1311.6	1310.4	1309.2	1308.1
152.5°	1330.9	1332.3	1333.8	1333.7	1332.1	1330.6	1329.0	1327.5
155°	1359.3	1360.8	1362.2	1361.9	1360.0	1358.2	1356.3	1354.4
157.5°	1383.4	1384.9	1386.6	1386.4	1384.6	1382.8	1381.0	1379.1
160°	1397.3	1398.7	1400.1	1400.0	1398.4	1396.7	1395.1	1393.4
162.5°	1410.3	1411.9	1413.5	1413.2	1411.3	1409.2	1407.2	1405.2
165°	1426.2	1427.8	1429.4	1429.4	1427.8	1426.2	1424.5	1422.9
167.5°	1439.4	1441.1	1442.7	1442.5	1440.4	1438.3	1436.1	1434.1
170°	1446.2	1447.9	1449.5	1449.2	1447.2	1445.0	1442.9	1440.8
172.5°	1451.2	1452.9	1454.5	1454.3	1452.2	1450.1	1447.9	1445.9
175°	1456.7	1458.4	1460.0	1459.7	1457.3	1455.0	1452.6	1450.3
177.5°	1457.3	1458.6	1460.0	1459.7	1458.1	1456.4	1454.7	1453.0
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5

(END OF REPORT)